



ENGLISH

Datasheet

Stock No: 487-277

RS Pro 2m power cord, C13 to C14 (IEC), 10 A, 250 V



Product Details

C13/14 Mains Lead

Brought to you under the trusted RS Brand, this IEC mains leads consists of a 3-pin C13 to C14 shrouded plug and socket connector on either end of 3-core BASEC approved cable. These mains leads are rated at 250 V ac, 10A maximum, and feature black PVC mouldings and cable sheath.

This C13 to C14 power cord is ideal to use as an extension lead, and commonly used in office floor planning and stage management.

This C13 to C14 power cord is ideal to use as an extension lead, and commonly used in office floor planning and stage management.

Features and Benefits:







- Suitable for appliances with protection class I according To IEC 61140
- Female C13 to Male C14 plugs
- Rated at 250 Vac, 10 A maximum
- Kite mark licence No. 6745

Available in this Range:

- Stock No. 116-3095 is a C13 to C14 power cord, 1.8m
- Stock No. 487-277 is a C13 to C14 power cord, 2m
- Stock No. 286-2610 is a right angle C13 to right angle C14 power cord, 2m
- Stock No. 870-2215 is a C13 to C14 power cord, 1m

Approvals

BEAB

	C3	C4		C13	C14
	C5	C6		C15	C16
	C7	C8		C19	C20

Specifications:

Connector A	C13
Connector B	C14
Length	2m
Current Rating	10 A
Voltage Rating	250 V
Connector A Type	IEC
Connector B Type	IEC
Connector A Gender	Female
Connector B Angle	Straight
Connector A Angle	Straight
Connector B Gender	Male