




SURGE SUPPRESSOR, RC COUPLING,
AC 24...48V, DC 24...70V,
FOR MOTOR CONTACTORS SZ S0,

General technical data:

product brand name		SIRIUS
product designation		surge suppressor
Size of the contactor		S0
Design of the surge suppressor		with RC elements
Ambient temperature		
• during storage	°C	-40 ... +80
• during operating	°C	-25 ... +60

Control circuit:

Type of voltage / of the controlled supply voltage		AC/DC
Control supply voltage frequency		
• 1 / rated value	Hz	50
• 2 / rated value	Hz	60
Control supply voltage / 1		
• for DC		
• initial rated value	V	24
• final rated value	V	70
• at 50 Hz / for AC		
• initial rated value	V	24
• final rated value	V	48

- at 60 Hz / for AC
- final rated value
- initial rated value

V	48
V	24

Installation/mounting/dimensions:

mounting position		any
Type of mounting		clip-on
Width	mm	30
Height	mm	19
Depth	mm	12

Certificates/approvals:

Verification of suitability	CE / UL / CSA / CCC	
General Product Approval	Declaration of Conformity	Test Certificates
 CSA  GOST  UL  EG-Konf.	Special Test Certificate	

Shipping Approval



Shipping Approval other



Further information:

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<http://www.siemens.com/industrial-controls/mall>

CAX-Online-Generator




<http://www.siemens.com/cax>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/3RT2926-1CB00/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3RT2926-1CB00



last change:

Jun 22, 2012