



Ty-Rap®

TY54SM

Premium cable tie with stainless steel locking barb - cable tie for panel mounting (pushmount). Fastening and panel mounting in one.

T&B Catalog Number: TY54SM
EAN Number: 05414363066606
UPC Number: 78621061308
Description: Premium, panel mounting cable tie, 150 x 3.5 mm, natural Polyamide 6.6



**BUREAU
VERITAS**

Technical Information

Type	panel mounting
Material	Polyamide 6.6
Material Locking Barb	316 grade stainless steel
Temperature Range	-40°C to +85°C
Flammability Rating	UL 94 V-2
Colour	natural
Halogen free	yes
Silicone free	yes

Approvals

Other approval	BVQ
----------------	-----

Ordering Information

Length (mm)	150
Width (mm)	3.5
Thickness (mm)	1
Max. Bundle Diameter (mm)	32
Min. Bundle Diameter (mm)	2
Min. Tensile Strength (N)	130
Diameter of Mounting Hole (mm)	4.5 - 5.2
Panel Thickness from ... to (mm)	0.1 - 2.5
Quantity (pieces)	1000
Packaging Type	bag

Storage Conditions

Nylon (Polyamide) is inherently susceptible to environmental conditions. Polyamide 6.6 cable ties are moisturised to optimum performance levels at machine-side and should be stored in cool dry areas out of direct sunlight. Cable ties are packaged in plastic bags to contain moisture and should remain sealed until ready for use.

Tooling

ERG50, WT193A
