



ENGLISH

## Datasheet

Stock No: 235-843

# RS Pro Xenon Beacon, Flashing, Surface Mount, 115 V ac



## Product Details

### Xenon Beacons, Single/Double Flash

Weatherproof and dustproof to IP56 these beacons offer high quality solutions for industrial environments and process applications.



ENGLISH

Nominal flash output of 5J  
Optional single or double flash  
Approximately 80 flash per minute  
High protection rating of IP56  
Optional cage guard available  
Surge protection for safety against peak voltage  
Full internal suppression for maximum interference reduction  
Operating temperature range: -30°C to +50°C  
166mm diameter  
Three point mounting

**Note**

Lens must be purchased separately

**Supplied with**

Bulb

**Specifications:**

Supply Voltage	115 V ac
Light Effect	Flashing
Lens Colour	Lens Not Included
Mounting Style	Surface Mount
Bulb Type	Xenon
Current Type	AC
Base Diameter	166mm
Housing Colour	Black
Lamp Included	Yes
Series	V10993
Height	207mm
Maximum Temperature	+50°C
Minimum Temperature	-30°C