

Datasheet

## RS Pro Electrolytic Scale Inhibitor, 3L/s

RS Stock No: **738-2693**



### Product Details

RS Pro electrolytic scale inhibitor maintains the flow rate up to 3 L/s. It is plugged into the main electrical 230 V supply to draw power to the main control unit where it is passed through a 12 V transformer and out to the aerial wires, wound around the pipework. This electronic scale inhibitor fits on hot and cold water pipes in horizontally, vertically or diagonal orientation without any plumbing. It is suitable for PVC, copper, lead and iron pipework.

### Features and Benefits

- 2 x 2 m lengths of single cable fixed (antennae aerials)
- 4 screws (to mount the unit to a suitable fixture)
- 4 Cable ties (to secure signal cable when coiled)
- Fits on hot and cold water pipes, horizontally, vertically or diagonal no plumbing required
- Prevents any further build up of hard scale



ENGLISH

### Specifications:

Scale Prevention Mechanism	Electrolytic
Maximum Flow Rate	3 L/s
Finish	Nickel Plated
Length	100 mm
Material	PP