

## Fluke 312 Clamp Meter



- Digital display: 3-3/4 digits with maximum reading of 3999
- Analog Display: Fast 42-segment analog bar graph display
- Overload: Display OL when input signal; exceeds measuring limit in 40A, 400A resistance and continuity function
- Sample Rate: 2 times/Sec, 20 times for digital bar graph
- Low battery indication: display battery icon when below its required voltage
- Power source: 9V battery
- Auto Power Off.
- Clamp Open Size:
  - 312- 36mm ( 1.42 inch)
  - Dimension ( L x W x H) 254 x 66 x 37mm
  - Weight 422g

### Specification:

- AC amp 40/400/1000A
- AC voltage 750V
- Resistance 400/4000 ohm
- Connectivity test <50 ohm
- DC voltage 1000V
- Diode test up to 2 V

### Content:

- 1 x clamp meter
- 1 x carrying case
- 1 x pairs of test lead
- 1 x English manual