

**MNX PCM 175/125 G**



Sample photo

**Order symbol:** PCM 175/125 G  
**Product nbr:** 6016322  
**Description:** Enclosure, PC  
**Remarks:** Grey cover

**EAN:** 6418074052254  
**EI. number:**  
 Finland: 3435228  
 Electric No. 8212027527  
 Denmark:  
 Electric No. Sweden: 2535340

Including: Base with metric knock-outs and TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:				Accessories:	
	Length	Width	Height		
<b>mm:</b>	180	180	125	MIN 15	DIN-15 Mounting rail
<b>inch:</b>	7.1	7.1	4.9	MIV 15	DIN-35 Mounting rail
<b>Materials:</b>				FP A 175/180	Front plate (Aluminium)
<b>Material:</b>	Polycarbonate			HFP 180	Front plate hinge series
<b>Base colour:</b>	RAL 7035 -light grey			FP 22046	Wall fastening lug (4 pcs)
<b>Cover screws material:</b>	Polyamide			<b>Rating:</b>	
<b>Cover colour:</b>	RAL 7035 -light grey			Ingress Protection (EN 60529): IP66/IP67	
<b>Cover screws colour:</b>	Grey			Impact Resistance (EN 62262): IK08	
<b>Gasket material:</b>	TPE			Electrical insulation: Totally insulated	
<b>Temperatures:</b>				Halogen free (DIN/VDE 0472, Part 815): 1	
<b>Temperature °C (short term):</b>	-40 ... 120 °C			UV resistance: UL 508	
<b>Temperature °C (continuous):</b>	-40 ... 80 °C			Flammability Rating: UL 746C 5V	
<b>Temperature °F (short term):</b>	-40 ... 250 °F			Glow Wire Test (IEC 695-2-1) °C: 960	
<b>Temperature °F (continuous):</b>	-40 ... 175 °F			NEMA Class: NEMA 1, 4, 4X, 6, 12, 13	
<b>Accessories:</b>				<b>Certificates:</b>	
MIV 175	Mounting plate (Galvanized steel)			Germanischer Lloyd (GL)	
				SGS Fimko	
				Gost R	

