

## Datasheet

Art.No. 92.050.1053.1

Distributor GST18i5V 2P1T V SW

T-connector GST18i5, 5 pole, 1 input and 2 outputs 5 pole, 250/400 V, 20 A, colour of coding: black



Art.No.	92.050.1053.1
EAN	4015573655058
Order unit	100 pieces

## Approvals



## Technical data

### General

Rated current	20 A
Rated voltage	400 V
Rated impulse voltage	4 kV
Pollution degree	2
Mechanical coding	Code 1
Interlockable	Yes
Color of coding/ contact carrier	Black
Marking of poles	

### Model

Number of poles	5
Number of inputs	1
Number of outputs	2
Type of fastening	No
Degree of protection (IP)	IP40
Type of distributor	T-distributor

### Material

Housing material	Polyamide
Halogen free	Yes
Contact material	CuZn
Insulation components continuous temperature	100 °C

Surface finish	Silver-plated
----------------	---------------

**Dimensions**

Length	44 mm
Width	47.7 mm
Height	43 mm

Drawings

Teile-Nr./part number	Farbe/colour	Typ/type
92.050.1053.0	weiß/white	GST1815V 2P1T V WS
92.050.1053.1	schwarz/black	GST1815V 2P1T V SW

Freioleranz nach DIN -		CAD - Zeichnung, keine manuellen Änderungen		1. Verwendung: -		Bl.: 1 von 1	
/	Maßstab	Werkstoff und Oberfläche:		2001	Tag	Name	Zeichnung Nr.
/	2:1			Entworfen	07.12.	Bayer F. 100	T 92.050.1053.0 01K
/				Geprüft	-	-	
/				Normspez.	-	-	Ersatz für: -
/				Benennung			
/				VERTEILER_T_FORM			
/				distribution rack T-form			
Technische Daten / Blatt		Änderung					