

Datasheet

RS Pro Standard DIN Rail Terminal, ZRK series, 4mm², 600 V, 35A, Spring Termination, Blue, Double Level

RS Stock No: **763-7488**



Product Details

RS Pro standard DIN rail terminal in blue colour, has a voltage rating of 600 V and current rating of 35 A. This double level, spring termination DIN rail terminal provides safe and quick connections for 4 mm² solid and stranded wires, with or without wire-end ferrules. The earth terminal features a PE foot contact that is snapped on, ensuring mechanical and electrical safety on both sides of the terminal without screws. The DIN rail terminal meets UL and CSA standards.

Features and Benefits

- This system provides safe and quick connections for solid and stranded wires, with or without wire-end ferrules.
- The earth terminals feature a PE foot contact that is snapped on, ensuring mechanical and electrical safety on both sides of the terminal without screws.
- Spring termination system

**Specifications:**

Cable CSA	4 mm ²
Colour	Blue
Current Rating	35 A
Maximum Operating Temperature	+120°C
Minimum Operating Temperature	-40°C
Number of Levels	Double
Termination Method	Spring
Voltage Rating	600 V
Wire Size	20 to 10 AWG
Clamping Area	0.08 to 6 mm
Dimensions	78.5 x 6.1 x 42 mm
Material	Nylon 66
Standards Met	UL, CSA