



ENGLISH

Datasheet

RS Pro 73 mm Hardal SUPRA (HDS) End Mill, 16mm Cut Length, 12mm Cut Diameter, 2 Flutes

RS Stock No: **736-9410**



Product Details

RS Pro 73 mm hardal SUPRA (HDS) end mill offers a new high performance alternative to conventional HSS and carbide endmill. This high speed alloy with a hardness of up to 70HRc guarantees an extremely stable cutting edge. The TiALN Black Panther coating gives the necessary resistance to heat and oxidation. This combination allows the HDS endmill to show excellent results even when run dry. It has 16 mm cut length and 12 mm cut diameter with 2 flutes.

Features and Benefits

- High tensile strength
- Very good wear resistance
- Suitable for dry cutting
- Extreme oxidation resistance
- Black Panther coating DN 630+



ENGLISH

Specifications:

Cut Length	16 mm
Cutter Diameter	12 mm
Material	Hardal SUPRA (HDS)
Number of Flutes	2
Overall Length	73 mm
Shank Diameter	12 mm
Shank Type	Weldon