

# Digital wireless monitoring set

Art. no. TVAC18000B

Page 1 of 2



- Complete set with recorder, 2 x wireless outdoor cameras, 3 x power supply units and accessories
- Simple step-by-step installation with app and QR code (iOS, Android)
- App access of up to 4 cameras
- Recording on max. 32 GB micro-SD card (accessory) or max. 2 TB external hard disk drive via USB port
- Up to three months of continuous recording with 500 GB external hard disk drive (accessory)
- Sturdy, weatherproof outdoor cameras (IP66)
- Professional integrated motion detection (PIR sensor) with alarm function
- VGA resolution and infrared night vision function
- Low network load thanks to compressed data transfer (H.264 compression)
- Integrated motion detection (PIR sensor)

Complete set with recorder, 2 x wireless outdoor cameras, 3 x power supply units and accessories

The compact digital wireless monitoring set from ABUS reliably protects small properties day and night: The VGA resolution makes for brilliant picture sharpness which is guaranteed even in darkness due to the integrated infrared night vision function. Sensitive motion detection identifies movement in the detection field of the camera and sets off an alarm in the event of unauthorised access. Using the app, you can access the video images of up to four cameras simultaneously and see if everything is okay.

Intuitive installation with app and QR code for iOS and Android

The wireless monitoring set is also installed using the app and a QR code. Even technical laymen can set up the video surveillance system quickly and easily. Since all components communicate wirelessly, the system can be installed with almost no mess.

Up to 3 months of continuous recording thanks to low network load

The efficient H.264 data compression reduces the data volume of the image data to a minimum, thereby enabling one to three months of continuous recording when connected to an external 500 GB hard disk drive. Recording is done either on a micro SD card or via a USB port on an external hard disk drive with a maximum of 2 TB. All storage media are available as accessories and can be integrated into the wireless monitoring set

# Digital wireless monitoring set

Art. no. TVAC18000B

Page 2 of 2

---

according to your preferences.

**Technical Data:**

Dimensions	20 x 20 x 5 mm
Resolution	640 x 480 Pixel
Recording modes	Schedule, motion detection, manual
Output	HDMI
Frequency	2.4 GHz
Wireless range	20 m

Network access	RJ45 (10/100 Mbps)
DC voltage supply	12 V
Storage medium	SD card, max. 32 GB, External hard disk, max. 2 TB
Power consumption	2000 mA
Transmission channels	4
Video compression	H.264