



### Main

Range	TeSys
Device short name	LA4K
Product or component type	Suppressor module
Product compatibility	LC1 LP1

### Complementary

Mounting location	Front side
Mounting mode	Clip-on
Suppressor technology	Varistor (peak limiting)
Control circuit voltage	12...24 V AC 12...24 V DC
Maximum peak voltage	2 Uc
Local signalling	LED
Quantity per set	Set of 5
Height	25 mm
Width	6 mm
Depth	22 mm
Product weight	0.01 kg

### Environment

Standards	BS 5424 IEC 60947 NF C 63-110 VDE 0660
Product certifications	CSA UL
IP degree of protection	IP2x conforming to VDE 0106
Protective treatment	TC conforming to IEC 60068 TC conforming to DIN 50016
Ambient air temperature for operation	-25...50 °C
Ambient air temperature for storage	-50...80 °C

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.