

Datasheet

Item No. 92.232.4000.1

Cable assembly GST18I3K1BS 15 40SW

Extension cable, female - male, length 4m, GST18i3, 3 pole, 250V/16A, cable type H05VV, cross section 1,5 mm², color of coding: black, color of cable: black



Item No.	92.232.4000.1
EAN	4015573326880
order unit	25 Piece(s)

Approvals



Technical data

General

Rated current	16 A
Rated voltage	250 V
Rated impulse voltage	4 kV
Pollution degree	2
Mechanical coding	Yes
Interlockable	Yes
Color of coding/ contact carrier	Black
Color of housing inclusive strain relief	Black

Model

Number of poles	3
Nominal cross section conductor	1.5 mm ²
Degree of protection (IP)	IP40
Cable type	H05VV-F
Cable colour	Black
Cable diameter	8.3 mm
Version of cable	Female - male

Material

Surface finish	Tin-plated
Halogen free	No
Continuous temperature of cable	70 °C
Insulation components continuous temperature	100 °C

Dimensions

