



Application Range

Robust watertight cable gland with conical sealing element for pumps and floater switches.

Technical Data

Material: Body: Nickel Plated Brass
 Seal: CR/NBR
 O Ring: NBR

Protection Rating: IP68

Temperature Range: -20°C to +80°C

Article List

RS Part Number	Description	Thread Size	Clamping Range (mm)	Spanner Wrench (mm)	Overall Length (mm)	Thread Length (mm)
4330923	Cable gland, metal	M12	3 – 4.8	14	26	5
4330939	Cable gland, metal	M16	4.5 – 6.8	18	26.5	7
2127696	Cable gland, metal	M25	15.8 – 17.8	30	28	13
2127719	Cable gland, metal	M32	21.8 – 23.8	30	29.5	13