

Specifications for BMP71 Label Printer Tags

Article No.	114731
Brady Material No.	B-109
Material Type	Polyethylene Tag
Colour	White
Finish	Matt
Order Reference	M71-12-109
Printable Area - Height (mm)	52.07
Printable Area - Width (mm)	17.78
Printer Compatibility	BMP71
Size - Height (mm)	76.20
Size - Width (mm)	19.05
Additional Information	Cross-laminated polyethylene provides extreme tear resistance and excellent cold-weather performance.
Thickness (mm)	0.216
Total Qty per Pack	100 Label(s) / Box
Vertical Repeat (mm)	76.20
Ribbon Series	M71-R4300
Application	Voice & Data Communication
Industry	Data & Telecommunications;Electrical
Description	Multi-purpose identification tag, where durability is required.
Max. Characters per Line	45
Max. Lines of Text	6
Max. Service Temp. °C	49
Min. Service Temp. °C	-40
# of Holes	4

Shape	Rectangle
Voice/Data Application	Communications Cables