



Feature-Packed Industrial Labeler with PC Connection

- Connects to PC via USB cable. Use Rhino Connect™ software to create labels on your PC and download them to the labeler for printing on site
- Meets all ANSI and TIA/EIA-606-B industry labeling standards
- Exclusive, one-touch “Hot Keys” automatically size, space and format label text for electrical and patch panels, terminal and 110 blocks, wire and cable flags, horizontal and vertical wraps, vertical and fixed-length applications including 5 line print capability
- Prints 6 bar code types including Code 39 and Code 128
- Symbol library includes more than 250 pre-programmed industry symbols, terms, fractions and punctuation marks
- Basic and advanced serial capabilities print single- and dual-character incremental labels
- Last-label memory and storage for up to 1000 of the labels you use most



Single Unit Includes:

- Rhino 6000 Label Printer
- 24mm x 5.5m White Vinyl Label Cartridge
- User Manual CD-ROM & Quick Reference Guide
- Rechargeable Battery Pack
- AC Adapter
- USB Cable



Kit Includes everything in single unit, plus:

- 9mm x 5.5m White Vinyl Tape Cartridge
- Carry Case
- Rhino Connect Software CD-ROM



Quick Specs

Unit Dimensions (H x W x L)	63 x 137 x 246mm
Weight (excluding battery)	1.8Kg
Mac®/PC Compatible	PC only
Accepts Label Sizes	6mm, 9mm, 12mm, 19mm, 24mm
Tape Platform	IND Rhino™
Resolution	180 dpi
Printing System	Thermal Transfer
Print Speed	10mm/sec
Barcodes	6
Cutter Type	Electronic
Batteries	6 AA (not included) or Rechargeable (included)
AC Adapter	Yes (included)
Country of Origin	China

Item Number	Description		Length (cm)	Width (cm)	Height (cm)	Weight (Kg)	QTY	EAN	Customer Price
S0773780	RHINO 6000 ABC UK	Unit	9.1	28.2	31.3	1.8	1	5411313001700	
		Shelf	-	-	-	-	-	-	
		Case	33.0	29.5	32.5	5.6	3	25411313001704	
		Pallet	120.0	80.0	112.5	159.4	108	-	
S0771940	RHINO 6000 Hard Case Kit	Unit	10.2	45.0	24.9	3.4	1	5411313226776	
		Shelf	-	-	-	-	-	-	
		Case	48.3	33.0	36.0	10.3	3	15411313226773	
		Pallet	120.0	80.0	87.0	107.5	54	-	
Accessories									
S0721430	RHINO AC Adapter	Unit	11.5	5.9	8.9	0.2	1	5411313400756	
S0899390	RHINO 6000 Rechargeable Battery	Unit	8.8	6.7	3.0	0.1	1	3501170899397	

IND Vinyl

Ideal for both indoor and outdoor applications. Available in the widest range of colors that meet OSHA, ANSI and ISO color standards.

- UL recognized component to UL 969
- RoHS compliant
- Temperature rating: -40°C to 80°C

IND Flexible Nylon

Specifically designed for curved surfaces and wire and cable marking.

- UL recognized component to UL 969
- RoHS compliant
- Temperature rating: -10°C to 80°C

IND Permanent Polyester

Professional, polished finish ideal for panels, blocks, faceplates, shelves, bins, beams and more.

- UL recognized component to UL 969
- RoHS compliant
- For flat surfaces only
- Temperature rating: -40°C to 150°C

IND Heat-Shrink Tube

For high-end cable identification. A 3:1 shrink ratio helps ensure a secure fit on wires and cables.

- Meets MIL-M-81531, MIL-STD-202G, SAE-DTL-23053/5 (Class 1 & 3)
- UL recognized as a component to UL 224
- RoHS compliant
- Temperature rating: -55°C to 135°C

IND Compatible Labels

Width	Length	A	A	A	A	A	A	A	A	A	A	A
IND VINYL												
9mm	5.5m	18443	-	-	-	-	-	1805437	-	-	-	-
12mm	5.5m	18444	-	18432	18435	1805413	1805416	1805435	1805414	1805243	1805415	1805412
19mm	5.5m	18445	-	18433	18436	1805419	1805422	1805436	1805420	1805417	1805421	1805418
24mm	5.5m	1805430	-	1805431	1805427	1805425	1805429	1805432	1805426	1805423	1805428	1805424
IND PERMANENT POLYESTER												
6mm	5.5m	1805442	1805440	-	-	1805441	-	-	-	-	-	-
9mm	5.5m	18482	18508DMO	-	-	18485	-	-	-	-	-	-
12mm	5.5m	18483	622289	-	-	18486	-	-	-	-	-	-
19mm	5.5m	18484	622290	-	-	18487	-	-	-	-	-	-
24mm	5.5m	1734523	1805433	-	-	1805434	-	-	-	-	-	-
IND FLEXIBLE NYLON												
12mm	3.5m	18488	-	18490	-	-	-	-	-	-	-	-
19mm	3.5m	18489	-	18491	-	-	-	-	-	-	-	-
24mm	3.5m	1734524	-	1734525	-	-	-	-	-	-	-	-
IND HEAT-SHRINK TUBE												
6mm	1.5m	18051	-	18052	-	-	-	-	-	-	-	-
9mm	1.5m	18053	-	18054	-	-	-	-	-	-	-	-
12mm	1.5m	18055	-	18056	-	-	-	-	-	-	-	-
19mm	1.5m	18057	-	18058	-	-	-	-	-	-	-	-
24mm	1.5m	1805443	-	1805444	-	-	-	-	-	-	-	-

Country of Origin: Belgium

DISTRIBUTED BY:
Newell Europe Sàrl
Chemin de Blandonnet 10
1214 Vernier – Switzerland
WWW.DYMO.COM

13-0103

INTERNAL USE ONLY. NOT FOR DISTRIBUTION.

This information is being provided for general information purposes and the compliance standards and certifications referenced herein are based on current standards which are subject to change.



A **Newell Rubbermaid** Brand

©2014 Newell Europe LLC

A NewellRubbermaid Company™	 RMZ Millennia Business Park Campus - 2, 5th Floor No. 143, Dr.M. G. R. Road Kandanchavadi Chennai 600 086 India T +91 44 4213 7777 www.schawk.com		 Cyan Magenta Yellow Black		Use the PANTONE MATCHING SYSTEM for accurate color reproduction	
	VERSION		JOB DESCRIPTION : NRM_EU_Writing_Dymo_1362812_EMEA Product Handbooks_UK Masters FILE NAME : DY_1362812_2014_EMEA_RH6000_TechSheet_v4.indd		BRAND : WRITING-DYMO	
	4 Date: 10-08-2014 Operator : VM		SCHAWK JOB # : 310253G NRM JOB # : 1362812 SAP / FG # : N/A COMPONENT # : N/A NO OF PAGES : 2		DIELINE : XXXXX UPC : XXXXX VENDOR : XXXXX	
	Note :					