This document was generated on 12/23/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 30700-1244

Status: Active

Overview: H-DAC 64™ Dual-Row High Density Automotive Connectors

Description: 2.54mm, 3.50mm Pitch, H-DAC 64™ Hybrid Female Harness Assembly, 24 Circuits, Polarization Option A without Bridge, Gray



Series image - Reference only

Documents:

- 3D Model
- Drawing (PDF)
- Product Specification PS-30968-024 (PDF)
- Product Specification PS-34646-001 (PDF)
- Application Specification AS-30700-000 (PDF)
- RoHS Certificate of Compliance (PDF)

General

Product Family	Crimp Housings
Series	30700
Application	Power, Wire-to-Wire
Comments	Polarization Option A
Overview	H-DAC 64™ Dual-Row High Density Automotive Connectors
Product Name	H-DAC 64™
UPC	822348688838

Physical

Circuits (maximum)	24
Color - Resin	Gray
Gender	Female
Glow-Wire Compliant	No
Lock to Mating Part	Yes
Material - Resin	High Performance Thermoplastic
Net Weight	13.050/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.54mm, 3.50mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40°C to +100°C

Electrical

Current - Maximum per Contact	7A

Material Info

Reference - Drawing Numbers

Application Specification	AS-30700-000
Product Specification	PS-30968-024, PS-34646-001
Sales Drawing	SD-30700-124

EU RoHS
ELV and RoHS Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen

China RoHS

Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, click here

Please visit the Contact Us section for any non-product compliance questions.

Search Parts in this Series
30700Series

Mates With
30700 Header, 30968 Crimp Housing

Use With
34230 Terminal

This document was generated on 12/23/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION