

Datasheet

Switchgear Cable

8114582
8114589
8114586
8114595
8114598



Image representative of range

Conductor: 126/0.40mm Plain Annealed Copper (Class 5 to IEC 60228)

Insulation: PVC (Type TI1 to BS EN 50363)

Insulation Radial Thickness: 1.00mm

Diameter Over Insulation: 9.00mm (Maximum)

Voltage Rating: 600/1000V

Conductor Resistance: 1.21 Ω /km @ 20°C (Nominal)

Cable Weight: 161.90 kg/km (Nominal)

Standard: BS 6231:2006