

Datasheet

RS Paging & Desktop Microphone, Unidirectional 1000 Ω

Stock Number: 360-3983



ELECTRONICAL SPECIFICATIONS:

- 3.1 Directional Characteristics : Uni-directional (Cardioid)
- 3.2 Element : Back Electret Condenser
- 3.3 Frequency : 80 Hz ~ 14,000 Hz
- 3.4 Impedance : 1,000 $\Omega \pm 30\%$ (at 1,000 Hz)
- 3.5 Sensitivity : -72 dB ± 3 dB (0 dB = 1 V/microbar,
1,000 Hz indicated by open circuit)
- 3.6 Operating Voltage : Battery; 1.5V D.C. (LR44)
- 3.7 Switch : On/Standby/Off, Slide Type

MECHANICAL SPECIFICATIONS:

4.1 Dimensions : $\varnothing 8\text{mm}$ (mic head) x 332mm (total length)

4.2 Weight : 171g

FREQUENCY RESPONSE CURVE:

