



Datasheet

RS PRO Coil Tube 8mm Diameter, 5m Long Clear Fluoropolymer 16 bar

Stock number: 486-8939

EN



Specifications

Attribute	Value
Manufacturer Series	1005T
Colour	Clear
Maximum Operating Length	5m
Tube Inside Diameter	6mm
Tube Outside Diameter	8mm
Material	Fluoropolymer
Maximum Operating Pressure	16 bar
Maximum Operating Temperature	+150°C
Minimum Operating Temperature	-40°C
Special Features	High Abrasion Resistance, PTFE Tubing with High Resistance to Aggressive & Corrosive Agents

Product Details

FEP 140 Tubing

FEP 140 tubing is highly resistant to chemicals and high temperatures. These tubes also boast high abrasion resistance. FEP 140 tubes also have excellent sealing properties thanks to the teflon.

PTFE tubing with high resistance to aggressive and corrosive agents

High abrasion resistance

Meets requirements of FDA 177.1550

Temperature Range -40°C to +150°C

Note

Stainless steel ferrules are necessary when using FEP tube at all temperatures compatible with the fitting/tubing assembly

Approvals

FDA 177.1550