

## UNIVERSAL PROGRAMMER ZIF48 SOCKET, USB2.0 PORT OR STAND-ALONE MODE FOR EPROMs, EEPROMs, FLASHs, PLDs, MICROCONTROLLERS

Support over 36000 devices



# SUPERPRO-611S



### Introduction:

The SuperPro-611S is an universal programmer equipped with ARM7 processor in USB-2. Thanks to its ZIF48 socket it can program over 36.000 different components among EPROMs, EEPROMs, FLASHs memories, PLDs and microcontrollers. A LCD display screen of 20 x 2 characters as well as a keypad allow to use this programmer in stand-alone mode. This mode enables it, thanks to the addition of an optional classical compact Flash card (512 Mb or 1Gb) inserted in the back of the programmer, to download numerous algorithms in the SuperPro-611S. Therefore, this allows it to operate without a computer in cases when you need to use it away from the office, or just when you want to use the SuperPro-611S as a production programmer to make copies very quickly with the automatic detection of a device's presence to start programming (5 times faster than when it is connected to a PC). It can program low-voltage components until 1,2V. It does not need any adapters for all components in SDIP package. The programming is extremely fast thanks to the use of algorithm technology downloaded in the CPU of the programmer during the selection of a device. The SuperPro-611S can also test the pins of the inserted device to detect possible faults : incorrect insertion of the device, defective pin...etc. It is also protected against shorts and overvoltage. An optional ISP adapter permits to program components soldered on printed circuits or devices in special packages. The software runs under Windows 98/ME/NT/2000/XP/Windows7/Windows8/Windows10 (32/64 bits). It allows advanced production functions such as an automatic programming as soon as the device is detected, verification of the device ID and automatic generation of serial numbers in the device. Free updates are regularly available on the Internet.

### Features:

Accepts standard file formats: JEDEC, INTEL (Extended) HEX, HOLTEK, EMC(.CDS), INTEL HEX16, Motorola S record, BINARY, Tektronix (linear & segmented), and auto find format.  
Manages 16 and 32 bit word split (Set Programming).  
Automatically identifies the manufacturer and type of E(E)PROMs, auto identifies TTL/CMOS logic IC.  
Device insertion test and poor pin contact check.  
Universal DIP, PLCC, QFP, TSOP, PSOP, SOIC, SSOP, SDIP adapters, (support from 6 pin to 300 pin device packages).  
Auto-run mode starts programming automatically upon detection of chip insertion.  
Supports Windows XP / VISTA / Windows 7 / Windows 8.1 / Windows10 (32bits and 64bits) with 100MB of spare capacity.

### Hardware & Electrical specifications:

Dimensions product : 145 x 200 x 65mm. Weight : 600g  
Dimensions packaging : 320 x 300 x 90mm. Weight : 1600g  
Power supply : adapter with AC input 85V to 260V, 50Hz/60Hz, output 12Vdc.  
Interface : connect to laptop or PC through USB port (USB 2.0 high speed)  
Support : ZIF48 universal pin-drivers, (support 8 pins to 48 pins DIP package).

### Item includes:

- Programmer with 48 pins ZIF socket.
- Power pack 85-260Vac / 12Vdc.
- USB-B to USB-A cable.
- Software on CD.
- User manual in English and French.

**Products informations : [www.seeit.fr](http://www.seeit.fr)**

### Options :

ISP-HEADER01 : ICSP adapter.  
Universal adapters PLCC, SO, QFP,...

↓ **Devices list programmed below** ↓



## DEVICES LIST SUPERPRO-611S

(Universal programmer with ZIF48pins drivers)

Push "CTRL + F" keys to find a component

Universal programmer SuperPro-611S

Total manufacturers : 238

Total devices : 36940

Revision 1652

Explanation to read a device:

Example: 24LC16B@SOIC8 [SA602A]

24LC16B: Device name

@SOIC8: Package name

[SA602A]: Adapter name (if needed)

### Manufacturers:

ABOV	ACE	ACE Technology	ACT
ACTRANS	ADESTO	ADVANCE GROUP	
AiT Semiconductor		ALI (Acer)	ALL24SERIES
ALLIANCE	ALTERA	AMD	AMIC
AMS	ANACHIP	APLUS FLASH	ARTSCHIP
ASAHI KASEI (AKM)	ASD	ASI	
Asic Microelectronics		ASP	ASTIGP-MICROCHIP
ATC	ATMEL	ATMEL W&M	ATMEL-CUSTOM
ATMEL-CUSTOMER	ATO	AUSTIN	AXELITE
BELLING	BENCHMARQ	BERGMICRO	BJX
BMT	BOCH	Bookly Micro	BRIGHT
CATALYST	CBC Microelectronics		CERAMATE
CETC58	CFEON	CHINGIS	CHIPMAST
CHIPON	CHIPSWINNER	CKD Technology	CORERIVER
CWI	CYGNAL	CYPRESS	CYROD
DALLAS	DENSE-PAC	DEUTRON	EASTSOFT
E-CMOS	EFST	ELECTRONIC ARRAYS	
EMTC	EON	EOREX	ESIGMA
ESMT	ESTEK	E-TRAND	EVERSPIN
EXCELSEMI	EXEL	FAIRCHILD	FIDELIX
FIRST-RANK Technology		FORCE TECHNOLOGIES	
FORWARD	FREESCALE	Fremont Micro Devices	
FUDAN	FUJITSU	GAMMA	GATELEVEL
GENCORE	GENERAL (GI)	GENERALPLUS	GENERIC
GIANTEC	GIGADEVICE	GOAL	GREEN-ENGINE
GREENLIANT	GREENWICH	GTM	HAIER
HARRIS	HITACHI	HOLTEK	HONGKONG
HOPEFIND	HUAJIE Technology		HYNIX
HYNIX-CUSTOMER	HYUNDAI	IC Microsystems	ICE
ICMIC	ICSI	ICT	IDT
IK Semiconductor	IMT	INFINEON	INTEGRAL
INTEL	INTELSIL	INTERSIL	ISSI
JSC	K-LINE	KODENSHI	LATTICE
LG	LG Semicon	LINKSMART	LITAO
LIZE	LUMINARY	LYONTEK	MACRONIX
MAGNACHIP	MAXCOM	MAXIM	MAXWELL

MEGAWIN	MICON	MICROCHIP	MICROCHIP (SST)
MICRON	MIRA	MITSUBISHI	MOSEL-VITELIC
MOSMIC	MOSTEK	MOTOROLA	MT
MXIC	MY-MS	MYSON	NAMUGA
NANOIC	NANSI	NANTRONICS	NATRONICS
NEC	NEXFLASH	NJRC	NOVATEK
NSC	NTE	NUMONYX	NUVOTON
NXP	OKI	ON	ON Semiconductor
On-Bright	PARAGON	PCT	PHILIPS
PJ	PMC	PORTEK	POWERFLASH
POWER-RAIL	PSS	PTC	QISDA-CUSTOMER
QIXIN	QP semiconductor	Quick Pulse	RAMTRON
RATO	RAYDIUM	REALTEK	RENESAS
RICOH	ROCKWELL	ROHM	SAIFUN
SAMSUNG	SANYO	SEEQ	SEIKO
SGS-THOMSON	SHARP	SIEMENS	SIERRA
SIGNETICS	Silicon Laboratories		SIMTEK
SMOS	SONIX	SONY	
SPACE ELECTRONICS [SEi]		SPANSION	SSSC
SST	SST-CUSTOMER	SSU	ST
STC	SUMMIT	SUNMOON	SUNPLUS
SYNCOMOS	SYNERTEK	SYNTEK	TECHCODE
TEKMOS	TEMIC	Terra Semiconductor	
TI	TMC	TOSHIBA	TURBO IC
UMC	UNIGEN	VERSACHIPS	VLSI
WELTREND	WHITE ELECTRONIC DESIGNS		WINBOND
WING Shing	WSI	XELTEK	XICOR
XILINX	XINNOVA	XUMARS	YMC
YSS	YXLDZ	ZETTA	ZHENGXIN
ZILOG	ZMD		

### **Devices list :**

ABOV

### **MICROCONTROLLER**

GMS34004TK	GMS34004TM
GMS34004TW	GMS34112TK
GMS34112TK@SOIC20 [SA404]	GMS34112TK@SSOP20 [SA626A]
GMS34140TK	GMS34140TK@SOIC24 [SA404]
GMS80C701	GMS80C701@PLCC44 [SA244]
GMS80C701@TQFP44 [SA675-B4805]	GMS81004 (dip20)
GMS81004 (dip24)	GMS81004 (dip28)
GMS81004@PLCC44 [SA244]	GMS81004@SOIC20 [SA404]
GMS81004@SOIC24 [SA404]	GMS81004@SOIC28 [SA404]
GMS81008 (dip20)	GMS81008 (dip24)
GMS81008 (dip28)	GMS81008@PLCC44 [SA244]
GMS81008@SOIC20 [SA404]	GMS81008@SOIC24 [SA404]
GMS81008@SOIC28 [SA404]	GMS81016 (dip20)
GMS81016 (dip24)	GMS81016 (dip28)
GMS81016@PLCC44 [SA244]	GMS81016@SOIC20 [SA404]
GMS81016@SOIC24 [SA404]	GMS81016@SOIC28 [SA404]

GMS81024(dip20)	GMS81024(dip24)
GMS81024(dip28)	GMS81024@PLCC44 [SA244]
GMS81024@SOIC20 [SA404]	GMS81024@SOIC24 [SA404]
GMS81024@SOIC28 [SA404]	GMS81032(dip20)
GMS81032(dip24)	GMS81032(dip28)
GMS81032@PLCC44 [SA244]	GMS81032@SOIC20 [SA404]
GMS81032@SOIC24 [SA404]	GMS81032@SOIC28 [SA404]
GMS81504AT [SA653]	GMS81504T [SA653]
GMS81516	GMS81516AT
GMS81516BT	GMS81524
GMS81524AT	GMS81524BT
GMS81604T	GMS81604T@PLCC44 [SA244]
GMS81604T@SDIP42 [SA028]	GMS81608T
GMS81608T@PLCC44 [SA244]	GMS81608T@SDIP42 [SA028]
GMS81C5016(dip28)	GMS81C5016(dip40)
GMS81C5016@PLCC44 [SA244]	GMS81C5016@SOIC28 [SA404]
GMS81C5016@TQFP44 [SA675-B4805]	GMS81C5024(dip28)
GMS81C5024(dip40)	GMS81C5024@PLCC44 [SA244]
GMS81C5024@SOIC28 [SA404]	GMS81C5024@TQFP44 [SA675-B4805]
GMS81C5032(dip28)	GMS81C5032(dip40)
GMS81C5032@PLCC44 [SA244]	GMS81C5032@SOIC28 [SA404]
GMS81C5032@TQFP44 [SA675-B4805]	GMS82516T
GMS82516T@MQFP44 [SA675-B4805]	GMS82516T@SDIP42 [SA028]
GMS82524T	GMS82524T@MQFP44 [SA675-B4805]
GMS82524T@SDIP42 [SA028]	GMS87C1102
GMS87C1102@SOP16 [SA404]	GMS87C1202
GMS87C1202@SOP20 [SA404]	GMS87C1404
GMS87C1404@SOP28 [SA404]	GMS87C1408
GMS87C1408@SOP28 [SA404]	GMS87C5032(dip28)
GMS87C5032(dip40)	GMS87C5032@PLCC44 [SA244]
GMS87C5032@SOIC28 [SA404]	GMS87C5032@TQFP44 [SA675-B4805]
GMS97C1051	GMS97C1051@SOIC20 [SA404]
GMS97C2051	GMS97C2051@SOIC20 [SA404]
GMS97C51	GMS97C51@PLCC44 [SA244]
GMS97C51@TQFP44 [SA675-B4805]	GMS97C51H
GMS97C51H@PLCC44 [SA244]	GMS97C51H@TQFP44 [SA675-B4805]
GMS97C52	GMS97C52@PLCC44 [SA244]
GMS97C52@TQFP44 [SA675-B4805]	GMS97C52H
GMS97C52H@PLCC44 [SA244]	GMS97C52H@TQFP44 [SA675-B4805]
GMS97C54	GMS97C54@PLCC44 [SA244]
GMS97C54@TQFP44 [SA675-B4805]	GMS97C54H
GMS97C54H@PLCC44 [SA244]	GMS97C54H@TQFP44 [SA675-B4805]
GMS97C56	GMS97C56@PLCC44 [SA244]
GMS97C56@TQFP44 [SA675-B4805]	GMS97C56H
GMS97C56H@PLCC44 [SA244]	GMS97C56H@TQFP44 [SA675-B4805]
GMS97C58	GMS97C58@PLCC44 [SA244]
GMS97C58@TQFP44 [SA675-B4805]	GMS97C58H
GMS97C58H@PLCC44 [SA244]	GMS97C58H@TQFP44 [SA675-B4805]
GMS97L1051	GMS97L1051@SOIC20 [SA404]
GMS97L2051	GMS97L2051@SOIC20 [SA404]
GMS97L51	GMS97L51@PLCC44 [SA244]
GMS97L51@TQFP44 [SA675-B4805]	GMS97L52
GMS97L52@PLCC44 [SA244]	GMS97L52@TQFP44 [SA675-B4805]

GMS97L54  
GMS97L54@TQFP44 [SA675-B4805]  
GMS97L56@PLCC44 [SA244]  
GMS97L58  
GMS97L58@TQFP44 [SA675-B4805]  
GMS99C51@PLCC44 [SA244]  
GMS99C52  
GMS99C52@TQFP44 [SA675-B4805]  
GMS99C58@PLCC44 [SA244]  
HMS81004E (dip20)  
HMS81004E (dip28)  
HMS81004E@SOIC20 [SA404]  
HMS81004E@SOIC28 [SA404]  
HMS81008E (dip24)  
HMS81008E@PLCC44 [SA244]  
HMS81008E@SOIC24 [SA404]  
HMS81016E (dip20)  
HMS81016E (dip28)  
HMS81016E@SOIC20 [SA404]  
HMS81016E@SOIC28 [SA404]  
HMS81020ET (dip24)  
HMS81020ET@SOIC20 [SA404]  
HMS81020ET@SOIC28 [SA404]  
HMS81020TL (dip24)  
HMS81020TL@SOIC20 [SA404]  
HMS81020TL@SOIC28 [SA404]  
HMS81024E (dip24)  
HMS81024E@PLCC44 [SA244]  
HMS81024E@SOIC24 [SA404]  
HMS81032 (dip20)  
HMS81032 (dip28)  
HMS81032@SOIC24 [SA404]  
HMS81032ET (dip20)  
HMS81032ET (dip28)  
HMS81032ET@SOIC24 [SA404]  
HMS81032T (dip20)  
HMS81032T (dip28)  
HMS81032T@SOIC24 [SA404]  
HMS81032TL (dip20)  
HMS81032TL (dip28)  
HMS81032TL@SOIC24 [SA404]  
HMS87C1102A  
HMS87C1104A  
HMS87C1202A  
HMS87C1204A  
HMS87C1302A@SDIP24 [SA653]  
HMS87C1304A@SDIP24 [SA653]  
HMS87C1404B  
HMS87C1404B@SOIC28 [SA404]  
HMS87C1408B@SDIP28 [SA653]  
HMS87C1416B  
HMS87C1416B@SOIC28 [SA404]  
HMS87C1516B

GMS97L54@PLCC44 [SA244]  
GMS97L56  
GMS97L56@TQFP44 [SA675-B4805]  
GMS97L58@PLCC44 [SA244]  
GMS99C51  
GMS99C51@TQFP44 [SA675-B4805]  
GMS99C52@PLCC44 [SA244]  
GMS99C58  
GMS99C58@TQFP44 [SA675-B4805]  
HMS81004E (dip24)  
HMS81004E@PLCC44 [SA244]  
HMS81004E@SOIC24 [SA404]  
HMS81008E (dip20)  
HMS81008E (dip28)  
HMS81008E@SOIC20 [SA404]  
HMS81008E@SOIC28 [SA404]  
HMS81016E (dip24)  
HMS81016E@PLCC44 [SA244]  
HMS81016E@SOIC24 [SA404]  
HMS81020ET (dip20)  
HMS81020ET (dip28)  
HMS81020ET@SOIC24 [SA404]  
HMS81020TL (dip20)  
HMS81020TL (dip28)  
HMS81020TL@SOIC24 [SA404]  
HMS81024E (dip20)  
HMS81024E (dip28)  
HMS81024E@SOIC20 [SA404]  
HMS81024E@SOIC28 [SA404]  
HMS81032 (dip24)  
HMS81032@SOIC20 [SA404]  
HMS81032@SOIC28 [SA404]  
HMS81032ET (dip24)  
HMS81032ET@SOIC20 [SA404]  
HMS81032ET@SOIC28 [SA404]  
HMS81032T (dip24)  
HMS81032T@SOIC20 [SA404]  
HMS81032T@SOIC28 [SA404]  
HMS81032TL (dip24)  
HMS81032TL@SOIC20 [SA404]  
HMS81032TL@SOIC28 [SA404]  
HMS87C1102A@SOP16 [SA404]  
HMS87C1104A@SOP16 [SA404]  
HMS87C1202A@SOP20 [SA404]  
HMS87C1204A@SOP20 [SA404]  
HMS87C1302A@SOP24 [SA404]  
HMS87C1304A@SOP24 [SA404]  
HMS87C1404B@SDIP28 [SA653]  
HMS87C1408B  
HMS87C1408B@SOIC28 [SA404]  
HMS87C1416B@SDIP28 [SA653]  
HMS87C1508B  
HMS87C1608B

HMS87C1616B  
HMS87C1716B@SDIP42 [SA028]  
HMS87C1816B@TQFP44 [SA675-B4805]  
HMS87C5216@PLCC44 [SA244]  
HMS87C5216@TQFP44 [SA675-B4805]  
HMS99C51@PLCC44 [SA244]  
HMS99C52  
HMS99C52@TQFP44 [SA675-B4805]  
HMS99C58@PLCC44 [SA244]  
MC40P5001D@SOP20 [SA404]  
MC40P5004BD@SOP20 (2K) [SA404]  
MC40P5004BR@TSSOP20 (1K) [SA643]  
MC40P5004BR@TSSOP20 (4K) [SA643]  
MC40P5104BM@SOP16 (1K) [SA602]  
MC40P5104BM@SOP16 (4K) [SA602]  
MC40P5204BD@SOP24 (1K) [SA404]  
MC40P5204BD@SOP24 (4K) [SA404]  
MC40P5404BD@SOP20 (1K) [SA404]  
MC40P5404BD@SOP20 (4K) [SA404]  
MC40P6004BD@SOP20 (2K) [SA404]  
MC40P6004BR@TSSOP20 (1K) [SA643]  
MC40P6004BR@TSSOP20 (4K) [SA643]  
MC40P6104M@SOP16 (2K) [SA602]  
MC80F0504  
MC80F0504@SSOP16 [SA626A]  
MC80F0604  
MC80F0604@SSOP20 [SA626A]  
MC80F0704@QFN28  
MC80F0708  
MC80F0708@SOP28 [SA783]  
MC80F0804@SOP32 [SA715]  
MC80F0808@SOP32 [SA715]  
MC80F7108@MQFP44 [SA675-B4805]  
MC81F4104B  
MC81F4104S@SSOP10 [\$\$\$\$\$]  
MC81F4204D@SOP20 [SA404]  
MC81F4204R@TSSOP16 [SA026]  
MC81F4204W@TSSOP20 [SA026]  
MC81F4215D@SOP20 [SA404]  
MC81F4216D@SOP20 [SA404]  
MC81F4315G  
MC81F4315L@LQFP32 [SA636]  
MC81F4315S@SSOP24 [SA026]  
MC81F4316G  
MC81F4316M@SOP28 [SA404]  
MC81F4416K@SDIP42 [SA028]  
MC95FG104M@SOP8 [SA602]  
MC96F6332D@SOP32 [SA715]  
MC96F6332M@SOP28 [SA404]  
HMS87C1708B@SDIP42 [SA028]  
HMS87C1808B@TQFP44 [SA675-B4805]  
HMS87C5216  
HMS87C5216@S0IC28 [SA404]  
HMS99C51  
HMS99C51@TQFP44 [SA675-B4805]  
HMS99C52@PLCC44 [SA244]  
HMS99C58  
HMS99C58@TQFP44 [SA675-B4805]  
MC40P5004BD@SOP20 (1K) [SA404]  
MC40P5004BD@SOP20 (4K) [SA404]  
MC40P5004BR@TSSOP20 (2K) [SA643]  
MC40P5101D@SOP20 [SA404]  
MC40P5104BM@SOP16 (2K) [SA602]  
MC40P5201D@SOP24 [SA404]  
MC40P5204BD@SOP24 (2K) [SA404]  
MC40P5301D@SOP24 [SA404]  
MC40P5404BD@SOP20 (2K) [SA404]  
MC40P6004BD@SOP20 (1K) [SA404]  
MC40P6004BD@SOP20 (4K) [SA404]  
MC40P6004BR@TSSOP20 (2K) [SA643]  
MC40P6104M@SOP16 (1K) [SA602]  
MC40P6104M@SOP16 (4K) [SA602]  
MC80F0504@SOP16 [SA783]  
MC80F0504[153mil]@SOP16 [SA602]  
MC80F0604@SOP20 [SA783]  
MC80F0704  
MC80F0704@SOP28 [SA783]  
MC80F0708@QFN28  
MC80F0804@SDIP32 [SA653]  
MC80F0808@SDIP32 [SA653]  
MC80F7108@LQFP44 [SA245A-B4805]  
MC80F7208@SDIP42 [SA028]  
MC81F4104M@SOP8 [SA602A]  
MC81F4204B  
MC81F4204M@SOP16 [SA404]  
MC81F4204V  
MC81F4215B  
MC81F4216B  
MC81F4315D@SOP32 [SA715]  
MC81F4315K@SDIP32 [SA653]  
MC81F4315M@SOP28 [SA404]  
MC81F4316D@SOP32 [SA715]  
MC81F4316K@SDIP32 [SA653]  
MC81F4316S@SSOP24 [SA026]  
MC81F4416Q@MQFP44 [SA675-B4805]  
MC95FG104S@SOP10 [\$\$\$\$\$]  
MC96F6332L@QFP32 [SA636]  
MC96F6432Q@QFP44 [SA675-B4805]

## E (E) PROM/FRAM/NVRAM

ACE24C32@SON8 [SA724]

ACE24C64@SON8 [SA724]

## ACE Technology

### E (E) PROM/FRAM/NVRAM

ACE24C02A

ACE24C02A@TSSOP8 [SA643]

ACE24C04A@SOIC8 [SA602A]

ACE24C08A

ACE24C08A@TSSOP8 [SA643]

ACE24C128@SOIC8 [SA602A]

ACE24C16A

ACE24C16A@TSSOP8 [SA643]

ACE24C256@SOIC8 [SA602A]

ACE24C32

ACE24C32@TSSOP8 [SA643]

ACE24C64@SOIC8 [SA602A]

ACE24LC02

ACE24LC02@TSSOP8 [SA643]

ACE24LC04@SOIC8 [SA602A]

ACE24LC08

ACE24LC08@TSSOP8 [SA643]

ACE24LC16@SOIC8 [SA602A]

ACE93C46 (08bit)

ACE93C46 (08bit)@TSSOP8 [SA643]

ACE93C46 (16bit)@SOIC8 [SA602A]

ACE24C02A@SOIC8 [SA602A]

ACE24C04A

ACE24C04A@TSSOP8 [SA643]

ACE24C08A@SOIC8 [SA602A]

ACE24C128

ACE24C128@TSSOP8 [SA643]

ACE24C16A@SOIC8 [SA602A]

ACE24C256

ACE24C256@TSSOP8 [SA643]

ACE24C32@SOIC8 [SA602A]

ACE24C64

ACE24C64@TSSOP8 [SA643]

ACE24LC02@SOIC8 [SA602A]

ACE24LC04

ACE24LC04@TSSOP8 [SA643]

ACE24LC08@SOIC8 [SA602A]

ACE24LC16

ACE24LC16@TSSOP8 [SA643]

ACE93C46 (08bit)@SOIC8 [SA602A]

ACE93C46 (16bit)

ACE93C46 (16bit)@TSSOP8 [SA643]

## ACT

### E (E) PROM/FRAM/NVRAM

93LC46 (08bit)

93LC46 (16bit)

93LC56 (08bit)

93LC56 (16bit)

93LC66 (08bit)

93LC66 (16bit)

93LC86 (08bit)

93LC86 (16bit)

93LC46 (08bit)@SOIC8 [SA602A]

93LC46 (16bit)@SOIC8 [SA602A]

93LC56 (08bit)@SOIC8 [SA602A]

93LC56 (16bit)@SOIC8 [SA602A]

93LC66 (08bit)@SOIC8 [SA602A]

93LC66 (16bit)@SOIC8 [SA602A]

93LC86 (08bit)@SOIC8 [SA602A]

93LC86 (16bit)@SOIC8 [SA602A]

## ACTRANS

### E (E) PROM/FRAM/NVRAM

AC25010@SOIC8 [SA602A]

AC25LC010@SOIC8 [SA602A]

AC39LV010@PLCC32 [SA015A1T]

AC39LV020@PLCC32 [SA015A1T]

AC25512@SOIC8 [SA602A]

AC25LC512@SOIC8 [SA602A]

AC39LV010@VSOP32 [SA620-B4807]

AC39LV020@VSOP32 [SA620-B4807]

AC39LV040@PLCC32 [SA015A1T]	AC39LV040@VSOP32 [SA620-B4807]
AC39LV080@TSOP40 [SA409T-B4002]	AC39LV088@TSOP48 [SB247-B4806]
AC39LV512@PLCC32 [SA015A1T]	AC39LV512@VSOP32 [SA620-B4807]
AC39LV800@TSOP48 [SB247-B4806]	AC39VF800@TSOP48 [SB247-B4806]

## ADESTO

### E (E) PROM/FRAM/NVRAM

AT25DN512C@DFN8 [SA724]	AT25DN512C@SOIC8 [SA602A]
AT25DN512C@TSSOP [SA605B]	AT25SF041@SOIC8 [SA602A]
AT25SF041@TSSOP8 [SA605B]	AT25SF041@USON8 [SA724]
AT25SF081@SOIC8 [SA602A]	AT25SF081@TSSOP8 [SA605B]
AT25SF081@USON8 [SA724]	AT25SF161@SOIC8 [SA602A]
AT25SF161@TSSOP8 [SA605B]	AT25SF161@USON8 [SA724]
AT25XE021A@SOIC8 [SA602A]	AT25XE021A@TSSOP8 [SA643]
AT25XE021A@UDFN8 (2*3) [SA724]	AT25XE021A@UDFN8 (5*6) [SA683]
AT45DB041E (page256)@MLF8 [SA683]	
AT45DB041E (page256)@SOIC8 [150] [SA602]	
AT45DB041E (page256)@SOIC8 [200] [SA023A]	
AT45DB041E (page264)@MLF8 [SA683]	
AT45DB041E (page264)@SOIC8 [150] [SA602]	
AT45DB041E (page264)@SOIC8 [200] [SA023A]	
AT45DB321E (page512)@QFN8 [SA684]	
AT45DB321E (page512)@SOIC8 [SA605B@90]	
AT45DB321E (page512)@UDFN8 [SA683]	
AT45DB321E (page528)@QFN8 [SA684]	
AT45DB321E (page528)@SOIC8 [SA605B@90]	
AT45DB321E (page528)@UDFN8 [SA683]	
AT45DB641E (page256)@SOIC8 [SA605B]	
AT45DB641E (page264)@SOIC8 [SA605B]	
RM24EP128A@SOIC8 [SA602A]	RM24EP128B@SOIC8 [SA602A]
RM24EP32A@SOIC8 [SA602A]	RM24EP32B@SOIC8 [SA602A]
RM24EP32C@SOIC8 [SA602A]	RM24EP64A@SOIC8 [SA602A]
RM24EP64B@SOIC8 [SA602A]	RM24EP64C@SOIC8 [SA602A]
RM25C128A@SOIC8 [SA602A]	RM25C128A@TSSOP8 [SA643]
RM25C256A@SOIC8 [SA602A]	RM25C256A@TSSOP8 [SA643]
RM25C32A	RM25C32A@SOIC8 [SA602A]
RM25C32A@TSSOP8 [SA643]	RM25C64A
RM25C64A@SOIC8 [SA602A]	RM25C64A@TSSOP8 [SA643]

## ADVANCE GROUP

### E (E) PROM/FRAM/NVRAM

AF24BC01	AF24BC01@SOIC8 [SA602A]
AF24BC01@TSOP8 [SA643]	AF24BC02
AF24BC02@SOIC8 [SA602A]	AF24BC02@TSOP8 [SA643]
AF24BC04	AF24BC04@SOIC8 [SA602A]
AF24BC04@TSOP8 [SA643]	AF24BC08
AF24BC08@SOIC8 [SA602A]	AF24BC08@TSOP8 [SA643]
AF24BC16	AF24BC16@SOIC8 [SA602A]

AF24BC16@TSOP8 [SA643]  
AF24C128@SOIC8 [SA602A]  
AF24C256  
AF24C256@TSOP8 [SA643]  
AF24C32@SOIC8 [SA602A]  
AF24C64  
AF24C64@TSOP8 [SA643]  
AF93C46 (08bit)@SOIC8 [SA602A]  
AF93C46 (16bit)  
AF93C46 (16bit)@TSOP8 [SA643]  
AF93C56 (08bit)@SOIC8 [SA602A]  
AF93C56 (16bit)  
AF93C56 (16bit)@TSOP8 [SA643]  
AF93C66 (08bit)@SOIC8 [SA602A]  
AF93C66 (16bit)  
AF93C66 (16bit)@TSOP8 [SA643]  
AF93C86 (08bit)@SOIC8 [SA602A]  
AF93C86 (16bit)  
AF93C86 (16bit)@TSOP8 [SA643]

AF24C128  
AF24C128@TSOP8 [SA643]  
AF24C256@SOIC8 [SA602A]  
AF24C32  
AF24C32@TSOP8 [SA643]  
AF24C64@SOIC8 [SA602A]  
AF93C46 (08bit)  
AF93C46 (08bit)@TSOP8 [SA643]  
AF93C46 (16bit)@SOIC8 [SA602A]  
AF93C56 (08bit)  
AF93C56 (08bit)@TSOP8 [SA643]  
AF93C56 (16bit)@SOIC8 [SA602A]  
AF93C66 (08bit)  
AF93C66 (08bit)@TSOP8 [SA643]  
AF93C66 (16bit)@SOIC8 [SA602A]  
AF93C86 (08bit)  
AF93C86 (08bit)@TSOP8 [SA643]  
AF93C86 (16bit)@SOIC8 [SA602A]

## MICROCONTROLLER

AG89P51  
AG89P51@PQFP44  
AG89P51A@PLCC44  
AG89P52  
AG89P52@PQFP44

AG89P51@PLCC44  
AG89P51A  
AG89P51A@PQFP44  
AG89P52@PLCC44

## AiT Semiconductor

### E (E) PROM/FRAM/NVRAM

A24C02  
A24C02@SOT23-5 [SA717]  
A24C04  
A24C04@SOT23-5 [SA717]  
A24C08  
A24C08@SOT23-5 [SA717]  
A24C128@SOP8 [SA602A]  
A24C16  
A24C16@SOT23-5 [SA717]  
A24C256@SOP8 [SA602A]  
A24C32@DFN8 [SA724]  
A24C32@TSSOP8 [SA643]  
A24C64@TSSOP8 [SA643]  
A93C46 (08bit)@tsSOP8 [SA643]  
A93C46 (16bit)@TSSOP8 [SA643]  
A93C56 (08bit)@tsSOP8 [SA643]  
A93C56 (16bit)@TSSOP8 [SA643]  
A93C66 (08bit)@tsSOP8 [SA643]  
A93C66 (16bit)@TSSOP8 [SA643]

A24C02@SOP8 [SA602A]  
A24C02@TSSOP8 [SA643]  
A24C04@SOP8 [SA602A]  
A24C04@TSSOP8 [SA643]  
A24C08@SOP8 [SA602A]  
A24C08@TSSOP8 [SA643]  
A24C128@TSSOP8 [SA643]  
A24C16@SOP8 [SA602A]  
A24C16@TSSOP8 [SA643]  
A24C256@TSSOP8 [SA643]  
A24C32@SOP8 [SA602A]  
A24C64@SOP8 [SA602A]  
A93C46 (08bit)@SOP8 [SA602A]  
A93C46 (16bit)@SOP8 [SA602A]  
A93C56 (08bit)@SOP8 [SA602A]  
A93C56 (16bit)@SOP8 [SA602A]  
A93C66 (08bit)@SOP8 [SA602A]  
A93C66 (16bit)@SOP8 [SA602A]

## ALI (Acer)

### E (E) PROM/FRAM/NVRAM

M8720

M8720@PLCC32 [SA015A1T]

### MICROCONTROLLER

M6759

M6759@PLCC44 [SA244]

M6759@TQFP44 [SA675-B4805]

## ALL24SERIES

### E (E) PROM/FRAM/NVRAM

24C01 (ISP)

24C02 (ISP)

24C04 (ISP)

24C08 (ISP)

24C128 (ISP)

24C16 (ISP)

24C256 (ISP)

24C32 (ISP)

24C64 (ISP)

## ALLIANCE

### E (E) PROM/FRAM/NVRAM

AS29F200B@PSOP44 [SA638]

AS29F200B@TSOP48 [SB247-B4806]

AS29F200T@PSOP44 [SA638]

AS29F200T@TSOP48 [SB247-B4806]

AS29LV160B@TSOP48 [SB247-B4806]

AS29LV160T@TSOP48 [SB247-B4806]

AS29LV400B@TSOP48 [SB247-B4806]

AS29LV400T@TSOP48 [SB247-B4806]

AS29LV800B@TSOP48 [SB247-B4806]

AS29LV800T@TSOP48 [SB247-B4806]

## ALTERA

### E (E) PROM/FRAM/NVRAM

EPC1 (LC)@PLCC20 [SA001A-B2001]

EPC1 (LI)@PLCC20 [SA001A-B2001]

EPC1 (PC8)

EPC1 (PI8)

EPC1441 (LC)@PLCC20 [SA001A-B2001]

EPC1441 (LI)@PLCC20 [SA001A-B2001]

EPC1441 (PC8)

EPC1441 (PI8)

EPC1441 (TC)@TQFP32 [SA636]

EPC1441 (TI)@TQFP32 [SA636]

EPC2 (LC)@PLCC20 [SA001A-B2001]

EPC2 (LI)@PLCC20 [SA001A-B2001]

EPC2 (TC)@TQFP32 [SA636]

EPC2 (TI)@TQFP32 [SA636]

EPCS128@SOIC16 [SA404]

EPCS16@SOIC16 [SA404]

EPCS16@SOIC8 [SA602A]

EPCS16N@SOIC16 [SA404]

EPCS1SI8@SOIC8 [SA602]

EPCS4SI8@SOIC8 [SA602]

EPCS64SI16N [SA404]

## PLD

EP600	EP600@PLCC28 [SA008A]
EP600@SOIC24 [SA404]	EP600I
EP600I@PLCC28 [SA008A]	EP600I@SOIC24 [SA404]
EP610	EP610@PLCC28 [SA008A]
EP610@SOIC24 [SA404]	EP610A
EP610A@PLCC28 [SA008A]	EP610A@SOIC24 [SA404]
EP610I	EP610I@PLCC28 [SA008A]
EP610I@SOIC24 [SA404]	EP610T
EP610T@PLCC28 [SA008A]	EP610T@SOIC24 [SA404]
EP630	EP630@PLCC28 [SA008A]
EP630@SOIC24 [SA404]	EP900
EP900@PLCC44 [SA244]	EP900I
EP900I@PLC44 [SA244]	EP910
EP910@PLCC44 [SA244]	EP910A
EP910A@PLCC44 [SA244]	EP910I
EP910I@PLCC44 [SA244]	EP910T
EP910T@PLCC44 [SA244]	EPM7032@PLCC44 [SA244]
EPM7032@TQFP44 [SA245A-B4805]	
EPM7032AE@JLCC44 (7032 mode) [SA244]	
EPM7032AE@PLCC44 (7032 mode) [SA244]	
EPM7032AE@PLCC44 (7032AE mode) [SA244]	
EPM7032AE@PLCC44 (7032S mode) [SA244]	
EPM7032AE@PQFP44 (7032 mode) [SA245A-B4805]	
EPM7032AE@TQFP44 (7032 mode) [SA245A-B4805]	
EPM7032AE@TQFP44 (7032AE mode) [SA245A-B4805]	
EPM7032AE@TQFP44 (7032S mode) [SA245A-B4805]	
EPM7032S@PLCC44 (7032 mode) [SA244]	
EPM7032S@PLCC44 (7032S mode) [SA244]	
EPM7032S@TQFP44 (7032 mode) [SA245A-B4805]	
EPM7032S@TQFP44 (7032S mode) [SA245A-B4805]	
EPM7032V@PLCC44 [SA244]	EPM7032V@TQFP44 [SA245A-B4805]
EPM7064@PLCC44 [SA244]	EPM7064@TQFP44 [SA245A-B4805]
EPM7064AE@PLCC44 (7064AE mode) [SA244]	
EPM7064AE@PLCC44 (7064S mode) [SA244]	
EPM7064AE@TQFP44 (7064AE mode) [SA245A-B4805]	
EPM7064AE@TQFP44 (7064S mode) [SA245A-B4805]	
EPM7064S@PLCC44 (7064 mode) [SA244]	
EPM7064S@PLCC44 (7064S mode) [SA244]	
EPM7064S@TQFP44 (7064 mode) [SA245A-B4805]	
EPM7064S@TQFP44 (7064S mode) [SA245A-B4805]	

## AMD

### E (E) PROM/FRAM/NVRAM

AM25FL005D@SOIC8 [SA602A]	AM25FL005D@USON8 [SA683]
AM25FL010D@SOIC8 [SA602A]	AM25FL010D@USON8 [SA683]
AM25FL016A@SOIC16 [SA783]	AM25FL016A@SOIC16 (ISP)
AM25FL016A@WSON8 [SA684]	AM25FL016A@WSON8 (ISP)
AM25FL020D@SOIC8 [SA602A]	AM25FL020D@USON8 [SA683]

AM25FL032A@SOIC16 [SA783]  
AM25FL032A@WSON8 [SA684]  
AM25FL040D@SOIC8 [SA602A]  
AM25FL080D@SOIC8 [SA602A]  
AM27128  
AM27128 (DC)@PLCC32 [SA015A1T]  
AM27128A  
AM27128A (F)@PLCC32 [SA015A1T]  
AM27128A (PC)@PLCC32 [SA015A1T]  
AM2716  
AM27256  
AM27256AP  
AM27256F  
AM27256PC  
AM2732  
AM2732B  
AM27512@PLCC32 [SA015A1T]  
AM27512DC@PLCC32 [SA015A1T]  
AM27512F@PLCC32 [SA015A1T]  
AM27512PC@PLCC32 [SA015A1T]  
AM2764  
AM2764A  
AM2764A (DC)@PLCC32 [SA015A1T]  
AM2764A (DI)  
AM2764A (F)  
AM2764A (JC)  
AM2764A (LCB)  
AM2764A (LEB)  
AM2764A (PC)@PLCC32 [SA015A1T]  
AM27C010  
AM27C010@TSOP32 [SA410T-B4001]  
AM27C020@PLCC32 [SA015A1T]  
AM27C040  
AM27C040@TSOP32 [SA410T-B4001]  
AM27C080@PLCC32 [SA015A1T]  
AM27C100  
AM27C100@TSOP32 [SA410T-B4001]  
AM27C1024@PLCC44 [SA244]  
AM27C128@PLCC32 [SA015A1T]  
AM27C2048@PLCC44 [SA244]  
AM27C256  
AM27C256 (F)@PLCC32 [SA015A1T]  
AM27C256 (PC)@PLCC32 [SA015A1T]  
AM27C400  
AM27C4096  
AM27C512  
AM27C512 (P)@PLCC32 [SA015A1T]  
AM27C64  
AM27H010  
AM27H010@TSOP32 [SA410T-B4001]  
AM27H256@PLCC32 [SA015A1T]  
AM27HB010@PLCC32 [SA015A1T]  
AM27LV010

AM25FL032A@SOIC16 (ISP)  
AM25FL032A@WSON8 (ISP)  
AM25FL040D@USON8 [SA683]  
AM25FL080D@USON8 [SA683]  
AM27128 (DC)  
AM27128@PLCC32 [SA015A1T]  
AM27128A (F)  
AM27128A (PC)  
AM27128A@PLCC32 [SA015A1T]  
AM2716B  
AM27256@PLCC32 [SA015A1T]  
AM27256AP@PLCC32 [SA015A1T]  
AM27256F@PLCC32 [SA015A1T]  
AM27256PC@PLCC32 [SA015A1T]  
AM2732A  
AM27512  
AM27512DC  
AM27512F  
AM27512PC  
AM27513  
AM2764@PLCC32 [SA015A1T]  
AM2764A (DC)  
AM2764A (DCB)  
AM2764A (DIB)  
AM2764A (F)@PLCC32 [SA015A1T]  
AM2764A (LC)  
AM2764A (LE)  
AM2764A (PC)  
AM2764A@PLCC32 [SA015A1T]  
AM27C010@PLCC32 [SA015A1T]  
AM27C020  
AM27C020@TSOP32 [SA410T-B4001]  
AM27C040@PLCC32 [SA015A1T]  
AM27C080  
AM27C080@TSOP32 [SA410T-B4001]  
AM27C100@PLCC32 [SA015A1T]  
AM27C1024  
AM27C128  
AM27C2048  
AM27C2048@TSOP40 [SA409T-B4002]  
AM27C256 (F)  
AM27C256 (PC)  
AM27C256@PLCC32 [SA015A1T]  
AM27C400@PLCC44 [SA244]  
AM27C4096@PLCC44 [SA244]  
AM27C512 (P)  
AM27C512@PLCC32 [SA015A1T]  
AM27C64@PLCC32 [SA015A1T]  
AM27H010@PLCC32 [SA015A1T]  
AM27H256  
AM27HB010  
AM27HB010@TSOP32 [SA410T-B4001]  
AM27LV010@PLCC32 [SA015A1T]

AM27LV010@TSOP32 [SA603] AM27LV010B  
AM27LV010B@PLCC32 [SA015A1T] AM27LV010B@TSOP32 [SA410T-B4001]  
AM27LV020 AM27LV020@PLCC32 [SA015A1T]  
AM27LV020@TSOP32 [SA410T-B4001] AM27LV020B  
AM27LV020B@PLCC32 [SA015A1T] AM27LV020B@TSOP32 [SA410T-B4001]  
AM2816A AM2817A  
AM2817A@PLCC32 [SA015A1T] AM2817A@SOIC28 [SA404]  
AM2864A AM2864A (E)  
AM2864A (E)@PLCC32 [SA015A1T] AM2864A@PLCC32 [SA015A1T]  
AM2864B AM2864B (E)  
AM2864B (E)@PLCC32 [SA015A1T] AM2864B@PLCC32 [SA015A1T]  
AM28F001 AM28F001@PLCC32 [SA015A1T]  
AM28F001@TSOP32 [SA410T-B4001] AM28F010  
AM28F010 (REVERSE)@TSOP32 [SA410T-B4001]  
AM28F010@PLCC32 [SA015A1T] AM28F010@TSOP32 [SA410T-B4001]  
AM28F010A  
AM28F010A (REVERSE)@TSOP32 [SA410T-B4001]  
AM28F010A@PLCC32 [SA015A1T] AM28F010A@TSOP32 [SA410T-B4001]  
AM28F020  
AM28F020 (REVERSE)@TSOP32 [SA410T-B4001]  
AM28F020@PLCC32 [SA015A1T] AM28F020@TSOP32 [SA410T-B4001]  
AM28F020A  
AM28F020A (REVERSE)@TSOP32 [SA410T-B4001]  
AM28F020A@PLCC32 [SA015A1T] AM28F020A@TSOP32 [SA410T-B4001]  
AM28F256  
AM28F256 (REVERSE)@TSOP32 [SA410T-B4001]  
AM28F256@PLCC32 [SA015A1T] AM28F256@TSOP32 [SA410T-B4001]  
AM28F256A  
AM28F256A (REVERSE)@TSOP32 [SA410T-B4001]  
AM28F256A@PLCC32 [SA015A1T] AM28F256A@TSOP32 [SA410T-B4001]  
AM28F512  
AM28F512 (REVERSE)@TSOP32 [SA410T-B4001]  
AM28F512@PLCC32 [SA015A1T] AM28F512@TSOP32 [SA410T-B4001]  
AM28F512A  
AM28F512A (REVERSE)@TSOP32 [SA410T-B4001]  
AM28F512A@PLCC32 [SA015A1T] AM28F512A@TSOP32 [SA410T-B4001]  
AM28F512AF  
AM28F512AF (REVERSE)@TSOP32 [SA410T-B4001]  
AM28F512AF@PLCC32 [SA015A1T] AM28F512AF@TSOP32 [SA410T-B4001]  
AM28F512F  
AM28F512F (REVERSE)@TSOP32 [SA410T-B4001]  
AM28F512F@PLCC32 [SA015A1T] AM28F512F@TSOP32 [SA410T-B4001]  
AM29DL161DB@TSOP48 [SB247-B4806] AM29DL161DT@TSOP48 [SB247-B4806]  
AM29DL162CB@TSOP48 [SB247-B4806] AM29DL162CT@TSOP48 [SB247-B4806]  
AM29DL162DB@TSOP48 [SB247-B4806] AM29DL162DT@TSOP48 [SB247-B4806]  
AM29DL163CB@TSOP48 [SB247-B4806] AM29DL163CT@TSOP48 [SB247-B4806]  
AM29DL163DB@TSOP48 [SB247-B4806] AM29DL163DT@TSOP48 [SB247-B4806]  
AM29DL164CB@TSOP48 [SB247-B4806] AM29DL164CT@TSOP48 [SB247-B4806]  
AM29DL164DB@TSOP48 [SB247-B4806] AM29DL164DT@TSOP48 [SB247-B4806]  
AM29DL320GB@TSOP48 [SB247-B4806] AM29DL320GT@TSOP48 [SB247-B4806]  
AM29DL321CB@TSOP48 [SB247-B4806] AM29DL321CT@TSOP48 [SB247-B4806]  
AM29DL322CB@TSOP48 [SB247-B4806] AM29DL322CT@TSOP48 [SB247-B4806]  
AM29DL322DB@TSOP48 [SB247-B4806] AM29DL322DT@TSOP48 [SB247-B4806]

AM29DL322GB@TSOP48 [SB247-B4806] AM29DL322GT@TSOP48 [SB247-B4806]  
AM29DL323CB@TSOP48 [SB247-B4806] AM29DL323CT@TSOP48 [SB247-B4806]  
AM29DL323DB@TSOP48 [SB247-B4806] AM29DL323DT@TSOP48 [SB247-B4806]  
AM29DL323GB@TSOP48 [SB247-B4806] AM29DL323GT@TSOP48 [SB247-B4806]  
AM29DL324CB@TSOP48 [SB247-B4806] AM29DL324CT@TSOP48 [SB247-B4806]  
AM29DL324DB@TSOP48 [SB247-B4806] AM29DL324DT@TSOP48 [SB247-B4806]  
AM29DL324GB@TSOP48 [SB247-B4806] AM29DL324GT@TSOP48 [SB247-B4806]  
AM29DL400BB (REVERSE)@TSOP48 [SB247-B4806]  
AM29DL400BB@PSOP44 [SA638] AM29DL400BB@TSOP48 [SB247-B4806]  
AM29DL400BT (REVERSE)@TSOP48 [SB247-B4806]  
AM29DL400BT@PLCC44 [SA638] AM29DL400BT@TSOP48 [SB247-B4806]  
AM29DL640D@TSOP48 [SB247-B4806] AM29DL640G@TSOP48 [SB247-B4806]  
AM29DL800B@PSOP44 [SA638] AM29DL800B@TSOP48 [SB247-B4806]  
AM29DL800BB (REVERSE)@TSOP48 [SB247-B4806]  
AM29DL800BB@PSOP44 [SA638] AM29DL800BB@TSOP48 [SB247-B4806]  
AM29DL800BT (REVERSE)@TSOP48 [SB247-B4806]  
AM29DL800BT@PSOP44 [SA638] AM29DL800BT@TSOP48 [SB247-B4806]  
AM29DL800T@PSOP44 [SA638] AM29DL800T@TSOP48 [SB247-B4806]  
AM29DS163CB@TSOP48 [SB247-B4806] AM29DS163CT@TSOP48 [SB247-B4806]  
AM29DS163DB@TSOP48 [SB247-B4806] AM29DS163DT@TSOP48 [SB247-B4806]  
AM29DS323DB@TSOP48 [SB247-B4806] AM29DS323DT@TSOP48 [SB247-B4806]  
AM29F002B AM29F002B@PLCC32 [SA015A1T]  
AM29F002B@TSOP32 [SA410T-B4001] AM29F002BB  
AM29F002BB@PLCC32 [SA015A1T] AM29F002BB@TSOP32 [SA410T-B4001]  
AM29F002BT AM29F002BT@PLCC32 [SA015A1T]  
AM29F002BT@TSOP32 [SA410T-B4001] AM29F002NB  
AM29F002NB@PLCC32 [SA015A1T] AM29F002NB@TSOP32 [SA410T-B4001]  
AM29F002NBB AM29F002NBB@PLCC32 [SA015A1T]  
AM29F002NBB@TSOP32 [SA410T-B4001] AM29F002NBT@PLCC32 [SA015A1T]  
AM29F002NBT AM29F002NBT@TSOP32 [SA410T-B4001]  
AM29F002NT AM29F002NT@PLCC32 [SA015A1T]  
AM29F002NT@TSOP32 [SA410T-B4001] AM29F002T  
AM29F002T@PLCC32 [SA015A1T] AM29F002T@TSOP32 [SA410T-B4001]  
AM29F004BB AM29F004BB@PLCC32 [SA015A1T]  
AM29F004BB@TSOP32 [SA410T-B4001] AM29F004BT  
AM29F004BT@PLCC32 [SA015A1T] AM29F004BT@TSOP32 [SA410T-B4001]  
AM29F010  
AM29F010 (REVERSE)@TSOP32 [SA410T-B4001]  
AM29F010@PLCC32 [SA015A1T] AM29F010@TSOP32 [SA410T-B4001]  
AM29F010A  
AM29F010A (REVERSE)@TSOP32 [SA410T-B4001]  
AM29F010A@PLCC32 [SA015A1T] AM29F010A@TSOP32 [SA410T-B4001]  
AM29F010B  
AM29F010B (REVERSE)@TSOP32 [SA410T-B4001]  
AM29F010B@PLCC32 [SA015A1T] AM29F010B@TSOP32 [SA410T-B4001]  
AM29F016@PSOP44 [SA638] AM29F016@TSOP40 [SA409T-B4002]  
AM29F016@TSOP48 [SB247-B4806] AM29F016B@PSOP44 [SA638]  
AM29F016B@TSOP40 [SA409T-B4002] AM29F016B@TSOP48 [SB247-B4806]  
AM29F016D (REVERSE)@TSOP48 [SB247-B4806]  
AM29F016D@PSOP44 [SA638] AM29F016D@TSOP40 [SA409T-B4002]  
AM29F016D@TSOP48 [SB247-B4806]  
AM29F017B (REVERSE)@TSOP40 [SA409T-B4002]

AM29F017B (REVERSE)@TSOP48 [SB247-B4806]  
AM29F017B@TSOP40 [SA409T-B4002] AM29F017B@TSOP48 [SB247-B4806]  
AM29F017D (REVERSE)@TSOP48 [SB247-B4806]  
AM29F017D@TSOP40 [SA409T-B4002] AM29F017D@TSOP48 [SB247-B4806]  
AM29F032B@PSOP44 [SA638] AM29F032B@TSOP40 [SA409T-B4002]  
AM29F040 AM29F040@PLCC32 [SA015A1T]  
AM29F040@TSOP32 [SA410T-B4001] AM29F040A  
AM29F040A@PLCC32 [SA015A1T] AM29F040A@TSOP32 [SA410T-B4001]  
AM29F040B  
AM29F040B (Reverse)@TSOP32 [SA410T-B4001]  
AM29F040B@PLCC32 [SA015A1T] AM29F040B@TSOP32 [SA410T-B4001]  
AM29F080 (REVERSE)@TSOP40 [SA409T-B4002]  
AM29F080@PSOP44 [SA638] AM29F080@TSOP40 [SA409T-B4002]  
AM29F080B@PSOP44 [SA638] AM29F080B@TSOP40 [SA409T-B4002]  
AM29F100B (REVERSE)@TSOP48 [SB247-B4806]  
AM29F100B@PSOP44 [SA638] AM29F100B@TSOP48 [SB247-B4806]  
AM29F100T (REVERSE)@TSOP48 [SB247-B4806]  
AM29F100T@PSOP44 [SA638] AM29F100T@TSOP48 [SB247-B4806]  
AM29F160DB (REVERSE)@TSOP48 [SB247-B4806]  
AM29F160DB@TSOP48 [SB247-B4806]  
AM29F160DT (REVERSE)@TSOP48 [SB247-B4806]  
AM29F160DT@TSOP48 [SB247-B4806]  
AM29F200AB (REVERSE)@TSOP48 [SB247-B4806]  
AM29F200AB@PSOP44 [SA638] AM29F200AB@TSOP48 [SB247-B4806]  
AM29F200AT (REVERSE)@TSOP48 [SB247-B4806]  
AM29F200AT@PSOP44 [SA638] AM29F200AT@TSOP48 [SB247-B4806]  
AM29F200BB (REVERSE)@TSOP48 [SB247-B4806]  
AM29F200BB@PSOP44 [SA638] AM29F200BB@TSOP48 [SB247-B4806]  
AM29F200BT (REVERSE)@TSOP48 [SB247-B4806]  
AM29F200BT@PSOP44 [SA638] AM29F200BT@TSOP48 [SB247-B4806]  
AM29F400AB (REVERSE)@TSOP48 [SB247-B4806]  
AM29F400AB@PSOP44 [SA638] AM29F400AB@TSOP48 [SB247-B4806]  
AM29F400AT (REVERSE)@TSOP48 [SB247-B4806]  
AM29F400AT@PSOP44 [SA638] AM29F400AT@TSOP48 [SB247-B4806]  
AM29F400BB (REVERSE)@TSOP48 [SB247-B4806]  
AM29F400BB@PSOP44 [SA638] AM29F400BB@TSOP48 [SB247-B4806]  
AM29F400BT (REVERSE)@TSOP48 [SB247-B4806]  
AM29F400BT@PSOP44 [SA638] AM29F400BT@TSOP48 [SB247-B4806]  
AM29F800B (REVERSE)@TSOP48 [SB247-B4806]  
AM29F800B@PSOP44 [SA638] AM29F800B@TSOP48 [SB247-B4806]  
AM29F800BB (REVERSE)@TSOP48 [SB247-B4806]  
AM29F800BB@PSOP44 [SA638] AM29F800BB@TSOP48 [SB247-B4806]  
AM29F800BT (REVERSE)@TSOP48 [SB247-B4806]  
AM29F800BT@PSOP44 [SA638] AM29F800BT@TSOP48 [SB247-B4806]  
AM29F800T (REVERSE)@TSOP48 [SB247-B4806]  
AM29F800T@PSOP44 [SA638] AM29F800T@TSOP48 [SB247-B4806]  
AM29LL800B@TSOP48 [SB247-B4806] AM29LL800BB@TSOP48 [SB247-B4806]  
AM29LL800BT@TSOP48 [SB247-B4806] AM29LL800T@TSOP48 [SB247-B4806]  
AM29LV001BB (REVERSE)@TSOP32 [SA410T-B4001]  
AM29LV001BB@PLCC32 [SA015A1T]  
AM29LV001BB@TSOP32 [SA410T-B4001]  
AM29LV001BT (REVERSE)@TSOP32 [SA410T-B4001]  
AM29LV001BT@PLCC32 [SA015A1T]

AM29LV001BT@TSOP32 [SA410T-B4001]  
AM29LV002@TSOP40 [SA409T-B4002] AM29LV002B@TSOP40 [SA409T-B4002]  
AM29LV002BB@TSOP40 [SA409T-B4002]  
AM29LV002BT@TSOP40 [SA409T-B4002]  
AM29LV004B@TSOP40 [SA409T-B4002]  
AM29LV004BB@TSOP40 [SA409T-B4002]  
AM29LV004BT@TSOP40 [SA409T-B4002]  
AM29LV004T@TSOP40 [SA409T-B4002] AM29LV008B@TSOP40 [SA409T-B4002]  
AM29LV008BB@TSOP40 [SA409T-B4002]  
AM29LV008BT@TSOP40 [SA409T-B4002]  
AM29LV008T@TSOP40 [SA409T-B4002] AM29LV010B@PLCC32 [SA015A1T]  
AM29LV010B@TSOP32 [SA410T-B4001]  
AM29LV017B (REVERSE)@TSOP40 [SA409T-B4002]  
AM29LV017B@TSOP40 [SA409T-B4002]  
AM29LV017D (REVERSE)@TSOP40 [SA409T-B4002]  
AM29LV017D@TSOP40 [SA409T-B4002] AM29LV020B@PLCC32 [SA015A1T]  
AM29LV020B@TSOP32 [SA410T-B4001] AM29LV033C@TSOP40 [SA409T-B4002]  
AM29LV033MU@TSOP40 [SA409T-B4002]  
AM29LV040B@PLCC32 [SA015A1T] AM29LV040B@TSOP32 [SA410T-B4001]  
AM29LV040E@PLCC32 [SA015A1T] AM29LV040E@TSOP32 [SA410T-B4001]  
AM29LV040J@PLCC32 [SA015A1T] AM29LV040J@TSOP32 [SA410T-B4001]  
AM29LV065D@TSOP48 [SB247-B4806] AM29LV065MU@TSOP48 [SB247-B4806]  
AM29LV080@TSOP40 [SA409T-B4002] AM29LV081@TSOP40 [SA409T-B4002]  
AM29LV081B@TSOP40 [SA409T-B4002]  
AM29LV116BB@TSOP40 [SA409T-B4002]  
AM29LV116BT@TSOP40 [SA409T-B4002]  
AM29LV116DB@TSOP40 [SA409T-B4002]  
AM29LV116DT@TSOP40 [SA409T-B4002]  
AM29LV160BB (REVERSE)@TSOP48 [SB247-B4806]  
AM29LV160BB@PSOP44 [SA638] AM29LV160BB@TSOP48 [SB247-B4806]  
AM29LV160BT (REVERSE)@TSOP48 [SB247-B4806]  
AM29LV160BT@PSOP44 [SA638] AM29LV160BT@TSOP48 [SB247-B4806]  
AM29LV160DB (REVERSE)@TSOP48 [SB247-B4806]  
AM29LV160DB@PSOP44 [SA638] AM29LV160DB@TSOP48 [SB247-B4806]  
AM29LV160DT (REVERSE)@TSOP48 [SB247-B4806]  
AM29LV160DT@PSOP44 [SA638] AM29LV160DT@TSOP48 [SB247-B4806]  
AM29LV160DT@TSOP48 (slow) [SA247-B4806]  
AM29LV160MB (REVERSE)@TSOP48 [SB247-B4806]  
AM29LV160MB@PSOP44 [SA638] AM29LV160MB@TSOP48 [SB247-B4806]  
AM29LV160MT (REVERSE)@TSOP48 [SB247-B4806]  
AM29LV160MT@PSOP44 [SA638] AM29LV160MT@TSOP48 [SB247-B4806]  
AM29LV200B (REVERSE)@TSOP48 [SB247-B4806]  
AM29LV200B@PSOP44 [SA638] AM29LV200B@TSOP48 [SB247-B4806]  
AM29LV200BB (REVERSE)@TSOP48 [SB247-B4806]  
AM29LV200BB@PSOP44 [SA638] AM29LV200BB@TSOP48 [SB247-B4806]  
AM29LV200BT (REVERSE)@TSOP48 [SB247-B4806]  
AM29LV200BT@PSOP44 [SA638] AM29LV200BT@TSOP48 [SB247-B4806]  
AM29LV200T (REVERSE)@TSOP48 [SB247-B4806]  
AM29LV200T@PSOP44 [SA638] AM29LV200T@TSOP48 [SB247-B4806]  
AM29LV320DB@TSOP48 [SB247-B4806] AM29LV320DT@TSOP48 [SB247-B4806]  
AM29LV320FB@TSOP48 [SB247-B4806] AM29LV320FT@TSOP48 [SB247-B4806]  
AM29LV320MB@TSOP48 [SB247-B4806] AM29LV320MT@TSOP48 [SB247-B4806]  
AM29LV400B (REVERSE)@TSOP48 [SB247-B4806]

AM29LV400B@PSOP44 [SA638] AM29LV400B@TSOP48 [SB247-B4806]  
AM29LV400BB (REVERSE)@TSOP48 [SB247-B4806]  
AM29LV400BB@PSOP44 [SA638] AM29LV400BB@TSOP48 [SB247-B4806]  
AM29LV400BT (REVERSE)@TSOP48 [SB247-B4806]  
AM29LV400BT@PSOP44 [SA638] AM29LV400BT@TSOP48 [SB247-B4806]  
AM29LV400T (REVERSE)@TSOP48 [SB247-B4806]  
AM29LV400T@PSOP44 [SA638] AM29LV400T@TSOP48 [SB247-B4806]  
AM29LV640MB@TSOP48 [SB247-B4806] AM29LV640MT@TSOP48 [SB247-B4806]  
AM29LV641DH (REVERSE)@TSOP48 [SB247-B4806]  
AM29LV641DH@TSOP48 [SB247-B4806]  
AM29LV641DL (REVERSE)@TSOP48 [SB247-B4806]  
AM29LV641DL@TSOP48 [SB247-B4806]  
AM29LV641GH (REVERSE)@TSOP48 [SB247-B4806]  
AM29LV641GH@TSOP48 [SB247-B4806]  
AM29LV641GL (REVERSE)@TSOP48 [SB247-B4806]  
AM29LV641GL@TSOP48 [SB247-B4806]  
AM29LV641MH (REVERSE)@TSOP48 [SB247-B4806]  
AM29LV641MH@TSOP48 [SB247-B4806]  
AM29LV641ML (REVERSE)@TSOP48 [SB247-B4806]  
AM29LV641ML@TSOP48 [SB247-B4806]  
AM29LV800B (REVERSE)@TSOP48 [SB247-B4806]  
AM29LV800B@PSOP44 [SA638] AM29LV800B@TSOP48 [SB247-B4806]  
AM29LV800BB (REVERSE)@TSOP48 [SB247-B4806]  
AM29LV800BB@PSOP44 [SA638] AM29LV800BB@TSOP48 [SB247-B4806]  
AM29LV800BT (REVERSE)@TSOP48 [SB247-B4806]  
AM29LV800BT@PSOP44 [SA638] AM29LV800BT@TSOP48 [SB247-B4806]  
AM29LV800DB (REVERSE)@TSOP48 [SB247-B4806]  
AM29LV800DB@PSOP44 [SA638] AM29LV800DB@TSOP48 [SB247-B4806]  
AM29LV800DT (REVERSE)@TSOP48 [SB247-B4806]  
AM29LV800DT@PSOP44 [SA638] AM29LV800DT@TSOP48 [SB247-B4806]  
AM29LV800T (REVERSE)@TSOP48 [SB247-B4806]  
AM29LV800T@PSOP44 [SA638] AM29LV800T@TSOP48 [SB247-B4806]  
AM29PL160BB@PSOP44 [SA638] AM29PL160BB@TSOP48 [SB247-B4806]  
AM29PL160CB@PSOP44 [SA638] AM29PL160CB@TSOP48 [SB247-B4806]  
AM29PL160CT@PSOP44 [SA638] AM29PL160CT@TSOP48 [SB247-B4806]  
AM29SL160BB@TSOP48 [SB247-B4806] AM29SL160BT@TSOP48 [SB247-B4806]  
AM29SL160CB@TSOP48 [SB247-B4806] AM29SL160CT@TSOP48 [SB247-B4806]  
AM29SL400CB@TSOP48 [SB247-B4806] AM29SL400CT@TSOP48 [SB247-B4806]  
AM29SL800BB (REVERSE)@TSOP48 [SB247-B4806]  
AM29SL800BB@TSOP48 [SB247-B4806]  
AM29SL800BT (REVERSE)@TSOP48 [SB247-B4806]  
AM29SL800BT@TSOP48 [SB247-B4806]  
AM29SL800CB (REVERSE)@TSOP48 [SB247-B4806]  
AM29SL800CB@TSOP48 [SB247-B4806]  
AM29SL800CT (REVERSE)@TSOP48 [SB247-B4806]  
AM29SL800CT@TSOP48 [SB247-B4806]  
AM29SL800DB (REVERSE)@TSOP48 [SB247-B4806]  
AM29SL800DB@TSOP48 [SB247-B4806]  
AM29SL800DT (REVERSE)@TSOP48 [SB247-B4806]  
AM29SL800DT@TSOP48 [SB247-B4806] AM9716  
AM9732 AM9732A  
AM9764 AM9764@PLCC32 [SA015A1T]

## PLD

PALC16L8Q	PALC16L8Q@PLCC20 [SA001A-B2001]
PALC16L8Z	PALC16L8Z@PLCC20 [SA001A-B2001]
PALC16R4Q	PALC16R4Q@PLCC20 [SA001A-B2001]
PALC16R4Z	PALC16R4Z@PLCC20 [SA001A-B2001]
PALC16R6Q	PALC16R6Q@PLCC20 [SA001A-B2001]
PALC16R6Z	PALC16R6Z@PLCC20 [SA001A-B2001]
PALC16R8Q	PALC16R8Q@PLCC20 [SA001A-B2001]
PALC16R8Z	PALC16R8Z@PLCC20 [SA001A-B2001]
PALCE16V8H	PALCE16V8H@PLCC20 [SA001A-B2001]
PALCE16V8H@SOIC20 [SA404]	PALCE16V8Q
PALCE16V8Q@PLCC20 [SA001A-B2001]	PALCE16V8Q@SOIC20 [SA404]
PALCE16V8Z	PALCE16V8Z@PLCC20 [SA001A-B2001]
PALCE16V8Z@SOIC20 [SA404]	PALCE20V8H
PALCE20V8H@PLCC28 [SA008A]	PALCE20V8H@SOIC24 [SA620-B4807]
PALCE20V8Q	PALCE20V8Q@PLCC28 [SA008A]
PALCE20V8Q@SOIC24 [SA620-B4807]	PALLV16V8
PALLV16V8@PLCC20 [SA001A-B2001]	PALLV16V8@SOIC20 [SA404]
PALLV16V8Z	PALLV16V8Z@PLCC20 [SA001A-B2001]
PALLV16V8Z@SOIC20 [SA404]	

## MICROCONTROLLER

AM87C51	AM87C51@PLCC44 [SA244]
AM87C51@TQFP44 [SA675-B4805]	AM87C521
AM87C521@PLCC44 [SA244]	AM87C521@TQFP44 [SA675-B4805]
AM87C541	AM87C541@PLCC44 [SA244]
AM87C541@TQFP44 [SA675-B4805]	

## AMIC

### E (E) PROM/FRAM/NVRAM

A25L010	A25L010[150mil]@SOP8 [SA602A]
A25L010[209mil]@SOP8 [SA605B]	A25L010A
A25L010A@SOP8 [SA602A]	A25L010A@TSSOP8 [SA605B]
A25L010A@USON8 [SA724]	A25L010A@WSON8 [SA683]
A25L016	A25L016@SOP8 [SA605B]
A25L016T [SA684]	A25L016T@SOP16 [SA404]
A25L016T@SOP8(150mil) [SA602A]	A25L016T@SOP8(209mil) [SA605B]
A25L016T@WSON8 [SA683]	A25L016U [SA683]
A25L016U@SOP16 [SA404]	A25L016U@SOP8(150mil) [SA602A]
A25L016U@SOP8(209mil) [SA605B]	A25L016U@WSON8 [SA683]
A25L020	A25L020[150mil]@SOP8 [SA602A]
A25L020[209mil]@SOP8 [SA605B]	A25L020B
A25L020B[150mil]@SOP8 [SA602A]	A25L020B[209mil]@SOP8 [SA605B]
A25L020C	A25L020C@SOP8 [SA602A]
A25L020C@USON8 [SA724]	A25L020C@WSON8 [SA683]
A25L032	A25L032 (NEW)
A25L032 (NEW)@SOP16 [SA783]	A25L032 (NEW)@SOP8 [SA605B]

A25L032 (OTP)  
A25L032 (OTP)@SOP8 [SA605B]  
A25L032@SOP8 [SA605B]  
A25L032A@SOP16 [SA783]  
A25L040  
A25L040@SOP16 [SA404]  
A25L040A  
A25L040A@SOP8 (209 mil) [SA605B]  
A25L05P (Bottom)  
A25L05P (Bottom) [150mil]@SOP8 [SA602A]  
A25L05P (Bottom) [209mil]@SOP8 [SA605B]  
A25L05P (Top)  
A25L05P (Top) [150mil]@SOP8 [SA602A]  
A25L05P (Top) [209mil]@SOP8 [SA605B]  
A25L080  
A25L080@SOP16  
A25L080A  
A25L080A@SOP16  
A25L080B  
A25L080B@WSON8 [SA683]  
A25L10P (Bottom)@QFN8 [SA683]  
A25L10P (Bottom) [150mil]@SOP8 [SA602A]  
A25L10P (Bottom) [209mil]@SOP8 [SA605B]  
A25L10P (Top)  
A25L10P (Top) [150mil]@SOP8 [SA602A]  
A25L10P (Top) [209mil]@SOP8 [SA605B]  
A25L16P (Bottom Boot)@QFN8 [SA683]  
A25L16P (Bottom Boot)@QFN8 (ISP)  
A25L16P (Bottom Boot)@SOP16 [SA783]  
A25L16P (Bottom Boot)@SOP16 (ISP)  
A25L16P (Bottom Boot)@SOP8 [SA605B]  
A25L16P (Bottom Boot)@SOP8 (ISP)  
A25L16P (Top Boot)@QFN8 (ISP)  
A25L16P (Top Boot)@SOP16 (ISP)  
A25L16P (Top Boot)@SOP8 (ISP)  
A25L20P (Bottom)@QFN8 [SA683]  
A25L20P (Bottom) [150mil]@SOP8 [SA602A]  
A25L20P (Bottom) [209mil]@SOP8 [SA605B]  
A25L20P (Top)  
A25L20P (Top) [150mil]@SOP8 [SA602A]  
A25L20P (Top) [209mil]@SOP8 [SA605B]  
A25L40P (Bottom)  
A25L40P (Bottom)@SOP16  
A25L40P (Top)  
A25L40P (Top)@SOP16  
A25L42P (Bottom Boot)  
A25L42P (Bottom Boot)@QFN8 [SA683]  
A25L42P (Bottom Boot)@SOP16 [SA404]  
A25L42P (Bottom Boot)@SOP8 [SA602A]  
A25L42P (Top Boot)  
A25L42P (Top Boot)@SOP16 [SA404]  
A25L512  
A25L512 [209mil]@SOP8 [SA605B]

A25L032 (OTP)@SOP16 [SA404]  
A25L032@SOP16 [SA783]  
A25L032A  
A25L032A@SOP8 [SA605B]  
A25L040@QFN8 [SA683]  
A25L040@SOP8 [SA602A]  
A25L040A@SOP8 (150 mil) [SA602A]  
A25L040A@WSON8 [SA683]  
A25L05P (Bottom)@QFN8 [SA683]  
A25L05P (Top)@QFN8 [SA683]  
A25L080@QFN8 [SA683]  
A25L080@SOP8 [SA605B]  
A25L080A@QFN8 [SA683]  
A25L080A@SOP8 [SA605B]  
A25L080B@SOP8 [SA605B]  
A25L10P (Bottom)  
A25L10P (Top)@QFN8 [SA683]  
A25L16P (Top Boot)@QFN8 [SA684]  
A25L16P (Top Boot)@SOP16 [SA783]  
A25L16P (Top Boot)@SOP8 [SA605B]  
A25L20P (Bottom)  
A25L20P (Top)@QFN8 [SA683]  
A25L40P (Bottom)@QFN8 [SA683]  
A25L40P (Bottom)@SOP8 [SA602A]  
A25L40P (Top)@QFN8 [SA683]  
A25L40P (Top)@SOP8 [SA602A]  
A25L42P (Top Boot)@QFN8 [SA683]  
A25L42P (Top Boot)@SOP8 [SA602A]  
A25L512 [150mil]@SOP8 [SA602A]  
A25L5120

A25L5120[150mil]@SOP8 [SA602A]  
A25L512A  
A25L512A@TSSOP8 [SA605B]  
A25L512A@WSON8 [SA683]  
A25L80P@QFN8 [SA683]  
A25L80P@SOP8 [SA605B]  
A25L82P(Bottom Boot)@QFN8 [SA683]  
A25L82P(Bottom Boot)@SOP16 [SA404]  
A25L82P(Bottom Boot)@SOP8 [SA605B]  
A25L82P(Top Boot)  
A25L82P(Top Boot)@SOP16 [SA404]  
A25LQ032A  
A25LQ032A@SOP8 [SA605B]  
A25LQ16@SOP8 [SA605B]  
A25LQ32B  
A25LQ32B@WSON8 [SA683]  
A25LQ64@SOP16 [SA783]  
A25LQ64@WSON8 [SA683]  
A25LQ64N@SOP16 [SA783]  
A25LQ64N@WSON8 [SA683]  
A25LS080@QFN8 [SA683]  
A25LS080@SOP8 [SA605B]  
A25LS512[150mil]@SOP8 [SA602A]  
A25LS5120  
A25LS5120[209mil]@SOP8 [SA605B]  
A27020@PLCC32 [SA015A1T]  
A27020L  
A27020L@TSOP32 [SA410T-B4001]  
A275308@PLCC32 [SA015A1T]  
A276308(E)  
A276308(E)@SOIC28 [SA404]  
A276308@SOIC28 [SA404]  
A276308A(L)  
A276308A(L)@SOIC28 [SA404]  
A276308A@SOIC28 [SA404]  
A277308@PLCC32 [SA015A1T]  
A277308A@PLCC32 [SA015A1T]  
A278308@PLCC32 [SA015A1T]  
A278308A(L)  
A278308A@PLCC32 [SA015A1T]  
A279308@PLCC32 [SA015A1T]  
A290011T@PLCC32 [SA015A1T]  
A290011U  
A290011U@TSOP32 [SA410T-B4001]  
A29001T@PLCC32 [SA015A1T]  
A29001U  
A29001U@TSOP32 [SA410T-B4001]  
A290021T@PLCC32 [SA015A1T]  
A290021U  
A290021U@TSOP32 [SA410T-B4001]  
A29002T@PLCC32 [SA015A1T]  
A29002U  
A29002U@TSOP32 [SA410T-B4001]  
A25L5120[209mil]@SOP8 [SA605B]  
A25L512A@SOP8 [SA602A]  
A25L512A@USON8 [SA724]  
A25L80P  
A25L80P@SOP16  
A25L82P(Bottom Boot)  
A25L82P(Top Boot)@QFN8 [SA683]  
A25L82P(Top Boot)@SOP8 [SA605B]  
A25LQ032A@SOP16 [SA783]  
A25LQ16  
A25LQ16@WSON8 [SA683]  
A25LQ32B@SOP8 [SA605B]  
A25LQ64@BGA24 [TA088]  
A25LQ64@SOP8 [SA605B]  
A25LQ64N@BGA24 [TA088]  
A25LQ64N@SOP8 [SA605B]  
A25LS080  
A25LS080@SOP16 [SA404]  
A25LS512  
A25LS512[209mil]@SOP8 [SA605B]  
A25LS5120[150mil]@SOP8 [SA602A]  
A27020  
A27020@TSOP32 [SA410T-B4001]  
A27020L@PLCC32 [SA015A1T]  
A275308  
A276308  
A276308(E)@PLCC32 [SA015A1T]  
A276308@PLCC32 [SA015A1T]  
A276308A  
A276308A(L)@PLCC32 [SA015A1T]  
A276308A@PLCC32 [SA015A1T]  
A277308  
A277308A  
A278308  
A278308A  
A278308A(L)@PLCC32 [SA015A1T]  
A279308  
A290011T  
A290011T@TSOP32 [SA410T-B4001]  
A290011U@PLCC32 [SA015A1T]  
A29001T  
A29001T@TSOP32 [SA410T-B4001]  
A29001U@PLCC32 [SA015A1T]  
A290021T  
A290021T@TSOP32 [SA410T-B4001]  
A290021U@PLCC32 [SA015A1T]  
A29002T  
A29002T@TSOP32 [SA410T-B4001]  
A29002U@PLCC32 [SA015A1T]  
A29010

A29010@PLCC32 [SA015A1T]  
A29040  
A29040@TSOP32 [SA410T-B4001]  
A29040A@PLCC32 [SA015A1T]  
A29040B  
A29040B@TSOP32 [SA410T-B4001]  
A29040C@PLCC32 [SA015A1T]  
A29160TM@PSOP44 [SA638]  
A29160UM@PSOP44 [SA638]  
A29400TM@PSOP44 [SA638]  
A29400UM@PSOP44 [SA638]  
A29512  
A29512@TSOP32 [SA410T-B4001]  
A29512A@PLCC32 [SA015A1T]  
A29800TM@PSOP44 [SA638]  
A29800UM@PSOP44 [SA638]  
A29801TM@PSOP44 [SA638]  
A29801UM@PSOP44 [SA638]  
A29DL162TV@TSOP48 [SB247-B4806]  
A29DL163TV@TSOP48 [SB247-B4806]  
A29DL164TV@TSOP48 [SB247-B4806]  
A29DL320FTV@TSOP48 [SB247-B4806]  
A29DL322TV@TSOP48 [SB247-B4806]  
A29DL323TV(olD)@TSOP48 [SB247-B4806]  
A29DL323TV@TSOP48 [SB247-B4806]  
A29DL323UV(olD)@TSOP48 [SB247-B4806]  
A29DL323UV@TSOP48 [SB247-B4806]  
A29DL324TV(olD)@TSOP48 [SB247-B4806]  
A29DL324TV@TSOP48 [SB247-B4806]  
A29DL324UV(olD)@TSOP48 [SB247-B4806]  
A29DL324UV@TSOP48 [SB247-B4806]  
A29L004ATV@TSOP32 [SA410T-B4001]  
A29L004ATY@VSOP32 [SA620-B4807]  
A29L004AUV@TSOP32 [SA410T-B4001]  
A29L004AUY@VSOP32 [SA620-B4807]  
A29L004T@TSOP32 [SA410T-B4001]  
A29L004T@VSOP32 [SA620-B4807]  
A29L004U@TSOP32 [SA410T-B4001]  
A29L004U@VSOP32 [SA620-B4807]  
A29L008AUV@TSOP40 [SA409T-B4002]  
A29L008U@TSOP40 [SA409T-B4002]  
A29L040@PLCC32 [SA015A1T]  
A29L040@VSOP32 [SA620-B4807]  
A29L160ATV@TSOP48 [SB247-B4806]  
A29L160AUV@TSOP48 [SB247-B4806]  
A29L160AUV@TSOP48(slow) [SB247-B4806]  
A29L160BTV@TSOP48 [SB247-B4806]  
A29L160FTV@TSOP48 [SB247-B4806]  
A29L160HTV@TSOP48 [SB247-B4806]  
A29L160TM@PSOP44 [SA638]  
A29L160UM@PSOP44 [SA638]  
A29L320ATV@TSOP48 [SB247-B4806]  
A29L400ATM@PSOP44 [SA638]  
A29010@TSOP32 [SA410T-B4001]  
A29040@PLCC32 [SA015A1T]  
A29040A  
A29040A@TSOP32 [SA410T-B4001]  
A29040B@PLCC32 [SA015A1T]  
A29040C  
A29040C@TSOP32 [SA410T-B4001]  
A29160TV@TSOP48 [SB247-B4806]  
A29160UV@TSOP48 [SB247-B4806]  
A29400TV@TSOP48 [SB247-B4806]  
A29400UV@TSOP48 [SB247-B4806]  
A29512@PLCC32 [SA015A1T]  
A29512A  
A29512A@TSOP32 [SA410T-B4001]  
A29800TV@TSOP48 [SB247-B4806]  
A29800UV@TSOP48 [SB247-B4806]  
A29801TV@TSOP48 [SB247-B4806]  
A29801UV@TSOP48 [SB247-B4806]  
A29DL162UV@TSOP48 [SB247-B4806]  
A29DL163UV@TSOP48 [SB247-B4806]  
A29DL164UV@TSOP48 [SB247-B4806]  
A29DL320FUV@TSOP48 [SB247-B4806]  
A29DL322UV@TSOP48 [SB247-B4806]  
A29L004ATL@PLCC32 [SA015A1T]  
A29L004ATW@TSOP40 [SA409T-B4002]  
A29L004AUL@PLCC32 [SA015A1T]  
A29L004AUW@TSOP40 [SA409T-B4002]  
A29L004T@PLCC32 [SA015A1T]  
A29L004T@TSOP40 [SA409T-B4002]  
A29L004U@PLCC32 [SA015A1T]  
A29L004U@TSOP40 [SA409T-B4002]  
A29L008ATV@TSOP40 [SA409T-B4002]  
A29L008T@TSOP40 [SA409T-B4002]  
A29L040  
A29L040@TSOP32 [SA410T-B4001]  
A29L160ATM@PSOP44 [SA638]  
A29L160AUM@PSOP44 [SA638]  
A29L160BUV@TSOP48 [SB247-B4806]  
A29L160FUV@TSOP48 [SB247-B4806]  
A29L160HUV@TSOP48 [SB247-B4806]  
A29L160TV@TSOP48 [SB247-B4806]  
A29L160UV@TSOP48 [SB247-B4806]  
A29L320AUV@TSOP48 [SB247-B4806]  
A29L400ATV@TSOP48 [SB247-B4806]

A29L400AUM@PSOP44 [SA638]  
A29L400TM@PSOP44 [SA638]  
A29L400UM@PSOP44 [SA638]  
A29L800ATM@PSOP44 [SA638]  
A29L800AUM@PSOP44 [SA638]  
A29L800HTM@PSOP44 [SA638]  
A29L800HUM@PSOP44 [SA638]  
A29L800TM@PSOP44 [SA638]  
A29L800UM@PSOP44 [SA638]  
A49LF004@PLCC32 [SA015A1T]  
A49LF004M@PLCC32 [SA015A1T]  
A49LF040AT@PLCC32 [SA015A1T]  
A49LF040T@PLCC32 [SA015A1T]  
A50FW040@PLCC32 [SA015A1T]  
A50FW040M@PLCC32 [SA015A1T]  
A50LPW040@PLCC32 [SA015A1T]  
A617308  
A61L5308  
A623308 (M)  
A623308 (V)@TSOP28 [SA430T-B4003]  
A625308 (R)@TSOP28 [SA430T-B4003]  
A62L256  
A62L256 (R)@TSOP28 [SA430T-B4003]  
A62S6308 (M)  
A62S7308A (M)  
A62S8308A (M)  
A62W5308 (M)  
A62W5308 (R)@TSOP28 [SA430T-B4003]  
A62W5308 (V)@TSOP28 [SA430T-B4003]

A29L400AUV@TSOP48 [SB247-B4806]  
A29L400TV@TSOP48 [SB247-B4806]  
A29L400UV@TSOP48 [SB247-B4806]  
A29L800ATV@TSOP48 [SB247-B4806]  
A29L800AUV@TSOP48 [SB247-B4806]  
A29L800HTV@TSOP48 [SB247-B4806]  
A29L800HUV@TSOP48 [SB247-B4806]  
A29L800TV@TSOP48 [SB247-B4806]  
A29L800UV@TSOP48 [SB247-B4806]  
A49LF004@VSOP32 [SA620-B4807]  
A49LF004M@VSOP32 [SA620-B4807]  
A49LF040AT@VSOP32 [SA620-B4807]  
A49LF040T@VSOP32 [SA620-B4807]  
A50FW040@VSOP32 [SA620-B4807]  
A50FW040M@VSOP32 [SA620-B4807]  
A50LPW040@VSOP32 [SA620-B4807]  
A617308@TSOP32  
A61L5308@TSOP28 [SA430T-B4003]  
A623308 (R)@TSOP28 [SA430T-B4003]  
A625308 (M)  
A625308 (V)@TSOP28 [SA430T-B4003]  
A62L256 (M)  
A62L256 (V)@TSOP28 [SA430T-B4003]  
A62S6308 (X)@TSOP32  
A62S7308A (X)@TSOP32  
A62S8308A (X)@TSOP32

## AMS

### MICROCONTROLLER

AS5030 [SA643]  
AS5032 [SA643]  
AS5034 [SA643]  
AS5031 [SA643]  
AS5033 [SA643]  
AS5035 [SA643]

## ANACHIP

### E (E) PROM/FRAM/NVRAM

27CX010  
27CX010@TSOP32 [SA410T-B4001]  
27CX321  
27CX641  
93C46  
93C46A  
93C56A  
93C66A  
93CX46  
93CX56  
27CX010@PLCC32 [SA015A1T]  
27CX256  
27CX322  
27CX642  
93C46@SOIC8 [SA602A]  
93C46A@SOIC8 [SA602A]  
93C56A@SOIC8 [SA602A]  
93C66A@SOIC8 [SA602A]  
93CX46@SOIC8 [SA602A]  
93CX56@SOIC8 [SA602A]

93CX66  
AM24LC02  
AM24LC02@TSSOP8 [SA643]  
AM24LC04@SOIC8 [SA602A]  
AM24LC08  
AM24LC08@TSSOP8 [SA643]  
AM24LC16@SOIC8 [SA602A]  
AM24LC21  
AM24LC21@TSSOP8 [SA643]  
AM24LC21B@SOIC8 [SA602A]  
AM93LC46(08bit)  
AM93LC46(08bit)@TSOP8 [SA643]  
AM93LC46(16bit)@SOIC8 [SA602A]  
AM93LC56(08bit)  
AM93LC56(08bit)@TSOP8 [SA643]  
AM93LC56(16bit)@SOIC8 [SA602A]  
AM93LC66(08bit)  
AM93LC66(08bit)@TSOP8 [SA643]  
AM93LC66(16bit)@SOIC8 [SA602A]  
AM93LC86(08bit)  
AM93LC86(08bit)@TSOP8 [SA643]  
AM93LC86(16bit)@SOIC8 [SA602A]

93CX66@SOIC8 [SA602A]  
AM24LC02@SOIC8 [SA602A]  
AM24LC04  
AM24LC04@TSSOP8 [SA643]  
AM24LC08@SOIC8 [SA602A]  
AM24LC16  
AM24LC16@TSSOP8 [SA643]  
AM24LC21@SOIC8 [SA602A]  
AM24LC21B  
AM24LC21B@TSSOP8 [SA643]  
AM93LC46(08bit)@SOIC8 [SA602A]  
AM93LC46(16bit)  
AM93LC46(16bit)@TSOP8 [SA643]  
AM93LC56(08bit)@SOIC8 [SA602A]  
AM93LC56(16bit)  
AM93LC56(16bit)@TSOP8 [SA643]  
AM93LC66(08bit)@SOIC8 [SA602A]  
AM93LC66(16bit)  
AM93LC66(16bit)@TSOP8 [SA643]  
AM93LC86(08bit)@SOIC8 [SA602A]  
AM93LC86(16bit)  
AM93LC86(16bit)@TSOP8 [SA643]

## PLD

PA7024  
PA7024(JN)@PLCC28 [SA008A]  
PA7140  
PA7140@TQFP44 [SA245A-B4805]  
PA7540(J)@PLCC28 [SA008A]  
PA7572  
PA7572@TQFP44 [SA245A-B4805]  
PEEL18CV8Z@PLCC20 [SA001A-B2001]  
PEEL18CV8Z@TSOP20 [SA026]  
PEEL18LV8Z@PLCC20 [SA001A-B2001]  
PEEL18LV8Z@TSOP20 [SA026]  
PEEL22CV10A@PLCC28 [SA008A]  
PEEL22CV10A@TSOP24 [SA026]  
PEEL22CV10A+@PLCC28 [SA008A]  
PEEL22CV10A+@TSOP24 [SA026]  
PEEL22CV10A++@PLCC28 [SA008A]  
PEEL22CV10A++@TSOP24 [SA026]  
PEEL22CV10AZ@PLCC28 [SA008A]  
PEEL22CV10AZ@TSOP24 [SA026]  
PEEL22CV10AZ+@PLCC28 [SA008A]  
PEEL22CV10AZ+@TSOP24 [SA026]  
PEEL22CV10AZ++@PLCC28 [SA008A]  
PEEL22CV10AZ++@TSOP24 [SA026]  
PEEL22LV10AZ@PLCC28 [SA008A]  
PEEL22LV10AZ@TSOP24 [SA026]  
PEEL22LV10AZ+@PLCC28 [SA008A]  
PEEL22LV10AZ+@TSOP24 [SA026]

PA7024(J)@PLCC28 [SA008A]  
PA7024@SOIC24 [SA404]  
PA7140@PLCC44 [SA244]  
PA7540  
PA7540(JN)@PLCC28 [SA008A]  
PA7572@PLCC44 [SA244]  
PEEL18CV8Z  
PEEL18CV8Z@SOIC20 [SA404]  
PEEL18LV8Z  
PEEL18LV8Z@SOIC20 [SA404]  
PEEL22CV10A  
PEEL22CV10A@SOIC24 [SA404]  
PEEL22CV10A+  
PEEL22CV10A+@SOIC24 [SA404]  
PEEL22CV10A++  
PEEL22CV10A++@SOIC24 [SA404]  
PEEL22CV10AZ  
PEEL22CV10AZ@SOIC24 [SA404]  
PEEL22CV10AZ+  
PEEL22CV10AZ+@SOIC24 [SA404]  
PEEL22CV10AZ++  
PEEL22CV10AZ++@SOIC24 [SA404]  
PEEL22LV10AZ  
PEEL22LV10AZ@SOIC24 [SA404]  
PEEL22LV10AZ+  
PEEL22LV10AZ+@SOIC24 [SA404]  
PEEL22LV10AZ++

PEEL22LV10AZ++@PLCC28 [SA008A]  
PEEL22LV10AZ++@TSOP24 [SA026]

PEEL22LV10AZ++@SOIC24 [SA404]

## APLUS FLASH

### E (E) PROM/FRAM/NVRAM

AF24BC01	AF24BC01@SOIC8 [SA602A]
AF24BC01@TSSOP8 [SA643]	AF24BC02
AF24BC02@SOIC8 [SA602A]	AF24BC02@TSSOP8 [SA643]
AF24BC04	AF24BC04@SOIC8 [SA602A]
AF24BC04@TSSOP8 [SA643]	AF24BC08
AF24BC08@SOIC8 [SA602A]	AF24BC08@TSSOP8 [SA643]
AF24BC128	AF24BC128@SOIC8 [SA602A]
AF24BC128@TSOP8 [SA643]	AF24BC16
AF24BC16@SOIC8 [SA602A]	AF24BC16@TSSOP8 [SA643]
AF24BC256	AF24BC256@SOIC8 [SA602A]
AF24BC256@TSOP8 [SA643]	AF24BC32
AF24BC32@SOIC8 [SA602A]	AF24BC32@TSOP8 [SA643]
AF24BC64	AF24BC64@SOIC8 [SA602A]
AF24BC64@TSOP8 [SA643]	AF24C128
AF24C128@SOIC8 [SA602A]	AF24C128@TSOP8 [SA643]
AF24C256	AF24C256@SOIC8 [SA602A]
AF24C256@TSOP8 [SA643]	AF24C32
AF24C32@SOIC8 [SA602A]	AF24C32@TSOP8 [SA643]
AF24C64	AF24C64@SOIC8 [SA602A]
AF24C64@TSOP8 [SA643]	AF25BC08
AF25BC08@SOIC8 [SA602A]	AF25BC08@TSOP8 [SA643]
AF25BC128	AF25BC128@SOIC8 [SA602A]
AF25BC128@TSOP8 [SA643]	AF25BC16
AF25BC16@SOIC8 [SA602A]	AF25BC16@TSOP8 [SA643]
AF25BC256	AF25BC256@SOIC8 [SA602A]
AF25BC256@TSOP8 [SA643]	AF25BC32
AF25BC32@SOIC8 [SA602A]	AF25BC32@TSOP8 [SA643]
AF25BC64	AF25BC64@SOIC8 [SA602A]
AF25BC64@TSOP8 [SA643]	AF93BC46 (08bit)
AF93BC46 (08bit)@SOIC8 [SA602A]	AF93BC46 (08bit)@TSOP8 [SA643]
AF93BC46 (16bit)	AF93BC46 (16bit)@SOIC8 [SA602A]
AF93BC46 (16bit)@TSOP8 [SA643]	AF93BC56 (08bit)
AF93BC56 (08bit)@SOIC8 [SA602A]	AF93BC56 (08bit)@TSOP8 [SA643]
AF93BC56 (16bit)	AF93BC56 (16bit)@SOIC8 [SA602A]
AF93BC56 (16bit)@TSOP8 [SA643]	AF93BC66 (08bit)
AF93BC66 (08bit)@SOIC8 [SA602A]	AF93BC66 (08bit)@TSOP8 [SA643]
AF93BC66 (16bit)	AF93BC66 (16bit)@SOIC8 [SA602A]
AF93BC66 (16bit)@TSOP8 [SA643]	AF93BC86 (08bit)
AF93BC86 (08bit)@SOIC8 [SA602A]	AF93BC86 (08bit)@TSOP8 [SA643]
AF93BC86 (16bit)	AF93BC86 (16bit)@SOIC8 [SA602A]
AF93BC86 (16bit)@TSOP8 [SA643]	AF93C46 (08bit)
AF93C46 (08bit)@SOIC8 [SA602A]	AF93C46 (08bit)@TSOP8 [SA643]
AF93C46 (16bit)	AF93C46 (16bit)@SOIC8 [SA602A]
AF93C46 (16bit)@TSOP8 [SA643]	AF93C56 (08bit)
AF93C56 (08bit)@SOIC8 [SA602A]	AF93C56 (08bit)@TSOP8 [SA643]

AF93C56 (16bit)  
AF93C56 (16bit)@TSOP8 [SA643]  
AF93C66 (08bit)@SOIC8 [SA602A]  
AF93C66 (16bit)  
AF93C66 (16bit)@TSOP8 [SA643]  
AF93C86 (08bit)@SOIC8 [SA602A]  
AF93C86 (16bit)  
AF93C86 (16bit)@TSOP8 [SA643]

AF93C56 (16bit)@SOIC8 [SA602A]  
AF93C66 (08bit)  
AF93C66 (08bit)@TSOP8 [SA643]  
AF93C66 (16bit)@SOIC8 [SA602A]  
AF93C86 (08bit)  
AF93C86 (08bit)@TSOP8 [SA643]  
AF93C86 (16bit)@SOIC8 [SA602A]

## ARTSCHIP

### E (E) PROM/FRAM/NVRAM

24AA02  
24AA02@MSOP8 [SA666]  
24AA02@SOT5 [SA717]  
24LC01A  
24LC01A@SOIC8 [SA602A]  
24LC01A@TSSOP8 [SA643]  
24LC01B@SOIC8 [SA602A]  
24LC01B@TSSOP8 [SA643]  
24LC02A@MAP8  
24LC02A@SOT5 [SA717]  
24LC02B  
24LC02B@MSOP8 [SA666]  
24LC02B@SOT5 [SA717]  
24LC04A  
24LC04A@SOIC8 [SA602A]  
24LC04A@TSSOP8 [SA643]  
24LC04B@DFN8 [SA724]  
24LC04B@SOIC8 [SA602A]  
24LC04B@TSSOP8 [SA643]  
24LC08A@MAP8  
24LC08A@SOT5 [SA717]  
24LC08B  
24LC08B@MSOP8 [SA666]  
24LC08B@SOT5 [SA717]  
24LC16A  
24LC16A@SOIC8 [SA602A]  
24LC16A@TSSOP8 [SA643]  
24LC256B@MSOP8 [SA666]  
24LC256B@TSSOP8 [SA643]  
24LC32@SOIC14 [SA026]  
24LC32@TSSOP8 [SA643]  
24LC64@SOIC14 [SA026]  
24LC64@TSSOP8 [SA643]

24AA02@DFN8 [SA724]  
24AA02@SOIC8 [SA602A]  
24AA02@TSSOP8 [SA643]  
24LC01A@MAP8  
24LC01A@SOT5 [SA717]  
24LC01B  
24LC01B@SOT5 [SA717]  
24LC02A  
24LC02A@SOIC8 [SA602A]  
24LC02A@TSSOP8 [SA643]  
24LC02B@DFN8 [SA724]  
24LC02B@SOIC8 [SA602A]  
24LC02B@TSSOP8 [SA643]  
24LC04A@MAP8  
24LC04A@SOT5 [SA717]  
24LC04B  
24LC04B@MSOP8 [SA666]  
24LC04B@SOT5 [SA717]  
24LC08A  
24LC08A@SOIC8 [SA602A]  
24LC08A@TSSOP8 [SA643]  
24LC08B@DFN8 [SA724]  
24LC08B@SOIC8 [SA602A]  
24LC08B@TSSOP8 [SA643]  
24LC16A@MAP8  
24LC16A@SOT5 [SA717]  
24LC256B  
24LC256B@SOIC8 [SA602A]  
24LC32  
24LC32@SOIC8 [SA602A]  
24LC64  
24LC64@SOIC8 [SA602A]

## ASAHI KASEI (AKM)

### E (E) PROM/FRAM/NVRAM

AK27CX321

AK27CX322

AK27CX641

AK6002A (F) @SOP8 [SA602A]  
AK6003A (V) @TSSOP8 [SA643]  
AK6004A (M) @SSOP8 [SA605B]  
AK6010A (F) @SOP8 [SA602A]  
AK6416A (M) @SSOP8 [SA026]  
AK6420A (F) @SOP8 [SA602A]  
AK6420B (H) @MSOP8 [SA666]  
AK6440A (M) @SSOP8 [SA026]  
AK6480A (F) @SOP8 [SA602A]  
AK6480B (H) @MSOP8 [SA666]  
AK6480C (H) @MSOP8 [SA666]  
AK6480C (M) @SSOP8 [SA026]  
AK6481C (M) @SSOP8 [SA026]  
AK6508C (U) @USON8  
AK6510C (M) @SSOP8 [SA643]  
AK6512C (M) @SSOP8 [SA643]  
AK6514C (N) @QFN20 [SA692]  
AK93C10A (F) @SOP8 [SA602A]  
AK93C45  
AK93C45A (F) @SOP8 [SA602A]  
AK93C45A (V) @TSSOP8 [SA643]  
AK93C45B (L) @SON8 [\$\$\$\$\$]  
AK93C45C (U) @USON8 [\$\$\$\$\$]  
AK93C45L (F) @SOP8 [SA602A]  
AK93C46 (F) @SOP8 [SA602A]  
AK93C46A (NF) @SOP8 [SA602A]  
AK93C46B (H) @MSOP8 [SA666]  
AK93C46C (T) @MSOP8 [SA666]  
AK93C46L  
AK93C51A (V) @TSSOP8 [SA643]  
AK93C55 (F) @SOP8 [SA602A]  
AK93C55A (NF) @SOP8 [SA602A]  
AK93C55B (H) @MSOP8 [SA666]  
AK93C55C (T) @MSOP8 [SA666]  
AK93C55L  
AK93C56  
AK93C56A (F) @SOP8 [SA602A]  
AK93C56A (V) @TSSOP8 [SA643]  
AK93C56B (L) @SON8 [\$\$\$\$\$]  
AK93C56C (U) @USON8 [\$\$\$\$\$]  
AK93C56L (F) @SOP8 [SA602A]  
AK93C65  
AK93C65A (F) @SOP8 [SA602A]  
AK93C65A (V) @TSSOP8 [SA643]  
AK93C65B (L) @SON8 [\$\$\$\$\$]  
AK93C65C (U) @USON8 [\$\$\$\$\$]  
AK93C65L (F) @SOP8 [SA602A]  
AK93C66 (F) @SOP8 [SA602A]  
AK93C66A (NF) @SOP8 [SA602A]  
AK93C66B (H) @MSOP8 [SA666]  
AK93C66C (T) @MSOP8 [SA666]  
AK93C66L

AK27CX642

AK6002A (V) @TSSOP8 [SA643]  
AK6004A (F) @SOP8 [SA602A]  
AK6008A (F) @SOP8 [SA602A]  
AK6012A (F) @SOP8 [SA602A]  
AK6416C (F) @SOP8 [SA602A]  
AK6420A (M) @SSOP8 [SA026]  
AK6440A (F) @SOP8 [SA602A]  
AK6440B (H) @MSOP8 [SA666]  
AK6480A (M) @SSOP8 [SA026]  
AK6480C (F) @SOP8 [SA602A]  
AK6480C (L) @SON8  
AK6481C (H) @MSOP8 [SA666]  
AK6508C (T) @MSOP8 [SA666]  
AK6510C (L) @SONW8  
AK6512C (L) @SONW8  
AK6514C (F) @SOP8 [SA602]  
AK6516C (F) @SOP8 [SA602]  
AK93C41A (V) @TSSOP8 [SA643]  
AK93C45 (F) @SOP8 [SA602A]  
AK93C45A (NF) @SOP8 [SA602A]  
AK93C45B (H) @MSOP8 [SA666]  
AK93C45C (T) @MSOP8 [SA666]  
AK93C45L  
AK93C46  
AK93C46A (F) @SOP8 [SA602A]  
AK93C46A (V) @TSSOP8 [SA643]  
AK93C46B (L) @SON8 [\$\$\$\$\$]  
AK93C46C (U) @USON8 [\$\$\$\$\$]  
AK93C46L (F) @SOP8 [SA602A]  
AK93C55  
AK93C55A (F) @SOP8 [SA602A]  
AK93C55A (V) @TSSOP8 [SA643]  
AK93C55B (L) @SON8 [\$\$\$\$\$]  
AK93C55C (U) @USON8 [\$\$\$\$\$]  
AK93C55L (F) @SOP8 [SA602A]  
AK93C56 (F) @SOP8 [SA602A]  
AK93C56A (NF) @SOP8 [SA602A]  
AK93C56B (H) @MSOP8 [SA666]  
AK93C56C (T) @MSOP8 [SA666]  
AK93C56L  
AK93C61A (V) @TSSOP8 [SA643]  
AK93C65 (F) @SOP8 [SA602A]  
AK93C65A (NF) @SOP8 [SA602A]  
AK93C65B (H) @MSOP8 [SA666]  
AK93C65C (T) @MSOP8 [SA666]  
AK93C65L  
AK93C66  
AK93C66A (F) @SOP8 [SA602A]  
AK93C66A (V) @TSSOP8 [SA643]  
AK93C66B (L) @SON8 [\$\$\$\$\$]  
AK93C66C (U) @USON8 [\$\$\$\$\$]  
AK93C66L (F) @SOP8 [SA602A]

AK93C75  
AK93C75A (F)@SOP8 [SA602A]  
AK93C75A (V)@TSSOP8 [SA643]  
AK93C75L  
AK93C85  
AK93C85L  
AK93C95A (F)@SOP8 [SA602A]  
AK9824 (M)@SSOP8 [SA026]

AK93C75 (F)@SOP8 [SA602A]  
AK93C75A (NF)@SOP8 [SA602A]  
AK93C75B (H)@MSOP8 [SA666]  
AK93C75L (F)@SOP8 [SA602A]  
AK93C85 (F)@SOP8 [SA602A]  
AK93C85L (F)@SOP8 [SA602A]  
AK9822 (M)@SSOP8 [SA026]  
AK9844@SOIC14 [SA602]

## ASD

### E (E) PROM/FRAM/NVRAM

AE29F1008

AE29F2008

## ASI

### E (E) PROM/FRAM/NVRAM

AS58C1001  
AS58C1001@SSOP32 [SA687]

AS58C1001@PLCC32 [SA015A1T]

## Asic Microelectronics

### E (E) PROM/FRAM/NVRAM

AX24C02@SOP8 [SA602A]  
AX24C08@SOP8 [SA602A]

AX24C04@SOP8 [SA602A]  
AX24C16@SOP8 [SA602A]

## ASP

### MICROCONTROLLER

AP827C51  
AP827C52  
AP827C54  
AP827C58

AP827C51@PLCC44 [SA244]  
AP827C52@PLCC44 [SA244]  
AP827C54@PLCC44 [SA244]  
AP827C58@PLCC44 [SA244]

## ASTIGP-MICROCHIP

### MICROCONTROLLER

PIC16F616  
PIC16F616@SOIC14 [SA602]

PIC16F616@QFN16 [SA727]  
PIC16F616@TSSOP14 [SA026]

## ATC

### E (E) PROM/FRAM/NVRAM

ATC24C02	ATC24C02@SOIC8 [SA602A]
ATC24C02@TSSOP8 [SA643]	ATC24C04
ATC24C04@SOIC8 [SA602A]	ATC24C04@TSSOP8 [SA643]
ATC24C08	ATC24C08@SOIC8 [SA602A]
ATC24C08@TSSOP8 [SA643]	ATC24C16
ATC24C16@SOIC8 [SA602A]	ATC24C16@TSSOP8 [SA643]
ATC24LC02	ATC24LC02@SOIC8 [SA602A]
ATC24LC02@TSSOP8 [SA643]	ATC24LC02A
ATC24LC02A@SOIC8 [SA602A]	ATC24LC02A@TSSOP8 [SA643]
ATC24LC04	ATC24LC04@SOIC8 [SA602A]
ATC24LC04@TSSOP8 [SA643]	ATC24LC08
ATC24LC08@SOIC8 [SA602A]	ATC24LC08@TSSOP8 [SA643]
ATC24LC16	ATC24LC16@SOIC8 [SA602A]
ATC24LC16@TSSOP8 [SA643]	ATC93C46 (08bit)
ATC93C46 (08bit)@SOIC8 [SA602A]	ATC93C46 (16bit)
ATC93C46 (16bit)@SOIC8 [SA602A]	ATC93C46R (08bit)@SOIC8 [SA602A]
ATC93C46R (16bit)@SOIC8 [SA602A]	ATC93C56 (08bit)
ATC93C56 (08bit)@SOIC8 [SA602A]	ATC93C56 (16bit)
ATC93C56 (16bit)@SOIC8 [SA602A]	ATC93C56R (08bit)@SOIC8 [SA602A]
ATC93C56R (16bit)@SOIC8 [SA602A]	ATC93C66 (08bit)
ATC93C66 (08bit)@SOIC8 [SA602A]	ATC93C66 (16bit)
ATC93C66 (16bit)@SOIC8 [SA602A]	ATC93C66R (08bit)@SOIC8 [SA602A]
ATC93C66R (16bit)@SOIC8 [SA602A]	ATC93LC46 (08bit)
ATC93LC46 (08bit)@SOIC8 [SA602A]	ATC93LC46 (16bit)
ATC93LC46 (16bit)@SOIC8 [SA602A]	ATC93LC46R (08bit)@SOIC8 [SA602A]
ATC93LC46R (16bit)@SOIC8 [SA602A]	ATC93LC56 (08bit)
ATC93LC56 (08bit)@SOIC8 [SA602A]	ATC93LC56 (16bit)
ATC93LC56 (16bit)@SOIC8 [SA602A]	ATC93LC56R (08bit)@SOIC8 [SA602A]
ATC93LC56R (16bit)@SOIC8 [SA602A]	ATC93LC66 (08bit)
ATC93LC66 (08bit)@SOIC8 [SA602A]	ATC93LC66 (16bit)
ATC93LC66 (16bit)@SOIC8 [SA602A]	ATC93LC66R (08bit)@SOIC8 [SA602A]
ATC93LC66R (16bit)@SOIC8 [SA602A]	

## ATMEL

### E (E) PROM/FRAM/NVRAM

AT17C002@PLCC20 [SA001A-B2001]	AT17C002@PLCC44 [SA244]
AT17C002@SOIC20 [SA404]	AT17C002@TQFP44 [SA245A-B4805]
AT17C002A@PLCC20 [SA001A-B2001]	AT17C002A@TQFP32 [SA636]
AT17C010	AT17C010@PLCC20 [SA001A-B2001]
AT17C010A	AT17C010A@PLCC20 [SA001A-B2001]
AT17C020@PLCC20 [SA001A-B2001]	AT17C020A@PLCC20 [SA001A-B2001]
AT17C040@PLCC44 [SA244]	AT17C040@TQFP44 [SA245A-B4805]
AT17C128	AT17C128@PLCC20 [SA001A-B2001]
AT17C128@SOIC20 [SA404]	AT17C128@SOIC8 [SA602A]
AT17C128A@PLCC20 [SA001A-B2001]	AT17C256
AT17C256@PLCC20 [SA001A-B2001]	AT17C256@SOIC20 [SA404]
AT17C256@SOIC8 [SA602A]	AT17C256A@PLCC20 [SA001A-B2001]
AT17C512	AT17C512@PLCC20 [SA001A-B2001]
AT17C512A	AT17C512A@PLCC20 [SA001A-B2001]
AT17C65	AT17C65@PLCC20 [SA001A-B2001]

AT17C65@SOIC20 [SA404] AT17C65@SOIC8 [SA602A]  
AT17C65A@PLCC20 [SA001A-B2001] AT17F040@LAP8 [SA760]  
AT17F040@PLCC20 [SA001A-B2001]  
AT17F040@PLCC20 (Virtex Pinout) [SA001A-B2001]  
AT17F040A@LAP8 [SA760] AT17F040A@PLCC20 [SA001A-B2001]  
AT17F040A@TQFP32 [SA636] AT17F080@LAP8 [SA760]  
AT17F080@PLCC20 [SA001A-B2001] AT17F080@PLCC44 [SA244]  
AT17F080@TQFP44 [SA245A-B4805] AT17F080A@LAP8 [SA760]  
AT17F080A@PLCC20 [SA001A-B2001] AT17F080A@TQFP32 [SA636]  
AT17F16@LAP8 [SA760] AT17F16@PLCC20 [SA001A-B2001]  
AT17F16@PLCC44 [SA244] AT17F16@TQFP44 [SA245A-B4805]  
AT17F16A@LAP8 [SA760] AT17F16A@PLCC20 [SA001A-B2001]  
AT17F32@PLCC44 [SA244] AT17F32A@PLCC44 [SA244]  
AT17LV002@PLCC20 [SA001A-B2001] AT17LV002@PLCC44 [SA244]  
AT17LV002@SOIC20 [SA404] AT17LV002@TQFP44 [SA245A-B4805]  
AT17LV002A@PLCC20 [SA001A-B2001] AT17LV002A@TQFP32 [SA636]  
AT17LV010 AT17LV010@PLCC20 [SA001A-B2001]  
AT17LV010A AT17LV010A@PLCC20 [SA001A-B2001]  
AT17LV020@PLCC20 [SA001A-B2001] AT17LV020A@PLCC20 [SA001A-B2001]  
AT17LV040@PLCC44 [SA244] AT17LV040@TQFP44 [SA245A-B4805]  
AT17LV128 AT17LV128@PLCC20 [SA001A-B2001]  
AT17LV128@SOIC20 [SA404] AT17LV128@SOIC8 [SA602A]  
AT17LV128A@PLCC20 [SA001A-B2001] AT17LV256  
AT17LV256@PLCC20 [SA001A-B2001] AT17LV256@SOIC20 [SA404]  
AT17LV256@SOIC8 [SA602A] AT17LV256A@PLCC20 [SA001A-B2001]  
AT17LV512 AT17LV512@PLCC20 [SA001A-B2001]  
AT17LV512A AT17LV512A@PLCC20 [SA001A-B2001]  
AT17LV65 AT17LV65@PLCC20 [SA001A-B2001]  
AT17LV65@SOIC20 [SA404] AT17LV65@SOIC8 [SA602A]  
AT17LV65A@PLCC20 [SA001A-B2001] AT17N002@SOIC20 [SA404]  
AT17N002@TQFP44 [SA245A-B4805] AT17N010  
AT17N010@SOIC20 [SA404] AT17N040@TQFP44 [SA245A-B4805]  
AT17N256 AT17N256@SOIC20 [SA404]  
AT17N256@SOIC8 [SA602A] AT17N512  
AT17N512@SOIC20 [SA404] AT24C01  
AT24C01@MSOP8 [SA666] AT24C01@SOIC8 [SA602A]  
AT24C01@TSSOP8 [SA643] AT24C01A  
AT24C01A@MAP8 [SA724] AT24C01A@SOIC8 [SA602A]  
AT24C01A@SOT23-5 [SA717] AT24C01A@TSSOP8 [SA643]  
AT24C01B AT24C01B@MAP8 [SA724]  
AT24C01B@SOIC8 [SA602A] AT24C01B@SOT23 [SA717]  
AT24C01B@TSSOP8 [SA643] AT24C01C  
AT24C01C@MAP8 [SA724] AT24C01C@SOIC8 [SA602A]  
AT24C01C@SOT23 [SA717] AT24C01C@TSSOP8 [SA643]  
AT24C01D AT24C01D@dBGA8 [\$\$\$\$\$]  
AT24C01D@MAP8 [SA724] AT24C01D@SOIC8 [SA602A]  
AT24C01D@SOT23 [SA717] AT24C01D@TSSOP8 [SA643]  
AT24C02 AT24C02@SOIC8 [SA602]  
AT24C02@TSSOP8 [SA643] AT24C02A  
AT24C02A@SOIC8 [SA602A] AT24C02A@TSSOP8 [SA643]  
AT24C02B AT24C02B (HAIER)  
AT24C02B@MAP8 [SA724] AT24C02B@SOIC8 [SA602A]  
AT24C02B@SOT23 [SA717] AT24C02B@TSSOP8 [SA643]

AT24C02C  
AT24C02C@SOIC8 [SA602A]  
AT24C02C@TSSOP8 [SA643]  
AT24C02D  
AT24C02D@SOIC8 [SA602A]  
AT24C02D@TSSOP8 [SA643]  
AT24C04  
AT24C04@SOIC8 [SA602A]  
AT24C04@TSSOP8 [SA643]  
AT24C04A@MAP8 [SA724]  
AT24C04A@TSSOP8 [SA643]  
AT24C04B@MAP8 [SA724]  
AT24C04B@SOT23 [SA717]  
AT24C04C  
AT24C04C@SOT23 [SA717]  
AT24C04D  
AT24C04D@SOIC8 [SA602A]  
AT24C04D@TSSOP8 [SA643]  
AT24C08  
AT24C08@SOIC8 [SA602A]  
AT24C08A  
AT24C08A@SOIC8 [SA602A]  
AT24C08B  
AT24C08B@SOIC8 [SA602A]  
AT24C08B@TSSOP8 [SA643]  
AT24C08C@SOIC8 [SA602A]  
AT24C08C@TSSOP8 [SA643]  
AT24C08D@DBG8 [\$\$\$\$\$]  
AT24C08D@SOT23 [SA717]  
AT24C08D@UDFN8 [SA724]  
AT24C1024@LAP8 [SA684]  
AT24C1024@SOIC8 [SA605B]  
AT24C1024B(1.8V)@LAP8 [SA684]  
AT24C1024B(1.8V)@SOIC8(150mil) [SA602A]  
AT24C1024B(1.8V)@SOIC8(200mil) [SA605B]  
AT24C1024B(1.8V)@TSSOP8 [SA643]  
AT24C1024B(2.5V)@LAP8 [SA684]  
AT24C1024B(2.5V)@SOIC8(150mil) [SA602A]  
AT24C1024B(2.5V)@SOIC8(200mil) [SA605B]  
AT24C1024B(2.5V)@TSSOP8 [SA643]  
AT24C11@SOIC8 [SA602A]  
AT24C128(1.8V)  
AT24C128(1.8V)@SAP8 [SA683]  
AT24C128(1.8V)@TSSOP8 [SA643]  
AT24C128(2.7V)@MAP8 [SA724]  
AT24C128(2.7V)@SOIC8 [SA602A]  
AT24C128(2.7V)@TSSOP8 [SA643]  
AT24C128B@MAP8 [SA724]  
AT24C128B@SOIC8 [SA602A]  
AT24C128C@SOIC8 [SA602A]  
AT24C128C@VFBGA8 [\$\$\$\$\$]  
AT24C16@SOIC8 [SA602A]  
AT24C164  
AT24C02C@DBG8 [\$\$\$\$\$]  
AT24C02C@SOT23 [SA717]  
AT24C02C@UDFN8 [SA724]  
AT24C02D@DBG8 [\$\$\$\$\$]  
AT24C02D@SOT23 [SA717]  
AT24C02D@UDFN8 [SA724]  
AT24C04@MAP8 [SA724]  
AT24C04@SOT23-5 [SA717]  
AT24C04A  
AT24C04A@SOIC8 [SA602A]  
AT24C04B  
AT24C04B@SOIC8 [SA602A]  
AT24C04B@TSSOP8 [SA643]  
AT24C04C@SOIC8 [SA602A]  
AT24C04C@TSSOP8 [SA643]  
AT24C04D@DBG8 [\$\$\$\$\$]  
AT24C04D@SOT23 [SA717]  
AT24C04D@UDFN8 [SA724]  
AT24C08@MAP8 [SA724]  
AT24C08@TSSOP8 [SA643]  
AT24C08A@MAP8 [SA724]  
AT24C08A@TSSOP8 [SA643]  
AT24C08B@MAP8 [SA724]  
AT24C08B@SOT23 [SA717]  
AT24C08C  
AT24C08C@SOT23 [SA717]  
AT24C08D  
AT24C08D@SOIC8 [SA602A]  
AT24C08D@TSSOP8 [SA643]  
AT24C1024  
AT24C1024@SAP8 [SA683]  
AT24C1024B(1.8V)  
AT24C1024B(1.8V)@SAP8 [SA683]  
AT24C1024B(2.5V)  
AT24C1024B(2.5V)@SAP8 [SA683]  
AT24C11  
AT24C11@TSSOP8 [SA643]  
AT24C128(1.8V)@MAP8 [SA724]  
AT24C128(1.8V)@SOIC8 [SA602A]  
AT24C128(2.7V)  
AT24C128(2.7V)@SAP8 [SA683]  
AT24C128(2.7V)@SSOP8 [SA605B]  
AT24C128B  
AT24C128B@SAP8 [SA683]  
AT24C128B@TSSOP8 [SA643]  
AT24C128C@TSSOP8 [SA643]  
AT24C16  
AT24C16@TSSOP8 [SA643]  
AT24C164@SOIC8 [SA602A]

AT24C16A  
AT24C16A@SOIC8 [SA602A]  
AT24C16B  
AT24C16B@SOIC8 [SA602A]  
AT24C16C  
AT24C16C@SOIC8 [SA602A]  
AT24C16C@TSSOP8 [SA643]  
AT24C16C@XDFN8  
AT24C21@SOIC8 [SA602A]  
AT24C256 (1.8V)@MAP8 [SA724]  
AT24C256 (1.8V)@SOIC8 [SA602A]  
AT24C256 (2.7V)  
AT24C256 (2.7V)@SAP8 [SA683]  
AT24C256 (2.7V)@TSSOP8 [SA643]  
AT24C256B@MAP8 [SA724]  
AT24C256B@SOIC8 [SA602A]  
AT24C256C  
AT24C256C@SOIC8 [SA602A]  
AT24C32  
AT24C32@TSSOP8 [SA643]  
AT24C32A@MAP8 [SA724]  
AT24C32A@TSSOP8 [SA643]  
AT24C32C@MAP8 [SA724]  
AT24C32C@SOIC8 [SA602A]  
AT24C32D@SOIC8 [SA602A]  
AT24C32D@TSSOP8 [SA643]  
AT24C32D@VDFN8  
AT24C512 (1.8V)@LAP8 [SA684]  
AT24C512 (1.8V)@SOIC8 [SA602A]  
AT24C512 (2.7V)  
AT24C512 (2.7V)@SAP8 [SA683]  
AT24C512 (2.7V)@TSSOP8 [SA643]  
AT24C512B@LAP8 [SA684]  
AT24C512B@SOIC8 (150 mil) [SA602A]  
AT24C512B@SOIC8 (200 mil) [SA605B]  
AT24C512B@TSSOP8 [SA643]  
AT24C512C@SOIC8 (150 mil) [SA602A]  
AT24C512C@SOIC8 (200 mil) [SA605B]  
AT24C512C@TSSOP8 [SA643]  
AT24C64  
AT24C64@TSSOP8 [SA643]  
AT24C64A@MAP8 [SA724]  
AT24C64A@TSSOP8 [SA643]  
AT24C64B@SOIC8 [SA602A]  
AT24C64C  
AT24C64C@SAP8 [SA683]  
AT24C64C@TSSOP8 [SA643]  
AT24C64D@SOT23 [SA724]  
AT24C64D@UDFN8 [SA724]  
AT24CM01@SOIC8 [150 mil] [SA602A]  
AT24CM01@TSSOP8 [SA643]  
AT24CM02@SOIC8 [150 mil] [SA602A]  
AT24CM02@TSSOP8 [SA643]

AT24C16A@MAP8 [SA724]  
AT24C16A@TSSOP8 [SA643]  
AT24C16B@MAP8 [SA724]  
AT24C16B@TSSOP8 [SA643]  
AT24C16C@dBGA8 [\$\$\$\$\$\$]  
AT24C16C@SOT23 [SA717]  
AT24C16C@UDFN8 [SA724]  
AT24C21 [SA724]  
AT24C256 (1.8V)  
AT24C256 (1.8V)@SAP8 [SA683]  
AT24C256 (1.8V)@TSSOP8 [SA643]  
AT24C256 (2.7V)@MAP8 [SA724]  
AT24C256 (2.7V)@SOIC8 [SA602A]  
AT24C256B  
AT24C256B@SAP8 [SA683]  
AT24C256B@TSSOP8 [SA643]  
AT24C256C@dBGA8 [\$\$\$\$\$\$]  
AT24C256C@TSSOP8 [SA643]  
AT24C32@SOIC8 [SA602A]  
AT24C32A  
AT24C32A@SOIC8 [SA602A]  
AT24C32C  
AT24C32C@SAP8 [SA683]  
AT24C32C@TSSOP8 [SA643]  
AT24C32D@SOT23 [SA724]  
AT24C32D@UDFN8 [SA724]  
AT24C512 (1.8V)  
AT24C512 (1.8V)@SAP8 [SA683]  
AT24C512 (1.8V)@TSSOP8 [SA643]  
AT24C512 (2.7V)@LAP8 [SA684]  
AT24C512 (2.7V)@SOIC8 [SA602A]  
AT24C512B  
AT24C512B@SAP8 [SA683]  
  
AT24C512C@UDFN8 [SA724]  
AT24C64@SOIC8 [SA602A]  
AT24C64A  
AT24C64A@SOIC8 [SA602A]  
AT24C64B  
AT24C64B@TSSOP8 [SA643]  
AT24C64C@MAP8 [SA724]  
AT24C64C@SOIC8 [SA602A]  
AT24C64D@SOIC8 [SA602A]  
AT24C64D@TSSOP8 [SA643]  
AT24C64D@VDFN8  
AT24CM01@SOIC8 [200 mil] [SA605B]  
AT24CM01@WLCSP8  
AT24CM02@SOIC8 [200 mil] [SA605B]  
AT24CM02@WLCSP8

AT24CS01@SOIC8 [SA602A]  
AT24CS01@TSSOP8 [SA643]  
AT24CS02@SOIC8 [SA602A]  
AT24CS02@TSSOP8 [SA643]  
AT24CS04@SOIC8 [SA602A]  
AT24CS04@TSSOP8 [SA643]  
AT24CS08@SOIC8 [SA602A]  
AT24CS08@TSSOP8 [SA643]  
AT24CS128  
AT24CS16  
AT24CS16@SOIC8 [SA602A]  
AT24HC02B  
AT24HC02B@TSSOP8 [SA643]  
AT24HC02C@SOIC8 [SA602A]  
AT24HC04B@MAP8 [SA724]  
AT24HC04B@TSSOP8 [SA643]  
AT24MAC402@SOIC8 [SA602A]  
AT24MAC402@TSSOP8 [SA643]  
AT24MAC602@SOIC8 [SA602A]  
AT24MAC602@TSSOP8 [SA643]  
AT24RF08AN@SOIC8 [SA602A]  
AT24RF08BN@SOIC8 [SA602A]  
AT24RF08CN@SOIC8 [SA602A]  
AT25010  
AT25010A  
AT25010A@TSSOP8 [SA643]  
AT25010B@SOIC8 [SA602A]  
AT25020  
AT25020A  
AT25020A@TSSOP8 [SA643]  
AT25020B@SOIC8 [SA602A]  
AT25040  
AT25040@SOIC8 [SA602A]  
AT25040A  
AT25040A@SOIC8 [SA602A]  
AT25080  
AT25080@TSSOP14 [SA026]  
AT25080@TSSOP8 [SA643]  
AT25080A@SOIC8 [SA602A]  
AT25080A@TSSOP8 [SA643]  
AT25080B@MAP8 [SA724]  
AT25080B@TSSOP8 [SA643]  
AT25128@SOIC16 [SA602]  
AT25128@TSSOP14 [SA026]  
AT25128A  
AT25128A@SOIC8(4.0) [SA602A]  
AT25128A@TSSOP14 [SA026]  
AT25128B  
AT25128B@TSSOP8 [SA643]  
AT25160  
AT25160@TSSOP14 [SA026]  
AT25160@TSSOP8 [SA643]  
AT25160A@SOIC8 [SA602A]

AT24CS01@SOT23 [SA717]  
AT24CS01@UDFN8 [SA724]  
AT24CS02@SOT23 [SA717]  
AT24CS02@UDFN8 [SA724]  
AT24CS04@SOT23 [SA717]  
AT24CS04@UDFN8 [SA724]  
AT24CS08@SOT23 [SA717]  
AT24CS08@UDFN8 [SA724]  
AT24CS128@SOIC8 [SA602A]  
AT24CS16@MAP8 [SA724]  
AT24CS16@TSSOP8 [SA643]  
AT24HC02B@SOIC8 [SA602A]  
AT24HC02C  
AT24HC04B  
AT24HC04B@SOIC8 [SA602A]  
AT24HC0CB@TSSOP8 [SA643]  
AT24MAC402@SOT23 [SA717]  
AT24MAC402@UDFN8 [SA724]  
AT24MAC602@SOT23 [SA717]  
AT24MAC602@UDFN8 [SA724]  
AT24RF08AT@TSSOP14 [SA026]  
AT24RF08BT@TSSOP14 [SA026]  
AT24RF08CT@TSSOP14 [SA026]  
AT25010@SOIC8 [SA602A]  
AT25010A@SOIC8 [SA602A]  
AT25010B  
AT25010B@TSSOP8 [SA643]  
AT25020@SOIC8 [SA602A]  
AT25020A@SOIC8 [SA602A]  
AT25020B  
AT25020B@TSSOP8 [SA643]  
AT25040 (ISP)  
AT25040@SOIC8 (ISP)  
AT25040A (ISP)  
AT25040A@SOIC8 (ISP)  
AT25080@SOIC8 [SA602A]  
AT25080@TSSOP20 [SA026]  
AT25080A  
AT25080A@TSSOP14 [SA026]  
AT25080B  
AT25080B@SOIC8 [SA602A]  
AT25128  
AT25128@SOIC8 [SA602A]  
AT25128@TSSOP20 [SA026]  
AT25128A@SAP8 [SA683]  
AT25128A@SOIC8(5.4) [SA605B]  
AT25128A@TSSOP8 [SA643]  
AT25128B@SOIC8 [SA602A]  
AT25128B@UDFN8 [SA724]  
AT25160@SOIC8 [SA602A]  
AT25160@TSSOP20 [SA026]  
AT25160A  
AT25160A@TSSOP14 [SA026]

AT25160A@TSSOP8 [SA643]  
AT25160B@MAP8 [SA724]  
AT25160B@TSSOP8 [SA643]  
AT25256@SOIC16 [SA602]  
AT25256@TSSOP14 [SA026]  
AT25256A  
AT25256A@SOIC8(4.0) [SA602A]  
AT25256A@TSSOP14 [SA026]  
AT25256B  
AT25256B@TSSOP8 [SA643]  
AT25320  
AT25320@TSSOP14 [SA026]  
AT25320@TSSOP8 [SA643]  
AT25320A@SOIC8 [SA602A]  
AT25320A@TSSOP8 [SA643]  
AT25320B@MAP8 [SA724]  
AT25320B@TSSOP8 [SA643]  
AT25512@SOIC8 [SA602A]  
AT25640  
AT25640@TSSOP14 [SA026]  
AT25640@TSSOP8 [SA643]  
AT25640A@SOIC8 [SA602A]  
AT25640A@TSSOP8 [SA643]  
AT25640B@MAP8 [SA724]  
AT25640B@TSSOP8 [SA643]  
AT25DF021(OTP)@UDFN8 [SA683]  
AT25DF021@UDFN8 [SA683]  
AT25DF041A@SOIC8(4.0) [SA602A]  
AT25DF081@SOIC8 [SA602A]  
AT25DF081A@SOIC8 [SA605B]  
AT25DF161(OTP)@SOIC8(4.0) [SA602A]  
AT25DF161(OTP)@SOIC8(5.4) [SA023A]  
AT25DF161(OTP)@UDFN8 [SA683]  
AT25DF161@SOIC8(4.0) [SA602A]  
AT25DF321@SOIC16 [SA404]  
AT25DF321A(OTP)@SOIC16 [SA404]  
AT25DF321A(OTP)@UDFN8 [SA683]  
AT25DF641(OTP)@UDFN8 [SA684]  
AT25DL161@SOIC8 [SA602A]  
AT25DN011@DFN8 [SA724]  
AT25DN011@TSSOP8 [SA643]  
AT25F1024(W)@SOIC8 [SA605B]  
AT25F1024@SOIC8 [SA602A]  
AT25F1024A  
AT25F1024A(W)@VQFPN8 [SA684]  
AT25F1024A@VQFPN8 [SA683]  
AT25F2048(W)@SOIC8 [SA605B]  
AT25F2048@SOIC8 [SA602A]  
AT25F2048A  
AT25F2048A(W)@VQFPN8 [SA684]  
AT25F2048A@VQFPN8 [SA683]  
AT25F4096(W)@SOIC8 [SA605B]  
AT25F4096@SOIC8 [SA602A]

AT25160B  
AT25160B@SOIC8 [SA602A]  
AT25256  
AT25256@SOIC8 [SA602A]  
AT25256@TSSOP20 [SA643]  
AT25256A@SAP8 [SA683]  
AT25256A@SOIC8(5.4) [SA605B]  
AT25256A@TSSOP8 [SA643]  
AT25256B@SOIC8 [SA602A]  
AT25256B@UDFN8 [SA724]  
AT25320@SOIC8 [SA602A]  
AT25320@TSSOP20 [SA026]  
AT25320A  
AT25320A@TSSOP14 [SA026]  
AT25320B  
AT25320B@SOIC8 [SA602A]  
AT25512@SAP8 [SA683]  
AT25512@TSSOP8 [SA643]  
AT25640@SOIC8 [SA602A]  
AT25640@TSSOP20 [SA026]  
AT25640A  
AT25640A@TSSOP14 [SA026]  
AT25640B  
AT25640B@SOIC8 [SA602A]  
AT25DF021(OTP)@SOIC8 [SA602A]  
AT25DF021@SOIC8 [SA602A]  
AT25DF041A@MLF8 [SA683]  
AT25DF041A@SOIC8(5.4) [SA605B]  
AT25DF081@UDFN8 [SA683]  
AT25DF081A@UDFN8 [SA683]  
AT25DF161@MLF8 [SA683]  
AT25DF161@SOIC8(5.4) [SA023A]  
AT25DF321@SOIC8 [SA023A]  
AT25DF321A(OTP)@SOIC8 [SA023A]  
AT25DF641(OTP)@SOIC16 [SA404]  
AT25DL161@dBGA8 [\$\$\$\$\$\$]  
AT25DL161@UDFN8 [SA683]  
AT25DN011@SOIC8 [SA602A]  
AT25F1024  
AT25F1024(W)@VQFPN8 [SA684]  
AT25F1024@VQFPN8 [SA683]  
AT25F1024A(W)@SOIC8 [SA605B]  
AT25F1024A@SOIC8 [SA602A]  
AT25F2048  
AT25F2048(W)@VQFPN8 [SA684]  
AT25F2048@VQFPN8 [SA683]  
AT25F2048A(W)@SOIC8 [SA605B]  
AT25F2048A@SOIC8 [SA602A]  
AT25F4096  
AT25F4096(W)@VQFPN8 [SA684]  
AT25F4096@VQFPN8 [SA683]

AT25F4096A  
AT25F4096A(W)@VQFPN8 [SA684]  
AT25F4096A@VQFPN8 [SA683]  
AT25F512(W)@SOIC8 [SA605B]  
AT25F512@SOIC8 [SA602A]  
AT25F512A  
AT25F512A(W)@VQFPN8 [SA684]  
AT25F512A@VQFPN8 [SA683]  
AT25F512B@UDFN8 [SA724]  
AT25FS010@SOIC8 [SA602A]  
AT25FS040@SOIC8 [SA602A]  
AT25HP256(W)@VQFPN8 [SA684]  
AT25HP256@SOIC8 [SA602A]  
AT25HP512  
AT25HP512@SOIC16 [SA404]  
AT25HP512@VQFPN8 [SA683]  
AT25P1024@VQFPN8 [SA684]  
AT26DF041@SOIC8(4.0) [SA602A]  
AT26DF081@SOIC8(4.0) [SA602A]  
AT26DF081A@SOIC8(4.0) [SA602A]  
AT26DF161@MLF8 [SA683]  
AT26DF161A@MLF8 [SA683]  
AT26DF161A@SOIC8(5.4) [SA023A]  
AT26DF321@MLF8(6\*8mm) [SA684]  
AT26DF321@SOIC8 [SA023A]  
AT26F004@SOIC8(4.0) [SA602A]  
AT27011  
AT27256  
AT27BV010  
AT27BV010@TSOP32 [SA410T-B4001]  
AT27BV020  
AT27BV020@TSOP32 [SA410T-B4001]  
AT27BV040  
AT27BV040@TSOP32 [SA410T-B4001]  
AT27BV1024@PLCC44 [SA244]  
AT27BV256  
AT27BV256@TSOP28 [SA430T-B4003]  
AT27BV400@PSOP44 [SA638]  
AT27BV4096  
AT27BV4096@VSOP40 [SA623-B4002]  
AT27BV512@PLCC32 [SA015A1T]  
AT27BV512@TSOP28 [SA430T-B4003]  
AT27BV520@TSOP28 [SA430T-B4003]  
AT27C010  
AT27C010@TSOP32 [SA410T-B4001]  
AT27C010L@PLCC32 [SA015A1T]  
AT27C020  
AT27C020@TSOP32 [SA410T-B4001]  
AT27C040@PLCC32 [SA015A1T]  
AT27C080  
AT27C080@TSOP32 [SA410T-B4001]  
AT27C1024@PLCC44 [SA244]  
AT27C1024L

AT25F4096A(W)@SOIC8 [SA605B]  
AT25F4096A@SOIC8 [SA602A]  
AT25F512  
AT25F512(W)@VQFPN8 [SA684]  
AT25F512@VQFPN8 [SA683]  
AT25F512A(W)@SOIC8 [SA605B]  
AT25F512A@SOIC8 [SA602A]  
AT25F512B@SOIC8 [SA602A]  
AT25FS010@SAP8 [SA683]  
AT25FS040@SAP8 [SA683]  
AT25HP256  
AT25HP256@SOIC16 [SA404]  
AT25HP256@VQFPN8 [SA683]  
AT25HP512(W)@VQFPN8 [SA684]  
AT25HP512@SOIC8 [SA602A]  
AT25P1024@SOIC20 [SA404]  
AT26DF041@MLF8 [SA683]  
AT26DF041@SOIC8(5.4) [SA605B]  
AT26DF081@SOIC8(5.4) [SA023A]  
AT26DF081A@SOIC8(5.4) [SA023A]  
AT26DF161@SOIC8 [SA023A]  
AT26DF161A@SOIC8(4.0) [SA602A]  
AT26DF321@MLF8(5\*6mm) [SA683]  
AT26DF321@SOIC16 [SA404]  
AT26F004@MLF8 [SA683]  
AT26F004@SOIC8(5.4) [SA023A]  
AT27011@PLCC32 [SA015A1T]  
AT2732A  
AT27BV010@PLCC32 [SA015A1T]  
AT27BV010@VSOP32 [SA620-B4807]  
AT27BV020@PLCC32 [SA015A1T]  
AT27BV020@VSOP32 [SA620-B4807]  
AT27BV040@PLCC32 [SA015A1T]  
AT27BV040@VSOP32 [SA620-B4807]  
AT27BV1024@VSOP40 [SA623-B4002]  
AT27BV256@PLCC32 [SA015A1T]  
AT27BV400@PLCC44 [SA244]  
AT27BV400@TSOP48 [SB247-B4806]  
AT27BV4096@PLCC44 [SA244]  
AT27BV512  
AT27BV512@SOIC28 [SA404]  
AT27BV520@SOIC20 [SA404]  
AT27BV520@TSSOP20 [SA026]  
AT27C010@PLCC32 [SA015A1T]  
AT27C010L  
AT27C010L@TSOP32 [SA410T-B4001]  
AT27C020@PLCC32 [SA015A1T]  
AT27C040  
AT27C040@TSOP32 [SA410T-B4001]  
AT27C080@PLCC32 [SA015A1T]  
AT27C1024  
AT27C1024@VSOP40 [SA623-B4002]  
AT27C1024L@PLCC44 [SA244]

AT27C128  
AT27C2048  
AT27C2048@VSOP40 [SA623-B4002]  
AT27C256@PLCC32 [SA015A1T]  
AT27C256R@PLCC32 [SA015A1T]  
AT27C256R@TSOP28 [SA430T-B4003]  
AT27C4096@PLCC44 [SA244]  
AT27C512  
AT27C512R  
AT27C512R@SOIC28 [SA404]  
AT27C513  
AT27C513@SOIC28 [SA404]  
AT27C513R@SOIC28 [SA404]  
AT27C515@PLCC32 [SA015A1T]  
AT27C516@PLCC44 [SA244]  
AT27C520@SOIC20 [SA404]  
AT27C520@TSSOP20 [SA026]  
AT27C800  
AT27C800@PSOP44 [SA638]  
AT27HC1024  
AT27HC256  
AT27HC256L  
AT27HC256R  
AT27HC256RL  
AT27HC64  
AT27HC641  
AT27HC641R  
AT27HC642  
AT27HC642R  
AT27HC64L  
AT27LV010  
AT27LV010@TSOP32 [SA410T-B4001]  
AT27LV010A  
AT27LV010A@TSOP32 [SA410T-B4001]  
AT27LV020A  
AT27LV020A@TSOP32 [SA410T-B4001]  
AT27LV040  
AT27LV040@TSOP32 [SA410T-B4001]  
AT27LV040A  
AT27LV040A@TSOP32 [SA410T-B4001]  
AT27LV1024  
AT27LV1026@PLCC44 [SA244]  
AT27LV256A  
AT27LV256A@SOIC28 [SA630]  
AT27LV256R  
AT27LV256R@SOIC28 [SA630]  
AT27LV4096  
AT27LV512A  
AT27LV512A@SOIC28 [SA404]  
AT27LV512R  
AT27LV512R@TSOP28 [SA430T-B4003]  
AT27LV520@TSOP28 [SA430T-B4003]  
AT27LV800  
AT27C128@PLCC32 [SA015A1T]  
AT27C2048@PLCC44 [SA244]  
AT27C256  
AT27C256R  
AT27C256R@SOIC28 [SA630]  
AT27C4096  
AT27C4096@VSOP40 [SA623-B4002]  
AT27C512@PLCC32 [SA015A1T]  
AT27C512R@PLCC32 [SA015A1T]  
AT27C512R@TSOP28 [SA430T-B4003]  
AT27C513@PLCC32 [SA015A1T]  
AT27C513R@PLCC32 [SA015A1T]  
AT27C515  
AT27C516  
AT27C516@VSOP40 [SA623-B4002]  
AT27C520@TSOP28 [SA430T-B4003]  
AT27C64  
AT27C800@PLCC44 [SA244]  
AT27C800@TSOP48 [SB247-B4806]  
AT27HC1024@PLCC44 [SA244]  
AT27HC256@PLCC32 [SA015A1T]  
AT27HC256L@PLCC32 [SA015A1T]  
AT27HC256R@PLCC32 [SA015A1T]  
AT27HC256RL@PLCC32 [SA015A1T]  
AT27HC64@PLCC32 [SA015A1T]  
AT27HC641@PLCC28 [SA008A]  
AT27HC641R@PLCC28 [SA008A]  
AT27HC642@PLCC28 [SA008A]  
AT27HC642R@PLCC28 [SA008A]  
AT27HC64L@PLCC32 [SA015A1T]  
AT27LV010@PLCC32 [SA015A1T]  
AT27LV010@VSOP32 [SA620-B4807]  
AT27LV010A@PLCC32 [SA015A1T]  
AT27LV010A@VSOP32 [SA620-B4807]  
AT27LV020A@PLCC32 [SA015A1T]  
AT27LV020A@VSOP32 [SA620-B4807]  
AT27LV040@PLCC32 [SA015A1T]  
AT27LV040@VSOP32 [SA620-B4807]  
AT27LV040A@PLCC32 [SA015A1T]  
AT27LV040A@VSOP32 [SA620-B4807]  
AT27LV1024@PLCC44 [SA244]  
AT27LV1026@TSOP40 [SA623-B4002]  
AT27LV256A@PLCC32 [SA015A1T]  
AT27LV256A@TSOP28 [SA430T-B4003]  
AT27LV256R@PLCC32 [SA015A1T]  
AT27LV256R@TSOP28 [SA430T-B4003]  
AT27LV4096@PLCC44 [SA244]  
AT27LV512A@PLCC32 [SA015A1T]  
AT27LV512A@TSOP28 [SA430T-B4003]  
AT27LV512R@PLCC32 [SA015A1T]  
AT27LV520@SOIC20 [SA404]  
AT27LV520@TSSOP20 [SA026]  
AT27LV800@PSOP44 [SA638]

AT27RW1024@PLCC44 [SA244]  
AT28BV16  
AT28BV16@S0IC24 [SA404]  
AT28BV256  
AT28BV256@S0IC28 [SA404]  
AT28BV64  
AT28BV64@S0IC28 [SA404]  
AT28BV64B  
AT28BV64B@S0IC28 [SA404]  
AT28C010  
AT28C010@PLCC44 [SA244]  
AT28C010E  
AT28C010E@PLCC44 [SA244]  
AT28C04  
AT28C040  
AT28C040@PLCC44 [SA244]  
AT28C04E  
AT28C04F  
AT28C16  
AT28C16@S0IC24 [SA404]  
AT28C16E  
AT28C16F  
AT28C17  
AT28C17@S0IC28 [SA404]  
AT28C17E@PLCC32 [SA015A1T]  
AT28C17F@PLCC32 [SA015A1T]  
AT28C256@PLCC32 [SA015A1T]  
AT28C256@TSOP28 [SA430T-B4003]  
AT28C256E@PLCC32 [SA015A1T]  
AT28C256E@TSOP28 [SA430T-B4003]  
AT28C256F@PLCC32 [SA015A1T]  
AT28C64@PLCC32 [SA015A1T]  
AT28C64@TSOP28 [SA430T-B4003]  
AT28C64B@PLCC32 [SA015A1T]  
AT28C64B@TSOP28 [SA430T-B4003]  
AT28C64E@PLCC32 [SA015A1T]  
AT28C64F  
AT28C64F@TSOP28 [SA430T-B4003]  
AT28C64X@PLCC32 [SA015A1T]  
AT28C64X@TSOP28 [SA430T-B4003]  
AT28HC04@PLCC32 [SA015A1T]  
AT28HC16L  
AT28HC191L  
AT28HC256@PLCC32 [SA015A1T]  
AT28HC256E  
AT28HC256F  
AT28HC256L  
AT28HC256LE  
AT28HC291  
AT28HC291L  
AT28HC64  
AT28HC64@TSOP28 [SA430T-B4003]  
AT28HC64B@PLCC32 [SA015A1T]  
AT27RW1024@TSOP40 [SA623-B4002]  
AT28BV16@PLCC32 [SA015A1T]  
AT28BV16@TSOP28 [SA430TA-B4003]  
AT28BV256@PLCC32 [SA015A1T]  
AT28BV256@TSOP28 [SA430T-B4003]  
AT28BV64@PLCC32 [SA015A1T]  
AT28BV64@TSOP28 [SA430T-B4003]  
AT28BV64B@PLCC32 [SA015A1T]  
AT28BV64B@TSOP28 [SA430T-B4003]  
AT28C010@PLCC32 [SA015A1T]  
AT28C010@TSOP32 [SA410T-B4001]  
AT28C010E@PLCC32 [SA015A1T]  
AT28C010E@TSOP32 [SA410T-B4001]  
AT28C04@PLCC32 [SA015A1T]  
AT28C040@PLCC32 [SA015A1T]  
AT28C040@TSOP48 [SB247-B4806]  
AT28C04E@PLCC32 [SA015A1T]  
AT28C04F@PLCC32 [SA015A1T]  
AT28C16@PLCC32 [SA015A1T]  
AT28C16@TSOP28 [SA430TA-B4003]  
AT28C16E@PLCC32 [SA015A1T]  
AT28C16F@PLCC32 [SA015A1T]  
AT28C17@PLCC32 [SA015A1T]  
AT28C17E  
AT28C17F  
AT28C256  
AT28C256@S0IC28 [SA404]  
AT28C256E  
AT28C256E@S0IC28 [SA404]  
AT28C256F  
AT28C64  
AT28C64@S0IC28 [SA404]  
AT28C64B  
AT28C64B@S0IC28 [SA404]  
AT28C64E  
AT28C64E@TSOP28 [SA430T-B4003]  
AT28C64F@PLCC32 [SA015A1T]  
AT28C64X  
AT28C64X@S0IC28 [SA404]  
AT28HC04  
AT28HC16  
AT28HC191  
AT28HC256  
AT28HC256@TSOP28 [SA430T-B4003]  
AT28HC256E@PLCC32 [SA015A1T]  
AT28HC256F@PLCC32 [SA015A1T]  
AT28HC256L@PLCC32 [SA015A1T]  
AT28HC256LE@PLCC32 [SA015A1T]  
AT28HC291@PLCC28 [SA008A]  
AT28HC291L@PLCC28 [SA008A]  
AT28HC64@PLCC32 [SA015A1T]  
AT28HC64B  
AT28HC64B@S0IC28 [SA404]

AT28HC64B@TSOP28 [SA430T-B4003]  
AT28HC64BF@PLCC32 [SA015A1T]  
AT28HC64BF@TSOP28 [SA430T-B4003]  
AT28HC64L@PLCC32 [SA015A1T]  
AT28LV010  
AT28LV010@TSOP32 [SA410T-B4001]  
AT28LV256@PLCC32 [SA015A1T]  
AT28LV64  
AT28LV64B  
AT28LV64B@SOIC28 [SA404]  
AT28MC010  
AT28MC010@PLCC44 [SA244]  
AT28MC020  
AT28MC020@PLCC44 [SA244]  
AT28MC040  
AT28MC040@PLCC44 [SA244]  
AT28PC64  
AT28PC64@TSOP28 [SA430T-B4003]  
AT28PC64E@PLCC32 [SA015A1T]  
AT29BV010A@PLCC32 [SA015A1T]  
AT29BV020@PLCC32 [SA015A1T]  
AT29BV040A@TSOP32 [SA410T-B4001]  
AT29C010@PLCC32 [SA015A1T]  
AT29C010A  
AT29C010A@TSOP32 [SA410T-B4001]  
AT29C020@PLCC32 [SA015A1T]  
AT29C040  
AT29C040@TSOP32 [SA410T-B4001]  
AT29C040A@PLCC32 [SA015A1T]  
AT29C1024@PLCC44 [SA244]  
AT29C256  
AT29C256@TSOP28 [SA430T-B4003]  
AT29C257@PLCC32 [SA015A1T]  
AT29C512@PLCC32 [SA015A1T]  
AT29LV010  
AT29LV010@TSOP32 [SA410T-B4001]  
AT29LV010A@TSOP32 [SA410T-B4001]  
AT29LV020@PLCC32 [SA015A1T]  
AT29LV040A  
AT29LV040A@TSOP32 [SA410T-B4001]  
AT29LV1024@TSOP48 [SB247-B4806]  
AT29LV256@PLCC32 [SA015A1T]  
AT29LV512  
AT29LV512@TSOP32 [SA410T-B4001]  
AT32C16@PLCC44  
AT34C02@SOIC8 [SA602A]  
AT34C02B  
AT34C02B@TSSOP8 [SA643]  
AT34C02C@MAP8 [SA724]  
AT34C02C@TSSOP8 [SA643]  
AT45BCM021D (page256)@SOIC8 [SA023A]  
AT45D011@PLCC32 [SA015A1T]  
AT45D011@TSSOP14 [SA026]

AT28HC64BF  
AT28HC64BF@SOIC28 [SA404]  
AT28HC64L  
AT28HC64L@TSOP28 [SA430T-B4003]  
AT28LV010@PLCC32 [SA015A1T]  
AT28LV256  
AT28LV256@TSOP28 [SA430T-B4003]  
AT28LV64@PLCC32 [SA015A1T]  
AT28LV64B@PLCC32 [SA015A1T]  
AT28LV64B@TSOP28 [SA430T-B4003]  
AT28MC010@PLCC32 [SA015A1T]  
AT28MC010@TSOP32 [SA410T-B4001]  
AT28MC020@PLCC32 [SA015A1T]  
AT28MC020@TSOP32 [SA410T-B4001]  
AT28MC040@PLCC32 [SA015A1T]  
AT28MC040@TSOP32 [SA410T-B4001]  
AT28PC64@PLCC32 [SA015A1T]  
AT28PC64E  
AT28PC64E@TSOP28 [SA430T-B4003]  
AT29BV010A@TSOP32 [SA410T-B4001]  
AT29BV020@TSOP32 [SA410T-B4001]  
AT29C010  
AT29C010@TSOP32 [SA410T-B4001]  
AT29C010A@PLCC32 [SA015A1T]  
AT29C020  
AT29C020@TSOP32 [SA410T-B4001]  
AT29C040@PLCC32 [SA015A1T]  
AT29C040A  
AT29C040A@TSOP32 [SA410T-B4001]  
AT29C1024@TSOP48 [SB247-B4806]  
AT29C256@PLCC32 [SA015A1T]  
AT29C257  
AT29C512  
AT29C512@TSOP32 [SA410T-B4001]  
AT29LV010@PLCC32 [SA015A1T]  
AT29LV010A@PLCC32 [SA015A1T]  
AT29LV020  
AT29LV020@TSOP32 [SA410T-B4001]  
AT29LV040A@PLCC32 [SA015A1T]  
AT29LV1024@PLCC44 [SA244]  
AT29LV256  
AT29LV256@TSOP28 [SA430T-B4003]  
AT29LV512@PLCC32 [SA015A1T]  
AT32C16  
AT34C02  
AT34C02@TSSOP8 [SA643]  
AT34C02B@SOIC8 [SA602A]  
AT34C02C  
AT34C02C@SOIC8 [SA602A]  
AT45D011@SOIC8 [SA023A]  
AT45D021@PLCC32 [SA015A1T]

AT45D021@SOIC28 [SA630] AT45D021@TSOP28 [SA430T-B4003]  
AT45D041@PLCC32 [SA015A1T] AT45D041@SOIC28 [SA630]  
AT45D041@TSOP28 [SA430T-B4003] AT45D081@SOIC28 [SA630]  
AT45D081@TSOP32 [SA410T-B4001] AT45D161@PLCC32 [SA015A1T]  
AT45D161@SOIC28 [SA630] AT45D161@TSOP28 [SA430T-B4003]  
AT45DB011@PLCC32 [SA015A1T] AT45DB011@SOIC8 [SA023A]  
AT45DB011@TSSOP14 [SA026] AT45DB011B@PLCC32 [SA015A1T]  
AT45DB011B@SOIC8 [SA023A] AT45DB011B@TSSOP14 [SA026]  
AT45DB011D@SOIC8 [SA023A]  
AT45DB011D@SOIC8[150 mil] [SA602]  
AT45DB011D@UDFN8 [SA683] AT45DB021@PLCC32 [SA015A1T]  
AT45DB021@SOIC28 [SA630] AT45DB021@TSOP28 [SA430T-B4003]  
AT45DB021A@PLCC32 [SA015A1T] AT45DB021A@SOIC28 [SA630]  
AT45DB021A@TSOP28 [SA430T-B4003] AT45DB021B@SOIC28 [SA630]  
AT45DB021B@SOIC8 [SA023A] AT45DB021B@TSOP28 [SA430T-B4003]  
AT45DB021D@SOIC8 [SA023A]  
AT45DB021D@SOIC8[150 mil] [SA602]  
AT45DB021D@UDFN8 [SA683] AT45DB021E@SOIC8 [SA023A]  
AT45DB021E@SOIC8(256B) [SA023A]  
AT45DB021E@SOIC8[150 mil] [SA602]  
AT45DB021E@SOIC8[150 mil](256B) [SA602]  
AT45DB021E@UDFN8 [SA683] AT45DB021E@UDFN8(256B) [SA683]  
AT45DB041@PLCC32 [SA015A1T] AT45DB041@SOIC28 [SA630]  
AT45DB041@TSOP28 [SA430T-B4003] AT45DB041A@PLCC32 [SA015A1T]  
AT45DB041A@SOIC28 [SA630] AT45DB041A@TSOP28 [SA430T-B4003]  
AT45DB041B@CASON8 [SA684] AT45DB041B@SOIC28 [SA630]  
AT45DB041B@SOIC8 [SA023A] AT45DB041B@TSOP28 [SA430T-B4003]  
AT45DB041D(page256)@MLF8 [SA683]  
AT45DB041D(page256)@SOIC8[150] [SA602]  
AT45DB041D(page256)@SOIC8[200] [SA023A]  
AT45DB041D(page264)@MLF8 [SA683]  
AT45DB041D(page264)@SOIC8[150] [SA602]  
AT45DB041D(page264)@SOIC8[200] [SA023A]  
AT45DB041E(page256)@MLF8 [SA683]  
AT45DB041E(page256)@SOIC8[150] [SA602]  
AT45DB041E(page256)@SOIC8[200] [SA023A]  
AT45DB041E(page264)@MLF8 [SA683]  
AT45DB041E(page264)@SOIC8[150] [SA602]  
AT45DB041E(page264)@SOIC8[200] [SA023A]  
AT45DB081@SOIC28 [SA630] AT45DB081@TSOP32 [SA410T-B4001]  
AT45DB081A@PLCC32 [SA015A1T] AT45DB081A@SOIC28 [SA630]  
AT45DB081A@TSOP28 [SA430T-B4003] AT45DB081B@CASON8 [SA684]  
AT45DB081B@CBGA14 [\$\$\$\$\$\$] AT45DB081B@SOIC28 [SA630]  
AT45DB081B@SOIC8 [SA023A] AT45DB081B@TSOP28 [SA430T-B4003]  
AT45DB081D(256 byte)@MLF8 [SA683]  
AT45DB081D(256 byte)@SOIC8 [SA023A]  
AT45DB081D(256 byte)@SOIC8[150] [SA602]  
AT45DB081D@MLF8 [SA683] AT45DB081D@SOIC8 [SA023A]  
AT45DB081D@SOIC8[150 mil] [SA602]  
AT45DB161@PLCC32 [SA015A1T] AT45DB161@SOIC28 [SA630]  
AT45DB161@TSOP28 [SA430T-B4003] AT45DB161B@CASON8 [SA684]  
AT45DB161B@SOIC28 [SA630] AT45DB161B@TSOP28 [SA430T-B4003]  
AT45DB161D(page512)@SOIC8 [SA023A]

AT45DB161D(page528)@SOIC8 [SA023A]  
AT45DB161E@QFN8[512B] [SA683] AT45DB161E@QFN8[528B] [SA683]  
AT45DB161E@SOIC8(150 mil)[512B] [SA602]  
AT45DB161E@SOIC8(150 mil)[528B] [SA602]  
AT45DB161E@SOIC8[512B] [SA023A] AT45DB161E@SOIC8[528B] [SA023A]  
AT45DB321@TSOP32 [SA410T-B4001] AT45DB321B@SOIC28 [SA630]  
AT45DB321B@TSOP32 [SA410T-B4001] AT45DB321C@CASON8 [SA684]  
AT45DB321C@SOIC28 [SA630] AT45DB321C@TSOP28 [SA430T-B4003]  
AT45DB642@TSOP40 [SA409T-B4002] AT45DB642D@CASON8 [SA684]  
AT45DB642D@CASON8(ISP)  
AT45DB642D@CASON8[page1024] [SA684]  
AT45DB642D@TSOP28 [SA430T-B4003] AT45DB642D@TSOP28(ISP)  
AT45DB642D@TSOP28[page1024] [SA430T-B4003]  
AT49BV001 AT49BV001@PLCC32 [SA015A1T]  
AT49BV001@TSOP32 [SA410T-B4001] AT49BV001@VSOP32 [SA620-B4807]  
AT49BV001A AT49BV001A@PLCC32 [SA015A1T]  
AT49BV001A@TSOP32 [SA410T-B4001] AT49BV001A@VSOP32 [SA620-B4807]  
AT49BV001AN AT49BV001AN@PLCC32 [SA015A1T]  
AT49BV001AN@TSOP32 [SA410T-B4001]  
AT49BV001AN@VSOP32 [SA620-B4807] AT49BV001ANT  
AT49BV001ANT@PLCC32 [SA015A1T]  
AT49BV001ANT@TSOP32 [SA410T-B4001]  
AT49BV001ANT@VSOP32 [SA620-B4807]  
AT49BV001AT AT49BV001AT@PLCC32 [SA015A1T]  
AT49BV001AT@TSOP32 [SA410T-B4001]  
AT49BV001AT@VSOP32 [SA620-B4807] AT49BV001N  
AT49BV001N@PLCC32 [SA015A1T] AT49BV001N@TSOP32 [SA410T-B4001]  
AT49BV001N@VSOP32 [SA620-B4807] AT49BV001NT  
AT49BV001NT@PLCC32 [SA015A1T]  
AT49BV001NT@TSOP32 [SA410T-B4001]  
AT49BV001NT@VSOP32 [SA620-B4807] AT49BV001T  
AT49BV001T@PLCC32 [SA015A1T] AT49BV001T@TSOP32 [SA410T-B4001]  
AT49BV001T@VSOP32 [SA620-B4807] AT49BV002  
AT49BV002@PLCC32 [SA015A1T] AT49BV002@TSOP32 [SA410T-B4001]  
AT49BV002@VSOP32 [SA620-B4807] AT49BV002A  
AT49BV002A@PLCC32 [SA015A1T] AT49BV002A@TSOP32 [SA410T-B4001]  
AT49BV002A@VSOP32 [SA620-B4807] AT49BV002AN  
AT49BV002AN@PLCC32 [SA015A1T]  
AT49BV002AN@TSOP32 [SA410T-B4001]  
AT49BV002AN@VSOP32 [SA620-B4807] AT49BV002ANT  
AT49BV002ANT@PLCC32 [SA015A1T]  
AT49BV002ANT@TSOP32 [SA410T-B4001]  
AT49BV002ANT@VSOP32 [SA620-B4807]  
AT49BV002AT AT49BV002AT@PLCC32 [SA015A1T]  
AT49BV002AT@TSOP32 [SA410T-B4001]  
AT49BV002AT@VSOP32 [SA620-B4807] AT49BV002N  
AT49BV002N@PLCC32 [SA015A1T] AT49BV002N@TSOP32 [SA410T-B4001]  
AT49BV002N@VSOP32 [SA620-B4807] AT49BV002NT  
AT49BV002NT@PLCC32 [SA015A1T]  
AT49BV002NT@TSOP32 [SA410T-B4001]  
AT49BV002NT@VSOP32 [SA620-B4807] AT49BV002T  
AT49BV002T@PLCC32 [SA015A1T] AT49BV002T@TSOP32 [SA410T-B4001]  
AT49BV002T@VSOP32 [SA620-B4807] AT49BV008@TSOP40 [SA409T-B4002]

AT49BV008A@TSOP40 [SA409T-B4002]  
AT49BV008AT@TSOP40 [SA409T-B4002]  
AT49BV010  
AT49BV010@TSOP32 [SA410T-B4001]  
AT49BV020  
AT49BV020@TSOP32 [SA410T-B4001]  
AT49BV040  
AT49BV040@TSOP32 [SA410T-B4001]  
AT49BV040A@PLCC32 [SA015A1T]  
AT49BV040A@VSOP32 [SA620-B4807]  
AT49BV040B@TSOP32 [SA410T-B4001]  
AT49BV040T  
AT49BV040T@TSOP32 [SA410T-B4001]  
AT49BV080@PSOP44 [SA638]  
AT49BV080T@PSOP44 [SA638]  
AT49BV1024A@TSOP40 [SA623-B4002]  
AT49BV1604@TSOP48 [SB247-B4806]  
AT49BV1604AT@TSOP48 [SB247-B4806]  
AT49BV1604T@TSOP48 [SB247-B4806]  
AT49BV160CT@TSOP48 [SB247-B4806]  
AT49BV160DT@TSOP48 [SB247-B4806]  
AT49BV161@TSOP48 [SB247-B4806]  
AT49BV1614A@TSOP48 [SB247-B4806]  
AT49BV1614AT@TSOP48 [SB247-B4806]  
AT49BV1614T@TSOP48 [SB247-B4806]  
AT49BV1618T@TSOP48 [SB247-B4806]  
AT49BV162A@TSOP48 [SB247-B4806]  
AT49BV163A@TSOP48 [SB247-B4806]  
AT49BV163D@TSOP48 [SB247-B4806]  
AT49BV2048@PSOP44 [SA638]  
AT49BV2048A@PSOP44 [SA638]  
AT49BV2048B@TSOP48 [SB247-B4806]  
AT49BV320A@TSOP48 [SB247-B4806]  
AT49BV320C@TSOP48 [SB247-B4806]  
AT49BV320D@TSOP48 [SB247-B4806]  
AT49BV320T@TSOP48 [SB247-B4806]  
AT49BV3214T@TSOP48 [SB247-B4806]  
AT49BV3218T@TSOP48 [SB247-B4806]  
AT49BV322A@TSOP48 [SB247-B4806]  
AT49BV322D@TSOP48 [SB247-B4806]  
AT49BV4096@PSOP44 [SA638]  
AT49BV4096A@PSOP44 [SA638]  
AT49BV512  
AT49BV512@TSOP32 [SA410T-B4001]  
AT49BV6416@TSOP48 [SB247-B4806]  
AT49BV642D@TSOP48 [SB247-B4806]  
AT49BV8004@TSOP48 [SB247-B4806]  
AT49BV8011@TSOP48 [SB247-B4806]  
AT49BV802A@TSOP48 [SB247-B4806]  
AT49BV802D@TSOP48 [SB247-B4806]  
AT49BV8192@PSOP44 [SA638]  
AT49BV8192A@PSOP44 [SA638]  
AT49BV8192AT@PSOP44 [SA638]  
AT49BV010@PLCC32 [SA015A1T]  
AT49BV010@VSOP32 [SA620-B4807]  
AT49BV020@PLCC32 [SA015A1T]  
AT49BV020@VSOP32 [SA620-B4807]  
AT49BV040@PLCC32 [SA015A1T]  
AT49BV040@VSOP32 [SA620-B4807]  
AT49BV040A@TSOP32 [SA410T-B4001]  
AT49BV040B@PLCC32 [SA015A1T]  
AT49BV040B@VSOP32 [SA620-B4807]  
AT49BV040T@PLCC32 [SA015A1T]  
AT49BV040T@VSOP32 [SA620-B4807]  
AT49BV080@TSOP40 [SA409T-B4002]  
AT49BV080T@TSOP40 [SA409T-B4002]  
AT49BV160@TSOP48 [SB247-B4806]  
AT49BV1604A@TSOP48 [SB247-B4806]  
AT49BV160C@TSOP48 [SB247-B4806]  
AT49BV160D@TSOP48 [SB247-B4806]  
AT49BV160T@TSOP48 [SB247-B4806]  
AT49BV1614@TSOP48 [SB247-B4806]  
AT49BV1618@TSOP48 [SB247-B4806]  
AT49BV161T@TSOP48 [SB247-B4806]  
AT49BV162AT@TSOP48 [SB247-B4806]  
AT49BV163AT@TSOP48 [SB247-B4806]  
AT49BV163DT@TSOP48 [SB247-B4806]  
AT49BV2048@TSOP48 [SB247-B4806]  
AT49BV2048A@TSOP48 [SB247-B4806]  
AT49BV320@TSOP48 [SB247-B4806]  
AT49BV320AT@TSOP48 [SB247-B4806]  
AT49BV320CT@TSOP48 [SB247-B4806]  
AT49BV320DT@TSOP48 [SB247-B4806]  
AT49BV321@TSOP48 [SB247-B4806]  
AT49BV3218@TSOP48 [SB247-B4806]  
AT49BV321T@TSOP48 [SB247-B4806]  
AT49BV322AT@TSOP48 [SB247-B4806]  
AT49BV322DT@TSOP48 [SB247-B4806]  
AT49BV4096@TSOP48 [SB247-B4806]  
AT49BV4096A@TSOP48 [SB247-B4806]  
AT49BV512@PLCC32 [SA015A1T]  
AT49BV512@VSOP32 [SA620-B4807]  
AT49BV6416T@TSOP48 [SB247-B4806]  
AT49BV642DT@TSOP48 [SB247-B4806]  
AT49BV8004T@TSOP48 [SB247-B4806]  
AT49BV8011T@TSOP48 [SB247-B4806]  
AT49BV802AT@TSOP48 [SB247-B4806]  
AT49BV802DT@TSOP48 [SB247-B4806]  
AT49BV8192@TSOP48 [SB247-B4806]  
AT49BV8192A@TSOP48 [SB247-B4806]

AT49BV8192AT@TSOP48 [SB247-B4806]  
AT49BV8192T@PSOP44 [SA638]  
AT49F001  
AT49F001@TSOP32 [SA410T-B4001]  
AT49F001A  
AT49F001A@TSOP32 [SA410T-B4001]  
AT49F001AN  
AT49F001AN@TSOP32 [SA410T-B4001]  
AT49F001ANT  
AT49F001ANT@TSOP32 [SA410T-B4001]  
AT49F001ANT@VSOP32 [SA620-B4807]  
AT49F001AT@PLCC32 [SA015A1T]  
AT49F001AT@VSOP32 [SA620-B4807]  
AT49F001N@PLCC32 [SA015A1T]  
AT49F001N@VSOP32 [SA620-B4807]  
AT49F001NT@PLCC32 [SA015A1T]  
AT49F001NT@VSOP32 [SA620-B4807]  
AT49F001T@PLCC32 [SA015A1T]  
AT49F001T@VSOP32 [SA620-B4807]  
AT49F002@PLCC32 [SA015A1T]  
AT49F002@VSOP32 [SA620-B4807]  
AT49F002A@PLCC32 [SA015A1T]  
AT49F002A@VSOP32 [SA620-B4807]  
AT49F002AN@PLCC32 [SA015A1T]  
AT49F002AN@VSOP32 [SA620-B4807]  
AT49F002ANT@PLCC32 [SA015A1T]  
AT49F002ANT@TSOP32 [SA410T-B4001]  
AT49F002ANT@VSOP32 [SA620-B4807]  
AT49F002AT@PLCC32 [SA015A1T]  
AT49F002AT@VSOP32 [SA620-B4807]  
AT49F002N@PLCC32 [SA015A1T]  
AT49F002N@VSOP32 [SA620-B4807]  
AT49F002NT@PLCC32 [SA015A1T]  
AT49F002NT@VSOP32 [SA620-B4807]  
AT49F002T@PLCC32 [SA015A1T]  
AT49F002T@VSOP32 [SA620-B4807]  
AT49F008A@TSOP40 [SA409T-B4002]  
AT49F010  
AT49F010@TSOP32 [SA410T-B4001]  
AT49F020@PLCC32 [SA015A1T]  
AT49F040  
AT49F040@TSOP32 [SA410T-B4001]  
AT49F040A@PLCC32 [SA015A1T]  
AT49F040T  
AT49F040T@TSOP32 [SA410T-B4001]  
AT49F080@TSOP40 [SA409T-B4002]  
AT49F080T@TSOP40 [SA409T-B4002]  
AT49F1024A@TSOP40 [SA623-B4002]  
AT49F1025@TSOP40 [SA623-B4002]  
AT49F1604T@TSOP48 [SB247-B4806]  
AT49F1614T@TSOP48 [SB247-B4806]  
AT49F2048@TSOP48 [SB247-B4806]  
AT49F2048A@TSOP48 [SB247-B4806]

AT49BV8192T@TSOP48 [SB247-B4806]  
AT49F001@PLCC32 [SA015A1T]  
AT49F001@VSOP32 [SA620-B4807]  
AT49F001A@PLCC32 [SA015A1T]  
AT49F001A@VSOP32 [SA620-B4807]  
AT49F001AN@PLCC32 [SA015A1T]  
AT49F001AN@VSOP32 [SA620-B4807]  
AT49F001ANT@PLCC32 [SA015A1T]  
AT49F001AT  
AT49F001AT@TSOP32 [SA410T-B4001]  
AT49F001N  
AT49F001N@TSOP32 [SA410T-B4001]  
AT49F001NT  
AT49F001NT@TSOP32 [SA410T-B4001]  
AT49F001T  
AT49F001T@TSOP32 [SA410T-B4001]  
AT49F002  
AT49F002@TSOP32 [SA410T-B4001]  
AT49F002A  
AT49F002A@TSOP32 [SA410T-B4001]  
AT49F002AN  
AT49F002AN@TSOP32 [SA410T-B4001]  
AT49F002ANT  
AT49F002AT  
AT49F002AT@TSOP32 [SA410T-B4001]  
AT49F002N  
AT49F002N@TSOP32 [SA410T-B4001]  
AT49F002NT  
AT49F002NT@TSOP32 [SA410T-B4001]  
AT49F002T  
AT49F002T@TSOP32 [SA410T-B4001]  
AT49F008@TSOP40 [SA409T-B4002]  
AT49F008AT@TSOP40 [SA409T-B4002]  
AT49F010@PLCC32 [SA015A1T]  
AT49F020  
AT49F020@TSOP32 [SA410T-B4001]  
AT49F040@PLCC32 [SA015A1T]  
AT49F040A  
AT49F040A@TSOP32 [SA410T-B4001]  
AT49F040T@PLCC32 [SA015A1T]  
AT49F080@PSOP44 [SA638]  
AT49F080T@PSOP44 [SA638]  
AT49F1024@TSOP40 [SA623-B4002]  
AT49F1025@PLCC44 [SA244]  
AT49F1604@TSOP48 [SB247-B4806]  
AT49F1614@TSOP48 [SB247-B4806]  
AT49F2048@PSOP44 [SA638]  
AT49F2048A@PSOP44 [SA638]  
AT49F4096@PSOP44 [SA638]

AT49F4096@TSOP48 [SB247-B4806]  
AT49F4096A@TSOP48 [SB247-B4806]  
AT49F512@PLCC32 [SA015A1T]  
AT49F512@VSOP32 [SA620-B4807]  
AT49F516@TSOP40 [SA623-B4002]  
AT49F8004T@TSOP48 [SB247-B4806]  
AT49F8011T@TSOP48 [SB247-B4806]  
AT49F8192@TSOP48 [SB247-B4806]  
AT49F8192A@TSOP48 [SB247-B4806]  
AT49F8192AT@TSOP48 [SB247-B4806]  
AT49F8192T@TSOP48 [SB247-B4806]  
AT49HBV010@PLCC32 [SA015A1T]  
AT49HBV010@VSOP32 [SA620-B4807]  
AT49HF010@PLCC32 [SA015A1T]  
AT49HLV010  
AT49HLV010@TSOP32 [SA410T-B4001]  
AT49LH002@PLCC32 [SA015A1T]  
AT49LH004@PLCC32 [SA015A1T]  
AT49LH00B4@PLCC32 [SA015A1T]  
AT49LL020@PLCC32 [SA015A1T]  
AT49LL040@PLCC32 [SA015A1T]  
AT49LL080@PLCC32 [SA015A1T]  
AT49LV001  
AT49LV001@TSOP32 [SA410T-B4001]  
AT49LV001N  
AT49LV001N@TSOP32 [SA410T-B4001]  
AT49LV001NT  
AT49LV001NT@TSOP32 [SA410T-B4001]  
AT49LV001NT@VSOP32 [SA620-B4807]  
AT49LV001T@PLCC32 [SA015A1T]  
AT49LV001T@VSOP32 [SA620-B4807]  
AT49LV002@PLCC32 [SA015A1T]  
AT49LV002@VSOP32 [SA620-B4807]  
AT49LV002N@PLCC32 [SA015A1T]  
AT49LV002N@VSOP32 [SA620-B4807]  
AT49LV002NT@PLCC32 [SA015A1T]  
AT49LV002NT@TSOP32 [SA410T-B4001]  
AT49LV002NT@VSOP32 [SA620-B4807]  
AT49LV002T@PLCC32 [SA015A1T]  
AT49LV002T@VSOP32 [SA620-B4807]  
AT49LV008A@TSOP40 [SA409T-B4002]  
AT49LV008AT@TSOP40 [SA409T-B4002]  
AT49LV010  
AT49LV010@TSOP32 [SA410T-B4001]  
AT49LV020  
AT49LV020@TSOP32 [SA410T-B4001]  
AT49LV040  
AT49LV040@TSOP32 [SA410T-B4001]  
AT49LV040T  
AT49LV040T@TSOP32 [SA410T-B4001]  
AT49LV080@PSOP44 [SA638]  
AT49LV080T@PSOP44 [SA638]  
AT49LV1024@TSOP40 [SA623-B4002]  
AT49F4096A@PSOP44 [SA638]  
AT49F512  
AT49F512@TSOP32 [SA410T-B4001]  
AT49F516@PLCC44 [SA244]  
AT49F8004@TSOP48 [SB247-B4806]  
AT49F8011@TSOP48 [SB247-B4806]  
AT49F8192@PSOP44 [SA638]  
AT49F8192A@PSOP44 [SA638]  
AT49F8192AT@PSOP44 [SA638]  
AT49F8192T@PSOP44 [SA638]  
AT49HBV010  
AT49HBV010@TSOP32 [SA410T-B4001]  
AT49HF010  
AT49HF010@TSOP32 [SA410T-B4001]  
AT49HLV010@PLCC32 [SA015A1T]  
AT49HLV010@VSOP32 [SA620-B4807]  
AT49LH002@TSOP40 [SA409T-B4002]  
AT49LH004@TSOP40 [SA409T-B4002]  
AT49LH00B4@TSOP40 [SA409T-B4002]  
AT49LL020@TSOP40 [SA409T-B4002]  
AT49LL040@TSOP40 [SA409T-B4002]  
AT49LL080@TSOP40 [SA409T-B4002]  
AT49LV001@PLCC32 [SA015A1T]  
AT49LV001@VSOP32 [SA620-B4807]  
AT49LV001N@PLCC32 [SA015A1T]  
AT49LV001N@VSOP32 [SA620-B4807]  
AT49LV001NT@PLCC32 [SA015A1T]  
AT49LV001T  
AT49LV001T@TSOP32 [SA410T-B4001]  
AT49LV002  
AT49LV002@TSOP32 [SA410T-B4001]  
AT49LV002N  
AT49LV002N@TSOP32 [SA410T-B4001]  
AT49LV002NT  
AT49LV002T  
AT49LV002T@TSOP32 [SA410T-B4001]  
AT49LV008@TSOP40 [SA409T-B4002]  
AT49LV010@PLCC32 [SA015A1T]  
AT49LV010@VSOP32 [SA620-B4807]  
AT49LV020@PLCC32 [SA015A1T]  
AT49LV020@VSOP32 [SA620-B4807]  
AT49LV040@PLCC32 [SA015A1T]  
AT49LV040@VSOP32 [SA620-B4807]  
AT49LV040T@PLCC32 [SA015A1T]  
AT49LV040T@VSOP32 [SA620-B4807]  
AT49LV080@TSOP40 [SA409T-B4002]  
AT49LV080T@TSOP40 [SA409T-B4002]  
AT49LV1024A@TSOP40 [SA623-B4002]

AT49LV1025@PLCC44 [SA244]  
AT49LV1604@TSOP48 [SB247-B4806]  
AT49LV160T@TSOP48 [SB247-B4806]  
AT49LV1614@TSOP48 [SB247-B4806]  
AT49LV1614AT@TSOP48 [SB247-B4806]  
AT49LV1614T@TSOP48 [SB247-B4806]  
AT49LV2048@PSOP44 [SA638]  
AT49LV2048A@PSOP44 [SA638]  
AT49LV2048B@TSOP48 [SB247-B4806]  
AT49LV320T@TSOP48 [SB247-B4806]  
AT49LV3218@TSOP48 [SB247-B4806]  
AT49LV321T@TSOP48 [SB247-B4806]  
AT49LV4096A@TSOP48 [SB247-B4806]  
AT49LV8011T@TSOP48 [SB247-B4806]  
AT49LV8192@TSOP48 [SB247-B4806]  
AT49LV8192A@TSOP48 [SB247-B4806]  
AT49LV8192AT@TSOP48 [SB247-B4806]  
AT49LV8192T@PSOP44 [SA638]  
AT49LW040@PLCC32 [SA015A1T]  
AT49LW080@PLCC32 [SA015A1T]  
AT49SV163D@TSOP48 [SB247-B4806]  
AT49SV322A@TSOP48 [SB247-B4806]  
AT49SV322D@TSOP48 [SB247-B4806]  
AT49SV802A@TSOP48 [SB247-B4806]  
AT59C11  
AT59C12  
AT59C13  
AT59C22  
AT88SC0104  
AT88SC0204  
AT88SC0404@SOIC8 [SA602]  
AT88SC0808C@SOIC8 (FULL) [SA602]  
AT93C46 (08bit)@SOIC8 [SA602A]  
AT93C46 (16bit)  
AT93C46 (16bit)@TSSOP8 [SA643]  
AT93C46A@SOIC8 [SA602A]  
AT93C46C  
AT93C46C@TSSOP8 [SA643]  
AT93C46D (08bit)@MAP8 [SA724]  
AT93C46D (08bit)@TSSOP8 [SA643]  
AT93C46D (16bit)@MAP8 [SA724]  
AT93C46D (16bit)@TSSOP8 [SA643]  
AT93C46E@SOIC8 [SA602A]  
AT93C56 (08bit)  
AT93C56 (16bit)  
AT93C56A (08bit)  
AT93C56A (08bit)@TSSOP8 [SA643]  
AT93C56A (16bit)  
AT93C56A (16bit)@TSSOP8 [SA643]  
AT93C56AW (16bit)@SOIC8 [SA605B]  
AT93C56B (08bit)@SOIC8 [SA602A]  
AT93C56B (08bit)@UDFN8 [SA724]  
AT93C56B (08bit)@XDFN8  
AT49LV160@TSOP48 [SB247-B4806]  
AT49LV1604T@TSOP48 [SB247-B4806]  
AT49LV161@TSOP48 [SB247-B4806]  
AT49LV1614A@TSOP48 [SB247-B4806]  
AT49LV161T@TSOP48 [SB247-B4806]  
AT49LV2048@TSOP48 [SB247-B4806]  
AT49LV2048A@TSOP48 [SB247-B4806]  
AT49LV320@TSOP48 [SB247-B4806]  
AT49LV321@TSOP48 [SB247-B4806]  
AT49LV3218T@TSOP48 [SB247-B4806]  
AT49LV4096A@PSOP44 [SA638]  
AT49LV8011@TSOP48 [SB247-B4806]  
AT49LV8192@PSOP44 [SA638]  
AT49LV8192A@PSOP44 [SA638]  
AT49LV8192AT@PSOP44 [SA638]  
AT49LV8192T@TSOP48 [SB247-B4806]  
AT49LW040@TSOP40 [SA409T-B4002]  
AT49LW080@TSOP40 [SA409T-B4002]  
AT49SV163DT@TSOP48 [SB247-B4806]  
AT49SV322AT@TSOP48 [SB247-B4806]  
AT49SV322DT@TSOP48 [SB247-B4806]  
AT49SV802AT@TSOP48 [SB247-B4806]  
AT59C11@SOIC8 [SA602A]  
AT59C12@SOIC8 [SA602A]  
AT59C13@SOIC8 [SA602A]  
AT59C22@SOIC8 [SA602A]  
AT88SC0104@SOIC8 [SA602]  
AT88SC0204@SOIC8 [SA602]  
AT88SC0808@SOIC8 [SA602]  
AT93C46 (08bit)  
AT93C46 (08bit)@TSSOP8 [SA643]  
AT93C46 (16bit)@SOIC8 [SA602A]  
AT93C46A  
AT93C46A@TSSOP8 [SA643]  
AT93C46C@SOIC8 [SA602A]  
AT93C46D (08bit)  
AT93C46D (08bit)@SOIC8 [SA602A]  
AT93C46D (16bit)  
AT93C46D (16bit)@SOIC8 [SA602A]  
AT93C46E  
AT93C46E@TSSOP8 [SA643]  
AT93C56 (08bit)@SOIC8 [SA602A]  
AT93C56 (16bit)@SOIC8 [SA602A]  
AT93C56A (08bit)@SOIC8 [SA602A]  
AT93C56A (08bit)@UDFN8 [SA724]  
AT93C56A (16bit)@SOIC8 [SA602A]  
AT93C56AW (08bit)@SOIC8 [SA605B]  
AT93C56B (08bit)  
AT93C56B (08bit)@TSSOP8 [SA643]  
AT93C56B (08bit)@VFNGA8 [\$\$\$\$\$]  
AT93C56B (16bit)

AT93C56B(16bit)@SOIC8 [SA602A]	AT93C56B(16bit)@TSSOP8 [SA643]
AT93C56B(16bit)@UDFN8 [SA724]	AT93C56B(16bit)@VFNGA8 [\$\$\$\$\$]
AT93C56B(16bit)@XDFN8	AT93C57
AT93C57@SOIC8 [SA602A]	AT93C66(08bit)
AT93C66(08bit)@SOIC8 [SA602A]	AT93C66(16bit)
AT93C66(16bit)@SOIC8 [SA602A]	AT93C66A(08bit)
AT93C66A(08bit)@SOIC8 [SA602A]	AT93C66A(08bit)@TSSOP8 [SA643]
AT93C66A(16bit)	AT93C66A(16bit)@SOIC8 [SA602A]
AT93C66A(16bit)@TSSOP8 [SA643]	AT93C66A(16bit)@UDFN8 [SA724]
AT93C66AW(08bit)@SOIC8 [SA605B]	AT93C66AW(16bit)@SOIC8 [SA605B]
AT93C66B(08bit)	AT93C66B(08bit)@SOIC8 [SA602A]
AT93C66B(08bit)@TSSOP8 [SA643]	AT93C66B(08bit)@UDFN8 [SA724]
AT93C66B(08bit)@VFNGA8 [\$\$\$\$\$]	AT93C66B(08bit)@XDFN8
AT93C66B(16bit)	AT93C66B(16bit)@SOIC8 [SA602A]
AT93C66B(16bit)@TSSOP8 [SA643]	AT93C66B(16bit)@UDFN8 [SA724]
AT93C66B(16bit)@VFNGA8 [\$\$\$\$\$]	AT93C66B(16bit)@XDFN8
AT93C86(08bit)	AT93C86(08bit)@SOIC8 [SA602A]
AT93C86(08bit)@TSSOP8 [SA643]	AT93C86(16bit)
AT93C86(16bit)@SOIC8 [SA602A]	AT93C86(16bit)@TSSOP8 [SA643]
AT93C86A(08bit)	AT93C86A(08bit)@SOIC8 [SA602A]
AT93C86A(08bit)@TSSOP8 [SA643]	AT93C86A(16bit)
AT93C86A(16bit)@SOIC8 [SA602A]	AT93C86A(16bit)@TSSOP8 [SA643]
NS0001@SOIC8 [SA602]	

## DRAM & SRAM

AT3864L	AT3864L@TSOP28 [SA643]
AT38H256	AT38H256@TSOP28 [SA643]

## PLD

ATF16LV8C	ATF16LV8C@PLCC20 [SA001A-B2001]
ATF16LV8C@SOIC20 [SA404]	ATF16LV8C@TSOP20 [SA026]
ATF16LV8CEXT	
ATF16LV8CEXT@PLCC20 [SA001A-B2001]	ATF16LV8CEXT@TSOP20 [SA026]
ATF16LV8CEXT@SOIC20 [SA404]	ATF16V8B@PLCC20 [SA001A-B2001]
ATF16V8B	ATF16V8B@TSOP20 [SA026]
ATF16V8B@SOIC20 [SA404]	ATF16V8BL@PLCC20 [SA001A-B2001]
ATF16V8BL	ATF16V8BL@TSOP20 [SA026]
ATF16V8BL@SOIC20 [SA404]	ATF16V8BQ@PLCC20 [SA001A-B2001]
ATF16V8BQ	ATF16V8BQ@TSOP20 [SA026]
ATF16V8BQ@SOIC20 [SA404]	ATF16V8BQL@PLCC20 [SA001A-B2001]
ATF16V8BQL	ATF16V8BQL@TSOP20 [SA026]
ATF16V8BQL@SOIC20 [SA404]	ATF16V8C@PLCC20 [SA001A-B2001]
ATF16V8C	ATF16V8C@TSOP20 [SA026]
ATF16V8C@SOIC20 [SA404]	
ATF16V8CEXT	
ATF16V8CEXT@PLCC20 [SA001A-B2001]	ATF16V8CEXT@TSOP20 [SA026]
ATF16V8CEXT@SOIC20 [SA404]	ATF16V8CZ@PLCC20 [SA001A-B2001]
ATF16V8CZ	ATF16V8CZ@TSOP20 [SA026]
ATF16V8CZ@SOIC20 [SA404]	ATF20V8B@PLCC28 [SA008A]
ATF20V8B	

ATF20V8B@SOIC24 [SA620-B4807]  
ATF20V8BL@PLCC28 [SA008A]  
ATF20V8BQ  
ATF20V8BQ@SOIC24 [SA620-B4807]  
ATF20V8BQL@PLCC28 [SA008A]  
ATF22LV10C  
ATF22LV10C (UES)@PLCC28 [SA008A]  
ATF22LV10C (UES)@TSSOP24 [SA026]  
ATF22LV10C@SOIC24 [SA404]  
ATF22LV10CEXT  
ATF22LV10CEXT@SOIC24 [SA404]  
ATF22LV10CQZ  
ATF22LV10CQZ (UES)@PLCC28 [SA008A]  
ATF22LV10CQZ (UES)@SOIC24 [SA404]  
ATF22LV10CQZ (UES)@TSSOP24 [SA026]  
ATF22LV10CQZ@PLCC28 [SA008A]  
ATF22LV10CQZ@TSSOP24 [SA026]  
ATF22LV10CZ (UES)  
ATF22LV10CZ (UES)@SOIC24 [SA404]  
ATF22LV10CZ@PLCC28 [SA008A]  
ATF22LV10CZ@TSSOP24 [SA026]  
ATF22V10B@PLCC28 [SA008A]  
ATF22V10BL  
ATF22V10BL@SOIC24 [SA404]  
ATF22V10BQ@PLCC28 [SA008A]  
ATF22V10BQL  
ATF22V10BQL@SOIC24 [SA404]  
ATF22V10C (UES)  
ATF22V10C (UES)@SOIC24 [SA404]  
ATF22V10C@PLCC28 [SA008A]  
ATF22V10C@TSSOP24 [SA026]  
ATF22V10CEXT@PLCC28 [SA008A]  
ATF22V10CEXT@TSSOP24 [SA026]  
ATF22V10CQ (UES)  
ATF22V10CQ (UES)@SOIC24 [SA404]  
ATF22V10CQ@PLCC28 [SA008A]  
ATF22V10CQ@TSSOP24 [SA026]  
ATF22V10CQZ (UES)  
ATF22V10CQZ (UES)@SOIC24 [SA404]  
ATF22V10CQZ@PLCC28 [SA008A]  
ATF22V10CQZ@TSSOP24 [SA026]  
ATF22V10CZ (UES)  
ATF22V10CZ (UES)@SOIC24 [SA404]  
ATF22V10CZ@PLCC28 [SA008A]  
ATF22V10CZ@TSSOP24 [SA026]  
ATV750@PLCC28 [SA008A]  
ATV750B  
ATV750B@SOIC24 [SA404]  
ATV750BL@PLCC28 [SA008A]  
ATV750L  
ATV750L@SOIC24 [SA404]

ATF20V8BL  
ATF20V8BL@SOIC24 [SA620-B4807]  
ATF20V8BQ@PLCC28 [SA008A]  
ATF20V8BQL  
ATF20V8BQL@SOIC24 [SA620-B4807]  
ATF22LV10C (UES)  
ATF22LV10C (UES)@SOIC24 [SA404]  
ATF22LV10C@PLCC28 [SA008A]  
ATF22LV10C@TSSOP24 [SA026]  
ATF22LV10CEXT@PLCC28 [SA008A]  
ATF22LV10CEXT@TSSOP24 [SA026]  
ATF22LV10CQZ (UES)  
  
ATF22LV10CQZ@SOIC24 [SA404]  
ATF22LV10CZ  
ATF22LV10CZ (UES)@PLCC28 [SA008A]  
ATF22LV10CZ (UES)@TSSOP24 [SA026]  
ATF22LV10CZ@SOIC24 [SA404]  
ATF22V10B  
ATF22V10B@SOIC24 [SA404]  
ATF22V10BL@PLCC28 [SA008A]  
ATF22V10BQ  
ATF22V10BQ@SOIC24 [SA404]  
ATF22V10BQL@PLCC28 [SA008A]  
ATF22V10C  
ATF22V10C (UES)@PLCC28 [SA008A]  
ATF22V10C (UES)@TSSOP24 [SA026]  
ATF22V10C@SOIC24 [SA404]  
ATF22V10CEXT  
ATF22V10CEXT@SOIC24 [SA404]  
ATF22V10CQ  
ATF22V10CQ (UES)@PLCC28 [SA008A]  
ATF22V10CQ (UES)@TSSOP24 [SA026]  
ATF22V10CQ@SOIC24 [SA404]  
ATF22V10CQZ  
ATF22V10CQZ (UES)@PLCC28 [SA008A]  
ATF22V10CQZ (UES)@TSSOP24 [SA026]  
ATF22V10CQZ@SOIC24 [SA404]  
ATF22V10CZ  
ATF22V10CZ (UES)@PLCC28 [SA008A]  
ATF22V10CZ (UES)@TSSOP24 [SA026]  
ATF22V10CZ@SOIC24 [SA404]  
ATV750  
ATV750@SOIC24 [SA404]  
ATV750B@PLCC28 [SA008A]  
ATV750BL  
ATV750BL@SOIC24 [SA404]  
ATV750L@PLCC28 [SA008A]

## MICROCONTROLLER

AT32UC3A0128@TQFP144 (ISP)  
AT32UC3A0512@TQFP144 (ISP)  
AT32UC3A1256@TQFP100 (ISP)  
AT32UC3B0128@QFN64 (ISP)  
AT32UC3B0256@QFN64 (ISP)  
AT32UC3B064@QFN64 (ISP)  
AT32UC3B1128@QFN48 (ISP)  
AT32UC3B1256@QFN48 (ISP)  
AT32UC3B164@QFN48 (ISP)  
AT80F51  
AT80F51@TQFP44 [SA245A-B4805]  
AT80F52@PLCC44 [SA244]  
AT87C51RB2  
AT87C51RB2@TQFP44 [SA675-B4805]  
AT87C51RC2@PLCC44 [SA244]  
AT87C51RD2  
AT87C51RD2@TQFP44 [SA675-B4805]  
AT87C51U2@PLCC44 [SA244]  
AT87C52X2  
AT87C52X2@TQFP44 [SA675-B4805]  
AT87C54X2@PLCC44 [SA244]  
AT87C58X2  
AT87C58X2@TQFP44 [SA675-B4805]  
AT87F51@PLCC44 [SA244]  
AT87F51RC  
AT87F51RC@TQFP44 [SA675-B4805]  
AT87F52@PLCC44 [SA244]  
AT87F55  
AT87F55@TQFP44 [SA675-B4805]  
AT87F55WD@PLCC44 [SA244]  
AT87LV51  
AT87LV51@TQFP44 [SA675-B4805]  
AT87LV52@PLCC44 [SA244]  
AT89C1051  
AT89C1051U  
AT89C2051  
AT89C2051X2  
AT89C4051  
AT89C51  
AT89C51@PQFP44 [SA675-B4805]  
AT89C51AC2@PLCC44 [SA244]  
AT89C51AC3@PLCC44 [SA244]  
AT89C51CC01@PLCC44 [SA244]  
AT89C51CC01@TQFP44 [SA245A-B4805]  
AT89C51CC03C@PLCC44 [SA244]  
AT89C51CC03C@TQFP44 [SA245A-B4805]  
AT89C51CC03CA@PLCC44 [SA244]  
AT89C51CC03CA@TQFP44 [SA245A-B4805]  
AT89C51CC03U@PLCC44 [SA244]  
AT89C51CC03U@TQFP44 [SA245A-B4805]  
AT89C51CC03UA@PLCC44 [SA244]

AT32UC3A0256@TQFP144 (ISP)  
AT32UC3A1128@TQFP100 (ISP)  
AT32UC3A1512@TQFP100 (ISP)  
AT32UC3B0128@TQFP64 (ISP)  
AT32UC3B0256@TQFP64 (ISP)  
AT32UC3B064@TQFP64 (ISP)  
AT32UC3B1128@TQFP48 (ISP)  
AT32UC3B1256@TQFP48 (ISP)  
AT32UC3B164@TQFP48 (ISP)  
AT80F51@PLCC44 [SA244]  
AT80F52  
AT80F52@TQFP44 [SA245A-B4805]  
AT87C51RB2@PLCC44 [SA244]  
AT87C51RC2  
AT87C51RC2@TQFP44 [SA675-B4805]  
AT87C51RD2@PLCC44 [SA244]  
AT87C51U2  
AT87C51U2@TQFP44 [SA675-B4805]  
AT87C52X2@PLCC44 [SA244]  
AT87C54X2  
AT87C54X2@TQFP44 [SA675-B4805]  
AT87C58X2@PLCC44 [SA244]  
AT87F51  
AT87F51@TQFP44 [SA675-B4805]  
AT87F51RC@PLCC44 [SA244]  
AT87F52  
AT87F52@TQFP44 [SA675-B4805]  
AT87F55@PLCC44 [SA244]  
AT87F55WD  
AT87F55WD@TQFP44 [SA675-B4805]  
AT87LV51@PLCC44 [SA244]  
AT87LV52  
AT87LV52@TQFP44 [SA675-B4805]  
AT89C1051@SOIC20 [SA404]  
AT89C1051U@SOIC20 [SA404]  
AT89C2051@SOIC20 [SA404]  
AT89C2051X2@SOIC20 [SA404]  
AT89C4051@SOIC20 [SA404]  
AT89C51@PLCC44 [SA244]  
AT89C51@TQFP44 [SA245A-B4805]  
AT89C51AC2@TQFP44 [SA245A-B4805]  
AT89C51AC3@TQFP44 [SA245A-B4805]

AT89C51CC03UA@TQFP44 [SA245A-B4805]  
AT89C51ED2 AT89C51ED2@PLCC44 [SA244]  
AT89C51ED2@PLCC68(\*) [SA648-B6808]  
AT89C51ED2@TQFP44 [SA245A-B4805]  
AT89C51ED2@TQFP64(\*) [TA054-B006]  
AT89C51IC2@PLCC44 [SA244] AT89C51IC2@TQFP44 [SA245A-B4805]  
AT89C51ID2 AT89C51ID2@PLCC44 [SA244]  
AT89C51ID2@PLCC68(\*) [SA648-B6808]  
AT89C51ID2@TQFP44 [SA245A-B4805]  
AT89C51ID2@TQFP64(\*) [TA054-B006]  
AT89C51RB2 AT89C51RB2@PLCC44 [SA244]  
AT89C51RB2@TQFP44 [SA245A-B4805] AT89C51RC  
AT89C51RC@PLCC44 [SA244] AT89C51RC@TQFP44 [SA245A-B4805]  
AT89C51RC2 AT89C51RC2@PLCC44 [SA244]  
AT89C51RC2@TQFP44 [SA245A-B4805] AT89C51RD2  
AT89C51RD2@PLCC44 [SA244]  
AT89C51RD2@PLCC68(\*) [SA648-B6808]  
AT89C51RD2@TQFP44 [SA245A-B4805]  
AT89C51RD2@TQFP64(\*) [TA054-B006]  
AT89C51RE2@PLCC44 [SA244] AT89C51RE2@VQFP44 [SA245A-B4805]  
AT89C52 AT89C52@PLCC44 [SA244]  
AT89C52@PQFP44 [SA675-B4805] AT89C52@TQFP44 [SA245A-B4805]  
AT89C55 AT89C55@PLCC44 [SA244]  
AT89C55@PQFP44 [SA675-B4805] AT89C55@TQFP44 [SA245A-B4805]  
AT89C55WD AT89C55WD@PLCC44 [SA244]  
AT89C55WD@TQFP44 [SA245A-B4805] AT89LP2051  
AT89LP2051@S0IC20 [SA404] AT89LP2051@TSSOP20 [SA026]  
AT89LP2052 AT89LP2052 (ISP)  
AT89LP2052@S0IC20 [SA404] AT89LP2052@S0IC20 (ISP)  
AT89LP2052@TSSOP20 [SA026] AT89LP2052@TSSOP20 (ISP)  
AT89LP213 AT89LP213 (ISP)  
AT89LP213@TSSOP14 [SA626A] AT89LP213@TSSOP14 (ISP)  
AT89LP214 AT89LP214 (ISP)  
AT89LP214@TSSOP14 [SA626A] AT89LP214@TSSOP14 (ISP)  
AT89LP216 AT89LP216 (ISP)  
AT89LP216@S0IC16 [SA404] AT89LP216@S0IC16 (ISP)  
AT89LP216@TSSOP16 [SA626A] AT89LP216@TSSOP16 (ISP)  
AT89LP3240 AT89LP3240 (ISP)  
AT89LP3240@MLF44 [SA712] AT89LP3240@MLF44 (ISP)  
AT89LP3240@PLCC44 [SA244] AT89LP3240@PLCC44 (ISP)  
AT89LP3240@TQFP44 [SA245A-B4805] AT89LP3240@TQFP44 (ISP)  
AT89LP4051 AT89LP4051@S0IC20 [SA404]  
AT89LP4051@TSSOP20 [SA026] AT89LP4052  
AT89LP4052 (ISP) AT89LP4052@S0IC20 [SA404]  
AT89LP4052@S0IC20 (ISP) AT89LP4052@TSSOP20 [SA026]  
AT89LP4052@TSSOP20 (ISP) AT89LP428  
AT89LP428 (ISP) AT89LP428@PLCC32 [SA015A1T]  
AT89LP428@PLCC32 (ISP) AT89LP428@TQFP32 [SA636]  
AT89LP428@TQFP32 (ISP) AT89LP51  
AT89LP51@PLCC44 [SA244] AT89LP51@TQFP44 [SA245A-B4805]  
AT89LP51ED2 AT89LP51ED2@MLF44 [SA712]  
AT89LP51ED2@PLCC44 [SA244]  
AT89LP51ED2@TQFP44 [SA245A-B4805]

AT89LP51ID2  
AT89LP51ID2@MLF44 [SA712]  
AT89LP51ID2@TQFP44 [SA245A-B4805]  
AT89LP51RB2  
AT89LP51RB2@MLF44 [SA712]  
AT89LP51RB2@TQFP44 [SA245A-B4805]  
AT89LP51RC2  
AT89LP51RC2@MLF44 [SA712]  
AT89LP51RC2@TQFP44 [SA245A-B4805]  
AT89LP51RD2  
AT89LP51RD2@MLF44 [SA712]  
AT89LP51RD2@TQFP44 [SA245A-B4805]  
AT89LP52  
AT89LP52@TQFP44 [SA245A-B4805]  
AT89LP6440 (ISP)  
AT89LP6440@MLF44 (ISP)  
AT89LP6440@PLCC44 (ISP)  
AT89LP6440@TQFP44 (ISP)  
AT89LP828 (ISP)  
AT89LP828@PLCC32 (ISP)  
AT89LP828@TQFP32 (ISP)  
AT89LS51 (ISP)  
AT89LS51@PLCC44 (ISP)  
AT89LS51@TQFP44 (ISP)  
AT89LS52 (ISP)  
AT89LS52@PLCC44 (ISP)  
AT89LS52@TQFP44 (ISP)  
AT89LS53 (ISP)  
AT89LS53@PLCC44 (ISP)  
AT89LS53@TQFP44 (ISP)  
AT89LS8252 (ISP)  
AT89LS8252@PLCC44 (ISP)  
AT89LS8252@TQFP44 (ISP)  
AT89LV51@PLCC44 [SA244]  
AT89LV52  
AT89LV52@TQFP44 [SA245A-B4805]  
AT89LV55@PLCC44 [SA244]  
AT89S2051  
AT89S4051  
AT89S51  
AT89S51@PLCC44 [SA244]  
AT89S51@TQFP44 [SA245A-B4805]  
AT89S52  
AT89S52@PLCC44 [SA244]  
AT89S52@TQFP44 [SA245A-B4805]  
AT89S53  
AT89S53@PLCC44 [SA244]  
AT89S53@TQFP44 [SA245A-B4805]  
AT89S54  
AT89S54@TQFP44 [SA245A-B4805]  
AT89S58@PLCC44 [SA244]  
AT89S64  
AT89S64@TQFP44 [SA245A-B4805]

AT89LP51ID2 (isp)  
AT89LP51ID2@PLCC44 [SA244]  
AT89LP51RB2 (isp)  
AT89LP51RB2@PLCC44 [SA244]  
AT89LP51RC2 (isp)  
AT89LP51RC2@PLCC44 [SA244]  
AT89LP51RD2 (isp)  
AT89LP51RD2@PLCC44 [SA244]  
AT89LP52@PLCC44 [SA244]  
AT89LP6440  
AT89LP6440@MLF44 [SA712]  
AT89LP6440@PLCC44 [SA244]  
AT89LP6440@TQFP44 [SA245A-B4805]  
AT89LP828  
AT89LP828@PLCC32 [SA015A1T]  
AT89LP828@TQFP32 [SA636]  
AT89LS51  
AT89LS51@PLCC44 [SA244]  
AT89LS51@TQFP44 [SA245A-B4805]  
AT89LS52  
AT89LS52@PLCC44 [SA244]  
AT89LS52@TQFP44 [SA245A-B4805]  
AT89LS53  
AT89LS53@PLCC44 [SA244]  
AT89LS53@TQFP44 [SA245A-B4805]  
AT89LS8252  
AT89LS8252@PLCC44 [SA244]  
AT89LS8252@TQFP44 [SA245A-B4805]  
AT89LV51  
AT89LV51@TQFP44 [SA245A-B4805]  
AT89LV52@PLCC44 [SA244]  
AT89LV55  
AT89LV55@TQFP44 [SA245A-B4805]  
AT89S2051@SOIC20 [SA404]  
AT89S4051@SOIC20 [SA404]  
AT89S51 (ISP)  
AT89S51@PLCC44 (ISP)  
AT89S51@TQFP44 (ISP)  
AT89S52 (ISP)  
AT89S52@PLCC44 (ISP)  
AT89S52@TQFP44 (ISP)  
AT89S53 (ISP)  
AT89S53@PLCC44 (ISP)  
AT89S53@TQFP44 (ISP)  
AT89S54@PLCC44 [SA244]  
AT89S58  
AT89S58@TQFP44 [SA245A-B4805]  
AT89S64@PLCC44 [SA244]  
AT89S8252

AT89S8252 (ISP)  
AT89S8252@PLCC44 (ISP)  
AT89S8252@TQFP44 [SA245A-B4805]  
AT89S8253  
AT89S8253@TQFP44 [SA245A-B4805]  
AT90LS2323@SOIC8 [SA605B]  
AT90LS2333@TQFP32 [SA636]  
AT90LS2343@SOIC8 [SA605B]  
AT90LS4433@TQFP32 [SA636]  
AT90LS4434@PLCC44 [SA244]  
AT90LS8535  
AT90LS8535@TQFP44 [SA245A-B4805]  
AT90PWM161@SOIC20 [SA404]  
AT90S1200@SOIC20 [SA404]  
AT90S1200A  
AT90S1200A@SSOP20 [SA626A]  
AT90S2313@SOIC20 [SA404]  
AT90S2323@SOIC8 [SA605B]  
AT90S2333@TQFP32 [SA636]  
AT90S2343@SOIC8 [SA605B]  
AT90S4414@PLCC44 [SA244]  
AT90S4433  
AT90S4434  
AT90S4434@TQFP44 [SA245A-B4805]  
AT90S8515@PLCC44 [SA244]  
AT90S8535  
AT90S8535@TQFP44 [SA245A-B4805]  
AT90USB162@QFN32 (ISP)  
AT90USB162@VQFP32 (ISP)  
AT90USB82@QFN32 (ISP)  
ATC71RBX2@PLCC44 [SA244]  
ATC71RCX2  
ATC71RCX2@TQFP44 [SA675-B4805]  
ATC71RDX2@PLCC44 [SA244]  
ATC87C51  
ATC87C51@TQFP44 [SA675-B4805]  
ATC87C52@PLCC44 [SA244]  
ATC87C54  
ATC87C54@TQFP44 [SA675-B4805]  
ATC87C58@PLCC44 [SA244]  
ATMEGA128@MLF64 (ISP)  
ATMEGA1280@CBGA100 (ISP)  
ATMEGA1280V@CBGA100 (ISP)  
ATMEGA1281@MLF64 (ISP)  
ATMEGA1281V@MLF64 (ISP)  
ATMEGA1284  
ATMEGA1284@MLF44 [SA712]  
ATMEGA1284@TQFP44 (ISP)  
ATMEGA1284P (ISP)  
ATMEGA1284P@MLF44 (ISP)  
ATMEGA1284P@TQFP44 [SA245A-B4805]  
ATMEGA1284P@TQFP44 (ISP)  
ATMEGA1284PV (ISP)

AT89S8252@PLCC44 [SA244]  
AT89S8252@PQFP44 [SA675-B4805]  
AT89S8252@TQFP44 (ISP)  
AT89S8253@PLCC44 [SA244]  
AT90LS2323  
AT90LS2333  
AT90LS2343  
AT90LS4433  
AT90LS4434  
AT90LS4434@TQFP44 [SA245A-B4805]  
AT90LS8535@PLCC44 [SA244]  
AT90PWM161@QFN32 [SA686]  
AT90S1200  
AT90S1200@SSOP20 [SA626A]  
AT90S1200A@SOIC20 [SA404]  
AT90S2313  
AT90S2323  
AT90S2333  
AT90S2343  
AT90S4414  
AT90S4414@TQFP44 [SA245A-B4805]  
AT90S4433@TQFP32 [SA636]  
AT90S4434@PLCC44 [SA244]  
AT90S8515  
AT90S8515@TQFP44 [SA245A-B4805]  
AT90S8535@PLCC44 [SA244]  
AT90USB162@QFN32 [SA686]  
AT90USB162@VQFP32 [SA636]  
AT90USB82@QFN32 [SA686]  
ATC71RBX2  
ATC71RBX2@TQFP44 [SA675-B4805]  
ATC71RCX2@PLCC44 [SA244]  
ATC71RDX2  
ATC71RDX2@TQFP44 [SA675-B4805]  
ATC87C51@PLCC44 [SA244]  
ATC87C52  
ATC87C52@TQFP44 [SA675-B4805]  
ATC87C54@PLCC44 [SA244]  
ATC87C58  
ATC87C58@TQFP44 [SA675-B4805]  
ATMEGA128@TQFP64 (ISP)  
ATMEGA1280@TQFP100 (ISP)  
ATMEGA1280V@TQFP100 (ISP)  
ATMEGA1281@TQFP64 (ISP)  
ATMEGA1281V@TQFP64 (ISP)  
ATMEGA1284 (ISP)  
ATMEGA1284@MLF44 (ISP)  
ATMEGA1284P  
ATMEGA1284P@MLF44 [SA712]  
  
ATMEGA1284PV  
ATMEGA1284PV@MLF44 [SA712]

ATMEGA1284PV@MLF44 (ISP)  
ATMEGA1284PV@TQFP44 [SA245A-B4805]  
ATMEGA1284PV@TQFP44 (ISP)  
ATMEGA128L@MLF64 (ISP)  
ATMEGA16  
ATMEGA16@TQFP44 [SA245A-B4805]  
ATMEGA161@TQFP44 [SA675-B4805]  
ATMEGA161L@TQFP44 [SA675-B4805]  
ATMEGA162 (ISP)  
ATMEGA162@MLF44 (ISP)  
ATMEGA162@TQFP44 (ISP)  
ATMEGA162V (ISP)  
ATMEGA162V@MLF44 (ISP)  
ATMEGA162V@TQFP44 (ISP)  
ATMEGA163@TQFP44 [SA675-B4805]  
ATMEGA163L@TQFP44 [SA675-B4805]  
ATMEGA164 (ISP)  
ATMEGA164@MLF44 (ISP)  
ATMEGA164@TQFP44 (ISP)  
ATMEGA164A (ISP)  
ATMEGA164A@MLF44 (ISP)  
ATMEGA164A@TQFP44 (ISP)  
ATMEGA164A@VFBGA49 (ISP)  
ATMEGA164P (ISP)  
ATMEGA164P@MLF44 (ISP)  
ATMEGA164P@TQFP44 (ISP)  
ATMEGA164PA (ISP)  
ATMEGA164PA@MLF44 (ISP)  
ATMEGA164PA@TQFP44 [SA245A-B4805]  
ATMEGA164PA@TQFP44 (ISP)  
ATMEGA164PA@VFBGA49 (ISP)  
ATMEGA164PV (ISP)  
ATMEGA164PV@MLF44 (ISP)  
ATMEGA164PV@TQFP44 [SA245A-B4805]  
ATMEGA164PV@TQFP44 (ISP)  
ATMEGA164V (ISP)  
ATMEGA164V@MLF44 (ISP)  
ATMEGA164V@TQFP44 (ISP)  
ATMEGA168 (ISP)  
ATMEGA168@MLF32 [SA686]  
ATMEGA168@MLP32 (ISP)  
ATMEGA168@TQFP32 (ISP)  
ATMEGA168A@MLF28 [SA780]  
ATMEGA168A@TQFP32 [SA636]  
ATMEGA168P (ISP)  
ATMEGA168P@MLF32 [SA686]  
ATMEGA168P@MLP32 (ISP)  
ATMEGA168P@TQFP32 (ISP)  
ATMEGA168PA@MLF28 [SA780]  
ATMEGA168PA@TQFP32 [SA636]  
ATMEGA168PV (ISP)  
ATMEGA168PV@MLF32 [SA686]  
ATMEGA168PV@MLP32 (ISP)  
ATMEGA1284-Q44 [SA245A-B4805]  
ATMEGA128L@TQFP64 (ISP)  
ATMEGA16@MLF44 [SA712]  
ATMEGA161  
ATMEGA161L  
ATMEGA162  
ATMEGA162@MLF44 [SA712]  
ATMEGA162@TQFP44 [SA245A-B4805]  
ATMEGA162V  
ATMEGA162V@MLF44 [SA712]  
ATMEGA162V@TQFP44 [SA245A-B4805]  
ATMEGA163  
ATMEGA163L  
ATMEGA164  
ATMEGA164@MLF44 [SA712]  
ATMEGA164@TQFP44 [SA245A-B4805]  
ATMEGA164A  
ATMEGA164A@MLF44 [SA712]  
ATMEGA164A@TQFP44 [SA245A-B4805]  
ATMEGA164A@VFBGA49 [\$\$\$\$\$]  
ATMEGA164P  
ATMEGA164P@MLF44 [SA712]  
ATMEGA164P@TQFP44 [SA245A-B4805]  
ATMEGA164PA  
ATMEGA164PA@MLF44 [SA712]  
  
ATMEGA164PA@VFBGA49 [\$\$\$\$\$]  
ATMEGA164PV  
ATMEGA164PV@MLF44 [SA712]  
  
ATMEGA164V  
ATMEGA164V@MLF44 [SA712]  
ATMEGA164V@TQFP44 [SA245A-B4805]  
ATMEGA168  
ATMEGA168@MLF28 [SA780]  
ATMEGA168@MLP28 (ISP)  
ATMEGA168@TQFP32 [SA636]  
ATMEGA168A  
ATMEGA168A@MLF32 [SA686]  
ATMEGA168P  
ATMEGA168P@MLF28 [SA780]  
ATMEGA168P@MLP28 (ISP)  
ATMEGA168P@TQFP32 [SA636]  
ATMEGA168PA  
ATMEGA168PA@MLF32 [SA686]  
ATMEGA168PV  
ATMEGA168PV@MLF28 [SA780]  
ATMEGA168PV@MLP28 (ISP)  
ATMEGA168PV@TQFP32 [SA636]

ATMEGA168PV@TQFP32 (ISP)  
ATMEGA168V (ISP)  
ATMEGA168V@MLF32 [SA686]  
ATMEGA168V@MLP32 (ISP)  
ATMEGA168V@TQFP32 (ISP)  
ATMEGA169@TQFP64 (ISP)  
ATMEGA169P@TQFP64 (ISP)  
ATMEGA169PV@TQFP64 (ISP)  
ATMEGA169V@TQFP64 (ISP)  
ATMEGA16A@MLF44 [SA712]  
ATMEGA16HVA@TSOP28 (ISP)  
ATMEGA16L@MLF44 [SA712]  
ATMEGA16M1@MLF32 [SA686]  
ATMEGA16M1@TQFP32 [SA636]  
ATMEGA16U2@MLF32 [SA686]  
ATMEGA16U4@MLF44 [SA712]  
ATMEGA16U4@TQFP44 [SA245A-B4805]  
ATMEGA2560@CBGA100 (ISP)  
ATMEGA2560V@CBGA100 (ISP)  
ATMEGA2561@MLF64 (ISP)  
ATMEGA2561V@MLF64 (ISP)  
ATMEGA32  
ATMEGA32@TQFP44 [SA245A-B4805]  
ATMEGA323@TQFP44 [SA675-B4805]  
ATMEGA323L@TQFP44 [SA675-B4805]  
ATMEGA324 (ISP)  
ATMEGA324@MLF44 (ISP)  
ATMEGA324@TQFP44 (ISP)  
ATMEGA324A (ISP)  
ATMEGA324A@MLF44 (ISP)  
ATMEGA324A@TQFP44 (ISP)  
ATMEGA324A@VFBGA49 (ISP)  
ATMEGA324P (ISP)  
ATMEGA324P@MLF44 (ISP)  
ATMEGA324P@TQFP44 (ISP)  
ATMEGA324PA (ISP)  
ATMEGA324PA@MLF44 (ISP)  
ATMEGA324PA@TQFP44 [SA245A-B4805]  
ATMEGA324PA@TQFP44 (ISP)  
ATMEGA324PA@VFBGA49 (ISP)  
ATMEGA324PV (ISP)  
ATMEGA324PV@MLF44 (ISP)  
ATMEGA324PV@TQFP44 [SA245A-B4805]  
ATMEGA324PV@TQFP44 (ISP)  
ATMEGA324V (ISP)  
ATMEGA324V@MLF44 (ISP)  
ATMEGA324V@TQFP44 (ISP)  
ATMEGA328@MLF28 [SA780]  
ATMEGA328@TQFP32 [SA636]  
ATMEGA328P (ISP)  
ATMEGA328P@MLF32 [SA686]  
ATMEGA328P@MLP32 (ISP)  
ATMEGA328P@TQFP32 (ISP)

ATMEGA168V  
ATMEGA168V@MLF28 [SA780]  
ATMEGA168V@MLP28 (ISP)  
ATMEGA168V@TQFP32 [SA636]  
ATMEGA169@MLF64 (ISP)  
ATMEGA169P@MLF64 (ISP)  
ATMEGA169PV@MLF64 (ISP)  
ATMEGA169V@MLF64 (ISP)  
ATMEGA16A  
ATMEGA16A@TQFP44 [SA245A-B4805]  
ATMEGA16L  
ATMEGA16L@TQFP44 [SA245A-B4805]  
ATMEGA16M1@MLF32 (ISP)  
ATMEGA16M1@TQFP32 (ISP)  
ATMEGA16U2@VQFP32 [SA636]  
ATMEGA16U4@MLF44 (ISP)  
ATMEGA16U4@TQFP44 (ISP)  
ATMEGA2560@TQFP100 (ISP)  
ATMEGA2560V@TQFP100 (ISP)  
ATMEGA2561@TQFP64 (ISP)  
ATMEGA2561V@TQFP64 (ISP)  
ATMEGA32@MLF44 [SA712]  
ATMEGA323  
ATMEGA323L  
ATMEGA324  
ATMEGA324@MLF44 [SA712]  
ATMEGA324@TQFP44 [SA245A-B4805]  
ATMEGA324A  
ATMEGA324A@MLF44 [SA712]  
ATMEGA324A@TQFP44 [SA245A-B4805]  
ATMEGA324A@VFBGA49 [\$\$\$\$\$]  
ATMEGA324P  
ATMEGA324P@MLF44 [SA712]  
ATMEGA324P@TQFP44 [SA245A-B4805]  
ATMEGA324PA  
ATMEGA324PA@MLF44 [SA712]  
  
ATMEGA324PA@VFBGA49 [\$\$\$\$\$]  
ATMEGA324PV  
ATMEGA324PV@MLF44 [SA712]  
  
ATMEGA324V  
ATMEGA324V@MLF44 [SA712]  
ATMEGA324V@TQFP44 [SA245A-B4805]  
ATMEGA328  
ATMEGA328@MLF32 [SA686]  
ATMEGA328P  
ATMEGA328P@MLF28 [SA780]  
ATMEGA328P@MLP28 (ISP)  
ATMEGA328P@TQFP32 [SA636]  
ATMEGA328PB@TQFP32 [SA636]

ATMEGA328PV  
ATMEGA328PV@MLF28 [SA780]  
ATMEGA328PV@MLP28 (ISP)  
ATMEGA328PV@TQFP32 [SA636]  
ATMEGA32A  
ATMEGA32A@TQFP44 [SA245A-B4805]  
ATMEGA32C1@MLF32 (ISP)  
ATMEGA32C1@TQFP32 (ISP)  
ATMEGA32L@MLF44 [SA712]  
ATMEGA32M1@MLF32 [SA686]  
ATMEGA32M1@TQFP32 [SA636]  
ATMEGA32U2@MLF32 [SA686]  
ATMEGA32U4@MLF44 [SA712]  
ATMEGA32U4@TQFP44 [SA245A-B4805]  
ATMEGA406@LQFP48 [SA248-B4804]  
ATMEGA48 (ISP)  
ATMEGA48@MLF32 [SA686]  
ATMEGA48@MLP32 (ISP)  
ATMEGA48@TQFP32 (ISP)  
ATMEGA48A@MLF28 [SA780]  
ATMEGA48A@TQFP32 [SA636]  
ATMEGA48P (ISP)  
ATMEGA48P@MLF32 [SA686]  
ATMEGA48P@MLP32 (ISP)  
ATMEGA48P@TQFP32 (ISP)  
ATMEGA48PA@MLF28 [SA780]  
ATMEGA48PA@TQFP32 [SA636]  
ATMEGA48PV (ISP)  
ATMEGA48PV@MLF32 [SA686]  
ATMEGA48PV@MLP32 (ISP)  
ATMEGA48PV@TQFP32 (ISP)  
ATMEGA48V (ISP)  
ATMEGA48V@MLF32 [SA686]  
ATMEGA48V@MLP32 (ISP)  
ATMEGA48V@TQFP32 (ISP)  
ATMEGA64@TQFP64 (ISP)  
ATMEGA640@TQFP100 (ISP)  
ATMEGA640V@TQFP100 (ISP)  
ATMEGA644 (ISP)  
ATMEGA644@MLF44 (ISP)  
ATMEGA644@TQFP44 (ISP)  
ATMEGA644A (ISP)  
ATMEGA644A@MLF44 (ISP)  
ATMEGA644A@TQFP44 (ISP)  
ATMEGA644P (ISP)  
ATMEGA644P@MLF44 (ISP)  
ATMEGA644P@TQFP44 (ISP)  
ATMEGA644PA (ISP)  
ATMEGA644PA@MLF44 (ISP)  
ATMEGA644PA@TQFP44 [SA245A-B4805]  
ATMEGA644PA@TQFP44 (ISP)  
ATMEGA644PV (ISP)  
ATMEGA644PV@MLF44 (ISP)

ATMEGA328PV (ISP)  
ATMEGA328PV@MLF32 [SA686]  
ATMEGA328PV@MLP32 (ISP)  
ATMEGA328PV@TQFP32 (ISP)  
ATMEGA32A@MLF44 [SA712]  
ATMEGA32C1@MLF32 [SA686]  
ATMEGA32C1@TQFP32 [SA636]  
ATMEGA32L  
ATMEGA32L@TQFP44 [SA245A-B4805]  
ATMEGA32M1@MLF32 (ISP)  
ATMEGA32M1@TQFP32 (ISP)  
ATMEGA32U2@VQFP32 [SA636]  
ATMEGA32U4@MLF44 (ISP)  
ATMEGA32U4@TQFP44 (ISP)  
ATMEGA48  
ATMEGA48@MLF28 [SA780]  
ATMEGA48@MLP28 (ISP)  
ATMEGA48@TQFP32 [SA636]  
ATMEGA48A  
ATMEGA48A@MLF32 [SA686]  
ATMEGA48P  
ATMEGA48P@MLF28 [SA780]  
ATMEGA48P@MLP28 (ISP)  
ATMEGA48P@TQFP32 [SA636]  
ATMEGA48PA  
ATMEGA48PA@MLF32 [SA686]  
ATMEGA48PV  
ATMEGA48PV@MLF28 [SA780]  
ATMEGA48PV@MLP28 (ISP)  
ATMEGA48PV@TQFP32 [SA636]  
ATMEGA48V  
ATMEGA48V@MLF28 [SA780]  
ATMEGA48V@MLP28 (ISP)  
ATMEGA48V@TQFP32 [SA636]  
ATMEGA64@MLF64 (ISP)  
ATMEGA640@CBGA100 (ISP)  
ATMEGA640V@CBGA100 (ISP)  
ATMEGA644  
ATMEGA644@MLF44 [SA712]  
ATMEGA644@TQFP44 [SA245A-B4805]  
ATMEGA644A  
ATMEGA644A@MLF44 [SA712]  
ATMEGA644A@TQFP44 [SA245A-B4805]  
ATMEGA644P  
ATMEGA644P@MLF44 [SA712]  
ATMEGA644P@TQFP44 [SA245A-B4805]  
ATMEGA644PA  
ATMEGA644PA@MLF44 [SA712]  
ATMEGA644PV  
ATMEGA644PV@MLF44 [SA712]

ATMEGA644PV@TQFP44 [SA245A-B4805]  
ATMEGA644PV@TQFP44 (ISP)  
ATMEGA644V (ISP)  
ATMEGA644V@MLF44 (ISP)  
ATMEGA644V@TQFP44 (ISP)  
ATMEGA64C1@MLF32 (ISP)  
ATMEGA64C1@TQFP32 (ISP)  
ATMEGA64L@TQFP64 (ISP)  
ATMEGA64M1@MLF32 (ISP)  
ATMEGA64M1@TQFP32 (ISP)  
ATMEGA8 (ISP)  
ATMEGA8@MLF32 (ISP)  
ATMEGA8@TQFP32 (ISP)  
ATMEGA8515@MLF44 [SA712]  
ATMEGA8515@TQFP44 [SA245A-B4805]  
ATMEGA8515L@MLF44 [SA712]  
ATMEGA8515L@TQFP44 [SA245A-B4805]  
ATMEGA8535  
ATMEGA8535@MLF44 [SA712]  
ATMEGA8535@PLCC44 [SA244]  
ATMEGA8535@TQFP44 [SA245A-B4805]  
ATMEGA8535L  
ATMEGA8535L@MLF44 [SA712]  
ATMEGA8535L@PLCC44 [SA244]  
ATMEGA8535L@TQFP44 [SA245A-B4805]  
ATMEGA8535L@TQFP44 (ISP)  
ATMEGA88 (ISP)  
ATMEGA88@MLF32 [SA686]  
ATMEGA88@MLP32 (ISP)  
ATMEGA88@TQFP32 (ISP)  
ATMEGA88A@MLF28 [SA780]  
ATMEGA88A@TQFP32 [SA636]  
ATMEGA88P (ISP)  
ATMEGA88P@MLF32 [SA686]  
ATMEGA88P@MLP32 (ISP)  
ATMEGA88P@TQFP32 (ISP)  
ATMEGA88PA@MLF28 [SA780]  
ATMEGA88PA@TQFP32 [SA636]  
ATMEGA88PV (ISP)  
ATMEGA88PV@MLF32 [SA686]  
ATMEGA88PV@MLP32 (ISP)  
ATMEGA88PV@TQFP32 (ISP)  
ATMEGA88V (ISP)  
ATMEGA88V@MLF32 [SA686]  
ATMEGA88V@MLP32 (ISP)  
ATMEGA88V@TQFP32 (ISP)  
ATMEGA8A@MLF32 [SA686]  
ATMEGA8HVA@TSOP28 (ISP)  
ATMEGA8L (ISP)  
ATMEGA8L@MLF32 (ISP)  
ATMEGA8L@TQFP32 (ISP)  
ATMEGA8U2@VQFP32 [SA636]  
ATtiny10 (ISP)

ATMEGA644V  
ATMEGA644V@MLF44 [SA712]  
ATMEGA644V@TQFP44 [SA245A-B4805]  
ATMEGA64C1@MLF32 [SA686]  
ATMEGA64C1@TQFP32 [SA636]  
ATMEGA64L@MLF64 (ISP)  
ATMEGA64M1@MLF32 [SA686]  
ATMEGA64M1@TQFP32 [SA636]  
ATMEGA8  
ATMEGA8@MLF32 [SA686]  
ATMEGA8@TQFP32 [SA636]  
ATMEGA8515  
ATMEGA8515@PLCC44 [SA244]  
ATMEGA8515L  
ATMEGA8515L@PLCC44 [SA244]  
ATMEGA8535 (ISP)  
ATMEGA8535@MLF44 (ISP)  
ATMEGA8535@PLCC44 (ISP)  
ATMEGA8535@TQFP44 (ISP)  
ATMEGA8535L (ISP)  
ATMEGA8535L@MLF44 (ISP)  
ATMEGA8535L@PLCC44 (ISP)  
ATMEGA88  
ATMEGA88@MLF28 [SA780]  
ATMEGA88@MLP28 (ISP)  
ATMEGA88@TQFP32 [SA636]  
ATMEGA88A  
ATMEGA88A@MLF32 [SA686]  
ATMEGA88P  
ATMEGA88P@MLF28 [SA780]  
ATMEGA88P@MLP28 (ISP)  
ATMEGA88P@TQFP32 [SA636]  
ATMEGA88PA  
ATMEGA88PA@MLF32 [SA686]  
ATMEGA88PV  
ATMEGA88PV@MLF28 [SA780]  
ATMEGA88PV@MLP28 (ISP)  
ATMEGA88PV@TQFP32 [SA636]  
ATMEGA88V  
ATMEGA88V@MLF28 [SA780]  
ATMEGA88V@MLP28 (ISP)  
ATMEGA88V@TQFP32 [SA636]  
ATMEGA8A  
ATMEGA8A@TQFP32 [SA636]  
ATMEGA8L  
ATMEGA8L@MLF32 [SA686]  
ATMEGA8L@TQFP32 [SA636]  
ATMEGA8U2@MLF32 [SA686]  
ATtiny10  
ATtiny10@SOIC8 [SA023A]

ATtiny10@SOIC8 (ISP)  
ATtiny10@SOT23 (ISP)  
ATtiny11  
ATtiny11@SOIC8 [SA023A]  
ATtiny11L  
ATtiny11L@SOIC8 [SA023A]  
ATtiny12  
ATtiny12@SOIC8 [SA023A]  
ATtiny12L  
ATtiny12L@SOIC8 [SA023A]  
ATtiny12V  
ATtiny12V@SOIC8 [SA023A]  
ATtiny13  
ATtiny13@MLF10 [SA695A]  
ATtiny13@MLF20 [SA692]  
ATtiny13@SOIC8 (3.9\*6.2) [SA602]  
ATtiny13@SOIC8 (5.5\*8.0) [SA023A]  
ATtiny13A  
ATtiny13A@MLF20 [SA692]  
ATtiny13A@SOIC8 (5.5\*8.0) [SA023A]  
ATtiny13V  
ATtiny13V@MLF10 [SA695A]  
ATtiny13V@MLF20 [SA692]  
ATtiny13V@SOIC8 (3.9\*6.2) [SA602]  
ATtiny13V@SOIC8 (5.5\*8.0) [SA023A]  
ATtiny13V@SOIC8 (5.5\*8.0) (ISP)  
ATtiny15 (ISP)  
ATtiny15@SOIC8 (ISP)  
ATtiny15L (ISP)  
ATtiny15L@SOIC8 (ISP)  
ATtiny1634@SOIC20 [SA404]  
ATtiny167@QFN32 (ISP)  
ATtiny167@SOIC20 (ISP)  
ATtiny167@TSSOP20 (ISP)  
ATtiny20@SOIC14 [SA602]  
ATtiny2313  
ATtiny2313@MLF20 [SA692]  
ATtiny2313@SOIC20 [SA404]  
ATtiny2313A  
ATtiny2313A@SOIC20 [SA404]  
ATtiny2313V (ISP)  
ATtiny2313V@QFN20 (ISP)  
ATtiny2313V@SOIC20 (ISP)  
ATtiny24 (ISP)  
ATtiny24@MLF20 [SA692]  
ATtiny24@MLF20 (low vol isp)  
ATtiny24@SOIC14 (ISP)  
ATtiny24A  
ATtiny24A@MLF20 (4\*4) [SA692]  
ATtiny24V  
ATtiny24V (low vol isp)  
ATtiny24V@MLF20 (ISP)  
ATtiny24V@SOIC14 [SA602]  
ATtiny10@SOT23 [SA717]  
ATtiny10@UDFN8 [\$\$\$\$\$\$]  
ATtiny11 (ISP)  
ATtiny11@SOIC8 (ISP)  
ATtiny11L (ISP)  
ATtiny11L@SOIC8 (ISP)  
ATtiny12 (ISP)  
ATtiny12@SOIC8 (ISP)  
ATtiny12L (ISP)  
ATtiny12L@SOIC8 (ISP)  
ATtiny12V (ISP)  
ATtiny12V@SOIC8 (ISP)  
ATtiny13 (ISP)  
ATtiny13@MLF10 (ISP)  
ATtiny13@MLF20 (ISP)  
ATtiny13@SOIC8 (3.9\*6.2) (ISP)  
ATtiny13@SOIC8 (5.5\*8.0) (ISP)  
ATtiny13A@MLF10 [SA695A]  
ATtiny13A@SOIC8 (3.9\*6.2) [SA602]  
ATtiny13V (ISP)  
ATtiny13V@MLF10 (ISP)  
ATtiny13V@MLF20 (ISP)  
ATtiny13V@SOIC8 (3.9\*6.2) (ISP)  
ATtiny15  
ATtiny15@SOIC8 [SA023A]  
ATtiny15L  
ATtiny15L@SOIC8 [SA023A]  
ATtiny1634@QFN20 [SA692]  
ATtiny167@QFN32 [SA686]  
ATtiny167@SOIC20 [SA404]  
ATtiny167@TSSOP20 [SA026]  
ATtiny20@QFN20 [\$\$\$\$\$\$]  
ATtiny20@TSSOP14 [SA026]  
ATtiny2313 (ISP)  
ATtiny2313@QFN20 (ISP)  
ATtiny2313@SOIC20 (ISP)  
ATtiny2313A@QFN20 [SA692]  
ATtiny2313V  
ATtiny2313V@MLF20 [SA692]  
ATtiny2313V@SOIC20 [SA404]  
ATtiny24  
ATtiny24 (low vol isp)  
ATtiny24@MLF20 (ISP)  
ATtiny24@SOIC14 [SA602]  
ATtiny24@SOIC14 (low vol isp)  
ATtiny24A@MLF20 (3\*3) [\$\$\$\$\$\$]  
ATtiny24A@SOIC14 [SA602]  
ATtiny24V (ISP)  
ATtiny24V@MLF20 [SA692]  
ATtiny24V@MLF20 (low vol isp)  
ATtiny24V@SOIC14 (ISP)

ATtiny24V@SOIC14(low vol isp)  
ATtiny25 (ISP)  
ATtiny25@MLF20 [SA692]  
ATtiny25@MLF20(low vol isp)  
ATtiny25@SOIC8 (ISP)  
ATtiny25V  
ATtiny25V(low vol isp)  
ATtiny25V@MLF20 (ISP)  
ATtiny25V@SOIC8 [SA023A]  
ATtiny25V@SOIC8(low vol isp)  
ATtiny26 (ISP)  
ATtiny26(new) (ISP)  
ATtiny26(new)@SOIC20 [SA404]  
ATtiny26(new)@TSSOP20 [SA026]  
ATtiny26@MLF32 [SA686]  
ATtiny26@SOIC20 [SA404]  
ATtiny26@TSSOP20 [SA026]  
ATtiny261  
ATtiny261@MLF32 [SA686]  
ATtiny261@SOIC20 [SA404]  
ATtiny261A  
ATtiny261A@MLF32 [SA686]  
ATtiny261A@SOIC20 [SA404]  
ATtiny261V  
ATtiny261V@MLF32 [SA686]  
ATtiny261V@SOIC20 [SA404]  
ATtiny26L  
ATtiny26L(new)  
ATtiny26L(new)@MLF32 [SA686]  
ATtiny26L(new)@SOIC20 (ISP)  
ATtiny26L(new)@TSSOP20 (ISP)  
ATtiny26L@MLF32 (ISP)  
ATtiny26L@SOIC20 (ISP)  
ATtiny26L@TSSOP20 (ISP)  
ATtiny26N@MLF32 (ISP)  
ATtiny28L@MLF32 [SA686]  
ATtiny28V  
ATtiny28V@TQFP32 [SA636]  
ATtiny4@UDFN8 [\$\$\$\$\$]  
ATtiny40@SOIC20 [SA404]  
ATtiny4313  
ATtiny4313@SOIC20 [SA404]  
ATtiny43U@SOIC20 [SA404]  
ATtiny44 (ISP)  
ATtiny44@MLF20 [SA692]  
ATtiny44@MLF20(low vol isp)  
ATtiny44@SOIC14 (ISP)  
ATtiny44A  
ATtiny44A@MLF20 (4\*4) [SA692]  
ATtiny44V  
ATtiny44V(low vol isp)  
ATtiny44V@MLF20 (ISP)  
ATtiny44V@SOIC14 [SA602]

ATtiny25  
ATtiny25(low vol isp)  
ATtiny25@MLF20 (ISP)  
ATtiny25@SOIC8 [SA023A]  
ATtiny25@SOIC8(low vol isp)  
ATtiny25V (ISP)  
ATtiny25V@MLF20 [SA692]  
ATtiny25V@MLF20(low vol isp)  
ATtiny25V@SOIC8 (ISP)  
ATtiny26  
ATtiny26(new)  
ATtiny26(new)@MLF32 [SA686]  
ATtiny26(new)@SOIC20 (ISP)  
ATtiny26(new)@TSSOP20 (ISP)  
ATtiny26@MLF32 (ISP)  
ATtiny26@SOIC20 (ISP)  
ATtiny26@TSSOP20 (ISP)  
ATtiny261 (ISP)  
ATtiny261@MLF32 (ISP)  
ATtiny261@SOIC20 (ISP)  
ATtiny261A (ISP)  
ATtiny261A@MLF32 (ISP)  
ATtiny261A@SOIC20 (ISP)  
ATtiny261V (ISP)  
ATtiny261V@MLF32 (ISP)  
ATtiny261V@SOIC20 (ISP)  
ATtiny26L (ISP)  
ATtiny26L(new) (ISP)  
ATtiny26L(new)@SOIC20 [SA404]  
ATtiny26L(new)@TSSOP20 [SA026]  
ATtiny26L@MLF32 [SA686]  
ATtiny26L@SOIC20 [SA404]  
ATtiny26L@TSSOP20 [SA026]  
ATtiny26LN@MLF32 (ISP)  
ATtiny28L  
ATtiny28L@TQFP32 [SA636]  
ATtiny28V@MLF32 [SA686]  
ATtiny4@SOT23 [SA717]  
ATtiny40@QFN20 [\$\$\$\$\$]  
ATtiny40@TSSOP20 [SA026]  
ATtiny4313@QFN20 [SA692]  
ATtiny43U@MLF20 [SA692]  
ATtiny44  
ATtiny44(low vol isp)  
ATtiny44@MLF20 (ISP)  
ATtiny44@SOIC14 [SA602]  
ATtiny44@SOIC14(low vol isp)  
ATtiny44A@MLF20 (3\*3) [\$\$\$\$\$]  
ATtiny44A@SOIC14 [SA602]  
ATtiny44V (ISP)  
ATtiny44V@MLF20 [SA692]  
ATtiny44V@MLF20(low vol isp)  
ATtiny44V@SOIC14 (ISP)

ATtiny44V@SOIC14(low vol isp)  
ATtiny45 (ISP)  
ATtiny45@MLF20 [SA692]  
ATtiny45@MLF20(low vol isp)  
ATtiny45@SOIC8 (ISP)  
ATtiny45V  
ATtiny45V(low vol isp)  
ATtiny45V@MLF20 (ISP)  
ATtiny45V@SOIC8 [SA023A]  
ATtiny45V@SOIC8(low vol isp)  
ATtiny461 (ISP)  
ATtiny461@MLF32 (ISP)  
ATtiny461@SOIC20 (ISP)  
ATtiny461A (ISP)  
ATtiny461A@MLF32 (ISP)  
ATtiny461A@SOIC20 (ISP)  
ATtiny461V (ISP)  
ATtiny461V@MLF32 (ISP)  
ATtiny461V@SOIC20 (ISP)  
ATtiny48 (ISP)  
ATtiny48@MLF28 (ISP)  
ATtiny48@MLF32 (ISP)  
ATtiny48@TQFP32 (ISP)  
ATtiny48V (ISP)  
ATtiny48V@MLF28 (ISP)  
ATtiny48V@MLF32 (ISP)  
ATtiny48V@TQFP32 (ISP)  
ATtiny5@UDFN8 [\$\$\$\$\$]  
ATtiny828@TQFP32 [SA636]  
ATtiny84 (ISP)  
ATtiny84@MLF20 [SA692]  
ATtiny84@MLF20(low vol isp)  
ATtiny84@SOIC14 (ISP)  
ATtiny84A  
ATtiny84A@MLF20(4\*4) [SA692]  
ATtiny84V  
ATtiny84V(low vol isp)  
ATtiny84V@MLF20 (ISP)  
ATtiny84V@SOIC14 [SA602]  
ATtiny84V@SOIC14(low vol isp)  
ATtiny85 (ISP)  
ATtiny85@MLF20 [SA692]  
ATtiny85@MLF20(low vol isp)  
ATtiny85@SOIC8 (ISP)  
ATtiny85V  
ATtiny85V(low vol isp)  
ATtiny85V@MLF20 (ISP)  
ATtiny85V@SOIC8 [SA023A]  
ATtiny85V@SOIC8(low vol isp)  
ATtiny861 (ISP)  
ATtiny861@MLF32 (ISP)  
ATtiny861@SOIC20 (ISP)  
ATtiny861A (ISP)

ATtiny45  
ATtiny45(low vol isp)  
ATtiny45@MLF20 (ISP)  
ATtiny45@SOIC8 [SA023A]  
ATtiny45@SOIC8(low vol isp)  
ATtiny45V (ISP)  
ATtiny45V@MLF20 [SA692]  
ATtiny45V@MLF20(low vol isp)  
ATtiny45V@SOIC8 (ISP)  
ATtiny461  
ATtiny461@MLF32 [SA686]  
ATtiny461@SOIC20 [SA404]  
ATtiny461A  
ATtiny461A@MLF32 [SA686]  
ATtiny461A@SOIC20 [SA404]  
ATtiny461V  
ATtiny461V@MLF32 [SA686]  
ATtiny461V@SOIC20 [SA404]  
ATtiny48  
ATtiny48@MLF28 [SA780]  
ATtiny48@MLF32 [SA686]  
ATtiny48@TQFP32 [SA636]  
ATtiny48V  
ATtiny48V@MLF28 [SA780]  
ATtiny48V@MLF32 [SA686]  
ATtiny48V@TQFP32 [SA636]  
ATtiny5@SOT23 [SA717]  
ATtiny828@MLF32 [SA686]  
ATtiny84  
ATtiny84(low vol isp)  
ATtiny84@MLF20 (ISP)  
ATtiny84@SOIC14 [SA602]  
ATtiny84@SOIC14(low vol isp)  
ATtiny84A@MLF20(3\*3) [\$\$\$\$\$]  
ATtiny84A@SOIC14 [SA602]  
ATtiny84V (ISP)  
ATtiny84V@MLF20 [SA692]  
ATtiny84V@MLF20(low vol isp)  
ATtiny84V@SOIC14 (ISP)  
ATtiny85  
ATtiny85(low vol isp)  
ATtiny85@MLF20 (ISP)  
ATtiny85@SOIC8 [SA023A]  
ATtiny85@SOIC8(low vol isp)  
ATtiny85V (ISP)  
ATtiny85V@MLF20 [SA692]  
ATtiny85V@MLF20(low vol isp)  
ATtiny85V@SOIC8 (ISP)  
ATtiny861  
ATtiny861@MLF32 [SA686]  
ATtiny861@SOIC20 [SA404]  
ATtiny861A  
ATtiny861A@MLF32 [SA686]

ATtiny861A@MLF32 (ISP)	ATtiny861A@SOIC20 [SA404]
ATtiny861A@SOIC20 (ISP)	ATtiny861V
ATtiny861V (ISP)	ATtiny861V@MLF32 [SA686]
ATtiny861V@MLF32 (ISP)	ATtiny861V@SOIC20 [SA404]
ATtiny861V@SOIC20 (ISP)	ATtiny87@QFN32 [SA686]
ATtiny87@QFN32 (ISP)	ATtiny87@SOIC20 [SA404]
ATtiny87@SOIC20 (ISP)	ATtiny87@TSSOP20 [SA026]
ATtiny87@TSSOP20 (ISP)	ATtiny88
ATtiny88 (ISP)	ATtiny88@MLF28 [SA780]
ATtiny88@MLF28 (ISP)	ATtiny88@MLF32 [SA686]
ATtiny88@MLF32 (ISP)	ATtiny88@TQFP32 [SA636]
ATtiny88@TQFP32 (ISP)	ATtiny88V
ATtiny88V (ISP)	ATtiny88V@MLF28 [SA780]
ATtiny88V@MLF28 (ISP)	ATtiny88V@MLF32 [SA686]
ATtiny88V@MLF32 (ISP)	ATtiny88V@TQFP32 [SA636]
ATtiny88V@TQFP32 (ISP)	ATtiny9@SOT23 [SA717]
ATtiny9@UDFN8 [\$\$\$\$\$]	T89F64
T89F64@PLCC44 [SA244]	T89F64@TQFP44 [SA245A-B4805]

## ATMEL W&M

### MICROCONTROLLER

AT89C5115@PLCC28 [SA008A]	AT89C5115@SOIC28 [SA404]
AT89C5115@TQFP32 [SA636]	AT89C51CC02@PLCC28 [SA008A]
AT89C51CC02@SOIC28 [SA404]	AT89C51CC02@TQFP32 [SA636]
T89C5115@PLCC28 [SA008A]	T89C5115@SOIC28 [SA404]
T89C5115@TQFP32 [SA636]	T89C51AC2@PLCC44 [SA244]
T89C51AC2@TQFP44 [SA245A-B4805]	T89C51CC01@PLCC44 [SA244]
T89C51CC01@TQFP44 [SA245A-B4805]	T89C51CC02@PLCC28 [SA008A]
T89C51CC02@SOIC24 [SA404]	T89C51CC02@SOIC28 [SA404]
T89C51CC02@TQFP32 [SA636]	T89C51IB2@PLCC44 [SA244]
T89C51IB2@TQFP44 [SA245A-B4805]	T89C51IC2@PLCC44 [SA244]
T89C51IC2@TQFP44 [SA245A-B4805]	T89C51RB2
T89C51RB2@PLCC44 [SA244]	T89C51RB2@TQFP44 [SA245A-B4805]
T89C51RC2	T89C51RC2@PLCC44 [SA244]
T89C51RC2@TQFP44 [SA245A-B4805]	T89C51RD2
T89C51RD2@PLCC44 [SA244]	T89C51RD2@TQFP44 [SA245A-B4805]
T89F64	T89F64@PLCC44 [SA244]
T89F64@TQFP44 [SA245A-B4805]	TS87C51RB2
TS87C51RB2@PLCC44 [SA244]	TS87C51RB2@TQFP44 [SA675-B4805]
TS87C51RC2	TS87C51RC2@PLCC44 [SA244]
TS87C51RC2@TQFP44 [SA675-B4805]	TS87C51RD2
TS87C51RD2@PLCC44 [SA244]	TS87C51RD2@TQFP44 [SA675-B4805]
TS87C51U2	TS87C51U2@PLCC44 [SA244]
TS87C51U2@TQFP44 [SA675-B4805]	TS87C52X2
TS87C52X2@PLCC44 [SA244]	TS87C52X2@TQFP44 [SA675-B4805]
TS87C54X2	TS87C54X2@PLCC44 [SA244]
TS87C54X2@TQFP44 [SA675-B4805]	TS87C58X2
TS87C58X2@PLCC44 [SA244]	TS87C58X2@TQFP44 [SA675-B4805]
TSC87251A1@PLCC44 [SA244]	TSC87251G1
TSC87251G1@PLCC44 [\$\$\$\$\$]	TSC87251G1A

TSC87251G1A@PLCC44 [SA244]  
TSC87251G2D@PLCC44 [SA244]  
TSC87251G2D@TQFP44 [SA245A-B4805]  
TSC87C51  
TSC87C51@TQFP44 [SA675-B4805]

TSC87251G2D  
TSC87C51@PLCC44 [SA244]

## ATMEL-CUSTOM

### MICROCONTROLLER

ATMEGA88PA@MLF32 [SA686]

## ATMEL-CUSTOMER

### E (E) PROM/FRAM/NVRAM

AT88SC018CM(intusurg) [SA602A]

## ATO

### E (E) PROM/FRAM/NVRAM

AFND1G08U3@TSOP48 [SB247-B4806]

## AUSTIN

### E (E) PROM/FRAM/NVRAM

AS8E512K8

AS8E512K8@SOJ32 [SA646]

## AXELITE

### E (E) PROM/FRAM/NVRAM

AX24C02A@DFN8 [SA724]  
AX24C02A@SOT23-5 [SA717]  
AX24C04A@DFN8 [SA724]  
AX24C04A@SOT23-5 [SA717]  
AX24C08A@DFN8 [SA724]  
AX24C08A@SOT23-5 [SA717]  
AX24C128A@SOP8 [SA602A]  
AX24C16A@DFN8 [SA724]  
AX24C16A@SOT23-5 [SA717]  
AX24C256A@SOP8 [SA602A]  
AX24C32A@SOP8 [SA602A]  
AX24C64A@SOP8 [SA602A]

AX24C02A@SOP8 [SA602A]  
AX24C02A@TSSOP8 [SA643]  
AX24C04A@SOP8 [SA602A]  
AX24C04A@TSSOP8 [SA643]  
AX24C08A@SOP8 [SA602A]  
AX24C08A@TSSOP8 [SA643]  
AX24C128A@TSSOP8 [SA643]  
AX24C16A@SOP8 [SA602A]  
AX24C16A@TSSOP8 [SA643]  
AX24C256A@TSSOP8 [SA643]  
AX24C32A@TSSOP8 [SA643]  
AX24C64A@TSSOP8 [SA643]

## BELLING

## E (E) PROM/FRAM/NVRAM

BL24C02	BL24C02@SOP8 [SA602A]
BL24C02@TSSOP8 [SA643]	BL24C04
BL24C04@SOP8 [SA602A]	BL24C04@TSSOP8 [SA643]
BL24C08	BL24C08@SOP8 [SA602A]
BL24C08@TSSOP8 [SA643]	BL24C128
BL24C128@SOP8 [SA602A]	BL24C128@TSSOP8 [SA643]
BL24C16	BL24C16@SOP8 [SA602A]
BL24C16@TSSOP8 [SA643]	BL24C256
BL24C256@SOP8 [SA602A]	BL24C256@TSSOP8 [SA643]
BL24C32	BL24C32@SOP8 [SA602A]
BL24C32@TSSOP8 [SA643]	BL24C512
BL24C512@SOP8 [SA602A]	BL24C512@TSSOP8 [SA643]
BL24C64	BL24C64@SOP8 [SA602A]
BL24C64@TSSOP8 [SA643]	

## BENCHMARK

### E (E) PROM/FRAM/NVRAM

BQ3285	BQ3287
BQ3287A	BQ4010
BQ4010Y	BQ4011
BQ4011Y	BQ4013
BQ4013Y	BQ4014
BQ4014Y	BQ4015
BQ4015Y	BQ4822
BQ4822Y	BQ4830Y
BQ4832Y	BQ4842Y

## BERGMICRO

### E (E) PROM/FRAM/NVRAM

BG25Q10A@SOIC8[150 mil] [SA602A]	BG25Q10A@SOIC8[200 mil] [SA605B]
BG25Q16A	BG25Q16A@SOP8 [SA605B]
BG25Q20A@SOIC8[150 mil] [SA602A]	BG25Q20A@SOIC8[200 mil] [SA605B]
BG25Q32A@SOIC8[150 mil] [SA605B]	BG25Q32A@SOIC8[200 mil] [SA605B]
BG25Q40A	BG25Q40A@SOP8[150mil] [SA602A]
BG25Q40A@SOP8[200mil] [SA605B]	BG25Q40A@WSON8 [SA683]
BG25Q512A@SOP8[150mil] [SA602A]	BG25Q512A@SOP8[200mil] [SA605B]
BG25Q80A	BG25Q80A@SOP8[150mil] [SA602A]
BG25Q80A@SOP8[200mil] [SA605B]	BG25Q80A@WSON8 [SA683]

## BJX

### E (E) PROM/FRAM/NVRAM

BJX24LC02	BJX24LC02@SOIC8 [SA602A]
-----------	--------------------------

BJX24LC02@TSSOP8 [SA643]  
BJX24LC04@SOIC8 [SA602A]  
BJX24LC08  
BJX24LC08@TSSOP8 [SA643]  
BJX24LC16@SOIC8 [SA602A]

BJX24LC04  
BJX24LC04@TSSOP8 [SA643]  
BJX24LC08@SOIC8 [SA602A]  
BJX24LC16  
BJX24LC16@TSSOP8 [SA643]

## BMT

### E (E) PROM/FRAM/NVRAM

BM29LV160B@TSOP48 [SB247-B4806]

BM29LV160T@TSOP48 [SB247-B4806]

## BOCH

### MICROCONTROLLER

CY8C24533

## Bookly Micro

### E (E) PROM/FRAM/NVRAM

24C02  
24C02@MSOP8 [SA666]  
24C02@TSSOP8 [SA643]  
24C04@DFN8 [SA724]  
24C04@SOIC8 [SA602A]  
24C08  
24C08@MSOP8 [SA666]  
24C08@TSSOP8 [SA643]  
24C16@DFN8 [SA724]  
24C16@SOIC8 [SA602A]

24C02@DFN8 [SA724]  
24C02@SOIC8 [SA602A]  
24C04  
24C04@MSOP8 [SA666]  
24C04@TSSOP8 [SA643]  
24C08@DFN8 [SA724]  
24C08@SOIC8 [SA602A]  
24C16  
24C16@MSOP8 [SA666]  
24C16@TSSOP8 [SA643]

## BRIGHT

### E (E) PROM/FRAM/NVRAM

BM29F040  
BM29F040@TSOP32 [SA410T-B4001]  
BM29F400B@TSOP48 [SB247-B4806]  
BM29F400T@TSOP48 [SB247-B4806]

BM29F040@PLCC32 [SA015A1T]  
BM29F400B@PSOP44 [SA638]  
BM29F400T@PSOP44 [SA638]

## CATALYST

### E (E) PROM/FRAM/NVRAM

CAT1021 (L)  
CAT1021 (R)@MSOP8 [SA643]  
CAT1021 (U)@TSSOP8 [SA643]

CAT1021 (P)  
CAT1021 (S)@SOIC8 [SA602A]  
CAT1021 (V)@SOIC8 [SA602A]

CAT1021 (Y)@TSSOP8 [SA643]  
CAT1022 (L)  
CAT1022 (R)@MSOP8 [SA643]  
CAT1022 (U)@TSSOP8 [SA643]  
CAT1022 (Y)@TSSOP8 [SA643]  
CAT1023 (L)  
CAT1023 (R)@MSOP8 [SA643]  
CAT1023 (U)@TSSOP8 [SA643]  
CAT1023 (Y)@TSSOP8 [SA643]  
CAT1024 (L)  
CAT1024 (R)@MSOP8 [SA643]  
CAT1024 (U)@TSSOP8 [SA643]  
CAT1024 (Y)@TSSOP8 [SA643]  
CAT1025 (L)  
CAT1025 (R)@MSOP8 [SA643]  
CAT1025 (U)@TSSOP8 [SA643]  
CAT1025 (Y)@TSSOP8 [SA643]  
CAT1026 (L)  
CAT1026 (R)@MSOP8 [SA643]  
CAT1026 (U)@TSSOP8 [SA643]  
CAT1026 (Y)@TSSOP8 [SA643]  
CAT1027 (L)  
CAT1027 (R)@MSOP8 [SA643]  
CAT1027 (U)@TSSOP8 [SA643]  
CAT1027 (Y)@TSSOP8 [SA643]  
CAT1161 (J)@SOIC8 [SA602A]  
CAT1162 (J)@SOIC8 [SA602A]  
CAT1163 (J)@SOIC8 [SA602A]  
CAT1320  
CAT1320@TDFN8  
CAT1321  
CAT1321@TDFN8  
CAT14002@SOIC8 [SA602A]  
CAT14008@SOIC8 [SA602A]  
CAT15002@SOIC8 [SA602A]  
CAT15008@SOIC8 [SA602A]  
CAT1640  
CAT1640@TDFN8  
CAT1641  
CAT1641@TDFN8  
CAT2210  
CAT2210I  
CAT2212  
CAT2212I  
CAT22C10  
CAT22C10I  
CAT22C12  
CAT22C12I  
CAT24AA01@SOIC8 [SA602A]  
CAT24AA02@SOIC8 [SA602A]  
CAT24AA04@SOIC8 [SA602A]  
CAT24AA08@SOIC8 [SA602A]  
CAT24AA16@SOIC8 [SA602A]

CAT1021 (Z)@MSOP8 [SA643]  
CAT1022 (P)  
CAT1022 (S)@SOIC8 [SA602A]  
CAT1022 (V)@SOIC8 [SA602A]  
CAT1022 (Z)@MSOP8 [SA643]  
CAT1023 (P)  
CAT1023 (S)@SOIC8 [SA602A]  
CAT1023 (V)@SOIC8 [SA602A]  
CAT1023 (Z)@MSOP8 [SA643]  
CAT1024 (P)  
CAT1024 (S)@SOIC8 [SA602A]  
CAT1024 (V)@SOIC8 [SA602A]  
CAT1024 (Z)@MSOP8 [SA643]  
CAT1025 (P)  
CAT1025 (S)@SOIC8 [SA602A]  
CAT1025 (V)@SOIC8 [SA602A]  
CAT1025 (Z)@MSOP8 [SA643]  
CAT1026 (P)  
CAT1026 (S)@SOIC8 [SA602A]  
CAT1026 (V)@SOIC8 [SA602A]  
CAT1026 (Z)@MSOP8 [SA643]  
CAT1027 (P)  
CAT1027 (S)@SOIC8 [SA602A]  
CAT1027 (V)@SOIC8 [SA602A]  
CAT1027 (Z)@MSOP8 [SA643]  
CAT1161 (P)  
CAT1162 (P)  
CAT1163 (P)  
CAT1320@SOIC8 [SA602A]  
CAT1320@TSSOP8 [SA643]  
CAT1321@SOIC8 [SA602A]  
CAT1321@TSSOP8 [SA643]  
CAT14004@SOIC8 [SA602A]  
CAT14016@SOIC8 [SA602A]  
CAT15004@SOIC8 [SA602A]  
CAT15016@SOIC8 [SA602A]  
CAT1640@SOIC8 [SA602A]  
CAT1640@TSSOP8 [SA643]  
CAT1641@SOIC8 [SA602A]  
CAT1641@TSSOP8 [SA643]  
CAT2210@SOIC16 [SA404]  
CAT2210I@SOIC16 [SA404]  
CAT2212@SOIC20 [SA404]  
CAT2212I@SOIC20 [SA404]  
CAT22C10@SOIC16 [SA404]  
CAT22C10I@SOIC16 [SA404]  
CAT22C12@SOIC20 [SA404]  
CAT22C12I@SOIC20 [SA404]  
CAT24AA01@TSOT-23 [SA717]  
CAT24AA02@TSOT-23 [SA717]  
CAT24AA04@TSOT-23 [SA717]  
CAT24AA08@TSOT-23 [SA717]  
CAT24AA16@TSOT-23 [SA717]

CAT24AC128  
CAT24AC128@TSSOP14 [SA026]  
CAT24AC128@UDFN8 [SA724]  
CAT24C00@SOIC8 [SA602A]  
CAT24C01  
CAT24C01@SOIC14 [SA602]  
CAT24C01@TDFN8 [SA724]  
CAT24C01@TSSOP8 [SA643]  
CAT24C01B(L)  
CAT24C01B(R)@MSOP8 [SA643]  
CAT24C01B(W)@SOIC8 [SA602A]  
CAT24C01B(Z)@MSOP8 [SA643]  
CAT24C02@MSOP8 [SA666]  
CAT24C02@SOIC8 [SA602A]  
CAT24C02@TSOT-23 [SA717]  
CAT24C021  
CAT24C023  
CAT24C03@SOIC8 [SA602A]  
CAT24C03@TSSOP8 [SA643]  
CAT24C04@MSOP8 [SA666]  
CAT24C04@SOIC8 [SA602A]  
CAT24C04@TSOT-23 [SA717]  
CAT24C041  
CAT24C043  
CAT24C05@SOIC8 [SA602A]  
CAT24C05@TSSOP8 [SA643]  
CAT24C08@MSOP8 [SA666]  
CAT24C08@SOIC8 [SA602A]  
CAT24C08@TSOT-23 [SA717]  
CAT24C081  
CAT24C083  
CAT24C08I@SOIC8 [SA602A]  
CAT24C09@SOIC8 [SA602A]  
CAT24C09@TSSOP8 [SA643]  
CAT24C128@SOIC8 [SA602A]  
CAT24C128@UDFN8 [SA724]  
CAT24C16@SOIC14 [SA602]  
CAT24C16@TDFN8 [SA724]  
CAT24C161  
CAT24C163  
CAT24C164@SOIC8 [SA602A]  
CAT24C16I  
CAT24C208(J)@SOIC8 [SA602A]  
CAT24C208(P)  
CAT24C208(U)@TSSOP8 [SA643]  
CAT24C208(Y)@TSSOP8 [SA643]  
CAT24C21  
CAT24C21@TSSOP8 [SA643]  
CAT24C256@SOIC8 [SA602A]  
CAT24C32@SOIC8 [SA602A]  
CAT24C44  
CAT24C64  
CAT24C64@TSSOP8 [SA643]

CAT24AC128@SOIC8 [SA602A]  
CAT24AC128@TSSOP8 [SA643]  
CAT24C00  
CAT24C00@TSSOP8 [SA643]  
CAT24C01@MSOP8 [SA666]  
CAT24C01@SOIC8 [SA602A]  
CAT24C01@TSOT-23 [SA717]  
CAT24C01B(J)@SOIC8 [SA602A]  
CAT24C01B(P)  
CAT24C01B(U)@TSSOP8 [SA643]  
CAT24C01B(Y)@TSSOP8 [SA643]  
CAT24C02  
CAT24C02@SOIC14 [SA602]  
CAT24C02@TDFN8 [SA724]  
CAT24C02@TSSOP8 [SA643]  
CAT24C022  
CAT24C03  
CAT24C03@TDFN8 [SA724]  
CAT24C04  
CAT24C04@SOIC14 [SA602]  
CAT24C04@TDFN8 [SA724]  
CAT24C04@TSSOP8 [SA643]  
CAT24C042  
CAT24C05  
CAT24C05@TDFN8 [SA724]  
CAT24C08  
CAT24C08@SOIC14 [SA602]  
CAT24C08@TDFN8 [SA724]  
CAT24C08@TSSOP8 [SA643]  
CAT24C082  
CAT24C08I  
CAT24C09  
CAT24C09@TDFN8 [SA724]  
CAT24C128  
CAT24C128@TSSOP8 [SA643]  
CAT24C16  
CAT24C16@SOIC8 [SA602A]  
CAT24C16@TSSOP8 [SA643]  
CAT24C162  
CAT24C164  
CAT24C164@TSSOP8 [SA643]  
CAT24C16I@SOIC8 [SA602A]  
CAT24C208(L)  
CAT24C208(R)@MSOP8 [SA666]  
CAT24C208(W)@SOIC8 [SA602A]  
CAT24C208(Z)@MSOP8 [SA666]  
CAT24C21@SOIC8 [SA602A]  
CAT24C256  
CAT24C32  
CAT24C32@UDFN8 [SA724]  
CAT24C44@SOIC8 [SA602A]  
CAT24C64@SOIC8 [SA602A]  
CAT24F32

CAT24F32@SOIC8 [SA602A]  
CAT24F32A  
CAT24F32A@TSSOP8 [SA643]  
CAT24FC01@SOIC14 [SA602]  
CAT24FC01@TDFN8 [SA724]  
CAT24FC02  
CAT24FC02@SOIC8 [SA602A]  
CAT24FC02@TSSOP8 [SA643]  
CAT24FC16@SOIC14 [SA602]  
CAT24FC16@TDFN8 [SA724]  
CAT24FC17  
CAT24FC17@TDFN8 [SA724]  
CAT24FC256  
CAT24FC256@TDFN8 [SA683]  
CAT24FC32  
CAT24FC32@TDFN8 [SA683]  
CAT24FC64  
CAT24FC64@TDFN8 [SA683]  
CAT24FC65  
CAT24FC65@TDFN8 [SA683]  
CAT24FC66  
CAT24FC66@TDFN8 [SA683]  
CAT24LC02  
CAT24LC02@TDFN8 [SA724]  
CAT24WC01  
CAT24WC01@TSSOP8 [SA643]  
CAT24WC02@SOIC8 [SA602A]  
CAT24WC03  
CAT24WC03@TSSOP8 [SA643]  
CAT24WC04@SOIC8 [SA602A]  
CAT24WC05  
CAT24WC05@TSSOP8 [SA643]  
CAT24WC08@SOIC8 [SA602A]  
CAT24WC09  
CAT24WC09@TSSOP8 [SA643]  
CAT24WC128@SOIC8 [SA602A]  
CAT24WC129  
CAT24WC16  
CAT24WC16@TSSOP8 [SA643]  
CAT24WC164@SOIC8 [SA602A]  
CAT24WC17  
CAT24WC17@TSSOP8 [SA643]  
CAT24WC256@SOIC8 [SA602A]  
CAT24WC257@SOIC8 [SA602A]  
CAT24WC32@SOIC8 [SA602A]  
CAT24WC33@SOIC8 [SA602A]  
CAT24WC64@SOIC8 [SA602A]  
CAT24WC65  
CAT24WC66  
CAT25010  
CAT25010 (U)@TSSOP8 [SA602A]  
CAT25020 (S)@SOIC8 [SA605B]  
CAT25040

CAT24F32@TSSOP8 [SA643]  
CAT24F32A@SOIC8 [SA602A]  
CAT24FC01  
CAT24FC01@SOIC8 [SA602A]  
CAT24FC01@TSSOP8 [SA643]  
CAT24FC02@SOIC14 [SA602]  
CAT24FC02@TDFN8 [SA724]  
CAT24FC16  
CAT24FC16@SOIC8 [SA602A]  
CAT24FC16@TSSOP8 [SA643]  
CAT24FC17@SOIC8 [SA602A]  
CAT24FC17@TSSOP8 [SA643]  
CAT24FC256@SOIC8 [SA602A]  
CAT24FC256@TSSOP8 [SA643]  
CAT24FC32@SOIC8 [SA602A]  
CAT24FC32@TSSOP8 [SA643]  
CAT24FC64@SOIC8 [SA602A]  
CAT24FC64@TSSOP8 [SA643]  
CAT24FC65@SOIC8 [SA602A]  
CAT24FC65@TSSOP8 [SA643]  
CAT24FC66@SOIC8 [SA602A]  
CAT24FC66@TSSOP8 [SA643]  
CAT24LC02@SOIC8 [SA602A]  
CAT24LC02@TSSOP8 [SA643]  
CAT24WC01@SOIC8 [SA602A]  
CAT24WC02  
CAT24WC02@TSSOP8 [SA643]  
CAT24WC03@SOIC8 [SA602A]  
CAT24WC04  
CAT24WC04@TSSOP8 [SA643]  
CAT24WC05@SOIC8 [SA602A]  
CAT24WC08  
CAT24WC08@TSSOP8 [SA643]  
CAT24WC09@SOIC8 [SA602A]  
CAT24WC128  
CAT24WC128@TSSOP8 [SA643]  
CAT24WC129@SOIC8 [SA602A]  
CAT24WC16@SOIC8 [SA602A]  
CAT24WC164  
CAT24WC164@TSSOP8 [SA643]  
CAT24WC17@SOIC8 [SA602A]  
CAT24WC256  
CAT24WC257  
CAT24WC32  
CAT24WC33  
CAT24WC64  
CAT24WC64@TSSOP8 [SA643]  
CAT24WC65@SOIC8 [SA602A]  
CAT24WC66@SOIC8 [SA602A]  
CAT25010 (S)@SOIC8 [SA605B]  
CAT25020  
CAT25020 (U)@TSSOP8 [SA602A]  
CAT25040 (S)@SOIC8 [SA605B]

CAT25040 (U)@TSSOP8 [SA602A]  
CAT25080@SOIC8 [SA602A]  
CAT25080@TSSOP8 [SA643]  
CAT25128  
CAT25128@TDFN8 [SA724]  
CAT25160  
CAT25160@TDFN8 [SA724]  
CAT25160@UDFN8  
CAT25256@SOIC8 [SA602A]  
CAT25256@TSSOP8 [SA643]  
CAT25320@SOIC8 [SA602A]  
CAT25320@TSSOP8 [SA643]  
CAT25640@SOIC8 [SA602A]  
CAT25640@TSSOP8 [SA643]  
CAT25C01@SOIC16 [SA602]  
CAT25C01@TSSOP14 [SA643]  
CAT25C02  
CAT25C02@SOIC8 [SA602A]  
CAT25C02@TSSOP8 [SA643]  
CAT25C03@SOIC8 [SA602A]  
CAT25C03@TSSOP8 [SA643]  
CAT25C04@SOIC16 [SA602]  
CAT25C04@TSSOP14 [SA026]  
CAT25C05  
CAT25C05@TSSOP14 [SA026]  
CAT25C08  
CAT25C08@SOIC8 [SA602A]  
CAT25C08@TSSOP8 [SA643]  
CAT25C09@SOIC8 [SA602A]  
CAT25C09@TSSOP8 [SA643]  
CAT25C11@SOIC8 [SA602A]  
CAT25C11@TSSOP8 [SA643]  
CAT25C128@SOIC16 [SA602]  
CAT25C128@SOIC8[150 mil] [SA602A]  
CAT25C128@SOIC8[208 mil] [SA605B]  
CAT25C128@TSSOP14 [SA026]  
CAT25C16  
CAT25C16@SOIC8 [SA602A]  
CAT25C16@TSSOP8 [SA643]  
CAT25C17@SOIC8 [SA602A]  
CAT25C17@TSSOP8 [SA643]  
CAT25C256@SOIC16 [SA602]  
CAT25C256@SOIC8[150 mil] [SA602A]  
CAT25C256@SOIC8[208 mil] [SA605B]  
CAT25C256@TSSOP14 [SA026]  
CAT25C32  
CAT25C32@TSSOP14 [SA026]  
CAT25C33  
CAT25C33@TSSOP14 [SA026]  
CAT25C64@SOIC8 [SA602A]  
CAT25C64@TSSOP20 [SA026]  
CAT25C65@SOIC8 [SA602A]  
CAT27010  
CAT25080  
CAT25080@TDFN8 [SA724]  
CAT25080@UDFN8  
CAT25128@SOIC8 [SA602A]  
CAT25128@TSSOP8 [SA643]  
CAT25160@SOIC8 [SA602A]  
CAT25160@TSSOP8 [SA643]  
CAT25256  
CAT25256@TDFN8 [SA724]  
CAT25320  
CAT25320@TDFN8 [SA724]  
CAT25640  
CAT25640@TDFN8 [SA724]  
CAT25C01  
CAT25C01@SOIC8 [SA602A]  
CAT25C01@TSSOP8 [SA643]  
CAT25C02@SOIC16 [SA602]  
CAT25C02@TSSOP14 [SA026]  
CAT25C03  
CAT25C03@TSSOP14 [SA026]  
CAT25C04  
CAT25C04@SOIC8 [SA602A]  
CAT25C04@TSSOP8 [SA643]  
CAT25C05@SOIC8 [SA602A]  
CAT25C05@TSSOP8 [SA643]  
CAT25C08@SOIC16 [SA602]  
CAT25C08@TSSOP14 [SA026]  
CAT25C09  
CAT25C09@TSSOP14 [SA026]  
CAT25C11  
CAT25C11@TSSOP14 [SA026]  
CAT25C128  
CAT25C128@TSSOP20 [SA026]  
CAT25C16@SOIC16 [SA602]  
CAT25C16@TSSOP14 [SA026]  
CAT25C17  
CAT25C17@TSSOP14 [SA026]  
CAT25C256  
CAT25C256@TSSOP20 [SA026]  
CAT25C32@SOIC8 [SA602A]  
CAT25C32@TSSOP20 [SA026]  
CAT25C33@SOIC8 [SA602A]  
CAT25C64  
CAT25C64@TSSOP14 [SA026]  
CAT25C65  
CAT25C65@TSSOP14 [SA026]  
CAT27010@PLCC32 [SA015A1T]

CAT27010@TSOP32 [SA410T-B4001]      CAT27128A  
CAT27256      CAT27512  
CAT27512@PLCC32 [SA015A1T]      CAT2764A  
CAT27C16A      CAT27C210  
CAT27C210@PLCC44 [SA244]      CAT27HC256  
CAT27HC256@PLCC32 [SA015A1T]      CAT27HC256I  
CAT27HC256I@PLCC32 [SA015A1T]      CAT28C16A  
CAT28C16A@PLCC32 [SA015A1T]      CAT28C16A@SOIC24 [SA404]  
CAT28C16AI      CAT28C16AI@PLCC32 [SA015A1T]  
CAT28C16AI@SOIC24 [SA404]      CAT28C17A  
CAT28C17A@PLCC32 [SA015A1T]      CAT28C17AI  
CAT28C17AI@PLCC32 [SA015A1T]      CAT28C256  
CAT28C256@PLCC32 [SA015A1T]      CAT28C256@TSOP28 [SA430T-B4003]  
CAT28C256I      CAT28C256I@PLCC32 [SA015A1T]  
CAT28C256I@TSOP28 [SA430T-B4003]      CAT28C257  
CAT28C257@PLCC32 [SA015A1T]      CAT28C257@TSOP28 [SA430T-B4003]  
CAT28C512      CAT28C512@PLCC32 [SA015A1T]  
CAT28C512@TSOP32 [SA410T-B4001]      CAT28C512@TSOP40 [SA409T-B4002]  
CAT28C513@PLCC32 [SA015A1T]      CAT28C64A  
CAT28C64A@PLCC32 [SA015A1T]      CAT28C64A@SOIC28 [SA404]  
CAT28C64AI      CAT28C64AI@PLCC32 [SA015A1T]  
CAT28C64AI@SOIC28 [SA404]      CAT28C64B  
CAT28C64B@PLCC32 [SA015A1T]      CAT28C64B@SOIC28 [SA404]  
CAT28C64B@TSOP28 [SA430T-B4003]      CAT28C64BI  
CAT28C64BI@PLCC32 [SA015A1T]      CAT28C64BI@TSOP28 [SA430T-B4003]  
CAT28C65B      CAT28C65B@PLCC32 [SA015A1T]  
CAT28C65B@TSOP28 [SA430T-B4003]      CAT28C65BI  
CAT28C65BI@PLCC32 [SA015A1T]      CAT28C65BI@TSOP28 [SA430T-B4003]  
CAT28F001N-B@PLCC32 [SA015A1T]      CAT28F001N-T@PLCC32 [SA015A1T]  
CAT28F001P-B      CAT28F001P-T  
CAT28F001T-B@TSOP32 [SA410T-B4001]  
CAT28F001T-T@TSOP32 [SA410T-B4001]  
CAT28F002B      CAT28F002B@TSOP40 [SA409T-B4002]  
CAT28F002T      CAT28F002T@TSOP40 [SA409T-B4002]  
CAT28F010  
CAT28F010 (REVERSE)@TSOP32 [SA410T-B4001]  
CAT28F010@PLCC32 [SA015A1T]      CAT28F010@TSOP32 [SA410T-B4001]  
CAT28F010I  
CAT28F010I (REVERSE)@TSOP32 [SA410T-B4001]  
CAT28F010I@PLCC32 [SA015A1T]      CAT28F010I@TSOP32 [SA410T-B4001]  
CAT28F020  
CAT28F020 (REVERSE)@TSOP32 [SA410T-B4001]  
CAT28F020@PLCC32 [SA015A1T]      CAT28F020@TSOP32 [SA410T-B4001]  
CAT28F020I  
CAT28F020I (REVERSE)@TSOP32 [SA410T-B4001]  
CAT28F020I@PLCC32 [SA015A1T]      CAT28F020I@TSOP32 [SA410T-B4001]  
CAT28F102      CAT28F102@PLCC44 [SA244]  
CAT28F102@TSOP40 [SA623-B4002]      CAT28F512  
CAT28F512 (REVERSE)@TSOP32 [SA410T-B4001]  
CAT28F512@PLCC32 [SA015A1T]      CAT28F512@TSOP32 [SA410T-B4001]  
CAT28F512I  
CAT28F512I (REVERSE)@TSOP32 [SA410T-B4001]  
CAT28F512I@PLCC32 [SA015A1T]      CAT28F512I@TSOP32 [SA410T-B4001]

CAT28LV256  
CAT28LV256@TSOP28 [SA430T-B4003]  
CAT28LV64@PLCC32 [SA015A1T]  
CAT28LV65  
CAT28LV65@TSOP28 [SA430T-B4003]  
CAT33C101 (08bit)@SOIC8 [SA602A]  
CAT33C101 (16bit)@SOIC8 [SA602A]  
CAT33C101H (08bit)@SOIC8 [SA602A]  
CAT33C101H (16bit)@SOIC8 [SA602A]  
CAT33C101I (08bit)@SOIC8 [SA602A]  
CAT33C101I (16bit)@SOIC8 [SA602A]  
CAT33C104 (08bit)@SOIC8 [SA602A]  
CAT33C104 (16bit)@SOIC8 [SA602A]  
CAT33C104I (08bit)@SOIC8 [SA602A]  
CAT33C104I (16bit)@SOIC8 [SA602A]  
CAT34AC02@SOIC8 [SA602A]  
CAT34C02  
CAT34C02@TDFN8 [SA724]  
CAT34FC02  
CAT34FC02@TDFN8 [SA724]  
CAT34RC02  
CAT34RC02@TDFN8 [SA724]  
CAT34TS02@TDFN8 [SA724]  
CAT34WC02@SOIC8 [SA602A]  
CAT34WC02@TSSOP8 [SA643]  
CAT35C102H  
CAT35C104 (08bit)  
CAT35C104 (16bit)  
CAT35C104H (08bit)  
CAT35C104I (08bit)  
CAT35C104I (16bit)  
CAT59C11  
CAT59C11A  
CAT59C11H  
CAT59C11I  
CAT64LC10 (J)@SOIC8 [SA602A]  
CAT64LC10 (S)@SOIC8 [SA602A]  
CAT64LC10 (UR)@TSSOP8 [SA643]  
CAT64LC20 (P)  
CAT64LC20 (U)@TSSOP8 [SA026]  
CAT64LC40 (J)@SOIC8 [SA602A]  
CAT64LC40 (S)@SOIC8 [SA602A]  
CAT64LC40 (UR)@TSSOP8 [SA026]  
CAT93C46 (08bit) (J)@SOIC8 [SA602A]  
CAT93C46 (08bit) (K)@SOIC8 [SA605B]  
CAT93C46 (08bit) (S)@SOIC8 [SA602A]  
CAT93C46 (08bit) (U)@TSSOP8 [SA643]  
CAT93C46 (16bit)  
CAT93C46 (16bit) (J)@SOIC8 [SA602A]  
CAT93C46 (16bit) (K)@SOIC8 [SA605B]  
CAT93C46 (16bit) (S)@SOIC8 [SA602A]  
CAT93C46 (16bit) (U)@TSSOP8 [SA643]  
CAT93C46A  
CAT28LV256@PLCC32 [SA015A1T]  
CAT28LV64  
CAT28LV64@TSOP28 [SA430T-B4003]  
CAT28LV65@PLCC32 [SA015A1T]  
CAT33C101 (08bit)  
CAT33C101 (16bit)  
CAT33C101H (08bit)  
CAT33C101H (16bit)  
CAT33C101I (08bit)  
CAT33C101I (16bit)  
CAT33C104 (08bit)  
CAT33C104 (16bit)  
CAT33C104I (08bit)  
CAT33C104I (16bit)  
CAT34AC02  
CAT34AC02@TSSOP8 [SA643]  
CAT34C02@SOIC8 [SA602A]  
CAT34C02@TSSOP8 [SA643]  
CAT34FC02@SOIC8 [SA602A]  
CAT34FC02@TSSOP8 [SA643]  
CAT34RC02@SOIC8 [SA602A]  
CAT34RC02@TSSOP8 [SA643]  
CAT34WC02  
CAT34WC02@TDFN8 [SA724]  
CAT35C102  
CAT35C102I  
CAT35C104 (08bit)@SOIC8 [SA602A]  
CAT35C104 (16bit)@SOIC8 [SA602A]  
CAT35C104H (08bit)@SOIC8 [SA602A]  
CAT35C104I (08bit)@SOIC8 [SA602A]  
CAT35C104I (16bit)@SOIC8 [SA602A]  
CAT59C11@SOIC8 [SA602A]  
CAT59C11A@SOIC8 [SA602A]  
CAT59C11H@SOIC8 [SA602A]  
CAT59C11I@SOIC8 [SA602A]  
CAT64LC10 (P)  
CAT64LC10 (U)@TSSOP8 [SA643]  
CAT64LC20 (J)@SOIC8 [SA602A]  
CAT64LC20 (S)@SOIC8 [SA602A]  
CAT64LC20 (UR)@TSSOP8 [SA026]  
CAT64LC40 (P)  
CAT64LC40 (U)@TSSOP8 [SA026]  
CAT93C46 (08bit)  
CAT93C46R (08bit)

CAT93C46R(08bit)(V)@SOIC8 [SA602A]  
CAT93C46R(08bit)(VP2)@TDFN8 [SA724]  
CAT93C46R(08bit)(W)@SOIC8 [SA602A]  
CAT93C46R(08bit)(X)@SOIC8 [SA602A]  
CAT93C46R(08bit)(Y)@TSSOP8 [SA643]  
CAT93C46R(16bit)(V)@SOIC8 [SA602A]  
CAT93C46R(16bit)(VP2)@TDFN8 [SA724]  
CAT93C46R(16bit)(W)@SOIC8 [SA602A]  
CAT93C46R(16bit)(X)@SOIC8 [SA602A]  
CAT93C46R(16bit)(Y)@TSSOP8 [SA643]  
CAT93C46R-16  
CAT93C56(08bit)@SOIC8 [SA602A]  
CAT93C56(08bit)@TDFN8 [SA724]  
CAT93C56(08bit)@UDFN8 [SA703]  
CAT93C56(16bit)@SOIC8 [SA602A]  
CAT93C57  
CAT93C66(08bit)@SOIC8 [SA602A]  
CAT93C66(16bit)  
CAT93C66(16bit)@TSSOP8 [SA643]  
CAT93C76(08bit)  
CAT93C76(08bit)(J)@SOIC8 [SA602A]  
CAT93C76(08bit)(K)@SOIC8 [SA605B]  
CAT93C76(08bit)(S)@SOIC8 [SA602A]  
CAT93C76(08bit)(U)@TSSOP8 [SA643]  
CAT93C76(16bit)  
CAT93C76(16bit)(J)@SOIC8 [SA602A]  
CAT93C76(16bit)(K)@SOIC8 [SA605B]  
CAT93C76(16bit)(S)@SOIC8 [SA602A]  
CAT93C76(16bit)(U)@TSSOP8 [SA643]  
CAT93C86(08bit)  
CAT93C86(08bit)(J)@SOIC8 [SA602A]  
CAT93C86(08bit)(K)@SOIC8 [SA605B]  
CAT93C86(08bit)(S)@SOIC8 [SA602A]  
CAT93C86(08bit)(U)@TSSOP8 [SA643]  
CAT93C86(16bit)  
CAT93C86(16bit)(J)@SOIC8 [SA602A]  
CAT93C86(16bit)(K)@SOIC8 [SA605B]  
CAT93C86(16bit)(S)@SOIC8 [SA602A]  
CAT93C86(16bit)(U)@TSSOP8 [SA643]  
CAT93H46(08bit)  
CAT93H46(08bit)(J)@SOIC8 [SA602A]  
CAT93H46(08bit)(K)@SOIC8 [SA605B]  
CAT93H46(08bit)(S)@SOIC8 [SA602A]  
CAT93H46(08bit)(U)@TSSOP8 [SA643]  
CAT93H46(16bit)  
CAT93H46(16bit)(J)@SOIC8 [SA602A]  
CAT93H46(16bit)(K)@SOIC8 [SA605B]  
CAT93H46(16bit)(S)@SOIC8 [SA602A]  
CAT93H46(16bit)(U)@TSSOP8 [SA643]  
CAT93HC46(08bit)  
CAT93HC46(08bit)(J)@SOIC8 [SA602A]  
CAT93HC46(08bit)(K)@SOIC8 [SA605B]  
CAT93HC46(08bit)(S)@SOIC8 [SA602A]

CAT93C56(08bit)  
CAT93C56(08bit)@SSOP8 [SA605B]  
CAT93C56(08bit)@TSSOP8 [SA643]  
CAT93C56(16bit)  
CAT93C56A  
CAT93C66(08bit)  
CAT93C66(08bit)@TSSOP8 [SA643]  
CAT93C66(16bit)@SOIC8 [SA602A]  
CAT93C66A

CAT93HC46(08bit)(U)@TSSOP8 [SA643]  
CAT93HC46(16bit)  
CAT93HC46(16bit)(J)@SOIC8 [SA602A]  
CAT93HC46(16bit)(K)@SOIC8 [SA605B]  
CAT93HC46(16bit)(S)@SOIC8 [SA602A]  
CAT93HC46(16bit)(U)@TSSOP8 [SA643]

## DRAM & SRAM

CAT71C256  
CAT71C256L  
CAT71C256@TSOP28 [SA643]  
CAT71C256L@TSOP28 [SA643]

## CBC Microelectronics

### E (E) PROM/FRAM/NVRAM

MC24LC02  
MC24LC02@TSSOP8 [SA643]  
MC24LC04@SOP8 [SA602A]  
MC24LC08  
MC24LC08@TSSOP8 [SA643]  
MC24LC16@SOP8 [SA602A]  
MC24LC02@SOP8 [SA602A]  
MC24LC04  
MC24LC04@TSSOP8 [SA643]  
MC24LC08@SOP8 [SA602A]  
MC24LC16  
MC24LC16@TSSOP8 [SA643]

## CERAMATE

### E (E) PROM/FRAM/NVRAM

24LC02  
24LC02@TSSOP8 [SA643]  
24LC08@SOIC8 [SA602A]  
24LC16  
24LC16@TSSOP8 [SA643]  
24LLC02@SOIC8 [SA602A]  
24LLC08  
24LLC08@TSSOP8 [SA643]  
93LC46@SOIC8 [SA602A]  
93LC46R@SOIC8 [SA602A]  
93LC56@SOIC8 [SA602A]  
93LC66@SOIC8 [SA602A]  
24LC02@SOIC8 [SA602A]  
24LC08  
24LC08@TSSOP8 [SA643]  
24LC16@SOIC8 [SA602A]  
24LLC02  
24LLC02@TSSOP8 [SA643]  
24LLC08@SOIC8 [SA602A]  
93LC46  
93LC46R  
93LC56  
93LC66

## CETC58

### PLD

JGAL16V8B  
JGAL22V10D  
JGAL20V8B

## CFEON

## E (E) PROM/FRAM/NVRAM

EN25F16  
EN25F16@SOP8 [SA605B]  
EN25F32  
EN25F32@SOP8 [SA605B]  
EN25F80  
EN25F80@VDFN8 [SA683]  
EN25QA32@SOP8 [SA605B]  
EN25QH16  
EN25QH16@SOP8 (200 mil) [SA605B]  
EN25QH32  
EN25QH32@VDFN8 [SA683]  
EN25QH64@SOP8 [SA605B]  
EN25T16@SOP8 [SA605B]  
EN25T80  
EN25T80@VDFN8 [SA683]  
EN29F002AB@PLCC32 [SA015A1T]  
EN29F002ANB  
EN29F002ANB@TSOP32 [SA410T-B4001]  
EN29F002ANT  
EN29F002ANT@TSOP32 [SA410T-B4001]  
EN29F002AT  
EN29F002AT@TSOP32 [SA410T-B4001]  
EN29F002B@PLCC32 [SA015A1T]  
EN29F002NB  
EN29F002NB@TSOP32 [SA410T-B4001]  
EN29F002NT@PLCC32 [SA015A1T]  
EN29F002T  
EN29F002T@TSOP32 [SA410T-B4001]  
EN29F010@PLCC32 [SA015A1T]  
EN29F010@VSOP32 [SA620-B4807]  
EN29F040@PLCC32 [SA015A1T]  
EN29F040A  
EN29F040A@TSOP32 [SA410T-B4001]  
EN29F512  
EN29F512@TSOP32 [SA410T-B4001]  
EN29F800B@TSOP48 [SB247-B4806]  
EN29GL064AB@TSOP48 [SB247-B4806]  
EN29GL064B@TSOP48 [SB247-B4806]  
EN29LV010@PLCC32 [SA015A1T]  
EN29LV010@VSOP32 [SA620-B4807]  
EN29LV040@TSOP32 [SA410T-B4001]  
EN29LV040A  
EN29LV040A@TSOP32 [SA410T-B4001]  
EN29LV160AB@TSOP48 [SB247-B4806]  
EN29LV160B@TSOP48 [SB247-B4806]  
EN29LV160BT@TSOP48 [SB247-B4806]  
EN29LV160T@TSOP48 [SB247-B4806]  
EN29LV320AB@TSOP48 [SB247-B4806]  
EN29LV320B@TSOP48 [SB247-B4806]  
EN29LV320BT@TSOP48 [SB247-B4806]  
EN29LV320CT@TSOP48 [SB247-B4806]  
EN25F16@SOP16 [SA404]  
EN25F16@VDFN8 [SA683]  
EN25F32@SOP16 [SA404]  
EN25F32@VDFN8 [SA683]  
EN25F80@SOP8 [SA605B]  
EN25QA32  
EN25QA32@VDFN8 [SA683]  
EN25QH16@SOP8 (150 mil) [SA602A]  
EN25QH16@VDFN8 [SA684]  
EN25QH32@SOP8 [SA605B]  
EN25QH64  
EN25QH64@VDFN8 [SA683]  
EN25T16@VDFN8 [SA683]  
EN25T80@SOP8 [SA605B]  
EN29F002AB  
EN29F002AB@TSOP32 [SA410T-B4001]  
EN29F002ANB@PLCC32 [SA015A1T]  
EN29F002ANT@PLCC32 [SA015A1T]  
EN29F002AT@PLCC32 [SA015A1T]  
EN29F002B  
EN29F002B@TSOP32 [SA410T-B4001]  
EN29F002NB@PLCC32 [SA015A1T]  
EN29F002NT  
EN29F002NT@TSOP32 [SA410T-B4001]  
EN29F002T@PLCC32 [SA015A1T]  
EN29F010  
EN29F010@TSOP32 [SA410T-B4001]  
EN29F040  
EN29F040@TSOP32 [SA410T-B4001]  
EN29F040A@PLCC32 [SA015A1T]  
EN29F080@TSOP40 [SA409T-B4002]  
EN29F512@PLCC32 [SA015A1T]  
EN29F512@VSOP32 [SA620-B4807]  
EN29F800T@TSOP48 [SB247-B4806]  
EN29GL064AT@TSOP48 [SB247-B4806]  
EN29GL064T@TSOP48 [SB247-B4806]  
EN29LV010@TSOP32 [SA410T-B4001]  
EN29LV040@PLCC32 [SA015A1T]  
EN29LV040@VSOP32 [SA620-B4807]  
EN29LV040A@PLCC32 [SA015A1T]  
EN29LV040A@VSOP32 [SA620-B4807]  
EN29LV160AT@TSOP48 [SB247-B4806]  
EN29LV160BB@TSOP48 [SB247-B4806]  
EN29LV160CB@TSOP48 [SB247-B4806]  
EN29LV160TB@TSOP48 [SB247-B4806]  
EN29LV320AT@TSOP48 [SB247-B4806]  
EN29LV320BB@TSOP48 [SB247-B4806]  
EN29LV320CB@TSOP48 [SB247-B4806]  
EN29LV320T@TSOP48 [SB247-B4806]

EN29LV400AB@TSOP48 [SB247-B4806]	EN29LV400AT@TSOP48 [SB247-B4806]
EN29LV400B@TSOP48 [SB247-B4806]	EN29LV400T@TSOP48 [SB247-B4806]
EN29LV512@PLCC32 [SA015A1T]	EN29LV512@TSOP32 [SA410T-B4001]
EN29LV512@VSOP32 [SA620-B4807]	EN29LV640AB@TSOP48 [SB247-B4806]
EN29LV640AT@TSOP48 [SB247-B4806]	EN29LV640B@TSOP48 [SB247-B4806]
EN29LV640H@TSOP48 [SB247-B4806]	EN29LV640L@TSOP48 [SB247-B4806]
EN29LV640T@TSOP48 [SB247-B4806]	EN29LV641H@TSOP48 [SB247-B4806]
EN29LV641L@TSOP48 [SB247-B4806]	EN29LV800AB@TSOP48 [SB247-B4806]
EN29LV800AT@TSOP48 [SB247-B4806]	EN29LV800B@TSOP48 [SB247-B4806]
EN29LV800BB@TSOP48 [SB247-B4806]	EN29LV800BT@TSOP48 [SB247-B4806]
EN29LV800CB@TSOP48 [SB247-B4806]	EN29LV800CT@TSOP48 [SB247-B4806]
EN29LV800T@TSOP48 [SB247-B4806]	EN29PL032@TSOP48 [SB247-B4806]
EN29PL032A@TSOP48 [SB247-B4806]	EN29PL064@TSOP48 [SB247-B4806]
EN29SL160B@TSOP48 [SB247-B4806]	EN29SL160T@TSOP48 [SB247-B4806]
EN29SL400B@TSOP48 [SB247-B4806]	EN29SL400T@TSOP48 [SB247-B4806]
EN29SL800B@TSOP48 [SB247-B4806]	EN29SL800T@TSOP48 [SB247-B4806]
EN39LV010@PLCC32 [SA015A1T]	EN39LV010@VSOP32 [SA620-B4807]
EN39SL800@TSOP48 [SA247-B4806]	

## CHINGIS

### E (E) PROM/FRAM/NVRAM

PM25LD010@SOP8 [SA602A]	PM25LD010@TSSOP8 [SA643]
PM25LD010@WSON8 [SA683]	PM25LD010C@SOP8 [SA602A]
PM25LD010C@SOP8 (SG) [SA602A]	PM25LD010C@TSSOP8 [SA643]
PM25LD010C@TSSOP8 (SG) [SA643]	PM25LD010C@WSON8 [SA683]
PM25LD010C@WSON8 (SG) [SA683]	PM25LD020@SOP8 [SA602A]
PM25LD020@TSSOP8 [SA643]	PM25LD020@WSON8 [SA683]
PM25LD020C@SOP8 [SA602A]	PM25LD020C@SOP8 (SG) [SA602A]
PM25LD020C@TSSOP8 [SA643]	PM25LD020C@TSSOP8 (SG) [SA643]
PM25LD020C@WSON8 [SA683]	PM25LD020C@WSON8 (SG) [SA683]
PM25LD040 (B)@SOIC8 [SA605B]	PM25LD040 (Q)@WSON8 [SA683]
PM25LD040 (S)@SOIC8 [SA602A]	PM25LD256C@SOP8 [SA602A]
PM25LD256C@TSSOP8 [SA643]	PM25LD256C@WSON8 [SA683]
PM25LD512@SOP8 [SA602A]	PM25LD512@TSSOP8 [SA643]
PM25LD512@WSON8 [SA683]	PM25LD512C@SOP8 [SA602A]
PM25LD512C@TSSOP8 [SA643]	PM25LD512C@WSON8 [SA683]
PM25LV010 (B)@SOIC8 [SA605B]	PM25LV010 (Q)@WSON8 [SA683]
PM25LV010 (S)@SOIC8 [SA602A]	PM25LV020 (B)@SOIC8 [SA605B]
PM25LV020 (Q)@WSON8 [SA683]	PM25LV020 (S)@SOIC8 [SA602A]
PM25LV040 (B)@SOIC8 [SA605B]	PM25LV040 (Q)@WSON8 [SA683]
PM25LV040 (S)@SOIC8 [SA602A]	PM25LV512 (B)@SOIC8 [SA605B]
PM25LV512 (Q)@WSON8 [SA683]	PM25LV512 (S)@SOIC8 [SA602A]
PM25W020 (B)@SOIC8 [SA605B]	PM25W020 (Q)@WSON8 [SA683]
PM25W020 (S)@SOIC8 [SA602A]	PM29F002B
PM29F002B@PLCC32 [SA015A1T]	PM29F002T
PM29F002T@PLCC32 [SA015A1T]	PM29F004B
PM29F004B@PLCC32 [SA015A1T]	PM29F004T
PM29F004T@PLCC32 [SA015A1T]	PM29LV002B
PM29LV002B@PLCC32 [SA015A1T]	PM29LV002B@VSOP32 [SA620-B4807]
PM29LV002T	PM29LV002T@PLCC32 [SA015A1T]

PM29LV002T@VSOP32 [SA620-B4807] PM29LV004B@PLCC32 [SA015A1T]  
PM29LV004B@VSOP32 [SA620-B4807] PM29LV004T@PLCC32 [SA015A1T]  
PM29LV004T@VSOP32 [SA620-B4807] PM29LV104RB@PLCC32 [SA015A1T]  
PM29LV104RB@VSOP32 [SA620-B4807] PM29LV104RT@PLCC32 [SA015A1T]  
PM29LV104RT@VSOP32 [SA620-B4807] PM37LV512  
PM37LV512@VSOP32 [SA620-B4807]  
PM39F010 PM39F010@PLCC32 [SA015A1T]  
PM39F010@VSOP32 [SA620-B4807] PM39F020  
PM39F020@PLCC32 [SA015A1T] PM39F020@VSOP32 [SA620-B4807]  
PM39F040 PM39F040@PLCC32 [SA015A1T]  
PM39F040@VSOP32 [SA620-B4807] PM39LV010@PLCC32 [SA015A1T]  
PM39LV010@VSOP32 [SA620-B4807] PM39LV010R@PLCC32 [SA015A1T]  
PM39LV010R@VSOP32 [SA620-B4807] PM39LV020@PLCC32 [SA015A1T]  
PM39LV020@VSOP32 [SA620-B4807] PM39LV040@PLCC32 [SA015A1T]  
PM39LV040@VSOP32 [SA620-B4807] PM39LV512@PLCC32 [SA015A1T]  
PM39LV512@VSOP32 [SA620-B4807] PM39LV512R@PLCC32 [SA015A1T]  
PM39LV512R@VSOP32 [SA620-B4807] PM49FL002T@PLCC32 [SA015A1T]  
PM49FL002T@VSOP32 [SA620-B4807] PM49FL004T@PLCC32 [SA015A1T]  
PM49FL004T@VSOP32 [SA620-B4807] PM49FL008T@PLCC32 [SA015A1T]  
PM49FL008T@VSOP32 [SA620-B4807] PM49LP002T@PLCC32 [SA015A1T]  
PM49LP002T@VSOP32 [SA620-B4807]

## CHIPMAST

### MICROCONTROLLER

M151-S1@SOP16 [SA602] M151-S2@SOP16 [SA602]  
M152-S2@SOP16 [SA602]

## CHIPON

### MICROCONTROLLER

C61F120 C61F120@QFN8 [SA683]  
C61F120@SOIC8 [SA605B] C61F120@SSOP8 [SA602]  
C61F121 C61F121@SOIC14 [SA602]  
C61F121@TSSOP14 [SA026] C61F132  
C61F132@QFN8 [SA683] C61F132@SOIC8 [SA605B]  
C61F132@SSOP20 [SA626A] C61F132@SSOP8 [SA602]  
C61F133 C61F133@SOIC14 [SA602]  
C61F133@TSSOP14 [SA026] C61F182  
C61F182@QFN28 [SA685] C61F182@SOIC28 [SA404]  
C61F182@SSOP28 [SA626A] C61F183  
C61F183@QFN28 [SA685] C61F183@SOIC28 [SA404]  
C61F183@SSOP28 [SA626A] C61F184  
C61F184@QFN44 [SA712] C61F184@QFP44 [SA245A-B4805]  
C61F186 C61F186@QFN28 [SA685]  
C61F186@SOIC28 [SA404] C61F186@SSOP28 [SA626A]  
C61F187 C61F187@QFN44 [SA712]  
C61F187@QFP44 [SA245A-B4805] C61F21  
C61F21@QFN8 [SA744] C61F21@SOIC8 [SA605B]  
C61F21@SSOP8 [SA602] C61F23

C61F23@QFN16 [SA727]  
C61F23@TSSOP14 [SA026]

C61F23@SOIC14 [SA602]

## CHIPSWINNER

### E (E) PROM/FRAM/NVRAM

CW24C02  
CW24C02@SOP8 [SA602A]  
CW24C02@TSOT23-5 [SA717]  
CW24C02B  
CW24C02B@SOP8 [SA602A]  
CW24C02B@TSOT23-5 [SA717]  
CW24C02C  
CW24C02C@SOP8 [SA602A]  
CW24C02C@TSOT23-5 [SA717]  
CW24C04  
CW24C04@SOP8 [SA602A]  
CW24C04@TSOT23-5 [SA717]  
CW24C04A  
CW24C04A@SOP8 [SA602A]  
CW24C04A@TSOT23-5 [SA717]  
CW24C08  
CW24C08@SOP8 [SA602A]  
CW24C08@TSOT23-5 [SA717]  
CW24C08B  
CW24C08B@SOP8 [SA602A]  
CW24C08B@TSOT23-5 [SA717]  
CW24C08C  
CW24C08C@SOP8 [SA602A]  
CW24C08C@TSOT23-5 [SA717]  
CW24C128  
CW24C128@SOP8 [SA602A]  
CW24C16  
CW24C16@SOP8 [SA602A]  
CW24C16@TSOT23-5 [SA717]  
CW24C16A  
CW24C16A@SOP8 [SA602A]  
CW24C16A@TSOT23-5 [SA717]  
CW24C256  
CW24C256@SOP8 [SA602A]  
CW24C32  
CW24C32@SOP8 [SA602A]  
CW24C64  
CW24C64@SOP8 [SA602A]  
CW25P01@SOP8 [SA602A]  
CW25P05@SOP8 [SA602A]

CW24C02@DFN8 [SA724]  
CW24C02@SOT23-5 [SA717]  
CW24C02@TSSOP8 [SA643]  
CW24C02B@DFN8 [SA724]  
CW24C02B@SOT23-5 [SA717]  
CW24C02B@TSSOP8 [SA643]  
CW24C02C@DFN8 [SA724]  
CW24C02C@SOT23-5 [SA717]  
CW24C02C@TSSOP8 [SA643]  
CW24C04@DFN8 [SA724]  
CW24C04@SOT23-5 [SA717]  
CW24C04@TSSOP8 [SA643]  
CW24C04A@DFN8 [SA724]  
CW24C04A@SOT23-5 [SA717]  
CW24C04A@TSSOP8 [SA643]  
CW24C08@DFN8 [SA724]  
CW24C08@SOT23-5 [SA717]  
CW24C08@TSSOP8 [SA643]  
CW24C08B@DFN8 [SA724]  
CW24C08B@SOT23-5 [SA717]  
CW24C08B@TSSOP8 [SA643]  
CW24C08C@DFN8 [SA724]  
CW24C08C@SOT23-5 [SA717]  
CW24C08C@TSSOP8 [SA643]  
CW24C128@DFN8 [SA724]  
CW24C128@TSSOP8 [SA643]  
CW24C16@DFN8 [SA724]  
CW24C16@SOT23-5 [SA717]  
CW24C16@TSSOP8 [SA643]  
CW24C16A@DFN8 [SA724]  
CW24C16A@SOT23-5 [SA717]  
CW24C16A@TSSOP8 [SA643]  
CW24C256@DFN8 [SA724]  
CW24C256@TSSOP8 [SA643]  
CW24C32@DFN8 [SA724]  
CW24C32@TSSOP8 [SA643]  
CW24C64@DFN8 [SA724]  
CW24C64@TSSOP8 [SA643]  
CW25P02@SOP8 [SA602A]  
CW25P10@SOP8 [SA602A]

## CKD Technology

### E (E) PROM/FRAM/NVRAM

CKD24A02

CKD24A02@SOP8 [SA602A]

## CORERIVER

### E (E) PROM/FRAM/NVRAM

CR24C01	CR24C01@SOIC8 [SA602A]
CR24C01@TDFN8 [SA724]	CR24C01@TSSOP8 [SA643]
CR24C02	CR24C02@SOIC8 [SA602A]
CR24C02@TDFN8 [SA724]	CR24C02@TSSOP8 [SA643]
CR24C04	CR24C04@SOIC8 [SA602A]
CR24C04@TDFN8 [SA724]	CR24C04@TSSOP8 [SA643]
CR24C08	CR24C08@SOIC8 [SA602A]
CR24C08@TDFN8 [SA724]	CR24C08@TSSOP8 [SA643]
CR24C128	CR24C128@SOIC8 [SA602A]
CR24C128@TSSOP8 [SA643]	CR24C16
CR24C16@SOIC8 [SA602A]	CR24C16@TDFN8 [SA724]
CR24C16@TSSOP8 [SA643]	CR24C256
CR24C256@SOIC8 [SA602A]	CR24C256@TSSOP8 [SA643]
CR24C32	CR24C32@SOIC8 [SA602A]
CR24C32@TSSOP8 [SA643]	CR24C64
CR24C64@SOIC8 [SA602A]	CR24C64@TSSOP8 [SA643]

### MICROCONTROLLER

GC89L541A0@LQFP44 [SA675-B4805]	GC89L541A0@MLF32 [SA686]
GC89L541A0@MQFP44 [SA782]	GC89L541A0@PQFP44 [SA782]
GC89L541A0@QFN32 [SA686]	GC89L581A0@LQFP44 [SA675-B4805]
GC89L581A0@MLF32 [SA686]	GC89L581A0@MQFP44 [SA782]
GC89L581A0@PQFP44 [SA782]	GC89L581A0@QFN32 [SA686]
GC89L591A0@LQFP44 [SA675-B4805]	GC89L591A0@MLF32 [SA686]
GC89L591A0@MQFP44 [SA782]	GC89L591A0@PQFP44 [SA782]
GC89L591A0@QFN32 [SA686]	

## CWI

### E (E) PROM/FRAM/NVRAM

39LV040@VSOP32 [SA620-B4807]

## CYGNAL

### MICROCONTROLLER

C8051F330@MLP20 [SA692]	C8051F330D
C8051F330-GM@MLP20 [SA692]	C8051F330-GP
C8051F350-GQ@LQFP32 [SA636]	C8051F351-GM@QFN28 [SA697]
C8051F352-GQ@LQFP32 [SA636]	C8051F353-GM@QFN28 [SA697]

## CYPRESS

### E (E) PROM/FRAM/NVRAM

CY14B256Q	CY14B256Q@S0IC16 [SA602]
CY14B256Q@S0IC8 [SA602A]	CY14C256Q
CY14C256Q@S0IC16 [SA602]	CY14C256Q@S0IC8 [SA602A]
CY14E256Q	CY14E256Q@S0IC16 [SA602]
CY14E256Q@S0IC8 [SA602A]	CY27C010
CY27C010@PLCC32 [SA015A1T]	CY27C010@TSOP32 [SA410T-B4001]
CY27C020	CY27C020@PLCC32 [SA015A1T]
CY27C020@TSOP32 [SA410T-B4001]	CY27C040
CY27C040@PLCC32 [SA015A1T]	CY27C040@TSOP32 [SA410T-B4001]
CY27C256	CY27C256@PLCC32 [SA015A1T]
CY27C256@TSOP28 [SA430T-B4003]	CY27C512
CY27C512@PLCC32 [SA015A1T]	CY27C512@TSOP28 [SA430T-B4003]
CY27H010	CY27H010@PLCC32 [SA015A1T]
CY27H010@TSOP32 [SA410T-B4001]	CY27H256
CY27H256@PLCC32 [SA015A1T]	CY27H256@TSOP28 [SA430T-B4003]
CY27H512	CY27H512@PLCC32 [SA015A1T]
CY27H512@TSOP28 [SA430T-B4003]	CY7C251
CY7C251@PLCC32 [\$\$\$\$\$]	CY7C254
CY7C254@PLCC32 [\$\$\$\$\$]	CY7C256
CY7C256@PLCC32 [SA015A1T]	CY7C261
CY7C261@PLCC28 [SA008A]	CY7C263
CY7C263@PLCC28 [SA008A]	CY7C264
CY7C264@PLCC28 [SA008A]	CY7C291
CY7C291@PLCC28 [\$\$\$\$\$]	CY7C291A
CY7C291A@PLCC28 [SA008A]	CY7C292
CY7C292@PLCC28 [\$\$\$\$\$]	CY7C292A
CY7C292A@PLCC28 [SA008A]	CY7C293A
CY7C293A@PLCC28 [SA008A]	

### DRAM & SRAM

CY62128@S0IC32 [SA687]	CY62128@SOJ32 [SA661]
CY62128@VSOP32 [SA620-B4807]	CY62128L@S0IC32 [SA687]
CY62128L@SOJ32 [SA661]	CY62128L@VSOP32 [SA620-B4807]
CY62128LL@S0IC32 [SA687]	CY62128LL@SOJ32
CY62128LL@VSOP32 [SA620-B4807]	CY7C192
CY7C192@SOJ28 [SA646]	

### PLD

PALC16L8	PALC16L8@PLCC20 [SA001A-B2001]
PALC16L8L	PALC16L8L@PLCC20 [SA001A-B2001]
PALC16R4	PALC16R4@PLCC20 [SA001A-B2001]
PALC16R4L	PALC16R4L@PLCC20 [SA001A-B2001]
PALC16R6	PALC16R6@PLCC20 [SA001A-B2001]
PALC16R6L	PALC16R6L@PLCC20 [SA001A-B2001]
PALC16R8	PALC16R8@PLCC20 [SA001A-B2001]
PALC16R8L	PALC16R8L@PLCC20 [SA001A-B2001]

PALC22V10D  
PALCE16V8  
PALCE20V8  
PALCE20V8L  
PALCE22V10  
PLDC20G10  
PLDC20G10B  
PLDC20RA10

PALC22V10D@PLCC28 [SA008A]  
PALCE16V8@PLCC20 [SA001A-B2001]  
PALCE20V8@PLCC28 [SA008A]  
PALCE20V8L@PLCC28 [SA008A]  
PALCE22V10@PLCC28 [SA008A]  
PLDC20G10@PLCC28 [SA008A]  
PLDC20G10B@PLCC28 [SA008A]  
PLDC20RA10@PLCC28

## MICROCONTROLLER

CG6457AM@SSOP20 (ISP)  
CY14B256@S0IC32 [SA715]  
CY14B256L@S0IC32 [SA715]  
CY7C60113@SSOP28 [SA626A]  
CY7C60113C@SSOP28 [SA626A]  
CY7C60123  
CY7C60123@SSOP48 [SA669]  
CY7C60123C  
CY7C60123C@SSOP48 [SA669]  
CY7C60223  
CY7C60223@QSOP24 (ISP)  
CY7C60223@S0IC24 (ISP)  
CY7C60223C (ISP)  
CY7C60223C@S0IC24 [SA404]  
CY7C60323@MLF32 (ISP)  
CY7C60333@MLF32 (ISP)  
CY7C60445@QFN32 (ISP)  
CY7C60456@QFN48 (ISP)  
CY7C63000@S0IC20 [SA404]  
CY7C63000A@S0IC20 [SA404]  
CY7C63000C@S0IC20 [SA404]  
CY7C63001@S0IC20 [SA404]  
CY7C63001A@S0IC20 [SA404]  
CY7C63001C@S0IC20 [SA404]  
CY7C63100@S0IC24 [SA404]  
CY7C63100A@S0IC24 [SA404]  
CY7C63100C@S0IC24 [SA404]  
CY7C63101@S0IC24 [SA404]  
CY7C63101A@S0IC24 [SA404]  
CY7C63101C@S0IC24 [SA404]  
CY7C63200@S0IC18 [SA404]  
CY7C63200A@S0IC18 [SA404]  
CY7C63200C@S0IC18 [SA404]  
CY7C63201@S0IC18 [SA404]  
CY7C63201A@S0IC18 [SA404]  
CY7C63201C@S0IC18 [SA404]  
CY7C63310 (ISP)  
CY7C63310@S0IC16 (ISP)  
CY7C63310C (ISP)  
CY7C63310C@S0IC16 (ISP)  
CY7C63801 (ISP)

CG6462AM@S0IC8 (ISP)  
CY14B256@SSOP48 [SA669]  
CY14B256L@SSOP48 [SA669]  
CY7C60113@SSOP28 (ISP)  
CY7C60113C@SSOP28 (ISP)  
CY7C60123 (ISP)  
CY7C60123@SSOP48 (ISP)  
CY7C60123C (ISP)  
CY7C60123C@SSOP48 (ISP)  
CY7C60223 (ISP)  
CY7C60223@S0IC24 [SA404]  
CY7C60223C  
CY7C60223C@QSOP24 (ISP)  
CY7C60223C@S0IC24 (ISP)  
CY7C60323@SSOP28 (ISP)  
CY7C60443@QFN32 (ISP)  
CY7C60455@QFN48 (ISP)  
CY7C63000  
CY7C63000A  
CY7C63000C  
CY7C63001  
CY7C63001A  
CY7C63001C  
CY7C63100  
CY7C63100A  
CY7C63100C  
CY7C63101  
CY7C63101A  
CY7C63101C  
CY7C63200  
CY7C63200A  
CY7C63200C  
CY7C63201  
CY7C63201A  
CY7C63201C  
CY7C63310  
CY7C63310@S0IC16 [SA602]  
CY7C63310C  
CY7C63310C@S0IC16 [SA602]  
CY7C63801  
CY7C63801@S0IC16 [SA602]

CY7C63801@S0IC16 (ISP)  
CY7C63801C (ISP)  
CY7C63801C@S0IC16 (ISP)  
CY7C63803@S0IC16 (ISP)  
CY7C63803C@S0IC16 (ISP)  
CY7C63813 (ISP)  
CY7C63813@S0IC18 (ISP)  
CY7C63813C (ISP)  
CY7C63813C@S0IC18 (ISP)  
CY7C63823 (ISP)  
CY7C63823@S0IC24 [SA404]  
CY7C63823C  
CY7C63823C@QSOP24 (ISP)  
CY7C63823C@S0IC24 (ISP)  
CY7C63833C@QFN32 (ISP)  
CY7C63903@SSOP28 (ISP)  
CY7C63903C@SSOP28 (ISP)  
CY7C63913 (ISP)  
CY7C63913C (ISP)  
CY7C63923@SSOP48 (ISP)  
CY7C63923C@SSOP48 (ISP)  
CY7C64215@SSOP28 (ISP)  
CY7C64316@QFN16 (ISP)  
CY7C64345@QFN32 (ISP)  
CY7C64356@QFN48 (ISP)  
CY8C20234@MLF16 (ISP)  
CY8C20266@QFN16 (ISP)  
CY8C20334@MLF24 (ISP)  
CY8C20366@QFN24 (ISP)  
CY8C20434@MLF32 (ISP)  
CY8C20466@QFN32 (ISP)  
CY8C20546@SSOP48 (ISP)  
CY8C20646@QFN48 (ISP)  
CY8C21123@S0IC8 (ISP)  
CY8C21234@S0IC16 (ISP)  
CY8C21323@SSOP20 (ISP)  
CY8C21434@MLF32 (ISP)  
CY8C21634@MLF32 (ISP)  
CY8C24123@S0IC8 (ISP)  
CY8C24123A@S0IC8 (ISP)  
CY8C24223@S0IC20 (ISP)  
CY8C24223A (ISP)  
CY8C24223A@SSOP20 (ISP)  
CY8C24423 (ISP)  
CY8C24423@MLF32 (ISP)  
CY8C24423@S0IC28 (ISP)  
CY8C24423@SSOP28 (ISP)  
CY8C24423A (ISP)  
CY8C24423A@MLF32 (ISP)  
CY8C24423A@S0IC28 (ISP)  
CY8C24423A@SSOP28 (ISP)  
CY8C24533 (ISP)  
CY8C24533@S0IC28 (ISP)

CY7C63801C  
CY7C63801C@S0IC16 [SA602]  
CY7C63803@S0IC16 [SA602]  
CY7C63803C@S0IC16 [SA602]  
CY7C63813  
CY7C63813@S0IC18 [SA404]  
CY7C63813C  
CY7C63813C@S0IC18 [SA404]  
CY7C63823  
CY7C63823@QSOP24 (ISP)  
CY7C63823@S0IC24 (ISP)  
CY7C63823C (ISP)  
CY7C63823C@S0IC24 [SA404]  
CY7C63833@QFN32 (ISP)  
CY7C63903@SSOP28 [SA626A]  
CY7C63903C@SSOP28 [SA626A]  
CY7C63913  
CY7C63913C  
CY7C63923@SSOP48 [SA669]  
CY7C63923C@SSOP48 [SA669]  
CY7C64215@MLF56 (ISP)  
CY7C64315@QFN16 (ISP)  
CY7C64343@QFN32 (ISP)  
CY7C64355@QFN48 (ISP)  
CY8C20000@MLF48 (ISP)  
CY8C20246@QFN16 (ISP)  
CY8C20324@MLF24 (ISP)  
CY8C20346@QFN24 (ISP)  
CY8C20424@MLF32 (ISP)  
CY8C20446@QFN32 (ISP)  
CY8C20534@SSOP28 (ISP)  
CY8C20566@SSOP48 (ISP)  
CY8C20666@QFN48 (ISP)  
CY8C21223@S0IC16 (ISP)  
CY8C21323@MLF24 (ISP)  
CY8C21334@SSOP20 (ISP)  
CY8C21534@SSOP28 (ISP)  
CY8C24123 (ISP)  
CY8C24123A (ISP)  
CY8C24223 (ISP)  
CY8C24223@SSOP20 (ISP)  
CY8C24223A@S0IC20 (ISP)  
CY8C24423  
CY8C24423@MLF32 [SA686]  
CY8C24423@S0IC28 [SA404]  
CY8C24423@SSOP28 [SA626A]  
CY8C24423A  
CY8C24423A@MLF32 [SA686]  
CY8C24423A@S0IC28 [SA404]  
CY8C24423A@SSOP28 [SA626A]  
CY8C24533  
CY8C24533@S0IC28 [SA404]  
CY8C24533@SSOP28 [SA626A]

CY8C24533@SSOP28 (ISP)  
CY8C24533A (ISP)  
CY8C24533A@S0IC28 (ISP)  
CY8C24533A@SSOP28 (ISP)  
CY8C24533C@S0IC28 [SA404]  
CY8C24633 (ISP)  
CY8C24633@SSOP28 (ISP)  
CY8C24633A@S0IC28 (ISP)  
CY8C24794@MLF56 (ISP)  
CY8C24994@MLF68 (ISP)  
CY8C25122C (ISP)  
CY8C26233@S0IC20 (ISP)  
CY8C26233C (ISP)  
CY8C26233C@SSOP20 (ISP)  
CY8C26443@S0IC28 (ISP)  
CY8C26443C (ISP)  
CY8C26443C@SSOP28 (ISP)  
CY8C26643@SSOP48 (ISP)  
CY8C26643C (ISP)  
CY8C26643C@TQFP44 (ISP)  
CY8C27143 (ISP)  
CY8C27243 (ISP)  
CY8C27243@S0IC20 (ISP)  
CY8C27243@SSOP20 (ISP)  
CY8C27443 (ISP)  
CY8C27443@S0IC28 (ISP)  
CY8C27443@SSOP28 (ISP)  
CY8C27466@SSOP28 (ISP)  
CY8C27543@TQFP44 (ISP)  
CY8C27643@MLF48 [SA696]  
CY8C27643@SSOP48 [SA669]  
CY8C27666@MLF48 (ISP)  
CY8C27866@TQFP100 (ISP)  
CY8C29466@SSOP28 (ISP)  
CY8C29666@MLF48 (ISP)  
CY8C29866@TQFP100 (ISP)  
CY8CLED08@QFN48 (ISP)  
CY8CLED08@SSOP48 (ISP)  
CY8CLED16@SSOP28 (ISP)  
CY8CTMD200@QFN16 [SA743]  
CY8CTMD200@QFN32 [SA686]  
CY8CTMD200@SSOP48 [SA669]  
CY8CTMD200A@QFN24 [SA710]  
CY8CTMD200A@QFN48 [SA696]  
CY8CTMD201@QFN16 [SA743]  
CY8CTMD201@QFN32 [SA686]  
CY8CTMD201@SSOP48 [SA669]  
CY8CTMD201A@QFN24 [SA710]  
CY8CTMD201A@QFN48 [SA696]  
CYRF69103@QFN40 (ISP)  
CYRF69213@QFN40 (ISP)

CY8C24533A  
CY8C24533A@S0IC28 [SA404]  
CY8C24533A@SSOP28 [SA626A]  
CY8C24533C  
CY8C24533C@SSOP28 [SA626A]  
CY8C24633@S0IC28 (ISP)  
CY8C24633A (ISP)  
CY8C24633A@SSOP28 (ISP)  
CY8C24894@MLF56 (ISP)  
CY8C25122 (ISP)  
CY8C26233 (ISP)  
CY8C26233@SSOP20 (ISP)  
CY8C26233C@S0IC20 (ISP)  
CY8C26443 (ISP)  
CY8C26443@SSOP28 (ISP)  
CY8C26443C@S0IC28 (ISP)  
CY8C26643 (ISP)  
CY8C26643@TQFP44 (ISP)  
CY8C26643C@SSOP48 (ISP)  
CY8C27143  
CY8C27243  
CY8C27243@S0IC20 [SA404]  
CY8C27243@SSOP20 [SA626A]  
CY8C27443  
CY8C27443@S0IC28 [SA404]  
CY8C27443@SSOP28 [SA626A]  
CY8C27466 (ISP)  
CY8C27543@TQFP44 [SA245A-B4805]  
CY8C27566@TQFP44 (ISP)  
CY8C27643@MLF48 (ISP)  
CY8C27643@SSOP48 (ISP)  
CY8C27666@SSOP48 (ISP)  
CY8C29466 (ISP)  
CY8C29566@TQFP44 (ISP)  
CY8C29666@SSOP48 (ISP)  
CY8CLED04@QFN68 (ISP)  
CY8CLED08@SSOP28 (ISP)  
CY8CLED16@QFN48 (ISP)  
CY8CLED16@SSOP48 (ISP)  
CY8CTMD200@QFN24 [SA710]  
CY8CTMD200@QFN48 [SA696]  
CY8CTMD200A@QFN16 [SA743]  
CY8CTMD200A@QFN32 [SA686]  
CY8CTMD200A@SSOP48 [SA669]  
CY8CTMD201@QFN24 [SA710]  
CY8CTMD201@QFN48 [SA696]  
CY8CTMD201A@QFN16 [SA743]  
CY8CTMD201A@QFN32 [SA686]  
CY8CTMD201A@SSOP48 [SA669]  
CYRF69103C@QFN40 (ISP)  
CYRF69213C@QFN40 (ISP)

# CYROD

## MICROCONTROLLER

CRD89C4051  
CRD89C51  
CRD89C51@TQFP44 [SA675-B4805]  
CRD89C512RD@PLCC44 [SA244]  
CRD89C51AA  
CRD89C51AA@TQFP44 [SA675-B4805]  
CRD89C51AA1TB@PLCC44 [SA244]  
CRD89C51AA1TB@TQFP44 [SA675-B4805]  
CRD89C51AA1TB@TQFP48 [SA248-B4804]  
CRD89C51AB1T  
CRD89C51AB1T@TQFP44 [SA675-B4805]  
CRD89C51AB1T@TQFP48 [SA248-B4804]  
CRD89C51AB1TA  
CRD89C51AB1TA@TQFP44 [SA675-B4805]  
CRD89C51AB1TA@TQFP48 [SA248-B4804]  
CRD89C51AB1TB  
CRD89C51AB1TB@TQFP44 [SA675-B4805]  
CRD89C51AB1TB@TQFP48 [SA248-B4804]  
CRD89C51AC1T  
CRD89C51AC1T@TQFP44 [SA675-B4805]  
CRD89C51AC1T@TQFP48 [SA248-B4804]  
CRD89C51AD  
CRD89C51AD@TQFP44 [SA675-B4805]  
CRD89C51AD1T@PLCC44 [SA244]  
CRD89C51AD1T@TQFP44 [SA675-B4805]  
CRD89C51AD1T@TQFP48 [SA248-B4804]  
CRD89C51AR1TB  
CRD89C51AR1TB@TQFP44 [SA675-B4805]  
CRD89C51AR1TB@TQFP48 [SA248-B4804]  
CRD89C51RA  
CRD89C51RA@TQFP44 [SA675-B4805]  
CRD89C51RA2 (ISP)  
CRD89C51RA2@PLCC44 (ISP)  
CRD89C51RA2@TQFP44 (ISP)  
CRD89C51RB@PLCC44 [SA244]  
CRD89C51RB2  
CRD89C51RB2@PLCC44 [SA244]  
CRD89C51RB2@TQFP44 [SA675-B4805]  
CRD89C51RC  
CRD89C51RC@TQFP44 [SA675-B4805]  
CRD89C51RD@PLCC44 [SA244]  
CRD89C51RE  
CRD89C51RE@TQFP44 [SA675-B4805]  
CRD89C665@PLCC44 [SA244]  
CRD89L4051  
CRD89L51  
CRD89L51@TQFP44 [SA675-B4805]  
CRD89L51AA1TB@PLCC44 [SA244]  
CRD89L51AA1TB@TQFP44 [SA675-B4805]

CRD89C4051@SOIC20 [SA023A]  
CRD89C51@PLCC44 [SA244]  
CRD89C512RD  
CRD89C512RD@TQFP44 [SA675-B4805]  
CRD89C51AA@PLCC44 [SA244]  
CRD89C51AA1TB  
CRD89C51AB1T@PLCC44 [SA244]  
CRD89C51AB1TA@PLCC44 [SA244]  
CRD89C51AB1TB@PLCC44 [SA244]  
CRD89C51AC1T@PLCC44 [SA244]  
CRD89C51AD@PLCC44 [SA244]  
CRD89C51AD1T  
CRD89C51AR1TB@PLCC44 [SA244]  
CRD89C51RA@PLCC44 [SA244]  
CRD89C51RA2  
CRD89C51RA2@PLCC44 [SA244]  
CRD89C51RA2@TQFP44 [SA675-B4805]  
CRD89C51RB  
CRD89C51RB@TQFP44 [SA675-B4805]  
CRD89C51RB2 (ISP)  
CRD89C51RB2@PLCC44 (ISP)  
CRD89C51RB2@TQFP44 (ISP)  
CRD89C51RC@PLCC44 [SA244]  
CRD89C51RD  
CRD89C51RD@TQFP44 [SA675-B4805]  
CRD89C51RE@PLCC44 [SA244]  
CRD89C665  
CRD89C665@TQFP44 [SA675-B4805]  
CRD89L4051@SOIC20 [SA023A]  
CRD89L51@PLCC44 [SA244]  
CRD89L51AA1TB

CRD89L51AA1TB@TQFP48 [SA248-B4804]	
CRD89L51AB1T	CRD89L51AB1T@PLCC44 [SA244]
CRD89L51AB1T@TQFP44 [SA675-B4805]	
CRD89L51AB1T@TQFP48 [SA248-B4804]	
CRD89L51AB1TA	CRD89L51AB1TA@PLCC44 [SA244]
CRD89L51AB1TA@TQFP44 [SA675-B4805]	
CRD89L51AB1TA@TQFP48 [SA248-B4804]	
CRD89L51AB1TB	CRD89L51AB1TB@PLCC44 [SA244]
CRD89L51AB1TB@TQFP44 [SA675-B4805]	
CRD89L51AB1TB@TQFP48 [SA248-B4804]	
CRD89L51AC1T	CRD89L51AC1T@PLCC44 [SA244]
CRD89L51AC1T@TQFP44 [SA675-B4805]	
CRD89L51AC1T@TQFP48 [SA248-B4804]	
CRD89L51AD	CRD89L51AD@PLCC44 [SA244]
CRD89L51AD@TQFP44 [SA675-B4805]	CRD89L51AD1T
CRD89L51AD1T@PLCC44 [SA244]	
CRD89L51AD1T@TQFP44 [SA675-B4805]	
CRD89L51AD1T@TQFP48 [SA248-B4804]	
CRD89L51AR1TB	CRD89L51AR1TB@PLCC44 [SA244]
CRD89L51AR1TB@TQFP44 [SA675-B4805]	
CRD89L51AR1TB@TQFP48 [SA248-B4804]	
CRD89L51RA	CRD89L51RA@PLCC44 [SA244]
CRD89L51RA@TQFP44 [SA675-B4805]	CRD89L51RA2
CRD89L51RA2 (ISP)	CRD89L51RA2@PLCC44 [SA244]
CRD89L51RA2@PLCC44 (ISP)	CRD89L51RA2@TQFP44 [SA675-B4805]
CRD89L51RA2@TQFP44 (ISP)	CRD89L51RB
CRD89L51RB@PLCC44 [SA244]	CRD89L51RB@TQFP44 [SA675-B4805]
CRD89L51RB2	CRD89L51RB2 (ISP)
CRD89L51RB2@PLCC44 [SA244]	CRD89L51RB2@PLCC44 (ISP)
CRD89L51RB2@TQFP44 [SA675-B4805]	CRD89L51RB2@TQFP44 (ISP)
CRD89L51RC	CRD89L51RC@PLCC44 [SA244]
CRD89L51RC@TQFP44 [SA675-B4805]	CRD89L51RD
CRD89L51RD@PLCC44 [SA244]	CRD89L51RD@TQFP44 [SA675-B4805]
CRD89L665	CRD89L665@PLCC44 [SA244]
CRD89L665@TQFP44 [SA675-B4805]	

## DALLAS

### E (E) PROM/FRAM/NVRAM

DS1073M-100	DS1073M-60
DS1073M-66	DS1073M-80
DS1073Z-100@SOIC8 [SA602A]	DS1073Z-60@SOIC8 [SA602A]
DS1073Z-66@SOIC8 [SA602A]	DS1073Z-80@SOIC8 [SA602A]
DS1077LU-100	DS1077LU-120
DS1077LU-125	DS1077LU-133
DS1077LU-40	DS1077LU-50
DS1077LU-60	DS1077LU-66
DS1077LZ-100 [SA602A]	DS1077LZ-120 [SA602A]
DS1077LZ-125 [SA602A]	DS1077LZ-133 [SA602A]
DS1077LZ-40@SOIC8 [SA602A]	DS1077LZ-50@SOIC8 [SA602A]
DS1077LZ-60@SOIC8 [SA602A]	DS1077LZ-66@SOIC8 [SA602A]

DS1077U-100	DS1077U-120
DS1077U-125	DS1077U-133
DS1077U-40	DS1077U-50
DS1077U-60	DS1077U-66
DS1077Z-100 [SA602A]	DS1077Z-120 [SA602A]
DS1077Z-125 [SA602A]	DS1077Z-133 [SA602A]
DS1077Z-40@SOIC8 [SA602A]	DS1077Z-50@SOIC8 [SA602A]
DS1077Z-60@SOIC8 [SA602A]	DS1077Z-66@SOIC8 [SA602A]
DS1086U	DS1086Z [SA602A]
DS1220AB	DS1220AD
DS1220Y	DS1225AB
DS1225AD	DS1225D
DS1225E	DS1225Y
DS1230AB	DS1230W
DS1230Y	DS1235AB
DS1235Y	DS1243Y
DS1244	DS1244Y
DS1245AB	DS1245EE
DS1245W	DS1245Y
DS1248W	DS1248Y
DS1249AB	DS1249W
DS1249Y	DS1250AB
DS1250W	DS1250Y
DS1251AB	DS1251W
DS1251Y	DS1256W
DS1256Y	DS1258AB
DS1258W	DS1258Y
DS1265AB	DS1265W
DS1265Y	DS1270AB
DS1270W	DS1270Y
DS1284	DS1284N
DS1284Q@PLCC28 [SA008A]	DS1284QN@PLCC28 [SA008A]
DS1286	DS1286I
DS1287	DS1287A
DS12887	DS12887A
DS12C887	DS12C887+
DS12C887A	DS1330AB
DS1330Y	DS1345AB
DS1345W	DS1345Y
DS1350AB	DS1350W
DS1350Y	DS1385
DS1386 (32K)	DS1386 (8K)
DS1387	DS14285
DS14287	DS1485
DS1485@SOIC28 [SA630]	DS1486
DS1488	DS1501
DS1511	DS1553
DS1553W	DS1554
DS1554W	DS1556
DS1630AB	DS1630Y
DS1642	DS1643
DS1644	DS1645AB
DS1645EE	DS1645Y

DS1646  
DS1650AB  
DS1685-3  
DS1685-5  
DS1687-3  
DS17287-3  
DS1742  
DS1743  
DS1744  
DS1746  
DS1747W  
DS17487-5  
DS17887-5  
DS2406P@TSOC6 [\$\$\$\$\$\$]  
DS2430AP@TSOC6 [\$\$\$\$\$\$]  
DS2431@T0-92  
DS2432P@TSOC6 [\$\$\$\$\$\$]  
DS2433S (3. 9)@SOIC8 [SA602A]  
DS2460@SOIC8 [SA602]  
DS2502P@TSOC6 [\$\$\$\$\$\$]  
DS2502UNW  
DS2502UNW@SOT-23 [SA717]  
DS2505  
DS2506  
DS4510@uSOP10 [SA602]  
DS4550@TSSOP20 [SA026]

DS1647  
DS1650Y [\$\$\$\$\$\$]  
DS1685-3@SOP24 [SA404]  
DS1685-5@SOP24 [SA404]  
DS1687-5  
DS17287-5  
DS1742W  
DS1743W  
DS1744W  
DS1747  
DS17487-3  
DS17887-3  
DS2406@T0-92  
DS2430A@T0-92  
DS2431@TDFN6 [\$\$\$\$\$\$]  
DS2431P@TSOC6 [\$\$\$\$\$\$]  
DS2433@PR-35  
DS2433S (5. 5)@SOIC8 [SA605B]  
DS2502  
DS2502S@SOIC8 [SA602A]  
DS2502UNW@SOIC8 [SA602A]  
DS2502UNW@TSOC6 [\$\$\$\$\$\$]  
DS2505S@TSOC6 [\$\$\$\$\$\$]  
DS2506S@SOIC8 [SA605B]  
DS4520@TSSOP16 [SA026]

## MICROCONTROLLER

DS5000[32K]  
DS5000T[32K]  
DS87C520  
DS87C520@TQFP44 [SA245A-B4805]  
DS89C420 (rev. A)  
DS89C420 (rev. A)@TQFP44 [SA245A-B4805]  
DS89C420@PLCC44 [SA244]  
DS89C430  
DS89C430@TQFP44 [SA245A-B4805]  
DS89C440@PLCC44 [SA244]  
DS89C450  
DS89C450@TQFP44 [SA245A-B4805]  
DS5000[8K]  
DS5000T[8K]  
DS87C520@PLCC44 [SA244]  
DS89C420  
DS89C420 (rev. A)@PLCC44 [SA244]  
DS89C420@TQFP44 [SA245A-B4805]  
DS89C430@PLCC44 [SA244]  
DS89C440  
DS89C440@TQFP44 [SA245A-B4805]  
DS89C450@PLCC44 [SA244]

## DENSE-PAC

### E (E) PROM/FRAM/NVRAM

DPV27C101  
DPV27C256  
DPV27C512  
DPV27C101@PLCC32 [SA015A1T]  
DPV27C256@PLCC32 [SA015A1T]  
DPV27C512@PLCC32 [SA015A1T]

## DEUTRON

## E (E) PROM/FRAM/NVRAM

AC25LV010	AC25LV010@SOIC8 [SA602A]
AC25LV512	AC25LV512@SOIC8 [SA602A]
P439LV010@PLCC32 [SA015A1T]	P439LV010@VSOP32 [SA620-B4807]
P439LV040@PLCC32 [SA015A1T]	P439LV040@VSOP32 [SA620-B4807]
P439LV088@TSOP48 [SB247-B4806]	P439VF800@TSOP48 [SB247-B4806]

## EASTSOFT

### MICROCONTROLLER

HR7P169FGD	HR7P169FGD@ISP
HR7P169FGDD	HR7P169FGDD@ISP
HR7P169FGS [SA404]	HR7P169FGS@ISP
HR7P169FGS3 [SA602]	HR7P169FGS3@ISP
HR7P169FGS4 [SA602]	HR7P169FGS4@ISP
HR7P169FGS5 [SA602A]	HR7P169FGS5@ISP
HR7P169FGTF [SA026]	HR7P169FGTF@ISP
HR7P170FHD	HR7P170FHD@ISP
HR7P170FHS [SA404]	HR7P170FHS@ISP
HR7P170FHS3 [SA602]	HR7P170FHS3@ISP
HR7P170FHS4 [SA602]	HR7P170FHS4@ISP
HR7P170FHS5 [SA602A]	HR7P170FHS5@ISP
HR7P201FHD	HR7P201FHD@ISP
HR7P201FHS [SA404]	HR7P201FHS@ISP
HR7P201FHS3 [SA602]	HR7P201FHS3@ISP
HR7P201FHS4 [SA602]	HR7P201FHS4@ISP
HR7P201FHS5 [SA602A]	HR7P201FHS5@ISP

## E-CMOS

### E (E) PROM/FRAM/NVRAM

EC24C01	EC24C01@DFN8 [SA724]
EC24C01@SOIC8 [SA602A]	EC24C01@TSSOP8 [SA643]
EC24C02	EC24C02@DFN8 [SA724]
EC24C02@SOIC8 [SA602A]	EC24C02@TSSOP8 [SA643]
EC24C02A	EC24C02A@DFN8 [SA724]
EC24C02A@SOIC8 [SA602A]	EC24C02A@TSSOP8 [SA643]
EC24C04	EC24C04@DFN8 [SA724]
EC24C04@SOIC8 [SA602A]	EC24C04@TSSOP8 [SA643]
EC24C04A	EC24C04A@DFN8 [SA724]
EC24C04A@SOIC8 [SA602A]	EC24C04A@TSSOP8 [SA643]
EC24C08	EC24C08@DFN8 [SA724]
EC24C08@SOIC8 [SA602A]	EC24C08@TSSOP8 [SA643]
EC24C08A	EC24C08A@DFN8 [SA724]
EC24C08A@SOIC8 [SA602A]	EC24C08A@TSSOP8 [SA643]
EC24C128	EC24C128@DFN8 [SA724]
EC24C128@SOIC8 [SA602A]	EC24C128@TSSOP8 [SA643]
EC24C16	EC24C16@DFN8 [SA724]

EC24C16@SOIC8 [SA602A]  
EC24C16A  
EC24C16A@SOIC8 [SA602A]  
EC24C256  
EC24C256@SOIC8 [SA602A]  
EC24C32  
EC24C32@SOIC8 [SA602A]  
EC24C64  
EC24C64@SOIC8 [SA602A]

EC24C16@TSSOP8 [SA643]  
EC24C16A@DFN8 [SA724]  
EC24C16A@TSSOP8 [SA643]  
EC24C256@DFN8 [SA724]  
EC24C256@TSSOP8 [SA643]  
EC24C32@DFN8 [SA724]  
EC24C32@TSSOP8 [SA643]  
EC24C64@DFN8 [SA724]  
EC24C64@TSSOP8 [SA643]

## EFST

### E (E) PROM/FRAM/NVRAM

EM25LV010@SOIC8 [SA602A]  
EM25LV512@SOIC8 [SA602A]  
F49B002UA  
F49L004BA@PLCC32 [SA015A1T]  
F49L004UA@PLCC32 [SA015A1T]  
F49L040A@PLCC32 [SA015A1T]  
F49L160BA@TSOP48 [SB247-B4806]  
F49L400BA@TSOP48 [SB247-B4806]  
F49L800BA@TSOP48 [SB247-B4806]

EM25LV010@VFQFPN8 [SA684]  
EM25LV512@VFQFPN8 [SA684]  
F49B002UA@PLCC32 [SA015A1T]  
F49L004BA@TSOP40 [SA409T-B4002]  
F49L004UA@TSOP40 [SA409T-B4002]  
F49L040A@VSOP32 [SA620-B4807]  
F49L160UA@TSOP48 [SB247-B4806]  
F49L400UA@TSOP48 [SB247-B4806]  
F49L800UA@TSOP48 [SB247-B4806]

## ELECTRONIC ARRAYS

### E (E) PROM/FRAM/NVRAM

EA2716

## EMTC

### E (E) PROM/FRAM/NVRAM

EM24C02  
EM24C02@TSSOP8 [SA643]  
EM24C04@SOIC8 [SA602A]  
EM24C08  
EM24C08@TSSOP8 [SA643]  
EM24C16@SOIC8 [SA602A]  
EM25SL512@SOIC8 [SA602A]  
EM29SF002AB@PLCC32 [SA015A1T]  
EM29SF002AB@TSOP32 [SA410T-B4001]  
EM29SF002AT  
EM29SF002AT@TSOP32 [SA410T-B4001]  
EM29SF002NAB  
EM29SF002NAB@TSOP32 [SA410T-B4001]  
EM29SF002NAT  
EM29SF002NAT@TSOP32 [SA410T-B4001]

EM24C02@SOIC8 [SA602A]  
EM24C04  
EM24C04@TSSOP8 [SA643]  
EM24C08@SOIC8 [SA602A]  
EM24C16  
EM24C16@TSSOP8 [SA643]  
EM29SF002AB  
EM29SF002AT@PLCC32 [SA015A1T]  
EM29SF002NAB@PLCC32 [SA015A1T]  
EM29SF002NAT@PLCC32 [SA015A1T]

# EON

## E (E) PROM/FRAM/NVRAM

EN25B05 (Bottom Boot)@SOP8 (4. 0) [SA602A]  
EN25B05 (Bottom Boot)@SOP8 (5. 4) [SA605B]  
EN25B05 (Bottom Boot)@VDFN8 [SA683]  
EN25B05 (Top Boot)@SOP8 (4. 0) [SA602A]  
EN25B05 (Top Boot)@SOP8 (5. 4) [SA605B]  
EN25B05 (Top Boot)@VDFN8 [SA683]  
EN25B10 (Bottom Boot)@SOP8 (4. 0) [SA602A]  
EN25B10 (Bottom Boot)@SOP8 (5. 4) [SA605B]  
EN25B10 (Bottom Boot)@VDFN8 [SA683]  
EN25B10 (Top Boot)@SOP8 (4. 0) [SA602A]  
EN25B10 (Top Boot)@SOP8 (5. 4) [SA605B]  
EN25B10 (Top Boot)@VDFN8 [SA683]  
EN25B16 (Bottom Boot)@SOP8 [SA605B]  
EN25B16 (Bottom Boot)@SOP8 (ISP) EN25B16 (Bottom Boot)@VFQFN8 (ISP)  
EN25B16 (Bottom Boot)@VFQFPN8 [SA684]  
EN25B16 (Top Boot)@SOP8 [SA605B] EN25B16 (Top Boot)@SOP8 (ISP)  
EN25B16 (Top Boot)@VFQFN8 (ISP)  
EN25B16 (Top Boot)@VFQFPN8 [SA684]  
EN25B20 (Bottom Boot)@SOP8 (4. 0) [SA602A]  
EN25B20 (Bottom Boot)@SOP8 (5. 4) [SA605B]  
EN25B20 (Bottom Boot)@VDFN8 [SA683]  
EN25B20 (Top Boot)@SOP8 (4. 0) [SA602A]  
EN25B20 (Top Boot)@SOP8 (5. 4) [SA605B]  
EN25B20 (Top Boot)@VDFN8 [SA683]  
EN25B32 (Bottom Boot)@SOP16 [SA404]  
EN25B32 (Bottom Boot)@SOP16 (ISP) [SA404]  
EN25B32 (Bottom Boot)@SOP8 [SA605B]  
EN25B32 (Bottom Boot)@SOP8 (ISP)  
EN25B32 (Bottom Boot)@VDFN8 [SA684]  
EN25B32 (Bottom Boot)@VDFN8 (ISP) EN25B32 (Top Boot)@SOP16 [SA404]  
EN25B32 (Top Boot)@SOP16 (ISP) [SA404]  
EN25B32 (Top Boot)@SOP8 [SA605B] EN25B32 (Top Boot)@SOP8 (ISP)  
EN25B32 (Top Boot)@VDFN8 [SA684] EN25B32 (Top Boot)@VDFN8 (ISP)  
EN25B40 (Bottom Boot)@SOP8 (4. 0) [SA602A]  
EN25B40 (Bottom Boot)@SOP8 (5. 4) [SA605B]  
EN25B40 (Bottom Boot)@VDFN8 [SA683]  
EN25B40 (Top Boot)@SOP8 (4. 0) [SA602A]  
EN25B40 (Top Boot)@SOP8 (5. 4) [SA605B]  
EN25B40 (Top Boot)@VDFN8 [SA683]  
EN25B64 (Bottom Boot)@SOP16 [SA404]  
EN25B64 (Bottom Boot)@SOP16 (ISP) [SA404]  
EN25B64 (Bottom Boot)@VDFN8 [SA684]  
EN25B64 (Bottom Boot)@VDFN8 (ISP) EN25B64 (Top Boot)@SOP16 [SA404]  
EN25B64 (Top Boot)@SOP16 (ISP) [SA404]  
EN25B64 (Top Boot)@VDFN8 [SA684] EN25B64 (Top Boot)@VDFN8 (ISP)  
EN25B80 (Bottom Boot)@SOP8 (4. 0) [SA602A]  
EN25B80 (Bottom Boot)@SOP8 (5. 4) [SA605B]  
EN25B80 (Bottom Boot)@VDFN8 [SA683]  
EN25B80 (Top Boot)@SOP8 (4. 0) [SA602A]

EN25B80(Top Boot)@SOP8(5.4) [SA605B]  
EN25B80(Top Boot)@VDFN8 [SA683] EN25D16  
EN25D16@SOP16 [SA783] EN25D16@SOP8 [SA605B]  
EN25D16@VDFN8 [SA684] EN25D80  
EN25D80@SOP8 [SA605B] EN25D80@VDFN8 [SA683]  
EN25F05@SOP8(4.0) [SA602A] EN25F05@SOP8(5.4) [SA605B]  
EN25F05@VDFN8 [SA683] EN25F10@SOP8(4.0) [SA602A]  
EN25F10@SOP8(5.4) [SA605B] EN25F10@VDFN8 [SA683]  
EN25F16 EN25F16@SOP16 [SA783]  
EN25F16@SOP8 [SA605B] EN25F16@VDFN8 [SA684]  
EN25F20@SOP8(4.0) [SA602A] EN25F20@SOP8(5.4) [SA605B]  
EN25F20@VDFN8 [SA683] EN25F32  
EN25F32@SOP16 [SA404] EN25F32@SOP8 [SA605B]  
EN25F32@VDFN8 [SA684]  
EN25F40(fast mode)@SOP8(150mil) [SA602A]  
EN25F40(fast mode)@SOP8(200mil) [SA605B]  
EN25F40(fast mode)@VDFN8 [SA683] EN25F40@SOP8(150mil) [SA602A]  
EN25F40@SOP8(200mil) [SA605B] EN25F40@VDFN8 [SA683]  
EN25F64@DFN8 [SA684] EN25F64@SOP16 [SA404]  
EN25F64@SOP8 [SA605B] EN25F64@VDFN8 [SA683]  
EN25F80 EN25F80@SOP8(4.0) [SA602A]  
EN25F80@SOP8(5.4) [SA605B] EN25F80@VDFN8 [SA683]  
EN25LF05@SOP8(4.0) [SA602A] EN25LF05@SOP8(5.4) [SA605B]  
EN25LF05@VDFN8 [SA683] EN25LF10@SOP8(4.0) [SA602A]  
EN25LF10@SOP8(5.4) [SA605B] EN25LF10@VDFN8 [SA683]  
EN25LF20@SOP8 [SA605B] EN25LF20@VDFN8 [SA683]  
EN25LF40 EN25LF40@SOP8(150mil) [SA602A]  
EN25LF40@SOP8(200mil) [SA605B] EN25LF40@VDFN8 [SA683]  
EN25LV010@SOIC8 [SA602A] EN25LV010@VFQFPN8 [SA684]  
EN25LV020@SOIC8 [SA602A] EN25LV020@VFQFPN8 [SA684]  
EN25LV040@SOIC8 [SA602A] EN25LV040@VFQFPN8 [SA684]  
EN25LV080@SOIC8 [SA602A] EN25LV080@VFQFPN8 [SA684]  
EN25LV160@SOIC8 [SA602A] EN25LV160@SOIC8(ISP)  
EN25LV160@VFQFPN8 [SA684] EN25LV160@VFQFPN8(ISP)  
EN25LV512@SOIC8 [SA602A] EN25LV512@VFQFPN8 [SA684]  
EN25P05@SOP8(4.0) [SA602A] EN25P05@SOP8(5.4) [SA605B]  
EN25P05@VDFN8 [SA683] EN25P10@SOP8(4.0) [SA602A]  
EN25P10@SOP8(5.4) [SA605B] EN25P10@VDFN8 [SA683]  
EN25P16@SOP8 [SA605B] EN25P16@SOP8(ISP)  
EN25P16@VFQFPN8 [SA684] EN25P16@VFQFPN8(ISP)  
EN25P20@SOP8(4.0) [SA602A] EN25P20@SOP8(5.4) [SA605B]  
EN25P20@VDFN8 [SA683] EN25P32@SOP16 [SA404]  
EN25P32@SOP16(ISP) EN25P32@SOP8 [SA605B]  
EN25P32@SOP8(ISP) EN25P32@VDFN8 [SA684]  
EN25P32@VDFN8(ISP) EN25P40@SOP8(4.0) [SA602A]  
EN25P40@SOP8(5.4) [SA605B] EN25P40@VDFN8 [SA683]  
EN25P64@SOP16 [SA404] EN25P64@SOP16(ISP) [SA404]  
EN25P64@VDFN8 [SA684] EN25P64@VDFN8(ISP)  
EN25P80@SOP8(4.0) [SA602A] EN25P80@SOP8(5.4) [SA605B]  
EN25P80@VDFN8 [SA683] EN25Q16  
EN25Q16@SOP16 [SA783] EN25Q16@SOP8(4.0) [SA605B]  
EN25Q16@SOP8(5.4) [SA602A] EN25Q16@VDFN8 [SA684]  
EN25Q16A EN25Q16A@SOP16 [SA783]

EN25Q16A@SOP8(4.0) [SA602A@90] EN25Q16A@SOP8(5.4) [SA605B]  
EN25Q16A@VDFN8 [SA684] EN25Q32A  
EN25Q32A@SOP8 [SA605B] EN25Q32A@VDFN8 [SA683]  
EN25Q32B EN25Q32B@SOP8 [SA605B]  
EN25Q32B@VDFN8 [SA683] EN25Q40@SOP8(4.0) [SA605B]  
EN25Q40@SOP8(5.4) [SA602A] EN25Q40@VDFN8 [SA683]  
EN25Q40A@SOP8(4.0) [SA605B] EN25Q40A@SOP8(5.4) [SA602A]  
EN25Q40A@USON8 [SA724] EN25Q40A@VDFN8 [SA683]  
EN25Q64@SOP16 [SA404] EN25Q64@SOP8 [SA605B]  
EN25Q64@VDFN8(5\*6mm) [SA683] EN25Q64@VDFN8(6\*8mm) [SA684]  
EN25Q80A@SOP8(4.0) [SA602A] EN25Q80A@SOP8(5.4) [SA605B]  
EN25Q80A@VDFN8 [SA683] EN25S10@SOP8 [SA602A]  
EN25S10@VDFN8 [SA724] EN25S16@SOP8 [SA605B]  
EN25S16@VFQFPN8 [SA684] EN25S20@SOP8 [SA602A]  
EN25S20@VDFN8 [SA724]  
EN25S32(Bottom Boot)@SOP16 [SA404]  
EN25S32(Bottom Boot)@SOP16(ISP) [SA404]  
EN25S32(Bottom Boot)@SOP8 [SA605B]  
EN25S32(Bottom Boot)@SOP8(ISP)  
EN25S32(Bottom Boot)@VDFN8 [SA684]  
EN25S32(Bottom Boot)@VDFN8(ISP) EN25S32(Top Boot)@SOP16 [SA404]  
EN25S32(Top Boot)@SOP16(ISP) [SA404]  
EN25S32(Top Boot)@SOP8 [SA605B] EN25S32(Top Boot)@SOP8(ISP)  
EN25S32(Top Boot)@VDFN8 [SA684] EN25S32(Top Boot)@VDFN8(ISP)  
EN25S32@SOP16 [SA404] EN25S32@SOP8 [SA605B]  
EN25S32@VDFN8 [SA684] EN25S32@VSOP8 [SA605B]  
EN25S40@SOP8 [SA602A] EN25S40@VDFN8(2\*3mm) [SA724]  
EN25S40@VDFN8(5\*6mm) [SA683] EN25S64@VDFN8 [SA683]  
EN25S64@VSOP8 [SA605B] EN25S80@SOP8(150mil) [SA602A]  
EN25S80@SOP8(200mil) [SA605B] EN25S80@VDFN8 [SA683]  
EN25T16@SOP8 [SA605B] EN25T16@VFQFPN8 [SA684]  
EN25T40@SOP8(150mil) [SA602A] EN25T40@SOP8(209mil) [SA605B]  
EN25T40@VDFN8 [SA683] EN25T80  
EN25T80@SOP8 [SA605B] EN25T80@VDFN8 [SA683]  
EN27C010 EN27C010@PLCC32 [SA015A1T]  
EN27C512 EN27C512@PLCC32  
EN27LN1G08@TSOP48 [SB247-B4806] EN29F002AB  
EN29F002AB@PLCC32 [SA015A1T] EN29F002AB@TSOP32 [SA410T-B4001]  
EN29F002ANB EN29F002ANB@PLCC32 [SA015A1T]  
EN29F002ANB@TSOP32 [SA410T-B4001]  
EN29F002ANT EN29F002ANT@PLCC32 [SA015A1T]  
EN29F002ANT@TSOP32 [SA410T-B4001]  
EN29F002AT EN29F002AT@PLCC32 [SA015A1T]  
EN29F002AT@TSOP32 [SA410T-B4001] EN29F002B  
EN29F002B@PLCC32 [SA015A1T] EN29F002B@TSOP32 [SA410T-B4001]  
EN29F002NB EN29F002NB@PLCC32 [SA015A1T]  
EN29F002NB@TSOP32 [SA410T-B4001] EN29F002NT  
EN29F002NT@PLCC32 [SA015A1T] EN29F002NT@TSOP32 [SA410T-B4001]  
EN29F002T EN29F002T@PLCC32 [SA015A1T]  
EN29F002T@TSOP32 [SA410T-B4001] EN29F010  
EN29F010@PLCC32 [SA015A1T] EN29F010@TSOP32 [SA410T-B4001]  
EN29F010@VSOP32 [SA620-B4807] EN29F040  
EN29F040@PLCC32 [SA015A1T] EN29F040@TSOP32 [SA410T-B4001]

EN29F040A	EN29F040A@PLCC32 [SA015A1T]
EN29F040A@TSOP32 [SA410T-B4001]	EN29F080@TSOP40 [SA409T-B4002]
EN29F512	EN29F512@PLCC32 [SA015A1T]
EN29F512@TSOP32 [SA410T-B4001]	EN29F512@VSOP32 [SA620-B4807]
EN29F800B@TSOP48 [SB247-B4806]	EN29F800T@TSOP48 [SB247-B4806]
EN29LV010@PLCC32 [SA015A1T]	EN29LV010@TSOP32 [SA410T-B4001]
EN29LV010@VSOP32 [SA620-B4807]	EN29LV040@PLCC32 [SA015A1T]
EN29LV040@TSOP32 [SA410T-B4001]	EN29LV040@VSOP32 [SA620-B4807]
EN29LV040A	EN29LV040A@PLCC32 [SA015A1T]
EN29LV040A@TSOP32 [SA410T-B4001]	EN29LV040A@VSOP32 [SA620-B4807]
EN29LV160AB@TSOP48 [SB247-B4806]	EN29LV160AT@TSOP48 [SB247-B4806]
EN29LV160B@TSOP48 [SB247-B4806]	EN29LV160BB@TSOP48 [SB247-B4806]
EN29LV160BT@TSOP48 [SB247-B4806]	EN29LV160T@TSOP48 [SB247-B4806]
EN29LV320AB@TSOP48 [SB247-B4806]	EN29LV320AT@TSOP48 [SB247-B4806]
EN29LV320B@TSOP48 [SB247-B4806]	EN29LV320T@TSOP48 [SB247-B4806]
EN29LV400AB@TSOP48 [SB247-B4806]	EN29LV400AT@TSOP48 [SB247-B4806]
EN29LV400B@TSOP48 [SB247-B4806]	EN29LV400T@TSOP48 [SB247-B4806]
EN29LV512@PLCC32 [SA015A1T]	EN29LV512@TSOP32 [SA410T-B4001]
EN29LV512@VSOP32 [SA620-B4807]	EN29LV640B@TSOP48 [SB247-B4806]
EN29LV640H@TSOP48 [SB247-B4806]	EN29LV640L@TSOP48 [SB247-B4806]
EN29LV640T@TSOP48 [SB247-B4806]	EN29LV641H@TSOP48 [SB247-B4806]
EN29LV641L@TSOP48 [SB247-B4806]	EN29LV800AB@TSOP48 [SB247-B4806]
EN29LV800AT@TSOP48 [SB247-B4806]	EN29LV800B@TSOP48 [SB247-B4806]
EN29LV800BB@TSOP48 [SB247-B4806]	EN29LV800BT@TSOP48 [SB247-B4806]
EN29LV800CB@TSOP48 [SB247-B4806]	EN29LV800CT@TSOP48 [SB247-B4806]
EN29LV800T@TSOP48 [SB247-B4806]	EN29PL032@TSOP48 [SB247-B4806]
EN29PL064@TSOP48 [SB247-B4806]	EN29SL160B@TSOP48 [SB247-B4806]
EN29SL160T@TSOP48 [SB247-B4806]	EN29SL400B@TSOP48 [SB247-B4806]
EN29SL400T@TSOP48 [SB247-B4806]	EN29SL800B@TSOP48 [SB247-B4806]
EN29SL800T@TSOP48 [SB247-B4806]	

## EOREX

### E (E) PROM/FRAM/NVRAM

EM24LC02@SOP8 [SA602A]

## ESIGMA

### E (E) PROM/FRAM/NVRAM

ES27LN1G08@TSOP48 [SB247-B4806]

## ESMT

### E (E) PROM/FRAM/NVRAM

EM25LV010@SOIC8 [SA602A]	EM25LV010@VFQFPN8 [SA684]
EM25LV512@SOIC8 [SA602A]	EM25LV512@VFQFPN8 [SA684]
F25D04QA@SOIC8 [SA602A]	F25D04QA@WSON8 [SA683]
F25D08QA@SOIC8 (150mil) [SA602A]	F25D08QA@SOIC8 (200mil) [SA605B]

F25D08QA@WSON8 [SA683] F25D64QA@SOIC8 [SA605B]  
F25D64QA@WSON8 [SA683] F25L004AB  
F25L004AB@SOIC8 (150mil) [SA602A] F25L004AB@SOIC8 (200mil) [SA605B]  
F25L004AT F25L004AT@SOIC8 (150mil) [SA602A]  
F25L004AT@SOIC8 (200mil) [SA605B] F25L008AB@SOIC8 [SA605B]  
F25L008AT@SOIC8 [SA605B] F25L016AB@SOIC8 [SA605B]  
F25L016AT@SOIC8 [SA605B] F25L01PA  
F25L01PA (2D)@SOIC8 [SA602A] F25L01PA (2D)@TSSOP8 [SA643]  
F25L01PA@SOIC8 (150mil) [SA602A] F25L01PA@SOIC8 (200mil) [SA605B]  
F25L02PA  
F25L02PA (2F)@SOIC8 (150mil) [SA602A]  
F25L02PA (2F)@SOIC8 (200mil) [SA605B]  
F25L02PA (2F)@WSON8 [SA683] F25L02PA@SOIC8 (150mil) [SA602A]  
F25L02PA@SOIC8 (200mil) [SA605B] F25L04PA  
F25L04PA@SOIC8 (150mil) [SA602A] F25L04PA@SOIC8 (200mil) [SA605B]  
F25L05PA (2D)@SOIC8 [SA602A] F25L05PA (2D)@TSSOP8 [SA643]  
F25L08PA (2G)  
F25L08PA (2G)@SOIC8 (150mil) [SA602A]  
F25L08PA (2G)@SOIC8 (200mil) [SA605B]  
F25L08PA (2G)@WSON8 [SA683]  
F25L08PA (AAI-PROGRAM)@SOIC8 [SA605B]  
F25L08PA (PAGE-PROGRAM)@SOIC8 [SA605B]  
F25L08QA@SOIC8 (150mil) [SA602A] F25L08QA@SOIC8 (200mil) [SA605B]  
F25L16PA (2S)  
F25L16PA (2S)@SOIC8 (150mil) [SA602A]  
F25L16PA (2S)@SOIC8 (200mil) [SA605B]  
F25L16PA (2S)@SOIC8 [SA404] F25L16PA (2S)@WSON8 [SA683]  
F25L16PA (AAI-PROGRAM)@SOIC8 [SA605B]  
F25L16PA (PAGE-PROGRAM)@SOIC8 [SA605B]  
F25L16QA F25L16QA@SOIC16 [SA404]  
F25L16QA@SOIC8 (150mil) [SA602A] F25L16QA@SOIC8 (200mil) [SA605B]  
F25L16QA@WSON8 [SA683] F25L320PA (4K OTP)@SOIC16 [SA404]  
F25L320PA (4K OTP)@SOIC8 [SA605B] F25L320PA@SOIC16 [SA404]  
F25L320PA@SOIC8 [SA605B]  
F25L32PA (4K OTP) (new)@SOIC16 [SA404]  
F25L32PA (4K OTP) (new)@SOIC8 [SA605B]  
F25L32PA (4K OTP)@SOIC16 [SA404] F25L32PA (4K OTP)@SOIC8 [SA605B]  
F25L32PA (new)@SOIC16 [SA404] F25L32PA (new)@SOIC8 [SA605B]  
F25L32PA@SOIC16 [SA404] F25L32PA@SOIC8 [SA605B]  
F25L32QA (2S)@SOIC16 [SA404] F25L32QA (2S)@SOIC8 [SA605B]  
F25L32QA (2S)@WSON8 [SA683] F25L32QA (4K OTP)@SOIC16 [SA404]  
F25L32QA (4K OTP)@SOIC8 [SA605B] F25L32QA@SOIC16 [SA404]  
F25L32QA@SOIC8 [SA605B] F25L64QA@SOIC16 [SA404]  
F25L64QA@SOIC8 [SA605B] F25L64QA@WSON8 [SA683]  
F29L064BGA@TSOP48 [SB247-B4806] F29L064UGA@TSOP48 [SB247-B4806]  
F49B002UA F49B002UA@PLCC32 [SA015A1T]  
F49L004BA@PLCC32 [SA015A1T] F49L004BA@TSOP40 [SA409T-B4002]  
F49L004UA@PLCC32 [SA015A1T] F49L004UA@TSOP40 [SA409T-B4002]  
F49L040A@PLCC32 [SA015A1T] F49L040A@VSOP32 [SA620-B4807]  
F49L160BA@TSOP48 [SB247-B4806] F49L160UA@TSOP48 [SB247-B4806]  
F49L320BA@TSOP48 [SB247-B4806] F49L320UA@TSOP48 [SB247-B4806]  
F49L400BA@TSOP48 [SB247-B4806] F49L400UA@TSOP48 [SB247-B4806]  
F49L800BA@TSOP48 [SB247-B4806] F49L800UA@TSOP48 [SB247-B4806]

F59D1G81A@TSOP48 [SB247-B4806]  
F59D4G81A@TSOP48 [SB247-B4806]  
F59L1G81LA@TSOP48 [SB247-B4806]  
F59L2G81A@TSOP48 [SB247-B4806]  
F59L512M81A@TSOP48 [SB247-B4806]

F59D2G81A@TSOP48 [SB247-B4806]  
F59L1G81A@TSOP48 [SB247-B4806]  
F59L1G81MA@TSOP48 [SB247-B4806]  
F59L4G81A@TSOP48 [SB247-B4806]

## ESTEK

### E (E) PROM/FRAM/NVRAM

24C02  
24C02@TSSOP8 [SA643]  
24C04@SOP8 [SA602A]  
24C08  
24C08@TSSOP8 [SA643]  
24C16@SOP8 [SA602A]  
K24C32  
K24C32@TSSOP8 [SA643]  
K24C64@SOP8 [SA602A]

24C02@SOP8 [SA602A]  
24C04  
24C04@TSSOP8 [SA643]  
24C08@SOP8 [SA602A]  
24C16  
24C16@TSSOP8 [SA643]  
K24C32@SOP8 [SA602A]  
K24C64  
K24C64@TSSOP8 [SA643]

## E-TRAND

### E (E) PROM/FRAM/NVRAM

AMI29DL163BT@TSOP48 [SB247-B4806]  
AMI29DL163TT@TSOP48 [SB247-B4806]

## EVERSPIN

### E (E) PROM/FRAM/NVRAM

M24A16B@FBGA48 [\$\$\$\$\$]  
MROA08B@FBGA48 [\$\$\$\$\$]  
MROA08B@TSOP44 [SA645]  
MROA16A@TSOP44 [SA645]  
MROA16B@TSOP44 [SA645]  
MRODL08B@FBGA48 [\$\$\$\$\$]  
MR20H40CDCR [SA683]  
MR20H40MDC [SA683]  
MR20H40MPU  
MR256A08@SOIC32 [SA715]  
MR256A08B@FBGA48 [\$\$\$\$\$]  
MR256A08B@TSOP44 [SA645]  
MR25H10CDC [SA683]  
MR25H10MDC [SA683]  
MR25H256CDC [SA683]  
MR25H256MDC [SA683]  
MR25H40CDC [SA683]  
MR25H40CPU  
MR25H40MDCR [SA683]  
MR2A08A@FBGA48 [\$\$\$\$\$]

M24A16B@TSOP44 [SA645]  
MROA08B@SOIC32 [SA715]  
MROA16A@FBGA48 [\$\$\$\$\$]  
MROA16B@FBGA48 [\$\$\$\$\$]  
MROD08B@FBGA48 [\$\$\$\$\$]  
MR20H40CDC [SA683]  
MR20H40CPU  
MR20H40MDCR [SA683]  
MR256A08@FBGA48 [\$\$\$\$\$]  
MR256A08@TSOP44 [SA645]  
MR256A08B@SOIC32 [SA715]  
MR256D08B@FBGA48 [\$\$\$\$\$]  
MR25H10CDCR [SA683]  
MR25H10MDCR [SA683]  
MR25H256CDCR [SA683]  
MR25H256MDCR [SA683]  
MR25H40CDCR [SA683]  
MR25H40MDC [SA683]  
MR25H40MPU  
MR2A08A@TSOP44 [SA645]

MR2A16A@FBGA48 [\$\$\$\$\$]  
MR4A08B@FBGA48 [\$\$\$\$\$]  
MR4A16B@FBGA48 [\$\$\$\$\$]

MR2A16A@TSOP44 [SA645]  
MR4A08B@TSOP44 [SA645]  
MR4A16B@TSOP48 [SA024-B4806]

## EXCELSEMI

### E (E) PROM/FRAM/NVRAM

ES25M16  
ES25M16@SOP8[150 mil] [SA605B]  
ES25M40  
ES25M40@SOP8[150 mil] [SA605B]  
ES25M80  
ES25M80@SOP8[150 mil] [SA605B]  
ES25P16@SOP8 [SA605B]  
ES25P80@SOP8 [SA605B]  
ES29LV160DB@TSOP48 [SB247-B4806]  
ES29LV160DT@TSOP48 [SB247-B4806]  
ES29LV160ET@TSOP48 [SB247-B4806]  
ES29LV160FT@TSOP48 [SB247-B4806]  
ES29LV320DT@TSOP48 [SB247-B4806]  
ES29LV320ET@TSOP48 [SB247-B4806]  
ES29LV320FT@TSOP48 [SB247-B4806]  
ES29LV400DT@TSOP48 [SB247-B4806]  
ES29LV400ET@TSOP48 [SB247-B4806]  
ES29LV800DB@TSOP48 [SB247-B4806]  
ES29LV800DT@TSOP48 [SB247-B4806]  
ES29LV800ET@TSOP48 [SB247-B4806]

ES25M16@SOP16 [SA404]  
ES25M16@SOP8[208 mil] [SA602A]  
ES25M40@SOP16 [SA404]  
ES25M40@SOP8[208 mil] [SA602A]  
ES25M80@SOP16 [SA404]  
ES25M80@SOP8[208 mil] [SA602A]  
ES25P40@SOP8 [SA605B]  
ES29LV160DB@PSOP44 [SA638]  
ES29LV160DT@PSOP44 [SA638]  
ES29LV160EB@TSOP48 [SB247-B4806]  
ES29LV160FB@TSOP48 [SB247-B4806]  
ES29LV320DB@TSOP48 [SB247-B4806]  
ES29LV320EB@TSOP48 [SB247-B4806]  
ES29LV320FB@TSOP48 [SB247-B4806]  
ES29LV400DB@TSOP48 [SB247-B4806]  
ES29LV400EB@TSOP48 [SB247-B4806]  
ES29LV800DB@PSOP44 [SA638]  
ES29LV800DT@PSOP44 [SA638]  
ES29LV800EB@TSOP48 [SB247-B4806]

## EXEL

### E (E) PROM/FRAM/NVRAM

XL24C01A  
XL24C04  
XL24C16@S0IC8 [SA602A]  
XL28C256  
XL28C256@TSOP28 [SA430T-B4003]  
XL9010 (F) [SA602A]  
XL9020 (F) [SA602A]  
XL9040 (F) [SA602A]  
XL9346@S0IC8 [SA602A]  
XL93CS56@S0IC8 [SA602A]  
XL93CS66  
XL93CS66@TSSOP8 [SA643]  
XL93LC46@S0IC8 [SA602A]  
XL93LC46A@S0IC8 [SA602A]  
XL93LC56@S0IC8 [SA602A]  
XL93LC56A@S0IC8 [SA602A]  
XL93LC66A@S0IC8 [SA602A]  
XLE28C16A  
XLE28C16B

XL24C02  
XL24C16  
XL24C32  
XL28C256@PLCC32 [SA015A1T]  
XL9010  
XL9020  
XL9040  
XL9346  
XL93CS56  
XL93CS56@TSSOP8 [SA643]  
XL93CS66@S0IC8 [SA602A]  
XL93LC46  
XL93LC46A  
XL93LC56  
XL93LC56A  
XL93LC66A  
XL9764  
XLE28C16A@PLCC32 [SA015A1T]  
XLE28C16B@PLCC32 [SA015A1T]

XLE28C16B@SOIC24 [SA404]  
XLM28C16A@PLCC32 [SA015A1T]  
XLM46P15  
XLS2816A  
XLS2817A  
XLS28C16A@PLCC32 [SA015A1T]  
XLS28C16B@PLCC32 [SA015A1T]  
XLS28C64B  
XLS28C64B@SOIC28 [SA404]  
XLS46P15  
XLS93C46@SOIC8 [SA602A]  
XLS93C56@SOIC8 [SA602A]  
XLS93C66@SOIC8 [SA602A]  
XLS93CS46@SOIC8 [SA602A]  
XLS93LC06  
XLS93LC66

XLM28C16A  
XLM46C15  
XLS2804A  
XLS2816A@PLCC32 [SA015A1T]  
XLS28C16A  
XLS28C16B  
XLS28C16B@SOIC24 [SA404]  
XLS28C64B@PLCC32 [SA015A1T]  
XLS46C15  
XLS93C46  
XLS93C56  
XLS93C66  
XLS93CS46  
XLS93CS46@TSSOP8 [SA643]  
XLS93LC06@SOIC8 [SA602A]  
XLS93LC66@SOIC8 [SA602A]

## FAIRCHILD

### E (E) PROM/FRAM/NVRAM

FM24C02 (M8)@SOIC8 [SA602A]  
FM24C02 (N)  
FM24C03 (MT8)@TSSOP8 [SA643]  
FM24C04 (M8)@SOIC8 [SA602A]  
FM24C04 (N)  
FM24C05 (MT8)@TSSOP8 [SA643]  
FM24C08 (M8)@SOIC8 [SA602A]  
FM24C08 (N)  
FM24C09 (MT8)@TSSOP8 [SA643]  
FM24C128 (MT8)@TSSOP8 [SA643]  
FM24C128 (N)  
FM24C16 (MT8)@TSSOP8 [SA643]  
FM24C17 (M8)@SOIC8 [SA602A]  
FM24C17 (N)  
FM24C256 (N)  
FM24C32 (N)  
FM27C010@PLCC32 [SA015A1T]  
FM27C040  
FM27C040@TSOP32 [SA410T-B4001]  
FM27C256@PLCC32 [SA015A1T]  
FM27C256Q@PLCC32 [SA015A1T]  
FM27C512@PLCC32 [SA015A1T]  
FM93C06 (M8) (08bit)@SOIC8 [SA602A]  
FM93C06 (M8) (16bit)@SOIC8 [SA602A]  
FM93C06 (MT8) (08bit)@TSSOP8 [SA643]  
FM93C06 (MT8) (16bit)@TSSOP8 [SA643]  
FM93C06 (N) (08bit)  
FM93C14 (16bit)  
FM93C46 (MT8)@TSSOP8 [SA643]  
FM93C46A (M8) (08bit)@SOIC8 [SA602A]  
FM93C46A (M8) (16bit)@SOIC8 [SA602A]

FM24C02 (MT8)@TSSOP8 [SA643]  
FM24C03 (M8)@SOIC8 [SA602A]  
FM24C03 (N)  
FM24C04 (MT8)@TSSOP8 [SA643]  
FM24C05 (M8)@SOIC8 [SA602A]  
FM24C05 (N)  
FM24C08 (MT8)@TSSOP8 [SA643]  
FM24C09 (M8)@SOIC8 [SA602A]  
FM24C09 (N)  
FM24C128 (MW8)@SOIC8 [SA602A]  
FM24C16 (M8)@SOIC8 [SA602A]  
FM24C16 (N)  
FM24C17 (MT8)@TSSOP8 [SA643]  
FM24C256 (M8)@SOIC8 [SA602A]  
FM24C32 (M8)@SOIC8 [SA602A]  
FM27C010  
FM27C010@TSOP32 [SA410T-B4001]  
FM27C040@PLCC32 [SA015A1T]  
FM27C256  
FM27C256Q  
FM27C512  
  
FM93C06 (N) (16bit)  
FM93C46 (M8)@SOIC8 [SA602A]  
FM93C46 (N)

FM93C46A(MT8) (08bit)@TSSOP8 [SA643]  
FM93C46A(MT8) (16bit)@TSSOP8 [SA643]  
FM93C46A(N) (08bit) FM93C46A(N) (16bit)  
FM93C56(M8)@SOIC8 [SA602A] FM93C56(MT8)@TSSOP8 [SA643]  
FM93C56(N)  
FM93C56A(M8) (08bit)@SOIC8 [SA602A]  
FM93C56A(M8) (16bit)@SOIC8 [SA602A]  
FM93C56A(MT8) (08bit)@TSSOP8 [SA643]  
FM93C56A(MT8) (16bit)@TSSOP8 [SA643]  
FM93C56A(N) (08bit) FM93C56A(N) (16bit)  
FM93C66(M8)@SOIC8 [SA602A] FM93C66(MT8)@TSSOP8 [SA643]  
FM93C66(N)  
FM93C66A(M8) (08bit)@SOIC8 [SA602A]  
FM93C66A(M8) (16bit)@SOIC8 [SA602A]  
FM93C66A(MT8) (08bit)@TSSOP8 [SA643]  
FM93C66A(MT8) (16bit)@TSSOP8 [SA643]  
FM93C66A(N) (08bit) FM93C66A(N) (16bit)  
FM93C76(M8) (16bit)@SOIC8 [SA602A]  
FM93C76(MT8) (16bit)@TSSOP8 [SA643]  
FM93C76(N) (16bit)  
FM93C76A(M8) (08bit)@SOIC8 [SA602A]  
FM93C76A(M8) (16bit)@SOIC8 [SA602A]  
FM93C76A(MT8) (08bit)@TSSOP8 [SA643]  
FM93C76A(MT8) (16bit)@TSSOP8 [SA643]  
FM93C76A(N) (08bit) FM93C76A(N) (16bit)  
FM93C86(M8) (16bit)@SOIC8 [SA602A]  
FM93C86(MT8) (16bit)@TSSOP8 [SA643]  
FM93C86(N) (16bit)  
FM93C86A(M8) (08bit)@SOIC8 [SA602A]  
FM93C86A(M8) (16bit)@SOIC8 [SA602A]  
FM93C86A(MT8) (08bit)@TSSOP8 [SA643]  
FM93C86A(MT8) (16bit)@TSSOP8 [SA643]  
FM93C86A(N) (08bit) FM93C86A(N) (16bit)  
FM93CS06(M8)@SOIC8 [SA602A] FM93CS06(MT8)@TSSOP8 [SA643]  
FM93CS06(N) FM93CS46(M8)@SOIC8 [SA602A]  
FM93CS46(MT8)@TSSOP8 [SA643] FM93CS46(N)  
FM93CS56(M8)@SOIC8 [SA602A] FM93CS56(MT8)@TSSOP8 [SA643]  
FM93CS56(N) FM93CS66(M8)@SOIC8 [SA602A]  
FM93CS66(MT8)@TSSOP8 [SA643] FM93CS66(N)  
FM93S46(M8)@SOIC8 [SA602A] FM93S46(MT8)@TSSOP8 [SA643]  
FM93S46(N) FM93S56(M8)@SOIC8 [SA602A]  
FM93S56(MT8)@TSSOP8 [SA643] FM93S56(N)  
FM93S66(M8)@SOIC8 [SA602A] FM93S66(MT8)@TSSOP8 [SA643]  
FM93S66(N) MM2716  
MM2716E NM24C02(M8)@SOIC8 [SA602A]  
NM24C02(MT8)@TSSOP8 [SA643] NM24C02(N)  
NM24C02L(M8)@SOIC8 [SA602A] NM24C02L(MT8)@TSSOP8 [SA643]  
NM24C02L(N) NM24C03(M8)@SOIC8 [SA602A]  
NM24C03(MT8)@TSSOP8 [SA643] NM24C03(N)  
NM24C04(M8)@SOIC8 [SA602A] NM24C04(MT8)@TSSOP8 [SA643]  
NM24C04(N) NM24C05(M8)@SOIC8 [SA602A]  
NM24C05(MT8)@TSSOP8 [SA643] NM24C05(N)  
NM24C08(M8)@SOIC8 [SA602A] NM24C08(MT8)@TSSOP8 [SA643]

NM24C08 (N)  
NM24C09 (MT8)@TSSOP8 [SA643]  
NM24C16 (M8)@SOIC8 [SA602A]  
NM24C16 (N)  
NM24C17 (MT8)@TSSOP8 [SA643]  
NM24C65 (M8)SOIC8 [SA602A]  
NM27C010  
NM27C010@TSOP32 [SA410T-B4001]  
NM27C020@PLCC32 [SA015A1T]  
NM27C020Q  
NM27C020Q@TSOP32 [SA410T-B4001]  
NM27C040@PLCC32 [SA015A1T]  
NM27C128  
NM27C210  
NM27C240  
NM27C256  
NM27C512  
NM27C64Q  
NM27LC256  
NM27LC512  
NM27LV010  
NM27LV010@TSOP32 [SA410T-B4001]  
NM27LV210@PLCC44 [SA244]  
NM27LV512@PLCC32 [SA015A1T]  
NM27P040@PLCC32 [SA015A1T]  
NM27P210  
NM27P512  
NM93C66 (M8) (16bit)@SOIC8 [SA602A]  
NM93C66 (MT8) (16bit)@TSSOP8 [SA643]  
NM93C66 (N) (16bit)  
NM93CS06 (MT8)@TSSOP8 [SA643]  
NM93CS46 (M8)@SOIC8 [SA602A]  
NM93CS46 (N)  
NM93CS56 (MT8)@TSSOP8 [SA643]  
NM93CS66 (M8)@SOIC8 [SA602A]  
NM93CS66 (N)  
NMC27C010  
NMC27C010@TSOP32 [SA410T-B4001]  
NMC27C1024@PLCC44 [SA244]  
NMC27C128B@PLCC32 [SA015A1T]  
NMC27C128BN@PLCC32 [SA015A1T]  
NMC27C128BQ@PLCC32 [SA015A1T]  
NMC27C16  
NMC27C16BQE  
NMC27C16HQ  
NMC27C256  
NMC27C256B  
NMC27C256Q  
NMC27C32  
NMC27C32BQ  
NMC27C32EH  
NMC27C512  
NMC27C512A

NM24C09 (M8)@SOIC8 [SA602A]  
NM24C09 (N)  
NM24C16 (MT8)@TSSOP8 [SA643]  
NM24C17 (M8)@SOIC8 [SA602A]  
NM24C17 (N)  
NM24C65 (N)  
NM27C010@PLCC32 [SA015A1T]  
NM27C020  
NM27C020@TSOP32 [SA410T-B4001]  
NM27C020Q@PLCC32 [SA015A1T]  
NM27C040  
NM27C040@TSOP32 [SA410T-B4001]  
NM27C128@PLCC32 [SA015A1T]  
NM27C210@PLCC44 [SA244]  
NM27C240@PLCC44 [SA244]  
NM27C256@PLCC32 [SA015A1T]  
NM27C512@PLCC32 [SA015A1T]  
NM27C64Q@PLCC32 [SA015A1T]  
NM27LC256@PLCC32 [SA015A1T]  
NM27LC512@PLCC32 [SA015A1T]  
NM27LV010@PLCC32 [SA015A1T]  
NM27LV210  
NM27LV512  
NM27P040  
NM27P040@TSOP32 [SA410T-B4001]  
NM27P210@PLCC44 [SA244]  
NM27P512@PLCC32 [SA015A1T]  
NM93CS06 (M8)@SOIC8 [SA602A]  
NM93CS06 (N)  
NM93CS46 (MT8)@TSSOP8 [SA643]  
NM93CS56 (M8)@SOIC8 [SA602A]  
NM93CS56 (N)  
NM93CS66 (MT8)@TSSOP8 [SA643]  
NMC2732  
NMC27C010@PLCC32 [SA015A1T]  
NMC27C1024  
NMC27C128B  
NMC27C128BN  
NMC27C128BQ  
NMC27C128CQ  
NMC27C16BQ  
NMC27C16H  
NMC27C16Q  
NMC27C256@PLCC32 [SA015A1T]  
NMC27C256B@PLCC32 [SA015A1T]  
NMC27C256Q@PLCC32 [SA015A1T]  
NMC27C32B  
NMC27C32E  
NMC27C32H  
NMC27C512@PLCC32 [SA015A1T]  
NMC27C512A@PLCC32 [SA015A1T]

NMC27C512AN	NMC27C512AN@PLCC32 [SA015A1T]
NMC27C64	NMC27C64 (BN)
NMC27C64 (N)	NMC27CP128
NMC87C257Q	NMC87C257Q@PLCC32 [SA015A1T]
NMC87C257V	NMC87C257V@PLCC32 [SA015A1T]
NMC9346 (M8) (16bit)@SOIC8 [SA602A]	
NMC9346 (MT8) (16bit)@TSSOP8 [SA643]	
NMC9346 (N) (16bit)	
NMC93C46 (M8) (16bit)@SOIC8 [SA602A]	
NMC93C46 (MT8) (16bit)@TSSOP8 [SA643]	
NMC93C46 (N) (16bit)	
NMC93C46A (M8) (16bit)@SOIC8 [SA602A]	
NMC93C46A (MT8) (16bit)@TSSOP8 [SA643]	
NMC93C46A (N) (16bit)	
NMC93C56 (M8) (16bit)@SOIC8 [SA602A]	
NMC93C56 (MT8) (16bit)@TSSOP8 [SA643]	
NMC93C56 (N) (16bit)	
NMC93C66 (M8) (16bit)@SOIC8 [SA602A]	
NMC93C66 (MT8) (16bit)@TSSOP8 [SA643]	
NMC93C66 (N) (16bit)	NMC93CS06 (M8)@SOIC8 [SA602A]
NMC93CS06 (MT8)@TSSOP8 [SA643]	NMC93CS06 (N)
NMC93CS46 (M8)@SOIC8 [SA602A]	NMC93CS46 (MT8)@TSSOP8 [SA643]
NMC93CS46 (N)	NMC93CS56 (M8)@SOIC8 [SA602A]
NMC93CS56 (MT8)@TSSOP8 [SA643]	NMC93CS56 (N)
NMC93CS66 (M8)@SOIC8 [SA602A]	NMC93CS66 (MT8)@TSSOP8 [SA643]
NMC93CS66 (N)	NMC9817

## MICROCONTROLLER

ACE1001 (M8)@SOIC8 [SA602A]	ACE1001 (M8X)@SOIC8 [SA602A]
ACE1001 (MT8)@TSSOP8 [SA026]	ACE1001 (MT8X)@TSSOP8 [SA026]
ACE1001E (M8)@SOIC8 [SA602A]	ACE1001E (M8X)@SOIC8 [SA602A]
ACE1001E (MT8)@TSSOP8 [SA026]	ACE1001E (MT8X)@TSSOP8 [SA026]
ACE1001L (M8)@SOIC8 [SA602A]	ACE1001L (M8X)@SOIC8 [SA602A]
ACE1001L (MT8)@TSSOP8 [SA026]	ACE1001L (MT8X)@TSSOP8 [SA026]
ACE1101 (EMT8)@TSSOP8 [SA026]	ACE1101 (EMT8X)@TSSOP8 [SA026]
ACE1101 (EN)	ACE1101 (EN14)
ACE1101 (LMT8)@TSSOP8 [SA026]	ACE1101 (LMT8X)@TSSOP8 [SA026]
ACE1101 (LN)	ACE1101 (LN14)
ACE1101 (MT8)@TSSOP8 [SA026]	ACE1101 (MT8X)@TSSOP8 [SA026]
ACE1101 (N)	ACE1101 (N14)
ACE1101 (VMT8)@TSSOP8 [SA026]	ACE1101 (VMT8X)@TSSOP8 [SA026]
ACE1101 (VN)	ACE1101 (VN14)
ACE1101B (EMT8)@TSSOP8 [SA026]	ACE1101B (EMT8X)@TSSOP8 [SA026]
ACE1101B (EN)	ACE1101B (EN14)
ACE1101B (MT8)@TSSOP8 [SA026]	ACE1101B (MT8X)@TSSOP8 [SA026]
ACE1101B (N)	ACE1101B (N14)
ACE1101B (VMT8)@TSSOP8 [SA026]	ACE1101B (VMT8X)@TSSOP8 [SA026]
ACE1101B (VN)	ACE1101B (VN14)
ACE1202 (dip14)	ACE1202 (dip8)
ACE1202 (M14)@SOIC14 [SA602]	ACE1202 (M8)@SOIC8 [SA602A]
ACE12022 (dip14)	ACE12022 (dip8)

ACE12022 (M14)@SOIC14 [SA602]  
ACE12022B (dip14)  
ACE12022B (M14)@SOIC14 [SA602]  
ACE12022BE (dip14)  
ACE12022BE (M14)@SOIC14 [SA602]  
ACE12022BV (dip14)  
ACE12022BV (M14)@SOIC14 [SA602]  
ACE12022E (dip14)  
ACE12022E (M14)@SOIC14 [SA602]  
ACE1202B (dip14)  
ACE1202B (M14)@SOIC14 [SA602]  
ACE1202BE (dip14)  
ACE1202BE (M14)@SOIC14 [SA602]  
ACE1202BV (dip14)  
ACE1202BV (M14)@SOIC14 [SA602]  
ACE1202E (dip14)  
ACE1202E (M14)@SOIC14 [SA602]  
ACE1202L (dip14)  
ACE1202L (M14)@SOIC14 [SA602]  
ACE1202V (dip8)  
ACE1202V (M8)@SOIC8 [SA602A]  
ACE1501 (EM8)@SOIC8 [SA602A]  
ACE1501 (EMT)@TSOP14 [SA026]  
ACE1501 (EMT8X)@TSSOP8 [SA026]  
ACE1501 (EMX)@SOIC14 [SA602]  
ACE1501 (EN14)  
ACE1501 (VM8)@SOIC8 [SA602A]  
ACE1501 (VMT)@TSOP14 [SA026]  
ACE1501 (VMT8X)@TSSOP8 [SA026]  
ACE1501 (VMX)@SOIC14 [SA602]  
ACE1501 (VN14)  
ACE1502 (EM8)@SOIC8 [SA602A]  
ACE1502 (EMT8)@TSSOP8 [SA026]  
ACE1502 (EN14)  
ACE1502 (VM8)@SOIC8 [SA602A]  
ACE1502 (VMT8)@TSSOP8 [SA026]  
ACE1502 (VN14)  
ACE8000 (M8X)@SOIC8 [SA602A]  
ACE8000E (M8X)@SOIC8 [SA602A]  
ACE8001 (M8X)@SOIC8 [SA602A]  
ACE8001 (MT8X)@TSSOP8 [SA026]  
ACE8001E (M8X)@SOIC8 [SA602A]  
ACE8001E (MT8X)@TSSOP8 [SA026]  
FMS7401L (EMT8X)@TSSOP8 [SA026]  
FMS7401L (EMX)@SOIC14 [SA602A]  
FMS7401L (EN14)  
FMS7401L (VN14)

ACE12022 (M8)@SOIC8 [SA602A]  
ACE12022B (dip8)  
ACE12022B (M8)@SOIC8 [SA602A]  
ACE12022BE (dip8)  
ACE12022BE (M8)@SOIC8 [SA602A]  
ACE12022BV (dip8)  
ACE12022BV (M8)@SOIC8 [SA602A]  
ACE12022E (dip8)  
ACE12022E (M8)@SOIC8 [SA602A]  
ACE1202B (dip8)  
ACE1202B (M8)@SOIC8 [SA602A]  
ACE1202BE (dip8)  
ACE1202BE (M8)@SOIC8 [SA602A]  
ACE1202BV (dip8)  
ACE1202BV (M8)@SOIC8 [SA602A]  
ACE1202E (dip8)  
ACE1202E (M8)@SOIC8 [SA602A]  
ACE1202L (dip8)  
ACE1202L (M8)@SOIC8 [SA602A]  
ACE1202V (M14)@SOIC14 [SA602]  
ACE1501 (EM)@SOIC14 [SA602]  
ACE1501 (EM8X)@SOIC8 [SA602A]  
ACE1501 (EMT8)@TSSOP8 [SA026]  
ACE1501 (EMTX)@TSOP14 [SA026]  
ACE1501 (EN)  
ACE1501 (VM)@SOIC14 [SA602]  
ACE1501 (VM8X)@SOIC8 [SA602A]  
ACE1501 (VMT8)@TSSOP8 [SA026]  
ACE1501 (VMTX)@TSOP14 [SA026]  
ACE1501 (VN)  
ACE1502 (EM)@SOIC14 [SA602]  
ACE1502 (EMT)@TSOP14 [SA026]  
ACE1502 (EN)  
ACE1502 (VM)@SOIC14 [SA602]  
ACE1502 (VMT)@TSOP14 [SA026]  
ACE1502 (VN)  
ACE8000 (M8)@SOIC8 [SA602A]  
ACE8000E (M8)@SOIC8 [SA602A]  
ACE8001 (M8)@SOIC8 [SA602A]  
ACE8001 (MT8)@TSSOP8 [SA026]  
ACE8001E (M8)@SOIC8 [SA602A]  
ACE8001E (MT8)@TSSOP8 [SA026]  
FMS7401L (EM8X)@SOIC8 [SA602A]  
FMS7401L (EMTX)@TSSOP14 [SA026]  
FMS7401L (EN)  
FMS7401L (VN)

## FIDELIX

E (E) PROM/FRAM/NVRAM

FM25Q16  
FM25Q16@WSON8 [SA683]  
FM25Q16A@SOP8 [SA602A]  
FM25Q32A  
FM25Q32A@SOP8(150 mil) [SA602A]  
FM25Q32A@WSON8 [SA683]

FM25Q16@SOP8 [SA605B]  
FM25Q16A  
FM25Q16A@WSON8 [SA683]  
FM25Q32A@SOP16 [SA783]  
FM25Q32A@SOP8(200 mil) [SA605B]  
FMND1G08U3B@TSOP48 [SB247-B4806]

## FIRST-RANK Technology

### E (E) PROM/FRAM/NVRAM

T24C02  
T24C02@TSSOP8 [SA643]  
T24C04@SOP8 [SA602A]  
T24C08  
T24C08@TSSOP8 [SA643]  
T24C16@SOP8 [SA602A]

T24C02@SOP8 [SA602A]  
T24C04  
T24C04@TSSOP8 [SA643]  
T24C08@SOP8 [SA602A]  
T24C16  
T24C16@TSSOP8 [SA643]

## FORCE TECHNOLOGIES

### E (E) PROM/FRAM/NVRAM

FT24C01  
FT24C01@TSOP8 [SA643]  
FT24C01A@SOIC8 [SA602A]  
FT24C02  
FT24C02@TSOP8 [SA643]  
FT24C02A@SOIC8 [SA602A]  
FT24C04  
FT24C04@TSOP8 [SA643]  
FT24C04A@SOIC8 [SA602A]  
FT24C08  
FT24C08@TSOP8 [SA643]  
FT24C08A@SOIC8 [SA602A]  
FT24C128  
FT24C128@TSOP8 [SA643]  
FT24C128A@SOIC8 [SA602A]  
FT24C16  
FT24C16@TSOP8 [SA643]  
FT24C16A@SOIC8 [SA602A]  
FT24C256  
FT24C256@TSOP8 [SA643]  
FT24C256A@SOIC8 [SA602A]  
FT24C32  
FT24C32@TSOP8 [SA643]  
FT24C32A@SOIC8 [SA602A]  
FT24C64  
FT24C64@TSOP8 [SA643]  
FT24C64A@SOIC8 [SA602A]  
FT27C010  
FT27C010@TSOP32 [SA410T-B4001]  
FT27C020@PLCC32 [SA015A1T]

FT24C01@SOIC8 [SA602A]  
FT24C01A  
FT24C01A@TSOP8 [SA643]  
FT24C02@SOIC8 [SA602A]  
FT24C02A  
FT24C02A@TSOP8 [SA643]  
FT24C04@SOIC8 [SA602A]  
FT24C04A  
FT24C04A@TSOP8 [SA643]  
FT24C08@SOIC8 [SA602A]  
FT24C08A  
FT24C08A@TSOP8 [SA643]  
FT24C128@SOIC8 [SA602A]  
FT24C128A  
FT24C128A@TSOP8 [SA643]  
FT24C16@SOIC8 [SA602A]  
FT24C16A  
FT24C16A@TSOP8 [SA643]  
FT24C256@SOIC8 [SA602A]  
FT24C256A  
FT24C256A@TSOP8 [SA643]  
FT24C32@SOIC8 [SA602A]  
FT24C32A  
FT24C32A@TSOP8 [SA643]  
FT24C64@SOIC8 [SA602A]  
FT24C64A  
FT24C64A@TSOP8 [SA643]  
FT27C010@PLCC32 [SA015A1T]  
FT27C020  
FT27C020@TSOP32

FT27C040	FT27C040@PLCC32 [SA015A1T]
FT27C040@TSOP32 [SA410T-B4001]	FT27C16
FT27C256	FT27C256@PLCC32 [SA015A1T]
FT27C64	FT27C64@PLCC32 [SA015A1T]
FT27HC256	FT27HC256@PLCC32 [SA015A1T]
FT27HC64	FT27HC64@PLCC32 [SA015A1T]
FT28C010	FT28C010@JLCC32 [SA412A]
FT28C010@PLCC32 [SA015A1T]	FT28C010@PLCC44 [SA244]
FT28C010@TSOP32 [SA410T-B4001]	FT28C010E
FT28C010E@JLCC32 [SA412A]	FT28C010E@PLCC32 [SA015A1T]
FT28C010E@PLCC44 [SA244]	FT28C010E@TSOP32 [SA410T-B4001]
FT28C020	FT28C020@JLCC32 [SA412A]
FT28C020@PLCC32 [SA015A1T]	FT28C020@PLCC44 [SA244]
FT28C020@TSOP32 [SA410T-B4001]	FT28C040
FT28C040@JLCC32 [SA412A]	FT28C040@PLCC32 [SA015A1T]
FT28C040@PLCC44 [SA244]	FT28C040@TSOP32 [SA410T-B4001]
FT28C16	FT28C16@PLCC32 [SA015A1T]
FT28C256	FT28C256@JLCC32 [SA412A]
FT28C256@PLCC32 [SA015A1T]	FT28C256@SOIC28 [SA404]
FT28C256@TSOP28 [SA430T-B4003]	FT28C256B
FT28C256B@JLCC32 [SA412A]	FT28C256B@PLCC32 [SA015A1T]
FT28C256B@SOIC28 [SA404]	FT28C256B@TSOP28 [SA430T-B4003]
FT28C64	FT28C64@PLCC32 [SA015A1T]
FT28C64@SOIC28 [SA404]	FT28C64@TSOP28 [SA430T-B4003]
FT28C64B	FT28C64B@JLCC32 [SA412A]
FT28C64B@PLCC32 [SA015A1T]	FT28C64B@SOIC28 [SA404]
FT28C64B@TSOP28 [SA430T-B4003]	FT28C64X
FT28C64X@PLCC32 [SA015A1T]	FT28C64X@SOIC28 [SA404]
FT28C64X@TSOP28 [SA430T-B4003]	FT28HC64
FT28HC64@PLCC32 [SA015A1T]	FT28HC64@TSOP28 [SA430T-B4003]
FT58C1001	FT58C1001@SSOP32 [SA687]
FT58C1001@VSOP32 [SA620-B4807]	

## FORWARD

### [E \(E\) PROM/FRAM/NVRAM](#)

24LC01	24LC01@SOIC8 [SA602A]
24LC02	24LC02@SOIC8 [SA602A]
24LC04	24LC04@SOIC8 [SA602A]
24LC08	24LC08@SOIC8 [SA602A]
24LC16	24LC16@SOIC8 [SA602A]
24LC32	24LC32@SOIC8 [SA602A]
24LC64	24LC64@SOIC8 [SA602A]

## FREESCALE

### [E \(E\) PROM/FRAM/NVRAM](#)

MR2A16A@TSOP44 [SA645]

## MICROCONTROLLER

MC56F8023MFAE@QFP32 [SA636]	MC56F8023VFAE@QFP32 [SA636]
MC56F8025VLD@QFP44 [SA245A-B4805]	
MC56F8033VLC@QFP32 [SA636]	
MC56F8035VLD@QFP44 [SA245A-B4805]	
MC56F8036MFAE@QFP48 [SA248-B4804]	
MC56F8036VFAE@QFP48 [SA248-B4804]	
MC68HC908JB12DW@SOIC28 [SA404]	MC68HC908JB12DWE@SOIC28 [SA404]
MC68HC908JB12JDW@SOIC20 [SA404]	MC68HC908JB12JDWE@SOIC20 [SA404]
MC68HC908JB16DW@SOIC28 [SA404]	MC68HC908JB16DWE@SOIC28 [SA404]
MC68HC908JB16FA@QFP32 [SA636]	MC68HC908JB16FAE@QFP32 [SA636]
MC68HC908JB16JDW@SOIC20 [SA404]	MC68HC908JB16JDWE@SOIC20 [SA404]
MC68HC908JB8ADW@SOIC28 [SA404]	MC68HC908JB8ADWE@SOIC28 [SA404]
MC68HC908JB8FB@TQFP44 [SA245A-B4805]	
MC68HC908JB8FBE@TQFP44 [SA245A-B4805]	
MC68HC908JB8JDW@SOIC20 [SA404]	MC68HC908JB8JDWE@SOIC20 [SA404]
MC68HC908JB8JP	MC68HC908JB8JPE
MC68HC908JK1CDW@SOIC20 [SA404]	MC68HC908JK1CDWE@SOIC20 [SA404]
MC68HC908JK1CP	MC68HC908JK1CPE
MC68HC908JK1ECDW@SOIC20 [SA404]	MC68HC908JK1ECDWE@SOIC20 [SA404]
MC68HC908JK1ECP	MC68HC908JK1ECPE
MC68HC908JK1EMDW@SOIC20 [SA404]	MC68HC908JK1EMDWE@SOIC20 [SA404]
MC68HC908JK1EMP	MC68HC908JK1EMPE
MC68HC908JK1EVDW@SOIC20 [SA404]	MC68HC908JK1EVDWE@SOIC20 [SA404]
MC68HC908JK1EVP	MC68HC908JK1EVPE
MC68HC908JK1MDW@SOIC20 [SA404]	MC68HC908JK1MDWE@SOIC20 [SA404]
MC68HC908JK1MP	MC68HC908JK1MPE
MC68HC908JK1VDW@SOIC20 [SA404]	MC68HC908JK1VDWE@SOIC20 [SA404]
MC68HC908JK1VP	MC68HC908JK1VPE
MC68HC908JK3CDW@SOIC20 [SA404]	MC68HC908JK3CDWE@SOIC20 [SA404]
MC68HC908JK3CP	MC68HC908JK3CPE
MC68HC908JK3ECDW@SOIC20 [SA404]	MC68HC908JK3ECDWE@SOIC20 [SA404]
MC68HC908JK3ECP	MC68HC908JK3ECPE
MC68HC908JK3EMDW@SOIC20 [SA404]	MC68HC908JK3EMDWE@SOIC20 [SA404]
MC68HC908JK3EMP	MC68HC908JK3EMPE
MC68HC908JK3EVDW@SOIC20 [SA404]	MC68HC908JK3EVDWE@SOIC20 [SA404]
MC68HC908JK3EVP	MC68HC908JK3EVPE
MC68HC908JK3MDW@SOIC20 [SA404]	MC68HC908JK3MDWE@SOIC20 [SA404]
MC68HC908JK3MP	MC68HC908JK3MPE
MC68HC908JK3VDW@SOIC20 [SA404]	MC68HC908JK3VDWE@SOIC20 [SA404]
MC68HC908JK3VP	MC68HC908JK3VPE
MC68HC908JL3CDW@SOIC28 [SA404]	MC68HC908JL3CDWE@SOIC28 [SA404]
MC68HC908JL3CP	MC68HC908JL3CPE
MC68HC908JL3ECDW@SOIC28 [SA404]	MC68HC908JL3ECDWE@SOIC28 [SA404]
MC68HC908JL3ECP	MC68HC908JL3ECPE
MC68HC908JL3EMDW@SOIC28 [SA404]	MC68HC908JL3EMDWE@SOIC28 [SA404]
MC68HC908JL3EMP	MC68HC908JL3EMPE
MC68HC908JL3EVDW@SOIC28 [SA404]	MC68HC908JL3EVDWE@SOIC28 [SA404]
MC68HC908JL3EVP	MC68HC908JL3EVPE
MC68HC908JL3MDW@SOIC28 [SA404]	MC68HC908JL3MDWE@SOIC28 [SA404]
MC68HC908JL3MP	MC68HC908JL3MPE
MC68HC908JL3VDW@SOIC28 [SA404]	MC68HC908JL3VDWE@SOIC28 [SA404]

MC68HC908JL3VP	MC68HC908JL3VPE
MC68HC908KK3ECDW@SOIC20 [SA404]	MC68HC908KK3ECDWE@SOIC20 [SA404]
MC68HC908KK3ECP	MC68HC908KK3ECPE
MC68HC908KK3EMDW@SOIC20 [SA404]	MC68HC908KK3EMDWE@SOIC20 [SA404]
MC68HC908KK3EMP	MC68HC908KK3EMPE
MC68HC908KK3EVDW@SOIC20 [SA404]	MC68HC908KK3EVDWE@SOIC20 [SA404]
MC68HC908KK3EVP	MC68HC908KK3EVPE
MC68HC908KL3ECDW@SOIC28 [SA404]	MC68HC908KL3ECDWE@SOIC28 [SA404]
MC68HC908KL3ECP	MC68HC908KL3ECPE
MC68HC908KL3EMDW@SOIC28 [SA404]	MC68HC908KL3EMDWE@SOIC28 [SA404]
MC68HC908KL3EMP	MC68HC908KL3EMPE
MC68HC908KL3EVDW@SOIC28 [SA404]	MC68HC908KL3EVDWE@SOIC28 [SA404]
MC68HC908KL3EVP	MC68HC908KL3EVPE
MC68HC908QT1ACDW@SOIC8 [SA605B]	
MC68HC908QT1ACDW@SOIC8 (a-trim) [SA605B]	
MC68HC908QT1ACDWE@SOIC8 [SA605B]	
MC68HC908QT1ACDWE@SOIC8 (a-trim) [SA605B]	
MC68HC908QT1ACP	MC68HC908QT1ACP (a-trim)
MC68HC908QT1ACPE	MC68HC908QT1ACPE (a-trim)
MC68HC908QT1AMDW@SOIC8 [SA605B]	
MC68HC908QT1AMDW@SOIC8 (a-trim) [SA605B]	
MC68HC908QT1AMDWE@SOIC8 [SA605B]	
MC68HC908QT1AMDWE@SOIC8 (a-trim) [SA605B]	
MC68HC908QT1AMP	MC68HC908QT1AMP (a-trim)
MC68HC908QT1AMPE	MC68HC908QT1AMPE (a-trim)
MC68HC908QT1AVDW@SOIC8 [SA605B]	
MC68HC908QT1AVDW@SOIC8 (a-trim) [SA605B]	
MC68HC908QT1AVDWE@SOIC8 [SA605B]	
MC68HC908QT1AVDWE@SOIC8 (a-trim) [SA605B]	
MC68HC908QT1AVP	MC68HC908QT1AVP (a-trim)
MC68HC908QT1AVPE	MC68HC908QT1AVPE (a-trim)
MC68HC908QT1CDW@SOIC8 [SA605B]	MC68HC908QT1CDWE@SOIC8 [SA605B]
MC68HC908QT1CP	MC68HC908QT1CPE
MC68HC908QT1MDW@SOIC8 [SA605B]	MC68HC908QT1MDWE@SOIC8 [SA605B]
MC68HC908QT1MP	MC68HC908QT1MPE
MC68HC908QT1VDW@SOIC8 [SA605B]	MC68HC908QT1VDWE@SOIC8 [SA605B]
MC68HC908QT1VP	MC68HC908QT1VPE
MC68HC908QT2ACDW@SOIC8 [SA605B]	
MC68HC908QT2ACDW@SOIC8 (a-trim) [SA605B]	
MC68HC908QT2ACDWE@SOIC8 [SA605B]	
MC68HC908QT2ACDWE@SOIC8 (a-trim) [SA605B]	
MC68HC908QT2ACP	MC68HC908QT2ACP (a-trim)
MC68HC908QT2ACPE	MC68HC908QT2ACPE (a-trim)
MC68HC908QT2AMDW@SOIC8 [SA605B]	
MC68HC908QT2AMDW@SOIC8 (a-trim) [SA605B]	
MC68HC908QT2AMDWE@SOIC8 [SA605B]	
MC68HC908QT2AMDWE@SOIC8 (a-trim) [SA605B]	
MC68HC908QT2AMP	MC68HC908QT2AMP (a-trim)
MC68HC908QT2AMPE	MC68HC908QT2AMPE (a-trim)
MC68HC908QT2AVDW@SOIC8 [SA605B]	
MC68HC908QT2AVDW@SOIC8 (a-trim) [SA605B]	
MC68HC908QT2AVDWE@SOIC8 [SA605B]	
MC68HC908QT2AVDWE@SOIC8 (a-trim) [SA605B]	

MC68HC908QT2AVP	MC68HC908QT2AVP (a-trim)
MC68HC908QT2AVPE	MC68HC908QT2AVPE (a-trim)
MC68HC908QT2CDW@SOIC8 [SA605B]	MC68HC908QT2CDWE@SOIC8 [SA605B]
MC68HC908QT2CP	MC68HC908QT2CPE
MC68HC908QT2MDW@SOIC8 [SA605B]	MC68HC908QT2MDWE@SOIC8 [SA605B]
MC68HC908QT2MP	MC68HC908QT2MPE
MC68HC908QT2VDW@SOIC8 [SA605B]	MC68HC908QT2VDWE@SOIC8 [SA605B]
MC68HC908QT2VP	MC68HC908QT2VPE
MC68HC908QT4ACDW@SOIC8 [SA605B]	
MC68HC908QT4ACDW@SOIC8 (a-trim) [SA605B]	
MC68HC908QT4ACDWE@SOIC8 [SA605B]	
MC68HC908QT4ACDWE@SOIC8 (a-trim) [SA605B]	
MC68HC908QT4ACP	MC68HC908QT4ACP (a-trim)
MC68HC908QT4ACPE	MC68HC908QT4ACPE (a-trim)
MC68HC908QT4AMDW@SOIC8 [SA605B]	
MC68HC908QT4AMDW@SOIC8 (a-trim) [SA605B]	
MC68HC908QT4AMDWE@SOIC8 [SA605B]	
MC68HC908QT4AMDWE@SOIC8 (a-trim) [SA605B]	
MC68HC908QT4AMP	MC68HC908QT4AMP (a-trim)
MC68HC908QT4AMPE	MC68HC908QT4AMPE (a-trim)
MC68HC908QT4AVDW@SOIC8 [SA605B]	
MC68HC908QT4AVDW@SOIC8 (a-trim) [SA605B]	
MC68HC908QT4AVDWE@SOIC8 [SA605B]	
MC68HC908QT4AVDWE@SOIC8 (a-trim) [SA605B]	
MC68HC908QT4AVP	MC68HC908QT4AVP (a-trim)
MC68HC908QT4AVPE	MC68HC908QT4AVPE (a-trim)
MC68HC908QT4CDW@SOIC8 [SA605B]	MC68HC908QT4CDWE@SOIC8 [SA605B]
MC68HC908QT4CP	MC68HC908QT4CPE
MC68HC908QT4MDW@SOIC8 [SA605B]	MC68HC908QT4MDWE@SOIC8 [SA605B]
MC68HC908QT4MP	MC68HC908QT4MPE
MC68HC908QT4VDW@SOIC8 [SA605B]	MC68HC908QT4VDWE@SOIC8 [SA605B]
MC68HC908QT4VP	MC68HC908QT4VPE
MC68HLC908JK1EIDW@SOIC20 [SA404]	
MC68HLC908JK1EIDWE@SOIC20 [SA404]	
MC68HLC908JK1EIP	MC68HLC908JK1EIPE
MC68HLC908JK3EIDW@SOIC20 [SA404]	
MC68HLC908JK3EIDWE@SOIC20 [SA404]	
MC68HLC908JK3EIP	MC68HLC908JK3EIPE
MC68HLC908JL3EIDW@SOIC28 [SA404]	
MC68HLC908JL3EIDWE@SOIC28 [SA404]	
MC68HLC908JL3EIP	MC68HLC908JL3EIPE
MC68HRC908JK1CDW@SOIC20 [SA404]	MC68HRC908JK1CDWE@SOIC20 [SA404]
MC68HRC908JK1CP	MC68HRC908JK1CPE
MC68HRC908JK1ECDW@SOIC20 [SA404]	
MC68HRC908JK1ECDWE@SOIC20 [SA404]	
MC68HRC908JK1ECP	MC68HRC908JK1ECPE
MC68HRC908JK1EMDW@SOIC20 [SA404]	
MC68HRC908JK1EMDWE@SOIC20 [SA404]	
MC68HRC908JK1EMP	MC68HRC908JK1EMPE
MC68HRC908JK1EVDW@SOIC20 [SA404]	
MC68HRC908JK1EVDWE@SOIC20 [SA404]	
MC68HRC908JK1EVP	MC68HRC908JK1EVPE
MC68HRC908JK1MDW@SOIC20 [SA404]	MC68HRC908JK1MDWE@SOIC20 [SA404]

MC68HRC908JK1MP	MC68HRC908JK1MPE
MC68HRC908JK1VDW@SOIC20 [SA404]	MC68HRC908JK1VDWE@SOIC20 [SA404]
MC68HRC908JK1VP	MC68HRC908JK1VPE
MC68HRC908JK3CDW@SOIC20 [SA404]	MC68HRC908JK3CDWE@SOIC20 [SA404]
MC68HRC908JK3CP	MC68HRC908JK3CPE
MC68HRC908JK3ECDW@SOIC20 [SA404]	
MC68HRC908JK3ECDWE@SOIC20 [SA404]	MC68HRC908JK3ECPE
MC68HRC908JK3ECP	
MC68HRC908JK3EMDW@SOIC20 [SA404]	
MC68HRC908JK3EMDWE@SOIC20 [SA404]	MC68HRC908JK3EMPE
MC68HRC908JK3EMP	
MC68HRC908JK3EVDW@SOIC20 [SA404]	
MC68HRC908JK3EVDWE@SOIC20 [SA404]	MC68HRC908JK3EVPE
MC68HRC908JK3EVP	MC68HRC908JK3MDWE@SOIC20 [SA404]
MC68HRC908JK3MDW@SOIC20 [SA404]	MC68HRC908JK3MPE
MC68HRC908JK3MP	MC68HRC908JK3VDWE@SOIC20 [SA404]
MC68HRC908JK3VDW@SOIC20 [SA404]	MC68HRC908JK3VPE
MC68HRC908JK3VP	MC68HRC908JL3CDWE@SOIC28 [SA404]
MC68HRC908JL3CDW@SOIC28 [SA404]	MC68HRC908JL3CPE
MC68HRC908JL3CP	
MC68HRC908JL3ECDW@SOIC28 [SA404]	MC68HRC908JL3ECPE
MC68HRC908JL3ECDWE@SOIC28 [SA404]	
MC68HRC908JL3ECP	
MC68HRC908JL3EMDW@SOIC28 [SA404]	MC68HRC908JL3EMPE
MC68HRC908JL3EMDWE@SOIC28 [SA404]	
MC68HRC908JL3EMP	
MC68HRC908JL3EVDW@SOIC28 [SA404]	MC68HRC908JL3EVPE
MC68HRC908JL3EVDWE@SOIC28 [SA404]	MC68HRC908JL3MDWE@SOIC28 [SA404]
MC68HRC908JL3EVP	MC68HRC908JL3MPE
MC68HRC908JL3MDW@SOIC28 [SA404]	MC68HRC908JL3VDWE@SOIC28 [SA404]
MC68HRC908JL3MP	MC68HRC908JL3VPE
MC68HRC908JL3VDW@SOIC28 [SA404]	MC9RS08KA4CPGE(auto trim)
MC68HRC908JL3VP	MC9RS08KA4CPJE(auto trim)
MC9RS08KA4CPG(auto trim)	
MC9RS08KA4CPJ(auto trim)	
MC9RS08KA4CTG@TSSOP16(auto trim) [SA643]	
MC9RS08KA4CTGE@TSSOP16(auto trim) [SA643]	
MC9RS08KA4CWG@SOIC16(auto trim) [SA404]	
MC9RS08KA4CWGE@SOIC16(auto trim) [SA404]	
MC9RS08KA4CWJ@SOIC20(auto trim) [SA404]	
MC9RS08KA4CWJE@SOIC20(auto trim) [SA404]	
MC9RS08KA4MPG(auto trim)	MC9RS08KA4MPGE(auto trim)
MC9RS08KA4MPJ(auto trim)	MC9RS08KA4MPJE(auto trim)
MC9RS08KA4MTG@TSSOP16(auto trim) [SA643]	
MC9RS08KA4MTGE@TSSOP16(a trim) [SA643]	
MC9RS08KA4MWG@SOIC16(auto trim) [SA404]	
MC9RS08KA4MWGE@SOIC16(auto trim) [SA404]	
MC9RS08KA4MWJ@SOIC20(auto trim) [SA404]	
MC9RS08KA4MWJE@SOIC20(auto trim) [SA404]	
MC9RS08KA4VPG(auto trim)	MC9RS08KA4VPGE(auto trim)
MC9RS08KA4VPJ(auto trim)	MC9RS08KA4VPJE(auto trim)
MC9RS08KA4VTG@TSSOP16(auto trim) [SA643]	
MC9RS08KA4VTGE@TSSOP16(auto trim) [SA643]	

MC9RS08KA4VWG@SOIC16(auto trim) [SA404]  
MC9RS08KA4VWGE@SOIC16(auto trim) [SA404]  
MC9RS08KA4VWJ@SOIC20(auto trim) [SA404]  
MC9RS08KA4VWJE@SOIC20(auto trim) [SA404]  
MC9RS08KA8CPG(auto trim) MC9RS08KA8CPGE(auto trim)  
MC9RS08KA8CPJ(auto trim) MC9RS08KA8CPJE(auto trim)  
MC9RS08KA8CTG@TSSOP16(auto trim) [SA643]  
MC9RS08KA8CTGE@TSSOP16(auto trim) [SA643]  
MC9RS08KA8CWG@SOIC16(auto trim) [SA404]  
MC9RS08KA8CWGE@SOIC16(auto trim) [SA404]  
MC9RS08KA8CWJ@SOIC20(auto trim) [SA404]  
MC9RS08KA8CWJE@SOIC20(auto trim) [SA404]  
MC9RS08KA8MPG(auto trim) MC9RS08KA8MPGE(auto trim)  
MC9RS08KA8MPJ(auto trim) MC9RS08KA8MPJE(auto trim)  
MC9RS08KA8MTG@TSSOP16(auto trim) [SA643]  
MC9RS08KA8MTGE@TSSOP16(a trim) [SA643]  
MC9RS08KA8MWG@SOIC16(auto trim) [SA404]  
MC9RS08KA8MWGE@SOIC16(auto trim) [SA404]  
MC9RS08KA8MWJ@SOIC20(auto trim) [SA404]  
MC9RS08KA8MWJE@SOIC20(auto trim) [SA404]  
MC9RS08KA8VPG(auto trim) MC9RS08KA8VPGE(auto trim)  
MC9RS08KA8VPJ(auto trim) MC9RS08KA8VPJE(auto trim)  
MC9RS08KA8VTG@TSSOP16(auto trim) [SA643]  
MC9RS08KA8VTGE@TSSOP16(a trim) [SA643]  
MC9RS08KA8VWG@SOIC16(auto trim) [SA404]  
MC9RS08KA8VWGE@SOIC16(auto trim) [SA404]  
MC9RS08KA8VWJ@SOIC20(auto trim) [SA404]  
MC9RS08KA8VWJE@SOIC20(auto trim) [SA404]  
MC9S08AC128CFG@QFP44 [SA245A-B4805]  
MC9S08AC128CFGE@QFP44 [SA245A-B4805]  
MC9S08AC128MFG@QFP44 [SA245A-B4805]  
MC9S08AC128MFGE@QFP44 [SA245A-B4805]  
MC9S08AC128VFG@QFP44 [SA245A-B4805]  
MC9S08AC128VFGE@QFP44 [SA245A-B4805]  
MC9S08AC16CFG@LQFP44 [SA245A-B4805]  
MC9S08AC16CFG@LQFP44(\*) [\$\$\$\$\$]  
MC9S08AC16CFGE@LQFP44 [SA245A-B4805]  
MC9S08AC16CFGE@LQFP44(\*) [\$\$\$\$\$]  
MC9S08AC16CFJ@QFP32 [SA636] MC9S08AC16CFJE@QFP32 [SA636]  
MC9S08AC16MFG@LQFP44 [SA245A-B4805]  
MC9S08AC16MFG@LQFP44(\*) [\$\$\$\$\$]  
MC9S08AC16MFGE@LQFP44 [SA245A-B4805]  
MC9S08AC16MFGE@LQFP44(\*) [\$\$\$\$\$]  
MC9S08AC16MFJ@QFP32 [SA636] MC9S08AC16MFJE@QFP32 [SA636]  
MC9S08AC16VFG@LQFP44 [SA245A-B4805]  
MC9S08AC16VFG@LQFP44(\*) [\$\$\$\$\$]  
MC9S08AC16VFGE@LQFP44 [SA245A-B4805]  
MC9S08AC16VFGE@LQFP44(\*) [\$\$\$\$\$]  
MC9S08AC16VFJ@QFP32 [SA636] MC9S08AC16VFJE@QFP32 [SA636]  
MC9S08AC32CFG@LQFP44 [SA245A-B4805]  
MC9S08AC32CFG@LQFP44(\*) [\$\$\$\$\$]  
MC9S08AC32CFGE@LQFP44 [SA245A-B4805]  
MC9S08AC32CFGE@LQFP44(\*) [\$\$\$\$\$]

MC9S08AC32CFJ@QFP32 [SA636] MC9S08AC32CFJE@QFP32 [SA636]  
MC9S08AC32MFG@LQFP44 (\*) [\$\$\$\$\$]  
MC9S08AC32MFG@LQFP44 [SA245A-B4805]  
MC9S08AC32MFG@LQFP44 (\*) [\$\$\$\$\$]  
MC9S08AC32MFJ@QFP32 [SA636] MC9S08AC32MFJE@QFP32 [SA636]  
MC9S08AC32VFG@LQFP44 [SA245A-B4805]  
MC9S08AC32VFG@LQFP44 (\*) [\$\$\$\$\$]  
MC9S08AC32VFG@LQFP44 [SA245A-B4805]  
MC9S08AC32VFG@LQFP44 (\*) [\$\$\$\$\$]  
MC9S08AC32VFJ@QFP32 [SA636] MC9S08AC32VFJE@QFP32 [SA636]  
MC9S08AC48CFG@LQFP44 [SA245A-B4805]  
MC9S08AC48CFG@LQFP44 (\*) [\$\$\$\$\$]  
MC9S08AC48CFG@LQFP44 [SA245A-B4805]  
MC9S08AC48CFG@LQFP44 (\*) [\$\$\$\$\$]  
MC9S08AC48CFJ@QFP32 [SA636] MC9S08AC48CFJE@QFP32 [SA636]  
MC9S08AC48MFG@LQFP44 [SA245A-B4805]  
MC9S08AC48MFG@LQFP44 (\*) [\$\$\$\$\$]  
MC9S08AC48MFG@LQFP44 [SA245A-B4805]  
MC9S08AC48MFG@LQFP44 (\*) [\$\$\$\$\$]  
MC9S08AC48MFJ@QFP32 [SA636] MC9S08AC48MFJE@QFP32 [SA636]  
MC9S08AC48VFG@LQFP44 [SA245A-B4805]  
MC9S08AC48VFG@LQFP44 (\*) [\$\$\$\$\$]  
MC9S08AC48VFG@LQFP44 [SA245A-B4805]  
MC9S08AC48VFG@LQFP44 (\*) [\$\$\$\$\$]  
MC9S08AC48VFJ@QFP32 [SA636] MC9S08AC48VFJE@QFP32 [SA636]  
MC9S08AC60CFG@LQFP44 [SA245A-B4805]  
MC9S08AC60CFG@LQFP44 (\*) [\$\$\$\$\$]  
MC9S08AC60CFG@LQFP44 [SA245A-B4805]  
MC9S08AC60CFG@LQFP44 (\*) [\$\$\$\$\$]  
MC9S08AC60CFJ@QFP32 [SA636] MC9S08AC60CFJE@QFP32 [SA636]  
MC9S08AC60MFG@LQFP44 [SA245A-B4805]  
MC9S08AC60MFG@LQFP44 (\*) [\$\$\$\$\$]  
MC9S08AC60MFG@LQFP44 [SA245A-B4805]  
MC9S08AC60MFG@LQFP44 (\*) [\$\$\$\$\$]  
MC9S08AC60MFJ@QFP32 [SA636] MC9S08AC60MFJE@QFP32 [SA636]  
MC9S08AC60VFG@LQFP44 [SA245A-B4805]  
MC9S08AC60VFG@LQFP44 (\*) [\$\$\$\$\$]  
MC9S08AC60VFG@LQFP44 [SA245A-B4805]  
MC9S08AC60VFG@LQFP44 (\*) [\$\$\$\$\$]  
MC9S08AC60VFJ@QFP32 [SA636] MC9S08AC60VFJE@QFP32 [SA636]  
MC9S08AC8CFG@LQFP44 [SA245A-B4805]  
MC9S08AC8CFG@LQFP44 (\*) [\$\$\$\$\$]  
MC9S08AC8CFG@LQFP44 [SA245A-B4805]  
MC9S08AC8CFG@LQFP44 (\*) [\$\$\$\$\$]  
MC9S08AC8CFJ@QFP32 [SA636] MC9S08AC8CFJE@QFP32 [SA636]  
MC9S08AC8CFJE@QFP32 [SA636]  
MC9S08AC8MFG@LQFP44 [SA245A-B4805]  
MC9S08AC8MFG@LQFP44 (\*) [\$\$\$\$\$]  
MC9S08AC8MFG@LQFP44 [SA245A-B4805]  
MC9S08AC8MFG@LQFP44 (\*) [\$\$\$\$\$]  
MC9S08AC8MFJ@QFP32 [SA636] MC9S08AC8MFJE@QFP32 [SA636]  
MC9S08AC8MFJE@QFP32 [SA636]  
MC9S08AC8VFG@LQFP44 [SA245A-B4805]  
MC9S08AC8VFG@LQFP44 (\*) [\$\$\$\$\$]  
MC9S08AC8VFG@LQFP44 [SA245A-B4805]

MC9S08AC8VFGE@LQFP44 (\*) [\$\$\$\$\$\$] MC9S08AC8VFJ@QFP32 [SA636]  
MC9S08AC8VFJE@QFP32 [SA636]  
MC9S08AC96CFG@QFP44 [SA245A-B4805]  
MC9S08AC96CFGE@QFP44 [SA245A-B4805]  
MC9S08AC96MFG@QFP44 [SA245A-B4805]  
MC9S08AC96MFGE@QFP44 [SA245A-B4805]  
MC9S08AC96VFG@QFP44 [SA245A-B4805]  
MC9S08AC96VFGE@QFP44 [SA245A-B4805]  
MC9S08AW16CFG@LQFP44 [SA245A-B4805]  
MC9S08AW16CFG@LQFP44 (\*) [\$\$\$\$\$\$]  
MC9S08AW16CFGE@LQFP44 [SA245A-B4805]  
MC9S08AW16CFGE@LQFP44 (\*) [\$\$\$\$\$\$]  
MC9S08AW16MFG@LQFP44 [SA245A-B4805]  
MC9S08AW16MFG@LQFP44 (\*) [\$\$\$\$\$\$]  
MC9S08AW16MFGE@LQFP44 [SA245A-B4805]  
MC9S08AW16MFGE@LQFP44 (\*) [\$\$\$\$\$\$]  
MC9S08AW16VFG@LQFP44 [SA245A-B4805]  
MC9S08AW16VFG@LQFP44 (\*) [\$\$\$\$\$\$]  
MC9S08AW16VFGE@LQFP44 [SA245A-B4805]  
MC9S08AW16VFGE@LQFP44 (\*) [\$\$\$\$\$\$]  
MC9S08AW32CFG@LQFP44 [SA245A-B4805]  
MC9S08AW32CFG@LQFP44 (\*) [\$\$\$\$\$\$]  
MC9S08AW32CFGE@LQFP44 [SA245A-B4805]  
MC9S08AW32CFGE@LQFP44 (\*) [\$\$\$\$\$\$]  
MC9S08AW32MFG@LQFP44 [SA245A-B4805]  
MC9S08AW32MFG@LQFP44 (\*) [\$\$\$\$\$\$]  
MC9S08AW32MFGE@LQFP44 [SA245A-B4805]  
MC9S08AW32MFGE@LQFP44 (\*) [\$\$\$\$\$\$]  
MC9S08AW32VFG@LQFP44 [SA245A-B4805]  
MC9S08AW32VFG@LQFP44 (\*) [\$\$\$\$\$\$]  
MC9S08AW32VFGE@LQFP44 [SA245A-B4805]  
MC9S08AW32VFGE@LQFP44 (\*) [\$\$\$\$\$\$]  
MC9S08AW48CFG@LQFP44 [SA245A-B4805]  
MC9S08AW48CFG@LQFP44 (\*) [\$\$\$\$\$\$]  
MC9S08AW48CFGE@LQFP44 [SA245A-B4805]  
MC9S08AW48CFGE@LQFP44 (\*) [\$\$\$\$\$\$]  
MC9S08AW48MFG@LQFP44 [SA245A-B4805]  
MC9S08AW48MFG@LQFP44 (\*) [\$\$\$\$\$\$]  
MC9S08AW48MFGE@LQFP44 [SA245A-B4805]  
MC9S08AW48MFGE@LQFP44 (\*) [\$\$\$\$\$\$]  
MC9S08AW48VFG@LQFP44 [SA245A-B4805]  
MC9S08AW48VFG@LQFP44 (\*) [\$\$\$\$\$\$]  
MC9S08AW48VFGE@LQFP44 [SA245A-B4805]  
MC9S08AW48VFGE@LQFP44 (\*) [\$\$\$\$\$\$]  
MC9S08AW60CFG@LQFP44 [SA245A-B4805]  
MC9S08AW60CFG@LQFP44 (\*) [\$\$\$\$\$\$]  
MC9S08AW60CFGE@LQFP44 [SA245A-B4805]  
MC9S08AW60CFGE@LQFP44 (\*) [\$\$\$\$\$\$]  
MC9S08AW60MFG@LQFP44 [SA245A-B4805]  
MC9S08AW60MFG@LQFP44 (\*) [\$\$\$\$\$\$]  
MC9S08AW60MFGE@LQFP44 [SA245A-B4805]  
MC9S08AW60MFGE@LQFP44 (\*) [\$\$\$\$\$\$]  
MC9S08AW60VFG@LQFP44 [SA245A-B4805]

MC9S08AW60VFG@LQFP44(\*) [\$\$\$\$\$]  
MC9S08AW60VFGE@LQFP44 [SA245A-B4805]  
MC9S08AW60VFGE@LQFP44(\*) [\$\$\$\$\$]  
MC9S08DN16CLC@QFP32 [SA636] MC9S08DN16CLCE@QFP32 [SA636]  
MC9S08DN16CLF@QFP48 [SA248-B4804]  
MC9S08DN16CLFE@QFP48 [SA248-B4804]  
MC9S08DN16MLC@QFP32 [SA636] MC9S08DN16MLCE@QFP32 [SA636]  
MC9S08DN16MLF@QFP48 [SA248-B4804]  
MC9S08DN16MLFE@QFP48 [SA248-B4804]  
MC9S08DN16VLC@QFP32 [SA636] MC9S08DN16VLCE@QFP32 [SA636]  
MC9S08DN16VLF@QFP48 [SA248-B4804]  
MC9S08DN16VLFE@QFP48 [SA248-B4804]  
MC9S08DN32CLC@QFP32 [SA636] MC9S08DN32CLCE@QFP32 [SA636]  
MC9S08DN32CLF@QFP48 [SA248-B4804]  
MC9S08DN32CLFE@QFP48 [SA248-B4804]  
MC9S08DN32MLC@QFP32 [SA636] MC9S08DN32MLCE@QFP32 [SA636]  
MC9S08DN32MLF@QFP48 [SA248-B4804]  
MC9S08DN32MLFE@QFP48 [SA248-B4804]  
MC9S08DN32VLC@QFP32 [SA636] MC9S08DN32VLCE@QFP32 [SA636]  
MC9S08DN32VLF@QFP48 [SA248-B4804]  
MC9S08DN32VLFE@QFP48 [SA248-B4804]  
MC9S08DN48CLC@QFP32 [SA636] MC9S08DN48CLCE@QFP32 [SA636]  
MC9S08DN48CLF@QFP48 [SA248-B4804]  
MC9S08DN48CLFE@QFP48 [SA248-B4804]  
MC9S08DN48MLC@QFP32 [SA636] MC9S08DN48MLCE@QFP32 [SA636]  
MC9S08DN48MLF@QFP48 [SA248-B4804]  
MC9S08DN48MLFE@QFP48 [SA248-B4804]  
MC9S08DN48VLC@QFP32 [SA636] MC9S08DN48VLCE@QFP32 [SA636]  
MC9S08DN48VLF@QFP48 [SA248-B4804]  
MC9S08DN48VLFE@QFP48 [SA248-B4804]  
MC9S08DN60CLC@QFP32 [SA636] MC9S08DN60CLCE@QFP32 [SA636]  
MC9S08DN60CLF@QFP48 [SA248-B4804]  
MC9S08DN60CLFE@QFP48 [SA248-B4804]  
MC9S08DN60MLC@QFP32 [SA636] MC9S08DN60MLCE@QFP32 [SA636]  
MC9S08DN60MLF@QFP48 [SA248-B4804]  
MC9S08DN60MLFE@QFP48 [SA248-B4804]  
MC9S08DN60VLC@QFP32 [SA636] MC9S08DN60VLCE@QFP32 [SA636]  
MC9S08DN60VLF@QFP48 [SA248-B4804]  
MC9S08DN60VLFE@QFP48 [SA248-B4804]  
MC9S08DV128CLF@QFP48 [SA248-B4804]  
MC9S08DV128CLFE@QFP48 [SA248-B4804]  
MC9S08DV128MLF@QFP48 [SA248-B4804]  
MC9S08DV128MLFE@QFP48 [SA248-B4804]  
MC9S08DV128VLF@QFP48 [SA248-B4804]  
MC9S08DV128VLFE@QFP48 [SA248-B4804]  
MC9S08DV16CLC@QFP32 [SA636] MC9S08DV16CLCE@QFP32 [SA636]  
MC9S08DV16CLF@QFP48 [SA248-B4804]  
MC9S08DV16CLFE@QFP48 [SA248-B4804]  
MC9S08DV16MLC@QFP32 [SA636] MC9S08DV16MLCE@QFP32 [SA636]  
MC9S08DV16MLF@QFP48 [SA248-B4804]  
MC9S08DV16MLFE@QFP48 [SA248-B4804]  
MC9S08DV16VLC@QFP32 [SA636] MC9S08DV16VLCE@QFP32 [SA636]  
MC9S08DV32CLC@QFP32 [SA636] MC9S08DV32CLCE@QFP32 [SA636]

MC9S08DV32CLF@QFP48 [SA248-B4804]  
MC9S08DV32CLFE@QFP48 [SA248-B4804]  
MC9S08DV32MLC@QFP32 [SA636] MC9S08DV32MLCE@QFP32 [SA636]  
MC9S08DV32MLF@QFP48 [SA248-B4804]  
MC9S08DV32MLFE@QFP48 [SA248-B4804]  
MC9S08DV32VLC@QFP32 [SA636] MC9S08DV32VLCE@QFP32 [SA636]  
MC9S08DV32VLF@QFP48 [SA248-B4804]  
MC9S08DV32VLFE@QFP48 [SA248-B4804]  
MC9S08DV48CLC@QFP32 [SA636] MC9S08DV48CLCE@QFP32 [SA636]  
MC9S08DV48CLF@QFP48 [SA248-B4804]  
MC9S08DV48CLFE@QFP48 [SA248-B4804]  
MC9S08DV48MLC@QFP32 [SA636] MC9S08DV48MLCE@QFP32 [SA636]  
MC9S08DV48MLF@QFP48 [SA248-B4804]  
MC9S08DV48MLFE@QFP48 [SA248-B4804]  
MC9S08DV48VLC@QFP32 [SA636] MC9S08DV48VLCE@QFP32 [SA636]  
MC9S08DV48VLF@QFP48 [SA248-B4804]  
MC9S08DV48VLFE@QFP48 [SA248-B4804]  
MC9S08DV60CLC@QFP32 [SA636] MC9S08DV60CLCE@QFP32 [SA636]  
MC9S08DV60CLF@QFP48 [SA248-B4804]  
MC9S08DV60CLFE@QFP48 [SA248-B4804]  
MC9S08DV60MLC@QFP32 [SA636] MC9S08DV60MLCE@QFP32 [SA636]  
MC9S08DV60MLF@QFP48 [SA248-B4804]  
MC9S08DV60MLFE@QFP48 [SA248-B4804]  
MC9S08DV60VLC@QFP32 [SA636] MC9S08DV60VLCE@QFP32 [SA636]  
MC9S08DV60VLF@QFP48 [SA248-B4804]  
MC9S08DV60VLFE@QFP48 [SA248-B4804]  
MC9S08DV96CLF@QFP48 [SA248-B4804]  
MC9S08DV96CLFE@QFP48 [SA248-B4804]  
MC9S08DV96MLF@QFP48 [SA248-B4804]  
MC9S08DV96MLFE@QFP48 [SA248-B4804]  
MC9S08DV96VLF@QFP48 [SA248-B4804]  
MC9S08DV96VLFE@QFP48 [SA248-B4804]  
MC9S08DZ128CLF@QFP48 [SA248-B4804]  
MC9S08DZ128CLFE@QFP48 [SA248-B4804]  
MC9S08DZ128MLF@QFP48 [SA248-B4804]  
MC9S08DZ128MLFE@QFP48 [SA248-B4804]  
MC9S08DZ128VLF@QFP48 [SA248-B4804]  
MC9S08DZ128VLFE@QFP48 [SA248-B4804]  
MC9S08DZ16CLC@QFP32 [SA636] MC9S08DZ16CLCE@QFP32 [SA636]  
MC9S08DZ16CLF@QFP48 [SA248-B4804]  
MC9S08DZ16CLFE@QFP48 [SA248-B4804]  
MC9S08DZ16MLC@QFP32 [SA636] MC9S08DZ16MLCE@QFP32 [SA636]  
MC9S08DZ16MLF@QFP48 [SA248-B4804]  
MC9S08DZ16MLFE@QFP48 [SA248-B4804]  
MC9S08DZ16VLC@QFP32 [SA636] MC9S08DZ16VLCE@QFP32 [SA636]  
MC9S08DZ16VLF@QFP48 [SA248-B4804]  
MC9S08DZ16VLFE@QFP48 [SA248-B4804]  
MC9S08DZ32CLC@QFP32 [SA636] MC9S08DZ32CLCE@QFP32 [SA636]  
MC9S08DZ32CLF@QFP48 [SA248-B4804]  
MC9S08DZ32CLFE@QFP48 [SA248-B4804]  
MC9S08DZ32MLC@QFP32 [SA636] MC9S08DZ32MLCE@QFP32 [SA636]  
MC9S08DZ32MLF@QFP48 [SA248-B4804]  
MC9S08DZ32MLFE@QFP48 [SA248-B4804]

MC9S08DZ32VLC@QFP32 [SA636] MC9S08DZ32VLCE@QFP32 [SA636]  
MC9S08DZ32VLF@QFP48 [SA248-B4804]  
MC9S08DZ32VLFE@QFP48 [SA248-B4804]  
MC9S08DZ48CLC@QFP32 [SA636] MC9S08DZ48CLCE@QFP32 [SA636]  
MC9S08DZ48CLF@QFP48 [SA248-B4804]  
MC9S08DZ48CLFE@QFP48 [SA248-B4804]  
MC9S08DZ48MLC@QFP32 [SA636] MC9S08DZ48MLCE@QFP32 [SA636]  
MC9S08DZ48MLF@QFP48 [SA248-B4804]  
MC9S08DZ48MLFE@QFP48 [SA248-B4804]  
MC9S08DZ48VLC@QFP32 [SA636] MC9S08DZ48VLCE@QFP32 [SA636]  
MC9S08DZ48VLF@QFP48 [SA248-B4804]  
MC9S08DZ48VLFE@QFP48 [SA248-B4804]  
MC9S08DZ60CLC@QFP32 [SA636] MC9S08DZ60CLCE@QFP32 [SA636]  
MC9S08DZ60CLF@QFP48 [SA248-B4804]  
MC9S08DZ60CLFE@QFP48 [SA248-B4804]  
MC9S08DZ60MLC@QFP32 [SA636] MC9S08DZ60MLCE@QFP32 [SA636]  
MC9S08DZ60MLF@QFP48 [SA248-B4804]  
MC9S08DZ60MLFE@QFP48 [SA248-B4804]  
MC9S08DZ60VLC@QFP32 [SA636] MC9S08DZ60VLCE@QFP32 [SA636]  
MC9S08DZ60VLF@QFP48 [SA248-B4804]  
MC9S08DZ60VLFE@QFP48 [SA248-B4804]  
MC9S08DZ96CLF@QFP48 [SA248-B4804]  
MC9S08DZ96CLFE@QFP48 [SA248-B4804]  
MC9S08DZ96MLF@QFP48 [SA248-B4804]  
MC9S08DZ96MLFE@QFP48 [SA248-B4804]  
MC9S08DZ96VLF@QFP48 [SA248-B4804]  
MC9S08DZ96VLFE@QFP48 [SA248-B4804]  
MC9S08EL16CTJ@TSSOP20 [SA026] MC9S08EL16CTJE@TSSOP20 [SA026]  
MC9S08EL16CTL@TSSOP28 [SA643] MC9S08EL16CTLE@TSSOP28 [SA643]  
MC9S08EL16MTJ@TSSOP20 [SA026] MC9S08EL16MTJE@TSSOP20 [SA026]  
MC9S08EL16MTL@TSSOP28 [SA643] MC9S08EL16MTLE@TSSOP28 [SA643]  
MC9S08EL16VTJ@TSSOP20 [SA026] MC9S08EL16VTJE@TSSOP20 [SA026]  
MC9S08EL16VTL@TSSOP28 [SA643] MC9S08EL16VTLE@TSSOP28 [SA643]  
MC9S08EL32CTJ@TSSOP20 [SA026] MC9S08EL32CTJE@TSSOP20 [SA026]  
MC9S08EL32CTL@TSSOP28 [SA643] MC9S08EL32CTLE@TSSOP28 [SA643]  
MC9S08EL32MTJ@TSSOP20 [SA026] MC9S08EL32MTJE@TSSOP20 [SA026]  
MC9S08EL32MTL@TSSOP28 [SA643] MC9S08EL32MTLE@TSSOP28 [SA643]  
MC9S08EL32VTJ@TSSOP20 [SA026] MC9S08EL32VTJE@TSSOP20 [SA026]  
MC9S08EL32VTL@TSSOP28 [SA643] MC9S08EL32VTLE@TSSOP28 [SA643]  
MC9S08FL16CBM@SDIP32 [SA653]  
MC9S08FL16CBM@SDIP32(auto trim) [SA653]  
MC9S08FL16CLC@LQFP32 [SA636]  
MC9S08FL16CLC@LQFP32(auto trim) [SA636]  
MC9S08FL16MBM@SDIP32 [SA653]  
MC9S08FL16MBM@SDIP32(auto trim) [SA653]  
MC9S08FL16MLC@LQFP32 [SA636]  
MC9S08FL16MLC@LQFP32(auto trim) [SA636]  
MC9S08FL16VBM@SDIP32 [SA653]  
MC9S08FL16VBM@SDIP32(auto trim) [SA653]  
MC9S08FL16VLC@LQFP32 [SA636]  
MC9S08FL16VLC@LQFP32(auto trim) [SA636]  
MC9S08FL8CBM@SDIP32 [SA653]  
MC9S08FL8CBM@SDIP32(auto trim) [SA653]

MC9S08FL8CLC@LQFP32 [SA636]  
MC9S08FL8CLC@LQFP32(auto trim) [SA636]  
MC9S08FL8MBM@SDIP32 [SA653]  
MC9S08FL8MBM@SDIP32(auto trim) [SA653]  
MC9S08FL8MLC@LQFP32 [SA636]  
MC9S08FL8MLC@LQFP32(auto trim) [SA636]  
MC9S08FL8VBM@SDIP32 [SA653]  
MC9S08FL8VBM@SDIP32(auto trim) [SA653]  
MC9S08FL8VLC@LQFP32 [SA636]  
MC9S08FL8VLC@LQFP32(auto trim) [SA636]  
MC9S08GT16ACB@SDIP42 [SA028] MC9S08GT16ACBE@SDIP42 [SA028]  
MC9S08GT16ACFB@LQFP44 [SA675-B4805]  
MC9S08GT16ACFBE@LQFP44 [SA675-B4805]  
MC9S08GT16AMB@SDIP42 [SA028] MC9S08GT16AMBE@SDIP42 [SA028]  
MC9S08GT16AMFB@LQFP44 [SA675-B4805]  
MC9S08GT16AMFBE@LQFP44 [SA675-B4805]  
MC9S08GT16AVB@SDIP42 [SA028] MC9S08GT16AVBE@SDIP42 [SA028]  
MC9S08GT16AVFB@LQFP44 [SA675-B4805]  
MC9S08GT16AVFBE@LQFP44 [SA675-B4805]  
MC9S08GT16CB@SDIP42 [SA028] MC9S08GT16CBE@SDIP42 [SA028]  
MC9S08GT16CFB@LQFP44 [SA675-B4805]  
MC9S08GT16CFBE@LQFP44 [SA675-B4805]  
MC9S08GT16MB@SDIP42 [SA028] MC9S08GT16MBE@SDIP42 [SA028]  
MC9S08GT16MFB@LQFP44 [SA675-B4805]  
MC9S08GT16MFBE@LQFP44 [SA675-B4805]  
MC9S08GT16VB@SDIP42 [SA028] MC9S08GT16VBE@SDIP42 [SA028]  
MC9S08GT16VFB@LQFP44 [SA675-B4805]  
MC9S08GT16VFBE@LQFP44 [SA675-B4805]  
MC9S08GT32ACB@SDIP42 [SA028] MC9S08GT32ACBE@SDIP42 [SA028]  
MC9S08GT32ACFB@LQFP44 [SA675-B4805]  
MC9S08GT32ACFBE@LQFP44 [SA675-B4805]  
MC9S08GT32AMB@SDIP42 [SA028] MC9S08GT32AMBE@SDIP42 [SA028]  
MC9S08GT32AMFB@LQFP44 [SA675-B4805]  
MC9S08GT32AMFBE@LQFP44 [SA675-B4805]  
MC9S08GT32AVB@SDIP42 [SA028] MC9S08GT32AVBE@SDIP42 [SA028]  
MC9S08GT32AVFB@LQFP44 [SA675-B4805]  
MC9S08GT32AVFBE@LQFP44 [SA675-B4805]  
MC9S08GT32CB@SDIP42 [SA028] MC9S08GT32CBE@SDIP42 [SA028]  
MC9S08GT32CFB@LQFP44 [SA675-B4805]  
MC9S08GT32CFBE@LQFP44 [SA675-B4805]  
MC9S08GT32MB@SDIP42 [SA028] MC9S08GT32MBE@SDIP42 [SA028]  
MC9S08GT32MFB@LQFP44 [SA675-B4805]  
MC9S08GT32MFBE@LQFP44 [SA675-B4805]  
MC9S08GT32VB@SDIP42 [SA028] MC9S08GT32VBE@SDIP42 [SA028]  
MC9S08GT32VFB@LQFP44 [SA675-B4805]  
MC9S08GT32VFBE@LQFP44 [SA675-B4805]  
MC9S08GT60ACB@SDIP42 [SA028] MC9S08GT60ACBE@SDIP42 [SA028]  
MC9S08GT60ACFB@LQFP44 [SA675-B4805]  
MC9S08GT60ACFBE@LQFP44 [SA675-B4805]  
MC9S08GT60AMB@SDIP42 [SA028] MC9S08GT60AMBE@SDIP42 [SA028]  
MC9S08GT60AMFB@LQFP44 [SA675-B4805]  
MC9S08GT60AMFBE@LQFP44 [SA675-B4805]  
MC9S08GT60AVB@SDIP42 [SA028] MC9S08GT60AVBE@SDIP42 [SA028]

MC9S08GT60AVFB@LQFP44 [SA675-B4805]  
MC9S08GT60AVFBE@LQFP44 [SA675-B4805]  
MC9S08GT60CB@SDIP42 [SA028] MC9S08GT60CBE@SDIP42 [SA028]  
MC9S08GT60CFB@LQFP44 [SA675-B4805]  
MC9S08GT60CFBE@LQFP44 [SA675-B4805]  
MC9S08GT60MB@SDIP42 [SA028] MC9S08GT60MBE@SDIP42 [SA028]  
MC9S08GT60MFB@LQFP44 [SA675-B4805]  
MC9S08GT60MFBE@LQFP44 [SA675-B4805]  
MC9S08GT60VB@SDIP42 [SA028] MC9S08GT60VBE@SDIP42 [SA028]  
MC9S08GT60VFB@LQFP44 [SA675-B4805]  
MC9S08GT60VFBE@LQFP44 [SA675-B4805]  
MC9S08GT8ACB@SDIP42 [SA028] MC9S08GT8ACBE@SDIP42 [SA028]  
MC9S08GT8ACFB@LQFP44 [SA675-B4805]  
MC9S08GT8ACFBE@LQFP44 [SA675-B4805]  
MC9S08GT8AMB@SDIP42 [SA028] MC9S08GT8AMBE@SDIP42 [SA028]  
MC9S08GT8AMFB@LQFP44 [SA675-B4805]  
MC9S08GT8AMFBE@LQFP44 [SA675-B4805]  
MC9S08GT8AVB@SDIP42 [SA028] MC9S08GT8AVBE@SDIP42 [SA028]  
MC9S08GT8AVFB@LQFP44 [SA675-B4805]  
MC9S08GT8AVFBE@LQFP44 [SA675-B4805]  
MC9S08JM16CLC@QFP32 [SA636] MC9S08JM16CLCE@QFP32 [SA636]  
MC9S08JM16CLD@QFP44 [SA245A-B4805]  
MC9S08JM16CLDE@QFP44 [SA245A-B4805]  
MC9S08JM16MLC@QFP32 [SA636] MC9S08JM16MLCE@QFP32 [SA636]  
MC9S08JM16MLD@QFP44 [SA245A-B4805]  
MC9S08JM16MLDE@QFP44 [SA245A-B4805]  
MC9S08JM16VLC@QFP32 [SA636] MC9S08JM16VLCE@QFP32 [SA636]  
MC9S08JM16VLD@QFP44 [SA245A-B4805]  
MC9S08JM16VLDE@QFP44 [SA245A-B4805]  
MC9S08JM32CLD@QFP44 [SA245A-B4805]  
MC9S08JM32CLDE@QFP44 [SA245A-B4805]  
MC9S08JM32MLD@QFP44 [SA245A-B4805]  
MC9S08JM32MLDE@QFP44 [SA245A-B4805]  
MC9S08JM32VLD@QFP44 [SA245A-B4805]  
MC9S08JM32VLDE@QFP44 [SA245A-B4805]  
MC9S08JM60CLD@QFP44 [SA245A-B4805]  
MC9S08JM60CLDE@QFP44 [SA245A-B4805]  
MC9S08JM60MLD@QFP44 [SA245A-B4805]  
MC9S08JM60MLDE@QFP44 [SA245A-B4805]  
MC9S08JM60VLD@QFP44 [SA245A-B4805]  
MC9S08JM60VLDE@QFP44 [SA245A-B4805]  
MC9S08JM8CLC@QFP32 [SA636] MC9S08JM8CLCE@QFP32 [SA636]  
MC9S08JM8CLD@QFP44 [SA245A-B4805]  
MC9S08JM8CLDE@QFP44 [SA245A-B4805]  
MC9S08JM8MLC@QFP32 [SA636] MC9S08JM8MLCE@QFP32 [SA636]  
MC9S08JM8MLD@QFP44 [SA245A-B4805]  
MC9S08JM8MLDE@QFP44 [SA245A-B4805]  
MC9S08JM8VLC@QFP32 [SA636] MC9S08JM8VLCE@QFP32 [SA636]  
MC9S08JM8VLD@QFP44 [SA245A-B4805]  
MC9S08JM8VLDE@QFP44 [SA245A-B4805]  
MC9S08JS16CWJ@SOIC20 [SA404] MC9S08JS16LCWJ@SOIC20 [SA404]  
MC9S08JS16LMWJ@SOIC20 [SA404] MC9S08JS16LVWJ@SOIC20 [SA404]  
MC9S08JS16MWJ@SOIC20 [SA404] MC9S08JS16VWJ@SOIC20 [SA404]

MC9S08JS8CWJ@SOIC20 [SA404]                    MC9S08JS8LCWJ@SOIC20 [SA404]  
MC9S08JS8LMWJ@SOIC20 [SA404]                    MC9S08JS8LVWJ@SOIC20 [SA404]  
MC9S08JS8MWJ@SOIC20 [SA404]                    MC9S08JS8VWJ@SOIC20 [SA404]  
MC9S08LG16CLF@QFP48 [SA248-B4804]  
MC9S08LG16CLF@QFP48(auto trim) [SA248-B4804]  
MC9S08LG16CLFE@QFP48 [SA248-B4804]  
MC9S08LG16CLFE@QFP48(auto trim) [SA248-B4804]  
MC9S08LG16MLF@QFP48 [SA248-B4804]  
MC9S08LG16MLF@QFP48(auto trim) [SA248-B4804]  
MC9S08LG16MLFE@QFP48 [SA248-B4804]  
MC9S08LG16MLFE@QFP48(auto trim) [SA248-B4804]  
MC9S08LG16VLF@QFP48 [SA248-B4804]  
MC9S08LG16VLF@QFP48(auto trim) [SA248-B4804]  
MC9S08LG16VLFE@QFP48 [SA248-B4804]  
MC9S08LG16VLFE@QFP48(auto trim) [SA248-B4804]  
MC9S08LG32CLF@QFP48 [SA248-B4804]  
MC9S08LG32CLF@QFP48(auto trim) [SA248-B4804]  
MC9S08LG32CLFE@QFP48 [SA248-B4804]  
MC9S08LG32CLFE@QFP48(auto trim) [SA248-B4804]  
MC9S08LG32MLF@QFP48 [SA248-B4804]  
MC9S08LG32MLF@QFP48(auto trim) [SA248-B4804]  
MC9S08LG32MLFE@QFP48 [SA248-B4804]  
MC9S08LG32MLFE@QFP48(auto trim) [SA248-B4804]  
MC9S08LG32VLF@QFP48 [SA248-B4804]  
MC9S08LG32VLF@QFP48(auto trim) [SA248-B4804]  
MC9S08LG32VLFE@QFP48 [SA248-B4804]  
MC9S08LG32VLFE@QFP48(auto trim) [SA248-B4804]  
MC9S08LL16CLF@LQFP48 [SA248-B4804]  
MC9S08LL16CLF@LQFP48(auto trim) [SA248-B4804]  
MC9S08LL16MLF@LQFP48 [SA248-B4804]  
MC9S08LL16MLF@LQFP48(auto trim) [SA248-B4804]  
MC9S08LL16VLF@LQFP48 [SA248-B4804]  
MC9S08LL16VLF@LQFP48(auto trim) [SA248-B4804]  
MC9S08LL8CLF@LQFP48 [SA248-B4804]  
MC9S08LL8CLF@LQFP48(auto trim) [SA248-B4804]  
MC9S08LL8VLF@LQFP48 [SA248-B4804]  
MC9S08LL8VLF@LQFP48(auto trim) [SA248-B4804]  
MC9S08MP12CLC@QFP32 [SA636]  
MC9S08MP12CLF@QFP48 [SA248-B4804]  
MC9S08MP12CWL@SOIC28 [SA404]                    MC9S08MP12MLC@QFP32 [SA636]  
MC9S08MP12MLF@QFP48 [SA248-B4804]  
MC9S08MP12MWL@SOIC28 [SA404]                    MC9S08MP12VLC@QFP32 [SA636]  
MC9S08MP12VLF@QFP48 [SA248-B4804]  
MC9S08MP12VWL@SOIC28 [SA404]                    MC9S08MP16CLC@QFP32 [SA636]  
MC9S08MP16CLF@QFP48 [SA248-B4804]  
MC9S08MP16CWL@SOIC28 [SA404]                    MC9S08MP16MLC@QFP32 [SA636]  
MC9S08MP16MLF@QFP48 [SA248-B4804]  
MC9S08MP16MWL@SOIC28 [SA404]                    MC9S08MP16VLC@QFP32 [SA636]  
MC9S08MP16VLF@QFP48 [SA248-B4804]  
MC9S08MP16VWL@SOIC28 [SA404]                    MC9S08QA2CDN@SOIC8 [SA602]  
MC9S08QA2CDNE@SOIC8 [SA602]                    MC9S08QA2CPA  
MC9S08QA2CPAE                                    MC9S08QA2MDN@SOIC8 [SA602]  
MC9S08QA2MDNE@SOIC8 [SA602]                    MC9S08QA2MPA

MC9S08QA2MPAE  
MC9S08QA2VDNE@SOIC8 [SA602]  
MC9S08QA2VPAE  
MC9S08QA4CDNE@SOIC8 [SA602]  
MC9S08QA4CPAE  
MC9S08QA4MDNE@SOIC8 [SA602]  
MC9S08QA4MPAE  
MC9S08QA4VDNE@SOIC8 [SA602]  
MC9S08QA4VPAE  
MC9S08QB4CWL@SOIC28 [SA404]  
MC9S08QB4MWL@SOIC28 [SA404]  
MC9S08QB4VWL@SOIC28 [SA404]  
MC9S08QB8CWL@SOIC28 [SA404]  
MC9S08QB8MWL@SOIC28 [SA404]  
MC9S08QB8VWL@SOIC28 [SA404]  
MC9S08QD2CPC(auto trim)  
MC9S08QD2CPCE(auto trim)  
MC9S08QD2CSC@SOIC8(auto trim) [SA602]  
MC9S08QD2CSCE@SOIC8 [SA602]  
MC9S08QD2CSCE@SOIC8(auto trim) [SA602]  
MC9S08QD2MPC  
MC9S08QD2MPCE  
MC9S08QD2MSC@SOIC8 [SA602]  
MC9S08QD2MSC@SOIC8(auto trim) [SA602]  
MC9S08QD2MSCE@SOIC8 [SA602]  
MC9S08QD2MSCE@SOIC8(auto trim) [SA602]  
MC9S08QD2VPC  
MC9S08QD2VPCE  
MC9S08QD2VSC@SOIC8 [SA602]  
MC9S08QD2VSC@SOIC8(auto trim) [SA602]  
MC9S08QD2VSCE@SOIC8 [SA602]  
MC9S08QD2VSCE@SOIC8(auto trim) [SA602]  
MC9S08QD4CPC  
MC9S08QD4CPCE  
MC9S08QD4CSC@SOIC8 [SA602]  
MC9S08QD4CSC@SOIC8(auto trim) [SA602]  
MC9S08QD4CSCE@SOIC8 [SA602]  
MC9S08QD4CSCE@SOIC8(auto trim) [SA602]  
MC9S08QD4MPC  
MC9S08QD4MPCE  
MC9S08QD4MSC@SOIC8 [SA602]  
MC9S08QD4MSC@SOIC8(auto trim) [SA602]  
MC9S08QD4MSCE@SOIC8 [SA602]  
MC9S08QD4MSCE@SOIC8(auto trim) [SA602]  
MC9S08QD4VPC  
MC9S08QD4VPCE  
MC9S08QD4VSC@SOIC8 [SA602]  
MC9S08QD4VSC@SOIC8(auto trim) [SA602]  
MC9S08QD4VSCE@SOIC8 [SA602]  
MC9S08QD4VSCE@SOIC8(auto trim) [SA602]  
MC9S08QE128CLC@QFP32 [SA636]  
MC9S08QE128CLD@QFP44 [SA245A-B4805]  
MC9S08QE128CLDE@QFP44 [SA245A-B4805]  
MC9S08QA2VDN@SOIC8 [SA602]  
MC9S08QA2VPA  
MC9S08QA4CDN@SOIC8 [SA602]  
MC9S08QA4CPA  
MC9S08QA4MDN@SOIC8 [SA602]  
MC9S08QA4MPA  
MC9S08QA4VDN@SOIC8 [SA602]  
MC9S08QA4VPA  
MC9S08QB4CTG@TSSOP16 [SA643]  
MC9S08QB4MTG@TSSOP16 [SA643]  
MC9S08QB4VTG@TSSOP16 [SA643]  
MC9S08QB8CTG@TSSOP16 [SA643]  
MC9S08QB8MTG@TSSOP16 [SA643]  
MC9S08QB8VTG@TSSOP16 [SA643]  
MC9S08QD2CPC  
MC9S08QD2CPCE  
MC9S08QD2CSC@SOIC8 [SA602]  
MC9S08QD2MPC(auto trim)  
MC9S08QD2MPCE(auto trim)  
MC9S08QD2VPC(auto trim)  
MC9S08QD2VPCE(auto trim)  
MC9S08QD4CPC(auto trim)  
MC9S08QD4CPCE(auto trim)  
MC9S08QD4MPC(auto trim)  
MC9S08QD4MPCE(auto trim)  
MC9S08QD4VPC(auto trim)  
MC9S08QD4VPCE(auto trim)  
MC9S08QE128CLCE@QFP32 [SA636]

MC9S08QE128MLC@QFP32 [SA636] MC9S08QE128MLCE@QFP32 [SA636]  
MC9S08QE128MLD@QFP44 [SA245A-B4805]  
MC9S08QE128MLDE@QFP44 [SA245A-B4805]  
MC9S08QE128VLC@QFP32 [SA636] MC9S08QE128VLCE@QFP32 [SA636]  
MC9S08QE128VLD@QFP44 [SA245A-B4805]  
MC9S08QE128VLDE@QFP44 [SA245A-B4805]  
MC9S08QE16CLC@QFP32 [SA636]  
MC9S08QE16CLC@QFP32(auto trim) [SA636]  
MC9S08QE16CLCE@QFP32 [SA636]  
MC9S08QE16CLCE@QFP32(auto trim) [SA636]  
MC9S08QE16CLD@QFP44 [SA245A-B4805]  
MC9S08QE16CLD@QFP44(auto trim) [SA245A-B4805]  
MC9S08QE16CLDE@QFP44 [SA245A-B4805]  
MC9S08QE16CLDE@QFP44(auto trim) [SA245A-B4805]  
MC9S08QE16CWL@SOIC28 [SA404]  
MC9S08QE16CWL@SOIC28(auto trim) [SA404]  
MC9S08QE16CWLE@SOIC28 [SA404]  
MC9S08QE16CWLE@SOIC28(auto trim) [SA404]  
MC9S08QE16MLC@QFP32 [SA636]  
MC9S08QE16MLC@QFP32(auto trim) [SA636]  
MC9S08QE16MLCE@QFP32 [SA636]  
MC9S08QE16MLCE@QFP32(auto trim) [SA636]  
MC9S08QE16MLD@QFP44 [SA245A-B4805]  
MC9S08QE16MLD@QFP44(auto trim) [SA245A-B4805]  
MC9S08QE16MLDE@QFP44 [SA245A-B4805]  
MC9S08QE16MLDE@QFP44(auto trim) [SA245A-B4805]  
MC9S08QE16MWL@SOIC28 [SA404]  
MC9S08QE16MWL@SOIC28(auto trim) [SA404]  
MC9S08QE16MWLE@SOIC28 [SA404]  
MC9S08QE16MWLE@SOIC28(auto trim) [SA404]  
MC9S08QE16VLC@QFP32 [SA636]  
MC9S08QE16VLC@QFP32(auto trim) [SA636]  
MC9S08QE16VLCE@QFP32 [SA636]  
MC9S08QE16VLCE@QFP32(auto trim) [SA636]  
MC9S08QE16VLD@QFP44 [SA245A-B4805]  
MC9S08QE16VLD@QFP44(auto trim) [SA245A-B4805]  
MC9S08QE16VLDE@QFP44 [SA245A-B4805]  
MC9S08QE16VLDE@QFP44(auto trim) [SA245A-B4805]  
MC9S08QE16VWL@SOIC28 [SA404]  
MC9S08QE16VWL@SOIC28(auto trim) [SA404]  
MC9S08QE16VWLE@SOIC28 [SA404]  
MC9S08QE16VWLE@SOIC28(auto trim) [SA404]  
MC9S08QE32CLC@QFP32 [SA636]  
MC9S08QE32CLC@QFP32(auto trim) [SA636]  
MC9S08QE32CLCE@QFP32 [SA636]  
MC9S08QE32CLCE@QFP32(auto trim) [SA636]  
MC9S08QE32CLD@QFP44 [SA245A-B4805]  
MC9S08QE32CLD@QFP44(auto trim) [SA245A-B4805]  
MC9S08QE32CLDE@QFP44 [SA245A-B4805]  
MC9S08QE32CLDE@QFP44(auto trim) [SA245A-B4805]  
MC9S08QE32CWL@SOIC28 [SA404]  
MC9S08QE32CWL@SOIC28(auto trim) [SA404]  
MC9S08QE32CWLE@SOIC28 [SA404]

MC9S08QE32CWLE@SOIC28(auto trim) [SA404]  
MC9S08QE32MLC@QFP32 [SA636]  
MC9S08QE32MLC@QFP32(auto trim) [SA636]  
MC9S08QE32MLCE@QFP32 [SA636]  
MC9S08QE32MLCE@QFP32(auto trim) [SA636]  
MC9S08QE32MLD@QFP44 [SA245A-B4805]  
MC9S08QE32MLD@QFP44(auto trim) [SA245A-B4805]  
MC9S08QE32MLDE@QFP44 [SA245A-B4805]  
MC9S08QE32MLDE@QFP44(auto trim) [SA245A-B4805]  
MC9S08QE32MWL@SOIC28 [SA404]  
MC9S08QE32MWL@SOIC28(auto trim) [SA404]  
MC9S08QE32MWLE@SOIC28 [SA404]  
MC9S08QE32MWLE@SOIC28(auto trim) [SA404]  
MC9S08QE32VLC@QFP32 [SA636]  
MC9S08QE32VLC@QFP32(auto trim) [SA636]  
MC9S08QE32VLCE@QFP32 [SA636]  
MC9S08QE32VLCE@QFP32(auto trim) [SA636]  
MC9S08QE32VLD@QFP44 [SA245A-B4805]  
MC9S08QE32VLD@QFP44(auto trim) [SA245A-B4805]  
MC9S08QE32VLDE@QFP44 [SA245A-B4805]  
MC9S08QE32VLDE@QFP44(auto trim) [SA245A-B4805]  
MC9S08QE32VWL@SOIC28 [SA404]  
MC9S08QE32VWL@SOIC28(auto trim) [SA404]  
MC9S08QE32VWLE@SOIC28 [SA404]  
MC9S08QE32VWLE@SOIC28(auto trim) [SA404]  
MC9S08QE4CLC@QFP32 [SA636]  
MC9S08QE4CLC@QFP32(auto trim) [SA636]  
MC9S08QE4CLCE@QFP32 [SA636]  
MC9S08QE4CLCE@QFP32(auto trim) [SA636]  
MC9S08QE4CPG MC9S08QE4CPG(auto trim)  
MC9S08QE4CPGE MC9S08QE4CPGE(auto trim)  
MC9S08QE4CTG@TSSOP16 [SA026]  
MC9S08QE4CTG@TSSOP16(auto trim) [SA026]  
MC9S08QE4CTGE@TSSOP16 [SA026]  
MC9S08QE4CTGE@TSSOP16(auto trim) [SA026]  
MC9S08QE4CWJ@SOIC20 [SA404]  
MC9S08QE4CWJ@SOIC20(auto trim) [SA404]  
MC9S08QE4CWJE@SOIC20 [SA404]  
MC9S08QE4CWJE@SOIC20(auto trim) [SA404]  
MC9S08QE4CWL@SOIC28 [SA404]  
MC9S08QE4CWL@SOIC28(auto trim) [SA404]  
MC9S08QE4CWLE@SOIC28 [SA404]  
MC9S08QE4CWLE@SOIC28(auto trim) [SA404]  
MC9S08QE4MLC@QFP32 [SA636]  
MC9S08QE4MLC@QFP32(auto trim) [SA636]  
MC9S08QE4MLCE@QFP32 [SA636]  
MC9S08QE4MLCE@QFP32(auto trim) [SA636]  
MC9S08QE4MPG MC9S08QE4MPG(auto trim)  
MC9S08QE4MPGE MC9S08QE4MPGE(auto trim)  
MC9S08QE4MTG@TSSOP16 [SA026]  
MC9S08QE4MTG@TSSOP16(auto trim) [SA026]  
MC9S08QE4MTGE@TSSOP16 [SA026]  
MC9S08QE4MTGE@TSSOP16(auto trim) [SA026]

MC9S08QE4MWJ@SOIC20 [SA404]  
MC9S08QE4MWJ@SOIC20(auto trim) [SA404]  
MC9S08QE4MWJE@SOIC20 [SA404]  
MC9S08QE4MWJE@SOIC20(auto trim) [SA404]  
MC9S08QE4MWL@SOIC28 [SA404]  
MC9S08QE4MWL@SOIC28(auto trim) [SA404]  
MC9S08QE4MWLE@SOIC28 [SA404]  
MC9S08QE4MWLE@SOIC28(auto trim) [SA404]  
MC9S08QE4VLC@QFP32 [SA636]  
MC9S08QE4VLC@QFP32(auto trim) [SA636]  
MC9S08QE4VLCE@QFP32 [SA636]  
MC9S08QE4VLCE@QFP32(auto trim) [SA636]  
MC9S08QE4VPG MC9S08QE4VPG(auto trim)  
MC9S08QE4VPGE MC9S08QE4VPGE(auto trim)  
MC9S08QE4VTG@TSSOP16 [SA026]  
MC9S08QE4VTG@TSSOP16(auto trim) [SA026]  
MC9S08QE4VTGE@TSSOP16 [SA026]  
MC9S08QE4VTGE@TSSOP16(auto trim) [SA026]  
MC9S08QE4VWJ@SOIC20 [SA404]  
MC9S08QE4VWJ@SOIC20(auto trim) [SA404]  
MC9S08QE4VWJE@SOIC20 [SA404]  
MC9S08QE4VWJE@SOIC20(auto trim) [SA404]  
MC9S08QE4VWL@SOIC28 [SA404]  
MC9S08QE4VWL@SOIC28(auto trim) [SA404]  
MC9S08QE4VWLE@SOIC28 [SA404]  
MC9S08QE4VWLE@SOIC28(auto trim) [SA404]  
MC9S08QE64CLC@QFP32 [SA636] MC9S08QE64CLCE@QFP32 [SA636]  
MC9S08QE64CLD@QFP44 [SA245A-B4805]  
MC9S08QE64CLDE@QFP44 [SA245A-B4805]  
MC9S08QE64MLC@QFP32 [SA636] MC9S08QE64MLCE@QFP32 [SA636]  
MC9S08QE64MLD@QFP44 [SA245A-B4805]  
MC9S08QE64MLDE@QFP44 [SA245A-B4805]  
MC9S08QE64VLC@QFP32 [SA636] MC9S08QE64VLCE@QFP32 [SA636]  
MC9S08QE64VLD@QFP44 [SA245A-B4805]  
MC9S08QE64VLDE@QFP44 [SA245A-B4805]  
MC9S08QE8CLC@QFP32 [SA636]  
MC9S08QE8CLC@QFP32(auto trim) [SA636]  
MC9S08QE8CLCE@QFP32 [SA636]  
MC9S08QE8CLCE@QFP32(auto trim) [SA636]  
MC9S08QE8CPG MC9S08QE8CPG(auto trim)  
MC9S08QE8CPGE MC9S08QE8CPGE(auto trim)  
MC9S08QE8CTG@TSSOP16 [SA026]  
MC9S08QE8CTG@TSSOP16(auto trim) [SA026]  
MC9S08QE8CTGE@TSSOP16 [SA026]  
MC9S08QE8CTGE@TSSOP16(auto trim) [SA026]  
MC9S08QE8CWJ@SOIC20 [SA404]  
MC9S08QE8CWJ@SOIC20(auto trim) [SA404]  
MC9S08QE8CWJE@SOIC20 [SA404]  
MC9S08QE8CWJE@SOIC20(auto trim) [SA404]  
MC9S08QE8CWL@SOIC28 [SA404]  
MC9S08QE8CWL@SOIC28(auto trim) [SA404]  
MC9S08QE8CWLE@SOIC28 [SA404]  
MC9S08QE8CWLE@SOIC28(auto trim) [SA404]

MC9S08QE8MLC@QFP32 [SA636]  
MC9S08QE8MLC@QFP32(auto trim) [SA636]  
MC9S08QE8MLCE@QFP32 [SA636]  
MC9S08QE8MLCE@QFP32(auto trim) [SA636]  
MC9S08QE8MPG MC9S08QE8MPG(auto trim)  
MC9S08QE8MPGE MC9S08QE8MPGE(auto trim)  
MC9S08QE8MTG@TSSOP16 [SA026]  
MC9S08QE8MTG@TSSOP16(auto trim) [SA026]  
MC9S08QE8MTGE@TSSOP16 [SA026]  
MC9S08QE8MTGE@TSSOP16(auto trim) [SA026]  
MC9S08QE8MWJ@SOIC20 [SA404]  
MC9S08QE8MWJ@SOIC20(auto trim) [SA404]  
MC9S08QE8MWJE@SOIC20 [SA404]  
MC9S08QE8MWJE@SOIC20(auto trim) [SA404]  
MC9S08QE8MWL@SOIC28 [SA404]  
MC9S08QE8MWL@SOIC28(auto trim) [SA404]  
MC9S08QE8MWLE@SOIC28 [SA404]  
MC9S08QE8MWLE@SOIC28(auto trim) [SA404]  
MC9S08QE8VLC@QFP32 [SA636]  
MC9S08QE8VLC@QFP32(auto trim) [SA636]  
MC9S08QE8VLC@QFP32 [SA636]  
MC9S08QE8VLC@QFP32(auto trim) [SA636]  
MC9S08QE8VPG MC9S08QE8VPG(auto trim)  
MC9S08QE8VPGE MC9S08QE8VPGE(auto trim)  
MC9S08QE8VTG@TSSOP16 [SA026]  
MC9S08QE8VTG@TSSOP16(auto trim) [SA026]  
MC9S08QE8VTGE@TSSOP16 [SA026]  
MC9S08QE8VTGE@TSSOP16(auto trim) [SA026]  
MC9S08QE8VWJ@SOIC20 [SA404]  
MC9S08QE8VWJ@SOIC20(auto trim) [SA404]  
MC9S08QE8VWJE@SOIC20 [SA404]  
MC9S08QE8VWJE@SOIC20(auto trim) [SA404]  
MC9S08QE8VWL@SOIC28 [SA404]  
MC9S08QE8VWL@SOIC28(auto trim) [SA404]  
MC9S08QE8VWLE@SOIC28 [SA404]  
MC9S08QE8VWLE@SOIC28(auto trim) [SA404]  
MC9S08QE96CLC@QFP32 [SA636] MC9S08QE96CLCE@QFP32 [SA636]  
MC9S08QE96CLD@QFP44 [SA245A-B4805]  
MC9S08QE96CLDE@QFP44 [SA245A-B4805]  
MC9S08QE96MLC@QFP32 [SA636] MC9S08QE96MLCE@QFP32 [SA636]  
MC9S08QE96MLD@QFP44 [SA245A-B4805]  
MC9S08QE96MLDE@QFP44 [SA245A-B4805]  
MC9S08QE96VLC@QFP32 [SA636] MC9S08QE96VLCE@QFP32 [SA636]  
MC9S08QE96VLD@QFP44 [SA245A-B4805]  
MC9S08QE96VLDE@QFP44 [SA245A-B4805]  
MC9S08QG4CDN@SOIC8 [SA602] MC9S08QG4CDNE@SOIC8 [SA602]  
MC9S08QG4CDT@TSSOP16 [SA026] MC9S08QG4CDTE@TSSOP16 [SA026]  
MC9S08QG4CPA MC9S08QG4CPAE  
MC9S08QG4MDN@SOIC8 [SA602] MC9S08QG4MDNE@SOIC8 [SA602]  
MC9S08QG4MDT@TSSOP16 [SA026] MC9S08QG4MDTE@TSSOP16 [SA026]  
MC9S08QG4MPA MC9S08QG4MPAE  
MC9S08QG4VDN@SOIC8 [SA602] MC9S08QG4VDNE@SOIC8 [SA602]  
MC9S08QG4VDT@TSSOP16 [SA026] MC9S08QG4VDTE@TSSOP16 [SA026]

MC9S08QG4VPA	MC9S08QG4VPAE
MC9S08QG8CDN@SOIC8 [SA602]	MC9S08QG8CDNE@SOIC8 [SA602]
MC9S08QG8CDT@TSSOP16 [SA026]	MC9S08QG8CDTE@TSSOP16 [SA026]
MC9S08QG8CPB	MC9S08QG8CPBE
MC9S08QG8MDN@SOIC8 [SA602]	MC9S08QG8MDNE@SOIC8 [SA602]
MC9S08QG8MDT@TSSOP16 [SA026]	MC9S08QG8MDTE@TSSOP16 [SA026]
MC9S08QG8MPB	MC9S08QG8MPBE
MC9S08QG8VDN@SOIC8 [SA602]	MC9S08QG8VDNE@SOIC8 [SA602]
MC9S08QG8VDT@TSSOP16 [SA026]	MC9S08QG8VDTE@TSSOP16 [SA026]
MC9S08QG8VPB	MC9S08QG8VPBE
MC9S08RC16CDW@SOIC28 [SA404]	MC9S08RC16CDWE@SOIC28 [SA404]
MC9S08RC16CFG@LQFP44 [SA245A-B4805]	
MC9S08RC16CFGE@LQFP44 [SA245A-B4805]	
MC9S08RC16CFJ@LQFP32 [SA636]	MC9S08RC16CFJE@LQFP32 [SA636]
MC9S08RC16CP	MC9S08RC16CPE
MC9S08RC16MDW@SOIC28 [SA404]	MC9S08RC16MDWE@SOIC28 [SA404]
MC9S08RC16MFG@LQFP44 [SA245A-B4805]	
MC9S08RC16MFGE@LQFP44 [SA245A-B4805]	
MC9S08RC16MFJ@LQFP32 [SA636]	MC9S08RC16MFJE@LQFP32 [SA636]
MC9S08RC16MP	MC9S08RC16MPE
MC9S08RC16VDW@SOIC28 [SA404]	MC9S08RC16VDWE@SOIC28 [SA404]
MC9S08RC16VFG@LQFP44 [SA245A-B4805]	
MC9S08RC16VFGE@LQFP44 [SA245A-B4805]	
MC9S08RC16VFJ@LQFP32 [SA636]	MC9S08RC16VFJE@LQFP32 [SA636]
MC9S08RC16VP	MC9S08RC16VPE
MC9S08RC32CDW@SOIC28 [SA404]	MC9S08RC32CDWE@SOIC28 [SA404]
MC9S08RC32CFG@LQFP44 [SA245A-B4805]	
MC9S08RC32CFGE@LQFP44 [SA245A-B4805]	
MC9S08RC32CFJ@LQFP32 [SA636]	MC9S08RC32CFJE@LQFP32 [SA636]
MC9S08RC32CP	MC9S08RC32CPE
MC9S08RC32MDW@SOIC28 [SA404]	MC9S08RC32MDWE@SOIC28 [SA404]
MC9S08RC32MFG@LQFP44 [SA245A-B4805]	
MC9S08RC32MFGE@LQFP44 [SA245A-B4805]	
MC9S08RC32MFJ@LQFP32 [SA636]	MC9S08RC32MFJE@LQFP32 [SA636]
MC9S08RC32MP	MC9S08RC32MPE
MC9S08RC32VDW@SOIC28 [SA404]	MC9S08RC32VDWE@SOIC28 [SA404]
MC9S08RC32VFG@LQFP44 [SA245A-B4805]	
MC9S08RC32VFGE@LQFP44 [SA245A-B4805]	
MC9S08RC32VFJ@LQFP32 [SA636]	MC9S08RC32VFJE@LQFP32 [SA636]
MC9S08RC32VP	MC9S08RC32VPE
MC9S08RC60CDW@SOIC28 [SA404]	MC9S08RC60CDWE@SOIC28 [SA404]
MC9S08RC60CFG@LQFP44 [SA245A-B4805]	
MC9S08RC60CFGE@LQFP44 [SA245A-B4805]	
MC9S08RC60CFJ@LQFP32 [SA636]	MC9S08RC60CFJE@LQFP32 [SA636]
MC9S08RC60CP	MC9S08RC60CPE
MC9S08RC60MDW@SOIC28 [SA404]	MC9S08RC60MDWE@SOIC28 [SA404]
MC9S08RC60MFG@LQFP44 [SA245A-B4805]	
MC9S08RC60MFGE@LQFP44 [SA245A-B4805]	
MC9S08RC60MFJ@LQFP32 [SA636]	MC9S08RC60MFJE@LQFP32 [SA636]
MC9S08RC60MP	MC9S08RC60MPE
MC9S08RC60VDW@SOIC28 [SA404]	MC9S08RC60VDWE@SOIC28 [SA404]
MC9S08RC60VFG@LQFP44 [SA245A-B4805]	
MC9S08RC60VFGE@LQFP44 [SA245A-B4805]	

MC9S08RC60VFJ@LQFP32 [SA636]	MC9S08RC60VFJE@LQFP32 [SA636]
MC9S08RC60VP	MC9S08RC60VPE
MC9S08RC8CDW@SOIC28 [SA404]	MC9S08RC8CDWE@SOIC28 [SA404]
MC9S08RC8CFG@LQFP44 [SA245A-B4805]	
MC9S08RC8CFGE@LQFP44 [SA245A-B4805]	
MC9S08RC8CFJ@LQFP32 [SA636]	MC9S08RC8CFJE@LQFP32 [SA636]
MC9S08RC8CP	MC9S08RC8CPE
MC9S08RC8MDW@SOIC28 [SA404]	MC9S08RC8MDWE@SOIC28 [SA404]
MC9S08RC8MFG@LQFP44 [SA245A-B4805]	
MC9S08RC8MFGE@LQFP44 [SA245A-B4805]	
MC9S08RC8MFJ@LQFP32 [SA636]	MC9S08RC8MFJE@LQFP32 [SA636]
MC9S08RC8MP	MC9S08RC8MPE
MC9S08RC8VDW@SOIC28 [SA404]	MC9S08RC8VDWE@SOIC28 [SA404]
MC9S08RC8VFG@LQFP44 [SA245A-B4805]	
MC9S08RC8VFGE@LQFP44 [SA245A-B4805]	
MC9S08RC8VFJ@LQFP32 [SA636]	MC9S08RC8VFJE@LQFP32 [SA636]
MC9S08RC8VP	MC9S08RC8VPE
MC9S08RD16CDW@SOIC28 [SA404]	MC9S08RD16CDWE@SOIC28 [SA404]
MC9S08RD16CFG@LQFP44 [SA245A-B4805]	
MC9S08RD16CFGE@LQFP44 [SA245A-B4805]	
MC9S08RD16CFJ@LQFP32 [SA636]	MC9S08RD16CFJE@LQFP32 [SA636]
MC9S08RD16CP	MC9S08RD16CPE
MC9S08RD16MDW@SOIC28 [SA404]	MC9S08RD16MDWE@SOIC28 [SA404]
MC9S08RD16MFG@LQFP44 [SA245A-B4805]	
MC9S08RD16MFGE@LQFP44 [SA245A-B4805]	
MC9S08RD16MFJ@LQFP32 [SA636]	MC9S08RD16MFJE@LQFP32 [SA636]
MC9S08RD16MP	MC9S08RD16MPE
MC9S08RD16VDW@SOIC28 [SA404]	MC9S08RD16VDWE@SOIC28 [SA404]
MC9S08RD16VFG@LQFP44 [SA245A-B4805]	
MC9S08RD16VFGE@LQFP44 [SA245A-B4805]	
MC9S08RD16VFJ@LQFP32 [SA636]	MC9S08RD16VFJE@LQFP32 [SA636]
MC9S08RD16VP	MC9S08RD16VPE
MC9S08RD32CDW@SOIC28 [SA404]	MC9S08RD32CDWE@SOIC28 [SA404]
MC9S08RD32CFG@LQFP44 [SA245A-B4805]	
MC9S08RD32CFGE@LQFP44 [SA245A-B4805]	
MC9S08RD32CFJ@LQFP32 [SA636]	MC9S08RD32CFJE@LQFP32 [SA636]
MC9S08RD32CP	MC9S08RD32CPE
MC9S08RD32MDW@SOIC28 [SA404]	MC9S08RD32MDWE@SOIC28 [SA404]
MC9S08RD32MFG@LQFP44 [SA245A-B4805]	
MC9S08RD32MFGE@LQFP44 [SA245A-B4805]	
MC9S08RD32MFJ@LQFP32 [SA636]	MC9S08RD32MFJE@LQFP32 [SA636]
MC9S08RD32MP	MC9S08RD32MPE
MC9S08RD32VDW@SOIC28 [SA404]	MC9S08RD32VDWE@SOIC28 [SA404]
MC9S08RD32VFG@LQFP44 [SA245A-B4805]	
MC9S08RD32VFGE@LQFP44 [SA245A-B4805]	
MC9S08RD32VFJ@LQFP32 [SA636]	MC9S08RD32VFJE@LQFP32 [SA636]
MC9S08RD32VP	MC9S08RD32VPE
MC9S08RD60CDW@SOIC28 [SA404]	MC9S08RD60CDWE@SOIC28 [SA404]
MC9S08RD60CFG@LQFP44 [SA245A-B4805]	
MC9S08RD60CFGE@LQFP44 [SA245A-B4805]	
MC9S08RD60CFJ@LQFP32 [SA636]	MC9S08RD60CFJE@LQFP32 [SA636]
MC9S08RD60CP	MC9S08RD60CPE
MC9S08RD60MDW@SOIC28 [SA404]	MC9S08RD60MDWE@SOIC28 [SA404]

MC9S08RD60MFG@LQFP44 [SA245A-B4805]  
MC9S08RD60MFGE@LQFP44 [SA245A-B4805]  
MC9S08RD60MFJ@LQFP32 [SA636] MC9S08RD60MFJE@LQFP32 [SA636]  
MC9S08RD60MP MC9S08RD60MPE  
MC9S08RD60VDW@SOIC28 [SA404] MC9S08RD60VDWE@SOIC28 [SA404]  
MC9S08RD60VFG@LQFP44 [SA245A-B4805]  
MC9S08RD60VFGE@LQFP44 [SA245A-B4805]  
MC9S08RD60VFJ@LQFP32 [SA636] MC9S08RD60VFJE@LQFP32 [SA636]  
MC9S08RD60VP MC9S08RD60VPE  
MC9S08RD8CDW@SOIC28 [SA404] MC9S08RD8CDWE@SOIC28 [SA404]  
MC9S08RD8CFG@LQFP44 [SA245A-B4805]  
MC9S08RD8CFGE@LQFP44 [SA245A-B4805]  
MC9S08RD8CFJ@LQFP32 [SA636] MC9S08RD8CFJE@LQFP32 [SA636]  
MC9S08RD8CP MC9S08RD8CPE  
MC9S08RD8MDW@SOIC28 [SA404] MC9S08RD8MDWE@SOIC28 [SA404]  
MC9S08RD8MFG@LQFP44 [SA245A-B4805]  
MC9S08RD8MFGE@LQFP44 [SA245A-B4805]  
MC9S08RD8MFJ@LQFP32 [SA636] MC9S08RD8MFJE@LQFP32 [SA636]  
MC9S08RD8MP MC9S08RD8MPE  
MC9S08RD8VDW@SOIC28 [SA404] MC9S08RD8VDWE@SOIC28 [SA404]  
MC9S08RD8VFG@LQFP44 [SA245A-B4805]  
MC9S08RD8VFGE@LQFP44 [SA245A-B4805]  
MC9S08RD8VFJ@LQFP32 [SA636] MC9S08RD8VFJE@LQFP32 [SA636]  
MC9S08RD8VP MC9S08RD8VPE  
MC9S08RE16CDW@SOIC28 [SA404] MC9S08RE16CDWE@SOIC28 [SA404]  
MC9S08RE16CFG@LQFP44 [SA245A-B4805]  
MC9S08RE16CFGE@LQFP44 [SA245A-B4805]  
MC9S08RE16CFJ@LQFP32 [SA636] MC9S08RE16CFJE@LQFP32 [SA636]  
MC9S08RE16CP MC9S08RE16CPE  
MC9S08RE16MDW@SOIC28 [SA404] MC9S08RE16MDWE@SOIC28 [SA404]  
MC9S08RE16MFG@LQFP44 [SA245A-B4805]  
MC9S08RE16MFGE@LQFP44 [SA245A-B4805]  
MC9S08RE16MFJ@LQFP32 [SA636] MC9S08RE16MFJE@LQFP32 [SA636]  
MC9S08RE16MP MC9S08RE16MPE  
MC9S08RE16VDW@SOIC28 [SA404] MC9S08RE16VDWE@SOIC28 [SA404]  
MC9S08RE16VFG@LQFP44 [SA245A-B4805]  
MC9S08RE16VFGE@LQFP44 [SA245A-B4805]  
MC9S08RE16VFJ@LQFP32 [SA636] MC9S08RE16VFJE@LQFP32 [SA636]  
MC9S08RE16VP MC9S08RE16VPE  
MC9S08RE32CDW@SOIC28 [SA404] MC9S08RE32CDWE@SOIC28 [SA404]  
MC9S08RE32CFG@LQFP44 [SA245A-B4805]  
MC9S08RE32CFGE@LQFP44 [SA245A-B4805]  
MC9S08RE32CFJ@LQFP32 [SA636] MC9S08RE32CFJE@LQFP32 [SA636]  
MC9S08RE32CP MC9S08RE32CPE  
MC9S08RE32MDW@SOIC28 [SA404] MC9S08RE32MDWE@SOIC28 [SA404]  
MC9S08RE32MFG@LQFP44 [SA245A-B4805]  
MC9S08RE32MFGE@LQFP44 [SA245A-B4805]  
MC9S08RE32MFJ@LQFP32 [SA636] MC9S08RE32MFJE@LQFP32 [SA636]  
MC9S08RE32MP MC9S08RE32MPE  
MC9S08RE32VDW@SOIC28 [SA404] MC9S08RE32VDWE@SOIC28 [SA404]  
MC9S08RE32VFG@LQFP44 [SA245A-B4805]  
MC9S08RE32VFGE@LQFP44 [SA245A-B4805]  
MC9S08RE32VFJ@LQFP32 [SA636] MC9S08RE32VFJE@LQFP32 [SA636]

MC9S08RE32VP	MC9S08RE32VPE
MC9S08RE60CDW@SOIC28 [SA404]	MC9S08RE60CDWE@SOIC28 [SA404]
MC9S08RE60CFG@LQFP44 [SA245A-B4805]	
MC9S08RE60CFGE@LQFP44 [SA245A-B4805]	
MC9S08RE60CFJ@LQFP32 [SA636]	MC9S08RE60CFJE@LQFP32 [SA636]
MC9S08RE60CP	MC9S08RE60CPE
MC9S08RE60MDW@SOIC28 [SA404]	MC9S08RE60MDWE@SOIC28 [SA404]
MC9S08RE60MFG@LQFP44 [SA245A-B4805]	
MC9S08RE60MFGE@LQFP44 [SA245A-B4805]	
MC9S08RE60MFJ@LQFP32 [SA636]	MC9S08RE60MFJE@LQFP32 [SA636]
MC9S08RE60MP	MC9S08RE60MPE
MC9S08RE60VDW@SOIC28 [SA404]	MC9S08RE60VDWE@SOIC28 [SA404]
MC9S08RE60VFG@LQFP44 [SA245A-B4805]	
MC9S08RE60VFGE@LQFP44 [SA245A-B4805]	
MC9S08RE60VFJ@LQFP32 [SA636]	MC9S08RE60VFJE@LQFP32 [SA636]
MC9S08RE60VP	MC9S08RE60VPE
MC9S08RE8CDW@SOIC28 [SA404]	MC9S08RE8CDWE@SOIC28 [SA404]
MC9S08RE8CFG@LQFP44 [SA245A-B4805]	
MC9S08RE8CFGE@LQFP44 [SA245A-B4805]	
MC9S08RE8CFJ@LQFP32 [SA636]	MC9S08RE8CFJE@LQFP32 [SA636]
MC9S08RE8CP	MC9S08RE8CPE
MC9S08RE8MDW@SOIC28 [SA404]	MC9S08RE8MDWE@SOIC28 [SA404]
MC9S08RE8MFG@LQFP44 [SA245A-B4805]	
MC9S08RE8MFGE@LQFP44 [SA245A-B4805]	
MC9S08RE8MFJ@LQFP32 [SA636]	MC9S08RE8MFJE@LQFP32 [SA636]
MC9S08RE8MP	MC9S08RE8MPE
MC9S08RE8VDW@SOIC28 [SA404]	MC9S08RE8VDWE@SOIC28 [SA404]
MC9S08RE8VFG@LQFP44 [SA245A-B4805]	
MC9S08RE8VFGE@LQFP44 [SA245A-B4805]	
MC9S08RE8VFJ@LQFP32 [SA636]	MC9S08RE8VFJE@LQFP32 [SA636]
MC9S08RE8VP	MC9S08RE8VPE
MC9S08RG16CDW@SOIC28 [SA404]	MC9S08RG16CDWE@SOIC28 [SA404]
MC9S08RG16CFG@LQFP44 [SA245A-B4805]	
MC9S08RG16CFGE@LQFP44 [SA245A-B4805]	
MC9S08RG16CFJ@LQFP32 [SA636]	MC9S08RG16CFJE@LQFP32 [SA636]
MC9S08RG16CP	MC9S08RG16CPE
MC9S08RG16MDW@SOIC28 [SA404]	MC9S08RG16MDWE@SOIC28 [SA404]
MC9S08RG16MFG@LQFP44 [SA245A-B4805]	
MC9S08RG16MFGE@LQFP44 [SA245A-B4805]	
MC9S08RG16MFJ@LQFP32 [SA636]	MC9S08RG16MFJE@LQFP32 [SA636]
MC9S08RG16MP	MC9S08RG16MPE
MC9S08RG16VDW@SOIC28 [SA404]	MC9S08RG16VDWE@SOIC28 [SA404]
MC9S08RG16VFG@LQFP44 [SA245A-B4805]	
MC9S08RG16VFGE@LQFP44 [SA245A-B4805]	
MC9S08RG16VFJ@LQFP32 [SA636]	MC9S08RG16VFJE@LQFP32 [SA636]
MC9S08RG16VP	MC9S08RG16VPE
MC9S08RG32CDW@SOIC28 [SA404]	MC9S08RG32CDWE@SOIC28 [SA404]
MC9S08RG32CFG@LQFP44 [SA245A-B4805]	
MC9S08RG32CFGE@LQFP44 [SA245A-B4805]	
MC9S08RG32CFJ@LQFP32 [SA636]	MC9S08RG32CFJE@LQFP32 [SA636]
MC9S08RG32CP	MC9S08RG32CPE
MC9S08RG32MDW@SOIC28 [SA404]	MC9S08RG32MDWE@SOIC28 [SA404]
MC9S08RG32MFG@LQFP44 [SA245A-B4805]	

MC9S08RG32MFGE@LQFP44 [SA245A-B4805]  
MC9S08RG32MFJ@LQFP32 [SA636] MC9S08RG32MFJE@LQFP32 [SA636]  
MC9S08RG32MP MC9S08RG32MPE  
MC9S08RG32VDW@SOIC28 [SA404] MC9S08RG32VDWE@SOIC28 [SA404]  
MC9S08RG32VFG@LQFP44 [SA245A-B4805]  
MC9S08RG32VFGE@LQFP44 [SA245A-B4805]  
MC9S08RG32VFJ@LQFP32 [SA636] MC9S08RG32VFJE@LQFP32 [SA636]  
MC9S08RG32VP MC9S08RG32VPE  
MC9S08RG60CDW@SOIC28 [SA404] MC9S08RG60CDWE@SOIC28 [SA404]  
MC9S08RG60CFG@LQFP44 [SA245A-B4805]  
MC9S08RG60CFGE@LQFP44 [SA245A-B4805]  
MC9S08RG60CFJ@LQFP32 [SA636] MC9S08RG60CFJE@LQFP32 [SA636]  
MC9S08RG60CP MC9S08RG60CPE  
MC9S08RG60MDW@SOIC28 [SA404] MC9S08RG60MDWE@SOIC28 [SA404]  
MC9S08RG60MFG@LQFP44 [SA245A-B4805]  
MC9S08RG60MFGE@LQFP44 [SA245A-B4805]  
MC9S08RG60MFJ@LQFP32 [SA636] MC9S08RG60MFJE@LQFP32 [SA636]  
MC9S08RG60MP MC9S08RG60MPE  
MC9S08RG60VDW@SOIC28 [SA404] MC9S08RG60VDWE@SOIC28 [SA404]  
MC9S08RG60VFG@LQFP44 [SA245A-B4805]  
MC9S08RG60VFGE@LQFP44 [SA245A-B4805]  
MC9S08RG60VFJ@LQFP32 [SA636] MC9S08RG60VFJE@LQFP32 [SA636]  
MC9S08RG60VP MC9S08RG60VPE  
MC9S08RG8CDW@SOIC28 [SA404] MC9S08RG8CDWE@SOIC28 [SA404]  
MC9S08RG8CFG@LQFP44 [SA245A-B4805]  
MC9S08RG8CFGE@LQFP44 [SA245A-B4805]  
MC9S08RG8CFJ@LQFP32 [SA636] MC9S08RG8CFJE@LQFP32 [SA636]  
MC9S08RG8CP MC9S08RG8CPE  
MC9S08RG8MDW@SOIC28 [SA404] MC9S08RG8MDWE@SOIC28 [SA404]  
MC9S08RG8MFG@LQFP44 [SA245A-B4805]  
MC9S08RG8MFGE@LQFP44 [SA245A-B4805]  
MC9S08RG8MFJ@LQFP32 [SA636] MC9S08RG8MFJE@LQFP32 [SA636]  
MC9S08RG8MP MC9S08RG8MPE  
MC9S08RG8VDW@SOIC28 [SA404] MC9S08RG8VDWE@SOIC28 [SA404]  
MC9S08RG8VFG@LQFP44 [SA245A-B4805]  
MC9S08RG8VFGE@LQFP44 [SA245A-B4805]  
MC9S08RG8VFJ@LQFP32 [SA636] MC9S08RG8VFJE@LQFP32 [SA636]  
MC9S08SG16CTG@TSSOP16 [SA026] MC9S08SG16CTGE@TSSOP16 [SA026]  
MC9S08SG16CTJ@TSSOP20 [SA026] MC9S08SG16CTJE@TSSOP20 [SA026]  
MC9S08SG16CTL@TSSOP28 [SA643] MC9S08SG16CTLE@TSSOP28 [SA643]  
MC9S08SG16MTG@TSSOP16 [SA026] MC9S08SG16MTGE@TSSOP16 [SA026]  
MC9S08SG16MTJ@TSSOP20 [SA026] MC9S08SG16MTJE@TSSOP20 [SA026]  
MC9S08SG16MTL@TSSOP28 [SA643] MC9S08SG16MTLE@TSSOP28 [SA643]  
MC9S08SG16VTG@TSSOP16 [SA026] MC9S08SG16VTGE@TSSOP16 [SA026]  
MC9S08SG16VTJ@TSSOP20 [SA026] MC9S08SG16VTJE@TSSOP20 [SA026]  
MC9S08SG16VTL@TSSOP28 [SA643] MC9S08SG16VTLE@TSSOP28 [SA643]  
MC9S08SG32CTG@TSSOP16 [SA026] MC9S08SG32CTGE@TSSOP16 [SA026]  
MC9S08SG32CTJ@TSSOP20 [SA026] MC9S08SG32CTJE@TSSOP20 [SA026]  
MC9S08SG32CTL@TSSOP28 [SA643] MC9S08SG32CTLE@TSSOP28 [SA643]  
MC9S08SG32MTG@TSSOP16 [SA026] MC9S08SG32MTGE@TSSOP16 [SA026]  
MC9S08SG32MTJ@TSSOP20 [SA026] MC9S08SG32MTJE@TSSOP20 [SA026]  
MC9S08SG32MTL@TSSOP28 [SA643] MC9S08SG32MTLE@TSSOP28 [SA643]  
MC9S08SG32VTG@TSSOP16 [SA026] MC9S08SG32VTGE@TSSOP16 [SA026]

MC9S08SG32VTJ@TSSOP20 [SA026]      MC9S08SG32VTJE@TSSOP20 [SA026]  
MC9S08SG32VTL@TSSOP28 [SA643]      MC9S08SG32VTLE@TSSOP28 [SA643]  
MC9S08SG4CSC@SOIC8 [SA602]      MC9S08SG4CSCE@SOIC8 [SA602]  
MC9S08SG4CTG@TSSOP16 [SA026]      MC9S08SG4CTGE@TSSOP16 [SA026]  
MC9S08SG4CTJ@TSSOP20 [SA026]      MC9S08SG4CTJE@TSSOP20 [SA026]  
MC9S08SG4MSC@SOIC8 [SA602]      MC9S08SG4MSCE@SOIC8 [SA602]  
MC9S08SG4MTG@TSSOP16 [SA026]      MC9S08SG4MTGE@TSSOP16 [SA026]  
MC9S08SG4MTJ@TSSOP20 [SA026]      MC9S08SG4MTJE@TSSOP20 [SA026]  
MC9S08SG4VSC@SOIC8 [SA602]      MC9S08SG4VSCE@SOIC8 [SA602]  
MC9S08SG4VTG@TSSOP16 [SA026]      MC9S08SG4VTGE@TSSOP16 [SA026]  
MC9S08SG4VTJ@TSSOP20 [SA026]      MC9S08SG4VTJE@TSSOP20 [SA026]  
MC9S08SG8CSC@SOIC8 [SA602]      MC9S08SG8CSCE@SOIC8 [SA602]  
MC9S08SG8CTG@TSSOP16 [SA026]      MC9S08SG8CTGE@TSSOP16 [SA026]  
MC9S08SG8CTJ@TSSOP20 [SA026]      MC9S08SG8CTJE@TSSOP20 [SA026]  
MC9S08SG8MSC@SOIC8 [SA602]      MC9S08SG8MSCE@SOIC8 [SA602]  
MC9S08SG8MTG@TSSOP16 [SA026]      MC9S08SG8MTGE@TSSOP16 [SA026]  
MC9S08SG8MTJ@TSSOP20 [SA026]      MC9S08SG8MTJE@TSSOP20 [SA026]  
MC9S08SG8VSC@SOIC8 [SA602]      MC9S08SG8VSCE@SOIC8 [SA602]  
MC9S08SG8VTG@TSSOP16 [SA026]      MC9S08SG8VTGE@TSSOP16 [SA026]  
MC9S08SG8VTJ@TSSOP20 [SA026]      MC9S08SG8VTJE@TSSOP20 [SA026]  
MC9S08SH16CTG@TSSOP16 [SA026]      MC9S08SH16CTGE@TSSOP16 [SA026]  
MC9S08SH16CTJ@TSSOP20 [SA026]      MC9S08SH16CTJE@TSSOP20 [SA026]  
MC9S08SH16CTL@TSSOP28 [SA643]      MC9S08SH16CTLE@TSSOP28 [SA643]  
MC9S08SH16CWL@SOIC28 [SA404]      MC9S08SH16CWLE@SOIC28 [SA404]  
MC9S08SH16MTG@TSSOP16 [SA026]      MC9S08SH16MTGE@TSSOP16 [SA026]  
MC9S08SH16MTJ@TSSOP20 [SA026]      MC9S08SH16MTJE@TSSOP20 [SA026]  
MC9S08SH16MTL@TSSOP28 [SA643]      MC9S08SH16MTLE@TSSOP28 [SA643]  
MC9S08SH16MWL@SOIC28 [SA404]      MC9S08SH16MWLE@SOIC28 [SA404]  
MC9S08SH16VTG@TSSOP16 [SA026]      MC9S08SH16VTGE@TSSOP16 [SA026]  
MC9S08SH16VTJ@TSSOP20 [SA026]      MC9S08SH16VTJE@TSSOP20 [SA026]  
MC9S08SH16VTL@TSSOP28 [SA643]      MC9S08SH16VTLE@TSSOP28 [SA643]  
MC9S08SH16VWL@SOIC28 [SA404]      MC9S08SH16VWLE@SOIC28 [SA404]  
MC9S08SH32CTG@TSSOP16 [SA026]      MC9S08SH32CTGE@TSSOP16 [SA026]  
MC9S08SH32CTJ@TSSOP20 [SA026]      MC9S08SH32CTJE@TSSOP20 [SA026]  
MC9S08SH32CTL@TSSOP28 [SA643]      MC9S08SH32CTLE@TSSOP28 [SA643]  
MC9S08SH32CWL@SOIC28 [SA404]      MC9S08SH32CWLE@SOIC28 [SA404]  
MC9S08SH32MTG@TSSOP16 [SA026]      MC9S08SH32MTGE@TSSOP16 [SA026]  
MC9S08SH32MTJ@TSSOP20 [SA026]      MC9S08SH32MTJE@TSSOP20 [SA026]  
MC9S08SH32MTL@TSSOP28 [SA643]      MC9S08SH32MTLE@TSSOP28 [SA643]  
MC9S08SH32MWL@SOIC28 [SA404]      MC9S08SH32MWLE@SOIC28 [SA404]  
MC9S08SH32VTG@TSSOP16 [SA026]      MC9S08SH32VTGE@TSSOP16 [SA026]  
MC9S08SH32VTJ@TSSOP20 [SA026]      MC9S08SH32VTJE@TSSOP20 [SA026]  
MC9S08SH32VTL@TSSOP28 [SA643]      MC9S08SH32VTLE@TSSOP28 [SA643]  
MC9S08SH32VWL@SOIC28 [SA404]      MC9S08SH32VWLE@SOIC28 [SA404]  
MC9S08SH4CPJ  
MC9S08SH4CPJE  
MC9S08SH4CSC@SOIC8 [SA602]  
MC9S08SH4CSC@SOIC8(auto trim) [SA602]  
MC9S08SH4CSCE@SOIC8 [SA602]  
MC9S08SH4CSCE@SOIC8(auto trim) [SA602]  
MC9S08SH4CTG@TSSOP16 [SA026]  
MC9S08SH4CTG@TSSOP16(auto trim) [SA026]  
MC9S08SH4CTGE@TSSOP16 [SA026]

MC9S08SH4CTGE@TSSOP16(auto trim) [SA026]  
MC9S08SH4CTJ@TSSOP20 [SA026]  
MC9S08SH4CTJ@TSSOP20(auto trim) [SA026]  
MC9S08SH4CTJE@TSSOP20 [SA026]  
MC9S08SH4CTJE@TSSOP20(auto trim) [SA026]  
MC9S08SH4CWJ@SOIC20 [SA404]  
MC9S08SH4CWJ@SOIC20(auto trim) [SA404]  
MC9S08SH4CWJE@SOIC20 [SA404]  
MC9S08SH4CWJE@SOIC20(auto trim) [SA404]  
MC9S08SH4MPJ MC9S08SH4MPJ(auto trim)  
MC9S08SH4MPJE MC9S08SH4MPJE(auto trim)  
MC9S08SH4MSC@SOIC8 [SA602]  
MC9S08SH4MSC@SOIC8(auto trim) [SA602]  
MC9S08SH4MSCE@SOIC8 [SA602]  
MC9S08SH4MSCE@SOIC8(auto trim) [SA602]  
MC9S08SH4MTG@TSSOP16 [SA026]  
MC9S08SH4MTG@TSSOP16(auto trim) [SA026]  
MC9S08SH4MTGE@TSSOP16 [SA026]  
MC9S08SH4MTGE@TSSOP16(auto trim) [SA026]  
MC9S08SH4MTJ@TSSOP20 [SA026]  
MC9S08SH4MTJ@TSSOP20(auto trim) [SA026]  
MC9S08SH4MTJE@TSSOP20 [SA026]  
MC9S08SH4MTJE@TSSOP20(auto trim) [SA026]  
MC9S08SH4MWJ@SOIC20 [SA404]  
MC9S08SH4MWJ@SOIC20(auto trim) [SA404]  
MC9S08SH4MWJE@SOIC20 [SA404]  
MC9S08SH4MWJE@SOIC20(auto trim) [SA404]  
MC9S08SH4VPJ MC9S08SH4VPJ(auto trim)  
MC9S08SH4VPJE MC9S08SH4VPJE(auto trim)  
MC9S08SH4VSC@SOIC8 [SA602]  
MC9S08SH4VSC@SOIC8(auto trim) [SA602]  
MC9S08SH4VSCE@SOIC8 [SA602]  
MC9S08SH4VSCE@SOIC8(auto trim) [SA602]  
MC9S08SH4VTG@TSSOP16 [SA026]  
MC9S08SH4VTG@TSSOP16(auto trim) [SA026]  
MC9S08SH4VTGE@TSSOP16 [SA026]  
MC9S08SH4VTGE@TSSOP16(auto trim) [SA026]  
MC9S08SH4VTJ@TSSOP20 [SA026]  
MC9S08SH4VTJ@TSSOP20(auto trim) [SA026]  
MC9S08SH4VTJE@TSSOP20 [SA026]  
MC9S08SH4VTJE@TSSOP20(auto trim) [SA026]  
MC9S08SH4VWJ@SOIC20 [SA404]  
MC9S08SH4VWJ@SOIC20(auto trim) [SA404]  
MC9S08SH4VWJE@SOIC20 [SA404]  
MC9S08SH4VWJE@SOIC20(auto trim) [SA404]  
MC9S08SH8CPJ MC9S08SH8CPJ(auto trim)  
MC9S08SH8CPJE MC9S08SH8CPJE(auto trim)  
MC9S08SH8CSC@SOIC8 [SA602]  
MC9S08SH8CSC@SOIC8(auto trim) [SA602]  
MC9S08SH8CSCE@SOIC8 [SA602]  
MC9S08SH8CSCE@SOIC8(auto trim) [SA602]  
MC9S08SH8CTG@TSSOP16 [SA026]  
MC9S08SH8CTG@TSSOP16(auto trim) [SA026]

MC9S08SH8CTGE@TSSOP16 [SA026]  
MC9S08SH8CTGE@TSSOP16(auto trim) [SA026]  
MC9S08SH8CTJ@TSSOP20 [SA026]  
MC9S08SH8CTJ@TSSOP20(auto trim) [SA026]  
MC9S08SH8CTJE@TSSOP20 [SA026]  
MC9S08SH8CTJE@TSSOP20(auto trim) [SA026]  
MC9S08SH8CWJ@SOIC20 [SA404]  
MC9S08SH8CWJ@SOIC20(auto trim) [SA404]  
MC9S08SH8CWJE@SOIC20 [SA404]  
MC9S08SH8CWJE@SOIC20(auto trim) [SA404]  
MC9S08SH8MPJ MC9S08SH8MPJ(auto trim)  
MC9S08SH8MPJE MC9S08SH8MPJE(auto trim)  
MC9S08SH8MSC@SOIC8 [SA602]  
MC9S08SH8MSC@SOIC8(auto trim) [SA602]  
MC9S08SH8MSCE@SOIC8 [SA602]  
MC9S08SH8MSCE@SOIC8(auto trim) [SA602]  
MC9S08SH8MTG@TSSOP16 [SA026]  
MC9S08SH8MTG@TSSOP16(auto trim) [SA026]  
MC9S08SH8MTGE@TSSOP16 [SA026]  
MC9S08SH8MTGE@TSSOP16(auto trim) [SA026]  
MC9S08SH8MTJ@TSSOP20 [SA026]  
MC9S08SH8MTJ@TSSOP20(auto trim) [SA026]  
MC9S08SH8MTJE@TSSOP20 [SA026]  
MC9S08SH8MTJE@TSSOP20(auto trim) [SA026]  
MC9S08SH8MWJ@SOIC20 [SA404]  
MC9S08SH8MWJ@SOIC20(auto trim) [SA404]  
MC9S08SH8MWJE@SOIC20 [SA404]  
MC9S08SH8MWJE@SOIC20(auto trim) [SA404]  
MC9S08SH8VPJ MC9S08SH8VPJ(auto trim)  
MC9S08SH8VPJE MC9S08SH8VPJE(auto trim)  
MC9S08SH8VSC@SOIC8 [SA602]  
MC9S08SH8VSC@SOIC8(auto trim) [SA602]  
MC9S08SH8VSCE@SOIC8 [SA602]  
MC9S08SH8VSCE@SOIC8(auto trim) [SA602]  
MC9S08SH8VTG@TSSOP16 [SA026]  
MC9S08SH8VTG@TSSOP16(auto trim) [SA026]  
MC9S08SH8VTGE@TSSOP16 [SA026]  
MC9S08SH8VTGE@TSSOP16(auto trim) [SA026]  
MC9S08SH8VTJ@TSSOP20 [SA026]  
MC9S08SH8VTJ@TSSOP20(auto trim) [SA026]  
MC9S08SH8VTJE@TSSOP20 [SA026]  
MC9S08SH8VTJE@TSSOP20(auto trim) [SA026]  
MC9S08SH8VWJ@SOIC20 [SA404]  
MC9S08SH8VWJ@SOIC20(auto trim) [SA404]  
MC9S08SH8VWJE@SOIC20 [SA404]  
MC9S08SH8VWJE@SOIC20(auto trim) [SA404]  
MC9S08SL16CTJ@TSSOP20 [SA026] MC9S08SL16CTJE@TSSOP20 [SA026]  
MC9S08SL16CTL@TSSOP28 [SA643] MC9S08SL16CTLE@TSSOP28 [SA643]  
MC9S08SL16MTJ@TSSOP20 [SA026] MC9S08SL16MTJE@TSSOP20 [SA026]  
MC9S08SL16MTL@TSSOP28 [SA643] MC9S08SL16MTLE@TSSOP28 [SA643]  
MC9S08SL16VTJ@TSSOP20 [SA026] MC9S08SL16VTJE@TSSOP20 [SA026]  
MC9S08SL16VTL@TSSOP28 [SA643] MC9S08SL16VTLE@TSSOP28 [SA643]  
MC9S08SL8CTJ@TSSOP20 [SA026] MC9S08SL8CTJE@TSSOP20 [SA026]

MC9S08SL8CTL@TSSOP28 [SA643]	MC9S08SL8CTLE@TSSOP28 [SA643]
MC9S08SL8MTJ@TSSOP20 [SA026]	MC9S08SL8MTJE@TSSOP20 [SA026]
MC9S08SL8MTL@TSSOP28 [SA643]	MC9S08SL8MTLE@TSSOP28 [SA643]
MC9S08SL8VTJ@TSSOP20 [SA026]	MC9S08SL8VTJE@TSSOP20 [SA026]
MC9S08SL8VTL@TSSOP28 [SA643]	MC9S08SL8VTLE@TSSOP28 [SA643]
MC9S08SV16CBM@SDIP32 [SA653]	MC9S08SV16CLC@LQFP32 [SA636]
MC9S08SV16MBM@SDIP32 [SA653]	MC9S08SV16MLC@LQFP32 [SA636]
MC9S08SV16VBM@SDIP32 [SA653]	MC9S08SV16VLC@LQFP32 [SA636]
MC9S08SV8CBM@SDIP32 [SA653]	MC9S08SV8CLC@LQFP32 [SA636]
MC9S08SV8MBM@SDIP32 [SA653]	MC9S08SV8MLC@LQFP32 [SA636]
MC9S08SV8VBM@SDIP32 [SA653]	MC9S08SV8VLC@LQFP32 [SA636]
PC9S08SG4CSC@SOIC8 [SA602]	PC9S08SG4CSCE@SOIC8 [SA602]
PC9S08SG4CTG@TSSOP16 [SA026]	PC9S08SG4CTGE@TSSOP16 [SA026]
PC9S08SG4CTJ@TSSOP20 [SA026]	PC9S08SG4CTJE@TSSOP20 [SA026]
PC9S08SG4MSC@SOIC8 [SA602]	PC9S08SG4MSCE@SOIC8 [SA602]
PC9S08SG4MTG@TSSOP16 [SA026]	PC9S08SG4MTGE@TSSOP16 [SA026]
PC9S08SG4MTJ@TSSOP20 [SA026]	PC9S08SG4MTJE@TSSOP20 [SA026]
PC9S08SG4VSC@SOIC8 [SA602]	PC9S08SG4VSCE@SOIC8 [SA602]
PC9S08SG4VTG@TSSOP16 [SA026]	PC9S08SG4VTGE@TSSOP16 [SA026]
PC9S08SG4VTJ@TSSOP20 [SA026]	PC9S08SG4VTJE@TSSOP20 [SA026]
PC9S08SG8CSC@SOIC8 [SA602]	PC9S08SG8CSCE@SOIC8 [SA602]
PC9S08SG8CTG@TSSOP16 [SA026]	PC9S08SG8CTGE@TSSOP16 [SA026]
PC9S08SG8CTJ@TSSOP20 [SA026]	PC9S08SG8CTJE@TSSOP20 [SA026]
PC9S08SG8MSC@SOIC8 [SA602]	PC9S08SG8MSCE@SOIC8 [SA602]
PC9S08SG8MTG@TSSOP16 [SA026]	PC9S08SG8MTGE@TSSOP16 [SA026]
PC9S08SG8MTJ@TSSOP20 [SA026]	PC9S08SG8MTJE@TSSOP20 [SA026]
PC9S08SG8VSC@SOIC8 [SA602]	PC9S08SG8VSCE@SOIC8 [SA602]
PC9S08SG8VTG@TSSOP16 [SA026]	PC9S08SG8VTGE@TSSOP16 [SA026]
PC9S08SG8VTJ@TSSOP20 [SA026]	PC9S08SG8VTJE@TSSOP20 [SA026]
PC9S08SH4CPJ	PC9S08SH4CPJ(auto trim)
PC9S08SH4CPJE	PC9S08SH4CPJE(auto trim)
PC9S08SH4CSC@SOIC8 [SA602]	
PC9S08SH4CSC@SOIC8(auto trim) [SA602]	
PC9S08SH4CSCE@SOIC8 [SA602]	
PC9S08SH4CSCE@SOIC8(auto trim) [SA602]	
PC9S08SH4CTG@TSSOP16 [SA026]	
PC9S08SH4CTG@TSSOP16(auto trim) [SA026]	
PC9S08SH4CTGE@TSSOP16 [SA026]	
PC9S08SH4CTGE@TSSOP16(auto trim) [SA026]	
PC9S08SH4CTJ@TSSOP20 [SA026]	
PC9S08SH4CTJ@TSSOP20(auto trim) [SA026]	
PC9S08SH4CTJE@TSSOP20 [SA026]	
PC9S08SH4CTJE@TSSOP20(auto trim) [SA026]	
PC9S08SH4CWJ@SOIC20 [SA404]	
PC9S08SH4CWJ@SOIC20(auto trim) [SA404]	
PC9S08SH4CWJE@SOIC20 [SA404]	
PC9S08SH4CWJE@SOIC20(auto trim) [SA404]	
PC9S08SH4MPJ	PC9S08SH4MPJ(auto trim)
PC9S08SH4MPJE	PC9S08SH4MPJE(auto trim)
PC9S08SH4MSC@SOIC8 [SA602]	
PC9S08SH4MSC@SOIC8(auto trim) [SA602]	
PC9S08SH4MSCE@SOIC8 [SA602]	
PC9S08SH4MSCE@SOIC8(auto trim) [SA602]	

PC9S08SH4MTG@TSSOP16 [SA026]  
PC9S08SH4MTG@TSSOP16(auto trim) [SA026]  
PC9S08SH4MTGE@TSSOP16 [SA026]  
PC9S08SH4MTGE@TSSOP16(auto trim) [SA026]  
PC9S08SH4MTJ@TSSOP20 [SA026]  
PC9S08SH4MTJ@TSSOP20(auto trim) [SA026]  
PC9S08SH4MTJE@TSSOP20 [SA026]  
PC9S08SH4MTJE@TSSOP20(auto trim) [SA026]  
PC9S08SH4MWJ@SOIC20 [SA404]  
PC9S08SH4MWJ@SOIC20(auto trim) [SA404]  
PC9S08SH4MWJE@SOIC20 [SA404]  
PC9S08SH4MWJE@SOIC20(auto trim) [SA404]  
PC9S08SH4VPJ PC9S08SH4VPJ(auto trim)  
PC9S08SH4VPJE PC9S08SH4VPJE(auto trim)  
PC9S08SH4VSC@SOIC8 [SA602]  
PC9S08SH4VSC@SOIC8(auto trim) [SA602]  
PC9S08SH4VSCE@SOIC8 [SA602]  
PC9S08SH4VSCE@SOIC8(auto trim) [SA602]  
PC9S08SH4VTG@TSSOP16 [SA026]  
PC9S08SH4VTG@TSSOP16(auto trim) [SA026]  
PC9S08SH4VTGE@TSSOP16 [SA026]  
PC9S08SH4VTGE@TSSOP16(auto trim) [SA026]  
PC9S08SH4VTJ@TSSOP20 [SA026]  
PC9S08SH4VTJ@TSSOP20(auto trim) [SA026]  
PC9S08SH4VTJE@TSSOP20 [SA026]  
PC9S08SH4VTJE@TSSOP20(auto trim) [SA026]  
PC9S08SH4VWJ@SOIC20 [SA404]  
PC9S08SH4VWJ@SOIC20(auto trim) [SA404]  
PC9S08SH4VWJE@SOIC20 [SA404]  
PC9S08SH4VWJE@SOIC20(auto trim) [SA404]  
PC9S08SH8CPJ PC9S08SH8CPJ(auto trim)  
PC9S08SH8CPJE PC9S08SH8CPJE(auto trim)  
PC9S08SH8CSC@SOIC8 [SA602]  
PC9S08SH8CSC@SOIC8(auto trim) [SA602]  
PC9S08SH8CSCE@SOIC8 [SA602]  
PC9S08SH8CSCE@SOIC8(auto trim) [SA602]  
PC9S08SH8CTG@TSSOP16 [SA026]  
PC9S08SH8CTG@TSSOP16(auto trim) [SA026]  
PC9S08SH8CTGE@TSSOP16 [SA026]  
PC9S08SH8CTGE@TSSOP16(auto trim) [SA026]  
PC9S08SH8CTJ@TSSOP20 [SA026]  
PC9S08SH8CTJ@TSSOP20(auto trim) [SA026]  
PC9S08SH8CTJE@TSSOP20 [SA026]  
PC9S08SH8CTJE@TSSOP20(auto trim) [SA026]  
PC9S08SH8CWJ@SOIC20 [SA404]  
PC9S08SH8CWJ@SOIC20(auto trim) [SA404]  
PC9S08SH8CWJE@SOIC20 [SA404]  
PC9S08SH8CWJE@SOIC20(auto trim) [SA404]  
PC9S08SH8MPJ PC9S08SH8MPJ(auto trim)  
PC9S08SH8MPJE PC9S08SH8MPJE(auto trim)  
PC9S08SH8MSC@SOIC8 [SA602]  
PC9S08SH8MSC@SOIC8(auto trim) [SA602]  
PC9S08SH8MSCE@SOIC8 [SA602]

PC9S08SH8MSCE@SOIC8(auto trim) [SA602]  
PC9S08SH8MTG@TSSOP16 [SA026]  
PC9S08SH8MTG@TSSOP16(auto trim) [SA026]  
PC9S08SH8MTGE@TSSOP16 [SA026]  
PC9S08SH8MTGE@TSSOP16(auto trim) [SA026]  
PC9S08SH8MTJ@TSSOP20 [SA026]  
PC9S08SH8MTJ@TSSOP20(auto trim) [SA026]  
PC9S08SH8MTJE@TSSOP20 [SA026]  
PC9S08SH8MTJE@TSSOP20(auto trim) [SA026]  
PC9S08SH8MWJ@SOIC20 [SA404]  
PC9S08SH8MWJ@SOIC20(auto trim) [SA404]  
PC9S08SH8MWJE@SOIC20 [SA404]  
PC9S08SH8MWJE@SOIC20(auto trim) [SA404]  
PC9S08SH8VPJ PC9S08SH8VPJ(auto trim)  
PC9S08SH8VPJE PC9S08SH8VPJE(auto trim)  
PC9S08SH8VSC@SOIC8 [SA602]  
PC9S08SH8VSC@SOIC8(auto trim) [SA602]  
PC9S08SH8VSCE@SOIC8 [SA602]  
PC9S08SH8VSCE@SOIC8(auto trim) [SA602]  
PC9S08SH8VTG@TSSOP16 [SA026]  
PC9S08SH8VTG@TSSOP16(auto trim) [SA026]  
PC9S08SH8VTGE@TSSOP16 [SA026]  
PC9S08SH8VTGE@TSSOP16(auto trim) [SA026]  
PC9S08SH8VTJ@TSSOP20 [SA026]  
PC9S08SH8VTJ@TSSOP20(auto trim) [SA026]  
PC9S08SH8VTJE@TSSOP20 [SA026]  
PC9S08SH8VTJE@TSSOP20(auto trim) [SA026]  
PC9S08SH8VWJ@SOIC20 [SA404]  
PC9S08SH8VWJ@SOIC20(auto trim) [SA404]  
PC9S08SH8VWJE@SOIC20 [SA404]  
PC9S08SH8VWJE@SOIC20(auto trim) [SA404]  
S9S08AW16ACLM@QFP32 [SA636]  
S9S08AW16ACLS@QFP44 [SA245A-B4805]  
S9S08AW16ACLS@QFP44(\*) [\$\$\$\$\$\$] S9S08AW16AMLM@QFP32 [SA636]  
S9S08AW16AMLS@QFP44 [SA245A-B4805]  
S9S08AW16AMLS@QFP44(\*) [\$\$\$\$\$\$] S9S08AW16AVFT@QFN48 [SA696]  
S9S08AW16AVLM@QFP32 [SA636]  
S9S08AW16AVLS@QFP44 [SA245A-B4805]  
S9S08AW16AVLS@QFP44(\*) [\$\$\$\$\$\$] S9S08AW8ACLM@QFP32 [SA636]  
S9S08AW8ACLS@QFP44 [SA245A-B4805]  
S9S08AW8ACLS@QFP44(\*) [\$\$\$\$\$\$] S9S08AW8AMFT@QFN48 [SA696]  
S9S08AW8AMLM@QFP32 [SA636]  
S9S08AW8AMLS@QFP44 [SA245A-B4805]  
S9S08AW8AMLS@QFP44(\*) [\$\$\$\$\$\$] S9S08AW8AVLM@QFP32 [SA636]  
S9S08AW8AVLS@QFP44 [SA245A-B4805]  
S9S08AW8AVLS@QFP44(\*) [\$\$\$\$\$\$] S9S08SG4CSC@SOIC8 [SA602]  
S9S08SG4CSCE@SOIC8 [SA602] S9S08SG4CTG@TSSOP16 [SA026]  
S9S08SG4CTGE@TSSOP16 [SA026] S9S08SG4CTJ@TSSOP20 [SA026]  
S9S08SG4CTJE@TSSOP20 [SA026] S9S08SG4MSC@SOIC8 [SA602]  
S9S08SG4MSCE@SOIC8 [SA602] S9S08SG4MTG@TSSOP16 [SA026]  
S9S08SG4MTGE@TSSOP16 [SA026] S9S08SG4MTJ@TSSOP20 [SA026]  
S9S08SG4MTJE@TSSOP20 [SA026] S9S08SG4VSC@SOIC8 [SA602]  
S9S08SG4VSCE@SOIC8 [SA602] S9S08SG4VTG@TSSOP16 [SA026]

S9S08SG4VTGE@TSSOP16 [SA026]                    S9S08SG4VTJ@TSSOP20 [SA026]  
S9S08SG4VTJE@TSSOP20 [SA026]                    S9S08SG8CSC@SOIC8 [SA602]  
S9S08SG8CSCE@SOIC8 [SA602]                    S9S08SG8CTG@TSSOP16 [SA026]  
S9S08SG8CTGE@TSSOP16 [SA026]                    S9S08SG8CTJ@TSSOP20 [SA026]  
S9S08SG8CTJE@TSSOP20 [SA026]                    S9S08SG8MSC@SOIC8 [SA602]  
S9S08SG8MSCE@SOIC8 [SA602]                    S9S08SG8MTG@TSSOP16 [SA026]  
S9S08SG8MTGE@TSSOP16 [SA026]                    S9S08SG8MTJ@TSSOP20 [SA026]  
S9S08SG8MTJE@TSSOP20 [SA026]                    S9S08SG8VSC@SOIC8 [SA602]  
S9S08SG8VSCE@SOIC8 [SA602]                    S9S08SG8VTG@TSSOP16 [SA026]  
S9S08SG8VTGE@TSSOP16 [SA026]                    S9S08SG8VTJ@TSSOP20 [SA026]  
S9S08SG8VTJE@TSSOP20 [SA026]                    S9S08SH4CPJ  
S9S08SH4CPJ(auto trim)                    S9S08SH4CPJE  
S9S08SH4CPJE(auto trim)                    S9S08SH4CSC@SOIC8 [SA602]  
S9S08SH4CSC@SOIC8(auto trim) [SA602]  
S9S08SH4CSCE@SOIC8 [SA602]  
S9S08SH4CSCE@SOIC8(auto trim) [SA602]  
S9S08SH4CTG@TSSOP16 [SA026]  
S9S08SH4CTG@TSSOP16(auto trim) [SA026]  
S9S08SH4CTGE@TSSOP16 [SA026]  
S9S08SH4CTGE@TSSOP16(auto trim) [SA026]  
S9S08SH4CTJ@TSSOP20 [SA026]  
S9S08SH4CTJ@TSSOP20(auto trim) [SA026]  
S9S08SH4CTJE@TSSOP20 [SA026]  
S9S08SH4CTJE@TSSOP20(auto trim) [SA026]  
S9S08SH4CWJ@SOIC20 [SA404]  
S9S08SH4CWJ@SOIC20(auto trim) [SA404]  
S9S08SH4CWJE@SOIC20 [SA404]  
S9S08SH4CWJE@SOIC20(auto trim) [SA404]  
S9S08SH4MPJ                    S9S08SH4MPJ(auto trim)  
S9S08SH4MPJE                    S9S08SH4MPJE(auto trim)  
S9S08SH4MSC@SOIC8 [SA602]  
S9S08SH4MSC@SOIC8(auto trim) [SA602]  
S9S08SH4MSCE@SOIC8 [SA602]  
S9S08SH4MSCE@SOIC8(auto trim) [SA602]  
S9S08SH4MTG@TSSOP16 [SA026]  
S9S08SH4MTG@TSSOP16(auto trim) [SA026]  
S9S08SH4MTGE@TSSOP16 [SA026]  
S9S08SH4MTGE@TSSOP16(auto trim) [SA026]  
S9S08SH4MTJ@TSSOP20 [SA026]  
S9S08SH4MTJ@TSSOP20(auto trim) [SA026]  
S9S08SH4MTJE@TSSOP20 [SA026]  
S9S08SH4MTJE@TSSOP20(auto trim) [SA026]  
S9S08SH4MWJ@SOIC20 [SA404]  
S9S08SH4MWJ@SOIC20(auto trim) [SA404]  
S9S08SH4MWJE@SOIC20 [SA404]  
S9S08SH4MWJE@SOIC20(auto trim) [SA404]  
S9S08SH4VPJ                    S9S08SH4VPJ(auto trim)  
S9S08SH4VPJE                    S9S08SH4VPJE(auto trim)  
S9S08SH4VSC@SOIC8 [SA602]  
S9S08SH4VSC@SOIC8(auto trim) [SA602]  
S9S08SH4VSCE@SOIC8 [SA602]  
S9S08SH4VSCE@SOIC8(auto trim) [SA602]  
S9S08SH4VTG@TSSOP16 [SA026]

S9S08SH4VTG@TSSOP16(auto trim) [SA026]  
S9S08SH4VTGE@TSSOP16 [SA026]  
S9S08SH4VTGE@TSSOP16(auto trim) [SA026]  
S9S08SH4VTJ@TSSOP20 [SA026]  
S9S08SH4VTJ@TSSOP20(auto trim) [SA026]  
S9S08SH4VTJE@TSSOP20 [SA026]  
S9S08SH4VTJE@TSSOP20(auto trim) [SA026]  
S9S08SH4VWJ@SOIC20 [SA404]  
S9S08SH4VWJ@SOIC20(auto trim) [SA404]  
S9S08SH4VWJE@SOIC20 [SA404]  
S9S08SH4VWJE@SOIC20(auto trim) [SA404]  
S9S08SH8CPJ S9S08SH8CPJ(auto trim)  
S9S08SH8CPJE S9S08SH8CPJE(auto trim)  
S9S08SH8CSC@SOIC8 [SA602]  
S9S08SH8CSC@SOIC8(auto trim) [SA602]  
S9S08SH8CSCE@SOIC8 [SA602]  
S9S08SH8CSCE@SOIC8(auto trim) [SA602]  
S9S08SH8CTG@TSSOP16 [SA026]  
S9S08SH8CTG@TSSOP16(auto trim) [SA026]  
S9S08SH8CTGE@TSSOP16 [SA026]  
S9S08SH8CTGE@TSSOP16(auto trim) [SA026]  
S9S08SH8CTJ@TSSOP20 [SA026]  
S9S08SH8CTJ@TSSOP20(auto trim) [SA026]  
S9S08SH8CTJE@TSSOP20 [SA026]  
S9S08SH8CTJE@TSSOP20(auto trim) [SA026]  
S9S08SH8CWJ@SOIC20 [SA404]  
S9S08SH8CWJ@SOIC20(auto trim) [SA404]  
S9S08SH8CWJE@SOIC20 [SA404]  
S9S08SH8CWJE@SOIC20(auto trim) [SA404]  
S9S08SH8MPJ S9S08SH8MPJ(auto trim)  
S9S08SH8MPJE S9S08SH8MPJE(auto trim)  
S9S08SH8MSC@SOIC8 [SA602]  
S9S08SH8MSC@SOIC8(auto trim) [SA602]  
S9S08SH8MSCE@SOIC8 [SA602]  
S9S08SH8MSCE@SOIC8(auto trim) [SA602]  
S9S08SH8MTG@TSSOP16 [SA026]  
S9S08SH8MTG@TSSOP16(auto trim) [SA026]  
S9S08SH8MTGE@TSSOP16 [SA026]  
S9S08SH8MTGE@TSSOP16(auto trim) [SA026]  
S9S08SH8MTJ@TSSOP20 [SA026]  
S9S08SH8MTJ@TSSOP20(auto trim) [SA026]  
S9S08SH8MTJE@TSSOP20 [SA026]  
S9S08SH8MTJE@TSSOP20(auto trim) [SA026]  
S9S08SH8MWJ@SOIC20 [SA404]  
S9S08SH8MWJ@SOIC20(auto trim) [SA404]  
S9S08SH8MWJE@SOIC20 [SA404]  
S9S08SH8MWJE@SOIC20(auto trim) [SA404]  
S9S08SH8VPJ S9S08SH8VPJ(auto trim)  
S9S08SH8VPJE S9S08SH8VPJE(auto trim)  
S9S08SH8VSC@SOIC8 [SA602]  
S9S08SH8VSC@SOIC8(auto trim) [SA602]  
S9S08SH8VSCE@SOIC8 [SA602]  
S9S08SH8VSCE@SOIC8(auto trim) [SA602]

S9S08SH8VTG@TSSOP16 [SA026]  
S9S08SH8VTG@TSSOP16(auto trim) [SA026]  
S9S08SH8VTGE@TSSOP16 [SA026]  
S9S08SH8VTGE@TSSOP16(auto trim) [SA026]  
S9S08SH8VTJ@TSSOP20 [SA026]  
S9S08SH8VTJ@TSSOP20(auto trim) [SA026]  
S9S08SH8VTJE@TSSOP20 [SA026]  
S9S08SH8VTJE@TSSOP20(auto trim) [SA026]  
S9S08SH8VWJ@SOIC20 [SA404]  
S9S08SH8VWJ@SOIC20(auto trim) [SA404]  
S9S08SH8VWJE@SOIC20 [SA404]  
S9S08SH8VWJE@SOIC20(auto trim) [SA404]

## Fremont Micro Devices

### E (E) PROM/FRAM/NVRAM

FT24C02	FT24C02@SOP8 [SA602A]
FT24C02@TSSOP8 [SA643]	FT24C02A
FT24C02A@SOP8 [SA602A]	FT24C02A@TSSOP8 [SA643]
FT24C04	FT24C04@SOP8 [SA602A]
FT24C04@TSSOP8 [SA643]	FT24C04A
FT24C04A@SOP8 [SA602A]	FT24C04A@TSSOP8 [SA643]
FT24C08	FT24C08@SOP8 [SA602A]
FT24C08@TSSOP8 [SA643]	FT24C08A
FT24C08A@SOP8 [SA602A]	FT24C08A@TSSOP8 [SA643]
FT24C128	FT24C128@SOP8 [SA602A]
FT24C128@TSSOP8 [SA643]	FT24C128A
FT24C128A@SOP8 [SA602A]	FT24C128A@TSSOP8 [SA643]
FT24C16	FT24C16@SOP8 [SA602A]
FT24C16@TSSOP8 [SA643]	FT24C16A
FT24C16A@SOP8 [SA602A]	FT24C16A@TSSOP8 [SA643]
FT24C256	FT24C256@SOP8 [SA602A]
FT24C256@TSSOP8 [SA643]	FT24C256A
FT24C256A@SOP8 [SA602A]	FT24C256A@TSSOP8 [SA643]
FT24C32	FT24C32@SOP8 [SA602A]
FT24C32@TSSOP8 [SA643]	FT24C32A
FT24C32A@SOP8 [SA602A]	FT24C32A@TSSOP8 [SA643]
FT24C512A	FT24C512A@SOP8 [SA602A]
FT24C512A@TSSOP8 [SA643]	FT24C64
FT24C64@SOP8 [SA602A]	FT24C64@TSSOP8 [SA643]
FT24C64A	FT24C64A@SOP8 [SA602A]
FT24C64A@TSSOP8 [SA643]	FT25C016
FT25C016@SOIC8 [SA602A]	FT25C016@TSSOP8 [SA643]
FT25C016A	FT25C016A@SOIC8 [SA602A]
FT25C016A@TSSOP8 [SA643]	FT25C064
FT25C064@SOIC8 [SA602A]	FT25C064@TSSOP8 [SA643]
FT25C064A	FT25C064A@SOIC8 [SA602A]
FT25C064A@TSSOP8 [SA643]	FT25H16
FT25H16@SOP8 (150mil) [SA602A]	FT25H16@SOP8 (200mil) [SA605B]
FT25H16@VSOP8 [SA605B]	FT34C02
FT34C02@SOP8 [SA602A]	FT34C02@TSSOP8 [SA643]

FT34C02A  
FT34C02A@TSSOP8 [SA643]  
FT93C46 (08bit)@SOP8 [SA602A]  
FT93C46 (16bit)  
FT93C46 (16bit)@TSSOP8 [SA643]  
FT93C46A (08bit)@SOP8 [SA602A]  
FT93C46A (16bit)  
FT93C46A (16bit)@TSSOP8 [SA643]  
FT93C56 (08bit)@SOP8 [SA602A]  
FT93C56 (16bit)  
FT93C56 (16bit)@TSSOP8 [SA643]  
FT93C56A (08bit)@SOP8 [SA602A]  
FT93C56A (16bit)  
FT93C56A (16bit)@TSSOP8 [SA643]  
FT93C66 (08bit)@SOP8 [SA602A]  
FT93C66 (16bit)  
FT93C66 (16bit)@TSSOP8 [SA643]  
FT93C66A (08bit)@SOP8 [SA602A]  
FT93C66A (16bit)  
FT93C66A (16bit)@TSSOP8 [SA643]  
FT93C86 (08bit)@SOP8 [SA602A]  
FT93C86 (16bit)  
FT93C86 (16bit)@TSSOP8 [SA643]  
FT93C86A (08bit)@SOP8 [SA602A]  
FT93C86A (16bit)  
FT93C86A (16bit)@TSSOP8 [SA643]

FT34C02A@SOP8 [SA602A]  
FT93C46 (08bit)  
FT93C46 (08bit)@TSSOP8 [SA643]  
FT93C46 (16bit)@SOP8 [SA602A]  
FT93C46A (08bit)  
FT93C46A (08bit)@TSSOP8 [SA643]  
FT93C46A (16bit)@SOP8 [SA602A]  
FT93C56 (08bit)  
FT93C56 (08bit)@TSSOP8 [SA643]  
FT93C56 (16bit)@SOP8 [SA602A]  
FT93C56A (08bit)  
FT93C56A (08bit)@TSSOP8 [SA643]  
FT93C56A (16bit)@SOP8 [SA602A]  
FT93C66 (08bit)  
FT93C66 (08bit)@TSSOP8 [SA643]  
FT93C66 (16bit)@SOP8 [SA602A]  
FT93C66A (08bit)  
FT93C66A (08bit)@TSSOP8 [SA643]  
FT93C66A (16bit)@SOP8 [SA602A]  
FT93C86 (08bit)  
FT93C86 (08bit)@TSSOP8 [SA643]  
FT93C86 (16bit)@SOP8 [SA602A]  
FT93C86A (08bit)  
FT93C86A (08bit)@TSSOP8 [SA643]  
FT93C86A (16bit)@SOP8 [SA602A]

## FUDAN

### E (E) PROM/FRAM/NVRAM

FM24C02A  
FM24C02A@TSSOP8 [SA643]  
FM24C02B@SOIC8 [SA602A]  
FM24C02C  
FM24C02C@TSSOP8 [SA643]  
FM24C02D@SOP8 [SA602A]  
FM24C04A  
FM24C04A@TSSOP8 [SA643]  
FM24C04B@SOIC8 [SA602A]  
FM24C04D  
FM24C04D@TSSOP8 [SA643]  
FM24C08A@SOP8 [SA602A]  
FM24C08B  
FM24C08B@SOIC8 [SA602A]  
FM24C08D  
FM24C08D@TSSOP8 [SA643]  
FM24C1024A@SOP8 [SA602A]  
FM24C128A  
FM24C128A@SOP8 [SA602A]  
FM24C128A@TSSOP8 [SA643]  
FM24C16A@SOIC8 [SA602A]

FM24C02A@SOIC8 [SA602A]  
FM24C02B  
FM24C02B@TSSOP8 [SA643]  
FM24C02C@SOP8 [SA602A]  
FM24C02D  
FM24C02D@TSSOP8 [SA643]  
FM24C04A@SOP8 [SA602A]  
FM24C04B  
FM24C04B@TSSOP8 [SA643]  
FM24C04D@SOP8 [SA602A]  
FM24C08A  
FM24C08A@TSSOP8 [SA643]  
FM24C08B (ISP)  
FM24C08B@TSSOP8 [SA643]  
FM24C08D@SOP8 [SA602A]  
FM24C1024A  
FM24C1024A@TSSOP8 [SA643]  
FM24C128A@MSOP8 [SA666]  
FM24C128A@TDFN8 [SA724]  
FM24C16A  
FM24C16A@TSSOP8 [SA643]

FM24C16B  
FM24C16B@TSSOP8 [SA643]  
FM24C16D@SOP8 [SA602A]  
FM24C256A  
FM24C256A@SOP8 [SA602A]  
FM24C256A@TSSOP8 [SA643]  
FM24C32A@SOIC8 [SA602A]  
FM24C512A  
FM24C512A@TSSOP8 [SA643]  
FM24C512D@SOP8 [SA602A]  
FM24C64A  
FM24C64A@TSSOP8 [SA643]  
FM25128@SOP8 [SA602A]  
FM25128@USON8 [SA724]  
FM25256@SOP8 [SA602A]  
FM25256@USON8 [SA724]  
FM25512@TSSOP8 [SA643]  
FM25F005@SOP8 [SA602A]  
FM25F005@TSSOP8 [SA643]  
FM25F01@TDFN8 [SA724]  
FM25F02@SOP8 (150mil) [SA602A]  
FM25F02@TDFN8 [SA683]  
FM25F02A@SOP8 (208mil) [SA605B]  
FM25F04@SOP8 (150mil) [SA602A]  
FM25F04@TDFN8 [SA683]  
FM25F04A@SOP8 (208mil) [SA605B]  
FM25Q08@SOP8 (150mil) [SA602A]  
FM25Q08@TDFN8 [SA683]  
FM25Q16@SOP8 (208mil) [SA605B]  
FM25Q32@SOP8 (150mil) [SA602A]  
FM25Q32@TDFN8 [SA683]  
FM93C46 (08bit)@SOP8 [SA602A]  
FM93C46 (08bit)@TSOT23-6L [SA717]  
FM93C46 (16bit)  
FM93C46 (16bit)@TDFN8 [SA724]  
FM93C46 (16bit)@TSSOP8 [SA643]  
FM93C56 (08bit)@SOP8 [SA602A]  
FM93C56 (08bit)@TSOT23-6L [SA717]  
FM93C56 (16bit)  
FM93C56 (16bit)@TDFN8 [SA724]  
FM93C56 (16bit)@TSSOP8 [SA643]  
FM93C66 (08bit)@SOP8 [SA602A]  
FM93C66 (08bit)@TSOT23-6L [SA717]  
FM93C66 (16bit)  
FM93C66 (16bit)@TDFN8 [SA724]  
FM93C66 (16bit)@TSSOP8 [SA643]

FM24C16B@SOIC8 [SA602A]  
FM24C16D  
FM24C16D@TSSOP8 [SA643]  
FM24C256A@MSOP8 [SA666]  
FM24C256A@TDFN8 [SA724]  
FM24C32A  
FM24C32A@TSSOP8 [SA643]  
FM24C512A@SOP8 [SA602A]  
FM24C512D  
FM24C512D@TSSOP8 [SA643]  
FM24C64A@SOIC8 [SA602A]  
FM25128  
FM25128@TSSOP8 [SA643]  
FM25256  
FM25256@TSSOP8 [SA643]  
FM25512@SOP8 [SA602A]  
FM25512@USON8 [SA724]  
FM25F005@TDFN8 [SA724]  
FM25F01@SOP8 [SA602A]  
FM25F01@TSSOP8 [SA643]  
FM25F02@SOP8 (208mil) [SA605B]  
FM25F02A@SOP8 (150mil) [SA602A]  
FM25F02A@TDFN8 [SA683]  
FM25F04@SOP8 (208mil) [SA605B]  
FM25F04A@SOP8 (150mil) [SA602A]  
FM25F04A@TDFN8 [SA683]  
FM25Q08@SOP8 (208mil) [SA605B]  
FM25Q16@SOP8 (150mil) [SA602A]  
FM25Q16@TDFN8 [SA683]  
FM25Q32@SOP8 (208mil) [SA605B]  
FM93C46 (08bit)  
FM93C46 (08bit)@TDFN8 [SA724]  
FM93C46 (08bit)@TSSOP8 [SA643]  
FM93C46 (16bit)@SOP8 [SA602A]  
FM93C46 (16bit)@TSOT23-6L [SA717]  
FM93C56 (08bit)  
FM93C56 (08bit)@TDFN8 [SA724]  
FM93C56 (08bit)@TSSOP8 [SA643]  
FM93C56 (16bit)@SOP8 [SA602A]  
FM93C56 (16bit)@TSOT23-6L [SA717]  
FM93C66 (08bit)  
FM93C66 (08bit)@TDFN8 [SA724]  
FM93C66 (08bit)@TSSOP8 [SA643]  
FM93C66 (16bit)@SOP8 [SA602A]  
FM93C66 (16bit)@TSOT23-6L [SA717]

## FUJITSU

### E (E) PROM/FRAM/NVRAM

MB85R256@SOP28 [SA630]

MB85R256@TSOP28 [SA643]

MB85R256A@SOP28 [SA630] MB85R256A@TSOP28 [SA643]  
MB85RC128 MB85RC128@SOIC8 [SA602A]  
MB85RC16 MB85RC16@SOIC8 [SA602A]  
MB85RC64 MB85RC64@SOIC8 [SA602A]  
MBM2212 MBM271001  
MBM271001@PLCC32 [SA015A1T] MBM271001@TSOP32 [SA410T-B4001]  
MBM27128 MBM27128@PLCC32 [SA015A1T]  
MBM2716 MBM2716H  
MBM27256 MBM27256@PLCC32 [SA015A1T]  
MBM2732 MBM2732A  
MBM2764 MBM2764@PLCC32 [SA015A1T]  
MBM27C1000 MBM27C1000@PLCC32 [SA015A1T]  
MBM27C1000@TSOP32 [SA410T-B4001] MBM27C1001  
MBM27C1001@PLCC32 [SA015A1T] MBM27C1001@TSOP32 [SA410T-B4001]  
MBM27C1024 MBM27C1024@PLCC44 [SA244]  
MBM27C128 MBM27C128@PLCC32 [SA015A1T]  
MBM27C128P MBM27C128P@PLCC32 [SA015A1T]  
MBM27C2000 MBM27C2000@PLCC32 [SA015A1T]  
MBM27C2000@TSOP32 [SA410T-B4001] MBM27C2001  
MBM27C2001@PLCC32 [SA015A1T] MBM27C2001@TSOP32 [SA410T-B4001]  
MBM27C2048 MBM27C256  
MBM27C256@PLCC32 [SA015A1T] MBM27C256A  
MBM27C256A@PLCC32 [SA015A1T] MBM27C256AP  
MBM27C256AP@PLCC32 [SA015A1T] MBM27C256H  
MBM27C256H@PLCC32 [SA015A1T] MBM27C32A  
MBM27C4001 MBM27C4001@PLCC32 [SA015A1T]  
MBM27C4001@TSOP32 [SA410T-B4001] MBM27C4096  
MBM27C512 MBM27C512@PLCC32 [SA015A1T]  
MBM27C512P MBM27C512P@PLCC32 [SA015A1T]  
MBM27C64 MBM27C64@PLCC32 [SA015A1T]  
MBM28C64 MBM28C65  
MBM28F010  
MBM28F010 (REVERSE)@TSOP32 [SA410T-B4001]  
MBM28F010@PLCC32 [SA015A1T] MBM28F010@SOP32 [SA438T]  
MBM28F010@TSOP32 [SA410T-B4001]  
MBM29DL161BD (REVERSE)@TSOP48 [SB247-B4806]  
MBM29DL161BD@TSOP48 [SB247-B4806]  
MBM29DL161BE (REVERSE)@TSOP48 [SB247-B4806]  
MBM29DL161BE@TSOP48 [SB247-B4806]  
MBM29DL161TD (REVERSE)@TSOP48 [SB247-B4806]  
MBM29DL161TD@TSOP48 [SB247-B4806]  
MBM29DL161TE (REVERSE)@TSOP48 [SB247-B4806]  
MBM29DL161TE@TSOP48 [SB247-B4806]  
MBM29DL162BD (REVERSE)@TSOP48 [SB247-B4806]  
MBM29DL162BD@TSOP48 [SB247-B4806]  
MBM29DL162BE (REVERSE)@TSOP48 [SB247-B4806]  
MBM29DL162BE@TSOP48 [SB247-B4806]  
MBM29DL162TD (REVERSE)@TSOP48 [SB247-B4806]  
MBM29DL162TD@TSOP48 [SB247-B4806]  
MBM29DL162TE (REVERSE)@TSOP48 [SB247-B4806]  
MBM29DL162TE@TSOP48 [SB247-B4806]  
MBM29DL163BD (REVERSE)@TSOP48 [SB247-B4806]  
MBM29DL163BD@TSOP48 [SB247-B4806]

MBM29DL163BE (REVERSE)@TSOP48 [SB247-B4806]  
MBM29DL163BE@TSOP48 [SB247-B4806]  
MBM29DL163TD (REVERSE)@TSOP48 [SB247-B4806]  
MBM29DL163TD@TSOP48 [SB247-B4806]  
MBM29DL163TE (REVERSE)@TSOP48 [SB247-B4806]  
MBM29DL163TE@TSOP48 [SB247-B4806]  
MBM29DL164BD (REVERSE)@TSOP48 [SB247-B4806]  
MBM29DL164BD@TSOP48 [SB247-B4806]  
MBM29DL164BE (REVERSE)@TSOP48 [SB247-B4806]  
MBM29DL164BE@TSOP48 [SB247-B4806]  
MBM29DL164TD (REVERSE)@TSOP48 [SB247-B4806]  
MBM29DL164TD@TSOP48 [SB247-B4806]  
MBM29DL164TE (REVERSE)@TSOP48 [SB247-B4806]  
MBM29DL164TE@TSOP48 [SB247-B4806]  
MBM29DL320BF@TSOP48 [SB247-B4806]  
MBM29DL320TF@TSOP48 [SB247-B4806]  
MBM29DL321BD (REVERSE)@TSOP48 [SB247-B4806]  
MBM29DL321BD@TSOP48 [SB247-B4806]  
MBM29DL321BE (REVERSE)@TSOP48 [SB247-B4806]  
MBM29DL321BE@TSOP48 [SB247-B4806]  
MBM29DL321TD (REVERSE)@TSOP48 [SB247-B4806]  
MBM29DL321TD@TSOP48 [SB247-B4806]  
MBM29DL321TE (REVERSE)@TSOP48 [SB247-B4806]  
MBM29DL321TE@TSOP48 [SB247-B4806]  
MBM29DL322BD (REVERSE)@TSOP48 [SB247-B4806]  
MBM29DL322BD@TSOP48 [SB247-B4806]  
MBM29DL322BE (REVERSE)@TSOP48 [SB247-B4806]  
MBM29DL322BE@TSOP48 [SB247-B4806]  
MBM29DL322TD (REVERSE)@TSOP48 [SB247-B4806]  
MBM29DL322TD@TSOP48 [SB247-B4806]  
MBM29DL322TE (REVERSE)@TSOP48 [SB247-B4806]  
MBM29DL322TE@TSOP48 [SB247-B4806]  
MBM29DL323BD (REVERSE)@TSOP48 [SB247-B4806]  
MBM29DL323BD@TSOP48 [SB247-B4806]  
MBM29DL323BE (REVERSE)@TSOP48 [SB247-B4806]  
MBM29DL323BE@TSOP48 [SB247-B4806]  
MBM29DL323BF@TSOP48 [SB247-B4806]  
MBM29DL323TD (REVERSE)@TSOP48 [SB247-B4806]  
MBM29DL323TD@TSOP48 [SB247-B4806]  
MBM29DL323TE (REVERSE)@TSOP48 [SB247-B4806]  
MBM29DL323TE@TSOP48 [SB247-B4806]  
MBM29DL323TF@TSOP48 [SB247-B4806]  
MBM29DL324BD (REVERSE)@TSOP48 [SB247-B4806]  
MBM29DL324BD@TSOP48 [SB247-B4806]  
MBM29DL324BE (REVERSE)@TSOP48 [SB247-B4806]  
MBM29DL324BE@TSOP48 [SB247-B4806]  
MBM29DL324TD (REVERSE)@TSOP48 [SB247-B4806]  
MBM29DL324TD@TSOP48 [SB247-B4806]  
MBM29DL324TE (REVERSE)@TSOP48 [SB247-B4806]  
MBM29DL324TE@TSOP48 [SB247-B4806]  
MBM29DL32BF@TSOP48 [SB247-B4806]      MBM29DL32TF@TSOP48 [SB247-B4806]  
MBM29DL34BF@TSOP48 [SB247-B4806]      MBM29DL34TF@TSOP48 [SB247-B4806]  
MBM29DL400BB@PSOP44 [SA638]

MBM29DL400BB@TSOP48 [SB247-B4806]  
MBM29DL400BC (REVERSE)@TSOP48 [SB247-B4806]  
MBM29DL400BC@PSOP44 [SA638]  
MBM29DL400BC@TSOP48 [SB247-B4806]  
MBM29DL400BT@PSOP44 [SA638]  
MBM29DL400BT@TSOP48 [SB247-B4806]  
MBM29DL400TC (REVERSE)@TSOP48 [SB247-B4806]  
MBM29DL400TC@PSOP44 [SA638]  
MBM29DL400TC@TSOP48 [SB247-B4806]  
MBM29DL640E (REVERSE)@TSOP48 [SB247-B4806]  
MBM29DL640E@TSOP48 [SB247-B4806] MBM29DL64DF@TSOP48 [SB247-B4806]  
MBM29DL800B@PSOP44 [SA638] MBM29DL800B@TSOP48 [SB247-B4806]  
MBM29DL800BA (REVERSE)@TSOP48 [SB247-B4806]  
MBM29DL800BA@PSOP44 [SA638]  
MBM29DL800BA@TSOP48 [SB247-B4806]  
MBM29DL800BB@PSOP44 [SA638]  
MBM29DL800BB@TSOP48 [SB247-B4806]  
MBM29DL800BT@PSOP44 [SA638]  
MBM29DL800BT@TSOP48 [SB247-B4806]  
MBM29DL800T@PSOP44 [SA638] MBM29DL800T@TSOP48 [SB247-B4806]  
MBM29DL800TA (REVERSE)@TSOP48 [SB247-B4806]  
MBM29DL800TA@PSOP44 [SA638]  
MBM29DL800TA@TSOP48 [SB247-B4806]  
MBM29DS163BE@TSOP48 [SB247-B4806]  
MBM29DS163TE@TSOP48 [SB247-B4806]  
MBM29F001B MBM29F001B@PLCC32 [SA015A1T]  
MBM29F001B@TSOP32 [SA410T-B4001] MBM29F001T  
MBM29F001T@PLCC32 [SA015A1T] MBM29F001T@TSOP32 [SA410T-B4001]  
MBM29F002B MBM29F002B@PLCC32 [SA015A1T]  
MBM29F002B@TSOP32 [SA410T-B4001] MBM29F002NB  
MBM29F002NB@PLCC32 [SA015A1T]  
MBM29F002NB@TSOP32 [SA410T-B4001]  
MBM29F002NT MBM29F002NT@PLCC32 [SA015A1T]  
MBM29F002NT@TSOP32 [SA410T-B4001]  
MBM29F002T MBM29F002T@PLCC32 [SA015A1T]  
MBM29F002T@TSOP32 [SA410T-B4001] MBM29F010  
MBM29F010@PLCC32 [SA015A1T] MBM29F010@TSOP32 [SA410T-B4001]  
MBM29F010A MBM29F010A@PLCC32 [SA015A1T]  
MBM29F010A@TSOP32 [SA410T-B4001] MBM29F016@PSOP44 [SA638]  
MBM29F016@TSOP40 [SA409T-B4002] MBM29F016@TSOP48 [SB247-B4806]  
MBM29F016A@PSOP44 [SA638] MBM29F016A@TSOP40 [SA409T-B4002]  
MBM29F016A@TSOP48 [SB247-B4806] MBM29F016B@PSOP44 [SA638]  
MBM29F016B@TSOP40 [SA409T-B4002] MBM29F016B@TSOP48 [SB247-B4806]  
MBM29F017A (REVERSE)@TSOP48 [SB247-B4806]  
MBM29F017A@TSOP48 [SB247-B4806] MBM29F017B@TSOP48 [SB247-B4806]  
MBM29F017D@TSOP40 [SA409T-B4002] MBM29F017D@TSOP48 [SB247-B4806]  
MBM29F032B@PSOP44 [SA638] MBM29F032B@TSOP40 [SA409T-B4002]  
MBM29F033C@TSOP40 [SA409T-B4002] MBM29F040  
MBM29F040@PLCC32 [SA015A1T] MBM29F040@TSOP32 [SA410T-B4001]  
MBM29F040B MBM29F040B@PLCC32 [SA015A1T]  
MBM29F040B@TSOP32 [SA410T-B4001] MBM29F040C@PLCC32 [SA015A1T]  
MBM29F040C@TSOP32 [SA410T-B4001] MBM29F080@PSOP44 [SA638]  
MBM29F080@TSOP40 [SA409T-B4002]

MBM29F080A (REVERSE)@TSOP40 [SA409T-B4002]  
MBM29F080A (REVERSE)@TSOP48 [SB247-B4806]  
MBM29F080A@PSOP44 [SA638] MBM29F080A@TSOP40 [SA409T-B4002]  
MBM29F080A@TSOP48 [SB247-B4806] MBM29F080B@PSOP44 [SA638]  
MBM29F080B@TSOP40 [SA409T-B4002] MBM29F100B@PSOP44 [SA638]  
MBM29F100B@TSOP48 [SB247-B4806] MBM29F100T@PSOP44 [SA638]  
MBM29F100T@TSOP48 [SB247-B4806]  
MBM29F160BE (REVERSE)@TSOP48 [SB247-B4806]  
MBM29F160BE@TSOP48 [SB247-B4806]  
MBM29F160TE (REVERSE)@TSOP48 [SB247-B4806]  
MBM29F160TE@TSOP48 [SB247-B4806] MBM29F200AB@PSOP44 [SA638]  
MBM29F200AB@TSOP48 [SB247-B4806] MBM29F200AT@PSOP44 [SA638]  
MBM29F200AT@TSOP48 [SB247-B4806] MBM29F200B@PSOP44 [SA638]  
MBM29F200B@TSOP48 [SB247-B4806]  
MBM29F200BC (REVERSE)@TSOP48 [SB247-B4806]  
MBM29F200BC@PSOP44 [SA638] MBM29F200BC@TSOP48 [SB247-B4806]  
MBM29F200T@PSOP44 [SA638] MBM29F200T@TSOP48 [SB247-B4806]  
MBM29F200TC (REVERSE)@TSOP48 [SB247-B4806]  
MBM29F200TC@PSOP44 [SA638] MBM29F200TC@TSOP48 [SB247-B4806]  
MBM29F400AB@PSOP44 [SA638] MBM29F400AB@TSOP48 [SB247-B4806]  
MBM29F400AT@PSOP44 [SA638] MBM29F400AT@TSOP48 [SB247-B4806]  
MBM29F400B@PSOP44 [SA638] MBM29F400B@TSOP48 [SB247-B4806]  
MBM29F400BB@PSOP44 [SA638] MBM29F400BB@TSOP48 [SB247-B4806]  
MBM29F400BC (REVERSE)@TSOP48 [SB247-B4806]  
MBM29F400BC@PSOP44 [SA638] MBM29F400BC@TSOP48 [SB247-B4806]  
MBM29F400BT@PSOP44 [SA638] MBM29F400BT@TSOP48 [SB247-B4806]  
MBM29F400T@PSOP44 [SA638] MBM29F400T@TSOP48 [SB247-B4806]  
MBM29F400TC (REVERSE)@TSOP48 [SB247-B4806]  
MBM29F400TC@PSOP44 [SA638] MBM29F400TC@TSOP48 [SB247-B4806]  
MBM29F800B@PSOP44 [SA638] MBM29F800B@TSOP48 [SB247-B4806]  
MBM29F800BA (REVERSE)@TSOP48 [SB247-B4806]  
MBM29F800BA@PSOP44 [SA638] MBM29F800BA@TSOP48 [SB247-B4806]  
MBM29F800BB@PSOP44 [SA638] MBM29F800BB@TSOP48 [SB247-B4806]  
MBM29F800BT@PSOP44 [SA638] MBM29F800BT@TSOP48 [SB247-B4806]  
MBM29F800T@PSOP44 [SA638] MBM29F800T@TSOP48 [SB247-B4806]  
MBM29F800TA (REVERSE)@TSOP48 [SB247-B4806]  
MBM29F800TA@PSOP44 [SA638] MBM29F800TA@TSOP48 [SB247-B4806]  
MBM29LL800B@TSOP48 [SB247-B4806]  
MBM29LL800BB@TSOP48 [SB247-B4806]  
MBM29LL800BT@TSOP48 [SB247-B4806]  
MBM29LL800T@TSOP48 [SB247-B4806] MBM29LV001B@PLCC32 [SA015A1T]  
MBM29LV001BB (REVERSE)@TSOP32 [SA410T-B4001]  
MBM29LV001BB@PLCC32 [SA015A1T]  
MBM29LV001BB@TSOP32 [SA410T-B4001]  
MBM29LV001BC (REVERSE)@TSOP32 [SA410T-B4001]  
MBM29LV001BC@PLCC32 [SA015A1T]  
MBM29LV001BC@TSOP32 [SA410T-B4001]  
MBM29LV001BT (REVERSE)@TSOP32 [SA410T-B4001]  
MBM29LV001BT@PLCC32 [SA015A1T]  
MBM29LV001BT@TSOP32 [SA410T-B4001]  
MBM29LV001T@TSOP32 [SA410T-B4001]  
MBM29LV001TC (REVERSE)@TSOP32 [SA410T-B4001]  
MBM29LV001TC@PLCC32 [SA015A1T]

MBM29LV001TC@TSOP32 [SA410T-B4001]  
MBM29LV002B@TSOP40 [SA409T-B4002]  
MBM29LV002T@TSOP40 [SA409T-B4002]  
MBM29LV004B@TSOP40 [SA409T-B4002]  
MBM29LV004BB@TSOP40 [SA409T-B4002]  
MBM29LV004BT@TSOP40 [SA409T-B4002]  
MBM29LV004T@TSOP40 [SA409T-B4002]  
MBM29LV008B@TSOP40 [SA409T-B4002]  
MBM29LV008BB@TSOP40 [SA409T-B4002]  
MBM29LV008BT@TSOP40 [SA409T-B4002]  
MBM29LV008T@TSOP40 [SA409T-B4002]  
MBM29LV016/B@TSOP40 [SA409T-B4002]  
MBM29LV016/T@TSOP40 [SA409T-B4002]  
MBM29LV016B@TSOP40 [SA409T-B4002]  
MBM29LV017@TSOP40 [SA409T-B4002]  
MBM29LV017B@TSOP40 [SA409T-B4002]  
MBM29LV017E@TSOP40 [SA409T-B4002]  
MBM29LV033C@TSOP40 [SA409T-B4002]  
MBM29LV080@TSOP40 [SA409T-B4002]  
MBM29LV080A@TSOP40 [SA409T-B4002]  
MBM29LV081@TSOP40 [SA409T-B4002]  
MBM29LV081B@TSOP40 [SA409T-B4002]  
MBM29LV116B@TSOP40 [SA409T-B4002]  
MBM29LV160B (REVERSE)@TSOP48 [SB247-B4806]  
MBM29LV160B@TSOP48 [SB247-B4806]  
MBM29LV160BE (REVERSE)@TSOP48 [SB247-B4806]  
MBM29LV160BE@PSOP44 [SA638]  
MBM29LV160BE@TSOP48 [SB247-B4806]  
MBM29LV160BM@TSOP48 [SB247-B4806]  
MBM29LV160T (REVERSE)@TSOP48 [SB247-B4806]  
MBM29LV160T@TSOP48 [SB247-B4806]  
MBM29LV160TE (REVERSE)@TSOP48 [SB247-B4806]  
MBM29LV160TE@PSOP44 [SA638]  
MBM29LV160TE@TSOP48 [SB247-B4806]  
MBM29LV160TM@TSOP48 [SB247-B4806]  
MBM29LV200B@PSOP44 [SA638] MBM29LV200B@TSOP48 [SB247-B4806]  
MBM29LV200BB@PSOP44 [SA638]  
MBM29LV200BB@TSOP48 [SB247-B4806]  
MBM29LV200BC (REVERSE)@TSOP48 [SB247-B4806]  
MBM29LV200BC@PSOP44 [SA638]  
MBM29LV200BC@TSOP48 [SB247-B4806]  
MBM29LV200BT@PSOP44 [SA638]  
MBM29LV200BT@TSOP48 [SB247-B4806]  
MBM29LV200T@PSOP44 [SA638] MBM29LV200T@TSOP48 [SB247-B4806]  
MBM29LV200TC (REVERSE)@TSOP48 [SB247-B4806]  
MBM29LV200TC@PSOP44 [SA638]  
MBM29LV200TC@TSOP48 [SB247-B4806]  
MBM29LV320BE (REVERSE)@TSOP48 [SB247-B4806]  
MBM29LV320BE@TSOP48 [SB247-B4806]  
MBM29LV320TE (REVERSE)@TSOP48 [SB247-B4806]  
MBM29LV320TE@TSOP48 [SB247-B4806]  
MBM29LV400B@PSOP44 [SA638] MBM29LV400B@TSOP48 [SB247-B4806]  
MBM29LV400BB@PSOP44 [SA638]

MBM29LV400BB@TSOP48 [SB247-B4806]  
MBM29LV400BC@PSOP44 [SA638]  
MBM29LV400BC@TSOP48 [SB247-B4806]  
MBM29LV400BT@PSOP44 [SA638]  
MBM29LV400BT@TSOP48 [SB247-B4806]  
MBM29LV400T@PSOP44 [SA638] MBM29LV400T@TSOP48 [SB247-B4806]  
MBM29LV400TC@PSOP44 [SA638]  
MBM29LV400TC@TSOP48 [SB247-B4806]  
MBM29LV650UE (REVERSE)@TSOP48 [SB247-B4806]  
MBM29LV650UE@TSOP48 [SB247-B4806]  
MBM29LV651UE (REVERSE)@TSOP48 [SB247-B4806]  
MBM29LV651UE@TSOP48 [SB247-B4806]  
MBM29LV800B@PSOP44 [SA638] MBM29LV800B@TSOP48 [SB247-B4806]  
MBM29LV800BA (REVERSE)@TSOP48 [SB247-B4806]  
MBM29LV800BA@PSOP44 [SA638]  
MBM29LV800BA@TSOP48 [SB247-B4806]  
MBM29LV800BB@PSOP44 [SA638]  
MBM29LV800BB@TSOP48 [SB247-B4806]  
MBM29LV800BE (REVERSE)@TSOP48 [SB247-B4806]  
MBM29LV800BE@PSOP44 [SA638]  
MBM29LV800BE@TSOP48 [SB247-B4806]  
MBM29LV800BT@PSOP44 [SA638]  
MBM29LV800BT@TSOP48 [SB247-B4806]  
MBM29LV800T@PSOP44 [SA638] MBM29LV800T@TSOP48 [SB247-B4806]  
MBM29LV800TA (REVERSE)@TSOP48 [SB247-B4806]  
MBM29LV800TA@PSOP44 [SA638]  
MBM29LV800TA@TSOP48 [SB247-B4806]  
MBM29LV800TE (REVERSE)@TSOP48 [SB247-B4806]  
MBM29LV800TE@PSOP44 [SA638]  
MBM29LV800TE@TSOP48 [SB247-B4806]  
MBM29PL160BD@PSOP44 [SA638]  
MBM29PL160BD@TSOP48 [SB247-B4806]  
MBM29PL160TD@PSOP44 [SA638]  
MBM29PL160TD@TSOP48 [SB247-B4806]  
MBM29PL32BM@TSOP48 [SB247-B4806] MBM29PL32TM@TSOP48 [SB247-B4806]  
MBM29PL64LM@TSOP48 [SB247-B4806] MBM29PL65LM@TSOP48 [SB247-B4806]  
MBM29SL160BD (REVERSE)@TSOP48 [SB247-B4806]  
MBM29SL160BD@TSOP48 [SB247-B4806]  
MBM29SL160TD (REVERSE)@TSOP48 [SB247-B4806]  
MBM29SL160TD@TSOP48 [SB247-B4806]  
MBM29SL800BD (REVERSE)@TSOP48 [SB247-B4806]  
MBM29SL800BD@TSOP48 [SB247-B4806]  
MBM29SL800TD (REVERSE)@TSOP48 [SB247-B4806]  
MBM29SL800TD@TSOP48 [SB247-B4806]

## DRAM & SRAM

MB81C78A

MB81C78A@SOIC28

## MICROCONTROLLER

MB89F202@SDIP32 [SA653]

MB89F202@SSOP34 [SA689]

MB89F202A@SDIP32 [SA653]  
MB89F202R@QFP32 [SA636]  
MB89F202R@SSOP34 [SA689]  
MB89F202RA@SDIP32 [SA653]  
MB95F202HAP@SDIP24 [SA653]  
MB95F202HP@SDIP24 [SA653]  
MB95F202KAP@SDIP24 [SA653]  
MB95F202KP@SDIP24 [SA653]  
MB95F203HAP@SDIP24 [SA653]  
MB95F203HP@SDIP24 [SA653]  
MB95F203KAP@SDIP24 [SA653]  
MB95F203KP@SDIP24 [SA653]  
MB95F204HAP@SDIP24 [SA653]  
MB95F204HP@SDIP24 [SA653]  
MB95F204KAP@SDIP24 [SA653]  
MB95F204KP@SDIP24 [SA653]  
MB95F212HPF@SOP8 [SA605B]  
MB95F212KPF@SOP8 [SA605B]  
MB95F213HPF@SOP8 [SA605B]  
MB95F213KPF@SOP8 [SA605B]  
MB95F214HPF@SOP8 [SA605B]  
MB95F214KPF@SOP8 [SA605B]  
MB95F222HPF@SOP16 [SA605B]  
MB95F222KPF@SOP16 [SA605B]  
MB95F223HPF@SOP16 [SA605B]  
MB95F223KPF@SOP16 [SA605B]  
MB95F224HPF@SOP16 [SA605B]  
MB95F224KPF@SOP16 [SA605B]  
MB95F232HP@SDIP24 [SA653]  
MB95F232KP@SDIP24 [SA653]  
MB95F233HP@SDIP24 [SA653]  
MB95F233KP@SDIP24 [SA653]  
MB95F234HP@SDIP24 [SA653]  
MB95F234KP@SDIP24 [SA653]  
MB95F242HP  
MB95F242KP  
MB95F243HP  
MB95F243KP  
MB95F244HP  
MB95F244KP  
MB95F252HP  
MB95F252KP  
MB95F253HP  
MB95F253KP  
MB95F254HP  
MB95F254KP  
MB95F262HP@SDIP24 [SA653]  
MB95F262HPFT [SA643]  
MB95F262HWQN [SA686]  
MB95F262KPF@SOP20 [SA783]  
MB95F262KPS@TSOP20 [SA643]  
MB95F263HP@SDIP24 [SA653]  
MB95F263HPFT [SA643]

MB89F202A@SSOP34 [SA689]  
MB89F202R@SDIP32 [SA653]  
MB89F202RA@QFP32 [SA636]  
MB89F202RA@SSOP34 [SA689]  
MB95F202HAPF@SOP20 [SA783]  
MB95F202HPF@SOP20 [SA783]  
MB95F202KAPF@SOP20 [SA783]  
MB95F202KPF@SOP20 [SA783]  
MB95F203HAPF@SOP20 [SA783]  
MB95F203HPF@SOP20 [SA783]  
MB95F203KAPF@SOP20 [SA783]  
MB95F203KPF@SOP20 [SA783]  
MB95F204HAPF@SOP20 [SA783]  
MB95F204HPF@SOP20 [SA783]  
MB95F204KAPF@SOP20 [SA783]  
MB95F204KPF@SOP20 [SA783]  
MB95F212HPH  
MB95F212KPH  
MB95F213HPH  
MB95F213KPH  
MB95F214HPH  
MB95F214KPH  
MB95F222HPH  
MB95F222KPH  
MB95F223HPH  
MB95F223KPH  
MB95F224HPH  
MB95F224KPH  
MB95F232HPF@SOP20 [SA783]  
MB95F232KPF@SOP20 [SA783]  
MB95F233HPF@SOP20 [SA783]  
MB95F233KPF@SOP20 [SA783]  
MB95F234HPF@SOP20 [SA783]  
MB95F234KPF@SOP20 [SA783]  
MB95F242HPF@SOP8 [SA605B]  
MB95F242KPF@SOP8 [SA605B]  
MB95F243HPF@SOP8 [SA605B]  
MB95F243KPF@SOP8 [SA605B]  
MB95F244HPF@SOP8 [SA605B]  
MB95F244KPF@SOP8 [SA605B]  
MB95F252HPF@SOP16 [SA605B]  
MB95F252KPF@SOP16 [SA605B]  
MB95F253HPF@SOP16 [SA605B]  
MB95F253KPF@SOP16 [SA605B]  
MB95F254HPF@SOP16 [SA605B]  
MB95F254KPF@SOP16 [SA605B]  
MB95F262HPF@SOP20 [SA783]  
MB95F262HPS@TSOP20 [SA643]  
MB95F262KP@SDIP24 [SA653]  
MB95F262KPFT [SA643]  
MB95F262KWQN [SA686]  
MB95F263HPF@SOP20 [SA783]  
MB95F263HPS@TSOP20 [SA643]

MB95F263HWQN [SA686] MB95F263KP@SDIP24 [SA653]  
MB95F263KPF@SOP20 [SA783] MB95F263KPFT [SA643]  
MB95F263KPS@TSOP20 [SA643] MB95F263KWQN [SA686]  
MB95F264HP@SDIP24 [SA653] MB95F264HPF@SOP20 [SA783]  
MB95F264HPFT [SA643] MB95F264HPS@SSOP20 [SA643]  
MB95F264HWQN [SA686] MB95F264KP@SDIP24 [SA653]  
MB95F264KPF@SOP20 [SA783] MB95F264KPFT [SA643]  
MB95F264KPS@SSOP20 [SA643] MB95F264KWQN [SA686]  
MB95F272HP MB95F272HPF@SOP8 [SA605B]  
MB95F272KP MB95F272KPF@SOP8 [SA605B]  
MB95F273HP MB95F273HPF@SOP8 [SA605B]  
MB95F273KP MB95F273KPF@SOP8 [SA605B]  
MB95F274HP MB95F274HPF@SOP8 [SA605B]  
MB95F274KP MB95F274KPF@SOP8 [SA605B]  
MB95F282HP MB95F282HPF@SOP16 [SA605B]  
MB95F282HWQN [SA686] MB95F282KP  
MB95F282KPF@SOP16 [SA605B] MB95F282KWQN [SA686]  
MB95F283HP MB95F283HPF@SOP16 [SA605B]  
MB95F283HWQN [SA686] MB95F283KP  
MB95F283KPF@SOP16 [SA605B] MB95F283KWQN [SA686]  
MB95F284HP MB95F284HPF@SOP16 [SA605B]  
MB95F284HWQN [SA686] MB95F284KP  
MB95F284KPF@SOP16 [SA605B] MB95F284KWQN [SA686]  
MB95F332HP@SDIP32 [SA653]  
MB95F332HP@SDIP32 (Parallel) [SA653]  
MB95F332HPF@LQFP32 [SA636]  
MB95F332HPF@LQFP32 (Parallel) [SA636]  
MB95F332HWQN [SA686]  
MB95F332HWQN@QFN32 (Parallel) [SA686]  
MB95F332KP@SDIP32 [SA653]  
MB95F332KP@SDIP32 (Parallel) [SA653]  
MB95F332KPF@LQFP32 [SA636]  
MB95F332KPF@LQFP32 (Parallel) [SA636]  
MB95F332KWQN [SA686]  
MB95F332KWQN@QFN32 (Parallel) [SA686]  
MB95F333HP@SDIP32 [SA653]  
MB95F333HP@SDIP32 (Parallel) [SA653]  
MB95F333HPF@LQFP32 [SA636]  
MB95F333HPF@LQFP32 (Parallel) [SA636]  
MB95F333HWQN [SA686]  
MB95F333HWQN@QFN32 (Parallel) [SA686]  
MB95F333KP@SDIP32 [SA653]  
MB95F333KP@SDIP32 (Parallel) [SA653]  
MB95F333KPF@LQFP32 [SA636]  
MB95F333KPF@LQFP32 (Parallel) [SA636]  
MB95F333KWQN [SA686]  
MB95F333KWQN@QFN32 (Parallel) [SA686]  
MB95F334HP@SDIP32 [SA653]  
MB95F334HP@SDIP32 (Parallel) [SA653]  
MB95F334HPF@LQFP32 [SA636]  
MB95F334HPF@LQFP32 (Parallel) [SA636]  
MB95F334HWQN [SA686]  
MB95F334HWQN@QFN32 (Parallel) [SA686]

MB95F334KP@SDIP32 [SA653]  
MB95F334KP@SDIP32 (Parallel) [SA653]  
MB95F334KPF@LQFP32 [SA636]  
MB95F334KPF@LQFP32 (Parallel) [SA636]  
MB95F334KWQN [SA686]  
MB95F334KWQN@QFN32 (Parallel) [SA686]  
MB95F352E@QFP32 (Parallel) [SA636]  
MB95F352E@SOIC24 (Parallel) [SA404]  
MB95F352E@SSOP24 (Parallel) [SA643]  
MB95F352L@QFP32 (Parallel) [SA636]  
MB95F352L@SOIC24 (Parallel) [SA404]  
MB95F352L@SSOP24 (Parallel) [SA643]  
MB95F353E@QFP32 (Parallel) [SA636]  
MB95F353E@SOIC24 (Parallel) [SA404]  
MB95F353E@SSOP24 (Parallel) [SA643]  
MB95F353L@QFP32 (Parallel) [SA636]  
MB95F353L@SOIC24 (Parallel) [SA404]  
MB95F353L@SSOP24 (Parallel) [SA643]  
MB95F354E@QFP32 (Parallel) [SA636]  
MB95F354E@SOIC24 (Parallel) [SA404]  
MB95F354E@SSOP24 (Parallel) [SA643]  
MB95F354L@QFP32 (Parallel) [SA636]  
MB95F354L@SOIC24 (Parallel) [SA404]  
MB95F354L@SSOP24 (Parallel) [SA643]  
MB95F562HP [SA653] MB95F562HPF [SA404]  
MB95F562HPFT [SA026] MB95F562HPS [SA026]  
MB95F562HWQN [SA686] MB95F562KP [SA653]  
MB95F562KPF [SA404] MB95F562KPFT [SA026]  
MB95F562KPS [SA026] MB95F562KWQN [SA686]  
MB95F563HP [SA653] MB95F563HPF [SA404]  
MB95F563HPFT [SA026] MB95F563HPS [SA026]  
MB95F563HWQN [SA686] MB95F563KP [SA653]  
MB95F563KPF [SA404] MB95F563KPFT [SA026]  
MB95F563KPS [SA026] MB95F563KWQN [SA686]  
MB95F564HP [SA653] MB95F564HPF [SA404]  
MB95F564HPFT [SA026] MB95F564HPS [SA026]  
MB95F564HWQN [SA686] MB95F564KP [SA653]  
MB95F564KPF [SA404] MB95F564KPFT [SA026]  
MB95F564KPS [SA026] MB95F564KWQN [SA686]  
MB95F572HP MB95F572HPF [SA605B]  
MB95F572KP MB95F572KPF [SA605B]  
MB95F573HP MB95F573HPF [SA605B]  
MB95F573KP MB95F573KPF [SA605B]  
MB95F574HP MB95F574HPF [SA605B]  
MB95F574KP MB95F574KPF [SA605B]  
MB95F582HP MB95F582HPF [SA605B]  
MB95F582KP MB95F582KP [SA605B]  
MB95F582KWQN [SA686]  
MB95F583HP MB95F583HPF [SA605B]  
MB95F583KP MB95F583KP [SA605B]  
MB95F583KWQN [SA686]  
MB95F584HP MB95F584HPF [SA605B]  
MB95F584KP MB95F584KP [SA686]

MB95F584KPF [SA605B]	MB95F584KWQN [SA686]
MB95F632HP [SA653]	MB95F632HPF [SA636]
MB95F632HWQN [SA686]	MB95F632KP [SA653]
MB95F632KPF [SA636]	MB95F632KWQN [SA686]
MB95F633HP [SA653]	MB95F633HPF [SA636]
MB95F633HWQN [SA686]	MB95F633KP [SA653]
MB95F633KPF [SA636]	MB95F633KWQN [SA686]
MB95F634HP [SA653]	MB95F634HPF [SA636]
MB95F634HWQN [SA686]	MB95F634KP [SA653]
MB95F634KPF [SA636]	MB95F634KWQN [SA686]
MB95F636HP [SA653]	MB95F636HPF [SA636]
MB95F636HWQN [SA686]	MB95F636KP [SA653]
MB95F636KPF [SA636]	MB95F636KWQN [SA686]
MB95R202HAP@SDIP24 [SA653]	MB95R202HAPF@SOP20 [SA404]
MB95R202HP@SDIP24 [SA653]	MB95R202HPF@SOP20 [SA404]
MB95R202KAP@SDIP24 [SA653]	MB95R202KAPF@SOP20 [SA404]
MB95R202KP@SDIP24 [SA653]	MB95R202KPF@SOP20 [SA404]
MB95R203HAP@SDIP24 [SA653]	MB95R203HAPF@SOP20 [SA404]
MB95R203HP@SDIP24 [SA653]	MB95R203HPF@SOP20 [SA404]
MB95R203KAP@SDIP24 [SA653]	MB95R203KAPF@SOP20 [SA404]
MB95R203KP@SDIP24 [SA653]	MB95R203KPF@SOP20 [SA404]
MB95R204HAP@SDIP24 [SA653]	MB95R204HAPF@SOP20 [SA404]
MB95R204HP@SDIP24 [SA653]	MB95R204HPF@SOP20 [SA404]
MB95R204KAP@SDIP24 [SA653]	MB95R204KAPF@SOP20 [SA404]
MB95R204KP@SDIP24 [SA653]	MB95R204KPF@SOP20 [SA404]
MB95R212HPF@SOP8 [SA605B]	MB95R212HPH
MB95R212KPF@SOP8 [SA605B]	MB95R212KPH
MB95R213HPF@SOP8 [SA605B]	MB95R213HPH
MB95R213KPF@SOP8 [SA605B]	MB95R213KPH
MB95R214HPF@SOP8 [SA605B]	MB95R214HPH
MB95R214KPF@SOP8 [SA605B]	MB95R214KPH
MB95R222HPF@SOP16 [SA605B]	MB95R222HPH
MB95R222KPF@SOP16 [SA605B]	MB95R222KPH
MB95R223HPF@SOP16 [SA605B]	MB95R223HPH
MB95R223KPF@SOP16 [SA605B]	MB95R223KPH
MB95R224HPF@SOP16 [SA605B]	MB95R224HPH
MB95R224KPF@SOP16 [SA605B]	MB95R224KPH

## GAMMA

### E (E) PROM/FRAM/NVRAM

GAMNXX001JF9TC@TSOP48 [SB247-B4806]

## GATELEVEL

### E (E) PROM/FRAM/NVRAM

GM24LC02B	GM24LC02B@SOIC8 [SA602A]
GM24LC02B@TSSOP8 [SA643]	GM24LC04B
GM24LC04B@SOIC8 [SA602A]	GM24LC04B@TSSOP8 [SA643]
GM24LC08B	GM24LC08B@SOIC8 [SA602A]

GM24LC08B@TSSOP8 [SA643]  
GM24LC16B@SOIC8 [SA602A]

GM24LC16B  
GM24LC16B@TSSOP8 [SA643]

## GENCORE

### MICROCONTROLLER

GC87C520A0  
GC87C520A0@TQFP44 [SA245A-B4805]  
GC87C520G0@PLCC44 [SA244]  
GC89L541A0@LQFP44 [SA675-B4805]  
GC89L541A0@MQFP44 [SA782]  
GC89L541A0@QFN32 [SA686]  
GC89L581A0@MLF32 [SA686]  
GC89L581A0@PQFP44 [SA782]  
GC89L591A0@LQFP44 [SA675-B4805]  
GC89L591A0@MQFP44 [SA782]  
GC89L591A0@QFN32 [SA686]

GC87C520A0@PLCC44 [SA244]  
GC87C520G0  
GC87C520G0@TQFP44 [SA245A-B4805]  
GC89L541A0@MLF32 [SA686]  
GC89L541A0@PQFP44 [SA782]  
GC89L581A0@LQFP44 [SA675-B4805]  
GC89L581A0@MQFP44 [SA782]  
GC89L581A0@QFN32 [SA686]  
GC89L591A0@MLF32 [SA686]  
GC89L591A0@PQFP44 [SA782]

## GENERAL (GI)

### E (E) PROM/FRAM/NVRAM

27256  
27C128@PLCC32 [SA015A1T]  
27C256@PLCC32 [SA015A1T]  
27C513  
27C64@PLCC32 [SA015A1T]  
27HC291  
27HC641  
27HC64L  
28C04A  
28C16  
28C16F  
28C17F  
ER5911@SOIC8 [SA602A]  
GI5911@SOIC8 [SA602A]  
GI59C11@SOIC8 [SA602A]  
GI59C12@SOIC8 [SA602A]

27C128  
27C256  
27C512  
27C64  
27HC191  
27HC64  
27HC641L  
28C04  
28C04F  
28C16A  
28C17  
ER5911  
GI5911  
GI59C11  
GI59C12  
GR27C513

## GENERALPLUS

### E (E) PROM/FRAM/NVRAM

GPR25L005E@SOP8 [SA602A]  
GPR25L021B@SOP8 [SA602A]  
GPR25L081B@SOP8 [SA602A]  
GPR25L162B  
GPR25L6404E@SOP16 [SA404]  
GPR25L6404E@SOP8 [SA605B]

GPR25L011E@SOP8 [SA602A]  
GPR25L041B@SOP8 [SA602A]  
GPR25L1284E@SOP16 [SA404]  
GPR25L322B@SOP8 [SA602A]  
GPR25L6404E@SOP16 (OTP) [SA404]  
GPR25L6404E@SOP8 (OTP) [SA605B]



GT25C01@SOP8 [SA602A]  
GT25C02  
GT25C02@TSSOP8 [SA643]  
GT25C04@SOP8 [SA602A]  
GT25C08  
GT25C08@TSSOP8 [SA643]  
GT25C128@TSSOP8 [SA643]  
GT25C16@SOIC8 [SA602A]  
GT25C256@SOIC8 [SA602A]  
GT25C32  
GT25C32@TSSOP8 [SA643]  
GT25C64@SOIC8 [SA602A]  
GT34C02  
GT34C02@SOP8 [SA602A]  
GT93C46 (08bit)  
GT93C46 (08bit)@TSSOP8 [SA643]  
GT93C46 (16bit)@SOIC8 [SA602A]  
GT93C56 (08bit)  
GT93C56 (08bit)@TSSOP8 [SA643]  
GT93C56 (16bit)@SOIC8 [SA602A]  
GT93C66 (08bit)  
GT93C66 (08bit)@TSSOP8 [SA643]  
GT93C66 (16bit)@SOIC8 [SA602A]  
GT93C76 (08bit)  
GT93C76 (08bit)@TSSOP8 [SA643]  
GT93C76 (16bit)@SOIC8 [SA602A]  
GT93C86 (08bit)  
GT93C86 (08bit)@TSSOP8 [SA643]  
GT93C86 (16bit)@SOIC8 [SA602A]

GT25C01@TSSOP8 [SA643]  
GT25C02@SOP8 [SA602A]  
GT25C04  
GT25C04@TSSOP8  
GT25C08@SOIC8 [SA602A]  
GT25C128@SOIC8 [SA602A]  
GT25C16  
GT25C16@TSSOP8 [SA643]  
GT25C256@TSSOP8 [SA643]  
GT25C32@SOIC8 [SA602A]  
GT25C64  
GT25C64@TSSOP8 [SA643]  
GT34C02@MSOP8 [SA666]  
GT34C02@TSSOP8 [SA643]  
GT93C46 (08bit)@SOIC8 [SA602A]  
GT93C46 (16bit)  
GT93C46 (16bit)@TSSOP8 [SA643]  
GT93C56 (08bit)@SOIC8 [SA602A]  
GT93C56 (16bit)  
GT93C56 (16bit)@TSSOP8 [SA643]  
GT93C66 (08bit)@SOIC8 [SA602A]  
GT93C66 (16bit)  
GT93C66 (16bit)@TSSOP8 [SA643]  
GT93C76 (08bit)@SOIC8 [SA602A]  
GT93C76 (16bit)  
GT93C76 (16bit)@TSSOP8 [SA643]  
GT93C86 (08bit)@SOIC8 [SA602A]  
GT93C86 (16bit)  
GT93C86 (16bit)@TSSOP8 [SA643]

## GIGADEVICE

### E (E) PROM/FRAM/NVRAM

GD25B64B  
GD25B64B@SOP8 [SA605B]  
GD25B64B@WSON8 [SA683]  
GD25D05B@TSSOP8 [SA643]  
GD25D10B@SOP8 [SA602A]  
GD25D10B@USON8 [\$\$\$\$\$]  
GD25D40@SOP8 [SA605B]  
GD25D80@SOP8 [SA605B]  
GD25E16@SOP8 [SA605B]  
GD25E40@SOP8 [SA605B]  
GD25E64B@SOP8 [SA605B]  
GD25E80B@SOP8 [SA605B]  
GD25F40  
GD25F80  
GD25LQ128@SOP16 [SA783]  
GD25LQ128@WSON8 [SA684]  
GD25LQ16@TSOP8 [SA605B]  
GD25LQ16@WSON8 [SA683]

GD25B64B@SOP16 [SA783]  
GD25B64B@TFBGA24 [TA088]  
GD25D05B@SOP8 [SA602A]  
GD25D05B@USON8 [\$\$\$\$\$]  
GD25D10B@TSSOP8 [SA643]  
GD25D40  
GD25D80  
GD25E16  
GD25E40  
GD25E40@TSSOP8 [SA602A]  
GD25E80B  
GD25E80B@TSSOP8 [SA602A]  
GD25F40@SOP8 [SA605B]  
GD25F80@SOP8 [SA605B]  
GD25LQ128@SOP8 [SA605B]  
GD25LQ16@SOP8 [SA605B]  
GD25LQ16@USON8 [\$\$\$\$\$]  
GD25LQ20B@SOP8 [SA602A]

GD25LQ20B@TSOP8 [SA643]                   GD25LQ20B@USON8 [SA683]  
GD25LQ20B@WSON8 [SA683]                   GD25LQ32@SOP8 [SA605B]  
GD25LQ32@WSON8 [SA683]                   GD25LQ40@SOP8 [SA602A]  
GD25LQ40@TSOP8 [SA643]                   GD25LQ40@USON8 [SA683]  
GD25LQ40@WSON8 [SA683]                   GD25LQ40B@SOP8 [SA602A]  
GD25LQ40B@TSOP8 [SA643]                   GD25LQ40B@USON8 [SA683]  
GD25LQ40B@WSON8 [SA683]                   GD25LQ512C@WSON8 [SA684]  
GD25LQ64@TSOP8 [SA605B]                   GD25LQ64@WSON8 [SA683]  
GD25LQ64B@SOP16 [SA783]                   GD25LQ64B@SOP8 [SA605B]  
GD25LQ64B@WSON8 [SA683]                   GD25LQ80@SOP8 [SA602A]  
GD25LQ80@USON8 [\$\$\$\$\$]                   GD25LQ80@WSON8 [SA683]  
GD25LQ80B@SOP8 [SA602A]                   GD25LQ80B@USON8 [\$\$\$\$\$]  
GD25LQ80B@WSON8 [SA683]                   GD25M21B@SOIC8 [SA602A]  
GD25M21B@TSSOP8 [SA643]                   GD25M21B@USON8 [SA724]  
GD25M41B@SOIC8 [SA602A]                   GD25M41B@TSSOP8 [SA643]  
GD25M41B@USON8 [SA724]                   GD25Q10  
GD25Q10@SOP8(150 mil) [SA602A]           GD25Q10@SOP8(200 mil) [SA605B]  
GD25Q10@USON8 [SA724]                   GD25Q128B@SOP16 [SA783]  
GD25Q128B@WSON8 [SA684]                   GD25Q16  
GD25Q16@SOP8 [SA605B]                   GD25Q16B  
GD25Q16B@SOP8 [SA605B]                   GD25Q16C  
GD25Q16C@SOP8 [SA605B]                   GD25Q20  
GD25Q20@SOP8(150 mil) [SA602A]           GD25Q20@SOP8(200 mil) [SA605B]  
GD25Q20@USON8 [SA724]                   GD25Q20B@SOIC8 [SA602A]  
GD25Q20B@TSSOP8 [SA643]                   GD25Q20B@USON8 [SA724]  
GD25Q21B@SOIC8 [SA602A]                   GD25Q21B@TSSOP8 [SA643]  
GD25Q21B@USON8 [SA724]                   GD25Q32  
GD25Q32(4\*256 Security) [SA605B]           GD25Q32@SOP8 [SA605B]  
GD25Q32@SOP8(4\*256 Security) [SA605B]   GD25Q32B@SOP8 [SA605B]  
GD25Q32B                                   GD25Q32C@SOP8 [SA605B]  
GD25Q32C                                   GD25Q40  
GD25Q32C@TFBGA24 [TA088]                   GD25Q40@SOP8(200 mil) [SA605B]  
GD25Q40@SOP8(150 mil) [SA602A]           GD25Q40B@SOIC8 [SA602A]  
GD25Q40@USON8 [SA724]                   GD25Q40B@USON8 [SA724]  
GD25Q40B@TSSOP8 [SA643]                   GD25Q41B@TSSOP8 [SA643]  
GD25Q41B@SOIC8 [SA602A]                   GD25Q512  
GD25Q41B@USON8 [SA724]                   GD25Q512@TSSOP8 [SA643]  
GD25Q512@SOP8 [SA602A]                   GD25Q64B  
GD25Q512@USON8 [SA724]                   GD25Q64B@SOP8 [SA605B]  
GD25Q64B@SOP16 [SA783]                   GD25Q64B@WSON8[6\*5] [SA683]  
GD25Q64B@TSOP8 [SA605B]                   GD25Q64C@SOP16 [SA783]  
GD25Q64B@WSON8[6\*8] [SA684]               GD25Q64C@TSOP8 [SA605B]  
GD25Q64C@SOP8 [SA605B]                   GD25Q80  
GD25Q64C@WSON8 [SA683]                   GD25Q80@SOP8(200 mil) [SA605B]  
GD25Q80@SOP8(150 mil) [SA602A]           GD25Q80B@SOP8(150 mil) [SA602A]  
GD25Q80B                                   GD25Q80B@USON8 [SA724]  
GD25Q80B@SOP8(200 mil) [SA605B]           GD25Q80C@SOP8(150 mil) [SA602A]  
GD25Q80C                                   GD25Q80C@USON8 [SA724]  
GD25Q80C@SOP8(200 mil) [SA605B]           GD25T80@SOP8 [SA605B]  
GD25T80                                   GD25VQ21B@TSSOP8 [SA643]  
GD25VQ21B@SOIC8 [SA602A]                   GD25VQ41B@SOIC8 [SA602A]  
GD25VQ21B@USON8 [SA724]                   GD25VQ41B@USON8 [SA724]  
GD25VQ41B@TSSOP8 [SA643]

MD25D16  
MD25D16@SOP8 (200 mil) [SA602A]  
MD25D20@SOP8 (150 mil) [SA602A]  
MD25D20@USON8 [SA724]  
MD25D40@SOP8 (150 mil) [SA602A]  
MD25D40@USON8 [SA724]  
MD25D80@SOP8 (150 mil) [SA602A]  
S64M80GX  
S64M80GX@SOP8 [SA605B]  
S64M80GX@WSON8 [SA684]

MD25D16@SOP8 (150 mil) [SA605B]  
MD25D20  
MD25D20@SOP8 (200 mil) [SA605B]  
MD25D40  
MD25D40@SOP8 (200 mil) [SA605B]  
MD25D80  
MD25D80@SOP8 (200 mil) [SA605B]  
S64M80GX@SOP16 [SA404]  
S64M80GX@TFBGA24 [TA088]

## GOAL

### MICROCONTROLLER

VRS1000  
VRS1000@TQFP44 [SA245A-B4805]  
VRS1050@PLCC44 [SA244]  
VRS1100  
VRS1100@TQFP44 [SA245A-B4805]  
VRS540@PLCC44 [SA244]  
VRS550  
VRS550@TQFP44 [SA245A-B4805]  
VRS560@PLCC44 [SA244]  
VRS570  
VRS570@TQFP44 [SA245A-B4805]  
VRS580@PLCC44 [SA244]  
VRS700  
VRS700@TQFP44 [SA245A-B4805]  
VRS900@PLCC44 [SA244]

VRS1000@PLCC44 [SA244]  
VRS1050  
VRS1050@TQFP44 [SA245A-B4805]  
VRS1100@PLCC44 [SA244]  
VRS540  
VRS540@TQFP44 [SA245A-B4805]  
VRS550@PLCC44 [SA244]  
VRS560  
VRS560@TQFP44 [SA245A-B4805]  
VRS570@PLCC44 [SA244]  
VRS580  
VRS580@TQFP44 [SA245A-B4805]  
VRS700@PLCC44 [SA244]  
VRS900  
VRS900@TQFP44 [SA245A-B4805]

## GREEN-ENGINE

### E (E) PROM/FRAM/NVRAM

GE24C01  
GE24C01@TSSOP8 [SA643]  
GE24C02@SOP8 [SA602A]  
GE24C04  
GE24C04@TSSOP8 [SA643]

GE24C01@SOP8 [SA602A]  
GE24C02  
GE24C02@TSSOP8 [SA643]  
GE24C04@SOP8 [SA602A]

## GREENLIANT

### E (E) PROM/FRAM/NVRAM

GLS29EE512  
GLS29EE512@TSOP32 [SA410T-B4001]  
GLS29SF020@PLCC32 [SA015A1T]  
GLS29SF040@PLCC32 [SA015A1T]  
GLS29VF020@PLCC32 [SA015A1T]  
GLS29VF040@PLCC32 [SA015A1T]

GLS29EE512@PLCC32 [SA015A1T]  
GLS29EE512@VSOP32 [SA620-B4807]  
GLS29SF020@VSOP32 [SA620-B4807]  
GLS29SF040@VSOP32 [SA620-B4807]  
GLS29VF020@VSOP32 [SA620-B4807]  
GLS29VF040@VSOP32 [SA620-B4807]

GLS37VF010	GLS37VF010@PLCC32 [SA015A1T]
GLS37VF010@VSOP32 [SA620-B4807]	GLS37VF020
GLS37VF020@PLCC32 [SA015A1T]	GLS37VF020@VSOP32 [SA620-B4807]
GLS37VF040	GLS37VF040@PLCC32 [SA015A1T]
GLS37VF040@VSOP32 [SA620-B4807]	GLS37VF512
GLS37VF512@PLCC32 [SA015A1T]	GLS37VF512@VSOP32 [SA620-B4807]
SST36VF1601G@TSOP48 [SB247-B4806]	
SST36VF1602G@TSOP48 [SB247-B4806]	
SST36VF3203@TSOP48 [SB247-B4806]	SST36VF3204@TSOP48 [SB247-B4806]

## GREENWICH

### E (E) PROM/FRAM/NVRAM

GR27128	GR27256
GR27512	GR2764

## GTM

### E (E) PROM/FRAM/NVRAM

GP24BC01	GP24BC01@SOP8 [SA602A]
GP24BC01@TSSOP8 [SA643]	GP24BC02
GP24BC02@SOP8 [SA602A]	GP24BC02@TSSOP8 [SA643]
GP24BC04	GP24BC04@SOP8 [SA602A]
GP24BC04@TSSOP8 [SA643]	GP24BC08
GP24BC08@SOP8 [SA602A]	GP24BC08@TSSOP8 [SA643]
GP24BC16	GP24BC16@SOP8 [SA602A]
GP24BC16@TSSOP8 [SA643]	

## HAIER

### MICROCONTROLLER

HR6P58P1D1L	HR6P58P1D2L
HR6P58P1RL@SSOP10 [SA626A]	HR6P58P1S2L [SA602A]
HR6P58P1YL@SOP14 [SA404]	HR6P59P2D2HL
HR6P59P2DHL	HR6P59P2DL
HR6P59P2RHL@SSOP10 [SA626A]	HR6P59P2S2HL [SA605B]
HR6P59P2SHL@SOP14 [SA404]	HR6P59P2SL@SOP14 [SA602]
HR6P59P2YHL [SA602A]	HR6P60P2D2HL
HR6P60P2DL	HR6P60P2DLA
HR6P60P2EL	HR6P60P2ELA
HR6P60P2RHL@SSOP20 [SA026]	HR6P60P2RL@SSOP20 [SA626A]
HR6P60P2RLA@SSOP20 [SA626A]	HR6P60P2S1HL@SOP20 [SA404]
HR6P60P2S2HL@SOP18 [SA404]	HR6P60P2SL@SOP20 [SA404]
HR6P60P2SLA@SOP20 [SA404]	HR6P60P2XL@SOP18 [SA404]
HR6P60P2XLA@SOP18 [SA404]	HR6P60P2YL@SOP14 [SA404]
HR6P60P2YLA@SOP14 [SA404]	HR6P61P2D1L
HR6P61P2D2L	HR6P61P2D3L
HR6P61P2D4L	HR6P61P2S1L@SOP20 [SA404]

HR6P61P2S2L@SOP18 [SA404] HR6P61P2S3L@SOP16 [SA404]  
HR6P61P2S4L@SOP14 [SA404] HR6P62P4D  
HR6P62P4DH HR6P62P4DHL  
HR6P62P4DHL (INTOSC) HR6P62P4DHL-D  
HR6P62P4DHL-D (INTOSC)  
HR6P62P4NHL (INTOSC)@SOP20 [SA626A]  
HR6P62P4NHL@SSOP20 [SA626A]  
HR6P62P4NHLD (INTOSC)@SSOP20 [SA626A]  
HR6P62P4NHLD@SSOP20 [SA626A]  
HR6P62P4RHL (INTOSC)@SOP20 [SA626A]  
HR6P62P4RHL@SSOP20 [SA626A]  
HR6P62P4RHL-D (INTOSC)@SSOP20 [SA626A]  
HR6P62P4RHL-D@SSOP20 [SA626A] HR6P62P4SH@SOP20 [SA404]  
HR6P62P4SHL (INTOSC)@SOP20 [SA404]  
HR6P62P4SHL@SOP20 [SA404]  
HR6P62P4SHLD (INTOSC)@SOP20 [SA404]  
HR6P62P4SHLD@SOP20 [SA404]  
HR6P62P4XHL (INTOSC)@SOP18 [SA404]  
HR6P62P4XHL@SOP18 [SA404]  
HR6P62P4XHL-D (INTOSC)@SOP18 [SA404]  
HR6P62P4XHL-D@SOP18 [SA404] HR6P62P4YHL@SOP14 [SA026]  
HR6P62P4YHLD@SOP14 [SA026] HR6P67P4D  
HR6P67P4DL HR6P67P4DL-B  
HR6P67P4DLR HR6P67P4DLRB  
HR6P67P4SL@SOP14 [SA602] HR6P67P4SL-B@SOP14 [SA404]  
HR6P67P4SLR@SOP14 [SA602] HR6P67P4SLRB@SOP14 [SA404]  
HR6P71F8D HR6P71F8D (BOREN)  
HR6P71F8D (BOREN) (ISP) HR6P71F8D (ISP)  
HR6P71F8D (REVERSE) HR6P71F8S (BOREN)@SOP20 [SA404]  
HR6P71F8S (BOREN)@SOP20 (ISP) HR6P71F8S (REVERSE)@SOP20 [SA404]  
HR6P71F8S@SOP20 [SA404] HR6P71F8S@SOP20 (ISP)  
HR6P72P4D HR6P72P4DL  
HR6P72P4S@SOP28 HR6P72P4SL@SOP28 [SA404]  
HR6P73P8DB HR6P73P8DBL  
HR6P73P8SB@SOP28 [SA404] HR6P73P8SBL@SOP28 [SA404]  
HR6P73PGD HR6P73PGDH  
HR6P73PGDHL HR6P73PGS@SOP28 [SA404]  
HR6P73PGSH@SOP28 [SA404] HR6P73PGSHL@SOP28 [SA404]  
HR6P76PGD HR6P76PGDL  
HR6P76PGS@SOP28 HR6P76PGSL@SOP28 [SA404]  
HR6P77PGD HR6P77PGDL  
HR6P77PGL@LQFP44 [SA245A-B4805] HR6P77PGL@LQFP44 [SA245A-B4805]  
HR6P90FGD HR6P90FGD (ISP)  
HR6P90FGS@SOP28 [SA404] HR6P90FGS@SOP28 (ISP)  
HR6P90FHD HR6P90FHD (ISP)  
HR6P90FHS@SOP28 [SA404] HR6P90FHS@SOP28 (ISP)  
HR6P91FGS@SOP32 [SA715] HR6P91FGS@SOP32 (ISP)  
HR6P91FHS@SOP32 [SA715] HR6P91FHS@SOP32 (ISP)  
HR6P92FGD HR6P92FGD (ISP)  
HR6P92FGL@LQFP44 [SA245A-B4805] HR6P92FGL@LQFP44 (ISP)  
HR6P92FHD HR6P92FHD (ISP)  
HR6P92FHL@LQFP44 [SA245A-B4805] HR6P92FHL@LQFP44 (ISP)  
HR6P95F8D HR6P95F8D (ISP)

HR6P95F8S@SOP28  
HR6P97FGD (ISP)  
HR6P97FGS@SOP28 (ISP)  
HR6P98FGD (ISP)  
HR6P98FGL@LQFP44 (ISP)  
HR7P171F8D1  
HR7P171F8D3  
HR7P171F8S1@SOP20 [SA404]  
HR7P171F8S3@SOP16 [SA404]  
HR7P187F4D1  
HR7P187F4S1@SOP14 [SA602]

HR6P95F8S@SOP28 (ISP)  
HR6P97FGD-E (ISP)  
HR6P97FGS-E@SOP28 (ISP)  
HR6P98FGD-E (ISP)  
HR6P98FGL-E@LQFP44 (ISP)  
HR7P171F8D2  
HR7P171F8D4  
HR7P171F8S2@SOP18 [SA404]  
HR7P171F8S4@SOP14 [SA602]  
HR7P187F4D2  
HR7P187F4S2@SOP8 [SA602]

## HARRIS

### E (E) PROM/FRAM/NVRAM

HM-6616

M1-6617/883

### DRAM & SRAM

HM65642

HM65642@TSOP28 [SA643]

## HITACHI

### E (E) PROM/FRAM/NVRAM

HN27128AG	HN27128AP
HN27256G	HN27256P
HN27512G	HN27512P
HN27C101AG	HN27C101AP
HN27C101G	HN27C101P
HN27C1024HG	HN27C1024HG@PLCC44 [SA244]
HN27C256AG	HN27C256FP
HN27C256G	HN27C256HG
HN27C301AG	HN27C301AP
HN27C301G	HN27C301P
HN27C4000FP	HN27C4000G
HN27C4001	HN27C4001@TSOP32 [SA410T-B4001]
HN27C4001G	HN27C4096A
HN27C4096A@PLCC44 [SA244]	HN27C4096FP
HN27C4096FP@PLCC44 [SA244]	HN27C4096G
HN27C4096G@PLCC44 [SA244]	HN27C512G
HN27C512G@PLCC32 [SA015A1T]	HN27C64G
HN28F101	
HN28F101 (REVERSE)@TSOP32 [SA410T-B4001]	
HN28F101@PLCC32 [SA015A1T]	HN28F101@SOP32 [SA438T]
HN28F101@TSOP32 [SA410T-B4001]	HN462716G
HN462732G	HN48016
HN48016P	HN4827128G
HN4827128P	HN482732AG
HN482764G	HN482764P

HN58064 (FP)@SOIC28 [SA404]	HN58064 (P)
HN58C1001 (FP)@SSOP32 [SA687]	HN58C1001 (P)
HN58C1001 (T)@VSOP32 [SA620-B4807]	
HN58C256	HN58C256A (FP)@SOP28 [SA404]
HN58C256A (P)	
HN58C256A (T)@TSOP28 [SA430T-B4003]	
HN58C256FP@SOIC28 [SA723]	
HN58C257A (T)@TSOP32 [SA620-B4807]	
HN58C65 (FP)@SOIC28 [SA404]	HN58C65 (P)
HN58V24256	HN58V24256@SOIC8 [SA602A]
HN58V24256@TSSOP14 [SA026]	HN58V24512
HN58V24512@SOIC8 [SA602A]	HN58V256A
HN58V256A@TSOP28 [SA430T-B4003]	HN58V65A
HN58V65A@SOIC28 [\$\$\$\$\$]	HN58V65A@TSOP28 [SA430T-B4003]
HN58V66A	HN58V66A@SOIC28 [SA404]
HN58V66A@TSOP28 [SA430T-B4003]	HN58W241000
HN58W241000@SOIC8[150mil] [SA602A]	
HN58W241000@SOIC8[200mil] [SA605B]	
HN58X2402	HN58X2402@SOIC8 [SA602A]
HN58X2402@TSSOP8 [SA643]	HN58X2404
HN58X2404@SOIC8 [SA602A]	HN58X2404@TSSOP8 [SA643]
HN58X2408	HN58X2408@SOIC8 [SA602A]
HN58X2408@TSSOP8 [SA643]	HN58X24128
HN58X24128@SOIC8 [SA602A]	HN58X2416
HN58X2416@SOIC8 [SA602A]	HN58X2416@TSSOP8 [SA643]
HN58X24256	HN58X24256@SOIC8 [SA602A]
HN58X2432	HN58X2432@SOIC8 [SA602A]
HN58X2432@TSSOP8 [SA643]	HN58X24512
HN58X24512@SOIC8 [SA602A]	HN58X2464
HN58X2464@SOIC8 [SA602A]	HN58X2464@TSSOP8 [SA643]
HN58X2502@SOIC8 [SA602A]	HN58X2502@TSSOP8 [SA643]
HN58X2504@SOIC8 [SA602A]	HN58X2504@TSSOP8 [SA643]
HN58X25128@SOIC8 [SA602A]	HN58X25128@TSSOP14 [SA026]
HN58X25256@SOIC8 [SA602A]	HN58X25256@TSSOP14 [SA026]
HN58X2532@SOIC8 [SA602A]	HN58X2532@TSSOP8 [SA643]
HN58X2564@SOIC8 [SA602A]	HN58X2564@TSSOP8 [SA643]
HT29VB800@TSOP48 [SA247-B4806]	HT29VT800@TSOP48 [SA247-B4806]
HT29WB800@TSOP48 [SA247-B4806]	HT29WT800@TSOP48 [SA247-B4806]

## DRAM & SRAM

HM62256	HM62256@TSOP28 [SA643]
HM62256B	HM62256B@TSOP28 [SA643]
HM6264A	HM6264A@TSOP28 [SA643]
HM628128	HM628128@TSOP32 [SA410T-B4001]
HM628128A	HM628128A@TSOP32 [SA410T-B4001]
HM62832	HM62832@TSOP28 [SA643]
HM62832H	HM62832H@TSOP28 [SA643]
HM628512	HM628512@TSOP32 [SA410T-B4001]
HM65256B	HM65256B@TSOP28 [SA643]
HM658128	HM658128@TSOP32 [SA410T-B4001]
HM66204	HM66204@TSOP32 [SA410T-B4001]

# HOLTEK

## E (E) PROM/FRAM/NVRAM

HT24C01	HT24C01@SOIC8 [SA602A]
HT24C02	HT24C02@SOIC8 [SA602A]
HT24C04	HT24C04@SOIC8 [SA602A]
HT24C08	HT24C16
HT24LC01	HT24LC01@SOIC8 [SA602A]
HT24LC01@TSSOP8 [SA643]	HT24LC02
HT24LC02@SOIC8 [SA602A]	HT24LC02@TSSOP8 [SA643]
HT24LC04	HT24LC04@SOIC8 [SA602A]
HT24LC08	HT24LC08@SOIC8 [SA602A]
HT24LC16	HT24LC16@SOIC8 [SA602A]
HT24LC32	HT24LC32@SOIC8 [SA602A]
HT24LC64	HT24LC64@SOIC8 [SA602A]
HT25LC512@SOIC8 [SA602A]	HT27C010
HT27C010@PLCC32 [SA015A1T]	HT27C010@SOP32 [SA603]
HT27C020	HT27C020@PLCC32 [SA015A1T]
HT27C020@SOP32 [SA603]	HT27C040
HT27C040@PLCC32 [SA015A1T]	HT27C040@SOP32 [SA603]
HT27C4096	HT27C4096@PLCC44 [SA244]
HT27C512	HT27C512@SOP28 [SA404]
HT27C512-A@PLCC32 [SA015A1T]	HT27C512-B@PLCC32 [SA015A1T]
HT27LC010	HT27LC010@PLCC32 [SA015A1T]
HT27LC010@SOP32 [SA603]	HT27LC010@TSOP32 [SA410T-B4001]
HT27LC020	HT27LC020@PLCC32 [SA015A1T]
HT27LC020@SOP32 [SA603]	HT27LC020@TSOP32 [SA410T-B4001]
HT27LC040	HT27LC040@PLCC32 [SA015A1T]
HT27LC040@SOP32 [SA603]	HT27LC040@TSOP32 [SA410T-B4001]
HT27LC4096	HT27LC4096@PLCC44 [SA244]
HT27LC512	HT27LC512@SOP28 [SA404]
HT27LC512@TSOP28 [SA430T-B4003]	HT27LC512-A@PLCC32 [SA015A1T]
HT27LC512-B@PLCC32 [SA015A1T]	HT93C46 (16bit)
HT93C46 (16bit)@SOP8-A [SA602A]	HT93C46 (16bit)@SOP8-B [SA602A]
HT93C46 (16bit)@TSSOP8 [SA643]	HT93C56 (16bit)
HT93C56 (16bit)@SOP8-A [SA602A]	HT93C56 (16bit)@SOP8-B [SA602A]
HT93C56 (16bit)@TSSOP8 [SA643]	HT93C66 (16bit)
HT93C66 (16bit)@SOP8-A [SA602A]	HT93C66 (16bit)@SOP8-B [SA602A]
HT93C66 (16bit)@TSSOP8 [SA643]	HT93LC46A (08bit)
HT93LC46A (08bit)@SOP8-A [SA602A]	HT93LC46A (08bit)@SOP8-B [SA602A]
HT93LC46A (08bit)@TSSOP8 [SA643]	HT93LC46A (16bit)
HT93LC46A (16bit)@SOP8-A [SA602A]	HT93LC46A (16bit)@SOP8-B [SA602A]
HT93LC46A (16bit)@TSSOP8 [SA643]	HT93LC46B (08bit)
HT93LC46B (08bit)@SOP8-A [SA602A]	HT93LC46B (08bit)@SOP8-B [SA602A]
HT93LC46B (08bit)@TSSOP8 [SA643]	HT93LC46B (16bit)
HT93LC46B (16bit)@SOP8-A [SA602A]	HT93LC46B (16bit)@SOP8-B [SA602A]
HT93LC46B (16bit)@TSSOP8 [SA643]	HT93LC56A (08bit)
HT93LC56A (08bit)@SOP8-A [SA602A]	HT93LC56A (08bit)@SOP8-B [SA602A]
HT93LC56A (08bit)@TSSOP8 [SA643]	HT93LC56A (16bit)
HT93LC56A (16bit)@SOP8-A [SA602A]	HT93LC56A (16bit)@SOP8-B [SA602A]

HT93LC56A (16bit)@TSSOP8 [SA643]	HT93LC56B (08bit)
HT93LC56B (08bit)@SOP8-A [SA602A]	HT93LC56B (08bit)@SOP8-B [SA602A]
HT93LC56B (08bit)@TSSOP8 [SA643]	HT93LC56B (16bit)
HT93LC56B (16bit)@SOP8-A [SA602A]	HT93LC56B (16bit)@SOP8-B [SA602A]
HT93LC56B (16bit)@TSSOP8 [SA643]	HT93LC66A (08bit)
HT93LC66A (08bit)@SOP8-A [SA602A]	HT93LC66A (08bit)@SOP8-B [SA602A]
HT93LC66A (08bit)@TSSOP8 [SA643]	HT93LC66A (16bit)
HT93LC66A (16bit)@SOP8-A [SA602A]	HT93LC66A (16bit)@SOP8-B [SA602A]
HT93LC66A (16bit)@TSSOP8 [SA643]	HT93LC66B (08bit)
HT93LC66B (08bit)@SOP8-A [SA602A]	HT93LC66B (08bit)@SOP8-B [SA602A]
HT93LC66B (08bit)@TSSOP8 [SA643]	HT93LC66B (16bit)
HT93LC66B (16bit)@SOP8-A [SA602A]	HT93LC66B (16bit)@SOP8-B [SA602A]
HT93LC66B (16bit)@TSSOP8 [SA643]	HT93LC76 (08bit)
HT93LC76 (08bit)@SOP8-A [SA602A]	HT93LC76 (08bit)@SOP8-B [SA602A]
HT93LC76 (08bit)@TSSOP8 [SA643]	HT93LC76 (16bit)
HT93LC76 (16bit)@SOP8-A [SA602A]	HT93LC76 (16bit)@SOP8-B [SA602A]
HT93LC76 (16bit)@TSSOP8 [SA643]	HT93LC86 (08bit)
HT93LC86 (08bit)@SOP8-A [SA602A]	HT93LC86 (08bit)@SOP8-B [SA602A]
HT93LC86 (08bit)@TSSOP8 [SA643]	HT93LC86 (16bit)
HT93LC86 (16bit)@SOP8-A [SA602A]	HT93LC86 (16bit)@SOP8-B [SA602A]
HT93LC86 (16bit)@TSSOP8 [SA643]	

## MICROCONTROLLER

HT46R22	HT46R22@SOP24 [SA404]
HT46R23 (dip24)	HT46R23 (dip28)
HT46R23@SOP24 [SA404]	HT46R23@SOP28 [SA404]
HT46R232	HT46R232@SOP28 [SA404]
HT46R232@SSOP48 [SA669]	HT46R24
HT46R24@SOP28 [SA404]	HT46R24@SSOP48 [SA669]
HT46R342@QFP44 [SA675-B4805]	HT46R46 (dip18)
HT46R46 (dip20)	HT46R46@SOP18 [SA404]
HT46R46@SOP20 [SA404]	HT46R46@SSOP20 [SA674]
HT46R46-H	HT46R46-H@SOP18 [SA404]
HT46R47 (dip18)	HT46R47 (dip20)
HT46R47@SOP18 [SA404]	HT46R47@SOP20 [SA404]
HT46R47@SSOP20 [SA674]	HT46R47-H
HT46R47-H@SOP18 [SA404]	HT46R48 (dip20)
HT46R48 (dip24)	HT46R48@SOP20 [SA404]
HT46R48@SOP24 [SA404]	HT46R48@SSOP24 [SA674]
HT46R51A (dip18)	HT46R51A@SOP20 [SA404]
HT46R51A@SSOP20 [SA674]	HT46R52A (dip18)
HT46R52A@SOP20 [SA404]	HT46R52A@SSOP20 [SA674]
HT46R53A (dip28)	HT46R53A@SOP28 [SA404]
HT46R54A (dip28)	HT46R54A@SOP28 [SA404]
HT46RB50	HT46RB50@SOP28 [SA404]
HT46RB50@SSOP48 [SA669]	HT46RB70
HT46RB70@SOP28 [SA404]	HT46RB70@SSOP48 [SA669]
HT46RU22	HT46RU22@SOP24 [SA404]
HT46RU22@SSOP24 [SA674]	HT46RU25@SSOP48 [SA669]
HT47R10A@QFP44 [SA675-B4805]	HT48R05A
HT48R05A@SOP16 [SA026]	HT48R05A@SOP18 [SA404]

HT48R06A  
HT48R06A@SOP18 [SA404]  
HT48R07A@SOP24 [SA404]  
HT48R08A  
HT48R08A@SOP18 [SA404]  
HT48R09A@SOP24 [SA404]  
HT48R10A  
HT48R30A(dip24)  
HT48R30A@SOP24 [SA404]  
HT48R502A@SSOP48 [SA669]  
HT48R50A@SOP28 [SA669]  
HT48R52A@QFP44 [SA675-B4805]  
HT48R70A@SSOP48 [SA669]  
HT48RA0-1@SOP24 [SA404]  
HT48RA0-2@SOP20 [SA404]  
HT48RA0-3  
HT48RA1@SOP28 [SA404]  
HT48RA3  
HT48RA3@SSOP28 [SA674]  
HT48RA5@SOP28 [SA404]  
HT48RB50  
HT48RB50@SSOP48 [SA669]  
HT48RB8@SSOP48 [SA669]  
HT49R30A@SSOP48 [SA669]  
HT82A523R@LQFP32 [SA636]  
HT82A821R@SSOP24 [SA674]  
HT82A832R@QFP48 [SA248-B4804]  
HT82J97E@SOP20 [SA404]  
HT82K68E  
HT82K68E@SOP28 [SA404]  
HT82K94E@SSOP48 [SA669]  
HT82K95A@SOP28 [SA404]  
HT82K95E@QFN32 [SA686]  
HT82K95E@SOP28 [SA404]  
HT82K96A@SOP28 [SA404]  
HT82K96E(dip20)  
HT82K96E@SOP20 [SA404]  
HT82K96E@SSOP48 [SA669]  
HT82M99E(dip20)  
HT82M99E@SOP20 [SA404]  
HT82M9AE@SOP24 [SA404]  
HT82M9AE@SSOP24 [SA674]  
HT82M9BE@SOP28 [SA404]  
HT82M9BE@SSOP28 [SA626A]  
HT95A10P@SOP28 [SA404]  
HT95A20P@SSOP48 [SA669]  
HT95A30P@SSOP48 [SA669]  
HT48R06A@SOP16 [SA602]  
HT48R07A  
HT48R07A@SSOP24 [SA674]  
HT48R08A@SOP16 [SA026]  
HT48R09A  
HT48R09A@SSOP24 [SA674]  
HT48R10A@SOP24 [SA404]  
HT48R30A(dip28)  
HT48R30A@SOP28 [SA404]  
HT48R50A  
HT48R50A@SSOP48 [SA669]  
HT48R54A@QFP44 [SA675-B4805]  
HT48RA0-1  
HT48RA0-2  
HT48RA0-2@SSOP20 [SA674]  
HT48RA0-3@SOP20 [SA404]  
HT48RA1@SSOP28 [SA626A]  
HT48RA3@SOP28 [SA404]  
HT48RA5  
HT48RA5@SSOP28 [SA674]  
HT48RB50@SOP28 [SA404]  
HT48RB8@SOP28 [SA404]  
HT49R10A@QFP44 [SA675-B4805]  
HT49R50A@SSOP48 [SA669]  
HT82A821R@SOP24 [SA404]  
HT82A822R@SSOP48 [SA669]  
HT82A832R@SSOP48 [SA669]  
HT82J97E@SOP28 [SA404]  
HT82K68E@SOP20 [SA404]  
HT82K68E@SSOP48 [SA669]  
HT82K95A@QFN32 [SA686]  
HT82K95A@SSOP48 [SA669]  
HT82K95E@SOP20 [SA404]  
HT82K95E@SSOP48 [SA669]  
HT82K96A@SSOP48 [SA669]  
HT82K96E(dip40)  
HT82K96E@SOP28 [SA404]  
HT82M99E(dip18)  
HT82M99E@SOP18 [SA404]  
HT82M9AE@SOP20 [SA404]  
HT82M9AE@SSOP20 [SA674]  
HT82M9BE@SOP24 [SA404]  
HT82M9BE@SSOP24 [SA674]  
HT95A100@SOP28 [SA404]  
HT95A200@SSOP48 [SA669]  
HT95A300@SSOP48 [SA669]

## HONGKONG

E (E) PROM/FRAM/NVRAM

HK1215  
HK1235  
HK1255  
HK1275  
HK1295  
HK12B5  
OKS1235  
OKS1255  
OKS1275  
OKS1295  
OKS12B5

HK1225  
HK1245  
HK1265  
HK1285  
HK12A5  
OKS1225  
OKS1245  
OKS1265  
OKS1285  
OKS12A5

## HOPEFIND

### E (E) PROM/FRAM/NVRAM

HM24LC01  
HM24LC01@TSSOP8 [SA643]  
HM24LC02@SOP8 [SA602A]  
HM24LC04  
HM24LC04@TSSOP8 [SA643]  
HM24LC08@SOP8 [SA602A]  
HM24LC16  
HM24LC16@TSSOP8 [SA643]

HM24LC01@SOP8 [SA602A]  
HM24LC02  
HM24LC02@TSSOP8 [SA643]  
HM24LC04@SOP8 [SA602A]  
HM24LC08  
HM24LC08@TSSOP8 [SA643]  
HM24LC16@SOP8 [SA602A]

## HUAJIE Technology

### E (E) PROM/FRAM/NVRAM

K24C02  
K24C02@TSSOP8 [SA643]  
K24C02C@SOP8 [SA602A]  
K24C04  
K24C04@TSSOP8 [SA643]  
K24C04C@SOP8 [SA602A]  
K24C08  
K24C08@TSSOP8 [SA643]  
K24C08C@SOP8 [SA602A]  
K24C16  
K24C16@TSSOP8 [SA643]  
K24C16C@SOP8 [SA602A]  
K34C02  
K34C02@TSSOP8 [SA643]

K24C02@SOP8 [SA602A]  
K24C02C  
K24C02C@TSSOP8 [SA643]  
K24C04@SOP8 [SA602A]  
K24C04C  
K24C04C@TSSOP8 [SA643]  
K24C08@SOP8 [SA602A]  
K24C08C  
K24C08C@TSSOP8 [SA643]  
K24C16@SOP8 [SA602A]  
K24C16C  
K24C16C@TSSOP8 [SA643]  
K34C02@SOP8 [SA602A]

## HYNIX

### E (E) PROM/FRAM/NVRAM

H27U1G8F2BTR@TSOP48 [SB247-B4806]  
H27U2G8F2CTR@TSIP48 [SB247-B4806]  
H27U4G8F2DTR@TSOP48 [SB247-B4806]

H27U4G8T2BTR@TSOP48 [SB247-B4806]  
HY2764  
HY27UF081G2A@TSOP48 [SB247-B4806]  
HY27UF084G2B@TSOP48 [SB247-B4806]  
HY29DL162BT@TSOP48 [SB247-B4806]  
HY29DL163BT@TSOP48 [SB247-B4806]  
HY29DS162BT@TSOP48 [SB247-B4806]  
HY29DS163BT@TSOP48 [SB247-B4806]  
HY29F002T  
HY29F002T@TSOP32 [SA410T-B4001]  
HY29F040@PLCC32 [SA015A1T]  
HY29F040A  
HY29F040A@TSOP32 [SA410T-B4001]  
HY29F200B@PSOP44 [SA638]  
HY29F200T@PSOP44 [SA638]  
HY29F400ABG@PSOP44 [SA638]  
HY29F400ATG@PSOP44 [SA638]  
HY29F400BG@PSOP44 [SA638]  
HY29F400TG@PSOP44 [SA638]  
HY29F800ABG@PSOP44 [SA638]  
HY29F800ATG@PSOP44 [SA638]  
HY29F800BG@PSOP44 [SA638]  
HY29F800TG@PSOP44 [SA638]  
HY29LV160BT@TSOP48 [SB247-B4806]  
HY29LV320BT@TSOP48 [SB247-B4806]  
HY29LV400BT@TSOP48 [SB247-B4806]  
HY29LV800BG@PSOP44 [SA638]  
HY29LV800TG@PSOP44 [SA638]  
HY93C46  
HY93C56  
HY93C66  
HY93C76  
HY93C86

HY27C64A  
HY29DL162TT@TSOP48 [SB247-B4806]  
HY29DL163TT@TSOP48 [SB247-B4806]  
HY29DS162TT@TSOP48 [SB247-B4806]  
HY29DS163TT@TSOP48 [SB247-B4806]  
HY29F002T@PLCC32 [SA015A1T]  
HY29F040  
HY29F040@TSOP32 [SA410T-B4001]  
HY29F040A@PLCC32 [SA015A1T]  
HY29F080@TSOP40 [SA409T-B4002]  
HY29F200B@TSOP48 [SB247-B4806]  
HY29F200T@TSOP48 [SB247-B4806]  
HY29F400ABT@TSOP48 [SB247-B4806]  
HY29F400ATT@TSOP48 [SB247-B4806]  
HY29F400BT@TSOP48 [SB247-B4806]  
HY29F400TT@TSOP48 [SB247-B4806]  
HY29F800ABT@TSOP48 [SB247-B4806]  
HY29F800ATT@TSOP48 [SB247-B4806]  
HY29F800BT@TSOP48 [SB247-B4806]  
HY29F800TT@TSOP48 [SB247-B4806]  
HY29LV160TT@TSOP48 [SB247-B4806]  
HY29LV320TT@TSOP48 [SB247-B4806]  
HY29LV400TT@TSOP48 [SB247-B4806]  
HY29LV800BT@TSOP48 [SB247-B4806]  
HY29LV800TT@TSOP48 [SB247-B4806]  
HY93C46@SOIC8 [SA602A]  
HY93C56@SOIC8 [SA602A]  
HY93C66@SOIC8 [SA602A]  
HY93C76@SOIC8 [SA602A]  
HY93C86@SOIC8 [SA602A]

## DRAM & SRAM

HY62256A  
HY6264A  
HY62256A@TSOP28 [SA643]  
HY6264A@TSOP28 [SA643]

## MICROCONTROLLER

GMS34004TK  
GMS34004TW  
GMS34112TK@SOIC20 [SA404]  
GMS34140TK  
GMS81004 (dip20)  
GMS81004 (dip28)  
GMS81004@SOIC20 [SA404]  
GMS81004@SOIC28 [SA404]  
GMS81008 (dip24)  
GMS81008@PLCC44 [SA244]  
GMS81008@SOIC24 [SA404]  
GMS34004TM  
GMS34112TK  
GMS34112TK@SSOP20 [SA626A]  
GMS34140TK@SOIC24 [SA404]  
GMS81004 (dip24)  
GMS81004@PLCC44 [SA244]  
GMS81004@SOIC24 [SA404]  
GMS81008 (dip20)  
GMS81008 (dip28)  
GMS81008@SOIC20 [SA404]  
GMS81008@SOIC28 [SA404]

GMS81016 (dip20)	GMS81016 (dip24)
GMS81016 (dip28)	GMS81016@PLCC44 [SA244]
GMS81016@S0IC20 [SA404]	GMS81016@S0IC24 [SA404]
GMS81016@S0IC28 [SA404]	GMS81024 (dip20)
GMS81024 (dip24)	GMS81024 (dip28)
GMS81024@PLCC44 [SA244]	GMS81024@S0IC20 [SA404]
GMS81024@S0IC24 [SA404]	GMS81024@S0IC28 [SA404]
GMS81032 (dip20)	GMS81032 (dip24)
GMS81032 (dip28)	GMS81032@PLCC44 [SA244]
GMS81032@S0IC20 [SA404]	GMS81032@S0IC24 [SA404]
GMS81032@S0IC28 [SA404]	GMS81504AT [SA653]
GMS81504T [SA653]	GMS81516
GMS81516AT	GMS81516BT
GMS81524	GMS81524AT
GMS81524BT	GMS81604T
GMS81604T@PLCC44 [SA244]	GMS81604T@SDIP42 [SA028]
GMS81608T	GMS81608T@PLCC44 [SA244]
GMS81608T@SDIP42 [SA028]	GMS81C5016 (dip28)
GMS81C5016 (dip40)	GMS81C5016@PLCC44 [SA244]
GMS81C5016@S0IC28 [SA404]	GMS81C5016@TQFP44 [SA675-B4805]
GMS81C5024 (dip28)	GMS81C5024 (dip40)
GMS81C5024@PLCC44 [SA244]	GMS81C5024@S0IC28 [SA404]
GMS81C5024@TQFP44 [SA675-B4805]	GMS81C5032 (dip28)
GMS81C5032 (dip40)	GMS81C5032@PLCC44 [SA244]
GMS81C5032@S0IC28 [SA404]	GMS81C5032@TQFP44 [SA675-B4805]
GMS82516T	GMS82516T@MQFP44 [SA675-B4805]
GMS82516T@SDIP42 [SA028]	GMS82524T
GMS82524T@MQFP44 [SA675-B4805]	GMS82524T@SDIP42 [SA028]
GMS87C1102	GMS87C1102@SOP16 [SA404]
GMS87C1202	GMS87C1202@SOP20 [SA404]
GMS87C1404	GMS87C1404@SOP28 [SA404]
GMS87C1408	GMS87C1408@SOP28 [SA404]
GMS87C5032 (dip28)	GMS87C5032 (dip40)
GMS87C5032@PLCC44 [SA244]	GMS87C5032@S0IC28 [SA404]
GMS87C5032@TQFP44 [SA675-B4805]	GMS97C1051
GMS97C1051@S0IC20 [SA404]	GMS97C2051
GMS97C2051@S0IC20 [SA404]	GMS97C51
GMS97C51@PLCC44 [SA244]	GMS97C51@TQFP44 [SA675-B4805]
GMS97C52	GMS97C52@PLCC44 [SA244]
GMS97C52@TQFP44 [SA675-B4805]	GMS97C54
GMS97C54@PLCC44 [SA244]	GMS97C54@TQFP44 [SA675-B4805]
GMS97C56	GMS97C56@PLCC44 [SA244]
GMS97C56@TQFP44 [SA675-B4805]	GMS97C58
GMS97C58@PLCC44 [SA244]	GMS97C58@TQFP44 [SA675-B4805]
GMS97L1051	GMS97L1051@S0IC20 [SA404]
GMS97L2051	GMS97L2051@S0IC20 [SA404]
GMS97L51	GMS97L51@PLCC44 [SA244]
GMS97L51@TQFP44 [SA675-B4805]	GMS97L52
GMS97L52@PLCC44 [SA244]	GMS97L52@TQFP44 [SA675-B4805]
GMS97L54	GMS97L54@PLCC44 [SA244]
GMS97L54@TQFP44 [SA675-B4805]	GMS97L56
GMS97L56@PLCC44 [SA244]	GMS97L56@TQFP44 [SA675-B4805]
GMS97L58	GMS97L58@PLCC44 [SA244]

GMS97L58@TQFP44 [SA675-B4805]  
GMS99C51@PLCC44 [SA244]  
GMS99C52  
GMS99C52@TQFP44 [SA675-B4805]  
GMS99C58@PLCC44 [SA244]  
HMS81004E (dip20)  
HMS81004E (dip28)  
HMS81004E@SOIC20 [SA404]  
HMS81004E@SOIC28 [SA404]  
HMS81008E (dip24)  
HMS81008E@PLCC44 [SA244]  
HMS81008E@SOIC24 [SA404]  
HMS81016E (dip20)  
HMS81016E (dip28)  
HMS81016E@SOIC20 [SA404]  
HMS81016E@SOIC28 [SA404]  
HMS81020ET (dip24)  
HMS81020ET@SOIC20 [SA404]  
HMS81020ET@SOIC28 [SA404]  
HMS81020TL (dip24)  
HMS81020TL@SOIC20 [SA404]  
HMS81020TL@SOIC28 [SA404]  
HMS81024E (dip24)  
HMS81024E@PLCC44 [SA244]  
HMS81024E@SOIC24 [SA404]  
HMS81032 (dip20)  
HMS81032 (dip28)  
HMS81032@SOIC24 [SA404]  
HMS81032ET (dip20)  
HMS81032ET (dip28)  
HMS81032ET@SOIC24 [SA404]  
HMS81032T (dip20)  
HMS81032T (dip28)  
HMS81032T@SOIC24 [SA404]  
HMS81032TL (dip20)  
HMS81032TL (dip28)  
HMS81032TL@SOIC24 [SA404]  
HMS87C1102A  
HMS87C1104A  
HMS87C1202A  
HMS87C1204A  
HMS87C1302A@SDIP24 [SA653]  
HMS87C1304A@SDIP24 [SA653]  
HMS87C1404B  
HMS87C1404B@SOIC28 [SA404]  
HMS87C1408B@SDIP28 [SA653]  
HMS87C1416B  
HMS87C1416B@SOIC28 [SA404]  
HMS87C1516B  
HMS87C1616B  
HMS87C1716B@SDIP42 [SA028]  
HMS87C1816B@TQFP44 [SA675-B4805]  
HMS87C5216@PLCC44 [SA244]

GMS99C51  
GMS99C51@TQFP44 [SA675-B4805]  
GMS99C52@PLCC44 [SA244]  
GMS99C58  
GMS99C58@TQFP44 [SA675-B4805]  
HMS81004E (dip24)  
HMS81004E@PLCC44 [SA244]  
HMS81004E@SOIC24 [SA404]  
HMS81008E (dip20)  
HMS81008E (dip28)  
HMS81008E@SOIC20 [SA404]  
HMS81008E@SOIC28 [SA404]  
HMS81016E (dip24)  
HMS81016E@PLCC44 [SA244]  
HMS81016E@SOIC24 [SA404]  
HMS81020ET (dip20)  
HMS81020ET (dip28)  
HMS81020ET@SOIC24 [SA404]  
HMS81020TL (dip20)  
HMS81020TL (dip28)  
HMS81020TL@SOIC24 [SA404]  
HMS81024E (dip20)  
HMS81024E (dip28)  
HMS81024E@SOIC20 [SA404]  
HMS81024E@SOIC28 [SA404]  
HMS81032 (dip24)  
HMS81032@SOIC20 [SA404]  
HMS81032@SOIC28 [SA404]  
HMS81032ET (dip24)  
HMS81032ET@SOIC20 [SA404]  
HMS81032ET@SOIC28 [SA404]  
HMS81032T (dip24)  
HMS81032T@SOIC20 [SA404]  
HMS81032T@SOIC28 [SA404]  
HMS81032TL (dip24)  
HMS81032TL@SOIC20 [SA404]  
HMS81032TL@SOIC28 [SA404]  
HMS87C1102A@SOP16 [SA404]  
HMS87C1104A@SOP16 [SA404]  
HMS87C1202A@SOP20 [SA404]  
HMS87C1204A@SOP20 [SA404]  
HMS87C1302A@SOP24 [SA404]  
HMS87C1304A@SOP24 [SA404]  
HMS87C1404B@SDIP28 [SA653]  
HMS87C1408B  
HMS87C1408B@SOIC28 [SA404]  
HMS87C1416B@SDIP28 [SA653]  
HMS87C1508B  
HMS87C1608B  
HMS87C1708B@SDIP42 [SA028]  
HMS87C1808B@TQFP44 [SA675-B4805]  
HMS87C5216  
HMS87C5216@SOIC28 [SA404]

HMS87C5216@TQFP44 [SA675-B4805]  
HMS99C51@PLCC44 [SA244]  
HMS99C52  
HMS99C52@TQFP44 [SA675-B4805]  
HMS99C58@PLCC44 [SA244]

HMS99C51  
HMS99C51@TQFP44 [SA675-B4805]  
HMS99C52@PLCC44 [SA244]  
HMS99C58  
HMS99C58@TQFP44 [SA675-B4805]

## HYNIX-CUSTOMER

### E (E) PROM/FRAM/NVRAM

HY27UF082G2B (SP)@TSOP48 [SB247-B4806]

## HYUNDAI

### E (E) PROM/FRAM/NVRAM

HY2764  
HY29DL162BT@TSOP48 [SB247-B4806]  
HY29DL163BT@TSOP48 [SB247-B4806]  
HY29DS162BT@TSOP48 [SB247-B4806]  
HY29DS163BT@TSOP48 [SB247-B4806]  
HY29F002T  
HY29F002T@TSOP32 [SA410T-B4001]  
HY29F040@PLCC32 [SA015A1T]  
HY29F040A  
HY29F040A@TSOP32 [SA410T-B4001]  
HY29F200B@PSOP44 [SA638]  
HY29F200T@PSOP44 [SA638]  
HY29F400ABG@PSOP44 [SA638]  
HY29F400ATG@PSOP44 [SA638]  
HY29F400BG@PSOP44 [SA638]  
HY29F400TG@PSOP44 [SA638]  
HY29F800ABG@PSOP44 [SA638]  
HY29F800ATG@PSOP44 [SA638]  
HY29F800BG@PSOP44 [SA638]  
HY29F800TG@PSOP44 [SA638]  
HY29LV160BT@TSOP48 [SB247-B4806]  
HY29LV320BT@TSOP48 [SB247-B4806]  
HY29LV400BT@TSOP48 [SB247-B4806]  
HY29LV800BG@PSOP44 [SA638]  
HY29LV800TG@PSOP44 [SA638]  
HY93C46  
HY93C56  
HY93C66  
HY93C76  
HY93C86

HY27C64A  
HY29DL162TT@TSOP48 [SB247-B4806]  
HY29DL163TT@TSOP48 [SB247-B4806]  
HY29DS162TT@TSOP48 [SB247-B4806]  
HY29DS163TT@TSOP48 [SB247-B4806]  
HY29F002T@PLCC32 [SA015A1T]  
HY29F040  
HY29F040@TSOP32 [SA410T-B4001]  
HY29F040A@PLCC32 [SA015A1T]  
HY29F080@TSOP40 [SA409T-B4002]  
HY29F200B@TSOP48 [SB247-B4806]  
HY29F200T@TSOP48 [SB247-B4806]  
HY29F400ABT@TSOP48 [SB247-B4806]  
HY29F400ATT@TSOP48 [SB247-B4806]  
HY29F400BT@TSOP48 [SB247-B4806]  
HY29F400TT@TSOP48 [SB247-B4806]  
HY29F800ABT@TSOP48 [SB247-B4806]  
HY29F800ATT@TSOP48 [SB247-B4806]  
HY29F800BT@TSOP48 [SB247-B4806]  
HY29F800TT@TSOP48 [SB247-B4806]  
HY29LV160TT@TSOP48 [SB247-B4806]  
HY29LV320TT@TSOP48 [SB247-B4806]  
HY29LV400TT@TSOP48 [SB247-B4806]  
HY29LV800BT@TSOP48 [SB247-B4806]  
HY29LV800TT@TSOP48 [SB247-B4806]  
HY93C46@SOIC8 [SA602A]  
HY93C56@SOIC8 [SA602A]  
HY93C66@SOIC8 [SA602A]  
HY93C76@SOIC8 [SA602A]  
HY93C86@SOIC8 [SA602A]

### DRAM & SRAM

HY62256A  
HY6264A

HY62256A@TSOP28 [SA643]  
HY6264A@TSOP28 [SA643]

## MICROCONTROLLER

GMS34004TK  
GMS34004TW  
GMS34112TK@SOIC20 [SA404]  
GMS34140TK  
GMS81004 (dip20)  
GMS81004 (dip28)  
GMS81004@SOIC20 [SA404]  
GMS81004@SOIC28 [SA404]  
GMS81008 (dip24)  
GMS81008@PLCC44 [SA244]  
GMS81008@SOIC24 [SA404]  
GMS81016 (dip20)  
GMS81016 (dip28)  
GMS81016@SOIC20 [SA404]  
GMS81016@SOIC28 [SA404]  
GMS81024 (dip24)  
GMS81024@PLCC44 [SA244]  
GMS81024@SOIC24 [SA404]  
GMS81032 (dip20)  
GMS81032 (dip28)  
GMS81032@SOIC20 [SA404]  
GMS81032@SOIC28 [SA404]  
GMS81504T [SA653]  
GMS81516AT  
GMS81524  
GMS81524BT  
GMS81604T@PLCC44 [SA244]  
GMS81608T  
GMS81608T@SDIP42 [SA028]  
GMS81C5016 (dip40)  
GMS81C5016@SOIC28 [SA404]  
GMS81C5024 (dip28)  
GMS81C5024@PLCC44 [SA244]  
GMS81C5024@TQFP44 [SA675-B4805]  
GMS81C5032 (dip40)  
GMS81C5032@SOIC28 [SA404]  
GMS82516T  
GMS82516T@SDIP42 [SA028]  
GMS82524T@MQFP44 [SA675-B4805]  
GMS87C1102  
GMS87C1202  
GMS87C1404  
GMS87C1408  
GMS87C5032 (dip28)  
GMS87C5032@PLCC44 [SA244]  
GMS87C5032@TQFP44 [SA675-B4805]  
GMS97C1051@SOIC20 [SA404]  
GMS97C2051@SOIC20 [SA404]  
GMS97C51@PLCC44 [SA244]

GMS34004TM  
GMS34112TK  
GMS34112TK@SSOP20 [SA626A]  
GMS34140TK@SOIC24 [SA404]  
GMS81004 (dip24)  
GMS81004@PLCC44 [SA244]  
GMS81004@SOIC24 [SA404]  
GMS81008 (dip20)  
GMS81008 (dip28)  
GMS81008@SOIC20 [SA404]  
GMS81008@SOIC28 [SA404]  
GMS81016 (dip24)  
GMS81016@PLCC44 [SA244]  
GMS81016@SOIC24 [SA404]  
GMS81024 (dip20)  
GMS81024 (dip28)  
GMS81024@SOIC20 [SA404]  
GMS81024@SOIC28 [SA404]  
GMS81032 (dip24)  
GMS81032@PLCC44 [SA244]  
GMS81032@SOIC24 [SA404]  
GMS81504AT [SA653]  
GMS81516  
GMS81516BT  
GMS81524AT  
GMS81604T  
GMS81604T@SDIP42 [SA028]  
GMS81608T@PLCC44 [SA244]  
GMS81C5016 (dip28)  
GMS81C5016@PLCC44 [SA244]  
GMS81C5016@TQFP44 [SA675-B4805]  
GMS81C5024 (dip40)  
GMS81C5024@SOIC28 [SA404]  
GMS81C5032 (dip28)  
GMS81C5032@PLCC44 [SA244]  
GMS81C5032@TQFP44 [SA675-B4805]  
GMS82516T@MQFP44 [SA675-B4805]  
GMS82524T  
GMS82524T@SDIP42 [SA028]  
GMS87C1102@SOP16 [SA404]  
GMS87C1202@SOP20 [SA404]  
GMS87C1404@SOP28 [SA404]  
GMS87C1408@SOP28 [SA404]  
GMS87C5032 (dip40)  
GMS87C5032@SOIC28 [SA404]  
GMS97C1051  
GMS97C2051  
GMS97C51  
GMS97C51@TQFP44 [SA675-B4805]

GMS97C52  
GMS97C52@TQFP44 [SA675-B4805]  
GMS97C54@PLCC44 [SA244]  
GMS97C56  
GMS97C56@TQFP44 [SA675-B4805]  
GMS97C58@PLCC44 [SA244]  
GMS97L1051  
GMS97L2051  
GMS97L51  
GMS97L51@TQFP44 [SA675-B4805]  
GMS97L52@PLCC44 [SA244]  
GMS97L54  
GMS97L54@TQFP44 [SA675-B4805]  
GMS97L56@PLCC44 [SA244]  
GMS97L58  
GMS97L58@TQFP44 [SA675-B4805]  
GMS99C51@PLCC44 [SA244]  
GMS99C52  
GMS99C52@TQFP44 [SA675-B4805]  
GMS99C58@PLCC44 [SA244]  
HMS81004E (dip20)  
HMS81004E (dip28)  
HMS81004E@SOIC20 [SA404]  
HMS81004E@SOIC28 [SA404]  
HMS81008E (dip24)  
HMS81008E@PLCC44 [SA244]  
HMS81008E@SOIC24 [SA404]  
HMS81016E (dip20)  
HMS81016E (dip28)  
HMS81016E@SOIC20 [SA404]  
HMS81016E@SOIC28 [SA404]  
HMS81020ET (dip24)  
HMS81020ET@SOIC20 [SA404]  
HMS81020ET@SOIC28 [SA404]  
HMS81020TL (dip24)  
HMS81020TL@SOIC20 [SA404]  
HMS81020TL@SOIC28 [SA404]  
HMS81024E (dip24)  
HMS81024E@PLCC44 [SA244]  
HMS81024E@SOIC24 [SA404]  
HMS81032 (dip20)  
HMS81032 (dip28)  
HMS81032@SOIC24 [SA404]  
HMS81032ET (dip20)  
HMS81032ET (dip28)  
HMS81032ET@SOIC24 [SA404]  
HMS81032T (dip20)  
HMS81032T (dip28)  
HMS81032T@SOIC24 [SA404]  
HMS81032TL (dip20)  
HMS81032TL (dip28)  
HMS81032TL@SOIC24 [SA404]  
HMS87C1102A

GMS97C52@PLCC44 [SA244]  
GMS97C54  
GMS97C54@TQFP44 [SA675-B4805]  
GMS97C56@PLCC44 [SA244]  
GMS97C58  
GMS97C58@TQFP44 [SA675-B4805]  
GMS97L1051@SOIC20 [SA404]  
GMS97L2051@SOIC20 [SA404]  
GMS97L51@PLCC44 [SA244]  
GMS97L52  
GMS97L52@TQFP44 [SA675-B4805]  
GMS97L54@PLCC44 [SA244]  
GMS97L56  
GMS97L56@TQFP44 [SA675-B4805]  
GMS97L58@PLCC44 [SA244]  
GMS99C51  
GMS99C51@TQFP44 [SA675-B4805]  
GMS99C52@PLCC44 [SA244]  
GMS99C58  
GMS99C58@TQFP44 [SA675-B4805]  
HMS81004E (dip24)  
HMS81004E@PLCC44 [SA244]  
HMS81004E@SOIC24 [SA404]  
HMS81008E (dip20)  
HMS81008E (dip28)  
HMS81008E@SOIC20 [SA404]  
HMS81008E@SOIC28 [SA404]  
HMS81016E (dip24)  
HMS81016E@PLCC44 [SA244]  
HMS81016E@SOIC24 [SA404]  
HMS81020ET (dip20)  
HMS81020ET (dip28)  
HMS81020ET@SOIC24 [SA404]  
HMS81020TL (dip20)  
HMS81020TL (dip28)  
HMS81020TL@SOIC24 [SA404]  
HMS81024E (dip20)  
HMS81024E (dip28)  
HMS81024E@SOIC20 [SA404]  
HMS81024E@SOIC28 [SA404]  
HMS81032 (dip24)  
HMS81032@SOIC20 [SA404]  
HMS81032@SOIC28 [SA404]  
HMS81032ET (dip24)  
HMS81032ET@SOIC20 [SA404]  
HMS81032ET@SOIC28 [SA404]  
HMS81032T (dip24)  
HMS81032T@SOIC20 [SA404]  
HMS81032T@SOIC28 [SA404]  
HMS81032TL (dip24)  
HMS81032TL@SOIC20 [SA404]  
HMS81032TL@SOIC28 [SA404]  
HMS87C1102A@SOP16 [SA404]

HMS87C1104A	HMS87C1104A@SOP16 [SA404]
HMS87C1202A	HMS87C1202A@SOP20 [SA404]
HMS87C1204A	HMS87C1204A@SOP20 [SA404]
HMS87C1302A@SDIP24 [SA653]	HMS87C1302A@SOP24 [SA404]
HMS87C1304A@SDIP24 [SA653]	HMS87C1304A@SOP24 [SA404]
HMS87C1404B	HMS87C1404B@SDIP28 [SA653]
HMS87C1404B@SOIC28 [SA404]	HMS87C1408B
HMS87C1408B@SDIP28 [SA653]	HMS87C1408B@SOIC28 [SA404]
HMS87C1416B	HMS87C1416B@SDIP28 [SA653]
HMS87C1416B@SOIC28 [SA404]	HMS87C1508B
HMS87C1516B	HMS87C1608B
HMS87C1616B	HMS87C1708B@SDIP42 [SA028]
HMS87C1716B@SDIP42 [SA028]	HMS87C1808B@TQFP44 [SA675-B4805]
HMS87C1816B@TQFP44 [SA675-B4805]	HMS87C5216
HMS87C5216@PLCC44 [SA244]	HMS87C5216@SOIC28 [SA404]
HMS87C5216@TQFP44 [SA675-B4805]	HMS99C51
HMS99C51@PLCC44 [SA244]	HMS99C51@TQFP44 [SA675-B4805]
HMS99C52	HMS99C52@PLCC44 [SA244]
HMS99C52@TQFP44 [SA675-B4805]	HMS99C58
HMS99C58@PLCC44 [SA244]	HMS99C58@TQFP44 [SA675-B4805]

## IC Microsystems

### E (E) PROM/FRAM/NVRAM

X24C00	X24C00@MSOP8 [SA666]
X24C00@SOIC8 [SA602A]	X24C01
X24C01@MSOP8 [SA666]	X24C01@SOIC14 [SA602]
X24C01@SOIC8 [SA602A]	X24C01A
X24C01A@MSOP8 [SA666]	X24C01A@SOIC8 [SA602A]
X24C02	X24C02@MSOP8 [SA666]
X24C02@SOIC14 [SA602]	X24C02@SOIC8 [SA602A]
X24C04	X24C04@MSOP8 [SA666]
X24C04@SOIC14 [SA602]	X24C04@SOIC8 [SA602A]
X24C08	X24C08@MSOP8 [SA666]
X24C08@SOIC14 [SA602]	X24C08@SOIC8 [SA602A]
X24C16	X24C16@MSOP8 [SA666]
X24C16@SOIC14 [SA602]	X24C16@SOIC8 [SA602A]

## ICE

### E (E) PROM/FRAM/NVRAM

ICE25P05	ICE25P05@SOIC8 [SA602A]
ICE27C010	ICE27C010@PLCC32 [SA015A1T]
ICE27C010@TSOP32 [SA410T-B4001]	ICE27C020
ICE27C020@PLCC32 [SA015A1T]	ICE27C020@TSOP32 [SA410T-B4001]
ICE27C512	ICE27C512@PLCC32 [SA015A1T]
ICE27C512@TSOP28 [SA430T-B4003]	ICE27LC010
ICE27LC010@PLCC32 [SA015A1T]	ICE27LC010@TSOP32 [SA410T-B4001]
ICE27LC020	ICE27LC020@PLCC32 [SA015A1T]
ICE27LC020@TSOP32 [SA410T-B4001]	ICE27LC512

ICE27LC512@PLCC32 [SA015A1T]  
ICE28LF010  
ICE37C512  
ICE37C512@TSOP32 [SA410T-B4001]  
ICE37LC512@PLCC32 [SA015A1T]

ICE27LC512@TSOP28 [SA430T-B4003]  
ICE28LF010@PLCC32 [SA015A1T]  
ICE37C512@PLCC32 [SA015A1T]  
ICE37LC512  
ICE37LC512@TSOP32 [SA410T-B4001]

## ICMIC

### E (E) PROM/FRAM/NVRAM

X76F101  
X76F400@SOIC8 [SA026]

X76F101@SOIC8 [SA602A]  
X76F400@TSSOP8 [SA026]

## ICSI

### MICROCONTROLLER

IC89LV51A  
IC89LV51A@TQFP44 [SA675-B4805]  
IC89LV52A@PLCC44 [SA244]  
IS89C51A  
IS89C51A@TQFP44 [SA675-B4805]  
IS89C52A@PLCC44 [SA244]  
IS89C54  
IS89C54@TQFP44 [SA675-B4805]  
IS89C58@PLCC44 [SA244]  
IS89C64  
IS89C64@TQFP44 [SA675-B4805]  
IS89E54@PLCC44 [SA244]  
IS89E58  
IS89E58@TQFP44 [SA675-B4805]  
IS89E64@PLCC44 [SA244]

IC89LV51A@PLCC44 [SA244]  
IC89LV52A  
IC89LV52A@TQFP44 [SA675-B4805]  
IS89C51A@PLCC44 [SA244]  
IS89C52A  
IS89C52A@TQFP44 [SA675-B4805]  
IS89C54@PLCC44 [SA244]  
IS89C58  
IS89C58@TQFP44 [SA675-B4805]  
IS89C64@PLCC44 [SA244]  
IS89E54  
IS89E54@TQFP44 [SA675-B4805]  
IS89E58@PLCC44 [SA244]  
IS89E64  
IS89E64@TQFP44 [SA675-B4805]

## ICT

### E (E) PROM/FRAM/NVRAM

27CX010  
27CX010@TSOP32 [SA410T-B4001]  
27CX321  
27CX641  
93C46  
93C46A  
93C56A  
93C66A  
93CX46  
93CX56  
93CX66

27CX010@PLCC32 [SA015A1T]  
27CX256  
27CX322  
27CX642  
93C46@SOIC8 [SA602A]  
93C46A@SOIC8 [SA602A]  
93C56A@SOIC8 [SA602A]  
93C66A@SOIC8 [SA602A]  
93CX46@SOIC8 [SA602A]  
93CX56@SOIC8 [SA602A]  
93CX66@SOIC8 [SA602A]

## PLD

PA7024  
PA7024(JN)@PLCC28 [SA008A]  
PA7140  
PA7140@TQFP44 [SA245A-B4805]  
PA7540(J)@PLCC28 [SA008A]  
PA7572  
PA7572@TQFP44 [SA245A-B4805]  
PEEL18CV8Z@PLCC20 [SA001A-B2001]  
PEEL18CV8Z@TSOP20 [SA026]  
PEEL18LV8Z@PLCC20 [SA001A-B2001]  
PEEL18LV8Z@TSOP20 [SA026]  
PEEL22CV10A@PLCC28 [SA008A]  
PEEL22CV10A@TSOP24 [SA026]  
PEEL22CV10A+@PLCC28 [SA008A]  
PEEL22CV10A+@TSOP24 [SA026]  
PEEL22CV10A++@PLCC28 [SA008A]  
PEEL22CV10A++@TSOP24 [SA026]  
PEEL22CV10AZ@PLCC28 [SA008A]  
PEEL22CV10AZ@TSOP24 [SA026]  
PEEL22CV10AZ+@PLCC28 [SA008A]  
PEEL22CV10AZ+@TSOP24 [SA026]  
PEEL22CV10AZ++@PLCC28 [SA008A]  
PEEL22CV10AZ++@TSOP24 [SA026]  
PEEL22LV10AZ@PLCC28 [SA008A]  
PEEL22LV10AZ@TSOP24 [SA026]  
PEEL22LV10AZ+@PLCC28 [SA008A]  
PEEL22LV10AZ+@TSOP24 [SA026]  
PEEL22LV10AZ++@PLCC28 [SA008A]  
PEEL22LV10AZ++@TSOP24 [SA026]

PA7024(J)@PLCC28 [SA008A]  
PA7024@SOIC24 [SA404]  
PA7140@PLCC44 [SA244]  
PA7540  
PA7540(JN)@PLCC28 [SA008A]  
PA7572@PLCC44 [SA244]  
PEEL18CV8Z  
PEEL18CV8Z@SOIC20 [SA404]  
PEEL18LV8Z  
PEEL18LV8Z@SOIC20 [SA404]  
PEEL22CV10A  
PEEL22CV10A@SOIC24 [SA404]  
PEEL22CV10A+  
PEEL22CV10A+@SOIC24 [SA404]  
PEEL22CV10A++  
PEEL22CV10A++@SOIC24 [SA404]  
PEEL22CV10AZ  
PEEL22CV10AZ@SOIC24 [SA404]  
PEEL22CV10AZ+  
PEEL22CV10AZ+@SOIC24 [SA404]  
PEEL22CV10AZ++  
PEEL22CV10AZ++@SOIC24 [SA404]  
PEEL22LV10AZ  
PEEL22LV10AZ@SOIC24 [SA404]  
PEEL22LV10AZ+  
PEEL22LV10AZ+@SOIC24 [SA404]  
PEEL22LV10AZ++  
PEEL22LV10AZ++@SOIC24 [SA404]

## IDT

### E (E) PROM/FRAM/NVRAM

IDT5V9885@TQFP32 [SA636]

IDT5V9885@VFQFPN28 [SA685]

## IK Semiconductor

### E (E) PROM/FRAM/NVRAM

IK24LC02B  
IK24LC04B  
IK24LC08B  
IK24LC16B

IK24LC02B@SOIC8 [SA602A]  
IK24LC04B@SOIC8 [SA602A]  
IK24LC08B@SOIC8 [SA602A]  
IK24LC16B@SOIC8 [SA602A]

## IMT

### E (E) PROM/FRAM/NVRAM

IM29F001B

IM29F001B (REVERSE)@TSOP32 [SA410T-B4001]	
IM29F001B@PLCC32 [SA015A1T]	IM29F001B@TSOP32 [SA410T-B4001]
IM29F001B@VSOP32 [SA620-B4807]	IM29F001T
IM29F001T (REVERSE)@TSOP32 [SA410T-B4001]	
IM29F001T@PLCC32 [SA015A1T]	IM29F001T@TSOP32 [SA410T-B4001]
IM29F001T@VSOP32 [SA620-B4807]	IM29F002B
IM29F002B (REVERSE)@TSOP32 [SA410T-B4001]	
IM29F002B@PLCC32 [SA015A1T]	IM29F002B@TSOP32 [SA410T-B4001]
IM29F002B@VSOP32 [SA620-B4807]	IM29F002T
IM29F002T (REVERSE)@TSOP32 [SA410T-B4001]	
IM29F002T@PLCC32 [SA015A1T]	IM29F002T@TSOP32 [SA410T-B4001]
IM29F002T@VSOP32 [SA620-B4807]	IM29F004B
IM29F004B (REVERSE)@TSOP32 [SA410T-B4001]	
IM29F004B@PLCC32 [SA015A1T]	IM29F004B@TSOP32 [SA410T-B4001]
IM29F004B@VSOP32 [SA620-B4807]	IM29F004T
IM29F004T (REVERSE)@TSOP32 [SA410T-B4001]	
IM29F004T@PLCC32 [SA015A1T]	IM29F004T@TSOP32 [SA410T-B4001]
IM29F004T@VSOP32 [SA620-B4807]	IM29LV004B
IM29LV004B (REVERSE)@TSOP32 [SA410T-B4001]	
IM29LV004B@PLCC32 [SA015A1T]	IM29LV004B@TSOP32 [SA410T-B4001]
IM29LV004B@VSOP32 [SA620-B4807]	IM29LV004T
IM29LV004T (REVERSE)@TSOP32 [SA410T-B4001]	
IM29LV004T@PLCC32 [SA015A1T]	IM29LV004T@TSOP32 [SA410T-B4001]
IM29LV004T@VSOP32 [SA620-B4807]	IM29LV400B@PSOP44 [SA638]
IM29LV400B@TSOP48 [SA247-B4806]	IM29LV400T@PSOP44 [SA638]
IM29LV400T@TSOP48 [SA247-B4806]	

## INFINEON

### MICROCONTROLLER

TLE7810G@SOIC28 [SA404]	XMC1100-T016F0008 [SA026]
XMC1100-T016F0016 [SA026]	XMC1100-T016F0064 [SA026]
XMC1100-T038F0016 [SA693]	XMC1100-T038F0032 [SA693]
XMC1100-T038F0064 [SA693]	XMC1201-T038F0016 [SA693]
XMC1201-T038F0032 [SA693]	XMC1201-T038F0064 [SA693]
XMC1201-T038F0200 [SA693]	XMC1202-T016X0016 [SA026]
XMC1202-T016X0032 [SA026]	XMC1202-T028X0016 [SA643]
XMC1202-T028X0032 [SA643]	XMC1301-T016F0008 [SA026]
XMC1301-T016F0016 [SA026]	XMC1301-T038F0008 [SA693]
XMC1301-T038F0016 [SA693]	XMC1301-T038F0032 [SA693]
XMC1301-T038F0064 [SA693]	XMC1302-T038X0016 [SA693]
XMC1302-T038X0032 [SA693]	XMC1302-T038X0064 [SA693]
XMC1302-T038X0200 [SA693]	

## INTEGRAL

### E (E) PROM/FRAM/NVRAM

IN24AA02A	IN24AA02A@SOIC8 [SA602A]
IN24AA02B	IN24AA02B@SOIC8 [SA602A]
IN24LC02B	IN24LC02B@SOIC8 [SA602A]

IN24LC04B  
IN24LC08B  
IN24LC16B

IN24LC04B@SOIC8 [SA602A]  
IN24LC08B@SOIC8 [SA602A]  
IN24LC16B@SOIC8 [SA602A]

## INTEL

### E (E) PROM/FRAM/NVRAM

27010	27010@PLCC32 [SA015A1T]
27010@TSOP32 [SA410T-B4001]	27128
27128A	27128B
2716	27210
27256	2732
2732A	27512
2764	2764A
27C010	27C010@PLCC32 [SA015A1T]
27C010@TSOP32 [SA410T-B4001]	27C010A
27C010A@PLCC32 [SA015A1T]	27C010A@TSOP32 [SA410T-B4001]
27C020	27C020@PLCC32 [SA015A1T]
27C020@TSOP32 [SA410T-B4001]	27C040
27C040@PLCC32 [SA015A1T]	27C040@TSOP32 [SA410T-B4001]
27C100	27C100@PLCC32 [SA015A1T]
27C100@TSOP32 [SA410T-B4001]	27C128
27C128@PLCC32 [SA015A1T]	27C210
27C210@PLCC44 [SA244]	27C220
27C220@PLCC44 [SA244]	27C240
27C240@PLCC44 [SA244]	27C256
27C256@PLCC32 [SA015A1T]	27C400
27C400@PLCC44 [SA244]	27C512
27C512@PLCC32 [SA015A1T]	27C64
27C64@PLCC32 [SA015A1T]	27C800
27S512	2816A
2817A	2864A
68C257	68C257@PLCC32 [SA015A1T]
87C256	87C257
87C257@PLCC32 [SA015A1T]	87C64
D27011	D27513
D27C011	D27C513
D2816	D28F256
D28F256A	D28F512
E28F001BX-B@TSOP32 [SA410T-B4001]	E28F002BEB@TSOP40 [SA409T-B4002]
E28F001BX-T@TSOP32 [SA410T-B4001]	E28F002BLB@TSOP40 [SA409T-B4002]
E28F002BCT@TSOP40 [SA409T-B4002]	E28F002BVB@TSOP40 [SA409T-B4002]
E28F002BET@TSOP40 [SA409T-B4002]	E28F002BVB@TSOP40 [SA409T-B4002]
E28F002BLT@TSOP40 [SA409T-B4002]	E28F002BVB@TSOP40 [SA409T-B4002]
E28F002BVT@TSOP40 [SA409T-B4002]	E28F002BVB@TSOP40 [SA409T-B4002]
E28F002BXT@TSOP40 [SA409T-B4002]	E28F004B5B@TSOP40 [SA409T-B4002]
E28F004B5T@TSOP40 [SA409T-B4002]	E28F004BEB@TSOP40 [SA409T-B4002]
E28F004BET@TSOP40 [SA409T-B4002]	E28F004BLB@TSOP40 [SA409T-B4002]
E28F004BLT@TSOP40 [SA409T-B4002]	E28F004BVB@TSOP40 [SA409T-B4002]
E28F004BVT@TSOP40 [SA409T-B4002]	E28F004BVB@TSOP40 [SA409T-B4002]
E28F004BXT@TSOP40 [SA409T-B4002]	E28F004S3@TSOP40 [SA409T-B4002]

E28F004S5@TSOP40 [SA409T-B4002] E28F004SC@TSOP40 [SA409T-B4002]  
E28F008BEB@TSOP40 [SA409T-B4002] E28F008BET@TSOP40 [SA409T-B4002]  
E28F008BLB@TSOP40 [SA409T-B4002] E28F008BLT@TSOP40 [SA409T-B4002]  
E28F008BVB@TSOP40 [SA409T-B4002] E28F008BVT@TSOP40 [SA409T-B4002]  
E28F008BXB@TSOP40 [SA409T-B4002] E28F008BXT@TSOP40 [SA409T-B4002]  
E28F008S3@TSOP40 [SA409T-B4002] E28F008S5@TSOP40 [SA409T-B4002]  
E28F008SA@TSOP40 [SA409T-B4002]  
E28F008SA-L@TSOP40 [SA409T-B4002]  
E28F008SC@TSOP40 [SA409T-B4002] E28F010@TSOP32 [SA410T-B4001]  
E28F016S3@TSOP40 [SA409T-B4002] E28F016S5@TSOP40 [SA409T-B4002]  
E28F016SC@TSOP40 [SA409T-B4002] E28F020@TSOP32 [SA410T-B4001]  
E28F200B5B@TSOP48 [SB247-B4806] E28F200B5T@TSOP48 [SB247-B4806]  
E28F200CVB@TSOP48 [SB247-B4806] E28F200CVT@TSOP48 [SB247-B4806]  
E28F256@TSOP32 [SA410T-B4001] E28F256A@TSOP32 [SA410T-B4001]  
E28F400B5B@TSOP48 [SB247-B4806] E28F400B5T@TSOP48 [SB247-B4806]  
E28F400CVB@TSOP48 [SB247-B4806] E28F400CVT@TSOP48 [SB247-B4806]  
E28F512@TSOP32 [SA410T-B4001] E28F800B5B@TSOP48 [SB247-B4806]  
E28F800B5T@TSOP48 [SB247-B4806] E28F800CEB@TSOP48 [SB247-B4806]  
E28F800CET@TSOP48 [SB247-B4806] E28F800CVB@TSOP48 [SB247-B4806]  
E28F800CVT@TSOP48 [SB247-B4806] E82802AA@TSOP40 [SA409T-B4002]  
E82802AB@TSOP40 [SA409T-B4002] E82802AC@TSOP40 [SA409T-B4002]  
F28F008SA@TSOP40 (REVERSE) [SA409T-B4002]  
F28F010@TSOP32 [SA410T-B4001] F28F020@TSOP32 [SA410T-B4001]  
F28F020@TSOP32 (REVERSE) [SA410T-B4001]  
F28F256@TSOP32 [SA410T-B4001] F28F256A@TSOP32 [SA410T-B4001]  
F28F512@TSOP32 [SA410T-B4001]  
JS28F160B3BD@TSOP48 [SB247-B4806]  
JS28F160B3TD@TSOP48 [SB247-B4806]  
JS28F160C3BD@TSOP48 [SB247-B4806]  
JS28F160C3TD@TSOP48 [SB247-B4806]  
JS28F320B3BD@TSOP48 [SB247-B4806]  
JS28F320B3TD@TSOP48 [SB247-B4806]  
JS28F320C3BD@TSOP48 [SB247-B4806]  
JS28F320C3TD@TSOP48 [SB247-B4806]  
JS28F800C3BD@TSOP48 [SB247-B4806]  
JS28F800C3TD@TSOP48 [SB247-B4806]  
M28F010  
M28F010@TSOP32 [SA410T-B4001] M28F010@PLCC32 [SA015A1T]  
N28F001BN-T@PLCC32 [SA015A1T] N28F001BN-B@PLCC32 [SA015A1T]  
N28F001BX-T@PLCC32 [SA015A1T] N28F001BX-B@PLCC32 [SA015A1T]  
N28F020@PLCC32 [SA015A1T] N28F010@PLCC32 [SA015A1T]  
N28F256A@PLCC32 [SA015A1T] N28F256@PLCC32 [SA015A1T]  
N28F512@PLCC32 [SA015A1T] N28F512@PLCC32 [SA015A1T]  
N29F040 N82802AA@PLCC32 [SA015A1T]  
N82802AB@PLCC32 [SA015A1T] N82802AC@PLCC32 [SA015A1T]  
P27011 P27128A  
P27128A@PLCC32 [SA015A1T] P27128B  
P27128B@PLCC32 [SA015A1T] P27256  
P27256@PLCC32 [SA015A1T] P27512  
P27513 P2764A  
P2764A@PLCC32 [SA015A1T] P27C011  
P27C128 P27C128@PLCC32 [SA015A1T]  
P27C256 P27C256@PLCC32 [SA015A1T]  
P27C513 P27C64

P27C64@PLCC32 [SA015A1T]  
P28F001BX-T  
P28F010  
P28F256  
P28F512  
P87C64@PLCC32 [SA015A1T]  
PA28F004S5@PSOP44 [SA638]  
PA28F008S3@PSOP44 [SA638]  
PA28F008SA@PSOP44 [SA638]  
PA28F008SC@PSOP44 [SA638]  
PA28F016S5@PSOP44 [SA638]  
PA28F200B5B@PSOP44 [SA638]  
PA28F200BVB@PSOP44 [SA638]  
PA28F200BXB@PSOP44 [SA638]  
PA28F400B5B@PSOP44 [SA638]  
PA28F400BLB@PSOP44 [SA638]  
PA28F400BVB@PSOP44 [SA638]  
PA28F400BXB@PSOP44 [SA638]  
PA28F800B5B@PSOP44 [SA638]  
PA28F800BVB@PSOP44 [SA638]  
QB25F016S33B60@SOIC8 [SA605B]  
QB25F160S33B60@SOIC16 [SA404]  
QB25F320S33B60@SOIC16 [SA404]  
QB25F640S33B60@SOIC16 [SA404]  
QH25F016S33B60@SOIC8 [SA605B]  
QH25F160S33B60@SOIC16 [SA404]  
QH25F320S33B60@SOIC16 [SA404]  
QH25F640S33B60@SOIC16 [SA404]  
TB28F004S3@PSOP44 [SA638]  
TB28F004SC@PSOP44 [SA638]  
TB28F008S5@PSOP44 [SA638]  
TB28F008SA-L@PSOP44 [SA638]  
TB28F016S3@PSOP44 [SA638]  
TB28F016SC@PSOP44 [SA638]  
TB28F200B5T@PSOP44 [SA638]  
TB28F200BVT@PSOP44 [SA638]  
TB28F200BXT@PSOP44 [SA638]  
TB28F400B5T@PSOP44 [SA638]  
TB28F400BVT@PSOP44 [SA638]  
TB28F400BXT@PSOP44 [SA638]  
TB28F800B5T@PSOP44 [SA638]  
TB28F800BVT@PSOP44 [SA638]  
TE28F002BEB@TSOP40 [SA409T-B4002]  
TE28F002BET@TSOP40 [SA409T-B4002]  
TE28F002BVB@TSOP40 [SA409T-B4002]  
TE28F002BVT@TSOP40 [SA409T-B4002]  
TE28F002BXB@TSOP40 [SA409T-B4002]  
TE28F002BXT@TSOP40 [SA409T-B4002]  
TE28F004BEB@TSOP40 [SA409T-B4002]  
TE28F004BET@TSOP40 [SA409T-B4002]  
TE28F004BVB@TSOP40 [SA409T-B4002]  
TE28F004BVT@TSOP40 [SA409T-B4002]  
TE28F004BXB@TSOP40 [SA409T-B4002]

P28F001BX-B  
P28F002BCT  
P28F020  
P28F256A  
P87C64  
PA28F004S3@PSOP44 [SA638]  
PA28F004SC@PSOP44 [SA638]  
PA28F008S5@PSOP44 [SA638]  
PA28F008SA-L@PSOP44 [SA638]  
PA28F016S3@PSOP44 [SA638]  
PA28F016SC@PSOP44 [SA638]  
PA28F200B5T@PSOP44 [SA638]  
PA28F200BVT@PSOP44 [SA638]  
PA28F200BXT@PSOP44 [SA638]  
PA28F400B5T@PSOP44 [SA638]  
PA28F400BLT@PSOP44 [SA638]  
PA28F400BVT@PSOP44 [SA638]  
PA28F400BXT@PSOP44 [SA638]  
PA28F800B5T@PSOP44 [SA638]  
PA28F800BVT@PSOP44 [SA638]  
QB25F016S33T60@SOIC8 [SA605B]  
QB25F160S33T60@SOIC16 [SA404]  
QB25F320S33T60@SOIC16 [SA404]  
QB25F640S33T60@SOIC16 [SA404]  
QH25F016S33T60@SOIC8 [SA605B]  
QH25F160S33T60@SOIC16 [SA404]  
QH25F320S33T60@SOIC16 [SA404]  
QH25F640S33T60@SOIC16 [SA404]  
TB28F004S5@PSOP44 [SA638]  
TB28F008S3@PSOP44 [SA638]  
TB28F008SA@PSOP44 [SA638]  
TB28F008SC@PSOP44 [SA638]  
TB28F016S5@PSOP44 [SA638]  
TB28F200B5B@PSOP44 [SA638]  
TB28F200BVB@PSOP44 [SA638]  
TB28F200BXB@PSOP44 [SA638]  
TB28F400B5B@PSOP44 [SA638]  
TB28F400BVB@PSOP44 [SA638]  
TB28F400BXB@PSOP44 [SA638]  
TB28F800B5B@PSOP44 [SA638]  
TB28F800BVB@PSOP44 [SA638]

TE28F004BXT@TSOP40 [SA409T-B4002]  
TE28F004S3@TSOP40 [SA409T-B4002] TE28F004S5@TSOP40 [SA409T-B4002]  
TE28F004SC@TSOP40 [SA409T-B4002]  
TE28F008B3B@TSOP40 [SA409T-B4002]  
TE28F008B3BA@TSOP40 [SA409T-B4002]  
TE28F008B3T@TSOP40 [SA409T-B4002]  
TE28F008B3TA@TSOP40 [SA409T-B4002]  
TE28F008BEB@TSOP40 [SA409T-B4002]  
TE28F008BET@TSOP40 [SA409T-B4002]  
TE28F008BVB@TSOP40 [SA409T-B4002]  
TE28F008BVT@TSOP40 [SA409T-B4002]  
TE28F008C3BA@TSOP40 [SA409T-B4002]  
TE28F008C3TA@TSOP40 [SA409T-B4002]  
TE28F008S3@TSOP40 [SA409T-B4002] TE28F008S5@TSOP40 [SA409T-B4002]  
TE28F008SA@TSOP40 [SA409T-B4002]  
TE28F008SA-L@TSOP40 [SA409T-B4002]  
TE28F008SC@TSOP40 [SA409T-B4002]  
TE28F016B3B@TSOP40 [SA409T-B4002]  
TE28F016B3T@TSOP40 [SA409T-B4002]  
TE28F016C3BA@TSOP40 [SA409T-B4002]  
TE28F016C3TA@TSOP40 [SA409T-B4002]  
TE28F016S3@TSOP40 [SA409T-B4002] TE28F016S5@TSOP40 [SA409T-B4002]  
TE28F016SC@TSOP40 [SA409T-B4002] TE28F160B3B@TSOP48 [SB247-B4806]  
TE28F160B3BA@TSOP48 [SB247-B4806]  
TE28F160B3BC@TSOP48 [SB247-B4806]  
TE28F160B3BD@TSOP48 [SB247-B4806]  
TE28F160B3T@TSOP48 [SB247-B4806]  
TE28F160B3TA@TSOP48 [SB247-B4806]  
TE28F160B3TC@TSOP48 [SB247-B4806]  
TE28F160B3TD@TSOP48 [SB247-B4806]  
TE28F160C3BA@TSOP48 [SB247-B4806]  
TE28F160C3BC@TSOP48 [SB247-B4806]  
TE28F160C3BD@TSOP48 [SB247-B4806]  
TE28F160C3TA@TSOP48 [SB247-B4806]  
TE28F160C3TC@TSOP48 [SB247-B4806]  
TE28F160C3TD@TSOP48 [SB247-B4806]  
TE28F200B5B@TSOP48 [SB247-B4806] TE28F200B5T@TSOP48 [SB247-B4806]  
TE28F200CVB@TSOP48 [SB247-B4806] TE28F200CVT@TSOP48 [SB247-B4806]  
TE28F320B3B@TSOP48 [SB247-B4806]  
TE28F320B3BA@TSOP48 [SB247-B4806]  
TE28F320B3BC@TSOP48 [SB247-B4806]  
TE28F320B3BD@TSOP48 [SB247-B4806]  
TE28F320B3T@TSOP48 [SB247-B4806]  
TE28F320B3TA@TSOP48 [SB247-B4806]  
TE28F320B3TC@TSOP48 [SB247-B4806]  
TE28F320B3TD@TSOP48 [SB247-B4806]  
TE28F320C3BA@TSOP48 [SB247-B4806]  
TE28F320C3BC@TSOP48 [SB247-B4806]  
TE28F320C3BD@TSOP48 [SB247-B4806]  
TE28F320C3TA@TSOP48 [SB247-B4806]  
TE28F320C3TC@TSOP48 [SB247-B4806]  
TE28F320C3TD@TSOP48 [SB247-B4806]  
TE28F400B3B@TSOP48 [SB247-B4806] TE28F400B3T@TSOP48 [SB247-B4806]

TE28F400B5B@TSOP48 [SB247-B4806]	TE28F400B5T@TSOP48 [SB247-B4806]
TE28F400CEB@TSOP48 [SB247-B4806]	TE28F400CET@TSOP48 [SB247-B4806]
TE28F400CVB@TSOP48 [SB247-B4806]	TE28F400CVT@TSOP48 [SB247-B4806]
TE28F640B3BC@TSOP48 [SB247-B4806]	
TE28F640B3TC@TSOP48 [SB247-B4806]	
TE28F640C3BC@TSOP48 [SB247-B4806]	
TE28F640C3TC@TSOP48 [SB247-B4806]	
TE28F800B3B@TSOP48 [SB247-B4806]	
TE28F800B3BA@TSOP48 [SB247-B4806]	
TE28F800B3T@TSOP48 [SB247-B4806]	
TE28F800B3TA@TSOP48 [SB247-B4806]	
TE28F800B5B@TSOP48 [SB247-B4806]	TE28F800B5T@TSOP48 [SB247-B4806]
TE28F800C3BA@TSOP48 [SB247-B4806]	
TE28F800C3BD@TSOP48 [SB247-B4806]	
TE28F800C3TA@TSOP48 [SB247-B4806]	
TE28F800C3TD@TSOP48 [SB247-B4806]	
TE28F800CEB@TSOP48 [SB247-B4806]	TE28F800CET@TSOP48 [SB247-B4806]
TE28F800CVB@TSOP48 [SB247-B4806]	TE28F800CVT@TSOP48 [SB247-B4806]

## PLD

5C090	5C090@PLCC44 [SA244]
85C090	85C090@PLCC44 [SA244]
IPLD910	IPLD910@PLCC44 [SA244]

## MICROCONTROLLER

87C151SA	87C151SA@PLCC44 [SA244]
87C151SB	87C151SB@PLCC44 [SA244]
87C251SA	87C251SA@PLCC44 [SA244]
87C251SB	87C251SB@PLCC44 [SA244]
87C251SP	87C251SP@PLCC44 [SA244]
87C251SQ	87C251SQ@PLCC44 [SA244]
87C51	87C51@PLCC44 [SA244]
87C51@TQFP44 [SA675-B4805]	87C51FA
87C51FA@PLCC44 [SA244]	87C51FA@TQFP44 [SA675-B4805]
87C51FB	87C51FB@PLCC44 [SA244]
87C51FB@TQFP44 [SA675-B4805]	87C51FC
87C51FC@PLCC44 [SA244]	87C51FC@TQFP44 [SA245A-B4805]
87C51RA	87C51RA@PLCC44 [SA244]
87C51RA@TQFP44 [SA675-B4805]	87C51RB
87C51RB@PLCC44 [SA244]	87C51RB@TQFP44 [SA675-B4805]
87C51RC	87C51RC@PLCC44 [SA244]
87C51RC@TQFP44 [SA245A-B4805]	87C52
87C52@PLCC44 [SA244]	87C52@TQFP44 [SA675-B4805]
87C54	87C54@PLCC44 [SA244]
87C54@TQFP44 [SA245A-B4805]	87C58
87C58@PLCC44 [SA244]	87C58@TQFP44 [SA245A-B4805]
87L51FA	87L51FA@PLCC44 [SA244]
87L51FA@TQFP44 [SA675-B4805]	87L51FB
87L51FB@PLCC44 [SA244]	87L51FB@TQFP44 [SA675-B4805]
87L51FC@PLCC44 [SA244]	87L51FC@TQFP44 [SA245A-B4805]

87L52  
87L52@TQFP44 [SA675-B4805]  
87L54@TQFP44 [SA245A-B4805]  
87L58@TQFP44 [SA245A-B4805]

87L52@PLCC44 [SA244]  
87L54@PLCC44 [SA244]  
87L58@PLCC44 [SA244]

## INTELSIL

### E (E) PROM/FRAM/NVRAM

HS-6617RH  
HS-6617RH-T  
HS-6664RH  
HS-6664RH-T  
HS-6883RH  
HS-6883RH-T

HS-6617RH@SOIC24 [SA404]  
HS-6617RH-T@SOIC24 [SA404]  
HS-6664RH@SOIC28 [SA404]  
HS-6664RH-T@SOIC28 [SA404]  
HS-6883RH@SOIC24 [SA404]  
HS-6883RH-T@SOIC24 [SA404]

## INTERSIL

### E (E) PROM/FRAM/NVRAM

X4043  
X4043@SOIC8 [SA602A]  
X4045@MSOP8 [SA026]

X4043@MSOP8 [SA026]  
X4045  
X4045@SOIC8 [SA602A]

## ISSI

### E (E) PROM/FRAM/NVRAM

IS24C01  
IS24C01@SOIC8 [SA602A]  
IS24C01B  
IS24C01B@SOIC8 [SA602A]  
IS24C01C  
IS24C01C@SOIC8 [SA602A]  
IS24C02  
IS24C02@SOIC8 [SA602A]  
IS24C02A  
IS24C02A@MSOP8 [SA666]  
IS24C02A@TSSOP8 [SA643]  
IS24C02B@DFN8  
IS24C02B@SOIC8 [SA602A]  
IS24C02C  
IS24C02C@MSOP8 [SA666]  
IS24C02C@TSSOP8 [SA643]  
IS24C02E@DFN8  
IS24C02E@SOIC8 [SA602A]  
IS24C04  
IS24C04@SOIC8 [SA602A]  
IS24C04A  
IS24C04A@MSOP8 [SA666]  
IS24C04A@TSSOP8 [SA643]

IS24C01@MSOP8 [SA666]  
IS24C01@TSSOP8 [SA643]  
IS24C01B@MSOP8 [SA666]  
IS24C01B@TSSOP8 [SA643]  
IS24C01C@MSOP8 [SA666]  
IS24C01C@TSSOP8 [SA643]  
IS24C02@MSOP8 [SA666]  
IS24C02@TSSOP8 [SA643]  
IS24C02A@DFN8  
IS24C02A@SOIC8 [SA602A]  
IS24C02B  
IS24C02B@MSOP8 [SA666]  
IS24C02B@TSSOP8 [SA643]  
IS24C02C@DFN8  
IS24C02C@SOIC8 [SA602A]  
IS24C02E  
IS24C02E@MSOP8 [SA666]  
IS24C02E@TSSOP8 [SA643]  
IS24C04@MSOP8 [SA666]  
IS24C04@TSSOP8 [SA643]  
IS24C04A@DFN8  
IS24C04A@SOIC8 [SA602A]  
IS24C04B

IS24C04B@DFN8  
IS24C04B@S0IC8 [SA602A]  
IS24C08  
IS24C08@S0IC8 [SA602A]  
IS24C08A  
IS24C08A@MSOP8 [SA666]  
IS24C08A@TSSOP8 [SA643]  
IS24C08B@DFN8  
IS24C08B@S0IC8 [SA602A]  
IS24C128  
IS24C128@TSSOP14 [SA026]  
IS24C128B@S0IC8 [SA602A]  
IS24C16  
IS24C16@S0IC8 [SA602A]  
IS24C16A  
IS24C16A@S0IC8 [SA602A]  
IS24C16B  
IS24C16B@S0IC8 [SA602A]  
IS24C256  
IS24C256@TSSOP14 [SA026]  
IS24C256A@S0IC8 [SA602A]  
IS24C256C  
IS24C256C@TSSOP14 [SA026]  
IS24C32@S0IC8 [SA602A]  
IS24C32A  
IS24C32A@S0IC8 [SA602A]  
IS24C32B  
IS24C32B@TSSOP8 [SA643]  
IS24C32C@DFN8 [SA724]  
IS24C32C@S0IC8 [SA602A]  
IS24C64  
IS24C64@TSSOP8 [SA643]  
IS24C64A@MSOP8 [SA666]  
IS24C64A@TSSOP8 [SA643]  
IS24C64B@S0IC8 [SA602A]  
IS24C64C  
IS24C64C@S0IC8 [SA602A]  
IS24L128  
IS24L128@S0IC8 (200mil) [SA605B]  
IS24L256@S0IC8 (150mil) [SA602A]  
IS25C01  
IS25C01@TSSOP8 [SA643]  
IS25C02@S0IC8 [SA602A]  
IS25C04  
IS25C04@TSSOP8  
IS25C08@S0IC8 [SA602A]  
IS25C128@S0IC8 [SA602A]  
IS25C128A-S8 [SA602A]  
IS25C16  
IS25C16@TSSOP8 [SA643]  
IS25C256@TSSOP8 [SA643]  
IS25C256A@TSSOP8 [SA643]  
IS25C32A@S0IC8 [SA602A]  
IS24C04B@MSOP8 [SA666]  
IS24C04B@TSSOP8 [SA643]  
IS24C08@MSOP8 [SA666]  
IS24C08@TSSOP8 [SA643]  
IS24C08A@DFN8  
IS24C08A@S0IC8 [SA602A]  
IS24C08B  
IS24C08B@MSOP8 [SA666]  
IS24C08B@TSSOP8 [SA643]  
IS24C128@S0IC8 [SA602A]  
IS24C128B  
IS24C128B@TSSOP14 [SA026]  
IS24C16@MSOP8 [SA666]  
IS24C16@TSSOP8 [SA643]  
IS24C16A@MSOP8 [SA666]  
IS24C16A@TSSOP8 [SA643]  
IS24C16B@MSOP8 [SA666]  
IS24C16B@TSSOP8 [SA643]  
IS24C256@S0IC8 [SA602A]  
IS24C256A  
IS24C256A@TSSOP14 [SA026]  
IS24C256C@S0IC8 [SA602A]  
IS24C32  
IS24C32@TSSOP8 [SA643]  
IS24C32A@MSOP8 [SA666]  
IS24C32A@TSSOP8 [SA643]  
IS24C32B@S0IC8 [SA602A]  
IS24C32C  
IS24C32C@MSOP8 [SA666]  
IS24C32C@TSSOP8 [SA643]  
IS24C64@S0IC8 [SA602A]  
IS24C64A  
IS24C64A@S0IC8 [SA602A]  
IS24C64B  
IS24C64B@TSSOP8 [SA643]  
IS24C64C@MSOP8 [SA666]  
IS24C64C@TSSOP8 [SA643]  
IS24L128@S0IC8 (150mil) [SA602A]  
IS24L256  
IS24L256@S0IC8 (200mil) [SA605B]  
IS25C01@S0IC8 [SA602A]  
IS25C02  
IS25C02@TSSOP8 [SA643]  
IS25C04@S0IC8 [SA602A]  
IS25C08  
IS25C08@TSSOP8 [SA643]  
IS25C128@TSSOP8 [SA643]  
IS25C128A-T8 [SA643]  
IS25C16@S0IC8 [SA602A]  
IS25C256@S0IC8 [SA602A]  
IS25C256A@S0IC8 [SA602A]  
IS25C32A  
IS25C32A@TSSOP8 [SA643]

IS25C32B  
IS25C32B@TSSOP8 [SA643]  
IS25C64A@SOIC8 [SA602A]  
IS25C64B  
IS25C64B@TSSOP8 [SA643]  
IS25CD010@SOIC8[150 mil] [SA602A]  
IS25CD010@SOIC8[200 mil] [SA643]  
IS25CD025@SOIC8 [SA602A]  
IS25CD512  
IS25CD512@SOIC8[200mil] [SA605B]  
IS25CD512@USON8 [SA724]  
IS25CQ032C@SOIC8 [SA605B]  
IS25LD010@SOIC8 [SA602A]  
IS25LD010@WSON8 [SA683]  
IS25LD020@TSSOP8 [SA643]  
IS25LD040@SOIC8 [SA602A]  
IS25LD040-B8 [SA605B]  
IS25LD256C@TSSOP8 [SA643]  
IS25LD512@SOIC8 [SA602A]  
IS25LD512@WSON8 [SA683]  
IS25LP032@SOIC8 [SA605B]  
IS25LP032@USON8 [SA683]  
IS25LP032@WSON8 [SA684]  
IS25LP064@SOIC8 [SA605B]  
IS25LP064@USON8 [SA683]  
IS25LP064@WSON8 [SA684]  
IS25LQ010A@SOIC8[150 mil] [SA602A]  
IS25LQ010A@SOIC8[200 mil] [SA643]  
IS25LQ010A@WSON8 [SA683]  
IS25LQ020A@SOIC8[150 mil] [SA602A]  
IS25LQ020A@SOIC8[200 mil] [SA643]  
IS25LQ020A@WSON8 [SA683]  
IS25LQ025B@SOIC8[150 mil] [SA602A]  
IS25LQ025B@SOIC8[200 mil] [SA605B]  
IS25LQ025B@TSSOP8 [SA643]  
IS25LQ025B@VSOP8 [SA602A]  
IS25LQ032B@SOIC8 [SA605B]  
IS25LQ032C@SOIC8 [SA605B]  
IS25LQ080@SOIC8[150 mil] [SA602A]  
IS25LQ080@SOIC8[200 mil] [SA605B]  
IS25LQ080@VVSOP8 [SA602A]  
IS25LQ080B@SOIC8[150 mil] [SA602A]  
IS25LQ080B@SOIC8[200 mil] [SA605B]  
IS25LQ080B@VVSOP8 [SA602A]  
IS25LQ512B@SOIC8[150 mil] [SA602A]  
IS25LQ512B@SOIC8[200 mil] [SA605B]  
IS25LQ512B@TSSOP8 [SA643]  
IS25LQ512B@VSOP8 [SA602A]  
IS25WD020@SOIC8(150mil) [SA602A]  
IS25WD020@VVSOP8 [SA602A]  
IS25WD040@SOIC8(150mil) [SA602A]  
IS25WD040@VVSOP8 [SA602A]  
IS27C010

IS25C32B@SOIC8 [SA602A]  
IS25C64A  
IS25C64A@TSSOP8 [SA643]  
IS25C64B@SOIC8 [SA602A]  
  
IS25CD010@WSON8 [SA683]  
IS25CD025@TSSOP8 [SA643]  
IS25CD512@SOIC8[150mil] [SA602A]  
IS25CD512@TSSOP8 [SA026]  
IS25CD512@WSON8 [SA683]  
IS25CQ032C@WSON8 [SA684]  
IS25LD010@TSSOP8 [SA643]  
IS25LD020@SOIC8 [SA602A]  
IS25LD020@WSON8 [SA683]  
IS25LD040@WSON8 [SA683]  
IS25LD256C@SOIC8 [SA602A]  
IS25LD256C@WSON8 [SA683]  
IS25LD512@TSSOP8 [SA643]  
IS25LP032@SOIC16 [SA783]  
IS25LP032@TFBGA24 [TA088]  
IS25LP032@VSOP8 [SA605B]  
IS25LP064@SOIC16 [SA783]  
IS25LP064@TFBGA24 [TA088]  
IS25LP064@VSOP8 [SA605B]  
  
IS25LQ025B@USON8 [SA724]  
IS25LQ025B@WSON8 [SA683]  
IS25LQ032B@WSON8 [SA684]  
IS25LQ032C@WSON8 [SA684]  
  
IS25LQ080@WSON8 [SA683]  
  
IS25LQ080B@WSON8 [SA683]  
  
IS25LQ512B@USON8 [SA724]  
IS25LQ512B@WSON8 [SA683]  
IS25WD020@SOIC8(200mil) [SA605B]  
IS25WD020@WSON8 [SA683]  
IS25WD040@SOIC8(200mil) [SA605B]  
IS25WD040@WSON8 [SA683]  
IS27C010@PLCC32 [SA015A1T]

IS27C010@TSOP32 [SA410T-B4001]	IS27C020
IS27C020@PLCC32 [SA015A1T]	IS27C020@TSOP32 [SA410T-B4001]
IS27C256	IS27C256@PLCC32 [SA015A1T]
IS27C512	IS27C512@PLCC32 [SA015A1T]
IS27C512@TSOP28 [SA430T-B4003]	IS27HC010
IS27HC010@PLCC32 [SA015A1T]	IS27HC010@TSOP32 [SA410T-B4001]
IS27HC020	IS27HC020@PLCC32 [SA015A1T]
IS27HC020@TSOP32 [SA410T-B4001]	IS27HC256
IS27HC256@PLCC32 [SA015A1T]	IS27HC512
IS27HC512@PLCC32 [SA015A1T]	IS27HC512@TSOP28 [SA430T-B4003]
IS27LV010	IS27LV010@PLCC32 [SA015A1T]
IS27LV010@TSOP32 [SA410T-B4001]	IS27LV512
IS27LV512@PLCC32 [SA015A1T]	IS27LV512@TSOP28 [SA430T-B4003]
IS28F010	IS28F010@PLCC32 [SA015A1T]
IS28F010@TSOP32 [SA410T-B4001]	IS28F010A
IS28F010A@PLCC32 [SA015A1T]	IS28F010A@TSOP32 [SA410T-B4001]
IS28F020	IS28F020@PLCC32 [SA015A1T]
IS28F020@TSOP32 [SA410T-B4001]	IS29F010
IS29F010@PLCC32 [SA015A1T]	IS29F010@TSOP32 [SA410T-B4001]
IS34C02	IS34C02@MSOP8 [SA666]
IS34C02@SOIC8 [SA602A]	IS34C02@TSSOP8 [SA643]
IS34C02B@DFN8	IS34C02B@TSSOP8 [SA643]
IS93C46	IS93C46@SOIC8 [SA602A]
IS93C46A(08bit)	IS93C46A(08bit)@SOIC8 [SA602A]
IS93C46A(08bit)@TSSOP8 [SA643]	IS93C46A(16bit)
IS93C46A(16bit)@SOIC8 [SA602A]	IS93C46A(16bit)@TSSOP8 [SA643]
IS93C46B	IS93C46B@SOIC8 [SA602A]
IS93C46B@TSSOP8 [SA643]	IS93C46D(08bit)
IS93C46D(08bit)@SOIC8 [SA602A]	IS93C46D(08bit)@TSSOP8 [SA643]
IS93C46D(16bit)	IS93C46D(16bit)@SOIC8 [SA602A]
IS93C46D(16bit)@TSSOP8 [SA643]	IS93C56
IS93C56@SOIC8 [SA602A]	IS93C56A(08bit)
IS93C56A(08bit)@SOIC8 [SA602A]	IS93C56A(08bit)@TSSOP8 [SA643]
IS93C56A(16bit)	IS93C56A(16bit)@SOIC8 [SA602A]
IS93C56A(16bit)@TSSOP8 [SA643]	IS93C66
IS93C66@SOIC8 [SA602A]	IS93C66A(08bit)
IS93C66A(08bit)@SOIC8 [SA602A]	IS93C66A(08bit)@TSSOP8 [SA643]
IS93C66A(16bit)	IS93C66A(16bit)@SOIC8 [SA602A]
IS93C66A(16bit)@TSSOP8 [SA643]	IS93C76A(08bit)
IS93C76A(08bit)@SOIC8 [SA602A]	IS93C76A(08bit)@TSSOP8 [SA643]
IS93C76A(16bit)	IS93C76A(16bit)@SOIC8 [SA602A]
IS93C76A(16bit)@TSSOP8 [SA643]	IS93C86A(08bit)
IS93C86A(08bit)@SOIC8 [SA602A]	IS93C86A(08bit)@TSSOP8 [SA643]
IS93C86A(16bit)	IS93C86A(16bit)@SOIC8 [SA602A]
IS93C86A(16bit)@TSSOP8 [SA643]	

## DRAM & SRAM

IS61C1024	IS61C1024(300m)@SOJ32 [SA646]
IS61C1024(400m)@SOJ32 [SA661]	IS61C1024@TSOP32 [SA410T-B4001]
IS61C1024L	IS61C1024L(300m)@SOJ32 [SA646]
IS61C1024L(400m)@SOJ32 [SA661]	IS61C1024L@TSOP32 [SA410T-B4001]

IS61C256AH	IS61C256AH@SOJ28
IS61C256AH@TSOP28 [SA643]	IS61C512
IS61C512 (300m)@SOJ32 [SA646]	IS61C512 (400m)@SOJ32 [SA661]
IS61C512@TSOP32 [SA410T-B4001]	IS61C64AH
IS61C64AH@SOJ28	IS61C64AH@TSOP28 [SA643]
IS61LV256	IS61LV256@SOJ28
IS61LV256@TSOP28 [SA643]	IS61M256
IS61M256@SOJ28	IS61M256@TSOP28 [SA643]
IS62C1024	IS62C1024 (300m)@SOJ32 [SA646]
IS62C1024 (400m)@SOJ32 [SA661]	IS62C1024@TSOP32 [SA410T-B4001]
IS62C256	IS62C256@SOJ28
IS62C256@TSOP28 [SA643]	IS62C512
IS62C512 (300m)@SOJ32 [SA646]	IS62C512 (400m)@SOJ32 [SA661]
IS62C512@TSOP32 [SA410T-B4001]	IS62C64
IS62C64@SOJ28	IS62C64@TSOP28 [SA643]
IS62LV256	IS62LV256@SOJ28
IS62LV256@TSOP28 [SA643]	

## MICROCONTROLLER

IS89C51A	IS89C51A@PLCC44 [SA244]
IS89C51A@TQFP44 [SA675-B4805]	IS89C52A
IS89C52A@PLCC44 [SA244]	IS89C52A@TQFP44 [SA675-B4805]

## JSC

### E (E) PROM/FRAM/NVRAM

JS25BU01QA@SOIC8[150 mil] [SA602A]	
JS25BU01QA@SOIC8[200 mil] [SA605B]	
JS25BU01QA@VSOP8 [SA602A]	JS25BU01QA@WSON8 [SA683]
JS25BU02QA@SOIC8[150 mil] [SA602A]	
JS25BU02QA@SOIC8[200 mil] [SA605B]	
JS25BU02QA@VSOP8 [SA602A]	JS25BU02QA@WSON8 [SA683]
JS25BU04QA@SOIC8[150 mil] [SA602A]	
JS25BU04QA@SOIC8[200 mil] [SA605B]	
JS25BU04QA@VSOP8 [SA602A]	JS25BU04QA@WSON8 [SA683]
JS25BU08QA@SOIC8[150 mil] [SA602A]	
JS25BU08QA@SOIC8[200 mil] [SA605B]	
JS25BU08QA@VSOP8 [SA602A]	JS25BU08QA@WSON8 [SA683]
JS25BU16QA@SOIC8[150 mil] [SA602A]	
JS25BU16QA@SOIC8[200 mil] [SA605B]	
JS25BU16QA@VSOP8 [SA602A]	JS25BU16QA@WSON8 [SA683]
JS25BU32QA@SOIC8[150 mil] [SA602A]	
JS25BU32QA@SOIC8[200 mil] [SA605B]	
JS25BU32QA@VSOP8 [SA602A]	JS25BU32QA@WSON8 [SA683]
JS25BU5KQA@SOIC8[150 mil] [SA602A]	
JS25BU5KQA@SOIC8[200 mil] [SA605B]	
JS25BU5KQA@VSOP8 [SA602A]	JS25BU5KQA@WSON8 [SA683]
JS25P01QA@DFN8 [SA724]	JS25P01QA@SOP8[150 mil] [SA602A]
JS25P01QA@SOP8[200 mil] [SA605B]	JS25P01QA@VDFN8 [SA683]
JS25P01QA@VSOP8 [SA602A]	JS25P01QA@VVSOP8 [SA602A]

JS25P01QA@WSON8 [SA683]  
JS25P02QA@SOP8[150 mil] [SA602A]  
JS25P02QA@VDFN8 [SA683]  
JS25P02QA@VVSOP8 [SA602A]  
JS25P04QA@DFN8 [SA724]  
JS25P04QA@SOP8[200 mil] [SA605B]  
JS25P04QA@VSOP8 [SA602A]  
JS25P04QA@WSON8 [SA683]  
JS25P08QA@SOP8[150 mil] [SA602A]  
JS25P08QA@VDFN8 [SA683]  
JS25P08QA@VVSOP8 [SA602A]  
JS25P16QA@DFN8 [SA724]  
JS25P16QA@SOP8[200 mil] [SA605B]  
JS25P16QA@VSOP8 [SA602A]  
JS25P16QA@WSON8 [SA683]

JS25P02QA@DFN8 [SA724]  
JS25P02QA@SOP8[200 mil] [SA605B]  
JS25P02QA@VSOP8 [SA602A]  
JS25P02QA@WSON8 [SA683]  
JS25P04QA@SOP8[150 mil] [SA602A]  
JS25P04QA@VDFN8 [SA683]  
JS25P04QA@VVSOP8 [SA602A]  
JS25P08QA@DFN8 [SA724]  
JS25P08QA@SOP8[200 mil] [SA605B]  
JS25P08QA@VSOP8 [SA602A]  
JS25P08QA@WSON8 [SA683]  
JS25P16QA@SOP8[150 mil] [SA602A]  
JS25P16QA@VDFN8 [SA683]  
JS25P16QA@VVSOP8 [SA602A]

## K-LINE

### E (E) PROM/FRAM/NVRAM

K24C32  
K24C32@TSSOP8 [SA643]  
K24C64@SOIC8 [SA602A]

K24C32@SOIC8 [SA602A]  
K24C64  
K24C64@TSSOP8 [SA643]

## KODENSHI

### E (E) PROM/FRAM/NVRAM

KK24LC02B  
KK24LC04B  
KK24LC08B  
KK24LC16B

KK24LC02B@SOIC8 [SA602A]  
KK24LC04B@SOIC8 [SA602A]  
KK24LC08B@SOIC8 [SA602A]  
KK24LC16B@SOIC8 [SA602A]

## LATTICE

### PLD

GAL16LV8  
GAL16LV8C  
GAL16LV8D  
GAL16LV8Z  
GAL16LV8ZD  
GAL16V8  
GAL16V8@SOIC20 [SA404]  
GAL16V8A@PLCC20 [SA001A-B2001]  
GAL16V8B  
GAL16V8B@SOIC20 [SA404]  
GAL16V8C@PLCC20 [SA001A-B2001]  
GAL16V8D  
GAL16V8D@SOIC20 [SA404]  
GAL16V8Z@PLCC20 [SA001A-B2001]

GAL16LV8@PLCC20 [SA001A-B2001]  
GAL16LV8C@PLCC20 [SA001A-B2001]  
GAL16LV8D@PLCC20 [SA001A-B2001]  
GAL16LV8Z@PLCC20 [SA001A-B2001]  
GAL16LV8ZD@PLCC20 [SA001A-B2001]  
GAL16V8@PLCC20 [SA001A-B2001]  
GAL16V8A  
GAL16V8A@SOIC20 [SA404]  
GAL16V8B@PLCC20 [SA001A-B2001]  
GAL16V8C  
GAL16V8C@SOIC20 [SA404]  
GAL16V8D@PLCC20 [SA001A-B2001]  
GAL16V8Z  
GAL16V8Z@SOIC20 [SA404]

GAL18V10  
GAL18V10B  
GAL20LV8  
GAL20LV8Z  
GAL20LV8ZD  
GAL20RA10  
GAL20RA10B  
GAL20V8  
GAL20V8A  
GAL20V8B  
GAL20V8C  
GAL20V8Z  
GAL20XV10  
GAL20XV10B  
GAL22V10  
GAL22V10@SOIC24 [SA404]  
GAL22V10A@PLCC28 [SA008A]  
GAL22V10B  
GAL22V10B@SOIC24 [SA404]  
GAL22V10BQ@PLCC28 [SA008A]  
GAL22V10C  
GAL22V10C@SOIC24 [SA404]  
GAL22V10D@PLCC28 [SA008A]  
GAL26CLV12  
GAL26CLV12@SOIC28 [SA404]  
GAL26CLV12B  
GAL26CLV12B@SOIC28 [SA404]  
GAL26CLV12C  
GAL26CLV12C@SOIC28 [SA404]  
GAL26CLV12D  
GAL26CLV12D@SOIC28 [SA404]  
GAL26CLV12Z  
GAL26CLV12Z@SOIC28 [SA404]  
GAL26CLV12ZD  
GAL26CLV12ZD@SOIC28 [SA404]  
GAL26CV12  
GAL26CV12B  
GAL26CV12C  
GAL26V12C  
GAL6001B  
ispGAL22LV10  
ispGAL22LV10@SSOP28 [SA626A]  
ispGAL22LV10A@PLCC28 [SA008A]  
ispGAL22LV10B  
ispGAL22LV10B@SSOP28 [SA626A]  
ispGAL22LV10C@PLCC28 [SA008A]  
ispGAL22LV10D  
ispGAL22LV10D@SSOP28 [SA626A]  
ispGAL22V10AB@QFN32 [SA686]  
ispGAL22V10AC@QFN32 [SA686]  
ispGAL22V10AV@QFN32 [SA686]  
ispGAL22V10AZC@QFN32 [SA686]  
ispLSI1016@TQFP44 [SA245A-B4805]  
GAL18V10@PLCC20 [SA001A-B2001]  
GAL18V10B@PLCC20 [SA001A-B2001]  
GAL20LV8@PLCC28 [SA008A]  
GAL20LV8Z@PLCC28 [SA008A]  
GAL20LV8ZD@PLCC28 [SA008A]  
GAL20RA10@PLCC28 [SA008A]  
GAL20RA10B@PLCC28 [SA008A]  
GAL20V8@PLCC28 [SA008A]  
GAL20V8A@PLCC28 [SA008A]  
GAL20V8B@PLCC28 [SA008A]  
GAL20V8C@PLCC28 [SA008A]  
GAL20V8Z@PLCC28 [SA008A]  
GAL20XV10@PLCC28 [SA008A]  
GAL20XV10B@PLCC28 [SA008A]  
GAL22V10@PLCC28 [SA008A]  
GAL22V10A  
GAL22V10A@SOIC24 [SA404]  
GAL22V10B@PLCC28 [SA008A]  
GAL22V10BQ  
GAL22V10BQ@SOIC24 [SA404]  
GAL22V10C@PLCC28 [SA008A]  
GAL22V10D  
GAL22V10D@SOIC24 [SA404]  
GAL26CLV12@PLCC28 [SA008A]  
GAL26CLV12@TSOP28 [SA643]  
GAL26CLV12B@PLCC28 [SA008A]  
GAL26CLV12B@TSOP28 [SA643]  
GAL26CLV12C@PLCC28 [SA008A]  
GAL26CLV12C@TSOP28 [SA643]  
GAL26CLV12D@PLCC28 [SA008A]  
GAL26CLV12D@TSOP28 [SA643]  
GAL26CLV12Z@PLCC28 [SA008A]  
GAL26CLV12Z@TSOP28 [SA643]  
GAL26CLV12ZD@PLCC28 [SA008A]  
GAL26CLV12ZD@TSOP28 [SA643]  
GAL26CV12@PLCC28 [SA008A]  
GAL26CV12B@PLCC28 [SA008A]  
GAL26CV12C@PLCC28 [SA008A]  
GAL26V12C@PLCC28 [SA008A]  
GAL6001B@PLCC28 [SA008A]  
ispGAL22LV10@PLCC28 [SA008A]  
ispGAL22LV10A  
ispGAL22LV10A@SSOP28 [SA626A]  
ispGAL22LV10B@PLCC28 [SA008A]  
ispGAL22LV10C  
ispGAL22LV10C@SSOP28 [SA626A]  
ispGAL22LV10D@PLCC28 [SA008A]  
ispGAL22V10AB@PLCC28 [SA008A]  
ispGAL22V10AC@PLCC28 [SA008A]  
ispGAL22V10AV@PLCC28 [SA008A]  
ispGAL22V10AZC@PLCC28 [SA008A]  
ispLSI1016@PLCC44 [SA244]  
ispLSI1016E@PLCC44 [SA244]

ispLSI1016E@TQFP44 [SA245A-B4805]

ispLSI1016EA@PLCC44 [\$\$\$\$\$\$]

ispLSI1016EA@TQFP44 [\$\$\$\$\$\$]

## LG

### MICROCONTROLLER

uPD78F9234MC [SA689]

uPD78F9234SD [SA653]

## LG Semicon

### DRAM & SRAM

GM76C256CL

GM76C256CL@SSOP28 [SA430TA-B4003]

GM76C256CL@TSOP28 [SA643]

GM76C256CLL

GM76C256CLL@SSOP28 [SA430TA-B4003]

GM76C256CLL@TSOP28 [SA643]

GM76C8128CL

GM76C8128CL@SSOP32 [SA438T]

GM76C8128CL@TSOP32 [SA410T-B4001]

GM76C8128CL@VSOP32 [SA620-B4807]

GM76C8128CLL

GM76C8128CLL@SSOP32 [SA438T]

GM76C8128CLL@TSOP32 [SA410T-B4001]

GM76C8128CLL@VSOP32 [SA620-B4807]

GM76C88AL

GM76C88AL@SSOP28

GM76C88AL@TSOP28 [SA643]

GM76U256CL

GM76U256CL@SSOP28

GM76U256CL@TSOP28 [SA643]

GM76U256CLL

GM76U256CLL@SSOP28

GM76U256CLL@TSOP28 [SA643]

GM76U8128CL

GM76U8128CL@SSOP32 [SA438T]

GM76U8128CL@TSOP32 [SA410T-B4001]

GM76U8128CLL

GM76U8128CL@VSOP32 [SA620-B4807]

GM76U8128CLL@SSOP32 [SA438T]

GM76U8128CLL@TSOP32 [SA410T-B4001]

GM76U8128CLL@VSOP32 [SA620-B4807]

GM76U8128DL

GM76U8128DL@SSOP32 [SA438T]

GM76U8128DL@TSOP32 [SA410T-B4001]

GM76U8128DLL

GM76U8128DL@VSOP32 [SA620-B4807]

GM76U8128DLL@SSOP32 [SA438T]

GM76U8128DLL@TSOP32 [SA410T-B4001]

GM76U8128DLL@VSOP32 [SA620-B4807]

GM76U8512L

GM76U8512L@SSOP32

GM76U8512L@TSOP32 [SA410T-B4001]

GM76U8512L@VSOP32 [SA620-B4807]

GM76U8512LL

GM76U8512LL@SSOP32 [SA438T]

GM76U8512LL@TSOP32 [SA410T-B4001]

GM76U8512LL@VSOP32 [SA620-B4807]

GM76V256CL

GM76V256CL@SSOP28

GM76V256CL@TSOP28 [SA643]

GM76V256CLL

GM76V256CLL@SSOP28

GM76V256CLL@TSOP28 [SA643]

GM76V8128CL

GM76V8128CL@SSOP32 [SA438T]

GM76V8128CL@TSOP32 [SA410T-B4001]

GM76V8128CL@VSOP32 [SA620-B4807]

GM76V8128CLL

GM76V8128CLL@SSOP32 [SA438T]	
GM76V8128CLL@TSOP32 [SA410T-B4001]	
GM76V8128CLL@VSOP32 [SA620-B4807]	
GM76V8128DL	GM76V8128DL@SSOP32 [SA438T]
GM76V8128DL@TSOP32 [SA410T-B4001]	
GM76V8128DL@VSOP32 [SA620-B4807]	GM76V8128DLL
GM76V8128DLL@SSOP32 [SA438T]	
GM76V8128DLL@TSOP32 [SA410T-B4001]	
GM76V8128DLL@VSOP32 [SA620-B4807]	
GM76V8512L	GM76V8512L@SSOP32 [SA438T]
GM76V8512L@TSOP32 [SA410T-B4001]	GM76V8512L@VSOP32 [SA620-B4807]
GM76V8512LL	GM76V8512LL@SSOP32 [SA438T]
GM76V8512LL@TSOP32 [SA410T-B4001]	
GM76V8512LL@VSOP32 [SA620-B4807]	GM77C8128A
GM77C8128A@SSOP32 [SA438T]	GM77C8128A@TSOP32 [SA410T-B4001]
GM77C8128A@VSOP32 [SA620-B4807]	

## MICROCONTROLLER

GMS34004TK	GMS34004TM
GMS34004TW	GMS34112TK
GMS34112TK@SOIC20 [SA404]	GMS34112TK@SSOP20 [SA626A]
GMS34140TK	GMS34140TK@SOIC24 [SA404]
GMS80C701	GMS80C701@PLCC44 [SA244]
GMS80C701@TQFP44 [SA675-B4805]	GMS81004(dip20)
GMS81004(dip24)	GMS81004(dip28)
GMS81004@PLCC44 [SA244]	GMS81004@SOIC20 [SA404]
GMS81004@SOIC24 [SA404]	GMS81004@SOIC28 [SA404]
GMS81008(dip20)	GMS81008(dip24)
GMS81008(dip28)	GMS81008@PLCC44 [SA244]
GMS81008@SOIC20 [SA404]	GMS81008@SOIC24 [SA404]
GMS81008@SOIC28 [SA404]	GMS81016(dip20)
GMS81016(dip24)	GMS81016(dip28)
GMS81016@PLCC44 [SA244]	GMS81016@SOIC20 [SA404]
GMS81016@SOIC24 [SA404]	GMS81016@SOIC28 [SA404]
GMS81024(dip20)	GMS81024(dip24)
GMS81024(dip28)	GMS81024@PLCC44 [SA244]
GMS81024@SOIC20 [SA404]	GMS81024@SOIC24 [SA404]
GMS81024@SOIC28 [SA404]	GMS81032(dip20)
GMS81032(dip24)	GMS81032(dip28)
GMS81032@PLCC44 [SA244]	GMS81032@SOIC20 [SA404]
GMS81032@SOIC24 [SA404]	GMS81032@SOIC28 [SA404]
GMS81504AT [SA653]	GMS81504T [SA653]
GMS81516	GMS81516AT
GMS81516BT	GMS81524
GMS81524AT	GMS81524BT
GMS81604T	GMS81604T@PLCC44 [SA244]
GMS81604T@SDIP42 [SA028]	GMS81608T
GMS81608T@PLCC44 [SA244]	GMS81608T@SDIP42 [SA028]
GMS81C5016(dip28)	GMS81C5016(dip40)
GMS81C5016@PLCC44 [SA244]	GMS81C5016@SOIC28 [SA404]
GMS81C5016@TQFP44 [SA675-B4805]	GMS81C5024(dip28)

GMS81C5024(dip40)	GMS81C5024@PLCC44 [SA244]
GMS81C5024@S0IC28 [SA404]	GMS81C5024@TQFP44 [SA675-B4805]
GMS81C5032(dip28)	GMS81C5032(dip40)
GMS81C5032@PLCC44 [SA244]	GMS81C5032@S0IC28 [SA404]
GMS81C5032@TQFP44 [SA675-B4805]	GMS82516T
GMS82516T@MQFP44 [SA675-B4805]	GMS82516T@SDIP42 [SA028]
GMS82524T	GMS82524T@MQFP44 [SA675-B4805]
GMS82524T@SDIP42 [SA028]	GMS87C1102
GMS87C1102@SOP16 [SA404]	GMS87C1202
GMS87C1202@SOP20 [SA404]	GMS87C1404
GMS87C1404@SOP28 [SA404]	GMS87C1408
GMS87C1408@SOP28 [SA404]	GMS87C5032(dip28)
GMS87C5032(dip40)	GMS87C5032@PLCC44 [SA244]
GMS87C5032@S0IC28 [SA404]	GMS87C5032@TQFP44 [SA675-B4805]
GMS97C1051	GMS97C1051@S0IC20 [SA404]
GMS97C2051	GMS97C2051@S0IC20 [SA404]
GMS97C51	GMS97C51@PLCC44 [SA244]
GMS97C51@TQFP44 [SA675-B4805]	GMS97C52
GMS97C52@PLCC44 [SA244]	GMS97C52@TQFP44 [SA675-B4805]
GMS97C54	GMS97C54@PLCC44 [SA244]
GMS97C54@TQFP44 [SA675-B4805]	GMS97C56
GMS97C56@PLCC44 [SA244]	GMS97C56@TQFP44 [SA675-B4805]
GMS97C58	GMS97C58@PLCC44 [SA244]
GMS97C58@TQFP44 [SA675-B4805]	GMS97L1051
GMS97L1051@S0IC20 [SA404]	GMS97L2051
GMS97L2051@S0IC20 [SA404]	GMS97L51
GMS97L51@PLCC44 [SA244]	GMS97L51@TQFP44 [SA675-B4805]
GMS97L52	GMS97L52@PLCC44 [SA244]
GMS97L52@TQFP44 [SA675-B4805]	GMS97L54
GMS97L54@PLCC44 [SA244]	GMS97L54@TQFP44 [SA675-B4805]
GMS97L56	GMS97L56@PLCC44 [SA244]
GMS97L56@TQFP44 [SA675-B4805]	GMS97L58
GMS97L58@PLCC44 [SA244]	GMS97L58@TQFP44 [SA675-B4805]
GMS99C51	GMS99C51@PLCC44 [SA244]
GMS99C51@TQFP44 [SA675-B4805]	GMS99C52
GMS99C52@PLCC44 [SA244]	GMS99C52@TQFP44 [SA675-B4805]
GMS99C58	GMS99C58@PLCC44 [SA244]
GMS99C58@TQFP44 [SA675-B4805]	

## LINKSMART

### E (E) PROM/FRAM/NVRAM

L24C02	L24C02@SSOP8 [SA602A]
L24C02@TSOP8 [SA643]	L24C04
L24C04@SSOP8 [SA602A]	L24C04@TSOP8 [SA643]
L29004C	L29004C@PLCC32 [SA015A1T]
L29004C@TSOP32 [SA410T-B4001]	L29S160F@TSOP48 [SB247-B4806]
L29S160F-B@TSOP48 [SB247-B4806]	L29S400F@PSOP44 [SA638]
L29S400F@TSOP48 [SB247-B4806]	L29S400F-B@PSOP44 [SA638]
L29S400F-B@TSOP48 [SB247-B4806]	L29S800F@TSOP48 [SB247-B4806]
L29S800F-B@TSOP48 [SB247-B4806]	L29W800E@TSOP48 [SB247-B4806]

L29W800E-B@TSOP48 [SB247-B4806]  
LST28001@PLCC32 [SA015A1T]  
LST28002  
LST28002@TSOP32 [SA410T-B4001]  
LST28004@PLCC32 [SA015A1T]

LST28001  
LST28001@TSOP32 [SA410T-B4001]  
LST28002@PLCC32 [SA015A1T]  
LST28004  
LST28004@TSOP32 [SA410T-B4001]

## LITAO

### E (E) PROM/FRAM/NVRAM

L24C01  
L24C04  
L24C16

L24C02  
L24C08

## LIZE

### E (E) PROM/FRAM/NVRAM

L24C02  
L24C02@TSSOP8 [SA643]  
L24C04@SOP8 [SA602A]  
L24C08  
L24C08@TSSOP8 [SA643]  
L24C16@SOP8 [SA602A]

L24C02@SOP8 [SA602A]  
L24C04  
L24C04@TSSOP8 [SA643]  
L24C08@SOP8 [SA602A]  
L24C16  
L24C16@TSSOP8 [SA643]

## LUMINARY

### MICROCONTROLLER

LM3S101 (new)@SOIC28 (ISP)  
LM3S102 (new)@SOIC28 (ISP)  
LM3S1110@BGA108 (ISP)  
LM3S1133@BGA108 (ISP)  
LM3S1138@BGA108 (ISP)  
LM3S1150@BGA108 (ISP)  
LM3S1162@BGA108 (ISP)  
LM3S1165@BGA108 (ISP)  
LM3S1332@BGA108 (ISP)  
LM3S1435@BGA108 (ISP)  
LM3S1439@BGA108 (ISP)  
LM3S1512@BGA108 (ISP)  
LM3S1538@BGA108 (ISP)  
LM3S1601@BGA108 (ISP)  
LM3S1607@TQFP64 (ISP)  
LM3S1608@TQFP100 (ISP)  
LM3S1620@TQFP100 (ISP)  
LM3S1626@TQFP64 (ISP)  
LM3S1635@BGA108 (ISP)  
LM3S1637@BGA108 (ISP)  
LM3S1751@BGA108 (ISP)  
LM3S1776@TQFP64 (ISP)

LM3S101 (old)@SOIC28 (ISP)  
LM3S102 (old)@SOIC28 (ISP)  
LM3S1110@TQFP100 (ISP)  
LM3S1133@TQFP100 (ISP)  
LM3S1138@TQFP100 (ISP)  
LM3S1150@TQFP100 (ISP)  
LM3S1162@TQFP100 (ISP)  
LM3S1165@TQFP100 (ISP)  
LM3S1332@TQFP100 (ISP)  
LM3S1435@TQFP100 (ISP)  
LM3S1439@TQFP100 (ISP)  
LM3S1512@TQFP100 (ISP)  
LM3S1538@TQFP100 (ISP)  
LM3S1601@TQFP100 (ISP)  
LM3S1608@BGA108 (ISP)  
LM3S1620@BGA108 (ISP)  
LM3S1625@TQFP64 (ISP)  
LM3S1627@TQFP64 (ISP)  
LM3S1635@TQFP100 (ISP)  
LM3S1637@TQFP100 (ISP)  
LM3S1751@TQFP100 (ISP)  
LM3S1850@BGA108 (ISP)

LM3S1850@TQFP100 (ISP)  
LM3S1911@TQFP100 (ISP)  
LM3S1918@TQFP100 (ISP)  
LM3S1937@TQFP100 (ISP)  
LM3S1958@TQFP100 (ISP)  
LM3S1960@TQFP100 (ISP)  
LM3S1968@TQFP100 (ISP)  
LM3S2016@TQFP100 (ISP)  
LM3S2110@TQFP100 (ISP)  
LM3S2139@TQFP100 (ISP)  
LM3S2410@BGA108 (ISP)  
LM3S2412@BGA108 (ISP)  
LM3S2432@BGA108 (ISP)  
LM3S2533@BGA108 (ISP)  
LM3S2601@BGA108 (ISP)  
LM3S2608@BGA108 (ISP)  
LM3S2616@TQFP64 (ISP)  
LM3S2620@TQFP100 (ISP)  
LM3S2637@TQFP100 (ISP)  
LM3S2651@TQFP100 (ISP)  
LM3S2678@TQFP64 (ISP)  
LM3S2730@TQFP100 (ISP)  
LM3S2739@TQFP100 (ISP)  
LM3S2911@BGA108 (ISP)  
LM3S2918@BGA108 (ISP)  
LM3S2939@BGA108 (ISP)  
LM3S2948@BGA108 (ISP)  
LM3S2950@BGA108 (ISP)  
LM3S2965@BGA108 (ISP)  
LM3S300@LQFP48 (ISP)  
LM3S301 (old) @LQFP48 (ISP)  
LM3S310 (new) @LQFP48 (ISP)  
LM3S315 (new) @LQFP48 (ISP)  
LM3S316 (new) @LQFP48 (ISP)  
LM3S317 (new) @LQFP48 (ISP)  
LM3S328 (new) @LQFP48 (ISP)  
LM3S3651@TQFP64 (ISP)  
LM3S3739@TQFP100 (ISP)  
LM3S3748@TQFP100 (ISP)  
LM3S3749@TQFP100 (ISP)  
LM3S3759@TQFP100 (ISP)  
LM3S3768@TQFP100 (ISP)  
LM3S5652@TQFP64 (ISP)  
LM3S5732@TQFP64 (ISP)  
LM3S5737@TQFP100 (ISP)  
LM3S5739@TQFP100 (ISP)  
LM3S5747@TQFP100 (ISP)  
LM3S5749@TQFP100 (ISP)  
LM3S5757@BGA108 (ISP)  
LM3S5762@TQFP64 (ISP)  
LM3S5767@TQFP100 (ISP)  
LM3S5768@TQFP100 (ISP)  
LM3S5769@TQFP100 (ISP)  
LM3S1911@BGA108 (ISP)  
LM3S1918@BGA108 (ISP)  
LM3S1937@BGA108 (ISP)  
LM3S1958@BGA108 (ISP)  
LM3S1960@BGA108 (ISP)  
LM3S1968@BGA108 (ISP)  
LM3S2016@BGA108 (ISP)  
LM3S2110@BGA108 (ISP)  
LM3S2139@BGA108 (ISP)  
LM3S2276@TQFP64 (ISP)  
LM3S2410@TQFP100 (ISP)  
LM3S2412@TQFP100 (ISP)  
LM3S2432@TQFP100 (ISP)  
LM3S2533@TQFP100 (ISP)  
LM3S2601@TQFP100 (ISP)  
LM3S2608@TQFP100 (ISP)  
LM3S2620@BGA108 (ISP)  
LM3S2637@BGA108 (ISP)  
LM3S2651@BGA108 (ISP)  
LM3S2671@TQFP64 (ISP)  
LM3S2730@BGA108 (ISP)  
LM3S2739@BGA108 (ISP)  
LM3S2776@TQFP64 (ISP)  
LM3S2911@TQFP100 (ISP)  
LM3S2918@TQFP100 (ISP)  
LM3S2939@TQFP100 (ISP)  
LM3S2948@TQFP100 (ISP)  
LM3S2950@TQFP100 (ISP)  
LM3S2965@TQFP100 (ISP)  
LM3S301 (new) @LQFP48 (ISP)  
LM3S308@LQFP48 (ISP)  
LM3S310 (old) @LQFP48 (ISP)  
LM3S315 (old) @LQFP48 (ISP)  
LM3S316 (old) @LQFP48 (ISP)  
LM3S317 (old) @LQFP48 (ISP)  
LM3S328 (old) @LQFP48 (ISP)  
LM3S3739@BGA108 (ISP)  
LM3S3748@BGA108 (ISP)  
LM3S3749@BGA108 (ISP)  
LM3S3759@BGA108 (ISP)  
LM3S3768@BGA108 (ISP)  
LM3S5632@TQFP64 (ISP)  
LM3S5662@TQFP64 (ISP)  
LM3S5737@BGA108 (ISP)  
LM3S5739@BGA108 (ISP)  
LM3S5747@BGA108 (ISP)  
LM3S5749@BGA108 (ISP)  
LM3S5752@TQFP64 (ISP)  
LM3S5757@TQFP100 (ISP)  
LM3S5767@BGA108 (ISP)  
LM3S5768@BGA108 (ISP)  
LM3S5769@BGA108 (ISP)  
LM3S600@LQFP48 (ISP)

LM3S601 (new)@LQFP48 (ISP)  
LM3S608@LQFP48 (ISP)  
LM3S610 (old)@LQFP48 (ISP)  
LM3S6100@TQFP100 (ISP)  
LM3S611 (old)@LQFP48 (ISP)  
LM3S6110@TQFP100 (ISP)  
LM3S612 (old)@LQFP48 (ISP)  
LM3S613 (old)@LQFP48 (ISP)  
LM3S615 (old)@LQFP48 (ISP)  
LM3S617 (old)@LQFP48 (ISP)  
LM3S618 (old)@LQFP48 (ISP)  
LM3S628 (old)@LQFP48 (ISP)  
LM3S6420@TQFP100 (ISP)  
LM3S6422@TQFP100 (ISP)  
LM3S6432@TQFP100 (ISP)  
LM3S6537@TQFP100 (ISP)  
LM3S6610@TQFP100 (ISP)  
LM3S6611@TQFP100 (ISP)  
LM3S6618@TQFP100 (ISP)  
LM3S6633@TQFP100 (ISP)  
LM3S6637@TQFP100 (ISP)  
LM3S6730@TQFP100 (ISP)  
LM3S6753@TQFP100 (ISP)  
LM3S6816@TQFP100 (ISP)  
LM3S6911@TQFP100 (ISP)  
LM3S6916@TQFP100 (ISP)  
LM3S6918@TQFP100 (ISP)  
LM3S6938@TQFP100 (ISP)  
LM3S6950@TQFP100 (ISP)  
LM3S6952@TQFP100 (ISP)  
LM3S6965@TQFP100 (ISP)  
LM3S801 (new)@LQFP48 (ISP)  
LM3S808@LQFP48 (ISP)  
LM3S811 (old)@LQFP48 (ISP)  
LM3S812 (old)@LQFP48 (ISP)  
LM3S815 (old)@LQFP48 (ISP)  
LM3S817 (old)@LQFP48 (ISP)  
LM3S818 (old)@LQFP48 (ISP)  
LM3S828 (old)@LQFP48 (ISP)  
LM3S8530@TQFP100 (ISP)  
LM3S8538@TQFP100 (ISP)  
LM3S8630@TQFP100 (ISP)  
LM3S8730@TQFP100 (ISP)  
LM3S8733@TQFP100 (ISP)  
LM3S8738@TQFP100 (ISP)  
LM3S8930@TQFP100 (ISP)  
LM3S8933@TQFP100 (ISP)  
LM3S8938@TQFP100 (ISP)  
LM3S8962@TQFP100 (ISP)  
LM3S8970@TQFP100 (ISP)  
LM3S8971@TQFP100 (ISP)

LM3S601 (old)@LQFP48 (ISP)  
LM3S610 (new)@LQFP48 (ISP)  
LM3S6100@BGA108 (ISP)  
LM3S611 (new)@LQFP48 (ISP)  
LM3S6110@BGA108 (ISP)  
LM3S612 (new)@LQFP48 (ISP)  
LM3S613 (new)@LQFP48 (ISP)  
LM3S615 (new)@LQFP48 (ISP)  
LM3S617 (new)@LQFP48 (ISP)  
LM3S618 (new)@LQFP48 (ISP)  
LM3S628 (new)@LQFP48 (ISP)  
LM3S6420@BGA108 (ISP)  
LM3S6422@BGA108 (ISP)  
LM3S6432@BGA108 (ISP)  
LM3S6537@BGA108 (ISP)  
LM3S6610@BGA108 (ISP)  
LM3S6611@BGA108 (ISP)  
LM3S6618@BGA108 (ISP)  
LM3S6633@BGA108 (ISP)  
LM3S6637@BGA108 (ISP)  
LM3S6730@BGA108 (ISP)  
LM3S6753@BGA108 (ISP)  
LM3S6816@BGA108 (ISP)  
LM3S6911@BGA108 (ISP)  
LM3S6916@BGA108 (ISP)  
LM3S6918@BGA108 (ISP)  
LM3S6938@BGA108 (ISP)  
LM3S6950@BGA108 (ISP)  
LM3S6952@BGA108 (ISP)  
LM3S6965@BGA108 (ISP)  
LM3S800@LQFP48 (ISP)  
LM3S801 (old)@LQFP48 (ISP)  
LM3S811 (new)@LQFP48 (ISP)  
LM3S812 (new)@LQFP48 (ISP)  
LM3S815 (new)@LQFP48 (ISP)  
LM3S817 (new)@LQFP48 (ISP)  
LM3S818 (new)@LQFP48 (ISP)  
LM3S828 (new)@LQFP48 (ISP)  
LM3S8530@BGA108 (ISP)  
LM3S8538@BGA108 (ISP)  
LM3S8630@BGA108 (ISP)  
LM3S8730@BGA108 (ISP)  
LM3S8733@BGA108 (ISP)  
LM3S8738@BGA108 (ISP)  
LM3S8930@BGA108 (ISP)  
LM3S8933@BGA108 (ISP)  
LM3S8938@BGA108 (ISP)  
LM3S8962@BGA108 (ISP)  
LM3S8970@BGA108 (ISP)  
LM3S8971@BGA108 (ISP)

## LYONTEK

### E (E) PROM/FRAM/NVRAM

LY24C02	LY24C02@SOIC8 [SA602A]
LY24C02@TSSOP8 [SA643]	LY24C04
LY24C04@SOIC8 [SA602A]	LY24C04@TSSOP8 [SA643]
LY24C08	LY24C08@SOIC8 [SA602A]
LY24C08@TSSOP8 [SA643]	LY24C16
LY24C16@SOIC8 [SA602A]	LY24C16@TSSOP8 [SA643]

## MACRONIX

### E (E) PROM/FRAM/NVRAM

KH25L1005	KH25L1005 (ISP)
KH25L1005@SON8 [SA683]	KH25L1005@SON8 (ISP)
KH25L1005@SOP8 [SA602A]	KH25L1005@SOP8 (ISP)
KH25L1005A	KH25L1005A@SON8 [SA683]
KH25L1005A@SOP8 [SA602A]	
KH25L12805D@SON8 (Fast Mode) [SA684]	
KH25L12805D@SOP16 (Fast Mode) [SA404]	
KH25L12805N@SOP16 [SA404]	
KH25L12805N@SOP16 (Fast Mode) [SA404]	
KH25L12835F@SOP16 [SA404]	KH25L12835F@SOP8 [SA605B]
KH25L12835F@WSON8 (6*5mm) [SA683]	KH25L12835F@WSON8 (8*6mm) [SA684]
KH25L1605@SON8 [SA684]	
KH25L1605@SON8 (Fast Mode) [SA684]	
KH25L1605@SOP16 [SA404]	
KH25L1605@SOP16 (Fast Mode) [SA404]	
KH25L1605A@SON8 [SA684]	
KH25L1605A@SON8 (Fast Mode) [SA684]	
KH25L1605A@SOP16 [SA404]	
KH25L1605A@SOP16 (Fast Mode) [SA404]	
KH25L1605A@SOP8 [SA605B]	
KH25L1605A@SOP8 (Fast Mode) [SA605B]	
KH25L1605D@SON8 [SA684]	
KH25L1605D@SON8 (Fast Mode) [SA684]	
KH25L1605D@SOP16 [SA404]	
KH25L1605D@SOP16 (Fast Mode) [SA404]	
KH25L1605D@SOP8 (150) (Fast Mode) [SA602A]	
KH25L1605D@SOP8 (200) (Fast Mode) [SA605B]	
KH25L1606E	KH25L1606E (512bit)
KH25L1606E (512bit)@SOIC16 [SA404]	
KH25L1606E (512bit)@SOIC8 (150mil) [SA602A]	
KH25L1606E (512bit)@SOIC8 (200mil) [SA605B]	
KH25L1606E (512bit)@USON8 [SA744]	KH25L1606E (512bit)@WSON8 [SA683]
KH25L1606E@SOP16 [SA404]	
KH25L1606E@SOP8 (150 mil) [SA602A]	
KH25L1606E@SOP8 (200 mil) [SA605B]	
KH25L1606E@USON8 [SA744]	KH25L1606E@WSON8 [SA683]
KH25L1636D@SOP16 [SA404]	KH25L1636D@SOP8 (150mil) [SA602A]

KH25L1636D@SOP8 (200mil) [SA605B]      KH25L1636D@WSON8 [SA683]  
KH25L1673E@SOP8 [SA605B]      KH25L2005  
KH25L2005 (ISP)      KH25L2005@SON8 [SA683]  
KH25L2005@SON8 (ISP)      KH25L2005@SOP8 [SA602A]  
KH25L2005@SOP8 (ISP)      KH25L2025  
KH25L2025@SON8 [SA683]      KH25L2025@SOP8 [SA602A]  
KH25L25635F@SOP16 [SA783]      KH25L25635F@WSON8 [SA684]  
KH25L3205@SOP16 [SA404]  
KH25L3205@SOP16 (Fast Mode) [SA404]  
KH25L3205@SOP8 [SA605B]  
KH25L3205@SOP8 (Fast Mode) [SA605B]  
KH25L3205A@SON8 [SA684]  
KH25L3205A@SON8 (Fast Mode) [SA684]  
KH25L3205A@SOP16 [SA404]  
KH25L3205A@SOP16 (Fast Mode) [SA404]  
KH25L3205A@SOP8 [SA605B]  
KH25L3205A@SOP8 (Fast Mode) [SA605B]  
KH25L3205D@SON8 (Fast Mode) [SA684]  
KH25L3205D@SOP16 [SA404]  
KH25L3205D@SOP16 (Fast Mode) [SA404]  
KH25L3205D@SOP8 [SA605B]  
KH25L3205D@SOP8 (Fast Mode) [SA605B]  
KH25L3206E [SA605B]      KH25L3206E (512bit)  
KH25L3206E (512bit)@SOIC16 [SA404]  
KH25L3206E (512bit)@SOIC8 [SA605B]  
KH25L3206E (512bit)@USON8 [SA744]      KH25L3206E (512bit)@WSON8 [SA683]  
KH25L3206E@SOP16 [SA404]      KH25L3206E@SOP8 [SA605B]  
KH25L3206E@USON8 [SA744]      KH25L3206E@WSON8 [SA683]  
KH25L3236D@SOP16 [SA404]      KH25L3236D@SOP8 (150mil) [SA602A]  
KH25L3236D@SOP8 (200mil) [SA605B]      KH25L3236D@WSON8 [SA683]  
KH25L3239E@SOP8 [SA605B]      KH25L3239E@VSOP8 [SA605B]  
KH25L3239E@WSON8 [SA683]      KH25L3273E@SOP16 [SA404]  
KH25L3273E@SOP8 [SA605B]      KH25L3273E@VSOP8 [SA605B]  
KH25L3273E@WSON8 [SA683]      KH25L4005  
KH25L4005 (150mil)@SOP8 [SA602A]      KH25L4005 (150mil)@SOP8 (ISP)  
KH25L4005 (209mil)@SOP8 [SA605B]      KH25L4005 (209mil)@SOP8 (ISP)  
KH25L4005 (ISP)      KH25L4005@SON8 [SA683]  
KH25L4005@SON8 (ISP)      KH25L4005A  
KH25L4005A (150mil)@SOP8 [SA602A]      KH25L4005A (150mil)@SOP8 (ISP)  
KH25L4005A (209mil)@SOP8 [SA605B]      KH25L4005A (209mil)@SOP8 (ISP)  
KH25L4005A (ISP)      KH25L4005A@SON8 [SA683]  
KH25L4005A@SON8 (ISP)      KH25L4006E  
KH25L4006E@SOP8 (150 mil) [SA602A]  
KH25L4006E@SOP8 (200 mil) [SA605B]  
KH25L4006E@WSON8 [SA683]  
KH25L4025A (150mil)@SOP8 [SA602A]      KH25L4025A  
KH25L4025A@SON8 [SA683]      KH25L4025A (209mil)@SOP8 [SA605B]  
KH25L512@SOP8 [SA602A]      KH25L512@SON8 [SA683]  
KH25L5121E@TSSOP8 [SA643]      KH25L5121E@SOP8 [SA602A]  
KH25L512A@SON8 [SA683]      KH25L512A  
KH25L6405@SOP16 [SA404]      KH25L512A@SOP8 [SA602A]  
KH25L6405@SOP16 (Fast Mode) [SA404]  
KH25L6405@SOP8 [SA605B]

KH25L6405@SOP8 (Fast Mode) [SA605B]  
KH25L6405D@SON8 (Fast Mode) [SA684]  
KH25L6405D@SOP16 [SA404]  
KH25L6405D@SOP16 (Fast Mode) [SA404]  
KH25L6405D@SOP8 [SA605B]  
KH25L6405MC@SOP8 [SA605B]  
KH25L6406E@SOP8 [SA605B]  
KH25L6473E@SOP16 [SA404]  
KH25L6473E@VSOP8 [SA605B]  
KH25L8005  
KH25L8005 (150mil)@SOP8 (ISP)  
KH25L8005 (209mil)@SOP8 (ISP)  
KH25L8005@SON8 [SA683]  
KH25L8006E  
KH25L8006E (512bit)@SOIC8 (150mil) [SA602A]  
KH25L8006E (512bit)@SOIC8 (200mil) [SA605B]  
KH25L8006E (512bit)@USON8 [SA744]  
KH25L8006E@SOP8 (150 mil) [SA602A]  
KH25L8006E@SOP8 (200 mil) [SA605B]  
KH25L8006E@USON8 [SA744]  
KH25L8025  
KH25L8025 (209mil)@SOP8 [SA605B]  
KH25L8036D  
KH25L8036D@SOP8 (150mil) [SA602A]  
KH25L8036D@WSON8 [SA683]  
KH25U4033E@SOP8 [SA602A]  
KH25U4033E@USON8 [SA744]  
KH25U6439F@SOP8 [SA605B]  
KH25U6439F@WSON8 [SA683]  
KH29LV004CB@TSOP40 [SA409T-B4002]  
KH29LV004CT@PLCC32 [SA015A1T]  
KH29LV004CT@TSOP40 [SA409T-B4002]  
KH29LV008CB@TSOP40 [SA409T-B4002]  
KH29LV008CT@TSOP40 [SA409T-B4002]  
KH29LV040C  
KH29LV040C@PLCC32 [SA015A1T]  
KH29LV160CBT@TSOP48 [SB247-B4806]  
KH29LV160CTT@TSOP48 [SB247-B4806]  
KH29LV160DBT@TSOP48 [SB247-B4806]  
KH29LV160DTT@TSOP48 [SB247-B4806]  
KH29LV320CBT@TSOP48 [SB247-B4806]  
KH29LV320CTT@TSOP48 [SB247-B4806]  
KH29LV320DBT@TSOP48 [SB247-B4806]  
KH29LV320DTT@TSOP48 [SB247-B4806]  
KH29LV320EBT@TSOP48 [SB247-B4806]  
KH29LV320ETT@TSOP48 [SB247-B4806]  
KH29LV400CBT@TSOP48 [SB247-B4806]  
KH29LV400CTT@TSOP48 [SB247-B4806]  
KH29LV640DBT@TSOP48 [SB247-B4806]  
KH29LV640DTT@TSOP48 [SB247-B4806]  
KH29LV800CBT@TSOP48 [SB247-B4806]  
KH29LV800CTT@TSOP48 [SB247-B4806]  
KH29SV400CBT@TSOP48 [SB247-B4806]  
KH29SV400CTT@TSOP48 [SB247-B4806]

KH25L6405MC@SOP16 [SA404]  
KH25L6406E@SOP16 [SA783]  
KH25L6406E@WSON8 [SA684]  
KH25L6473E@SOP8 [SA605B]  
KH25L6473E@WSON8 [SA683]  
KH25L8005 (150mil)@SOP8 [SA602A]  
KH25L8005 (209mil)@SOP8 [SA605B]  
KH25L8005 (ISP)  
KH25L8005@SON8 (ISP)  
KH25L8006E (512bit)  
KH25L8006E (512bit)@WSON8 [SA683]  
KH25L8006E@WSON8 [SA683]  
KH25L8025 (150mil)@SOP8 [SA602A]  
KH25L8025@SON8 [SA683]  
KH25L8036D@SOP16 [SA404]  
KH25L8036D@SOP8 (200mil) [SA605B]  
KH25L8073E@SOP8 [SA605B]  
KH25U4033E@TSSOP8 [SA643]  
KH25U4033E@WSON8 [SA683]  
KH25U6439F@VSOP8 [SA605B]  
KH29LV004CB@PLCC32 [SA015A1T]  
KH29LV040C@PLCC32 [SA015A1T]

MX25L1005	MX25L1005 (ISP)
MX25L1005@SON8 [SA683]	MX25L1005@SON8 (ISP)
MX25L1005@SOP8 [SA602A]	MX25L1005@SOP8 (ISP)
MX25L1005@USON8 [SA724]	MX25L1005A
MX25L1005A@SON8 [SA683]	MX25L1005A@SOP8 [SA602A]
MX25L1005C@SOP8 [SA602A]	MX25L1005C@USON8 [SA724]
MX25L1006E@SOP8 [SA602A]	MX25L1006E@USON8 [SA724]
MX25L1006E@WLCSP8 [\$\$\$\$\$]	MX25L1021E@SOP8 [SA602A]
MX25L1025C@SOP8 [SA602A]	MX25L1026E@SOP8 [SA602A]
MX25L12805D@SON8 (Fast Mode) [SA684]	
MX25L12805D@SOP16 (512bit OTP) [SA783]	
MX25L12805D@SOP16 (Fast Mode) [SA404]	
MX25L12805D@WSON8 (512bit OTP) [SA684]	
MX25L12805N@SOP16 [SA404]	
MX25L12805N@SOP16 (Fast Mode) [SA404]	
MX25L12835E@SOP16 [SA404]	MX25L12835E@WSON8 [SA684]
MX25L12835F@SOP16 [SA404]	MX25L12835F@SOP8 [SA605B]
MX25L12835F@WSON8 (6*5mm) [SA683]	MX25L12835F@WSON8 (8*6mm) [SA684]
MX25L12836E@SOP16 [SA404]	MX25L12836E@SOP8 [SA605B]
MX25L12836E@WSON8 [SA684]	MX25L12845E@SOP16 [SA783]
MX25L12845E@WSON8 [SA684]	MX25L12845E@WSON8 (*) [SA684]
MX25L12845G@SOP16 [SA404]	MX25L12845G@SOP8 [SA605B]
MX25L12845G@WSON8 [SA684]	MX25L12855E@SOP16 [SA404]
MX25L12865E@SOP16 [SA404]	MX25L12865E@SOP8 [SA605B]
MX25L12865E@WSON8 [SA684]	MX25L12865F@SOP16 [SA404]
MX25L12865F@SOP8 [SA605B]	MX25L12865F@WSON8 [SA684]
MX25L12873F@SOP16 [SA404]	MX25L12873F@SOP8 [SA605B]
MX25L12873F@WSON8 [SA683]	MX25L12875E@SOP16 [SA404]
MX25L12875E@SOP8 [SA605B]	MX25L12875E@WSON8 [SA684]
MX25L1605@SON8 [SA684]	
MX25L1605@SON8 (Fast Mode) [SA684]	
MX25L1605@SOP16 [SA404]	
MX25L1605@SOP16 (Fast Mode) [SA404]	
MX25L1605A@SON8 [SA684]	
MX25L1605A@SON8 (Fast Mode) [SA684]	
MX25L1605A@SOP16 [SA404]	
MX25L1605A@SOP16 (Fast Mode) [SA404]	
MX25L1605A@SOP8 [SA605B]	
MX25L1605A@SOP8 (Fast Mode) [SA605B]	
MX25L1605D (512bit OTP)	MX25L1605D@SON8 [SA684]
MX25L1605D@SON8 (Fast Mode) [SA684]	
MX25L1605D@SOP16 [SA404]	
MX25L1605D@SOP16 (512bit OTP) [SA783]	
MX25L1605D@SOP16 (Fast Mode) [SA404]	
MX25L1605D@SOP8 (150) (Fast Mode) [SA602A]	
MX25L1605D@SOP8 (200) (Fast Mode) [SA605B]	
MX25L1605D@SOP8 (512bit OTP) (150) [SA602A]	
MX25L1605D@SOP8 (512bit OTP) (200) [SA605B]	
MX25L1605D@USON8 [SA744]	
MX25L1605D@USON8 (512bit OTP) [SA744]	
MX25L1605D@USON8 (Fast Mode) [SA744]	
MX25L1605D@WSON8 (512bit OTP) [SA683]	
MX25L1606E	MX25L1606E (512bit)

MX25L1606E(512bit)@SOIC16 [SA404]  
MX25L1606E(512bit)@SOIC8(150mil) [SA602A]  
MX25L1606E(512bit)@SOIC8(200mil) [SA605B]  
MX25L1606E(512bit)@USON8 [SA744]      MX25L1606E(512bit)@WSON8 [SA683]  
MX25L1606E@SOP16 [SA404]  
MX25L1606E@SOP8(150 mil) [SA602A]  
MX25L1606E@SOP8(200 mil) [SA605B]  
MX25L1606E@USON8 [SA744]      MX25L1606E@WSON8 [SA683]  
MX25L1606EG@SOP8(200 mil) [SA605B]  
MX25L1608D      MX25L1608D@SOP16 [SA783]  
MX25L1608D@SOP8(150mil) [SA602A]      MX25L1608D@SOP8(200mil) [SA605B]  
MX25L1608D@USON8 [SA744]      MX25L1608D@WSON8 [SA683]  
MX25L1608E@SOP8(150mil) [SA602A]      MX25L1608E@SOP8(200mil) [SA605B]  
MX25L1615D@SOP16 [SA404]      MX25L1615D@SOP8 [SA605B]  
MX25L1633E@SOP16 [SA404]      MX25L1633E@SOP8 [SA605B]  
MX25L1633E@WSON8 [SA683]      MX25L1635D@SOP16 [SA404]  
MX25L1635D@SOP8(150mil) [SA602A]      MX25L1635D@SOP8(200mil) [SA605B]  
MX25L1635D@WSON8 [SA683]      MX25L1635E@SOP8 [SA605B]  
MX25L1636D@SOP16 [SA404]      MX25L1636D@SOP8(150mil) [SA602A]  
MX25L1636D@SOP8(200mil) [SA605B]      MX25L1636D@WSON8 [SA683]  
MX25L1636E@SOP8 [SA605B]      MX25L1673E@SOP8 [SA605B]  
MX25L1675E@SOP8 [SA605B]      MX25L1675E@WSON8 [SA683]  
MX25L2005      MX25L2005(ISP)  
MX25L2005@SON8 [SA683]      MX25L2005@SON8(ISP)  
MX25L2005@SOP8 [SA602A]      MX25L2005@SOP8(ISP)  
MX25L2005C@SOP8 [SA602A]      MX25L2005C@USON8 [SA683]  
MX25L2006E@SOP8 [SA602A]      MX25L2006E@WSON8 [SA683]  
MX25L2025      MX25L2025@SON8 [SA683]  
MX25L2025@SOP8 [SA602A]      MX25L2026C@SOP8 [SA602A]  
MX25L2026E@SOP8 [SA602A]      MX25L2026E@WSON8 [SA683]  
MX25L25635E@SOP16 [SA783]      MX25L25635E@WSON8 [SA684]  
MX25L3205@SOP16 [SA404]  
MX25L3205@SOP16(Fast Mode) [SA404]  
MX25L3205@SOP8 [SA605B]  
MX25L3205@SOP8(Fast Mode) [SA605B]  
MX25L3205A@SON8 [SA684]  
MX25L3205A@SON8(Fast Mode) [SA684]  
MX25L3205A@SOP16 [SA404]  
MX25L3205A@SOP16(Fast Mode) [SA404]  
MX25L3205A@SOP8 [SA605B]  
MX25L3205A@SOP8(Fast Mode) [SA605B]  
MX25L3205D(512bit OTP)  
MX25L3205D@SON8(Fast Mode) [SA684]  
MX25L3205D@SOP16 [SA404]  
MX25L3205D@SOP16(512bit OTP) [SA783]  
MX25L3205D@SOP16(Fast Mode) [SA404]  
MX25L3205D@SOP8 [SA605B]  
MX25L3205D@SOP8(512bit OTP) [SA605B]  
MX25L3205D@SOP8(Fast Mode) [SA605B]  
MX25L3205D@USON8 [SA744]  
MX25L3205D@USON8(512bit OTP) [SA744]  
MX25L3205D@USON8(Fast Mode) [SA744]  
MX25L3205D@WSON8(512bit OTP) [SA683]

MX25L3206E [SA605B]  
MX25L3206E (512bit)@S0IC16 [SA783]  
MX25L3206E (512bit)@S0IC8 [SA605B]  
MX25L3206E (512bit)@USON8 [SA744]  
MX25L3206E@SOP16 [SA783]  
MX25L3206E@USON8 [SA744]  
MX25L3208D  
MX25L3208D@SOP8 [SA605B]  
MX25L3208D@WSON8 [SA683]  
MX25L3215D@SOP16 [SA404]  
MX25L3225D@SOP8 [SA605B]  
MX25L3233F@SOP16 [SA783]  
MX25L3233F@SOP8 (150 mil) [SA605B]  
MX25L3233F@SOP8 (200 mil) [SA605B]  
MX25L3233F@USON8 [SA744]  
MX25L3235D@SOP16 [SA404]  
MX25L3235D@WSON8 [SA683]  
MX25L3235E@WSON8 [SA683]  
MX25L3236D@SOP8 (150mil) [SA602A]  
MX25L3236D@WSON8 [SA683]  
MX25L3237D@WSON8 [SA683]  
MX25L3239E@VSOP8 [SA605B]  
MX25L3273E@SOP16 [SA404]  
MX25L3273E@VSOP8 [SA605B]  
MX25L3275E@SOP16 [SA404]  
MX25L3275E@WSON8 [SA683]  
MX25L4005 (150mil)@SOP8 [SA602A]  
MX25L4005 (209mil)@SOP8 [SA605B]  
MX25L4005 (ISP)  
MX25L4005@SON8 (ISP)  
MX25L4005A (150mil)@SOP8 [SA602A]  
MX25L4005A (209mil)@SOP8 [SA605B]  
MX25L4005A (ISP)  
MX25L4005A@SON8 (ISP)  
MX25L4005C  
MX25L4005C@TSSOP8 [SA605B]  
MX25L4006E  
MX25L4006E@SOP8 (150 mil) [SA602A]  
MX25L4006E@SOP8 (200 mil) [SA605B]  
MX25L4006E@USON8 [SA724]  
MX25L4006EG@SOP8 (200 mil) [SA605B]  
MX25L4025@SOP8 [SA602A]  
MX25L4025A (150mil)@SOP8 [SA602A]  
MX25L4025A@SON8 [SA683]  
MX25L4026E@SOP8 [SA602A]  
MX25L512@SOP8 [SA602A]  
MX25L5121E@SOP8 [SA602A]  
MX25L512A  
MX25L512A@SOP8 [SA602A]  
MX25L512C@TSSOP8 [SA643]  
MX25L512E@SOP8 [SA602A]  
MX25L512E@USON8 [SA724]  
MX25L6405@SOP16 (Fast Mode) [SA404]  
MX25L3206E (512bit)  
MX25L3206E (512bit)@WSON8 [SA683]  
MX25L3206E@SOP8 [SA605B]  
MX25L3206E@WSON8 [SA683]  
MX25L3208D@SOP16 [SA783]  
MX25L3208D@USON8 [SA744]  
MX25L3208E@SOP8 [SA605B]  
MX25L3215D@SOP8 [SA605B]  
MX25L3233F [SA605B]  
MX25L3233F@WSON8 [SA683]  
MX25L3235D@SOP8 [SA605B]  
MX25L3235E@SOP8 [SA605B]  
MX25L3236D@SOP16 [SA404]  
MX25L3236D@SOP8 (200mil) [SA605B]  
MX25L3237D@SOP16 [SA404]  
MX25L3239E@SOP8 [SA605B]  
MX25L3239E@WSON8 [SA683]  
MX25L3273E@SOP8 [SA605B]  
MX25L3273E@WSON8 [SA683]  
MX25L3275E@SOP8 [SA605B]  
MX25L4005  
MX25L4005 (150mil)@SOP8 (ISP)  
MX25L4005 (209mil)@SOP8 (ISP)  
MX25L4005@SON8 [SA683]  
MX25L4005A  
MX25L4005A (150mil)@SOP8 (ISP)  
MX25L4005A (209mil)@SOP8 (ISP)  
MX25L4005A@SON8 [SA683]  
MX25L4005A@USON8 [SA744]  
MX25L4005C@SOP8 [SA602A]  
MX25L4005C@USON8 [SA683]  
MX25L4006E@WSON8 [SA683]  
MX25L4025A  
MX25L4025A (209mil)@SOP8 [SA605B]  
MX25L4026D@SOP8 [SA602A]  
MX25L512@SON8 [SA683]  
MX25L512@USON8 [SA724]  
MX25L5121E@TSSOP8 [SA643]  
MX25L512A@SON8 [SA683]  
MX25L512C  
MX25L512C@USON8 [SA724]  
MX25L512E@TSSOP8 [SA643]  
MX25L6405@SOP16 [SA404]



MX25R3233F@USON8 [SA744]  
MX25R3235F@SOP8 [SA602A]  
MX25R3235F@WSON8 [SA683]  
MX25R6435F@USON8 [SA744]  
MX25U12835F@SOP16 [SA404]  
MX25U12835F@WSON8 [SA684]  
MX25U1631@USON8 (4\*4mm) [SA744]  
MX25U1635@SOIC8 [SA602A]  
MX25U1635@USON8 (4\*4mm) [SA744]  
MX25U1635E@SOP8 (150mil) [SA602A]  
MX25U1635E@USON8 [SA744]  
MX25U2032E@SOP8 [SA602A]  
MX25U2032E@WSON8 [SA683]  
MX25U2033E@USON8 [SA744]  
MX25U3235E@SOP8 (150mil) [SA602A]  
MX25U3235E@USON8 [SA744]  
MX25U3235F@SOP8 [SA605B]  
MX25U4032E@SOP8 [SA602A]  
MX25U4032E@WSON8 [SA683]  
MX25U4033E@TSSOP8 [SA643]  
MX25U4033E@WSON8 [SA683]  
MX25U4035@USON8 (4\*4mm) [SA744]  
MX25U6435E@WSON8 [SA683]  
MX25U6435F@WSON8 [SA683]  
MX25U6439F@VSOP8 [SA605B]  
MX25U6473F@SOP8 [SA605B]  
MX25U8032E@SOP8 (200mil) [SA605B]  
MX25U8032E@USON8 (4\*4) [SA744]  
MX25U8033E@SOP8 (150mil) [SA602A]  
MX25U8033E@USON8 (4\*3) [\$\$\$\$\$]  
MX25U8033E@WSON8 [SA683]  
MX25U8035@USON8 (4\*4mm) [SA744]  
MX25U8035E@SOP8 (150mil) [SA602A]  
MX25U8035E@USON8 [SA744]  
MX25V1006E@TSSOP8 [SA643]  
MX25V2006E@SOP8 [SA602A]  
MX25V4005  
MX25V4005C@SOP8  
MX25V4006E@SOP8 [SA602A]  
MX25V4035@SOP8 [SA602A]  
MX25V512@USON8 [SA724]  
MX25V512C@USON8 [SA724]  
MX25V512E@USON8 [SA724]  
MX25V6433F@VSOP8 [SA605B]  
MX25V8005@SOP8 [SA602A]  
MX25V8006E (512bit)@SOIC8 [SA602A]  
MX25V8006E (512bit)@WSON8 [SA683]  
MX25V8006E@WSON8 [SA683]  
MX25V8035@WSON8 [SA683]  
MX26C1000@PLCC32 [SA015A1T]  
MX26C1000@TSOP32 [SA410T-B4001]  
MX26C1000B@PLCC32 [SA015A1T]  
MX26C1000B@TSOP32 [SA410T-B4001]  
MX25R3233F@WSON8 [SA683]  
MX25R3235F@USON8 [SA744]  
MX25R6435F@SOP8 [SA605B]  
MX25R6435F@WSON8 [SA683]  
MX25U12835F@USON8 [SA683]  
MX25U1631@USON8 (4\*3mm) [\$\$\$\$\$]  
MX25U1631@USON8 (6\*5mm) [SA683]  
MX25U1635@USON8 (4\*3mm) [\$\$\$\$\$]  
MX25U1635@USON8 (6\*5mm) [SA683]  
MX25U1635E@SOP8 (200mil) [SA605B]  
MX25U1635E@WSON8 [SA683]  
MX25U2032E@USON8 [SA744]  
MX25U2033E@SOP8 [SA602A]  
MX25U2033E@WSON8 [SA683]  
MX25U3235E@SOP8 (200mil) [SA605B]  
MX25U3235E@WSON8 [SA683]  
MX25U3235F@WSON8 [SA683]  
MX25U4032E@USON8 [SA744]  
MX25U4033E@SOP8 [SA602A]  
MX25U4033E@USON8 [SA744]  
MX25U4035@SOIC8 [SA602A]  
MX25U4035@USON8 (6\*5mm) [SA683]  
MX25U6435F@SOP8 [SA605B]  
MX25U6439F@SOP8 [SA605B]  
MX25U6439F@WSON8 [SA683]  
MX25U8032E@SOP8 (150mil) [SA602A]  
MX25U8032E@USON8 (4\*3) [\$\$\$\$\$]  
MX25U8032E@WSON8 [SA683]  
MX25U8033E@SOP8 (200mil) [SA605B]  
MX25U8033E@USON8 (4\*4) [SA744]  
MX25U8035@SOIC8 [SA602A]  
MX25U8035@USON8 (6\*5mm) [SA683]  
MX25U8035E@SOP8 (200mil) [SA605B]  
MX25U8035E@WSON8 [SA683]  
MX25V1006E@USON8 [SA724]  
MX25V2006E@WSON8 [SA683]  
MX25V4005@USON8 [SA683]  
MX25V4005C@WSON8 [SA683]  
MX25V4006E@WSON8 [SA683]  
MX25V4035@WSON8 [SA683]  
MX25V512C@TSSOP8 [SA643]  
MX25V512E@SOP8 [SA602A]  
MX25V6433F@SOP8 [SA605B]  
MX25V6433F@WSON8 [SA683]  
MX25V8005@WSON8 [SA683]  
MX25V8006E@SOP8 [SA602A]  
MX25V8035@SOP8 [SA602A]  
MX26C1000  
MX26C1000@SOIC32 [SA603]  
MX26C1000B  
MX26C1000B@SOIC32 [SA438T]  
MX26C2000B

MX26C2000B@PLCC32 [SA015A1T]  
MX26C2000B@TSOP32 [SA410T-B4001]  
MX26C512A@PLCC32 [SA015A1T]  
MX26C512A@TSOP28 [SA430T-B4003]  
MX26L12811MC@PSOP44 [SA638]  
MX26L6420@PSOP44 [SA638]  
MX26LV004B@PLCC32 [SA015A1T]  
MX26LV004T@PLCC32 [SA015A1T]  
MX26LV008B@TSOP40 [SA409T-B4002]  
MX26LV040  
MX26LV040@TSOP32 [SA410T-B4001]  
MX26LV160TT@TSOP48 [SA247-B4806]  
MX26LV400TT@TSOP48 [SA247-B4806]  
MX26LV800BT@TSOP48 [SA247-B4806]  
MX26LV800TT@TSOP48 [SA247-B4806]  
MX27C1000@PLCC32 [SA015A1T]  
MX27C1000@TSOP32 [SA410T-B4001]  
MX27C1000A@PLCC32 [SA015A1T]  
MX27C1000A@TSOP32 [SA410T-B4001]  
MX27C1001@PLCC32 [SA015A1T]  
MX27C1001@TSOP32 [SA410T-B4001]  
MX27C1024@PLCC44 [SA244]  
MX27C1024@VSOP40 [SA623-B4002]  
MX27C1024A@PLCC44 [SA244]  
MX27C1024A@VSOP40 [SA623-B4002]  
MX27C1024B@PLCC44 [SA244]  
MX27C1024B@VSOP40 [SA623-B4002]  
MX27C1610  
MX27C2000@PLCC32 [SA015A1T]  
MX27C2000@TSOP32 [SA410T-B4001]  
MX27C2000A@PLCC32 [SA015A1T]  
MX27C2000A@TSOP32 [SA410T-B4001]  
MX27C2048@PLCC44 [SA244]  
MX27C2100  
MX27C256@PLCC32 [SA015A1T]  
MX27C4000@PLCC32 [SA015A1T]  
MX27C4000@TSOP32 [SA410T-B4001]  
MX27C4000A@PLCC32 [SA015A1T]  
MX27C4000A@TSOP32 [SA410T-B4001]  
MX27C4096@PLCC44 [SA244]  
MX27C4111  
MX27C512@PLCC32 [SA015A1T]  
MX27C516@PLCC44 [SA244]  
MX27C8000  
MX27C8000@SOIC32 [SA603]  
MX27C8000A  
MX27C8000A@SOIC32 [SA603]  
MX27C8100  
MX27C8111  
MX27L1000  
MX27L1000@TSOP32 [SA410T-B4001]  
MX27L2000@PLCC32 [SA015A1T]  
MX27L256  
MX26C2000B@SOIC32 [SA438T]  
MX26C512A  
MX26C512A@SOIC28 [SA630]  
MX26L12711MC@PSOP44 [SA638]  
MX26L6419T@TSOP48 [SB247-B4806]  
MX26L6420@TSOP48 [SA643]  
MX26LV004B@TSOP40 [SA409T-B4002]  
MX26LV004T@TSOP40 [SA409T-B4002]  
MX26LV008T@TSOP40 [SA409T-B4002]  
MX26LV040@PLCC32 [SA015A1T]  
MX26LV160BT@TSOP48 [SA247-B4806]  
MX26LV400BT@TSOP48 [SA247-B4806]  
MX26LV800BM@PSOP44 [SA638]  
MX26LV800TM@PSOP44 [SA638]  
MX27C1000  
MX27C1000@SOIC32 [SA603]  
MX27C1000A  
MX27C1000A@SOIC32 [SA603]  
MX27C1001  
MX27C1001@SOIC32 [SA603]  
MX27C1024  
MX27C1024@SOP40 [SA682]  
MX27C1024A  
MX27C1024A@SOP40 [SA682]  
MX27C1024B  
MX27C1024B@SOP40 [SA682]  
MX27C1100  
MX27C2000  
MX27C2000@SOIC32 [SA603]  
MX27C2000A  
MX27C2000A@SOIC32 [SA603]  
MX27C2048  
MX27C2048@VSOP40 [SA623-B4002]  
MX27C256  
MX27C4000  
MX27C4000@SOIC32 [SA603]  
MX27C4000A  
MX27C4000A@SOIC32 [SA603]  
MX27C4096  
MX27C4100  
MX27C512  
MX27C516  
MX27C516@VSOP40 [SA623-B4002]  
MX27C8000@PLCC32 [SA015A1T]  
MX27C8000@TSOP32 [SA410T-B4001]  
MX27C8000A@PLCC32 [SA015A1T]  
MX27C8000A@TSOP32 [SA410T-B4001]  
MX27C8100@PSOP44 [SA638]  
MX27C8111@PSOP44 [SA638]  
MX27L1000@PLCC32 [SA015A1T]  
MX27L2000  
MX27L2000@TSOP32 [SA410T-B4001]  
MX27L256@PLCC32 [SA015A1T]

MX27L256@TSOP32 [SA430T-B4003]      MX27L4000  
MX27L4000@PLCC32 [SA015A1T]      MX27L4000@TSOP32 [SA410T-B4001]  
MX27L4096      MX27L4096@PLCC44 [SA244]  
MX27L512      MX27L512@PLCC32 [SA015A1T]  
MX27L512@TSOP28 [SA430T-B4003]      MX28F002B@TSOP40 [SA409T-B4002]  
MX28F002T@TSOP40 [SA409T-B4002]      MX28F1000  
MX28F1000 (REVERSE)@TSOP32 [SA410T-B4001]  
MX28F1000@PLCC32 [SA015A1T]      MX28F1000@SOP32 [SA438T]  
MX28F1000@TSOP32 [SA410T-B4001]      MX28F1000P  
MX28F1000P (REVERSE)@TSOP32 [SA410T-B4001]  
MX28F1000P@PLCC32 [SA015A1T]      MX28F1000P@TSOP32 [SA410T-B4001]  
MX28F160C3BT@TSOP48 [SB247-B4806]  
MX28F160C3TT@TSOP48 [SB247-B4806]  
MX28F2000  
MX28F2000 (REVERSE)@TSOP32 [SA410T-B4001]  
MX28F2000@PLCC32 [SA015A1T]      MX28F2000@TSOP32 [SA410T-B4001]  
MX28F2000P  
MX28F2000P (REVERSE)@TSOP32 [SA410T-B4001]  
MX28F2000P@PLCC32 [SA015A1T]      MX28F2000P@TSOP32 [SA410T-B4001]  
MX28F2100B@PSOP44 [SA638]      MX28F2100B@TSOP48 [SB247-B4806]  
MX28F2100T@PSOP44 [SA638]      MX28F2100T@TSOP48 [SB247-B4806]  
MX28F4000      MX28F4000@PLCC32 [SA015A1T]  
MX28F4000@SOP32 [SA438T]      MX28F4000@TSOP32 [SA410T-B4001]  
MX28F640C3BT@TSOP48 [SB247-B4806]  
MX28F640C3TT@TSOP48 [SB247-B4806]  
MX29F001B      MX29F001B@PLCC32 [SA015A1T]  
MX29F001B@TSOP32 [SA410T-B4001]      MX29F001T  
MX29F001T@PLCC32 [SA015A1T]      MX29F001T@TSOP32 [SA410T-B4001]  
MX29F002B      MX29F002B@PLCC32 [SA015A1T]  
MX29F002B@TSOP32 [SA410T-B4001]      MX29F002NB  
MX29F002NB@PLCC32 [SA015A1T]      MX29F002NB@TSOP32 [SA410T-B4001]  
MX29F002NT      MX29F002NT@PLCC32 [SA015A1T]  
MX29F002NT@TSOP32 [SA410T-B4001]      MX29F002T  
MX29F002T@PLCC32 [SA015A1T]      MX29F002T@TSOP32 [SA410T-B4001]  
MX29F004B      MX29F004B@PLCC32 [SA015A1T]  
MX29F004B@TSOP32 [SA410T-B4001]      MX29F004T  
MX29F004T@PLCC32 [SA015A1T]      MX29F004T@TSOP32 [SA410T-B4001]  
MX29F016 (REVERSE)@TSOP40 [SA409T-B4002]  
MX29F016 (REVERSE)@TSOP48 [SB247-B4806]  
MX29F016@PSOP44 [SA638]      MX29F016@TSOP40 [SA409T-B4002]  
MX29F016@TSOP48 [SB247-B4806]      MX29F022B  
MX29F022B@PLCC32 [SA015A1T]      MX29F022B@TSOP32 [SA410T-B4001]  
MX29F022NB      MX29F022NB@PLCC32 [SA015A1T]  
MX29F022NB@TSOP32 [SA410T-B4001]      MX29F022NT  
MX29F022NT@PLCC32 [SA015A1T]      MX29F022NT@TSOP32 [SA410T-B4001]  
MX29F022T      MX29F022T@PLCC32 [SA015A1T]  
MX29F022T@TSOP32 [SA410T-B4001]      MX29F040  
MX29F040@PLCC32 [SA015A1T]      MX29F040@TSOP32 [SA410T-B4001]  
MX29F040C      MX29F040C@PLCC32 [SA015A1T]  
MX29F040C@TSOP32 [SA410T-B4001]  
MX29F080 (REVERSE)@TSOP40 [SA409T-B4002]  
MX29F080@PSOP44 [SA638]      MX29F080@TSOP40 [SA409T-B4002]  
MX29F100B@PSOP44 [SA638]      MX29F100B@TSOP48 [SB247-B4806]

MX29F100T@PSOP44 [SA638] MX29F100T@TSOP48 [SB247-B4806]  
MX29F1610@PSOP44 [SA638] MX29F1610@TSOP48 [SB247-B4806]  
MX29F1610A@PSOP44 [SA638] MX29F1610A@TSOP48 [SB247-B4806]  
MX29F1610B@TSOP48 [SB247-B4806] MX29F1611@PSOP44 [SA638]  
MX29F1615  
MX29F200B (REVERSE)@TSOP48 [SB247-B4806]  
MX29F200B@PSOP44 [SA638] MX29F200B@TSOP48 [SB247-B4806]  
MX29F200CB@PSOP44 [SA638] MX29F200CB@TSOP48 [SA247-B4806]  
MX29F200CT@PSOP44 [SA638] MX29F200CT@TSOP48 [SA247-B4806]  
MX29F200T (REVERSE)@TSOP48 [SB247-B4806]  
MX29F200T@PSOP44 [SA638] MX29F200T@TSOP48 [SB247-B4806]  
MX29F4000  
MX29F400B (REVERSE)@TSOP48 [SB247-B4806]  
MX29F400B@PSOP44 [SA638] MX29F400B@TSOP48 [SB247-B4806]  
MX29F400CB@PSOP44 [SA638] MX29F400CB@TSOP48 [SA247-B4806]  
MX29F400CT@PSOP44 [SA638] MX29F400CT@TSOP48 [SA247-B4806]  
MX29F400T (REVERSE)@TSOP48 [SB247-B4806]  
MX29F400T@PSOP44 [SA638] MX29F400T@TSOP48 [SB247-B4806]  
MX29F800B (REVERSE)@TSOP48 [SB247-B4806]  
MX29F800B@PSOP44 [SA638] MX29F800B@TSOP48 [SB247-B4806]  
MX29F800CBM@PSOP44 [SA638] MX29F800CBT@TSOP48 [SA247-B4806]  
MX29F800CTM@PSOP44 [SA638] MX29F800CTT@TSOP48 [SA247-B4806]  
MX29F800T (REVERSE)@TSOP48 [SB247-B4806]  
MX29F800T@PSOP44 [SA638] MX29F800T@TSOP48 [SB247-B4806]  
MX29F8100@PSOP44 [SA638] MX29F8100@TSOP48 [SB247-B4806]  
MX29L1611@PSOP44 [SA638] MX29L1611@TSOP48 [SB247-B4806]  
MX29L3211@PSOP44 [SA638] MX29L3211@TSOP48 [SB247-B4806]  
MX29L8100B@TSOP48 [SB247-B4806] MX29L8100G  
MX29L8100T@TSOP48 [SB247-B4806] MX29LA320MB@TSOP48 [SB247-B4806]  
MX29LA320MT@TSOP48 [SB247-B4806] MX29LV002CB@PLCC32 [SA015A1T]  
MX29LV002CB@TSOP32 [SA410T-B4001]  
MX29LV002CT@PLCC32 [SA015A1T]  
MX29LV002CT@TSOP32 [SA410T-B4001]  
MX29LV002NCB@PLCC32 [SA015A1T]  
MX29LV002NCB@TSOP32 [SA410T-B4001]  
MX29LV002NCT@PLCC32 [SA015A1T]  
MX29LV002NCT@TSOP32 [SA410T-B4001]  
MX29LV004B@PLCC32 [SA015A1T] MX29LV004B@TSOP40 [SA409T-B4002]  
MX29LV004CB@PLCC32 [SA015A1T]  
MX29LV004CB@TSOP40 [SA409T-B4002]  
MX29LV004CT@PLCC32 [SA015A1T]  
MX29LV004CT@TSOP40 [SA409T-B4002]  
MX29LV004T@PLCC32 [SA015A1T] MX29LV004T@TSOP40 [SA409T-B4002]  
MX29LV008B@TSOP40 [SA409T-B4002]  
MX29LV008BB@TSOP40 [SA409T-B4002]  
MX29LV008BT@TSOP40 [SA409T-B4002]  
MX29LV008CB@TSOP40 [SA409T-B4002]  
MX29LV008CT@TSOP40 [SA409T-B4002]  
MX29LV008T@TSOP40 [SA409T-B4002]  
MX29LV017AT@TSOP40 [SA409T-B4002]  
MX29LV017BT@TSOP40 [SA409T-B4002]  
MX29LV033AT@TSOP40 [SA409T-B4002]  
MX29LV033M@TSOP40 [SA409T-B4002] MX29LV033T@TSOP40 [SA409T-B4002]

MX29LV040@PLCC32 [SA015A1T]  
MX29LV040C@PLCC32 [SA015A1T]  
MX29LV065BT@TSOP48 [SB247-B4806]  
MX29LV081@TSOP40 [SA409T-B4002]  
MX29LV128DT@TSOP48 [SB247-B4806]  
MX29LV160AB(0.4)@CSP48 [\$\$\$\$\$\$]  
MX29LV160AB@TSOP48 [SB247-B4806]  
MX29LV160AT(0.4)@CSP48 [\$\$\$\$\$\$]  
MX29LV160AT@TSOP48 [SB247-B4806]  
MX29LV160B(0.4)@CSP48 [\$\$\$\$\$\$]  
MX29LV160B@TSOP48 [SB247-B4806]  
MX29LV160BB(0.4)@CSP48 [\$\$\$\$\$\$]  
MX29LV160BB@TSOP48 [SB247-B4806]  
MX29LV160BT(0.4)@CSP48 [\$\$\$\$\$\$]  
MX29LV160BT@TSOP48 [SB247-B4806]  
MX29LV160CBT@TSOP48 [SB247-B4806]  
MX29LV160CBXB(0.3)@CSP48 [\$\$\$\$\$\$]  
MX29LV160CBXE(0.4)@CSP48 [\$\$\$\$\$\$]  
MX29LV160CTM@PSOP44 [SA638]  
MX29LV160CTT@TSOP48 [SB247-B4806]  
MX29LV160CTXB(0.3)@CSP48 [\$\$\$\$\$\$]  
MX29LV160CTXE(0.4)@CSP48 [\$\$\$\$\$\$]  
MX29LV160DBT@TSOP48 [SB247-B4806]  
MX29LV160DTT@TSOP48 [SB247-B4806]  
MX29LV160T(0.3)@CSP48 [\$\$\$\$\$\$]  
MX29LV160T@PSOP44 [SA638]  
MX29LV161DBT@TSOP48 [SB247-B4806]  
MX29LV161DTT@TSOP48 [SB247-B4806]  
MX29LV320ABT@TSOP48 [SB247-B4806]  
MX29LV320ABXB@CSP48 [\$\$\$\$\$\$]  
MX29LV320ATT@TSOP48 [SB247-B4806]  
MX29LV320ATXB@CSP48 [\$\$\$\$\$\$]  
MX29LV320BT@TSOP48 [SB247-B4806]  
MX29LV320BXE@CSP48 [\$\$\$\$\$\$]  
MX29LV320CBT@TSOP48 [SB247-B4806]  
MX29LV320CBXB@CSP48 [\$\$\$\$\$\$]  
MX29LV320CTT@TSOP48 [SB247-B4806]  
MX29LV320CTXB@CSP48 [\$\$\$\$\$\$]  
MX29LV320DBT@TSOP48 [SB247-B4806]  
MX29LV320DTT@TSOP48 [SB247-B4806]  
MX29LV320EBT@TSOP48 [SB247-B4806]  
MX29LV320ETT@TSOP48 [SB247-B4806]  
MX29LV320MB@PSOP44 [SA638]  
MX29LV320MT@PSOP44 [SA638]  
MX29LV320TT@TSOP48 [SB247-B4806]  
MX29LV320TXE@CSP48 [\$\$\$\$\$\$]  
MX29LV321DBT@TSOP48 [SB247-B4806]  
MX29LV321DBXB@CSP48 [\$\$\$\$\$\$]  
MX29LV321DTT@TSOP48 [SB247-B4806]  
MX29LV400B@PSOP44 [SA638]  
MX29LV400BX(0.3)@CSP48 [\$\$\$\$\$\$]  
MX29LV400CBM@PSOP44 [SA638]  
MX29LV400CBT@TSOP48 [SB247-B4806]

MX29LV040@TSOP32 [SA410T-B4001]  
MX29LV040C@TSOP32 [SA410T-B4001]  
MX29LV065M@TSOP48 [SB247-B4806]  
MX29LV128DB@TSOP48 [SB247-B4806]  
MX29LV160AB(0.3)@CSP48 [\$\$\$\$\$\$]  
MX29LV160AB@PSOP44 [SA638]  
MX29LV160AT(0.3)@CSP48 [\$\$\$\$\$\$]  
MX29LV160AT@PSOP44 [SA638]  
MX29LV160B(0.3)@CSP48 [\$\$\$\$\$\$]  
MX29LV160B@PSOP44 [SA638]  
MX29LV160BB(0.3)@CSP48 [\$\$\$\$\$\$]  
MX29LV160BB@PSOP44 [SA638]  
MX29LV160BT(0.3)@CSP48 [\$\$\$\$\$\$]  
MX29LV160BT@PSOP44 [SA638]  
MX29LV160CBM@PSOP44 [SA638]

MX29LV160T(0.4)@CSP48 [\$\$\$\$\$\$]  
MX29LV160T@TSOP48 [SB247-B4806]

MX29LV320ABXE@CSP48 [\$\$\$\$\$\$]

MX29LV320ATXE@CSP48 [\$\$\$\$\$\$]  
MX29LV320BXB@CSP48 [\$\$\$\$\$\$]

MX29LV320CBXE@CSP48 [\$\$\$\$\$\$]

MX29LV320CTXE@CSP48 [\$\$\$\$\$\$]

MX29LV320MB@TSOP48 [SB247-B4806]  
MX29LV320MT@TSOP48 [SB247-B4806]  
MX29LV320TXB@CSP48 [\$\$\$\$\$\$]

MX29LV400B@TSOP48 [SB247-B4806]  
MX29LV400BX(0.4)@CSP48 [\$\$\$\$\$\$]

MX29LV400CBXB (0. 3)@CSP48 [\$\$\$\$\$]  
MX29LV400CBXE (0. 4)@CSP48 [\$\$\$\$\$]  
MX29LV400CTM@PSOP44 [SA638]  
MX29LV400CTT@TSOP48 [SB247-B4806]  
MX29LV400CTXB (0. 3)@CSP48 [\$\$\$\$\$]  
MX29LV400CTXE (0. 4)@CSP48 [\$\$\$\$\$]  
MX29LV400T@PSOP44 [SA638]  
MX29LV400TX (0. 3)@CSP48 [\$\$\$\$\$]  
MX29LV640BBT@TSOP48 [SB247-B4806]  
MX29LV640BT@TSOP48 [SB247-B4806]  
MX29LV640BTT@TSOP48 [SB247-B4806]  
MX29LV640BUT@TSOP48 [SB247-B4806]  
MX29LV640DBM@PSOP44 [SA638]  
MX29LV640DBT@TSOP48 [SB247-B4806]  
MX29LV640DTM@PSOP44 [SA638]  
MX29LV640DTT@TSOP48 [SB247-B4806]  
MX29LV640EBT@TSOP48 [SB247-B4806]  
MX29LV640ETT@TSOP48 [SB247-B4806]  
MX29LV640MB@TSOP48 [SB247-B4806]  
MX29LV640TT@TSOP48 [SB247-B4806]  
MX29LV641MH@TSOP48 [SB247-B4806]  
MX29LV800AB (0. 3)@CSP48 [\$\$\$\$\$]  
MX29LV800AB@PSOP44 [SA638]  
MX29LV800AT (0. 3)@CSP48 [\$\$\$\$\$]  
MX29LV800AT@PSOP44 [SA638]  
MX29LV800B (0. 3)@CSP48 [\$\$\$\$\$]  
MX29LV800B@PSOP44 [SA638]  
MX29LV800CBM@PSOP44 [SA638]  
MX29LV800CBT@TSOP48 [SB247-B4806]  
MX29LV800CBXB (0. 3)@CSP48 [\$\$\$\$\$]  
MX29LV800CBXE (0. 4)@CSP48 [\$\$\$\$\$]  
MX29LV800CTM@PSOP44 [SA638]  
MX29LV800CTT@TSOP48 [SB247-B4806]  
MX29LV800CTXB (0. 3)@CSP48 [\$\$\$\$\$]  
MX29LV800CTXE (0. 4)@CSP48 [\$\$\$\$\$]  
MX29LV800T (0. 3)@CSP48 [\$\$\$\$\$]  
MX29LV800T@PSOP44 [SA638]  
MX29LW160BT@TSOP48 [SB247-B4806]  
MX29LW161BT@TSOP48 [SB247-B4806]  
MX29LW320BT@TSOP48 [SB247-B4806]  
MX29LW321BT@TSOP48 [SB247-B4806]  
MX29SL402CBT@TSOP48 [SB247-B4806]  
MX29SL402CTT@TSOP48 [SB247-B4806]  
MX29SL800CB@TSOP48 [SB247-B4806]  
MX29SL800CBXB (0. 30)@CSP48 [\$\$\$\$\$]  
MX29SL800CBXE (0. 40)@CSP48 [\$\$\$\$\$]  
MX29SL800CBXH (0. 30)@CSP48 [\$\$\$\$\$]  
MX29SL800CT@TSOP48 [SB247-B4806]  
MX29SL800CTXB (0. 30)@CSP48 [\$\$\$\$\$]  
MX29SL800CTXE (0. 40)@CSP48 [\$\$\$\$\$]  
MX29SL800CTXH (0. 30)@CSP48 [\$\$\$\$\$]  
MX29SL802CBT@TSOP48 [SB247-B4806]  
MX29SL802CTT@TSOP48 [SB247-B4806]

MX29LV400T@TSOP48 [SB247-B4806]  
MX29LV400TX (0. 4)@CSP48 [\$\$\$\$\$]

MX29LV640MT@TSOP48 [SB247-B4806]  
MX29LV640UT@TSOP48 [SB247-B4806]  
MX29LV641ML@TSOP48 [SB247-B4806]  
MX29LV800AB (0. 4)@CSP48 [\$\$\$\$\$]  
MX29LV800AB@TSOP48 [SB247-B4806]  
MX29LV800AT (0. 4)@CSP48 [\$\$\$\$\$]  
MX29LV800AT@TSOP48 [SB247-B4806]  
MX29LV800B (0. 4)@CSP48 [\$\$\$\$\$]  
MX29LV800B@TSOP48 [SB247-B4806]

MX29LV800T (0. 4)@CSP48 [\$\$\$\$\$]  
MX29LV800T@TSOP48 [SB247-B4806]  
MX29LW160TT@TSOP48 [SB247-B4806]  
MX29LW161TT@TSOP48 [SB247-B4806]  
MX29LW320TT@TSOP48 [SB247-B4806]  
MX29LW321TT@TSOP48 [SB247-B4806]

## MICROCONTROLLER

MX10E8050I  
MX10E8050I@TQFP44 [SA245A-B4805]  
MX10EXAU@TQFP44 [SA245A-B4805]  
MX10FMAXD  
MX10FMAXD@TQFP44 [SA675-B4805]

MX10E8050I@PLCC44 [SA244]  
MX10EXAQ@PLCC44 [SA244]  
MX10FLCD  
MX10FMAXD@PLCC44 [SA244]

## MAGNACHIP

### MICROCONTROLLER

GMS34004TK  
GMS34004TW  
GMS34112TK@SOIC20 [SA404]  
GMS34140TK  
GMS81504AT [SA653]  
GMS81604T  
GMS81604T@SDIP42 [SA028]  
GMS81608T@PLCC44 [SA244]  
GMS87C1102  
GMS87C1202  
GMS87C1404  
GMS87C1408  
GMS97C1051  
GMS97C2051  
GMS97C51  
GMS97C51@TQFP44 [SA675-B4805]  
GMS97C51H@PLCC44 [SA244]  
GMS97C52  
GMS97C52@TQFP44 [SA675-B4805]  
GMS97C52H@PLCC44 [SA244]  
GMS97C54  
GMS97C54@TQFP44 [SA675-B4805]  
GMS97C54H@PLCC44 [SA244]  
GMS97C56  
GMS97C56@TQFP44 [SA675-B4805]  
GMS97C56H@PLCC44 [SA244]  
GMS97C58  
GMS97C58@TQFP44 [SA675-B4805]  
GMS97C58H@PLCC44 [SA244]  
GMS97L1051  
GMS97L2051  
GMS97L51  
GMS97L51@TQFP44 [SA675-B4805]  
GMS97L52@PLCC44 [SA244]  
GMS97L54  
GMS97L54@TQFP44 [SA675-B4805]  
GMS97L56@PLCC44 [SA244]  
GMS97L58  
GMS97L58@TQFP44 [SA675-B4805]

GMS34004TM  
GMS34112TK  
GMS34112TK@SSOP20 [SA626A]  
GMS34140TK@SOIC24 [SA404]  
GMS81504T [SA653]  
GMS81604T@PLCC44 [SA244]  
GMS81608T  
GMS81608T@SDIP42 [SA028]  
GMS87C1102@SOP16 [SA404]  
GMS87C1202@SOP20 [SA404]  
GMS87C1404@SOP28 [SA404]  
GMS87C1408@SOP28 [SA404]  
GMS97C1051@SOIC20 [SA404]  
GMS97C2051@SOIC20 [SA404]  
GMS97C51@PLCC44 [SA244]  
GMS97C51H  
GMS97C51H@TQFP44 [SA675-B4805]  
GMS97C52@PLCC44 [SA244]  
GMS97C52H  
GMS97C52H@TQFP44 [SA675-B4805]  
GMS97C54@PLCC44 [SA244]  
GMS97C54H  
GMS97C54H@TQFP44 [SA675-B4805]  
GMS97C56@PLCC44 [SA244]  
GMS97C56H  
GMS97C56H@TQFP44 [SA675-B4805]  
GMS97C58@PLCC44 [SA244]  
GMS97C58H  
GMS97C58H@TQFP44 [SA675-B4805]  
GMS97L1051@SOIC20 [SA404]  
GMS97L2051@SOIC20 [SA404]  
GMS97L51@PLCC44 [SA244]  
GMS97L52  
GMS97L52@TQFP44 [SA675-B4805]  
GMS97L54@PLCC44 [SA244]  
GMS97L56  
GMS97L56@TQFP44 [SA675-B4805]  
GMS97L58@PLCC44 [SA244]  
HMS87C1404B

HMS87C1404B@SDIP28 [SA653]  
HMS87C1408B  
HMS87C1408B@SOIC28 [SA404]  
HMS87C1416B@SDIP28 [SA653]  
HMS87C1508B  
HMS87C1608B  
HMS87C1708B@SDIP42 [SA028]  
HMS87C1808B@TQFP44 [SA675-B4805]  
HMS87C5216  
HMS87C5216@SOIC28 [SA404]  
MC80F0504  
MC80F0504@SSOP16 [SA626A]  
MC80F0604  
MC80F0604@SSOP20 [SA626A]  
MC80F0704@QFN28  
MC80F0708  
MC80F0708@SOP28 [SA783]  
MC80F0804@SOP32 [SA715]  
MC80F0808@SOP32 [SA715]

HMS87C1404B@SOIC28 [SA404]  
HMS87C1408B@SDIP28 [SA653]  
HMS87C1416B  
HMS87C1416B@SOIC28 [SA404]  
HMS87C1516B  
HMS87C1616B  
HMS87C1716B@SDIP42 [SA028]  
HMS87C1816B@TQFP44 [SA675-B4805]  
HMS87C5216@PLCC44 [SA244]  
HMS87C5216@TQFP44 [SA675-B4805]  
MC80F0504@SOP16 [SA783]  
MC80F0504[153mil]@SOP16 [SA602]  
MC80F0604@SOP20 [SA783]  
MC80F0704  
MC80F0704@SOP28 [SA783]  
MC80F0708@QFN28  
MC80F0804@SDIP32 [SA653]  
MC80F0808@SDIP32 [SA653]

## MAXCOM

### E (E) PROM/FRAM/NVRAM

MAX24A02  
MAX24A02@TSSOP8 [SA643]  
MAX24A04@SOP8 [SA602A]  
MAX24A08  
MAX24A08@TSSOP8 [SA643]  
MAX24A16@SOP8 [SA602A]

MAX24A02@SOP8 [SA602A]  
MAX24A04  
MAX24A04@TSSOP8 [SA643]  
MAX24A08@SOP8 [SA602A]  
MAX24A16  
MAX24A16@TSSOP8 [SA643]

## MAXIM

### E (E) PROM/FRAM/NVRAM

DS1220AB  
DS1220Y  
DS1225AD  
DS1225E  
DS1230AB  
DS1230Y  
DS1235Y  
DS1244  
DS1245AB  
DS1245W  
DS1248W  
DS1249AB  
DS1249Y  
DS1250W  
DS1251AB  
DS1251Y  
DS1256Y

DS1220AD  
DS1225AB  
DS1225D  
DS1225Y  
DS1230W  
DS1235AB  
DS1243Y  
DS1244Y  
DS1245EE  
DS1245Y  
DS1248Y  
DS1249W  
DS1250AB  
DS1250Y  
DS1251W  
DS1256W  
DS1258AB

DS1258W	DS1258Y
DS1265AB	DS1265W
DS1265Y	DS1270AB
DS1270W	DS1270Y
DS1284	DS1284N
DS1284Q@PLCC28 [SA008A]	DS1284QN@PLCC28 [SA008A]
DS1286	DS1286I
DS1287	DS1287A
DS12887	DS12887A
DS12C887	DS12C887A
DS1386 (32K)	DS1386 (8K)
DS1485	DS1485@SOIC28 [SA630]
DS1488	DS1501
DS1511	DS1553
DS1553W	DS1554
DS1554W	DS1556
DS1642	DS1643
DS1644	DS1645AB
DS1645EE	DS1645Y
DS1646	DS1647
DS1650AB	DS1650Y
DS1685-3	DS1685-3@SOP24 [SA404]
DS1685-5	DS1685-5@SOP24 [SA404]
DS1687-3	DS1687-5
DS17287-3	DS17287-5
DS1742	DS1742W
DS1743	DS1743W
DS1744	DS1744W
DS1746	DS1747
DS1747W	DS17487-3
DS17487-5	DS17887-3
DS17887-5	DS2430A@TO-92
DS2430AP@TSOC6 [\$\$\$\$\$]	DS2431@TDFN6 [\$\$\$\$\$]
DS2431@TO-92	DS2431P@TSOC6 [\$\$\$\$\$]
DS2432P@TSOC6 [\$\$\$\$\$]	DS2433@PR-35
DS2433S (3. 9)@SOIC8 [SA602A]	DS2433S (5. 5)@SOIC8 [SA605B]
DS2502	DS2502P@TSOC6 [\$\$\$\$\$]
DS2502S@SOIC8 [SA602A]	DS2502UNW
DS2502UNW@SOIC8 [SA602A]	DS2502UNW@SOT-23 [SA717]
DS2502UNW@TSOC6 [\$\$\$\$\$]	DS2505
DS2505S@TSOC6 [\$\$\$\$\$]	DS2506
DS2506S@SOIC8 [SA602A]	DS4510@uSOP10 [SA602]
DS4520@TSSOP16 [SA026]	DS4550@TSSOP20 [SA026]

## MICROCONTROLLER

DS2760@TSSOP16 [\$\$\$\$\$]	DS5000 [ 8K]
DS5000 [32K]	DS5000T [ 8K]
DS5000T [32K]	DS87C520
DS87C520@PLCC44 [SA244]	DS87C520@TQFP44 [SA245A-B4805]
DS89C420 (rev. A)	DS89C420 (rev. A)@PLCC44 [SA244]
DS89C420 (rev. A)@TQFP44 [SA245A-B4805]	

## MAXWELL

### E (E) PROM/FRAM/NVRAM

28C010	28C010@PLCC32 [SA015A1T]
28C010@TSOP32 [SA410T-B4001]	28C010T
28C010T@PLCC32 [SA015A1T]	28C010T@TSOP32 [SA410T-B4001]
28C011	28C011@PLCC32 [SA015A1T]
28C011@TSOP32 [SA410T-B4001]	28C011T
28C011T@PLCC32 [SA015A1T]	28C011T@TSOP32 [SA410T-B4001]

## MEGAWIN

### E (E) PROM/FRAM/NVRAM

MM25SB512@SOIC8 [SA602A]	MM29F040
MM29F040@PLCC32 [SA015A1T]	MM29F040@TSOP32 [SA410T-B4001]
MM29LF040	MM29LF040@PLCC32 [SA015A1T]
MM29LF040@TSOP32 [SA410T-B4001]	

### MICROCONTROLLER

MA805-24A	MA805-24A@QFP44 [SA245A-B4805]
MA805-24A@QFP48 [SA248-B4804]	MA805-32A
MA805-32A@QFP44 [SA245A-B4805]	MA805-32A@QFP48 [SA248-B4804]
MA805-64A	MA805-64A@QFP44 [SA245A-B4805]
MA805-64A@QFP48 [SA248-B4804]	MA806-24A
MA806-24A@QFP44 [SA245A-B4805]	MA806-24A@QFP48 [SA248-B4804]
MA806-32A	MA806-32A@QFP44 [SA245A-B4805]
MA806-32A@QFP48 [SA248-B4804]	MA806-64A
MA806-64A@QFP44 [SA245A-B4805]	MA806-64A@QFP48 [SA248-B4804]
MA807A@QFP44 [SA245A-B4805]	MA808A@QFP44 [SA245A-B4805]
MA816A@QFP44 [SA245A-B4805]	MG82FE532AD@QFP48 [SA248-B4804]
MG82FE532AE	MG82FE532AF@QFP44 [SA675-B4805]
MG82FE532AP@PLCC44 [SA244]	MG82FE564AD@QFP48 [SA248-B4804]
MG82FE564AE	MG82FE564AF@QFP44 [SA675-B4805]
MG82FE564AP@PLCC44 [SA244]	MG82FG5A32AD@QFP48 [SA248-B4804]
MG82FG5A64AD@QFP48 [SA248-B4804]	MG82FL532AD@QFP48 [SA248-B4804]
MG82FL532AE	MG82FL532AF@QFP44 [SA675-B4805]
MG82FL532AP@PLCC44 [SA244]	MG82FL564AD@QFP48 [SA248-B4804]
MG82FL564AE	MG82FL564AF@QFP44 [SA675-B4805]
MG82FL564AP@PLCC44 [SA244]	MG84FG516AD@QFP48 [SA248-B4804]
MG86FE104AS@SOP16 [SA602]	MG86FE104AS@SOP20 [SA404]
MG86FE104AS@SOP8 [SA602]	MG86FE508AS@SOP20 [SA404]
MG86FE508AS@SOP28 [SA404]	MG86FL104AS@SOP16 [SA602]
MG86FL104AS@SOP20 [SA404]	MG86FL104AS@SOP8 [SA602]
MG86FL508AS@SOP20 [SA404]	MG86FL508AS@SOP28 [SA404]
MG87FE2051AE@DIP18	MG87FE2051AE@DIP18
MG87FE2051AE@DIP20	MG87FE2051AS@SOP16 [SA404]
MG87FE2051AS@SOP18 [SA404]	MG87FE2051AS@SOP20 [SA404]

MG87FE4051AE@DIP16  
MG87FE4051AE@DIP20  
MG87FE4051AS@SOP18 [SA404]  
MG87FE51AE  
MG87FE51AP@PLCC44 [SA244]  
MG87FE52AF@TQFP44 [SA675-B4805]  
MG87FE6051AE@DIP16  
MG87FE6051AE@DIP20  
MG87FE6051AS@SOP18 [SA404]  
MG87FL2051AE@DIP16  
MG87FL2051AE@DIP20  
MG87FL2051AS@SOP18 [SA404]  
MG87FL4051AE@DIP16  
MG87FL4051AE@DIP20  
MG87FL4051AS@SOP18 [SA404]  
MG87FL51AE  
MG87FL51AP@PLCC44 [SA244]  
MG87FL52AF@TQFP44 [SA675-B4805]  
MG87FL6051AE@DIP16  
MG87FL6051AE@DIP20  
MG87FL6051AS@SOP18 [SA404]  
MPC82E52AE  
MPC82E52AT@SSOP20 [SA643]  
MPC82E54AE2  
MPC82E54AS@SOP20 [SA404]  
MPC82E54AT@SSOP20 [SA643]  
MPC82G516AD@LQFP48 [SA248-B4804]  
MPC82G516AF@PQFP44 [SA675-B4805]  
MPC82L52AE  
MPC82L52AT@SSOP20 [SA643]  
MPC82L54AE2  
MPC82L54AS@SOP20 [SA404]  
MPC82L54AT@SSOP20 [SA643]  
MPC89E515AE  
MPC89E515AP@PLCC44 [SA244]  
MPC89E51AF@PQFP44 [SA675-B4805]  
MPC89E52AE  
MPC89E52AP@PLCC44 [SA244]  
MPC89E53AF@PQFP44 [SA675-B4805]  
MPC89E54AE  
MPC89E54AP@PLCC44 [SA244]  
MPC89E58AF@PQFP44 [SA675-B4805]  
MPC89L515AE  
MPC89L515AP@PLCC44 [SA244]  
MPC89L516X2@PLCC44 [SA244]  
MPC89L516X2@TQFP44 [SA245A-B4805]  
MPC89L51AE  
MPC89L51AP@PLCC44 [SA244]  
MPC89L52AF@PQFP44 [SA675-B4805]  
MPC89L53AE  
MPC89L53AP@PLCC44 [SA244]  
MPC89L54AF@PQFP44 [SA675-B4805]  
MPC89L556X2

MG87FE4051AE@DIP18  
MG87FE4051AS@SOP16 [SA404]  
MG87FE4051AS@SOP20 [SA404]  
MG87FE51AF@TQFP44 [SA675-B4805]  
MG87FE52AE  
MG87FE52AP@PLCC44 [SA244]  
MG87FE6051AE@DIP18  
MG87FE6051AS@SOP16 [SA404]  
MG87FE6051AS@SOP20 [SA404]  
MG87FL2051AE@DIP18  
MG87FL2051AS@SOP16 [SA404]  
MG87FL2051AS@SOP20 [SA404]  
MG87FL4051AE@DIP18  
MG87FL4051AS@SOP16 [SA404]  
MG87FL4051AS@SOP20 [SA404]  
MG87FL51AF@TQFP44 [SA675-B4805]  
MG87FL52AE  
MG87FL52AP@PLCC44 [SA244]  
MG87FL6051AE@DIP18  
MG87FL6051AS@SOP16 [SA404]  
MG87FL6051AS@SOP20 [SA404]  
MPC82E52AS@SOP20 [SA404]  
MPC82E54AE  
MPC82E54AP@PLCC32 [SA015A1T]  
MPC82E54AS2@SOP28 [SA404]  
MPC82E54AT2@SSOP28 [SA643]  
MPC82G516AE  
MPC82G516AP@PLCC44 [SA244]  
MPC82L52AS@SOP20 [SA404]  
MPC82L54AE  
MPC82L54AP@PLCC32 [SA015A1T]  
MPC82L54AS2@SOP28 [SA404]  
MPC82L54AT2@SSOP28 [SA643]  
MPC89E515AF@PQFP44 [SA675-B4805]  
MPC89E51AE  
MPC89E51AP@PLCC44 [SA244]  
MPC89E52AF@PQFP44 [SA675-B4805]  
MPC89E53AE  
MPC89E53AP@PLCC44 [SA244]  
MPC89E54AF@PQFP44 [SA675-B4805]  
MPC89E58AE  
MPC89E58AP@PLCC44 [SA244]  
MPC89L515AF@PQFP44 [SA675-B4805]  
MPC89L516X2  
MPC89L51AF@PQFP44 [SA675-B4805]  
MPC89L52AE  
MPC89L52AP@PLCC44 [SA244]  
MPC89L53AF@PQFP44 [SA675-B4805]  
MPC89L54AE  
MPC89L54AP@PLCC44 [SA244]  
MPC89L556X2@PLCC44 [SA244]

MPC89L556X2@TQFP44 [SA245A-B4805]  
MPC89L58AE  
MPC89L58AP@PLCC44 [SA244]

MPC89L58AF@PQFP44 [SA675-B4805]

## MICON

### MICROCONTROLLER

MDT10P21(dip18)	MDT10P21(dip20)
MDT10P21(dip22)	MDT10P21@SOP18 [SA404]
MDT10P21@SOP20 [SA404]	MDT10P21@SOP24 [SA404]
MDT10P22(dip18)	MDT10P22(dip20)
MDT10P22(dip22)	MDT10P22@SOP18 [SA404]
MDT10P22@SOP20 [SA404]	MDT10P22@SOP24 [SA404]
MDT10P23(dip18)	MDT10P23(dip20)
MDT10P23(dip22)	MDT10P23@SOP18 [SA404]
MDT10P23@SOP20 [SA404]	MDT10P23@SOP24 [SA404]
MDT10P41A1	MDT10P41A1@SOP16 [SA404]
MDT10P41A2	MDT10P41A2@SOP16 [SA404]
MDT10P43P11	MDT10P43P21
MDT10P43S11@SOP18 [SA404]	MDT10P43S21@SOP20 [SA404]
MDT10P55A1	MDT10P55A1@SOP14 [SA602]
MDT10P55A2	MDT10P55A2@SOP14 [SA602]
MDT10P55A3	MDT10P55A3@SOP14 [SA602]
MDT10P55A4	MDT10P55A4@SOP14 [SA602]
MDT10P55B1	MDT10P55B1@SOP14 [SA602]
MDT10P55B2	MDT10P55B2@SOP14 [SA602]
MDT10P55B3	MDT10P55B3@SOP14 [SA602]
MDT10P55B4	MDT10P55B4@SOP14 [SA602]
MDT10P61	MDT10P61@SOP18 [SA404]
MDT10P61@SSOP20 [SA626A]	MDT10P62
MDT10P62@SOP28 [SA404]	MDT10P62@SSOP28 [SA626A]
MDT10P621	MDT10P621@SOP28 [SA404]
MDT10P621@SSOP28 [SA626A]	MDT10P64
MDT10P64@PLCC44 [SA244]	MDT10P64@QFP44 [SA675-B4805]
MDT10P65(dip28)	MDT10P65(dip42)
MDT10P65@SDIP42 [SA028]	MDT10P65@SOP28 [SA404]
MDT10P651	MDT10P651@PLCC44 [SA244]
MDT10P651@QFP44 [SA675-B4805]	MDT10P65A1@QFP44 [SA675-B4805]
MDT10P65A2@QFP44 [SA675-B4805]	MDT10P72
MDT10P72@SOP28 [SA404]	MDT10P72@SSOP28 [SA626A]
MDT10P721	MDT10P721@SOP28 [SA404]
MDT10P721@SSOP28 [SA626A]	MDT10P73
MDT10P73@SOP28 [SA404]	MDT10P73@SSOP28 [SA626A]
MDT10P74	MDT10P74@PLCC44 [SA244]
MDT10P74@QFP44 [SA675-B4805]	MDT2005
MDT2005@SOP18 [SA404]	MDT2005@SSOP20 [SA626A]
MDT2010	MDT2010@SOP18 [SA404]
MDT2010@SSOP20 [SA626A]	MDT2020
MDT2020@SOP28 [SA404]	MDT2020@SSOP28 [SA626A]
MDT2030	MDT2030@SOP18 [SA404]
MDT2030@SSOP20 [SA626A]	MDT2050

MDT2050@SOP18 [SA404]  
MDT2051  
MDT2051@SSOP20 [SA626A]  
MDT2060@SOP18 [SA404]

MDT2050@SSOP20 [SA626A]  
MDT2051@SOP18 [SA404]  
MDT2060  
MDT2060@SSOP20 [SA626A]

## MICROCHIP

### E (E) PROM/FRAM/NVRAM

23A256  
23A256@TSSOP8 [SA643]  
23A640@SOIC8 [SA602A]  
23K256  
23K256@TSSOP8 [SA643]  
23K640@SOIC8 [SA602A]  
24AA00  
24AA00@SOIC8 [SA602A]  
24AA00@TSSOP8 [SA643]  
24AA01@DFN8 [SA724]  
24AA01@TSSOP8 [SA643]  
24AA014@SOIC8 [SA602A]  
24AA02  
24AA02@MSOP8 [SA666]  
24AA02@SOT-23-5 [SA717]  
24AA024  
24AA024@MSOP8 [SA666]  
24AA024@TSSOP8 [SA643]  
24AA025@DFN8 [SA724]  
24AA025@SOIC8 [SA602A]  
24AA04  
24AA04@SOIC8 [SA602A]  
24AA08  
24AA08@SOIC8 [SA602A]  
24AA1025  
24AA1025@TSSOP8 [SA643]  
24AA1026@SOIC8 [SA605B]  
24AA128  
24AA128@MSOP8 [SA666]  
24AA128@TSSOP14 [SA026]  
24AA16  
24AA16@SOIC8 [SA602A]  
24AA164  
24AA164@TSSOP8 [SA643]  
24AA174@SOIC8 [SA602A]  
24AA256  
24AA256@MSOP8 [SA666]  
24AA256@TSSOP14 [SA026]  
24AA32  
24AA32@DFN8 [SA724]  
24AA32@SOIC8 [SA602A]  
24AA32A  
24AA32A@DFN8 [SA724]

23A256@SOIC8 [SA602A]  
23A640  
23A640@TSSOP8 [SA643]  
23K256@SOIC8 [SA602A]  
23K640  
23K640@TSSOP8 [SA643]  
24AA00@DFN8 [SA724]  
24AA00@SOT-23 [SA717]  
24AA01  
24AA01@SOIC8 [SA602A]  
24AA014  
24AA014@TSSOP8 [SA643]  
24AA02@DFN8 [SA724]  
24AA02@SOIC8 [SA602A]  
24AA02@TSSOP8 [SA643]  
24AA024@DFN8 [SA724]  
24AA024@SOIC8 [SA602A]  
24AA025  
24AA025@MSOP8 [SA666]  
24AA025@TSSOP8 [SA643]  
24AA04@DFN8 [SA724]  
24AA04@TSSOP8 [SA643]  
24AA08@DFN8 [SA724]  
24AA08@TSSOP8 [SA643]  
24AA1025@SOIC8 [SA605B]  
24AA1026  
24AA1026@TSSOP8 [SA605B]  
24AA128@DFN8 [SA724]  
24AA128@SOIC8 [SA602A]  
24AA128@TSSOP8 [SA643]  
24AA16@DFN8 [SA724]  
24AA16@TSSOP8 [SA643]  
24AA164@SOIC8 [SA602A]  
24AA174  
24AA174@TSSOP8 [SA643]  
24AA256@DFN8 [SA724]  
24AA256@SOIC8 [SA602A]  
24AA256@TSSOP8 [SA643]  
24AA32 (Rotated)@TSSOP8 [SA643]  
24AA32@MSOP8 [SA666]  
24AA32@TSSOP8 [SA643]  
24AA32A (Rotated)@TSSOP8 [SA643]  
24AA32A@MSOP8 [SA666]

24AA32A@S0IC8 [SA602A]  
24AA32A@TSSOP8 [SA643]  
24AA32AF (Rotated)@TSSOP8 [SA643]  
24AA32AF@MSOP8 [SA666]  
24AA32AF@TSSOP8 [SA643]  
24AA512@DFN8 [SA683]  
24AA512@TSSOP14 [SA602]  
24AA515@S0IC8 [SA605B]  
24AA52@DFN8 [SA724]  
24AA52@S0IC8 [SA602A]  
24AA64  
24AA64@DFN8 [SA724]  
24AA64@S0IC8 [SA602A]  
24AA64F  
24AA64F@DFN8 [SA724]  
24AA64F@S0IC8 [SA602A]  
24AA65  
24AA65@S0IC8 [SA602A]  
24C00  
24C00@S0IC8 [SA602A]  
24C00@TSSOP8 [SA643]  
24C01A  
24C01C  
24C01C@TSSOP8 [SA643]  
24C02A  
24C02C  
24C02C@TSSOP8 [SA643]  
24C04A  
24C04A@TSSOP8 [SA643]  
24C08@S0IC8 [SA602A]  
24C08B@S0IC8 [SA602A]  
24C16@S0IC8 [SA602A]  
24C16B@S0IC8 [SA602A]  
24C32@DFN8 [SA724]  
24C64  
24C64@S0IC8 [SA602A]  
24C65  
24C65@S0IC8 [SA602A]  
24FC1025@S0IC8 [SA605B]  
24FC1026  
24FC1026@TSSOP8 [SA605B]  
24FC128@DFN8 [SA724]  
24FC128@S0IC8 [SA602A]  
24FC128@TSSOP8 [SA643]  
24FC256@DFN8 [SA724]  
24FC256@S0IC8 [SA602A]  
24FC256@TSSOP8 [SA643]  
24FC32@DFN8 [SA724]  
24FC512  
24FC512@S0IC8 [SA605B]  
24FC515  
24FC64  
24FC64@DFN8 [SA724]  
24AA32A@SOT-23 [SA717]  
24AA32AF  
24AA32AF@DFN8 [SA724]  
24AA32AF@S0IC8 [SA602A]  
24AA512  
24AA512@S0IC8 [SA605B]  
24AA515  
24AA52  
24AA52@MSOP8 [SA666]  
24AA52@TSSOP8 [SA643]  
24AA64 (Rotated)@TSSOP8 [SA643]  
24AA64@MSOP8 [SA666]  
24AA64@TSSOP8 [SA643]  
24AA64F (Rotated)@TSSOP8 [SA643]  
24AA64F@MSOP8 [SA666]  
24AA64F@TSSOP8 [SA643]  
24AA65@DFN8 [SA724]  
24AA65@TSSOP8 [SA643]  
24C00@DFN8 [SA724]  
24C00@SOT-23 [SA717]  
24C01  
24C01A@S0IC8 [SA602A]  
24C01C@S0IC8 [SA602A]  
24C02  
24C02A@S0IC8 [SA602A]  
24C02C@S0IC8 [SA602A]  
24C04  
24C04A@S0IC8 [SA602A]  
24C08  
24C08B  
24C16  
24C16B  
24C32  
24C32@S0IC8 [SA602A]  
24C64@DFN8 [SA724]  
24C64@TSSOP8 [SA643]  
24C65@DFN8 [SA724]  
24FC1025  
24FC1025@TSSOP8 [SA643]  
24FC1026@S0IC8 [SA605B]  
24FC128  
24FC128@MSOP8 [SA666]  
24FC128@TSSOP14 [SA026]  
24FC256  
24FC256@MSOP8 [SA666]  
24FC256@TSSOP14 [SA026]  
24FC32  
24FC32@S0IC8 [SA602A]  
24FC512@DFN8 [SA683]  
24FC512@TSSOP14 [SA602]  
24FC515@S0IC8 [SA605B]  
24FC64 (Rotated)@TSSOP8 [SA643]  
24FC64@MSOP8 [SA666]

24FC64@SOIC8 [SA602A]  
24FC65  
24FC65@SOIC8 [SA602A]  
24LC00@DFN8 [SA724]  
24LC00@SOT-23 [SA717]  
24LC01  
24LC014@SOIC8 [SA602A]  
24LC01B  
24LC01B@SOIC8 [SA602A]  
24LC02  
24LC024@SOIC8 [SA602A]  
24LC025  
24LC025@TSSOP8 [SA643]  
24LC02B@DFN8 [SA724]  
24LC02B@SOIC8 [SA602A]  
24LC02B@TSSOP8 [SA643]  
24LC04B  
24LC04B@SOIC8 [SA602A]  
24LC08  
24LC08B@DFN8 [SA724]  
24LC08B@TSSOP8 [SA643]  
24LC1025@SOIC8 [SA605B]  
24LC1026  
24LC1026@TSSOP8 [SA605B]  
24LC128@DFN8 [SA724]  
24LC128@SOIC8 [SA602A]  
24LC128@TSSOP8 [SA643]  
24LC16@MSOP8 [SA666]  
24LC164  
24LC16B  
24LC16B@SOIC8 [SA602A]  
24LC174  
24LC21  
24LC21A  
24LC22A  
24LC256  
24LC256@MSOP8 [SA666]  
24LC256@SOIC8(200mil) [SA605B]  
24LC256@TSSOP8 [SA643]  
24LC32@SOIC8 [SA602A]  
24LC32A@DFN8 [SA724]  
24LC32A@SOT-23 [SA717]  
24LC32AF  
24LC32AF@SOIC8 [SA602A]  
24LC512  
24LC512@SOIC8(150 mil) [SA602A]  
24LC512@TSSOP14 [SA602]  
24LC515@SOIC8 [SA605B]  
24LC64(Rotated)@TSSOP8 [SA643]  
24LC64@DFN8 [SA724]  
24LC64@SOIC8 [SA602A]  
24LC64F  
24LC64F@DFN8 [SA724]  
24FC64@TSSOP8 [SA643]  
24FC65@DFN8 [SA724]  
24LC00  
24LC00@SOIC8 [SA602A]  
24LC00@TSSOP8 [SA643]  
24LC014  
24LC014@TSSOP8 [SA643]  
24LC01B@DFN8 [SA724]  
24LC01B@TSSOP8 [SA643]  
24LC024  
24LC024@TSSOP8 [SA643]  
24LC025@SOIC8 [SA602A]  
24LC02B  
24LC02B@MSOP8 [SA666]  
24LC02B@SOT-23-5 [SA717]  
24LC04  
24LC04B@DFN8 [SA724]  
24LC04B@TSSOP8 [SA643]  
24LC08B  
24LC08B@SOIC8 [SA602A]  
24LC1025  
24LC1025@TSSOP8 [SA643]  
24LC1026@SOIC8 [SA605B]  
24LC128  
24LC128@MSOP8 [SA666]  
24LC128@TSSOP14 [SA026]  
24LC16  
24LC16@SOIC8 [SA602A]  
24LC164@SOIC8 [SA602A]  
24LC16B@DFN8 [SA724]  
24LC16B@TSSOP8 [SA643]  
24LC174@SOIC8 [SA602A]  
24LC21@SOIC8 [SA602A]  
24LC21A@SOIC8 [SA602A]  
24LC22A@SOIC8 [SA602A]  
24LC256@DFN8 [SA724]  
24LC256@SOIC8(150mil) [SA602A]  
24LC256@TSSOP14 [SA026]  
24LC32  
24LC32A  
24LC32A@SOIC8 [SA602A]  
24LC32A@TSSOP8 [SA643]  
24LC32AF@DFN8 [SA724]  
24LC32AF@TSSOP8 [SA643]  
24LC512@DFN8 [SA683]  
24LC512@SOIC8(200 mil) [SA605B]  
24LC515  
24LC64  
24LC64(SM)@SOIC8 [SA605B]  
24LC64@MSOP8 [SA666]  
24LC64@TSSOP8 [SA643]  
24LC64F(Rotated)@TSSOP8 [SA643]  
24LC64F@MSOP8 [SA666]

24LC64F@SOIC8 [SA602A]  
24LC65  
24LC65@SOIC8 [SA602A]  
24LCS21@SOIC8 [SA602A]  
24LCS21A@SOIC8 [SA602A]  
24LCS22@SOIC8 [SA602A]  
24LCS22A@SOIC8 [SA602A]  
24LCS52@DFN8 [SA724]  
24LCS52@SOIC8 [SA602A]  
24LCS61  
24LCS62  
24VL014  
24VL014@SOIC8 [SA602A]  
24VL014@TDFN8 [SA724]  
24VL024  
24VL024@SOIC8 [SA602A]  
24VL024@TSSOP8 [SA643]  
24VL025@MSOP8 [SA666]  
24VL025@SOT-23 [SA717]  
24VL025@TSSOP8 [SA643]  
25A512@TSSOP8 [SA643]  
25AA010A@DFN8 [SA683]  
25AA010A@SOIC8 [SA602A]  
25AA010A@TSSOP8 [SA643]  
25AA010A[X-Rotated]@TSSOP8 [SA643]  
25AA020A  
25AA020A@MSOP8 [SA605B]  
25AA020A@SOT-23 [SA717]  
25AA020A[X-Rotated]@TSSOP8 [SA643]  
25AA040  
25AA040@TSSOP8 [SA643]  
25AA040A@DFN8 [SA683]  
25AA040A@SOIC8 [SA602A]  
25AA040A@TSSOP8 [SA643]  
25AA040A[X-Rotated]@TSSOP8 [SA643]  
25AA080  
25AA080A  
25AA080A@SOIC8 [SA602A]  
25AA080B  
25AA080B@SOIC8 [SA602A]  
25AA080C  
25AA080C@SOIC8 [SA602A]  
25AA080D  
25AA080D@SOIC8 [SA602A]  
25AA1024  
25AA1024@SOIC8 [SA602A]  
25AA128  
25AA128@SOIC8 (4.0) [SA602A]  
25AA128@TSSOP8 [SA643]  
25AA128[X-Rotated]@TSSOP8 [SA643]  
25AA160  
25AA160A  
25AA160A@SOIC8 [SA602A]  
24LC64F@TSSOP8 [SA643]  
24LC65@DFN8 [SA724]  
24LCS21  
24LCS21A  
24LCS22  
24LCS22A  
24LCS52  
24LCS52@MSOP8 [SA666]  
24LCS52@TSSOP8 [SA643]  
24LCS61@SOIC8 [SA602A]  
24LCS62@SOIC8 [SA602A]  
24VL014@MSOP8 [SA666]  
24VL014@SOT-23 [SA717]  
24VL014@TSSOP8 [SA643]  
24VL024@MSOP8 [SA666]  
24VL024@TDFN8 [SA724]  
24VL025  
24VL025@SOIC8 [SA602A]  
24VL025@TDFN8 [SA724]  
25A512@SOIC8 [SA602A]  
25AA010A  
25AA010A@MSOP8 [SA605B]  
25AA010A@SOT-23 [SA717]  
25AA020A@DFN8 [SA683]  
25AA020A@SOIC8 [SA602A]  
25AA020A@TSSOP8 [SA643]  
25AA040@SOIC8 [SA602A]  
25AA040A  
25AA040A@MSOP8 [SA605B]  
25AA040A@SOT-23 [SA717]  
25AA080@SOIC8 [SA602A]  
25AA080A@MSOP8 [SA605B]  
25AA080A@TSSOP8 [SA643]  
25AA080B@MSOP8 [SA605B]  
25AA080B@TSSOP8 [SA643]  
25AA080C@MSOP8 [SA605B]  
25AA080C@TSSOP8 [SA643]  
25AA080D@MSOP8 [SA605B]  
25AA080D@TSSOP8 [SA643]  
25AA1024@DFN8 [SA683]  
25AA1024@SOIJ8 [SA605B]  
25AA128@DFN8 [SA683]  
25AA128@SOIC8 (5.4) [SA605B]  
25AA160@SOIC8 [SA602A]  
25AA160A@MSOP8 [SA605B]  
25AA160A@TSSOP8 [SA643]

25AA160B  
25AA160B@SOIC8 [SA602A]  
25AA160C  
25AA160C@SOIC8 [SA602A]  
25AA160C@TSSOP8 [SA643]  
25AA160D@MSOP8 [SA605B]  
25AA160D@TDFN8 [SA724]  
25AA256  
25AA256@SOIC8(4.0) [SA602A]  
25AA256@TSSOP8 [SA643]  
25AA256[X-Rotated]@TSSOP8 [SA643]  
25AA320  
25AA320@TSSOP14 [SA026]  
25AA320A  
25AA320A@MSOP8 [SA605B]  
25AA320A@TDFN8 [SA724]  
25AA320A@XTSSOP8 [SA643]  
25AA512@DFN8 [SA683]  
25AA512@SOIJ8 [SA605B]  
25AA640@SOIC8 [SA602A]  
25AA640A  
25AA640A@MSOP8 [SA605B]  
25AA640A@TDFN8 [SA724]  
25AA640A@XTSSOP8 [SA643]  
25C040@SOIC8 [SA602A]  
25C080  
25C160  
25C320  
25C320@TSSOP14 [SA026]  
25C640  
25C640@TSSOP8 [SA643]  
25LC010A@DFN8 [SA683]  
25LC010A@SOIC8 [SA602A]  
25LC010A@TSSOP8 [SA643]  
25LC010A[X-Rotated]@TSSOP8 [SA643]  
25LC020A  
25LC020A@MSOP8 [SA605B]  
25LC020A@SOT-23 [SA717]  
25LC020A[X-Rotated]@TSSOP8 [SA643]  
25LC040  
25LC040@TSSOP8  
25LC040A@DFN8 [SA683]  
25LC040A@SOIC8 [SA602A]  
25LC040A@TSSOP8 [SA643]  
25LC040A[X-Rotated]@TSSOP8 [SA643]  
25LC080  
25LC080A  
25LC080A@SOIC8 [SA602A]  
25LC080B  
25LC080B@SOIC8 [SA602A]  
25LC080C  
25LC080C@SOIC8 [SA602A]  
25LC080D  
25AA160B@MSOP8 [SA605B]  
25AA160B@TSSOP8 [SA643]  
25AA160C@MSOP8 [SA605B]  
25AA160C@TDFN8 [SA724]  
25AA160D  
25AA160D@SOIC8 [SA602A]  
25AA160D@TSSOP8 [SA643]  
25AA256@DFN8 [SA683]  
25AA256@SOIC8(5.4) [SA605B]  
25AA320@SOIC8 [SA602A]  
25AA320@TSSOP8 [SA643]  
25AA320A@DFN8 [SA683]  
25AA320A@SOIC8 [SA602A]  
25AA320A@TSSOP8 [SA643]  
25AA512  
25AA512@SOIC8 [SA602A]  
25AA640  
25AA640@TSSOP8 [SA643]  
25AA640A@DFN8 [SA683]  
25AA640A@SOIC8 [SA602A]  
25AA640A@TSSOP8 [SA643]  
25C040  
25C040@TSSOP8 [SA643]  
25C080@SOIC8 [SA602A]  
25C160@SOIC8 [SA602A]  
25C320@SOIC8 [SA602A]  
25C320@TSSOP8 [SA643]  
25C640@SOIC8 [SA602A]  
25LC010A  
25LC010A@MSOP8 [SA605B]  
25LC010A@SOT-23 [SA717]  
25LC020A@DFN8 [SA683]  
25LC020A@SOIC8 [SA602A]  
25LC020A@TSSOP8 [SA643]  
25LC040@SOIC8 [SA602A]  
25LC040A  
25LC040A@MSOP8 [SA605B]  
25LC040A@SOT-23 [SA717]  
25LC080@SOIC8 [SA602A]  
25LC080A@MSOP8 [SA605B]  
25LC080A@TSSOP8 [SA643]  
25LC080B@MSOP8 [SA605B]  
25LC080B@TSSOP8 [SA643]  
25LC080C@MSOP8 [SA605B]  
25LC080C@TSSOP8 [SA643]  
25LC080D@MSOP8 [SA605B]

25LC080D@SOIC8 [SA602A]  
25LC1024  
25LC1024@SOIC8 [SA602A]  
25LC128  
25LC128@SOIC8(4.0) [SA602A]  
25LC128@TSSOP8 [SA643]  
25LC128[X-Rotated]@TSSOP8 [SA643]  
25LC160  
25LC160A  
25LC160A@SOIC8 [SA602A]  
25LC160B  
25LC160B@SOIC8 [SA602A]  
25LC160C  
25LC160C@SOIC8 [SA602A]  
25LC160C@TSSOP8 [SA643]  
25LC160D@MSOP8 [SA605B]  
25LC160D@TDFN8 [SA724]  
25LC256  
25LC256@SOIC8(4.0) [SA602A]  
25LC256@TSSOP8 [SA643]  
25LC256[X-Rotated]@TSSOP8 [SA643]  
25LC320  
25LC320@TSSOP14 [SA026]  
25LC320A  
25LC320A@MSOP8 [SA605B]  
25LC320A@TDFN8 [SA724]  
25LC320A@XTSSOP8 [SA643]  
25LC512@DFN8 [SA683]  
25LC512@SOIJ8 [SA605B]  
25LC640@SOIC8 [SA602A]  
25LC640A  
25LC640A@MSOP8 [SA605B]  
25LC640A@TDFN8 [SA724]  
25LC640A@XTSSOP8 [SA643]  
27256@PLCC32 [SA015A1T]  
27C128@PLCC32 [SA015A1T]  
27C128A@PLCC32 [SA015A1T]  
27C256@PLCC32 [SA015A1T]  
27C512  
27C512A  
27C513  
27C64@PLCC32 [SA015A1T]  
27HC1616  
27HC1616L  
27HC191  
27HC191@SOIC24 [SA404]  
27HC256@PLCC32 [SA015A1T]  
27HC256L@PLCC32 [SA015A1T]  
27HC291@PLCC28 [SA008A]  
27HC416  
27HC64  
27HC64@SOIC28 [SA404]  
27HC641@PLCC28 [SA008A]

25LC080D@TSSOP8 [SA643]  
25LC1024@DFN8 [SA683]  
25LC1024@SOIJ8 [SA605B]  
25LC128@DFN8 [SA683]  
25LC128@SOIC8(5.4) [SA605B]  
25LC160@SOIC8 [SA602A]  
25LC160A@MSOP8 [SA605B]  
25LC160A@TSSOP8 [SA643]  
25LC160B@MSOP8 [SA605B]  
25LC160B@TSSOP8 [SA643]  
25LC160C@MSOP8 [SA605B]  
25LC160C@TDFN8 [SA724]  
25LC160D  
25LC160D@SOIC8 [SA602A]  
25LC160D@TSSOP8 [SA643]  
25LC256@DFN8 [SA683]  
25LC256@SOIC8(5.4) [SA605B]  
25LC320(SN)@SOIC8 [SA602A]  
25LC320@TSSOP8 [SA643]  
25LC320A@DFN8 [SA683]  
25LC320A@SOIC8 [SA602A]  
25LC320A@TSSOP8 [SA643]  
25LC512  
25LC512@SOIC8 [SA602A]  
25LC640  
25LC640@TSSOP8 [SA643]  
25LC640A@DFN8 [SA683]  
25LC640A@SOIC8 [SA602A]  
25LC640A@TSSOP8 [SA643]  
27256  
27C128  
27C128A  
27C256  
27C32A  
27C512@PLCC32 [SA015A1T]  
27C512A@PLCC32 [SA015A1T]  
27C64  
27C64@SOIC28 [SA404]  
27HC1616@PLCC44 [SA244]  
27HC1616L@PLCC44 [SA244]  
27HC191@PLCC28 [SA008A]  
27HC256  
27HC256L  
27HC291  
27HC291@SOIC24 [SA404]  
27HC416@PLCC44 [SA244]  
27HC64@PLCC32 [SA015A1T]  
27HC641  
27HC641@SOIC24 [SA404]

27HC641L  
27HC641L@SOIC24 [SA404]  
27HC64L@PLCC32 [SA015A1T]  
27LV256  
27LV64  
2864  
28C04  
28C04@SOIC24 [SA404]  
28C04A@PLCC32 [SA015A1T]  
28C04AF  
28C04AF@SOIC24 [SA404]  
28C04F@PLCC32 [SA015A1T]  
28C16  
28C16@SOIC24 [SA404]  
28C16A@PLCC32 [SA015A1T]  
28C16AF  
28C16AF@SOIC24 [SA404]  
28C16F@PLCC32 [SA015A1T]  
28C17  
28C17@SOIC28 [SA404]  
28C17A@PLCC32 [SA015A1T]  
28C17AF  
28C17AF@SOIC28 [SA404]  
28C17F@PLCC32 [SA015A1T]  
28C256  
28C256F  
28C64A  
28C64A@SOIC28 [SA404]  
28C64AF  
28C64AF@SOIC28 [SA404]  
28LV64A@PLCC32 [SA015A1T]  
28PC64  
59C11  
85C72  
85C82  
85C92  
93AA46 (08bit)  
93AA46 (16bit)  
93AA46A (08bit)  
93AA46A (08bit)@MSOP8 [SA666]  
93AA46A (08bit)@SOT-23 [SA717]  
93AA46B (16bit)  
93AA46B (16bit)@MSOP8 [SA666]  
93AA46B (16bit)@SOT-23 [SA717]  
93AA46C (08bit)  
93AA46C (08bit)@MSOP8 [SA666]  
93AA46C (08bit)@TSSOP8 [SA643]  
93AA46C (16bit)@DFN8  
93AA46C (16bit)@SOIC8 [SA602A]  
93AA56 (08bit)  
93AA56 (16bit)  
93AA56A (08bit)  
93AA56A (08bit)@MSOP8 [SA666]

27HC641L@PLCC28 [SA008A]  
27HC64L  
27HC64L@SOIC28 [SA404]  
27LV256@PLCC32 [SA015A1T]  
2817  
2864@PLCC32 [SA015A1T]  
28C04@PLCC32 [SA015A1T]  
28C04A  
28C04A@SOIC24 [SA404]  
28C04AF@PLCC32 [SA015A1T]  
28C04F  
28C04F@SOIC24 [SA404]  
28C16@PLCC32 [SA015A1T]  
28C16A  
28C16A@SOIC24 [SA404]  
28C16AF@PLCC32 [SA015A1T]  
28C16F  
28C16F@SOIC24 [SA404]  
28C17@PLCC32 [SA015A1T]  
28C17A  
28C17A@SOIC28 [SA404]  
28C17AF@PLCC32 [SA015A1T]  
28C17F  
28C17F@SOIC28 [SA404]  
28C256@PLCC32 [SA015A1T]  
28C256F@PLCC32 [SA015A1T]  
28C64A@PLCC32 [SA015A1T]  
28C64A@TSOP32 [SA410T-B4001]  
28C64AF@PLCC32 [SA015A1T]  
28LV64A  
28LV64A@SOIC28 [SA404]  
28PC64@PLCC32 [SA015A1T]  
59C11@SOIC8 [SA602A]  
85C72@SOIC8 [SA602A]  
85C82@SOIC8 [SA602A]  
85C92@SOIC8 [SA602A]  
93AA46 (08bit)@SOIC8 [SA602A]  
93AA46 (16bit)@SOIC8 [SA602A]  
93AA46A (08bit)@DFN8  
93AA46A (08bit)@SOIC8 [SA602A]  
93AA46A (08bit)@TSSOP8 [SA643]  
93AA46B (16bit)@DFN8  
93AA46B (16bit)@SOIC8 [SA602A]  
93AA46B (16bit)@TSSOP8 [SA643]  
93AA46C (08bit)@DFN8  
93AA46C (08bit)@SOIC8 [SA602A]  
93AA46C (16bit)  
93AA46C (16bit)@MSOP8 [SA666]  
93AA46C (16bit)@TSSOP8 [SA643]  
93AA56 (08bit)@SOIC8 [SA602A]  
93AA56 (16bit)@SOIC8 [SA602A]  
93AA56A (08bit)@DFN8  
93AA56A (08bit)@SOIC8 [SA602A]

93AA56A(08bit)@SOT-23 [SA717]  
93AA56B(16bit)  
93AA56B(16bit)@MSOP8 [SA666]  
93AA56B(16bit)@SOT-23 [SA717]  
93AA56C(08bit)  
93AA56C(08bit)@MSOP8 [SA666]  
93AA56C(08bit)@TSSOP8 [SA643]  
93AA56C(16bit)@DFN8  
93AA56C(16bit)@SOIC8 [SA602A]  
93AA66(08bit)  
93AA66(16bit)  
93AA66A(08bit)  
93AA66A(08bit)@MSOP8 [SA666]  
93AA66A(08bit)@SOT-23 [SA717]  
93AA66B(16bit)  
93AA66B(16bit)@MSOP8 [SA666]  
93AA66B(16bit)@SOT-23 [SA717]  
93AA66C(08bit)  
93AA66C(08bit)@MSOP8 [SA666]  
93AA66C(08bit)@TSSOP8 [SA643]  
93AA66C(16bit)@DFN8  
93AA66C(16bit)@SOIC8 [SA602A]  
93AA76(08bit)  
93AA76(16bit)  
93AA76A(08bit)  
93AA76A(08bit)@MSOP8 [SA666]  
93AA76A(08bit)@SOT-23 [SA717]  
93AA76B(16bit)  
93AA76B(16bit)@MSOP8 [SA666]  
93AA76B(16bit)@SOT-23 [SA717]  
93AA76C(08bit)  
93AA76C(08bit)@MSOP8 [SA666]  
93AA76C(08bit)@TSSOP8 [SA643]  
93AA76C(16bit)@DFN8  
93AA76C(16bit)@SOIC8 [SA602A]  
93AA86(08bit)  
93AA86(16bit)  
93AA86A(08bit)  
93AA86A(08bit)@MSOP8 [SA666]  
93AA86A(08bit)@SOT-23 [SA717]  
93AA86B(16bit)  
93AA86B(16bit)@MSOP8 [SA666]  
93AA86B(16bit)@SOT-23 [SA717]  
93AA86C(08bit)  
93AA86C(08bit)@MSOP8 [SA666]  
93AA86C(08bit)@TSSOP8 [SA643]  
93AA86C(16bit)@DFN8  
93AA86C(16bit)@SOIC8 [SA602A]  
93C06(08bit)  
93C06(16bit)  
93C46(08bit)  
93C46(16bit)  
93C46A(08bit)

93AA56A(08bit)@TSSOP8 [SA643]  
93AA56B(16bit)@DFN8  
93AA56B(16bit)@SOIC8 [SA602A]  
93AA56B(16bit)@TSSOP8 [SA643]  
93AA56C(08bit)@DFN8  
93AA56C(08bit)@SOIC8 [SA602A]  
93AA56C(16bit)  
93AA56C(16bit)@MSOP8 [SA666]  
93AA56C(16bit)@TSSOP8 [SA643]  
93AA66(08bit)@SOIC8 [SA602A]  
93AA66(16bit)@SOIC8 [SA602A]  
93AA66A(08bit)@DFN8  
93AA66A(08bit)@SOIC8 [SA602A]  
93AA66A(08bit)@TSSOP8 [SA643]  
93AA66B(16bit)@DFN8  
93AA66B(16bit)@SOIC8 [SA602A]  
93AA66B(16bit)@TSSOP8 [SA643]  
93AA66C(08bit)@DFN8  
93AA66C(08bit)@SOIC8 [SA602A]  
93AA66C(16bit)  
93AA66C(16bit)@MSOP8 [SA666]  
93AA66C(16bit)@TSSOP8 [SA643]  
93AA76(08bit)@SOIC8 [SA602A]  
93AA76(16bit)@SOIC8 [SA602A]  
93AA76A(08bit)@DFN8  
93AA76A(08bit)@SOIC8 [SA602A]  
93AA76A(08bit)@TSSOP8 [SA643]  
93AA76B(16bit)@DFN8  
93AA76B(16bit)@SOIC8 [SA602A]  
93AA76B(16bit)@TSSOP8 [SA643]  
93AA76C(08bit)@DFN8  
93AA76C(08bit)@SOIC8 [SA602A]  
93AA76C(16bit)  
93AA76C(16bit)@MSOP8 [SA666]  
93AA76C(16bit)@TSSOP8 [SA643]  
93AA86(08bit)@SOIC8 [SA602A]  
93AA86(16bit)@SOIC8 [SA602A]  
93AA86A(08bit)@DFN8  
93AA86A(08bit)@SOIC8 [SA602A]  
93AA86A(08bit)@TSSOP8 [SA643]  
93AA86B(16bit)@DFN8  
93AA86B(16bit)@SOIC8 [SA602A]  
93AA86B(16bit)@TSSOP8 [SA643]  
93AA86C(08bit)@DFN8  
93AA86C(08bit)@SOIC8 [SA602A]  
93AA86C(16bit)  
93AA86C(16bit)@MSOP8 [SA666]  
93AA86C(16bit)@TSSOP8 [SA643]  
93C06(08bit)@SOIC8 [SA602A]  
93C06(16bit)@SOIC8 [SA602A]  
93C46(08bit)@SOIC8 [SA602A]  
93C46(16bit)@SOIC8 [SA602A]  
93C46A(08bit)@DFN8

93C46A (08bit)@MSOP8 [SA666]  
93C46A (08bit)@SOT-23 [SA717]  
93C46B (16bit)  
93C46B (16bit)@MSOP8 [SA666]  
93C46B (16bit)@SOT-23 [SA717]  
93C46C (08bit)  
93C46C (08bit)@MSOP8 [SA666]  
93C46C (08bit)@TSSOP8 [SA643]  
93C46C (16bit)@DFN8  
93C46C (16bit)@SOIC8 [SA602A]  
93C56 (08bit)  
93C56 (16bit)  
93C56A (08bit)  
93C56A (08bit)@MSOP8 [SA666]  
93C56A (08bit)@SOT-23 [SA717]  
93C56B (16bit)  
93C56B (16bit)@MSOP8 [SA666]  
93C56B (16bit)@SOT-23 [SA717]  
93C56C (08bit)  
93C56C (08bit)@MSOP8 [SA666]  
93C56C (08bit)@TSSOP8 [SA643]  
93C56C (16bit)@DFN8  
93C56C (16bit)@SOIC8 [SA602A]  
93C66 (08bit)  
93C66 (16bit)  
93C66A (08bit)  
93C66A (08bit)@MSOP8 [SA666]  
93C66A (08bit)@SOT-23 [SA717]  
93C66B (16bit)  
93C66B (16bit)@MSOP8 [SA666]  
93C66B (16bit)@SOT-23 [SA717]  
93C66C (08bit)  
93C66C (08bit)@MSOP8 [SA666]  
93C66C (08bit)@TSSOP8 [SA643]  
93C66C (16bit)@DFN8  
93C66C (16bit)@SOIC8 [SA602A]  
93C76 (08bit)  
93C76 (16bit)  
93C76A (08bit)  
93C76A (08bit)@MSOP8 [SA666]  
93C76A (08bit)@SOT-23 [SA717]  
93C76B (16bit)  
93C76B (16bit)@MSOP8 [SA666]  
93C76B (16bit)@SOT-23 [SA717]  
93C76C (08bit)  
93C76C (08bit)@MSOP8 [SA666]  
93C76C (08bit)@TSSOP8 [SA643]  
93C76C (16bit)@DFN8  
93C76C (16bit)@SOIC8 [SA602A]  
93C86 (08bit)  
93C86 (16bit)  
93C86A (08bit)  
93C86A (08bit)@MSOP8 [SA666]

93C46A (08bit)@SOIC8 [SA602A]  
93C46A (08bit)@TSSOP8 [SA643]  
93C46B (16bit)@DFN8  
93C46B (16bit)@SOIC8 [SA602A]  
93C46B (16bit)@TSSOP8 [SA643]  
93C46C (08bit)@DFN8  
93C46C (08bit)@SOIC8 [SA602A]  
93C46C (16bit)  
93C46C (16bit)@MSOP8 [SA666]  
93C46C (16bit)@TSSOP8 [SA643]  
93C56 (08bit)@SOIC8 [SA602A]  
93C56 (16bit)@SOIC8 [SA602A]  
93C56A (08bit)@DFN8  
93C56A (08bit)@SOIC8 [SA602A]  
93C56A (08bit)@TSSOP8 [SA643]  
93C56B (16bit)@DFN8  
93C56B (16bit)@SOIC8 [SA602A]  
93C56B (16bit)@TSSOP8 [SA643]  
93C56C (08bit)@DFN8  
93C56C (08bit)@SOIC8 [SA602A]  
93C56C (16bit)  
93C56C (16bit)@MSOP8 [SA666]  
93C56C (16bit)@TSSOP8 [SA643]  
93C66 (08bit)@SOIC8 [SA602A]  
93C66 (16bit)@SOIC8 [SA602A]  
93C66A (08bit)@DFN8  
93C66A (08bit)@SOIC8 [SA602A]  
93C66A (08bit)@TSSOP8 [SA643]  
93C66B (16bit)@DFN8  
93C66B (16bit)@SOIC8 [SA602A]  
93C66B (16bit)@TSSOP8 [SA643]  
93C66C (08bit)@DFN8  
93C66C (08bit)@SOIC8 [SA602A]  
93C66C (16bit)  
93C66C (16bit)@MSOP8 [SA666]  
93C66C (16bit)@TSSOP8 [SA643]  
93C76 (08bit)@SOIC8 [SA602A]  
93C76 (16bit)@SOIC8 [SA602A]  
93C76A (08bit)@DFN8  
93C76A (08bit)@SOIC8 [SA602A]  
93C76A (08bit)@TSSOP8 [SA643]  
93C76B (16bit)@DFN8  
93C76B (16bit)@SOIC8 [SA602A]  
93C76B (16bit)@TSSOP8 [SA643]  
93C76C (08bit)@DFN8  
93C76C (08bit)@SOIC8 [SA602A]  
93C76C (16bit)  
93C76C (16bit)@MSOP8 [SA666]  
93C76C (16bit)@TSSOP8 [SA643]  
93C86 (08bit)@SOIC8 [SA602A]  
93C86 (16bit)@SOIC8 [SA602A]  
93C86A (08bit)@DFN8  
93C86A (08bit)@SOIC8 [SA602A]

93C86A(08bit)@SOT-23 [SA717]  
93C86B(16bit)  
93C86B(16bit)@MSOP8 [SA666]  
93C86B(16bit)@SOT-23 [SA717]  
93C86C(08bit)  
93C86C(08bit)@MSOP8 [SA666]  
93C86C(08bit)@TSSOP8 [SA643]  
93C86C(16bit)@DFN8  
93C86C(16bit)@SOIC8 [SA602A]  
93LC46(08bit)  
93LC46(16bit)  
93LC46A(08bit)  
93LC46A(08bit)@MSOP8 [SA666]  
93LC46A(08bit)@SOT-23 [SA717]  
93LC46A-R(08bit)@SOIC8 [SA602A]  
93LC46B(16bit)  
93LC46B(16bit)@MSOP8 [SA666]  
93LC46B(16bit)@SOT-23 [SA717]  
93LC46BX  
93LC46C(08bit)  
93LC46C(08bit)@MSOP8 [SA666]  
93LC46C(08bit)@TSSOP8 [SA643]  
93LC46C(16bit)@DFN8  
93LC46C(16bit)@SOIC8 [SA602A]  
93LC56(08bit)  
93LC56(16bit)  
93LC56A(08bit)  
93LC56A(08bit)@MSOP8 [SA666]  
93LC56A(08bit)@SOT-23 [SA717]  
93LC56B(16bit)  
93LC56B(16bit)@MSOP8 [SA666]  
93LC56B(16bit)@SOT-23 [SA717]  
93LC56BX  
93LC56C(08bit)  
93LC56C(08bit)@MSOP8 [SA666]  
93LC56C(08bit)@TSSOP8 [SA643]  
93LC56C(16bit)@DFN8  
93LC56C(16bit)@SOIC8 [SA602A]  
93LC66(08bit)  
93LC66(16bit)  
93LC66A(08bit)  
93LC66A(08bit)@MSOP8 [SA666]  
93LC66A(08bit)@SOT-23 [SA717]  
93LC66B(16bit)  
93LC66B(16bit)@MSOP8 [SA666]  
93LC66B(16bit)@SOT-23 [SA717]  
93LC66BX  
93LC66C(08bit)  
93LC66C(08bit)@MSOP8 [SA666]  
93LC66C(08bit)@TSSOP8 [SA643]  
93LC66C(16bit)@DFN8  
93LC66C(16bit)@SOIC8 [SA602A]  
93LC76(08bit)

93C86A(08bit)@TSSOP8 [SA643]  
93C86B(16bit)@DFN8  
93C86B(16bit)@SOIC8 [SA602A]  
93C86B(16bit)@TSSOP8 [SA643]  
93C86C(08bit)@DFN8  
93C86C(08bit)@SOIC8 [SA602A]  
93C86C(16bit)  
93C86C(16bit)@MSOP8 [SA666]  
93C86C(16bit)@TSSOP8 [SA643]  
93LC46(08bit)@SOIC8 [SA602A]  
93LC46(16bit)@SOIC8 [SA602A]  
93LC46A(08bit)@DFN8  
93LC46A(08bit)@SOIC8 [SA602A]  
93LC46A(08bit)@TSSOP8 [SA643]  
93LC46A-R(16bit)@SOIC8 [SA602A]  
93LC46B(16bit)@DFN8  
93LC46B(16bit)@SOIC8 [SA602A]  
93LC46B(16bit)@TSSOP8 [SA643]  
93LC46BX@SOIC8 [SA602A]  
93LC46C(08bit)@DFN8  
93LC46C(08bit)@SOIC8 [SA602A]  
93LC46C(16bit)  
93LC46C(16bit)@MSOP8 [SA666]  
93LC46C(16bit)@TSSOP8 [SA643]  
93LC56(08bit)@SOIC8 [SA602A]  
93LC56(16bit)@SOIC8 [SA602A]  
93LC56A(08bit)@DFN8  
93LC56A(08bit)@SOIC8 [SA602A]  
93LC56A(08bit)@TSSOP8 [SA643]  
93LC56B(16bit)@DFN8  
93LC56B(16bit)@SOIC8 [SA602A]  
93LC56B(16bit)@TSSOP8 [SA643]  
93LC56BX@SOIC8 [SA602A]  
93LC56C(08bit)@DFN8  
93LC56C(08bit)@SOIC8 [SA602A]  
93LC56C(16bit)  
93LC56C(16bit)@MSOP8 [SA666]  
93LC56C(16bit)@TSSOP8 [SA643]  
93LC66(08bit)@SOIC8 [SA602A]  
93LC66(16bit)@SOIC8 [SA602A]  
93LC66A(08bit)@DFN8  
93LC66A(08bit)@SOIC8 [SA602A]  
93LC66A(08bit)@TSSOP8 [SA643]  
93LC66B(16bit)@DFN8  
93LC66B(16bit)@SOIC8 [SA602A]  
93LC66B(16bit)@TSSOP8 [SA643]  
93LC66BX@SOIC8 [SA602A]  
93LC66C(08bit)@DFN8  
93LC66C(08bit)@SOIC8 [SA602A]  
93LC66C(16bit)  
93LC66C(16bit)@MSOP8 [SA666]  
93LC66C(16bit)@TSSOP8 [SA643]  
93LC76(08bit)@SOIC8 [SA602A]

93LC76(16bit)  
93LC76A(08bit)  
93LC76A(08bit)@MSOP8 [SA666]  
93LC76A(08bit)@SOT-23 [SA717]  
93LC76B(16bit)  
93LC76B(16bit)@MSOP8 [SA666]  
93LC76B(16bit)@SOT-23 [SA717]  
93LC76C(08bit)  
93LC76C(08bit)@MSOP8 [SA666]  
93LC76C(08bit)@TSSOP8 [SA643]  
93LC76C(16bit)@DFN8  
93LC76C(16bit)@SOIC8 [SA602A]  
93LC86(08bit)  
93LC86(16bit)  
93LC86A(08bit)  
93LC86A(08bit)@MSOP8 [SA666]  
93LC86A(08bit)@SOT-23 [SA717]  
93LC86B(16bit)  
93LC86B(16bit)@MSOP8 [SA666]  
93LC86B(16bit)@SOT-23 [SA717]  
93LC86C(08bit)  
93LC86C(08bit)@MSOP8 [SA666]  
93LC86C(08bit)@TSSOP8 [SA643]  
93LC86C(16bit)@DFN8  
93LC86C(16bit)@SOIC8 [SA602A]  
93LCS46  
93LCS46@SOIC8 [SA602A]  
93LCS56@SOIC14 [SA026]  
93LCS66  
93LCS66@SOIC8 [SA602A]  
ER5911@SOIC8 [SA602A]  
HCS101SN@SOIC8 [SA602A]  
HCS200SN@SOIC8 [SA602A]  
HCS201@SOIC8 [SA602A]  
HCS300SN@SOIC8 [SA602A]  
HCS301SN@SOIC8 [SA602A]  
HCS320SN@SOIC8 [SA602A]  
HCS360SN@SOIC8 [SA602A]  
HCS361SN@SOIC8 [SA602A]  
HCS362@SOIC8 [SA602A]  
HCS410  
HCS410@TSSOP8 [SA643]  
HCS412@SOIC8 [SA602A]  
HCS512@SOIC18 [SA602]  
MCP79510@TDFN10 [SA695A]  
MCP79511@TDFN10 [SA695A]  
MCP79512@TDFN10 [SA695A]  
MCP79520@TDFN10 [SA695A]  
MCP79521@TDFN10 [SA695A]  
MCP79522@TDFN10 [SA695A]  
MCP795B10@TSSOP14 [SA026]  
MCP795B11@TSSOP14 [SA026]  
MCP795B12@TSSOP14 [SA026]

93LC76(16bit)@SOIC8 [SA602A]  
93LC76A(08bit)@DFN8  
93LC76A(08bit)@SOIC8 [SA602A]  
93LC76A(08bit)@TSSOP8 [SA643]  
93LC76B(16bit)@DFN8  
93LC76B(16bit)@SOIC8 [SA602A]  
93LC76B(16bit)@TSSOP8 [SA643]  
93LC76C(08bit)@DFN8  
93LC76C(08bit)@SOIC8 [SA602A]  
93LC76C(16bit)  
93LC76C(16bit)@MSOP8 [SA666]  
93LC76C(16bit)@TSSOP8 [SA643]  
93LC86(08bit)@SOIC8 [SA602A]  
93LC86(16bit)@SOIC8 [SA602A]  
93LC86A(08bit)@DFN8  
93LC86A(08bit)@SOIC8 [SA602A]  
93LC86A(08bit)@TSSOP8 [SA643]  
93LC86B(16bit)@DFN8  
93LC86B(16bit)@SOIC8 [SA602A]  
93LC86B(16bit)@TSSOP8 [SA643]  
93LC86C(08bit)@DFN8  
93LC86C(08bit)@SOIC8 [SA602A]  
93LC86C(16bit)  
93LC86C(16bit)@MSOP8 [SA666]  
93LC86C(16bit)@TSSOP8 [SA643]  
93LCS46@SOIC14 [SA026]  
93LCS56  
93LCS56@SOIC8 [SA602A]  
93LCS66@SOIC14 [SA026]  
ER5911  
HCS101  
HCS200  
HCS201  
HCS300  
HCS301  
HCS320  
HCS360  
HCS361  
HCS362  
HCS362@TSSOP8 [SA643]  
HCS410@SOIC8 [SA602A]  
HCS412  
HCS512  
MCP79510@MSOP10 [SA666]  
MCP79511@MSOP10 [SA666]  
MCP79512@MSOP10 [SA666]  
MCP79520@MSOP10 [SA666]  
MCP79521@MSOP10 [SA666]  
MCP79522@MSOP10 [SA666]  
MCP795B10@SOIC14 [SA602]  
MCP795B11@SOIC14 [SA602]  
MCP795B12@SOIC14 [SA602]  
MCP795B20@SOIC14 [SA602]

MCP795B20@TSSOP14 [SA026]  
MCP795B21@TSSOP14 [SA026]  
MCP795B22@TSSOP14 [SA026]  
MCP795W10@TSSOP14 [SA026]  
MCP795W11@TSSOP14 [SA026]  
MCP795W12@TSSOP14 [SA026]  
MCP795W20@TSSOP14 [SA026]  
MCP795W21@TSSOP14 [SA026]  
MCP795W22@TSSOP14 [SA026]  
MCP98242@TDFN8 [SA724]  
MCP98242@UDFN8 [SA724]  
MCP98243@TDFN8 [SA724]  
MCP98243@UDFN8 [SA724]  
SST25PF020B@USON8 [SA724]  
SST25PF040B@SOIC8[150mil] [SA602A]  
SST25PF040B@SOIC8[200mil] [SA605B]  
SST25PF040B@WSON8 [SA683]  
SST25PF080B@SOIC8[150mil] [SA602A]  
SST25PF080B@SOIC8[200mil] [SA605B]  
SST25PF080B@WSON8 [SA683]  
SST38VF6401B@TSOP48 [SB247-B4806]  
SST38VF6402@TSOP48 [SB247-B4806]  
SST38VF6402B@TSOP48 [SB247-B4806]  
SST38VF6403@TSOP48 [SB247-B4806]  
SST38VF6403B@TSOP48 [SB247-B4806]  
SST38VF6404@TSOP48 [SB247-B4806]  
SST38VF6404B@TSOP48 [SB247-B4806]  
MCP795B21@SOIC14 [SA602]  
MCP795B22@SOIC14 [SA602]  
MCP795W10@SOIC14 [SA602]  
MCP795W11@SOIC14 [SA602]  
MCP795W12@SOIC14 [SA602]  
MCP795W20@SOIC14 [SA602]  
MCP795W21@SOIC14 [SA602]  
MCP795W22@SOIC14 [SA602]  
MCP98242@DFN8 [SA724]  
MCP98242@TSSOP8 [SA724]  
MCP98243@DFN8 [SA724]  
MCP98243@TSSOP8 [SA724]  
SST25PF020B@SOIC8 [SA602A]  
SST25PF020B@WSON8 [SA683]  
SST38VF6401@TSOP48 [SB247-B4806]

## MICROCONTROLLER

CF745  
CF745@SSOP20 [SA626A]  
CF7645@SOIC18 [SA404]  
CF7665@SOIC18 [SA404]  
CF7685@SOIC18 [SA404]  
CF775@SOIC28 [SA404]  
dsPIC30F2010  
dsPIC30F2010@SDIP28 [SA653]  
dsPIC30F2010@SOIC28 [SA404]  
dsPIC30F2011  
dsPIC30F2011@QFN28 (ISP)  
dsPIC30F2011@SOIC18 [SA404]  
dsPIC30F2012  
dsPIC30F2012@QFN28 (ISP)  
dsPIC30F2012@SOIC28 [SA404]  
dsPIC30F3010  
dsPIC30F3010@QFN44 (ISP)  
dsPIC30F3010@SOIC28 [SA404]  
dsPIC30F3011 (ISP)  
dsPIC30F3011@QFP44 [SA245A-B4805]  
dsPIC30F3011@QFP44 (ISP)  
dsPIC30F3012 (ISP)  
CF745@SOIC18 [SA404]  
CF7645  
CF7665  
CF7685  
CF775  
CF775@SSOP28 [SA626A]  
dsPIC30F2010 (ISP)  
dsPIC30F2010@SDIP28 (ISP)  
dsPIC30F2010@SOIC28 (ISP)  
dsPIC30F2011 (ISP)  
dsPIC30F2011@SDIP18 (ISP)  
dsPIC30F2011@SOIC18 (ISP)  
dsPIC30F2012 (ISP)  
dsPIC30F2012@SDIP28 (ISP)  
dsPIC30F2012@SOIC28 (ISP)  
dsPIC30F3010 (ISP)  
dsPIC30F3010@SDIP28 (ISP)  
dsPIC30F3010@SOIC28 (ISP)  
dsPIC30F3011@QFN44 (ISP)  
dsPIC30F3012  
dsPIC30F3012@QFN44 (ISP)

dsPIC30F3012@QFP44 [SA245A-B4805]  
dsPIC30F3012@QFP44 (ISP)  
dsPIC30F3012@SOIC18 [SA404]  
dsPIC30F3013  
dsPIC30F3013@QFN44 [SA737]  
dsPIC30F3013@QFP44 [SA245A-B4805]  
dsPIC30F3013@QFP44 (ISP)  
dsPIC30F3013@SDIP28 (ISP)  
dsPIC30F3013@SOIC28 (ISP)  
dsPIC30F3014 (ISP)  
dsPIC30F3014@QFP44 (ISP)  
dsPIC30F4011 (ISP)  
dsPIC30F4011@QFP44 (ISP)  
dsPIC30F4012 (ISP)  
dsPIC30F4012@SDIP28 (ISP)  
dsPIC30F4012@SOIC28 (ISP)  
dsPIC30F4013 (ISP)  
dsPIC30F4013@QFP44 (ISP)  
dsPIC30F5013@QFP80 (ISP)  
dsPIC30F5016@QFP80 (ISP)  
dsPIC30F6010@TQFP80 (ISP)  
dsPIC30F6010A@TQFP80 (ISP)  
dsPIC30F6011@TQFP64 (ISP)  
dsPIC30F6011A@TQFP64 (ISP)  
dsPIC30F6012@TQFP64 (ISP)  
dsPIC30F6012A@TQFP64 (ISP)  
dsPIC30F6013A@QFP80 (ISP)  
dsPIC30F6014@TQFP80 (ISP)  
dsPIC30F6014A@TQFP80 (ISP)  
dsPIC33EP128GP502  
dsPIC33EP128GP502@QFN28 [SA685]  
dsPIC33EP128GP502@SSOP28 [SA626A]  
dsPIC33EP128GP503 (ISP)  
dsPIC33EP128GP503@VTLA36 [\$\$\$\$\$]  
dsPIC33EP128GP504 (ISP)  
dsPIC33EP128GP504@TQFP44 [SA245A-B4805]  
dsPIC33EP128GP506 (ISP)  
dsPIC33EP128MC202 (ISP)  
dsPIC33EP128MC202@SOIC28 [SA404]  
dsPIC33EP128MC202@SSOP28 [SA626A]  
dsPIC33EP128MC203 (ISP)  
dsPIC33EP128MC204@QFN44 [SA737]  
dsPIC33EP128MC204@TQFP44 [SA245A-B4805]  
dsPIC33EP128MC206 (ISP)  
dsPIC33EP128MC502 (ISP)  
dsPIC33EP128MC502@SOIC28 [SA404]  
dsPIC33EP128MC502@SSOP28 [SA626A]  
dsPIC33EP128MC503 (ISP)  
dsPIC33EP128MC504@QFN44 [SA737]  
dsPIC33EP128MC504@TQFP44 [SA245A-B4805]  
dsPIC33EP128MC506 (ISP)  
dsPIC33EP256GP502 (ISP)  
dsPIC33EP256GP502@SOIC28 [SA404]

dsPIC30F3012@SDIP18 (ISP)  
dsPIC30F3012@SOIC18 (ISP)  
dsPIC30F3013 (ISP)  
dsPIC30F3013@QFN44 (ISP)  
dsPIC30F3013@SDIP28 [SA653]  
dsPIC30F3013@SOIC28 [SA404]  
dsPIC30F3014  
dsPIC30F3014@QFN44 (ISP)  
dsPIC30F4011  
dsPIC30F4011@QFN44 (ISP)  
dsPIC30F4012  
dsPIC30F4012@QFN44 (ISP)  
dsPIC30F4012@SOIC28 [SA404]  
dsPIC30F4013  
dsPIC30F4013@QFN44 (ISP)  
dsPIC30F5011@QFP64 (ISP)  
dsPIC30F5015@QFP64 (ISP)  
dsPIC30F6010@QFP80 (ISP)  
dsPIC30F6010A@QFP80 (ISP)  
dsPIC30F6011@QFP64 (ISP)  
dsPIC30F6011A@QFP64 (ISP)  
dsPIC30F6012@QFP64 (ISP)  
dsPIC30F6012A@QFP64 (ISP)  
dsPIC30F6013@QFP80 (ISP)  
dsPIC30F6014@QFP80 (ISP)  
dsPIC30F6014A@QFP80 (ISP)  
dsPIC30F6015@QFP64 (ISP)  
dsPIC33EP128GP502 (ISP)  
dsPIC33EP128GP502@SOIC28 [SA404]  
dsPIC33EP128GP504@QFN44 [SA737]  
dsPIC33EP128MC202  
dsPIC33EP128MC202@QFN28 [SA685]  
dsPIC33EP128MC204 (ISP)  
dsPIC33EP128MC502  
dsPIC33EP128MC502@QFN28 [SA685]  
dsPIC33EP128MC504 (ISP)  
dsPIC33EP256GP502  
dsPIC33EP256GP502@QFN28 [SA685]

dsPIC33EP256GP502@SSOP28 [SA626A]  
dsPIC33EP256GP503 (ISP) dsPIC33EP256GP504 (ISP)  
dsPIC33EP256GP504@QFN44 [SA737]  
dsPIC33EP256GP504@TQFP44 [SA245A-B4805]  
dsPIC33EP256GP506 (ISP) dsPIC33EP256MC202  
dsPIC33EP256MC202 (ISP) dsPIC33EP256MC202@QFN28 [SA685]  
dsPIC33EP256MC202@SOIC28 [SA404]  
dsPIC33EP256MC202@SSOP28 [SA626A]  
dsPIC33EP256MC203 (ISP) dsPIC33EP256MC204 (ISP)  
dsPIC33EP256MC204@QFN44 [SA737]  
dsPIC33EP256MC204@TQFP44 [SA245A-B4805]  
dsPIC33EP256MC206 (ISP) dsPIC33EP256MC502  
dsPIC33EP256MC502 (ISP) dsPIC33EP256MC502@QFN28 [SA685]  
dsPIC33EP256MC502@SOIC28 [SA404]  
dsPIC33EP256MC502@SSOP28 [SA626A]  
dsPIC33EP256MC503 (ISP) dsPIC33EP256MC504 (ISP)  
dsPIC33EP256MC504@QFN44 [SA737]  
dsPIC33EP256MC504@TQFP44 [SA245A-B4805]  
dsPIC33EP256MC506 (ISP) dsPIC33EP32GP502  
dsPIC33EP32GP502 (ISP) dsPIC33EP32GP502@QFN28 [SA685]  
dsPIC33EP32GP502@SOIC28 [SA404] dsPIC33EP32GP502@SSOP28 [SA626A]  
dsPIC33EP32GP503 (ISP) dsPIC33EP32GP504 (ISP)  
dsPIC33EP32GP504@QFN44 [SA737]  
dsPIC33EP32GP504@TQFP44 [SA245A-B4805]  
dsPIC33EP32MC202 dsPIC33EP32MC202 (ISP)  
dsPIC33EP32MC202@QFN28 [SA685] dsPIC33EP32MC202@SOIC28 [SA404]  
dsPIC33EP32MC202@SSOP28 [SA626A] dsPIC33EP32MC203 (ISP)  
dsPIC33EP32MC204 (ISP) dsPIC33EP32MC204@QFN44 [SA737]  
dsPIC33EP32MC204@TQFP44 [SA245A-B4805]  
dsPIC33EP32MC502 dsPIC33EP32MC502 (ISP)  
dsPIC33EP32MC502@QFN28 [SA685] dsPIC33EP32MC502@SOIC28 [SA404]  
dsPIC33EP32MC502@SSOP28 [SA626A] dsPIC33EP32MC503 (ISP)  
dsPIC33EP32MC504 (ISP) dsPIC33EP32MC504@QFN44 [SA737]  
dsPIC33EP32MC504@TQFP44 [SA245A-B4805]  
dsPIC33EP512GP502 dsPIC33EP512GP502 (ISP)  
dsPIC33EP512GP502@QFN28 [SA685] dsPIC33EP512GP502@SOIC28 [SA404]  
dsPIC33EP512GP504 (ISP) dsPIC33EP512GP504@QFN44 [SA737]  
dsPIC33EP512GP504@TQFP44 [SA245A-B4805]  
dsPIC33EP512GP506 (ISP) dsPIC33EP512MC202  
dsPIC33EP512MC202 (ISP) dsPIC33EP512MC202@QFN28 [SA685]  
dsPIC33EP512MC202@SOIC28 [SA404] dsPIC33EP512MC204 (ISP)  
dsPIC33EP512MC204@QFN44 [SA737]  
dsPIC33EP512MC204@TQFP44 [SA245A-B4805]  
dsPIC33EP512MC206 (ISP) dsPIC33EP512MC502  
dsPIC33EP512MC502 (ISP) dsPIC33EP512MC502@QFN28 [SA685]  
dsPIC33EP512MC502@SOIC28 [SA404] dsPIC33EP512MC504 (ISP)  
dsPIC33EP512MC504@QFN44 [SA737]  
dsPIC33EP512MC504@TQFP44 [SA245A-B4805]  
dsPIC33EP512MC506 (ISP) dsPIC33EP64GP502  
dsPIC33EP64GP502 (ISP) dsPIC33EP64GP502@QFN28 [SA685]  
dsPIC33EP64GP502@SOIC28 [SA404] dsPIC33EP64GP502@SSOP28 [SA626A]  
dsPIC33EP64GP503 (ISP) dsPIC33EP64GP504 (ISP)  
dsPIC33EP64GP504@QFN44 [SA737]

dsPIC33EP64GP504@TQFP44 [SA245A-B4805]  
dsPIC33EP64GP506 (ISP) dsPIC33EP64MC202  
dsPIC33EP64MC202 (ISP) dsPIC33EP64MC202@QFN28 [SA685]  
dsPIC33EP64MC202@S0IC28 [SA404] dsPIC33EP64MC202@SSOP28 [SA626A]  
dsPIC33EP64MC203 (ISP) dsPIC33EP64MC204 (ISP)  
dsPIC33EP64MC204@QFN44 [SA737]  
dsPIC33EP64MC204@TQFP44 [SA245A-B4805]  
dsPIC33EP64MC206 (ISP) dsPIC33EP64MC502  
dsPIC33EP64MC502 (ISP) dsPIC33EP64MC502@QFN28 [SA685]  
dsPIC33EP64MC502@S0IC28 [SA404] dsPIC33EP64MC502@SSOP28 [SA626A]  
dsPIC33EP64MC503 (ISP) dsPIC33EP64MC504 (ISP)  
dsPIC33EP64MC504@QFN44 [SA737]  
dsPIC33EP64MC504@TQFP44 [SA245A-B4805]  
dsPIC33EP64MC506 (ISP) dsPIC33FJ06GS101  
dsPIC33FJ06GS101 (ISP) dsPIC33FJ06GS101@S0IC18 [SA404]  
dsPIC33FJ06GS101@S0IC18 (ISP) dsPIC33FJ06GS102  
dsPIC33FJ06GS102 (ISP) dsPIC33FJ06GS102@QFN28 [SA685]  
dsPIC33FJ06GS102@QFN28 (ISP) dsPIC33FJ06GS102@S0IC28 [SA404]  
dsPIC33FJ06GS102@S0IC28 (ISP) dsPIC33FJ06GS202  
dsPIC33FJ06GS202 (ISP) dsPIC33FJ06GS202@QFN28 [SA685]  
dsPIC33FJ06GS202@QFN28 (ISP) dsPIC33FJ06GS202@S0IC28 [SA404]  
dsPIC33FJ06GS202@S0IC28 (ISP) dsPIC33FJ128GP202  
dsPIC33FJ128GP202 (ISP) dsPIC33FJ128GP202@QFN28 [\$\$\$\$\$\$]  
dsPIC33FJ128GP202@S0IC28 [SA404] dsPIC33FJ128GP204 (ISP)  
dsPIC33FJ128GP204@QFN44 [SA737]  
dsPIC33FJ128GP204@QFN44 (DELTA) [SA737]  
dsPIC33FJ128GP204@TQFP44 [SA245A-B4805]  
dsPIC33FJ128GP204@TQFP44 (DELTA) [SA245A-B4805]  
dsPIC33FJ128GP206 (ISP) dsPIC33FJ128GP206A (ISP)  
dsPIC33FJ128GP306 (ISP) dsPIC33FJ128GP306A (ISP)  
dsPIC33FJ128GP310 (ISP) dsPIC33FJ128GP310A (ISP)  
dsPIC33FJ128GP706 (ISP) dsPIC33FJ128GP706A (ISP)  
dsPIC33FJ128GP708 (ISP) dsPIC33FJ128GP708A (ISP)  
dsPIC33FJ128GP710 (ISP) dsPIC33FJ128GP710A (ISP)  
dsPIC33FJ128GP802 dsPIC33FJ128GP802 (ISP)  
dsPIC33FJ128GP802@QFN28 [\$\$\$\$\$\$] dsPIC33FJ128GP802@S0IC28 [SA404]  
dsPIC33FJ128GP804 (ISP) dsPIC33FJ128GP804@QFN44 [SA737]  
dsPIC33FJ128GP804@TQFP44 [SA245A-B4805]  
dsPIC33FJ128MC202 dsPIC33FJ128MC202 (ISP)  
dsPIC33FJ128MC202@QFN28 [\$\$\$\$\$\$] dsPIC33FJ128MC202@S0IC28 [SA404]  
dsPIC33FJ128MC204 (ISP) dsPIC33FJ128MC204@QFN44 [SA737]  
dsPIC33FJ128MC204@TQFP44 [SA245A-B4805]  
dsPIC33FJ128MC506 (ISP) dsPIC33FJ128MC506A (ISP)  
dsPIC33FJ128MC510 (ISP) dsPIC33FJ128MC510A (ISP)  
dsPIC33FJ128MC706 (ISP) dsPIC33FJ128MC706A (ISP)  
dsPIC33FJ128MC708 (ISP) dsPIC33FJ128MC708A (ISP)  
dsPIC33FJ128MC710 (ISP) dsPIC33FJ128MC710A (ISP)  
dsPIC33FJ128MC802 dsPIC33FJ128MC802 (ISP)  
dsPIC33FJ128MC802@QFN28 [\$\$\$\$\$\$] dsPIC33FJ128MC802@S0IC28 [SA404]  
dsPIC33FJ128MC804 (ISP) dsPIC33FJ128MC804@QFN44 [SA737]  
dsPIC33FJ128MC804@TQFP44 [SA245A-B4805]  
dsPIC33FJ12GP201 dsPIC33FJ12GP201 (ISP)  
dsPIC33FJ12GP201@S0IC18 [SA404] dsPIC33FJ12GP201@S0IC18 (ISP)

dsPIC33FJ12GP202  
dsPIC33FJ12GP202@QFN28 [SA685]  
dsPIC33FJ12GP202@S0IC28 [SA404]  
dsPIC33FJ12GP202@SSOP28 [SA626A]  
dsPIC33FJ12MC201  
dsPIC33FJ12MC201@S0IC20 [SA404]  
dsPIC33FJ12MC201@SSOP20 [SA626A]  
dsPIC33FJ12MC202  
dsPIC33FJ12MC202@QFN28 [SA685]  
dsPIC33FJ12MC202@S0IC28 [SA404]  
dsPIC33FJ12MC202@SSOP28 [SA626A]  
dsPIC33FJ16GP101  
dsPIC33FJ16GP101@SSOP20 [SA626A]  
dsPIC33FJ16GP102@QFN28 [SA685]  
dsPIC33FJ16GP102@SSOP28 [SA626A]  
dsPIC33FJ16GP304@QFN44 (ISP)  
dsPIC33FJ16GP304@TQFP44 [SA245A-B4805]  
dsPIC33FJ16GP304@TQFP44 (ISP)  
dsPIC33FJ16GS402 (ISP)  
dsPIC33FJ16GS402@QFN28 (ISP)  
dsPIC33FJ16GS402@S0IC28 (ISP)  
dsPIC33FJ16GS404@QFN44 (ISP)  
dsPIC33FJ16GS404@TQFP44 [SA245A-B4805]  
dsPIC33FJ16GS404@TQFP44 (ISP)  
dsPIC33FJ16GS502  
dsPIC33FJ16GS502@QFN28 [SA685]  
dsPIC33FJ16GS502@S0IC28 [SA404]  
dsPIC33FJ16GS504@QFN44 [SA737]  
dsPIC33FJ16GS504@TQFP44 [SA245A-B4805]  
dsPIC33FJ16GS504@TQFP44 (ISP)  
dsPIC33FJ16MC101  
dsPIC33FJ16MC101@SSOP20 [SA626A]  
dsPIC33FJ16MC102@QFN28 [SA685]  
dsPIC33FJ16MC102@SSOP28 [SA626A]  
dsPIC33FJ16MC304@QFN44 (ISP)  
dsPIC33FJ16MC304@TQFP44 [SA245A-B4805]  
dsPIC33FJ16MC304@TQFP44 (ISP)  
dsPIC33FJ256GP506A (ISP)  
dsPIC33FJ256GP510A (ISP)  
dsPIC33FJ256GP710A (ISP)  
dsPIC33FJ256MC510A (ISP)  
dsPIC33FJ256MC710A (ISP)  
dsPIC33FJ32GP101@S0IC18 [SA404]  
dsPIC33FJ32GP102  
dsPIC33FJ32GP102@S0IC28 [SA404]  
dsPIC33FJ32GP104@QFN44 [SA737]  
dsPIC33FJ32GP104@TQFP44 [SA245A-B4805]  
dsPIC33FJ32GP202  
dsPIC33FJ32GP202@QFN28 [SA685]  
dsPIC33FJ32GP202@S0IC28 [SA404]  
dsPIC33FJ32GP204@QFN44 [SA737]  
dsPIC33FJ32GP204@TQFP44 [SA245A-B4805]  
dsPIC33FJ32GP204@TQFP44 (ISP)  
dsPIC33FJ12GP202 (ISP)  
dsPIC33FJ12GP202@QFN28 (ISP)  
dsPIC33FJ12GP202@S0IC28 (ISP)  
dsPIC33FJ12GP202@SSOP28 (ISP)  
dsPIC33FJ12MC201 (ISP)  
dsPIC33FJ12MC201@S0IC20 (ISP)  
dsPIC33FJ12MC201@SSOP20 (ISP)  
dsPIC33FJ12MC202 (ISP)  
dsPIC33FJ12MC202@QFN28 (ISP)  
dsPIC33FJ12MC202@S0IC28 (ISP)  
dsPIC33FJ12MC202@SSOP28 (ISP)  
dsPIC33FJ16GP101@S0IC18 [SA404]  
dsPIC33FJ16GP102  
dsPIC33FJ16GP102@S0IC28 [SA404]  
dsPIC33FJ16GP304@QFN44 [SA737]  
dsPIC33FJ16GS402  
dsPIC33FJ16GS402@QFN28 [SA685]  
dsPIC33FJ16GS402@S0IC28 [SA404]  
dsPIC33FJ16GS404@QFN44 [SA737]  
dsPIC33FJ16GS404@VLAP44 (ISP)  
dsPIC33FJ16GS502 (ISP)  
dsPIC33FJ16GS502@QFN28 (ISP)  
dsPIC33FJ16GS502@S0IC28 (ISP)  
dsPIC33FJ16GS504@QFN44 (ISP)  
dsPIC33FJ16GS504@VLAP44 (ISP)  
dsPIC33FJ16MC101@S0IC20 [SA404]  
dsPIC33FJ16MC102  
dsPIC33FJ16MC102@S0IC28 [SA404]  
dsPIC33FJ16MC304@QFN44 [SA737]  
dsPIC33FJ256GP506 (ISP)  
dsPIC33FJ256GP510 (ISP)  
dsPIC33FJ256GP710 (ISP)  
dsPIC33FJ256MC510 (ISP)  
dsPIC33FJ256MC710 (ISP)  
dsPIC33FJ32GP101  
dsPIC33FJ32GP101@SSOP20 [SA626A]  
dsPIC33FJ32GP102@QFN28 [SA685]  
dsPIC33FJ32GP102@SSOP28 [SA626A]  
dsPIC33FJ32GP202 (ISP)  
dsPIC33FJ32GP202@QFN28 (ISP)  
dsPIC33FJ32GP202@S0IC28 (ISP)  
dsPIC33FJ32GP204@QFN44 (ISP)  
dsPIC33FJ32GP302

dsPIC33FJ32GP302 (ISP) dsPIC33FJ32GP302@QFN28 [SA685]  
dsPIC33FJ32GP302@QFN28 (ISP) dsPIC33FJ32GP302@S0IC28 [SA404]  
dsPIC33FJ32GP302@S0IC28 (ISP) dsPIC33FJ32GP304@QFN44 [SA737]  
dsPIC33FJ32GP304@QFN44 (ISP)  
dsPIC33FJ32GP304@TQFP44 [SA245A-B4805]  
dsPIC33FJ32GP304@TQFP44 (ISP) dsPIC33FJ32GS406@QFN64 (ISP)  
dsPIC33FJ32GS406@TQFP64 (ISP) dsPIC33FJ32GS606@QFN64 (ISP)  
dsPIC33FJ32GS606@TQFP64 (ISP) dsPIC33FJ32GS608@TQFP80 (ISP)  
dsPIC33FJ32GS610@TQFP100 (1) (ISP) dsPIC33FJ32GS610@TQFP100 (2) (ISP)  
dsPIC33FJ32MC101 dsPIC33FJ32MC101@S0IC20 [SA404]  
dsPIC33FJ32MC101@SSOP20 [SA626A] dsPIC33FJ32MC102@QFN28 [SA685]  
dsPIC33FJ32MC102@S0IC28 [SA404] dsPIC33FJ32MC102@SSOP28 [SA626A]  
dsPIC33FJ32MC104@QFN44 [SA737]  
dsPIC33FJ32MC104@TQFP44 [SA245A-B4805]  
dsPIC33FJ32MC202 dsPIC33FJ32MC202 (ISP)  
dsPIC33FJ32MC202@QFN28 [SA685] dsPIC33FJ32MC202@QFN28 (ISP)  
dsPIC33FJ32MC202@S0IC28 [SA404] dsPIC33FJ32MC202@S0IC28 (ISP)  
dsPIC33FJ32MC204@QFN44 [SA737] dsPIC33FJ32MC204@QFN44 (ISP)  
dsPIC33FJ32MC204@TQFP44 [SA245A-B4805]  
dsPIC33FJ32MC204@TQFP44 (ISP) dsPIC33FJ32MC302  
dsPIC33FJ32MC302 (ISP) dsPIC33FJ32MC302@QFN28 [SA685]  
dsPIC33FJ32MC302@QFN28 (ISP) dsPIC33FJ32MC302@S0IC28 [SA404]  
dsPIC33FJ32MC302@S0IC28 (ISP) dsPIC33FJ32MC304@QFN44 [SA737]  
dsPIC33FJ32MC304@QFN44 (ISP)  
dsPIC33FJ32MC304@TQFP44 [SA245A-B4805]  
dsPIC33FJ32MC304@TQFP44 (ISP) dsPIC33FJ64GP202  
dsPIC33FJ64GP202 (ISP) dsPIC33FJ64GP202@QFN28 [SA685]  
dsPIC33FJ64GP202@QFN28 (ISP) dsPIC33FJ64GP202@S0IC28 [SA404]  
dsPIC33FJ64GP202@S0IC28 (ISP) dsPIC33FJ64GP204@QFN44 [SA737]  
dsPIC33FJ64GP204@QFN44 (ISP)  
dsPIC33FJ64GP204@TQFP44 [SA245A-B4805]  
dsPIC33FJ64GP204@TQFP44 (ISP) dsPIC33FJ64GP206@QFN64 (ISP)  
dsPIC33FJ64GP206@TQFP64 (ISP) dsPIC33FJ64GP206A@QFN64 (ISP)  
dsPIC33FJ64GP206A@TQFP64 (ISP) dsPIC33FJ64GP306@QFN64 (ISP)  
dsPIC33FJ64GP306@TQFP64 (ISP) dsPIC33FJ64GP306A@QFN64 (ISP)  
dsPIC33FJ64GP306A@TQFP64 (ISP) dsPIC33FJ64GP310@TQFP100 (1) (ISP)  
dsPIC33FJ64GP310@TQFP100 (2) (ISP) dsPIC33FJ64GP310A@TQFP100 (1) (ISP)  
dsPIC33FJ64GP310A@TQFP100 (2) (ISP) dsPIC33FJ64GP706@QFN64 (ISP)  
dsPIC33FJ64GP706@TQFP64 (ISP) dsPIC33FJ64GP706A@QFN64 (ISP)  
dsPIC33FJ64GP706A@TQFP64 (ISP) dsPIC33FJ64GP708@TQFP80 (ISP)  
dsPIC33FJ64GP708A@TQFP80 (ISP) dsPIC33FJ64GP710@TQFP100 (1) (ISP)  
dsPIC33FJ64GP710@TQFP100 (2) (ISP) dsPIC33FJ64GP710A@TQFP100 (1) (ISP)  
dsPIC33FJ64GP710A@TQFP100 (2) (ISP) dsPIC33FJ64GP802  
dsPIC33FJ64GP802 (ISP) dsPIC33FJ64GP802@QFN28 [SA685]  
dsPIC33FJ64GP802@QFN28 (ISP) dsPIC33FJ64GP802@S0IC28 [SA404]  
dsPIC33FJ64GP802@S0IC28 (ISP) dsPIC33FJ64GP804@QFN44 [SA737]  
dsPIC33FJ64GP804@QFN44 (ISP)  
dsPIC33FJ64GP804@TQFP44 [SA245A-B4805]  
dsPIC33FJ64GP804@TQFP44 (ISP) dsPIC33FJ64GS406@QFN64 (ISP)  
dsPIC33FJ64GS406@TQFP64 (ISP) dsPIC33FJ64GS606@QFN64 (ISP)  
dsPIC33FJ64GS606@TQFP64 (ISP) dsPIC33FJ64GS608@TQFP80 (ISP)  
dsPIC33FJ64GS610@TQFP100 (1) (ISP) dsPIC33FJ64GS610@TQFP100 (2) (ISP)  
dsPIC33FJ64MC202 dsPIC33FJ64MC202 (ISP)

dsPIC33FJ64MC202@QFN28 [SA685]  
dsPIC33FJ64MC202@SOIC28 [SA404]  
dsPIC33FJ64MC204@QFN44 [SA737]  
dsPIC33FJ64MC204@TQFP44 [SA245A-B4805]  
dsPIC33FJ64MC204@TQFP44 (ISP)  
dsPIC33FJ64MC506@TQFP64 (ISP)  
dsPIC33FJ64MC506A@TQFP64 (ISP)  
dsPIC33FJ64MC508A@TQFP80 (ISP)  
dsPIC33FJ64MC510@TQFP100 (2) (ISP)  
dsPIC33FJ64MC510A@TQFP100 (2) ISP  
dsPIC33FJ64MC706@TQFP64 (ISP)  
dsPIC33FJ64MC706A@TQFP64 (ISP)  
dsPIC33FJ64MC710@TQFP100 (2) (ISP)  
dsPIC33FJ64MC710A@TQFP100 (2) ISP  
dsPIC33FJ64MC802 (ISP)  
dsPIC33FJ64MC802@QFN28 (ISP)  
dsPIC33FJ64MC802@SOIC28 (ISP)  
dsPIC33FJ64MC804@QFN44 (ISP)  
dsPIC33FJ64MC804@TQFP44 [SA245A-B4805]  
dsPIC33FJ64MC804@TQFP44 (ISP)  
HA2089@QFN16 [SA727]  
HA2089@TSSOP14 [SA026]  
HA2099@SOIC18 [SA404]  
HA3089  
HA3089@SOIC28 [SA404]  
HA3099  
HA3099@SOIC28 [SA404]  
MCP25020  
MCP25020@SOIC14 [SA404]  
MCP25020@TSSOP14 [SA602]  
MCP25025  
MCP25025@SOIC14 [SA404]  
MCP25025@TSSOP14 [SA602]  
MCP25050  
MCP25050@SOIC14 [SA404]  
MCP25050@TSSOP14 [SA602]  
MCP25055  
MCP25055@SOIC14 [SA404]  
MCP25055@TSSOP14 [SA602]  
MCV08A  
MCV08A@SOIC8[150mil] [SA602A]  
MCV14A  
MCV14A@TSSOP14 [SA026]  
MCV18A@SOIC18 [SA404]  
MCV28A  
MCV28A@SSOP28 [SA626A]  
PIC10F200 (ISP)  
PIC10F200@SOT6 [SA717]  
PIC10F202  
PIC10F202@DFN8 [SA724]  
PIC10F202@SOT6 (ISP)  
PIC10F204 (ISP)  
PIC10F204@SOT6 [SA717]  
dsPIC33FJ64MC202@QFN28 (ISP)  
dsPIC33FJ64MC202@SOIC28 (ISP)  
dsPIC33FJ64MC204@QFN44 (ISP)  
dsPIC33FJ64MC506@QFN64 (ISP)  
dsPIC33FJ64MC506A@QFN64 (ISP)  
dsPIC33FJ64MC508@TQFP80 (ISP)  
dsPIC33FJ64MC510@TQFP100 (1) (ISP)  
dsPIC33FJ64MC510A@TQFP100 (1) ISP  
dsPIC33FJ64MC706@QFN64 (ISP)  
dsPIC33FJ64MC706A@QFN64 (ISP)  
dsPIC33FJ64MC710@TQFP100 (1) (ISP)  
dsPIC33FJ64MC710A@TQFP100 (1) ISP  
dsPIC33FJ64MC802  
dsPIC33FJ64MC802@QFN28 [SA685]  
dsPIC33FJ64MC802@SOIC28 [SA404]  
dsPIC33FJ64MC804@QFN44 [SA737]  
HA2089  
HA2089@SOIC14 [SA602]  
HA2099  
HA2099@SSOP20 [SA626A]  
HA3089@QFN28 [SA685]  
HA3089@SSOP28 [SA626A]  
HA3099@QFN28 [SA685]  
HA3099@SSOP28 [SA626A]  
MCP25020 (ISP)  
MCP25020@SOIC14 (ISP)  
MCP25020@TSSOP14 (ISP)  
MCP25025 (ISP)  
MCP25025@SOIC14 (ISP)  
MCP25025@TSSOP14 (ISP)  
MCP25050 (ISP)  
MCP25050@SOIC14 (ISP)  
MCP25050@TSSOP14 (ISP)  
MCP25055 (ISP)  
MCP25055@SOIC14 (ISP)  
MCP25055@TSSOP14 (ISP)  
MCV08A@MSOP8 [SA666]  
MCV08A@SOIC8[200mil] [SA605B]  
MCV14A@SOIC14 [SA602]  
MCV18A  
MCV18A@SSOP20 [SA626A]  
MCV28A@SOIC28 [SA404]  
PIC10F200  
PIC10F200@DFN8 [SA724]  
PIC10F200@SOT6 (ISP)  
PIC10F202 (ISP)  
PIC10F202@SOT6 [SA717]  
PIC10F204  
PIC10F204@DFN8 [SA724]  
PIC10F204@SOT6 (ISP)

PIC10F206	PIC10F206 (ISP)
PIC10F206@DFN8 [SA724]	PIC10F206@SOT6 [SA717]
PIC10F206@SOT6 (ISP)	PIC10F220
PIC10F220 (ISP)	PIC10F220@DFN8 [SA724]
PIC10F220@SOT6 [SA717]	PIC10F220@SOT6 (ISP)
PIC10F222	PIC10F222 (ISP)
PIC10F222@DFN8 [SA724]	PIC10F222@SOT6 [SA717]
PIC10F222@SOT6 (ISP)	PIC10F320
PIC10F320 (32 WORD PRO)	PIC10F320 (32 WORD PRO) (ISP)
PIC10F320 (32 WORD PRO)@DFN8 [SA724]	
PIC10F320 (32 WORD PRO)@SOT-23 [SA717]	
PIC10F320 (ISP)	PIC10F320@DFN8 [SA724]
PIC10F320@SOT-23 [SA717]	PIC10F322
PIC10F322 (32 WORD PRO)	PIC10F322 (32 WORD PRO) (ISP)
PIC10F322 (32 WORD PRO)@DFN8 [SA724]	
PIC10F322 (32 WORD PRO)@SOT-23 [SA717]	
PIC10F322 (ISP)	PIC10F322@DFN8 [SA724]
PIC10F322@SOT-23 [SA717]	PIC10LF320
PIC10LF320 (32 WORD PRO)	PIC10LF320 (32 WORD PRO) (ISP)
PIC10LF320 (32 WORD PRO)@DFN8 [SA724]	
PIC10LF320 (32 WORD PRO)@SOT-23 [SA717]	
PIC10LF320 (ISP)	PIC10LF320@DFN8 [SA724]
PIC10LF320@SOT-23 [SA717]	PIC10LF322
PIC10LF322 (32 WORD PRO)	PIC10LF322 (32 WORD PRO) (ISP)
PIC10LF322 (32 WORD PRO)@DFN8 [SA724]	
PIC10LF322 (32 WORD PRO)@SOT-23 [SA717]	
PIC10LF322 (ISP)	PIC10LF322@DFN8 [SA724]
PIC10LF322@SOT-23 [SA717]	PIC12C508
PIC12C508 (ISP)	PIC12C508@SOIC8 [SA605B]
PIC12C508@SOIC8 (ISP)	PIC12C508A
PIC12C508A (ISP)	PIC12C508A (SM)@SOIC8 [SA605B]
PIC12C508A (SM)@SOIC8 (ISP)	PIC12C508A (SN)@SOIC8 [SA602]
PIC12C508A (SN)@SOIC8 (ISP)	PIC12C509
PIC12C509 (ISP)	PIC12C509 (SM)@SOIC8 [SA605B]
PIC12C509 (SM)@SOIC8 (ISP)	PIC12C509 (SN)@SOIC8 [SA602]
PIC12C509 (SN)@SOIC8 (ISP)	PIC12C509A
PIC12C509A (ISP)	PIC12C509A (SM)@SOIC8 [SA605B]
PIC12C509A (SM)@SOIC8 (ISP)	PIC12C509A (SN)@SOIC8 [SA602]
PIC12C509A (SN)@SOIC8 (ISP)	PIC12C509A@DFN8 [SA683]
PIC12C509A@DFN8 (ISP)	PIC12C671
PIC12C671 (ISP)	PIC12C671@DFN8 [SA683]
PIC12C671@DFN8 (ISP)	PIC12C671@SOIC8 [SA605B]
PIC12C671@SOIC8 (ISP)	PIC12C672
PIC12C672 (ISP)	PIC12C672@DFN8 [SA683]
PIC12C672@DFN8 (ISP)	PIC12C672@SOIC8 [SA605B]
PIC12C672@SOIC8 (ISP)	PIC12CE518
PIC12CE518 (ISP)	PIC12CE518@SOIC8 [SA605B]
PIC12CE518@SOIC8 (ISP)	PIC12CE519
PIC12CE519 (ISP)	PIC12CE519 (SM)@SOIC8 [SA605B]
PIC12CE519 (SM)@SOIC8 (ISP)	PIC12CE519 (SN)@SOIC8 [SA602]
PIC12CE519 (SN)@SOIC8 (ISP)	PIC12CE673
PIC12CE673 (ISP)	PIC12CE673@SOIC8 [SA605B]
PIC12CE673@SOIC8 (ISP)	PIC12CE674

PIC12CE674 (ISP)  
PIC12CE674@SOIC8 (ISP)  
PIC12F1501 (ISP)  
PIC12F1501 (MF)@DFN8 [SA703]  
PIC12F1501@MSOP8 [SA666]  
PIC12F1501@SOIC8 [SA602A]  
PIC12F1571  
PIC12F1571 (32 word)@DFN8 [SA703]  
PIC12F1571 (32 word)@MSOP8 [SA666]  
PIC12F1571 (32 word)@SOIC8 [SA602A]  
PIC12F1571@DFN8 [SA703]  
PIC12F1571@MSOP8 [SA666]  
PIC12F1572  
PIC12F1572 (32 word)@DFN8 [SA703]  
PIC12F1572 (32 word)@MSOP8 [SA666]  
PIC12F1572 (32 word)@SOIC8 [SA602A]  
PIC12F1572@DFN8 [SA703]  
PIC12F1572@MSOP8 [SA666]  
PIC12F1822  
PIC12F1822 (ISP) (HV)  
PIC12F1822 (LVISP)  
PIC12F1822@DFN8 (8-word) [SA703]  
PIC12F1822@DFN8 (LV) [SA724]  
PIC12F1822@SOIC8 (8-word) [SA602A]  
PIC12F1822@SOIC8 (ISP) (HV)  
PIC12F1840  
PIC12F1840@DFN8 [SA703]  
PIC12F1840@SOIC8 [SA602A]  
PIC12F1840E  
PIC12F1840E@SOIC8 [SA602A]  
PIC12F508 (ISP)  
PIC12F508@MSOP8 (ISP)  
PIC12F508@SOIC8 (ISP)  
PIC12F509 (ISP)  
PIC12F509@MSOP8 (ISP)  
PIC12F509@SOIC8 (ISP)  
PIC12F510 (ISP)  
PIC12F510@MSOP8 (ISP)  
PIC12F510@SOIC8 (150mil) (ISP)  
PIC12F510@SOIC8 (200mil) (ISP)  
PIC12F519 (ISP)  
PIC12F519@DFN8 (ISP)  
PIC12F519@MSOP8 (ISP)  
PIC12F519@SOIC8 (ISP)  
PIC12F529T39A (ISP)  
PIC12F529T48A (ISP)  
PIC12F609 (ISP)  
PIC12F609@DFN8 (ISP)  
PIC12F609@DFN8-S (ISP)  
PIC12F609@MSOP8 (ISP)  
PIC12F609@SOIC8 (ISP)  
PIC12F615 (ISP)  
PIC12F615@DFN8 (ISP)

PIC12CE674@SOIC8 [SA605B]  
PIC12F1501  
PIC12F1501 (MC)@DFN8 [SA724]  
PIC12F1501@DFN8 (ISP)  
PIC12F1501@MSOP8 (ISP)  
PIC12F1501@SOIC8 (ISP)  
PIC12F1571 (32 word)  
  
PIC12F1571@ISP  
PIC12F1571@SOIC8 [SA602A]  
PIC12F1572 (32 word)  
  
PIC12F1572@ISP  
PIC12F1572@SOIC8 [SA602A]  
PIC12F1822 (8-word)  
PIC12F1822 (LV)  
PIC12F1822@DFN8 [SA703]  
PIC12F1822@DFN8 (ISP) (HV)  
PIC12F1822@SOIC8 [SA602A]  
  
PIC12F1822@SOIC8 (LV) [SA602A]  
PIC12F1840 (ISP) (HV)  
PIC12F1840@DFN8 (ISP) (HV)  
PIC12F1840@SOIC8 (ISP) (HV)  
PIC12F1840E@DFN8 [SA703]  
PIC12F508  
PIC12F508@MSOP8 [SA666]  
PIC12F508@SOIC8 [SA602]  
PIC12F509  
PIC12F509@MSOP8 [SA666]  
PIC12F509@SOIC8 [SA602]  
PIC12F510  
PIC12F510@MSOP8 [SA666]  
PIC12F510@SOIC8 (150mil) [SA602A]  
PIC12F510@SOIC8 (200mil) [SA605B]  
PIC12F519  
PIC12F519@DFN8 [SA724]  
PIC12F519@MSOP8 [SA666]  
PIC12F519@SOIC8 [SA602A]  
PIC12F529T39A [SA026]  
PIC12F529T48A [SA026]  
PIC12F609  
PIC12F609@DFN8 [SA703]  
PIC12F609@DFN8-S [SA683]  
PIC12F609@MSOP8 [SA666]  
PIC12F609@SOIC8 [SA602A]  
PIC12F615  
PIC12F615@DFN8 [SA703]  
PIC12F615@DFN8-S [SA683]

PIC12F615@DFN8-S (ISP)	PIC12F615@MSOP8 [SA666]
PIC12F615@MSOP8 (ISP)	PIC12F615@SOIC8 [SA602A]
PIC12F615@SOIC8 (ISP)	PIC12F617
PIC12F617 (ISP)	PIC12F617@DFN8 [SA703]
PIC12F617@DFN8 (ISP)	PIC12F617@DFN8-S [SA683]
PIC12F617@DFN8-S (ISP)	PIC12F617@MSOP8 [SA666]
PIC12F617@MSOP8 (ISP)	PIC12F617@SOIC8 [SA602A]
PIC12F617@SOIC8 (ISP)	PIC12F629
PIC12F629 (ISP)	PIC12F629 (SM)@SOIC8 [SA605B]
PIC12F629 (SM)@SOIC8 (ISP)	PIC12F629 (SN)@SOIC8 [SA602]
PIC12F629 (SN)@SOIC8 (ISP)	PIC12F629@DFN8 [SA683]
PIC12F629@DFN8 (ISP)	PIC12F635
PIC12F635 (4-WORD PRO)	PIC12F635 (ISP)
PIC12F635 (MD)@DFN8 [SA744]	
PIC12F635 (MD)@DFN8 (4-WORD PRO) [SA744]	
PIC12F635 (MD)@DFN8 (ISP)	PIC12F635 (MF)@DFN8 [SA683]
PIC12F635 (MF)@DFN8 (4-WORD PRO) [SA683]	
PIC12F635 (MF)@DFN8 (ISP)	PIC12F635 (SM)@SOIC8 [SA605B]
PIC12F635 (SM)@SOIC8 (4-WORD PRO) [SA605B]	
PIC12F635 (SM)@SOIC8 (ISP)	PIC12F635 (SN)@SOIC8 [SA602]
PIC12F635 (SN)@SOIC8 (4-WORD PRO) [SA602]	
PIC12F635 (SN)@SOIC8 (ISP)	PIC12F675
PIC12F675 (ISP)	PIC12F675 (SM)@SOIC8 [SA605B]
PIC12F675 (SM)@SOIC8 (ISP)	PIC12F675 (SN)@SOIC8 [SA602]
PIC12F675 (SN)@SOIC8 (ISP)	PIC12F675@DFN8 [SA683]
PIC12F675@DFN8 (ISP)	PIC12F675@SSOP20 [SA626A]
PIC12F675@SSOP20 (ISP)	PIC12F683
PIC12F683 (4-WORD PRO)	PIC12F683 (ISP)
PIC12F683 (MD)@DFN8 [SA744]	
PIC12F683 (MD)@DFN8 (4-WORD PRO) [SA744]	
PIC12F683 (MD)@DFN8 (ISP)	PIC12F683 (MF)@DFN8 [SA683]
PIC12F683 (MF)@DFN8 (4-WORD PRO) [SA683]	
PIC12F683 (MF)@DFN8 (ISP)	PIC12F683 (SM)@SOIC8 [SA605B]
PIC12F683 (SM)@SOIC8 (4-WORD PRO) [SA605B]	
PIC12F683 (SM)@SOIC8 (ISP)	PIC12F683 (SN)@SOIC8 [SA602]
PIC12F683 (SN)@SOIC8 (4-WORD PRO) [SA602]	
PIC12F683 (SN)@SOIC8 (ISP)	PIC12F752
PIC12F752 (ISP)	PIC12F752@DFN8 [SA703]
PIC12F752@DFN8-S [SA683]	PIC12F752@MSOP8 [SA666]
PIC12F752@SOIC8 [SA602A]	PIC12HV609
PIC12HV609 (ISP)	PIC12HV609@DFN8 [SA703]
PIC12HV609@DFN8 (ISP)	PIC12HV609@DFN8-S [SA683]
PIC12HV609@DFN8-S (ISP)	PIC12HV609@MSOP8 [SA666]
PIC12HV609@MSOP8 (ISP)	PIC12HV609@SOIC8 [SA602A]
PIC12HV609@SOIC8 (ISP)	PIC12HV615
PIC12HV615 (ISP)	PIC12HV615@DFN8 [SA703]
PIC12HV615@DFN8 (ISP)	PIC12HV615@DFN8-S [SA683]
PIC12HV615@DFN8-S (ISP)	PIC12HV615@MSOP8 [SA666]
PIC12HV615@MSOP8 (ISP)	PIC12HV615@SOIC8 [SA602A]
PIC12HV615@SOIC8 (ISP)	PIC12HV752
PIC12HV752 (ISP)	PIC12HV752@DFN8 [SA703]
PIC12HV752@DFN8-S [SA683]	PIC12HV752@MSOP8 [SA666]
PIC12HV752@SOIC8 [SA602A]	PIC12LC508

PIC12LC508 (ISP)  
PIC12LC508@SOIC8 (ISP)  
PIC12LC508A (ISP)  
PIC12LC508A (SM)@SOIC8 (ISP)  
PIC12LC508A (SN)@SOIC8 (ISP)  
PIC12LC509 (ISP)  
PIC12LC509 (SM)@SOIC8 (ISP)  
PIC12LC509 (SN)@SOIC8 (ISP)  
PIC12LC509A (ISP)  
PIC12LC509A (SM)@SOIC8 (ISP)  
PIC12LC509A (SN)@SOIC8 (ISP)  
PIC12LC671 (ISP)  
PIC12LC671@DFN8 (ISP)  
PIC12LC671@SOIC8 (ISP)  
PIC12LC672 (ISP)  
PIC12LC672@DFN8 (ISP)  
PIC12LC672@SOIC8 (ISP)  
PIC12LF1501 (ISP)  
PIC12LF1501 (MF)@DFN8 [SA703]  
PIC12LF1501@MSOP8 [SA666]  
PIC12LF1501@SOIC8 [SA602A]  
PIC12LF1552  
PIC12LF1552 (MF)@DFN8 [SA703]  
PIC12LF1552@MSOP8 [SA666]  
PIC12LF1571  
PIC12LF1571 (32 word)@DFN8 [SA703]  
PIC12LF1571 (32 word)@MSOP8 [SA666]  
PIC12LF1571 (32 word)@SOIC8 [SA602A]  
PIC12LF1571@DFN8 [SA703]  
PIC12LF1571@MSOP8 [SA666]  
PIC12LF1572  
PIC12LF1572 (32 word)@DFN8 [SA703]  
PIC12LF1572 (32 word)@MSOP8 [SA666]  
PIC12LF1572 (32 word)@SOIC8 [SA602A]  
PIC12LF1572@DFN8 [SA703]  
PIC12LF1572@MSOP8 [SA666]  
PIC12LF1822  
PIC12LF1822 (ISP) (HV)  
PIC12LF1822 (LVISP)  
PIC12LF1822@DFN8 (8-word) [SA703]  
PIC12LF1822@DFN8 (LV) [SA724]  
PIC12LF1822@SOIC8 (8-word) [SA602A]  
PIC12LF1822@SOIC8 (ISP) (HV)  
PIC12LF1840  
PIC12LF1840@DFN8 [SA703]  
PIC12LF1840@SOIC8 [SA602A]  
PIC12LF1840E  
PIC12LF1840E@SOIC8 [SA602A]  
PIC12LF508  
PIC12LF508@MSOP8 [SA666]  
PIC12LF508@SOIC8 [SA602]  
PIC12LF509  
PIC12LF509@MSOP8 [SA666]

PIC12LC508@SOIC8 [SA605B]  
PIC12LC508A  
PIC12LC508A (SM)@SOIC8 [SA605B]  
PIC12LC508A (SN)@SOIC8 [SA602]  
PIC12LC509  
PIC12LC509 (SM)@SOIC8 [SA605B]  
PIC12LC509 (SN)@SOIC8 [SA602]  
PIC12LC509A  
PIC12LC509A (SM)@SOIC8 [SA605B]  
PIC12LC509A (SN)@SOIC8 [SA602]  
PIC12LC671  
PIC12LC671@DFN8 [SA683]  
PIC12LC671@SOIC8 [SA605B]  
PIC12LC672  
PIC12LC672@DFN8 [SA683]  
PIC12LC672@SOIC8 [SA605B]  
PIC12LF1501  
PIC12LF1501 (MC)@DFN8 [SA724]  
PIC12LF1501@DFN8 (ISP)  
PIC12LF1501@MSOP8 (ISP)  
PIC12LF1501@SOIC8 (ISP)  
PIC12LF1552 (MC)@DFN8 [SA724]  
PIC12LF1552@ISP  
PIC12LF1552@SOIC8 [SA602A]  
PIC12LF1571 (32 word)  
PIC12LF1571@ISP  
PIC12LF1571@SOIC8 [SA602A]  
PIC12LF1572 (32 word)  
PIC12LF1572@ISP  
PIC12LF1572@SOIC8 [SA602A]  
PIC12LF1822 (8-word)  
PIC12LF1822 (LV)  
PIC12LF1822@DFN8 [SA703]  
PIC12LF1822@DFN8 (ISP) (HV)  
PIC12LF1822@SOIC8 [SA602A]  
PIC12LF1822@SOIC8 (LV) [SA602A]  
PIC12LF1840 (ISP) (HV)  
PIC12LF1840@DFN8 (ISP) (HV)  
PIC12LF1840@SOIC8 (ISP) (HV)  
PIC12LF1840E@DFN8 [SA703]  
PIC12LF1840T48A [SA026]  
PIC12LF508 (ISP)  
PIC12LF508@MSOP8 (ISP)  
PIC12LF508@SOIC8 (ISP)  
PIC12LF509 (ISP)  
PIC12LF509@MSOP8 (ISP)

PIC12LF509@S0IC8 [SA602]  
PIC12LF519  
PIC12LF519@DFN8 [SA724]  
PIC12LF519@MSOP8 [SA666]  
PIC12LF519@S0IC8 [SA602A]  
PIC14000  
PIC14000@S0IC28 [SA404]  
PIC14000@SSOP28 [SA626A]  
PIC16C432  
PIC16C432@SSOP20 [SA626A]  
PIC16C433  
PIC16C433@S0IC18 [SA404]  
PIC16C505  
PIC16C52  
PIC16C54  
PIC16C54A  
PIC16C54A@SSOP20 [SA626A]  
PIC16C54B@S0IC18 [SA404]  
PIC16C54C  
PIC16C54C@SSOP20 [SA626A]  
PIC16C55@S0IC28 [SA404]  
PIC16C554 (ISP)  
PIC16C554@S0IC18 (ISP)  
PIC16C554@SSOP20 (ISP)  
PIC16C556 (ISP)  
PIC16C556@S0IC18 (ISP)  
PIC16C558 (ISP)  
PIC16C558@S0IC18 (ISP)  
PIC16C558@SSOP20 (ISP)  
PIC16C55A@S0IC28 [SA404]  
PIC16C56  
PIC16C56A  
PIC16C56A@SSOP20 [SA626A]  
PIC16C57@S0IC28 [SA404]  
PIC16C57C  
PIC16C57C@SSOP28 [SA626A]  
PIC16C58@S0IC18 [SA404]  
PIC16C58A@S0IC18 [SA404]  
PIC16C58B  
PIC16C58B@SSOP20 [SA626A]  
PIC16C61 (ISP)  
PIC16C61@S0IC18 (ISP)  
PIC16C62 (ISP)  
PIC16C62@S0IC28 (ISP)  
PIC16C62@SSOP28 (ISP)  
PIC16C620 (ISP)  
PIC16C620@S0IC18 (ISP)  
PIC16C620A (ISP)  
PIC16C620A@S0IC18 (ISP)  
PIC16C620A@SSOP20 (ISP)  
PIC16C621 (ISP)  
PIC16C621@S0IC18 (ISP)  
PIC16C621A (ISP)

PIC12LF509@S0IC8 (ISP)  
PIC12LF519 (ISP)  
PIC12LF519@DFN8 (ISP)  
PIC12LF519@MSOP8 (ISP)  
PIC12LF519@S0IC8 (ISP)  
PIC14000 (ISP)  
PIC14000@S0IC28 (ISP)  
PIC14000@SSOP28 (ISP)  
PIC16C432 (ISP)  
PIC16C432@SSOP20 (ISP)  
PIC16C433 (ISP)  
PIC16C433@S0IC18 (ISP)  
PIC16C505@S0IC14 [SA602]  
PIC16C52@S0IC18 [SA404]  
PIC16C54@S0IC18 [SA404]  
PIC16C54A@S0IC18 [SA404]  
PIC16C54B  
PIC16C54B@SSOP20 [SA626A]  
PIC16C54C@S0IC18 [SA404]  
PIC16C55  
PIC16C554  
PIC16C554@S0IC18 [SA404]  
PIC16C554@SSOP20 [SA626A]  
PIC16C556  
PIC16C556@S0IC18 [SA404]  
PIC16C558  
PIC16C558@S0IC18 [SA404]  
PIC16C558@SSOP20 [SA626A]  
PIC16C55A  
PIC16C55A@SSOP28 [SA626A]  
PIC16C56@S0IC18 [SA404]  
PIC16C56A@S0IC18 [SA404]  
PIC16C57  
PIC16C57@SSOP28 [SA626A]  
PIC16C57C@S0IC28 [SA404]  
PIC16C58  
PIC16C58A  
PIC16C58A@SSOP20 [SA626A]  
PIC16C58B@S0IC18 [SA404]  
PIC16C61  
PIC16C61@S0IC18 [SA404]  
PIC16C62  
PIC16C62@S0IC28 [SA404]  
PIC16C62@SSOP28 [SA626A]  
PIC16C620  
PIC16C620@S0IC18 [SA404]  
PIC16C620A  
PIC16C620A@S0IC18 [SA404]  
PIC16C620A@SSOP20 [SA626A]  
PIC16C621  
PIC16C621@S0IC18 [SA404]  
PIC16C621A  
PIC16C621A@S0IC18 [SA404]

PIC16C621A@S0IC18 (ISP)  
PIC16C621A@SSOP20 (ISP)  
PIC16C622 (ISP)  
PIC16C622@S0IC18 (ISP)  
PIC16C622A (ISP)  
PIC16C622A@S0IC18 (ISP)  
PIC16C622A@SSOP20 (ISP)  
PIC16C625 (ISP)  
PIC16C625@S0IC18 (ISP)  
PIC16C62A (ISP)  
PIC16C62A@S0IC28 (ISP)  
PIC16C62A@SSOP28 (ISP)  
PIC16C62B (ISP)  
PIC16C62B@S0IC28 (ISP)  
PIC16C62B@SSOP28 (ISP)  
PIC16C63 (ISP)  
PIC16C63@S0IC28 (ISP)  
PIC16C63A (ISP)  
PIC16C63A@S0IC28 (ISP)  
PIC16C63A@SSOP28 (ISP)  
PIC16C64 (ISP)  
PIC16C64@PLCC44 (ISP)  
PIC16C64@TQFP44 (ISP)  
PIC16C641@S0IC28 [SA404]  
PIC16C642  
PIC16C642@SSOP28 [SA626A]  
PIC16C64A (ISP)  
PIC16C64A@PLCC44 (ISP)  
PIC16C64A@TQFP44 (ISP)  
PIC16C65 (ISP)  
PIC16C65@PLCC44 (ISP)  
PIC16C65@TQFP44 (ISP)  
PIC16C65A (ISP)  
PIC16C65A@PLCC44 (ISP)  
PIC16C65A@TQFP44 (ISP)  
PIC16C65B (ISP)  
PIC16C65B@PLCC44 (ISP)  
PIC16C65B@TQFP44 (ISP)  
PIC16C66 (ISP)  
PIC16C66@S0IC28 (ISP)  
PIC16C661@PLCC44 [SA244]  
PIC16C662  
PIC16C662@TQFP44 [SA245A-B4805]  
PIC16C67 (ISP)  
PIC16C67@PLCC44 (ISP)  
PIC16C67@TQFP44 (ISP)  
PIC16C70 (ISP)  
PIC16C70@S0IC18 (ISP)  
PIC16C71 (ISP)  
PIC16C71@S0IC18 (ISP)  
PIC16C710 (ISP)  
PIC16C710@S0IC18 (ISP)  
PIC16C710@SSOP20 (ISP)  
PIC16C621A@SSOP20 [SA626A]  
PIC16C622  
PIC16C622@S0IC18 [SA404]  
PIC16C622A  
PIC16C622A@S0IC18 [SA404]  
PIC16C622A@SSOP20 [SA626A]  
PIC16C625  
PIC16C625@S0IC18 [SA404]  
PIC16C62A  
PIC16C62A@S0IC28 [SA404]  
PIC16C62A@SSOP28 [SA626A]  
PIC16C62B  
PIC16C62B@S0IC28 [SA404]  
PIC16C62B@SSOP28 [SA626A]  
PIC16C63  
PIC16C63@S0IC28 [SA404]  
PIC16C63A  
PIC16C63A@S0IC28 [SA404]  
PIC16C63A@SSOP28 [SA626A]  
PIC16C64  
PIC16C64@PLCC44 [SA244]  
PIC16C64@TQFP44 [SA245A-B4805]  
PIC16C641  
PIC16C641@SSOP28 [SA626A]  
PIC16C642@S0IC28 [SA404]  
PIC16C64A  
PIC16C64A@PLCC44 [SA244]  
PIC16C64A@TQFP44 [SA245A-B4805]  
PIC16C65  
PIC16C65@PLCC44 [SA244]  
PIC16C65@TQFP44 [SA245A-B4805]  
PIC16C65A  
PIC16C65A@PLCC44 [SA244]  
PIC16C65A@TQFP44 [SA245A-B4805]  
PIC16C65B  
PIC16C65B@PLCC44 [SA244]  
PIC16C65B@TQFP44 [SA245A-B4805]  
PIC16C66  
PIC16C66@S0IC28 [SA404]  
PIC16C661  
PIC16C661@TQFP44 [SA245A-B4805]  
PIC16C662@PLCC44 [SA244]  
PIC16C67  
PIC16C67@PLCC44 [SA244]  
PIC16C67@TQFP44 [SA245A-B4805]  
PIC16C70  
PIC16C70@S0IC18 [SA404]  
PIC16C71  
PIC16C71@S0IC18 [SA404]  
PIC16C710  
PIC16C710@S0IC18 [SA404]  
PIC16C710@SSOP20 [SA626A]  
PIC16C711

PIC16C711 (ISP)  
PIC16C711@S0IC18 (ISP)  
PIC16C711@SSOP20 (ISP)  
PIC16C712 (ISP)  
PIC16C712@S0IC18 (ISP)  
PIC16C712@SSOP20 (ISP)  
PIC16C715@S0IC18 [SA404]  
PIC16C716  
PIC16C716@S0IC18 [SA404]  
PIC16C716@SSOP20 [SA626A]  
PIC16C717  
PIC16C717@S0IC18 [SA404]  
PIC16C717@SSOP20 [SA626A]  
PIC16C71A  
PIC16C71A@S0IC18 [SA404]  
PIC16C72  
PIC16C72@S0IC28 [SA404]  
PIC16C72@SSOP28 [SA626A]  
PIC16C72A  
PIC16C72A@S0IC28 [SA404]  
PIC16C72A@SSOP28 [SA626A]  
PIC16C73  
PIC16C73@S0IC28 [SA404]  
PIC16C73A  
PIC16C73A@S0IC28 [SA404]  
PIC16C73B  
PIC16C73B@S0IC28 [SA404]  
PIC16C73B@SSOP28 [SA626A]  
PIC16C74  
PIC16C74@PLCC44 [SA244]  
PIC16C74@TQFP44 [SA245A-B4805]  
PIC16C745  
PIC16C745@S0IC28 [SA404]  
PIC16C74A  
PIC16C74A@PLCC44 [SA244]  
PIC16C74A@TQFP44 [SA245A-B4805]  
PIC16C74B  
PIC16C74B@MQFP44 [SA675-B4805]  
PIC16C74B@PLCC44 [SA244]  
PIC16C74B@TQFP44 [SA245A-B4805]  
PIC16C76  
PIC16C76@S0IC28 [SA404]  
PIC16C765  
PIC16C765@PLCC44 [SA244]  
PIC16C765@TQFP44 [SA245A-B4805]  
PIC16C77  
PIC16C77@PLCC44 [SA244]  
PIC16C77@TQFP44 [SA245A-B4805]  
PIC16C770  
PIC16C770@S0IC20 [SA404]  
PIC16C770@SSOP20 [SA626A]  
PIC16C771  
PIC16C771@S0IC20 [SA404]

PIC16C711@S0IC18 [SA404]  
PIC16C711@SSOP20 [SA626A]  
PIC16C712  
PIC16C712@S0IC18 [SA404]  
PIC16C712@SSOP20 [SA626A]  
PIC16C715  
PIC16C715@SSOP20 [SA626A]  
PIC16C716 (ISP)  
PIC16C716@S0IC18 (ISP)  
PIC16C716@SSOP20 (ISP)  
PIC16C717 (ISP)  
PIC16C717@S0IC18 (ISP)  
PIC16C717@SSOP20 (ISP)  
PIC16C71A (ISP)  
PIC16C71A@S0IC18 (ISP)  
PIC16C72 (ISP)  
PIC16C72@S0IC28 (ISP)  
PIC16C72@SSOP28 (ISP)  
PIC16C72A (ISP)  
PIC16C72A@S0IC28 (ISP)  
PIC16C72A@SSOP28 (ISP)  
PIC16C73 (ISP)  
PIC16C73@S0IC28 (ISP)  
PIC16C73A (ISP)  
PIC16C73A@S0IC28 (ISP)  
PIC16C73B (ISP)  
PIC16C73B@S0IC28 (ISP)  
PIC16C73B@SSOP28 (ISP)  
PIC16C74 (ISP)  
PIC16C74@PLCC44 (ISP)  
PIC16C74@TQFP44 (ISP)  
PIC16C745 (ISP)  
PIC16C745@S0IC28 (ISP)  
PIC16C74A (ISP)  
PIC16C74A@PLCC44 (ISP)  
PIC16C74A@TQFP44 (ISP)  
PIC16C74B (ISP)  
PIC16C74B@MQFP44 (ISP)  
PIC16C74B@PLCC44 (ISP)  
PIC16C74B@TQFP44 (ISP)  
PIC16C76 (ISP)  
PIC16C76@S0IC28 (ISP)  
PIC16C765 (ISP)  
PIC16C765@PLCC44 (ISP)  
PIC16C765@TQFP44 (ISP)  
PIC16C77 (ISP)  
PIC16C77@PLCC44 (ISP)  
PIC16C77@TQFP44 (ISP)  
PIC16C770 (ISP)  
PIC16C770@S0IC20 (ISP)  
PIC16C770@SSOP20 (ISP)  
PIC16C771 (ISP)  
PIC16C771@S0IC20 (ISP)

PIC16C771@SSOP20 [SA626A]	PIC16C771@SSOP20 (ISP)
PIC16C773	PIC16C773 (ISP)
PIC16C773@S0IC28 [SA404]	PIC16C773@S0IC28 (ISP)
PIC16C773@SSOP28 [SA626A]	PIC16C773@SSOP28 (ISP)
PIC16C774	PIC16C774 (ISP)
PIC16C774@PLCC44 [SA244]	PIC16C774@PLCC44 (ISP)
PIC16C774@TQFP44 [SA245A-B4805]	PIC16C774@TQFP44 (ISP)
PIC16C781	PIC16C781 (ISP)
PIC16C781@S0IC20 [SA404]	PIC16C781@S0IC20 (ISP)
PIC16C781@SSOP20 [SA626A]	PIC16C781@SSOP20 (ISP)
PIC16C782	PIC16C782 (ISP)
PIC16C782@S0IC20 [SA404]	PIC16C782@S0IC20 (ISP)
PIC16C782@SSOP20 [SA626A]	PIC16C782@SSOP20 (ISP)
PIC16C84	PIC16C84 (ISP)
PIC16C84@S0IC18 [SA404]	PIC16C84@S0IC18 (ISP)
PIC16C923@PLCC68 (ISP)	PIC16C923@SDIP64 (ISP)
PIC16C923@TQFP64 (ISP)	PIC16C924@PLCC68 (ISP)
PIC16C924@SDIP64 (ISP)	PIC16C924@TQFP64 (ISP)
PIC16C925@PLCC68 (ISP)	PIC16C925@TQFP64 (ISP)
PIC16C926@PLCC68 (ISP)	PIC16C926@TQFP64 (ISP)
PIC16CE623	PIC16CE623 (ISP)
PIC16CE623@S0IC18 [SA404]	PIC16CE623@S0IC18 (ISP)
PIC16CE624	PIC16CE624 (ISP)
PIC16CE624@S0IC18 [SA404]	PIC16CE624@S0IC18 (ISP)
PIC16CE625	PIC16CE625 (ISP)
PIC16CE625@S0IC18 [SA404]	PIC16CE625@S0IC18 (ISP)
PIC16CE625@SSOP20 [SA626A]	PIC16CE625@SSOP20 (ISP)
PIC16CR83	PIC16CR83 (ISP)
PIC16CR83@S0IC18 [SA404]	PIC16CR83@S0IC18 (ISP)
PIC16CR84	PIC16CR84 (ISP)
PIC16CR84@S0IC18 [SA404]	PIC16CR84@S0IC18 (ISP)
PIC16F1454	PIC16F1454 (ISP)
PIC16F1454@QFN16 [SA727]	PIC16F1454@S0IC14 [SA602]
PIC16F1454@TSSOP14 [SA026]	PIC16F1455
PIC16F1455 (ISP)	PIC16F1455@QFN16 [SA727]
PIC16F1455@S0IC14 [SA602]	PIC16F1455@TSSOP14 [SA026]
PIC16F1458	PIC16F1458 (ISP)
PIC16F1458@QFN20 [SA692]	PIC16F1458@S0IC20 [SA404]
PIC16F1458@SSOP20 [SA626A]	PIC16F1459
PIC16F1459 (ISP)	PIC16F1459@QFN20 [SA692]
PIC16F1459@S0IC20 [SA404]	PIC16F1459@SSOP20 [SA626A]
PIC16F1503	PIC16F1503 (ISP)
PIC16F1503@QFN16 [SA743]	PIC16F1503@QFN16 (ISP)
PIC16F1503@S0IC14 [SA602]	PIC16F1503@S0IC14 (ISP)
PIC16F1503@TSSOP14 [SA643]	PIC16F1503@TSSOP14 (ISP)
PIC16F1507	PIC16F1507 (ISP)
PIC16F1507@QFN20 [SA692]	PIC16F1507@QFN20 (ISP)
PIC16F1507@S0IC20 [SA404]	PIC16F1507@S0IC20 (ISP)
PIC16F1507@SSOP20 [SA626A]	PIC16F1507@SSOP20 (ISP)
PIC16F1508	PIC16F1508 (ISP)
PIC16F1508@QFN20 [SA692]	PIC16F1508@QFN20 (ISP)
PIC16F1508@S0IC20 [SA404]	PIC16F1508@S0IC20 (ISP)
PIC16F1508@SSOP20 [SA626A]	PIC16F1508@SSOP20 (ISP)

PIC16F1509  
PIC16F1509@QFN20 [SA692]  
PIC16F1509@SOIC20 [SA404]  
PIC16F1509@SSOP20 [SA626A]  
PIC16F1512  
PIC16F1512@SOIC28 [SA404]  
PIC16F1512@SSOP28 [SA626A]  
PIC16F1512@UQFN28 [\$\$\$\$\$]  
PIC16F1513  
PIC16F1513@SOIC28 [SA404]  
PIC16F1513@SSOP28 [SA626A]  
PIC16F1513@UQFN28 [\$\$\$\$\$]  
PIC16F1516  
PIC16F1516@SOIC28 [SA404]  
PIC16F1516@SSOP28 [SA626A]  
PIC16F1516@UQFN28 [\$\$\$\$\$]  
PIC16F1517  
PIC16F1517@TQFP44 [SA245A-B4805]  
PIC16F1517@UQFN40 [\$\$\$\$\$]  
PIC16F1518  
PIC16F1518@SOIC28 [SA404]  
PIC16F1518@SSOP28 [SA626A]  
PIC16F1518@UQFN28 [\$\$\$\$\$]  
PIC16F1519  
PIC16F1519@TQFP44 [SA245A-B4805]  
PIC16F1519@UQFN40 [\$\$\$\$\$]  
PIC16F1526@QFN64 (ISP)  
PIC16F1527@QFN64 (ISP)  
PIC16F1574  
PIC16F1574@QFN16 [SA743]  
PIC16F1574@TSSOP14 [SA026]  
PIC16F1575@ISP  
PIC16F1575-S14 [SA602]  
PIC16F1578  
PIC16F1578-Q20 [SA692]  
PIC16F1578-SS20 [SA626A]  
PIC16F1579@ISP  
PIC16F1579-S20 [SA404]  
PIC16F1703@ISP  
PIC16F1703@SOIC14 [SA602]  
PIC16F1704  
PIC16F1704@QFN16 [SA743]  
PIC16F1704@TSSOP14 [SA026]  
PIC16F1705@ISP  
PIC16F1705@SOIC14 [SA602]  
PIC16F1707  
PIC16F1707@QFN20 [SA692]  
PIC16F1707@SSOP20 [SA626A]  
PIC16F1708@ISP  
PIC16F1708@SOIC20 [SA404]  
PIC16F1709  
PIC16F1709@QFN20 [SA692]  
PIC16F1709@SSOP20 [SA626A]

PIC16F1509 (ISP)  
PIC16F1509@QFN20 (ISP)  
PIC16F1509@SOIC20 (ISP)  
PIC16F1509@SSOP20 (ISP)  
PIC16F1512 (ISP)  
PIC16F1512@SOIC28 (ISP)  
PIC16F1512@SSOP28 (ISP)  
PIC16F1512@UQFN28 (ISP)  
PIC16F1513 (ISP)  
PIC16F1513@SOIC28 (ISP)  
PIC16F1513@SSOP28 (ISP)  
PIC16F1513@UQFN28 (ISP)  
PIC16F1516 (ISP)  
PIC16F1516@SOIC28 (ISP)  
PIC16F1516@SSOP28 (ISP)  
PIC16F1516@UQFN28 (ISP)  
PIC16F1517 (ISP)  
PIC16F1517@TQFP44 (ISP)  
PIC16F1517@UQFN40 (ISP)  
PIC16F1518 (ISP)  
PIC16F1518@SOIC28 (ISP)  
PIC16F1518@SSOP28 (ISP)  
PIC16F1518@UQFN28 (ISP)  
PIC16F1519 (ISP)  
PIC16F1519@TQFP44 (ISP)  
PIC16F1519@UQFN40 (ISP)  
PIC16F1526@TQFP64 (ISP)  
PIC16F1527@TQFP64 (ISP)  
PIC16F1574@ISP  
PIC16F1574@SOIC14 [SA602]  
PIC16F1575  
PIC16F1575-Q16 [SA743]  
PIC16F1575-T14 [SA026]  
PIC16F1578@ISP  
PIC16F1578-S20 [SA404]  
PIC16F1579  
PIC16F1579-Q20 [SA692]  
PIC16F1579-SS20 [SA626A]  
PIC16F1703@QFN16 [SA743]  
PIC16F1703@TSSOP14 [SA026]  
PIC16F1704@ISP  
PIC16F1704@SOIC14 [SA602]  
PIC16F1705  
PIC16F1705@QFN16 [SA743]  
PIC16F1705@TSSOP14 [SA026]  
PIC16F1707@ISP  
PIC16F1707@SOIC20 [SA404]  
PIC16F1708  
PIC16F1708@QFN20 [SA692]  
PIC16F1708@SSOP20 [SA626A]  
PIC16F1709@ISP  
PIC16F1709@SOIC20 [SA404]  
PIC16F1782

PIC16F1782 (ISP)	PIC16F1782@SOIC28 [SA404]
PIC16F1782@SOIC28 (ISP)	PIC16F1782@SSOP28 [SA626A]
PIC16F1782@SSOP28 (ISP)	PIC16F1782@UQFN28 [SA685]
PIC16F1782@UQFN28 (ISP)	PIC16F1783
PIC16F1783 (ISP)	PIC16F1783@SOIC28 [SA404]
PIC16F1783@SOIC28 (ISP)	PIC16F1783@SSOP28 [SA626A]
PIC16F1783@SSOP28 (ISP)	PIC16F1783@UQFN28 [SA685]
PIC16F1783@UQFN28 (ISP)	PIC16F1784
PIC16F1784 (ISP)	PIC16F1784@QFN44 [SA737]
PIC16F1784@TQFP44 [SA245A-B4805]	PIC16F1784@UQFN40
PIC16F1786	PIC16F1786 (ISP)
PIC16F1786@QFN28 [SA685]	PIC16F1786@SOIC28 [SA404]
PIC16F1786@SSOP28 [SA626A]	PIC16F1787
PIC16F1787 (ISP)	PIC16F1787@QFN44 [SA737]
PIC16F1787@TQFP44 [SA245A-B4805]	PIC16F1787@UQFN40
PIC16F1788	PIC16F1788 (ISP)
PIC16F1788@QFN28 [SA685]	PIC16F1788@SOIC28 [SA404]
PIC16F1788@SSOP28 [SA626A]	PIC16F1789
PIC16F1789 (ISP)	PIC16F1789@QFN44 [SA737]
PIC16F1789@TQFP44 [SA245A-B4805]	PIC16F1789@UQFN40
PIC16F1823	PIC16F1823 (8-word)
PIC16F1823 (ISP) (HV)	PIC16F1823 (LV)
PIC16F1823 (LVISP)	PIC16F1823@QFN16 (3*3) [SA743]
PIC16F1823@QFN16 (3*3) (8-word) [SA743]	
PIC16F1823@QFN16 (3*3) (ISP) (HV)	
PIC16F1823@QFN16 (3*3) (LV) [SA743]	
PIC16F1823@QFN16 (4*4) [SA727]	
PIC16F1823@QFN16 (4*4) (8-word) [SA727]	
PIC16F1823@QFN16 (4*4) (ISP) (HV)	
PIC16F1823@QFN16 (4*4) (LV) [SA727]	
PIC16F1823@SOIC14 [SA602]	
PIC16F1823@SOIC14 (8-word) [SA602]	
PIC16F1823@SOIC14 (ISP) (HV)	PIC16F1823@SOIC14 (LV) [SA602]
PIC16F1823@TSSOP14 [SA643]	
PIC16F1823@TSSOP14 (8-word) [SA643]	
PIC16F1823@TSSOP14 (ISP) (HV)	PIC16F1823@TSSOP14 (LV) [SA026]
PIC16F1824	PIC16F1824 (8-word)
PIC16F1824 (ISP) (HV)	PIC16F1824 (LV)
PIC16F1824 (LVISP)	PIC16F1824@QFN16 (3*3) [SA743]
PIC16F1824@QFN16 (3*3) (8-word) [SA743]	
PIC16F1824@QFN16 (3*3) (ISP) (HV)	
PIC16F1824@QFN16 (3*3) (LV) [SA743]	
PIC16F1824@QFN16 (4*4) [SA727]	
PIC16F1824@QFN16 (4*4) (8-word) [SA727]	
PIC16F1824@QFN16 (4*4) (ISP) (HV)	
PIC16F1824@QFN16 (4*4) (LV) [SA727]	
PIC16F1824@SOIC14 [SA602]	
PIC16F1824@SOIC14 (8-word) [SA602]	
PIC16F1824@SOIC14 (ISP) (HV)	PIC16F1824@SOIC14 (LV) [SA602]
PIC16F1824@TSSOP14 [SA643]	
PIC16F1824@TSSOP14 (8-word) [SA643]	
PIC16F1824@TSSOP14 (ISP) (HV)	PIC16F1824@TSSOP14 (LV) [SA026]
PIC16F1825	PIC16F1825 (8-word)

PIC16F1825 (ISP) (HV)	PIC16F1825 (LV)
PIC16F1825 (LVISP)	PIC16F1825@QFN16 (3*3) [SA743]
PIC16F1825@QFN16 (3*3) (8-word) [SA743]	
PIC16F1825@QFN16 (3*3) (ISP) (HV)	
PIC16F1825@QFN16 (3*3) (LV) [SA743]	
PIC16F1825@QFN16 (4*4) [SA727]	
PIC16F1825@QFN16 (4*4) (8-word) [SA727]	
PIC16F1825@QFN16 (4*4) (ISP) (HV)	
PIC16F1825@QFN16 (4*4) (LV) [SA727]	
PIC16F1825@SOIC14 [SA602]	
PIC16F1825@SOIC14 (8-word) [SA602]	
PIC16F1825@SOIC14 (ISP) (HV)	PIC16F1825@SOIC14 (LV) [SA602]
PIC16F1825@TSSOP14 [SA643]	
PIC16F1825@TSSOP14 (8-word) [SA643]	
PIC16F1825@TSSOP14 (ISP) (HV)	PIC16F1825@TSSOP14 (LV) [SA026]
PIC16F1826	PIC16F1826 (8-word)
PIC16F1826 (ISP) (HV)	PIC16F1826 (LV)
PIC16F1826 (LVISP)	PIC16F1826@QFN28 [SA685]
PIC16F1826@QFN28 (8-word) [SA685]	PIC16F1826@QFN28 (ISP) (HV)
PIC16F1826@QFN28 (LV) [SA685]	PIC16F1826@SOIC18 [SA404]
PIC16F1826@SOIC18 (8-word) [SA404]	
PIC16F1826@SOIC18 (ISP) (HV)	PIC16F1826@SOIC18 (LV) [SA404]
PIC16F1826@SSOP20 [SA626A]	
PIC16F1826@SSOP20 (8-word) [SA626A]	
PIC16F1826@SSOP20 (ISP) (HV)	PIC16F1826@SSOP20 (LV) [SA626A]
PIC16F1826@UQFN28 [\$\$\$\$\$]	
PIC16F1826@UQFN28 (8-word) [\$\$\$\$\$]	
PIC16F1827	PIC16F1827 (8-word)
PIC16F1827 (ISP) (HV)	PIC16F1827 (LV)
PIC16F1827 (LVISP)	PIC16F1827@QFN28 [SA685]
PIC16F1827@QFN28 (8-word) [SA685]	PIC16F1827@QFN28 (ISP) (HV)
PIC16F1827@QFN28 (LV) [SA685]	PIC16F1827@SOIC18 [SA404]
PIC16F1827@SOIC18 (8-word) [SA404]	
PIC16F1827@SOIC18 (ISP) (HV)	PIC16F1827@SOIC18 (LV) [SA404]
PIC16F1827@SSOP20 [SA626A]	
PIC16F1827@SSOP20 (8-word) [SA626A]	
PIC16F1827@SSOP20 (ISP) (HV)	PIC16F1827@SSOP20 (LV) [SA626A]
PIC16F1827@UQFN28 [\$\$\$\$\$]	
PIC16F1827@UQFN28 (8-word) [\$\$\$\$\$]	
PIC16F1828	PIC16F1828 (8-word)
PIC16F1828 (ISP) (HV)	PIC16F1828 (LV)
PIC16F1828 (LVISP)	PIC16F1828@QFN20 [SA692]
PIC16F1828@QFN20 (8-word) [SA692]	PIC16F1828@QFN20 (ISP) (HV)
PIC16F1828@QFN20 (LV) [SA692]	PIC16F1828@SOIC20 [SA404]
PIC16F1828@SOIC20 (8-word) [SA404]	
PIC16F1828@SOIC20 (ISP) (HV)	PIC16F1828@SOIC20 (LV) [SA404]
PIC16F1828@TSSOP20 [SA626A]	
PIC16F1828@TSSOP20 (8-word) [SA626A]	
PIC16F1828@TSSOP20 (ISP) (HV)	PIC16F1828@TSSOP20 (LV) [SA626A]
PIC16F1829	PIC16F1829 (8-word)
PIC16F1829 (ISP) (HV)	PIC16F1829 (LV)
PIC16F1829 (LVISP)	PIC16F1829@QFN20 [SA692]
PIC16F1829@QFN20 (8-word) [SA692]	PIC16F1829@QFN20 (ISP) (HV)

PIC16F1829@QFN20 (LV) [SA692]	PIC16F1829@SOIC20 [SA404]
PIC16F1829@SOIC20 (8-word) [SA404]	
PIC16F1829@SOIC20 (ISP) (HV)	PIC16F1829@SOIC20 (LV) [SA404]
PIC16F1829@TSSOP20 [SA626A]	
PIC16F1829@TSSOP20 (8-word) [SA626A]	
PIC16F1829@TSSOP20 (ISP) (HV)	PIC16F1829@TSSOP20 (LV) [SA626A]
PIC16F1847	PIC16F1847 (ISP) (HV)
PIC16F1847@QFN28 [SA685]	PIC16F1847@QFN28 (ISP) (HV)
PIC16F1847@SOIC18 [SA404]	PIC16F1847@SOIC18 (ISP) (HV)
PIC16F1847@SSOP20 [SA626A]	PIC16F1847@SSOP20 (ISP) (HV)
PIC16F1847E	PIC16F1847E@QFN28 [SA685]
PIC16F1847E@SOIC18 [SA404]	PIC16F1847E@SSOP20 [SA626A]
PIC16F1933	PIC16F1933 (ISP) (HV)
PIC16F1933@QFN28 [SA685]	PIC16F1933@QFN28 (ISP) (HV)
PIC16F1933@QFN28[8-word pro] [SA685]	
PIC16F1933@SOIC28 [SA404]	PIC16F1933@SOIC28 (ISP) (HV)
PIC16F1933@SOIC28[8-word pro] [SA404]	
PIC16F1933@SSOP28 [SA626A]	PIC16F1933@SSOP28 (ISP) (HV)
PIC16F1933@SSOP28[8-word pro] [SA626A]	
PIC16F1933@UQFN28 [\$\$\$\$\$]	PIC16F1933[8-word pro]
PIC16F1934	PIC16F1934 (ISP) (HV)
PIC16F1934@QFN44 [SA737]	PIC16F1934@QFN44 (ISP) (HV)
PIC16F1934@QFN44[8-word pro] [SA737]	
PIC16F1934@TQFP44 [SA245A-B4805]	PIC16F1934@TQFP44 (ISP) (HV)
PIC16F1934@TQFP44[8-word pro] [SA245A-B4805]	
PIC16F1934[8-word pro]	PIC16F1936
PIC16F1936 (ISP) (HV)	PIC16F1936@QFN28 [SA685]
PIC16F1936@QFN28 (ISP) (HV)	
PIC16F1936@QFN28[8-word pro] [SA685]	
PIC16F1936@SOIC28 [SA404]	PIC16F1936@SOIC28 (ISP) (HV)
PIC16F1936@SOIC28[8-word pro] [SA404]	
PIC16F1936@SSOP28 [SA626A]	PIC16F1936@SSOP28 (ISP) (HV)
PIC16F1936@SSOP28[8-word pro] [SA626A]	
PIC16F1936@UQFN28 [\$\$\$\$\$]	PIC16F1936[8-word pro]
PIC16F1937	PIC16F1937 (ISP) (HV)
PIC16F1937@QFN44 [SA737]	PIC16F1937@QFN44 (ISP) (HV)
PIC16F1937@QFN44[8-word pro] [SA737]	
PIC16F1937@TQFP44 [SA245A-B4805]	PIC16F1937@TQFP44 (ISP) (HV)
PIC16F1937@TQFP44[8-word pro] [SA245A-B4805]	
PIC16F1937[8-word pro]	PIC16F1938
PIC16F1938 (ISP) (HV)	PIC16F1938@QFN28 [SA685]
PIC16F1938@QFN28 (ISP) (HV)	
PIC16F1938@QFN28[8-word pro] [SA685]	
PIC16F1938@SOIC28 [SA404]	PIC16F1938@SOIC28 (ISP) (HV)
PIC16F1938@SOIC28[8-word pro] [SA404]	
PIC16F1938@SSOP28 [SA626A]	PIC16F1938@SSOP28 (ISP) (HV)
PIC16F1938@SSOP28[8-word pro] [SA626A]	
PIC16F1938[8-word pro]	PIC16F1939
PIC16F1939 (ISP) (HV)	PIC16F1939@QFN44 (ISP) (HV)
PIC16F1939@TQFP44 [SA245A-B4805]	PIC16F1939@TQFP44 (ISP) (HV)
PIC16F1939@TQFP44[8-word pro] [SA245A-B4805]	
PIC16F1946@QFN64 (ISP) (HV)	PIC16F1946@TQFP64 (ISP) (HV)
PIC16F1947@QFN64 (ISP) (HV)	PIC16F1947@TQFP64 (ISP) (HV)

PIC16F505  
PIC16F505@SOIC14 [SA602]  
PIC16F505@TSSOP14 [SA026]  
PIC16F506  
PIC16F506@SOIC14 [SA602]  
PIC16F506@TSSOP14 [SA643]  
PIC16F526  
PIC16F526@SOIC14 [SA602]  
PIC16F526@TSSOP14 [SA026]  
PIC16F527  
PIC16F527@QFN20 [SA692]  
PIC16F527@SSOP20 [SA626A]  
PIC16F54 (ISP)  
PIC16F54@SOIC18 (ISP)  
PIC16F54@SSOP20 (ISP)  
PIC16F57 (ISP)  
PIC16F57@SOIC28 (ISP)  
PIC16F57@SSOP28 (ISP)  
PIC16F59 (ISP)  
PIC16F59@PLCC44 (ISP)  
PIC16F59@TQFP44 (ISP)  
PIC16F610 (ISP)  
PIC16F610@QFN16 (ISP)  
PIC16F610@SOIC14 (ISP)  
PIC16F610@TSSOP14 (ISP)  
PIC16F616 (ISP)  
PIC16F616@QFN16 (ISP)  
PIC16F616@SOIC14 (ISP)  
PIC16F616@TSSOP14 (ISP)  
PIC16F627 (ISP)  
PIC16F627@SOIC18 (ISP)  
PIC16F627@SSOP20 (ISP)  
PIC16F627A (ISP)  
PIC16F627A@SOIC18 (ISP)  
PIC16F627A@SSOP20 (ISP)  
PIC16F628 (ISP)  
PIC16F628@SOIC18 (ISP)  
PIC16F628@SSOP20 (ISP)  
PIC16F628A (ISP)  
PIC16F628A@SOIC18 (ISP)  
PIC16F628A@SSOP20 (ISP)  
PIC16F630 (ISP)  
PIC16F630@SOIC14 (ISP)  
PIC16F630@TSSOP14 (ISP)  
PIC16F631 (ISP)  
PIC16F631@QFN20 (ISP)  
PIC16F631@SOIC20 (ISP)  
PIC16F631@SSOP20 (ISP)  
PIC16F636 (4-WORD PRO)  
PIC16F636@QFN16 [SA727]  
PIC16F636@QFN16 (4-WORD PRO) [SA727]  
PIC16F636@QFN16 (ISP)  
PIC16F636@SOIC14 (4-WORD PRO) [SA602]

PIC16F505 (ISP)  
PIC16F505@SOIC14 (ISP)  
PIC16F505@TSSOP14 (ISP)  
PIC16F506 (ISP)  
PIC16F506@SOIC14 (ISP)  
PIC16F506@TSSOP14 (ISP)  
PIC16F526 (ISP)  
PIC16F526@SOIC14 (ISP)  
PIC16F526@TSSOP14 (ISP)  
PIC16F527 (ISP)  
PIC16F527@SOIC20 [SA404]  
PIC16F54  
PIC16F54@SOIC18 [SA404]  
PIC16F54@SSOP20 [SA626A]  
PIC16F57  
PIC16F57@SOIC28 [SA404]  
PIC16F57@SSOP28 [SA626A]  
PIC16F59  
PIC16F59@PLCC44 [SA244]  
PIC16F59@TQFP44 [SA245A-B4805]  
PIC16F610  
PIC16F610@QFN16 [SA727]  
PIC16F610@SOIC14 [SA602]  
PIC16F610@TSSOP14 [SA026]  
PIC16F616  
PIC16F616@QFN16 [SA727]  
PIC16F616@SOIC14 [SA602]  
PIC16F616@TSSOP14 [SA026]  
PIC16F627  
PIC16F627@SOIC18 [SA404]  
PIC16F627@SSOP20 [SA626A]  
PIC16F627A  
PIC16F627A@SOIC18 [SA404]  
PIC16F627A@SSOP20 [SA626A]  
PIC16F628  
PIC16F628@SOIC18 [SA404]  
PIC16F628@SSOP20 [SA626A]  
PIC16F628A  
PIC16F628A@SOIC18 [SA404]  
PIC16F628A@SSOP20 [SA626A]  
PIC16F630  
PIC16F630@SOIC14 [SA602]  
PIC16F630@TSSOP14 [SA026]  
PIC16F631  
PIC16F631@QFN20 [SA692]  
PIC16F631@SOIC20 [SA404]  
PIC16F631@SSOP20 [SA626A]  
PIC16F636  
PIC16F636 (ISP)  
PIC16F636@SOIC14 [SA602]

PIC16F636@SOIC14 (ISP)	PIC16F636@TSSOP14 [SA026]
PIC16F636@TSSOP14 (4-WORD PRO) [SA026]	
PIC16F636@TSSOP14 (ISP)	PIC16F639
PIC16F639 (ISP)	PIC16F639@QFN20 [SA692]
PIC16F639@QFN20 (ISP)	PIC16F639@SOIC20 [SA404]
PIC16F639@SOIC20 (ISP)	PIC16F639@SSOP20 [SA626A]
PIC16F639@SSOP20 (ISP)	PIC16F648A
PIC16F648A (ISP)	PIC16F648A@SOIC18 [SA404]
PIC16F648A@SOIC18 (ISP)	PIC16F648A@SSOP20 [SA626A]
PIC16F648A@SSOP20 (ISP)	PIC16F676
PIC16F676 (ISP)	PIC16F676@SOIC14 [SA602]
PIC16F676@SOIC14 (ISP)	PIC16F676@TSSOP14 [SA026]
PIC16F676@TSSOP14 (ISP)	PIC16F677
PIC16F677 (ISP)	PIC16F677@QFN20 [SA692]
PIC16F677@QFN20 (ISP)	PIC16F677@SOIC20 [SA404]
PIC16F677@SOIC20 (ISP)	PIC16F677@SSOP20 [SA626A]
PIC16F677@SSOP20 (ISP)	PIC16F684
PIC16F684 (4-WORD PRO)	PIC16F684 (ISP)
PIC16F684@QFN16 [SA727]	
PIC16F684@QFN16 (4-WORD PRO) [SA727]	
PIC16F684@QFN16 (ISP)	PIC16F684@SOIC14 [SA602]
PIC16F684@SOIC14 (4-WORD PRO) [SA602]	
PIC16F684@SOIC14 (ISP)	PIC16F684@TSSOP14 [SA026]
PIC16F684@TSSOP14 (4-WORD PRO) [SA026]	
PIC16F684@TSSOP14 (ISP)	PIC16F685
PIC16F685 (ISP)	PIC16F685@QFN20 [SA692]
PIC16F685@QFN20 (ISP)	PIC16F685@SOIC20 [SA404]
PIC16F685@SOIC20 (ISP)	PIC16F685@SSOP20 [SA626A]
PIC16F685@SSOP20 (ISP)	PIC16F687
PIC16F687 (ISP)	PIC16F687@QFN20 [SA692]
PIC16F687@QFN20 (ISP)	PIC16F687@SOIC20 [SA404]
PIC16F687@SOIC20 (ISP)	PIC16F687@SSOP20 [SA626A]
PIC16F687@SSOP20 (ISP)	PIC16F688
PIC16F688 (4-WORD PRO)	PIC16F688 (ISP)
PIC16F688@QFN16 [SA727]	
PIC16F688@QFN16 (4-WORD PRO) [SA727]	
PIC16F688@QFN16 (ISP)	PIC16F688@SOIC14 [SA602]
PIC16F688@SOIC14 (4-WORD PRO) [SA602]	
PIC16F688@SOIC14 (ISP)	PIC16F688@TSSOP14 [SA026]
PIC16F688@TSSOP14 (4-WORD PRO) [SA026]	
PIC16F688@TSSOP14 (ISP)	PIC16F689
PIC16F689 (ISP)	PIC16F689@QFN20 [SA692]
PIC16F689@QFN20 (ISP)	PIC16F689@SOIC20 [SA404]
PIC16F689@SOIC20 (ISP)	PIC16F689@SSOP20 [SA626A]
PIC16F689@SSOP20 (ISP)	PIC16F690
PIC16F690 (ISP)	PIC16F690@QFN20 [SA692]
PIC16F690@QFN20 (ISP)	PIC16F690@SOIC20 [SA404]
PIC16F690@SOIC20 (ISP)	PIC16F690@SSOP20 [SA626A]
PIC16F690@SSOP20 (ISP)	
PIC16F690@SSOP20 (REVERSE) [SA626A]	
PIC16F707	PIC16F707 (ISP)
PIC16F707@QFN44 [SA737]	PIC16F707@QFN44 (ISP)
PIC16F707@TQFP44 [SA245A-B4805]	PIC16F707@TQFP44 (ISP)

PIC16F716	PIC16F716 (4-WORD PRO)
PIC16F716 (ISP)	PIC16F716@SOIC18 [SA404]
PIC16F716@SOIC18 (4-WORD PRO) [SA404]	
PIC16F716@SOIC18 (ISP)	PIC16F716@SSOP20 [SA626A]
PIC16F716@SSOP20 (4-WORD PRO) [SA626A]	
PIC16F716@SSOP20 (ISP)	PIC16F72
PIC16F72 (ISP)	PIC16F72@QFN28 [SA685]
PIC16F72@QFN28 (ISP)	PIC16F72@SOIC28 [SA404]
PIC16F72@SOIC28 (ISP)	PIC16F72@SSOP28 [SA626A]
PIC16F72@SSOP28 (ISP)	PIC16F720
PIC16F720@QFN20 [SA692]	PIC16F720@SOIC20 [SA404]
PIC16F720@SSOP20 [SA626A]	PIC16F721
PIC16F721@QFN20 [SA692]	PIC16F721@SOIC20 [SA404]
PIC16F721@SSOP20 [SA626A]	PIC16F722
PIC16F722 (ISP)	PIC16F722@QFN28 [SA685]
PIC16F722@QFN28 (ISP)	PIC16F722@SOIC28 [SA404]
PIC16F722@SOIC28 (ISP)	PIC16F722@SSOP28 [SA626A]
PIC16F722@SSOP28 (ISP)	PIC16F722A
PIC16F722A (ISP)	PIC16F722A@QFN28 [SA685]
PIC16F722A@QFN28 (ISP)	PIC16F722A@SOIC28 [SA404]
PIC16F722A@SOIC28 (ISP)	PIC16F722A@SSOP28 [SA626A]
PIC16F722A@SSOP28 (ISP)	PIC16F723
PIC16F723 (ISP)	PIC16F723@QFN28 [SA685]
PIC16F723@QFN28 (ISP)	PIC16F723@SOIC28 [SA404]
PIC16F723@SOIC28 (ISP)	PIC16F723@SSOP28 [SA626A]
PIC16F723@SSOP28 (ISP)	PIC16F723A
PIC16F723A (ISP)	PIC16F723A@QFN28 [SA685]
PIC16F723A@QFN28 (ISP)	PIC16F723A@SOIC28 [SA404]
PIC16F723A@SOIC28 (ISP)	PIC16F723A@SSOP28 [SA626A]
PIC16F723A@SSOP28 (ISP)	PIC16F724
PIC16F724 (ISP)	PIC16F724@QFN44 [SA737]
PIC16F724@QFN44 (ISP)	PIC16F724@TQFP44 [SA245A-B4805]
PIC16F724@TQFP44 (ISP)	PIC16F726
PIC16F726 (ISP)	PIC16F726@QFN28 [SA685]
PIC16F726@QFN28 (ISP)	PIC16F726@SOIC28 [SA404]
PIC16F726@SOIC28 (ISP)	PIC16F726@SSOP28 [SA626A]
PIC16F726@SSOP28 (ISP)	PIC16F727
PIC16F727 (ISP)	PIC16F727@QFN44 [SA737]
PIC16F727@QFN44 (ISP)	PIC16F727@TQFP44 [SA245A-B4805]
PIC16F727@TQFP44 (ISP)	PIC16F73
PIC16F73 (ISP)	PIC16F73@QFN28 [SA685]
PIC16F73@SOIC28 [SA404]	PIC16F73@SOIC28 (ISP)
PIC16F73@SSOP28 [SA626A]	PIC16F73@SSOP28 (ISP)
PIC16F737	PIC16F737 (ISP)
PIC16F737@SOIC28 [SA404]	PIC16F737@SOIC28 (ISP)
PIC16F737@SSOP28 [SA626A]	PIC16F737@SSOP28 (ISP)
PIC16F74	PIC16F74 (ISP)
PIC16F74@PLCC44 [SA244]	PIC16F74@PLCC44 (ISP)
PIC16F74@TQFP44 [SA245A-B4805]	PIC16F74@TQFP44 (ISP)
PIC16F747	PIC16F747 (ISP)
PIC16F747@TQFP44 [SA245A-B4805]	PIC16F747@TQFP44 (ISP)
PIC16F753	PIC16F753 (ISP)
PIC16F753@SOIC14 [SA602]	PIC16F753@TSSOP14 [SA643]

PIC16F76  
PIC16F76@QFN28 [SA685]  
PIC16F76@S0IC28 (ISP)  
PIC16F76@SSOP28 (ISP)  
PIC16F767 (ISP)  
PIC16F767@S0IC28 (ISP)  
PIC16F767@SSOP28 (ISP)  
PIC16F77 (ISP)  
PIC16F77@PLCC44 (ISP)  
PIC16F77@TQFP44 (ISP)  
PIC16F777 (ISP)  
PIC16F777@TQFP44 (ISP)  
PIC16F785 (ISP)  
PIC16F785@QFN20 (ISP)  
PIC16F785@S0IC20 (ISP)  
PIC16F785@SSOP20 (ISP)  
PIC16F818 (ISP)  
PIC16F818@QFN28 (ISP)  
PIC16F818@S0IC18 (ISP)  
PIC16F818@SSOP20 (ISP)  
PIC16F819 (ISP)  
PIC16F819@QFN28 (ISP)  
PIC16F819@S0IC18 (ISP)  
PIC16F819@SSOP20 (ISP)  
PIC16F83 (ISP)  
PIC16F83@S0IC18 (ISP)  
PIC16F84 (ISP)  
PIC16F84@S0IC18 (ISP)  
PIC16F84A (ISP)  
PIC16F84A@S0IC18 (ISP)  
PIC16F84A@SSOP20 (ISP)  
PIC16F87 (ISP)  
PIC16F87@QFN28 (ISP)  
PIC16F87@S0IC18 (ISP)  
PIC16F87@SSOP20 (ISP)  
PIC16F870 (ISP)  
PIC16F870@S0IC28 (ISP)  
PIC16F870@SSOP28 (ISP)  
PIC16F871 (ISP)  
PIC16F871@MQFP44 (ISP)  
PIC16F871@PLCC44 (ISP)  
PIC16F871@TQFP44 (ISP)  
PIC16F872 (ISP)  
PIC16F872@S0IC28 (ISP)  
PIC16F872@SSOP28 (ISP)  
PIC16F873 (ISP)  
PIC16F873@S0IC28 (ISP)  
PIC16F873A (ISP) (High-V)  
PIC16F873A (ISP3.3v) (HV)  
PIC16F873A@QFN28 [SA685]  
PIC16F873A@QFN28 (ISP) (Low-V)  
PIC16F873A@QFN28 (ISP3.3v) (LV)  
PIC16F873A@S0IC28 (ISP) (High-V)  
PIC16F873A@S0IC28 (ISP) (Low-V)

PIC16F76 (ISP)  
PIC16F76@S0IC28 [SA404]  
PIC16F76@SSOP28 [SA626A]  
PIC16F767  
PIC16F767@S0IC28 [SA404]  
PIC16F767@SSOP28 [SA626A]  
PIC16F77  
PIC16F77@PLCC44 [SA244]  
PIC16F77@TQFP44 [SA245A-B4805]  
PIC16F777  
PIC16F777@TQFP44 [SA245A-B4805]  
PIC16F785  
PIC16F785@QFN20 [SA692]  
PIC16F785@S0IC20 [SA404]  
PIC16F785@SSOP20 [SA626A]  
PIC16F818  
PIC16F818@QFN28 [SA685]  
PIC16F818@S0IC18 [SA404]  
PIC16F818@SSOP20 [SA626A]  
PIC16F819  
PIC16F819@QFN28 [SA685]  
PIC16F819@S0IC18 [SA404]  
PIC16F819@SSOP20 [SA626A]  
PIC16F83  
PIC16F83@S0IC18 [SA404]  
PIC16F84  
PIC16F84@S0IC18 [SA404]  
PIC16F84A  
PIC16F84A@S0IC18 [SA404]  
PIC16F84A@SSOP20 [SA626A]  
PIC16F87  
PIC16F87@QFN28 [SA685]  
PIC16F87@S0IC18 [SA404]  
PIC16F87@SSOP20 [SA626A]  
PIC16F870  
PIC16F870@S0IC28 [SA404]  
PIC16F870@SSOP28 [SA626A]  
PIC16F871  
PIC16F871@MQFP44 [SA245A-B4805]  
PIC16F871@PLCC44 [SA244]  
PIC16F871@TQFP44 [SA245A-B4805]  
PIC16F872  
PIC16F872@S0IC28 [SA404]  
PIC16F872@SSOP28 [SA626A]  
PIC16F873  
PIC16F873@S0IC28 [SA404]  
PIC16F873A  
PIC16F873A (ISP) (Low-V)  
PIC16F873A (ISP3.3v) (LV)  
PIC16F873A@QFN28 (ISP) (High-V)  
PIC16F873A@QFN28 (ISP3.3v) (HV)  
PIC16F873A@S0IC28 [SA404]  
PIC16F873A@S0IC28 (ISP) (Low-V)

PIC16F873A@SOIC28 (ISP3. 3v) (HV)  
PIC16F873A@SSOP28 [SA626A]  
PIC16F873A@SSOP28 (ISP) (Low-V)  
PIC16F873A@SSOP28 (ISP3. 3v) (LV)  
PIC16F874 (ISP)  
PIC16F874@MQFP44 (ISP)  
PIC16F874@PLCC44 (ISP)  
PIC16F874@TQFP44 (ISP)  
PIC16F874A (ISP) (High-V)  
PIC16F874A (ISP3. 3v) (HV)  
PIC16F874A@PLCC44 [SA244]  
PIC16F874A@PLCC44 (ISP) (Low-V)  
PIC16F874A@PLCC44 (ISP3. 3v) (LV)  
PIC16F874A@TQFP44 (ISP) (High-V)  
PIC16F874A@TQFP44 (ISP3. 3v) (HV)  
PIC16F876  
PIC16F876@SOIC28 [SA404]  
PIC16F876A  
PIC16F876A (ISP) (Low-V)  
PIC16F876A (ISP3. 3v) (LV)  
PIC16F876A@QFN28 (ISP) (High-V)  
PIC16F876A@QFN28 (ISP3. 3v) (HV)  
PIC16F876A@SOIC28 [SA404]  
PIC16F876A@SOIC28 (ISP) (Low-V)  
PIC16F876A@SOIC28 (ISP3. 3v) (LV)  
PIC16F876A@SSOP28 (ISP) (High-V)  
PIC16F876A@SSOP28 (ISP3. 3v) (HV)  
PIC16F877  
PIC16F877@MQFP44 [SA245A-B4805]  
PIC16F877@PLCC44 [SA244]  
PIC16F877@TQFP44 [SA245A-B4805]  
PIC16F877A  
PIC16F877A (ISP) (Low-V)  
PIC16F877A (ISP3. 3v) (LV)  
PIC16F877A@PLCC44 (ISP) (High-V)  
PIC16F877A@PLCC44 (ISP3. 3v) (HV)  
PIC16F877A@TQFP44 [SA245A-B4805]  
PIC16F877A@TQFP44 (ISP) (Low-V)  
PIC16F877A@TQFP44 (ISP3. 3v) (LV)  
PIC16F88 (ISP)  
PIC16F88@QFN28 (ISP)  
PIC16F88@SOIC18 (ISP)  
PIC16F88@SSOP20 (ISP)  
PIC16F882 (ISP) (High-V)  
PIC16F882@QFN28 [SA685]  
PIC16F882@QFN28 (ISP) (Low-V)  
PIC16F882@SOIC28 (ISP) (High-V)  
PIC16F882@SSOP28 [SA626A]  
PIC16F882@SSOP28 (ISP) (Low-V)  
PIC16F883 (ISP) (High-V)  
PIC16F883@QFN28 [SA685]  
PIC16F883@QFN28 (ISP) (Low-V)  
PIC16F883@SOIC28 (ISP) (High-V)

PIC16F873A@SOIC28 (ISP3. 3v) (LV)  
PIC16F873A@SSOP28 (ISP) (High-V)  
PIC16F873A@SSOP28 (ISP3. 3v) (HV)  
PIC16F874  
PIC16F874@MQFP44 [SA245A-B4805]  
PIC16F874@PLCC44 [SA244]  
PIC16F874@TQFP44 [SA245A-B4805]  
PIC16F874A  
PIC16F874A (ISP) (Low-V)  
PIC16F874A (ISP3. 3v) (LV)  
PIC16F874A@PLCC44 (ISP) (High-V)  
PIC16F874A@PLCC44 (ISP3. 3v) (HV)  
PIC16F874A@TQFP44 [SA245A-B4805]  
PIC16F874A@TQFP44 (ISP) (Low-V)  
PIC16F874A@TQFP44 (ISP3. 3v) (LV)  
PIC16F876 (ISP)  
PIC16F876@SOIC28 (ISP)  
PIC16F876A (ISP) (High-V)  
PIC16F876A (ISP3. 3v) (HV)  
PIC16F876A@QFN28 [SA685]  
PIC16F876A@QFN28 (ISP) (Low-V)  
PIC16F876A@QFN28 (ISP3. 3v) (LV)  
PIC16F876A@SOIC28 (ISP) (High-V)  
PIC16F876A@SOIC28 (ISP3. 3v) (HV)  
PIC16F876A@SSOP28 [SA626A]  
PIC16F876A@SSOP28 (ISP) (Low-V)  
PIC16F876A@SSOP28 (ISP3. 3v) (LV)  
PIC16F877 (ISP)  
PIC16F877@MQFP44 (ISP)  
PIC16F877@PLCC44 (ISP)  
PIC16F877@TQFP44 (ISP)  
PIC16F877A (ISP) (High-V)  
PIC16F877A (ISP3. 3v) (HV)  
PIC16F877A@PLCC44 [SA244]  
PIC16F877A@PLCC44 (ISP) (Low-V)  
PIC16F877A@PLCC44 (ISP3. 3v) (LV)  
PIC16F877A@TQFP44 (ISP) (High-V)  
PIC16F877A@TQFP44 (ISP3. 3v) (HV)  
PIC16F88  
PIC16F88@QFN28 [SA685]  
PIC16F88@SOIC18 [SA404]  
PIC16F88@SSOP20 [SA626A]  
PIC16F882  
PIC16F882 (ISP) (Low-V)  
PIC16F882@QFN28 (ISP) (High-V)  
PIC16F882@SOIC28 [SA404]  
PIC16F882@SOIC28 (ISP) (Low-V)  
PIC16F882@SSOP28 (ISP) (High-V)  
PIC16F883  
PIC16F883 (ISP) (Low-V)  
PIC16F883@QFN28 (ISP) (High-V)  
PIC16F883@SOIC28 [SA404]  
PIC16F883@SOIC28 (ISP) (Low-V)

PIC16F883@SSOP28 [SA626A]  
PIC16F883@SSOP28 (ISP) (Low-V)  
PIC16F884 (ISP) (High-V)  
PIC16F884@QFN44 [SA712]  
PIC16F884@QFN44 (ISP) (Low-V)  
PIC16F884@QFN44 (ML) (ISP) (High-V)  
PIC16F884@TQFP44 [SA245A-B4805]  
PIC16F884@TQFP44 (ISP) (Low-V)  
PIC16F886 (ISP) (High-V)  
PIC16F886@QFN28 [SA685]  
PIC16F886@QFN28 (ISP) (Low-V)  
PIC16F886@SOIC28 (ISP) (High-V)  
PIC16F886@SSOP28 [SA626A]  
PIC16F886@SSOP28 (ISP) (Low-V)  
PIC16F887 (ISP) (High-V)  
PIC16F887@QFN44 [SA712]  
PIC16F887@QFN44 (ISP) (Low-V)  
PIC16F887@QFN44 (ML) (ISP) (High-V)  
PIC16F887@TQFP44 [SA245A-B4805]  
PIC16F887@TQFP44 (ISP) (Low-V)  
PIC16F913 (ISP)  
PIC16F913@QFN28 (ISP)  
PIC16F913@SOIC28 (ISP)  
PIC16F913@SSOP28 (ISP)  
PIC16F914 (ISP)  
PIC16F914@QFN44 (ISP)  
PIC16F914@QFN44 (ML) (ISP)  
PIC16F914@TQFP44 (ISP)  
PIC16F916 (ISP)  
PIC16F916@QFN28 (ISP)  
PIC16F916@SOIC28 (ISP)  
PIC16F916@SSOP28 (ISP)  
PIC16F917 (ISP)  
PIC16F917@QFN44 (ISP)  
PIC16F917@QFN44 (ML) (ISP)  
PIC16F917@TQFP44 (ISP)  
PIC16HV540  
PIC16HV540@SSOP20 [SA626A]  
PIC16HV610 (ISP)  
PIC16HV610@QFN16 (ISP)  
PIC16HV610@SOIC14 (ISP)  
PIC16HV610@TSSOP14 (ISP)  
PIC16HV616 (ISP)  
PIC16HV616@QFN16 (ISP)  
PIC16HV616@SOIC14 (ISP)  
PIC16HV616@TSSOP14 (ISP)  
PIC16HV753 (ISP)  
PIC16HV753@TSSOP14 [SA643]  
PIC16HV785 (ISP)  
PIC16HV785@QFN20 (ISP)  
PIC16HV785@SOIC20 (ISP)  
PIC16HV785@SSOP20 (ISP)  
PIC16LC505@SOIC14 [SA602]  
PIC16F883@SSOP28 (ISP) (High-V)  
PIC16F884  
PIC16F884 (ISP) (Low-V)  
PIC16F884@QFN44 (ISP) (High-V)  
PIC16F884@QFN44 (ML) [SA737]  
PIC16F884@QFN44 (ML) (ISP) (Low-V)  
PIC16F884@TQFP44 (ISP) (High-V)  
PIC16F886  
PIC16F886 (ISP) (Low-V)  
PIC16F886@QFN28 (ISP) (High-V)  
PIC16F886@SOIC28 [SA404]  
PIC16F886@SOIC28 (ISP) (Low-V)  
PIC16F886@SSOP28 (ISP) (High-V)  
PIC16F887  
PIC16F887 (ISP) (Low-V)  
PIC16F887@QFN44 (ISP) (High-V)  
PIC16F887@QFN44 (ML) [SA737]  
PIC16F887@QFN44 (ML) (ISP) (Low-V)  
PIC16F887@TQFP44 (ISP) (High-V)  
PIC16F913  
PIC16F913@QFN28 [SA685]  
PIC16F913@SOIC28 [SA404]  
PIC16F913@SSOP28 [SA626A]  
PIC16F914  
PIC16F914@QFN44 [SA712]  
PIC16F914@QFN44 (ML) [SA737]  
PIC16F914@TQFP44 [SA245A-B4805]  
PIC16F916  
PIC16F916@QFN28 [SA685]  
PIC16F916@SOIC28 [SA404]  
PIC16F916@SSOP28 [SA626A]  
PIC16F917  
PIC16F917@QFN44 [SA712]  
PIC16F917@QFN44 (ML) [SA737]  
PIC16F917@TQFP44 [SA245A-B4805]  
PIC16F946@TQFP64 (ISP)  
PIC16HV540@SOIC18 [SA404]  
PIC16HV610  
PIC16HV610@QFN16 [SA727]  
PIC16HV610@SOIC14 [SA602]  
PIC16HV610@TSSOP14 [SA026]  
PIC16HV616  
PIC16HV616@QFN16 [SA727]  
PIC16HV616@SOIC14 [SA602]  
PIC16HV616@TSSOP14 [SA026]  
PIC16HV753  
PIC16HV753@SOIC14 [SA602]  
PIC16HV785  
PIC16HV785@QFN20 [SA692]  
PIC16HV785@SOIC20 [SA404]  
PIC16HV785@SSOP20 [SA626A]  
PIC16LC505  
PIC16LC54A

PIC16LC54A@S0IC18 [SA404]  
PIC16LC54C  
PIC16LC54C@SSOP20 [SA626A]  
PIC16LC554 (ISP)  
PIC16LC554@S0IC18 (ISP)  
PIC16LC558 (ISP)  
PIC16LC558@S0IC18 (ISP)  
PIC16LC56A@S0IC18 [SA404]  
PIC16LC58A  
PIC16LC58A@SSOP20 [SA626A]  
PIC16LC58B@S0IC18 [SA404]  
PIC16LC620  
PIC16LC620@S0IC18 [SA404]  
PIC16LC620A  
PIC16LC620A@S0IC18 [SA404]  
PIC16LC620A@SSOP20 [SA626A]  
PIC16LC621A  
PIC16LC621A@S0IC18 [SA404]  
PIC16LC621A@SSOP20 [SA626A]  
PIC16LC622  
PIC16LC622@S0IC18 [SA404]  
PIC16LC62A  
PIC16LC62A@S0IC28 [SA404]  
PIC16LC62A@SSOP28 [SA626A]  
PIC16LC62B  
PIC16LC62B@S0IC28 [SA404]  
PIC16LC62B@SSOP28 [SA626A]  
PIC16LC63  
PIC16LC63@S0IC28 [SA404]  
PIC16LC63A  
PIC16LC63A@S0IC28 [SA404]  
PIC16LC63A@SSOP28 [SA626A]  
PIC16LC64A  
PIC16LC64A@PLCC44 [SA244]  
PIC16LC64A@TQFP44 [SA245A-B4805]  
PIC16LC65A  
PIC16LC65A@PLCC44 [SA244]  
PIC16LC65A@TQFP44 [SA245A-B4805]  
PIC16LC65B  
PIC16LC65B@PLCC44 [SA244]  
PIC16LC65B@TQFP44 [SA245A-B4805]  
PIC16LC66  
PIC16LC66@S0IC28 [SA404]  
PIC16LC67  
PIC16LC67@PLCC44 [SA244]  
PIC16LC67@TQFP44 [SA245A-B4805]  
PIC16LC71  
PIC16LC71@S0IC18 [SA404]  
PIC16LC710  
PIC16LC710@S0IC18 [SA404]  
PIC16LC710@SSOP20 [SA626A]  
PIC16LC711  
PIC16LC711@S0IC18 [SA404]  
PIC16LC54A@SSOP20 [SA626A]  
PIC16LC54C@S0IC18 [SA404]  
PIC16LC554  
PIC16LC554@S0IC18 [SA404]  
PIC16LC558  
PIC16LC558@S0IC18 [SA404]  
PIC16LC56A  
PIC16LC56A@SSOP20 [SA626A]  
PIC16LC58A@S0IC18 [SA404]  
PIC16LC58B  
PIC16LC58B@SSOP20 [SA626A]  
PIC16LC620 (ISP)  
PIC16LC620@S0IC18 (ISP)  
PIC16LC620A (ISP)  
PIC16LC620A@S0IC18 (ISP)  
PIC16LC620A@SSOP20 (ISP)  
PIC16LC621A (ISP)  
PIC16LC621A@S0IC18 (ISP)  
PIC16LC621A@SSOP20 (ISP)  
PIC16LC622 (ISP)  
PIC16LC622@S0IC18 (ISP)  
PIC16LC62A (ISP)  
PIC16LC62A@S0IC28 (ISP)  
PIC16LC62A@SSOP28 (ISP)  
PIC16LC62B (ISP)  
PIC16LC62B@S0IC28 (ISP)  
PIC16LC62B@SSOP28 (ISP)  
PIC16LC63 (ISP)  
PIC16LC63@S0IC28 (ISP)  
PIC16LC63A (ISP)  
PIC16LC63A@S0IC28 (ISP)  
PIC16LC63A@SSOP28 (ISP)  
PIC16LC64A (ISP)  
PIC16LC64A@PLCC44 (ISP)  
PIC16LC64A@TQFP44 (ISP)  
PIC16LC65A (ISP)  
PIC16LC65A@PLCC44 (ISP)  
PIC16LC65A@TQFP44 (ISP)  
PIC16LC65B (ISP)  
PIC16LC65B@PLCC44 (ISP)  
PIC16LC65B@TQFP44 (ISP)  
PIC16LC66 (ISP)  
PIC16LC66@S0IC28 (ISP)  
PIC16LC67 (ISP)  
PIC16LC67@PLCC44 (ISP)  
PIC16LC67@TQFP44 (ISP)  
PIC16LC71 (ISP)  
PIC16LC71@S0IC18 (ISP)  
PIC16LC710 (ISP)  
PIC16LC710@S0IC18 (ISP)  
PIC16LC710@SSOP20 (ISP)  
PIC16LC711 (ISP)  
PIC16LC711@S0IC18 (ISP)

PIC16LC711@SSOP20 [SA626A]	PIC16LC711@SSOP20 (ISP)
PIC16LC712	PIC16LC712 (ISP)
PIC16LC712@S0IC18 [SA404]	PIC16LC712@S0IC18 (ISP)
PIC16LC712@SSOP20 [SA626A]	PIC16LC712@SSOP20 (ISP)
PIC16LC715	PIC16LC715@S0IC18 [SA404]
PIC16LC716	PIC16LC716 (ISP)
PIC16LC716@S0IC18 [SA404]	PIC16LC716@S0IC18 (ISP)
PIC16LC716@SSOP20 [SA626A]	PIC16LC716@SSOP20 (ISP)
PIC16LC717	PIC16LC717 (ISP)
PIC16LC717@S0IC18 [SA404]	PIC16LC717@S0IC18 (ISP)
PIC16LC717@SSOP20 [SA626A]	PIC16LC717@SSOP20 (ISP)
PIC16LC72	PIC16LC72 (ISP)
PIC16LC72@S0IC28 [SA404]	PIC16LC72@S0IC28 (ISP)
PIC16LC72@SSOP28 [SA626A]	PIC16LC72@SSOP28 (ISP)
PIC16LC72A	PIC16LC72A (ISP)
PIC16LC72A@S0IC28 [SA404]	PIC16LC72A@S0IC28 (ISP)
PIC16LC72A@SSOP28 [SA626A]	PIC16LC72A@SSOP28 (ISP)
PIC16LC73A	PIC16LC73A (ISP)
PIC16LC73A@S0IC28 [SA404]	PIC16LC73A@S0IC28 (ISP)
PIC16LC73B	PIC16LC73B (ISP)
PIC16LC73B@S0IC28 [SA404]	PIC16LC73B@S0IC28 (ISP)
PIC16LC73B@SSOP28 [SA626A]	PIC16LC73B@SSOP28 (ISP)
PIC16LC74	PIC16LC74 (ISP)
PIC16LC74@PLCC44 [SA244]	PIC16LC74@PLCC44 (ISP)
PIC16LC74@TQFP44 [SA245A-B4805]	PIC16LC74@TQFP44 (ISP)
PIC16LC74A	PIC16LC74A (ISP)
PIC16LC74A@PLCC44 [SA244]	PIC16LC74A@PLCC44 (ISP)
PIC16LC74A@TQFP44 [SA245A-B4805]	PIC16LC74A@TQFP44 (ISP)
PIC16LC74B	PIC16LC74B (ISP)
PIC16LC74B@MQFP44 [SA675-B4805]	PIC16LC74B@MQFP44 (ISP)
PIC16LC74B@PLCC44 [SA244]	PIC16LC74B@PLCC44 (ISP)
PIC16LC74B@TQFP44 [SA245A-B4805]	PIC16LC74B@TQFP44 (ISP)
PIC16LC76	PIC16LC76 (ISP)
PIC16LC76@S0IC28 [SA404]	PIC16LC76@S0IC28 (ISP)
PIC16LC77	PIC16LC77 (ISP)
PIC16LC77@PLCC44 [SA244]	PIC16LC77@PLCC44 (ISP)
PIC16LC773	PIC16LC773 (ISP)
PIC16LC773@S0IC28 [SA404]	PIC16LC773@S0IC28 (ISP)
PIC16LC773@SSOP28 [SA626A]	PIC16LC773@SSOP28 (ISP)
PIC16LC774	PIC16LC774 (ISP)
PIC16LC774@PLCC44 [SA244]	PIC16LC774@PLCC44 (ISP)
PIC16LC774@TQFP44 [SA245A-B4805]	PIC16LC774@TQFP44 (ISP)
PIC16LC84	PIC16LC84 (ISP)
PIC16LC84@S0IC18 [SA404]	PIC16LC84@S0IC18 (ISP)
PIC16LC923@PLCC68 (ISP)	PIC16LC923@SDIP64 (ISP)
PIC16LC923@TQFP64 (ISP)	PIC16LC924@PLCC68 (ISP)
PIC16LC924@SDIP64 (ISP)	PIC16LC924@TQFP64 (ISP)
PIC16LC925@PLCC68 (ISP)	PIC16LC925@TQFP64 (ISP)
PIC16LC926@PLCC68 (ISP)	PIC16LC926@TQFP64 (ISP)
PIC16LCE623@S0IC18 [SA404]	PIC16LCE623@S0IC18 (ISP)
PIC16LCE623@SSOP20 [SA626A]	PIC16LCE623@SSOP20 (ISP)
PIC16LF1454	PIC16LF1454 (ISP)
PIC16LF1454@QFN16 [SA727]	PIC16LF1454@S0IC14 [SA602]

PIC16LF1454@TSSOP14 [SA026]  
PIC16LF1455 (ISP)  
PIC16LF1455@SOIC14 [SA602]  
PIC16LF1458  
PIC16LF1458@QFN20 [SA692]  
PIC16LF1458@SSOP20 [SA626A]  
PIC16LF1459 (ISP)  
PIC16LF1459@SOIC20 [SA404]  
PIC16LF1503  
PIC16LF1503@QFN16 [SA743]  
PIC16LF1503@SOIC14 [SA602]  
PIC16LF1503@TSSOP14 [SA643]  
PIC16LF1507  
PIC16LF1507@QFN20 [SA692]  
PIC16LF1507@SOIC20 [SA404]  
PIC16LF1507@SSOP20 [SA626A]  
PIC16LF1508  
PIC16LF1508@QFN20 [SA692]  
PIC16LF1508@SOIC20 [SA404]  
PIC16LF1508@SSOP20 [SA626A]  
PIC16LF1509  
PIC16LF1509@QFN20 [SA692]  
PIC16LF1509@SOIC20 [SA404]  
PIC16LF1509@SSOP20 [SA626A]  
PIC16LF1512  
PIC16LF1512@SOIC28 [SA404]  
PIC16LF1512@SSOP28 [SA626A]  
PIC16LF1512@UQFN28 [\$\$\$\$\$]  
PIC16LF1513  
PIC16LF1513@SOIC28 [SA404]  
PIC16LF1513@SSOP28 [SA626A]  
PIC16LF1513@UQFN28 [\$\$\$\$\$]  
PIC16LF1516  
PIC16LF1516@SOIC28 [SA404]  
PIC16LF1516@SSOP28 [SA626A]  
PIC16LF1516@UQFN28 [\$\$\$\$\$]  
PIC16LF1517  
PIC16LF1517@TQFP44 [SA245A-B4805]  
PIC16LF1517@TQFP44 (ISP)  
PIC16LF1517@UQFN40 (ISP)  
PIC16LF1518 (ISP)  
PIC16LF1518@SOIC28 (ISP)  
PIC16LF1518@SSOP28 (ISP)  
PIC16LF1518@UQFN28 (ISP)  
PIC16LF1519 (ISP)  
PIC16LF1519@TQFP44 [SA245A-B4805]  
PIC16LF1519@TQFP44 (ISP)  
PIC16LF1519@UQFN40 (ISP)  
PIC16LF1526@TQFP64 (ISP)  
PIC16LF1527@TQFP64 (ISP)  
PIC16LF1554@ISP  
PIC16LF1554@SOIC14 [SA602]  
PIC16LF1559

PIC16LF1455  
PIC16LF1455@QFN16 [SA727]  
PIC16LF1455@TSSOP14 [SA026]  
PIC16LF1458 (ISP)  
PIC16LF1458@SOIC20 [SA404]  
PIC16LF1459  
PIC16LF1459@QFN20 [SA692]  
PIC16LF1459@SSOP20 [SA626A]  
PIC16LF1503 (ISP)  
PIC16LF1503@QFN16 (ISP)  
PIC16LF1503@SOIC14 (ISP)  
PIC16LF1503@TSSOP14 (ISP)  
PIC16LF1507 (ISP)  
PIC16LF1507@QFN20 (ISP)  
PIC16LF1507@SOIC20 (ISP)  
PIC16LF1507@SSOP20 (ISP)  
PIC16LF1508 (ISP)  
PIC16LF1508@QFN20 (ISP)  
PIC16LF1508@SOIC20 (ISP)  
PIC16LF1508@SSOP20 (ISP)  
PIC16LF1509 (ISP)  
PIC16LF1509@QFN20 (ISP)  
PIC16LF1509@SOIC20 (ISP)  
PIC16LF1509@SSOP20 (ISP)  
PIC16LF1512 (ISP)  
PIC16LF1512@SOIC28 (ISP)  
PIC16LF1512@SSOP28 (ISP)  
PIC16LF1512@UQFN28 (ISP)  
PIC16LF1513 (ISP)  
PIC16LF1513@SOIC28 (ISP)  
PIC16LF1513@SSOP28 (ISP)  
PIC16LF1513@UQFN28 (ISP)  
PIC16LF1516 (ISP)  
PIC16LF1516@SOIC28 (ISP)  
PIC16LF1516@SSOP28 (ISP)  
PIC16LF1516@UQFN28 (ISP)  
PIC16LF1517 (ISP)  
PIC16LF1517@UQFN40 [\$\$\$\$\$]  
PIC16LF1518  
PIC16LF1518@SOIC28 [SA404]  
PIC16LF1518@SSOP28 [SA626A]  
PIC16LF1518@UQFN28 [\$\$\$\$\$]  
PIC16LF1519  
PIC16LF1519@UQFN40 [\$\$\$\$\$]  
PIC16LF1526@QFN64 (ISP)  
PIC16LF1527@QFN64 (ISP)  
PIC16LF1554  
PIC16LF1554@QFN16 [SA743]  
PIC16LF1554@TSSOP14 [SA643]  
PIC16LF1559@ISP

PIC16LF1559@QFN20 [SA692]  
PIC16LF1559@SSOP20 [SA626A]  
PIC16LF1574@ISP  
PIC16LF1574-S14 [SA602]  
PIC16LF1575  
PIC16LF1575-Q16 [SA743]  
PIC16LF1575-T14 [SA026]  
PIC16LF1578@ISP  
PIC16LF1578-S20 [SA404]  
PIC16LF1579  
PIC16LF1579-Q20 [SA692]  
PIC16LF1579-SS20 [SA626A]  
PIC16LF1703@QFN16 [SA743]  
PIC16LF1703@TSSOP14 [SA026]  
PIC16LF1704@ISP  
PIC16LF1704@SOIC14 [SA602]  
PIC16LF1705  
PIC16LF1705@QFN16 [SA743]  
PIC16LF1705@TSSOP14 [SA026]  
PIC16LF1707@ISP  
PIC16LF1707@SOIC20 [SA404]  
PIC16LF1708  
PIC16LF1708@QFN20 [SA692]  
PIC16LF1708@SSOP20 [SA626A]  
PIC16LF1709@ISP  
PIC16LF1709@SOIC20 [SA404]  
PIC16LF1782  
PIC16LF1782@SOIC28 [SA404]  
PIC16LF1782@SSOP28 [SA626A]  
PIC16LF1782@UQFN28 [SA685]  
PIC16LF1783  
PIC16LF1783@SOIC28 [SA404]  
PIC16LF1783@SSOP28 [SA626A]  
PIC16LF1783@UQFN28 [SA685]  
PIC16LF1784  
PIC16LF1784@QFN44 [SA737]  
PIC16LF1784@TQFP44 [SA245A-B4805]  
PIC16LF1784@UQFN40  
PIC16LF1786 (ISP)  
PIC16LF1786@SOIC28 [SA404]  
PIC16LF1787  
PIC16LF1787@QFN44 [SA737]  
PIC16LF1787@TQFP44 [SA245A-B4805]  
PIC16LF1787@UQFN40  
PIC16LF1788 (ISP)  
PIC16LF1788@SOIC28 [SA404]  
PIC16LF1789  
PIC16LF1789@QFN44 [SA737]  
PIC16LF1789@TQFP44 [SA245A-B4805]  
PIC16LF1789@UQFN40  
PIC16LF1823 (8-word)  
PIC16LF1823 (LV)  
PIC16LF1823@QFN16 (3\*3) [SA743]  
PIC16LF1559@SOIC20 [SA404]  
PIC16LF1574  
PIC16LF1574-Q16 [SA743]  
PIC16LF1574-T14 [SA026]  
PIC16LF1575@ISP  
PIC16LF1575-S14 [SA602]  
PIC16LF1578  
PIC16LF1578-Q20 [SA692]  
PIC16LF1578-SS20 [SA626A]  
PIC16LF1579@ISP  
PIC16LF1579-S20 [SA404]  
PIC16LF1703@ISP  
PIC16LF1703@SOIC14 [SA602]  
PIC16LF1704  
PIC16LF1704@QFN16 [SA743]  
PIC16LF1704@TSSOP14 [SA026]  
PIC16LF1705@ISP  
PIC16LF1705@SOIC14 [SA602]  
PIC16LF1707  
PIC16LF1707@QFN20 [SA692]  
PIC16LF1707@SSOP20 [SA626A]  
PIC16LF1708@ISP  
PIC16LF1708@SOIC20 [SA404]  
PIC16LF1709  
PIC16LF1709@QFN20 [SA692]  
PIC16LF1709@SSOP20 [SA626A]  
PIC16LF1782 (ISP)  
PIC16LF1782@SOIC28 (ISP)  
PIC16LF1782@SSOP28 (ISP)  
PIC16LF1782@UQFN28 (ISP)  
PIC16LF1783 (ISP)  
PIC16LF1783@SOIC28 (ISP)  
PIC16LF1783@SSOP28 (ISP)  
PIC16LF1783@UQFN28 (ISP)  
PIC16LF1784 (ISP)  
PIC16LF1786  
PIC16LF1786@QFN28 [SA685]  
PIC16LF1786@SSOP28 [SA626A]  
PIC16LF1787 (ISP)  
PIC16LF1788  
PIC16LF1788@QFN28 [SA685]  
PIC16LF1788@SSOP28 [SA626A]  
PIC16LF1789 (ISP)  
PIC16LF1823  
PIC16LF1823 (ISP) (HV)  
PIC16LF1823 (LVISP)

PIC16LF1823@QFN16 (3*3) (8-word) [SA743]	
PIC16LF1823@QFN16 (3*3) (ISP) (HV)	
PIC16LF1823@QFN16 (3*3) (LV) [SA743]	
PIC16LF1823@QFN16 (4*4) [SA727]	
PIC16LF1823@QFN16 (4*4) (8-word) [SA727]	
PIC16LF1823@QFN16 (4*4) (ISP) (HV)	
PIC16LF1823@QFN16 (4*4) (LV) [SA727]	
PIC16LF1823@SOIC14 [SA602]	
PIC16LF1823@SOIC14 (8-word) [SA602]	
PIC16LF1823@SOIC14 (ISP) (HV)	PIC16LF1823@SOIC14 (LV) [SA602]
PIC16LF1823@TSSOP14 [SA643]	
PIC16LF1823@TSSOP14 (8-word) [SA643]	
PIC16LF1823@TSSOP14 (ISP) (HV)	PIC16LF1823@TSSOP14 (LV) [SA026]
PIC16LF1824	PIC16LF1824 (8-word)
PIC16LF1824 (ISP) (HV)	PIC16LF1824 (LV)
PIC16LF1824 (LVISP)	PIC16LF1824@QFN16 (3*3) [SA743]
PIC16LF1824@QFN16 (3*3) (8-word) [SA743]	
PIC16LF1824@QFN16 (3*3) (ISP) (HV)	
PIC16LF1824@QFN16 (3*3) (LV) [SA743]	
PIC16LF1824@QFN16 (4*4) [SA727]	
PIC16LF1824@QFN16 (4*4) (8-word) [SA727]	
PIC16LF1824@QFN16 (4*4) (ISP) (HV)	
PIC16LF1824@QFN16 (4*4) (LV) [SA727]	
PIC16LF1824@SOIC14 [SA602]	
PIC16LF1824@SOIC14 (8-word) [SA602]	
PIC16LF1824@SOIC14 (ISP) (HV)	PIC16LF1824@SOIC14 (LV) [SA602]
PIC16LF1824@TSSOP14 [SA643]	
PIC16LF1824@TSSOP14 (8-word) [SA643]	
PIC16LF1824@TSSOP14 (ISP) (HV)	PIC16LF1824@TSSOP14 (LV) [SA026]
PIC16LF1825	PIC16LF1825 (8-word)
PIC16LF1825 (ISP) (HV)	PIC16LF1825 (LV)
PIC16LF1825 (LVISP)	PIC16LF1825@QFN16 (3*3) [SA743]
PIC16LF1825@QFN16 (3*3) (8-word) [SA743]	
PIC16LF1825@QFN16 (3*3) (ISP) (HV)	
PIC16LF1825@QFN16 (3*3) (LV) [SA743]	
PIC16LF1825@QFN16 (4*4) [SA727]	
PIC16LF1825@QFN16 (4*4) (8-word) [SA727]	
PIC16LF1825@QFN16 (4*4) (ISP) (HV)	
PIC16LF1825@QFN16 (4*4) (LV) [SA727]	
PIC16LF1825@SOIC14 [SA602]	
PIC16LF1825@SOIC14 (8-word) [SA602]	
PIC16LF1825@SOIC14 (ISP) (HV)	PIC16LF1825@SOIC14 (LV) [SA602]
PIC16LF1825@TSSOP14 [SA643]	
PIC16LF1825@TSSOP14 (8-word) [SA643]	
PIC16LF1825@TSSOP14 (ISP) (HV)	PIC16LF1825@TSSOP14 (LV) [SA026]
PIC16LF1826	PIC16LF1826 (8-word)
PIC16LF1826 (ISP) (HV)	PIC16LF1826 (LV)
PIC16LF1826 (LVISP)	PIC16LF1826@QFN28 [SA685]
PIC16LF1826@QFN28 (8-word) [SA685]	
PIC16LF1826@QFN28 (ISP) (HV)	PIC16LF1826@QFN28 (LV) [SA685]
PIC16LF1826@SOIC18 [SA404]	
PIC16LF1826@SOIC18 (8-word) [SA404]	
PIC16LF1826@SOIC18 (ISP) (HV)	PIC16LF1826@SOIC18 (LV) [SA404]

PIC16LF1826@SSOP20 [SA626A]	
PIC16LF1826@SSOP20 (8-word) [SA626A]	
PIC16LF1826@SSOP20 (ISP) (HV)	PIC16LF1826@SSOP20 (LV) [SA626A]
PIC16LF1826@UQFN28 [\$\$\$\$\$]	
PIC16LF1826@UQFN28 (8-word) [\$\$\$\$\$]	
PIC16LF1827	PIC16LF1827 (8-word)
PIC16LF1827 (ISP) (HV)	PIC16LF1827 (LV)
PIC16LF1827 (LVISP)	PIC16LF1827@QFN28 [SA685]
PIC16LF1827@QFN28 (8-word) [SA685]	
PIC16LF1827@QFN28 (ISP) (HV)	PIC16LF1827@QFN28 (LV) [SA685]
PIC16LF1827@S0IC18 [SA404]	
PIC16LF1827@S0IC18 (8-word) [SA404]	
PIC16LF1827@S0IC18 (ISP) (HV)	PIC16LF1827@S0IC18 (LV) [SA404]
PIC16LF1827@SSOP20 [SA626A]	
PIC16LF1827@SSOP20 (8-word) [SA626A]	
PIC16LF1827@SSOP20 (ISP) (HV)	PIC16LF1827@SSOP20 (LV) [SA626A]
PIC16LF1827@UQFN28 [\$\$\$\$\$]	
PIC16LF1827@UQFN28 (8-word) [\$\$\$\$\$]	
PIC16LF1828	PIC16LF1828 (8-word)
PIC16LF1828 (ISP) (HV)	PIC16LF1828 (LV)
PIC16LF1828 (LVISP)	PIC16LF1828@QFN20 [SA692]
PIC16LF1828@QFN20 (8-word) [SA692]	
PIC16LF1828@QFN20 (ISP) (HV)	PIC16LF1828@QFN20 (LV) [SA692]
PIC16LF1828@S0IC20 [SA404]	
PIC16LF1828@S0IC20 (8-word) [SA404]	
PIC16LF1828@S0IC20 (ISP) (HV)	PIC16LF1828@S0IC20 (LV) [SA404]
PIC16LF1828@TSSOP20 [SA626A]	
PIC16LF1828@TSSOP20 (8-word) [SA626A]	
PIC16LF1828@TSSOP20 (ISP) (HV)	PIC16LF1828@TSSOP20 (LV) [SA626A]
PIC16LF1829	PIC16LF1829 (8-word)
PIC16LF1829 (ISP) (HV)	PIC16LF1829 (LV)
PIC16LF1829 (LVISP)	PIC16LF1829@QFN20 [SA692]
PIC16LF1829@QFN20 (8-word) [SA692]	
PIC16LF1829@QFN20 (ISP) (HV)	PIC16LF1829@QFN20 (LV) [SA692]
PIC16LF1829@S0IC20 [SA404]	
PIC16LF1829@S0IC20 (8-word) [SA404]	
PIC16LF1829@S0IC20 (ISP) (HV)	PIC16LF1829@S0IC20 (LV) [SA404]
PIC16LF1829@TSSOP20 [SA626A]	
PIC16LF1829@TSSOP20 (8-word) [SA626A]	
PIC16LF1829@TSSOP20 (ISP) (HV)	PIC16LF1829@TSSOP20 (LV) [SA626A]
PIC16LF1847	PIC16LF1847 (ISP) (HV)
PIC16LF1847@QFN28 [SA685]	PIC16LF1847@QFN28 (ISP) (HV)
PIC16LF1847@S0IC18 [SA404]	PIC16LF1847@S0IC18 (ISP) (HV)
PIC16LF1847@SSOP20 [SA626A]	PIC16LF1847@SSOP20 (ISP) (HV)
PIC16LF1847E	PIC16LF1847E@QFN28 [SA685]
PIC16LF1847E@S0IC18 [SA404]	PIC16LF1847E@SSOP20 [SA626A]
PIC16LF1902	PIC16LF1902 (ISP) (HV)
PIC16LF1902@QFN28 [SA685]	PIC16LF1902@QFN28 (ISP) (HV)
PIC16LF1902@QFN28[8-word pro] [SA685]	
PIC16LF1902@S0IC28 [SA404]	PIC16LF1902@S0IC28 (ISP) (HV)
PIC16LF1902@S0IC28[8-word pro] [SA404]	
PIC16LF1902@SSOP28 [SA626A]	PIC16LF1902@SSOP28 (ISP) (HV)
PIC16LF1902@SSOP28[8-word pro] [SA626A]	

PIC16LF1902[8-word pro]	PIC16LF1903
PIC16LF1903 (ISP) (HV)	PIC16LF1903@QFN28 [SA685]
PIC16LF1903@QFN28 (ISP) (HV)	
PIC16LF1903@QFN28[8-word pro] [SA685]	
PIC16LF1903@SOIC28 [SA404]	PIC16LF1903@SOIC28 (ISP) (HV)
PIC16LF1903@SOIC28[8-word pro] [SA404]	
PIC16LF1903@SSOP28 [SA626A]	PIC16LF1903@SSOP28 (ISP) (HV)
PIC16LF1903@SSOP28[8-word pro] [SA626A]	
PIC16LF1903[8-word pro]	PIC16LF1904
PIC16LF1904 (ISP) (HV)	PIC16LF1904@TQFP44 (ISP) (HV)
PIC16LF1904@UQFN40 (ISP) (HV)	PIC16LF1906
PIC16LF1906 (ISP) (HV)	PIC16LF1906@QFN28 [SA685]
PIC16LF1906@QFN28 (ISP) (HV)	
PIC16LF1906@QFN28[8-word pro] [SA685]	
PIC16LF1906@SOIC28 [SA404]	PIC16LF1906@SOIC28 (ISP) (HV)
PIC16LF1906@SOIC28[8-word pro] [SA404]	
PIC16LF1906@SSOP28 [SA626A]	PIC16LF1906@SSOP28 (ISP) (HV)
PIC16LF1906@SSOP28[8-word pro] [SA626A]	
PIC16LF1906[8-word pro]	PIC16LF1907 (ISP) (HV)
PIC16LF1907@TQFP44 (ISP) (HV)	PIC16LF1907@UQFN40 (ISP) (HV)
PIC16LF1933	PIC16LF1933 (ISP) (HV)
PIC16LF1933@QFN28 [SA685]	PIC16LF1933@QFN28 (ISP) (HV)
PIC16LF1933@QFN28[8-word pro] [SA685]	
PIC16LF1933@SOIC28 [SA404]	PIC16LF1933@SOIC28 (ISP) (HV)
PIC16LF1933@SOIC28[8-word pro] [SA404]	
PIC16LF1933@SSOP28 [SA626A]	PIC16LF1933@SSOP28 (ISP) (HV)
PIC16LF1933@SSOP28[8-word pro] [SA626A]	
PIC16LF1933[8-word pro]	PIC16LF1934
PIC16LF1934 (ISP) (HV)	PIC16LF1934@QFN44 (ISP) (HV)
PIC16LF1934@TQFP44 [SA245A-B4805]	
PIC16LF1934@TQFP44 (ISP) (HV)	
PIC16LF1934@TQFP44[8-word pro] [SA245A-B4805]	
PIC16LF1934[8-word pro]	PIC16LF1936
PIC16LF1936 (ISP) (HV)	PIC16LF1936@QFN28 (ISP) (HV)
PIC16LF1936@SOIC28 [SA404]	PIC16LF1936@SOIC28 (ISP) (HV)
PIC16LF1936@SOIC28[8-word pro] [SA404]	
PIC16LF1936@SSOP28 [SA626A]	PIC16LF1936@SSOP28 (ISP) (HV)
PIC16LF1936@SSOP28[8-word pro] [SA626A]	
PIC16LF1936[8-word pro]	PIC16LF1937
PIC16LF1937 (ISP) (HV)	PIC16LF1937@QFN44 (ISP) (HV)
PIC16LF1937@TQFP44 [SA245A-B4805]	
PIC16LF1937@TQFP44 (ISP) (HV)	
PIC16LF1937@TQFP44[8-word pro] [SA245A-B4805]	
PIC16LF1937[8-word pro]	PIC16LF1938
PIC16LF1938 (ISP) (HV)	PIC16LF1938@QFN28 (ISP) (HV)
PIC16LF1938@SOIC28 [SA404]	PIC16LF1938@SOIC28 (ISP) (HV)
PIC16LF1938@SOIC28[8-word pro] [SA404]	
PIC16LF1938@SSOP28 [SA626A]	PIC16LF1938@SSOP28 (ISP) (HV)
PIC16LF1938@SSOP28[8-word pro] [SA626A]	
PIC16LF1938[8-word pro]	PIC16LF1939
PIC16LF1939 (ISP) (HV)	PIC16LF1939@QFN44 (ISP) (HV)
PIC16LF1939@TQFP44 [SA245A-B4805]	
PIC16LF1939@TQFP44 (ISP) (HV)	

PIC16LF1939@TQFP44 [8-word pro] [SA245A-B4805]	
PIC16LF1946@QFN64 (ISP) (HV)	PIC16LF1946@TQFP64 (ISP) (HV)
PIC16LF1947@QFN64 (ISP) (HV)	PIC16LF1947@TQFP64 (ISP) (HV)
PIC16LF505	PIC16LF505 (ISP)
PIC16LF505@SOIC14 [SA602]	PIC16LF505@SOIC14 (ISP)
PIC16LF505@TSSOP14 [SA026]	PIC16LF505@TSSOP14 (ISP)
PIC16LF506	PIC16LF506 (ISP)
PIC16LF506@SOIC14 [SA602]	PIC16LF506@SOIC14 (ISP)
PIC16LF506@TSSOP14 [SA643]	PIC16LF506@TSSOP14 (ISP)
PIC16LF526	PIC16LF526 (ISP)
PIC16LF526@SOIC14 [SA602]	PIC16LF526@SOIC14 (ISP)
PIC16LF526@TSSOP14 [SA026]	PIC16LF526@TSSOP14 (ISP)
PIC16LF54	PIC16LF54 (ISP)
PIC16LF54@SOIC18 [SA404]	PIC16LF54@SOIC18 (ISP)
PIC16LF54@SSOP20 [SA626A]	PIC16LF54@SSOP20 (ISP)
PIC16LF57	PIC16LF57 (ISP)
PIC16LF57@SOIC28 [SA404]	PIC16LF57@SOIC28 (ISP)
PIC16LF57@SSOP28 [SA626A]	PIC16LF57@SSOP28 (ISP)
PIC16LF59	PIC16LF59 (ISP)
PIC16LF59@PLCC44 [SA244]	PIC16LF59@PLCC44 (ISP)
PIC16LF59@TQFP44 [SA245A-B4805]	PIC16LF59@TQFP44 (ISP)
PIC16LF627	PIC16LF627 (ISP)
PIC16LF627@SOIC18 [SA404]	PIC16LF627@SOIC18 (ISP)
PIC16LF627@SSOP20 [SA626A]	PIC16LF627@SSOP20 (ISP)
PIC16LF627A	PIC16LF627A (ISP)
PIC16LF627A@SOIC18 [SA404]	PIC16LF627A@SOIC18 (ISP)
PIC16LF627A@SSOP20 [SA626A]	PIC16LF627A@SSOP20 (ISP)
PIC16LF628	PIC16LF628 (ISP)
PIC16LF628@SOIC18 [SA404]	PIC16LF628@SOIC18 (ISP)
PIC16LF628@SSOP20 [SA626A]	PIC16LF628@SSOP20 (ISP)
PIC16LF628A	PIC16LF628A (ISP)
PIC16LF628A@SOIC18 [SA404]	PIC16LF628A@SOIC18 (ISP)
PIC16LF628A@SSOP20 [SA626A]	PIC16LF628A@SSOP20 (ISP)
PIC16LF631	PIC16LF631 (ISP)
PIC16LF631@QFN20 [SA692]	PIC16LF631@QFN20 (ISP)
PIC16LF631@SOIC20 [SA404]	PIC16LF631@SOIC20 (ISP)
PIC16LF631@SSOP20 [SA626A]	PIC16LF631@SSOP20 (ISP)
PIC16LF639	PIC16LF639 (ISP)
PIC16LF639@QFN20 [SA692]	PIC16LF639@QFN20 (ISP)
PIC16LF639@SOIC20 [SA404]	PIC16LF639@SOIC20 (ISP)
PIC16LF639@SSOP20 [SA626A]	PIC16LF639@SSOP20 (ISP)
PIC16LF648A	PIC16LF648A (ISP)
PIC16LF648A@SOIC18 [SA404]	PIC16LF648A@SOIC18 (ISP)
PIC16LF648A@SSOP20 [SA626A]	PIC16LF648A@SSOP20 (ISP)
PIC16LF677	PIC16LF677 (ISP)
PIC16LF677@QFN20 [SA692]	PIC16LF677@QFN20 (ISP)
PIC16LF677@SOIC20 [SA404]	PIC16LF677@SOIC20 (ISP)
PIC16LF677@SSOP20 [SA626A]	PIC16LF677@SSOP20 (ISP)
PIC16LF685	PIC16LF685 (ISP)
PIC16LF685@QFN20 [SA692]	PIC16LF685@QFN20 (ISP)
PIC16LF685@SOIC20 [SA404]	PIC16LF685@SOIC20 (ISP)
PIC16LF685@SSOP20 [SA626A]	PIC16LF685@SSOP20 (ISP)
PIC16LF687	PIC16LF687 (ISP)

PIC16LF687@QFN20 [SA692]	PIC16LF687@QFN20 (ISP)
PIC16LF687@S0IC20 [SA404]	PIC16LF687@S0IC20 (ISP)
PIC16LF687@SSOP20 [SA626A]	PIC16LF687@SSOP20 (ISP)
PIC16LF689	PIC16LF689 (ISP)
PIC16LF689@QFN20 [SA692]	PIC16LF689@QFN20 (ISP)
PIC16LF689@S0IC20 [SA404]	PIC16LF689@S0IC20 (ISP)
PIC16LF689@SSOP20 [SA626A]	PIC16LF689@SSOP20 (ISP)
PIC16LF690	PIC16LF690 (ISP)
PIC16LF690@QFN20 [SA692]	PIC16LF690@QFN20 (ISP)
PIC16LF690@S0IC20 [SA404]	PIC16LF690@S0IC20 (ISP)
PIC16LF690@SSOP20 [SA626A]	PIC16LF690@SSOP20 (ISP)
PIC16LF707	PIC16LF707 (ISP)
PIC16LF707@QFN44 [SA737]	PIC16LF707@QFN44 (ISP)
PIC16LF707@TQFP44 [SA245A-B4805]	PIC16LF707@TQFP44 (ISP)
PIC16LF716	PIC16LF716 (4-WORD PRO)
PIC16LF716 (ISP)	PIC16LF716@S0IC18 [SA404]
PIC16LF716@S0IC18 (4-WORD PRO) [SA404]	
PIC16LF716@S0IC18 (ISP)	PIC16LF716@SSOP20 [SA626A]
PIC16LF716@SSOP20 (4-WORD PRO) [SA626A]	
PIC16LF716@SSOP20 (ISP)	PIC16LF72
PIC16LF72 (ISP)	PIC16LF72@QFN28 [SA685]
PIC16LF72@QFN28 (ISP)	PIC16LF72@S0IC28 [SA404]
PIC16LF72@S0IC28 (ISP)	PIC16LF72@SSOP28 [SA626A]
PIC16LF72@SSOP28 (ISP)	PIC16LF720
PIC16LF720@QFN20 [SA692]	PIC16LF720@S0IC20 [SA404]
PIC16LF720@SSOP20 [SA626A]	PIC16LF721
PIC16LF721@QFN20 [SA692]	PIC16LF721@S0IC20 [SA404]
PIC16LF721@SSOP20 [SA626A]	PIC16LF722
PIC16LF722 (ISP)	PIC16LF722@QFN28 [SA685]
PIC16LF722@QFN28 (ISP)	PIC16LF722@S0IC28 [SA404]
PIC16LF722@S0IC28 (ISP)	PIC16LF722@SSOP28 [SA626A]
PIC16LF722@SSOP28 (ISP)	PIC16LF722A
PIC16LF722A (ISP)	PIC16LF722A@QFN28 [SA685]
PIC16LF722A@QFN28 (ISP)	PIC16LF722A@S0IC28 [SA404]
PIC16LF722A@S0IC28 (ISP)	PIC16LF722A@SSOP28 [SA626A]
PIC16LF722A@SSOP28 (ISP)	PIC16LF723
PIC16LF723 (ISP)	PIC16LF723@QFN28 [SA685]
PIC16LF723@QFN28 (ISP)	PIC16LF723@S0IC28 [SA404]
PIC16LF723@S0IC28 (ISP)	PIC16LF723@SSOP28 [SA626A]
PIC16LF723@SSOP28 (ISP)	PIC16LF723A
PIC16LF723A (ISP)	PIC16LF723A@QFN28 [SA685]
PIC16LF723A@QFN28 (ISP)	PIC16LF723A@S0IC28 [SA404]
PIC16LF723A@S0IC28 (ISP)	PIC16LF723A@SSOP28 [SA626A]
PIC16LF723A@SSOP28 (ISP)	PIC16LF724
PIC16LF724 (ISP)	PIC16LF724@QFN44 [SA737]
PIC16LF724@QFN44 (ISP)	PIC16LF724@TQFP44 [SA245A-B4805]
PIC16LF724@TQFP44 (ISP)	PIC16LF726
PIC16LF726 (ISP)	PIC16LF726@QFN28 [SA685]
PIC16LF726@QFN28 (ISP)	PIC16LF726@S0IC28 [SA404]
PIC16LF726@S0IC28 (ISP)	PIC16LF726@SSOP28 [SA626A]
PIC16LF726@SSOP28 (ISP)	PIC16LF727
PIC16LF727 (ISP)	PIC16LF727@QFN44 [SA737]
PIC16LF727@QFN44 (ISP)	PIC16LF727@TQFP44 [SA245A-B4805]

PIC16LF727@TQFP44 (ISP)  
PIC16LF73 (ISP)  
PIC16LF73@S0IC28 [SA404]  
PIC16LF73@SSOP28 [SA626A]  
PIC16LF737  
PIC16LF737@S0IC28 [SA404]  
PIC16LF737@SSOP28 [SA626A]  
PIC16LF74  
PIC16LF74@PLCC44 [SA244]  
PIC16LF74@TQFP44 [SA245A-B4805]  
PIC16LF747  
PIC16LF747@TQFP44 [SA245A-B4805]  
PIC16LF76  
PIC16LF76@QFN28 [SA685]  
PIC16LF76@S0IC28 (ISP)  
PIC16LF76@SSOP28 (ISP)  
PIC16LF767 (ISP)  
PIC16LF767@S0IC28 (ISP)  
PIC16LF767@SSOP28 (ISP)  
PIC16LF77 (ISP)  
PIC16LF77@PLCC44 (ISP)  
PIC16LF77@TQFP44 (ISP)  
PIC16LF777 (ISP)  
PIC16LF777@TQFP44 (ISP)  
PIC16LF818 (ISP)  
PIC16LF818@QFN28 (ISP)  
PIC16LF818@S0IC18 (ISP)  
PIC16LF818@SSOP20 (ISP)  
PIC16LF819 (ISP)  
PIC16LF819@QFN28 (ISP)  
PIC16LF819@S0IC18 (ISP)  
PIC16LF819@SSOP20 (ISP)  
PIC16LF83 (ISP)  
PIC16LF83@S0IC18 (ISP)  
PIC16LF84 (ISP)  
PIC16LF84@S0IC18 (ISP)  
PIC16LF84A (ISP)  
PIC16LF84A@S0IC18 (ISP)  
PIC16LF84A@SSOP20 (ISP)  
PIC16LF87 (ISP)  
PIC16LF87@QFN28 (ISP)  
PIC16LF87@S0IC18 (ISP)  
PIC16LF87@SSOP20 (ISP)  
PIC16LF870 (ISP)  
PIC16LF870@S0IC28 (ISP)  
PIC16LF870@SSOP28 (ISP)  
PIC16LF871 (ISP)  
PIC16LF871@MQFP44 (ISP)  
PIC16LF871@PLCC44 (ISP)  
PIC16LF871@TQFP44 (ISP)  
PIC16LF872 (ISP)  
PIC16LF872@S0IC28 (ISP)  
PIC16LF872@SSOP28 (ISP)  
PIC16LF73  
PIC16LF73@QFN28 [SA685]  
PIC16LF73@S0IC28 (ISP)  
PIC16LF73@SSOP28 (ISP)  
PIC16LF737 (ISP)  
PIC16LF737@S0IC28 (ISP)  
PIC16LF737@SSOP28 (ISP)  
PIC16LF74 (ISP)  
PIC16LF74@PLCC44 (ISP)  
PIC16LF74@TQFP44 (ISP)  
PIC16LF747 (ISP)  
PIC16LF747@TQFP44 (ISP)  
PIC16LF76 (ISP)  
PIC16LF76@S0IC28 [SA404]  
PIC16LF76@SSOP28 [SA626A]  
PIC16LF767  
PIC16LF767@S0IC28 [SA404]  
PIC16LF767@SSOP28 [SA626A]  
PIC16LF77  
PIC16LF77@PLCC44 [SA244]  
PIC16LF77@TQFP44 [SA245A-B4805]  
PIC16LF777  
PIC16LF777@TQFP44 [SA245A-B4805]  
PIC16LF818  
PIC16LF818@QFN28 [SA685]  
PIC16LF818@S0IC18 [SA404]  
PIC16LF818@SSOP20 [SA626A]  
PIC16LF819  
PIC16LF819@QFN28 [SA685]  
PIC16LF819@S0IC18 [SA404]  
PIC16LF819@SSOP20 [SA626A]  
PIC16LF83  
PIC16LF83@S0IC18 [SA404]  
PIC16LF84  
PIC16LF84@S0IC18 [SA404]  
PIC16LF84A  
PIC16LF84A@S0IC18 [SA404]  
PIC16LF84A@SSOP20 [SA626A]  
PIC16LF87  
PIC16LF87@QFN28 [SA685]  
PIC16LF87@S0IC18 [SA404]  
PIC16LF87@SSOP20 [SA626A]  
PIC16LF870  
PIC16LF870@S0IC28 [SA404]  
PIC16LF870@SSOP28 [SA626A]  
PIC16LF871  
PIC16LF871@MQFP44 [SA245A-B4805]  
PIC16LF871@PLCC44 [SA244]  
PIC16LF871@TQFP44 [SA245A-B4805]  
PIC16LF872  
PIC16LF872@S0IC28 [SA404]  
PIC16LF872@SSOP28 [SA626A]  
PIC16LF873

PIC16LF873 (ISP)  
PIC16LF873@SOIC28 (ISP)  
PIC16LF873A (ISP) (High-V)  
PIC16LF873A (ISP3.3v) (HV)  
PIC16LF873A@QFN28 [SA685]  
PIC16LF873A@QFN28 (ISP) (Low-V)  
PIC16LF873A@QFN28 (ISP3.3v) (LV)  
PIC16LF873A@SOIC28 (ISP) (High-V)  
PIC16LF873A@SOIC28 (ISP3.3v) (HV)  
PIC16LF873A@SSOP28 [SA626A]  
PIC16LF873A@SSOP28 (ISP) (Low-V)  
PIC16LF873A@SSOP28 (ISP3.3v) (LV)  
PIC16LF874 (ISP)  
PIC16LF874@MQFP44 (ISP)  
PIC16LF874@PLCC44 (ISP)  
PIC16LF874@TQFP44 (ISP)  
PIC16LF874A (ISP) (High-V)  
PIC16LF874A (ISP3.3v) (HV)  
PIC16LF874A@PLCC44 [SA244]  
PIC16LF874A@PLCC44 (ISP) (Low-V)  
PIC16LF874A@PLCC44 (ISP3.3v) (LV)  
PIC16LF874A@TQFP44 [SA245A-B4805]  
PIC16LF874A@TQFP44 (ISP) (High-V)  
PIC16LF874A@TQFP44 (ISP3.3v) (HV)  
PIC16LF876  
PIC16LF876@SOIC28 [SA404]  
PIC16LF876A  
PIC16LF876A (ISP) (Low-V)  
PIC16LF876A (ISP3.3v) (LV)  
PIC16LF876A@QFN28 (ISP) (High-V)  
PIC16LF876A@QFN28 (ISP3.3v) (HV)  
PIC16LF876A@SOIC28 [SA404]  
PIC16LF876A@SOIC28 (ISP) (Low-V)  
PIC16LF876A@SOIC28 (ISP3.3v) (LV)  
PIC16LF876A@SSOP28 (ISP) (High-V)  
PIC16LF876A@SSOP28 (ISP3.3v) (HV)  
PIC16LF877  
PIC16LF877@MQFP44 [SA245A-B4805]  
PIC16LF877@PLCC44 [SA244]  
PIC16LF877@TQFP44 [SA245A-B4805]  
PIC16LF877A  
PIC16LF877A (ISP) (Low-V)  
PIC16LF877A (ISP3.3v) (LV)  
PIC16LF877A@PLCC44 (ISP) (High-V)  
PIC16LF877A@PLCC44 (ISP3.3v) (HV)  
PIC16LF877A@TQFP44 [SA245A-B4805]  
PIC16LF877A@TQFP44 (ISP) (High-V)  
PIC16LF877A@TQFP44 (ISP3.3v) (HV)  
PIC16LF88  
PIC16LF88@QFN28 [SA685]  
PIC16LF88@SOIC18 [SA404]  
PIC16LF88@SSOP20 [SA626A]  
PIC16LF913  
PIC16LF873@SOIC28 [SA404]  
PIC16LF873A  
PIC16LF873A (ISP) (Low-V)  
PIC16LF873A (ISP3.3v) (LV)  
PIC16LF873A@QFN28 (ISP) (High-V)  
PIC16LF873A@QFN28 (ISP3.3v) (HV)  
PIC16LF873A@SOIC28 [SA404]  
PIC16LF873A@SOIC28 (ISP) (Low-V)  
PIC16LF873A@SOIC28 (ISP3.3v) (LV)  
PIC16LF873A@SSOP28 (ISP) (High-V)  
PIC16LF873A@SSOP28 (ISP3.3v) (HV)  
PIC16LF874  
PIC16LF874@MQFP44 [SA245A-B4805]  
PIC16LF874@PLCC44 [SA244]  
PIC16LF874@TQFP44 [SA245A-B4805]  
PIC16LF874A  
PIC16LF874A (ISP) (Low-V)  
PIC16LF874A (ISP3.3v) (LV)  
PIC16LF874A@PLCC44 (ISP) (High-V)  
PIC16LF874A@PLCC44 (ISP3.3v) (HV)  
PIC16LF874A@TQFP44 (ISP) (Low-V)  
PIC16LF874A@TQFP44 (ISP3.3v) (LV)  
PIC16LF876 (ISP)  
PIC16LF876@SOIC28 (ISP)  
PIC16LF876A (ISP) (High-V)  
PIC16LF876A (ISP3.3v) (HV)  
PIC16LF876A@QFN28 [SA685]  
PIC16LF876A@QFN28 (ISP) (Low-V)  
PIC16LF876A@QFN28 (ISP3.3v) (LV)  
PIC16LF876A@SOIC28 (ISP) (High-V)  
PIC16LF876A@SOIC28 (ISP3.3v) (HV)  
PIC16LF876A@SSOP28 [SA626A]  
PIC16LF876A@SSOP28 (ISP) (Low-V)  
PIC16LF876A@SSOP28 (ISP3.3v) (LV)  
PIC16LF877 (ISP)  
PIC16LF877@MQFP44 (ISP)  
PIC16LF877@PLCC44 (ISP)  
PIC16LF877@TQFP44 (ISP)  
PIC16LF877A (ISP) (High-V)  
PIC16LF877A (ISP3.3v) (HV)  
PIC16LF877A@PLCC44 [SA244]  
PIC16LF877A@PLCC44 (ISP) (Low-V)  
PIC16LF877A@PLCC44 (ISP3.3v) (LV)  
PIC16LF877A@TQFP44 (ISP) (Low-V)  
PIC16LF877A@TQFP44 (ISP3.3v) (LV)  
PIC16LF88 (ISP)  
PIC16LF88@QFN28 (ISP)  
PIC16LF88@SOIC18 (ISP)  
PIC16LF88@SSOP20 (ISP)  
PIC16LF913 (ISP)

PIC16LF913@QFN28 [SA685]  
PIC16LF913@S0IC28 [SA404]  
PIC16LF913@SSOP28 [SA626A]  
PIC16LF914  
PIC16LF914@QFN44 [SA712]  
PIC16LF914@QFN44 (ML) [SA737]  
PIC16LF914@TQFP44 [SA245A-B4805]  
PIC16LF916  
PIC16LF916@QFN28 [SA685]  
PIC16LF916@S0IC28 [SA404]  
PIC16LF916@SSOP28 [SA626A]  
PIC16LF917  
PIC16LF917@QFN44 [SA712]  
PIC16LF917@QFN44 (ML) [SA737]  
PIC16LF917@TQFP44 [SA245A-B4805]  
PIC16LF946@TQFP64 (ISP)  
PIC16LV54A@S0IC18 [SA404]  
PIC16LV58A  
PIC16LV58A@SSOP20 [SA626A]  
PIC17C42@PLCC44 [SA244]  
PIC17C42A  
PIC17C42A@TQFP44 [SA245A-B4805]  
PIC17C43@PLCC44 [SA244]  
PIC17C44  
PIC17C44@TQFP44 [SA245A-B4805]  
PIC17LC42@PLCC44 [SA244]  
PIC17LC42A  
PIC17LC42A@TQFP44 [SA245A-B4805]  
PIC17LC43@PLCC44 [SA244]  
PIC17LC44  
PIC17LC44@TQFP44 [SA245A-B4805]  
PIC18C242@S0IC28 [SA404]  
PIC18C252@S0IC28 [SA404]  
PIC18C442@PLCC44 [SA244]  
PIC18C452  
PIC18C452@TQFP44 [SA245A-B4805]  
PIC18F1220 (ISP)  
PIC18F1220@S0IC18 [SA404]  
PIC18F1220@SSOP20 [SA626A]  
PIC18F1230  
PIC18F1230@QFN28 [SA685]  
PIC18F1230@S0IC18 [SA404]  
PIC18F1230@SSOP20 [SA626A]  
PIC18F1320  
PIC18F1320@QFN28 [SA685]  
PIC18F1320@S0IC18 (ISP)  
PIC18F1320@SSOP20 (ISP)  
PIC18F1330 (ISP)  
PIC18F1330@S0IC18 [SA404]  
PIC18F1330@SSOP20 [SA626A]  
PIC18F1330-ICD@QFN28 (ISP)  
PIC18F13K22 (ISP) (High-V)  
PIC18F13K22@QFN20 (ISP) (High-V)  
PIC16LF913@QFN28 (ISP)  
PIC16LF913@S0IC28 (ISP)  
PIC16LF913@SSOP28 (ISP)  
PIC16LF914 (ISP)  
PIC16LF914@QFN44 (ISP)  
PIC16LF914@QFN44 (ML) (ISP)  
PIC16LF914@TQFP44 (ISP)  
PIC16LF916 (ISP)  
PIC16LF916@QFN28 (ISP)  
PIC16LF916@S0IC28 (ISP)  
PIC16LF916@SSOP28 (ISP)  
PIC16LF917 (ISP)  
PIC16LF917@QFN44 (ISP)  
PIC16LF917@QFN44 (ML) (ISP)  
PIC16LF917@TQFP44 (ISP)  
PIC16LV54A  
PIC16LV54A@SSOP20 [SA626A]  
PIC16LV58A@S0IC18 [SA404]  
PIC17C42  
PIC17C42@TQFP44 [SA245A-B4805]  
PIC17C42A@PLCC44 [SA244]  
PIC17C43  
PIC17C43@TQFP44 [SA245A-B4805]  
PIC17C44@PLCC44 [SA244]  
PIC17LC42  
PIC17LC42@TQFP44 [SA245A-B4805]  
PIC17LC42A@PLCC44 [SA244]  
PIC17LC43  
PIC17LC43@TQFP44 [SA245A-B4805]  
PIC17LC44@PLCC44 [SA244]  
PIC18C242  
PIC18C252  
PIC18C442  
PIC18C442@TQFP44 [SA245A-B4805]  
PIC18C452@PLCC44 [SA244]  
PIC18F1220  
PIC18F1220@QFN28 [SA685]  
PIC18F1220@S0IC18 (ISP)  
PIC18F1220@SSOP20 (ISP)  
PIC18F1230 (ISP)  
PIC18F1230@QFN28 (ISP)  
PIC18F1230@S0IC18 (ISP)  
PIC18F1230@SSOP20 (ISP)  
PIC18F1320 (ISP)  
PIC18F1320@S0IC18 [SA404]  
PIC18F1320@SSOP20 [SA626A]  
PIC18F1330  
PIC18F1330@QFN28 (ISP)  
PIC18F1330@S0IC18 (ISP)  
PIC18F1330@SSOP20 (ISP)  
PIC18F13K22  
PIC18F13K22 (ISP) (Low-V)  
PIC18F13K22@QFN20 (ISP) (Low-V)

PIC18F13K22@S0IC20 [SA404]  
PIC18F13K22@S0IC20 (ISP) (Low-V)  
PIC18F13K22@SSOP20 (ISP) (High-V)  
PIC18F13K50  
PIC18F13K50 (ISP) (Low-V)  
PIC18F13K50@QFN20 (ISP) (Low-V)  
PIC18F13K50@S0IC20 (ISP) (High-V)  
PIC18F13K50@SSOP20 [SA626A]  
PIC18F13K50@SSOP20 (ISP) (Low-V)  
PIC18F14K22 (ISP) (High-V)  
PIC18F14K22@QFN20 (ISP) (High-V)  
PIC18F14K22@S0IC20 [SA404]  
PIC18F14K22@S0IC20 (ISP) (Low-V)  
PIC18F14K22@SSOP20 (ISP) (High-V)  
PIC18F14K50  
PIC18F14K50 (ISP) (Low-V)  
PIC18F14K50@QFN20 (ISP) (Low-V)  
PIC18F14K50@S0IC20 (ISP) (High-V)  
PIC18F14K50@SSOP20 [SA626A]  
PIC18F14K50@SSOP20 (ISP) (Low-V)  
PIC18F2220 (ISP)  
PIC18F2220@S0IC28 (ISP)  
PIC18F2221 (ISP) (Low-V)  
PIC18F2221@S0IC28 [SA404]  
PIC18F2221@SSOP28 [SA626A]  
PIC18F2320  
PIC18F2320@S0IC28 [SA404]  
PIC18F2321  
PIC18F2321@QFN28 (ISP) (Low-V)  
PIC18F2321@S0IC28 (ISP) (Low-V)  
PIC18F2321@SSOP28 (ISP) (Low-V)  
PIC18F2331 (ISP)  
PIC18F2331@S0IC28 (ISP)  
PIC18F23K20 (ISP) (High-V)  
PIC18F23K20@QFN28 [SA685]  
PIC18F23K20@QFN28 (ISP) (Low-V)  
PIC18F23K20@S0IC28 (ISP) (High-V)  
PIC18F23K20@SSOP28 [SA626A]  
PIC18F23K20@SSOP28 (ISP) (Low-V)  
PIC18F23K22 (ISP) (H-V)  
PIC18F23K22@QFN28 (ISP) (H-V)  
PIC18F23K22@S0IC28 (ISP) (H-V)  
PIC18F23K22@SSOP28 (ISP) (H-V)  
PIC18F2410 (ISP) (Low-V)  
PIC18F2410@S0IC28 [SA404]  
PIC18F2410@SSOP28 [SA626A]  
PIC18F242  
PIC18F242@S0IC28 [SA404]  
PIC18F2420  
PIC18F2420 (ISP) (Low-V)  
PIC18F2420@QFN28 (ISP) (High-V)  
PIC18F2420@S0IC28 [SA404]  
PIC18F2420@S0IC28 (ISP) (Low-V)  
PIC18F2420@SSOP28 [SA626A]  
PIC18F13K22@S0IC20 (ISP) (High-V)  
PIC18F13K22@SSOP20 [SA626A]  
PIC18F13K22@SSOP20 (ISP) (Low-V)  
PIC18F13K50 (ISP) (High-V)  
PIC18F13K50@QFN20 (ISP) (High-V)  
PIC18F13K50@S0IC20 [SA404]  
PIC18F13K50@S0IC20 (ISP) (Low-V)  
PIC18F13K50@SSOP20 (ISP) (High-V)  
PIC18F14K22  
PIC18F14K22 (ISP) (Low-V)  
PIC18F14K22@QFN20 (ISP) (Low-V)  
PIC18F14K22@S0IC20 (ISP) (High-V)  
PIC18F14K22@SSOP20 [SA626A]  
PIC18F14K22@SSOP20 (ISP) (Low-V)  
PIC18F14K50 (ISP) (High-V)  
PIC18F14K50@QFN20 (ISP) (High-V)  
PIC18F14K50@S0IC20 [SA404]  
PIC18F14K50@S0IC20 (ISP) (Low-V)  
PIC18F14K50@SSOP20 (ISP) (High-V)  
PIC18F2220  
PIC18F2220@S0IC28 [SA404]  
PIC18F2221  
PIC18F2221@QFN28 (ISP) (Low-V)  
PIC18F2221@S0IC28 (ISP) (Low-V)  
PIC18F2221@SSOP28 (ISP) (Low-V)  
PIC18F2320 (ISP)  
PIC18F2320@S0IC28 (ISP)  
PIC18F2321 (ISP) (Low-V)  
PIC18F2321@S0IC28 [SA404]  
PIC18F2321@SSOP28 [SA626A]  
PIC18F2331  
PIC18F2331@S0IC28 [SA404]  
PIC18F23K20  
PIC18F23K20 (ISP) (Low-V)  
PIC18F23K20@QFN28 (ISP) (High-V)  
PIC18F23K20@S0IC28 [SA404]  
PIC18F23K20@S0IC28 (ISP) (Low-V)  
PIC18F23K20@SSOP28 (ISP) (High-V)  
PIC18F23K22  
PIC18F23K22@QFN28 [SA685]  
PIC18F23K22@S0IC28 [SA404]  
PIC18F23K22@SSOP28 [SA626A]  
PIC18F2410  
PIC18F2410@QFN28 (ISP) (Low-V)  
PIC18F2410@S0IC28 (ISP) (Low-V)  
PIC18F2410@SSOP28 (ISP) (Low-V)  
PIC18F242 (ISP)  
PIC18F242@S0IC28 (ISP)  
PIC18F2420 (ISP) (High-V)  
PIC18F2420@QFN28 [SA685]  
PIC18F2420@QFN28 (ISP) (Low-V)  
PIC18F2420@S0IC28 (ISP) (High-V)  
PIC18F2420@SSOP28 [SA626A]

PIC18F2420@SSOP28 (ISP) (High-V)  
PIC18F2423  
PIC18F2423 (ISP) (Low-V)  
PIC18F2423@QFN28 (ISP) (Low-V)  
PIC18F2423@SOIC28 (ISP) (High-V)  
PIC18F2423@SSOP28 [SA626A]  
PIC18F2423@SSOP28 (ISP) (Low-V)  
PIC18F2431 (ISP)  
PIC18F2431@SOIC28 (ISP)  
PIC18F2439 (ISP)  
PIC18F2439@SOIC28 (ISP)  
PIC18F2450 (ISP) (Low-V)  
PIC18F2450@SOIC28 [SA404]  
PIC18F2450@SSOP28 [SA626A]  
PIC18F2455  
PIC18F2455 (ISP) (Low-V)  
PIC18F2455@SOIC28 (ISP) (High-V)  
PIC18F2455@SSOP28 [SA626A]  
PIC18F2455@SSOP28 (ISP) (Low-V)  
PIC18F2458 (ISP) (High-V)  
PIC18F2458@SOIC28 [SA404]  
PIC18F2458@SOIC28 (ISP) (Low-V)  
PIC18F2458@SSOP28 (ISP) (High-V)  
PIC18F248  
PIC18F248@SOIC28 [SA404]  
PIC18F2480  
PIC18F2480 (ISP) (Low-V)  
PIC18F2480@QFN28 (ISP) (Low-V)  
PIC18F2480@SOIC28 (ISP) (High-V)  
PIC18F2480@SSOP28 [SA626A]  
PIC18F2480@SSOP28 (ISP) (Low-V)  
PIC18F24J10 (ISP)  
PIC18F24J10@SOIC28 [SA404]  
PIC18F24J10@SSOP28 [SA626A]  
PIC18F24J11  
PIC18F24J11@QFN28 (ISP)  
PIC18F24J11@SOIC28 (ISP)  
PIC18F24J11@SSOP28 (ISP)  
PIC18F24J50 (ISP)  
PIC18F24J50@SOIC28 [SA404]  
PIC18F24J50@SSOP28 [SA626A]  
PIC18F24K20  
PIC18F24K20 (ISP) (Low-V)  
PIC18F24K20@QFN28 (ISP) (High-V)  
PIC18F24K20@SOIC28 [SA404]  
PIC18F24K20@SOIC28 (ISP) (Low-V)  
PIC18F24K20@SSOP28 (ISP) (High-V)  
PIC18F24K22  
PIC18F24K22@QFN28 [SA685]  
PIC18F24K22@SOIC28 [SA404]  
PIC18F24K22@SSOP28 [SA626A]  
PIC18F24K50  
PIC18F24K50@QFN28 [SA685]

PIC18F2420@SSOP28 (ISP) (Low-V)  
PIC18F2423 (ISP) (High-V)  
PIC18F2423@QFN28 (ISP) (High-V)  
PIC18F2423@SOIC28 [SA404]  
PIC18F2423@SOIC28 (ISP) (Low-V)  
PIC18F2423@SSOP28 (ISP) (High-V)  
PIC18F2431  
PIC18F2431@SOIC28 [SA404]  
PIC18F2439  
PIC18F2439@SOIC28 [SA404]  
PIC18F2450  
PIC18F2450@QFN28 (ISP) (Low-V)  
PIC18F2450@SOIC28 (ISP) (Low-V)  
PIC18F2450@SSOP28 (ISP) (Low-V)  
PIC18F2455 (ISP) (High-V)  
PIC18F2455@SOIC28 [SA404]  
PIC18F2455@SOIC28 (ISP) (Low-V)  
PIC18F2455@SSOP28 (ISP) (High-V)  
PIC18F2458  
PIC18F2458 (ISP) (Low-V)  
PIC18F2458@SOIC28 (ISP) (High-V)  
PIC18F2458@SSOP28  
PIC18F2458@SSOP28 (ISP) (Low-V)  
PIC18F248 (ISP)  
PIC18F248@SOIC28 (ISP)  
PIC18F2480 (ISP) (High-V)  
PIC18F2480@QFN28 (ISP) (High-V)  
PIC18F2480@SOIC28 [SA404]  
PIC18F2480@SOIC28 (ISP) (Low-V)  
PIC18F2480@SSOP28 (ISP) (High-V)  
PIC18F24J10  
PIC18F24J10@QFN28 (ISP)  
PIC18F24J10@SOIC28 (ISP)  
PIC18F24J10@SSOP28 (ISP)  
PIC18F24J11 (ISP)  
PIC18F24J11@SOIC28 [SA404]  
PIC18F24J11@SSOP28 [SA626A]  
PIC18F24J50  
PIC18F24J50@QFN28 (ISP)  
PIC18F24J50@SOIC28 (ISP)  
PIC18F24J50@SSOP28 (ISP)  
PIC18F24K20 (ISP) (High-V)  
PIC18F24K20@QFN28 [SA685]  
PIC18F24K20@QFN28 (ISP) (Low-V)  
PIC18F24K20@SOIC28 (ISP) (High-V)  
PIC18F24K20@SSOP28 [SA626A]  
PIC18F24K20@SSOP28 (ISP) (Low-V)  
PIC18F24K22 (ISP) (H-V)  
PIC18F24K22@QFN28 (ISP) (H-V)  
PIC18F24K22@SOIC28 (ISP) (H-V)  
PIC18F24K22@SSOP28 (ISP) (H-V)  
PIC18F24K50@ISP  
PIC18F24K50@SOIC28 [SA404]

PIC18F24K50@SSOP28 [SA626A]  
PIC18F2510 (ISP)  
PIC18F2510@S0IC28 [SA404]  
PIC18F2510@SSOP28 [SA626A]  
PIC18F2515  
PIC18F2515@S0IC28 [SA404]  
PIC18F2515@SSOP28 [SA626A]  
PIC18F252  
PIC18F252@S0IC28 [SA404]  
PIC18F2520  
PIC18F2520 (ISP) (Low-V)  
PIC18F2520@QFN28 (ISP) (High-V)  
PIC18F2520@S0IC28 [SA404]  
PIC18F2520@S0IC28 (ISP) (Low-V)  
PIC18F2520@SSOP28 (ISP) (High-V)  
PIC18F2523 (ISP) (High-V)  
PIC18F2523 (REV4=0)  
PIC18F2523@QFN28 (ISP) (High-V)  
PIC18F2523@S0IC28 (ISP) (High-V)  
PIC18F2523@S0IC28 (REV4=0) [SA404]  
PIC18F2523@S0IC28 (REV4=1) [SA404]  
PIC18F2523@SSOP28 (ISP) (High-V)  
PIC18F2523@SSOP28 (REV4=0) [SA626A]  
PIC18F2523@SSOP28 (REV4=1) [SA626A]  
PIC18F2525  
PIC18F2525@S0IC28 [SA404]  
PIC18F2525@SSOP28 [SA626A]  
PIC18F2539  
PIC18F2539@S0IC28 [SA404]  
PIC18F2550  
PIC18F2550 (ISP) (Low-V)  
PIC18F2550@S0IC28 (ISP) (High-V)  
PIC18F2550@SSOP28 [SA626A]  
PIC18F2550@SSOP28 (ISP) (Low-V)  
PIC18F2553 (ISP) (High-V)  
PIC18F2553@S0IC28 [SA404]  
PIC18F2553@S0IC28 (ISP) (Low-V)  
PIC18F2553@SSOP28 (ISP) (High-V)  
PIC18F258  
PIC18F258@S0IC28 [SA404]  
PIC18F2580  
PIC18F2580 (ISP) (Low-V)  
PIC18F2580@QFN28 (ISP) (Low-V)  
PIC18F2580@S0IC28 (ISP) (High-V)  
PIC18F2580@SSOP28 [SA626A]  
PIC18F2580@SSOP28 (ISP) (Low-V)  
PIC18F2585 (ISP) (High-V)  
PIC18F2585@SDIP28 [SA653]  
PIC18F2585@SDIP28 (ISP) (Low-V)  
PIC18F2585@S0IC28 (ISP) (High-V)  
PIC18F2585@SSOP28 [SA626A]  
PIC18F2585@SSOP28 (ISP) (Low-V)  
PIC18F25J10 (ISP)

PIC18F2510  
PIC18F2510@QFN28 (ISP)  
PIC18F2510@S0IC28 (ISP)  
PIC18F2510@SSOP28 (ISP)  
PIC18F2515 (ISP) (Low-V)  
PIC18F2515@S0IC28 (ISP) (Low-V)  
PIC18F2515@SSOP28 (ISP) (Low-V)  
PIC18F252 (ISP)  
PIC18F252@S0IC28 (ISP)  
PIC18F2520 (ISP) (High-V)  
PIC18F2520@QFN28 [SA685]  
PIC18F2520@QFN28 (ISP) (Low-V)  
PIC18F2520@S0IC28 (ISP) (High-V)  
PIC18F2520@SSOP28 [SA626A]  
PIC18F2520@SSOP28 (ISP) (Low-V)  
PIC18F2523 (ISP) (Low-V)  
PIC18F2523 (REV4=1)  
PIC18F2523@QFN28 (ISP) (Low-V)  
PIC18F2523@S0IC28 (ISP) (Low-V)  
PIC18F2523@SSOP28 (ISP) (Low-V)  
PIC18F2525 (ISP) (Low-V)  
PIC18F2525@S0IC28 (ISP) (Low-V)  
PIC18F2525@SSOP28 (ISP) (Low-V)  
PIC18F2539 (ISP)  
PIC18F2539@S0IC28 (ISP)  
PIC18F2550 (ISP) (High-V)  
PIC18F2550@S0IC28 [SA404]  
PIC18F2550@S0IC28 (ISP) (Low-V)  
PIC18F2550@SSOP28 (ISP) (High-V)  
PIC18F2553  
PIC18F2553 (ISP) (Low-V)  
PIC18F2553@S0IC28 (ISP) (High-V)  
PIC18F2553@SSOP28  
PIC18F2553@SSOP28 (ISP) (Low-V)  
PIC18F258 (ISP)  
PIC18F258@S0IC28 (ISP)  
PIC18F2580 (ISP) (High-V)  
PIC18F2580@QFN28 (ISP) (High-V)  
PIC18F2580@S0IC28 [SA404]  
PIC18F2580@S0IC28 (ISP) (Low-V)  
PIC18F2580@SSOP28 (ISP) (High-V)  
PIC18F2585  
PIC18F2585 (ISP) (Low-V)  
PIC18F2585@SDIP28 (ISP) (High-V)  
PIC18F2585@S0IC28 [SA404]  
PIC18F2585@S0IC28 (ISP) (Low-V)  
PIC18F2585@SSOP28 (ISP) (High-V)  
PIC18F25J10  
PIC18F25J10@QFN28 (ISP)

PIC18F25J10@S0IC28 [SA404]  
PIC18F25J10@SSOP28 [SA626A]  
PIC18F25J11  
PIC18F25J11@QFN28 (ISP)  
PIC18F25J11@S0IC28 (ISP)  
PIC18F25J11@SSOP28 (ISP)  
PIC18F25J50 (ISP)  
PIC18F25J50@S0IC28 [SA404]  
PIC18F25J50@SSOP28 [SA626A]  
PIC18F25K20  
PIC18F25K20 (ISP) (Low-V)  
PIC18F25K20@QFN28 (ISP) (High-V)  
PIC18F25K20@S0IC28 [SA404]  
PIC18F25K20@S0IC28 (ISP) (Low-V)  
PIC18F25K20@SSOP28 (ISP) (High-V)  
PIC18F25K22  
PIC18F25K22@QFN28 [SA685]  
PIC18F25K22@S0IC28 [SA404]  
PIC18F25K22@SSOP28 [SA626A]  
PIC18F25K50  
PIC18F25K50@QFN28 [SA685]  
PIC18F25K50@SSOP28 [SA626A]  
PIC18F25K80 (ISP)  
PIC18F25K80@QFN28 (ISP)  
PIC18F25K80@S0IC28 (ISP)  
PIC18F25K80@SSOP28 (ISP)  
PIC18F2610 (ISP) (Low-V)  
PIC18F2610@S0IC28 (ISP) (Low-V)  
PIC18F2610@SSOP28 (ISP) (Low-V)  
PIC18F2620 (ISP) (Low-V)  
PIC18F2620@S0IC28 (ISP) (Low-V)  
PIC18F2620@SSOP28 (ISP) (Low-V)  
PIC18F2680 (ISP) (High-V)  
PIC18F2680@SDIP28 [SA653]  
PIC18F2680@SDIP28 (ISP) (Low-V)  
PIC18F2680@S0IC28 (ISP) (High-V)  
PIC18F2680@SSOP28 [SA626A]  
PIC18F2680@SSOP28 (ISP) (Low-V)  
PIC18F2682 (ISP) (High-V)  
PIC18F2682@QFN28 (ISP) (High-V)  
PIC18F2682@S0IC28 [SA404]  
PIC18F2682@S0IC28 (ISP) (Low-V)  
PIC18F2682@SSOP28 (ISP) (High-V)  
PIC18F2685  
PIC18F2685 (ISP) (Low-V)  
PIC18F2685@QFN28 (ISP) (Low-V)  
PIC18F2685@S0IC28 (ISP) (High-V)  
PIC18F2685@SSOP28 [SA626A]  
PIC18F2685@SSOP28 (ISP) (Low-V)  
PIC18F26J11 (ISP)  
PIC18F26J11@S0IC28 [SA404]  
PIC18F26J11@SSOP28 [SA626A]  
PIC18F26J13

PIC18F25J10@S0IC28 (ISP)  
PIC18F25J10@SSOP28 (ISP)  
PIC18F25J11 (ISP)  
PIC18F25J11@S0IC28 [SA404]  
PIC18F25J11@SSOP28 [SA626A]  
PIC18F25J50  
PIC18F25J50@QFN28 (ISP)  
PIC18F25J50@S0IC28 (ISP)  
PIC18F25J50@SSOP28 (ISP)  
PIC18F25K20 (ISP) (High-V)  
PIC18F25K20@QFN28 [SA685]  
PIC18F25K20@QFN28 (ISP) (Low-V)  
PIC18F25K20@S0IC28 (ISP) (High-V)  
PIC18F25K20@SSOP28 [SA626A]  
PIC18F25K20@SSOP28 (ISP) (Low-V)  
PIC18F25K22 (ISP) (H-V)  
PIC18F25K22@QFN28 (ISP) (H-V)  
PIC18F25K22@S0IC28 (ISP) (H-V)  
PIC18F25K22@SSOP28 (ISP) (H-V)  
PIC18F25K50@ISP  
PIC18F25K50@S0IC28 [SA404]  
PIC18F25K80  
PIC18F25K80@QFN28 [SA685]  
PIC18F25K80@S0IC28 [SA404]  
PIC18F25K80@SSOP28 [SA626A]  
PIC18F2610  
PIC18F2610@S0IC28 [SA404]  
PIC18F2610@SSOP28 [SA626A]  
PIC18F2620  
PIC18F2620@S0IC28 [SA404]  
PIC18F2620@SSOP28 [SA626A]  
PIC18F2680  
PIC18F2680 (ISP) (Low-V)  
PIC18F2680@SDIP28 (ISP) (High-V)  
PIC18F2680@S0IC28 [SA404]  
PIC18F2680@S0IC28 (ISP) (Low-V)  
PIC18F2680@SSOP28 (ISP) (High-V)  
PIC18F2682  
PIC18F2682 (ISP) (Low-V)  
PIC18F2682@QFN28 (ISP) (Low-V)  
PIC18F2682@S0IC28 (ISP) (High-V)  
PIC18F2682@SSOP28 [SA626A]  
PIC18F2682@SSOP28 (ISP) (Low-V)  
PIC18F2685 (ISP) (High-V)  
PIC18F2685@QFN28 (ISP) (High-V)  
PIC18F2685@S0IC28 [SA404]  
PIC18F2685@S0IC28 (ISP) (Low-V)  
PIC18F2685@SSOP28 (ISP) (High-V)  
PIC18F26J11  
PIC18F26J11@QFN28 (ISP)  
PIC18F26J11@S0IC28 (ISP)  
PIC18F26J11@SSOP28 (ISP)  
PIC18F26J13 (ISP)

PIC18F26J13@QFN28 [SA685]  
PIC18F26J13@SOIC28 [SA404]  
PIC18F26J13@SSOP28 [SA626A]  
PIC18F26J50  
PIC18F26J50@QFN28 (ISP)  
PIC18F26J50@SOIC28 (ISP)  
PIC18F26J50@SSOP28 (ISP)  
PIC18F26J53 (ISP)  
PIC18F26J53@QFN28 (ISP)  
PIC18F26J53@SOIC28 (ISP)  
PIC18F26J53@SSOP28 (ISP)  
PIC18F26K20 (ISP) (High-V)  
PIC18F26K20@QFN28 [SA685]  
PIC18F26K20@QFN28 (ISP) (Low-V)  
PIC18F26K20@SOIC28 (ISP) (High-V)  
PIC18F26K20@SSOP28 [SA626A]  
PIC18F26K20@SSOP28 (ISP) (Low-V)  
PIC18F26K22 (ISP) (H-V)  
PIC18F26K22@QFN28 (ISP) (H-V)  
PIC18F26K22@SOIC28 (ISP) (H-V)  
PIC18F26K22@SSOP28 (ISP) (H-V)  
PIC18F26K50@ISP  
PIC18F26K50@SOIC28 [SA404]  
PIC18F26K80  
PIC18F26K80@QFN28 [SA685]  
PIC18F26K80@SOIC28 [SA404]  
PIC18F26K80@SSOP28 [SA626A]  
PIC18F27J13  
PIC18F27J13@QFN28 [SA685]  
PIC18F27J13@SOIC28 [SA404]  
PIC18F27J13@SSOP28 [SA626A]  
PIC18F27J53  
PIC18F27J53@QFN28 [SA685]  
PIC18F27J53@SOIC28 [SA404]  
PIC18F27J53@SSOP28 [SA626A]  
PIC18F4220  
PIC18F4220@QFN44 [SA712]  
PIC18F4220@QFN44 (ML) [SA737]  
PIC18F4220@TQFP44 [SA245A-B4805]  
PIC18F4221  
PIC18F4221@QFN44 [SA712]  
PIC18F4221@QFN44 (ML) [SA737]  
PIC18F4221@TQFP44 [SA245A-B4805]  
PIC18F4320  
PIC18F4320@QFN44 [SA712]  
PIC18F4320@QFN44 (ML) [SA737]  
PIC18F4320@TQFP44 [SA245A-B4805]  
PIC18F4321  
PIC18F4321@QFN44 [SA712]  
PIC18F4321@QFN44 (ML) [SA737]  
PIC18F4321@TQFP44 [SA245A-B4805]  
PIC18F4331  
PIC18F4331@TQFP44 [SA245A-B4805]

PIC18F26J13@QFN28 (ISP)  
PIC18F26J13@SOIC28 (ISP)  
PIC18F26J13@SSOP28 (ISP)  
PIC18F26J50 (ISP)  
PIC18F26J50@SOIC28 [SA404]  
PIC18F26J50@SSOP28 [SA626A]  
PIC18F26J53  
PIC18F26J53@QFN28 [SA685]  
PIC18F26J53@SOIC28 [SA404]  
PIC18F26J53@SSOP28 [SA626A]  
PIC18F26K20  
PIC18F26K20 (ISP) (Low-V)  
PIC18F26K20@QFN28 (ISP) (High-V)  
PIC18F26K20@SOIC28 [SA404]  
PIC18F26K20@SOIC28 (ISP) (Low-V)  
PIC18F26K20@SSOP28 (ISP) (High-V)  
PIC18F26K22  
PIC18F26K22@QFN28 [SA685]  
PIC18F26K22@SOIC28 [SA404]  
PIC18F26K22@SSOP28 [SA626A]  
PIC18F26K50  
PIC18F26K50@QFN28 [SA685]  
PIC18F26K50@SSOP28 [SA626A]  
PIC18F26K80 (ISP)  
PIC18F26K80@QFN28 (ISP)  
PIC18F26K80@SOIC28 (ISP)  
PIC18F26K80@SSOP28 (ISP)  
PIC18F27J13 (ISP)  
PIC18F27J13@QFN28 (ISP)  
PIC18F27J13@SOIC28 (ISP)  
PIC18F27J13@SSOP28 (ISP)  
PIC18F27J53 (ISP)  
PIC18F27J53@QFN28 (ISP)  
PIC18F27J53@SOIC28 (ISP)  
PIC18F27J53@SSOP28 (ISP)  
PIC18F4220 (ISP)  
PIC18F4220@QFN44 (ISP)  
PIC18F4220@QFN44 (ML) (ISP)  
PIC18F4220@TQFP44 (ISP)  
PIC18F4221 (ISP) (Low-V)  
PIC18F4221@QFN44 (ISP) (Low-V)  
PIC18F4221@QFN44 (ML) (ISP) (Low-V)  
PIC18F4221@TQFP44 (ISP) (Low-V)  
PIC18F4320 (ISP)  
PIC18F4320@QFN44 (ISP)  
PIC18F4320@QFN44 (ML) (ISP)  
PIC18F4320@TQFP44 (ISP)  
PIC18F4321 (ISP) (Low-V)  
PIC18F4321@QFN44 (ISP) (Low-V)  
PIC18F4321@QFN44 (ML) (ISP) (Low-V)  
PIC18F4321@TQFP44 (ISP) (Low-V)  
PIC18F4331 (ISP)  
PIC18F4331@TQFP44 (ISP)

PIC18F43K20  
PIC18F43K20 (ISP) (Low-V)  
PIC18F43K20@QFN44 (ISP) (High-V)  
PIC18F43K20@QFN44 (ML) [SA737]  
PIC18F43K20@QFN44 (ML) (ISP) (L-V)  
PIC18F43K20@TQFP44 [SA245A-B4805]  
PIC18F43K20@TQFP44 (ISP) (High-V)  
PIC18F43K22  
PIC18F43K22@QFN44 [SA712]  
PIC18F43K22@QFN44 (ML) [SA737]  
PIC18F43K22@TQFP44 [SA245A-B4805]  
PIC18F43K22@TQFP44 (ISP) (H-V)  
PIC18F4410 (ISP) (Low-V)  
PIC18F4410@QFN44 (ISP) (Low-V)  
PIC18F4410@QFN44 (ML) (ISP) (Low-V)  
PIC18F4410@TQFP44 (ISP) (Low-V)  
PIC18F442 (ISP)  
PIC18F442@PLCC44 (ISP)  
PIC18F442@TQFP44 [SA245A-B4805]  
PIC18F4420  
PIC18F4420@QFN44 [SA712]  
PIC18F4420@QFN44 (ML) [SA737]  
PIC18F4420@TQFP44 [SA245A-B4805]  
PIC18F4423  
PIC18F4423 (ISP) (Low-V)  
PIC18F4423@QFN44 (ISP) (High-V)  
PIC18F4423@QFN44 (ML) [SA737]  
PIC18F4423@QFN44 (ML) (ISP) (Low-V)  
PIC18F4423@TQFP44 (ISP) (High-V)  
PIC18F4431  
PIC18F4431@TQFP44 [SA245A-B4805]  
PIC18F4439  
PIC18F4439@TQFP44 [SA245A-B4805]  
PIC18F4450  
PIC18F4450@QFN44 [SA712]  
PIC18F4450@QFN44 (ML) [SA737]  
PIC18F4450@TQFP44 [SA245A-B4805]  
PIC18F4455  
PIC18F4455 (ISP) (Low-V)  
PIC18F4455@QFN44 (ISP) (High-V)  
PIC18F4455@QFN44 (ML) [SA737]  
PIC18F4455@QFN44 (ML) (ISP) (Low-V)  
PIC18F4455@TQFP44 (ISP) (High-V)  
PIC18F4458  
PIC18F4458 (ISP) (Low-V)  
PIC18F4458@QFN44 (ISP) (High-V)  
PIC18F4458@TQFP44 [SA245A-B4805]  
PIC18F4458@TQFP44 (ISP) (Low-V)  
PIC18F448 (ISP)  
PIC18F448@PLCC44 (ISP)  
PIC18F448@TQFP44 [SA245A-B4805]  
PIC18F4480  
PIC18F4480 (ISP) (Low-V)  
PIC18F43K20 (ISP) (High-V)  
PIC18F43K20@QFN44 [SA712]  
PIC18F43K20@QFN44 (ISP) (Low-V)  
PIC18F43K20@QFN44 (ML) (ISP) (H-V)  
PIC18F43K20@TQFP44 (ISP) (Low-V)  
PIC18F43K22 (ISP) (H-V)  
PIC18F43K22@QFN44 (ISP) (H-V)  
PIC18F43K22@QFN44 (ML) (ISP) (H-V)  
PIC18F4410  
PIC18F4410@QFN44 [SA712]  
PIC18F4410@QFN44 (ML) [SA737]  
PIC18F4410@TQFP44 [SA245A-B4805]  
PIC18F442  
PIC18F442@PLCC44 [SA244]  
PIC18F442@QFN44 [SA737]  
PIC18F442@TQFP44 (ISP)  
PIC18F4420 (ISP) (Low-V)  
PIC18F4420@QFN44 (ISP) (Low-V)  
PIC18F4420@QFN44 (ML) (ISP) (Low-V)  
PIC18F4420@TQFP44 (ISP) (Low-V)  
PIC18F4423 (ISP) (High-V)  
PIC18F4423@QFN44 [SA712]  
PIC18F4423@QFN44 (ISP) (Low-V)  
PIC18F4423@QFN44 (ML) (ISP) (H-V)  
PIC18F4423@TQFP44 [SA245A-B4805]  
PIC18F4423@TQFP44 (ISP) (Low-V)  
PIC18F4431 (ISP)  
PIC18F4431@TQFP44 (ISP)  
PIC18F4439 (ISP)  
PIC18F4439@TQFP44 (ISP)  
PIC18F4450 (ISP) (Low-V)  
PIC18F4450@QFN44 (ISP) (Low-V)  
PIC18F4450@QFN44 (ML) (ISP) (Low-V)  
PIC18F4450@TQFP44 (ISP) (Low-V)  
PIC18F4455 (ISP) (High-V)  
PIC18F4455@QFN44 [SA712]  
PIC18F4455@QFN44 (ISP) (Low-V)  
PIC18F4455@QFN44 (ML) (ISP) (H-V)  
PIC18F4455@TQFP44 [SA245A-B4805]  
PIC18F4455@TQFP44 (ISP) (Low-V)  
PIC18F4458 (ISP) (High-V)  
PIC18F4458@QFN44 [SA712]  
PIC18F4458@QFN44 (ISP) (Low-V)  
PIC18F4458@TQFP44 (ISP) (High-V)  
PIC18F448  
PIC18F448@PLCC44 [SA244]  
PIC18F448@QFN44 [SA737]  
PIC18F448@TQFP44 (ISP)  
PIC18F4480 (ISP) (High-V)  
PIC18F4480@QFN44 [SA712]

PIC18F4480@QFN44 (ISP) (High-V)  
PIC18F4480@QFN44 (ML) [SA737]  
PIC18F4480@QFN44 (ML) (ISP) (Low-V)  
PIC18F4480@TQFP44 (ISP) (High-V)  
PIC18F44J10  
PIC18F44J10@QFN44 [SA712]  
PIC18F44J10@QFN44 (ML) [SA737]  
PIC18F44J10@TQFP44 [SA245A-B4805]  
PIC18F44J10@TQFP44 (ISP)  
PIC18F44J11 (ISP)  
PIC18F44J11@QFN44 (ISP)  
PIC18F44J11@QFN44 (ML) (ISP)  
PIC18F44J11@TQFP44 [SA245A-B4805]  
PIC18F44J11@TQFP44 (ISP)  
PIC18F44J50 (ISP)  
PIC18F44J50@QFN44 (ISP)  
PIC18F44J50@QFN44 (ML) (ISP)  
PIC18F44J50@TQFP44 [SA245A-B4805]  
PIC18F44J50@TQFP44 (ISP)  
PIC18F44K20 (ISP) (High-V)  
PIC18F44K20@QFN44 [SA712]  
PIC18F44K20@QFN44 (ISP) (Low-V)  
PIC18F44K20@QFN44 (ML) (ISP) (H-V)  
PIC18F44K20@QFN44 (ML) (ISP) (L-V) [SA712]  
PIC18F44K20@TQFP44 [SA245A-B4805]  
PIC18F44K20@TQFP44 (ISP) (High-V)  
PIC18F44K22  
PIC18F44K22@QFN44 [SA712]  
PIC18F44K22@QFN44 (ML) [SA737]  
PIC18F44K22@TQFP44 [SA245A-B4805]  
PIC18F44K22@TQFP44 (ISP) (H-V)  
PIC18F4510 (ISP)  
PIC18F4510@QFN44 (ISP)  
PIC18F4510@QFN44 (ML) (ISP)  
PIC18F4510@TQFP44 (ISP)  
PIC18F4515 (ISP) (Low-V)  
PIC18F4515@QFN44 (ISP) (Low-V)  
PIC18F4515@QFN44 (ML) (ISP) (Low-V)  
PIC18F4515@TQFP44 (ISP) (Low-V)  
PIC18F452 (ISP)  
PIC18F452@PLCC44 (ISP)  
PIC18F452@TQFP44 [SA245A-B4805]  
PIC18F4520  
PIC18F4520@QFN44 [SA712]  
PIC18F4520@QFN44 (ML) [SA737]  
PIC18F4520@TQFP44 [SA245A-B4805]  
PIC18F4523  
PIC18F4523 (ISP) (Low-V)  
PIC18F4523@QFN44 (ISP) (High-V)  
PIC18F4523@QFN44 (ML) [SA737]  
PIC18F4523@QFN44 (ML) (ISP) (Low-V)  
PIC18F4523@TQFP44 (ISP) (High-V)  
PIC18F4525  
PIC18F4480@QFN44 (ISP) (Low-V)  
PIC18F4480@QFN44 (ML) (ISP) (H-V)  
PIC18F4480@TQFP44 [SA245A-B4805]  
PIC18F4480@TQFP44 (ISP) (Low-V)  
PIC18F44J10 (ISP)  
PIC18F44J10@QFN44 (ISP)  
PIC18F44J10@QFN44 (ML) (ISP)  
PIC18F44J11  
PIC18F44J11@QFN44 [SA712]  
PIC18F44J11@QFN44 (ML) [SA737]  
PIC18F44J50  
PIC18F44J50@QFN44 [SA712]  
PIC18F44J50@QFN44 (ML) [SA737]  
PIC18F44K20  
PIC18F44K20 (ISP) (Low-V)  
PIC18F44K20@QFN44 (ISP) (High-V)  
PIC18F44K20@QFN44 (ML) [SA737]  
PIC18F44K20@TQFP44 (ISP) (Low-V)  
PIC18F44K22 (ISP) (H-V)  
PIC18F44K22@QFN44 (ISP) (H-V)  
PIC18F44K22@QFN44 (ML) (ISP) (H-V)  
PIC18F4510  
PIC18F4510@QFN44 [SA712]  
PIC18F4510@QFN44 (ML) [SA737]  
PIC18F4510@TQFP44 [SA245A-B4805]  
PIC18F4515  
PIC18F4515@QFN44 [SA712]  
PIC18F4515@QFN44 (ML) [SA737]  
PIC18F4515@TQFP44 [SA245A-B4805]  
PIC18F452  
PIC18F452@PLCC44 [SA244]  
PIC18F452@QFN44 [SA737]  
PIC18F452@TQFP44 (ISP)  
PIC18F4520 (ISP)  
PIC18F4520@QFN44 (ISP)  
PIC18F4520@QFN44 (ML) (ISP)  
PIC18F4520@TQFP44 (ISP)  
PIC18F4523 (ISP) (High-V)  
PIC18F4523@QFN44 [SA712]  
PIC18F4523@QFN44 (ISP) (Low-V)  
PIC18F4523@QFN44 (ML) (ISP) (H-V)  
PIC18F4523@TQFP44 [SA245A-B4805]  
PIC18F4523@TQFP44 (ISP) (Low-V)  
PIC18F4525 (ISP) (Low-V)

PIC18F4525@QFN44 [SA712]  
PIC18F4525@QFN44 (ML) [SA737]  
PIC18F4525@TQFP44 [SA245A-B4805]  
PIC18F4539  
PIC18F4539@TQFP44 [SA245A-B4805]  
PIC18F4550  
PIC18F4550 (ISP) (Low-V)  
PIC18F4550@QFN44 (ISP) (High-V)  
PIC18F4550@QFN44 (ML) [SA737]  
PIC18F4550@QFN44 (ML) (ISP) (Low-V)  
PIC18F4550@TQFP44 (ISP) (High-V)  
PIC18F4553  
PIC18F4553 (ISP) (Low-V)  
PIC18F4553@QFN44 (ISP) (High-V)  
PIC18F4553@TQFP44 [SA245A-B4805]  
PIC18F4553@TQFP44 (ISP) (Low-V)  
PIC18F458 (ISP)  
PIC18F458@PLCC44 (ISP)  
PIC18F458@TQFP44 [SA245A-B4805]  
PIC18F4580  
PIC18F4580 (ISP) (Low-V)  
PIC18F4580@QFN44 (ISP) (High-V)  
PIC18F4580@QFN44 (ML) [SA737]  
PIC18F4580@QFN44 (ML) (ISP) (Low-V)  
PIC18F4580@TQFP44 (ISP) (High-V)  
PIC18F4585  
PIC18F4585 (ISP) (Low-V)  
PIC18F4585@QFN44 (ISP) (High-V)  
PIC18F4585@QFN44 (ML) [SA737]  
PIC18F4585@QFN44 (ML) (ISP) (Low-V)  
PIC18F4585@TQFP44 (ISP) (High-V)  
PIC18F45J10  
PIC18F45J10@QFN44 [SA712]  
PIC18F45J10@QFN44 (ML) [SA737]  
PIC18F45J10@TQFP44 [SA245A-B4805]  
PIC18F45J10@TQFP44 (ISP)  
PIC18F45J11 (ISP)  
PIC18F45J11@QFN44 (ISP)  
PIC18F45J11@QFN44 (ML) (ISP)  
PIC18F45J11@TQFP44 [SA245A-B4805]  
PIC18F45J11@TQFP44 (ISP)  
PIC18F45J50 (ISP)  
PIC18F45J50@QFN44 (ISP)  
PIC18F45J50@QFN44 (ML) (ISP)  
PIC18F45J50@TQFP44 [SA245A-B4805]  
PIC18F45J50@TQFP44 (ISP)  
PIC18F45K20 (ISP) (High-V)  
PIC18F45K20@QFN44 [SA712]  
PIC18F45K20@QFN44 (ISP) (Low-V)  
PIC18F45K20@QFN44 (ML) (ISP) (H-V)  
PIC18F45K20@TQFP44 [SA245A-B4805]  
PIC18F45K20@TQFP44 (ISP) (High-V)  
PIC18F45K22  
PIC18F4525@QFN44 (ISP) (Low-V)  
PIC18F4525@QFN44 (ML) (ISP) (Low-V)  
PIC18F4525@TQFP44 (ISP) (Low-V)  
PIC18F4539 (ISP)  
PIC18F4539@TQFP44 (ISP)  
PIC18F4550 (ISP) (High-V)  
PIC18F4550@QFN44 [SA712]  
PIC18F4550@QFN44 (ISP) (Low-V)  
PIC18F4550@QFN44 (ML) (ISP) (H-V)  
PIC18F4550@TQFP44 [SA245A-B4805]  
PIC18F4550@TQFP44 (ISP) (Low-V)  
PIC18F4553 (ISP) (High-V)  
PIC18F4553@QFN44 [SA712]  
PIC18F4553@QFN44 (ISP) (Low-V)  
PIC18F4553@TQFP44 (ISP) (High-V)  
PIC18F458  
PIC18F458@PLCC44 [SA244]  
PIC18F458@QFN44 [SA737]  
PIC18F458@TQFP44 (ISP)  
PIC18F4580 (ISP) (High-V)  
PIC18F4580@QFN44 [SA712]  
PIC18F4580@QFN44 (ISP) (Low-V)  
PIC18F4580@QFN44 (ML) (ISP) (H-V)  
PIC18F4580@TQFP44 [SA245A-B4805]  
PIC18F4580@TQFP44 (ISP) (Low-V)  
PIC18F4585 (ISP) (High-V)  
PIC18F4585@QFN44 [SA712]  
PIC18F4585@QFN44 (ISP) (Low-V)  
PIC18F4585@QFN44 (ML) (ISP) (H-V)  
PIC18F4585@TQFP44 [SA245A-B4805]  
PIC18F4585@TQFP44 (ISP) (Low-V)  
PIC18F45J10 (ISP)  
PIC18F45J10@QFN44 (ISP)  
PIC18F45J10@QFN44 (ML) (ISP)  
PIC18F45J11  
PIC18F45J11@QFN44 [SA712]  
PIC18F45J11@QFN44 (ML) [SA737]  
PIC18F45J50  
PIC18F45J50@QFN44 [SA712]  
PIC18F45J50@QFN44 (ML) [SA737]  
PIC18F45K20  
PIC18F45K20 (ISP) (Low-V)  
PIC18F45K20@QFN44 (ISP) (High-V)  
PIC18F45K20@QFN44 (ML) [SA737]  
PIC18F45K20@QFN44 (ML) (ISP) (L-V)  
PIC18F45K20@TQFP44 (ISP) (Low-V)  
PIC18F45K22 (ISP) (H-V)

PIC18F45K22@QFN44 [SA712]  
PIC18F45K22@QFN44 (ML) [SA737]  
PIC18F45K22@TQFP44 [SA245A-B4805]  
PIC18F45K22@TQFP44 (ISP) (H-V)  
PIC18F45K50@ISP  
PIC18F45K50@TQFP44 [SA245A-B4805]  
PIC18F45K80  
PIC18F45K80@QFN44 [SA737]  
PIC18F45K80@TQFP44 [SA245A-B4805]  
PIC18F45K80@TQFP44 (ISP)  
PIC18F4610 (ISP) (Low-V)  
PIC18F4610@QFN44 (ISP) (Low-V)  
PIC18F4610@QFN44 (ML) (ISP) (Low-V)  
PIC18F4610@TQFP44 (ISP) (Low-V)  
PIC18F4620 (ISP) (Low-V)  
PIC18F4620@QFN44 (ISP) (Low-V)  
PIC18F4620@QFN44 (ML) (ISP) (Low-V)  
PIC18F4620@TQFP44 (ISP) (Low-V)  
PIC18F4680 (ISP) (High-V)  
PIC18F4680@QFN44 [SA712]  
PIC18F4680@QFN44 (ISP) (Low-V)  
PIC18F4680@QFN44 (ML) (ISP) (H-V)  
PIC18F4680@TQFP44 [SA245A-B4805]  
PIC18F4680@TQFP44 (ISP) (Low-V)  
PIC18F4682 (ISP) (High-V)  
PIC18F4682@QFN44 [SA712]  
PIC18F4682@QFN44 (ISP) (Low-V)  
PIC18F4682@QFN44 (ML) (ISP) (H-V)  
PIC18F4682@TQFP44 [SA245A-B4805]  
PIC18F4682@TQFP44 (ISP) (Low-V)  
PIC18F4685 (ISP) (High-V)  
PIC18F4685@QFN44 [SA712]  
PIC18F4685@QFN44 (ISP) (Low-V)  
PIC18F4685@QFN44 (ML) (ISP) (H-V)  
PIC18F4685@TQFP44 [SA245A-B4805]  
PIC18F4685@TQFP44 (ISP) (Low-V)  
PIC18F46J11 (ISP)  
PIC18F46J11@QFN44 (ISP)  
PIC18F46J11@QFN44 (ML) (ISP)  
PIC18F46J11@TQFP44 [SA245A-B4805]  
PIC18F46J11@TQFP44 (ISP)  
PIC18F46J13 (ISP)  
PIC18F46J13@QFN44 (ML) [SA737]  
PIC18F46J13@TQFP44 [SA245A-B4805]  
PIC18F46J13@QFN44 (ISP)  
PIC18F46J13@TQFP44 (ISP)  
PIC18F46J50 (ISP)  
PIC18F46J50@QFN44 (ISP)  
PIC18F46J50@QFN44 (ML) (ISP)  
PIC18F46J50@TQFP44 [SA245A-B4805]  
PIC18F46J50@TQFP44 (ISP)  
PIC18F46J53 (ISP)  
PIC18F46J53@QFN44 (ML) [SA737]

PIC18F45K22@QFN44 (ISP) (H-V)  
PIC18F45K22@QFN44 (ML) (ISP) (H-V)  
PIC18F45K50  
PIC18F45K50@QFN44 [SA737]  
PIC18F45K80 (ISP)  
PIC18F45K80@QFN44 (ISP)  
PIC18F4610  
PIC18F4610@QFN44 [SA712]  
PIC18F4610@QFN44 (ML) [SA737]  
PIC18F4610@TQFP44 [SA245A-B4805]  
PIC18F4620  
PIC18F4620@QFN44 [SA712]  
PIC18F4620@QFN44 (ML) [SA737]  
PIC18F4620@TQFP44 [SA245A-B4805]  
PIC18F4680  
PIC18F4680 (ISP) (Low-V)  
PIC18F4680@QFN44 (ISP) (High-V)  
PIC18F4680@QFN44 (ML) [SA737]  
PIC18F4680@QFN44 (ML) (ISP) (Low-V)  
PIC18F4680@TQFP44 (ISP) (High-V)  
PIC18F4682  
PIC18F4682 (ISP) (Low-V)  
PIC18F4682@QFN44 (ISP) (High-V)  
PIC18F4682@QFN44 (ML) [SA737]  
PIC18F4682@QFN44 (ML) (ISP) (Low-V)  
PIC18F4682@TQFP44 (ISP) (High-V)  
PIC18F4685  
PIC18F4685 (ISP) (Low-V)  
PIC18F4685@QFN44 (ISP) (High-V)  
PIC18F4685@QFN44 (ML) [SA737]  
PIC18F4685@QFN44 (ML) (ISP) (Low-V)  
PIC18F4685@TQFP44 (ISP) (High-V)  
PIC18F46J11  
PIC18F46J11@QFN44 [SA712]  
PIC18F46J11@QFN44 (ML) [SA737]  
PIC18F46J13  
PIC18F46J13@QFN44 [SA712]  
PIC18F46J13@QFN44 (ML) (ISP)  
PIC18F46J50  
PIC18F46J50@QFN44 [SA712]  
PIC18F46J50@QFN44 (ML) [SA737]  
PIC18F46J53  
PIC18F46J53@QFN44 [SA712]

PIC18F46J53@TQFP44 [SA245A-B4805]	PIC18F46J53QFN44 (ML) (ISP)
PIC18F46J53QFN44 (ISP)	PIC18F46K20
PIC18F46J53TQFP44 (ISP)	PIC18F46K20 (ISP) (Low-V)
PIC18F46K20 (ISP) (High-V)	PIC18F46K20@QFN44 (ISP) (High-V)
PIC18F46K20@QFN44 [SA712]	PIC18F46K20@QFN44 (ML) [SA737]
PIC18F46K20@QFN44 (ISP) (Low-V)	PIC18F46K20@QFN44 (ML) (ISP) (L-V)
PIC18F46K20@QFN44 (ML) (ISP) (H-V)	PIC18F46K20@TQFP44 (ISP) (Low-V)
PIC18F46K20@TQFP44 [SA245A-B4805]	PIC18F46K22 (ISP) (H-V)
PIC18F46K20@TQFP44 (ISP) (High-V)	PIC18F46K22@QFN44 (ISP) (H-V)
PIC18F46K22	PIC18F46K22@QFN44 (ML) (ISP) (H-V)
PIC18F46K22@QFN44 [SA712]	
PIC18F46K22@QFN44 (ML) [SA737]	
PIC18F46K22@TQFP44 [SA245A-B4805]	
PIC18F46K22@TQFP44 (ISP) (H-V)	PIC18F46K50
PIC18F46K50@ISP	PIC18F46K50@QFN44 [SA737]
PIC18F46K50@TQFP44 [SA245A-B4805]	
PIC18F46K80	PIC18F46K80 (ISP)
PIC18F46K80@QFN44 [SA737]	PIC18F46K80@QFN44 (ISP)
PIC18F46K80@TQFP44 [SA245A-B4805]	
PIC18F46K80@TQFP44 (ISP)	PIC18F47J13
PIC18F47J13 (ISP)	PIC18F47J13@QFN44 [SA712]
PIC18F47J13@QFN44 (ML) [SA737]	
PIC18F47J13@TQFP44 [SA245A-B4805]	PIC18F47J13QFN44 (ML) (ISP)
PIC18F47J13QFN44 (ISP)	PIC18F47J53
PIC18F47J13TQFP44 (ISP)	PIC18F47J53@QFN44 [SA712]
PIC18F47J53 (ISP)	
PIC18F47J53@QFN44 (ML) [SA737]	
PIC18F47J53@TQFP44 [SA245A-B4805]	PIC18F47J53QFN44 (ML) (ISP)
PIC18F47J53QFN44 (ISP)	PIC18F6310@TQFP64 (ISP)
PIC18F47J53TQFP44 (ISP)	PIC18F6393@TQFP64 (ISP)
PIC18F6390@TQFP64 (ISP)	PIC18F63J90@TQFP64 (ISP)
PIC18F63J11@TQFP64 (ISP)	PIC18F6490@TQFP64 (ISP)
PIC18F6410@TQFP64 (ISP)	PIC18F64J11@TQFP64 (ISP)
PIC18F6493@TQFP64 (ISP)	PIC18F6520@TQFP64 (ISP)
PIC18F64J90@TQFP64 (ISP)	PIC18F6527@TQFP64 (ISP) (High-V)
PIC18F6525@TQFP64 (ISP)	PIC18F6585@PLCC68 (ISP)
PIC18F6527@TQFP64 (ISP) (Low-V)	PIC18F65J10@TQFP64 (ISP)
PIC18F6585@TQFP64 (ISP)	PIC18F65J11@TQFP64 (ISP)
PIC18F65J10@TQFP64 (ISP) (Enable)	PIC18F65J15@TQFP64 (ISP) (Enable)
PIC18F65J15@TQFP64 (ISP)	PIC18F65J90@TQFP64 (ISP)
PIC18F65J50@TQFP64 (ISP)	PIC18F65K22 (HVISP) (Enable)
PIC18F65K22 (HVISP) (Disable)	PIC18F65K22 (LVISP) (Enable)
PIC18F65K22 (LVISP) (Disable)	PIC18F65K80@TQFP64 (ISP)
PIC18F65K80@QFN64 (ISP)	PIC18F65K90 (HVISP) (Enable)
PIC18F65K90 (HVISP) (Disable)	PIC18F65K90 (LVISP) (Enable)
PIC18F65K90 (LVISP) (Disable)	PIC18F6621@TQFP64 (ISP)
PIC18F6620@TQFP64 (ISP)	PIC18F6622@TQFP64 (ISP) (Low-V)
PIC18F6622@TQFP64 (ISP) (High-V)	PIC18F6627@TQFP64 (ISP) (Low-V)
PIC18F6627@TQFP64 (ISP) (High-V)	PIC18F6628@TQFP64 (ISP) (Low-V)
PIC18F6628@TQFP64 (ISP) (High-V)	PIC18F6680@TQFP64 (ISP)
PIC18F6680@PLCC68 (ISP)	PIC18F66J10@TQFP64 (ISP) (Enable)
PIC18F66J10@TQFP64 (ISP)	PIC18F66J15@TQFP64 (ISP)
PIC18F66J11@TQFP64 (ISP)	

PIC18F66J15@TQFP64 (ISP) (Enable)	PIC18F66J16@TQFP64 (ISP)
PIC18F66J50@TQFP64 (ISP)	PIC18F66J55@TQFP64 (ISP)
PIC18F66J60@TQFP64 (ISP)	PIC18F66J65@TQFP64 (ISP)
PIC18F66J90@TQFP64 (ISP)	PIC18F66J93@TQFP64 (ISP)
PIC18F66K22 (HVISP) (Disable)	PIC18F66K22 (HVISP) (Enable)
PIC18F66K22 (LVISP) (Disable)	PIC18F66K22 (LVISP) (Enable)
PIC18F66K80@QFN64 (ISP)	PIC18F66K80@TQFP64 (ISP)
PIC18F66K90 (HVISP) (Disable)	PIC18F66K90 (HVISP) (Enable)
PIC18F66K90 (LVISP) (Disable)	PIC18F66K90 (LVISP) (Enable)
PIC18F6720@TQFP64 (ISP)	PIC18F6722@TQFP64 (ISP) (High-V)
PIC18F6722@TQFP64 (ISP) (Low-V)	PIC18F6723@TQFP64 (ISP) (High-V)
PIC18F6723@TQFP64 (ISP) (Low-V)	PIC18F67J10@TQFP64 (ISP)
PIC18F67J10@TQFP64 (ISP) (Enable)	PIC18F67J11@TQFP64 (ISP)
PIC18F67J50@TQFP64 (ISP)	PIC18F67J60@TQFP64 (ISP)
PIC18F67J90@TQFP64 (ISP)	PIC18F67J93@TQFP64 (ISP)
PIC18F67K22 (HVISP) (Disable)	PIC18F67K22 (HVISP) (Enable)
PIC18F67K22 (LVISP) (Disable)	PIC18F67K22 (LVISP) (Enable)
PIC18F67K90 (HVISP) (Disable)	PIC18F67K90 (HVISP) (Enable)
PIC18F67K90 (LVISP) (Disable)	PIC18F67K90 (LVISP) (Enable)
PIC18F8310@TQFP80 (ISP)	PIC18F8390@TQFP80 (ISP)
PIC18F8393@TQFP80 (ISP)	PIC18F83J11@TQFP80 (ISP)
PIC18F83J90@TQFP80 (ISP)	PIC18F8410@TQFP80 (ISP)
PIC18F8490@TQFP80 (ISP)	PIC18F8493@TQFP80 (ISP)
PIC18F84J11@TQFP80 (ISP)	PIC18F84J90@TQFP80 (ISP)
PIC18F8520@TQFP80 (ISP)	PIC18F8525@TQFP80 (ISP)
PIC18F8527@TQFP80 (ISP) (High-V)	PIC18F8527@TQFP80 (ISP) (Low-V)
PIC18F8585@TQFP80 (ISP)	PIC18F85J10@TQFP80 (ISP)
PIC18F85J10@TQFP80 (ISP) (Enable)	PIC18F85J11@TQFP80 (ISP)
PIC18F85J15@TQFP80 (ISP)	PIC18F85J15@TQFP80 (ISP) (Enable)
PIC18F85J50@TQFP80 (ISP)	PIC18F85J90@TQFP80 (ISP)
PIC18F85K22 (HVISP) (Disable)	PIC18F85K22 (HVISP) (Enable)
PIC18F85K22 (LVISP) (Disable)	PIC18F85K22 (LVISP) (Enable)
PIC18F85K90 (HVISP) (Disable)	PIC18F85K90 (HVISP) (Enable)
PIC18F85K90 (LVISP) (Disable)	PIC18F85K90 (LVISP) (Enable)
PIC18F8620@TQFP80 (ISP)	PIC18F8621@TQFP80 (ISP)
PIC18F8622@TQFP80 (ISP) (High-V)	PIC18F8622@TQFP80 (ISP) (Low-V)
PIC18F8627@TQFP80 (ISP) (High-V)	PIC18F8627@TQFP80 (ISP) (Low-V)
PIC18F8628@TQFP80 (ISP) (High-V)	PIC18F8628@TQFP80 (ISP) (Low-V)
PIC18F8680@TQFP80 (ISP)	PIC18F86J10@TQFP80 (ISP)
PIC18F86J10@TQFP80 (ISP) (Enable)	PIC18F86J11@TQFP80 (ISP)
PIC18F86J15@TQFP80 (ISP)	PIC18F86J15@TQFP80 (ISP) (Enable)
PIC18F86J16@TQFP80 (ISP)	PIC18F86J50@TQFP80 (ISP)
PIC18F86J55@TQFP80 (ISP)	PIC18F86J60@TQFP80 (ISP)
PIC18F86J65@TQFP80 (ISP)	PIC18F86J72@TQFP80 (ISP)
PIC18F86J72@TQFP80 (ISP) (Enable)	PIC18F86J90@TQFP80 (ISP)
PIC18F86J93@TQFP80 (ISP)	PIC18F86K22 (HVISP) (Disable)
PIC18F86K22 (HVISP) (Enable)	PIC18F86K22 (LVISP) (Disable)
PIC18F86K22 (LVISP) (Enable)	PIC18F86K90 (HVISP) (Disable)
PIC18F86K90 (HVISP) (Enable)	PIC18F86K90 (LVISP) (Disable)
PIC18F86K90 (LVISP) (Enable)	PIC18F8720@TQFP80 (ISP)
PIC18F8722@TQFP80 (ISP) (High-V)	PIC18F8722@TQFP80 (ISP) (Low-V)
PIC18F8723@TQFP80 (ISP) (High-V)	PIC18F8723@TQFP80 (ISP) (Low-V)
PIC18F87J10@TQFP80 (ISP)	PIC18F87J10@TQFP80 (ISP) (Enable)

PIC18F87J11@TQFP80 (ISP)  
PIC18F87J60@TQFP80 (ISP)  
PIC18F87J72@TQFP80 (ISP) (Enable)  
PIC18F87J93@TQFP80 (ISP)  
PIC18F87K22 (HVISP) (Enable)  
PIC18F87K22 (LVISP) (Enable)  
PIC18F87K90 (HVISP) (Enable)  
PIC18F87K90 (LVISP) (Enable)  
PIC18F96J65@TQFP100 (ISP)  
PIC18LC452  
PIC18LC452@TQFP44 [SA245A-B4805]  
PIC18LF1220 (ISP)  
PIC18LF1220@S0IC18 (ISP)  
PIC18LF1220@SSOP20 (ISP)  
PIC18LF1320 (ISP)  
PIC18LF1320@S0IC18 (ISP)  
PIC18LF1320@SSOP20 (ISP)  
PIC18LF13K22 (ISP) (High-V)  
PIC18LF13K22@QFN20 (ISP) (High-V)  
PIC18LF13K22@S0IC20 [SA404]  
PIC18LF13K22@S0IC20 (ISP) (Low-V)  
PIC18LF13K22@SSOP20 (ISP) (High-V)  
PIC18LF13K50  
PIC18LF13K50 (ISP) (Low-V)  
PIC18LF13K50@QFN20 (ISP) (Low-V)  
PIC18LF13K50@S0IC20 (ISP) (High-V)  
PIC18LF13K50@SSOP20 [SA626A]  
PIC18LF13K50@SSOP20 (ISP) (Low-V)  
PIC18LF14K22 (ISP) (High-V)  
PIC18LF14K22@QFN20 (ISP) (High-V)  
PIC18LF14K22@S0IC20 [SA404]  
PIC18LF14K22@S0IC20 (ISP) (Low-V)  
PIC18LF14K22@SSOP20 (ISP) (High-V)  
PIC18LF14K50  
PIC18LF14K50 (ISP) (Low-V)  
PIC18LF14K50@QFN20 (ISP) (Low-V)  
PIC18LF14K50@S0IC20 (ISP) (High-V)  
PIC18LF14K50@SSOP20 [SA626A]  
PIC18LF14K50@SSOP20 (ISP) (Low-V)  
PIC18LF2220 (ISP)  
PIC18LF2220@S0IC28 (ISP)  
PIC18LF2221 (ISP) (Low-V)  
PIC18LF2221@S0IC28 [SA404]  
PIC18LF2221@SSOP28 [SA626A]  
PIC18LF2320  
PIC18LF2320@S0IC28 [SA404]  
PIC18LF2321  
PIC18LF2321@QFN28 (ISP) (Low-V)  
PIC18LF2321@S0IC28 (ISP) (Low-V)  
PIC18LF2321@SSOP28 (ISP) (Low-V)  
PIC18LF2331 (ISP)  
PIC18LF2331@S0IC28 (ISP)  
PIC18LF23K22 (ISP) (H-V)  
PIC18F87J50@TQFP80 (ISP)  
PIC18F87J72@TQFP80 (ISP)  
PIC18F87J90@TQFP80 (ISP)  
PIC18F87K22 (HVISP) (Disable)  
PIC18F87K22 (LVISP) (Disable)  
PIC18F87K90 (HVISP) (Disable)  
PIC18F87K90 (LVISP) (Disable)  
PIC18F96J60@TQFP100 (ISP)  
PIC18F97J60@TQFP100 (ISP)  
PIC18LC452@PLCC44 [SA244]  
PIC18LF1220  
PIC18LF1220@S0IC18 [SA404]  
PIC18LF1220@SSOP20 [SA626A]  
PIC18LF1320  
PIC18LF1320@S0IC18 [SA404]  
PIC18LF1320@SSOP20 [SA626A]  
PIC18LF13K22  
PIC18LF13K22 (ISP) (Low-V)  
PIC18LF13K22@QFN20 (ISP) (Low-V)  
PIC18LF13K22@S0IC20 (ISP) (High-V)  
PIC18LF13K22@SSOP20 [SA626A]  
PIC18LF13K22@SSOP20 (ISP) (Low-V)  
PIC18LF13K50 (ISP) (High-V)  
PIC18LF13K50@QFN20 (ISP) (High-V)  
PIC18LF13K50@S0IC20 [SA404]  
PIC18LF13K50@S0IC20 (ISP) (Low-V)  
PIC18LF13K50@SSOP20 (ISP) (High-V)  
PIC18LF14K22  
PIC18LF14K22 (ISP) (Low-V)  
PIC18LF14K22@QFN20 (ISP) (Low-V)  
PIC18LF14K22@S0IC20 (ISP) (High-V)  
PIC18LF14K22@SSOP20 [SA626A]  
PIC18LF14K22@SSOP20 (ISP) (Low-V)  
PIC18LF14K50 (ISP) (High-V)  
PIC18LF14K50@QFN20 (ISP) (High-V)  
PIC18LF14K50@S0IC20 [SA404]  
PIC18LF14K50@S0IC20 (ISP) (Low-V)  
PIC18LF14K50@SSOP20 (ISP) (High-V)  
PIC18LF2220  
PIC18LF2220@S0IC28 [SA404]  
PIC18LF2221  
PIC18LF2221@QFN28 (ISP) (Low-V)  
PIC18LF2221@S0IC28 (ISP) (Low-V)  
PIC18LF2221@SSOP28 (ISP) (Low-V)  
PIC18LF2320 (ISP)  
PIC18LF2320@S0IC28 (ISP)  
PIC18LF2321 (ISP) (Low-V)  
PIC18LF2321@S0IC28 [SA404]  
PIC18LF2321@SSOP28 [SA626A]  
PIC18LF2331  
PIC18LF2331@S0IC28 [SA404]  
PIC18LF23K22  
PIC18LF23K22@QFN28 (ISP) (H-V)

PIC18LF23K22@S0IC28 [SA404]  
PIC18LF23K22@SSOP28 [SA626A]  
PIC18LF2410  
PIC18LF2410@QFN28 (ISP) (Low-V)  
PIC18LF2410@S0IC28 (ISP) (Low-V)  
PIC18LF2410@SSOP28 (ISP) (Low-V)  
PIC18LF242 (ISP)  
PIC18LF242@S0IC28 (ISP)  
PIC18LF2420 (ISP) (High-V)  
PIC18LF2420@QFN28 (ISP) (High-V)  
PIC18LF2420@S0IC28 [SA404]  
PIC18LF2420@S0IC28 (ISP) (Low-V)  
PIC18LF2420@SSOP28 (ISP) (High-V)  
PIC18LF2423  
PIC18LF2423 (ISP) (Low-V)  
PIC18LF2423@QFN28 (ISP) (Low-V)  
PIC18LF2423@S0IC28 (ISP) (High-V)  
PIC18LF2423@SSOP28 [SA626A]  
PIC18LF2423@SSOP28 (ISP) (Low-V)  
PIC18LF2431 (ISP)  
PIC18LF2431@S0IC28 (ISP)  
PIC18LF2439 (ISP)  
PIC18LF2439@S0IC28 (ISP)  
PIC18LF2450 (ISP) (Low-V)  
PIC18LF2450@S0IC28 [SA404]  
PIC18LF2450@SSOP28 [SA626A]  
PIC18LF2455  
PIC18LF2455 (ISP) (Low-V)  
PIC18LF2455@S0IC28 (ISP) (High-V)  
PIC18LF2455@SSOP28 [SA626A]  
PIC18LF2455@SSOP28 (ISP) (Low-V)  
PIC18LF248 (ISP)  
PIC18LF248@S0IC28 (ISP)  
PIC18LF2480 (ISP) (High-V)  
PIC18LF2480@QFN28 (ISP) (High-V)  
PIC18LF2480@S0IC28 [SA404]  
PIC18LF2480@S0IC28 (ISP) (Low-V)  
PIC18LF2480@SSOP28 (ISP) (High-V)  
PIC18LF24J10  
PIC18LF24J10@QFN28 (ISP)  
PIC18LF24J10@S0IC28 (ISP)  
PIC18LF24J10@SSOP28 (ISP)  
PIC18LF24J11 (ISP)  
PIC18LF24J11@S0IC28 [SA404]  
PIC18LF24J11@SSOP28 [SA626A]  
PIC18LF24J50  
PIC18LF24J50@QFN28 (ISP)  
PIC18LF24J50@S0IC28 (ISP)  
PIC18LF24J50@SSOP28 (ISP)  
PIC18LF24K22 (ISP) (H-V)  
PIC18LF24K22@QFN28 (ISP) (H-V)  
PIC18LF24K22@S0IC28 (ISP) (H-V)  
PIC18LF24K22@SSOP28 (ISP) (H-V)  
PIC18LF23K22@S0IC28 (ISP) (H-V)  
PIC18LF23K22@SSOP28 (ISP) (H-V)  
PIC18LF2410 (ISP) (Low-V)  
PIC18LF2410@S0IC28 [SA404]  
PIC18LF2410@SSOP28 [SA626A]  
PIC18LF242  
PIC18LF242@S0IC28 [SA404]  
PIC18LF2420  
PIC18LF2420 (ISP) (Low-V)  
PIC18LF2420@QFN28 (ISP) (Low-V)  
PIC18LF2420@S0IC28 (ISP) (High-V)  
PIC18LF2420@SSOP28 [SA626A]  
PIC18LF2420@SSOP28 (ISP) (Low-V)  
PIC18LF2423 (ISP) (High-V)  
PIC18LF2423@QFN28 (ISP) (High-V)  
PIC18LF2423@S0IC28 [SA404]  
PIC18LF2423@S0IC28 (ISP) (Low-V)  
PIC18LF2423@SSOP28 (ISP) (High-V)  
PIC18LF2431  
PIC18LF2431@S0IC28 [SA404]  
PIC18LF2439  
PIC18LF2439@S0IC28 [SA404]  
PIC18LF2450  
PIC18LF2450@QFN28 (ISP) (Low-V)  
PIC18LF2450@S0IC28 (ISP) (Low-V)  
PIC18LF2450@SSOP28 (ISP) (Low-V)  
PIC18LF2455 (ISP) (High-V)  
PIC18LF2455@S0IC28 [SA404]  
PIC18LF2455@S0IC28 (ISP) (Low-V)  
PIC18LF2455@SSOP28 (ISP) (High-V)  
PIC18LF248  
PIC18LF248@S0IC28 [SA404]  
PIC18LF2480  
PIC18LF2480 (ISP) (Low-V)  
PIC18LF2480@QFN28 (ISP) (Low-V)  
PIC18LF2480@S0IC28 (ISP) (High-V)  
PIC18LF2480@SSOP28 [SA626A]  
PIC18LF2480@SSOP28 (ISP) (Low-V)  
PIC18LF24J10 (ISP)  
PIC18LF24J10@S0IC28 [SA404]  
PIC18LF24J10@SSOP28 [SA626A]  
PIC18LF24J11  
PIC18LF24J11@QFN28 (ISP)  
PIC18LF24J11@S0IC28 (ISP)  
PIC18LF24J11@SSOP28 (ISP)  
PIC18LF24J50 (ISP)  
PIC18LF24J50@S0IC28 [SA404]  
PIC18LF24J50@SSOP28 [SA626A]  
PIC18LF24K22  
PIC18LF24K22@QFN28 [SA685]  
PIC18LF24K22@S0IC28 [SA404]  
PIC18LF24K22@SSOP28 [SA626A]  
PIC18LF24K50

PIC18LF24K50@ISP  
PIC18LF24K50@SOIC28 [SA404]  
PIC18LF2510  
PIC18LF2510@QFN28 (ISP)  
PIC18LF2510@SOIC28 (ISP)  
PIC18LF2510@SSOP28 (ISP)  
PIC18LF2515 (ISP) (Low-V)  
PIC18LF2515@SOIC28 (ISP) (Low-V)  
PIC18LF2515@SSOP28 (ISP) (Low-V)  
PIC18LF252 (ISP)  
PIC18LF252@SOIC28 (ISP)  
PIC18LF2520 (ISP) (High-V)  
PIC18LF2520@QFN28 [SA685]  
PIC18LF2520@QFN28 (ISP) (Low-V)  
PIC18LF2520@SOIC28 (ISP) (High-V)  
PIC18LF2520@SSOP28 [SA626A]  
PIC18LF2520@SSOP28 (ISP) (Low-V)  
PIC18LF2523 (ISP) (High-V)  
PIC18LF2523@QFN28 (ISP) (High-V)  
PIC18LF2523@SOIC28 [SA404]  
PIC18LF2523@SOIC28 (ISP) (Low-V)  
PIC18LF2523@SSOP28 (ISP) (High-V)  
PIC18LF2525  
PIC18LF2525@SOIC28 [SA404]  
PIC18LF2525@SSOP28 [SA626A]  
PIC18LF2539  
PIC18LF2539@SOIC28 [SA404]  
PIC18LF2550  
PIC18LF2550 (ISP) (Low-V)  
PIC18LF2550@SOIC28 (ISP) (High-V)  
PIC18LF2550@SSOP28 [SA626A]  
PIC18LF2550@SSOP28 (ISP) (Low-V)  
PIC18LF258 (ISP)  
PIC18LF258@SOIC28 (ISP)  
PIC18LF2580 (ISP) (High-V)  
PIC18LF2580@QFN28 (ISP) (High-V)  
PIC18LF2580@SOIC28 [SA404]  
PIC18LF2580@SOIC28 (ISP) (Low-V)  
PIC18LF2580@SSOP28 (ISP) (High-V)  
PIC18LF2585  
PIC18LF2585 (ISP) (Low-V)  
PIC18LF2585@SDIP28 (ISP) (High-V)  
PIC18LF2585@SOIC28 [SA404]  
PIC18LF2585@SOIC28 (ISP) (Low-V)  
PIC18LF2585@SSOP28 (ISP) (High-V)  
PIC18LF25J10  
PIC18LF25J10@QFN28 (ISP)  
PIC18LF25J10@SOIC28 (ISP)  
PIC18LF25J10@SSOP28 (ISP)  
PIC18LF25J11 (ISP)  
PIC18LF25J11@SOIC28 [SA404]  
PIC18LF25J11@SSOP28 [SA626A]  
PIC18LF25J50  
PIC18LF24K50@QFN28 [SA685]  
PIC18LF24K50@SSOP28 [SA626A]  
PIC18LF2510 (ISP)  
PIC18LF2510@SOIC28 [SA404]  
PIC18LF2510@SSOP28 [SA626A]  
PIC18LF2515  
PIC18LF2515@SOIC28 [SA404]  
PIC18LF2515@SSOP28 [SA626A]  
PIC18LF252  
PIC18LF252@SOIC28 [SA404]  
PIC18LF2520  
PIC18LF2520 (ISP) (Low-V)  
PIC18LF2520@QFN28 (ISP) (High-V)  
PIC18LF2520@SOIC28 [SA404]  
PIC18LF2520@SOIC28 (ISP) (Low-V)  
PIC18LF2520@SSOP28 (ISP) (High-V)  
PIC18LF2523  
PIC18LF2523 (ISP) (Low-V)  
PIC18LF2523@QFN28 (ISP) (Low-V)  
PIC18LF2523@SOIC28 (ISP) (High-V)  
PIC18LF2523@SSOP28 [SA626A]  
PIC18LF2523@SSOP28 (ISP) (Low-V)  
PIC18LF2525 (ISP) (Low-V)  
PIC18LF2525@SOIC28 (ISP) (Low-V)  
PIC18LF2525@SSOP28 (ISP) (Low-V)  
PIC18LF2539 (ISP)  
PIC18LF2539@SOIC28 (ISP)  
PIC18LF2550 (ISP) (High-V)  
PIC18LF2550@SOIC28 [SA404]  
PIC18LF2550@SOIC28 (ISP) (Low-V)  
PIC18LF2550@SSOP28 (ISP) (High-V)  
PIC18LF258  
PIC18LF258@SOIC28 [SA404]  
PIC18LF2580  
PIC18LF2580 (ISP) (Low-V)  
PIC18LF2580@QFN28 (ISP) (Low-V)  
PIC18LF2580@SOIC28 (ISP) (High-V)  
PIC18LF2580@SSOP28 [SA626A]  
PIC18LF2580@SSOP28 (ISP) (Low-V)  
PIC18LF2585 (ISP) (High-V)  
PIC18LF2585@SDIP28 [SA653]  
PIC18LF2585@SDIP28 (ISP) (Low-V)  
PIC18LF2585@SOIC28 (ISP) (High-V)  
PIC18LF2585@SSOP28 [SA626A]  
PIC18LF2585@SSOP28 (ISP) (Low-V)  
PIC18LF25J10 (ISP)  
PIC18LF25J10@SOIC28 [SA404]  
PIC18LF25J10@SSOP28 [SA626A]  
PIC18LF25J11  
PIC18LF25J11@QFN28 (ISP)  
PIC18LF25J11@SOIC28 (ISP)  
PIC18LF25J11@SSOP28 (ISP)  
PIC18LF25J50 (ISP)

PIC18LF25J50@QFN28 (ISP)  
PIC18LF25J50@SOIC28 (ISP)  
PIC18LF25J50@SSOP28 (ISP)  
PIC18LF25K22 (ISP) (H-V)  
PIC18LF25K22@QFN28 (ISP) (H-V)  
PIC18LF25K22@SOIC28 (ISP) (H-V)  
PIC18LF25K22@SSOP28 (ISP) (H-V)  
PIC18LF25K50@ISP  
PIC18LF25K50@SOIC28 [SA404]  
PIC18LF25K80  
PIC18LF25K80@QFN28 [SA685]  
PIC18LF25K80@SOIC28 [SA404]  
PIC18LF25K80@SSOP28 [SA626A]  
PIC18LF2610  
PIC18LF2610@SOIC28 [SA404]  
PIC18LF2610@SSOP28 [SA626A]  
PIC18LF2620  
PIC18LF2620@SOIC28 [SA404]  
PIC18LF2620@SSOP28 [SA626A]  
PIC18LF2680  
PIC18LF2680 (ISP) (Low-V)  
PIC18LF2680@SDIP28 (ISP) (High-V)  
PIC18LF2680@SOIC28 [SA404]  
PIC18LF2680@SOIC28 (ISP) (Low-V)  
PIC18LF2680@SSOP28 (ISP) (High-V)  
PIC18LF2682  
PIC18LF2682 (ISP) (Low-V)  
PIC18LF2682@QFN28 (ISP) (Low-V)  
PIC18LF2682@SOIC28 (ISP) (High-V)  
PIC18LF2682@SSOP28 [SA626A]  
PIC18LF2682@SSOP28 (ISP) (Low-V)  
PIC18LF2685 (ISP) (High-V)  
PIC18LF2685@QFN28 (ISP) (High-V)  
PIC18LF2685@SOIC28 [SA404]  
PIC18LF2685@SOIC28 (ISP) (Low-V)  
PIC18LF2685@SSOP28 (ISP) (High-V)  
PIC18LF26J11  
PIC18LF26J11@QFN28 (ISP)  
PIC18LF26J11@SOIC28 (ISP)  
PIC18LF26J11@SSOP28 (ISP)  
PIC18LF26J13 (ISP)  
PIC18LF26J13@QFN28 (ISP)  
PIC18LF26J13@SOIC28 (ISP)  
PIC18LF26J13@SSOP28 (ISP)  
PIC18LF26J50 (ISP)  
PIC18LF26J50@SOIC28 [SA626A]  
PIC18LF26J50@SSOP28  
PIC18LF26J53  
PIC18LF26J53@QFN28 [SA685]  
PIC18LF26J53@SOIC28 [SA404]  
PIC18LF26J53@SSOP28 [SA626A]  
PIC18LF26K22  
PIC18LF26K22@QFN28 [SA685]  
PIC18LF25J50@SOIC28 [SA404]  
PIC18LF25J50@SSOP28 [SA626A]  
PIC18LF25K22  
PIC18LF25K22@QFN28 [SA685]  
PIC18LF25K22@SOIC28 [SA404]  
PIC18LF25K22@SSOP28 [SA626A]  
PIC18LF25K50  
PIC18LF25K50@QFN28 [SA685]  
PIC18LF25K50@SSOP28 [SA626A]  
PIC18LF25K80 (ISP)  
PIC18LF25K80@QFN28 (ISP)  
PIC18LF25K80@SOIC28 (ISP)  
PIC18LF25K80@SSOP28 (ISP)  
PIC18LF2610 (ISP) (Low-V)  
PIC18LF2610@SOIC28 (ISP) (Low-V)  
PIC18LF2610@SSOP28 (ISP) (Low-V)  
PIC18LF2620 (ISP) (Low-V)  
PIC18LF2620@SOIC28 (ISP) (Low-V)  
PIC18LF2620@SSOP28 (ISP) (Low-V)  
PIC18LF2680 (ISP) (High-V)  
PIC18LF2680@SDIP28 [SA653]  
PIC18LF2680@SDIP28 (ISP) (Low-V)  
PIC18LF2680@SOIC28 (ISP) (High-V)  
PIC18LF2680@SSOP28 [SA626A]  
PIC18LF2680@SSOP28 (ISP) (Low-V)  
PIC18LF2682 (ISP) (High-V)  
PIC18LF2682@QFN28 (ISP) (High-V)  
PIC18LF2682@SOIC28 [SA404]  
PIC18LF2682@SOIC28 (ISP) (Low-V)  
PIC18LF2682@SSOP28 (ISP) (High-V)  
PIC18LF2685  
PIC18LF2685 (ISP) (Low-V)  
PIC18LF2685@QFN28 (ISP) (Low-V)  
PIC18LF2685@SOIC28 (ISP) (High-V)  
PIC18LF2685@SSOP28 [SA626A]  
PIC18LF2685@SSOP28 (ISP) (Low-V)  
PIC18LF26J11 (ISP)  
PIC18LF26J11@SOIC28 [SA404]  
PIC18LF26J11@SSOP28 [SA626A]  
PIC18LF26J13  
PIC18LF26J13@QFN28 [SA685]  
PIC18LF26J13@SOIC28 [SA404]  
PIC18LF26J13@SSOP28 [SA626A]  
PIC18LF26J50  
PIC18LF26J50@QFN28 (ISP)  
PIC18LF26J50@SOIC28 (ISP)  
PIC18LF26J50@SSOP28 (ISP)  
PIC18LF26J53 (ISP)  
PIC18LF26J53@QFN28 (ISP)  
PIC18LF26J53@SOIC28 (ISP)  
PIC18LF26J53@SSOP28 (ISP)  
PIC18LF26K22 (ISP) (H-V)  
PIC18LF26K22@QFN28 (ISP) (H-V)

PIC18LF26K22@SOIC28 [SA404]  
PIC18LF26K22@SSOP28 [SA626A]  
PIC18LF26K50  
PIC18LF26K50@QFN28 [SA685]  
PIC18LF26K50@SSOP28 [SA626A]  
PIC18LF26K80 (ISP)  
PIC18LF26K80@QFN28 (ISP)  
PIC18LF26K80@SOIC28 (ISP)  
PIC18LF26K80@SSOP28 (ISP)  
PIC18LF27J13 (ISP)  
PIC18LF27J13@QFN28 (ISP)  
PIC18LF27J13@SOIC28 (ISP)  
PIC18LF27J13@SSOP28 (ISP)  
PIC18LF27J53 (ISP)  
PIC18LF27J53@QFN28 (ISP)  
PIC18LF27J53@SOIC28 (ISP)  
PIC18LF27J53@SSOP28 (ISP)  
PIC18LF4220 (ISP)  
PIC18LF4220@QFN44 (ISP)  
PIC18LF4220@QFN44 (ML) (ISP)  
PIC18LF4220@TQFP44 [SA245A-B4805]  
PIC18LF4220@TQFP44 (ISP)  
PIC18LF4221 (ISP) (Low-V)  
PIC18LF4221@QFN44 (ISP) (Low-V)  
PIC18LF4221@QFN44 (ML) (ISP) (L-V)  
PIC18LF4221@TQFP44 [SA245A-B4805]  
PIC18LF4221@TQFP44 (ISP) (Low-V)  
PIC18LF4320 (ISP)  
PIC18LF4320@QFN44 (ISP)  
PIC18LF4320@QFN44 (ML) (ISP)  
PIC18LF4320@TQFP44 [SA245A-B4805]  
PIC18LF4320@TQFP44 (ISP)  
PIC18LF4321 (ISP) (Low-V)  
PIC18LF4321@QFN44 (ISP) (Low-V)  
PIC18LF4321@QFN44 (ML) (ISP) (L-V)  
PIC18LF4321@TQFP44 [SA245A-B4805]  
PIC18LF4321@TQFP44 (ISP) (Low-V)  
PIC18LF4331 (ISP)  
PIC18LF4331@TQFP44 [SA245A-B4805]  
PIC18LF4331@TQFP44 (ISP)  
PIC18LF43K22 (ISP) (H-V)  
PIC18LF43K22@QFN44 (ISP) (H-V)  
PIC18LF43K22@QFN44 (ML) (ISP) (H-V)  
PIC18LF43K22@TQFP44 [SA245A-B4805]  
PIC18LF43K22@TQFP44 (ISP) (H-V)  
PIC18LF4410 (ISP) (Low-V)  
PIC18LF4410@QFN44 (ISP) (Low-V)  
PIC18LF4410@QFN44 (ML) (ISP) (L-V)  
PIC18LF4410@TQFP44 [SA245A-B4805]  
PIC18LF4410@TQFP44 (ISP) (Low-V)  
PIC18LF442 (ISP)  
PIC18LF442@PLCC44 (ISP)  
PIC18LF442@TQFP44 [SA245A-B4805]

PIC18LF26K22@SOIC28 (ISP) (H-V)  
PIC18LF26K22@SSOP28 (ISP) (H-V)  
PIC18LF26K50@ISP  
PIC18LF26K50@SOIC28 [SA404]  
PIC18LF26K80  
PIC18LF26K80@QFN28 [SA685]  
PIC18LF26K80@SOIC28 [SA404]  
PIC18LF26K80@SSOP28 [SA626A]  
PIC18LF27J13  
PIC18LF27J13@QFN28 [SA685]  
PIC18LF27J13@SOIC28 [SA404]  
PIC18LF27J13@SSOP28 [SA626A]  
PIC18LF27J53  
PIC18LF27J53@QFN28 [SA685]  
PIC18LF27J53@SOIC28 [SA404]  
PIC18LF27J53@SSOP28 [SA626A]  
PIC18LF4220  
PIC18LF4220@QFN44 [SA712]  
PIC18LF4220@QFN44 (ML) [SA737]  
PIC18LF4221  
PIC18LF4221@QFN44 [SA712]  
PIC18LF4221@QFN44 (ML) [SA737]  
PIC18LF4320  
PIC18LF4320@QFN44 [SA712]  
PIC18LF4320@QFN44 (ML) [SA737]  
PIC18LF4321  
PIC18LF4321@QFN44 [SA712]  
PIC18LF4321@QFN44 (ML) [SA737]  
PIC18LF4331  
PIC18LF43K22  
PIC18LF43K22@QFN44 [SA712]  
PIC18LF43K22@QFN44 (ML) [SA737]  
PIC18LF4410  
PIC18LF4410@QFN44 [SA712]  
PIC18LF4410@QFN44 (ML) [SA737]  
PIC18LF442  
PIC18LF442@PLCC44 [SA244]  
PIC18LF442@QFN44 [SA737]  
PIC18LF442@TQFP44 (ISP)

PIC18LF4420	PIC18LF4420 (ISP) (Low-V)
PIC18LF4420@QFN44 [SA712]	PIC18LF4420@QFN44 (ISP) (Low-V)
PIC18LF4420@QFN44 (ML) [SA737]	PIC18LF4420@QFN44 (ML) (ISP) (L-V)
PIC18LF4420@TQFP44 [SA245A-B4805]	
PIC18LF4420@TQFP44 (ISP) (Low-V)	PIC18LF4423
PIC18LF4423 (ISP) (High-V)	PIC18LF4423 (ISP) (Low-V)
PIC18LF4423@QFN44 [SA712]	PIC18LF4423@QFN44 (ISP) (High-V)
PIC18LF4423@QFN44 (ISP) (Low-V)	PIC18LF4423@QFN44 (ML) [SA737]
PIC18LF4423@QFN44 (ML) (ISP) (H-V)	PIC18LF4423@QFN44 (ML) (ISP) (L-V)
PIC18LF4423@TQFP44 [SA245A-B4805]	
PIC18LF4423@TQFP44 (ISP) (High-V)	PIC18LF4423@TQFP44 (ISP) (Low-V)
PIC18LF4431	PIC18LF4431 (ISP)
PIC18LF4431@TQFP44 [SA245A-B4805]	
PIC18LF4431@TQFP44 (ISP)	PIC18LF4439
PIC18LF4439 (ISP)	
PIC18LF4439@TQFP44 [SA245A-B4805]	
PIC18LF4439@TQFP44 (ISP)	PIC18LF4450
PIC18LF4450 (ISP) (Low-V)	PIC18LF4450@QFN44 [SA712]
PIC18LF4450@QFN44 (ISP) (Low-V)	PIC18LF4450@QFN44 (ML) [SA737]
PIC18LF4450@QFN44 (ML) (ISP) (L-V)	
PIC18LF4450@TQFP44 [SA245A-B4805]	
PIC18LF4450@TQFP44 (ISP) (Low-V)	PIC18LF4455
PIC18LF4455 (ISP) (High-V)	PIC18LF4455 (ISP) (Low-V)
PIC18LF4455@QFN44 [SA712]	PIC18LF4455@QFN44 (ISP) (High-V)
PIC18LF4455@QFN44 (ISP) (Low-V)	PIC18LF4455@QFN44 (ML) [SA737]
PIC18LF4455@QFN44 (ML) (ISP) (H-V)	PIC18LF4455@QFN44 (ML) (ISP) (L-V)
PIC18LF4455@TQFP44 [SA245A-B4805]	
PIC18LF4455@TQFP44 (ISP) (High-V)	PIC18LF4455@TQFP44 (ISP) (Low-V)
PIC18LF448	PIC18LF448 (ISP)
PIC18LF448@PLCC44 [SA244]	PIC18LF448@PLCC44 (ISP)
PIC18LF448@QFN44 [SA737]	PIC18LF448@TQFP44 [SA245A-B4805]
PIC18LF448@TQFP44 (ISP)	PIC18LF4480
PIC18LF4480 (ISP) (High-V)	PIC18LF4480 (ISP) (Low-V)
PIC18LF4480@QFN44 [SA712]	PIC18LF4480@QFN44 (ISP) (High-V)
PIC18LF4480@QFN44 (ISP) (Low-V)	PIC18LF4480@QFN44 (ML) [SA737]
PIC18LF4480@QFN44 (ML) (ISP) (H-V)	PIC18LF4480@QFN44 (ML) (ISP) (L-V)
PIC18LF4480@TQFP44 [SA245A-B4805]	
PIC18LF4480@TQFP44 (ISP) (High-V)	PIC18LF4480@TQFP44 (ISP) (Low-V)
PIC18LF44J10	PIC18LF44J10 (ISP)
PIC18LF44J10@QFN44 [SA712]	PIC18LF44J10@QFN44 (ISP)
PIC18LF44J10@QFN44 (ML) [SA737]	PIC18LF44J10@QFN44 (ML) (ISP)
PIC18LF44J10@TQFP44 [SA245A-B4805]	
PIC18LF44J10@TQFP44 (ISP)	PIC18LF44J11
PIC18LF44J11 (ISP)	PIC18LF44J11@QFN44 [SA712]
PIC18LF44J11@QFN44 (ISP)	PIC18LF44J11@QFN44 (ML) [SA737]
PIC18LF44J11@QFN44 (ML) (ISP)	
PIC18LF44J11@TQFP44 [SA245A-B4805]	
PIC18LF44J11@TQFP44 (ISP)	PIC18LF44J50
PIC18LF44J50 (ISP)	PIC18LF44J50@QFN44 [SA712]
PIC18LF44J50@QFN44 (ISP)	PIC18LF44J50@QFN44 (ML) [SA737]
PIC18LF44J50@QFN44 (ML) (ISP)	
PIC18LF44J50@TQFP44 [SA245A-B4805]	
PIC18LF44J50@TQFP44 (ISP)	PIC18LF44K22

PIC18LF44K22 (ISP) (H-V)	PIC18LF44K22@QFN44 [SA712]
PIC18LF44K22@QFN44 (ISP) (H-V)	PIC18LF44K22@QFN44 (ML) [SA737]
PIC18LF44K22@QFN44 (ML) (ISP) (H-V)	
PIC18LF44K22@TQFP44 [SA245A-B4805]	
PIC18LF44K22@TQFP44 (ISP) (H-V)	PIC18LF44K22@UQFN40 [\$\$\$\$\$]
PIC18LF4510	PIC18LF4510 (ISP)
PIC18LF4510@QFN44 [SA712]	PIC18LF4510@QFN44 (ISP)
PIC18LF4510@QFN44 (ML) [SA737]	PIC18LF4510@QFN44 (ML) (ISP)
PIC18LF4510@TQFP44 [SA245A-B4805]	
PIC18LF4510@TQFP44 (ISP)	PIC18LF4515
PIC18LF4515 (ISP) (Low-V)	PIC18LF4515@QFN44 [SA712]
PIC18LF4515@QFN44 (ISP) (Low-V)	PIC18LF4515@QFN44 (ML) [SA737]
PIC18LF4515@QFN44 (ML) (ISP) (L-V)	
PIC18LF4515@TQFP44 [SA245A-B4805]	
PIC18LF4515@TQFP44 (ISP) (Low-V)	PIC18LF452
PIC18LF452 (ISP)	PIC18LF452@PLCC44 [SA244]
PIC18LF452@PLCC44 (ISP)	PIC18LF452@QFN44 [SA737]
PIC18LF452@TQFP44 [SA245A-B4805]	PIC18LF452@TQFP44 (ISP)
PIC18LF4520	PIC18LF4520 (ISP)
PIC18LF4520@QFN44 [SA712]	PIC18LF4520@QFN44 (ISP)
PIC18LF4520@QFN44 (ML) [SA737]	PIC18LF4520@QFN44 (ML) (ISP)
PIC18LF4520@TQFP44 [SA245A-B4805]	
PIC18LF4520@TQFP44 (ISP)	PIC18LF4523
PIC18LF4523 (ISP) (High-V)	PIC18LF4523 (ISP) (Low-V)
PIC18LF4523@QFN44 [SA712]	PIC18LF4523@QFN44 (ISP) (High-V)
PIC18LF4523@QFN44 (ISP) (Low-V)	PIC18LF4523@QFN44 (ML) [SA737]
PIC18LF4523@QFN44 (ML) (ISP) (H-V)	PIC18LF4523@QFN44 (ML) (ISP) (L-V)
PIC18LF4523@TQFP44 [SA245A-B4805]	
PIC18LF4523@TQFP44 (ISP) (High-V)	PIC18LF4523@TQFP44 (ISP) (Low-V)
PIC18LF4525	PIC18LF4525 (ISP) (Low-V)
PIC18LF4525@QFN44 [SA712]	PIC18LF4525@QFN44 (ISP) (Low-V)
PIC18LF4525@QFN44 (ML) [SA737]	PIC18LF4525@QFN44 (ML) (ISP) (L-V)
PIC18LF4525@TQFP44 [SA245A-B4805]	
PIC18LF4525@TQFP44 (ISP) (Low-V)	PIC18LF4539
PIC18LF4539 (ISP)	
PIC18LF4539@TQFP44 [SA245A-B4805]	PIC18LF4550
PIC18LF4539@TQFP44 (ISP)	PIC18LF4550 (ISP) (Low-V)
PIC18LF4550 (ISP) (High-V)	PIC18LF4550@QFN44 (ISP) (High-V)
PIC18LF4550@QFN44 [SA712]	PIC18LF4550@QFN44 (ML) [SA737]
PIC18LF4550@QFN44 (ISP) (Low-V)	PIC18LF4550@QFN44 (ML) (ISP) (L-V)
PIC18LF4550@QFN44 (ML) (ISP) (H-V)	
PIC18LF4550@TQFP44 [SA245A-B4805]	
PIC18LF4550@TQFP44 (ISP) (High-V)	PIC18LF4550@TQFP44 (ISP) (Low-V)
PIC18LF458	PIC18LF458 (ISP)
PIC18LF458@PLCC44 [SA244]	PIC18LF458@PLCC44 (ISP)
PIC18LF458@QFN44 [SA737]	PIC18LF458@TQFP44 [SA245A-B4805]
PIC18LF458@TQFP44 (ISP)	PIC18LF4580
PIC18LF4580 (ISP) (High-V)	PIC18LF4580 (ISP) (Low-V)
PIC18LF4580@QFN44 [SA712]	PIC18LF4580@QFN44 (ISP) (High-V)
PIC18LF4580@QFN44 (ISP) (Low-V)	PIC18LF4580@QFN44 (ML) [SA737]
PIC18LF4580@QFN44 (ML) (ISP) (H-V)	PIC18LF4580@QFN44 (ML) (ISP) (L-V)
PIC18LF4580@TQFP44 [SA245A-B4805]	
PIC18LF4580@TQFP44 (ISP) (High-V)	PIC18LF4580@TQFP44 (ISP) (Low-V)

PIC18LF4585	PIC18LF4585 (ISP) (High-V)
PIC18LF4585 (ISP) (Low-V)	PIC18LF4585@QFN44 [SA712]
PIC18LF4585@QFN44 (ISP) (High-V)	PIC18LF4585@QFN44 (ISP) (Low-V)
PIC18LF4585@QFN44 (ML) [SA737]	PIC18LF4585@QFN44 (ML) (ISP) (H-V)
PIC18LF4585@QFN44 (ML) (ISP) (L-V)	
PIC18LF4585@TQFP44 [SA245A-B4805]	
PIC18LF4585@TQFP44 (ISP) (High-V)	PIC18LF4585@TQFP44 (ISP) (Low-V)
PIC18LF45J10	PIC18LF45J10 (ISP)
PIC18LF45J10@QFN44 [SA712]	PIC18LF45J10@QFN44 (ISP)
PIC18LF45J10@QFN44 (ML) [SA737]	PIC18LF45J10@QFN44 (ML) (ISP)
PIC18LF45J10@TQFP44 [SA245A-B4805]	
PIC18LF45J10@TQFP44 (ISP)	PIC18LF45J11
PIC18LF45J11 (ISP)	PIC18LF45J11@QFN44 [SA712]
PIC18LF45J11@QFN44 (ISP)	PIC18LF45J11@QFN44 (ML) [SA737]
PIC18LF45J11@QFN44 (ML) (ISP)	
PIC18LF45J11@TQFP44 [SA245A-B4805]	
PIC18LF45J11@TQFP44 (ISP)	PIC18LF45J50
PIC18LF45J50 (ISP)	PIC18LF45J50@QFN44 [SA712]
PIC18LF45J50@QFN44 (ISP)	PIC18LF45J50@QFN44 (ML) [SA737]
PIC18LF45J50@QFN44 (ML) (ISP)	
PIC18LF45J50@TQFP44 [SA245A-B4805]	
PIC18LF45J50@TQFP44 (ISP)	PIC18LF45K22
PIC18LF45K22 (ISP) (H-V)	PIC18LF45K22@QFN44 [SA712]
PIC18LF45K22@QFN44 (ISP) (H-V)	PIC18LF45K22@QFN44 (ML) [SA737]
PIC18LF45K22@QFN44 (ML) (ISP) (H-V)	
PIC18LF45K22@TQFP44 [SA245A-B4805]	
PIC18LF45K22@TQFP44 (ISP) (H-V)	PIC18LF45K50
PIC18LF45K50@ISP	PIC18LF45K50@QFN44 [SA737]
PIC18LF45K50@TQFP44 [SA245A-B4805]	
PIC18LF45K50@UQFN40 [\$\$\$\$\$]	PIC18LF45K80
PIC18LF45K80 (ISP)	PIC18LF45K80@QFN44 [SA737]
PIC18LF45K80@QFN44 (ISP)	
PIC18LF45K80@TQFP44 [SA245A-B4805]	
PIC18LF45K80@TQFP44 (ISP)	PIC18LF4610
PIC18LF4610 (ISP) (Low-V)	PIC18LF4610@QFN44 [SA712]
PIC18LF4610@QFN44 (ISP) (Low-V)	PIC18LF4610@QFN44 (ML) [SA737]
PIC18LF4610@QFN44 (ML) (ISP) (L-V)	
PIC18LF4610@TQFP44 [SA245A-B4805]	
PIC18LF4610@TQFP44 (ISP) (Low-V)	PIC18LF4620
PIC18LF4620 (ISP) (Low-V)	PIC18LF4620@QFN44 [SA712]
PIC18LF4620@QFN44 (ISP) (Low-V)	PIC18LF4620@QFN44 (ML) [SA737]
PIC18LF4620@QFN44 (ML) (ISP) (L-V)	
PIC18LF4620@TQFP44 [SA245A-B4805]	
PIC18LF4620@TQFP44 (ISP) (Low-V)	PIC18LF4680
PIC18LF4680 (ISP) (High-V)	PIC18LF4680 (ISP) (Low-V)
PIC18LF4680@QFN44 [SA712]	PIC18LF4680@QFN44 (ISP) (High-V)
PIC18LF4680@QFN44 (ISP) (Low-V)	PIC18LF4680@QFN44 (ML) [SA737]
PIC18LF4680@QFN44 (ML) (ISP) (H-V)	PIC18LF4680@QFN44 (ML) (ISP) (L-V)
PIC18LF4680@TQFP44 [SA245A-B4805]	
PIC18LF4680@TQFP44 (ISP) (High-V)	PIC18LF4680@TQFP44 (ISP) (Low-V)
PIC18LF4682	PIC18LF4682 (ISP) (High-V)
PIC18LF4682 (ISP) (Low-V)	PIC18LF4682@QFN44 [SA712]
PIC18LF4682@QFN44 (ISP) (High-V)	PIC18LF4682@QFN44 (ISP) (Low-V)

PIC18LF4682@QFN44 (ML) [SA737]	PIC18LF4682@QFN44 (ML) (ISP) (H-V)
PIC18LF4682@QFN44 (ML) (ISP) (L-V)	
PIC18LF4682@TQFP44 [SA245A-B4805]	
PIC18LF4682@TQFP44 (ISP) (High-V)	PIC18LF4682@TQFP44 (ISP) (Low-V)
PIC18LF4685	PIC18LF4685 (ISP) (High-V)
PIC18LF4685 (ISP) (Low-V)	PIC18LF4685@QFN44 [SA712]
PIC18LF4685@QFN44 (ISP) (High-V)	PIC18LF4685@QFN44 (ISP) (Low-V)
PIC18LF4685@QFN44 (ML) [SA737]	PIC18LF4685@QFN44 (ML) (ISP) (H-V)
PIC18LF4685@QFN44 (ML) (ISP) (L-V)	
PIC18LF4685@TQFP44 [SA245A-B4805]	
PIC18LF4685@TQFP44 (ISP) (High-V)	PIC18LF4685@TQFP44 (ISP) (Low-V)
PIC18LF46J11	PIC18LF46J11 (ISP)
PIC18LF46J11@QFN44 [SA712]	PIC18LF46J11@QFN44 (ISP)
PIC18LF46J11@QFN44 (ML) [SA737]	PIC18LF46J11@QFN44 (ML) (ISP)
PIC18LF46J11@TQFP44 [SA245A-B4805]	
PIC18LF46J11@TQFP44 (ISP)	
PIC18LF46J13 (ISP)	PIC18LF46J13
PIC18LF46J13@QFN44 (ML) [SA737]	PIC18LF46J13@QFN44 [SA712]
PIC18LF46J13@TQFP44 [SA245A-B4805]	
PIC18LF46J13QFN44 (ISP)	PIC18LF46J13QFN44 (ML) (ISP)
PIC18LF46J13TQFP44 (ISP)	PIC18LF46J50
PIC18LF46J50 (ISP)	PIC18LF46J50@QFN44 [SA712]
PIC18LF46J50@QFN44 (ISP)	PIC18LF46J50@QFN44 (ML) [SA737]
PIC18LF46J50@QFN44 (ML) (ISP)	
PIC18LF46J50@TQFP44 [SA245A-B4805]	
PIC18LF46J50@TQFP44 (ISP)	PIC18LF46J53
PIC18LF46J53 (ISP)	PIC18LF46J53@QFN44 [SA712]
PIC18LF46J53@QFN44 (ML) [SA737]	
PIC18LF46J53@TQFP44 [SA245A-B4805]	
PIC18LF46J53QFN44 (ISP)	PIC18LF46J53QFN44 (ML) (ISP)
PIC18LF46J53TQFP44 (ISP)	PIC18LF46K22
PIC18LF46K22 (ISP) (H-V)	PIC18LF46K22@QFN44 [SA712]
PIC18LF46K22@QFN44 (ISP) (H-V)	PIC18LF46K22@QFN44 (ML) [SA737]
PIC18LF46K22@QFN44 (ML) (ISP) (H-V)	
PIC18LF46K22@TQFP44 [SA245A-B4805]	
PIC18LF46K22@TQFP44 (ISP) (H-V)	PIC18LF46K50
PIC18LF46K50@ISP	PIC18LF46K50@QFN44 [SA737]
PIC18LF46K50@TQFP44 [SA245A-B4805]	
PIC18LF46K80	PIC18LF46K80 (ISP)
PIC18LF46K80@QFN44 [SA737]	PIC18LF46K80@QFN44 (ISP)
PIC18LF46K80@TQFP44 [SA245A-B4805]	
PIC18LF46K80@TQFP44 (ISP)	PIC18LF47J13
PIC18LF47J13 (ISP)	PIC18LF47J13@QFN44 [SA712]
PIC18LF47J13@QFN44 (ML) [SA737]	
PIC18LF47J13@TQFP44 [SA245A-B4805]	
PIC18LF47J13QFN44 (ISP)	PIC18LF47J13QFN44 (ML) (ISP)
PIC18LF47J13TQFP44 (ISP)	PIC18LF47J53
PIC18LF47J53 (ISP)	PIC18LF47J53@QFN44 [SA712]
PIC18LF47J53@QFN44 (ML) [SA737]	
PIC18LF47J53@TQFP44 [SA245A-B4805]	
PIC18LF47J53QFN44 (ISP)	PIC18LF47J53QFN44 (ML) (ISP)
PIC18LF47J53TQFP44 (ISP)	PIC18LF6310@TQFP64 (ISP)
PIC18LF6390@TQFP64 (ISP)	PIC18LF6393@TQFP64 (ISP)

PIC18LF63J11@TQFP64 (ISP)	PIC18LF63J90@TQFP64 (ISP)
PIC18LF6410@TQFP64 (ISP)	PIC18LF6490@TQFP64 (ISP)
PIC18LF6493@TQFP64 (ISP)	PIC18LF64J11@TQFP64 (ISP)
PIC18LF64J90@TQFP64 (ISP)	PIC18LF6520@TQFP64 (ISP)
PIC18LF6525@TQFP64 (ISP)	PIC18LF6527@TQFP64 (ISP) (High-V)
PIC18LF6527@TQFP64 (ISP) (Low-V)	PIC18LF6585@PLCC68 (ISP)
PIC18LF6585@TQFP64 (ISP)	PIC18LF65J11@TQFP64 (ISP)
PIC18LF65J90@TQFP64 (ISP)	PIC18LF65K80@QFN64 (ISP)
PIC18LF65K80@TQFP64 (ISP)	PIC18LF6620@TQFP64 (ISP)
PIC18LF6621@TQFP64 (ISP)	PIC18LF6622@TQFP64 (ISP) (High-V)
PIC18LF6622@TQFP64 (ISP) (Low-V)	PIC18LF6627@TQFP64 (ISP) (High-V)
PIC18LF6627@TQFP64 (ISP) (Low-V)	PIC18LF6628@TQFP64 (ISP) (High-V)
PIC18LF6628@TQFP64 (ISP) (Low-V)	PIC18LF6680@PLCC68 (ISP)
PIC18LF6680@TQFP64 (ISP)	PIC18LF66K80@QFN64 (ISP)
PIC18LF66K80@TQFP64 (ISP)	PIC18LF6720@TQFP64 (ISP)
PIC18LF6722@TQFP64 (ISP) (High-V)	PIC18LF6722@TQFP64 (ISP) (Low-V)
PIC18LF6723@TQFP64 (ISP) (High-V)	PIC18LF6723@TQFP64 (ISP) (Low-V)
PIC18LF8310@TQFP80 (ISP)	PIC18LF8390@TQFP80 (ISP)
PIC18LF8393@TQFP80 (ISP)	PIC18LF83J11@TQFP80 (ISP)
PIC18LF83J90@TQFP80 (ISP)	PIC18LF8410@TQFP80 (ISP)
PIC18LF8490@TQFP80 (ISP)	PIC18LF8493@TQFP80 (ISP)
PIC18LF84J11@TQFP80 (ISP)	PIC18LF84J90@TQFP80 (ISP)
PIC18LF8520@TQFP80 (ISP)	PIC18LF8525@TQFP80 (ISP)
PIC18LF8527@TQFP80 (ISP) (High-V)	PIC18LF8527@TQFP80 (ISP) (Low-V)
PIC18LF8585@TQFP80 (ISP)	PIC18LF85J11@TQFP80 (ISP)
PIC18LF85J90@TQFP80 (ISP)	PIC18LF8620@TQFP80 (ISP)
PIC18LF8621@TQFP80 (ISP)	PIC18LF8622@TQFP80 (ISP) (High-V)
PIC18LF8622@TQFP80 (ISP) (Low-V)	PIC18LF8627@TQFP80 (ISP) (High-V)
PIC18LF8627@TQFP80 (ISP) (Low-V)	PIC18LF8628@TQFP80 (ISP) (High-V)
PIC18LF8628@TQFP80 (ISP) (Low-V)	PIC18LF8680@TQFP80 (ISP)
PIC18LF8720@TQFP80 (ISP)	PIC18LF8722@TQFP80 (ISP) (High-V)
PIC18LF8722@TQFP80 (ISP) (Low-V)	PIC18LF8723@TQFP80 (ISP) (High-V)
PIC18LF8723@TQFP80 (ISP) (Low-V)	PIC24EP128GP202
PIC24EP128GP202 (ISP)	PIC24EP128GP202@QFN28 [SA685]
PIC24EP128GP202@SOIC28 [SA404]	PIC24EP128GP202@SSOP28 [SA626A]
PIC24EP128GP203 (ISP)	PIC24EP128GP203@VTLA36 [\$\$\$\$\$]
PIC24EP128GP204 (ISP)	PIC24EP128GP204@QFN44 [SA737]
PIC24EP128GP204@TQFP44 [SA245A-B4805]	
PIC24EP128GP206 (ISP)	PIC24EP128MC202
PIC24EP128MC202 (ISP)	PIC24EP128MC202@QFN28 [SA685]
PIC24EP128MC202@SOIC28 [SA404]	PIC24EP128MC202@SSOP28 [SA626A]
PIC24EP128MC203 (ISP)	PIC24EP128MC203@VTLA36 [\$\$\$\$\$]
PIC24EP128MC204 (ISP)	PIC24EP128MC204@QFN44 [SA737]
PIC24EP128MC204@TQFP44 [SA245A-B4805]	
PIC24EP128MC204@VTLA44 [\$\$\$\$\$]	PIC24EP128MC206 (ISP)
PIC24EP256GP202	PIC24EP256GP202 (ISP)
PIC24EP256GP202@QFN28 [SA685]	PIC24EP256GP202@SOIC28 [SA404]
PIC24EP256GP202@SSOP28 [SA626A]	PIC24EP256GP203 (ISP)
PIC24EP256GP203@VTLA36 [\$\$\$\$\$]	PIC24EP256GP204 (ISP)
PIC24EP256GP204@QFN44 [SA737]	
PIC24EP256GP204@TQFP44 [SA245A-B4805]	
PIC24EP256GP206 (ISP)	PIC24EP256MC202
PIC24EP256MC202 (ISP)	PIC24EP256MC202@QFN28 [SA685]

PIC24EP256MC202@SOIC28 [SA404]	PIC24EP256MC202@SSOP28 [SA626A]
PIC24EP256MC203 (ISP)	PIC24EP256MC203@VTLA36 [\$\$\$\$\$]
PIC24EP256MC204 (ISP)	PIC24EP256MC204@QFN44 [SA737]
PIC24EP256MC204@TQFP44 [SA245A-B4805]	
PIC24EP256MC204@VTLA44 [\$\$\$\$\$]	PIC24EP256MC206 (ISP)
PIC24EP32GP202	PIC24EP32GP202 (ISP)
PIC24EP32GP202@QFN28 [SA685]	PIC24EP32GP202@SOIC28 [SA404]
PIC24EP32GP202@SSOP28 [SA626A]	PIC24EP32GP203 (ISP)
PIC24EP32GP203@VTLA36 [\$\$\$\$\$]	PIC24EP32GP204 (ISP)
PIC24EP32GP204@QFN44 [SA737]	
PIC24EP32GP204@TQFP44 [SA245A-B4805]	
PIC24EP32MC202	PIC24EP32MC202 (ISP)
PIC24EP32MC202@QFN28 [SA685]	PIC24EP32MC202@SOIC28 [SA404]
PIC24EP32MC202@SSOP28 [SA626A]	PIC24EP32MC203 (ISP)
PIC24EP32MC203@VTLA36 [\$\$\$\$\$]	PIC24EP32MC204 (ISP)
PIC24EP32MC204@QFN44 [SA737]	
PIC24EP32MC204@TQFP44 [SA245A-B4805]	
PIC24EP32MC204@VTLA44 [\$\$\$\$\$]	PIC24EP512GP202
PIC24EP512GP202 (ISP)	PIC24EP512GP202@QFN28 [SA685]
PIC24EP512GP202@SOIC28 [SA404]	PIC24EP512GP204 (ISP)
PIC24EP512GP204@QFN44 [SA737]	
PIC24EP512GP204@TQFP44 [SA245A-B4805]	
PIC24EP512GP204@VTLA44 [\$\$\$\$\$]	PIC24EP512GP206 (ISP)
PIC24EP512MC202	PIC24EP512MC202 (ISP)
PIC24EP512MC202@QFN28 [SA685]	PIC24EP512MC202@SOIC28 [SA404]
PIC24EP512MC204 (ISP)	PIC24EP512MC204@QFN44 [SA737]
PIC24EP512MC204@TQFP44 [SA245A-B4805]	
PIC24EP512MC204@VTLA44 [\$\$\$\$\$]	PIC24EP512MC206 (ISP)
PIC24EP64GP202	PIC24EP64GP202 (ISP)
PIC24EP64GP202@QFN28 [SA685]	PIC24EP64GP202@SOIC28 [SA404]
PIC24EP64GP202@SSOP28 [SA626A]	PIC24EP64GP203 (ISP)
PIC24EP64GP203@VTLA36 [\$\$\$\$\$]	PIC24EP64GP204 (ISP)
PIC24EP64GP204@QFN44 [SA737]	
PIC24EP64GP204@TQFP44 [SA245A-B4805]	
PIC24EP64GP204@VTLA44 [\$\$\$\$\$]	PIC24EP64GP206 (ISP)
PIC24EP64MC202	PIC24EP64MC202 (ISP)
PIC24EP64MC202@QFN28 [SA685]	PIC24EP64MC202@SOIC28 [SA404]
PIC24EP64MC202@SSOP28 [SA626A]	PIC24EP64MC203 (ISP)
PIC24EP64MC204 (ISP)	PIC24EP64MC204@QFN44 [SA737]
PIC24EP64MC204@TQFP44 [SA245A-B4805]	
PIC24EP64MC206 (ISP)	PIC24F04KA200
PIC24F04KA200 (ISP)	PIC24F04KA200@SOIC14 [SA404]
PIC24F04KA201	PIC24F04KA201 (ISP)
PIC24F04KA201@SOIC20 [SA404]	PIC24F04KA201@SSOP20 [SA626A]
PIC24F04KL100	PIC24F04KL100 (ISP)
PIC24F04KL100@SOIC14 [SA404]	PIC24F04KL101
PIC24F04KL101 (ISP)	PIC24F04KL101@SOIC20 [SA404]
PIC24F04KL101@SSOP20 [SA626A]	PIC24F08KA101
PIC24F08KA101 (ISP)	PIC24F08KA101@SOIC20 [SA404]
PIC24F08KA101@SSOP20 [SA626A]	PIC24F08KA102
PIC24F08KA102 (ISP)	PIC24F08KA102@SOIC28 [SA404]
PIC24F08KA102@SSOP28 [SA626A]	PIC24F08KL200
PIC24F08KL200 (ISP)	PIC24F08KL200@SOIC14 [SA404]

PIC24F08KL201  
PIC24F08KL201@S0IC20 [SA404]  
PIC24F08KL301  
PIC24F08KL301@S0IC20 [SA404]  
PIC24F08KL302  
PIC24F08KL302@S0IC28 [SA404]  
PIC24F08KL401  
PIC24F08KL401@S0IC20 [SA404]  
PIC24F08KL402  
PIC24F08KL402@S0IC28 [SA404]  
PIC24F16KA101  
PIC24F16KA101@S0IC20 [SA404]  
PIC24F16KA102  
PIC24F16KA102@S0IC28 [SA404]  
PIC24F16KA301  
PIC24F16KA301@S0IC20 [SA404]  
PIC24F16KA302  
PIC24F16KA302@S0IC28 [SA404]  
PIC24F16KA304 (ISP)  
PIC24F16KL401@S0IC20 [SA404]  
PIC24F16KL402  
PIC24F16KL402@S0IC28 [SA404]  
PIC24F32KA301  
PIC24F32KA301@S0IC20 [SA404]  
PIC24F32KA302  
PIC24F32KA302@S0IC28 [SA404]  
PIC24F32KA304 (ISP)  
PIC24FJ128DA110 (ISP)  
PIC24FJ128DA210 (ISP)  
PIC24FJ128GA006@TQFP64 (ISP)  
PIC24FJ128GA010@QFP100 (ISP)  
PIC24FJ128GA106@QFN64 (ISP)  
PIC24FJ128GA108@TQFP80 (ISP)  
PIC24FJ128GA110@TQFP100-2 (ISP)  
PIC24FJ128GA308 (ISP)  
PIC24FJ128GB106@QFN64 (ISP)  
PIC24FJ128GB108@TQFP80 (ISP)  
PIC24FJ128GB110@TQFP100-2 (ISP)  
PIC24FJ128GB210 (ISP)  
PIC24FJ128GC008 (ISP)  
PIC24FJ16GA002  
PIC24FJ16GA002@QFN28 [SA685]  
PIC24FJ16GA002@S0IC28 [SA404]  
PIC24FJ16GA002@SSOP28 [SA626A]  
PIC24FJ16GA004@QFN44 [SA737]  
PIC24FJ16GA004@TQFP44 [SA245A-B4805]  
PIC24FJ16GA004@TQFP44 (ISP)  
PIC24FJ192GA106@TQFP64 (ISP)  
PIC24FJ192GA110@TQFP100-1 (ISP)  
PIC24FJ192GB106@QFN64 (ISP)  
PIC24FJ192GB108@TQFP80 (ISP)  
PIC24FJ192GB110@TQFP100-2 (ISP)  
PIC24FJ256DA110 (ISP)  
PIC24F08KL201 (ISP)  
PIC24F08KL201@SSOP20 [SA626A]  
PIC24F08KL301 (ISP)  
PIC24F08KL301@SSOP20 [SA626A]  
PIC24F08KL302 (ISP)  
PIC24F08KL302@SSOP28 [SA626A]  
PIC24F08KL401 (ISP)  
PIC24F08KL401@SSOP20 [SA626A]  
PIC24F08KL402 (ISP)  
PIC24F08KL402@SSOP28 [SA626A]  
PIC24F16KA101 (ISP)  
PIC24F16KA101@SSOP20 [SA626A]  
PIC24F16KA102 (ISP)  
PIC24F16KA102@SSOP28 [SA626A]  
PIC24F16KA301 (ISP)  
PIC24F16KA301@SSOP20 [SA626A]  
PIC24F16KA302 (ISP)  
PIC24F16KA302@SSOP28 [SA626A]  
PIC24F16KL401 (ISP)  
PIC24F16KL401@SSOP20 [SA626A]  
PIC24F16KL402 (ISP)  
PIC24F16KL402@SSOP28 [SA626A]  
PIC24F32KA301 (ISP)  
PIC24F32KA301@SSOP20 [SA626A]  
PIC24F32KA302 (ISP)  
PIC24F32KA302@SSOP28 [SA626A]  
PIC24FJ128DA106 (ISP)  
PIC24FJ128DA206 (ISP)  
PIC24FJ128GA006@QFN64 (ISP)  
PIC24FJ128GA008@TQFP80 (ISP)  
PIC24FJ128GA010@TQFP100 (ISP)  
PIC24FJ128GA106@TQFP64 (ISP)  
PIC24FJ128GA110@TQFP100-1 (ISP)  
PIC24FJ128GA306 (ISP)  
PIC24FJ128GA310 (ISP)  
PIC24FJ128GB106@TQFP64 (ISP)  
PIC24FJ128GB110@TQFP100-1 (ISP)  
PIC24FJ128GB206 (ISP)  
PIC24FJ128GC006 (ISP)  
PIC24FJ128GC010 (ISP)  
PIC24FJ16GA002 (ISP)  
PIC24FJ16GA002@QFN28 (ISP)  
PIC24FJ16GA002@S0IC28 (ISP)  
PIC24FJ16GA002@SSOP28 (ISP)  
PIC24FJ16GA004@QFN44 (ISP)  
PIC24FJ192GA106@QFN64 (ISP)  
PIC24FJ192GA108@TQFP80 (ISP)  
PIC24FJ192GA110@TQFP100-2 (ISP)  
PIC24FJ192GB106@TQFP64 (ISP)  
PIC24FJ192GB110@TQFP100-1 (ISP)  
PIC24FJ256DA106 (ISP)  
PIC24FJ256DA206 (ISP)

PIC24FJ256DA210 (ISP)  
PIC24FJ256GA106@TQFP64 (ISP)  
PIC24FJ256GA110@TQFP100-1 (ISP)  
PIC24FJ256GB106@QFN64 (ISP)  
PIC24FJ256GB108@TQFP80 (ISP)  
PIC24FJ256GB110@TQFP100-2 (ISP)  
PIC24FJ256GB210 (ISP)  
PIC24FJ32GA002 (ISP)  
PIC24FJ32GA002@QFN28 (ISP)  
PIC24FJ32GA002@SOIC28 (ISP)  
PIC24FJ32GA002@SSOP28 (ISP)  
PIC24FJ32GA004@QFN44 (ISP)  
PIC24FJ32GA004@TQFP44 [SA245A-B4805]  
PIC24FJ32GA004@TQFP44 (ISP)  
PIC24FJ32GA102 (ISP)  
PIC24FJ32GA102@QFN28 (ISP)  
PIC24FJ32GA102@SOIC28 (ISP)  
PIC24FJ32GA104@QFN44 (ISP)  
PIC24FJ32GA104@TQFP44 [SA245A-B4805]  
PIC24FJ32GA104@TQFP44 (ISP)  
PIC24FJ32GB002 (ISP)  
PIC24FJ32GB002@QFN28 (ISP)  
PIC24FJ32GB002@SOIC28 (ISP)  
PIC24FJ32GB004@QFN44 (ISP)  
PIC24FJ32GB004@TQFP44 [SA245A-B4805]  
PIC24FJ32GB004@TQFP44 (ISP)  
PIC24FJ48GA002 (ISP)  
PIC24FJ48GA002@QFN28 (ISP)  
PIC24FJ48GA002@SOIC28 (ISP)  
PIC24FJ48GA002@SSOP28 (ISP)  
PIC24FJ48GA004@QFN44 (ISP)  
PIC24FJ48GA004@TQFP44 [SA245A-B4805]  
PIC24FJ48GA004@TQFP44 (ISP)  
PIC24FJ64GA002 (ISP)  
PIC24FJ64GA002@QFN28 (ISP)  
PIC24FJ64GA002@SOIC28 (ISP)  
PIC24FJ64GA002@SSOP28 (ISP)  
PIC24FJ64GA004@QFN44 (ISP)  
PIC24FJ64GA004@TQFP44 [SA245A-B4805]  
PIC24FJ64GA004@TQFP44 (ISP)  
PIC24FJ64GA006@TQFP64 (ISP)  
PIC24FJ64GA010@QFP100 (ISP)  
PIC24FJ64GA102  
PIC24FJ64GA102@QFN28 [SA685]  
PIC24FJ64GA102@SOIC28 [SA404]  
PIC24FJ64GA104@QFN44 [SA737]  
PIC24FJ64GA104@TQFP44 [SA245A-B4805]  
PIC24FJ64GA104@TQFP44 (ISP)  
PIC24FJ64GA106@TQFP64 (ISP)  
PIC24FJ64GA110@TQFP100-1 (ISP)  
PIC24FJ64GA306 (ISP)  
PIC24FJ64GA310 (ISP)  
PIC24FJ64GB002 (ISP)

PIC24FJ256GA106@QFN64 (ISP)  
PIC24FJ256GA108@TQFP80 (ISP)  
PIC24FJ256GA110@TQFP100-2 (ISP)  
PIC24FJ256GB106@TQFP64 (ISP)  
PIC24FJ256GB110@TQFP100-1 (ISP)  
PIC24FJ256GB206 (ISP)  
PIC24FJ32GA002  
PIC24FJ32GA002@QFN28 [SA685]  
PIC24FJ32GA002@SOIC28 [SA404]  
PIC24FJ32GA002@SSOP28 [SA626A]  
PIC24FJ32GA004@QFN44 [SA737]  
PIC24FJ32GA102  
PIC24FJ32GA102@QFN28 [SA685]  
PIC24FJ32GA102@SOIC28 [SA404]  
PIC24FJ32GA104@QFN44 [SA737]  
PIC24FJ32GB002  
PIC24FJ32GB002@QFN28 [SA685]  
PIC24FJ32GB002@SOIC28 [SA404]  
PIC24FJ32GB004@QFN44 [SA737]  
PIC24FJ48GA002  
PIC24FJ48GA002@QFN28 [SA685]  
PIC24FJ48GA002@SOIC28 [SA404]  
PIC24FJ48GA002@SSOP28 [SA626A]  
PIC24FJ48GA004@QFN44 [SA737]  
PIC24FJ64GA002  
PIC24FJ64GA002@QFN28 [SA685]  
PIC24FJ64GA002@SOIC28 [SA404]  
PIC24FJ64GA002@SSOP28 [SA626A]  
PIC24FJ64GA004@QFN44 [SA737]  
PIC24FJ64GA006@QFN64 (ISP)  
PIC24FJ64GA008@TQFP80 (ISP)  
PIC24FJ64GA010@TQFP100 (ISP)  
PIC24FJ64GA102 (ISP)  
PIC24FJ64GA102@QFN28 (ISP)  
PIC24FJ64GA102@SOIC28 (ISP)  
PIC24FJ64GA104@QFN44 (ISP)  
PIC24FJ64GA106@QFN64 (ISP)  
PIC24FJ64GA108@TQFP80 (ISP)  
PIC24FJ64GA110@TQFP100-2 (ISP)  
PIC24FJ64GA308 (ISP)  
PIC24FJ64GB002  
PIC24FJ64GB002@QFN28 [SA685]

PIC24FJ64GB002@QFN28 (ISP)	PIC24FJ64GB002@SOIC28 [SA404]
PIC24FJ64GB002@SOIC28 (ISP)	PIC24FJ64GB004@QFN44 [SA737]
PIC24FJ64GB004@QFN44 (ISP)	
PIC24FJ64GB004@TQFP44 [SA245A-B4805]	
PIC24FJ64GB004@TQFP44 (ISP)	PIC24FJ64GB106@QFN64 (ISP)
PIC24FJ64GB106@TQFP64 (ISP)	PIC24FJ64GB108@TQFP80 (ISP)
PIC24FJ64GB110@TQFP100-1 (ISP)	PIC24FJ64GB110@TQFP100-2 (ISP)
PIC24FJ64GC006 (ISP)	PIC24FJ64GC008 (ISP)
PIC24FJ64GC010 (ISP)	PIC24FJ96GA006@QFN64 (ISP)
PIC24FJ96GA006@TQFP64 (ISP)	PIC24FJ96GA008@TQFP80 (ISP)
PIC24FJ96GA010@QFP100 (ISP)	PIC24FJ96GA010@TQFP100 (ISP)
PIC24FV08KM101	PIC24FV08KM101 (ISP)
PIC24FV08KM101@SOIC28 [SA404]	PIC24FV08KM101@SSOP28 [SA626A]
PIC24FV08KM102	PIC24FV08KM102 (ISP)
PIC24FV08KM102@SOIC28 [SA404]	PIC24FV08KM102@SSOP28 [SA626A]
PIC24FV08KM202	PIC24FV08KM202 (ISP)
PIC24FV08KM202@SOIC28 [SA404]	PIC24FV08KM202@SSOP28 [SA626A]
PIC24FV08KM204 (ISP)	PIC24FV16KA301
PIC24FV16KA301 (ISP)	PIC24FV16KA301@SOIC20 [SA404]
PIC24FV16KA301@SSOP20 [SA626A]	PIC24FV16KA302
PIC24FV16KA302 (ISP)	PIC24FV16KA302@SOIC28 [SA404]
PIC24FV16KA302@SSOP28 [SA626A]	
PIC24FV16KA302@TQFP44 [SA245A-B4805]	
PIC24FV16KA304 (ISP)	PIC24FV16KM102
PIC24FV16KM102 (ISP)	PIC24FV16KM102@SOIC28 [SA404]
PIC24FV16KM102@SSOP28 [SA626A]	PIC24FV16KM104 (ISP)
PIC24FV16KM104@TQFP44 [SA245A-B4805]	
PIC24FV16KM202	PIC24FV16KM202 (ISP)
PIC24FV16KM202@SOIC28 [SA404]	PIC24FV16KM202@SSOP28 [SA626A]
PIC24FV16KM204 (ISP)	
PIC24FV16KM204@TQFP44 [SA245A-B4805]	
PIC24FV32KA301	PIC24FV32KA301 (ISP)
PIC24FV32KA301@SOIC20 [SA404]	PIC24FV32KA301@SSOP20 [SA626A]
PIC24FV32KA302	PIC24FV32KA302 (ISP)
PIC24FV32KA302@SOIC28 [SA404]	PIC24FV32KA302@SSOP28 [SA626A]
PIC24FV32KA302@TQFP44 [SA245A-B4805]	
PIC24FV32KA304 (ISP)	PIC24HJ128GP202
PIC24HJ128GP202 (ISP)	PIC24HJ128GP202@QFN28 [\$\$\$\$\$]
PIC24HJ128GP202@SOIC28 [SA404]	PIC24HJ128GP202@SSOP28 [SA626A]
PIC24HJ128GP204 (ISP)	PIC24HJ128GP204@QFN44 [SA737]
PIC24HJ128GP204@TQFP44 [SA245A-B4805]	
PIC24HJ128GP206 (ISP)	PIC24HJ128GP206A (ISP)
PIC24HJ128GP210 (ISP)	PIC24HJ128GP210A (ISP)
PIC24HJ128GP306 (ISP)	PIC24HJ128GP306A (ISP)
PIC24HJ128GP310 (ISP)	PIC24HJ128GP310A (ISP)
PIC24HJ128GP502	PIC24HJ128GP502 (ISP)
PIC24HJ128GP502@QFN28 [\$\$\$\$\$]	PIC24HJ128GP502@SOIC28 [SA404]
PIC24HJ128GP502@SSOP28 [SA626A]	PIC24HJ128GP504 (ISP)
PIC24HJ128GP504@QFN44 [SA737]	
PIC24HJ128GP504@TQFP44 [SA245A-B4805]	
PIC24HJ128GP504@TQFP44 (DELTA) [SA245A-B4805]	
PIC24HJ128GP506 (ISP)	PIC24HJ128GP506A (ISP)
PIC24HJ128GP510 (ISP)	PIC24HJ128GP510A (ISP)

PIC24HJ12GP201	PIC24HJ12GP201 (ISP)
PIC24HJ12GP201@SOIC18 [SA404]	PIC24HJ12GP201@SOIC18 (ISP)
PIC24HJ12GP202	PIC24HJ12GP202 (ISP)
PIC24HJ12GP202@QFN28 [SA685]	PIC24HJ12GP202@QFN28 (ISP)
PIC24HJ12GP202@SOIC28 [SA404]	PIC24HJ12GP202@SOIC28 (ISP)
PIC24HJ12GP202@SSOP28 [SA626A]	PIC24HJ12GP202@SSOP28 (ISP)
PIC24HJ16GP304@QFN44 [SA737]	PIC24HJ16GP304@QFN44 (ISP)
PIC24HJ16GP304@TQFP44 [SA245A-B4805]	
PIC24HJ16GP304@TQFP44 (ISP)	PIC24HJ256GP206 (ISP)
PIC24HJ256GP206A (ISP)	PIC24HJ256GP210 (ISP)
PIC24HJ256GP210A (ISP)	PIC24HJ256GP610 (ISP)
PIC24HJ256GP610A (ISP)	PIC24HJ32GP202
PIC24HJ32GP202 (ISP)	PIC24HJ32GP202@QFN28 [SA685]
PIC24HJ32GP202@QFN28 (ISP)	PIC24HJ32GP202@SOIC28 [SA404]
PIC24HJ32GP202@SOIC28 (ISP)	PIC24HJ32GP202@SSOP28 [SA626A]
PIC24HJ32GP202@SSOP28 (ISP)	PIC24HJ32GP204@QFN44 [SA737]
PIC24HJ32GP204@QFN44 (ISP)	
PIC24HJ32GP204@TQFP44 [SA245A-B4805]	
PIC24HJ32GP204@TQFP44 (ISP)	PIC24HJ32GP302
PIC24HJ32GP302 (ISP)	PIC24HJ32GP302@QFN28 [SA685]
PIC24HJ32GP302@QFN28 (ISP)	PIC24HJ32GP302@SOIC28 [SA404]
PIC24HJ32GP302@SOIC28 (ISP)	PIC24HJ32GP302@SSOP28 [SA626A]
PIC24HJ32GP302@SSOP28 (ISP)	PIC24HJ32GP304@QFN44 [SA737]
PIC24HJ32GP304@QFN44 (ISP)	
PIC24HJ32GP304@TQFP44 [SA245A-B4805]	
PIC24HJ32GP304@TQFP44 (ISP)	PIC24HJ64GP202
PIC24HJ64GP202 (ISP)	PIC24HJ64GP202@QFN28 [SA685]
PIC24HJ64GP202@QFN28 (ISP)	PIC24HJ64GP202@SOIC28 [SA404]
PIC24HJ64GP202@SOIC28 (ISP)	PIC24HJ64GP202@SSOP28 [SA626A]
PIC24HJ64GP202@SSOP28 (ISP)	PIC24HJ64GP204@QFN44 [SA737]
PIC24HJ64GP204@QFN44 (ISP)	
PIC24HJ64GP204@TQFP44 [SA245A-B4805]	
PIC24HJ64GP204@TQFP44 (ISP)	PIC24HJ64GP206@QFN64 (ISP)
PIC24HJ64GP206@TQFP64 (ISP)	PIC24HJ64GP206A@QFN64 (ISP)
PIC24HJ64GP206A@TQFP64 (ISP)	PIC24HJ64GP210@TQFP100 (12) (ISP)
PIC24HJ64GP210@TQFP100 (14) (ISP)	PIC24HJ64GP210A@TQFP100 (12) (ISP)
PIC24HJ64GP210A@TQFP100 (14) (ISP)	PIC24HJ64GP502
PIC24HJ64GP502 (ISP)	PIC24HJ64GP502@QFN28 [SA685]
PIC24HJ64GP502@QFN28 (ISP)	PIC24HJ64GP502@SOIC28 [SA404]
PIC24HJ64GP502@SOIC28 (ISP)	PIC24HJ64GP502@SSOP28 [SA626A]
PIC24HJ64GP502@SSOP28 (ISP)	PIC24HJ64GP504@QFN44 [SA737]
PIC24HJ64GP504@QFN44 (ISP)	
PIC24HJ64GP504@TQFP44 [SA245A-B4805]	
PIC24HJ64GP504@TQFP44 (ISP)	PIC24HJ64GP506@QFN64 (ISP)
PIC24HJ64GP506@TQFP64 (ISP)	PIC24HJ64GP506A@QFN64 (ISP)
PIC24HJ64GP506A@TQFP64 (ISP)	PIC24HJ64GP510@TQFP100 (12) (ISP)
PIC24HJ64GP510@TQFP100 (14) (ISP)	PIC24HJ64GP510A@TQFP100 (12) (ISP)
PIC24HJ64GP510A@TQFP100 (14) (ISP)	PIC30F1010
PIC30F1010@ISP	PIC30F1010@QFN28 [SA685]
PIC30F1010@SDIP28 [SA653]	PIC30F1010@SOIC28 [SA404]
PIC30F2020	PIC30F2020@ISP
PIC30F2020@QFN28 [SA685]	PIC30F2020@SDIP28 [SA653]
PIC30F2020@SOIC28 [SA404]	PIC30F2023@ISP

PIC30F2023@QFN44 [SA685]  
PS200  
PS200@SOIC20 [SA404]  
PS200@SSOP20 [SA626A]  
rfPIC12C509AF@SSOP20 [SA626A]  
rfPIC12C509AG@SOIC18 [SA404]  
rfPIC12LC509AF@SSOP20 [SA626A]  
rfPIC12LC509AG@SOIC18 [SA404]

PIC30F2023@TQFP44 [SA245A-B4805]  
PS200 (ISP)  
PS200@SOIC20 (ISP)  
PS200@SSOP20 (ISP)  
rfPIC12C509AF@SSOP20 (ISP)  
rfPIC12C509AG@SOIC18 (ISP)  
rfPIC12LC509AF@SSOP20 (ISP)  
rfPIC12LC509AG@SOIC18 (ISP)

## MICROCHIP (SST)

### E (E) PROM/FRAM/NVRAM

SST25LF010@SOIC8 (4.0) [SA602A]  
SST25LF010@WSON8 [SA683]  
SST25LF010A@SOIC8 (5.4) [SA605B]  
SST25LF016A@SOIC8 (4.0) [SA602A]  
SST25LF016A@WSON8 [SA683]  
SST25LF016B@SOIC8 (5.4) [SA605B]  
SST25LF020@SOIC8 (4.0) [SA602A]  
SST25LF020@WSON8 [SA683]  
SST25LF020A@SOIC8 (5.4) [SA605B]  
SST25LF040@SOIC8 (4.0) [SA602A]  
SST25LF040@WSON8 [SA683]  
SST25LF040A@SOIC8 (5.4) [SA605B]  
SST25LF080@SOIC8 (4.0) [SA602A]  
SST25LF080@WSON8 [SA683]  
SST25LF080A@SOIC8 (5.4) [SA605B]  
SST25VF010@SOIC8 (4.0) [SA602A]  
SST25VF010@WSON8 [SA683]  
SST25VF010A@SOIC8 (5.4) [SA605B]  
SST25VF016B@SOIC8 (4.0) [SA602A]  
SST25VF016B@WSON8 [SA683]  
SST25VF020@SOIC8 (5.4) [SA605B]  
SST25VF020B@SOIC8 (4.0) [SA602A]  
SST25VF020B@WSON8 [SA683]  
SST25VF032B@SOIC8 (4.0) [SA602A]  
SST25VF032B@WSON8 [SA683]  
SST25VF040@SOIC8 (5.4) [SA605B]  
SST25VF040B@SOIC8 (4.0) [SA602A]  
SST25VF040B@WSON8 [SA683]  
SST25VF064C@SOIC8 [SA605B]  
SST25VF080@SOIC8 (4.0) [SA602A]  
SST25VF080@WSON8 [SA683]  
SST25VF080B@SOIC8 (5.4) [SA605B]  
SST25VF512@SOIC8 (4.0) [SA602A]  
SST25VF512@WSON8 [SA683]  
SST25VF512A@SOIC8 (5.4) [SA605B]  
SST25WF010@SOIC8 (4.0) [SA602A]  
SST25WF010@WSON8 [SA683]  
SST25WF020@SOIC8 (5.4) [SA605B]  
SST25WF020A@SOIC8 (4.0) [SA602A]

SST25LF010@SOIC8 (5.4) [SA605B]  
SST25LF010A@SOIC8 (4.0) [SA602A]  
SST25LF010A@WSON8 [SA683]  
SST25LF016A@SOIC8 (5.4) [SA605B]  
SST25LF016B@SOIC8 (4.0) [SA602A]  
SST25LF016B@WSON8 [SA683]  
SST25LF020@SOIC8 (5.4) [SA605B]  
SST25LF020A@SOIC8 (4.0) [SA602A]  
SST25LF020A@WSON8 [SA683]  
SST25LF040@SOIC8 (5.4) [SA605B]  
SST25LF040A@SOIC8 (4.0) [SA602A]  
SST25LF040A@WSON8 [SA683]  
SST25LF080@SOIC8 (5.4) [SA605B]  
SST25LF080A@SOIC8 (4.0) [SA602A]  
SST25LF080A@WSON8 [SA683]  
SST25VF010@SOIC8 (5.4) [SA605B]  
SST25VF010A@SOIC8 (4.0) [SA602A]  
SST25VF010A@WSON8 [SA683]  
SST25VF016B@SOIC8 (5.4) [SA605B]  
SST25VF020@SOIC8 (4.0) [SA602A]  
SST25VF020@WSON8 [SA683]  
SST25VF020B@SOIC8 (5.4) [SA605B]  
SST25VF032B@SOIC16 [SA404]  
SST25VF032B@SOIC8 (5.4) [SA605B]  
SST25VF040@SOIC8 (4.0) [SA602A]  
SST25VF040@WSON8 [SA683]  
SST25VF040B@SOIC8 (5.4) [SA605B]  
SST25VF064C@SOIC16 [SA404]  
SST25VF064C@WSON8 [SA684]  
SST25VF080@SOIC8 (5.4) [SA605B]  
SST25VF080B@SOIC8 (4.0) [SA602A]  
SST25VF080B@WSON8 [SA683]  
SST25VF512@SOIC8 (5.4) [SA605B]  
SST25VF512A@SOIC8 (4.0) [SA602A]  
SST25VF512A@WSON8 [SA683]  
SST25WF010@SOIC8 (5.4) [SA605B]  
SST25WF020@SOIC8 (4.0) [SA602A]  
SST25WF020@WSON8 [SA683]  
SST25WF020A@SOIC8 (5.4) [SA605B]

SST25WF020A@WSON8 [SA683]	SST25WF040@SOIC8 (4. 0) [SA602A]
SST25WF040@SOIC8 (5. 4) [SA605B]	SST25WF040@WSON8 [SA683]
SST25WF080@SOIC8 (4. 0) [SA602A]	SST25WF080@SOIC8 (5. 4) [SA605B]
SST25WF080@WSON8 [SA683]	SST25WF080B@SOIC8 (4. 0) [SA602A]
SST25WF080B@SOIC8 (5. 4) [SA605B]	SST25WF080B@WSON8 [SA683]
SST25WF512@SOIC8 (4. 0) [SA602A]	SST25WF512@SOIC8 (5. 4) [SA605B]
SST25WF512@WSON8 [SA683]	SST26VF064B@SOIC16 [SA404]
SST26VF064B@SOIC8 [SA605B]	SST26VF064B@TFBGA24 [TA088]
SST26VF064B@WDFN8 [SA684]	SST26VF064BA@SOIC16 [SA404]
SST26VF064BA@SOIC8 [SA605B]	SST26VF064BA@TFBGA24 [TA088]
SST26VF064BA@WDFN8 [SA684]	

## MICRON

### E (E) PROM/FRAM/NVRAM

MT28F002B1VG-B@TSOP40 [SA409T-B4002]	
MT28F002B1VG-T@TSOP40 [SA409T-B4002]	
MT28F002B3VG-B@TSOP40 [SA409T-B4002]	
MT28F002B3VG-T@TSOP40 [SA409T-B4002]	
MT28F002B5VG-B@TSOP40 [SA409T-B4002]	
MT28F002B5VG-T@TSOP40 [SA409T-B4002]	
MT28F002C1VG-T@TSOP40 [SA409T-B4002]	
MT28F002C5VG-T@TSOP40 [SA409T-B4002]	
MT28F002VG-B@TSOP40 [SA409T-B4002]	
MT28F002VG-T@TSOP40 [SA409T-B4002]	
MT28F004B1VG-B@TSOP40 [SA409T-B4002]	
MT28F004B1VG-T@TSOP40 [SA409T-B4002]	
MT28F004B3VG-B@TSOP40 [SA409T-B4002]	
MT28F004B3VG-T@TSOP40 [SA409T-B4002]	
MT28F004B5VG-B@TSOP40 [SA409T-B4002]	
MT28F004B5VG-T@TSOP40 [SA409T-B4002]	
MT28F004VG-B@TSOP40 [SA409T-B4002]	
MT28F004VG-T@TSOP40 [SA409T-B4002]	
MT28F008B1VG-B@TSOP40 [SA409T-B4002]	
MT28F008B1VG-T@TSOP40 [SA409T-B4002]	
MT28F008B3VG-B@TSOP40 [SA409T-B4002]	
MT28F008B3VG-T@TSOP40 [SA409T-B4002]	
MT28F008B5VG-B@TSOP40 [SA409T-B4002]	
MT28F008B5VG-T@TSOP40 [SA409T-B4002]	
MT28F016S3VG@TSOP40 [SA409T-B4002]	
MT28F016S5VG@TSOP40 [SA409T-B4002]	
MT28F200B1SGB@PSOP44 [SA638]	MT28F200B1SGT@PSOP44 [SA638]
MT28F200B1WGB@TSOP48 [SB247-B4806]	
MT28F200B1WGT@TSOP48 [SB247-B4806]	
MT28F200B3SGB@PSOP44 [SA638]	MT28F200B3SGT@PSOP44 [SA638]
MT28F200B3WGB@TSOP48 [SB247-B4806]	
MT28F200B3WGT@TSOP48 [SB247-B4806]	
MT28F200B5SGB@PSOP44 [SA638]	MT28F200B5SGT@PSOP44 [SA638]
MT28F200B5WGB@TSOP48 [SB247-B4806]	
MT28F200B5WGT@TSOP48 [SB247-B4806]	
MT28F400B1SGB@PSOP44 [SA638]	MT28F400B1SGT@PSOP44 [SA638]

MT28F400B1WGB@TSOP48 [SB247-B4806]	
MT28F400B1WGT@TSOP48 [SB247-B4806]	
MT28F400B3SGB@PSOP44 [SA638]	MT28F400B3SGT@PSOP44 [SA638]
MT28F400B3WGB@TSOP48 [SB247-B4806]	
MT28F400B3WGT@TSOP48 [SB247-B4806]	
MT28F400B5SGB@PSOP44 [SA638]	MT28F400B5SGT@PSOP44 [SA638]
MT28F400B5WGB@TSOP48 [SB247-B4806]	
MT28F400B5WGT@TSOP48 [SB247-B4806]	
MT28F800B1SGB@PSOP44 [SA638]	MT28F800B1SGT@PSOP44 [SA638]
MT28F800B1WGB@TSOP48 [SB247-B4806]	
MT28F800B1WGT@TSOP48 [SB247-B4806]	
MT28F800B3SGB@PSOP44 [SA638]	MT28F800B3SGT@PSOP44 [SA638]
MT28F800B3WGB@TSOP48 [SB247-B4806]	
MT28F800B3WGT@TSOP48 [SB247-B4806]	
MT28F800B5SGB@PSOP44 [SA638]	MT28F800B5SGT@PSOP44 [SA638]
MT28F800B5WGB@TSOP48 [SB247-B4806]	
MT28F800B5WGT@TSOP48 [SB247-B4806]	
MT29F1G08ABADA@TSOP48 [SB247-B4806]	
MT29F1G08ABAEA@TSOP48 [SB247-B4806]	
MT29F2G08ABAEA@TSOP48 [SB247-B4806]	

## MIRA

### E (E) PROM/FRAM/NVRAM

PSU12A30BT@TSOP48 [SB247-B4806]	PSU1GA30BT@TSOP48 [SB247-B4806]
PSU1GA30HT@TSOP48 [SB247-B4806]	PSU4GA30AT@TSOP48 [SB247-B4806]

## mitsubishi

### E (E) PROM/FRAM/NVRAM

M5L27128K	M5L2716
M5L27256K	M5L2732
M5L2732A	M5L27512
M5L27512K	M5L2764K
M5L27C512A	M5M27128P
M5M27256P	M5M27512P
M5M2764P	M5M27C100K
M5M27C100K@PLCC32 [SA015A1T]	M5M27C100K@TSOP32 [SA410T-B4001]
M5M27C100P	M5M27C100P@PLCC32 [SA015A1T]
M5M27C100P@TSOP32 [SA410T-B4001]	M5M27C101JK
M5M27C101JK@PLCC32 [SA015A1T]	
M5M27C101JK@TSOP32 [SA410T-B4001]	
M5M27C101K	M5M27C101K@PLCC32 [SA015A1T]
M5M27C101K@TSOP32 [SA410T-B4001]	M5M27C101P
M5M27C101P@PLCC32 [SA015A1T]	M5M27C101P@TSOP32 [SA410T-B4001]
M5M27C102K	M5M27C102K@PLCC44 [SA244]
M5M27C102P	M5M27C102P@PLCC44 [SA244]
M5M27C128K	M5M27C201K
M5M27C201K@PLCC32 [SA015A1T]	M5M27C201K@TSOP32 [SA410T-B4001]
M5M27C202K	M5M27C202K@PLCC44 [SA244]

M5M27C256 (K)	M5M27C256 (P)
M5M27C256A (FP)	M5M27C256A (K)
M5M27C256A (P)	M5M27C401K
M5M27C401K@PLCC32 [SA015A1T]	M5M27C401K@TSOP32 [SA410T-B4001]
M5M27C402K	M5M27C512 (FP)
M5M27C512A (FP)	M5M27C512A (K)
M5M27C512A (P)	M5M28F101
M5M28F101 (REVERSE)@TSOP32 [SA410T-B4001]	
M5M28F101@PLCC32 [SA015A1T]	M5M28F101@SOP32 [SA438T]
M5M28F101@TSOP32 [SA410T-B4001]	M5M28F101A
M5M28F101A (REVERSE)@TSOP32 [SA410T-B4001]	
M5M28F101A@PLCC32 [SA015A1T]	M5M28F101A@SOIC32 [SA438T]
M5M28F101A@TSOP32 [SA410T-B4001]	
M5M28FB800 (VP)@TSOP48 [SA247-B4806]	
M5M28FT800 (VP)@TSOP48 [SA247-B4806]	
M5M29FB160A@TSOP48 [SA247-B4806]	M5M29FB800 (FP)@PSOP44 [SA638]
M5M29FB800 (VP)@TSOP48 [SA247-B4806]	
M5M29FT160A@TSOP48 [SA247-B4806]	M5M29FT800 (FP)@PSOP44 [SA638]
M5M29FT800 (VP)@TSOP48 [SA247-B4806]	
M5M29GB160B (VP)@TSOP48 [SA247-B4806]	
M5M29GB320 (VP)@TSOP48 [SA247-B4806]	
M5M29GB640VP@TSOP48 [SA247-B4806]	
M5M29GT160B (VP)@TSOP48 [SA247-B4806]	
M5M29GT320 (VP)@TSOP48 [SA247-B4806]	
M5M29GT640VP@TSOP48 [SA247-B4806]	
M5M29JB160A@TSOP48 [SA247-B4806]	M5M29JT160A@TSOP48 [SA247-B4806]
M6M80011A	M6M80011A@SOIC10 [SA605B]
M6M80011A@SOIC16 [SA605B]	M6M80021
M6M80021@SOIC10 [SA605B]	M6M80021@SOIC16 [SA605B]
M6M80041	M6M80041@SOIC10 [SA605B]

## MICROCONTROLLER

M30260F3AGP@QFP48 [SA248-B4804]	M30260F3TGP@QFP48 [SA248-B4804]
M30260F3VGP@QFP48 [SA248-B4804]	M30260F6AGP@QFP48 [SA248-B4804]
M30260F6TGP@QFP48 [SA248-B4804]	M30260F6VGP@QFP48 [SA248-B4804]
M30260F8AGP@QFP48 [SA248-B4804]	M30260F8TGP@QFP48 [SA248-B4804]
M30260F8VGP@QFP48 [SA248-B4804]	M30262F3GP@QFP48 [SA248-B4804]
M30262F4GP@QFP48 [SA248-B4804]	M30262F6GP@QFP48 [SA248-B4804]
M30262F8GP@QFP48 [SA248-B4804]	M30263F3AFP@SSOP42 [SA775]
M30263F6AFP@SSOP42 [SA775]	M30263F8AFP@SSOP42 [SA775]

## MOSEL-VITELIC

### E (E) PROM/FRAM/NVRAM

V29C31004B	V29C31004B@PLCC32 [SA015A1T]
V29C31004B@TSOP32 [SA410T-B4001]	V29C31004T
V29C31004T@PLCC32 [SA015A1T]	V29C31004T@TSOP32 [SA410T-B4001]
V29C51000B	V29C51000B@PLCC32 [SA015A1T]
V29C51000B@TSOP32 [SA410T-B4001]	V29C51000T
V29C51000T@PLCC32 [SA015A1T]	V29C51000T@TSOP32 [SA410T-B4001]

V29C51001B  
V29C51001B@TSOP32 [SA410T-B4001]  
V29C51001T@PLCC32 [SA015A1T]  
V29C51002B  
V29C51002B@TSOP32 [SA410T-B4001]  
V29C51002T@PLCC32 [SA015A1T]  
V29C51004B  
V29C51004B@TSOP32 [SA410T-B4001]  
V29C51004T@PLCC32 [SA015A1T]  
V29LC51000  
V29LC51000@TSOP32 [SA410T-B4001]  
V29LC51001@PLCC32 [SA015A1T]  
V29LC51002  
V29LC51002@TSOP32 [SA410T-B4001]

V29C51001B@PLCC32 [SA015A1T]  
V29C51001T  
V29C51001T@TSOP32 [SA410T-B4001]  
V29C51002B@PLCC32 [SA015A1T]  
V29C51002T  
V29C51002T@TSOP32 [SA410T-B4001]  
V29C51004B@PLCC32 [SA015A1T]  
V29C51004T  
V29C51004T@TSOP32 [SA410T-B4001]  
V29LC51000@PLCC32 [SA015A1T]  
V29LC51001  
V29LC51001@TSOP32 [SA410T-B4001]  
V29LC51002@PLCC32 [SA015A1T]

## MICROCONTROLLER

MSU1958  
MSU1958@TQFP44 [SA675-B4805]  
MSU2952@PLCC44 [SA244]  
MSU2958  
MSU2958@TQFP44 [SA675-B4805]  
MSU2964@PLCC44 [SA244]

MSU1958@PLCC44 [SA244]  
MSU2952  
MSU2952@TQFP44 [SA675-B4805]  
MSU2958@PLCC44 [SA244]  
MSU2964  
MSU2964@TQFP44 [SA675-B4805]

## MOSMIC

### MICROCONTROLLER

MOS33001  
MOS33001@TQFP44 [SA245A-B4805]  
MOS33002@PLCC44 [SA244]  
MOS33004  
MOS33004@TQFP44 [SA245A-B4805]  
MOS33008@PLCC44 [SA244]  
MOS33016  
MOS33016@TQFP44 [SA245A-B4805]  
MOS33032@PLCC44 [SA244]  
MOS33064  
MOS33064@TQFP44 [SA245A-B4805]  
MOS33128@PLCC44 [SA244]  
MOS33256  
MOS33256@TQFP44 [SA245A-B4805]

MOS33001@PLCC44 [SA244]  
MOS33002  
MOS33002@TQFP44 [SA245A-B4805]  
MOS33004@PLCC44 [SA244]  
MOS33008  
MOS33008@TQFP44 [SA245A-B4805]  
MOS33016@PLCC44 [SA244]  
MOS33032  
MOS33032@TQFP44 [SA245A-B4805]  
MOS33064@PLCC44 [SA244]  
MOS33128  
MOS33128@TQFP44 [SA245A-B4805]  
MOS33256@PLCC44 [SA244]

## MOSTEK

### E (E) PROM/FRAM/NVRAM

ET2716  
ETC2732  
MK2764  
MK48C12

ETC2716  
MK2716  
MK48C02  
MK48T02

MK48T08  
MK48T12B  
MK48Z02  
MK48Z12  
MK48Z18

MK48T12  
MK48T18  
MK48Z08  
MK48Z12B

## MOTOROLA

### E (E) PROM/FRAM/NVRAM

MC68764  
MCM2716

MC68766

### DRAM & SRAM

MCM60256A  
MCM60256AC  
MCM60256AV  
MCM60L256A  
MCM60L256AC  
MCM60L256AV  
MCM6206  
MCM6206C  
MCM6264  
MCM6264C  
MCM6706  
MCM6706A

MCM60256A@SOIC28 [SA630]  
MCM60256AC@SOIC28 [SA630]  
MCM60256AV@SOIC28 [SA630]  
MCM60L256A@SOIC28 [SA630]  
MCM60L256AC@SOIC28 [SA630]  
MCM60L256AV@SOIC28 [SA630]  
MCM6206@SOIC28 [SA630]  
MCM6206C@SOIC28 [SA630]  
MCM6264@SOIC28 [SA630]  
MCM6264C@SOIC28 [SA630]  
MCM6706@SOIC28 [SA630]  
MCM6706A@SOJ28 [SA630]

### MICROCONTROLLER

MC56F8023MFAE@QFP32 [SA636]  
MC56F8025VLD@QFP44 [SA245A-B4805]  
MC56F8033VLC@QFP32 [SA636]  
MC56F8035VLD@QFP44 [SA245A-B4805]  
MC56F8036MFAE@QFP48 [SA248-B4804]  
MC56F8036VFAE@QFP48 [SA248-B4804]  
MC68HC908JB12DW@SOIC28 [SA404]  
MC68HC908JB12JDW@SOIC20 [SA404]  
MC68HC908JB16DW@SOIC28 [SA404]  
MC68HC908JB16FA@QFP32 [SA636]  
MC68HC908JB16JDW@SOIC20 [SA404]  
MC68HC908JB8ADW@SOIC28 [SA404]  
MC68HC908JB8FB@TQFP44 [SA245A-B4805]  
MC68HC908JB8FBE@TQFP44 [SA245A-B4805]  
MC68HC908JB8JDW@SOIC20 [SA404]  
MC68HC908JB8JP  
MC68HC908JK1CDW@SOIC20 [SA404]  
MC68HC908JK1CP  
MC68HC908JK1ECDW@SOIC20 [SA404]  
MC68HC908JK1ECP  
MC68HC908JK1EMDW@SOIC20 [SA404]

MC56F8023VFAE@QFP32 [SA636]  
MC68HC908JB12DWE@SOIC28 [SA404]  
MC68HC908JB12JDWE@SOIC20 [SA404]  
MC68HC908JB16DWE@SOIC28 [SA404]  
MC68HC908JB16FAE@QFP32 [SA636]  
MC68HC908JB16JDWE@SOIC20 [SA404]  
MC68HC908JB8ADWE@SOIC28 [SA404]  
MC68HC908JB8JDWE@SOIC20 [SA404]  
MC68HC908JB8JPE  
MC68HC908JK1CDWE@SOIC20 [SA404]  
MC68HC908JK1CPE  
MC68HC908JK1ECDWE@SOIC20 [SA404]  
MC68HC908JK1ECP  
MC68HC908JK1EMDWE@SOIC20 [SA404]

MC68HC908JK1EMP	MC68HC908JK1EMPE
MC68HC908JK1EVDW@SOIC20 [SA404]	MC68HC908JK1EVDWE@SOIC20 [SA404]
MC68HC908JK1EVP	MC68HC908JK1EVPE
MC68HC908JK1MDW@SOIC20 [SA404]	MC68HC908JK1MDWE@SOIC20 [SA404]
MC68HC908JK1MP	MC68HC908JK1MPE
MC68HC908JK1VDW@SOIC20 [SA404]	MC68HC908JK1VDWE@SOIC20 [SA404]
MC68HC908JK1VP	MC68HC908JK1VPE
MC68HC908JK3CDW@SOIC20 [SA404]	MC68HC908JK3CDWE@SOIC20 [SA404]
MC68HC908JK3CP	MC68HC908JK3CPE
MC68HC908JK3ECDW@SOIC20 [SA404]	MC68HC908JK3ECDWE@SOIC20 [SA404]
MC68HC908JK3ECP	MC68HC908JK3ECPE
MC68HC908JK3EMDW@SOIC20 [SA404]	MC68HC908JK3EMDWE@SOIC20 [SA404]
MC68HC908JK3EMP	MC68HC908JK3EMPE
MC68HC908JK3EVDW@SOIC20 [SA404]	MC68HC908JK3EVDWE@SOIC20 [SA404]
MC68HC908JK3EVP	MC68HC908JK3EVPE
MC68HC908JK3MDW@SOIC20 [SA404]	MC68HC908JK3MDWE@SOIC20 [SA404]
MC68HC908JK3MP	MC68HC908JK3MPE
MC68HC908JK3VDW@SOIC20 [SA404]	MC68HC908JK3VDWE@SOIC20 [SA404]
MC68HC908JK3VP	MC68HC908JK3VPE
MC68HC908JL3CDW@SOIC28 [SA404]	MC68HC908JL3CDWE@SOIC28 [SA404]
MC68HC908JL3CP	MC68HC908JL3CPE
MC68HC908JL3ECDW@SOIC28 [SA404]	MC68HC908JL3ECDWE@SOIC28 [SA404]
MC68HC908JL3ECP	MC68HC908JL3ECPE
MC68HC908JL3EMDW@SOIC28 [SA404]	MC68HC908JL3EMDWE@SOIC28 [SA404]
MC68HC908JL3EMP	MC68HC908JL3EMPE
MC68HC908JL3EVDW@SOIC28 [SA404]	MC68HC908JL3EVDWE@SOIC28 [SA404]
MC68HC908JL3EVP	MC68HC908JL3EVPE
MC68HC908JL3MDW@SOIC28 [SA404]	MC68HC908JL3MDWE@SOIC28 [SA404]
MC68HC908JL3MP	MC68HC908JL3MPE
MC68HC908JL3VDW@SOIC28 [SA404]	MC68HC908JL3VDWE@SOIC28 [SA404]
MC68HC908JL3VP	MC68HC908JL3VPE
MC68HC908KK3ECDW@SOIC20 [SA404]	MC68HC908KK3ECDWE@SOIC20 [SA404]
MC68HC908KK3ECP	MC68HC908KK3ECPE
MC68HC908KK3EMDW@SOIC20 [SA404]	MC68HC908KK3EMDWE@SOIC20 [SA404]
MC68HC908KK3EMP	MC68HC908KK3EMPE
MC68HC908KK3EVDW@SOIC20 [SA404]	MC68HC908KK3EVDWE@SOIC20 [SA404]
MC68HC908KK3EVP	MC68HC908KK3EVPE
MC68HC908KL3ECDW@SOIC28 [SA404]	MC68HC908KL3ECDWE@SOIC28 [SA404]
MC68HC908KL3ECP	MC68HC908KL3ECPE
MC68HC908KL3EMDW@SOIC28 [SA404]	MC68HC908KL3EMDWE@SOIC28 [SA404]
MC68HC908KL3EMP	MC68HC908KL3EMPE
MC68HC908KL3EVDW@SOIC28 [SA404]	MC68HC908KL3EVDWE@SOIC28 [SA404]
MC68HC908KL3EVP	MC68HC908KL3EVPE
MC68HC908QT1ACDW@SOIC8 [SA605B]	
MC68HC908QT1ACDW@SOIC8 (a-trim) [SA605B]	
MC68HC908QT1ACDWE@SOIC8 [SA605B]	
MC68HC908QT1ACDWE@SOIC8 (a-trim) [SA605B]	
MC68HC908QT1ACP	MC68HC908QT1ACP (a-trim)
MC68HC908QT1ACPE	MC68HC908QT1ACPE (a-trim)
MC68HC908QT1AMDW@SOIC8 [SA605B]	
MC68HC908QT1AMDW@SOIC8 (a-trim) [SA605B]	
MC68HC908QT1AMDWE@SOIC8 [SA605B]	
MC68HC908QT1AMDWE@SOIC8 (a-trim) [SA605B]	

MC68HC908QT1AMP	MC68HC908QT1AMP (a-trim)
MC68HC908QT1AMPE	MC68HC908QT1AMPE (a-trim)
MC68HC908QT1AVDW@SOIC8 [SA605B]	
MC68HC908QT1AVDW@SOIC8 (a-trim) [SA605B]	
MC68HC908QT1AVDWE@SOIC8 [SA605B]	
MC68HC908QT1AVDWE@SOIC8 (a-trim) [SA605B]	
MC68HC908QT1AVP	MC68HC908QT1AVP (a-trim)
MC68HC908QT1AVPE	MC68HC908QT1AVPE (a-trim)
MC68HC908QT1CDW@SOIC8 [SA605B]	MC68HC908QT1CDWE@SOIC8 [SA605B]
MC68HC908QT1CP	MC68HC908QT1CPE
MC68HC908QT1MDW@SOIC8 [SA605B]	MC68HC908QT1MDWE@SOIC8 [SA605B]
MC68HC908QT1MP	MC68HC908QT1MPE
MC68HC908QT1VDW@SOIC8 [SA605B]	MC68HC908QT1VDWE@SOIC8 [SA605B]
MC68HC908QT1VP	MC68HC908QT1VPE
MC68HC908QT2ACDW@SOIC8 [SA605B]	
MC68HC908QT2ACDW@SOIC8 (a-trim) [SA605B]	
MC68HC908QT2ACDWE@SOIC8 [SA605B]	
MC68HC908QT2ACDWE@SOIC8 (a-trim) [SA605B]	
MC68HC908QT2ACP	MC68HC908QT2ACP (a-trim)
MC68HC908QT2ACPE	MC68HC908QT2ACPE (a-trim)
MC68HC908QT2AMDW@SOIC8 [SA605B]	
MC68HC908QT2AMDW@SOIC8 (a-trim) [SA605B]	
MC68HC908QT2AMDWE@SOIC8 [SA605B]	
MC68HC908QT2AMDWE@SOIC8 (a-trim) [SA605B]	
MC68HC908QT2AMP	MC68HC908QT2AMP (a-trim)
MC68HC908QT2AMPE	MC68HC908QT2AMPE (a-trim)
MC68HC908QT2AVDW@SOIC8 [SA605B]	
MC68HC908QT2AVDW@SOIC8 (a-trim) [SA605B]	
MC68HC908QT2AVDWE@SOIC8 [SA605B]	
MC68HC908QT2AVDWE@SOIC8 (a-trim) [SA605B]	
MC68HC908QT2AVP	MC68HC908QT2AVP (a-trim)
MC68HC908QT2AVPE	MC68HC908QT2AVPE (a-trim)
MC68HC908QT2CDW@SOIC8 [SA605B]	MC68HC908QT2CDWE@SOIC8 [SA605B]
MC68HC908QT2CP	MC68HC908QT2CPE
MC68HC908QT2MDW@SOIC8 [SA605B]	MC68HC908QT2MDWE@SOIC8 [SA605B]
MC68HC908QT2MP	MC68HC908QT2MPE
MC68HC908QT2VDW@SOIC8 [SA605B]	MC68HC908QT2VDWE@SOIC8 [SA605B]
MC68HC908QT2VP	MC68HC908QT2VPE
MC68HC908QT4ACDW@SOIC8 [SA605B]	
MC68HC908QT4ACDW@SOIC8 (a-trim) [SA605B]	
MC68HC908QT4ACDWE@SOIC8 [SA605B]	
MC68HC908QT4ACDWE@SOIC8 (a-trim) [SA605B]	
MC68HC908QT4ACP	MC68HC908QT4ACP (a-trim)
MC68HC908QT4ACPE	MC68HC908QT4ACPE (a-trim)
MC68HC908QT4AMDW@SOIC8 [SA605B]	
MC68HC908QT4AMDW@SOIC8 (a-trim) [SA605B]	
MC68HC908QT4AMDWE@SOIC8 [SA605B]	
MC68HC908QT4AMDWE@SOIC8 (a-trim) [SA605B]	
MC68HC908QT4AMP	MC68HC908QT4AMP (a-trim)
MC68HC908QT4AMPE	MC68HC908QT4AMPE (a-trim)
MC68HC908QT4AVDW@SOIC8 [SA605B]	
MC68HC908QT4AVDW@SOIC8 (a-trim) [SA605B]	
MC68HC908QT4AVDWE@SOIC8 [SA605B]	

MC68HC908QT4AVDWE@SOIC8 (a-trim) [SA605B]	
MC68HC908QT4AVP	MC68HC908QT4AVP (a-trim)
MC68HC908QT4AVPE	MC68HC908QT4AVPE (a-trim)
MC68HC908QT4CDW@SOIC8 [SA605B]	MC68HC908QT4CDWE@SOIC8 [SA605B]
MC68HC908QT4CP	MC68HC908QT4CPE
MC68HC908QT4MDW@SOIC8 [SA605B]	MC68HC908QT4MDWE@SOIC8 [SA605B]
MC68HC908QT4MP	MC68HC908QT4MPE
MC68HC908QT4VDW@SOIC8 [SA605B]	MC68HC908QT4VDWE@SOIC8 [SA605B]
MC68HC908QT4VP	MC68HC908QT4VPE
MC68HLC908JK1EIDW@SOIC20 [SA404]	
MC68HLC908JK1EIDWE@SOIC20 [SA404]	
MC68HLC908JK1EIP	MC68HLC908JK1EIPE
MC68HLC908JK3EIDW@SOIC20 [SA404]	
MC68HLC908JK3EIDWE@SOIC20 [SA404]	
MC68HLC908JK3EIP	MC68HLC908JK3EIPE
MC68HLC908JL3EIDW@SOIC28 [SA404]	
MC68HLC908JL3EIDWE@SOIC28 [SA404]	
MC68HLC908JL3EIP	MC68HLC908JL3EIPE
MC68HRC908JK1CDW@SOIC20 [SA404]	MC68HRC908JK1CDWE@SOIC20 [SA404]
MC68HRC908JK1CP	MC68HRC908JK1CPE
MC68HRC908JK1ECDW@SOIC20 [SA404]	
MC68HRC908JK1ECDWE@SOIC20 [SA404]	
MC68HRC908JK1ECP	MC68HRC908JK1ECPE
MC68HRC908JK1EMDW@SOIC20 [SA404]	
MC68HRC908JK1EMDWE@SOIC20 [SA404]	
MC68HRC908JK1EMP	MC68HRC908JK1EMPE
MC68HRC908JK1EVDW@SOIC20 [SA404]	
MC68HRC908JK1EVDWE@SOIC20 [SA404]	
MC68HRC908JK1EVP	MC68HRC908JK1EVPE
MC68HRC908JK1MDW@SOIC20 [SA404]	MC68HRC908JK1MDWE@SOIC20 [SA404]
MC68HRC908JK1MP	MC68HRC908JK1MPE
MC68HRC908JK1VDW@SOIC20 [SA404]	MC68HRC908JK1VDWE@SOIC20 [SA404]
MC68HRC908JK1VP	MC68HRC908JK1VPE
MC68HRC908JK3CDW@SOIC20 [SA404]	MC68HRC908JK3CDWE@SOIC20 [SA404]
MC68HRC908JK3CP	MC68HRC908JK3CPE
MC68HRC908JK3ECDW@SOIC20 [SA404]	
MC68HRC908JK3ECDWE@SOIC20 [SA404]	
MC68HRC908JK3ECP	MC68HRC908JK3ECPE
MC68HRC908JK3EMDW@SOIC20 [SA404]	
MC68HRC908JK3EMDWE@SOIC20 [SA404]	
MC68HRC908JK3EMP	MC68HRC908JK3EMPE
MC68HRC908JK3EVDW@SOIC20 [SA404]	
MC68HRC908JK3EVDWE@SOIC20 [SA404]	
MC68HRC908JK3EVP	MC68HRC908JK3EVPE
MC68HRC908JK3MDW@SOIC20 [SA404]	MC68HRC908JK3MDWE@SOIC20 [SA404]
MC68HRC908JK3MP	MC68HRC908JK3MPE
MC68HRC908JK3VDW@SOIC20 [SA404]	MC68HRC908JK3VDWE@SOIC20 [SA404]
MC68HRC908JK3VP	MC68HRC908JK3VPE
MC68HRC908JL3CDW@SOIC28 [SA404]	MC68HRC908JL3CDWE@SOIC28 [SA404]
MC68HRC908JL3CP	MC68HRC908JL3CPE
MC68HRC908JL3ECDW@SOIC28 [SA404]	
MC68HRC908JL3ECDWE@SOIC28 [SA404]	
MC68HRC908JL3ECP	MC68HRC908JL3ECPE

MC68HRC908JL3EMDW@SOIC28 [SA404]  
MC68HRC908JL3EMDWE@SOIC28 [SA404]  
MC68HRC908JL3EMP MC68HRC908JL3EMPE  
MC68HRC908JL3EVDW@SOIC28 [SA404]  
MC68HRC908JL3EVDWE@SOIC28 [SA404]  
MC68HRC908JL3EVP MC68HRC908JL3EVPE  
MC68HRC908JL3MDW@SOIC28 [SA404] MC68HRC908JL3MDWE@SOIC28 [SA404]  
MC68HRC908JL3MP MC68HRC908JL3MPE  
MC68HRC908JL3VDW@SOIC28 [SA404] MC68HRC908JL3VDWE@SOIC28 [SA404]  
MC68HRC908JL3VP MC68HRC908JL3VPE  
MC9RS08KA4CPG(auto trim) MC9RS08KA4CPGE(auto trim)  
MC9RS08KA4CPJ(auto trim) MC9RS08KA4CPJE(auto trim)  
MC9RS08KA4CTG@TSSOP16(auto trim) [SA643]  
MC9RS08KA4CTGE@TSSOP16(auto trim) [SA643]  
MC9RS08KA4CWG@SOIC16(auto trim) [SA404]  
MC9RS08KA4CWGE@SOIC16(auto trim) [SA404]  
MC9RS08KA4CWJ@SOIC20(auto trim) [SA404]  
MC9RS08KA4CWJE@SOIC20(auto trim) [SA404]  
MC9RS08KA4MPG(auto trim) MC9RS08KA4MPGE(auto trim)  
MC9RS08KA4MPJ(auto trim) MC9RS08KA4MPJE(auto trim)  
MC9RS08KA4MTG@TSSOP16(auto trim) [SA643]  
MC9RS08KA4MTGE@TSSOP16(a trim) [SA643]  
MC9RS08KA4MWG@SOIC16(auto trim) [SA404]  
MC9RS08KA4MWGE@SOIC16(auto trim) [SA404]  
MC9RS08KA4MWJ@SOIC20(auto trim) [SA404]  
MC9RS08KA4MWJE@SOIC20(auto trim) [SA404]  
MC9RS08KA4VPG(auto trim) MC9RS08KA4VPGE(auto trim)  
MC9RS08KA4VPJ(auto trim) MC9RS08KA4VPJE(auto trim)  
MC9RS08KA4VTG@TSSOP16(auto trim) [SA643]  
MC9RS08KA4VTGE@TSSOP16(auto trim) [SA643]  
MC9RS08KA4VWG@SOIC16(auto trim) [SA404]  
MC9RS08KA4VWGE@SOIC16(auto trim) [SA404]  
MC9RS08KA4VWJ@SOIC20(auto trim) [SA404]  
MC9RS08KA4VWJE@SOIC20(auto trim) [SA404]  
MC9RS08KA8CPG(auto trim) MC9RS08KA8CPGE(auto trim)  
MC9RS08KA8CPJ(auto trim) MC9RS08KA8CPJE(auto trim)  
MC9RS08KA8CTG@TSSOP16(auto trim) [SA643]  
MC9RS08KA8CTGE@TSSOP16(auto trim) [SA643]  
MC9RS08KA8CWG@SOIC16(auto trim) [SA404]  
MC9RS08KA8CWGE@SOIC16(auto trim) [SA404]  
MC9RS08KA8CWJ@SOIC20(auto trim) [SA404]  
MC9RS08KA8CWJE@SOIC20(auto trim) [SA404]  
MC9RS08KA8MPG(auto trim) MC9RS08KA8MPGE(auto trim)  
MC9RS08KA8MPJ(auto trim) MC9RS08KA8MPJE(auto trim)  
MC9RS08KA8MTG@TSSOP16(auto trim) [SA643]  
MC9RS08KA8MTGE@TSSOP16(a trim) [SA643]  
MC9RS08KA8MWG@SOIC16(auto trim) [SA404]  
MC9RS08KA8MWGE@SOIC16(auto trim) [SA404]  
MC9RS08KA8MWJ@SOIC20(auto trim) [SA404]  
MC9RS08KA8MWJE@SOIC20(auto trim) [SA404]  
MC9RS08KA8VPG(auto trim) MC9RS08KA8VPGE(auto trim)  
MC9RS08KA8VPJ(auto trim) MC9RS08KA8VPJE(auto trim)  
MC9RS08KA8VTG@TSSOP16(auto trim) [SA643]

MC9RS08KA8VTGE@TSSOP16(a trim) [SA643]  
MC9RS08KA8VWGE@SOIC16(auto trim) [SA404]  
MC9RS08KA8VWGE@SOIC16(auto trim) [SA404]  
MC9RS08KA8VWJ@SOIC20(auto trim) [SA404]  
MC9RS08KA8VWJE@SOIC20(auto trim) [SA404]

## MT

### MICROCONTROLLER

P89C668  
P89C668@TQFP44 [SA675-B4805]

P89C668@PLCC44 [SA244]

## MXIC

### E (E) PROM/FRAM/NVRAM

MX30LF1208AA@TSOP48 [SB247-B4806]  
MX30LF1G08AA@TSOP48 [SB247-B4806]

## MY-MS

### E (E) PROM/FRAM/NVRAM

MM24C01-2/3@SOIC8 [SA602A]  
MM24C01-3@SOIC8 [SA602A]  
MM24C02-3  
MM24C04-2/3@SOIC8 [SA602A]  
MM24C04-3@SOIC8 [SA602A]  
MM24C08-3  
MM24C16-2/3@SOIC8 [SA602A]  
MM24C16-3@SOIC8 [SA602A]

MM24C01-3  
MM24C02-2/3@SOIC8 [SA602A]  
MM24C02-3@SOIC8 [SA602A]  
MM24C04-3  
MM24C08-2/3@SOIC8 [SA602A]  
MM24C08-3@SOIC8 [SA602A]  
MM24C16-3

## MYSON

### MICROCONTROLLER

CS8954F@PQFP44 [SA675-B4805]  
CS8954V@PLCC44 [SA244]  
CS8955G@LQFP48 [SA248-B4804]  
CS8955HG@LQFP48 [SA248-B4804]  
CS8955HV@PLCC44 [SA244]  
CS8955V@PLCC44 [SA244]  
MTV212MN64I  
MTV212MS64I@SDIP42 [SA028]  
MTV212MV64I@PLCC44 [SA244]  
MTV230GMS@SDIP42 [SA028]  
MTV230MF@TQFP44 [SA675-B4805]  
MTV230MV@PLCC44 [SA244]  
MTV230PMS@SDIP42 [SA028]

CS8954N  
CS8955F@PQFP44 [SA675-B4805]  
CS8955HF@PQFP44 [SA675-B4805]  
CS8955HN  
CS8955N  
MTV212MN32  
MTV212MS32@SDIP42 [SA028]  
MTV212MV32@PLCC44 [SA244]  
MTV230GMF@TQFP44 [SA675-B4805]  
MTV230GMV@PLCC44 [SA244]  
MTV230MS@SDIP42 [SA028]  
MTV230PMF@TQFP44 [SA675-B4805]  
MTV230PMV@PLCC44 [SA244]



N25S32@S0IC8 [SA605B]  
N25S80  
N25S80@S0IC8[200mil] [SA605B]

N25S32@WSON8 [SA683]  
N25S80@S0IC8[150mil] [SA602A]  
N25S80@WSON8 [SA683]

## NATRONICS

### E (E) PROM/FRAM/NVRAM

NS29LV032FB@TSOP48 [SB247-B4806]      NS29LV032FT@TSOP48 [SB247-B4806]

## NEC

### E (E) PROM/FRAM/NVRAM

D2716D	uPD271000
uPD271000@PLCC32 [SA015A1T]	uPD271000@TSOP32 [SA410T-B4001]
uPD27128	uPD27128 (C)
uPD27128 (D)	uPD2716
uPD27256	uPD27256 (C)
uPD27256 (D)	uPD27256A
uPD27256A (C)	uPD27256A (D)
uPD2732	uPD2732A
uPD27512	uPD27512ACT
uPD27512AD	uPD2764
uPD2764C	uPD2764D
uPD27C1000	uPD27C1000@PLCC32 [SA015A1T]
uPD27C1000@TSOP32 [SA410T-B4001]	uPD27C1000A
uPD27C1000A@PLCC32 [SA015A1T]	
uPD27C1000A@TSOP32 [SA410T-B4001]	uPD27C1000AD@PLCC32 [SA015A1T]
uPD27C1000AD	
uPD27C1000AD@TSOP32 [SA410T-B4001]	uPD27C1001@PLCC32 [SA015A1T]
uPD27C1001	uPD27C1001A
uPD27C1001@TSOP32 [SA410T-B4001]	
uPD27C1001A@PLCC32 [SA015A1T]	
uPD27C1001A@TSOP32 [SA410T-B4001]	uPD27C1001D@PLCC32 [SA015A1T]
uPD27C1001D	
uPD27C1001D@TSOP32 [SA410T-B4001]	uPD27C1024A
uPD27C1024	uPD27C2001@PLCC32 [SA015A1T]
uPD27C2001	uPD27C2001D
uPD27C2001@TSOP32 [SA410T-B4001]	
uPD27C2001D@PLCC32 [SA015A1T]	
uPD27C2001D@TSOP32 [SA410T-B4001]	
uPD27C210	uPD27C256
uPD27C256A	uPD27C400
uPD27C4001	uPD27C4001@PLCC32 [SA015A1T]
uPD27C4001@TSOP32 [SA410T-B4001]	uPD27C4096
uPD27C512	uPD27C64 (C)
uPD27C64 (D)	uPD27C8000
uPD27C8001	uPD27C8001@PLCC32 [SA015A1T]
uPD27C8001@TSOP32 [SA410T-B4001]	uPD28C04
uPD28C04@S0IC24 [SA404]	uPD28C05
uPD28C05@S0IC24 [SA404]	uPD28C256

uPD28C64  
uPD29F008CB@TSOP40 [SA409T-B4002]  
uPD29F008CT@TSOP40 [SA409T-B4002]

uPD28C64@SOIC28 [SA404]

## MICROCONTROLLER

uPD78F9200 (A)@SSOP10 [SA026]  
uPD78F9200@SSOP10 [SA026]  
uPD78F9201 (A2)@SSOP10 [SA026]  
uPD78F9202 (A)@SSOP10 [SA026]  
uPD78F9202@SSOP10 [SA026]  
uPD78F9210 (A2)@SSOP16 [SA026]  
uPD78F9211 (A)@SSOP16 [SA026]  
uPD78F9211@SSOP16 [SA026]  
uPD78F9212 (A2)@SSOP16 [SA026]  
uPD78F9221 (A)@SSOP20 [SA689]  
uPD78F9221@SSOP20 [SA689]  
uPD78F9222 (A2)@SSOP20 [SA689]  
uPD78F9224 (A)@SSOP20 [SA689]  
uPD78F9224@SSOP20 [SA689]  
uPD78F9232 (A)@SSOP30 [SA689]  
uPD78F9232 (A2)@SSOP30 [SA689]  
uPD78F9232@SSOP30 [SA689]  
uPD78F9234 (A)@SSOP30 [SA689]  
uPD78F9234 (A2)@SSOP30 [SA689]  
uPD78F9234@SSOP30 [SA689]  
uPD78F9500 (A2)@SSOP10 [SA026]  
uPD78F9501 (A)@SSOP10 [SA026]  
uPD78F9501@SSOP10 [SA026]  
uPD78F9502 (A2)@SSOP10 [SA026]  
uPD78F9510 (A)@SSOP16 [SA026]  
uPD78F9510@SSOP16 [SA026]  
uPD78F9511 (A2)@SSOP16 [SA026]  
uPD78F9512 (A)@SSOP16 [SA026]  
uPD78F9512@SSOP16 [SA026]  
uPD78F9521 (A2)@SSOP20 [SA689]  
uPD78F9522 (A)@SSOP20 [SA689]  
uPD78F9522@SSOP20 [SA689]  
uPD78F9524 (A2)@SSOP20 [SA689]  
uPD78F9532 (A)@SDIP32 [SA653]  
uPD78F9532 (A2)@SDIP32 [SA653]  
uPD78F9532@SDIP32 [SA653]  
uPD78F9534 (A)@SDIP32 [SA653]  
uPD78F9534 (A2)@SDIP32 [SA653]  
uPD78F9534@SDIP32 [SA653]  
uPD79F8200 (A)@SSOP10 [SA026]  
uPD79F8200@SSOP10 [SA026]  
uPD79F8201 (A2)@SSOP10 [SA026]  
uPD79F8202 (A)@SSOP10 [SA026]  
uPD79F8202@SSOP10 [SA026]  
uPD79F8210 (A2)@SSOP16 [SA026]  
uPD79F8211 (A)@SSOP16 [SA026]

uPD78F9200 (A2)@SSOP10 [SA026]  
uPD78F9201 (A)@SSOP10 [SA026]  
uPD78F9201@SSOP10 [SA026]  
uPD78F9202 (A2)@SSOP10 [SA026]  
uPD78F9210 (A)@SSOP16 [SA026]  
uPD78F9210@SSOP16 [SA026]  
uPD78F9211 (A2)@SSOP16 [SA026]  
uPD78F9212 (A)@SSOP16 [SA026]  
uPD78F9212@SSOP16 [SA026]  
uPD78F9221 (A2)@SSOP20 [SA689]  
uPD78F9222 (A)@SSOP20 [SA689]  
uPD78F9222@SSOP20 [SA689]  
uPD78F9224 (A2)@SSOP20 [SA689]  
uPD78F9232 (A)@SDIP32 [SA653]  
uPD78F9232 (A2)@SDIP32 [SA653]  
uPD78F9232@SDIP32 [SA653]  
uPD78F9234 (A)@SDIP32 [SA653]  
uPD78F9234 (A2)@SDIP32 [SA653]  
uPD78F9234@SDIP32 [SA653]  
uPD78F9500 (A)@SSOP10 [SA026]  
uPD78F9500@SSOP10 [SA026]  
uPD78F9501 (A2)@SSOP10 [SA026]  
uPD78F9502 (A)@SSOP10 [SA026]  
uPD78F9502@SSOP10 [SA026]  
uPD78F9510 (A2)@SSOP16 [SA026]  
uPD78F9511 (A)@SSOP16 [SA026]  
uPD78F9511@SSOP16 [SA026]  
uPD78F9512 (A2)@SSOP16 [SA026]  
uPD78F9521 (A)@SSOP20 [SA689]  
uPD78F9521@SSOP20 [SA689]  
uPD78F9522 (A2)@SSOP20 [SA689]  
uPD78F9524 (A)@SSOP20 [SA689]  
uPD78F9524@SSOP20 [SA689]  
uPD78F9532 (A)@SSOP30 [SA689]  
uPD78F9532 (A2)@SSOP30 [SA689]  
uPD78F9532@SSOP30 [SA689]  
uPD78F9534 (A)@SSOP30 [SA689]  
uPD78F9534 (A2)@SSOP30 [SA689]  
uPD78F9534@SSOP30 [SA689]  
uPD79F8200 (A2)@SSOP10 [SA026]  
uPD79F8201 (A)@SSOP10 [SA026]  
uPD79F8201@SSOP10 [SA026]  
uPD79F8202 (A2)@SSOP10 [SA026]  
uPD79F8210 (A)@SSOP16 [SA026]  
uPD79F8210@SSOP16 [SA026]  
uPD79F8211 (A2)@SSOP16 [SA026]

uPD79F8211@SSOP16 [SA026]  
uPD79F8212(A2)@SSOP16 [SA026]  
uPD79F8221(A)@SSOP20 [SA689]  
uPD79F8221@SSOP20 [SA689]  
uPD79F8222(A2)@SSOP20 [SA689]  
uPD79F8224(A)@SSOP20 [SA689]  
uPD79F8224@SSOP20 [SA689]  
uPD79F8232(A)@SSOP30 [SA689]  
uPD79F8232(A2)@SSOP30 [SA689]  
uPD79F8232@SSOP30 [SA689]  
uPD79F8234(A)@SSOP30 [SA689]  
uPD79F8234(A2)@SSOP30 [SA689]  
uPD79F8234@SSOP30 [SA689]  
uPD79F8500(A2)@SSOP10 [SA026]  
uPD79F8501(A)@SSOP10 [SA026]  
uPD79F8501@SSOP10 [SA026]  
uPD79F8502(A2)@SSOP10 [SA026]  
uPD79F8510(A)@SSOP16 [SA026]  
uPD79F8510@SSOP16 [SA026]  
uPD79F8511(A2)@SSOP16 [SA026]  
uPD79F8512(A)@SSOP16 [SA026]  
uPD79F8512@SSOP16 [SA026]  
uPD79F8521(A2)@SSOP20 [SA689]  
uPD79F8522(A)@SSOP20 [SA689]  
uPD79F8522@SSOP20 [SA689]  
uPD79F8524(A2)@SSOP20 [SA689]  
uPD79F8532(A)@SDIP32 [SA653]  
uPD79F8532(A2)@SDIP32 [SA653]  
uPD79F8532@SDIP32 [SA653]  
uPD79F8534(A)@SDIP32 [SA653]  
uPD79F8534(A2)@SDIP32 [SA653]  
uPD79F8534@SDIP32 [SA653]

uPD79F8212(A)@SSOP16 [SA026]  
uPD79F8212@SSOP16 [SA026]  
uPD79F8221(A2)@SSOP20 [SA689]  
uPD79F8222(A)@SSOP20 [SA689]  
uPD79F8222@SSOP20 [SA689]  
uPD79F8224(A2)@SSOP20 [SA689]  
uPD79F8232(A)@SDIP32 [SA653]  
uPD79F8232(A2)@SDIP32 [SA653]  
uPD79F8232@SDIP32 [SA653]  
uPD79F8234(A)@SDIP32 [SA653]  
uPD79F8234(A2)@SDIP32 [SA653]  
uPD79F8234@SDIP32 [SA653]  
uPD79F8500(A)@SSOP10 [SA026]  
uPD79F8500@SSOP10 [SA026]  
uPD79F8501(A2)@SSOP10 [SA026]  
uPD79F8502(A)@SSOP10 [SA026]  
uPD79F8502@SSOP10 [SA026]  
uPD79F8510(A2)@SSOP16 [SA026]  
uPD79F8511(A)@SSOP16 [SA026]  
uPD79F8511@SSOP16 [SA026]  
uPD79F8512(A2)@SSOP16 [SA026]  
uPD79F8521(A)@SSOP20 [SA689]  
uPD79F8521@SSOP20 [SA689]  
uPD79F8522(A2)@SSOP20 [SA689]  
uPD79F8524(A)@SSOP20 [SA689]  
uPD79F8524@SSOP20 [SA689]  
uPD79F8532(A)@SSOP30 [SA689]  
uPD79F8532(A2)@SSOP30 [SA689]  
uPD79F8532@SSOP30 [SA689]  
uPD79F8534(A)@SSOP30 [SA689]  
uPD79F8534(A2)@SSOP30 [SA689]  
uPD79F8534@SSOP30 [SA689]

## NEXFLASH

### E (E) PROM/FRAM/NVRAM

NX25B40(Bottom Boot)@MLP8 [SA683]  
NX25B40(Bottom Boot)@SOIC8 [SA602A]  
NX25B40(Top Boot)@MLP8 [SA683]  
NX25P10@MLP8 [SA683]  
NX25P16@MLP8 [SA683]  
NX25P16@SOIC16 [SA783]  
NX25P16@SOIC8 [SA605B]  
NX25P20@MLP8 [SA683]  
NX25P32@MLP8 [SA605B]  
NX25P32@SOIC16 [SA783]  
NX25P40@MLP8 [SA683]  
NX25P64@MLP8 [SA683]  
NX25P64@SOIC16 [SA783]  
NX25P80@MLP8 [SA683]  
NX29F010

NX25B40(Top Boot)@SOIC8 [SA602A]  
NX25P10@SOIC8 [SA602A]  
NX25P16@MLP8 (ISP)  
NX25P16@SOIC16 (ISP)  
NX25P16@SOIC8 (ISP)  
NX25P20@SOIC8 [SA602A]  
NX25P32@MLP8 (ISP)  
NX25P32@SOIC16 (ISP)  
NX25P40@SOIC8 [SA602A]  
NX25P64@MLP8 (ISP)  
NX25P64@SOIC16 (ISP)  
NX25P80@SOIC8 [SA602A]  
NX29F010@PLCC32 [SA015A1T]

NX29F010@TSOP32 [SA410T-B4001]

## NJRC

### E (E) PROM/FRAM/NVRAM

NJU26040V

NJU26040V@SSOP32 [SA626A]

## NOVATEK

### MICROCONTROLLER

NT68F631@PLCC44 [SA244]

NT68F631ALG@PLCC44 [SA244]

NT68F631L@PLCC44 [SA244]

NT68F631U@SDIP42 [SA028]

NT68F632@PLCC44 [SA244]

NT68F632ALG@PLCC44 [SA244]

NT68F632L@PLCC44 [SA244]

NT68F632U@SDIP42 [SA028]

NT68F633@PLCC44 [SA244]

NT68F633L@PLCC44 [SA244]

NT68F633U@SDIP42 [SA028]

NT68F636@PLCC44 [SA244]

NT68F636L@PLCC44 [SA244]

NT68F636U@SDIP42 [SA028]

NT68F63L (0444)@PLCC44 [SA244]

NT68F63L (0448)@PLCC44 [SA244]

NT68F63L (0523)@PLCC44 [SA244]

NT68F63L@PLCC44 [SA244]

NT68F63LG@PLCC44 [SA244]

NT68F63U@SDIP42 [SA028]

NT68F63UG@SDIP42 [SA028]

NT68F631@SDIP42 [SA028]

NT68F631AUG@SDIP42 [SA028]

NT68F631LG@PLCC44 [SA244]

NT68F631UG@SDIP42 [SA028]

NT68F632@SDIP42 [SA028]

NT68F632AUG@SDIP42 [SA028]

NT68F632LG@PLCC44 [SA244]

NT68F632UG@SDIP42 [SA028]

NT68F633@SDIP42 [SA028]

NT68F633LG@PLCC44 [SA244]

NT68F633UG@SDIP42 [SA028]

NT68F636@SDIP42 [SA028]

NT68F636LG@PLCC44 [SA244]

NT68F636UG@SDIP42 [SA028]

NT68F63L (0444)@SDIP42 [SA028]

NT68F63L (0448)@SDIP42 [SA028]

NT68F63L (0523)@SDIP42 [SA028]

NT68F63LA@PLCC44 [SA244]

NT68F63LGG@PLCC44 [SA244]

NT68F63UA@SDIP42 [SA028]

NT68F63UGG@SDIP42 [SA028]

## NSC

### E (E) PROM/FRAM/NVRAM

2864

MM2716E

NM24C02@SOIC8 [SA602A]

NM24C02L

NM24C02L@TSOP8 [SA643]

NM24C03@SOIC8 [SA602A]

NM24C04

NM24C04@TSOP8 [SA643]

NM24C05@SOIC8 [SA602A]

NM24C08

NM24C09

NM24C16

NM24C17

MM2716

NM24C02

NM24C02@TSOP8 [SA643]

NM24C02L@SOIC8 [SA602A]

NM24C03

NM24C03@TSOP8 [SA643]

NM24C04@SOIC8 [SA602A]

NM24C05

NM24C05@TSOP8 [SA643]

NM24C08@SOIC8 [SA602A]

NM24C09@SOIC8 [SA602A]

NM24C16@SOIC8 [SA602A]

NM24C17@SOIC8 [SA602A]

NM27C010  
NM27C010@TSOP32 [SA410T-B4001]  
NM27C010Q@PLCC32 [SA015A1T]  
NM27C020  
NM27C020@TSOP32 [SA410T-B4001]  
NM27C020Q@PLCC32 [SA015A1T]  
NM27C040  
NM27C040@TSOP32 [SA410T-B4001]  
NM27C128  
NM27C210  
NM27C210Q  
NM27C240  
NM27C256  
NM27C400  
NM27C512@PLCC32 [SA015A1T]  
NM27C512Q@PLCC32 [SA015A1T]  
NM27C64Q@PLCC32 [SA015A1T]  
NM27CP256@PLCC32 [SA015A1T]  
NM27LC010@PLCC32 [SA015A1T]  
NM27LC256  
NM27LC512  
NM27LC64  
NM27LV010  
NM27LV010@TSOP32 [SA410T-B4001]  
NM27LV210@PLCC44 [SA244]  
NM27LV512@PLCC32 [SA015A1T]  
NM27P040  
NM27P040@TSOP32 [SA410T-B4001]  
NM27P210@PLCC44 [SA244]  
NM27P512@PLCC32 [SA015A1T]  
NM59C11@SOIC8 [SA602A]  
NM93C06 (08bit)@SOIC8 [SA602A]  
NM93C06 (16bit)@SOIC8 [SA602A]  
NM93C46@SOIC8 [SA602A]  
NM93C46A (08bit)@SOIC8 [SA602A]  
NM93C46A (16bit)@SOIC8 [SA602A]  
NM93C46AL (08bit)@SOIC8 [SA602A]  
NM93C46AL (16bit)@SOIC8 [SA602A]  
NM93C46ALZ (08bit)@SOIC8 [SA602A]  
NM93C46ALZ (16bit)@SOIC8 [SA602A]  
NM93C46L@SOIC8 [SA602A]  
NM93C46LZ@SOIC8 [SA602A]  
NM93C56@SOIC8 [SA602A]  
NM93C56A (08bit)@SOIC8 [SA602A]  
NM93C56A (16bit)@SOIC8 [SA602A]  
NM93C56AL (08bit)@SOIC8 [SA602A]  
NM93C56AL (16bit)@SOIC8 [SA602A]  
NM93C56ALZ (08bit)@SOIC8 [SA602A]  
NM93C56ALZ (16bit)@SOIC8 [SA602A]  
NM93C56L@SOIC8 [SA602A]  
NM93C56LZ@SOIC8 [SA602A]  
NM93C66@SOIC8 [SA602A]  
NM93C66A (08bit)  
NM27C010@PLCC32 [SA015A1T]  
NM27C010Q  
NM27C010Q@TSOP32 [SA410T-B4001]  
NM27C020@PLCC32 [SA015A1T]  
NM27C020Q  
NM27C020Q@TSOP32 [SA410T-B4001]  
NM27C040@PLCC32 [SA015A1T]  
NM27C1023  
NM27C128@PLCC32 [SA015A1T]  
NM27C210@PLCC44 [SA244]  
NM27C210Q@PLCC44 [SA244]  
NM27C240@PLCC44 [SA244]  
NM27C256@PLCC32 [SA015A1T]  
NM27C512  
NM27C512Q  
NM27C64Q  
NM27CP256  
NM27LC010  
NM27LC010@TSOP32 [SA410T-B4001]  
NM27LC256@PLCC32 [SA015A1T]  
NM27LC512@PLCC32 [SA015A1T]  
NM27LC64@PLCC32 [SA015A1T]  
NM27LV010@PLCC32 [SA015A1T]  
NM27LV210  
NM27LV512  
NM27LV512@TSOP32 [SA410T-B4001]  
NM27P040@PLCC32 [SA015A1T]  
NM27P210  
NM27P512  
NM59C11  
NM93C06 (08bit)  
NM93C06 (16bit)  
NM93C46  
NM93C46A (08bit)  
NM93C46A (16bit)  
NM93C46AL (08bit)  
NM93C46AL (16bit)  
NM93C46ALZ (08bit)  
NM93C46ALZ (16bit)  
NM93C46L  
NM93C46LZ  
NM93C56  
NM93C56A (08bit)  
NM93C56A (16bit)  
NM93C56AL (08bit)  
NM93C56AL (16bit)  
NM93C56ALZ (08bit)  
NM93C56ALZ (16bit)  
NM93C56L  
NM93C56LZ  
NM93C66  
NM93C66A  
NM93C66A (08bit)@SOIC8 [SA602A]

NM93C66A@SOIC8 [SA602A]  
NM93C66AL (08bit)@SOIC8 [SA602A]  
NM93C66AL (16bit)@SOIC8 [SA602A]  
NM93C66ALZ (08bit)@SOIC8 [SA602A]  
NM93C66ALZ (16bit)@SOIC8 [SA602A]  
NM93C66L@SOIC8 [SA602A]  
NM93C66LZ@SOIC8 [SA602A]  
NM93C86 (16bit)@SOIC8 [SA602A]  
NM93C86A (08bit)  
NM93C86A@SOIC8 [SA602A]  
NM93C86AL (08bit)@SOIC8 [SA602A]  
NM93C86AL (16bit)@SOIC8 [SA602A]  
NM93C86ALZ (08bit)@SOIC8 [SA602A]  
NM93C86ALZ (16bit)@SOIC8 [SA602A]  
NM93C86L@SOIC8 [SA602A]  
NM93C86LZ@SOIC8 [SA602A]  
NM93CS06 (MT8)@TSSOP8 [SA643]  
NM93CS46 (M8)@SOIC8 [SA602A]  
NM93CS46 (N)  
NM93CS56 (MT8)@TSSOP8 [SA643]  
NM93CS66 (M8)@SOIC8 [SA602A]  
NM93CS66 (N)  
NMC2732B  
NMC27C010  
NMC27C010@TSOP32 [SA410T-B4001]  
NMC27C1024@PLCC44 [SA244]  
NMC27C128B@PLCC32 [SA015A1T]  
NMC27C128BN@PLCC32 [SA015A1T]  
NMC27C128BQ@PLCC32 [SA015A1T]  
NMC27C128Q  
NMC27C16BQ  
NMC27C16H  
NMC27C16Q  
NMC27C210@PLCC44 [SA244]  
NMC27C210Q@PLCC44 [SA244]  
NMC27C256B@PLCC32 [SA015A1T]  
NMC27C256BQE  
NMC27C256Q  
NMC27C32  
NMC27C32BQ  
NMC27C32EH  
NMC27C512  
NMC27C512A  
NMC27C512AN  
NMC27C64  
NMC27C64BN  
NMC27CP128  
NMC27CP64  
NMC59C11@SOIC8 [SA602A]  
NMC87C257Q@PLCC32 [SA015A1T]  
NMC87C257V@PLCC32 [SA015A1T]  
NMC9306@SOIC8 [SA602A]  
NMC9307@SOIC8 [SA602A]  
NM93C66AL (08bit)  
NM93C66AL (16bit)  
NM93C66ALZ (08bit)  
NM93C66ALZ (16bit)  
NM93C66L  
NM93C66LZ  
NM93C86 (16bit)  
NM93C86A  
NM93C86A (08bit)@SOIC8 [SA602A]  
NM93C86AL (08bit)  
NM93C86AL (16bit)  
NM93C86ALZ (08bit)  
NM93C86ALZ (16bit)  
NM93C86L  
NM93C86LZ  
NM93CS06 (M8)@SOIC8 [SA602A]  
NM93CS06 (N)  
NM93CS46 (MT8)@TSSOP8 [SA643]  
NM93CS56 (M8)@SOIC8 [SA602A]  
NM93CS56 (N)  
NM93CS66 (MT8)@TSSOP8 [SA643]  
NMC2732  
NMC2732H  
NMC27C010@PLCC32 [SA015A1T]  
NMC27C1024  
NMC27C128B  
NMC27C128BN  
NMC27C128BQ  
NMC27C128CQ  
NMC27C16  
NMC27C16BQE  
NMC27C16HQ  
NMC27C210  
NMC27C210Q  
NMC27C256B  
NMC27C256BN  
NMC27C256BQM  
NMC27C256Q@PLCC32 [SA015A1T]  
NMC27C32B  
NMC27C32E  
NMC27C32H  
NMC27C512@PLCC32 [SA015A1T]  
NMC27C512A@PLCC32 [SA015A1T]  
NMC27C512AN@PLCC32 [SA015A1T]  
NMC27C64@PLCC32 [SA015A1T]  
NMC27C64N  
NMC27CP256  
NMC59C11  
NMC87C257Q  
NMC87C257V  
NMC9306  
NMC9307  
NMC9346

NMC9346@SOIC8 [SA602A]  
NMC93C56@SOIC14 [SA602]  
NMC93C66  
NMC93C86A  
NMC93C86A@SOIC8 [SA602A]  
NMC93CS06 (N)  
NMC93CS46 (N)  
NMC93CS56 (N)  
NMC93CS66 (N)  
NMC93S06 (N)  
NMC9817A  
NS9816A

NMC93C56  
NMC93C56@SOIC8 [SA602A]  
NMC93C66@SOIC14 [SA602]  
NMC93C86A@SOIC14 [SA602]  
NMC93CS06 (M14)@SOIC14 [SA602]  
NMC93CS46 (M14)@SOIC14 [SA602]  
NMC93CS56 (M14)@SOIC14 [SA602]  
NMC93CS66 (M14)@SOIC14 [SA602]  
NMC93S06 (M14)@SOIC14 [SA602]  
NMC9817  
NS2816A

## PLD

GAL16V8  
GAL16V8A

GAL16V8@PLCC20 [SA001A-B2001]  
GAL16V8A@PLCC20 [SA001A-B2001]

## NTE

### E (E) PROM/FRAM/NVRAM

NTE2532  
NTE25L32

NTE2532A

## NUMONYX

### E (E) PROM/FRAM/NVRAM

JR28F032M29EWB@TSOP48 [SB247-B4806]  
JR28F032M29EWH@TSOP48 [SB247-B4806]  
JR28F032M29EWL@TSOP48 [SB247-B4806]  
JR28F032M29EWT@TSOP48 [SB247-B4806]  
JR28F064M29EWB@TSOP48 [SB247-B4806]  
JR28F064M29EWH@TSOP48 [SB247-B4806]  
JR28F064M29EWL@TSOP48 [SB247-B4806]  
JR28F064M29EWT@TSOP48 [SB247-B4806]  
M25P10-A@SOIC8 [SA602A]  
M25P10-A@VFQFPN8 [SA683]  
M25P80@SOIC8(150 mil) [SA602A]  
M25P80@UFDFPN8 [SA724]  
M25PX16@SOIC16 [SA404]  
M25PX16@SOIC8(200 mil) [SA605B]  
M25PX32@SOIC16 [SA404]  
M25PX32@VFQFPN8 [SA683]  
M25PX64@VDFPN8 [SA684]  
M25PX80@SOIC8[150mil] [SA602A]  
M25PX80@VFQFPN8 [SA683]  
M28W320ECT@TSOP48 [SB247-B4806]  
M28W320FCT@TSOP48 [SB247-B4806]  
M28W640ECT@TSOP48 [SB247-B4806]

M25P10-A@UFDFPN8 [SA724]  
M25P80  
M25P80@SOIC8(200 mil) [SA605B]  
M25P80@VDFPN8 [SA683]  
M25PX16@SOIC8(150 mil) [SA602A]  
M25PX16@VFQFPN8 [SA683]  
M25PX32@SOIC8 [SA605B]  
M25PX64@SOIC16 [SA404]  
M25PX80  
M25PX80@SOIC8[200mil] [SA605B]  
M28W320ECB@TSOP48 [SB247-B4806]  
M28W320FCB@TSOP48 [SB247-B4806]  
M28W640ECB@TSOP48 [SB247-B4806]  
M28W640FCB@TSOP48 [SB247-B4806]

M28W640FCT@TSOP48 [SB247-B4806]	M28W640HCB@TSOP48 [SB247-B4806]
M28W640HCT@TSOP48 [SB247-B4806]	M29F160FB@TSOP48 [SA247-B4806]
M29F160FT@TSOP48 [SA247-B4806]	M29F200FB@PSOP44 [SA638]
M29F200FB@TSOP48 [SA247-B4806]	M29F200FT@PSOP44 [SA638]
M29F200FT@TSOP48 [SA247-B4806]	M29F400FB@PSOP44 [SA638]
M29F400FB@TSOP48 [SA247-B4806]	M29F400FT@PSOP44 [SA638]
M29F400FT@TSOP48 [SA247-B4806]	M29F800FB@PSOP44 [SA638]
M29F800FB@TSOP48 [SA247-B4806]	M29F800FT@PSOP44 [SA638]
M29F800FT@TSOP48 [SA247-B4806]	M29W064FB@TSOP48 [SB247-B4806]
M29W064FT@TSOP48 [SB247-B4806]	M29W160DB@PSOP44 [SA638]
M29W160DB@TSOP48 [SB247-B4806]	M29W160DT@PSOP44 [SA638]
M29W160DT@TSOP48 [SB247-B4806]	M29W160EB@PSOP44 [SA638]
M29W160EB@TSOP48 [SB247-B4806]	M29W160ET@PSOP44 [SA638]
M29W160ET@TSOP48 [SB247-B4806]	M29W160FB@TSOP48 [SB247-B4806]
M29W160FT@TSOP48 [SB247-B4806]	M29W320EB@TSOP48 [SB247-B4806]
M29W320ET@TSOP48 [SB247-B4806]	M29W400DB@PSOP44 [SA638]
M29W400DB@TSOP48 [SB247-B4806]	M29W400DT@PSOP44 [SA638]
M29W400DT@TSOP48 [SB247-B4806]	M29W400FB@TSOP48 [SB247-B4806]
M29W400FT@TSOP48 [SB247-B4806]	M29W640DB@TSOP48 [SB247-B4806]
M29W640DT@TSOP48 [SB247-B4806]	M29W641DH@TSOP48 [SB247-B4806]
M29W641DL@TSOP48 [SB247-B4806]	M29W800DB@PSOP44 [SA638]
M29W800DB@TSOP48 [SB247-B4806]	M29W800DT@PSOP44 [SA638]
M29W800DT@TSOP48 [SB247-B4806]	M29W800FB@TSOP48 [SB247-B4806]
M29W800FT@TSOP48 [SB247-B4806]	N25Q032@SOIC16 [SA404]
N25Q032@SOIC16(fast mode) [SA404]	
N25Q032@SOIC8(150mil) [SA602A]	
N25Q032@SOIC8(150mil)(fast mode) [SA602A]	
N25Q032@SOIC8(208mil) [SA605B]	
N25Q032@SOIC8(208mil)(fast mode) [SA605B]	
N25Q032@VDFPN8(6*5mm) [SA683]	
N25Q032@VDFPN8(6*5mm)(fast mode) [SA683]	
N25Q032@VDFPN8(8*6mm) [SA684]	
N25Q032@VDFPN8(8*6mm)(fast mode) [SA684]	
N25Q064@SOIC16 [SA404]	
N25Q064@SOIC16(fast mode) [SA404]	
N25Q064@SOIC8(150mil) [SA602A]	
N25Q064@SOIC8(150mil)(fast mode) [SA602A]	
N25Q064@SOIC8(208mil) [SA605B]	
N25Q064@SOIC8(208mil)(fast mode) [SA605B]	
N25Q064@VDFPN8(6*5mm) [SA683]	
N25Q064@VDFPN8(6*5mm)(fast mode) [SA683]	
N25Q064@VDFPN8(8*6mm) [SA684]	
N25Q064@VDFPN8(8*6mm)(fast mode) [SA684]	
N25Q064A@SOIC16 [SA404]	N25Q064A@SOIC8(150mil) [SA602A]
N25Q064A@SOIC8(208mil) [SA605B]	N25Q064A@VDFPN8(6*5mm) [SA683]
N25Q064A@VDFPN8(8*6mm) [SA684]	

## NUVOTON

### MICROCONTROLLER

M0516LAN@QFP48 [SA248-B4804]

M0516LBN@QFP48 [SA248-B4804]

M0516LDE@QFP48 [SA248-B4804]  
M0516ZAN@QFN32 [SA686]  
M0516ZDE@QF33 [SA686]  
M052LAN@QFP48 [SA248-B4804]  
M052LDE@QFP48 [SA248-B4804]  
M052ZAN@QFN32 [SA686]  
M052ZDE@QF33 [SA686]  
M054LAN@QFP48 [SA248-B4804]  
M054LDE@QFP48 [SA248-B4804]  
M054ZAN@QFN32 [SA686]  
M054ZDE@QF33 [SA686]  
M058LAN@QFP48 [SA248-B4804]  
M058LDE@QFP48 [SA248-B4804]  
M058SLAN@QFP48 [SA248-B4804]  
M058ZAN@QFN32 [SA686]  
M058ZDE@QF33 [SA686]  
MINI51FDE (ICP)@TSSOP20 [SA643]  
MINI51LAN@QFP48 [SA248-B4804]  
MINI51LDE (ICP)@QFP48 [SA248-B4804]  
MINI51LDE@QFP48 [SA248-B4804]  
MINI51TDE@QFN33 [\$\$\$\$\$]  
MINI51ZDE@QFN33 [SA686]  
MINI52LAN@QFN33 [SA686]  
MINI52LDE (ICP)@QFP48 [SA248-B4804]  
MINI52LDE@QFP48 [SA248-B4804]  
MINI52TDE@QFN33 [\$\$\$\$\$]  
MINI52ZDE@QFN33 [SA686]  
MINI54LAN@QFN33 [SA686]  
MINI54LDE (ICP)@QFP48 [SA248-B4804]  
MINI54LDE@QFP48 [SA248-B4804]  
MINI54TDE@QFN33 [\$\$\$\$\$]  
MINI54ZDE@QFN33 [SA686]  
MINI58LDE (ICP)@QFP48 [SA248-B4804]  
MINI58LDE@QFP48 [SA248-B4804]  
MINI58TDE@QFN33 [\$\$\$\$\$]  
MINI58ZDE@QFN33 [SA686]  
N76E885A@TSSOP20 [SA643]  
N78E055ADG  
N78E055ALG@TQFP48 [SA248-B4804]  
N78E059ADG  
N78E059ALG@TQFP48 [SA248-B4804]  
N78E366ADG  
N78E366ALG@LQFP48 [SA248-B4804]  
N78E517ADG  
N78E517ALG@LQFP48 [SA248-B4804]  
N79E234ALG@TQFP48 [SA248-B4804]  
N79E235ALG@TQFP48 [SA248-B4804]  
N79E342AKG  
N79E342RAKG  
N79E352AEG  
N79E352ALG@TQFP48 [SA248-B4804]  
N79E8132A@SSOP16  
N79E813A@SOIC20 [SA404]

M0516LDN@QFP48 [SA248-B4804]  
M0516ZBN@QFN32 [SA686]  
M0516ZDN@QF33 [SA686]  
M052LBN@QFP48 [SA248-B4804]  
M052LDN@QFP48 [SA248-B4804]  
M052ZBN@QFN32 [SA686]  
M052ZDN@QF33 [SA686]  
M054LBN@QFP48 [SA248-B4804]  
M054LDN@QFP48 [SA248-B4804]  
M054ZBN@QFN32 [SA686]  
M054ZDN@QF33 [SA686]  
M058LBN@QFP48 [SA248-B4804]  
M058LDN@QFP48 [SA248-B4804]  
M058SZAN@QF33 [SA686]  
M058ZBN@QFN32 [SA686]  
M058ZDN@QF33 [SA686]  
MINI51LAN@QFN33 [SA686]  
MINI51TDE (ICP)@QFN33 [\$\$\$\$\$]  
MINI51ZDE (ICP)@QFN33 [SA686]  
MINI52FDE (ICP)@TSSOP20 [SA643]  
MINI52LAN@QFP48 [SA248-B4804]  
MINI52TDE (ICP)@QFN33 [\$\$\$\$\$]  
MINI52ZDE (ICP)@QFN33 [SA686]  
MINI54FDE (ICP)@TSSOP20 [SA643]  
MINI54LAN@QFP48 [SA248-B4804]  
MINI54TDE (ICP)@QFN33 [\$\$\$\$\$]  
MINI54ZDE (ICP)@QFN33 [SA686]  
MINI58FDE (ICP)@TSSOP20 [SA643]  
MINI58TDE (ICP)@QFN33 [\$\$\$\$\$]  
MINI58ZDE (ICP)@QFN33 [SA686]  
N76E616A@LQFP48 [SA248-B4804]  
N76E885A@TSSOP28 [SA643]  
N78E055AFG@TQFP44 [SA675-B4805]  
N78E055APG@PLCC44 [SA244]  
N78E059AFG@TQFP44 [SA675-B4805]  
N78E059APG@PLCC44 [SA244]  
N78E366AFG@PQFP44 [SA675-B4805]  
N78E366APG@PLCC44 [SA244]  
N78E517AFG@PQFP44 [SA675-B4805]  
N78E517APG@PLCC44 [SA244]  
N79E234RALG@TQFP48 [SA248-B4804]  
N79E235RALG@TQFP48 [SA248-B4804]  
N79E342ASG@SOP16 [SA404]  
N79E342RASG@SOP16 [SA404]  
N79E352AFG@TQFP44 [SA675-B4805]  
N79E352APG@PLCC44 [SA244]  
N79E813A  
N79E813A@SOIC28 [SA404]

N79E813A@TSSOP20 [SA643]  
N79E814A  
N79E814A (ICP)@SOIC20 [SA404]  
N79E814A (ICP)@TSSOP20 [SA026]  
N79E814A@SOIC20 [SA404]  
N79E814A@TSSOP20 [SA643]  
N79E815A  
N79E815A (ICP)@SOIC20 [SA404]  
N79E815A (ICP)@TSSOP20 [SA026]  
N79E815A@SOIC20 [SA404]  
N79E815A@TSSOP20 [SA643]  
N79E8213AKG  
N79E8213RAKG  
N79E822A  
N79E823A  
N79E824A  
N79E825A  
N79E8432A@SSOP16  
N79E843A@SOIC20 [SA404]  
N79E844A  
N79E844A@TSSOP20 [SA643]  
N79E845A@SOIC20 [SA404]  
N79E853A@SOIC28 [SA404]  
N79E854A@SOIC28 [SA404]  
N79E855A@SOIC28 [SA404]  
N79E875ALG@TQFP48 [SA248-B4804]  
NUC029LAN@LQFP48 [SA248-B4804]  
W77E058A  
W77E058A@TQFP44 [SA675-B4805]  
W77E516@PLCC44 [SA244]  
W77E532  
W77E532@TQFP44 [SA675-B4805]  
W77E532A@PLCC44 [SA244]  
W77E58  
W77E58@TQFP44 [SA675-B4805]  
W77IE58@PLCC44 [SA244]  
W77L058A  
W77L058A@TQFP44 [SA675-B4805]  
W77L516A@PLCC44 [SA244]  
W77L532A  
W77L532A@TQFP44 [SA675-B4805]  
W77LE516@PLCC44 [SA244]  
W77LE532  
W77LE532@TQFP44 [SA675-B4805]  
W77LE58@PLCC44 [SA244]  
W77LE58A  
W77LE58A@TQFP44 [SA675-B4805]  
W78E051B@PLCC44 [SA244]  
W78E051C  
W78E051C@TQFP44 [SA675-B4805]  
W78E051DFG@PQFP44 [SA675-B4805]  
W78E051DPG@PLCC44 [SA244]  
W78E052B@PLCC44 [SA244]

N79E813A@TSSOP28 [SA643]  
N79E814A (ICP)  
N79E814A (ICP)@SOIC28 [SA404]  
N79E814A (ICP)@TSSOP28 [SA643]  
N79E814A@SOIC28 [SA404]  
N79E814A@TSSOP28 [SA643]  
N79E815A (ICP)  
N79E815A (ICP)@SOIC28 [SA404]  
N79E815A (ICP)@TSSOP28 [SA643]  
N79E815A@SOIC28 [SA404]  
N79E815A@TSSOP28 [SA643]  
N79E8213ASG@SOP20 [SA404]  
N79E8213RASG@SOP20 [SA404]  
N79E822A@SOP20 [SA404]  
N79E823A@SOP20 [SA404]  
N79E824A@SOP20 [SA404]  
N79E825A@SOP20 [SA404]  
N79E843A  
N79E843A@TSSOP20 [SA643]  
N79E844A@SOIC20 [SA404]  
N79E845A  
N79E845A@TSSOP20 [SA643]  
N79E853A@TSSOP28 [SA026]  
N79E854A@TSSOP28 [SA026]  
N79E855A@TSSOP28 [SA026]  
N79E875RALG@TQFP48 [SA248-B4804]  
NUC029TAN@QFN33 [SA248-B4804]  
W77E058A@PLCC44 [SA244]  
W77E516  
W77E516@TQFP44 [SA675-B4805]  
W77E532@PLCC44 [SA244]  
W77E532A  
W77E532A@TQFP44 [SA675-B4805]  
W77E58@PLCC44 [SA244]  
W77IE58  
W77IE58@TQFP44 [SA675-B4805]  
W77L058A@PLCC44 [SA244]  
W77L516A  
W77L516A@TQFP44 [SA675-B4805]  
W77L532A@PLCC44 [SA244]  
W77LE516  
W77LE516@TQFP44 [SA675-B4805]  
W77LE532@PLCC44 [SA244]  
W77LE58  
W77LE58@TQFP44 [SA675-B4805]  
W77LE58A@PLCC44 [SA244]  
W78E051B  
W78E051B@TQFP44 [SA675-B4805]  
W78E051C@PLCC44 [SA244]  
W78E051DDG  
W78E051DLG@LQFP48 [SA248-B4804]  
W78E052B  
W78E052B@TQFP44 [SA675-B4805]

W78E052C  
W78E052C@TQFP44 [SA675-B4805]  
W78E052DFG@PQFP44 [SA675-B4805]  
W78E052DPG@PLCC44 [SA244]  
W78E054B@PLCC44 [SA244]  
W78E054C  
W78E054C@TQFP44 [SA675-B4805]  
W78E054DFG@PQFP44 [SA675-B4805]  
W78E054DPG@PLCC44 [SA244]  
W78E058B@PLCC44 [SA244]  
W78E058DDG  
W78E058DLG@TQFP48 [SA248-B4804]  
W78E065  
W78E065@TQFP44 [SA675-B4805]  
W78E365@PLCC44 [SA244]  
W78E365A  
W78E365A@TQFP44 [SA675-B4805]  
W78E378  
W78E378P@PLCC44 [SA244]  
W78E51@PLCC44 [SA244]  
W78E516  
W78E516@TQFP44 [SA675-B4805]  
W78E516B@PLCC44 [SA244]  
W78E516DDG  
W78E516DLG@TQFP48 [SA248-B4804]  
W78E51B  
W78E51B@PQFP44 [SA675-B4805]  
W78E51C  
W78E51C@TQFP44 [SA675-B4805]  
W78E52@PLCC44 [SA244]  
W78E52B  
W78E52B@TQFP44 [SA675-B4805]  
W78E52C@PLCC44 [SA244]  
W78E54  
W78E54@PQFP44 [SA675-B4805]  
W78E54B  
W78E54B@TQFP44 [SA675-B4805]  
W78E54C@PLCC44 [SA244]  
W78E58  
W78E58@PQFP44 [SA675-B4805]  
W78E58B  
W78E58B@TQFP44 [SA675-B4805]  
W78E62B@PLCC44 [SA244]  
W78E65  
W78E65@TQFP44 [SA675-B4805]  
W78E858@PLCC44 [SA244]  
W78ERD2  
W78ERD2@TQFP44 [SA675-B4805]  
W78I051DFG@PQFP44 [SA675-B4805]  
W78I051DPG@PLCC44 [SA244]  
W78I052@PLCC44 [SA244]  
W78I052DFG@PQFP44 [SA675-B4805]  
W78I052DPG@PLCC44 [SA244]

W78E052C@PLCC44 [SA244]  
W78E052DDG  
W78E052DLG@LQFP48 [SA248-B4804]  
W78E054B  
W78E054B@TQFP44 [SA675-B4805]  
W78E054C@PLCC44 [SA244]  
W78E054DDG  
W78E054DLG@LQFP48 [SA248-B4804]  
W78E058B  
W78E058B@TQFP44 [SA675-B4805]  
W78E058DFG@TQFP44 [SA675-B4805]  
W78E058DPG@PLCC44 [SA244]  
W78E065@PLCC44 [SA244]  
W78E365  
W78E365@TQFP44 [SA675-B4805]  
W78E365A@PLCC44 [SA244]  
W78E374B  
W78E378E  
W78E51  
W78E51@TQFP44 [SA675-B4805]  
W78E516@PLCC44 [SA244]  
W78E516B  
W78E516B@TQFP44 [SA675-B4805]  
W78E516DFG@TQFP44 [SA675-B4805]  
W78E516DPG@PLCC44 [SA244]  
W78E51B@PLCC44 [SA244]  
W78E51B@TQFP44 [SA245A-B4805]  
W78E51C@PLCC44 [SA244]  
W78E52  
W78E52@TQFP44 [SA675-B4805]  
W78E52B@PLCC44 [SA244]  
W78E52C  
W78E52C@TQFP44 [SA675-B4805]  
W78E54@PLCC44 [SA244]  
W78E54@TQFP44 [SA245A-B4805]  
W78E54B@PLCC44 [SA244]  
W78E54C  
W78E54C@TQFP44 [SA675-B4805]  
W78E58@PLCC44 [SA244]  
W78E58@TQFP44 [SA245A-B4805]  
W78E58B@PLCC44 [SA244]  
W78E62B  
W78E62B@TQFP44 [SA675-B4805]  
W78E65@PLCC44 [SA244]  
W78E858  
W78E858@TQFP44 [SA675-B4805]  
W78ERD2@PLCC44 [SA244]  
W78I051DDG  
W78I051DLG@LQFP48 [SA248-B4804]  
W78I052  
W78I052DDG  
W78I052DLG@LQFP48 [SA248-B4804]  
W78I054

W78I054@PLCC44 [SA244]  
W78I054DFG@PQFP44 [SA675-B4805]  
W78I054DPG@PLCC44 [SA244]  
W78IE52@PLCC44 [SA244]  
W78IE54@PLCC44 [SA244]  
W78IRD2@PLCC44 [SA244]  
W78L051A  
W78L051A@TQFP44 [SA675-B4805]  
W78L051C@PLCC44 [SA244]  
W78L052A  
W78L052A@TQFP44 [SA675-B4805]  
W78L052C@PLCC44 [SA244]  
W78L054A  
W78L054A@TQFP44 [SA675-B4805]  
W78L054C@PLCC44 [SA244]  
W78L058A  
W78L058A@TQFP44 [SA675-B4805]  
W78L365@PLCC44 [SA244]  
W78L365@TQFP48 [SA248-B4804]  
W78L365A@PLCC44 [SA244]  
W78L365A@TQFP48 [SA248-B4804]  
W78L516@PLCC44 [SA244]  
W78L516A  
W78L516A@TQFP44 [SA675-B4805]  
W78L812A@PLCC44 [SA244]  
W78LE365  
W78LE365@TQFP44 [SA675-B4805]  
W78LE51  
W78LE51@TQFP44 [SA675-B4805]  
W78LE516@PLCC44 [SA244]  
W78LE51C  
W78LE51C@TQFP44 [SA675-B4805]  
W78LE52@PLCC44 [SA244]  
W78LE52C  
W78LE52C@TQFP44 [SA675-B4805]  
W78LE54@PLCC44 [SA244]  
W78LE54C  
W78LE54C@TQFP44 [SA675-B4805]  
W78LE58@PLCC44 [SA244]  
W78LE812  
W78LE812@TQFP44 [SA675-B4805]  
W79E201@TQFP44 [SA675-B4805]  
W79E2051 (dip16)  
W79E2051@SOIC14 [SA404]  
W79E2051@SOIC20 [SA404]  
W79E2051R@SOIC20 [SA404]  
W79E225APG@PLCC44 [SA244]  
W79E226APG@PLCC44 [SA244]  
W79E227APG@PLCC44 [SA244]  
W79E4051 (dip16)  
W79E4051@SOIC14 [SA404]  
W79E4051@SOIC20 [SA404]  
W79E4051R@SOIC20 [SA404]  
W78I054DDG  
W78I054DLG@LQFP48 [SA248-B4804]  
W78IE52  
W78IE54  
W78IRD2  
W78IRD2@TQFP44 [SA675-B4805]  
W78L051A@PLCC44 [SA244]  
W78L051C  
W78L051C@TQFP44 [SA675-B4805]  
W78L052A@PLCC44 [SA244]  
W78L052C  
W78L052C@TQFP44 [SA675-B4805]  
W78L054A@PLCC44 [SA244]  
W78L054C  
W78L054C@TQFP44 [SA675-B4805]  
W78L058A@PLCC44 [SA244]  
W78L365  
W78L365@TQFP44 [SA675-B4805]  
W78L365A  
W78L365A@TQFP44 [SA675-B4805]  
W78L516  
W78L516@TQFP44 [SA675-B4805]  
W78L516A@PLCC44 [SA244]  
W78L812A  
W78L812A@TQFP44 [SA675-B4805]  
W78LE365@PLCC44 [SA244]  
W78LE365@TQFP48 [SA248-B4804]  
W78LE51@PLCC44 [SA244]  
W78LE516  
W78LE516@TQFP44 [SA675-B4805]  
W78LE51C@PLCC44 [SA244]  
W78LE52  
W78LE52@TQFP44 [SA675-B4805]  
W78LE52C@PLCC44 [SA244]  
W78LE54  
W78LE54@TQFP44 [SA675-B4805]  
W78LE54C@PLCC44 [SA244]  
W78LE58  
W78LE58@TQFP44 [SA675-B4805]  
W78LE812@PLCC44 [SA244]  
W79E201@PLCC44 [SA244]  
W79E2051 (dip14)  
W79E2051 (dip20)  
W79E2051@SOIC16 [SA404]  
W79E2051R (dip20)  
W79E225ALG@TQFP48 [SA248-B4804]  
W79E226ALG@TQFP48 [SA248-B4804]  
W79E227ALG@TQFP48 [SA248-B4804]  
W79E4051 (dip14)  
W79E4051 (dip20)  
W79E4051@SOIC16 [SA404]  
W79E4051R (dip20)  
W79E532

W79E532@PLCC44 [SA244]  
W79E532A  
W79E532A@TQFP44 [SA675-B4805]  
W79E632  
W79E632@TQFP44 [SA675-B4805]  
W79E632A@PLCC44 [SA244]  
W79E633A@PLCC44 [SA244]  
W79E801A@SOIC20 [SA404]  
W79E802A@SOIC20 [SA404]  
W79E803A@SOIC20 [SA404]  
W79E804A@SOIC20 [SA404]  
W79E821A@SOIC20 [SA404]  
W79E822A@SOIC20 [SA404]  
W79E822B@SOIC20 [SA404]  
W79E823A@SOIC20 [SA404]  
W79E823B@SOIC20 [SA404]  
W79E824A@SOIC20 [SA404]  
W79E825A@SOIC20 [SA404]  
W79E831A@SOIC28 [SA404]  
W79E832A@SOIC28 [SA404]  
W79E833A@SOIC28 [SA404]  
W79E834A@SOIC28 [SA404]  
W79L532@PLCC44 [SA244]  
W79L632  
W79L632@TQFP44 [SA675-B4805]  
W79L632A@PLCC44 [SA244]  
W79L633A@PLCC44 [SA244]

W79E532@TQFP44 [SA675-B4805]  
W79E532A@PLCC44 [SA244]  
W79E533A@PLCC44 [SA244]  
W79E632@PLCC44 [SA244]  
W79E632A  
W79E632A@TQFP44 [SA675-B4805]  
W79E801A  
W79E802A  
W79E803A  
W79E804A  
W79E821A  
W79E822A  
W79E822B  
W79E823A  
W79E823B  
W79E824A  
W79E825A  
W79E831A  
W79E832A  
W79E833A  
W79E834A  
W79L532  
W79L532@TQFP44 [SA675-B4805]  
W79L632@PLCC44 [SA244]  
W79L632A  
W79L632A@TQFP44 [SA675-B4805]  
W99100DG@TQFP48 [SA248-B4804]

## NXP

### MICROCONTROLLER

LPC1111/101@LQFP48 [SA248-B4804]  
LPC1111/101@QFP44 [SA245A-B4805]  
LPC1111/102@QFN33 [SA701]  
LPC1111/103@LQFP48 [SA248-B4804]  
LPC1111/103@QFP44 [SA245A-B4805]  
LPC1111/201@QFN33 [SA701]  
LPC1111/202@LQFP48 [SA248-B4804]  
LPC1111/202@QFP44 [SA245A-B4805]  
LPC1111/203@QFN33 [SA701]  
LPC1111@LQFP48 [SA248-B4804]  
LPC1111@QFP44 [SA245A-B4805]  
LPC1112/101@QFN33 [SA701]  
LPC1112/102@LQFP48 [SA248-B4804]  
LPC1112/102@QFP44 [SA245A-B4805]  
LPC1112/103@QFN33 [SA701]  
LPC1112/201@LQFP48 [SA248-B4804]  
LPC1112/201@QFP44 [SA245A-B4805]  
LPC1112/202@QFN33 [SA701]  
LPC1112/203@LQFP48 [SA248-B4804]  
LPC1112/203@QFP44 [SA245A-B4805]

LPC1111/101@QFN33 [SA701]  
LPC1111/102@LQFP48 [SA248-B4804]  
LPC1111/102@QFP44 [SA245A-B4805]  
LPC1111/103@QFN33 [SA701]  
LPC1111/201@LQFP48 [SA248-B4804]  
LPC1111/201@QFP44 [SA245A-B4805]  
LPC1111/202@QFN33 [SA701]  
LPC1111/203@LQFP48 [SA248-B4804]  
LPC1111/203@QFP44 [SA245A-B4805]  
LPC1111@QFN33 [SA701]  
LPC1112/101@LQFP48 [SA248-B4804]  
LPC1112/101@QFP44 [SA245A-B4805]  
LPC1112/102@QFN33 [SA701]  
LPC1112/103@LQFP48 [SA248-B4804]  
LPC1112/103@QFP44 [SA245A-B4805]  
LPC1112/201@QFN33 [SA701]  
LPC1112/202@LQFP48 [SA248-B4804]  
LPC1112/202@QFP44 [SA245A-B4805]  
LPC1112/203@QFN33 [SA701]  
LPC1112@LQFP48 [SA248-B4804]

LPC1112@QFN33 [SA701]  
LPC1113/101@LQFP48 [SA248-B4804]  
LPC1113/101@QFP44 [SA245A-B4805]  
LPC1113/102@QFN33 [SA701]  
LPC1113/103@LQFP48 [SA248-B4804]  
LPC1113/103@QFP44 [SA245A-B4805]  
LPC1113/201@QFN33 [SA701]  
LPC1113/202@LQFP48 [SA248-B4804]  
LPC1113/202@QFP44 [SA245A-B4805]  
LPC1113/203@QFN33 [SA701]  
LPC1113@LQFP48 [SA248-B4804]  
LPC1113@QFP44 [SA245A-B4805]  
LPC1114/101@QFN33 [SA701]  
LPC1114/102@LQFP48 [SA248-B4804]  
LPC1114/102@QFP44 [SA245A-B4805]  
LPC1114/103@QFN33 [SA701]  
LPC1114/201@LQFP48 [SA248-B4804]  
LPC1114/201@QFP44 [SA245A-B4805]  
LPC1114/202@QFN33 [SA701]  
LPC1114/203@LQFP48 [SA248-B4804]  
LPC1114/203@QFP44 [SA245A-B4805]  
LPC1114@QFN33 [SA701]  
LPC11C12/101@LQFP48 [SA248-B4804]  
LPC11C12/102@LQFP48 [SA248-B4804]  
LPC11C12/103@LQFP48 [SA248-B4804]  
LPC11C12/201@LQFP48 [SA248-B4804]  
LPC11C12/202@LQFP48 [SA248-B4804]  
LPC11C12/203@LQFP48 [SA248-B4804]  
LPC11C12/301@LQFP48 [SA248-B4804]  
LPC11C12@LQFP48 [SA248-B4804]  
LPC11C14/101@LQFP48 [SA248-B4804]  
LPC11C14/102@LQFP48 [SA248-B4804]  
LPC11C14/103@LQFP48 [SA248-B4804]  
LPC11C14/201@LQFP48 [SA248-B4804]  
LPC11C14/202@LQFP48 [SA248-B4804]  
LPC11C14/203@LQFP48 [SA248-B4804]  
LPC11C14/301@LQFP48 [SA248-B4804]  
LPC11C14@LQFP48 [SA248-B4804]  
LPC11C22/101@LQFP48 [SA248-B4804]  
LPC11C22/102@LQFP48 [SA248-B4804]  
LPC11C22/103@LQFP48 [SA248-B4804]  
LPC11C22/201@LQFP48 [SA248-B4804]  
LPC11C22/202@LQFP48 [SA248-B4804]  
LPC11C22/203@LQFP48 [SA248-B4804]  
LPC11C22/301@LQFP48 [SA248-B4804]  
LPC11C22@LQFP48 [SA248-B4804]  
LPC11C24/101@LQFP48 [SA248-B4804]  
LPC11C24/102@LQFP48 [SA248-B4804]  
LPC11C24/103@LQFP48 [SA248-B4804]  
LPC11C24/201@LQFP48 [SA248-B4804]  
LPC11C24/202@LQFP48 [SA248-B4804]  
LPC11C24/203@LQFP48 [SA248-B4804]  
LPC11C24/301@LQFP48 [SA248-B4804]  
LPC1112@QFP44 [SA245A-B4805]  
LPC1113/101@QFN33 [SA701]  
LPC1113/102@LQFP48 [SA248-B4804]  
LPC1113/102@QFP44 [SA245A-B4805]  
LPC1113/103@QFN33 [SA701]  
LPC1113/201@LQFP48 [SA248-B4804]  
LPC1113/201@QFP44 [SA245A-B4805]  
LPC1113/202@QFN33 [SA701]  
LPC1113/203@LQFP48 [SA248-B4804]  
LPC1113/203@QFP44 [SA245A-B4805]  
LPC1113@QFN33 [SA701]  
LPC1114/101@LQFP48 [SA248-B4804]  
LPC1114/101@QFP44 [SA245A-B4805]  
LPC1114/102@QFN33 [SA701]  
LPC1114/103@LQFP48 [SA248-B4804]  
LPC1114/103@QFP44 [SA245A-B4805]  
LPC1114/201@QFN33 [SA701]  
LPC1114/202@LQFP48 [SA248-B4804]  
LPC1114/202@QFP44 [SA245A-B4805]  
LPC1114/203@QFN33 [SA701]  
LPC1114@LQFP48 [SA248-B4804]  
LPC1114@QFP44 [SA245A-B4805]

LPC11C24@LQFP48 [SA248-B4804]  
OM4371FN@PLCC44 [SA244]  
P83C660X2@PLCC44 [SA244]  
P83C661X2@PLCC44 [SA244]  
P87C51  
P87C51@TQFP44 [SA675-B4805]  
P87C51FA@PLCC44 [SA244]  
P87C51FB  
P87C51FB@TQFP44 [SA675-B4805]  
P87C51FC@PLCC44 [SA244]  
P87C51MA2@PLCC44 [SA244]  
P87C51MC2@PLCC44 [SA244]  
P87C51RA+@PLCC44 [SA244]  
P87C51RA2  
P87C51RA2@TQFP44 [SA675-B4805]  
P87C51RB+@PLCC44 [SA244]  
P87C51RB2  
P87C51RB2@TQFP44 [SA675-B4805]  
P87C51RC+@PLCC44 [SA244]  
P87C51RC2  
P87C51RC2@TQFP44 [SA675-B4805]  
P87C51RD+@PLCC44 [SA244]  
P87C51RD2  
P87C51RD2@TQFP44 [SA245A-B4805]  
P87C51SB@PLCC44 [SA244]  
P87C51SF  
P87C51SF@TQFP44 [SA675-B4805]  
P87C51UB@PLCC44 [SA244]  
P87C51UF  
P87C51UF@TQFP44 [SA675-B4805]  
P87C51X2@PLCC44 [SA244]  
P87C51X2@TTSOP38 [SA693]  
P87C52@PLCC44 [SA244]  
P87C524  
P87C524@TQFP44 [SA245A-B4805]  
P87C528@PLCC44 [SA244]  
P87C52SB  
P87C52SB@TQFP44 [SA675-B4805]  
P87C52SF@PLCC44 [SA244]  
P87C52UB  
P87C52UB@TQFP44 [SA675-B4805]  
P87C52UF@PLCC44 [SA244]  
P87C52X2  
P87C52X2@TQFP44 [SA245A-B4805]  
P87C54  
P87C54@TQFP44 [SA675-B4805]  
P87C54SB@PLCC44 [SA244]  
P87C54SF  
P87C54SF@TQFP44 [SA675-B4805]  
P87C54UB@PLCC44 [SA244]  
P87C54UF  
P87C54UF@TQFP44 [SA675-B4805]  
P87C54X2@PLCC44 [SA244]

OM4371FN  
OM4371FN@TQFP44 [SA245A-B4805]  
P83C660X2@TQFP44 [SA245A-B4805]  
P83C661X2@TQFP44 [SA245A-B4805]  
P87C51@PLCC44 [SA244]  
P87C51FA  
P87C51FA@TQFP44 [SA675-B4805]  
P87C51FB@PLCC44 [SA244]  
P87C51FC  
P87C51FC@TQFP44 [SA245A-B4805]  
P87C51MB2@PLCC44 [SA244]  
P87C51RA+  
P87C51RA+@TQFP44 [SA245A-B4805]  
P87C51RA2@PLCC44 [SA244]  
P87C51RB+  
P87C51RB+@TQFP44 [SA245A-B4805]  
P87C51RB2@PLCC44 [SA244]  
P87C51RC+  
P87C51RC+@TQFP44 [SA245A-B4805]  
P87C51RC2@PLCC44 [SA244]  
P87C51RD+  
P87C51RD+@TQFP44 [SA245A-B4805]  
P87C51RD2@PLCC44 [SA244]  
P87C51SB  
P87C51SB@TQFP44 [SA675-B4805]  
P87C51SF@PLCC44 [SA244]  
P87C51UB  
P87C51UB@TQFP44 [SA675-B4805]  
P87C51UF@PLCC44 [SA244]  
P87C51X2  
P87C51X2@TQFP44 [SA245A-B4805]  
P87C52  
P87C52@TQFP44 [SA675-B4805]  
P87C524@PLCC44 [SA244]  
P87C528  
P87C528@TQFP44 [SA245A-B4805]  
P87C52SB@PLCC44 [SA244]  
P87C52SF  
P87C52SF@TQFP44 [SA675-B4805]  
P87C52UB@PLCC44 [SA244]  
P87C52UF  
P87C52UF@TQFP44 [SA675-B4805]  
P87C52X2@PLCC44 [SA244]  
P87C52X2@TTSOP38 [SA693]  
P87C54@PLCC44 [SA244]  
P87C54SB  
P87C54SB@TQFP44 [SA675-B4805]  
P87C54SF@PLCC44 [SA244]  
P87C54UB  
P87C54UB@TQFP44 [SA675-B4805]  
P87C54UF@PLCC44 [SA244]  
P87C54X2  
P87C54X2@TQFP44 [SA245A-B4805]

P87C54X2@TTSOP38 [SA693]  
P87C550@PLCC44 [SA244]  
P87C575@PLCC44 [SA244]  
P87C576  
P87C576@TQFP44 [SA675-B4805]  
P87C58@PLCC44 [SA244]  
P87C58SB  
P87C58SB@TQFP44 [SA675-B4805]  
P87C58UB@PLCC44 [SA244]  
P87C58X2  
P87C58X2@TQFP44 [SA245A-B4805]  
P87C591@PLCC44 [SA244]  
P87C652  
P87C652@TQFP44 [SA675-B4805]  
P87C654@PLCC44 [SA244]  
P87C660X2@PLCC44 [SA244]  
P87C661X2@PLCC44 [SA244]  
P87CL52X2  
P87CL52X2@TQFP44 [SA245A-B4805]  
P87CL54X2  
P87CL54X2@TQFP44 [SA245A-B4805]  
P87L51FA  
P87L51FA@TQFP44 [SA675-B4805]  
P87L51FB@PLCC44 [SA244]  
P87LPC759  
P87LPC760  
P87LPC760@TSSOP14 [SA026]  
P87LPC761  
P87LPC762  
P87LPC762@PLCC44 [SA605B]  
P87LPC762@S0IC20 [SA404]  
P87LPC764  
P87LPC764@PLCC44 [SA605B]  
P87LPC764@S0IC20 [SA404]  
P87LPC764@TSSOP20 [SA643]  
P87LPC767  
P87LPC767@PLCC44 [SA605B]  
P87LPC767@S0IC20 [SA404]  
P87LPC768  
P87LPC768@S0IC20 [SA404]  
P87LPC769  
P87LPC769@PLCC44 [SA605B]  
P87LPC769@S0IC20 [SA404]  
P87LPC778  
P87LPC778@TSSOP20 [SA026]  
P87LPC779  
P87LPC779@TSSOP20 [SA026]  
P89C138  
P89C138@TQFP44 [SA245A-B4805]  
P89C238@PLCC44 [SA244]  
P89C51B  
P89C51B@TQFP44 [SA245A-B4805]  
P89C51RA+@PLCC44 [SA244]

P87C550  
P87C575  
P87C575@TQFP44 [SA675-B4805]  
P87C576@PLCC44 [SA244]  
P87C58  
P87C58@TQFP44 [SA675-B4805]  
P87C58SB@PLCC44 [SA244]  
P87C58UB  
P87C58UB@TQFP44 [SA675-B4805]  
P87C58X2@PLCC44 [SA244]  
P87C58X2@TTSOP38 [SA693]  
P87C591@TQFP44 [SA675-B4805]  
P87C652@PLCC44 [SA244]  
P87C654  
P87C654@TQFP44 [SA675-B4805]  
P87C660X2@TQFP44 [SA245A-B4805]  
P87C661X2@TQFP44 [SA245A-B4805]  
P87CL52X2@PLCC44 [SA244]  
P87CL52X2@TTSOP38 [SA693]  
P87CL54X2@PLCC44 [SA244]  
P87CL54X2@TTSOP38 [SA693]  
P87L51FA@PLCC44 [SA244]  
P87L51FB  
P87L51FB@TQFP44 [SA675-B4805]  
P87LPC759 (ISP)  
P87LPC760 (ISP)  
P87LPC760@TSSOP14 (ISP)  
P87LPC761 (ISP)  
P87LPC762 (ISP)  
P87LPC762@PLCC44 (ISP)  
P87LPC762@S0IC20 (ISP)  
P87LPC764 (ISP)  
P87LPC764@PLCC44 (ISP)  
P87LPC764@S0IC20 (ISP)  
P87LPC764@TSSOP20 (ISP)  
P87LPC767 (ISP)  
P87LPC767@PLCC44 (ISP)  
P87LPC767@S0IC20 (ISP)  
P87LPC768 (ISP)  
P87LPC768@S0IC20 (ISP)  
P87LPC769 (ISP)  
P87LPC769@PLCC44 (ISP)  
P87LPC769@S0IC20 (ISP)  
P87LPC778 (ISP)  
P87LPC778@TSSOP20 (ISP)  
P87LPC779 (ISP)  
P87LPC779@TSSOP20 (ISP)  
P89C138@PLCC44 [SA244]  
P89C238  
P89C238@TQFP44 [SA245A-B4805]  
P89C51B@PLCC44 [SA244]  
P89C51RA+  
P89C51RA+@TQFP44 [SA245A-B4805]

P89C51RA2B  
P89C51RA2B@TQFP44 [SA245A-B4805]  
P89C51RB+@PLCC44 [SA244]  
P89C51RB2B  
P89C51RB2B@TQFP44 [SA245A-B4805]  
P89C51RB2H@PLCC44 [SA244]  
P89C51RC+  
P89C51RC+@TQFP44 [SA245A-B4805]  
P89C51RC2B@PLCC44 [SA244]  
P89C51RC2H  
P89C51RC2H@TQFP44 [SA675-B4805]  
P89C51RD+@PLCC44 [SA244]  
P89C51RD2B  
P89C51RD2B@TQFP44 [SA245A-B4805]  
P89C51RD2H@PLCC44 [SA244]  
P89C51UB  
P89C51UB@TQFP44 [SA245A-B4805]  
P89C51UF@PLCC44 [SA244]  
P89C51X2  
P89C51X2@TQFP44 [SA245A-B4805]  
P89C51X2B@PLCC44 [SA244]  
P89C51X2F  
P89C51X2F@TQFP44 [SA245A-B4805]  
P89C52@PLCC44 [SA244]  
P89C52B  
P89C52B@TQFP44 [SA245A-B4805]  
P89C52UB@PLCC44 [SA244]  
P89C52UF  
P89C52UF@TQFP44 [SA245A-B4805]  
P89C52X2@PLCC44 [SA244]  
P89C52X2B  
P89C52X2B@TQFP44 [SA245A-B4805]  
P89C52X2F@PLCC44 [SA244]  
P89C536@PLCC44 [SA244]  
P89C54  
P89C54@TQFP44 [SA245A-B4805]  
P89C54B@PLCC44 [SA244]  
P89C54UB  
P89C54UB@TQFP44 [SA245A-B4805]  
P89C54UF@PLCC44 [SA244]  
P89C54X2  
P89C54X2@TQFP44 [SA245A-B4805]  
P89C54X2B@PLCC44 [SA244]  
P89C54X2F  
P89C54X2F@TQFP44 [SA245A-B4805]  
P89C58@PLCC44 [SA244]  
P89C58B  
P89C58B@TQFP44 [SA245A-B4805]  
P89C58UB@PLCC44 [SA244]  
P89C58UF  
P89C58UF@TQFP44 [SA245A-B4805]  
P89C58X2@PLCC44 [SA244]  
P89C58X2B

P89C51RA2B@PLCC44 [SA244]  
P89C51RB+  
P89C51RB+@TQFP44 [SA245A-B4805]  
P89C51RB2B@PLCC44 [SA244]  
P89C51RB2H  
P89C51RB2H@TQFP44 [SA675-B4805]  
P89C51RC+@PLCC44 [SA244]  
P89C51RC2B  
P89C51RC2B@TQFP44 [SA245A-B4805]  
P89C51RC2H@PLCC44 [SA244]  
P89C51RD+  
P89C51RD+@TQFP44 [SA245A-B4805]  
P89C51RD2B@PLCC44 [SA244]  
P89C51RD2H  
P89C51RD2H@TQFP44 [SA675-B4805]  
P89C51UB@PLCC44 [SA244]  
P89C51UF  
P89C51UF@TQFP44 [SA245A-B4805]  
P89C51X2@PLCC44 [SA244]  
P89C51X2B  
P89C51X2B@TQFP44 [SA245A-B4805]  
P89C51X2F@PLCC44 [SA244]  
P89C52  
P89C52@TQFP44 [SA245A-B4805]  
P89C52B@PLCC44 [SA244]  
P89C52UB  
P89C52UB@TQFP44 [SA245A-B4805]  
P89C52UF@PLCC44 [SA244]  
P89C52X2  
P89C52X2@TQFP44 [SA245A-B4805]  
P89C52X2B@PLCC44 [SA244]  
P89C52X2F  
P89C52X2F@TQFP44 [SA245A-B4805]  
P89C538@PLCC44 [SA244]  
P89C54@PLCC44 [SA244]  
P89C54B  
P89C54B@TQFP44 [SA245A-B4805]  
P89C54UB@PLCC44 [SA244]  
P89C54UF  
P89C54UF@TQFP44 [SA245A-B4805]  
P89C54X2@PLCC44 [SA244]  
P89C54X2B  
P89C54X2B@TQFP44 [SA245A-B4805]  
P89C54X2F@PLCC44 [SA244]  
P89C58  
P89C58@TQFP44 [SA245A-B4805]  
P89C58B@PLCC44 [SA244]  
P89C58UB  
P89C58UB@TQFP44 [SA245A-B4805]  
P89C58UF@PLCC44 [SA244]  
P89C58X2  
P89C58X2@TQFP44 [SA245A-B4805]  
P89C58X2B@PLCC44 [SA244]

P89C58X2B@TQFP44 [SA245A-B4805]  
P89C58X2F@PLCC44 [SA244]  
P89C60X2  
P89C60X2@TQFP44 [SA245A-B4805]  
P89C61X2@PLCC44 [SA244]  
P89C660  
P89C660@TQFP44 [SA675-B4805]  
P89C662@PLCC44 [SA244]  
P89C664  
P89C664@TQFP44 [SA675-B4805]  
P89C668@PLCC44 [SA244]  
P89C669  
P89C669@PLCC44 [SA244]  
P89C669X2@LQFP44 [SA245A-B4805]  
P89C738  
P89C738@TQFP44 [SA245A-B4805]  
P89C838@PLCC44 [SA244]  
P89CV51RB2@PLCC44 [SA244]  
P89CV51RC2@PLCC44 [SA244]  
P89CV51RD2@PLCC44 [SA244]  
P89LPC901 (FD) [SA602A]  
P89LPC901 (FN)  
P89LPC902 (FD) [SA602A]  
P89LPC902 (FN)  
P89LPC903 (FD) [SA602A]  
P89LPC904 (FD) [SA602A]  
P89LPC904 (FN)  
P89LPC906 (FD) [SA602A]  
P89LPC907 (FD) [SA602A]  
P89LPC908 (FD) [SA602A]  
P89LPC9102 (FTK)@HVSON10 [SA695A]  
P89LPC9107 (FDH)@TSSOP14 [SA643]  
P89LPC912 (FDH)@TSSOP14 [SA026]  
P89LPC913 (FDH)@TSSOP14 [SA026]  
P89LPC914 (FDH)@TSSOP14 [SA026]  
P89LPC915 (FDH)@TSSOP14 [SA026]  
P89LPC916 (FDH)@TSSOP16 [SA026]  
P89LPC917 (FDH)@TSSOP16 [SA026]  
P89LPC920 (FDH)@TSSOP20 [SA026]  
P89LPC920 (FN)  
P89LPC9201 (FDH)@TSSOP20 [SA026]  
P89LPC9201 (FN)  
P89LPC920A1 (FDH)@TSSOP20 [SA026]  
P89LPC920A1 (FN)  
P89LPC921 (FDH)@TSSOP20 [SA026]  
P89LPC921 (FN)  
P89LPC9211 (FDH)@TSSOP20 [SA026]  
P89LPC9211 (FN)  
P89LPC921A1 (FDH)@TSSOP20 [SA026]  
P89LPC921A1 (FN)  
P89LPC922 (FDH)@TSSOP20 [SA026]  
P89LPC922 (FN)  
P89LPC9221 (FDH)@TSSOP20 [SA026]

P89C58X2F  
P89C58X2F@TQFP44 [SA245A-B4805]  
P89C60X2@PLCC44 [SA244]  
P89C61X2  
P89C61X2@TQFP44 [SA245A-B4805]  
P89C660@PLCC44 [SA244]  
P89C662  
P89C662@TQFP44 [SA675-B4805]  
P89C664@PLCC44 [SA244]  
P89C668  
P89C668@TQFP44 [SA675-B4805]  
P89C669@LQFP44 [SA245A-B4805]  
P89C669X2  
P89C669X2@PLCC44 [SA244]  
P89C738@PLCC44 [SA244]  
P89C838  
P89C838@TQFP44 [SA245A-B4805]  
P89CV51RB2@TQFP44 [SA245A-B4805]  
P89CV51RC2@TQFP44 [SA245A-B4805]  
P89CV51RD2@TQFP44 [SA245A-B4805]  
P89LPC901 (FD) (ISP)  
P89LPC901 (FN) (ISP)  
P89LPC902 (FD) (ISP)  
P89LPC902 (FN) (ISP)  
P89LPC903 (FD) (ISP)  
P89LPC904 (FD) (ISP)  
P89LPC904 (FN) (ISP)  
P89LPC906 (FD) (ISP)  
P89LPC907 (FD) (ISP)  
P89LPC908 (FD) (ISP)  
P89LPC9103 (FTK)@HVSON10 [SA695A]  
P89LPC9107 (FN) [SA636]  
P89LPC912 (FDH)@TSSOP14 (ISP)  
P89LPC913 (FDH)@TSSOP14 (ISP)  
P89LPC914 (FDH)@TSSOP14 (ISP)  
P89LPC915 (FDH)@TSSOP14 (ISP)  
P89LPC916 (FDH)@TSSOP16 (ISP)  
P89LPC917 (FDH)@TSSOP16 (ISP)  
P89LPC920 (FDH)@TSSOP20 (ISP)  
P89LPC920 (FN) (ISP)  
P89LPC9201 (FDH)@TSSOP20 (ISP)  
P89LPC9201 (FN) (ISP)  
P89LPC920A1 (FDH)@TSSOP20 (ISP)  
P89LPC920A1 (FN) (ISP)  
P89LPC921 (FDH)@TSSOP20 (ISP)  
P89LPC921 (FN) (ISP)  
P89LPC9211 (FDH)@TSSOP20 (ISP)  
P89LPC9211 (FN) (ISP)  
P89LPC921A1 (FDH)@TSSOP20 (ISP)  
P89LPC921A1 (FN) (ISP)  
P89LPC922 (FDH)@TSSOP20 (ISP)  
P89LPC922 (FN) (ISP)  
P89LPC9221 (FDH)@TSSOP20 (ISP)

P89LPC9221 (FN)  
P89LPC9221A1 (FDH)@TSSOP20 [SA026]  
P89LPC9221A1 (FDH)@TSSOP20 (ISP)  
P89LPC9221A1 (FN) (ISP)  
P89LPC922A1 (FDH)@TSSOP20 (ISP)  
P89LPC922A1 (FN) (ISP)  
P89LPC924 (FDH)@TSSOP20 (ISP)  
P89LPC924 (FN) (ISP)  
P89LPC9241 (FDH)@TSSOP20 (ISP)  
P89LPC9241 (FN) (ISP)  
P89LPC924A1 (FDH)@TSSOP20 (ISP)  
P89LPC924A1 (FN) (ISP)  
P89LPC925 (FDH)@TSSOP20 (ISP)  
P89LPC925 (FN) (ISP)  
P89LPC9251 (FDH)@TSSOP20 (ISP)  
P89LPC9251 (FN) (ISP)  
P89LPC925A1 (FDH)@TSSOP20 (ISP)  
P89LPC925A1 (FN) (ISP)  
P89LPC930 (BA)@PLCC28 (ISP)  
P89LPC930 (BDH)@TSSOP28 (ISP)  
P89LPC9301 (BDH)@TSSOP28 [SA643]  
P89LPC9301FDH [SA643]  
P89LPC930FDH [SA643]  
P89LPC931 (BA)@PLCC28 (ISP)  
P89LPC931 (BDH)@TSSOP28 (ISP)  
P89LPC9311 (BDH)@TSSOP28 [SA643]  
P89LPC9311FDH [SA643]  
P89LPC931FDH [SA643]  
P89LPC932 (BDH)@TSSOP28 [SA643]  
P89LPC93201BA@PLCC28 [SA008A]  
P89LPC93201FA@PLCC28 [SA008A]  
P89LPC93201FHN@QFN28 [SA685]  
P89LPC9321BDH@TSSOP28 [SA643]  
P89LPC9321FDH@TSSOP28 [SA643]  
P89LPC932A1 (BA)@PLCC28 [SA008A]  
P89LPC932A1 (BDH)@TSSOP28 [SA643]  
P89LPC932A1 (FA)@PLCC28 [SA008A]  
P89LPC932A1 (FDH)@TSSOP28 (ISP)  
P89LPC932A1 (FHN)@HVQFN28 (ISP)  
P89LPC933 (BDH)@TSSOP28 (ISP)  
P89LPC933 (FDH)@TSSOP28 (ISP)  
P89LPC9331 (BDH)@TSSOP28 [SA643]  
P89LPC9331 (HDH)@TSSOP28 [SA643]  
P89LPC934 (BDH)@TSSOP28 (ISP)  
P89LPC934 (FDH)@TSSOP28 (ISP)  
P89LPC93401V  
P89LPC9341 (FDH)@TSSOP28 [SA643]  
P89LPC935 (BA)@PLCC28 [SA008A]  
P89LPC935 (BDH)@TSSOP28 [SA643]  
P89LPC935 (FA)@PLCC28 [SA008A]  
P89LPC935 (FDH)@TSSOP28 [SA643]  
P89LPC935 (FHN)@HVQFN28 [SA685]  
P89LPC93501BA@PLCC28 [SA008A]

P89LPC9221 (FN) (ISP)  
P89LPC9221A1 (FN)  
P89LPC922A1 (FDH)@TSSOP20 [SA026]  
P89LPC922A1 (FN)  
P89LPC924 (FDH)@TSSOP20 [SA026]  
P89LPC924 (FN)  
P89LPC9241 (FDH)@TSSOP20 [SA026]  
P89LPC9241 (FN)  
P89LPC924A1 (FDH)@TSSOP20 [SA026]  
P89LPC924A1 (FN)  
P89LPC925 (FDH)@TSSOP20 [SA026]  
P89LPC925 (FN)  
P89LPC9251 (FDH)@TSSOP20 [SA026]  
P89LPC9251 (FN)  
P89LPC925A1 (FDH)@TSSOP20 [SA026]  
P89LPC925A1 (FN)  
P89LPC930 (BA)@PLCC28 [SA008A]  
P89LPC930 (BDH)@TSSOP28 [SA643]  
P89LPC9301 (BA)@PLCC28 [SA008A]  
P89LPC9301FA [SA008A]  
P89LPC930FA [SA008A]  
P89LPC931 (BA)@PLCC28 [SA008A]  
P89LPC931 (BDH)@TSSOP28 [SA643]  
P89LPC9311 (BA)@PLCC28 [SA008A]  
P89LPC9311FA [SA008A]  
P89LPC931FA [SA008A]  
P89LPC932 (BA)@PLCC28 [SA008A]  
P89LPC932 (FA)@PLCC28 [SA008A]  
P89LPC93201BDH@TSSOP28 [SA643]  
P89LPC93201FDH@TSSOP28 [SA643]  
P89LPC9321BA@PLCC28 [SA008A]  
P89LPC9321FA@PLCC28 [SA008A]  
P89LPC9321FHN@QFN28 [SA685]  
P89LPC932A1 (BA)@PLCC28 (ISP)  
P89LPC932A1 (BDH)@TSSOP28 (ISP)  
P89LPC932A1 (FDH)@TSSOP28 [SA643]  
P89LPC932A1 (FHN)@HVQFN28 [SA685]  
P89LPC933 (BDH)@TSSOP28 [SA643]  
P89LPC933 (FDH)@TSSOP28 [SA643]  
P89LPC933 (HDH)@TSSOP28 [SA643]  
P89LPC9331 (FDH)@TSSOP28 [SA643]  
P89LPC934 (BDH)@TSSOP28 [SA643]  
P89LPC934 (FDH)@TSSOP28 [SA643]  
P89LPC93401 (FDH)@TSSOP28 [SA643]  
P89LPC9341 (BDH)@TSSOP28 [SA643]  
P89LPC9341V  
P89LPC935 (BA)@PLCC28 (ISP)  
P89LPC935 (BDH)@TSSOP28 (ISP)  
P89LPC935 (FA)@PLCC28 (ISP)  
P89LPC935 (FDH)@TSSOP28 (ISP)  
P89LPC935 (FHN)@HVQFN28 (ISP)  
P89LPC93501BDH@TSSOP28 [SA643]

P89LPC93501FA@PLCC28 [SA008A]	P89LPC93501FDH@TSSOP28 [SA643]
P89LPC93501FHN@QFN28 [SA685]	P89LPC9351BA@PLCC28 [SA008A]
P89LPC9351BDH@TSSOP28 [SA643]	P89LPC9351FA@PLCC28 [SA008A]
P89LPC9351FDH@TSSOP28 [SA643]	P89LPC9351FHN@QFN28 [SA685]
P89LPC936 (FA) @PLCC28 [SA008A]	P89LPC936 (FDH) @TSSOP28 [SA643]
P89LPC9361 (FA) @PLCC28 [SA008A]	P89LPC9361 (FDH) @TSSOP28 [SA643]
P89LPC938 (FA) @PLCC28 [SA008A]	P89LPC938 (FA) @PLCC28 (ISP)
P89LPC938 (FDH) @TSSOP28 [SA643]	P89LPC938 (FDH) @TSSOP28 (ISP)
P89LPC938 (FHN) @HVQFN28 [SA685]	P89LPC938 (FHN) @HVQFN28 (ISP)
P89LPC93801BA@PLCC28 [SA008A]	P89LPC93801BDH@TSSOP28 [SA643]
P89LPC93801FA@PLCC28 [SA008A]	P89LPC93801FDH@TSSOP28 [SA643]
P89LPC93801FHN@QFN28 [SA685]	P89LPC9381BA@PLCC28 [SA008A]
P89LPC9381BDH@TSSOP28 [SA643]	P89LPC9381FA@PLCC28 [SA008A]
P89LPC9381FDH@TSSOP28 [SA643]	P89LPC9381FHN@QFN28 [SA685]
P89LPC9401 (FBD) @LQFP64 (ISP)	P89LPC9408 (FBD) @LQFP64 (ISP)
P89LPC952@LQFP44 [SA245A-B4805]	P89LPC952@LQFP44 (ISP)
P89LPC952@LQFP48 [SA248-B4804]	P89LPC952@LQFP48 (ISP)
P89LPC952@PLCC44 [SA244]	P89LPC952@PLCC44 (ISP)
P89LPC954@LQFP44 [SA245A-B4805]	P89LPC954@LQFP44 (ISP)
P89LPC954@LQFP48 [SA248-B4804]	P89LPC954@LQFP48 (ISP)
P89LPC954@PLCC44 [SA244]	P89LPC954@PLCC44 (ISP)
P89LPC970FDH@TSSOP20 [SA026]	
P89LPC970FDH@TSSOP20 (serial) [SA026]	P89LPC970FN (serial)
P89LPC970FN	
P89LPC971FDH@TSSOP20 [SA026]	
P89LPC971FDH@TSSOP20 (serial) [SA026]	P89LPC971FN (serial)
P89LPC971FN	
P89LPC972FDH@TSSOP20 [SA026]	
P89LPC972FDH@TSSOP20 (serial) [SA026]	P89LPC972FN (serial)
P89LPC972FN	
P89LPC980FDH@TSSOP28 [SA643]	
P89LPC980FDH@TSSOP28 (serial) [SA643]	
P89LPC982FDH@TSSOP28 [SA643]	
P89LPC982FDH@TSSOP28 (serial) [SA643]	
P89LPC983FA@PLCC28 [SA008A]	
P89LPC983FA@PLCC28 (serial) [SA008A]	
P89LPC983FDH@TSSOP28 [SA643]	
P89LPC983FDH@TSSOP28 (serial) [SA643]	
P89LPC985FA@PLCC28 [SA008A]	
P89LPC985FA@PLCC28 (serial) [SA008A]	
P89LPC985FDH@TSSOP28 [SA643]	
P89LPC985FDH@TSSOP28 (serial) [SA643]	
P89LV51RB2	P89LV51RB2@PLCC44 [SA244]
P89LV51RB2@TQFP44 [SA245A-B4805]	P89LV51RB2FA@PLCC44 [SA244]
P89LV51RB2FBC@TQFP44 [SA245A-B4805]	
P89LV51RB2FN	P89LV51RC2
P89LV51RC2@PLCC44 [SA244]	P89LV51RC2@TQFP44 [SA245A-B4805]
P89LV51RC2FA@PLCC44 [SA244]	
P89LV51RC2FBC@TQFP44 [SA245A-B4805]	
P89LV51RC2FN	P89LV51RD2
P89LV51RD2 (new)	P89LV51RD2 (new) @PLCC44 [SA244]
P89LV51RD2 (new) @TQFP44 [SA245A-B4805]	
P89LV51RD2@PLCC44 [SA244]	P89LV51RD2@TQFP44 [SA245A-B4805]

P89LV51RD2BA (new)@PLCC44 [SA244]	P89LV51RD2BA@PLCC44 [SA244]
P89LV51RD2BBC (new)@TQFP44 [SA245A-B4805]	
P89LV51RD2BBC@TQFP44 [SA245A-B4805]	
P89LV51RD2BN	P89LV51RD2BN (new)
P89LV51RD2FA (new)@PLCC44 [SA244]	P89LV51RD2FA@PLCC44 [SA244]
P89LV51RD2FBC (new)@TQFP44 [SA245A-B4805]	
P89LV51RD2FBC@TQFP44 [SA245A-B4805]	
P89LV51RD2FN	P89LV51RD2FN (new)
P89V51RB2	P89V51RB2@PLCC44 [SA244]
P89V51RB2@TQFP44 [SA245A-B4805]	P89V51RB2FA@PLCC44 [SA244]
P89V51RB2FBC@TQFP44 [SA245A-B4805]	
P89V51RB2FN	P89V51RC2
P89V51RC2@PLCC44 [SA244]	P89V51RC2@TQFP44 [SA245A-B4805]
P89V51RC2FA@PLCC44 [SA244]	
P89V51RC2FBC@TQFP44 [SA245A-B4805]	
P89V51RC2FN	P89V51RD2
P89V51RD2 (new)	P89V51RD2 (new)@PLCC44 [SA244]
P89V51RD2 (new)@TQFP44 [SA245A-B4805]	
P89V51RD2@PLCC44 [SA244]	P89V51RD2@TQFP44 [SA245A-B4805]
P89V51RD2BA (new)@PLCC44 [SA244]	P89V51RD2BA@PLCC44 [SA244]
P89V51RD2BBC (new)@TQFP44 [SA245A-B4805]	
P89V51RD2BBC@TQFP44 [SA245A-B4805]	
P89V51RD2BN	P89V51RD2BN (new)
P89V51RD2FA (new)@PLCC44 [SA244]	P89V51RD2FA@PLCC44 [SA244]
P89V51RD2FBC (new)@TQFP44 [SA245A-B4805]	
P89V51RD2FBC@TQFP44 [SA245A-B4805]	
P89V51RD2FN	P89V51RD2FN (new)
P89V52X2	P89V52X2 (ISP)
P89V52X2@PLCC44 [SA244]	P89V52X2@PLCC44 (ISP)
P89V52X2@TQFP44 [SA245A-B4805]	P89V52X2@TQFP44 (ISP)
P89V54X2	P89V54X2 (ISP)
P89V54X2@PLCC44 [SA244]	P89V54X2@PLCC44 (ISP)
P89V54X2@TQFP44 [SA245A-B4805]	P89V54X2@TQFP44 (ISP)
P89V660@PLCC44 [SA244]	P89V660@TQFP44 [SA245A-B4805]
P89V662@PLCC44 [SA244]	P89V662@TQFP44 [SA245A-B4805]
P89V664@PLCC44 [SA244]	P89V664@TQFP44 [SA245A-B4805]
PCF7953AC1500@TSSOP28 [SA643]	PXAC37@PLCC44 [SA244]
PXAC37@TQFP44 [SA245A-B4805]	PXAG17@PLCC44 [SA244]
PXAG17@TQFP44 [SA245A-B4805]	PXAG27@PLCC44 [SA244]
PXAG27@TQFP44 [SA245A-B4805]	PXAG37@PLCC44 [SA244]
PXAG37@TQFP44 [SA245A-B4805]	PXAG39@PLCC44 [SA244]
PXAG39@TQFP44 [SA245A-B4805]	PXAG39K@PLCC44 [SA244]
PXAG39K@TQFP44 [SA245A-B4805]	PXAG49@PLCC44 [SA244]
PXAG49@TQFP44 [SA245A-B4805]	PXAG49K@PLCC44 [SA244]
PXAG49K@TQFP44 [SA245A-B4805]	

OKI

**E (E) PROM/FRAM/NVRAM**

MR27V1652E@PSOP44 [SA638]	MR27V401D
MR27V401D@PSOP32 [SA638]	MR27V401D@TSOP32 [SA620-B4807]

MR27V401E	MR27V401E@PSOP32 [SA638]
MR27V401E@TSOP32 [SA620-B4807]	MR27V402D
MR27V402D@PSOP40 [SA682]	MR27V402D@TSOP44 [SA638]
MR27V402E	MR27V402E@PSOP40 [SA682]
MR27V402E@TSOP44 [SA638]	MR27V802F@PSOP44 [SA638]
MR27V802F@TSOP44 [\$\$\$\$\$]	MR27V802F@TSOP48 [SB247-B4806]
MSM16812(08bit)	MSM16812(08bit)@SOIC8 [SA602A]
MSM271000	MSM271000@PLCC32 [SA015A1T]
MSM271000@TSOP32 [SA410T-B4001]	MSM271000AS
MSM271000AS@PLCC32 [SA015A1T]	
MSM271000AS@TSOP32 [SA410T-B4001]	
MSM27128	MSM27128A
MSM27128AS	MSM27128AZB-RS
MSM2716	MSM27256
MSM27256AS	MSM27256ZB-RS
MSM2732	MSM2732A
MSM27512	MSM27512AS
MSM27512ZB-RS	MSM2764
MSM2764A	MSM2764AS
MSM2764AZB-RS	MSM2764RS
MSM27C1024	MSM27C1024AS
MSM27C128	MSM27C128AZB-RS
MSM27C256	MSM27C256A
MSM27C256H	MSM27C256HZB
MSM27C256ZB	MSM27C64AS
MSM27C802CZ	MSM27C802CZ@PSOP44 [SA638]
MSM27C802CZ@TSOP44 [\$\$\$\$\$]	MSM2816A (RS)
MSM28C16A	

## DRAM & SRAM

MSM51256	MSM51256@SOIC28 [SA630]
MSM51257AL	MSM51257AL@SOIC28 [SA630]
MSM51257ALL	MSM51257ALL@SOIC28 [SA630]
MSM5165AL	MSM5165AL@SOIC28 [SA630]

## ON

### E (E) PROM/FRAM/NVRAM

CAT24C512	CAT24C512@MSOP8 [SA666]
CAT24C512@SOIC8[150 mil] [SA602A]	
CAT24C512@SOIC8[200 mil] [SA605B]	
CAT24C512@TSSOP8 [SA643]	CTA24C512@UDFN8 [SA684]

## ON Semiconductor

### E (E) PROM/FRAM/NVRAM

CAT13001(08bit)@SOIC8 [SA602A]	CAT13001(16bit)@SOIC8 [SA602A]
CAT13004(08bit)@SOIC8 [SA602A]	CAT13004(16bit)@SOIC8 [SA602A]

CAT13008(08bit)@SOIC8 [SA602A]	CAT13008(16bit)@SOIC8 [SA602A]
CAT13016(08bit)@SOIC8 [SA602A]	CAT13016(16bit)@SOIC8 [SA602A]
CAT1320	CAT1320@SOIC8 [SA602A]
CAT1320@TDFN8	CAT1320@TSSOP8 [SA643]
CAT1321	CAT1321@SOIC8 [SA602A]
CAT1321@TDFN8	CAT1321@TSSOP8 [SA643]
CAT14002@SOIC8 [SA602A]	CAT14004@SOIC8 [SA602A]
CAT14008@SOIC8 [SA602A]	CAT14016@SOIC8 [SA602A]
CAT15002@SOIC8 [SA602A]	CAT15004@SOIC8 [SA602A]
CAT15008@SOIC8 [SA602A]	CAT15016@SOIC8 [SA602A]
CAT1640	CAT1640@SOIC8 [SA602A]
CAT1640@TDFN8	CAT1640@TSSOP8 [SA643]
CAT1641	CAT1641@SOIC8 [SA602A]
CAT1641@TDFN8	CAT1641@TSSOP8 [SA643]
CAT24AA01@SOIC8 [SA602A]	CAT24AA01@TSOT-23 [SA717]
CAT24AA02@SOIC8 [SA602A]	CAT24AA02@TSOT-23 [SA717]
CAT24AA04@SOIC8 [SA602A]	CAT24AA04@TSOT-23 [SA717]
CAT24AA08@SOIC8 [SA602A]	CAT24AA08@TSOT-23 [SA717]
CAT24AA16@SOIC8 [SA602A]	CAT24AA16@TSOT-23 [SA717]
CAT24C32	CAT24C32@SOIC8 [SA602A]
CAT24C32@TDFN8 [SA724]	CAT24C32@TSSOP8 [SA643]
CAT24C32@UDFN8 [SA724]	CAT34TS02@TDFN8
CAT93C46R(08bit)	
CAT93C46R(08bit)(V)@SOIC8 [SA602A]	
CAT93C46R(08bit)(VP2)@TDFN8 [SA724]	
CAT93C46R(08bit)(W)@SOIC8 [SA602A]	
CAT93C46R(08bit)(X)@SOIC8 [SA602A]	
CAT93C46R(08bit)(Y)@TSSOP8 [SA643]	
CAT93C46R(16bit)(V)@SOIC8 [SA602A]	
CAT93C46R(16bit)(VP2)@TDFN8 [SA724]	
CAT93C46R(16bit)(W)@SOIC8 [SA602A]	
CAT93C46R(16bit)(X)@SOIC8 [SA602A]	
CAT93C46R(16bit)(Y)@TSSOP8 [SA643]	
CAT93C46R-16	CAT93C56(08bit)
CAT93C56(08bit)@SOIC8(150mil) [SA602A]	
CAT93C56(08bit)@SOIC8(208mil) [SA605B]	
CAT93C56(08bit)@TSSOP8 [SA643]	
CAT93C56(08bit)TDFN8(2*3) [SA724]	
CAT93C56(08bit)TDFN8(3*3) [SA703]	
CAT93C56(16bit)	
CAT93C56(16bit)@SOIC8(150mil) [SA602A]	
CAT93C56(16bit)@SOIC8(208mil) [SA605B]	
CAT93C56(16bit)@TSSOP8 [SA643]	
CAT93C56(16bit)TDFN8(2*3) [SA724]	
CAT93C56(16bit)TDFN8(3*3) [SA703]	
CAT93C57(08bit)	
CAT93C57(08bit)@SOIC8(150mil) [SA602A]	
CAT93C57(08bit)@SOIC8(208mil) [SA605B]	
CAT93C57(08bit)@TSSOP8 [SA643]	
CAT93C57(08bit)TDFN8(2*3) [SA724]	
CAT93C57(08bit)TDFN8(3*3) [SA703]	
CAT93C57(16bit)	
CAT93C57(16bit)@SOIC8(150mil) [SA602A]	

CAT93C57(16bit)@SOIC8(208mil) [SA605B]	
CAT93C57(16bit)@TSSOP8 [SA643]	
CAT93C57(16bit)TDFN8(2*3) [SA724]	
CAT93C57(16bit)TDFN8(3*3) [SA703]	
CAV24C02@SOIC8 [SA602A]	CAV24C02@TSSOP8 [SA643]
CAV24C04@SOIC8 [SA602A]	CAV24C04@TSSOP8 [SA643]
CAV24C08@SOIC8 [SA602A]	CAV24C08@TSSOP8 [SA643]
CAV24C16@SOIC8 [SA602A]	CAV24C16@TSSOP8 [SA643]
CAV24C32@SOIC8 [SA602A]	CAV24C32@TSSOP8 [SA643]
CAV24C64@SOIC8 [SA602A]	CAV24C64@TSSOP8 [SA643]

## On-Bright

### MICROCONTROLLER

OB37R04A1@SOP10 [SA602]	OB37R04A1@SOP14 [SA602]
OB37R04A1@SOP16 [SA602]	OB37R259A@SOP14 [SA602]
OB37R259A@SOP16 [SA602]	OB39A08T1@QFP32 [SA636]
OB39A08T1@SOP16 [SA602]	OB39A08T1@SOP20 [SA404]
OB39A08T1@SOP24 [SA404]	OB39A08T1@SOP28 [SA404]
OB39A08T2@SOP24 [SA404]	OB39A08T2@SOP28 [SA404]
OB39A16D1@QFP48 [SA248-B4804]	OB39A16D2@QFP48 [SA248-B4804]
OB39A16T1@QFP32 [SA636]	OB39A16T1@SOP16 [SA602]
OB39A16T1@SOP20 [SA404]	OB39A16T1@SOP24 [SA404]
OB39A16T1@SOP28 [SA404]	

## PARAGON

### E (E) PROM/FRAM/NVRAM

BN25F04A@SOP8 [SA605B]	PN24C02B@SOP8 [SA602A]
PN24C02B@SOT23 [SA717]	PN24C02B@TSSOP8 [SA643]
PN24C04A@SOP8 [SA602A]	PN24C04A@TSSOP8 [SA643]
PN24C08A@SOP8 [SA602A]	PN24C08A@TSSOP8 [SA643]
PN24C1024A@SOP8 [SA602A]	PN24C1024A@TSSOP8 [SA643]
PN24C128A@SOP8 [SA602A]	PN24C128A@TSSOP8 [SA643]
PN24C16A@SOP8 [SA602A]	PN24C16A@TSSOP8 [SA643]
PN24C256A@SOP8 [SA602A]	PN24C256A@TSSOP8 [SA643]
PN24C32A@SOP8 [SA602A]	PN24C32A@TSSOP8 [SA643]
PN24C512A@SOP8 [SA602A]	PN24C512A@TSSOP8 [SA643]
PN24C64A@SOP8 [SA602A]	PN24C64A@TSSOP8 [SA643]
PN25F04A@SOP8 [SA605B]	PN25F04A@TSSOP8 [SA602A]
PN25F08@SOP8[150 mil] [SA602A]	PN25F08@SOP8[208 mil] [SA605B]
PN25F08@TSSOP8 [SA026]	PN25F16@SOP8[150 mil] [SA602A]
PN25F16@SOP8[208 mil] [SA605B]	PN25F16@TSSOP8 [SA026]
PN25F32@SOP8 [SA605B]	

## PCT

### E (E) PROM/FRAM/NVRAM

PCT25LF010@SOIC8 (4. 0) [SA602A]	PCT25LF010@SOIC8 (5. 4) [SA605B]
PCT25LF010@WSON8 [SA683]	PCT25LF010A@SOIC8 (4. 0) [SA602A]
PCT25LF010A@SOIC8 (5. 4) [SA605B]	PCT25LF010A@WSON8 [SA683]
PCT25LF016A@SOIC8 (4. 0) [SA602A]	PCT25LF016A@SOIC8 (5. 4) [SA605B]
PCT25LF016A@WSON8 [SA683]	PCT25LF016B@SOIC8 (4. 0) [SA602A]
PCT25LF016B@SOIC8 (5. 4) [SA605B]	PCT25LF016B@WSON8 [SA683]
PCT25LF020@SOIC8 (4. 0) [SA602A]	PCT25LF020@SOIC8 (5. 4) [SA605B]
PCT25LF020@WSON8 [SA683]	PCT25LF020A@SOIC8 (4. 0) [SA602A]
PCT25LF020A@SOIC8 (5. 4) [SA605B]	PCT25LF020A@WSON8 [SA683]
PCT25LF040@SOIC8 (4. 0) [SA602A]	PCT25LF040@SOIC8 (5. 4) [SA605B]
PCT25LF040@WSON8 [SA683]	PCT25LF040A@SOIC8 (4. 0) [SA602A]
PCT25LF040A@SOIC8 (5. 4) [SA605B]	PCT25LF040A@WSON8 [SA683]
PCT25LF080@SOIC8 (4. 0) [SA602A]	PCT25LF080@SOIC8 (5. 4) [SA605B]
PCT25LF080@WSON8 [SA683]	PCT25LF080A@SOIC8 (4. 0) [SA602A]
PCT25LF080A@SOIC8 (5. 4) [SA605B]	PCT25LF080A@WSON8 [SA683]
PCT25VF010@SOIC8 (4. 0) [SA602A]	PCT25VF010@SOIC8 (5. 4) [SA605B]
PCT25VF010@WSON8 [SA683]	PCT25VF010A@SOIC8 (4. 0) [SA602A]
PCT25VF010A@SOIC8 (5. 4) [SA605B]	PCT25VF010A@WSON8 [SA683]
PCT25VF016B@SOIC8 (4. 0) [SA602A]	PCT25VF016B@SOIC8 (5. 4) [SA605B]
PCT25VF016B@WSON8 [SA683]	PCT25VF020@SOIC8 (4. 0) [SA602A]
PCT25VF020@SOIC8 (5. 4) [SA605B]	PCT25VF020@WSON8 [SA683]
PCT25VF020B@SOIC8 (4. 0) [SA602A]	PCT25VF020B@SOIC8 (5. 4) [SA605B]
PCT25VF020B@WSON8 [SA683]	PCT25VF032B@SOIC16 [SA404]
PCT25VF032B@SOIC8 (4. 0) [SA602A]	PCT25VF032B@SOIC8 (5. 4) [SA605B]
PCT25VF032B@WSON8 [SA683]	PCT25VF040@SOIC8 (4. 0) [SA602A]
PCT25VF040@SOIC8 (5. 4) [SA605B]	PCT25VF040@WSON8 [SA683]
PCT25VF040B@SOIC8 (4. 0) [SA602A]	PCT25VF040B@SOIC8 (5. 4) [SA605B]
PCT25VF040B@WSON8 [SA683]	PCT25VF080@SOIC8 (4. 0) [SA602A]
PCT25VF080@SOIC8 (5. 4) [SA605B]	PCT25VF080@WSON8 [SA683]
PCT25VF080B@SOIC8 (4. 0) [SA602A]	PCT25VF080B@SOIC8 (5. 4) [SA605B]
PCT25VF080B@WSON8 [SA683]	PCT25VF512@SOIC8 (4. 0) [SA602A]
PCT25VF512@SOIC8 (5. 4) [SA605B]	PCT25VF512@WSON8 [SA683]
PCT25VF512A@SOIC8 (4. 0) [SA602A]	PCT25VF512A@SOIC8 (5. 4) [SA605B]
PCT25VF512A@WSON8 [SA683]	PCT25WF010@SOIC8 (4. 0) [SA602A]
PCT25WF010@SOIC8 (5. 4) [SA605B]	PCT25WF010@WSON8 [SA683]
PCT25WF020@SOIC8 (4. 0) [SA602A]	PCT25WF020@SOIC8 (5. 4) [SA605B]
PCT25WF020@WSON8 [SA683]	PCT25WF040@SOIC8 (4. 0) [SA602A]
PCT25WF040@SOIC8 (5. 4) [SA605B]	PCT25WF040@WSON8 [SA683]
PCT25WF080@SOIC8 (4. 0) [SA602A]	PCT25WF080@SOIC8 (5. 4) [SA605B]
PCT25WF080@WSON8 [SA683]	PCT25WF512@SOIC8 (4. 0) [SA602A]
PCT25WF512@SOIC8 (5. 4) [SA605B]	PCT25WF512@WSON8 [SA683]

## PHILIPS

### E (E) PROM/FRAM/NVRAM

27C010	27C010@PLCC32 [SA015A1T]
27C010@TSOP32 [SA410T-B4001]	27C040
27C040@PLCC32 [SA015A1T]	27C040@TSOP32 [SA410T-B4001]
27C210	27C210@PLCC44 [SA244]
27C240	27C240@PLCC44 [SA244]
27C256	27C256@PLCC32

27C32  
27C512@PLCC32  
27C64@PLCC32 [SA015A1T]  
27C64A@PLCC32 [SA015A1T]  
27C64AF@PLCC32 [SA015A1T]  
27HC641@PLCC28  
PCA24S08@SOIC8 [SA602A]  
PCA8574 (P)  
PCA8574 (TS)@SSOP20 [SA026]  
PCA8574A (T)@SOIC16 [SA404]  
PCA8581  
PCA8581C  
PCA8582A  
PCA8582B  
PCA8582C  
PCA8582D  
PCA8582E  
PCA9500@HQVFN16 [SA747]  
PCA9500@TSSOP16 [SA026]  
PCA9501@SOIC20 [SA404]  
PCD8581  
PCD8581C  
PCD8582A  
PCD8582B  
PCD8582C  
PCD8582D  
PCD8582E  
PCF85102C  
PCF85103C  
PCF85116  
PCF8581  
PCF8581C  
PCF8582A  
PCF8582B  
PCF8582C  
PCF8582D  
PCF8582E  
PCF8594  
PCF8594C  
PCF8594D  
PCF8594E  
PCF8598  
PCF8598C  
PCF8598D  
PCF8598E

27C512  
27C64  
27C64A  
27C64AF  
27HC641  
27PC32  
PCA24S08@TSSOP8 [SA026]  
PCA8574 (T)@SOIC16 [SA404]  
PCA8574A (P)  
PCA8574A (TS)@SSOP20 [SA026]  
PCA8581@SOIC8 [SA602A]  
PCA8581C@SOIC8 [SA602A]  
PCA8582A@SOIC8 [SA602A]  
PCA8582B@SOIC8 [SA602A]  
PCA8582C@SOIC8 [SA602A]  
PCA8582D@SOIC8 [SA602A]  
PCA8582E@SOIC8 [SA602A]  
PCA9500@SOIC16 [SA404]  
PCA9501@HQVFN20  
PCA9501@TSSOP20 [SA026]  
PCD8581@SOIC8 [SA602A]  
PCD8581C@SOIC8 [SA602A]  
PCD8582A@SOIC8 [SA602A]  
PCD8582B@SOIC8 [SA602A]  
PCD8582C@SOIC8 [SA602A]  
PCD8582D@SOIC8 [SA602A]  
PCD8582E@SOIC8 [SA602A]  
PCF85102C@SOIC8 [SA602A]  
PCF85103C@SOIC8 [SA602A]  
PCF85116@SOIC8 [SA602A]  
PCF8581@SOIC8 [SA602A]  
PCF8581C@SOIC8 [SA602A]  
PCF8582A@SOIC8 [SA602A]  
PCF8582B@SOIC8 [SA602A]  
PCF8582C@SOIC8 [SA602A]  
PCF8582D@SOIC8 [SA602A]  
PCF8582E@SOIC8 [SA602A]  
PCF8594@SOIC8 [SA602A]  
PCF8594C@SOIC8 [SA602A]  
PCF8594D@SOIC8 [SA602A]  
PCF8594E@SOIC8 [SA602A]  
PCF8598@SOIC8 [SA605B]  
PCF8598C@SOIC8 [SA605B]  
PCF8598D@SOIC8 [SA605B]  
PCF8598E@SOIC8 [SA605B]

## MICROCONTROLLER

LPC1111/101@LQFP48 [SA248-B4804]  
LPC1111/101@QFP44 [SA245A-B4805]  
LPC1111/102@QFN33 [SA701]  
LPC1111/103@LQFP48 [SA248-B4804]

LPC1111/101@QFN33 [SA701]  
LPC1111/102@LQFP48 [SA248-B4804]  
LPC1111/102@QFP44 [SA245A-B4805]  
LPC1111/103@QFN33 [SA701]

LPC1111/103@QFP44 [SA245A-B4805]  
LPC1111/201@QFN33 [SA701]  
LPC1111/202@LQFP48 [SA248-B4804]  
LPC1111/202@QFP44 [SA245A-B4805]  
LPC1111/203@QFN33 [SA701]  
LPC1111@LQFP48 [SA248-B4804]  
LPC1111@QFP44 [SA245A-B4805]  
LPC1112/101@QFN33 [SA701]  
LPC1112/102@LQFP48 [SA248-B4804]  
LPC1112/102@QFP44 [SA245A-B4805]  
LPC1112/103@QFN33 [SA701]  
LPC1112/201@LQFP48 [SA248-B4804]  
LPC1112/201@QFP44 [SA245A-B4805]  
LPC1112/202@QFN33 [SA701]  
LPC1112/203@LQFP48 [SA248-B4804]  
LPC1112/203@QFP44 [SA245A-B4805]  
LPC1112@QFN33 [SA701]  
LPC1113/101@LQFP48 [SA248-B4804]  
LPC1113/101@QFP44 [SA245A-B4805]  
LPC1113/102@QFN33 [SA701]  
LPC1113/103@LQFP48 [SA248-B4804]  
LPC1113/103@QFP44 [SA245A-B4805]  
LPC1113/201@QFN33 [SA701]  
LPC1113/202@LQFP48 [SA248-B4804]  
LPC1113/202@QFP44 [SA245A-B4805]  
LPC1113/203@QFN33 [SA701]  
LPC1113@LQFP48 [SA248-B4804]  
LPC1113@QFP44 [SA245A-B4805]  
LPC1114/101@QFN33 [SA701]  
LPC1114/102@LQFP48 [SA248-B4804]  
LPC1114/102@QFP44 [SA245A-B4805]  
LPC1114/103@QFN33 [SA701]  
LPC1114/201@LQFP48 [SA248-B4804]  
LPC1114/201@QFP44 [SA245A-B4805]  
LPC1114/202@QFN33 [SA701]  
LPC1114/203@LQFP48 [SA248-B4804]  
LPC1114/203@QFP44 [SA245A-B4805]  
LPC1114@QFN33 [SA701]  
LPC11C12/101@LQFP48 [SA248-B4804]  
LPC11C12/102@LQFP48 [SA248-B4804]  
LPC11C12/103@LQFP48 [SA248-B4804]  
LPC11C12/201@LQFP48 [SA248-B4804]  
LPC11C12/202@LQFP48 [SA248-B4804]  
LPC11C12/203@LQFP48 [SA248-B4804]  
LPC11C12/301@LQFP48 [SA248-B4804]  
LPC11C12@LQFP48 [SA248-B4804]  
LPC11C14/101@LQFP48 [SA248-B4804]  
LPC11C14/102@LQFP48 [SA248-B4804]  
LPC11C14/103@LQFP48 [SA248-B4804]  
LPC11C14/201@LQFP48 [SA248-B4804]  
LPC11C14/202@LQFP48 [SA248-B4804]  
LPC11C14/203@LQFP48 [SA248-B4804]  
LPC11C14/301@LQFP48 [SA248-B4804]  
LPC1111/201@LQFP48 [SA248-B4804]  
LPC1111/201@QFP44 [SA245A-B4805]  
LPC1111/202@QFN33 [SA701]  
LPC1111/203@LQFP48 [SA248-B4804]  
LPC1111/203@QFP44 [SA245A-B4805]  
LPC1111@QFN33 [SA701]  
LPC1112/101@LQFP48 [SA248-B4804]  
LPC1112/101@QFP44 [SA245A-B4805]  
LPC1112/102@QFN33 [SA701]  
LPC1112/103@LQFP48 [SA248-B4804]  
LPC1112/103@QFP44 [SA245A-B4805]  
LPC1112/201@QFN33 [SA701]  
LPC1112/202@LQFP48 [SA248-B4804]  
LPC1112/202@QFP44 [SA245A-B4805]  
LPC1112/203@QFN33 [SA701]  
LPC1112@LQFP48 [SA248-B4804]  
LPC1112@QFP44 [SA245A-B4805]  
LPC1113/101@QFN33 [SA701]  
LPC1113/102@LQFP48 [SA248-B4804]  
LPC1113/102@QFP44 [SA245A-B4805]  
LPC1113/103@QFN33 [SA701]  
LPC1113/201@LQFP48 [SA248-B4804]  
LPC1113/201@QFP44 [SA245A-B4805]  
LPC1113/202@QFN33 [SA701]  
LPC1113/203@LQFP48 [SA248-B4804]  
LPC1113/203@QFP44 [SA245A-B4805]  
LPC1113@QFN33 [SA701]  
LPC1114/101@LQFP48 [SA248-B4804]  
LPC1114/101@QFP44 [SA245A-B4805]  
LPC1114/102@QFN33 [SA701]  
LPC1114/103@LQFP48 [SA248-B4804]  
LPC1114/103@QFP44 [SA245A-B4805]  
LPC1114/201@QFN33 [SA701]  
LPC1114/202@LQFP48 [SA248-B4804]  
LPC1114/202@QFP44 [SA245A-B4805]  
LPC1114/203@QFN33 [SA701]  
LPC1114@LQFP48 [SA248-B4804]  
LPC1114@QFP44 [SA245A-B4805]

LPC11C14@LQFP48 [SA248-B4804]  
LPC11C22/101@LQFP48 [SA248-B4804]  
LPC11C22/102@LQFP48 [SA248-B4804]  
LPC11C22/103@LQFP48 [SA248-B4804]  
LPC11C22/201@LQFP48 [SA248-B4804]  
LPC11C22/202@LQFP48 [SA248-B4804]  
LPC11C22/203@LQFP48 [SA248-B4804]  
LPC11C22/301@LQFP48 [SA248-B4804]  
LPC11C22@LQFP48 [SA248-B4804]  
LPC11C24/101@LQFP48 [SA248-B4804]  
LPC11C24/102@LQFP48 [SA248-B4804]  
LPC11C24/103@LQFP48 [SA248-B4804]  
LPC11C24/201@LQFP48 [SA248-B4804]  
LPC11C24/202@LQFP48 [SA248-B4804]  
LPC11C24/203@LQFP48 [SA248-B4804]  
LPC11C24/301@LQFP48 [SA248-B4804]  
LPC11C24@LQFP48 [SA248-B4804]  
OM4371FN@PLCC44 [SA244]  
P83C660X2@PLCC44 [SA244]  
P83C661X2@PLCC44 [SA244]  
P87C51  
P87C51@TQFP44 [SA675-B4805]  
P87C51FA@PLCC44 [SA244]  
P87C51FB  
P87C51FB@TQFP44 [SA675-B4805]  
P87C51FC@PLCC44 [SA244]  
P87C51MA2@PLCC44 [SA244]  
P87C51MC2@PLCC44 [SA244]  
P87C51RA+@PLCC44 [SA244]  
P87C51RA2  
P87C51RA2@TQFP44 [SA675-B4805]  
P87C51RB+@PLCC44 [SA244]  
P87C51RB2  
P87C51RB2@TQFP44 [SA675-B4805]  
P87C51RC+@PLCC44 [SA244]  
P87C51RC2  
P87C51RC2@TQFP44 [SA675-B4805]  
P87C51RD+@PLCC44 [SA244]  
P87C51RD2  
P87C51RD2@TQFP44 [SA675-B4805]  
P87C51SB@PLCC44 [SA244]  
P87C51SF  
P87C51SF@TQFP44 [SA675-B4805]  
P87C51UB@PLCC44 [SA244]  
P87C51UF  
P87C51UF@TQFP44 [SA675-B4805]  
P87C51X2@PLCC44 [SA244]  
P87C51X2@TTSOP38 [SA693]  
P87C52@PLCC44 [SA244]  
P87C524  
P87C524@TQFP44 [SA245A-B4805]  
P87C528@PLCC44 [SA244]  
P87C52SB  
OM4371FN  
OM4371FN@TQFP44 [SA245A-B4805]  
P83C660X2@TQFP44 [SA245A-B4805]  
P83C661X2@TQFP44 [SA245A-B4805]  
P87C51@PLCC44 [SA244]  
P87C51FA  
P87C51FA@TQFP44 [SA675-B4805]  
P87C51FB@PLCC44 [SA244]  
P87C51FC  
P87C51FC@TQFP44 [SA245A-B4805]  
P87C51MB2@PLCC44 [SA244]  
P87C51RA+  
P87C51RA+@TQFP44 [SA245A-B4805]  
P87C51RA2@PLCC44 [SA244]  
P87C51RB+  
P87C51RB+@TQFP44 [SA245A-B4805]  
P87C51RB2@PLCC44 [SA244]  
P87C51RC+  
P87C51RC+@TQFP44 [SA245A-B4805]  
P87C51RC2@PLCC44 [SA244]  
P87C51RD+  
P87C51RD+@TQFP44 [SA245A-B4805]  
P87C51RD2@PLCC44 [SA244]  
P87C51SB  
P87C51SB@TQFP44 [SA675-B4805]  
P87C51SF@PLCC44 [SA244]  
P87C51UB  
P87C51UB@TQFP44 [SA675-B4805]  
P87C51UF@PLCC44 [SA244]  
P87C51X2  
P87C51X2@TQFP44 [SA245A-B4805]  
P87C52  
P87C52@TQFP44 [SA675-B4805]  
P87C524@PLCC44 [SA244]  
P87C528  
P87C528@TQFP44 [SA245A-B4805]  
P87C52SB@PLCC44 [SA244]

P87C52SB@TQFP44 [SA675-B4805]  
P87C52SF@PLCC44 [SA244]  
P87C52UB  
P87C52UB@TQFP44 [SA675-B4805]  
P87C52UF@PLCC44 [SA244]  
P87C52X2  
P87C52X2@TQFP44 [SA245A-B4805]  
P87C54  
P87C54@TQFP44 [SA675-B4805]  
P87C54SB@PLCC44 [SA244]  
P87C54SF  
P87C54SF@TQFP44 [SA675-B4805]  
P87C54UB@PLCC44 [SA244]  
P87C54UF  
P87C54UF@TQFP44 [SA675-B4805]  
P87C54X2@PLCC44 [SA244]  
P87C54X2@TTSOP38 [SA693]  
P87C550@PLCC44 [SA244]  
P87C575@PLCC44 [SA244]  
P87C576  
P87C576@TQFP44 [SA675-B4805]  
P87C58@PLCC44 [SA244]  
P87C58SB  
P87C58SB@TQFP44 [SA675-B4805]  
P87C58UB@PLCC44 [SA244]  
P87C58X2  
P87C58X2@TQFP44 [SA245A-B4805]  
P87C591@PLCC44 [SA244]  
P87C652  
P87C652@TQFP44 [SA675-B4805]  
P87C654@PLCC44 [SA244]  
P87C660X2@PLCC44 [SA244]  
P87C661X2@PLCC44 [SA244]  
P87CL52X2  
P87CL52X2@TQFP44 [SA245A-B4805]  
P87CL54X2  
P87CL54X2@TQFP44 [SA245A-B4805]  
P87L51FA  
P87L51FA@TQFP44 [SA675-B4805]  
P87L51FB@PLCC44 [SA244]  
P87LPC759  
P87LPC760  
P87LPC760@TSSOP14 [SA026]  
P87LPC761  
P87LPC762  
P87LPC762@PLCC44 [SA605B]  
P87LPC762@S0IC20 [SA404]  
P87LPC764  
P87LPC764@PLCC44 [SA605B]  
P87LPC764@S0IC20 [SA404]  
P87LPC764@TSSOP20 [SA643]  
P87LPC767  
P87LPC767@PLCC44 [SA605B]

P87C52SF  
P87C52SF@TQFP44 [SA675-B4805]  
P87C52UB@PLCC44 [SA244]  
P87C52UF  
P87C52UF@TQFP44 [SA675-B4805]  
P87C52X2@PLCC44 [SA244]  
P87C52X2@TTSOP38 [SA693]  
P87C54@PLCC44 [SA244]  
P87C54SB  
P87C54SB@TQFP44 [SA675-B4805]  
P87C54SF@PLCC44 [SA244]  
P87C54UB  
P87C54UB@TQFP44 [SA675-B4805]  
P87C54UF@PLCC44 [SA244]  
P87C54X2  
P87C54X2@TQFP44 [SA245A-B4805]  
P87C550  
P87C575  
P87C575@TQFP44 [SA675-B4805]  
P87C576@PLCC44 [SA244]  
P87C58  
P87C58@TQFP44 [SA675-B4805]  
P87C58SB@PLCC44 [SA244]  
P87C58UB  
P87C58UB@TQFP44 [SA675-B4805]  
P87C58X2@PLCC44 [SA244]  
P87C58X2@TTSOP38 [SA693]  
P87C591@TQFP44 [SA675-B4805]  
P87C652@PLCC44 [SA244]  
P87C654  
P87C654@TQFP44 [SA675-B4805]  
P87C660X2@TQFP44 [SA245A-B4805]  
P87C661X2@TQFP44 [SA245A-B4805]  
P87CL52X2@PLCC44 [SA244]  
P87CL52X2@TTSOP38 [SA693]  
P87CL54X2@PLCC44 [SA244]  
P87CL54X2@TTSOP38 [SA693]  
P87L51FA@PLCC44 [SA244]  
P87L51FB  
P87L51FB@TQFP44 [SA675-B4805]  
P87LPC759 (ISP)  
P87LPC760 (ISP)  
P87LPC760@TSSOP14 (ISP)  
P87LPC761 (ISP)  
P87LPC762 (ISP)  
P87LPC762@PLCC44 (ISP)  
P87LPC762@S0IC20 (ISP)  
P87LPC764 (ISP)  
P87LPC764@PLCC44 (ISP)  
P87LPC764@S0IC20 (ISP)  
P87LPC764@TSSOP20 (ISP)  
P87LPC767 (ISP)  
P87LPC767@PLCC44 (ISP)

P87LPC767@S0IC20 [SA404]  
P87LPC768  
P87LPC768@S0IC20 [SA404]  
P87LPC769  
P87LPC769@PLCC44 [SA605B]  
P87LPC769@S0IC20 [SA404]  
P87LPC778  
P87LPC778@TSSOP20 [SA026]  
P87LPC779  
P87LPC779@TSSOP20 [SA026]  
P89C138  
P89C138@TQFP44 [SA245A-B4805]  
P89C238@PLCC44 [SA244]  
P89C51B  
P89C51B@TQFP44 [SA245A-B4805]  
P89C51RA+@PLCC44 [SA244]  
P89C51RA2B  
P89C51RA2B@TQFP44 [SA245A-B4805]  
P89C51RB+@PLCC44 [SA244]  
P89C51RB2B  
P89C51RB2B@TQFP44 [SA245A-B4805]  
P89C51RB2H@PLCC44 [SA244]  
P89C51RC+  
P89C51RC+@TQFP44 [SA245A-B4805]  
P89C51RC2B@PLCC44 [SA244]  
P89C51RC2H  
P89C51RC2H@TQFP44 [SA675-B4805]  
P89C51RD+@PLCC44 [SA244]  
P89C51RD2B  
P89C51RD2B@TQFP44 [SA245A-B4805]  
P89C51RD2H@PLCC44 [SA244]  
P89C51UB  
P89C51UB@TQFP44 [SA245A-B4805]  
P89C51UF@PLCC44 [SA244]  
P89C51X2  
P89C51X2@TQFP44 [SA245A-B4805]  
P89C51X2B@PLCC44 [SA244]  
P89C51X2F  
P89C51X2F@TQFP44 [SA245A-B4805]  
P89C52@PLCC44 [SA244]  
P89C52B  
P89C52B@TQFP44 [SA245A-B4805]  
P89C52UB@PLCC44 [SA244]  
P89C52UF  
P89C52UF@TQFP44 [SA245A-B4805]  
P89C52X2@PLCC44 [SA244]  
P89C52X2B  
P89C52X2B@TQFP44 [SA245A-B4805]  
P89C52X2F@PLCC44 [SA244]  
P89C536@PLCC44 [SA244]  
P89C54  
P89C54@TQFP44 [SA245A-B4805]  
P89C54B@PLCC44 [SA244]

P87LPC767@S0IC20 (ISP)  
P87LPC768 (ISP)  
P87LPC768@S0IC20 (ISP)  
P87LPC769 (ISP)  
P87LPC769@PLCC44 (ISP)  
P87LPC769@S0IC20 (ISP)  
P87LPC778 (ISP)  
P87LPC778@TSSOP20 (ISP)  
P87LPC779 (ISP)  
P87LPC779@TSSOP20 (ISP)  
P89C138@PLCC44 [SA244]  
P89C238  
P89C238@TQFP44 [SA245A-B4805]  
P89C51B@PLCC44 [SA244]  
P89C51RA+  
P89C51RA+@TQFP44 [SA245A-B4805]  
P89C51RA2B@PLCC44 [SA244]  
P89C51RB+  
P89C51RB+@TQFP44 [SA245A-B4805]  
P89C51RB2B@PLCC44 [SA244]  
P89C51RB2H  
P89C51RB2H@TQFP44 [SA675-B4805]  
P89C51RC+@PLCC44 [SA244]  
P89C51RC2B  
P89C51RC2B@TQFP44 [SA245A-B4805]  
P89C51RC2H@PLCC44 [SA244]  
P89C51RD+  
P89C51RD+@TQFP44 [SA245A-B4805]  
P89C51RD2B@PLCC44 [SA244]  
P89C51RD2H  
P89C51RD2H@TQFP44 [SA675-B4805]  
P89C51UB@PLCC44 [SA244]  
P89C51UF  
P89C51UF@TQFP44 [SA245A-B4805]  
P89C51X2@PLCC44 [SA244]  
P89C51X2B  
P89C51X2B@TQFP44 [SA245A-B4805]  
P89C51X2F@PLCC44 [SA244]  
P89C52  
P89C52@TQFP44 [SA245A-B4805]  
P89C52B@PLCC44 [SA244]  
P89C52UB  
P89C52UB@TQFP44 [SA245A-B4805]  
P89C52UF@PLCC44 [SA244]  
P89C52X2  
P89C52X2@TQFP44 [SA245A-B4805]  
P89C52X2B@PLCC44 [SA244]  
P89C52X2F  
P89C52X2F@TQFP44 [SA245A-B4805]  
P89C538@PLCC44 [SA244]  
P89C54@PLCC44 [SA244]  
P89C54B  
P89C54B@TQFP44 [SA245A-B4805]

P89C54UB  
P89C54UB@TQFP44 [SA245A-B4805]  
P89C54UF@PLCC44 [SA244]  
P89C54X2  
P89C54X2@TQFP44 [SA245A-B4805]  
P89C54X2B@PLCC44 [SA244]  
P89C54X2F  
P89C54X2F@TQFP44 [SA245A-B4805]  
P89C58@PLCC44 [SA244]  
P89C58B  
P89C58B@TQFP44 [SA245A-B4805]  
P89C58UB@PLCC44 [SA244]  
P89C58UF  
P89C58UF@TQFP44 [SA245A-B4805]  
P89C58X2@PLCC44 [SA244]  
P89C58X2B  
P89C58X2B@TQFP44 [SA245A-B4805]  
P89C58X2F@PLCC44 [SA244]  
P89C60X2  
P89C60X2@TQFP44 [SA245A-B4805]  
P89C61X2@PLCC44 [SA244]  
P89C660  
P89C660@TQFP44 [SA675-B4805]  
P89C662@PLCC44 [SA244]  
P89C664  
P89C664@TQFP44 [SA675-B4805]  
P89C668@PLCC44 [SA244]  
P89C669  
P89C669@PLCC44 [SA244]  
P89C669X2@LQFP44 [SA245A-B4805]  
P89C738  
P89C738@TQFP44 [SA245A-B4805]  
P89C838@PLCC44 [SA244]  
P89CV51RB2@PLCC44 [SA244]  
P89CV51RC2@PLCC44 [SA244]  
P89CV51RD2@PLCC44 [SA244]  
P89LPC901 (FD) [SA602A]  
P89LPC901 (FN)  
P89LPC902 (FD) [SA602A]  
P89LPC902 (FN)  
P89LPC903 (FD) [SA602A]  
P89LPC904 (FD) [SA602A]  
P89LPC904 (FN) [SA602A]  
P89LPC906 (FD) [SA602A]  
P89LPC907 (FD) [SA602A]  
P89LPC908 (FD) [SA602A]  
P89LPC9102 (FTK)@HVSON10 [SA695A]  
P89LPC9107 (FDH)@TSSOP14 [SA643]  
P89LPC912 (FDH)@TSSOP14 [SA026]  
P89LPC913 (FDH)@TSSOP14 [SA026]  
P89LPC914 (FDH)@TSSOP14 [SA026]  
P89LPC915 (FDH)@TSSOP14 [SA026]  
P89LPC916 (FDH)@TSSOP16 [SA026]

P89C54UB@PLCC44 [SA244]  
P89C54UF  
P89C54UF@TQFP44 [SA245A-B4805]  
P89C54X2@PLCC44 [SA244]  
P89C54X2B  
P89C54X2B@TQFP44 [SA245A-B4805]  
P89C54X2F@PLCC44 [SA244]  
P89C58  
P89C58@TQFP44 [SA245A-B4805]  
P89C58B@PLCC44 [SA244]  
P89C58UB  
P89C58UB@TQFP44 [SA245A-B4805]  
P89C58UF@PLCC44 [SA244]  
P89C58X2  
P89C58X2@TQFP44 [SA245A-B4805]  
P89C58X2B@PLCC44 [SA244]  
P89C58X2F  
P89C58X2F@TQFP44 [SA245A-B4805]  
P89C60X2@PLCC44 [SA244]  
P89C61X2  
P89C61X2@TQFP44 [SA245A-B4805]  
P89C660@PLCC44 [SA244]  
P89C662  
P89C662@TQFP44 [SA675-B4805]  
P89C664@PLCC44 [SA244]  
P89C668  
P89C668@TQFP44 [SA675-B4805]  
P89C669@LQFP44 [SA245A-B4805]  
P89C669X2  
P89C669X2@PLCC44 [SA244]  
P89C738@PLCC44 [SA244]  
P89C838  
P89C838@TQFP44 [SA245A-B4805]  
P89CV51RB2@TQFP44 [SA245A-B4805]  
P89CV51RC2@TQFP44 [SA245A-B4805]  
P89CV51RD2@TQFP44 [SA245A-B4805]  
P89LPC901 (FD) (ISP)  
P89LPC901 (FN) (ISP)  
P89LPC902 (FD) (ISP)  
P89LPC902 (FN) (ISP)  
P89LPC903 (FD) (ISP)  
P89LPC904 (FD) (ISP)  
P89LPC904 (FN) (ISP)  
P89LPC906 (FD) (ISP)  
P89LPC907 (FD) (ISP)  
P89LPC908 (FD) (ISP)  
P89LPC9103 (FTK)@HVSON10 [SA695A]  
P89LPC9107 (FN) [SA636]  
P89LPC912 (FDH)@TSSOP14 (ISP)  
P89LPC913 (FDH)@TSSOP14 (ISP)  
P89LPC914 (FDH)@TSSOP14 (ISP)  
P89LPC915 (FDH)@TSSOP14 (ISP)  
P89LPC916 (FDH)@TSSOP16 (ISP)

P89LPC917 (FDH)@TSSOP16 [SA026]  
P89LPC920 (FDH)@TSSOP20 [SA026]  
P89LPC920 (FN)  
P89LPC9201 (FDH)@TSSOP20 [SA026]  
P89LPC9201 (FN)  
P89LPC920A1 (FDH)@TSSOP20 [SA026]  
P89LPC920A1 (FN)  
P89LPC921 (FDH)@TSSOP20 [SA026]  
P89LPC921 (FN)  
P89LPC9211 (FDH)@TSSOP20 [SA026]  
P89LPC9211 (FN)  
P89LPC921A1 (FDH)@TSSOP20 [SA026]  
P89LPC921A1 (FN)  
P89LPC922 (FDH)@TSSOP20 [SA026]  
P89LPC922 (FN)  
P89LPC9221 (FDH)@TSSOP20 [SA026]  
P89LPC9221 (FN)  
P89LPC9221A1 (FDH)@TSSOP20 [SA026]  
P89LPC9221A1 (FDH)@TSSOP20 (ISP)  
P89LPC9221A1 (FN) (ISP)  
P89LPC922A1 (FDH)@TSSOP20 (ISP)  
P89LPC922A1 (FN) (ISP)  
P89LPC924 (FDH)@TSSOP20 (ISP)  
P89LPC924 (FN) (ISP)  
P89LPC9241 (FDH)@TSSOP20 (ISP)  
P89LPC9241 (FN) (ISP)  
P89LPC924A1 (FDH)@TSSOP20 (ISP)  
P89LPC924A1 (FN) (ISP)  
P89LPC925 (FDH)@TSSOP20 (ISP)  
P89LPC925 (FN) (ISP)  
P89LPC9251 (FDH)@TSSOP20 (ISP)  
P89LPC9251 (FN) (ISP)  
P89LPC925A1 (FDH)@TSSOP20 (ISP)  
P89LPC925A1 (FN) (ISP)  
P89LPC930 (BA)@PLCC28 (ISP)  
P89LPC930 (BDH)@TSSOP28 (ISP)  
P89LPC9301 (BDH)@TSSOP28 [SA643]  
P89LPC9301FDH [SA643]  
P89LPC930FDH [SA643]  
P89LPC931 (BA)@PLCC28 (ISP)  
P89LPC931 (BDH)@TSSOP28 (ISP)  
P89LPC9311 (BDH)@TSSOP28 [SA643]  
P89LPC9311FDH [SA643]  
P89LPC931FDH [SA643]  
P89LPC932 (BDH)@TSSOP28 [SA643]  
P89LPC93201BA@PLCC28 [SA008A]  
P89LPC93201FA@PLCC28 [SA008A]  
P89LPC93201FHN@QFN28 [SA685]  
P89LPC9321BDH@TSSOP28 [SA643]  
P89LPC9321FDH@TSSOP28 [SA643]  
P89LPC932A1 (BA)@PLCC28 [SA008A]  
P89LPC932A1 (BDH)@TSSOP28 [SA643]  
P89LPC932A1 (FA)@PLCC28 [SA008A]

P89LPC917 (FDH)@TSSOP16 (ISP)  
P89LPC920 (FDH)@TSSOP20 (ISP)  
P89LPC920 (FN) (ISP)  
P89LPC9201 (FDH)@TSSOP20 (ISP)  
P89LPC9201 (FN) (ISP)  
P89LPC920A1 (FDH)@TSSOP20 (ISP)  
P89LPC920A1 (FN) (ISP)  
P89LPC921 (FDH)@TSSOP20 (ISP)  
P89LPC921 (FN) (ISP)  
P89LPC9211 (FDH)@TSSOP20 (ISP)  
P89LPC9211 (FN) (ISP)  
P89LPC921A1 (FDH)@TSSOP20 (ISP)  
P89LPC921A1 (FN) (ISP)  
P89LPC922 (FDH)@TSSOP20 (ISP)  
P89LPC922 (FN) (ISP)  
P89LPC9221 (FDH)@TSSOP20 (ISP)  
P89LPC9221 (FN) (ISP)  
P89LPC9221A1 (FN)  
P89LPC922A1 (FDH)@TSSOP20 [SA026]  
P89LPC922A1 (FN)  
P89LPC924 (FDH)@TSSOP20 [SA026]  
P89LPC924 (FN)  
P89LPC9241 (FDH)@TSSOP20 [SA026]  
P89LPC9241 (FN)  
P89LPC924A1 (FDH)@TSSOP20 [SA026]  
P89LPC924A1 (FN)  
P89LPC925 (FDH)@TSSOP20 [SA026]  
P89LPC925 (FN)  
P89LPC9251 (FDH)@TSSOP20 [SA026]  
P89LPC9251 (FN)  
P89LPC925A1 (FDH)@TSSOP20 [SA026]  
P89LPC925A1 (FN)  
P89LPC930 (BA)@PLCC28 [SA008A]  
P89LPC930 (BDH)@TSSOP28 [SA643]  
P89LPC9301 (BA)@PLCC28 [SA008A]  
P89LPC9301FA [SA008A]  
P89LPC930FA [SA008A]  
P89LPC931 (BA)@PLCC28 [SA008A]  
P89LPC931 (BDH)@TSSOP28 [SA643]  
P89LPC9311 (BA)@PLCC28 [SA008A]  
P89LPC9311FA [SA008A]  
P89LPC931FA [SA008A]  
P89LPC932 (BA)@PLCC28 [SA008A]  
P89LPC932 (FA)@PLCC28 [SA008A]  
P89LPC93201BDH@TSSOP28 [SA643]  
P89LPC93201FDH@TSSOP28 [SA643]  
P89LPC9321BA@PLCC28 [SA008A]  
P89LPC9321FA@PLCC28 [SA008A]  
P89LPC9321FHN@QFN28 [SA685]  
P89LPC932A1 (BA)@PLCC28 (ISP)  
P89LPC932A1 (BDH)@TSSOP28 (ISP)  
P89LPC932A1 (FDH)@TSSOP28 [SA643]

P89LPC932A1 (FDH)@TSSOP28 (ISP)  
P89LPC932A1 (FHN)@HVQFN28 (ISP)  
P89LPC933 (BDH)@TSSOP28 (ISP)  
P89LPC933 (FDH)@TSSOP28 (ISP)  
P89LPC933 (HDH)@TSSOP28 (ISP)  
P89LPC9331 (BDH)@TSSOP28 [SA643]  
P89LPC9331 (HDH)@TSSOP28 [SA643]  
P89LPC934 (BDH)@TSSOP28 (ISP)  
P89LPC934 (FDH)@TSSOP28 (ISP)  
P89LPC93401V  
P89LPC9341 (FDH)@TSSOP28 [SA643]  
P89LPC935 (BA)@PLCC28 [SA008A]  
P89LPC935 (BDH)@TSSOP28 [SA643]  
P89LPC935 (FA)@PLCC28 [SA008A]  
P89LPC935 (FDH)@TSSOP28 [SA643]  
P89LPC935 (FHN)@HVQFN28 [SA685]  
P89LPC93501BA@PLCC28 [SA008A]  
P89LPC93501FA@PLCC28 [SA008A]  
P89LPC93501FHN@QFN28 [SA685]  
P89LPC9351BDH@TSSOP28 [SA643]  
P89LPC9351FDH@TSSOP28 [SA643]  
P89LPC936 (FA)@PLCC28 [SA008A]  
P89LPC9361 (FA)@PLCC28 [SA008A]  
P89LPC938 (FA)@PLCC28 [SA008A]  
P89LPC938 (FDH)@TSSOP28 [SA643]  
P89LPC938 (FHN)@HVQFN28 [SA685]  
P89LPC93801BA@PLCC28 [SA008A]  
P89LPC93801FA@PLCC28 [SA008A]  
P89LPC93801FHN@QFN28 [SA685]  
P89LPC9381BDH@TSSOP28 [SA643]  
P89LPC9381FDH@TSSOP28 [SA643]  
P89LPC9401 (FBD)@LQFP64 (ISP)  
P89LPC952@LQFP44 [SA245A-B4805]  
P89LPC952@LQFP48 [SA248-B4804]  
P89LPC952@PLCC44 [SA244]  
P89LPC954@LQFP44 [SA245A-B4805]  
P89LPC954@LQFP48 [SA248-B4804]  
P89LPC954@PLCC44 [SA244]  
P89LPC970FDH@TSSOP20 [SA026]  
P89LPC970FDH@TSSOP20 (serial) [SA026]  
P89LPC970FN  
P89LPC971FDH@TSSOP20 [SA026]  
P89LPC971FDH@TSSOP20 (serial) [SA026]  
P89LPC971FN  
P89LPC972FDH@TSSOP20 [SA026]  
P89LPC972FDH@TSSOP20 (serial) [SA026]  
P89LPC972FN  
P89LPC980FDH@TSSOP28 [SA643]  
P89LPC980FDH@TSSOP28 (serial) [SA643]  
P89LPC982FDH@TSSOP28 [SA643]  
P89LPC982FDH@TSSOP28 (serial) [SA643]  
P89LPC983FA@PLCC28 [SA008A]  
P89LPC983FA@PLCC28 (serial) [SA008A]  
P89LPC983FDH@TSSOP28 [SA643]  
P89LPC932A1 (FHN)@HVQFN28 [SA685]  
P89LPC933 (BDH)@TSSOP28 [SA643]  
P89LPC933 (FDH)@TSSOP28 [SA643]  
P89LPC933 (HDH)@TSSOP28 [SA643]  
P89LPC9331 (FDH)@TSSOP28 [SA643]  
P89LPC934 (BDH)@TSSOP28 [SA643]  
P89LPC934 (FDH)@TSSOP28 [SA643]  
P89LPC93401 (FDH)@TSSOP28 [SA643]  
P89LPC9341 (BDH)@TSSOP28 [SA643]  
P89LPC9341V  
P89LPC935 (BA)@PLCC28 (ISP)  
P89LPC935 (BDH)@TSSOP28 (ISP)  
P89LPC935 (FA)@PLCC28 (ISP)  
P89LPC935 (FDH)@TSSOP28 (ISP)  
P89LPC935 (FHN)@HVQFN28 (ISP)  
P89LPC93501BDH@TSSOP28 [SA643]  
P89LPC93501FDH@TSSOP28 [SA643]  
P89LPC9351BA@PLCC28 [SA008A]  
P89LPC9351FA@PLCC28 [SA008A]  
P89LPC9351FHN@QFN28 [SA685]  
P89LPC936 (FDH)@TSSOP28 [SA643]  
P89LPC9361 (FDH)@TSSOP28 [SA643]  
P89LPC938 (FA)@PLCC28 (ISP)  
P89LPC938 (FDH)@TSSOP28 (ISP)  
P89LPC938 (FHN)@HVQFN28 (ISP)  
P89LPC93801BDH@TSSOP28 [SA643]  
P89LPC93801FDH@TSSOP28 [SA643]  
P89LPC9381BA@PLCC28 [SA008A]  
P89LPC9381FA@PLCC28 [SA008A]  
P89LPC9381FHN@QFN28 [SA685]  
P89LPC9408 (FBD)@LQFP64 (ISP)  
P89LPC952@LQFP44 (ISP)  
P89LPC952@LQFP48 (ISP)  
P89LPC952@PLCC44 (ISP)  
P89LPC954@LQFP44 (ISP)  
P89LPC954@LQFP48 (ISP)  
P89LPC954@PLCC44 (ISP)  
P89LPC970FN (serial)  
P89LPC971FN (serial)  
P89LPC972FN (serial)

P89LPC983FDH@TSSOP28 (serial) [SA643]  
P89LPC985FA@PLCC28 [SA008A]  
P89LPC985FA@PLCC28 (serial) [SA008A]  
P89LPC985FDH@TSSOP28 [SA643]  
P89LPC985FDH@TSSOP28 (serial) [SA643]  
P89LV51RB2 P89LV51RB2@PLCC44 [SA244]  
P89LV51RB2@TQFP44 [SA245A-B4805] P89LV51RB2FA@PLCC44 [SA244]  
P89LV51RB2FBC@TQFP44 [SA245A-B4805]  
P89LV51RB2FN P89LV51RC2  
P89LV51RC2@PLCC44 [SA244] P89LV51RC2@TQFP44 [SA245A-B4805]  
P89LV51RC2FA@PLCC44 [SA244]  
P89LV51RC2FBC@TQFP44 [SA245A-B4805]  
P89LV51RC2FN P89LV51RD2  
P89LV51RD2 (new) P89LV51RD2 (new)@PLCC44 [SA244]  
P89LV51RD2 (new)@TQFP44 [SA245A-B4805]  
P89LV51RD2@PLCC44 [SA244] P89LV51RD2@TQFP44 [SA245A-B4805]  
P89LV51RD2BA (new)@PLCC44 [SA244] P89LV51RD2BA@PLCC44 [SA244]  
P89LV51RD2BBC (new)@TQFP44 [SA245A-B4805]  
P89LV51RD2BBC@TQFP44 [SA245A-B4805]  
P89LV51RD2BN P89LV51RD2BN (new)  
P89LV51RD2FA (new)@PLCC44 [SA244] P89LV51RD2FA@PLCC44 [SA244]  
P89LV51RD2FBC (new)@TQFP44 [SA245A-B4805]  
P89LV51RD2FBC@TQFP44 [SA245A-B4805]  
P89LV51RD2FN P89LV51RD2FN (new)  
P89V51RB2 P89V51RB2@PLCC44 [SA244]  
P89V51RB2@TQFP44 [SA245A-B4805] P89V51RB2FA@PLCC44 [SA244]  
P89V51RB2FBC@TQFP44 [SA245A-B4805]  
P89V51RB2FN P89V51RC2  
P89V51RC2@PLCC44 [SA244] P89V51RC2@TQFP44 [SA245A-B4805]  
P89V51RC2FA@PLCC44 [SA244]  
P89V51RC2FBC@TQFP44 [SA245A-B4805]  
P89V51RC2FN P89V51RD2  
P89V51RD2 (new) P89V51RD2 (new)@PLCC44 [SA244]  
P89V51RD2 (new)@TQFP44 [SA245A-B4805]  
P89V51RD2@PLCC44 [SA244] P89V51RD2@TQFP44 [SA245A-B4805]  
P89V51RD2BA (new)@PLCC44 [SA244] P89V51RD2BA@PLCC44 [SA244]  
P89V51RD2BBC (new)@TQFP44 [SA245A-B4805]  
P89V51RD2BBC@TQFP44 [SA245A-B4805]  
P89V51RD2BN P89V51RD2BN (new)  
P89V51RD2FA (new)@PLCC44 [SA244] P89V51RD2FA@PLCC44 [SA244]  
P89V51RD2FBC (new)@TQFP44 [SA245A-B4805]  
P89V51RD2FBC@TQFP44 [SA245A-B4805]  
P89V51RD2FN P89V51RD2FN (new)  
P89V52X2 P89V52X2 (ISP)  
P89V52X2@PLCC44 [SA244] P89V52X2@PLCC44 (ISP)  
P89V52X2@TQFP44 [SA245A-B4805] P89V52X2@TQFP44 (ISP)  
P89V54X2 P89V54X2 (ISP)  
P89V54X2@PLCC44 [SA244] P89V54X2@PLCC44 (ISP)  
P89V54X2@TQFP44 [SA245A-B4805] P89V54X2@TQFP44 (ISP)  
P89V660@PLCC44 [SA244] P89V660@TQFP44 [SA245A-B4805]  
P89V662@PLCC44 [SA244] P89V662@TQFP44 [SA245A-B4805]  
P89V664@PLCC44 [SA244] P89V664@TQFP44 [SA245A-B4805]  
PXAC37@PLCC44 [SA244] PXAC37@TQFP44 [SA245A-B4805]

PXAG17@PLCC44 [SA244]  
PXAG27@PLCC44 [SA244]  
PXAG37@PLCC44 [SA244]  
PXAG39@PLCC44 [SA244]  
PXAG39K@PLCC44 [SA244]  
PXAG49@PLCC44 [SA244]  
PXAG49K@PLCC44 [SA244]

PXAG17@TQFP44 [SA245A-B4805]  
PXAG27@TQFP44 [SA245A-B4805]  
PXAG37@TQFP44 [SA245A-B4805]  
PXAG39@TQFP44 [SA245A-B4805]  
PXAG39K@TQFP44 [SA245A-B4805]  
PXAG49@TQFP44 [SA245A-B4805]  
PXAG49K@TQFP44 [SA245A-B4805]

## PJ

### E (E) PROM/FRAM/NVRAM

PJ24C02  
PJ24C02@TSSOP8 [SA643]

PJ24C02@SOIC8 [SA602A]

## PMC

### E (E) PROM/FRAM/NVRAM

PM24C64  
PM24C64@TSOP8 [SA643]  
PM25LD512 (Q)@WSON8 [SA683]  
PM25LQ032@SOIC8 [SA605B]  
PM25LQ040 (B)@SOIC8 [SA605B]  
PM25LQ040 (S)@SOIC8 [SA602A]  
PM25LV010 (Q)@WSON8 [SA683]  
PM25LV010A (B)@SOIC8 [SA605B]  
PM25LV010A (S)@SOIC8 [SA602A]  
PM25LV020 (Q)@WSON8 [SA683]  
PM25LV040 (B)@SOIC8 [SA605B]  
PM25LV040 (S)@SOIC8 [SA602A]  
PM25LV512 (Q)@WSON8 [SA683]  
PM25LV512A (B)@SOIC8 [SA605B]  
PM25LV512A (S)@SOIC8 [SA602A]  
PM29F002B  
PM29F002T  
PM29F004B  
PM29F004T  
PM29LV002B  
PM29LV002B@VSOP32 [SA620-B4807]  
PM29LV002T@PLCC32 [SA015A1T]  
PM29LV004B@PLCC32 [SA015A1T]  
PM29LV004T@PLCC32 [SA015A1T]  
PM29LV104RB@PLCC32 [SA015A1T]  
PM29LV104RT@PLCC32 [SA015A1T]  
PM37LV512  
PM37LV512@VSOP32 [SA620-B4807]  
PM39F010@PLCC32 [SA015A1T]  
PM39F020  
PM39F020@VSOP32 [SA620-B4807]  
PM39F040@PLCC32 [SA015A1T]  
PM39LV010@PLCC32 [SA015A1T]

PM24C64@SOIC8 [SA602A]  
PM25LD512 (B)@SOIC8 [SA605B]  
PM25LD512 (S)@SOIC8 [SA602A]  
PM25LQ032@WSON8 [SA684]  
PM25LQ040 (Q)@WSON8 [SA683]  
PM25LV010 (B)@SOIC8 [SA605B]  
PM25LV010 (S)@SOIC8 [SA602A]  
PM25LV010A (Q)@WSON8 [SA683]  
PM25LV020 (B)@SOIC8 [SA605B]  
PM25LV020 (S)@SOIC8 [SA602A]  
PM25LV040 (Q)@WSON8 [SA683]  
PM25LV512 (B)@SOIC8 [SA605B]  
PM25LV512 (S)@SOIC8 [SA602A]  
PM25LV512A (Q)@WSON8 [SA683]  
PM25LV512A@TSSOP8 [SA643]  
PM29F002B@PLCC32 [SA015A1T]  
PM29F002T@PLCC32 [SA015A1T]  
PM29F004B@PLCC32 [SA015A1T]  
PM29F004T@PLCC32 [SA015A1T]  
PM29LV002B@PLCC32 [SA015A1T]  
PM29LV002T  
PM29LV002T@VSOP32 [SA620-B4807]  
PM29LV004B@VSOP32 [SA620-B4807]  
PM29LV004T@VSOP32 [SA620-B4807]  
PM29LV104RB@VSOP32 [SA620-B4807]  
PM29LV104RT@VSOP32 [SA620-B4807]  
PM37LV512@PLCC32 [SA015A1T]  
PM39F010  
PM39F010@VSOP32 [SA620-B4807]  
PM39F020@PLCC32 [SA015A1T]  
PM39F040  
PM39F040@VSOP32 [SA620-B4807]  
PM39LV010@VSOP32 [SA620-B4807]

PM39LV010R@PLCC32 [SA015A1T]  
PM39LV020@PLCC32 [SA015A1T]  
PM39LV040@PLCC32 [SA015A1T]  
PM39LV512@PLCC32 [SA015A1T]  
PM39LV512R@PLCC32 [SA015A1T]  
PM49FL002T@PLCC32 [SA015A1T]  
PM49FL004T@PLCC32 [SA015A1T]  
PM49FL008T@PLCC32 [SA015A1T]  
PM49LP002T@PLCC32 [SA015A1T]

PM39LV010R@VSOP32 [SA620-B4807]  
PM39LV020@VSOP32 [SA620-B4807]  
PM39LV040@VSOP32 [SA620-B4807]  
PM39LV512@VSOP32 [SA620-B4807]  
PM39LV512R@VSOP32 [SA620-B4807]  
PM49FL002T@VSOP32 [SA620-B4807]  
PM49FL004T@VSOP32 [SA620-B4807]  
PM49FL008T@VSOP32 [SA620-B4807]  
PM49LP002T@VSOP32 [SA620-B4807]

## PORTEK

### E (E) PROM/FRAM/NVRAM

PTK24A02T  
PTK24A04T  
PTK24A08T  
PTK24A16T

PTK24A02T@SOIC8 [SA602A]  
PTK24A04T@SOIC8 [SA602A]  
PTK24A08T@SOIC8 [SA602A]  
PTK24A16T@SOIC8 [SA602A]

## POWERFLASH

### E (E) PROM/FRAM/NVRAM

ASU1GA30HT@TSOP48 [SB247-B4806]

## POWER-RAIL

### MICROCONTROLLER

MP01002  
MP01006  
MP01010  
MP3004@LQFP64  
MP3004@QFP64  
MP6016X

MP01004  
MP01008  
MP3004@LQFP48  
MP3004@QFP32  
MP3004@SSOP28  
MP6116X

## PSS

### E (E) PROM/FRAM/NVRAM

PS24C256

PS24C256@SOIC8 [SA602A]

## PTC

### E (E) PROM/FRAM/NVRAM

PT28C020  
PT28C040  
PT29C020

PT28C020@PLCC32 [SA015A1T]  
PT28C040@PLCC32 [SA015A1T]  
PT29C020@PLCC32 [SA015A1T]

PT29C040

PT29C040@PLCC32 [SA015A1T]

## MICROCONTROLLER

PT8936

PT8936@TQFP44 [SA675-B4805]

PT8956@PLCC44 [SA244]

PT8936@PLCC44 [SA244]

PT8956

PT8956@TQFP44 [SA675-B4805]

## QISDA-CUSTOMER

### E (E) PROM/FRAM/NVRAM

AT24C32C

RM24C32C

BR24S32

## QIXIN

### MICROCONTROLLER

LS2051

LS4051

LS2051@SOIC20 [SA023A]

LS4051@SOIC20 [SA023A]

## QP semiconductor

### E (E) PROM/FRAM/NVRAM

QP7C271

QP7C271@PLCC32 [SA015A1T]

## Quick Pulse

### E (E) PROM/FRAM/NVRAM

27010

27040

27210

27512

27011

27128A

27256

2764A

## RAMTRON

### E (E) PROM/FRAM/NVRAM

FM1208

FM1608

FM1608B

FM16W08

FM1808

FM1808B

FM18L08

FM18W08

FM1208@SOIC24 [SA404]

FM1608@SOIC28 [SA404]

FM1608B@SOIC28 [SA404]

FM16W08@SOIC28 [SA404]

FM1808@SOIC28 [SA404]

FM1808B@SOIC28 [SA404]

FM18L08@SOIC28 [SA404]

FM18W08@SOIC28 [SA404]

FM20L08@TSOP32 [\$\$\$\$\$\$]  
 FM24164@SOIC8 [SA602A]  
 FM24C04 (S)@SOP8 [SA602A]  
 FM24C04A (S)@SOP8 [SA602A]  
 FM24C04C@SOIC8 [SA602A]  
 FM24C08A@SOP8 [SA602A]  
 FM24C16 (S)@SOP8 [SA602A]  
 FM24C16A (S)@SOP8 [SA602A]  
 FM24C16C@SOIC8 [SA602A]  
 FM24C512@SOIC8 [SA605B]  
 FM24C64@SOIC8 [SA602A]  
 FM24C64C@SOIC8 [SA602A]  
 FM24CL04@SOIC8 [SA602A]  
 FM24CL16  
 FM24CL16B@SOIC8 [SA602A]  
 FM24CL64@SOIC8 [SA602A]  
 FM24CL64B-GA@SOIC8 [SA602A]  
 FM24V02@SOIC8 [SA602A]  
 FM24V10@SOIC8 [SA602A]  
 FM24VN02@SOIC8 [SA602A]  
 FM24W256@SOIC8 (200mil) [SA605B]  
 FM25040@SOIC8 [SA602A]  
 FM25160  
 FM25640  
 FM25640B  
 FM25C160  
 FM25CL04@SOIC8 [SA602A]  
 FM25CL64@SOIC8 [SA602A]  
 FM25CL64B@TDFN8 [SA683]  
 FM25H20@SOIC8 [SA602A]  
 FM25L04B@SOIC8 [SA602A]  
 FM25L16@SOIC8 [SA602A]  
 FM25L256@SOIC8 [SA602A]  
 FM25L256B  
 FM25L256B@TDFN8  
 FM25L512@SOIC8 [SA602A]  
 FM25P16@SOIC8 [SA602A]  
 FM25V02@SOIC8 [SA602A]  
 FM25V05@SOIC8 [SA602A]  
 FM25V20@SOIC8 [SA602A]  
 FM25W256@SOIC8 [SA602A]  
 FM28V020@TSOP32 [\$\$\$\$\$\$]  
 FM28V200@TSOP32 [\$\$\$\$\$\$]  
 FM3104@SOIC14 [SA602]  
 FM31256@SOIC14 [SA602]  
 FM31L278@SOIC14 [SA602]  
 FM33256B@SOIC14 [SA602A]  
 FM3808@TSOP32 [SA620-B4807]

FM24164  
 FM24C04 (P)  
 FM24C04A (P)  
 FM24C04B@SOIC8 [SA602A]  
 FM24C08A  
 FM24C16 (P)  
 FM24C16A (P)  
 FM24C16B@SOIC8 [SA602A]  
 FM24C256@SOIC8 [SA602A]  
 FM24C64  
 FM24C64B@SOIC8 [SA602A]  
 FM24CL04  
 FM24CL04B@SOIC8 [SA602A]  
 FM24CL16@SOIC8 [SA602A]  
 FM24CL16B@TDFN8  
 FM24CL64B@SOIC8 [SA602A]  
 FM24V01@SOIC8 [SA602A]  
 FM24V05@SOIC8 [SA605B]  
 FM24VN01@SOIC8 [SA602A]  
 FM24W256@SOIC8 (150mil) [SA602A]  
 FM25040  
 FM25040B@SOIC8 [SA602A]  
 FM25160@SOIC8 [SA602A]  
 FM25640@SOIC8 [SA602]  
 FM25640B@SOIC8 [SA602]  
 FM25C160@SOIC8 [SA602A]  
 FM25CL64  
 FM25CL64B@SOIC8 [SA602A]  
 FM25E64@SOIC8 [SA602A]  
 FM25H20@TDFN8  
 FM25L16  
 FM25L256  
 FM25L256@TDFN8  
 FM25L256B@SOIC8 [SA602A]  
 FM25L512  
 FM25LX64@SOIC8 [SA602A]  
 FM25V01@SOIC8 [SA602A]  
 FM25V02@TDFN8  
 FM25V10@SOIC8 [SA602A]  
 FM25V20@TDFN8 [SA683]  
 FM28V020@SOIC28 [SA404]  
 FM28V100@TSOP32 [\$\$\$\$\$\$]  
 FM30C256@SOIC20 [SA404]  
 FM3116@SOIC14 [SA602]  
 FM3164@SOIC14 [SA602]  
 FM33256B  
 FM3808

## MICROCONTROLLER

VMX51C900

VMX51C900@PLCC44 [SA244]

VMX51C900@TQFP44 [SA245A-B4805]	VRS1000
VRS1000@PLCC44 [SA244]	VRS1000@TQFP44 [SA245A-B4805]
VRS1100	VRS1100@PLCC44 [SA244]
VRS1100@TQFP44 [SA245A-B4805]	VRS51C1000
VRS51C1000@PLCC44 [SA244]	VRS51C1000@TQFP44 [SA245A-B4805]
VRS51C1100	VRS51C1100@PLCC44 [SA244]
VRS51C1100@TQFP44 [SA245A-B4805]	VRS51C540
VRS51C540@PLCC44 [SA244]	VRS51C540@TQFP44 [SA245A-B4805]
VRS51C550	VRS51C550@PLCC44 [SA244]
VRS51C550@TQFP44 [SA245A-B4805]	VRS51C560
VRS51C560@PLCC44 [SA244]	VRS51C560@TQFP44 [SA245A-B4805]
VRS51C570	VRS51C570@PLCC44 [SA244]
VRS51C570@TQFP44 [SA245A-B4805]	VRS51C580
VRS51C580@PLCC44 [SA244]	VRS51C580@TQFP44 [SA245A-B4805]
VRS51C700	VRS51C700@PLCC44 [SA244]
VRS51C700@TQFP44 [SA245A-B4805]	VRS51L1050
VRS51L1050@PLCC44 [SA244]	VRS51L1050@TQFP44 [SA245A-B4805]
VRS51L540	VRS51L540@PLCC44 [SA244]
VRS51L540@TQFP44 [SA245A-B4805]	VRS51L550
VRS51L550@PLCC44 [SA244]	VRS51L550@TQFP44 [SA245A-B4805]
VRS51L560	VRS51L560@PLCC44 [SA244]
VRS51L560@TQFP44 [SA245A-B4805]	VRS51L570
VRS51L570@PLCC44 [SA244]	VRS51L570@TQFP44 [SA245A-B4805]
VRS51L580	VRS51L580@PLCC44 [SA244]
VRS51L580@TQFP44 [SA245A-B4805]	VRS51X540
VRS51X540@PLCC44 [SA244]	VRS51X540@TQFP44 [SA245A-B4805]
VRS51X550	VRS51X550@PLCC44 [SA244]
VRS51X550@TQFP44 [SA245A-B4805]	VRS51X560
VRS51X560@PLCC44 [SA244]	VRS51X560@TQFP44 [SA245A-B4805]
VRS51X570	VRS51X570@PLCC44 [SA244]
VRS51X570@TQFP44 [SA245A-B4805]	VRS51X580
VRS51X580@PLCC44 [SA244]	VRS51X580@TQFP44 [SA245A-B4805]
VRS540	VRS540@PLCC44 [SA244]
VRS540@TQFP44 [SA245A-B4805]	VRS550
VRS550@PLCC44 [SA244]	VRS550@TQFP44 [SA245A-B4805]
VRS560	VRS560@PLCC44 [SA244]
VRS560@TQFP44 [SA245A-B4805]	VRS570
VRS570@PLCC44 [SA244]	VRS570@TQFP44 [SA245A-B4805]
VRS580	VRS580@PLCC44 [SA244]
VRS580@TQFP44 [SA245A-B4805]	VRS700
VRS700@PLCC44 [SA244]	VRS700@TQFP44 [SA245A-B4805]
VRS900	VRS900@PLCC44 [SA244]
VRS900@TQFP44 [SA245A-B4805]	

## RATO

### E (E) PROM/FRAM/NVRAM

RT24A02	RT24A02@SOIC8 [SA602A]
RT24A02@TSSOP8 [SA643]	RT24A04
RT24A04@SOIC8 [SA602A]	RT24A04@TSSOP8 [SA643]
RT24A08	RT24A08@SOIC8 [SA602A]

RT24A08@TSSOP8 [SA643]  
RT24A16@SOIC8 [SA602A]  
RT93C46B(16bit)  
RT93C46B(16bit)@TSSOP8 [SA643]  
RT93LC46(08bit)@SOIC8 [SA602A]  
RT93LC46(16bit)  
RT93LC46(16bit)@TSSOP8 [SA643]

RT24A16  
RT24A16@TSSOP8 [SA643]  
RT93C46B(16bit)@SOIC8 [SA602A]  
RT93LC46(08bit)  
RT93LC46(08bit)@TSSOP8 [SA643]  
RT93LC46(16bit)@SOIC8 [SA602A]

## RAYDIUM

### E (E) PROM/FRAM/NVRAM

RM24C02@SOP8 [SA602A]  
RM24C08@SOP8 [SA602A]  
RM24C16@SOP8 [SA602A]  
RM24C64@SOP8 [SA602A]

RM24C04@SOP8 [SA602A]  
RM24C128@SOP8 [SA602A]  
RM24C32@SOP8 [SA602A]

## REALTEK

### MICROCONTROLLER

RTD2120L@LQFP48 [SA248-B4804]

RTD2120L@PLCC44 [SA244]

## RENESAS

### E (E) PROM/FRAM/NVRAM

HN58C256A (FP)@SOP28 [SA404]  
HN58C256A (T)@TSOP28 [SA430T-B4003]  
HN58C257A (T)@TSOP32 [SA620-B4807]  
HN58V24256  
HN58V24256@TSSOP14 [SA026]  
HN58V24512@SOIC8 [SA602A]  
HN58W241000@SOIC8 [SA602A]  
HN58X2402@SOIC8 [SA602A]  
HN58X2404  
HN58X2404@TSSOP8 [SA643]  
HN58X2408@SOIC8 [SA602A]  
HN58X24128  
HN58X2416  
HN58X2416@TSSOP8 [SA643]  
HN58X24256@SOIC8 [SA602A]  
HN58X2432@SOIC8 [SA602A]  
HN58X24512  
HN58X2464  
HN58X2464@TSSOP8 [SA643]  
HN58X2502@TSSOP8 [SA643]  
HN58X2504@TSSOP8 [SA643]  
HN58X2508@TSSOP8 [SA643]  
HN58X25128@TSSOP14 [SA026]  
HN58X2516@TSSOP8 [SA643]

HN58C256A (P)  
HN58V24256@SOIC8 [SA602A]  
HN58V24512  
HN58W241000  
HN58X2402  
HN58X2402@TSSOP8 [SA643]  
HN58X2404@SOIC8 [SA602A]  
HN58X2408  
HN58X2408@TSSOP8 [SA643]  
HN58X24128@SOIC8 [SA602A]  
HN58X2416@SOIC8 [SA602A]  
HN58X24256  
HN58X2432  
HN58X2432@TSSOP8 [SA643]  
HN58X24512@SOIC8 [SA602A]  
HN58X2464@SOIC8 [SA602A]  
HN58X2502@SOIC8 [SA602A]  
HN58X2504@SOIC8 [SA602A]  
HN58X2508@SOIC8 [SA602A]  
HN58X25128@SOIC8 [SA602A]  
HN58X2516@SOIC8 [SA602A]  
HN58X25256@SOIC8 [SA602A]

HN58X25256@TSSOP14 [SA026]	HN58X2532@SOIC8 [SA602A]
HN58X2532@TSSOP8 [SA643]	HN58X2564@SOIC8 [SA602A]
HN58X2564@TSSOP8 [SA643]	M5L2732
M5L2732A	
M5M29KB331 (AVP)@TSOP48 [SB247-B4806]	
M5M29KB641 (AVP)@TSOP48 [SB247-B4806]	
M5M29KE131BV@TSOP48 [SB247-B4806]	
M5M29KT331 (AVP)@TSOP48 [SB247-B4806]	
M5M29KT641 (AVP)@TSOP48 [SB247-B4806]	
R1EX24002A@SOP8 [SA602A]	R1EX24002A@TSSOP8 [SA643]
R1EX24004A@SOP8 [SA602A]	R1EX24004A@TSSOP8 [SA643]
R1EX24008A@SOP8 [SA602A]	R1EX24008A@TSSOP8 [SA643]
R1EX24016A@SOP8 [SA602A]	R1EX24016A@TSSOP8 [SA643]
R1EX24032A@SOP8 [SA602A]	R1EX24032A@TSSOP8 [SA643]
R1EX24064A@SOP8 [SA602A]	R1EX24064A@TSSOP8 [SA643]
R1EX24128A@SOP8 [SA602A]	R1EX24128A@TSSOP8 [SA643]
R1EX24256A@SOP8 [SA602A]	R1EX24256A@TSSOP8 [SA643]
R1EX24512A@SOP8 [SA602A]	R1EX24512A@TSSOP8 [SA643]
R1EX25002A@SOIC8 [SA602A]	R1EX25002A@TSSOP8 [SA643]
R1EX25004A@SOIC8 [SA602A]	R1EX25004A@TSSOP8 [SA643]
R1EX25008A@SOIC8 [SA602A]	R1EX25008A@TSSOP8 [SA643]
R1EX25016A@SOIC8 [SA602A]	R1EX25016A@TSSOP8 [SA643]
R1EX25032A@SOIC8 [SA602A]	R1EX25032A@TSSOP8 [SA643]
R1EX25064A@SOIC8 [SA602A]	R1EX25064A@TSSOP8 [SA643]

## DRAM & SRAM

R1LV0408C@SOP32 [SA687]	R1LV0408C@STSOP32 [SA620-B4807]
R1LV0408C@TSOP32 [SA410T-B4001]	

## MICROCONTROLLER

M30260F3AGP@QFP48 [SA248-B4804]	M30260F3TGP@QFP48 [SA248-B4804]
M30260F3VGP@QFP48 [SA248-B4804]	M30260F6AGP@QFP48 [SA248-B4804]
M30260F6TGP@QFP48 [SA248-B4804]	M30260F6VGP@QFP48 [SA248-B4804]
M30260F8AGP@QFP48 [SA248-B4804]	M30260F8TGP@QFP48 [SA248-B4804]
M30260F8VGP@QFP48 [SA248-B4804]	M30262F3GP@QFP48 [SA248-B4804]
M30262F4GP@QFP48 [SA248-B4804]	M30262F6GP@QFP48 [SA248-B4804]
M30262F8GP@QFP48 [SA248-B4804]	M30263F3AFP@SSOP42 [SA775]
M30263F6AFP@SSOP42 [SA775]	M30263F8AFP@SSOP42 [SA775]

## RICOH

### E (E) PROM/FRAM/NVRAM

RD27C256	RD27C32
RD27C64	

## ROCKWELL

## E (E) PROM/FRAM/NVRAM

R2764  
R2764P  
R2816

R2764C  
R27C64

## ROHM

### E (E) PROM/FRAM/NVRAM

BH9020 [SA602A]  
BR24A01A (FJ) [\$\$\$\$\$\$]  
BR24A02 (FJ) [\$\$\$\$\$\$]  
BR24A04 (FJ) [\$\$\$\$\$\$]  
BR24A08 (FJ) [\$\$\$\$\$\$]  
BR24A16 (FJ) [\$\$\$\$\$\$]  
BR24A32 (FJ) [\$\$\$\$\$\$]  
BR24A64 (FJ) [\$\$\$\$\$\$]  
BR24C01@TSSOP8 [SA643]  
BR24C01A  
BR24C01A (FJ) [\$\$\$\$\$\$]  
BR24C02  
BR24C02 (FJ) [\$\$\$\$\$\$]  
BR24C02@SOP8 [\$\$\$\$\$\$]  
BR24C02@TSSOP8 (3\*3mm) [SA666]  
BR24C04 (F) [\$\$\$\$\$\$]  
BR24C04 (FV) [SA643]  
BR24C04@TSSOP8 [SA643]  
BR24C08  
BR24C08 (FJ) [\$\$\$\$\$\$]  
BR24C08@SOP8 [\$\$\$\$\$\$]  
BR24C08@TSSOP8 (3\*3mm) [SA666]  
BR24C16 (F) [\$\$\$\$\$\$]  
BR24C16 (FV) [SA643]  
BR24C21 (F) [\$\$\$\$\$\$]  
BR24C21 (FV) [SA643]  
BR24C32 (F) [\$\$\$\$\$\$]  
BR24C64 (F) [\$\$\$\$\$\$]  
BR24E16 (F) [\$\$\$\$\$\$]  
BR24E16 (FV) [SA643]  
BR24G01 (F) [\$\$\$\$\$\$]  
BR24G01 (FV) [SA643]  
BR24G02 (F) [\$\$\$\$\$\$]  
BR24G02 (FV) [SA643]  
BR24G04 (F) [\$\$\$\$\$\$]  
BR24G04 (FV) [SA643]  
BR24G08 (FJ) [\$\$\$\$\$\$]  
BR24G08 (FVJ) [SA643]  
BR24G08 (FVT) [SA643]  
BR24G128 (F) [\$\$\$\$\$\$]  
BR24G128 (FV) [SA643]  
BR24G16

BR24A01A (F) [\$\$\$\$\$\$]  
BR24A02 (F) [\$\$\$\$\$\$]  
BR24A04 (F) [\$\$\$\$\$\$]  
BR24A08 (F) [\$\$\$\$\$\$]  
BR24A16 (F) [\$\$\$\$\$\$]  
BR24A32 (F) [\$\$\$\$\$\$]  
BR24A64 (F) [\$\$\$\$\$\$]  
BR24C01@SOP8 [\$\$\$\$\$\$]  
BR24C01@TSSOP8 (3\*3mm) [SA666]  
BR24C01A (F) [\$\$\$\$\$\$]  
BR24C01A (FV) [SA643]  
BR24C02 (F) [\$\$\$\$\$\$]  
BR24C02 (FV) [SA643]  
BR24C02@TSSOP8 [SA643]  
BR24C04  
BR24C04 (FJ) [\$\$\$\$\$\$]  
BR24C04@SOP8 [\$\$\$\$\$\$]  
BR24C04@TSSOP8 (3\*3mm) [SA666]  
BR24C08 (F) [\$\$\$\$\$\$]  
BR24C08 (FV) [SA643]  
BR24C08@TSSOP8 [SA643]  
BR24C16  
BR24C16 (FJ) [\$\$\$\$\$\$]  
BR24C21  
BR24C21 (FJ) [\$\$\$\$\$\$]  
BR24C32  
BR24C64  
BR24E16  
BR24E16 (FJ) [\$\$\$\$\$\$]  
BR24G01  
BR24G01 (FJ) [\$\$\$\$\$\$]  
BR24G02  
BR24G02 (FJ) [\$\$\$\$\$\$]  
BR24G04  
BR24G04 (FJ) [\$\$\$\$\$\$]  
BR24G08 (F) [\$\$\$\$\$\$]  
BR24G08 (FV) [SA643]  
BR24G08 (FVM) [SA666]  
BR24G128  
BR24G128 (FJ) [\$\$\$\$\$\$]  
BR24G128 (FVT) [SA643]  
BR24G16 (F) [\$\$\$\$\$\$]

BR24G16 (FJ) [\$\$\$\$\$\$]  
BR24G16 (FVM) [SA666]  
BR24G256 (F) [\$\$\$\$\$\$]  
BR24G256 (FV) [SA643]  
BR24G32  
BR24G32 (FJ) [\$\$\$\$\$\$]  
BR24G32 (FVT) [SA643]  
BR24G64 (F) [\$\$\$\$\$\$]  
BR24G64 (FV) [SA643]  
BR24L01A  
BR24L01A (FJ) [\$\$\$\$\$\$]  
BR24L01A (FVM) [SA666]  
BR24L02  
BR24L02 (FJ) [\$\$\$\$\$\$]  
BR24L02 (FVM) [SA666]  
BR24L04  
BR24L04 (FJ) [\$\$\$\$\$\$]  
BR24L04 (FVM) [SA666]  
BR24L08  
BR24L08 (FJ) [\$\$\$\$\$\$]  
BR24L08 (FVM) [SA666]  
BR24L16  
BR24L16 (FJ) [\$\$\$\$\$\$]  
BR24L16 (FVM) [SA666]  
BR24L32 (F) [\$\$\$\$\$\$]  
BR24L32 (FV) [SA643]  
BR24L64 (F) [\$\$\$\$\$\$]  
BR24L64 (FV) [SA643]  
BR24S08 (FJ) [\$\$\$\$\$\$]  
BR24S08 (FVJ) [SA643]  
BR24S08 (FVT) [SA643]  
BR24S128 (F) [\$\$\$\$\$\$]  
BR24S128 (FV) [SA643]  
BR24S16 (F) [\$\$\$\$\$\$]  
BR24S16 (FV) [SA643]  
BR24S256  
BR24S256 (FJ) [\$\$\$\$\$\$]  
BR24S32  
BR24S32 (FJ) [\$\$\$\$\$\$]  
BR24S64  
BR24S64 (FJ) [\$\$\$\$\$\$]  
BR24T01  
BR24T01 (FJ) [\$\$\$\$\$\$]  
BR24T02  
BR24T02 (FJ) [\$\$\$\$\$\$]  
BR24T02@VSON8 [SA724]  
BR24T04 (F) [\$\$\$\$\$\$]  
BR24T04 (FV) [SA643]  
BR24T08 (FJ) [\$\$\$\$\$\$]  
BR24T08 (FVJ) [SA643]  
BR24T08 (FVT) [SA643]  
BR24T128 (F) [\$\$\$\$\$\$]  
BR24T128 (FV) [SA643]

BR24G16 (FV) [SA643]  
BR24G256  
BR24G256 (FJ) [\$\$\$\$\$\$]  
BR24G256 (FVT) [SA643]  
BR24G32 (F) [\$\$\$\$\$\$]  
BR24G32 (FV) [SA643]  
BR24G64  
BR24G64 (FJ) [\$\$\$\$\$\$]  
BR24G64 (FVT) [SA643]  
BR24L01A (F) [\$\$\$\$\$\$]  
BR24L01A (FV) [SA643]  
BR24L01A@VSON8 [SA724]  
BR24L02 (F) [\$\$\$\$\$\$]  
BR24L02 (FV) [SA643]  
BR24L02@VSON8 [SA724]  
BR24L04 (F) [\$\$\$\$\$\$]  
BR24L04 (FV) [SA643]  
BR24L04@VSON8 [SA724]  
BR24L08 (F) [\$\$\$\$\$\$]  
BR24L08 (FV) [SA643]  
BR24L08@VSON8 [SA724]  
BR24L16 (F) [\$\$\$\$\$\$]  
BR24L16 (FV) [SA643]  
BR24L32  
BR24L32 (FJ) [\$\$\$\$\$\$]  
BR24L64  
BR24L64 (FJ) [\$\$\$\$\$\$]  
BR24S08 (F) [\$\$\$\$\$\$]  
BR24S08 (FV) [SA643]  
BR24S08 (FVM) [SA666]  
BR24S128  
BR24S128 (FJ) [\$\$\$\$\$\$]  
BR24S16  
BR24S16 (FJ) [\$\$\$\$\$\$]  
BR24S16 (FVM) [SA666]  
BR24S256 (F) [\$\$\$\$\$\$]  
BR24S256 (FV) [SA643]  
BR24S32 (F) [\$\$\$\$\$\$]  
BR24S32 (FV) [SA643]  
BR24S64 (F) [\$\$\$\$\$\$]  
BR24S64 (FV) [SA643]  
BR24T01 (F) [\$\$\$\$\$\$]  
BR24T01 (FV) [SA643]  
BR24T02 (F) [\$\$\$\$\$\$]  
BR24T02 (FV) [SA643]  
BR24T04  
BR24T04 (FJ) [\$\$\$\$\$\$]  
BR24T08 (F) [\$\$\$\$\$\$]  
BR24T08 (FV) [SA643]  
BR24T08 (FVM) [SA666]  
BR24T128  
BR24T128 (FJ) [\$\$\$\$\$\$]  
BR24T128 (FVT) [SA643]

BR24T16  
BR24T16 (FJ) [SA602A]  
BR24T16 (FVM) [SA666]  
BR24T1M  
BR24T256  
BR24T256 (FJ) [\$\$\$\$\$]  
BR24T256 (FVT) [SA643]  
BR24T32 (F) [\$\$\$\$\$]  
BR24T32 (FV) [SA643]  
BR24T32@VSON8 [SA724]  
BR24T512 (F) [SA602A@90]  
BR24T512 (FV) [SA643]  
BR24T64  
BR24T64 (FJ) [\$\$\$\$\$]  
BR24T64 (FVT) [SA643]  
BR25010@TSSOP8 [SA643]  
BR25020@TSSOP8 [SA643]  
BR25040@TSSOP8 [SA643]  
BR25080@TSSOP8 [SA643]  
BR25160@TSSOP8 [SA643]  
BR25H010 (F) [SA602A]  
BR25H020 (F) [SA602A]  
BR25H040 (F) [SA602A]  
BR25H080 (F) [SA602A]  
BR25H080 (FVT) [SA643]  
BR25H160 (FJ) [SA602A]  
BR25H320 (F) [SA602A]  
BR25H320 (FVT) [SA643]  
BR25L010 (F) [SA602A]  
BR25L010 (FV) [SA643]  
BR25L020  
BR25L020 (FJ) [SA602A]  
BR25L020 (FVM) [SA666]  
BR25L040 (F) [SA602A]  
BR25L040 (FV) [SA643]  
BR25L080  
BR25L080 (FJ) [SA602A]  
BR25L160  
BR25L160 (FJ) [SA602A]  
BR25L320  
BR25L320 (FJ) [SA602A]  
BR25L640  
BR25L640 (FJ) [SA602A]  
BR25S128F [\$\$\$\$\$]  
BR25S128FV [SA643]  
BR25S256F [\$\$\$\$\$]  
BR25S320F [\$\$\$\$\$]  
BR25S320FV [SA643]  
BR25S320FVM [SA666]  
BR25S320NUX [SA724]  
BR25S640FJ [SA602A]  
BR25S640FVJ [SA666]  
BR25S640FVT [SA643]

BR24T16 (F) [\$\$\$\$\$]  
BR24T16 (FV) [SA643]  
BR24T16@VSON8 [SA724]  
BR24T1MF [SA605B]  
BR24T256 (F) [\$\$\$\$\$]  
BR24T256 (FV) [SA643]  
BR24T32  
BR24T32 (FJ) [\$\$\$\$\$]  
BR24T32 (FVT) [SA643]  
BR24T512  
BR24T512 (FJ) [\$\$\$\$\$]  
BR24T512 (FVT) [SA643]  
BR24T64 (F) [\$\$\$\$\$]  
BR24T64 (FV) [SA643]  
BR25010@SOIC8 [SA602A]  
BR25020@SOIC8 [SA602A]  
BR25040@SOIC8 [SA602A]  
BR25080@SOIC8 [SA602A]  
BR25160@SOIC8 [SA602A]  
BR25320@SOIC8 [SA602A]  
BR25H010 (FJ) [SA602A]  
BR25H020 (FJ) [SA602A]  
BR25H040 (FJ) [SA602A]  
BR25H080 (FJ) [SA602A]  
BR25H160 (F) [SA602A]  
BR25H160 (FVT) [SA643]  
BR25H320 (FJ) [SA602A]  
BR25L010  
BR25L010 (FJ) [SA602A]  
BR25L010 (FVM) [SA666]  
BR25L020 (F) [SA602A]  
BR25L020 (FV) [SA643]  
BR25L040  
BR25L040 (FJ) [SA602A]  
BR25L040 (FVM) [SA666]  
BR25L080 (F) [SA602A]  
BR25L080 (FV) [SA643]  
BR25L160 (F) [SA602A]  
BR25L160 (FV) [SA643]  
BR25L320 (F) [SA602A]  
BR25L320 (FV) [SA643]  
BR25L640 (F) [SA602A]  
BR25L640 (FV) [SA643]  
BR25S128FJ [SA602A]  
BR25S128FVT [SA643]  
BR25S256FJ [SA602A]  
BR25S320FJ [SA602A]  
BR25S320FVJ [SA666]  
BR25S320FVT [SA643]  
BR25S640F [\$\$\$\$\$]  
BR25S640FV [SA643]  
BR25S640FVM [SA666]  
BR34C02A [SA643]

BR34L02  
BR34L02 (FJ) [SA602A]  
BR34L02 (FVM) [SA666]  
BR35H010FJ [SA602A]  
BR35H020FJ [SA602A]  
BR35H040FJ [SA602A]  
BR35H080FJ [SA602A]  
BR35H128F [\$\$\$\$\$]  
BR35H160F [\$\$\$\$\$]  
BR35H160FVM [SA666]  
BR35H320F [\$\$\$\$\$]  
BR35H320FVM [SA666]  
BR35H640F [\$\$\$\$\$]  
BR35H640FVT [SA643]  
BR9010 (F) [SA602A]  
BR9010 (RFV) [SA643]  
BR9016  
BR9016 (RFV) [SA643]  
BR9016A (RFV) [SA643]  
BR9020  
BR9020 (FV) [SA643]  
BR9020 (RFVM) [SA666]  
BR9040 (F) [SA602A]  
BR9040 (RFV) [SA643]  
BR9080  
BR9080 (RFV) [SA643]  
BR9080A (F) [SA602A]  
BR9080A (RFV) [SA643]  
BR93A46 (F) [SA602A]  
BR93A46 (RF) [SA602A]  
BR93A56 (F) [SA602A]  
BR93A56 (RF) [SA602A]  
BR93A66 (F) [SA602A]  
BR93A66 (RF) [SA602A]  
BR93A76 (F) [SA602A]  
BR93A76 (RF) [SA602A]  
BR93A86 (F) [SA602A]  
BR93A86 (RF) [SA602A]  
BR93C46  
BR93C46 (FJ) [SA602A]  
BR93C46 (RF) [SA602A]  
BR93C56  
BR93C56 (FJ) [SA602A]  
BR93C56 (RF) [SA602A]  
BR93C66  
BR93C66 (FJ) [SA602A]  
BR93C66 (RF) [SA602A]  
BR93H46 (RF) [SA605B]  
BR93H56 (RF) [SA605B]  
BR93H66 (RF) [SA605B]  
BR93H76 (RF) [SA605B]  
BR93H86 (RF) [SA605B]  
BR93L46

BR34L02 (F) [SA602A]  
BR34L02 (FV) [SA643]  
BR35H010F [\$\$\$\$\$]  
BR35H020F [\$\$\$\$\$]  
BR35H040F [\$\$\$\$\$]  
BR35H080F [\$\$\$\$\$]  
BR35H080FVT [SA643]  
BR35H128FJ [SA602A]  
BR35H160FJ [SA602A]  
BR35H160FVT [SA643]  
BR35H320FJ [SA602A]  
BR35H320FVT [SA643]  
BR35H640FJ [SA602A]  
BR9010  
BR9010 (FV) [SA643]  
BR9010 (RFVM) [SA666]  
BR9016 (F) [SA602A]  
BR9016A (F) [SA602A]  
BR9016A (RFVM) [SA666]  
BR9020 (F) [SA602A]  
BR9020 (RFV) [SA643]  
BR9040  
BR9040 (FV) [SA643]  
BR9040 (RFVM) [SA666]  
BR9080 (F) [SA602A]  
BR9080A  
BR9080A (FV) [SA643]  
BR9080A (RFVM) [SA666]  
BR93A46 (FJ) [SA602A]  
BR93A46 (RFJ) [SA602A]  
BR93A56 (FJ) [SA602A]  
BR93A56 (RFJ) [SA602A]  
BR93A66 (FJ) [SA602A]  
BR93A66 (RFJ) [SA602A]  
BR93A76 (FJ) [SA602A]  
BR93A76 (RFJ) [SA602A]  
BR93A86 (FJ) [SA602A]  
BR93A86 (RFJ) [SA602A]  
BR93C46 (F) [SA602A]  
BR93C46 (FV) [SA643]  
BR93C46 (RFJ) [SA602A]  
BR93C56 (F) [SA602A]  
BR93C56 (FV) [SA643]  
BR93C56 (RFJ) [SA602A]  
BR93C66 (F) [SA602A]  
BR93C66 (FV) [SA643]  
BR93C66 (RFJ) [SA602A]  
BR93H46 (RFJ) [SA605B]  
BR93H56 (RFJ) [SA605B]  
BR93H66 (RFJ) [SA605B]  
BR93H76 (RFJ) [SA605B]  
BR93H86 (RFJ) [SA605B]  
BR93L46 (F) [SA602A]

BR93L46 (FJ) [SA602A]	BR93L46 (FV) [SA643]
BR93L46 (RF) [SA602A]	BR93L46 (RFJ) [SA602A]
BR93L56	BR93L56 (F) [SA602A]
BR93L56 (FJ) [SA602A]	BR93L56 (FV) [SA643]
BR93L56 (RF) [SA602A]	BR93L56 (RFJ) [SA602A]
BR93L66	BR93L66 (F) [SA602A]
BR93L66 (FJ) [SA602A]	BR93L66 (FV) [SA643]
BR93L66 (RF) [SA602A]	BR93L66 (RFJ) [SA602A]
BR93L76 (F) [SA602A]	BR93L76 (FJ) [SA602A]
BR93L76 (RF) [SA602A]	BR93L76 (RFJ) [SA602A]
BR93L76 (RFV) [SA643]	BR93L76 (RFVJ) [SA666]
BR93L76 (RFVM) [SA666]	BR93L76 (RFVT) [SA643]
BR93L86 (F) [SA602A]	BR93L86 (FJ) [SA602A]
BR93L86 (RF) [SA602A]	BR93L86 (RFJ) [SA602A]
BR93L86 (RFV) [SA643]	BR93L86 (RFVJ) [SA666]
BR93L86 (RFVM) [SA666]	BR93L86 (RFVT) [SA643]
BR93LC46	BR93LC46 (F) [SA602A]
BR93LC46 (FJ) [SA602A]	BR93LC46 (FV) [SA643]
BR93LC46 (RF) [SA602A]	BR93LC46 (RFJ) [SA602A]
BR93LC56	BR93LC56 (F) [SA602A]
BR93LC56 (FJ) [SA602A]	BR93LC56 (FV) [SA643]
BR93LC56 (RF) [SA602A]	BR93LC56 (RFJ) [SA602A]
BR93LC66	BR93LC66 (F) [SA602A]
BR93LC66 (FJ) [SA602A]	BR93LC66 (FV) [SA643]
BR93LC66 (RF) [SA602A]	BR93LC66 (RFJ) [SA602A]
BR93LL46 (F) [SA602A]	BR93LL46 (FV) [SA643]
BR95010@SOP8 [SA602A]	BR95010@TSSOP8 [SA643]
BR95010@TSSOP8 (3*3) [SA666]	BR95020@SOP8 [SA602A]
BR95020@TSSOP8 [SA643]	BR95020@TSSOP8 (3*3) [SA666]
BR95040@SOP8 [SA602A]	BR95040@TSSOP8 [SA643]
BR95040@TSSOP8 (3*3) [SA666]	BR95080@SOP8 [SA602A]
BR95080@TSSOP8 [SA643]	BR95160@SOP8 [SA602A]
BR95160@TSSOP8 [SA643]	BR9877FV [SA643]
BRCA016GWZ-W	BU9829GUL-W
BU9832GUL-W	BU9833GUL-W
BU9844GUL-W	BU9847GUL-W
BU9880GUL-W	BU9888FV-W [SA643]
BU9889GUL-W	BU9890GUL-W
BU9891GUL-W	BU9897GUL-W
BU99901GUZ-W	

## SAIFUN

### E (E) PROM/FRAM/NVRAM

SA24C1024	SA24C1024@SOIC8 [SA602A]
SA24C512	SA24C512@SOIC8 [SA602A]
SA24C512@TSSOP8 [SA643]	SA25C020
SA25C020@MLF8 [SA683]	SA25C020@SOIC8 [SA602A]
SA25C040	SA25C040@MLF8 [SA683]
SA25C040@SOIC8 [SA602A]	SA25C080
SA25C080@MLF8 [SA683]	SA25C080@SOIC8 [SA602A]

SA25C1024 (H)  
SA25C1024 (H)@SOIC8 [SA602A]  
SA25C1024 (L)@CSP8 [SA683]  
SA25C512 (H)  
SA25C512 (H)@SOIC8 [SA602A]  
SA25C512 (L)@CSP8 [SA683]  
SA25F005  
SA25F005@SOIC8 [SA602A]  
SA25F010@MLF8 [SA683]  
SA25F020  
SA25F020@SOIC8 [SA602A]  
SA25F040@MLF8 [SA683]  
SA25F080  
SA25F080@SOIC8 [SA602A]  
SA25F160 (ISP)  
SA25F160@MLF8 (ISP)  
SA25F160@SOIC16 (ISP)

SA25C1024 (H)@CSP8 [SA683]  
SA25C1024 (L)  
SA25C1024 (L)@SOIC8 [SA602A]  
SA25C512 (H)@CSP8 [SA683]  
SA25C512 (L)  
SA25C512 (L)@SOIC8 [SA602A]  
SA25F005@MLF8 [SA683]  
SA25F010  
SA25F010@SOIC8 [SA602A]  
SA25F020@MLF8 [SA683]  
SA25F040  
SA25F040@SOIC8 [SA602A]  
SA25F080@MLF8 [SA683]  
SA25F160  
SA25F160@MLF8 [SA683]  
SA25F160@SOIC16 [SA602]

## SAMSUNG

### E (E) PROM/FRAM/NVRAM

K8D1616UBA@TSOP48 [SB247-B4806]	K8D1616UTA@TSOP48 [SB247-B4806]
K8D1716UBA@TSOP48 [SB247-B4806]	K8D1716UBC@TSOP48 [SB247-B4806]
K8D1716UTA@TSOP48 [SB247-B4806]	K8D1716UTC@TSOP48 [SB247-B4806]
K8D3216UBB@TSOP48 [SB247-B4806]	K8D3216UBC@TSOP48 [SB247-B4806]
K8D3216UBM@TSOP48 [SB247-B4806]	K8D3216UTB@TSOP48 [SB247-B4806]
K8D3216UTC@TSOP48 [SB247-B4806]	K8D3216UTM@TSOP48 [SB247-B4806]
K8D3216UTM@TSOP48 (new) [SB247-B4806]	
K8D3316UBC@TSOP48 [SB247-B4806]	K8D3316UBM@TSOP48 [SB247-B4806]
K8D3316UTC@TSOP48 [SB247-B4806]	K8D3316UTM@TSOP48 [SB247-B4806]
K8D6316UBM@TSOP48 [SB247-B4806]	K8D6316UTM@TSOP48 [SB247-B4806]
K8P3215UQB@TSOP48 [SB247-B4806]	K8P6415UQB@TSOP48 [SB247-B4806]
K9F1G08U0D@TSOP48 [SB247-B4806]	K9F1G08U0E@TSOP48 [SB247-B4806]
K9F2G08U0C@TSOP48 [SB247-B4806]	K9F4G08U0E@TSOP48 [SB247-B4806]
K9G4G08U0B@TSOP48 [SB247-B4806]	K9K8G08U0B@TSOP48 [SB247-B4806]
K9K8G08U0E@TSOP48 [SB247-B4806]	K9K8G08U0M@TSOP48 [SB247-B4806]
KM2816A	KM2816AI
KM2817A	KM2817AI
KM2864A	KM2864AH
KM2865A	KM2865AH
KM28C16	KM28C16@PLCC32 [SA015A1T]
KM28C16I	KM28C16I@PLCC32 [SA015A1T]
KM28C17	KM28C17@PLCC32 [SA015A1T]
KM28C17I	KM28C17I@PLCC32 [SA015A1T]
KM28C256	KM28C256@PLCC32 [SA015A1T]
KM28C256I	KM28C256I@PLCC32 [SA015A1T]
KM28C64	KM28C64@PLCC32 [SA015A1T]
KM28C64A	KM28C64A@PLCC32 [SA015A1T]
KM28C64B	KM28C64B@PLCC32 [SA015A1T]
KM28C64I	KM28C64I@PLCC32 [SA015A1T]
KM28C65	KM28C65@PLCC32 [SA015A1T]

KM28C65A  
KM28C65I  
KM93C06 (08bit)  
KM93C06 (G) (08bit)@SOIC8 [SA602A]  
KM93C06 (GD) (08bit)@SOIC8 [SA602A]  
KM93C06 (GD) (16bit)@SOIC8 [SA602A]  
KM93C07 (08bit)  
KM93C07 (G) (08bit)@SOIC8 [SA602A]  
KM93C07 (GD) (08bit)@SOIC8 [SA602A]  
KM93C07 (GD) (16bit)@SOIC8 [SA602A]  
KM93C46V  
KM93C46V (GD)@SOIC8 [SA602A]  
KM93C47V (G)@SOIC8 [SA602A]  
KM93C56V  
KM93C56V (GD)@SOIC8 [SA602A]  
KM93C57V (G)@SOIC8 [SA602A]  
KM93C66V  
KM93C66V (GD)@SOIC8 [SA602A]  
KM93C67V (G)@SOIC8 [SA602A]  
KS24C010  
KS24C010@TSSOP8 [SA643]  
KS24C011@SOIC8 [SA602A]  
KS24C020  
KS24C020@TSSOP8 [SA643]  
KS24C021@SOIC8 [SA602A]  
KS24C040  
KS24C040@TSSOP8 [SA643]  
KS24C041@SOIC8 [SA602A]  
KS24C080  
KS24C080@TSSOP8 [SA643]  
KS24C081@SOIC8 [SA602A]  
S524A40X10  
S524A40X10@TSSOP8 [SA643]  
S524A40X11@SOP8 [SA602A]  
S524A40X20  
S524A40X20@TSSOP8 [SA643]  
S524A40X21@SOP8 [SA602A]  
S524A40X40  
S524A40X40@TSSOP8 [SA643]  
S524A40X41@SOP8 [SA602A]  
S524A60X51  
S524A60X51@TSSOP8 [SA643]  
S524A60X81@SOP8 [SA602A]  
S524AB0X91  
S524AB0X91@TSSOP8 [SA643]  
S524AB0XB1@SOP8 [SA602A]  
S524AD0XD1  
S524AD0XD1@TSSOP8 [SA643]  
S524AD0XF1@SOP8 [SA602A]  
S524C20D11  
S524C20D11@TSSOP8 [SA643]  
S524C20D21@SOP8 [SA602A]  
S524C80D41  
KM28C65A@PLCC32 [SA015A1T]  
KM28C65I@PLCC32 [SA015A1T]  
KM93C06 (16bit)  
KM93C06 (G) (16bit)@SOIC8 [SA602A]  
KM93C07 (16bit)  
KM93C07 (G) (16bit)@SOIC8 [SA602A]  
KM93C46V (G)@SOIC8 [SA602A]  
KM93C47V  
KM93C47V (GD)@SOIC8 [SA602A]  
KM93C56V (G)@SOIC8 [SA602A]  
KM93C57V  
KM93C57V (GD)@SOIC8 [SA602A]  
KM93C66V (G)@SOIC8 [SA602A]  
KM93C67V  
KM93C67V (GD)@SOIC8 [SA602A]  
KS24C010@SOIC8 [SA602A]  
KS24C011  
KS24C011@TSSOP8 [SA643]  
KS24C020@SOIC8 [SA602A]  
KS24C021  
KS24C021@TSSOP8 [SA643]  
KS24C040@SOIC8 [SA602A]  
KS24C041  
KS24C041@TSSOP8 [SA643]  
KS24C080@SOIC8 [SA602A]  
KS24C081  
KS24C081@TSSOP8 [SA643]  
S524A40X10@SOP8 [SA602A]  
S524A40X11  
S524A40X11@TSSOP8 [SA643]  
S524A40X20@SOP8 [SA602A]  
S524A40X21  
S524A40X21@TSSOP8 [SA643]  
S524A40X40@SOP8 [SA602A]  
S524A40X41  
S524A40X41@TSSOP8 [SA643]  
S524A60X51@SOP8 [SA602A]  
S524A60X81  
S524A60X81@TSSOP8 [SA643]  
S524AB0X91@SOP8 [SA602A]  
S524AB0XB1  
S524AB0XB1@TSSOP8 [SA643]  
S524AD0XD1@SOP8 [SA602A]  
S524AD0XF1  
S524AD0XF1@TSSOP8 [SA643]  
S524C20D11@SOP8 [SA602A]  
S524C20D21  
S524C20D21@TSSOP8 [SA643]  
S524C80D41@SOP8 [SA602A]

S524C80D41@TSSOP8 [SA643]  
S524C80D81@SOP8 [SA602A]  
S524L50X51  
S524L50X51@TSSOP8 [SA643]  
S524LBOX91@SOP8 [SA602A]  
S524LBOXB1  
S524LBOXB1@TSSOP8 [SA643]

S524C80D81  
S524C80D81@TSSOP8 [SA643]  
S524L50X51@SOP8 [SA602A]  
S524LBOX91  
S524LBOX91@TSSOP8 [SA643]  
S524LBOXB1@SOP8 [SA602A]

## DRAM & SRAM

KM62256A  
KM62256AL  
KM6264A  
KM6264AL  
KM68257LP  
KM68257P  
KM6865LP  
KM6865P

KM62256A@SOIC28 [SA630]  
KM62256AL@SOIC28 [SA630]  
KM6264A@SOIC28 [SA630]  
KM6264AL@SOIC28 [SA630]  
KM68257LP@SOIC28 [SA630]  
KM68257P@SOIC28 [SA630]  
KM6865LP@SOIC28 [SA630]  
KM6865P@SOIC28 [SA630]

## PLD

CPL16L8  
CPL16L8L  
CPL16R4  
CPL16R4L  
CPL16R6  
CPL16R6L  
CPL16R8  
CPL16R8L

CPL16L8@PLCC20 [SA001A-B2001]  
CPL16L8L@PLCC20 [SA001A-B2001]  
CPL16R4@PLCC20 [SA001A-B2001]  
CPL16R4L@PLCC20 [SA001A-B2001]  
CPL16R6@PLCC20 [SA001A-B2001]  
CPL16R6L@PLCC20 [SA001A-B2001]  
CPL16R8@PLCC20 [SA001A-B2001]  
CPL16R8L@PLCC20 [SA001A-B2001]

## MICROCONTROLLER

S3F9444  
S3F9454(dip16)  
S3F9454@SOP20 [SA404]

S3F9444@SOP8 [SA602]  
S3F9454(dip20)  
S3F9454@SSOP20 [SA643]

## SANYO

### E (E) PROM/FRAM/NVRAM

LE24C041  
LE24C042  
LE24C081  
LE24C082  
LE24C161  
LE24C162  
LE24C322@MFP8 [SA654]  
LE24CB642M [SA605B]  
LE24L322@MFP8 [SA654]  
LE25FU106BTT@MSOP8 [SA654]

LE24C041@MFP8 [SA654]  
LE24C042@MFP8 [SA654]  
LE24C081@MFP8 [SA654]  
LE24C082@MFP8 [SA654]  
LE24C161@MFP8 [SA654]  
LE24C162@MFP8 [SA654]  
LE24C322@WLP6 [SA717]  
LE24CB642TT [SA602A]  
LE25FU106BMA@MFP8 [SA654]  
LE25FU406BMA@MFP8 [SA602A]

LE25FU406BTT@MSOP8 [SA654]                   LE25FU406C@SOP8 [SA602A]  
LE25FW056FN@VSON8 [SA683]                   LE25FW056MA@MFP8 [SA602A]  
LE25FW106M@SOP8 [SA602A]                   LE25FW106T@MSOP8 [SA654]  
LE25FW1606FN@VSON8 [SA683]                   LE25FW203ATT@MSOP8 [SA654]  
LE25FW206M@SOP8 [SA602A]                   LE25FW206T@MSOP8 [SA654]  
LE25FW406BMA@MFP8 [SA602A]                   LE25FW406BTT@MSOP8 [SA654]  
LE25FW406M@SOP8 [SA602A]                   LE25FW406T@MSOP8 [SA654]  
LE25FW806M@SOP8 [SA602A]                   LE25FW806T@MSOP8 [SA654]  
LE25U40C@SOP8 [SA602A]                   LE25U40C@USON8 [SA683]  
LE26CW006@WLP6 [SA717]                   LE28BW168T@TSOP48 [SA637B-B4806]  
LE28C1001AM@SOP32 [SA687]  
LE28C1001AT@TSOP32 [SA410T-B4001]  
LE28C1001ATS@VSOP32 [SA620-B4807]  
LE28C1001DT@TSOP32 [SA410T-B4001]  
LE28C1001DTS@VSOP32 [SA620-B4807]  
LE28CV1001AM@SOP32 [SA687]  
LE28CV1001AT@TSOP32 [SA410T-B4001]  
LE28CV1001ATS@VSOP32 [SA620-B4807]  
LE28CV1001DT@TSOP32 [SA410T-B4001]  
LE28CV1001DTS@VSOP32 [SA620-B4807]  
LE28CW1001DT@TSOP32 [SA410T-B4001]  
LE28CW1001DTS@VSOP32 [SA620-B4807]  
LE28DW1621T@TSOP48 [SB247-B4806]  
LE28DW8102T@TSOP48 [SA637B-B4806]  
LE28DW8163T@TSOP48 [SB247-B4806]           LE28F1101T@TSOP40 [SA623-B4002]  
LE28F1601T (REVERSE)@TSOP40 [SA623-B4002]  
LE28F1601T@TSOP40 [SA623-B4002]  
LE28F2001ATS@TSOP32 [SA620-B4807]  
LE28F4001ATS@TSOP32 [SA620-B4807]  
LE28F4001M@SSOP32 [SA438T]  
LE28F8001T (REVERSE)@TSOP40 [SA623-B4002]  
LE28F8001T@TSOP40 [SA623-B4002]           LE28FU4101T@TSOP48 [SB247-B4806]  
LE28FV1101T@TSOP40 [SA623-B4002]  
LE28FV1601T (REVERSE)@TSOP40 [SA623-B4002]  
LE28FV1601T@TSOP40 [SA623-B4002]  
LE28FV2001ATS@TSOP32 [SA620-B4807]  
LE28FV4001ATS@TSOP32 [SA620-B4807]  
LE28FV4001CTS@TSOP32 [SA620-B4807]  
LE28FV4001M@SSOP32 [SA438T]               LE28FV4001T@TSOP32 [SA620-B4807]  
LE28FV4101T@TSOP48 [SB247-B4806]  
LE28FV8001T (REVERSE)@TSOP40 [SA623-B4002]  
LE28FV8001T@TSOP40 [SA623-B4002]  
LE28FW1633TB@TSOP48 [SB247-B4806]  
LE28FW1633TT@TSOP48 [SB247-B4806]  
LE28FW4101T@TSOP48 [SB247-B4806]           LE28FW8201T@TSOP48 [SB247-B4806]  
LE28FW8203TB@TSOP48 [SB247-B4806]  
LE28FW8203TT@TSOP48 [SB247-B4806]

SEEQ

E (E) PROM/FRAM/NVRAM

27128  
2764  
2804  
2816A  
5516A  
5517A  
DE2817A  
DE2817AH  
DQ2817A  
DQ2817AH  
DQ2864  
DQ2864H  
DQ28C256  
DQ28C64  
DQ28C64A  
DQ28C65  
E28C64  
M28C64  
PQ2864  
PQ2864H  
PQ28C64  
PQ28C65

27256  
27C256  
2804A  
2816AH  
5516AH  
5517AH  
DE2817A@PLCC32 [SA015A1T]  
DE2817AH@PLCC32 [SA015A1T]  
DQ2817A@PLCC32 [SA015A1T]  
DQ2817AH@PLCC32 [SA015A1T]  
DQ2864@PLCC32 [SA015A1T]  
DQ2864H@PLCC32 [SA015A1T]  
DQ28C256@PLCC32 [SA015A1T]  
DQ28C64@PLCC32 [SA015A1T]  
DQ28C64A@PLCC32 [SA015A1T]  
DQ28C65@PLCC32 [SA015A1T]  
E28C64@PLCC32 [SA015A1T]  
M28C64@PLCC32 [SA015A1T]  
PQ2864@PLCC32 [SA015A1T]  
PQ2864H@PLCC32 [SA015A1T]  
PQ28C64@PLCC32 [SA015A1T]  
PQ28C65@PLCC32 [SA015A1T]

## SEIKO

### E (E) PROM/FRAM/NVRAM

S-22H10  
S-22H12  
S-22S10  
S-22S12  
S-24C01A (DP)  
S-24C01A (FJA)@SOIC8 [SA602A]  
S-24C01B (FJ)@SOIC8 [SA602A]  
S-24C01CFM  
S-24C01CPH  
S-24C02A (DPA)  
S-24C02B (DP)  
S-24C02CFJ [SA602A]  
S-24C02CFT [SA643]  
S-24C04A (DP)  
S-24C04A (FJA)@SOIC8 [SA602A]  
S-24C04B (FJ)@SOIC8 [SA602A]  
S-24C04CFM  
S-24C04CPH  
S-24C08A (FJA)@SOIC8 [SA602A]  
S-24C08CFM  
S-24C08CPH  
S-24C128CFM  
S-24C128CPH  
S-24C16A (FJA)@SOIC8 [SA602A]  
S-24C16CFM

S-22H10@SOP18 [SA404]  
S-22H12@SOP18 [SA404]  
S-22S10@SOP18 [SA404]  
S-22S12@SOP18 [SA404]  
S-24C01A (DPA)  
S-24C01B (DP)  
S-24C01CFJ [SA602A]  
S-24C01CFT [SA643]  
S-24C02A (DP)  
S-24C02A (FJA)@SOIC8 [SA602A]  
S-24C02B (FJ)@SOIC8 [SA602A]  
S-24C02CFM  
S-24C02CPH  
S-24C04A (DPA)  
S-24C04B (DP)  
S-24C04CFJ [SA602A]  
S-24C04CFT [SA643]  
S-24C08A (DPA)  
S-24C08CFJ [SA602A]  
S-24C08CFT [SA643]  
S-24C128CFJ [SA602A]  
S-24C128CFT [SA602A]  
S-24C16A (DPA)  
S-24C16CFJ [SA602A]  
S-24C16CFT [SA643]

S-24C16CPH  
S-24C256CFM  
S-24C256CPH  
S-24C32CFM  
S-24C32CPH  
S-24C512C-T8 [SA643]  
S-24C64CFM  
S-24C64CPH  
S-24CS01A (DP)  
S-24CS01A (FT)@TSSOP8 [SA643]  
S-24CS02A (FJ)@SOIC8 [SA602A]  
S-24CS04A (DP)  
S-24CS04A (FT)@TSSOP8 [SA643]  
S-24CS08A (FJ)@SOIC8 [SA602A]  
S-24CS16A (DP)  
S-24CS16A (FT)@TSSOP8 [SA643]  
S-24CS64A (FT)@TSSOP8 [SA643]  
S-24H30@SOP8 [\$\$\$\$\$\$]  
S-24H45@SOP8 [\$\$\$\$\$\$]  
S-24S30@SOP8 [\$\$\$\$\$\$]  
S-24S45@SOP8 [\$\$\$\$\$\$]  
S-25A020A@SOP8 [SA602A]  
S-25A080A@SOP8 [SA602A]  
S-25A320A@SOP8 [SA602A]  
S-25C010A@SOP8 [SA602A]  
S-25C020A@SOP8 [SA602A]  
S-25C040A@SOP8 [SA602A]  
S-25C080A@SOP8 [SA602A]  
S-25C128A@SOP8 [SA602A]  
S-25C160A@SOP8 [SA602A]  
S-25C256A@SOP8 [SA602A]  
S-25C320A@SOP8 [SA602A]  
S-25C512A@SOP8 [SA602A]  
S-25C640A@SOP8 [SA602A]  
S-25CM01A@SOP8 [SA602A]  
S-2817A@SOP28(\*) [SA404]  
S-2900A (FE)@SOP8 [SA602A]  
S-2911 (DP)  
S-29130A (DPA)  
S-29131A (DPA)  
S-29190A (DPA)  
S-29191A (DPA)  
S-29194A (DPA)  
S-29220A (DFJA)@SOIC8 [SA602A]  
S-29220A (FJA)@SOIC8 [SA602A]  
S-29221A (FJA)@SOIC8 [SA602A]  
S-29230A (DPA)  
S-29231A (DPA)  
S-29290A (DPA)  
S-29291A (DPA)  
S-29294A (DPA)  
S-29330A (DFJA)@SOIC8 [SA602A]  
S-29330A (FJA)@SOIC8 [SA602A]

S-24C256CFJ [SA602A]  
S-24C256CFT [SA602A]  
S-24C32CFJ [SA602A]  
S-24C32CFT [SA602A]  
S-24C512C-S8 [SA605B]  
S-24C64CFJ [SA602A]  
S-24C64CFT [SA602A]  
S-24CM01C-S8 [SA602A]  
S-24CS01A (FJ)@SOIC8 [SA602A]  
S-24CS02A (DP)  
S-24CS02A (FT)@TSSOP8 [SA643]  
S-24CS04A (FJ)@SOIC8 [SA602A]  
S-24CS08A (DP)  
S-24CS08A (FT)@TSSOP8 [SA643]  
S-24CS16A (FJ)@SOIC8 [SA602A]  
S-24CS64A (FJ)@SOIC8 [SA602A]  
S-24H30  
S-24H45  
S-24S30  
S-24S45  
S-25A010A@SOP8 [SA602A]  
S-25A040A@SOP8 [SA602A]  
S-25A160A@SOP8 [SA602A]  
S-25A640A@SOP8 [SA602A]  
S-25C010A@TSSOP8 [SA643]  
S-25C020A@TSSOP8 [SA643]  
S-25C040A@TSSOP8 [SA643]  
S-25C080A@TSSOP8 [SA643]  
S-25C128A@TSSOP8 [SA643]  
S-25C160A@TSSOP8 [SA643]  
S-25C256A@TSSOP8 [SA643]  
S-25C320A@TSSOP8 [SA643]  
S-25C512A@TSSOP8 [SA643]  
S-25C640A@TSSOP8 [SA643]  
S-2817A@SOP28 [SA404]  
S-2900A (DP)  
S-2900A (UP)@SOT-89-5 [SA717]  
S-29130A (DFJA)@SOIC8 [SA602A]  
S-29130A (FJA)@SOIC8 [SA602A]  
S-29131A (FJA)@SOIC8 [SA602A]  
S-29190A (FJA)@SOIC8 [SA602A]  
S-29191A (FJA)@SOIC8 [SA602A]  
S-29194A (FJA)@SOIC8 [SA602A]  
S-29220A (DPA)  
S-29221A (DPA)  
S-29230A (DFJA)@SOIC8 [SA602A]  
S-29230A (FJA)@SOIC8 [SA602A]  
S-29231A (FJA)@SOIC8 [SA602A]  
S-29290A (FJA)@SOIC8 [SA602A]  
S-29291A (FJA)@SOIC8 [SA602A]  
S-29294A (FJA)@SOIC8 [SA602A]  
S-29330A (DPA)  
S-29331A (DPA)

S-29331A (FJA)@SOIC8 [SA602A]  
S-29390A (FJA)@SOIC8 [SA602A]  
S-29391A (FJA)@SOIC8 [SA602A]  
S-29394A (FJA)@SOIC8 [SA602A]  
S-29430A@SOIC8 [SA602A]  
S-29530A@SOIC8 [SA602A]  
S-29630A@SOIC8 [SA602A]  
S-29L130A (FE)@SOIC8 [SA602A]  
S-29L131A (DFE)@SOIC8 [SA602A]  
S-29L194A (DFE)@SOIC8 [SA602A]  
S-29L220A (DFE)@SOIC8 [SA602A]  
S-29L220A (FS)@SSOP8 [SA643]  
S-29L221A (FS)@SSOP8 [SA643]  
S-29L294A (FS)@TSSOP8 [SA643]  
S-29L330A (FE)@SOIC8 [SA602A]  
S-29L331A (DFE)@SOIC8 [SA602A]  
S-29L394A (DFE)@SOIC8 [SA602A]  
S-29U130A (DFE)@SOIC8 [SA602A]  
S-29U131A (DFE)@SOIC8 [SA602A]  
S-29U194A (DFE)@SOIC8 [SA602A]  
S-29U220A (DFE)@SOIC8 [SA602A]  
S-29U221A (DFE)@SOIC8 [SA602A]  
S-29U294A (DFE)@SOIC8 [SA602A]  
S-29U330A (DFE)@SOIC8 [SA602A]  
S-29U331A (DFE)@SOIC8 [SA602A]  
S-29U394A (DFE)@SOIC8 [SA602A]  
S-29Z330A (DFJA)@SOIC8 [SA602A]  
S-29Z430A (DFJA)@SOIC8 [SA602A]  
S-93A46A (DOA)@SOIC8 [SA602A]  
S-93A66A (DOA)@SOIC8 [SA602A]  
S-93A86A@SOIC8 [SA602A]  
S-93C46A (DP)  
S-93C46A (FT)@TSSOP8 [SA643]  
S-93C46B (FJ)@SOIC8 [SA602A]  
S-93C56A (DFJ)@SOIC8 [SA602A]  
S-93C56A (FJ)@SOIC8 [SA602A]  
S-93C56B (DP)  
S-93C56B (FT)@TSSOP8 [SA643]  
S-93C66A (DP)  
S-93C66A (FT)@TSSOP8 [SA643]  
S-93C66B (FJ)@SOIC8 [SA602A]  
S-93C76A (DP)  
S-93C76A (FT)@TSSOP8 [SA643]  
S-93C86A (FJ)@SOIC8 [SA602A]  
S-93C86B@SOIC8 [SA602A]  
S-93L46A (DOI)@SOIC8 [SA602A]  
S-93L46A (DOI)@TSSOP8 [SA643]  
S-93L56A (DOI)@SOIC8 [SA602A]  
S-93L56A (DOI)@TSSOP8 [SA643]  
S-93L66A (DOI)@SOIC8 [SA602A]  
S-93L66A (DOI)@TSSOP8 [SA643]  
S-93L76A (DOI)@SOIC8 [SA602A]  
S-93L76A (DOI)@TSSOP8 [SA643]  
S-29390A (DPA)  
S-29391A (DPA)  
S-29394A (DPA)  
S-29430A  
S-29530A  
S-29630A  
S-29L130A (DFE)@SOIC8 [SA602A]  
S-29L130A (FS)@SSOP8 [SA643]  
S-29L131A (FS)@SSOP8 [SA643]  
S-29L194A (FS)@TSSOP8 [SA643]  
S-29L220A (FE)@SOIC8 [SA602A]  
S-29L221A (DFE)@SOIC8 [SA602A]  
S-29L294A (DFE)@SOIC8 [SA602A]  
S-29L330A (DFE)@SOIC8 [SA602A]  
S-29L330A (FS)@SSOP8 [SA643]  
S-29L331A (FS)@SSOP8 [SA643]  
S-29L394A (FS)@TSSOP8 [SA643]  
S-29U130A (FS)@SSOP8 [SA643]  
S-29U131A (FS)@SSOP8 [SA643]  
S-29U194A (FS)@TSSOP8 [SA643]  
S-29U220A (FS)@SSOP8 [SA643]  
S-29U221A (FS)@SSOP8 [SA643]  
S-29U294A (FS)@TSSOP8 [SA643]  
S-29U330A (FS)@SSOP8 [SA643]  
S-29U331A (FS)@SSOP8 [SA643]  
S-29U394A (FS)@TSSOP8 [SA643]  
S-29Z330A (FS)@SSOP8 [SA643]  
S-29Z430A (FS)@SSOP8 [SA643]  
S-93A56A (DOA)@SOIC8 [SA602A]  
S-93A66A (FJ)@SOIC8 [SA602A]  
S-93C46A (DFJ)@SOIC8 [SA602A]  
S-93C46A (FJ)@SOIC8 [SA602A]  
S-93C46B (DP)  
S-93C46B (FT)@TSSOP8 [SA643]  
S-93C56A (DP)  
S-93C56A (FT)@TSSOP8 [SA643]  
S-93C56B (FJ)@SOIC8 [SA602A]  
S-93C66A (DFJ)@SOIC8 [SA602A]  
S-93C66A (FJ)@SOIC8 [SA602A]  
S-93C66B (DP)  
S-93C66B (FT)@TSSOP8 [SA643]  
S-93C76A (FJ)@SOIC8 [SA602A]  
S-93C86A (DP)  
S-93C86A (FT)@TSSOP8 [SA643]  
S-93C86B@TSSOP8 [SA643]  
S-93L46A (DOI)@TMSOP8 [SA666]  
S-93L46A (ROI)@SOIC8 [SA602A]  
S-93L56A (DOI)@TMSOP8 [SA666]  
S-93L56A (ROI)@SOIC8 [SA602A]  
S-93L66A (DOI)@TMSOP8 [SA666]  
S-93L66A (ROI)@SOIC8 [SA602A]  
S-93L76A (DOI)@TMSOP8 [SA666]

## SGS-THOMSON

### E (E) PROM/FRAM/NVRAM

ET2716  
ETC2732  
M24128@SOIC8 [SA602A]  
M24164@SOIC8 [SA602A]  
M24256[3.9]@SOIC8 [SA602A]  
M24512  
M24512@TSOP8 [SA643]  
M24C04@SOIC8 [SA602A]  
M24C08@SOIC8 [SA602A]  
M24C08W@SOIC8 [SA602A]  
M24C64 (BN)  
M24C64 (DW)@TSSOP8 [SA602A]  
M24C64 (MW)@SOIC8 [SA602A]  
M2716  
M27256A  
M27512  
M2764A  
M27C1000@PLCC32 [SA015A1T]  
M27C1001  
M27C1001@TSOP32 [SA410T-B4001]  
M27C1024@PLCC44 [SA244]  
M27C160@PLCC44 [SA244]  
M27C2001  
M27C2001@TSOP32 [SA410T-B4001]  
M27C202@PLCC44 [SA244]  
M27C256B  
M27C400  
M27C4001@PLCC32 [SA015A1T]  
M27C4002  
M27C405  
M27C405@TSOP32 [SA410T-B4001]  
M27C512@PLCC32 [SA015A1T]  
M27C516@PLCC44 [SA244]  
M27C64A@PLCC32 [SA015A1T]  
M27C800@PLCC44 [SA244]  
M27C801  
M27C801@TSOP32 [SA410T-B4001]  
M27HC641@PLCC28 [SA008A]  
M27HC642@PLCC28 [SA008A]  
M27V101@PLCC32 [SA015A1T]  
M27V201  
M27V201@TSOP32 [SA410T-B4001]  
M27V401@PLCC32 [SA015A1T]  
M27V402  
M27V402@TSOP40 [SA409T-B4002]  
M27V512@PLCC32 [SA015A1T]  
M27V800  
ETC2716  
M24128  
M24164  
M24256  
M24256[5.5]@SOIC8 [SA023A]  
M24512@SOIC8 [SA605B]  
M24C04  
M24C08  
M24C08W  
M24C08W@TSOP8 [SA643]  
M24C64 (DL)@TSSOP14 [SA026]  
M24C64 (MN)@SOIC8 [SA023A]  
M27128A  
M27256  
M2732A  
M2764  
M27C1000  
M27C1000@TSOP32 [SA410T-B4001]  
M27C1001@PLCC32 [SA015A1T]  
M27C1024  
M27C160  
M27C160@PSOP44 [SA638]  
M27C2001@PLCC32 [SA015A1T]  
M27C202  
M27C202@VSOP40 [SA623-B4002]  
M27C256B@PLCC32 [SA015A1T]  
M27C4001  
M27C4001@TSOP32 [SA410T-B4001]  
M27C4002@PLCC44  
M27C405@PLCC32 [SA015A1T]  
M27C512  
M27C516  
M27C64A  
M27C800  
M27C800@PSOP44 [SA638]  
M27C801@PLCC32 [SA015A1T]  
M27HC641  
M27HC642  
M27V101  
M27V101@TSOP32 [SA410T-B4001]  
M27V201@PLCC32 [SA015A1T]  
M27V401  
M27V401@TSOP32 [SA410T-B4001]  
M27V402@PLCC44 [SA244]  
M27V512  
M27V512@TSOP28 [SA430T-B4003]  
M27V800@PLCC44 [SA244]

M27V801  
M27V801@TSOP32 [SA410T-B4001]  
M27W201@PLCC32 [SA015A1T]  
M28010  
M28010@TSOP32 [SA410T-B4001]  
M28C64C  
M28C64C@SOIC28 [SA404]  
M28F101  
M28F101 (REVERSE)@TSOP32 [SA410T-B4001]  
M28F101@PLCC32 [SA015A1T]  
M28F102  
M28F102@TSOP40 [SA623-B4002]  
M28F151 (REVERSE)@TSOP32 [SA410T-B4001]  
M28F151@PLCC32 [SA015A1T]  
M28F201  
M28F201 (REVERSE)@TSOP32 [SA410T-B4001]  
M28F201@PLCC32 [SA015A1T]  
M28F210@PSOP44 [SA638]  
M28F211@TSOP40 [SA409T-B4002]  
M28F220@TSOP48 [SB247-B4806]  
M28F256  
M28F256 (REVERSE)@TSOP32 [SA410T-B4001]  
M28F256@PLCC32 [SA015A1T]  
M28F411@TSOP40 [SA409T-B4002]  
M28F512  
M28F512 (REVERSE)@TSOP32 [SA410T-B4001]  
M28F512@PLCC32 [SA015A1T]  
M29F002B  
M29F002B@TSOP32 [SA410T-B4001]  
M29F002T@PLCC32 [SA015A1T]  
M29F040  
M29F040@TSOP32 [SA410T-B4001]  
M29F040B@PLCC32 [SA015A1T]  
M29F100B@PSOP44 [SA638]  
M29F100T@PSOP44 [SA638]  
M29F102B@PLCC44 [SA244]  
M29F102BB@PLCC44 [SA244]  
M29F200B@PSOP44 [SA638]  
M29F200T@PSOP44 [SA638]  
M29F400B@PSOP44 [SA638]  
M29F400T@PSOP44 [SA638]  
M29V040@PLCC32 [SA015A1T]  
M29W008B@TSOP40 [SA409T-B4002]  
M29W040@PLCC32 [SA015A1T]  
M29W400B@PSOP44 [SA638]  
M29W400T@PLCC44 [SA638]  
M29W512B@PLCC32 [SA015A1T]  
M29W800B@PSOP44 [SA638]  
M29W800T@PSOP44 [SA638]  
M48T35  
M48T35Y  
M48T59  
M48T59Y  
M27V801@PLCC32 [SA015A1T]  
M27W201  
M27W201@TSOP32 [SA410T-B4001]  
M28010@PLCC32 [SA015A1T]  
M28C16@PLCC32 [SA015A1T]  
M28C64C@PLCC32 [SA015A1T]  
M28C64C@TSOP28 [SA430T-B4003]  
M28F101@TSOP32 [SA410T-B4001]  
M28F102@PLCC44 [SA244]  
M28F151  
M28F151@TSOP32 [SA410T-B4001]  
M28F201@TSOP32 [SA410T-B4001]  
M28F210@TSOP48 [SB247-B4806]  
M28F220@PSOP44 [SA638]  
M28F221@TSOP40 [SA409T-B4002]  
M28F256@TSOP32 [SA410T-B4001]  
M28F421@TSOP40 [SA409T-B4002]  
M28F512@TSOP32 [SA410T-B4001]  
M29F002B@PLCC32 [SA015A1T]  
M29F002T  
M29F002T@TSOP32 [SA410T-B4001]  
M29F040@PLCC32 [SA015A1T]  
M29F040B  
M29F040B@TSOP32 [SA410T-B4001]  
M29F100B@TSOP48 [SB247-B4806]  
M29F100T@TSOP48 [SB247-B4806]  
M29F102B@TSOP40 [SA623-B4002]  
M29F102BB@TSOP40 [SA623-B4002]  
M29F200B@TSOP48 [SB247-B4806]  
M29F200T@TSOP48 [SB247-B4806]  
M29F400B@TSOP48 [SB247-B4806]  
M29F400T@TSOP48 [SB247-B4806]  
M29V040@TSOP32 [SA410T-B4001]  
M29W008T@TSOP40 [SA409T-B4002]  
M29W040@TSOP32 [SA410T-B4001]  
M29W400B@TSOP48 [SB247-B4806]  
M29W400T@TSOP48 [SB247-B4806]  
M29W512B@TSOP32 [SA620-B4807]  
M29W800B@TSOP48 [SB247-B4806]  
M29W800T@TSOP48 [SB247-B4806]  
M48T35@SOIC28 [SA404]  
M48T35Y@SOIC28 [SA404]  
M48T59@SOIC28 [SA404]  
M48T59Y@SOIC28 [SA404]

M48Z128	M48Z128Y
M48Z30	M48Z30Y
M48Z32	M48Z32Y
M50FW080@PLCC32 [SA015A1T]	M50FW080@TSOP40 [SA409T-B4002]
M50FW080@VSOP32 [SA620-B4807]	M87C257
M87C257@PLCC32 [SA015A1T]	M93C06 (08bit)
M93C06 (08bit)@SOIC8 [SA602A]	M93C06 (16bit)
M93C06 (16bit)@SOIC8 [SA602A]	M93S46
M93S46@SOIC8 [SA602A]	M93S46@TSSOP8
M95P02	M95P02@SOIC8 [SA602A]
M95P04	M95P04@SOIC8 [SA602A]
M95P08	M95P08@SOIC8 [SA602A]
MK48C02	MK48C02B
MK48C12	MK48C12B
MK48T02	MK48T02B
MK48T08	MK48T12
MK48T12B	MK48T18
MK48Z02	MK48Z02B
MK48Z08	MK48Z12
MK48Z12B	MK48Z18
MKI48Z02	MKI48Z02B
MKI48Z12	MKI48Z12B
MKI48Z18	ST24C01
ST24C01@SOIC8 [SA602A]	ST24C02A
ST24C02A@SOIC8 [SA602A]	ST24C16
ST24C16@SOIC8 [SA602A]	ST24W01
ST24W01@SOIC8 [SA602A]	ST24W02
ST24W02@SOIC8 [SA602A]	ST24W04C
ST24W04C@SOIC8 [SA602A]	ST27128A
ST27256	ST2764A
ST27C256	ST93C06 (08bit)
ST93C06 (08bit)@SOIC8 [SA602A]	ST93C06 (16bit)
ST93C06 (16bit)@SOIC8 [SA602A]	ST93CS46
ST93CS46@SOIC8 [SA602A]	TS27C256
TS27C64	TS27C64@PLCC32 [SA015A1T]
TS27C64A	TS27C64A@PLCC32 [SA015A1T]
TS28C16A	TS28C17A

## PLD

GAL16V8	GAL16V8A
---------	----------

## SHARP

### E (E) PROM/FRAM/NVRAM

LH28F002SCHN@PSOP44 [SA638]  
LH28F002SCHT@TSOP40 [SA409T-B4002]  
LH28F002SCN@PSOP44 [SA638]  
LH28F002SCT@TSOP40 [SA409T-B4002]  
LH28F004BVE (BT)@TSOP40 [SA409T-B4002]  
LH28F004BVE (TT)@TSOP40 [SA409T-B4002]

LH28F004BVHS (BT)@VSOP40 [SA623-B4002]  
LH28F004BVHS (TT)@VSOP40 [SA623-B4002]  
LH28F004BVT (BT)@TSOP40 [SA409T-B4002]  
LH28F004BVT (TT)@TSOP40 [SA409T-B4002]  
LH28F004SCHN@PSOP44 [SA638]  
LH28F004SCHS@VSOP40 [SA623-B4002]  
LH28F004SCHT@TSOP40 [SA409T-B4002]  
LH28F004SCN@PSOP44 [SA638] LH28F004SCS@VSOP40 [SA623-B4002]  
LH28F004SCT@TSOP40 [SA409T-B4002]  
LH28F008BJT (BTLZ1)@TSOP40 [SA409T-B4002]  
LH28F008BJT (TB)@TSOP40 [SA409T-B4002]  
LH28F008BJT (TT)@TSOP40 [SA409T-B4002]  
LH28F008BJT (TTLZ2)@TSOP40 [SA409T-B4002]  
LH28F008BVT (BT)@TSOP40 [SA409T-B4002]  
LH28F008BVT (TT)@TSOP40 [SA409T-B4002]  
LH28F008SAN@PSOP44 [SA638]  
LH28F008SAR@RTSOP40 [SA409T-B4002]  
LH28F008SAT@TSOP40 [SA409T-B4002]  
LH28F008SCH (L85)@RTSOP40 [SA409T-B4002]  
LH28F008SCH-L@TSOP40 [SA409T-B4002]  
LH28F008SCHN@PSOP44 [SA638]  
LH28F008SCH-V@TSOP40 [SA409T-B4002]  
LH28F008SCH-ZU-120@TSOP40 [SA409T-B4002]  
LH28F008SCN@PSOP44 [SA638] LH28F008SCN-L@PSOP44 [SA638]  
LH28F008SCT@TSOP40 [SA409T-B4002]  
LH28F008SCT-L@TSOP40 [SA409T-B4002]  
LH28F008SCT-V@TSOP40 [SA409T-B4002]  
LH28F008SCV@TSOP40 [SA409T-B4002]  
LH28F016SC@PSOP44 [SA638]  
LH28F016SCR (L95)@RTSOP40 [SA409T-B4002]  
LH28F016SCT-L95@TSOP40 [SA409T-B4002]  
LH28F128BFHE@TSOP48 [SB247-B4806]  
LH28F128BFND@PSOP44 [SA638]  
LH28F160BGE (B)@TSOP48 [SB247-B4806]  
LH28F160BGE (T)@TSOP48 [SB247-B4806]  
LH28F160BHEB@TSOP48 [SB247-B4806]  
LH28F160BHET@TSOP48 [SB247-B4806]  
LH28F160BJD  
LH28F160BJEB@TSOP48 [SB247-B4806]  
LH28F160BJET@TSOP48 [SB247-B4806]  
LH28F160BVE (BTL)@TSOP48 [SB247-B4806]  
LH28F160BVE (TTL)@TSOP48 [SB247-B4806]  
LH28F320BFN@PSOP44 [SA638] LH28F320BJD  
LH28F320BJE (PB) (OTP)@TSOP48 [SB247-B4806]  
LH28F320BJE (PB)@TSOP48 [SB247-B4806]  
LH28F320BJE (PT) (OTP)@TSOP48 [SB247-B4806]  
LH28F320BJE (PT)@TSOP48 [SB247-B4806]  
LH28F320BJHE (PB) (OTP)@TSOP48 [SB247-B4806]  
LH28F320BJHE (PT) (OTP)@TSOP48 [SB247-B4806]  
LH28F320BJN@PSOP44 [SA638] LH28F320BMN@PSOP44 [SA638]  
LH28F400BGE (B)@TSOP48 [SB247-B4806]  
LH28F400BGE (T)@TSOP48 [SB247-B4806]  
LH28F400BGHE (B)@TSOP48 [SB247-B4806]

LH28F400BGHE (T)@TSOP48 [SB247-B4806]  
LH28F400BGN (B)@PSOP44 [SA638] LH28F400BGN (T)@PSOP44 [SA638]  
LH28F400BVE (B)@TSOP48 [SB247-B4806]  
LH28F400BVE (T)@TSOP48 [SB247-B4806]  
LH28F400BVHE (B)@TSOP48 [SB247-B4806]  
LH28F400BVHE (T)@TSOP48 [SB247-B4806]  
LH28F400BVN (B)@PSOP44 [SA638] LH28F400BVN (T)@PSOP44 [SA638]  
LH28F640BFE (PB)@TSOP48 [SB247-B4806]  
LH28F640BFE (PT)@TSOP48 [SB247-B4806]  
LH28F800BGE (B)@TSOP48 [SB247-B4806]  
LH28F800BGE (T)@TSOP48 [SB247-B4806]  
LH28F800BGHE (B)@TSOP48 [SB247-B4806]  
LH28F800BGHE (T)@TSOP48 [SB247-B4806]  
LH28F800BGHE (TTL10)@TSOP48 [SB247-B4806]  
LH28F800BGN (B)@PSOP44 [SA638] LH28F800BGN (T)@PSOP44 [SA638]  
LH28F800BH-B@TSOP48 [SB247-B4806]  
LH28F800BJE (PB) (OTP)@TSOP48 [SB247-B4806]  
LH28F800BJE (PB)@TSOP48 [SB247-B4806]  
LH28F800BJE (PT) (OTP)@TSOP48 [SB247-B4806]  
LH28F800BJE (PT)@TSOP48 [SB247-B4806]  
LH28F800BJHE (PB) (OTP)@TSOP48 [SB247-B4806]  
LH28F800BJHE (PT) (OTP)@TSOP48 [SB247-B4806]  
LH28F800BJHG (PB) (OTP)@CSP48 [\$\$\$\$\$]  
LH28F800BJR (PT) (OTP)@TSOP48 [SB247-B4806]  
LH28F800BV-B@TSOP48 [SB247-B4806]  
LH28F800BVE (B)@TSOP48 [SB247-B4806]  
LH28F800BVE (T)@TSOP48 [SB247-B4806]  
LH28F800BVE (TV85)@TSOP48 [SB247-B4806]  
LH28F800BVHB@TSOP48 [SB247-B4806]  
LH28F800BVHE (B)@TSOP48 [SB247-B4806]  
LH28F800BVHT@TSOP48 [SB247-B4806]  
LH28F800BVN (TV85)@PSOP44 [SA638]  
LH28F800BV-T@TSOP48 [SB247-B4806]  
LHF00L03@PLCC32 [SA015A1T] LHF00L04@TSOP40 [SA409T-B4002]  
LHF00L06@TSOP40 [SA409T-B4002] LHF00L07@PLCC32 [SA015A1T]  
LHF00L12 (LH28F320T)@TSOP48 [SB247-B4806]  
LHF00L13 (LH28F320B)@TSOP48 [SB247-B4806]  
LHF00L14 (LH28F320T)@TSOP48 [SB247-B4806]  
LHF00L15 (LH28F320B)@TSOP48 [SB247-B4806]  
LHF00L28 (LH28F160T)@TSOP48 [SB247-B4806]  
LHF00L29 (LH28F160B)@TSOP48 [SB247-B4806]  
LHF00L30 (LH28F160T)@TSOP48 [SB247-B4806]  
LHF00L31 (LH28F160B)@TSOP48 [SB247-B4806]

## SIEMENS

### E (E) PROM/FRAM/NVRAM

SDA2526 SDA2526@SOIC8 [SA602A]  
SDA2546 SDA2546@SOIC8 [SA602A]  
SDA25X26 SDA25X26@SOIC8 [SA602A]  
SDA25X46 SDA25X46@SOIC8 [SA602A]

SDE2526	SDE2526@SOIC8 [SA602A]
SDE2546	SDE2546@SOIC8 [SA602A]
SDE25X26	SDE25X26@SOIC8 [SA602A]
SDE25X46	SDE25X46@SOIC8 [SA602A]
SLA24C01	SLA24C01@SOIC8 [SA602A]
SLA24C02	SLA24C02@SOIC8 [SA602A]
SLA24C04	SLA24C04@SOIC8 [SA602A]
SLA24C08	SLA24C08@SOIC8 [SA602A]
SLA24C16	SLA24C16@SOIC8 [SA602A]
SLA24C164	SLA24C164@SOIC8 [SA602A]
SLA24C32	SLA24C32@SOIC8 [SA602A]
SLA24C64	SLA24C64@SOIC8 [SA602A]
SLA25010	SLA25010@SOIC8 [SA602A]
SLA25020	SLA25020@SOIC8 [SA602A]
SLA25040	SLA25040@SOIC8 [SA602A]
SLA25080	SLA25080@SOIC8 [SA602A]
SLA25160	SLA25160@SOIC8 [SA602A]
SLE24C01	SLE24C01@SOIC8 [SA602A]
SLE24C02	SLE24C02@SOIC8 [SA602A]
SLE24C04	SLE24C04@SOIC8 [SA602A]
SLE24C08	SLE24C08@SOIC8 [SA602A]
SLE24C16	SLE24C16@SOIC8 [SA602A]
SLE24C164	SLE24C164@SOIC8 [SA602A]
SLE24C32	SLE24C32@SOIC8 [SA602A]
SLE24C64	SLE24C64@SOIC8 [SA602A]
SLE25010	SLE25010@SOIC8 [SA602A]
SLE25020	SLE25020@SOIC8 [SA602A]
SLE25040	SLE25040@SOIC8 [SA602A]
SLE25080	SLE25080@SOIC8 [SA602A]
SLE25160	SLE25160@SOIC8 [SA602A]

## MICROCONTROLLER

XMC1100-T016F0008 [SA026]	XMC1100-T016F0016 [SA026]
XMC1100-T016F0064 [SA026]	XMC1100-T038F0016 [SA693]
XMC1100-T038F0032 [SA693]	XMC1100-T038F0064 [SA693]
XMC1201-T038F0016 [SA693]	XMC1201-T038F0032 [SA693]
XMC1201-T038F0064 [SA693]	XMC1201-T038F0200 [SA693]
XMC1202-T016X0016 [SA026]	XMC1202-T016X0032 [SA026]
XMC1202-T028X0016 [SA643]	XMC1202-T028X0032 [SA643]
XMC1301-T016F0008 [SA026]	XMC1301-T016F0016 [SA026]
XMC1301-T038F0008 [SA693]	XMC1301-T038F0016 [SA693]
XMC1301-T038F0032 [SA693]	XMC1301-T038F0064 [SA693]
XMC1302-T038X0016 [SA693]	XMC1302-T038X0032 [SA693]
XMC1302-T038X0064 [SA693]	XMC1302-T038X0200 [SA693]

## SIERRA

### E (E) PROM/FRAM/NVRAM

SC22101CM [SA404]	SC22101CN
SC22201CM [SA404]	SC22201CN

## SIGNETICS

### E (E) PROM/FRAM/NVRAM

27C010	27C010@PLCC32 [SA015A1T]
27C010@TSOP32 [SA410T-B4001]	27C040
27C040@PLCC32 [SA015A1T]	27C040@TSOP32 [SA410T-B4001]
27C210	27C210@PLCC44 [SA244]
27C240	27C240@PLCC44 [SA244]
27C256	27C256@PLCC32 [SA015A1T]
27C512	27C512@PLCC32 [SA015A1T]
27C64A	27C64A@PLCC32 [SA015A1T]
27HC641	27HC641@PLCC28 [SA008A]
27HC642	27HC642@PLCC28 [SA008A]
PCA8582A	PCA8582A@SOIC8 [SA602A]
PCA8582B	PCA8582B@SOIC8 [SA602A]
PCA8582C	PCA8582C@SOIC8 [SA602A]
PCA8582D	PCA8582D@SOIC8 [SA602A]
PCA8582E	PCA8582E@SOIC8 [SA602A]
PCD8582A	PCD8582A@SOIC8 [SA602A]
PCD8582B	PCD8582B@SOIC8 [SA602A]
PCD8582C	PCD8582C@SOIC8 [SA602A]
PCD8582D	PCD8582D@SOIC8 [SA602A]
PCD8582E	PCD8582E@SOIC8 [SA602A]
PCF8582A	PCF8582A@SOIC8 [SA602A]
PCF8582B	PCF8582B@SOIC8 [SA602A]
PCF8582C	PCF8582C@SOIC8 [SA602A]
PCF8582D	PCF8582D@SOIC8 [SA602A]
PCF8582E	PCF8582E@SOIC8 [SA602A]
PCF8594	PCF8594@SOIC8 [SA602A]
PCF8594C	PCF8594C@SOIC8 [SA602A]
PCF8594D	PCF8594D@SOIC8 [SA602A]
PCF8594E	PCF8594E@SOIC8 [SA602A]
PCF8598	PCF8598@SOIC8 [SA605B]
PCF8598C	PCF8598C@SOIC8 [SA605B]
PCF8598D	PCF8598D@SOIC8 [SA605B]
PCF8598E	PCF8598E@SOIC8 [SA605B]

### MICROCONTROLLER

S87C51	S87C51@PLCC44 [SA244]
S87C51@TQFP44 [SA675-B4805]	S87C51FA
S87C51FA@PLCC44 [SA244]	S87C51FA@TQFP44 [SA675-B4805]
S87C51FB	S87C51FB@PLCC44 [SA244]
S87C51FB@TQFP44 [SA675-B4805]	S87C51FC
S87C51FC@PLCC44 [SA244]	S87C51FC@TQFP44 [SA245A-B4805]
S87C52	S87C52@PLCC44 [SA244]
S87C52@TQFP44 [SA675-B4805]	S87C524
S87C524@PLCC44 [SA244]	S87C524@TQFP44 [SA245A-B4805]
S87C528	S87C528@PLCC44 [SA244]
S87C528@TQFP44 [SA245A-B4805]	S87C54

S87C54@PLCC44 [SA244]  
S87C550  
S87C575  
S87C575@TQFP44 [SA675-B4805]  
S87C576@PLCC44 [SA244]  
S87C58  
S87C58@TQFP44 [SA675-B4805]  
S87C591@TQFP44 [SA675-B4805]  
S87C652@PLCC44 [SA244]  
S87C654  
S87C654@TQFP44 [SA675-B4805]  
S87L51FA@PLCC44 [SA244]  
S87L51FB  
S87L51FB@TQFP44 [SA675-B4805]

S87C54@TQFP44 [SA675-B4805]  
S87C550@PLCC44 [SA244]  
S87C575@PLCC44 [SA244]  
S87C576  
S87C576@TQFP44 [SA675-B4805]  
S87C58@PLCC44 [SA244]  
S87C591@PLCC44 [SA244]  
S87C652  
S87C652@TQFP44 [SA675-B4805]  
S87C654@PLCC44 [SA244]  
S87L51FA  
S87L51FA@TQFP44 [SA675-B4805]  
S87L51FB@PLCC44 [SA244]

## Silicon Laboratories

### MICROCONTROLLER

C8051F330@MLP20 [SA692]  
C8051F330-GM@MLP20 [SA692]  
C8051F350-GQ@LQFP32 [SA636]  
C8051F352-GQ@LQFP32 [SA636]  
C8051F330D  
C8051F330-GP  
C8051F351-GM@QFN28 [SA697]  
C8051F353-GM@QFN28 [SA697]

## SIMTEK

### E (E) PROM/FRAM/NVRAM

STK10C48  
STK10C48@SOIC28 (350 mil) [SA630]  
STK10C68@PLCC28 [SA008A]  
STK11C48  
STK11C48@SOIC28 (350 mil) [SA630]  
STK11C68@PLCC28 [SA008A]  
STK11C88  
STK11C88 (3V)@SOIC28 (300 mil) [SA404]  
STK11C88 (3V)@SOIC28 (350 mil) [SA630]  
STK11C88@SOIC28 (300 mil) [SA404]  
STK12C68  
STK12C68@SOIC28 [SA630]  
STK14C88 (3V)  
STK14C88 (3V)@SOIC32 (300 mil) [SA783]  
STK14C88 (3V)@SOIC32 (350 mil) [SA630]  
STK14C88@PLCC32 [SA015A1T]  
STK14C88@SOIC32 (350 mil) [SA630]  
STK15C68@SOIC28 [SA630]  
STK15C88@SOIC28 (300 mil) [SA404]  
STK16C68  
STK16C88 (3V)  
STK22C48  
STK22C48@SOIC28 (350 mil) [SA630]  
STK10C48@SOIC28 (300 mil) [SA404]  
STK10C68  
STK10C68@SOIC28 [SA630]  
STK11C48@SOIC28 (300 mil) [SA404]  
STK11C68  
STK11C68@SOIC28 [SA630]  
STK11C88 (3V)  
STK11C88@SOIC28 (350 mil) [SA630]  
STK12C68@PLCC28 [SA008A]  
STK14C88  
STK14C88 (3V)@PLCC32 [SA015A1T]  
STK14C88@SOIC32 (300 mil) [SA783]  
STK15C68  
STK15C88  
STK15C88@SOIC28 (350 mil) [SA630]  
STK16C88  
STK20C04  
STK22C48@SOIC28 (300 mil) [SA404]  
STK25C48

## SMOS

### E (E) PROM/FRAM/NVRAM

SPM27128  
SPM27C256  
SPM27C64H

SPM27128C  
SPM27C64

## SONIX

### MICROCONTROLLER

SN8P1504  
SN8P1504@SOP28 [SA404]  
SN8P1507@TQFP44 [SA675-B4805]  
SN8P1602@SOP18 [SA404]  
SN8P1603  
SN8P1603@SSOP20 [SA674]  
SN8P1604@SOP28 [SA404]  
SN8P1702@SOP18 [SA404]  
SN8P1704A  
SN8P1704B  
SN8P1706A  
SN8P1707A  
SN8P1707B@TQFP44 [SA675-B4805]  
SN8P1708A@SSOP48 [SA669]  
SN8P1708B@SSOP48 [SA669]  
SN8P1714@SOP18 [SA404]  
SN8P1716  
SN8P2501AP  
SN8P2501AX@TSSOP16 [SA026]  
SN8P2501BS@SOP14 [SA602]  
SN8P2502AP  
SN8P2502AX@TSSOP16 [SA026]  
SN8P2502BS@SOP14 [SA602]  
SN8P2504AP  
SN8P2504AX@TSSOP16 [SA026]  
SN8P2504BS@SOP14 [SA602]  
SN8P2602AP  
SN8P2602AX@SSOP20 [SA674]  
SN8P2602BS@SOP18 [SA023A]  
SN8P2603AP  
SN8P2603AX@SSOP20 [SA674]  
SN8P2603BS@SOP18 [SA023A]  
SN8P26042AP  
SN8P26042AX@SSOP20 [SA674]  
SN8P26042BS@SOP20 [SA023A]  
SN8P26042P  
SN8P26042X@SSOP20 [SA674]  
SN8P2604AS@SOP28 [SA404]  
SN8P2604BK  
SN8P2604BX@SSOP28 [SA626A]

SN8P1504@SOP18 [SA404]  
SN8P1506  
SN8P1602  
SN8P1602@SSOP20 [SA674]  
SN8P1603@SOP18 [SA404]  
SN8P1604  
SN8P1702  
SN8P1702@SSOP20 [SA674]  
SN8P1704A@SOP28 [SA404]  
SN8P1704B@SOP28 [SA404]  
SN8P1706B  
SN8P1707A@TQFP44 [SA675-B4805]  
SN8P1708A  
SN8P1708B  
SN8P1714  
SN8P1714@SOP28 [SA404]  
SN8P1717@TQFP44 [SA675-B4805]  
SN8P2501AS@SOP14 [SA602]  
SN8P2501BP  
SN8P2501BX@TSSOP16 [SA026]  
SN8P2502AS@SOP14 [SA602]  
SN8P2502BP  
SN8P2502BX@TSSOP16 [SA026]  
SN8P2504AS@SOP14 [SA602]  
SN8P2504BP  
SN8P2504BX@TSSOP16 [SA026]  
SN8P2602AS@SOP18 [SA023A]  
SN8P2602BP  
SN8P2602BX@SSOP20 [SA674]  
SN8P2603AS@SOP18 [SA023A]  
SN8P2603BP  
SN8P2603BX@SSOP20 [SA674]  
SN8P26042AS@SOP20 [SA023A]  
SN8P26042BP  
SN8P26042BX@SSOP20 [SA674]  
SN8P26042S@SOP20 [SA023A]  
SN8P2604AK  
SN8P2604AX@SSOP28 [SA626A]  
SN8P2604BS@SOP28 [SA404]  
SN8P2604K

SN8P2604S@SOP28 [SA404]  
SN8P2606P  
SN8P2608X@SSOP48 [SA669]  
SN8P2622S@SOP18 [SA023A]  
SN8P2624K  
SN8P2624X@SSOP28 [SA626A]  
SN8P2704AP  
SN8P2705AP  
SN8P2706AP  
SN8P2708AP  
SN8P2708AX@SSOP48 [SA669]  
SN8P2722S@SOP20 [SA023A]

SN8P2604X@SSOP28 [SA626A]  
SN8P2608P  
SN8P2622P  
SN8P2622X@SSOP20 [SA430T-B4003]  
SN8P2624S@SOP28 [SA404]  
SN8P2704AK@SDIP28 [SA653]  
SN8P2704AS@SOP28 [SA723]  
SN8P2705AS@SOP32 [SA687]  
SN8P2707AQ@QFP44 [SA675-B4805]  
SN8P2708AQ@LQFP48 [SA248-B4804]  
SN8P2722P  
SN8P2722X@SSOP20 [SA430T-B4003]

## SONY

### E (E) PROM/FRAM/NVRAM

CXK1011M@SOIC8 [SA602A]  
CXK1012P  
CXK1023P

CXK1011P  
CXK1013P  
CXK27C4001

### DRAM & SRAM

CXK581000

CXK581000@SOIC32 [SA630]

## SPACE ELECTRONICS[SEi]

### E (E) PROM/FRAM/NVRAM

28C010  
28C010@TSOP32 [SA410T-B4001]  
28C010T@PLCC32 [SA015A1T]  
28C011  
28C011@TSOP32 [SA410T-B4001]  
28C011T@PLCC32 [SA015A1T]

28C010@PLCC32 [SA015A1T]  
28C010T  
28C010T@TSOP32 [SA410T-B4001]  
28C011@PLCC32 [SA015A1T]  
28C011T  
28C011T@TSOP32 [SA410T-B4001]

## SPANSION

### E (E) PROM/FRAM/NVRAM

AM29DL161DB@TSOP48 [SB247-B4806]  
AM29DL162CB@TSOP48 [SB247-B4806]  
AM29DL162DB@TSOP48 [SB247-B4806]  
AM29DL163CB@TSOP48 [SB247-B4806]  
AM29DL163DB@TSOP48 [SB247-B4806]  
AM29DL164CB@TSOP48 [SB247-B4806]  
AM29DL164DB@TSOP48 [SB247-B4806]  
AM29DL320GB@TSOP48 [SB247-B4806]  
AM29DL321CB@TSOP48 [SB247-B4806]  
AM29DL322CB@TSOP48 [SB247-B4806]

AM29DL161DT@TSOP48 [SB247-B4806]  
AM29DL162CT@TSOP48 [SB247-B4806]  
AM29DL162DT@TSOP48 [SB247-B4806]  
AM29DL163CT@TSOP48 [SB247-B4806]  
AM29DL163DT@TSOP48 [SB247-B4806]  
AM29DL164CT@TSOP48 [SB247-B4806]  
AM29DL164DT@TSOP48 [SB247-B4806]  
AM29DL320GT@TSOP48 [SB247-B4806]  
AM29DL321CT@TSOP48 [SB247-B4806]  
AM29DL322CT@TSOP48 [SB247-B4806]

AM29DL322DB@TSOP48 [SB247-B4806] AM29DL322DT@TSOP48 [SB247-B4806]  
AM29DL322GB@TSOP48 [SB247-B4806] AM29DL322GT@TSOP48 [SB247-B4806]  
AM29DL323CB@TSOP48 [SB247-B4806] AM29DL323CT@TSOP48 [SB247-B4806]  
AM29DL323DB@TSOP48 [SB247-B4806] AM29DL323DT@TSOP48 [SB247-B4806]  
AM29DL323GB@TSOP48 [SB247-B4806] AM29DL323GT@TSOP48 [SB247-B4806]  
AM29DL324CB@TSOP48 [SB247-B4806] AM29DL324CT@TSOP48 [SB247-B4806]  
AM29DL324DB@TSOP48 [SB247-B4806] AM29DL324DT@TSOP48 [SB247-B4806]  
AM29DL324GB@TSOP48 [SB247-B4806] AM29DL324GT@TSOP48 [SB247-B4806]  
AM29DL400BB (REVERSE)@TSOP48 [SB247-B4806]  
AM29DL400BB@PSOP44 [SA638] AM29DL400BB@TSOP48 [SB247-B4806]  
AM29DL400BT (REVERSE)@TSOP48 [SB247-B4806]  
AM29DL400BT@PLCC44 [SA638] AM29DL400BT@TSOP48 [SB247-B4806]  
AM29DL640D@TSOP48 [SB247-B4806] AM29DL640G@TSOP48 [SB247-B4806]  
AM29DL800B@PSOP44 [SA638] AM29DL800B@TSOP48 [SB247-B4806]  
AM29DL800BB (REVERSE)@TSOP48 [SB247-B4806]  
AM29DL800BB@PSOP44 [SA638] AM29DL800BB@TSOP48 [SB247-B4806]  
AM29DL800BT (REVERSE)@TSOP48 [SB247-B4806]  
AM29DL800BT@PSOP44 [SA638] AM29DL800BT@TSOP48 [SB247-B4806]  
AM29DL800T@PSOP44 [SA638] AM29DL800T@TSOP48 [SB247-B4806]  
AM29DS163CB@TSOP48 [SB247-B4806] AM29DS163CT@TSOP48 [SB247-B4806]  
AM29DS163DB@TSOP48 [SB247-B4806] AM29DS163DT@TSOP48 [SB247-B4806]  
AM29DS323DB@TSOP48 [SB247-B4806] AM29DS323DT@TSOP48 [SB247-B4806]  
AM29F002B AM29F002B@PLCC32 [SA015A1T]  
AM29F002B@TSOP32 [SA410T-B4001] AM29F002BB  
AM29F002BB@PLCC32 [SA015A1T] AM29F002BB@TSOP32 [SA410T-B4001]  
AM29F002BT AM29F002BT@PLCC32 [SA015A1T]  
AM29F002BT@TSOP32 [SA410T-B4001] AM29F002NB  
AM29F002NB@PLCC32 [SA015A1T] AM29F002NB@TSOP32 [SA410T-B4001]  
AM29F002NBB AM29F002NBB@PLCC32 [SA015A1T]  
AM29F002NBB@TSOP32 [SA410T-B4001] AM29F002NBT@PLCC32 [SA015A1T]  
AM29F002NBT AM29F002NBT@TSOP32 [SA410T-B4001]  
AM29F002NT AM29F002NT@PLCC32 [SA015A1T]  
AM29F002NT@TSOP32 [SA410T-B4001] AM29F002T  
AM29F002T@PLCC32 [SA015A1T] AM29F002T@TSOP32 [SA410T-B4001]  
AM29F004BB AM29F004BB@PLCC32 [SA015A1T]  
AM29F004BB@TSOP32 [SA410T-B4001] AM29F004BT  
AM29F004BT@PLCC32 [SA015A1T] AM29F004BT@TSOP32 [SA410T-B4001]  
AM29F016@PSOP44 [SA638] AM29F016@TSOP40 [SA409T-B4002]  
AM29F016@TSOP48 [SB247-B4806] AM29F016B@PSOP44 [SA638]  
AM29F016B@TSOP40 [SA409T-B4002] AM29F016B@TSOP48 [SB247-B4806]  
AM29F016D@PSOP44 [SA638] AM29F016D@TSOP40 [SA409T-B4002]  
AM29F016D@TSOP48 [SB247-B4806]  
AM29F017B (REVERSE)@TSOP40 [SA409T-B4002]  
AM29F017B (REVERSE)@TSOP48 [SB247-B4806]  
AM29F017B@TSOP40 [SA409T-B4002] AM29F017B@TSOP48 [SB247-B4806]  
AM29F017D (REVERSE)@TSOP48 [SB247-B4806]  
AM29F017D@TSOP40 [SA409T-B4002] AM29F017D@TSOP48 [SB247-B4806]  
AM29F032B@PSOP44 [SA638] AM29F032B@TSOP40 [SA409T-B4002]  
AM29F040 AM29F040@PLCC32 [SA015A1T]  
AM29F040@TSOP32 [SA410T-B4001] AM29F040A  
AM29F040A@PLCC32 [SA015A1T] AM29F040A@TSOP32 [SA410T-B4001]  
AM29F040B

AM29F040B (Reverse)@TSOP32 [SA410T-B4001]  
AM29F040B@PLCC32 [SA015A1T] AM29F040B@TSOP32 [SA410T-B4001]  
AM29F080 (REVERSE)@TSOP40 [SA409T-B4002]  
AM29F080@PSOP44 [SA638] AM29F080@TSOP40 [SA409T-B4002]  
AM29F080B@PSOP44 [SA638] AM29F080B@TSOP40 [SA409T-B4002]  
AM29F100B (REVERSE)@TSOP48 [SB247-B4806]  
AM29F100B@PSOP44 [SA638] AM29F100B@TSOP48 [SB247-B4806]  
AM29F100T (REVERSE)@TSOP48 [SB247-B4806]  
AM29F100T@PSOP44 [SA638] AM29F100T@TSOP48 [SB247-B4806]  
AM29F160DB (REVERSE)@TSOP48 [SB247-B4806]  
AM29F160DB@TSOP48 [SB247-B4806]  
AM29F160DT (REVERSE)@TSOP48 [SB247-B4806]  
AM29F160DT@TSOP48 [SB247-B4806]  
AM29F200AB (REVERSE)@TSOP48 [SB247-B4806]  
AM29F200AB@PSOP44 [SA638] AM29F200AB@TSOP48 [SB247-B4806]  
AM29F200AT (REVERSE)@TSOP48 [SB247-B4806]  
AM29F200AT@PSOP44 [SA638] AM29F200AT@TSOP48 [SB247-B4806]  
AM29F200BB (REVERSE)@TSOP48 [SB247-B4806]  
AM29F200BB@PSOP44 [SA638] AM29F200BB@TSOP48 [SB247-B4806]  
AM29F200BT (REVERSE)@TSOP48 [SB247-B4806]  
AM29F200BT@PSOP44 [SA638] AM29F200BT@TSOP48 [SB247-B4806]  
AM29F400AB (REVERSE)@TSOP48 [SB247-B4806]  
AM29F400AB@PSOP44 [SA638] AM29F400AB@TSOP48 [SB247-B4806]  
AM29F400AT (REVERSE)@TSOP48 [SB247-B4806]  
AM29F400AT@PSOP44 [SA638] AM29F400AT@TSOP48 [SB247-B4806]  
AM29F400BB (REVERSE)@TSOP48 [SB247-B4806]  
AM29F400BB@PSOP44 [SA638] AM29F400BB@TSOP48 [SB247-B4806]  
AM29F400BT (REVERSE)@TSOP48 [SB247-B4806]  
AM29F400BT@PSOP44 [SA638] AM29F400BT@TSOP48 [SB247-B4806]  
AM29F800B (REVERSE)@TSOP48 [SB247-B4806]  
AM29F800B@PSOP44 [SA638] AM29F800B@TSOP48 [SB247-B4806]  
AM29F800BB (REVERSE)@TSOP48 [SB247-B4806]  
AM29F800BB@PSOP44 [SA638] AM29F800BB@TSOP48 [SB247-B4806]  
AM29F800BT (REVERSE)@TSOP48 [SB247-B4806]  
AM29F800BT@PSOP44 [SA638] AM29F800BT@TSOP48 [SB247-B4806]  
AM29F800T (REVERSE)@TSOP48 [SB247-B4806]  
AM29F800T@PSOP44 [SA638] AM29F800T@TSOP48 [SB247-B4806]  
AM29LL800B@TSOP48 [SB247-B4806] AM29LL800BB@TSOP48 [SB247-B4806]  
AM29LL800BT@TSOP48 [SB247-B4806] AM29LL800T@TSOP48 [SB247-B4806]  
AM29LV001BB (REVERSE)@TSOP32 [SA410T-B4001]  
AM29LV001BB@PLCC32 [SA015A1T]  
AM29LV001BB@TSOP32 [SA410T-B4001]  
AM29LV001BT (REVERSE)@TSOP32 [SA410T-B4001]  
AM29LV001BT@PLCC32 [SA015A1T]  
AM29LV001BT@TSOP32 [SA410T-B4001]  
AM29LV002@TSOP40 [SA409T-B4002] AM29LV002B@TSOP40 [SA409T-B4002]  
AM29LV002BB@TSOP40 [SA409T-B4002]  
AM29LV002BT@TSOP40 [SA409T-B4002]  
AM29LV004B@TSOP40 [SA409T-B4002]  
AM29LV004BB@TSOP40 [SA409T-B4002]  
AM29LV004BT@TSOP40 [SA409T-B4002]  
AM29LV004T@TSOP40 [SA409T-B4002] AM29LV008B@TSOP40 [SA409T-B4002]  
AM29LV008BB@TSOP40 [SA409T-B4002]

AM29LV008BT@TSOP40 [SA409T-B4002]  
AM29LV008T@TSOP40 [SA409T-B4002]  
AM29LV017B (REVERSE)@TSOP40 [SA409T-B4002]  
AM29LV017B@TSOP40 [SA409T-B4002]  
AM29LV017D (REVERSE)@TSOP40 [SA409T-B4002]  
AM29LV017D@TSOP40 [SA409T-B4002] AM29LV033C@TSOP40 [SA409T-B4002]  
AM29LV033MU@TSOP40 [SA409T-B4002]  
AM29LV065D@TSOP48 [SB247-B4806] AM29LV065MU@TSOP48 [SB247-B4806]  
AM29LV080@TSOP40 [SA409T-B4002] AM29LV081@TSOP40 [SA409T-B4002]  
AM29LV081B@TSOP40 [SA409T-B4002]  
AM29LV116BB@TSOP40 [SA409T-B4002]  
AM29LV116BT@TSOP40 [SA409T-B4002]  
AM29LV116DB@TSOP40 [SA409T-B4002]  
AM29LV116DT@TSOP40 [SA409T-B4002]  
AM29LV160BB (REVERSE)@TSOP48 [SB247-B4806]  
AM29LV160BB@PSOP44 [SA638] AM29LV160BB@TSOP48 [SB247-B4806]  
AM29LV160BT (REVERSE)@TSOP48 [SB247-B4806]  
AM29LV160BT@PSOP44 [SA638] AM29LV160BT@TSOP48 [SB247-B4806]  
AM29LV160DB (REVERSE)@TSOP48 [SB247-B4806]  
AM29LV160DB@PSOP44 [SA638] AM29LV160DB@TSOP48 [SB247-B4806]  
AM29LV160DT (REVERSE)@TSOP48 [SB247-B4806]  
AM29LV160DT@PSOP44 [SA638] AM29LV160DT@TSOP48 [SB247-B4806]  
AM29LV160MA@PSOP44 [SA638]  
AM29LV160MB (REVERSE)@TSOP48 [SB247-B4806]  
AM29LV160MB@PSOP44 [SA638] AM29LV160MB@TSOP48 [SB247-B4806]  
AM29LV160MT (REVERSE)@TSOP48 [SB247-B4806]  
AM29LV160MT@PSOP44 [SA638] AM29LV160MT@TSOP48 [SB247-B4806]  
AM29LV200B (REVERSE)@TSOP48 [SB247-B4806]  
AM29LV200B@PSOP44 [SA638] AM29LV200B@TSOP48 [SB247-B4806]  
AM29LV200BB (REVERSE)@TSOP48 [SB247-B4806]  
AM29LV200BB@PSOP44 [SA638] AM29LV200BB@TSOP48 [SB247-B4806]  
AM29LV200BT (REVERSE)@TSOP48 [SB247-B4806]  
AM29LV200BT@PSOP44 [SA638] AM29LV200BT@TSOP48 [SB247-B4806]  
AM29LV200T (REVERSE)@TSOP48 [SB247-B4806]  
AM29LV200T@PSOP44 [SA638] AM29LV200T@TSOP48 [SB247-B4806]  
AM29LV320DB@TSOP48 [SB247-B4806] AM29LV320DT@TSOP48 [SB247-B4806]  
AM29LV320FB@TSOP48 [SB247-B4806] AM29LV320FT@TSOP48 [SB247-B4806]  
AM29LV320MB@TSOP48 [SB247-B4806] AM29LV320MT@TSOP48 [SB247-B4806]  
AM29LV400B (REVERSE)@TSOP48 [SB247-B4806]  
AM29LV400B@PSOP44 [SA638] AM29LV400B@TSOP48 [SB247-B4806]  
AM29LV400BB (REVERSE)@TSOP48 [SB247-B4806]  
AM29LV400BB@PSOP44 [SA638] AM29LV400BB@TSOP48 [SB247-B4806]  
AM29LV400BT (REVERSE)@TSOP48 [SB247-B4806]  
AM29LV400BT@PSOP44 [SA638] AM29LV400BT@TSOP48 [SB247-B4806]  
AM29LV400T (REVERSE)@TSOP48 [SB247-B4806]  
AM29LV400T@PSOP44 [SA638] AM29LV400T@TSOP48 [SB247-B4806]  
AM29LV640MB@TSOP48 [SB247-B4806] AM29LV640MT@TSOP48 [SB247-B4806]  
AM29LV641DH (REVERSE)@TSOP48 [SB247-B4806]  
AM29LV641DH@TSOP48 [SB247-B4806]  
AM29LV641DL (REVERSE)@TSOP48 [SB247-B4806]  
AM29LV641DL@TSOP48 [SB247-B4806]  
AM29LV641GH (REVERSE)@TSOP48 [SB247-B4806]  
AM29LV641GH@TSOP48 [SB247-B4806]

AM29LV641GL (REVERSE)@TSOP48 [SB247-B4806]  
AM29LV641GL@TSOP48 [SB247-B4806]  
AM29LV641MH (REVERSE)@TSOP48 [SB247-B4806]  
AM29LV641MH@TSOP48 [SB247-B4806]  
AM29LV641ML (REVERSE)@TSOP48 [SB247-B4806]  
AM29LV641ML@TSOP48 [SB247-B4806]  
AM29LV800B (REVERSE)@TSOP48 [SB247-B4806]  
AM29LV800B@PSOP44 [SA638] AM29LV800B@TSOP48 [SB247-B4806]  
AM29LV800BB (REVERSE)@TSOP48 [SB247-B4806]  
AM29LV800BB@PSOP44 [SA638] AM29LV800BB@TSOP48 [SB247-B4806]  
AM29LV800BT (REVERSE)@TSOP48 [SB247-B4806]  
AM29LV800BT@PSOP44 [SA638] AM29LV800BT@TSOP48 [SB247-B4806]  
AM29LV800DB (REVERSE)@TSOP48 [SB247-B4806]  
AM29LV800DB@PSOP44 [SA638] AM29LV800DB@TSOP48 [SB247-B4806]  
AM29LV800DT (REVERSE)@TSOP48 [SB247-B4806]  
AM29LV800DT@PSOP44 [SA638] AM29LV800DT@TSOP48 [SB247-B4806]  
AM29LV800T (REVERSE)@TSOP48 [SB247-B4806]  
AM29LV800T@PSOP44 [SA638] AM29LV800T@TSOP48 [SB247-B4806]  
AM29PL160BB@PSOP44 [SA638] AM29PL160BB@TSOP48 [SB247-B4806]  
AM29PL160CB@PSOP44 [SA638] AM29PL160CB@TSOP48 [SB247-B4806]  
AM29PL160CT@PSOP44 [SA638] AM29PL160CT@TSOP48 [SB247-B4806]  
AM29SL160BB@TSOP48 [SB247-B4806] AM29SL160BT@TSOP48 [SB247-B4806]  
AM29SL160CB@TSOP48 [SB247-B4806] AM29SL160CT@TSOP48 [SB247-B4806]  
AM29SL400CB@TSOP48 [SB247-B4806] AM29SL400CT@TSOP48 [SB247-B4806]  
AM29SL800BB (REVERSE)@TSOP48 [SB247-B4806]  
AM29SL800BB@TSOP48 [SB247-B4806]  
AM29SL800BT (REVERSE)@TSOP48 [SB247-B4806]  
AM29SL800BT@TSOP48 [SB247-B4806]  
AM29SL800CB (REVERSE)@TSOP48 [SB247-B4806]  
AM29SL800CB@TSOP48 [SB247-B4806]  
AM29SL800CT (REVERSE)@TSOP48 [SB247-B4806]  
AM29SL800CT@TSOP48 [SB247-B4806]  
AM29SL800DB (REVERSE)@TSOP48 [SB247-B4806]  
AM29SL800DB@TSOP48 [SB247-B4806]  
AM29SL800DT (REVERSE)@TSOP48 [SB247-B4806]  
AM29SL800DT@TSOP48 [SB247-B4806]  
MBM29DL161BD (REVERSE)@TSOP48 [SB247-B4806]  
MBM29DL161BD@TSOP48 [SB247-B4806]  
MBM29DL161BE (REVERSE)@TSOP48 [SB247-B4806]  
MBM29DL161BE@TSOP48 [SB247-B4806]  
MBM29DL161TD (REVERSE)@TSOP48 [SB247-B4806]  
MBM29DL161TD@TSOP48 [SB247-B4806]  
MBM29DL161TE (REVERSE)@TSOP48 [SB247-B4806]  
MBM29DL161TE@TSOP48 [SB247-B4806]  
MBM29DL162BD (REVERSE)@TSOP48 [SB247-B4806]  
MBM29DL162BD@TSOP48 [SB247-B4806]  
MBM29DL162BE (REVERSE)@TSOP48 [SB247-B4806]  
MBM29DL162BE@TSOP48 [SB247-B4806]  
MBM29DL162TD (REVERSE)@TSOP48 [SB247-B4806]  
MBM29DL162TD@TSOP48 [SB247-B4806]  
MBM29DL162TE (REVERSE)@TSOP48 [SB247-B4806]  
MBM29DL162TE@TSOP48 [SB247-B4806]  
MBM29DL163BD (REVERSE)@TSOP48 [SB247-B4806]

MBM29DL163BD@TSOP48 [SB247-B4806]  
MBM29DL163BE (REVERSE)@TSOP48 [SB247-B4806]  
MBM29DL163BE@TSOP48 [SB247-B4806]  
MBM29DL163TD (REVERSE)@TSOP48 [SB247-B4806]  
MBM29DL163TD@TSOP48 [SB247-B4806]  
MBM29DL163TE (REVERSE)@TSOP48 [SB247-B4806]  
MBM29DL163TE@TSOP48 [SB247-B4806]  
MBM29DL164BD (REVERSE)@TSOP48 [SB247-B4806]  
MBM29DL164BD@TSOP48 [SB247-B4806]  
MBM29DL164BE (REVERSE)@TSOP48 [SB247-B4806]  
MBM29DL164BE@TSOP48 [SB247-B4806]  
MBM29DL164TD (REVERSE)@TSOP48 [SB247-B4806]  
MBM29DL164TD@TSOP48 [SB247-B4806]  
MBM29DL164TE (REVERSE)@TSOP48 [SB247-B4806]  
MBM29DL164TE@TSOP48 [SB247-B4806]  
MBM29DL320BF@TSOP48 [SB247-B4806]  
MBM29DL320TF@TSOP48 [SB247-B4806]  
MBM29DL321BD (REVERSE)@TSOP48 [SB247-B4806]  
MBM29DL321BD@TSOP48 [SB247-B4806]  
MBM29DL321BE (REVERSE)@TSOP48 [SB247-B4806]  
MBM29DL321BE@TSOP48 [SB247-B4806]  
MBM29DL321TD (REVERSE)@TSOP48 [SB247-B4806]  
MBM29DL321TD@TSOP48 [SB247-B4806]  
MBM29DL321TE (REVERSE)@TSOP48 [SB247-B4806]  
MBM29DL321TE@TSOP48 [SB247-B4806]  
MBM29DL322BD (REVERSE)@TSOP48 [SB247-B4806]  
MBM29DL322BD@TSOP48 [SB247-B4806]  
MBM29DL322BE (REVERSE)@TSOP48 [SB247-B4806]  
MBM29DL322BE@TSOP48 [SB247-B4806]  
MBM29DL322TD (REVERSE)@TSOP48 [SB247-B4806]  
MBM29DL322TD@TSOP48 [SB247-B4806]  
MBM29DL322TE (REVERSE)@TSOP48 [SB247-B4806]  
MBM29DL322TE@TSOP48 [SB247-B4806]  
MBM29DL323BD (REVERSE)@TSOP48 [SB247-B4806]  
MBM29DL323BD@TSOP48 [SB247-B4806]  
MBM29DL323BE (REVERSE)@TSOP48 [SB247-B4806]  
MBM29DL323BE@TSOP48 [SB247-B4806]  
MBM29DL323BF@TSOP48 [SB247-B4806]  
MBM29DL323TD (REVERSE)@TSOP48 [SB247-B4806]  
MBM29DL323TD@TSOP48 [SB247-B4806]  
MBM29DL323TE (REVERSE)@TSOP48 [SB247-B4806]  
MBM29DL323TE@TSOP48 [SB247-B4806]  
MBM29DL323TF@TSOP48 [SB247-B4806]  
MBM29DL324BD (REVERSE)@TSOP48 [SB247-B4806]  
MBM29DL324BD@TSOP48 [SB247-B4806]  
MBM29DL324BE (REVERSE)@TSOP48 [SB247-B4806]  
MBM29DL324BE@TSOP48 [SB247-B4806]  
MBM29DL324TD (REVERSE)@TSOP48 [SB247-B4806]  
MBM29DL324TD@TSOP48 [SB247-B4806]  
MBM29DL324TE (REVERSE)@TSOP48 [SB247-B4806]  
MBM29DL324TE@TSOP48 [SB247-B4806]  
MBM29DL32BF@TSOP48 [SB247-B4806] MBM29DL32TF@TSOP48 [SB247-B4806]  
MBM29DL34BF@TSOP48 [SB247-B4806] MBM29DL34TF@TSOP48 [SB247-B4806]

MBM29DL400BB@PSOP44 [SA638]  
MBM29DL400BB@TSOP48 [SB247-B4806]  
MBM29DL400BC (REVERSE)@TSOP48 [SB247-B4806]  
MBM29DL400BC@PSOP44 [SA638]  
MBM29DL400BC@TSOP48 [SB247-B4806]  
MBM29DL400BT@PSOP44 [SA638]  
MBM29DL400BT@TSOP48 [SB247-B4806]  
MBM29DL400TC (REVERSE)@TSOP48 [SB247-B4806]  
MBM29DL400TC@PSOP44 [SA638]  
MBM29DL400TC@TSOP48 [SB247-B4806]  
MBM29DL640E (REVERSE)@TSOP48 [SB247-B4806]  
MBM29DL640E@TSOP48 [SB247-B4806] MBM29DL64DF@TSOP48 [SB247-B4806]  
MBM29DL800B@PSOP44 [SA638] MBM29DL800B@TSOP48 [SB247-B4806]  
MBM29DL800BA (REVERSE)@TSOP48 [SB247-B4806]  
MBM29DL800BA@PSOP44 [SA638]  
MBM29DL800BA@TSOP48 [SB247-B4806]  
MBM29DL800BB@PSOP44 [SA638]  
MBM29DL800BB@TSOP48 [SB247-B4806]  
MBM29DL800BT@PSOP44 [SA638]  
MBM29DL800BT@TSOP48 [SB247-B4806]  
MBM29DL800T@PSOP44 [SA638] MBM29DL800T@TSOP48 [SB247-B4806]  
MBM29DL800TA (REVERSE)@TSOP48 [SB247-B4806]  
MBM29DL800TA@PSOP44 [SA638]  
MBM29DL800TA@TSOP48 [SB247-B4806]  
MBM29DS163BE@TSOP48 [SB247-B4806]  
MBM29DS163TE@TSOP48 [SB247-B4806]  
MBM29F001B MBM29F001B@PLCC32 [SA015A1T]  
MBM29F001B@TSOP32 [SA410T-B4001] MBM29F001T  
MBM29F001T@PLCC32 [SA015A1T] MBM29F001T@TSOP32 [SA410T-B4001]  
MBM29F002B MBM29F002B@PLCC32 [SA015A1T]  
MBM29F002B@TSOP32 [SA410T-B4001] MBM29F002NB  
MBM29F002NB@PLCC32 [SA015A1T]  
MBM29F002NB@TSOP32 [SA410T-B4001]  
MBM29F002NT MBM29F002NT@PLCC32 [SA015A1T]  
MBM29F002NT@TSOP32 [SA410T-B4001]  
MBM29F002T MBM29F002T@PLCC32 [SA015A1T]  
MBM29F002T@TSOP32 [SA410T-B4001] MBM29F010  
MBM29F010@PLCC32 [SA015A1T] MBM29F010@TSOP32 [SA410T-B4001]  
MBM29F010A MBM29F010A@PLCC32 [SA015A1T]  
MBM29F010A@TSOP32 [SA410T-B4001] MBM29F016@PSOP44 [SA638]  
MBM29F016@TSOP40 [SA409T-B4002] MBM29F016@TSOP48 [SB247-B4806]  
MBM29F016A@PSOP44 [SA638] MBM29F016A@TSOP40 [SA409T-B4002]  
MBM29F016A@TSOP48 [SB247-B4806] MBM29F016B@PSOP44 [SA638]  
MBM29F016B@TSOP40 [SA409T-B4002] MBM29F016B@TSOP48 [SB247-B4806]  
MBM29F017A (REVERSE)@TSOP48 [SB247-B4806]  
MBM29F017A@TSOP48 [SB247-B4806] MBM29F017B@TSOP48 [SB247-B4806]  
MBM29F017D@TSOP40 [SA409T-B4002] MBM29F017D@TSOP48 [SB247-B4806]  
MBM29F032B@PSOP44 [SA638] MBM29F032B@TSOP40 [SA409T-B4002]  
MBM29F033C@TSOP40 [SA409T-B4002] MBM29F040  
MBM29F040@PLCC32 [SA015A1T] MBM29F040@TSOP32 [SA410T-B4001]  
MBM29F040B MBM29F040B@PLCC32 [SA015A1T]  
MBM29F040B@TSOP32 [SA410T-B4001] MBM29F040C@PLCC32 [SA015A1T]  
MBM29F040C@TSOP32 [SA410T-B4001] MBM29F080@PSOP44 [SA638]

MBM29F080@TSOP40 [SA409T-B4002]  
MBM29F080A (REVERSE)@TSOP40 [SA409T-B4002]  
MBM29F080A (REVERSE)@TSOP48 [SB247-B4806]  
MBM29F080A@PSOP44 [SA638] MBM29F080A@TSOP40 [SA409T-B4002]  
MBM29F080A@TSOP48 [SB247-B4806] MBM29F080B@PSOP44 [SA638]  
MBM29F080B@TSOP40 [SA409T-B4002] MBM29F100B@PSOP44 [SA638]  
MBM29F100B@TSOP48 [SB247-B4806] MBM29F100T@PSOP44 [SA638]  
MBM29F100T@TSOP48 [SB247-B4806]  
MBM29F160BE (REVERSE)@TSOP48 [SB247-B4806]  
MBM29F160BE@TSOP48 [SB247-B4806]  
MBM29F160TE (REVERSE)@TSOP48 [SB247-B4806]  
MBM29F160TE@TSOP48 [SB247-B4806] MBM29F200AB@PSOP44 [SA638]  
MBM29F200AB@TSOP48 [SB247-B4806] MBM29F200AT@PSOP44 [SA638]  
MBM29F200AT@TSOP48 [SB247-B4806] MBM29F200B@PSOP44 [SA638]  
MBM29F200B@TSOP48 [SB247-B4806]  
MBM29F200BC (REVERSE)@TSOP48 [SB247-B4806]  
MBM29F200BC@PSOP44 [SA638] MBM29F200BC@TSOP48 [SB247-B4806]  
MBM29F200T@PSOP44 [SA638] MBM29F200T@TSOP48 [SB247-B4806]  
MBM29F200TC (REVERSE)@TSOP48 [SB247-B4806]  
MBM29F200TC@PSOP44 [SA638] MBM29F200TC@TSOP48 [SB247-B4806]  
MBM29F400AB@PSOP44 [SA638] MBM29F400AB@TSOP48 [SB247-B4806]  
MBM29F400AT@PSOP44 [SA638] MBM29F400AT@TSOP48 [SB247-B4806]  
MBM29F400B@PSOP44 [SA638] MBM29F400B@TSOP48 [SB247-B4806]  
MBM29F400BB@PSOP44 [SA638] MBM29F400BB@TSOP48 [SB247-B4806]  
MBM29F400BC (REVERSE)@TSOP48 [SB247-B4806]  
MBM29F400BC@PSOP44 [SA638] MBM29F400BC@TSOP48 [SB247-B4806]  
MBM29F400BT@PSOP44 [SA638] MBM29F400BT@TSOP48 [SB247-B4806]  
MBM29F400T@PSOP44 [SA638] MBM29F400T@TSOP48 [SB247-B4806]  
MBM29F400TC (REVERSE)@TSOP48 [SB247-B4806]  
MBM29F400TC@PSOP44 [SA638] MBM29F400TC@TSOP48 [SB247-B4806]  
MBM29F800B@PSOP44 [SA638] MBM29F800B@TSOP48 [SB247-B4806]  
MBM29F800BA (REVERSE)@TSOP48 [SB247-B4806]  
MBM29F800BA@PSOP44 [SA638] MBM29F800BA@TSOP48 [SB247-B4806]  
MBM29F800BB@PSOP44 [SA638] MBM29F800BB@TSOP48 [SB247-B4806]  
MBM29F800BT@PSOP44 [SA638] MBM29F800BT@TSOP48 [SB247-B4806]  
MBM29F800T@PSOP44 [SA638] MBM29F800T@TSOP48 [SB247-B4806]  
MBM29F800TA (REVERSE)@TSOP48 [SB247-B4806]  
MBM29F800TA@PSOP44 [SA638] MBM29F800TA@TSOP48 [SB247-B4806]  
MBM29LL800B@TSOP48 [SB247-B4806]  
MBM29LL800BB@TSOP48 [SB247-B4806]  
MBM29LL800BT@TSOP48 [SB247-B4806]  
MBM29LL800T@TSOP48 [SB247-B4806] MBM29LV001B@PLCC32 [SA015A1T]  
MBM29LV001BB (REVERSE)@TSOP32 [SA410T-B4001]  
MBM29LV001BB@PLCC32 [SA015A1T]  
MBM29LV001BB@TSOP32 [SA410T-B4001]  
MBM29LV001BC (REVERSE)@TSOP32 [SA410T-B4001]  
MBM29LV001BC@PLCC32 [SA015A1T]  
MBM29LV001BC@TSOP32 [SA410T-B4001]  
MBM29LV001BT (REVERSE)@TSOP32 [SA410T-B4001]  
MBM29LV001BT@PLCC32 [SA015A1T]  
MBM29LV001BT@TSOP32 [SA410T-B4001]  
MBM29LV001T@TSOP32 [SA410T-B4001]  
MBM29LV001TC (REVERSE)@TSOP32 [SA410T-B4001]

MBM29LV001TC@PLCC32 [SA015A1T]  
MBM29LV001TC@TSOP32 [SA410T-B4001]  
MBM29LV002B@TSOP40 [SA409T-B4002]  
MBM29LV002T@TSOP40 [SA409T-B4002]  
MBM29LV004B@TSOP40 [SA409T-B4002]  
MBM29LV004BB@TSOP40 [SA409T-B4002]  
MBM29LV004BT@TSOP40 [SA409T-B4002]  
MBM29LV004T@TSOP40 [SA409T-B4002]  
MBM29LV008B@TSOP40 [SA409T-B4002]  
MBM29LV008BB@TSOP40 [SA409T-B4002]  
MBM29LV008BT@TSOP40 [SA409T-B4002]  
MBM29LV008T@TSOP40 [SA409T-B4002]  
MBM29LV016/B@TSOP40 [SA409T-B4002]  
MBM29LV016/T@TSOP40 [SA409T-B4002]  
MBM29LV016B@TSOP40 [SA409T-B4002]  
MBM29LV017@TSOP40 [SA409T-B4002]  
MBM29LV017B@TSOP40 [SA409T-B4002]  
MBM29LV017E@TSOP40 [SA409T-B4002]  
MBM29LV033C@TSOP40 [SA409T-B4002]  
MBM29LV080@TSOP40 [SA409T-B4002]  
MBM29LV080A@TSOP40 [SA409T-B4002]  
MBM29LV081@TSOP40 [SA409T-B4002]  
MBM29LV081B@TSOP40 [SA409T-B4002]  
MBM29LV116B@TSOP40 [SA409T-B4002]  
MBM29LV160B (REVERSE)@TSOP48 [SB247-B4806]  
MBM29LV160B@TSOP48 [SB247-B4806]  
MBM29LV160BE (REVERSE)@TSOP48 [SB247-B4806]  
MBM29LV160BE@PSOP44 [SA638]  
MBM29LV160BE@TSOP48 [SB247-B4806]  
MBM29LV160BM@TSOP48 [SB247-B4806]  
MBM29LV160T (REVERSE)@TSOP48 [SB247-B4806]  
MBM29LV160T@TSOP48 [SB247-B4806]  
MBM29LV160TE (REVERSE)@TSOP48 [SB247-B4806]  
MBM29LV160TE@PSOP44 [SA638]  
MBM29LV160TE@TSOP48 [SB247-B4806]  
MBM29LV160TM@TSOP48 [SB247-B4806]  
MBM29LV200B@PSOP44 [SA638] MBM29LV200B@TSOP48 [SB247-B4806]  
MBM29LV200BB@PSOP44 [SA638]  
MBM29LV200BB@TSOP48 [SB247-B4806]  
MBM29LV200BC (REVERSE)@TSOP48 [SB247-B4806]  
MBM29LV200BC@PSOP44 [SA638]  
MBM29LV200BC@TSOP48 [SB247-B4806]  
MBM29LV200BT@PSOP44 [SA638]  
MBM29LV200BT@TSOP48 [SB247-B4806]  
MBM29LV200T@PSOP44 [SA638] MBM29LV200T@TSOP48 [SB247-B4806]  
MBM29LV200TC (REVERSE)@TSOP48 [SB247-B4806]  
MBM29LV200TC@PSOP44 [SA638]  
MBM29LV200TC@TSOP48 [SB247-B4806]  
MBM29LV320BE (REVERSE)@TSOP48 [SB247-B4806]  
MBM29LV320BE@TSOP48 [SB247-B4806]  
MBM29LV320TE (REVERSE)@TSOP48 [SB247-B4806]  
MBM29LV320TE@TSOP48 [SB247-B4806]  
MBM29LV400B@PSOP44 [SA638] MBM29LV400B@TSOP48 [SB247-B4806]

MBM29LV400BB@PSOP44 [SA638]  
MBM29LV400BB@TSOP48 [SB247-B4806]  
MBM29LV400BC@PSOP44 [SA638]  
MBM29LV400BC@TSOP48 [SB247-B4806]  
MBM29LV400BT@PSOP44 [SA638]  
MBM29LV400BT@TSOP48 [SB247-B4806]  
MBM29LV400T@PSOP44 [SA638] MBM29LV400T@TSOP48 [SB247-B4806]  
MBM29LV400TC@PSOP44 [SA638]  
MBM29LV400TC@TSOP48 [SB247-B4806]  
MBM29LV650UE (REVERSE)@TSOP48 [SB247-B4806]  
MBM29LV650UE@TSOP48 [SB247-B4806]  
MBM29LV651UE (REVERSE)@TSOP48 [SB247-B4806]  
MBM29LV651UE@TSOP48 [SB247-B4806]  
MBM29LV800B@PSOP44 [SA638] MBM29LV800B@TSOP48 [SB247-B4806]  
MBM29LV800BA (REVERSE)@TSOP48 [SB247-B4806]  
MBM29LV800BA@PSOP44 [SA638]  
MBM29LV800BA@TSOP48 [SB247-B4806]  
MBM29LV800BB@PSOP44 [SA638]  
MBM29LV800BB@TSOP48 [SB247-B4806]  
MBM29LV800BE (REVERSE)@TSOP48 [SB247-B4806]  
MBM29LV800BE@PSOP44 [SA638]  
MBM29LV800BE@TSOP48 [SB247-B4806]  
MBM29LV800BT@PSOP44 [SA638]  
MBM29LV800BT@TSOP48 [SB247-B4806]  
MBM29LV800T@PSOP44 [SA638] MBM29LV800T@TSOP48 [SB247-B4806]  
MBM29LV800TA (REVERSE)@TSOP48 [SB247-B4806]  
MBM29LV800TA@PSOP44 [SA638]  
MBM29LV800TA@TSOP48 [SB247-B4806]  
MBM29LV800TE (REVERSE)@TSOP48 [SB247-B4806]  
MBM29LV800TE@PSOP44 [SA638]  
MBM29LV800TE@TSOP48 [SB247-B4806]  
MBM29PL160BD@PSOP44 [SA638]  
MBM29PL160BD@TSOP48 [SB247-B4806]  
MBM29PL160TD@PSOP44 [SA638]  
MBM29PL160TD@TSOP48 [SB247-B4806]  
MBM29PL32BM@TSOP48 [SB247-B4806] MBM29PL32TM@TSOP48 [SB247-B4806]  
MBM29PL64LM@TSOP48 [SB247-B4806] MBM29PL65LM@TSOP48 [SB247-B4806]  
MBM29SL160BD (REVERSE)@TSOP48 [SB247-B4806]  
MBM29SL160BD@TSOP48 [SB247-B4806]  
MBM29SL160TD (REVERSE)@TSOP48 [SB247-B4806]  
MBM29SL160TD@TSOP48 [SB247-B4806]  
MBM29SL800BD (REVERSE)@TSOP48 [SB247-B4806]  
MBM29SL800BD@TSOP48 [SB247-B4806]  
MBM29SL800TD (REVERSE)@TSOP48 [SB247-B4806]  
MBM29SL800TD@TSOP48 [SB247-B4806]  
S25FL001D@SOIC8 [SA602A] S25FL001D@USON8 [SA683]  
S25FL002A@SOIC8 [SA605B] S25FL002A@USON8 [SA683]  
S25FL002D@SOIC8 [SA602A] S25FL002D@USON8 [SA683]  
S25FL004A@SOIC8 [SA605B] S25FL004A@USON8 [SA683]  
S25FL004D@SOIC8 [SA602A] S25FL004D@USON8 [SA683]  
S25FL004K@SOIC8 (150 mil) [SA602A]  
S25FL004K@SOIC8 (208 mil) [SA605B]  
S25FL008A@SOIC8 [SA605B] S25FL008A@USON8 [SA683]

S25FL008D@SOIC8 [SA602A] S25FL008D@USON8 [SA683]  
S25FL008K@SOIC8(150 mil) [SA602A]  
S25FL008K@SOIC8(208 mil) [SA605B]  
S25FL016A@SOIC16 [SA783] S25FL016A@SOIC16(ISP)  
S25FL016A@SOIC16(Normal mode) [SA404]  
S25FL016A@SOIC8 [SA605B] S25FL016A@SOIC8(ISP)  
S25FL016A@SOIC8(Normal mode) [SA605B]  
S25FL016A@WSON8 [SA684] S25FL016A@WSON8(ISP)  
S25FL016A@WSON8(Normal mode) [SA684]  
S25FL016K@SOIC16 [SA783]  
S25FL016K@SOIC8(150 mil) [SA602A]  
S25FL016K@SOIC8(208 mil) [SA605B]  
S25FL020A@SOIC8(4.0) [SA602A] S25FL020A@SOIC8(5.4) [SA605B]  
S25FL020A@USON8 [SA683] S25FL032A@SOIC16 [SA783]  
S25FL032A@SOIC16(ISP)  
S25FL032A@SOIC16(Normal mode) [SA404]  
S25FL032A@WSON8 [SA684] S25FL032A@WSON8(ISP)  
S25FL032A@WSON8(Normal mode) [SA684]  
S25FL032K@SOIC16 [SA783]  
S25FL032K@SOIC8(150 mil) [SA602A]  
S25FL032K@SOIC8(208 mil) [SA605B]  
S25FL032P@SOIC16 [SA783] S25FL032P@SOIC8 [SA605B]  
S25FL040A(Bottom Boot)@SOP8(4.0) [SA602A]  
S25FL040A(Bottom Boot)@SOP8(5.4) [SA605B]  
S25FL040A(Bottom Boot)@USON8 [SA683]  
S25FL040A(Top Boot)@SOP8(4.0) [SA602A]  
S25FL040A(Top Boot)@SOP8(5.4) [SA605B]  
S25FL040A(Top Boot)@USON8 [SA683]  
S25FL040A@SOP8(4.0) [SA602A] S25FL040A@SOP8(5.4) [SA605B]  
S25FL040A@USON8 [SA683] S25FL064A@SOIC16 [SA783]  
S25FL064A@SOIC16(ISP)  
S25FL064A@SOIC16(Normal mode) [SA404]  
S25FL064A@WSON8 [SA684] S25FL064A@WSON8(ISP)  
S25FL064A@WSON8(Normal mode) [SA684]  
S25FL064K@SOIC16 [SA783]  
S25FL064K@SOIC8(150 mil) [SA602A]  
S25FL064K@SOIC8(208 mil) [SA605B]  
S25FL064P@SOIC16 [SA783] S25FL064P@SOIC16(4K bit) [SA783]  
S25FL080A@SOIC8(4.0) [SA602A] S25FL080A@SOIC8(5.4) [SA605B]  
S25FL080A@USON8 [SA683] S25FL128K@SOIC16 [SA783]  
S25FL128P(256 KB)@SOIC16 [SA783] S25FL128P(256 KB)@SOIC16(ISP)  
S25FL128P(256 KB)@WSON8 [SA684] S25FL128P(256 KB)@WSON8(ISP)  
S25FL128P(64 KB)@SOIC16 [SA783] S25FL128P(64 KB)@SOIC16(ISP)  
S25FL128P(64 KB)@WSON8 [SA684] S25FL128P(64 KB)@WSON8(ISP)  
S25FL132K@BGA24(6\*4 pin) [TA088] S25FL132K@SOIC16 [SA783]  
S25FL132K@SOIC8(150 mil) [SA602A]  
S25FL132K@SOIC8(200 mil) [SA605B]  
S25FL132K@WSON8 [SA683] S25FL164K@BGA24(6\*4 pin) [TA088]  
S25FL164K@SOIC8(150 mil) [SA602A]  
S25FL164K@SOIC8(200 mil) [SA605B]  
S25FL204K@SOIC8[150 mil] [SA602A]  
S25FL204K@SOIC8[208 mil] [SA605B]  
S25FL208K@SOIC8[150 mil] [SA602A]

S25FL208K@SOIC8[208 mil] [SA605B]  
S25FL216K@SOIC8[150 mil] [SA602A]  
S25FL216K@SOIC8[208 mil] [SA605B]  
S25FLK05D@SOIC8 [SA602A] S25FLK05D@USON8 [SA683]  
S29AD016D11MFA01@PSOP44 [SA638] S29AD016D11MFA02@PSOP44 [SA638]  
S29AD016D11MFB01@PSOP44 [SA638] S29AD016D11MFB02@PSOP44 [SA638]  
S29AD016D11MFI01@PSOP44 [SA638] S29AD016D11MFI02@PSOP44 [SA638]  
S29AD016D11MFV01@PSOP44 [SA638] S29AD016D11MFV02@PSOP44 [SA638]  
S29AD016D11TFA01@TSOP48 [SB247-B4806]  
S29AD016D11TFA02@TSOP48 [SB247-B4806]  
S29AD016D11TFB01@TSOP48 [SB247-B4806]  
S29AD016D11TFB02@TSOP48 [SB247-B4806]  
S29AD016D11TFI01@TSOP48 [SB247-B4806]  
S29AD016D11TFI02@TSOP48 [SB247-B4806]  
S29AD016D11TFV01@TSOP48 [SB247-B4806]  
S29AD016D11TFV02@TSOP48 [SB247-B4806]  
S29AL002B55MAI01@PSOP44 [SA638] S29AL002B55MAI02@PSOP44 [SA638]  
S29AL002B55MFI01@PSOP44 [SA638] S29AL002B55MFI02@PSOP44 [SA638]  
S29AL002B55TAI01@TSOP48 [SB247-B4806]  
S29AL002B55TAI02@TSOP48 [SB247-B4806]  
S29AL002B55TFI01@TSOP48 [SB247-B4806]  
S29AL002B55TFI02@TSOP48 [SB247-B4806]  
S29AL004B55MAI01@PSOP44 [SA638] S29AL004B55MAI02@PSOP44 [SA638]  
S29AL004B55MFI01@PSOP44 [SA638] S29AL004B55MFI02@PSOP44 [SA638]  
S29AL004B55TAI01@TSOP48 [SB247-B4806]  
S29AL004B55TAI02@TSOP48 [SB247-B4806]  
S29AL004B55TFI01@TSOP48 [SB247-B4806]  
S29AL004B55TFI02@TSOP48 [SB247-B4806]  
S29AL004D55MAI01@PSOP44 [SA638] S29AL004D55MAI02@PSOP44 [SA638]  
S29AL004D55MANR1@PSOP44 [SA638] S29AL004D55MANR2@PSOP44 [SA638]  
S29AL004D55MFI01@PSOP44 [SA638] S29AL004D55MFI02@PSOP44 [SA638]  
S29AL004D55MFNR1@PSOP44 [SA638] S29AL004D55MFNR2@PSOP44 [SA638]  
S29AL004D55TAI01@TSOP48 [SB247-B4806]  
S29AL004D55TAI02@TSOP48 [SB247-B4806]  
S29AL004D55TANR1@TSOP48 [SB247-B4806]  
S29AL004D55TANR2@TSOP48 [SB247-B4806]  
S29AL004D55TFI01@TSOP48 [SB247-B4806]  
S29AL004D55TFI02@TSOP48 [SB247-B4806]  
S29AL004D55TFNR1@TSOP48 [SB247-B4806]  
S29AL004D55TFNR2@TSOP48 [SB247-B4806]  
S29AL004D70MAI01@PSOP44 [SA638] S29AL004D70MAI02@PSOP44 [SA638]  
S29AL004D70MAN01@PSOP44 [SA638] S29AL004D70MAN02@PSOP44 [SA638]  
S29AL004D70MFI01@PSOP44 [SA638] S29AL004D70MFI02@PSOP44 [SA638]  
S29AL004D70MFN01@PSOP44 [SA638] S29AL004D70MFN02@PSOP44 [SA638]  
S29AL004D70TAI01@TSOP48 [SB247-B4806]  
S29AL004D70TAI02@TSOP48 [SB247-B4806]  
S29AL004D70TAN01@TSOP48 [SB247-B4806]  
S29AL004D70TAN02@TSOP48 [SB247-B4806]  
S29AL004D70TFI01@TSOP48 [SB247-B4806]  
S29AL004D70TFI02@TSOP48 [SB247-B4806]  
S29AL004D70TFN01@TSOP48 [SB247-B4806]  
S29AL004D70TFN02@TSOP48 [SB247-B4806]  
S29AL004D90MAI01@PSOP44 [SA638] S29AL004D90MAI02@PSOP44 [SA638]

S29AL004D90MAN01@PSOP44 [SA638] S29AL004D90MAN02@PSOP44 [SA638]  
S29AL004D90MFI01@PSOP44 [SA638] S29AL004D90MFI02@PSOP44 [SA638]  
S29AL004D90MFN01@PSOP44 [SA638] S29AL004D90MFN02@PSOP44 [SA638]  
S29AL004D90TAI01@TSOP48 [SB247-B4806]  
S29AL004D90TAI02@TSOP48 [SB247-B4806]  
S29AL004D90TAN01@TSOP48 [SB247-B4806]  
S29AL004D90TAN02@TSOP48 [SB247-B4806]  
S29AL004D90TFI01@TSOP48 [SB247-B4806]  
S29AL004D90TFI02@TSOP48 [SB247-B4806]  
S29AL004D90TFN01@TSOP48 [SB247-B4806]  
S29AL004D90TFN02@TSOP48 [SB247-B4806]  
S29AL008D55MAIR1@PSOP44 [SA638] S29AL008D55MAIR2@PSOP44 [SA638]  
S29AL008D55MFIR1@PSOP44 [SA638] S29AL008D55MFIR2@PSOP44 [SA638]  
S29AL008D55TAIR1@TSOP48 [SB247-B4806]  
S29AL008D55TAIR2@TSOP48 [SB247-B4806]  
S29AL008D55TFIR1@TSOP48 [SB247-B4806]  
S29AL008D55TFIR2@TSOP48 [SB247-B4806]  
S29AL008D60MAI01@PSOP44 [SA638] S29AL008D60MAI02@PSOP44 [SA638]  
S29AL008D60MAN01@PSOP44 [SA638] S29AL008D60MAN02@PSOP44 [SA638]  
S29AL008D60MFI01@PSOP44 [SA638] S29AL008D60MFI02@PSOP44 [SA638]  
S29AL008D60MFN01@PSOP44 [SA638] S29AL008D60MFN02@PSOP44 [SA638]  
S29AL008D60TAI01@TSOP48 [SB247-B4806]  
S29AL008D60TAI02@TSOP48 [SB247-B4806]  
S29AL008D60TAN01@TSOP48 [SB247-B4806]  
S29AL008D60TAN02@TSOP48 [SB247-B4806]  
S29AL008D60TFI01@TSOP48 [SB247-B4806]  
S29AL008D60TFI02@TSOP48 [SB247-B4806]  
S29AL008D60TFN01@TSOP48 [SB247-B4806]  
S29AL008D60TFN02@TSOP48 [SB247-B4806]  
S29AL008D70MAI01@PSOP44 [SA638] S29AL008D70MAI02@PSOP44 [SA638]  
S29AL008D70MAN01@PSOP44 [SA638] S29AL008D70MAN02@PSOP44 [SA638]  
S29AL008D70MFI01@PSOP44 [SA638] S29AL008D70MFI02@PSOP44 [SA638]  
S29AL008D70MFN01@PSOP44 [SA638] S29AL008D70MFN02@PSOP44 [SA638]  
S29AL008D70TAI01@TSOP48 [SB247-B4806]  
S29AL008D70TAI02@TSOP48 [SB247-B4806]  
S29AL008D70TAN01@TSOP48 [SB247-B4806]  
S29AL008D70TAN02@TSOP48 [SB247-B4806]  
S29AL008D70TFI01@TSOP48 [SB247-B4806]  
S29AL008D70TFI02@TSOP48 [SB247-B4806]  
S29AL008D70TFN01@TSOP48 [SB247-B4806]  
S29AL008D70TFN02@TSOP48 [SB247-B4806]  
S29AL008D90MAI01@PSOP44 [SA638] S29AL008D90MAI02@PSOP44 [SA638]  
S29AL008D90MAN01@PSOP44 [SA638] S29AL008D90MAN02@PSOP44 [SA638]  
S29AL008D90MFI01@PSOP44 [SA638] S29AL008D90MFI02@PSOP44 [SA638]  
S29AL008D90MFN01@PSOP44 [SA638] S29AL008D90MFN02@PSOP44 [SA638]  
S29AL008D90TAI01@TSOP48 [SB247-B4806]  
S29AL008D90TAI02@TSOP48 [SB247-B4806]  
S29AL008D90TAN01@TSOP48 [SB247-B4806]  
S29AL008D90TAN02@TSOP48 [SB247-B4806]  
S29AL008D90TFI01@TSOP48 [SB247-B4806]  
S29AL008D90TFI02@TSOP48 [SB247-B4806]  
S29AL008D90TFN01@TSOP48 [SB247-B4806]  
S29AL008D90TFN02@TSOP48 [SB247-B4806]

S29AL008J55TFIR1@TSOP48 [SA247-B4806]  
S29AL008J55TFIR2@TSOP48 [SA247-B4806]  
S29AL008J55TFNR1@TSOP48 [SA247-B4806]  
S29AL008J55TFNR2@TSOP48 [SA247-B4806]  
S29AL008J70TFI01@TSOP48 [SA247-B4806]  
S29AL008J70TFI02@TSOP48 [SA247-B4806]  
S29AL008J70TFI03@TSOP48 [SA247-B4806]  
S29AL008J70TFI04@TSOP48 [SA247-B4806]  
S29AL008J70TFN01@TSOP48 [SA247-B4806]  
S29AL008J70TFN02@TSOP48 [SA247-B4806]  
S29AL016D70MAI01@PSOP44 [SA638] S29AL016D70MAI02@PSOP44 [SA638]  
S29AL016D70MAN01@PSOP44 [SA638] S29AL016D70MAN02@PSOP44 [SA638]  
S29AL016D70MFI01@PSOP44 [SA638] S29AL016D70MFI02@PSOP44 [SA638]  
S29AL016D70MFN01@PSOP44 [SA638] S29AL016D70MFN02@PSOP44 [SA638]  
S29AL016D70TAI01@TSOP48 [SB247-B4806]  
S29AL016D70TAI02@TSOP48 [SB247-B4806]  
S29AL016D70TAN01@TSOP48 [SB247-B4806]  
S29AL016D70TAN02@TSOP48 [SB247-B4806]  
S29AL016D70TFI01@TSOP48 [SB247-B4806]  
S29AL016D70TFI02@TSOP48 [SB247-B4806]  
S29AL016D70TFN01@TSOP48 [SB247-B4806]  
S29AL016D70TFN02@TSOP48 [SB247-B4806]  
S29AL016D90MAI01@PSOP44 [SA638] S29AL016D90MAI02@PSOP44 [SA638]  
S29AL016D90MAN01@PSOP44 [SA638] S29AL016D90MAN02@PSOP44 [SA638]  
S29AL016D90MFI01@PSOP44 [SA638] S29AL016D90MFI02@PSOP44 [SA638]  
S29AL016D90MFN01@PSOP44 [SA638] S29AL016D90MFN02@PSOP44 [SA638]  
S29AL016D90TAI01@TSOP48 [SB247-B4806]  
S29AL016D90TAI02@TSOP48 [SB247-B4806]  
S29AL016D90TAN01@TSOP48 [SB247-B4806]  
S29AL016D90TAN02@TSOP48 [SB247-B4806]  
S29AL016D90TFI01@TSOP48 [SB247-B4806]  
S29AL016D90TFI02@TSOP48 [SB247-B4806]  
S29AL016D90TFN01@TSOP48 [SB247-B4806]  
S29AL016D90TFN02@TSOP48 [SB247-B4806]  
S29AL016J55TFIR1@TSOP48 [SA247-B4806]  
S29AL016J55TFIR2@TSOP48 [SA247-B4806]  
S29AL016J55TFNR1@TSOP48 [SA247-B4806]  
S29AL016J55TFNR2@TSOP48 [SA247-B4806]  
S29AL016J70TFI01@TSOP48 [SA247-B4806]  
S29AL016J70TFI02@TSOP48 [SA247-B4806]  
S29AL016J70TFI03@TSOP48 [SA247-B4806]  
S29AL016J70TFI04@TSOP48 [SA247-B4806]  
S29AL016J70TFN01@TSOP48 [SA247-B4806]  
S29AL016J70TFN02@TSOP48 [SA247-B4806]  
S29AL016M10TAI01@TSOP48 [SB247-B4806]  
S29AL016M10TAI02@TSOP48 [SB247-B4806]  
S29AL016M10TAIR1@TSOP48 [SB247-B4806]  
S29AL016M10TAIR2@TSOP48 [SB247-B4806]  
S29AL016M10TFI01@TSOP48 [SB247-B4806]  
S29AL016M10TFI02@TSOP48 [SB247-B4806]  
S29AL016M10TFIR1@TSOP48 [SB247-B4806]  
S29AL016M10TFIR2@TSOP48 [SB247-B4806]  
S29AL016M90TAI01@TSOP48 [SB247-B4806]

S29AL016M90TAI02@TSOP48 [SB247-B4806]  
S29AL016M90TAIR1@TSOP48 [SB247-B4806]  
S29AL016M90TAIR2@TSOP48 [SB247-B4806]  
S29AL016M90TFI01@TSOP48 [SB247-B4806]  
S29AL016M90TFI02@TSOP48 [SB247-B4806]  
S29AL016M90TFIR1@TSOP48 [SB247-B4806]  
S29AL016M90TFIR2@TSOP48 [SB247-B4806]  
S29AL032D70TAI00@TSOP40 [SA409T-B4002]  
S29AL032D70TAI03@TSOP48 [SB247-B4806]  
S29AL032D70TAI04@TSOP48 [SB247-B4806]  
S29AL032D70TFI00@TSOP40 [SA409T-B4002]  
S29AL032D70TFI03@TSOP48 [SB247-B4806]  
S29AL032D70TFI04@TSOP48 [SB247-B4806]  
S29AL032D90TAI00@TSOP40 [SA409T-B4002]  
S29AL032D90TAI03@TSOP48 [SB247-B4806]  
S29AL032D90TAI04@TSOP48 [SB247-B4806]  
S29AL032D90TAN00@TSOP40 [SA409T-B4002]  
S29AL032D90TAN03@TSOP48 [SB247-B4806]  
S29AL032D90TAN04@TSOP48 [SB247-B4806]  
S29AL032D90TFI00@TSOP40 [SA409T-B4002]  
S29AL032D90TFI03@TSOP48 [SB247-B4806]  
S29AL032D90TFI04@TSOP48 [SB247-B4806]  
S29AL032D90TFN00@TSOP40 [SA409T-B4002]  
S29AL032D90TFN03@TSOP48 [SB247-B4806]  
S29AL032D90TFN04@TSOP48 [SB247-B4806]  
S29AS008J70TFI01@TSOP48 [SB247-B4806]  
S29AS008J70TFI02@TSOP48 [SB247-B4806]  
S29AS008J70TFI03@TSOP48 [SB247-B4806]  
S29AS008J70TFI04@TSOP48 [SB247-B4806]  
S29AS016J70TFI01@TSOP48 [SB247-B4806]  
S29AS016J70TFI02@TSOP48 [SB247-B4806]  
S29AS016J70TFI03@TSOP48 [SB247-B4806]  
S29AS016J70TFI04@TSOP48 [SB247-B4806]  
S29GL016A10TAI01@TSOP48 [SB247-B4806]  
S29GL016A10TAI02@TSOP48 [SB247-B4806]  
S29GL016A10TAI03@TSOP48 [SB247-B4806]  
S29GL016A10TAI04@TSOP48 [SB247-B4806]  
S29GL016A10TAIR1@TSOP48 [SB247-B4806]  
S29GL016A10TAIR2@TSOP48 [SB247-B4806]  
S29GL016A10TAIR3@TSOP48 [SB247-B4806]  
S29GL016A10TAIR4@TSOP48 [SB247-B4806]  
S29GL016A10TFI01@TSOP48 [SB247-B4806]  
S29GL016A10TFI02@TSOP48 [SB247-B4806]  
S29GL016A10TFI03@TSOP48 [SB247-B4806]  
S29GL016A10TFI04@TSOP48 [SB247-B4806]  
S29GL016A10TFIR1@TSOP48 [SB247-B4806]  
S29GL016A10TFIR2@TSOP48 [SB247-B4806]  
S29GL016A10TFIR3@TSOP48 [SB247-B4806]  
S29GL016A10TFIR4@TSOP48 [SB247-B4806]  
S29GL016A90TAIR1@TSOP48 [SB247-B4806]  
S29GL016A90TAIR2@TSOP48 [SB247-B4806]  
S29GL016A90TAIR3@TSOP48 [SB247-B4806]  
S29GL016A90TAIR4@TSOP48 [SB247-B4806]

S29GL016A90TFIR1@TSOP48 [SB247-B4806]  
S29GL016A90TFIR2@TSOP48 [SB247-B4806]  
S29GL016A90TFIR3@TSOP48 [SB247-B4806]  
S29GL016A90TFIR4@TSOP48 [SB247-B4806]  
S29GL032A10TAIR3@TSOP48 [SB247-B4806]  
S29GL032A10TAIR4@TSOP48 [SB247-B4806]  
S29GL032A10TFIR3@TSOP48 [SB247-B4806]  
S29GL032A10TFIR4@TSOP48 [SB247-B4806]  
S29GL032A11TAIR3@TSOP48 [SB247-B4806]  
S29GL032A11TAIR4@TSOP48 [SB247-B4806]  
S29GL032A11TFIR3@TSOP48 [SB247-B4806]  
S29GL032A11TFIR4@TSOP48 [SB247-B4806]  
S29GL032A90TAIR3@TSOP48 [SB247-B4806]  
S29GL032A90TAIR4@TSOP48 [SB247-B4806]  
S29GL032A90TFIR3@TSOP48 [SB247-B4806]  
S29GL032A90TFIR4@TSOP48 [SB247-B4806]  
S29GL032M10TAIR3@TSOP48 [SB247-B4806]  
S29GL032M10TAIR4@TSOP48 [SB247-B4806]  
S29GL032M10TBIR3@TSOP48 [SB247-B4806]  
S29GL032M10TBIR4@TSOP48 [SB247-B4806]  
S29GL032M10TCIR3@TSOP48 [SB247-B4806]  
S29GL032M10TCIR4@TSOP48 [SB247-B4806]  
S29GL032M10TFIR3@TSOP48 [SB247-B4806]  
S29GL032M10TFIR4@TSOP48 [SB247-B4806]  
S29GL032M11TAIR3@TSOP48 [SB247-B4806]  
S29GL032M11TAIR4@TSOP48 [SB247-B4806]  
S29GL032M11TBIR3@TSOP48 [SB247-B4806]  
S29GL032M11TBIR4@TSOP48 [SB247-B4806]  
S29GL032M11TCIR3@TSOP48 [SB247-B4806]  
S29GL032M11TCIR4@TSOP48 [SB247-B4806]  
S29GL032M11TFIR3@TSOP48 [SB247-B4806]  
S29GL032M11TFIR4@TSOP48 [SB247-B4806]  
S29GL032M90TACR0@TSOP40 [SA409T-B4002]  
S29GL032M90TACR3@TSOP48 [SB247-B4806]  
S29GL032M90TACR4@TSOP48 [SB247-B4806]  
S29GL032M90TAIR0@TSOP40 [SA409T-B4002]  
S29GL032M90TAIR3@TSOP48 [SB247-B4806]  
S29GL032M90TAIR4@TSOP48 [SB247-B4806]  
S29GL032M90TBIR3@TSOP48 [SB247-B4806]  
S29GL032M90TBIR4@TSOP48 [SB247-B4806]  
S29GL032M90TCIR3@TSOP48 [SB247-B4806]  
S29GL032M90TCIR4@TSOP48 [SB247-B4806]  
S29GL032M90TFCR0@TSOP40 [SA409T-B4002]  
S29GL032M90TFCR3@TSOP48 [SB247-B4806]  
S29GL032M90TFCR4@TSOP48 [SB247-B4806]  
S29GL032M90TFIR0@TSOP40 [SA409T-B4002]  
S29GL032M90TFIR3@TSOP48 [SB247-B4806]  
S29GL032M90TFIR4@TSOP48 [SB247-B4806]  
S29GL032N70TAI03@TSOP48 [SB247-B4806]  
S29GL032N70TAI04@TSOP48 [SB247-B4806]  
S29GL032N70TAIR3@TSOP48 [SB247-B4806]  
S29GL032N70TAIR4@TSOP48 [SB247-B4806]  
S29GL032N70TFI03@TSOP48 [SB247-B4806]

S29GL032N70TFI04@TSOP48 [SB247-B4806]  
S29GL032N70TFIR3@TSOP48 [SB247-B4806]  
S29GL032N70TFIR4@TSOP48 [SB247-B4806]  
S29GL032N90TAI03@TSOP48 [SB247-B4806]  
S29GL032N90TAI04@TSOP48 [SB247-B4806]  
S29GL032N90TAIR3@TSOP48 [SB247-B4806]  
S29GL032N90TAIR4@TSOP48 [SB247-B4806]  
S29GL032N90TFI03@TSOP48 [SB247-B4806]  
S29GL032N90TFI04@TSOP48 [SB247-B4806]  
S29GL032N90TFIR3@TSOP48 [SB247-B4806]  
S29GL032N90TFIR4@TSOP48 [SB247-B4806]  
S29GL064A10TAIR3@TSOP48 [SB247-B4806]  
S29GL064A10TAIR4@TSOP48 [SB247-B4806]  
S29GL064A10TAIR6@TSOP48 [SB247-B4806]  
S29GL064A10TAIR7@TSOP48 [SB247-B4806]  
S29GL064A10TAIR8@TSOP48 [SB247-B4806]  
S29GL064A10TAIR9@TSOP48 [SB247-B4806]  
S29GL064A10TFIR3@TSOP48 [SB247-B4806]  
S29GL064A10TFIR4@TSOP48 [SB247-B4806]  
S29GL064A10TFIR6@TSOP48 [SB247-B4806]  
S29GL064A10TFIR7@TSOP48 [SB247-B4806]  
S29GL064A10TFIR8@TSOP48 [SB247-B4806]  
S29GL064A10TFIR9@TSOP48 [SB247-B4806]  
S29GL064A11TAIR3@TSOP48 [SB247-B4806]  
S29GL064A11TAIR4@TSOP48 [SB247-B4806]  
S29GL064A11TAIR6@TSOP48 [SB247-B4806]  
S29GL064A11TAIR7@TSOP48 [SB247-B4806]  
S29GL064A11TAIR8@TSOP48 [SB247-B4806]  
S29GL064A11TAIR9@TSOP48 [SB247-B4806]  
S29GL064A11TFIR3@TSOP48 [SB247-B4806]  
S29GL064A11TFIR4@TSOP48 [SB247-B4806]  
S29GL064A11TFIR6@TSOP48 [SB247-B4806]  
S29GL064A11TFIR7@TSOP48 [SB247-B4806]  
S29GL064A11TFIR8@TSOP48 [SB247-B4806]  
S29GL064A11TFIR9@TSOP48 [SB247-B4806]  
S29GL064A90TAIR3@TSOP48 [SB247-B4806]  
S29GL064A90TAIR4@TSOP48 [SB247-B4806]  
S29GL064A90TAIR6@TSOP48 [SB247-B4806]  
S29GL064A90TAIR7@TSOP48 [SB247-B4806]  
S29GL064A90TAIR8@TSOP48 [SB247-B4806]  
S29GL064A90TAIR9@TSOP48 [SB247-B4806]  
S29GL064A90TFIR3@TSOP48 [SB247-B4806]  
S29GL064A90TFIR4@TSOP48 [SB247-B4806]  
S29GL064A90TFIR6@TSOP48 [SB247-B4806]  
S29GL064A90TFIR7@TSOP48 [SB247-B4806]  
S29GL064A90TFIR8@TSOP48 [SB247-B4806]  
S29GL064A90TFIR9@TSOP48 [SB247-B4806]  
S29GL064M10TAIR3@TSOP48 [SB247-B4806]  
S29GL064M10TAIR4@TSOP48 [SB247-B4806]  
S29GL064M10TAIR6@TSOP48 [SB247-B4806]  
S29GL064M10TAIR7@TSOP48 [SB247-B4806]  
S29GL064M10TBIR6@TSOP48 [SB247-B4806]  
S29GL064M10TBIR7@TSOP48 [SB247-B4806]

S29GL064M10TCIR6@TSOP48 [SB247-B4806]  
S29GL064M10TCIR7@TSOP48 [SB247-B4806]  
S29GL064M10TFIR3@TSOP48 [SB247-B4806]  
S29GL064M10TFIR4@TSOP48 [SB247-B4806]  
S29GL064M10TFIR6@TSOP48 [SB247-B4806]  
S29GL064M10TFIR7@TSOP48 [SB247-B4806]  
S29GL064M11TAIR3@TSOP48 [SB247-B4806]  
S29GL064M11TAIR4@TSOP48 [SB247-B4806]  
S29GL064M11TAIR6@TSOP48 [SB247-B4806]  
S29GL064M11TAIR7@TSOP48 [SB247-B4806]  
S29GL064M11TBIR6@TSOP48 [SB247-B4806]  
S29GL064M11TBIR7@TSOP48 [SB247-B4806]  
S29GL064M11TCIR6@TSOP48 [SB247-B4806]  
S29GL064M11TCIR7@TSOP48 [SB247-B4806]  
S29GL064M11TFIR3@TSOP48 [SB247-B4806]  
S29GL064M11TFIR4@TSOP48 [SB247-B4806]  
S29GL064M11TFIR6@TSOP48 [SB247-B4806]  
S29GL064M11TFIR7@TSOP48 [SB247-B4806]  
S29GL064M90TAIR0@TSOP48 [SB247-B4806]  
S29GL064M90TAIR3@TSOP48 [SB247-B4806]  
S29GL064M90TAIR4@TSOP48 [SB247-B4806]  
S29GL064M90TAIR6@TSOP48 [SB247-B4806]  
S29GL064M90TAIR7@TSOP48 [SB247-B4806]  
S29GL064M90TBIR6@TSOP48 [SB247-B4806]  
S29GL064M90TBIR7@TSOP48 [SB247-B4806]  
S29GL064M90TCIR6@TSOP48 [SB247-B4806]  
S29GL064M90TCIR7@TSOP48 [SB247-B4806]  
S29GL064M90TFIR0@TSOP48 [SB247-B4806]  
S29GL064M90TFIR3@TSOP48 [SB247-B4806]  
S29GL064M90TFIR4@TSOP48 [SB247-B4806]  
S29GL064M90TFIR6@TSOP48 [SB247-B4806]  
S29GL064M90TFIR7@TSOP48 [SB247-B4806]  
S29GL064N70TAI03@TSOP48 [SB247-B4806]  
S29GL064N70TAI04@TSOP48 [SB247-B4806]  
S29GL064N70TAI06@TSOP48 [SB247-B4806]  
S29GL064N70TAI07@TSOP48 [SB247-B4806]  
S29GL064N70TAIR3@TSOP48 [SB247-B4806]  
S29GL064N70TAIR4@TSOP48 [SB247-B4806]  
S29GL064N70TAIR6@TSOP48 [SB247-B4806]  
S29GL064N70TAIR7@TSOP48 [SB247-B4806]  
S29GL064N70TFI03@TSOP48 [SB247-B4806]  
S29GL064N70TFI04@TSOP48 [SB247-B4806]  
S29GL064N70TFI06@TSOP48 [SB247-B4806]  
S29GL064N70TFI07@TSOP48 [SB247-B4806]  
S29GL064N70TFIR3@TSOP48 [SB247-B4806]  
S29GL064N70TFIR4@TSOP48 [SB247-B4806]  
S29GL064N70TFIR6@TSOP48 [SB247-B4806]  
S29GL064N70TFIR7@TSOP48 [SB247-B4806]  
S29GL064N90TAI03@TSOP48 [SB247-B4806]  
S29GL064N90TAI04@TSOP48 [SB247-B4806]  
S29GL064N90TAI06@TSOP48 [SB247-B4806]  
S29GL064N90TAI07@TSOP48 [SB247-B4806]  
S29GL064N90TAIR3@TSOP48 [SB247-B4806]

S29GL064N90TAIR4@TSOP48 [SB247-B4806]  
S29GL064N90TAIR6@TSOP48 [SB247-B4806]  
S29GL064N90TAIR7@TSOP48 [SB247-B4806]  
S29GL064N90TAIV6@TSOP48 [SB247-B4806]  
S29GL064N90TAIV7@TSOP48 [SB247-B4806]  
S29GL064N90TFI03@TSOP48 [SB247-B4806]  
S29GL064N90TFI04@TSOP48 [SB247-B4806]  
S29GL064N90TFI06@TSOP48 [SB247-B4806]  
S29GL064N90TFI07@TSOP48 [SB247-B4806]  
S29GL064N90TFIR3@TSOP48 [SB247-B4806]  
S29GL064N90TFIR4@TSOP48 [SB247-B4806]  
S29GL064N90TFIR6@TSOP48 [SB247-B4806]  
S29GL064N90TFIR7@TSOP48 [SB247-B4806]  
S29GL064N90TFIV6@TSOP48 [SB247-B4806]  
S29GL064N90TFIV7@TSOP48 [SB247-B4806]  
S29JL032H55TAI01@TSOP48 [SB247-B4806]  
S29JL032H55TAI02@TSOP48 [SB247-B4806]  
S29JL032H55TAI21@TSOP48 [SB247-B4806]  
S29JL032H55TAI22@TSOP48 [SB247-B4806]  
S29JL032H55TAI31@TSOP48 [SB247-B4806]  
S29JL032H55TAI32@TSOP48 [SB247-B4806]  
S29JL032H55TAI41@TSOP48 [SB247-B4806]  
S29JL032H55TAI42@TSOP48 [SB247-B4806]  
S29JL032H55TFI01@TSOP48 [SB247-B4806]  
S29JL032H55TFI02@TSOP48 [SB247-B4806]  
S29JL032H55TFI21@TSOP48 [SB247-B4806]  
S29JL032H55TFI22@TSOP48 [SB247-B4806]  
S29JL032H55TFI31@TSOP48 [SB247-B4806]  
S29JL032H55TFI32@TSOP48 [SB247-B4806]  
S29JL032H55TFI41@TSOP48 [SB247-B4806]  
S29JL032H55TFI42@TSOP48 [SB247-B4806]  
S29JL032H60TAI01@TSOP48 [SB247-B4806]  
S29JL032H60TAI02@TSOP48 [SB247-B4806]  
S29JL032H60TAI21@TSOP48 [SB247-B4806]  
S29JL032H60TAI22@TSOP48 [SB247-B4806]  
S29JL032H60TAI31@TSOP48 [SB247-B4806]  
S29JL032H60TAI32@TSOP48 [SB247-B4806]  
S29JL032H60TAI41@TSOP48 [SB247-B4806]  
S29JL032H60TAI42@TSOP48 [SB247-B4806]  
S29JL032H60TFI01@TSOP48 [SB247-B4806]  
S29JL032H60TFI02@TSOP48 [SB247-B4806]  
S29JL032H60TFI21@TSOP48 [SB247-B4806]  
S29JL032H60TFI22@TSOP48 [SB247-B4806]  
S29JL032H60TFI31@TSOP48 [SB247-B4806]  
S29JL032H60TFI32@TSOP48 [SB247-B4806]  
S29JL032H60TFI41@TSOP48 [SB247-B4806]  
S29JL032H60TFI42@TSOP48 [SB247-B4806]  
S29JL032H70TAI01@TSOP48 [SB247-B4806]  
S29JL032H70TAI02@TSOP48 [SB247-B4806]  
S29JL032H70TAI21@TSOP48 [SB247-B4806]  
S29JL032H70TAI22@TSOP48 [SB247-B4806]  
S29JL032H70TAI31@TSOP48 [SB247-B4806]  
S29JL032H70TAI32@TSOP48 [SB247-B4806]

S29JL032H70TAI41@TSOP48 [SB247-B4806]  
S29JL032H70TAI42@TSOP48 [SB247-B4806]  
S29JL032H70TFI01@TSOP48 [SB247-B4806]  
S29JL032H70TFI02@TSOP48 [SB247-B4806]  
S29JL032H70TFI21@TSOP48 [SB247-B4806]  
S29JL032H70TFI22@TSOP48 [SB247-B4806]  
S29JL032H70TFI31@TSOP48 [SB247-B4806]  
S29JL032H70TFI32@TSOP48 [SB247-B4806]  
S29JL032H70TFI41@TSOP48 [SB247-B4806]  
S29JL032H70TFI42@TSOP48 [SB247-B4806]  
S29JL032H90TAI01@TSOP48 [SB247-B4806]  
S29JL032H90TAI02@TSOP48 [SB247-B4806]  
S29JL032H90TAI21@TSOP48 [SB247-B4806]  
S29JL032H90TAI22@TSOP48 [SB247-B4806]  
S29JL032H90TAI31@TSOP48 [SB247-B4806]  
S29JL032H90TAI32@TSOP48 [SB247-B4806]  
S29JL032H90TAI41@TSOP48 [SB247-B4806]  
S29JL032H90TAI42@TSOP48 [SB247-B4806]  
S29JL032H90TFI01@TSOP48 [SB247-B4806]  
S29JL032H90TFI02@TSOP48 [SB247-B4806]  
S29JL032H90TFI21@TSOP48 [SB247-B4806]  
S29JL032H90TFI22@TSOP48 [SB247-B4806]  
S29JL032H90TFI31@TSOP48 [SB247-B4806]  
S29JL032H90TFI32@TSOP48 [SB247-B4806]  
S29JL032H90TFI41@TSOP48 [SB247-B4806]  
S29JL032H90TFI42@TSOP48 [SB247-B4806]  
S29JL032J60TFI01@TSOP48 [SB247-B4806]  
S29JL032J60TFI02@TSOP48 [SB247-B4806]  
S29JL032J60TFI21@TSOP48 [SB247-B4806]  
S29JL032J60TFI22@TSOP48 [SB247-B4806]  
S29JL032J60TFI31@TSOP48 [SB247-B4806]  
S29JL032J60TFI32@TSOP48 [SB247-B4806]  
S29JL032J60TFI41@TSOP48 [SB247-B4806]  
S29JL032J60TFI42@TSOP48 [SB247-B4806]  
S29JL032J70TFI01@TSOP48 [SB247-B4806]  
S29JL032J70TFI02@TSOP48 [SB247-B4806]  
S29JL032J70TFI21@TSOP48 [SB247-B4806]  
S29JL032J70TFI22@TSOP48 [SB247-B4806]  
S29JL032J70TFI31@TSOP48 [SB247-B4806]  
S29JL032J70TFI32@TSOP48 [SB247-B4806]  
S29JL032J70TFI41@TSOP48 [SB247-B4806]  
S29JL032J70TFI42@TSOP48 [SB247-B4806]  
S29JL064H55TAI00@TSOP48 [SB247-B4806]  
S29JL064H55TFI00@TSOP48 [SB247-B4806]  
S29JL064H60TAI00@TSOP48 [SB247-B4806]  
S29JL064H60TFI00@TSOP48 [SB247-B4806]  
S29JL064H70TAI00@TSOP48 [SB247-B4806]  
S29JL064H70TAN00@TSOP48 [SB247-B4806]  
S29JL064H70TFI00@TSOP48 [SB247-B4806]  
S29JL064H70TFN00@TSOP48 [SB247-B4806]  
S29JL064H90TAI00@TSOP48 [SB247-B4806]  
S29JL064H90TAN00@TSOP48 [SB247-B4806]  
S29JL064H90TFI00@TSOP48 [SB247-B4806]

S29JL064H90TFN00@TSOP48 [SB247-B4806]  
S29JL064J55TFI00@TSOP48 [SB247-B4806]  
S29JL064J60TFI00@TSOP48 [SB247-B4806]  
S29JL064J70TFI00@TSOP48 [SB247-B4806]

## SSSC

### MICROCONTROLLER

SSU7301  
SSU7301@TQFP44 [SA675-B4805]

SSU7301@PLCC44 [SA244]

## SST

### E (E) PROM/FRAM/NVRAM

SST25LF010@SOIC8 (4. 0) [SA602A]	SST25LF010@SOIC8 (5. 4) [SA605B]
SST25LF010@WSON8 [SA683]	SST25LF010A@SOIC8 (4. 0) [SA602A]
SST25LF010A@SOIC8 (5. 4) [SA605B]	SST25LF010A@WSON8 [SA683]
SST25LF016A@SOIC8 (4. 0) [SA602A]	SST25LF016A@SOIC8 (5. 4) [SA605B]
SST25LF016A@WSON8 [SA683]	SST25LF016B@SOIC8 (4. 0) [SA602A]
SST25LF016B@SOIC8 (5. 4) [SA605B]	SST25LF016B@WSON8 [SA683]
SST25LF020@SOIC8 (4. 0) [SA602A]	SST25LF020@SOIC8 (5. 4) [SA605B]
SST25LF020@WSON8 [SA683]	SST25LF020A@SOIC8 (4. 0) [SA602A]
SST25LF020A@SOIC8 (5. 4) [SA605B]	SST25LF020A@WSON8 [SA683]
SST25LF040@SOIC8 (4. 0) [SA602A]	SST25LF040@SOIC8 (5. 4) [SA605B]
SST25LF040@WSON8 [SA683]	SST25LF040A@SOIC8 (4. 0) [SA602A]
SST25LF040A@SOIC8 (5. 4) [SA605B]	SST25LF040A@WSON8 [SA683]
SST25LF080@SOIC8 (4. 0) [SA602A]	SST25LF080@SOIC8 (5. 4) [SA605B]
SST25LF080@WSON8 [SA683]	SST25LF080A@SOIC8 (4. 0) [SA602A]
SST25LF080A@SOIC8 (5. 4) [SA605B]	SST25LF080A@WSON8 [SA683]
SST25PF020B@SOIC8 [SA602A]	SST25PF020B@USON8 [SA724]
SST25PF020B@WSON8 [SA683]	
SST25PF040B@SOIC8 [150mil] [SA602A]	
SST25PF040B@SOIC8 [200mil] [SA605B]	
SST25PF040B@WSON8 [SA683]	
SST25PF080B@SOIC8 [150mil] [SA602A]	
SST25PF080B@SOIC8 [200mil] [SA605B]	
SST25PF080B@WSON8 [SA683]	
SST25VF010@SOIC8 (5. 4) [SA605B]	SST25VF010@SOIC8 (4. 0) [SA602A]
SST25VF010A@SOIC8 (4. 0) [SA602A]	SST25VF010@WSON8 [SA683]
SST25VF010A@WSON8 [SA683]	SST25VF010A@SOIC8 (5. 4) [SA605B]
SST25VF016B@SOIC8 (5. 4) [SA605B]	SST25VF016B@SOIC8 (4. 0) [SA602A]
SST25VF020@SOIC8 (4. 0) [SA602A]	SST25VF016B@WSON8 [SA683]
SST25VF020@WSON8 [SA683]	SST25VF020@SOIC8 (5. 4) [SA605B]
SST25VF020B@SOIC8 (5. 4) [SA605B]	SST25VF020B@SOIC8 (4. 0) [SA602A]
SST25VF032B@SOIC16 [SA404]	SST25VF020B@WSON8 [SA683]
SST25VF032B@SOIC8 (5. 4) [SA605B]	SST25VF032B@SOIC8 (4. 0) [SA602A]
SST25VF040@SOIC8 (4. 0) [SA602A]	SST25VF032B@WSON8 [SA683]
SST25VF040@WSON8 [SA683]	SST25VF040@SOIC8 (5. 4) [SA605B]
SST25VF040B@SOIC8 (5. 4) [SA605B]	SST25VF040B@SOIC8 (4. 0) [SA602A]
SST25VF064C@SOIC16 [SA404]	SST25VF040B@WSON8 [SA683]
	SST25VF064C@SOIC8 [SA605B]

SST25VF064C@WSON8 [SA684]  
SST25VF080@SOIC8 (5.4) [SA605B]  
SST25VF080B@SOIC8 (4.0) [SA602A]  
SST25VF080B@WSON8 [SA683]  
SST25VF512@SOIC8 (5.4) [SA605B]  
SST25VF512A@SOIC8 (4.0) [SA602A]  
SST25VF512A@WSON8 [SA683]  
SST25WF010@SOIC8 (5.4) [SA605B]  
SST25WF020@SOIC8 (4.0) [SA602A]  
SST25WF020@WSON8 [SA683]  
SST25WF040@SOIC8 (5.4) [SA605B]  
SST25WF080@SOIC8 (4.0) [SA602A]  
SST25WF080@WSON8 [SA683]  
SST25WF512@SOIC8 (5.4) [SA605B]  
SST26VF016@SOIC8 [SA605B]  
SST26VF016B@SOIC8 [SA602A]  
SST26VF016B@WDFN8 [SA683]  
SST26VF032@SOIC8[150 mil] [SA602A]  
SST26VF032@SOIC8[200 mil] [SA605B]  
SST26VF032@WSON8 [SA683]  
SST26VF032B@SOIJ8 [SA602A]  
SST26VF032BA@SOIJ8 [SA602A]  
SST26WF016B@SOIC8 [SA602A]  
SST26WF016BA@SOIC8 [SA602A]  
SST27SF010  
SST27SF010@TSOP32 [SA410T-B4001]  
SST27SF020@PLCC32 [SA015A1T]  
SST27SF256  
SST27SF256@VSOP32 [SA620-B4807]  
SST27SF512@PLCC32 [SA015A1T]  
SST27VF010  
SST27VF010@TSOP32 [SA410T-B4001]  
SST27VF020@PLCC32 [SA015A1T]  
SST27VF040  
SST27VF040@TSOP32 [SA410T-B4001]  
SST27VF256@PLCC32 [SA015A1T]  
SST27VF512  
SST27VF512@VSOP32 [SA620-B4807]  
SST28EE011@PLCC32 [SA015A1T]  
SST28LE011  
SST28LE011@TSOP32 [SA410T-B4001]  
SST28LF040@PLCC32 [SA015A1T]  
SST28SF040  
SST28SF040@TSOP32 [SA410T-B4001]  
SST28SF040A@PLCC32 [SA015A1T]  
SST28SF040A@TSOP32 [SA410T-B4001]  
SST28VE011  
SST28VE011@TSOP32 [SA410T-B4001]  
SST28VF040@PLCC32 [SA015A1T]  
SST28VF040A  
SST28VF040A@TSOP32 [SA410T-B4001]  
SST29EE010  
SST29EE010@TSOP32 [SA410T-B4001]  
SST25VF080@SOIC8 (4.0) [SA602A]  
SST25VF080@WSON8 [SA683]  
SST25VF080B@SOIC8 (5.4) [SA605B]  
SST25VF512@SOIC8 (4.0) [SA602A]  
SST25VF512@WSON8 [SA683]  
SST25VF512A@SOIC8 (5.4) [SA605B]  
SST25WF010@SOIC8 (4.0) [SA602A]  
SST25WF010@WSON8 [SA683]  
SST25WF020@SOIC8 (5.4) [SA605B]  
SST25WF040@SOIC8 (4.0) [SA602A]  
SST25WF040@WSON8 [SA683]  
SST25WF080@SOIC8 (5.4) [SA605B]  
SST25WF512@SOIC8 (4.0) [SA602A]  
SST25WF512@WSON8 [SA683]  
SST26VF016@WSON8 [SA683]  
SST26VF016B@SOIJ8 [SA605B]  
SST26VF032B@SOIC8 [SA605B]  
SST26VF032B@WDFN8 [SA683]  
SST26VF032BA@WDFN8 [SA683]  
SST26WF016B@WDFN8 [SA683]  
SST26WF016BA@WDFN8 [SA683]  
SST27SF010@PLCC32 [SA015A1T]  
SST27SF020  
SST27SF020@TSOP32 [SA410T-B4001]  
SST27SF256@PLCC32 [SA015A1T]  
SST27SF512  
SST27SF512@VSOP32 [SA620-B4807]  
SST27VF010@PLCC32 [SA015A1T]  
SST27VF020  
SST27VF020@TSOP32 [SA410T-B4001]  
SST27VF040@PLCC32 [SA015A1T]  
SST27VF256  
SST27VF256@VSOP32 [SA620-B4807]  
SST27VF512@PLCC32 [SA015A1T]  
SST28EE011  
SST28EE011@TSOP32 [SA410T-B4001]  
SST28LE011@PLCC32 [SA015A1T]  
SST28LF040  
SST28LF040@TSOP32 [SA410T-B4001]  
SST28SF040@PLCC32 [SA015A1T]  
SST28SF040A  
SST28VE011@PLCC32 [SA015A1T]  
SST28VF040  
SST28VF040@TSOP32 [SA410T-B4001]  
SST28VF040A@PLCC32 [SA015A1T]  
SST29EE010@PLCC32 [SA015A1T]  
SST29EE010@VSOP32 [SA620-B4807]

SST29EE020	SST29EE020@PLCC32	[SA015A1T]
SST29EE020@TSOP32	SST29EE020@VSOP32	[SA620-B4807]
SST29EE512	SST29EE512@PLCC32	[SA015A1T]
SST29EE512@TSOP32	SST29EE512@VSOP32	[SA620-B4807]
SST29LE010	SST29LE010@PLCC32	[SA015A1T]
SST29LE010@TSOP32	SST29LE010@VSOP32	[SA620-B4807]
SST29LE020	SST29LE020@PLCC32	[SA015A1T]
SST29LE020@TSOP32	SST29LE020@VSOP32	[SA620-B4807]
SST29LE512	SST29LE512@PLCC32	[SA015A1T]
SST29LE512@TSOP32	SST29LE512@VSOP32	[SA620-B4807]
SST29SF010	SST29SF010@PLCC32	[SA015A1T]
SST29SF010@VSOP32	SST29SF020	
SST29SF020@PLCC32	SST29SF020@VSOP32	[SA620-B4807]
SST29SF040	SST29SF040@PLCC32	[SA015A1T]
SST29SF040@VSOP32	SST29SF512	
SST29SF512@PLCC32	SST29SF512@VSOP32	[SA620-B4807]
SST29VE010	SST29VE010@PLCC32	[SA015A1T]
SST29VE010@TSOP32	SST29VE010@VSOP32	[SA620-B4807]
SST29VE020	SST29VE020@PLCC32	[SA015A1T]
SST29VE020@TSOP32	SST29VE020@VSOP32	[SA620-B4807]
SST29VE512	SST29VE512@PLCC32	[SA015A1T]
SST29VE512@TSOP32	SST29VE512@VSOP32	[SA620-B4807]
SST29VF010	SST29VF010@PLCC32	[SA015A1T]
SST29VF010@VSOP32	SST29VF020	
SST29VF020@PLCC32	SST29VF020@VSOP32	[SA620-B4807]
SST29VF040	SST29VF040@PLCC32	[SA015A1T]
SST29VF040@VSOP32	SST29VF512	
SST29VF512@PLCC32	SST29VF512@VSOP32	[SA620-B4807]
SST31LF021@VSOP32	SST31LF021E@VSOP32	[SA620-B4807]
SST31LF041@TSOP40	SST31LF041A@VSOP32	[SA620-B4807]
SST31LF043@TSOP40	SST31LF043A@VSOP32	[SA620-B4807]
SST32HF162@TSOP48	SST32HF164@TSOP48	[SB247-B4806]
SST34HF1601B@TSOP48		
SST36VF1601@TSOP48		
SST36VF1601C@TSOP48		
SST36VF1601E@TSOP48		
SST36VF1601G@TSOP48		
SST36VF1602@TSOP48		
SST36VF1602C@TSOP48		
SST36VF1602E@TSOP48		
SST36VF1602G@TSOP48		
SST36VF3203@TSOP48	SST36VF3204@TSOP48	[SB247-B4806]
SST37VF010	SST37VF010@PLCC32	[SA015A1T]
SST37VF010@VSOP32	SST37VF020	
SST37VF020@PLCC32	SST37VF020@VSOP32	[SA620-B4807]
SST37VF040	SST37VF040@PLCC32	[SA015A1T]
SST37VF040@VSOP32	SST37VF512	
SST37VF512@PLCC32	SST37VF512@VSOP32	[SA620-B4807]
SST38UF166@TSOP48	SST38VF166@TSOP48	[SB247-B4806]
SST38VF6401@TSOP48		
SST38VF6401B@TSOP48		
SST38VF6402@TSOP48		
SST38VF6402B@TSOP48		

SST38VF6403@TSOP48 [SB247-B4806]  
SST38VF6403B@TSOP48 [SB247-B4806]  
SST38VF6404@TSOP48 [SB247-B4806]  
SST38VF6404B@TSOP48 [SB247-B4806]  
SST39LF010@PLCC32 [SA015A1T] SST39LF010@VSOP32 [SA620-B4807]  
SST39LF016@TSOP40 [SA409T-B4002] SST39LF020@PLCC32 [SA015A1T]  
SST39LF020@VSOP32 [SA620-B4807] SST39LF040@PLCC32 [SA015A1T]  
SST39LF040@VSOP32 [SA620-B4807] SST39LF080@TSOP40 [SA409T-B4002]  
SST39LF080Q@TSOP40 [SA409T-B4002]  
SST39LF100@VSOP40 [SA623-B4002] SST39LF160@TSOP48 [SB247-B4806]  
SST39LF200@TSOP48 [SA247-B4806] SST39LF200A@TSOP48 [SA247-B4806]  
SST39LF400@TSOP48 [SA247-B4806] SST39LF400A@TSOP48 [SA247-B4806]  
SST39LF512@PLCC32 [SA015A1T] SST39LF512@VSOP32 [SA620-B4807]  
SST39LF800@TSOP48 [SB247-B4806] SST39LF800A@TSOP48 [SB247-B4806]  
SST39LF801C@@TSOP48 [SB247-B4806]  
SST39LF802C@@TSOP48 [SB247-B4806]  
SST39LH010 SST39LH010@PLCC32 [SA015A1T]  
SST39LH010@TSOP32 [SA410T-B4001] SST39LH040  
SST39LH040@PLCC32 [SA015A1T] SST39LH040@TSOP32 [SA410T-B4001]  
SST39LH512 SST39LH512@PLCC32 [SA015A1T]  
SST39LH512@TSOP32 [SA410T-B4001] SST39SF010  
SST39SF010@PLCC32 [SA015A1T] SST39SF010@VSOP32 [SA620-B4807]  
SST39SF010A SST39SF010A@PLCC32 [SA015A1T]  
SST39SF010A@VSOP32 [SA620-B4807] SST39SF020  
SST39SF020@PLCC32 [SA015A1T] SST39SF020@VSOP32 [SA620-B4807]  
SST39SF020A SST39SF020A@PLCC32 [SA015A1T]  
SST39SF020A@VSOP32 [SA620-B4807] SST39SF020P  
SST39SF020P@PLCC32 [SA015A1T] SST39SF020P@VSOP32 [SA620-B4807]  
SST39SF040 SST39SF040@PLCC32 [SA015A1T]  
SST39SF040@VSOP32 [SA620-B4807] SST39SF040P  
SST39SF040P@PLCC32 [SA015A1T] SST39SF040P@VSOP32 [SA620-B4807]  
SST39SF512 SST39SF512@PLCC32 [SA015A1T]  
SST39SF512@VSOP32 [SA620-B4807] SST39SF512A  
SST39SF512A@PLCC32 [SA015A1T] SST39SF512A@VSOP32 [SA620-B4807]  
SST39VF010 SST39VF010@PLCC32 [SA015A1T]  
SST39VF010@VSOP32 [SA620-B4807] SST39VF016@TSOP40 [SA409T-B4002]  
SST39VF016Q@TSOP40 [SA409T-B4002]  
SST39VF020 SST39VF020@PLCC32 [SA015A1T]  
SST39VF020@VSOP32 [SA620-B4807] SST39VF020P  
SST39VF020P@PLCC32 [SA015A1T] SST39VF020P@VSOP32 [SA620-B4807]  
SST39VF040 SST39VF040@PLCC32 [SA015A1T]  
SST39VF040@VSOP32 [SA620-B4807] SST39VF040P  
SST39VF040P@PLCC32 [SA015A1T] SST39VF040P@VSOP32 [SA620-B4807]  
SST39VF080@TSOP40 [SA409T-B4002]  
SST39VF080Q@TSOP40 [SA409T-B4002]  
SST39VF088@TSOP48 [SB247-B4806] SST39VF100@VSOP40 [SA623-B4002]  
SST39VF160@TSOP48 [SB247-B4806]  
SST39VF160@TSOP48 (SLOW) [SA247-B4806]  
SST39VF1601@TSOP48 [SB247-B4806]  
SST39VF1601C@TSOP48 [SB247-B4806]  
SST39VF1602@TSOP48 [SB247-B4806]  
SST39VF1602C@TSOP48 [SB247-B4806]  
SST39VF160Q@TSOP48 [SB247-B4806] SST39VF1681@TSOP48 [SB247-B4806]

SST39VF1682@TSOP48 [SB247-B4806]	SST39VF200A@TSOP48 [SA247-B4806]
SST39VF320@TSOP48 [SB247-B4806]	SST39VF3201@TSOP48 [SB247-B4806]
SST39VF3201B@TSOP48 [SB247-B4806]	
SST39VF3201C@TSOP48 [SB247-B4806]	
SST39VF3202@TSOP48 [SB247-B4806]	
SST39VF3202B@TSOP48 [SB247-B4806]	
SST39VF3202C@TSOP48 [SB247-B4806]	
SST39VF400@TSOP48 [SA247-B4806]	SST39VF400A@TSOP48 [SA247-B4806]
SST39VF400Q@TSOP48 [SA247-B4806]	SST39VF512
SST39VF512@PLCC32 [SA015A1T]	SST39VF512@VSOP32 [SA620-B4807]
SST39VF6401@TSOP48 [SB247-B4806]	
SST39VF6401B@TSOP48 [SB247-B4806]	
SST39VF6402@TSOP48 [SB247-B4806]	
SST39VF6402B@TSOP48 [SB247-B4806]	
SST39VF800@TSOP48 [SB247-B4806]	SST39VF800A@TSOP48 [SB247-B4806]
SST39VF800Q@TSOP48 [SB247-B4806]	
SST39VF801C@@@TSOP48 [SB247-B4806]	
SST39VF802C@@@TSOP48 [SB247-B4806]	
SST49LF002@PLCC32 [SA015A1T]	SST49LF002@VSOP32 [SA620-B4807]
SST49LF002A@PLCC32 [SA015A1T]	SST49LF002A@VSOP32 [SA620-B4807]
SST49LF002B@PLCC32 [SA015A1T]	SST49LF003A@PLCC32 [SA015A1T]
SST49LF003A@VSOP32 [SA620-B4807]	SST49LF003B@PLCC32 [SA015A1T]
SST49LF004@PLCC32 [SA015A1T]	SST49LF004@VSOP32 [SA620-B4807]
SST49LF004A@PLCC32 [SA015A1T]	SST49LF004A@VSOP32 [SA620-B4807]
SST49LF004B@PLCC32 [SA015A1T]	SST49LF004B@VSOP32 [SA620-B4807]
SST49LF004B@VSOP40 [SA409T-B4002]	
SST49LF008@PLCC32 [SA015A1T]	SST49LF008@VSOP32 [SA620-B4807]
SST49LF008A@PLCC32 [SA015A1T]	
SST49LF008A@TSOP40 [SA409T-B4002]	
SST49LF008A@VSOP32 [SA620-B4807]	SST49LF020@PLCC32 [SA015A1T]
SST49LF020@VSOP32 [SA620-B4807]	SST49LF020A@PLCC32 [SA015A1T]
SST49LF020A@VSOP32 [SA620-B4807]	SST49LF030A@PLCC32 [SA015A1T]
SST49LF030A@VSOP32 [SA620-B4807]	SST49LF040@PLCC32 [SA015A1T]
SST49LF040@VSOP32 [SA620-B4807]	SST49LF040A@PLCC32 [SA015A1T]
SST49LF040A@VSOP32 [SA620-B4807]	SST49LF040B@PLCC32 [SA015A1T]
SST49LF040B@TSOP40 [SA409T-B4002]	
SST49LF040B@VSOP32 [SA620-B4807]	SST49LF080A@PLCC32 [SA015A1T]
SST49LF080A@VSOP32 [SA620-B4807]	

## MICROCONTROLLER

SST65P542R@SOIC28 [SA404]	SST89C54
SST89C54@PLCC44 [SA244]	SST89C54@TQFP44 [SA245A-B4805]
SST89C58	SST89C58@PLCC44 [SA244]
SST89C58@TQFP44 [SA245A-B4805]	SST89E516RD
SST89E516RD@PLCC44 [SA244]	
SST89E516RD@TQFP44 [SA245A-B4805]	SST89E516RD2@PLCC44 [SA244]
SST89E516RD2	
SST89E516RD2@TQFP44 [SA245A-B4805]	SST89E52RC@PLCC44 [SA244]
SST89E52RC	SST89E52RD
SST89E52RC@TQFP44 [SA245A-B4805]	SST89E52RD@TQFP44 [SA245A-B4805]
SST89E52RD@PLCC44 [SA244]	

SST89E52RD2	SST89E52RD2@PLCC44 [SA244]
SST89E52RD2@TQFP44 [SA245A-B4805]	
SST89E54RC	SST89E54RC@PLCC44 [SA244]
SST89E54RC@TQFP44 [SA245A-B4805]	SST89E54RD
SST89E54RD@PLCC44 [SA244]	SST89E54RD@TQFP44 [SA245A-B4805]
SST89E54RD2	SST89E54RD2@PLCC44 [SA244]
SST89E54RD2@TQFP44 [SA245A-B4805]	
SST89E54RD2A	SST89E54RD2A@PLCC44 [SA244]
SST89E54RD2A@TQFP44 [SA245A-B4805]	
SST89E54RDA	SST89E54RDA@PLCC44 [SA244]
SST89E54RDA@TQFP44 [SA245A-B4805]	
SST89E554RC	SST89E554RC@PLCC44 [SA244]
SST89E554RC@TQFP44 [SA245A-B4805]	
SST89E564	SST89E564@PLCC44 [SA244]
SST89E564@TQFP44 [SA245A-B4805]	SST89E564RD
SST89E564RD@PLCC44 [SA244]	
SST89E564RD@TQFP44 [SA245A-B4805]	
SST89E58RD	SST89E58RD@PLCC44 [SA244]
SST89E58RD@TQFP44 [SA245A-B4805]	SST89E58RD2
SST89E58RD2@PLCC44 [SA244]	
SST89E58RD2@TQFP44 [SA245A-B4805]	
SST89E58RD2A	SST89E58RD2A@PLCC44 [SA244]
SST89E58RD2A@TQFP44 [SA245A-B4805]	
SST89E58RDA	SST89E58RDA@PLCC44 [SA244]
SST89E58RDA@TQFP44 [SA245A-B4805]	
SST89V516RD	SST89V516RD@PLCC44 [SA244]
SST89V516RD@TQFP44 [SA245A-B4805]	
SST89V516RD2	SST89V516RD2@PLCC44 [SA244]
SST89V516RD2@TQFP44 [SA245A-B4805]	
SST89V52RD	SST89V52RD@PLCC44 [SA244]
SST89V52RD@TQFP44 [SA245A-B4805]	SST89V52RD2
SST89V52RD2@PLCC44 [SA244]	
SST89V52RD2@TQFP44 [SA245A-B4805]	
SST89V54RD2	SST89V54RD2@PLCC44 [SA244]
SST89V54RD2@TQFP44 [SA245A-B4805]	
SST89V554RC	SST89V554RC@PLCC44 [SA244]
SST89V554RC@TQFP44 [SA245A-B4805]	
SST89V564	SST89V564@PLCC44 [SA244]
SST89V564@TQFP44 [SA245A-B4805]	SST89V564RD
SST89V564RD@PLCC44 [SA244]	
SST89V564RD@TQFP44 [SA245A-B4805]	
SST89V58RD2	SST89V58RD2@PLCC44 [SA244]
SST89V58RD2@TQFP44 [SA245A-B4805]	

## SST-CUSTOMER

### E (E) PROM/FRAM/NVRAM

SST39SF010A@PLCC32 [SA015A1T]	SST39SF020A@PLCC32 [SA015A1T]
-------------------------------	-------------------------------

## SSU

## MICROCONTROLLER

SSU2C508  
SSU6C676  
SSU6C676@TSSOP14 [SA026]  
SSU6C74

SSU2C508N  
SSU6C676@SOIC14 [SA602]  
SSU6C73

## ST

### E (E) PROM/FRAM/NVRAM

ET2716  
ETC2732  
M13C02@SOIC8 [SA602A]  
M24128@MLP8 [SA724]  
M24128@TSOP8 [SA643]  
M24164@SOIC8 [SA602A]  
M24256@MLP8 [SA724]  
M24256@SOIC8[5.5] [SA605B]  
M24256@WLCSP8  
M24256BF@SOIC8[3.9] [SA602A]  
M24256BF@TSOP8 [SA643]  
M24256BR@MLP8 [SA724]  
M24256BR@SOIC8[5.5] [SA605B]  
M24256BW  
M24256BW@SOIC8[3.9] [SA602A]  
M24256BW@TSOP8 [SA643]  
M24512@SOIC8(150 mil) [SA602A]  
M24512@TSOP8 [SA643]  
M24C01@MLP8 [SA724]  
M24C01R  
M24C01R@SOIC8 [SA602A]  
M24C01W  
M24C01W@SOIC8 [SA602A]  
M24C02  
M24C02@SOIC8 [SA602A]  
M24C02R@MLP8 [SA724]  
M24C02R@TSOP8 [SA643]  
M24C02W@MLP8 [SA724]  
M24C02W@TSOP8 [SA643]  
M24C04@MLP8 [SA724]  
M24C04R  
M24C04R@SOIC8 [SA602A]  
M24C04W  
M24C04W@SOIC8 [SA602A]  
M24C08  
M24C08@MSOP8 [SA695A]  
M24C08@TSOP8 [SA643]  
M24C08R@MLP8 [SA724]  
M24C08R@SOIC8 [SA602A]  
M24C08W  
M24C08W@MSOP8 [SA695A]

ETC2716  
M13C02  
M24128  
M24128@SOIC8 [SA602A]  
M24164  
M24256  
M24256@SOIC8[3.9] [SA602A]  
M24256@TSOP8 [SA643]  
M24256BF@MLP8 [SA724]  
M24256BF@SOIC8[5.5] [SA605B]  
M24256BR  
M24256BR@SOIC8[3.9] [SA602A]  
M24256BR@TSOP8 [SA643]  
M24256BW@MLP8 [SA724]  
M24256BW@SOIC8[5.5] [SA605B]  
M24512  
M24512@SOIC8(200 mil) [SA605B]  
M24C01  
M24C01@SOIC8 [SA602A]  
M24C01R@MLP8 [SA724]  
M24C01R@TSOP8 [SA643]  
M24C01W@MLP8 [SA724]  
M24C01W@TSOP8 [SA643]  
M24C02@MLP8 [SA724]  
M24C02R  
M24C02R@SOIC8 [SA602A]  
M24C02W  
M24C02W@SOIC8 [SA602A]  
M24C04  
M24C04@SOIC8 [SA602A]  
M24C04R@MLP8 [SA724]  
M24C04R@TSOP8 [SA643]  
M24C04W@MLP8 [SA724]  
M24C04W@TSOP8 [SA643]  
M24C08@MLP8 [SA724]  
M24C08@SOIC8 [SA602A]  
M24C08R  
M24C08R@MSOP8 [SA695A]  
M24C08R@TSOP8 [SA643]  
M24C08W@MLP8 [SA724]  
M24C08W@SOIC8 [SA602A]

M24C08W@TSOP8 [SA643]  
M24C128 (MN)@SOIC8 [SA605B]  
M24C128@MLP8 [SA724]  
M24C128B (MN)@SOIC8 [SA605B]  
M24C128B@MLP8 [SA724]  
M24C16@MLP8 [SA724]  
M24C16R  
M24C16R@SOIC8 [SA602A]  
M24C16W  
M24C16W@SOIC8 [SA602A]  
M24C256 (BN)  
M24C256 (MW)@SOIC8 [SA602A]  
M24C256A (BN)  
M24C256A (MW)@SOIC8 [SA602A]  
M24C256B (BN)  
M24C256B (MW)@SOIC8 [SA602A]  
M24C256W (BN)  
M24C256W (MW)@SOIC8 [SA602A]  
M24C32 (BN)  
M24C32 (DW)@TSSOP8 [SA643]  
M24C32 (MW)@SOIC8 [SA602A]  
M24C32W (BN)  
M24C32W (DW)@TSSOP8 [SA643]  
M24C32W (MW)@SOIC8 [SA605B]  
M24C64 (BN)  
M24C64 (DW)@TSSOP8 [SA643]  
M24C64 (MW)@SOIC8 [SA602A]  
M24C64W (BN)  
M24C64W (DW)@TSSOP8 [SA643]  
M24C64W (MW)@SOIC8 [SA602A]  
M24CL04B  
M24CL04B@SOIC8 [SA602A]  
M24E16  
M24E32 (DW)@TSSOP8 [SA643]  
M24E32 (MW)@SOIC8 [SA602A]  
M24M01@SOIC8 [SA602A]  
M24M01-HR@SOIC8 (150 mil) [SA602A]  
M24M01-HR@SOIC8 (200 mil) [SA605B]  
M24M01-HR@WLCSP8  
M24M01-R@SOIC8 (200 mil) [SA605B]  
M24M01-W@SOIC8 (150 mil) [SA602A]  
M24M01-W@WLCSP8  
M24W01@SOIC8 [SA602A]  
M24W02@SOIC8 [SA602A]  
M24W04@SOIC8 [SA602A]  
M24W08@SOIC8 [SA602A]  
M24W16@SOIC8 [SA602A]  
M25C02  
M25C08  
M25E16  
M25P05@VQFPN8 [SA683]  
M25P05-A@TSSOP8 [SA643]  
M25P10@SOIC8 [SA602A]

M24C128 (BN)  
M24C128 (MW)@SOIC8 [SA602A]  
M24C128B (BN)  
M24C128B (MW)@SOIC8 [SA602A]  
M24C16  
M24C16@SOIC8 [SA602A]  
M24C16R@MLP8 [SA724]  
M24C16R@TSOP8 [SA643]  
M24C16W@MLP8 [SA724]  
M24C16W@TSOP8 [SA643]  
M24C256 (MN)@SOIC8 [SA605B]  
M24C256@MLP8 [SA724]  
M24C256A (MN)@SOIC8 [SA605B]  
M24C256A@MLP8 [SA724]  
M24C256B (MN)@SOIC8 [SA605B]  
M24C256B@MLP8 [SA724]  
M24C256W (MN)@SOIC8 [SA605B]  
M24C256W@MLP8 [SA724]  
M24C32 (DL)@TSSOP14 [SA026]  
M24C32 (MN)@SOIC8 [SA605B]  
M24C32@MLP8 [SA724]  
M24C32W (DL)@TSSOP14 [SA026]  
M24C32W (MN)@SOIC8 [SA602A]  
M24C32W@MLP8 [SA724]  
M24C64 (DL)@TSSOP14 [SA026]  
M24C64 (MN)@SOIC8 [SA605B]  
M24C64@MLP8 [SA724]  
M24C64W (DL)@TSSOP14 [SA026]  
M24C64W (MN)@SOIC8 [SA605B]  
M24C64W@MLP8 [SA724]  
M24CL04B@MLP8 [SA724]  
M24CL04B@TSOP8 [SA643]  
M24E32 (BN)  
M24E32 (MN)@SOIC8 [SA605B]  
M24M01@LGA8 [SA684]  
  
M24M01-R@SOIC8 (150 mil) [SA602A]  
M24M01-R@WLCSP8  
M24M01-W@SOIC8 (200 mil) [SA605B]  
M24W01  
M24W02  
M24W04  
M24W08  
M24W16  
M25C01  
M25C04  
M25C16  
M25P05@SOIC8 [SA602A]  
M25P05-A@SOIC8 [SA602A]  
M25P05-A@VDFPN8 [SA683]  
M25P10@UFDFPN8 [SA724]

M25P10@VQFPN8 [SA683]  
M25P10-A@VFQFPN8 [SA683]  
M25P128@SOIC16 (ISP)  
M25P128@VDFPN8 (ISP)  
M25P16@SOIC16 (ISP)  
M25P16@SOIC8 (150mil) (ISP)  
M25P16@SOIC8 (200mil) (ISP)  
M25P16@VDFPN8 (ISP)  
M25P16@VFQFPN8 (ISP)  
M25P20@VFQFPN8 [SA683]  
M25P32 (Fast Mode)@SOIC8 (150mil) [SA605B]  
M25P32 (Fast Mode)@SOIC8 (200mil) [SA683]  
M25P32 (Fast Mode)@VQFPN8 [SA684]  
M25P32@SOIC16 (ISP)  
M25P32@SOIC8 (ISP)  
M25P32@VDFPN8 (ISP)  
M25P32@VFQFPN8 (ISP)  
M25P40@VFQFPN8 [SA683]  
M25P64 (Fast Mode)@VDFPN8 [SA684]  
M25P64@SOIC16 (ISP)  
M25P64@VDFPN8 (ISP)  
M25P80@SOIC8 [SA605B]  
M25PE10@SOIC8 [SA602A]  
M25PE10@VQFPN8 [SA683]  
M25PE16@SOIC8 [SA605B]  
M25PE20@SOIC8 [SA602A]  
M25PE20@VQFPN8 [SA683]  
M25PE40@SOIC8 [SA605B]  
M25PE40@VQFPN8 [SA683]  
M25PE80@SOIC8 [SA605B]  
M25PE80@VQFPN8 [SA683]  
M25PX32@SOIC16 [SA404]  
M25PX32@VFQFPN8 [SA683]  
M25PX64@VDFPN8 [SA684]  
M25W02  
M25W08  
M25W166  
M2716  
M27256  
M2732A  
M2764  
M27C1000  
M27C1000@TSOP32 [SA410T-B4001]  
M27C1001@PLCC32 [SA015A1T]  
M27C1024  
M27C128B  
M27C160  
M27C160@PSOP44 [SA638]  
M27C160K@PLCC44 [SA244]  
M27C2001  
M27C2001@TSOP32 [SA410T-B4001]  
M27C202@PLCC44 [SA244]  
M27C256B  
M25P10-A@SOIC8 [SA602A]  
M25P128@SOIC16 [SA783]  
M25P128@VDFPN8 [SA684]  
M25P16@SOIC16 [SA783]  
M25P16@SOIC8 (150mil) [SA602A]  
M25P16@SOIC8 (200mil) [SA605B]  
M25P16@VDFPN8 [SA684]  
M25P16@VFQFPN8 [SA683]  
M25P20@SOIC8 [SA602A]  
M25P32 (Fast Mode)@SOIC16 [SA404]  
M25P32@SOIC16 [SA783]  
M25P32@SOIC8 [SA605B]  
M25P32@VDFPN8 [SA684]  
M25P32@VFQFPN8 [SA683]  
M25P40@SOIC8 [SA602A]  
M25P64 (Fast Mode)@SOIC16 [SA404]  
M25P64@SOIC16 [SA783]  
M25P64@VDFPN8 [SA684]  
M25P80@SOIC16 [SA404]  
M25P80@VFQFPN8 [SA683]  
M25PE10@SOIC8 (ISP)  
M25PE10@VQFPN8 (ISP)  
M25PE16@VQFPN8 [SA683]  
M25PE20@SOIC8 (ISP)  
M25PE20@VQFPN8 (ISP)  
M25PE40@SOIC8 (ISP)  
M25PE40@VQFPN8 (ISP)  
M25PE80@SOIC8 (ISP)  
M25PE80@VQFPN8 (ISP)  
M25PX32@SOIC8 [SA605B]  
M25PX64@SOIC16 [SA404]  
M25W01  
M25W04  
M25W16  
M27128A  
M2716F1  
M27256A  
M27512  
M2764A  
M27C1000@PLCC32 [SA015A1T]  
M27C1001  
M27C1001@TSOP32 [SA410T-B4001]  
M27C1024@PLCC44 [SA244]  
M27C16  
M27C160@PLCC44 [SA244]  
M27C160K  
M27C160K@PSOP44 [SA638]  
M27C2001@PLCC32 [SA015A1T]  
M27C202  
M27C202@VSOP40 [SA623-B4002]  
M27C256B@PLCC32 [SA015A1T]

M27C32  
M27C322@SDIP42 [SA028]  
M27C4001  
M27C4001@TSOP32 [SA410T-B4001]  
M27C4002@PLCC44 [SA244]  
M27C405@PLCC32 [SA015A1T]  
M27C512  
M27C513  
M27C516@PLCC44 [SA244]  
M27C64A@PLCC32 [SA015A1T]  
M27C800@PLCC44 [SA244]  
M27C801  
M27C801@TSOP32 [SA410T-B4001]  
M27HC641@PLCC28 [SA008A]  
M27HC642@PLCC28 [SA008A]  
M27V101@PLCC32 [SA015A1T]  
M27V102  
M27V160  
M27V160@PSOP44 [SA638]  
M27V160K@PLCC44 [SA244]  
M27V201  
M27V201@TSOP32 [SA410T-B4001]  
M27V322  
M27V401  
M27V401@TSOP32 [SA410T-B4001]  
M27V402@PLCC44 [SA244]  
M27V405  
M27V405@TSOP32 [SA410T-B4001]  
M27V512@PLCC32 [SA015A1T]  
M27V800  
M27V801  
M27V801@TSOP32 [SA410T-B4001]  
M27W016@PSOP44 [SA638]  
M27W016@TSOP48 [SB247-B4806]  
M27W032@TSOP48 [SB247-B4806]  
M27W064@TSOP48 [SB247-B4806]  
M27W101@PLCC32 [SA015A1T]  
M27W102  
M27W160  
M27W160@PSOP44 [SA638]  
M27W201@PLCC32 [SA015A1T]  
M27W202  
M27W202@VSOP40 [SA623-B4002]  
M27W400@PLCC44 [SA244]  
M27W401@PLCC32 [SA015A1T]  
M27W402  
M27W402@TSOP40 [SA409T-B4002]  
M27W512@PLCC32 [SA015A1T]  
M27W800  
M27W801  
M27W801@TSOP32 [SA410T-B4001]  
M28010@PLCC32 [SA015A1T]  
M28010R

M27C322  
M27C400  
M27C4001@PLCC32 [SA015A1T]  
M27C4002  
M27C405  
M27C405@TSOP32 [SA410T-B4001]  
M27C512@PLCC32 [SA015A1T]  
M27C516  
M27C64A  
M27C800  
M27C800@PSOP44 [SA638]  
M27C801@PLCC32 [SA015A1T]  
M27HC641  
M27HC642  
M27V101  
M27V101@TSOP32 [SA410T-B4001]  
M27V102@PLCC44 [SA244]  
M27V160@PLCC44 [SA244]  
M27V160K  
M27V160K@PSOP44 [SA638]  
M27V201@PLCC32 [SA015A1T]  
M27V256  
M27V322@SDIP42 [SA028]  
M27V401@PLCC32 [SA015A1T]  
M27V402  
M27V402@TSOP40 [SA409T-B4002]  
M27V405@PLCC32 [SA015A1T]  
M27V512  
M27V512@TSOP28 [SA430T-B4003]  
M27V800@PLCC44 [SA244]  
M27V801@PLCC32 [SA015A1T]  
M27W016  
M27W016@SDIP42 [SA028]  
M27W032@PSOP44 [SA638]  
M27W064@PSOP44 [SA638]  
M27W101  
M27W101@TSOP32 [SA410T-B4001]  
M27W102@PLCC44 [SA244]  
M27W160@PLCC44 [SA244]  
M27W201  
M27W201@TSOP32 [SA410T-B4001]  
M27W202@PLCC44 [SA244]  
M27W400  
M27W401  
M27W401@TSOP32 [SA410T-B4001]  
M27W402@PLCC44 [SA244]  
M27W512  
M27W512@TSOP28 [SA430T-B4003]  
M27W800@PLCC44 [SA244]  
M27W801@PLCC32 [SA015A1T]  
M28010  
M28010@TSOP32 [SA410T-B4001]  
M28010R@PLCC32 [SA015A1T]

M28010R@TSOP32 [SA410T-B4001] M28010W  
M28010W@PLCC32 [SA015A1T] M28010W@TSOP32 [SA410T-B4001]  
M28256 M28256@PLCC32 [SA015A1T]  
M28256@TSOP28 [SA430T-B4003] M28C010  
M28C010@PLCC32 [SA015A1T] M28C010@TSOP32 [SA410T-B4001]  
M28C010R M28C010R@PLCC32 [SA015A1T]  
M28C010R@TSOP32 [SA410T-B4001] M28C010W  
M28C010W@PLCC32 [SA015A1T] M28C010W@TSOP32 [SA410T-B4001]  
M28C16@PLCC32 [SA015A1T] M28C17@SOIC28 [SA404]  
M28C64 M28C64@PLCC32 [SA015A1T]  
M28C64@TSOP28 [SA430T-B4003] M28C64C  
M28C64C@PLCC32 [SA015A1T] M28C64C@SOIC28 [SA404]  
M28C64C@TSOP28 [SA430T-B4003] M28C64X  
M28C64X@PLCC32 [SA015A1T] M28C64X@TSOP28 [SA430T-B4003]  
M28F101  
M28F101 (REVERSE)@TSOP32 [SA410T-B4001]  
M28F101@PLCC32 [SA015A1T] M28F101@TSOP32 [SA410T-B4001]  
M28F102 M28F102@PLCC44 [SA244]  
M28F102@TSOP40 [SA623-B4002] M28F151  
M28F151 (REVERSE)@TSOP32 [SA410T-B4001]  
M28F151@PLCC32 [SA015A1T] M28F151@TSOP32 [SA410T-B4001]  
M28F201  
M28F201 (REVERSE)@TSOP32 [SA410T-B4001]  
M28F201@PLCC32 [SA015A1T] M28F201@TSOP32 [SA410T-B4001]  
M28F210@PSOP44 [SA638] M28F210@TSOP48 [SB247-B4806]  
M28F211@TSOP40 [SA409T-B4002] M28F220@PSOP44 [SA638]  
M28F220@TSOP48 [SB247-B4806] M28F221@TSOP40 [SA409T-B4002]  
M28F256  
M28F256 (REVERSE)@TSOP32 [SA410T-B4001]  
M28F256@PLCC32 [SA015A1T] M28F256@TSOP32 [SA410T-B4001]  
M28F411@TSOP40 [SA409T-B4002] M28F421@TSOP40 [SA409T-B4002]  
M28F512  
M28F512 (REVERSE)@TSOP32 [SA410T-B4001]  
M28F512@PLCC32 [SA015A1T] M28F512@TSOP32 [SA410T-B4001]  
M28LV64 M28LV64@PLCC32 [SA015A1T]  
M28LV64@TSOP28 [SA430T-B4003] M28V411@TSOP40 [SA409T-B4002]  
M28V421@TSOP40 [SA409T-B4002] M28W160B@TSOP48 [SB247-B4806]  
M28W160BB@TSOP48 [SB247-B4806] M28W160BT@TSOP48 [SB247-B4806]  
M28W160CB@TSOP48 [SB247-B4806] M28W160CT@TSOP48 [SB247-B4806]  
M28W160ECB@TSOP48 [SB247-B4806] M28W160ECT@TSOP48 [SB247-B4806]  
M28W160T@TSOP48 [SB247-B4806] M28W320CB@TSOP48 [SB247-B4806]  
M28W320CT@TSOP48 [SB247-B4806] M28W320ECB@TSOP48 [SB247-B4806]  
M28W320ECT@TSOP48 [SB247-B4806] M28W320FCB@TSOP48 [SB247-B4806]  
M28W320FCT@TSOP48 [SB247-B4806] M28W640CB@TSOP48 [SB247-B4806]  
M28W640CT@TSOP48 [SB247-B4806] M28W640ECB@TSOP48 [SB247-B4806]  
M28W640ECT@TSOP48 [SB247-B4806] M28W640FCB@TSOP48 [SB247-B4806]  
M28W640FCT@TSOP48 [SB247-B4806] M28W640HCB@TSOP48 [SB247-B4806]  
M28W640HCT@TSOP48 [SB247-B4806] M28W800B@TSOP48 [SB247-B4806]  
M28W800BB@TSOP48 [SB247-B4806] M28W800BT@TSOP48 [SB247-B4806]  
M28W800CB@TSOP48 [SB247-B4806] M28W800CT@TSOP48 [SB247-B4806]  
M28W800T@TSOP48 [SB247-B4806] M29DW323DB@TSOP48 [SB247-B4806]  
M29DW323DT@TSOP48 [SB247-B4806] M29DW324DB@TSOP48 [SB247-B4806]  
M29DW324DT@TSOP48 [SB247-B4806] M29DW640D@TSOP48 [SB247-B4806]

M29DW640F@TSOP48 [SB247-B4806]  
M29F002B  
M29F002B@TSOP32 [SA410T-B4001]  
M29F002BB@PLCC32 [SA015A1T]  
M29F002BNT  
M29F002BNT@TSOP32 [SA410T-B4001]  
M29F002BT@PLCC32 [SA015A1T]  
M29F002T  
M29F002T@TSOP32 [SA410T-B4001]  
M29F010B@PLCC32 [SA015A1T]  
M29F016B@PSOP44 [SA638]  
M29F016D@PSOP44 [SA638]  
M29F032D@TSOP40 [SA409T-B4002]  
M29F040@PLCC32 [SA015A1T]  
M29F040B  
M29F040B@TSOP32 [SA410T-B4001]  
M29F080A@TSOP40 [SA409T-B4002]  
M29F080D@TSOP40 [SA409T-B4002]  
M29F100B@TSOP48 [SB247-B4806]  
M29F100T@TSOP48 [SB247-B4806]  
M29F102B@TSOP40 [SA623-B4002]  
M29F102BB@TSOP40 [SA623-B4002]  
M29F160BT@TSOP48 [SB247-B4806]  
M29F160FT@TSOP48 [SA247-B4806]  
M29F200B@TSOP48 [SB247-B4806]  
M29F200BB@TSOP48 [SB247-B4806]  
M29F200BT@TSOP48 [SB247-B4806]  
M29F200FB@TSOP48 [SA247-B4806]  
M29F200FT@TSOP48 [SA247-B4806]  
M29F200T@TSOP48 [SB247-B4806]  
M29F400B@PSOP44 [SA638]  
M29F400BB@PSOP44 [SA638]  
M29F400BT@PSOP44 [SA638]  
M29F400FB@PSOP44 [SA638]  
M29F400FT@PSOP44 [SA638]  
M29F400T@PSOP44 [SA638]  
M29F512B@PLCC32 [SA015A1T]  
M29F640MT@TSOP48 [SA247-B4806]  
M29F800AB@TSOP48 [SB247-B4806]  
M29F800AT@TSOP48 [SB247-B4806]  
M29F800DB@TSOP48 [SB247-B4806]  
M29F800DT@TSOP48 [SB247-B4806]  
M29F800FB@TSOP48 [SA247-B4806]  
M29F800FT@TSOP48 [SA247-B4806]  
M29KW032E@TSOP48 [SB247-B4806]  
M29V040@PLCC32 [SA015A1T]  
M29W004B@TSOP40 [SA409T-B4002]  
M29W004BT@TSOP40 [SA409T-B4002]  
M29W008AB@TSOP40 [SA409T-B4002]  
M29W008B@TSOP40 [SA409T-B4002]  
M29W010B@PLCC32 [SA015A1T]  
M29W017D@TSOP40 [SA409T-B4002]  
M29W022BB@PLCC32 [SA015A1T]

M29DW641F@TSOP48 [SB247-B4806]  
M29F002B@PLCC32 [SA015A1T]  
M29F002BB  
M29F002BB@TSOP32 [SA410T-B4001]  
M29F002BNT@PLCC32 [SA015A1T]  
M29F002BT  
M29F002BT@TSOP32 [SA410T-B4001]  
M29F002T@PLCC32 [SA015A1T]  
M29F010B  
M29F010B@TSOP32 [SA410T-B4001]  
M29F016B@TSOP40 [SA409T-B4002]  
M29F016D@TSOP40 [SA409T-B4002]  
M29F040  
M29F040@TSOP32 [SA410T-B4001]  
M29F040B@PLCC32 [SA015A1T]  
M29F080A@PSOP44 [SA638]  
M29F080D@PSOP44 [SA638]  
M29F100B@PSOP44 [SA638]  
M29F100T@PSOP44 [SA638]  
M29F102B@PLCC44 [SA244]  
M29F102BB@PLCC44 [SA244]  
M29F160BB@TSOP48 [SB247-B4806]  
M29F160FB@TSOP48 [SA247-B4806]  
M29F200B@PSOP44 [SA638]  
M29F200BB@PSOP44 [SA638]  
M29F200BT@PSOP44 [SA638]  
M29F200FB@PSOP44 [SA638]  
M29F200FT@PSOP44 [SA638]  
M29F200T@PSOP44 [SA638]  
M29F320MT@TSOP48  
M29F400B@TSOP48 [SB247-B4806]  
M29F400BB@TSOP48 [SB247-B4806]  
M29F400BT@TSOP48 [SB247-B4806]  
M29F400FB@TSOP48 [SA247-B4806]  
M29F400FT@TSOP48 [SA247-B4806]  
M29F400T@TSOP48 [SB247-B4806]  
M29F512B@TSOP32 [SA620-B4807]  
M29F800AB@PSOP44 [SA638]  
M29F800AT@PSOP44 [SA638]  
M29F800DB@PSOP44 [SA638]  
M29F800DT@PSOP44 [SA638]  
M29F800FB@PSOP44 [SA638]  
M29F800FT@PSOP44 [SA638]  
M29KW016E@TSOP48 [SB247-B4806]  
M29KW064E@TSOP48 [SB247-B4806]  
M29V040@TSOP32 [SA410T-B4001]  
M29W004BB@TSOP40 [SA409T-B4002]  
M29W004T@TSOP40 [SA409T-B4002]  
M29W008AT@TSOP40 [SA409T-B4002]  
M29W008T@TSOP40 [SA409T-B4002]  
M29W010B@TSOP32 [SA410T-B4001]  
M29W022BB  
M29W022BB@TSOP32 [SA410T-B4001]

M29W022BT  
M29W022BT@TSOP32 [SA410T-B4001]  
M29W040@TSOP32 [SA410T-B4001]  
M29W040B@TSOP32 [SA410T-B4001]  
M29W064FT@TSOP48 [SB247-B4806]  
M29W102BT@TSOP40 [SA623-B4002]  
M29W116BT@TSOP40 [SA409T-B4002]  
M29W160BB@TSOP48 [SB247-B4806]  
M29W160BT@TSOP48 [SB247-B4806]  
M29W160DB@TSOP48 [SB247-B4806]  
M29W160DT@TSOP48 [SB247-B4806]  
M29W160EB(8bit)@TSOP48 [SB247-B4806]  
M29W160EB@PSOP44 [SA638]  
M29W160ET@PSOP44 [SA638]  
M29W160FB@TSOP48 [SB247-B4806]  
M29W200BB@PSOP44 [SA638]  
M29W200BT@PSOP44 [SA638]  
M29W256TD@TSOP48 [SB247-B4806]  
M29W320DB@TSOP48 [SB247-B4806]  
M29W320EB@TSOP48 [SB247-B4806]  
M29W320FB@TSOP48 [SB247-B4806]  
M29W400B@PSOP44 [SA638]  
M29W400BB@PSOP44 [SA638]  
M29W400BT@PSOP44 [SA638]  
M29W400DB@PSOP44 [SA638]  
M29W400DT@PSOP44 [SA638]  
M29W400T@PSOP44 [SA638]  
M29W512B@PLCC32 [SA015A1T]  
M29W640DB@TSOP48 [SB247-B4806]  
M29W640FB(Q\_Word)@TSOP48 [SB247-B4806]  
M29W640FB@TSOP48 [SB247-B4806]  
M29W640FT(Q\_Word)@TSOP48 [SB247-B4806]  
M29W640FT@TSOP48 [SB247-B4806]  
M29W640GB(Mirror)@TSOP48 [SB247-B4806]  
M29W640GB(Q\_Word)@TSOP48 [SB247-B4806]  
M29W640GH(Mirror)@TSOP48 [SB247-B4806]  
M29W640GH(Q\_Word)@TSOP48 [SB247-B4806]  
M29W640GL(Mirror)@TSOP48 [SB247-B4806]  
M29W640GL(Q\_Word)@TSOP48 [SB247-B4806]  
M29W640GSB(Mirror)@TSOP48 [SB247-B4806]  
M29W640GSB(Q\_Word)@TSOP48 [SB247-B4806]  
M29W640GSH(Mirror)@TSOP48 [SB247-B4806]  
M29W640GSH(Q\_Word)@TSOP48 [SB247-B4806]  
M29W640GSL(Mirror)@TSOP48 [SB247-B4806]  
M29W640GSL(Q\_Word)@TSOP48 [SB247-B4806]  
M29W640GST(Mirror)@TSOP48 [SB247-B4806]  
M29W640GST(Q\_Word)@TSOP48 [SB247-B4806]  
M29W640GT(Mirror)@TSOP48 [SB247-B4806]  
M29W640GT(Q\_Word)@TSOP48 [SB247-B4806]  
M29W641DH@TSOP48 [SB247-B4806]  
M29W800AB@PSOP44 [SA638]  
M29W800AT@PSOP44 [SA638]  
M29W800B@PSOP44 [SA638]  
M29W022BT@PLCC32 [SA015A1T]  
M29W040@PLCC32 [SA015A1T]  
M29W040B@PLCC32 [SA015A1T]  
M29W064FB@TSOP48 [SB247-B4806]  
M29W102BB@TSOP40 [SA623-B4002]  
M29W116BB@TSOP40 [SA409T-B4002]  
M29W160BB@PSOP44 [SA638]  
M29W160BT@PSOP44 [SA638]  
M29W160DB@PSOP44 [SA638]  
M29W160DT@PSOP44 [SA638]  
M29W160EB@TSOP48 [SB247-B4806]  
M29W160ET@TSOP48 [SB247-B4806]  
M29W160FT@TSOP48 [SB247-B4806]  
M29W200BB@TSOP48 [SB247-B4806]  
M29W200BT@TSOP48 [SB247-B4806]  
M29W256TP@TSOP48 [SB247-B4806]  
M29W320DT@TSOP48 [SB247-B4806]  
M29W320ET@TSOP48 [SB247-B4806]  
M29W320FT@TSOP48 [SB247-B4806]  
M29W400B@TSOP48 [SB247-B4806]  
M29W400BB@TSOP48 [SB247-B4806]  
M29W400BT@TSOP48 [SB247-B4806]  
M29W400DB@TSOP48 [SB247-B4806]  
M29W400DT@TSOP48 [SB247-B4806]  
M29W400T@TSOP48 [SB247-B4806]  
M29W512B@TSOP32 [SA620-B4807]  
M29W640DT@TSOP48 [SB247-B4806]  
M29W641DL@TSOP48 [SB247-B4806]  
M29W800AB@TSOP48 [SB247-B4806]  
M29W800AT@TSOP48 [SB247-B4806]  
M29W800B@TSOP48 [SB247-B4806]

M29W800DB@PSOP44 [SA638]  
M29W800DT@PSOP44 [SA638]  
M29W800T@PSOP44 [SA638]  
M34C02  
M34C02@SOIC8 [SA602A]  
M34D32  
M34D32@TSSOP8 [SA643]  
M34D64@SOIC8 [SA602A]  
M34E02  
M34E02@SOIC8 [SA602A]  
M35080  
M45PE10@SOIC8 [SA602A]  
M45PE16@SOIC8 [SA605B]  
M45PE20@SOIC8 [SA602A]  
M45PE20@VQFPN8 [SA683]  
M45PE40@SOIC8 [SA605B]  
M45PE40@VQFPN8 [SA683]  
M45PE80@SOIC16 [SA404]  
M45PE80@SOIC8 [SA605B]  
M45PE80@VQFPN8 [SA683]  
M48C02  
M48C12  
M48T02  
M48T08  
M48T128V  
M48T129V  
M48T12B  
M48T30  
M48T32  
M48T35  
M48T35AV  
M48T35AY  
M48T35Y  
M48T512AV  
M48T512V  
M48T513V  
M48T559  
M48T559Y  
M48T58  
M48T58Y  
M48T59  
M48T59V  
M48T59Y  
M48Z02  
M48Z08  
M48Z128  
M48Z128Y  
M48Z129Y  
M48Z18  
M48Z30Y  
M48Z32Y  
M48Z35@SOIC28 [SA404]  
M48Z35Y@SOIC28 [SA404]

M29W800DB@TSOP48 [SB247-B4806]  
M29W800DT@TSOP48 [SB247-B4806]  
M29W800T@TSOP48 [SB247-B4806]  
M34C02@MSOP8 [SA724]  
M34C02@TSOP8 [SA643]  
M34D32@SOIC8 [SA602A]  
M34D64  
M34D64@TSSOP8 [SA643]  
M34E02@MSOP8 [SA666]  
M34E02@TSOP8 [SA643]  
M35080@SOIC8 [SA602A]  
M45PE10@VQFPN8 [SA683]  
M45PE16@VQFPN8 [SA683]  
M45PE20@SOIC8 (ISP)  
M45PE20@VQFPN8 (ISP)  
M45PE40@SOIC8 (ISP)  
M45PE40@VQFPN8 (ISP)  
M45PE80@SOIC16 (ISP)  
M45PE80@SOIC8 (ISP)  
M45PE80@VQFPN8 (ISP)  
M48C02B  
M48C12B  
M48T02B  
M48T12  
M48T128Y  
M48T129Y  
M48T18  
M48T30Y  
M48T32Y  
M48T35@SOIC28 [SA404]  
M48T35AV@SOIC28 [SA404]  
M48T35AY@SOIC28 [SA404]  
M48T35Y@SOIC28 [SA404]  
M48T512AY  
M48T512Y  
M48T513Y  
M48T559@SOIC28 [SA630]  
M48T559Y@SOIC28 [SA630]  
M48T58@SOIC28 [SA404]  
M48T58Y@SOIC28 [SA404]  
M48T59@SOIC28 [SA404]  
M48T59V@SOIC28 [SA404]  
M48T59Y@SOIC28 [SA404]  
M48Z02B  
M48Z12  
M48Z128V  
M48Z129V  
M48Z12B  
M48Z30  
M48Z32  
M48Z35  
M48Z35Y  
M48Z512AV

M48Z512AY  
M48Z512Y  
M48Z513Y  
M48Z58@SOIC28 [SA404]  
M48Z58Y@SOIC28 [SA404]  
M48Z59@SOIC28 [SA404]  
M48Z59W@SOIC28 [SA404]  
M48Z59Y@SOIC28 [SA404]  
M50FLW040A@TSOP40 [SA409T-B4002]  
M50FLW040B@PLCC32 [SA015A1T]  
M50FLW040B@VSOP32 [SA620-B4807]  
M50FLW080A@TSOP40 [SA409T-B4002]  
M50FLW080B@PLCC32 [SA015A1T]  
M50FLW080B@VSOP32 [SA620-B4807]  
M50FW016@TSOP40 [SA409T-B4002]  
M50FW040@PLCC32 [SA015A1T]  
M50FW080@PLCC32 [SA015A1T]  
M50FW080@VSOP32 [SA620-B4807]  
M50LPW012@PLCC32 [SA015A1T]  
M50LPW040@PLCC32 [SA015A1T]  
M50LPW041@PLCC32 [SA015A1T]  
M50LPW080@PLCC32 [SA015A1T]  
M50LPW116@TSOP40 [SA409T-B4002]  
M59DR008F@TSOP48 [SB247-B4806]  
M59DR032B@TSOP48 [SB247-B4806]  
M59PW016@PSOP44 [SA638]  
M59PW016@TSOP48 [SB247-B4806]  
M59PW032@TSOP48 [SB247-B4806]  
M59PW1282@PSOP44 [SA638]  
M87C257@PLCC32 [SA015A1T]  
M93C06 (08bit)@SOIC8 [SA602A]  
M93C06 (16bit)@SOIC8 [SA602A]  
M93C46 (08bit)@MLP8 [SA694]  
M93C46 (08bit)@SOIC8 [SA602A]  
M93C46 (16bit)  
M93C46 (16bit)@MSOP8 [SA666]  
M93C46 (16bit)@TSSOP8 [SA643]  
M93C46R (08bit)@MLP8 [SA694]  
M93C46R (08bit)@SOIC8 [SA602A]  
M93C46R (16bit)  
M93C46R (16bit)@MSOP8 [SA666]  
M93C46R (16bit)@TSSOP8 [SA643]  
M93C46W (08bit)@MLP8 [SA694]  
M93C46W (08bit)@SOIC8 [SA602A]  
M93C46W (16bit)  
M93C46W (16bit)@MSOP8 [SA666]  
M93C46W (16bit)@TSSOP8 [SA643]  
M93C56 (08bit)@MLP8 [SA694]  
M93C56 (08bit)@SOIC8 [SA602A]  
M93C56 (16bit)  
M93C56 (16bit)@MSOP8 [SA666]  
M93C56 (16bit)@TSSOP8 [SA643]  
M93C56R (08bit)@MLP8 [SA694]  
M48Z512V  
M48Z513V  
M48Z58  
M48Z58Y  
M48Z59  
M48Z59W  
M48Z59Y  
M50FLW040A@PLCC32 [SA015A1T]  
M50FLW040A@VSOP32 [SA620-B4807]  
M50FLW040B@TSOP40 [SA409T-B4002]  
M50FLW080A@PLCC32 [SA015A1T]  
M50FLW080A@VSOP32 [SA620-B4807]  
M50FLW080B@TSOP40 [SA409T-B4002]  
M50FW002@PLCC32 [SA015A1T]  
M50FW020@PLCC32 [SA015A1T]  
M50FW040@TSOP40 [SA409T-B4002]  
M50FW080@TSOP40 [SA409T-B4002]  
M50LPW002@PLCC32 [SA015A1T]  
M50LPW020@PLCC32 [SA015A1T]  
M50LPW040@TSOP40 [SA409T-B4002]  
M50LPW041@TSOP40 [SA409T-B4002]  
M50LPW080@TSOP40 [SA409T-B4002]  
M59DR008E@TSOP48 [SB247-B4806]  
M59DR032A@TSOP48 [SB247-B4806]  
M59PW016  
M59PW016@SDIP42 [SA028]  
M59PW032@PSOP44 [SA638]  
M59PW064@PSOP44 [SA638]  
M87C257  
M93C06 (08bit)  
M93C06 (16bit)  
M93C46 (08bit)  
M93C46 (08bit)@MSOP8 [SA666]  
M93C46 (08bit)@TSSOP8 [SA643]  
M93C46 (16bit)@MLP8 [SA694]  
M93C46 (16bit)@SOIC8 [SA602A]  
M93C46R (08bit)  
M93C46R (08bit)@MSOP8 [SA666]  
M93C46R (08bit)@TSSOP8 [SA643]  
M93C46R (16bit)@MLP8 [SA694]  
M93C46R (16bit)@SOIC8 [SA602A]  
M93C46W (08bit)  
M93C46W (08bit)@MSOP8 [SA666]  
M93C46W (08bit)@TSSOP8 [SA643]  
M93C46W (16bit)@MLP8 [SA694]  
M93C46W (16bit)@SOIC8 [SA602A]  
M93C56 (08bit)  
M93C56 (08bit)@MSOP8 [SA666]  
M93C56 (08bit)@TSSOP8 [SA643]  
M93C56 (16bit)@MLP8 [SA694]  
M93C56 (16bit)@SOIC8 [SA602A]  
M93C56R (08bit)  
M93C56R (08bit)@MSOP8 [SA666]

M93C56R(08bit)@SOIC8 [SA602A]  
M93C56R(16bit)  
M93C56R(16bit)@MSOP8 [SA666]  
M93C56R(16bit)@TSSOP8 [SA643]  
M93C56W(08bit)@MLP8 [SA694]  
M93C56W(08bit)@SOIC8 [SA602A]  
M93C56W(16bit)  
M93C56W(16bit)@MSOP8 [SA666]  
M93C56W(16bit)@TSSOP8 [SA643]  
M93C66(08bit)@MLP8 [SA694]  
M93C66(08bit)@SOIC8 [SA602A]  
M93C66(16bit)  
M93C66(16bit)@MSOP8 [SA666]  
M93C66(16bit)@TSSOP8 [SA643]  
M93C66R(08bit)@MLP8 [SA694]  
M93C66R(08bit)@SOIC8 [SA602A]  
M93C66R(16bit)  
M93C66R(16bit)@MSOP8 [SA666]  
M93C66R(16bit)@TSSOP8 [SA643]  
M93C66W(08bit)@MLP8 [SA694]  
M93C66W(08bit)@SOIC8 [SA602A]  
M93C66W(16bit)  
M93C66W(16bit)@MSOP8 [SA666]  
M93C66W(16bit)@TSSOP8 [SA643]  
M93C76(08bit)@MLP8 [SA694]  
M93C76(08bit)@SOIC8 [SA602A]  
M93C76(16bit)  
M93C76(16bit)@MSOP8 [SA666]  
M93C76(16bit)@TSSOP8 [SA643]  
M93C76R(08bit)@MLP8 [SA694]  
M93C76R(08bit)@SOIC8 [SA602A]  
M93C76R(16bit)  
M93C76R(16bit)@MSOP8 [SA666]  
M93C76R(16bit)@TSSOP8 [SA643]  
M93C76W(08bit)@MLP8 [SA694]  
M93C76W(08bit)@SOIC8 [SA602A]  
M93C76W(16bit)  
M93C76W(16bit)@MSOP8 [SA666]  
M93C76W(16bit)@TSSOP8 [SA643]  
M93C86(08bit)@MLP8 [SA694]  
M93C86(08bit)@SOIC8 [SA602A]  
M93C86(16bit)  
M93C86(16bit)@MSOP8 [SA666]  
M93C86(16bit)@TSSOP8 [SA643]  
M93C86R(08bit)@MLP8 [SA694]  
M93C86R(08bit)@SOIC8 [SA602A]  
M93C86R(16bit)  
M93C86R(16bit)@MSOP8 [SA666]  
M93C86R(16bit)@TSSOP8 [SA643]  
M93C86W(08bit)@MLP8 [SA694]  
M93C86W(08bit)@SOIC8 [SA602A]  
M93C86W(16bit)  
M93C86W(16bit)@MSOP8 [SA666]

M93C56R(08bit)@TSSOP8 [SA643]  
M93C56R(16bit)@MLP8 [SA694]  
M93C56R(16bit)@SOIC8 [SA602A]  
M93C56W(08bit)  
M93C56W(08bit)@MSOP8 [SA666]  
M93C56W(08bit)@TSSOP8 [SA643]  
M93C56W(16bit)@MLP8 [SA694]  
M93C56W(16bit)@SOIC8 [SA602A]  
M93C66(08bit)  
M93C66(08bit)@MSOP8 [SA666]  
M93C66(08bit)@TSSOP8 [SA643]  
M93C66(16bit)@MLP8 [SA694]  
M93C66(16bit)@SOIC8 [SA602A]  
M93C66R(08bit)  
M93C66R(08bit)@MSOP8 [SA666]  
M93C66R(08bit)@TSSOP8 [SA643]  
M93C66R(16bit)@MLP8 [SA694]  
M93C66R(16bit)@SOIC8 [SA602A]  
M93C66W(08bit)  
M93C66W(08bit)@MSOP8 [SA666]  
M93C66W(08bit)@TSSOP8 [SA643]  
M93C66W(16bit)@MLP8 [SA694]  
M93C66W(16bit)@SOIC8 [SA602A]  
M93C76(08bit)  
M93C76(08bit)@MSOP8 [SA666]  
M93C76(08bit)@TSSOP8 [SA643]  
M93C76(16bit)@MLP8 [SA694]  
M93C76(16bit)@SOIC8 [SA602A]  
M93C76R(08bit)  
M93C76R(08bit)@MSOP8 [SA666]  
M93C76R(08bit)@TSSOP8 [SA643]  
M93C76R(16bit)@MLP8 [SA694]  
M93C76R(16bit)@SOIC8 [SA602A]  
M93C76W(08bit)  
M93C76W(08bit)@MSOP8 [SA666]  
M93C76W(08bit)@TSSOP8 [SA643]  
M93C76W(16bit)@MLP8 [SA694]  
M93C76W(16bit)@SOIC8 [SA602A]  
M93C86(08bit)  
M93C86(08bit)@MSOP8 [SA666]  
M93C86(08bit)@TSSOP8 [SA643]  
M93C86(16bit)@MLP8 [SA694]  
M93C86(16bit)@SOIC8 [SA602A]  
M93C86R(08bit)  
M93C86R(08bit)@MSOP8 [SA666]  
M93C86R(08bit)@TSSOP8 [SA643]  
M93C86R(16bit)@MLP8 [SA694]  
M93C86R(16bit)@SOIC8 [SA602A]  
M93C86W(08bit)  
M93C86W(08bit)@MSOP8 [SA666]  
M93C86W(08bit)@TSSOP8 [SA643]  
M93C86W(16bit)@MLP8 [SA694]  
M93C86W(16bit)@SOIC8 [SA602A]

M93C86W(16bit)@TSSOP8 [SA643]  
M93CS566@SOIC8 [SA602A]  
M93S46@SOIC8 [SA602A]  
M93S46R  
M93S46R@TSSOP8 [SA643]  
M93S46W@SOIC8 [SA602A]  
M93S56  
M93S56@TSSOP8 [SA643]  
M93S56R@SOIC8 [SA602A]  
M93S56W  
M93S56W@TSSOP8 [SA643]  
M93S66@SOIC8 [SA602A]  
M93S66R  
M93S66R@TSSOP8 [SA643]  
M93S66W@SOIC8 [SA602A]  
M95010  
M95010@SOIC8 [SA602A]  
M95010@TSSOP8 [SA643]  
M95020  
M95020@SOIC8 [SA602A]  
M95020@TSSOP8 [SA643]  
M95040  
M95040@SOIC8 [SA602A]  
M95040@TSSOP8 [SA643]  
M95080  
M95080@SOIC8 [SA602A]  
M95080@TSSOP14 [SA026]  
M95080@TSSOP8 [SA643]  
M95080@UFDFPN8 [SA724]  
M95128 (ISP)  
M95128@TSSOP14 (ISP)  
M95128@TSSOP8 (ISP)  
M95128[150mil]@SOIC8 (ISP)  
M95128[200mil]@SOIC8 (ISP)  
M95160 (ISP)  
M95160@SOIC8 (ISP)  
M95160@TSSOP14 (ISP)  
M95160@TSSOP8 (ISP)  
M95256  
M95256@TSSOP14 [SA026]  
M95256@TSSOP8 [SA643]  
M95256[150mil]@SOIC8 [SA602A]  
M95256[200mil]@SOIC8 [SA605B]  
M95320  
M95320@SOIC8 [SA602A]  
M95320@TSSOP14 [SA026]  
M95320@TSSOP8 [SA643]  
M95320@UFDFPN8 [SA724]  
M95512@SOIC8 (ISP)  
M95512@TSSOP8 (ISP)  
M95640 (ISP)  
M95640@SOIC8 (ISP)  
M95640@TSSOP14 (ISP)

M93CS566  
M93S46  
M93S46@TSSOP8 [SA643]  
M93S46R@SOIC8 [SA602A]  
M93S46W  
M93S46W@TSSOP8 [SA643]  
M93S56@SOIC8 [SA602A]  
M93S56R  
M93S56R@TSSOP8 [SA643]  
M93S56W@SOIC8 [SA602A]  
M93S66  
M93S66@TSSOP8 [SA643]  
M93S66R@SOIC8 [SA602A]  
M93S66W  
M93S66W@TSSOP8 [SA643]  
M95010 (ISP)  
M95010@SOIC8 (ISP)  
M95010@TSSOP8 (ISP)  
M95020 (ISP)  
M95020@SOIC8 (ISP) [SA602]  
M95020@TSSOP8 (ISP) [SA643]  
M95040 (ISP)  
M95040@SOIC8 (ISP) [SA602]  
M95040@TSSOP8 (ISP) [SA643]  
M95080 (ISP)  
M95080@SOIC8 (ISP)  
M95080@TSSOP14 (ISP)  
M95080@TSSOP8 (ISP)  
M95128  
M95128@TSSOP14 [SA026]  
M95128@TSSOP8 [SA643]  
M95128[150mil]@SOIC8 [SA602A]  
M95128[200mil]@SOIC8 [SA605B]  
M95160  
M95160@SOIC8 [SA602A]  
M95160@TSSOP14 [SA026]  
M95160@TSSOP8 [SA643]  
M95160@UFDFPN8 [SA724]  
M95256 (ISP)  
M95256@TSSOP14 (ISP)  
M95256@TSSOP8 (ISP)  
M95256[150mil]@SOIC8 (ISP)  
M95256[200mil]@SOIC8 (ISP)  
M95320 (ISP)  
M95320@SOIC8 (ISP)  
M95320@TSSOP14 (ISP)  
M95320@TSSOP8 (ISP)  
M95512@SOIC8 [SA602A]  
M95512@TSSOP8 [SA643]  
M95640  
M95640@SOIC8 [SA602A]  
M95640@TSSOP14 [SA026]  
M95640@TSSOP8 [SA643]

M95640@TSSOP8 (ISP)  
M95M01-R@SOP8 (150 mil) [SA602A]  
M95M01-R@WLCS8  
M95M01-W@SOP8 (200 mil) [SA605B]  
M95M02-DR@SOP8 (150 mil) [SA602A]  
M95M02-DR@WLCS8  
M95P02@SOIC8 [SA602A]  
M95P04@SOIC8 [SA602A]  
M95P08@SOIC8 [SA602A]  
MK48C02B  
MK48C12B  
MK48T02B  
MK48T12  
MK48T18  
MK48T32Y  
MK48T35@SOIC28 [SA404]  
MK48T35Y@SOIC28 [SA404]  
MK48T512Y  
MK48Z02B  
MK48Z12  
MK48Z18  
MK48Z32Y  
MK48Z35@SOIC28 [SA404]  
MK48Z35Y@SOIC28 [SA404]  
MK48Z512Y  
MKI48Z02B  
MKI48Z12B  
N29L064@FBGA48 [SA778]  
N29L064@TSOP48  
N29Q064@PSOP44  
NAND08GW3B2AN6@TSOP48 [SB247-B4806]  
NAND08GW3B2CN6@TSOP48 [SB247-B4806]  
ST24C01  
ST24C02A  
ST24C16  
ST24FC21  
ST24FW21  
ST24LC21B  
ST24LW21  
ST24W01  
ST24W02  
ST24W04C  
ST26C201  
ST26C201@TSOP32 [SA410T-B4001]  
ST27256  
ST27C256  
ST93C06 (08bit)@SOIC8 [SA602A]  
ST93C06 (16bit)@SOIC8 [SA602A]  
ST93C46 (08bit)@SOIC8 [SA602A]  
ST93C46 (16bit)@SOIC8 [SA602A]  
ST93C46A (08bit)@SOIC8 [SA602A]  
ST93C46A (16bit)@SOIC8 [SA602A]  
ST93C46C (08bit)@SOIC8 [SA602A]  
ST93C46C (16bit)@SOIC8 [SA602A]  
M95640@UDFPN8 [SA724]  
M95M01-R@SOP8 (200 mil) [SA605B]  
M95M01-W@SOP8 (150 mil) [SA602A]  
M95M01-W@WLCS8  
M95M02-DR@SOP8 (200 mil) [SA605B]  
M95P02  
M95P04  
M95P08  
MK48C02  
MK48C12  
MK48T02  
MK48T08  
MK48T12B  
MK48T32  
MK48T35  
MK48T35Y  
MK48T512V  
MK48Z02  
MK48Z08  
MK48Z12B  
MK48Z32  
MK48Z35  
MK48Z35Y  
MK48Z512V  
MKI48Z02  
MKI48Z12  
MKI48Z18  
N29L064@PSOP44  
N29Q064@BGA48 [SA778]  
N29Q064@TSOP48  
ST24C01@SOIC8 [SA602A]  
ST24C02A@SOIC8 [SA602A]  
ST24C16@SOIC8  
ST24FC21@SOIC8 [SA602A]  
ST24FW21@SOIC8 [SA602A]  
ST24LC21B@SOIC8 [SA602A]  
ST24LW21@SOIC8 [SA602A]  
ST24W01@SOIC8  
ST24W02@SOIC8  
ST24W04C@SOIC8  
ST26C201@PLCC32 [SA015A1T]  
ST27128A  
ST2764A  
ST93C06 (08bit)  
ST93C06 (16bit)  
ST93C46 (08bit)  
ST93C46 (16bit)  
ST93C46A (08bit)  
ST93C46A (16bit)  
ST93C46C (08bit)  
ST93C46C (16bit)

ST93C46C (16bit)@S0IC8 [SA602A]	ST93C46T (08bit)
ST93C46T (08bit)@S0IC8 [SA602A]	ST93C46T (16bit)
ST93C46T (16bit)@S0IC8 [SA602A]	ST93C47C (08bit)
ST93C47C (08bit)@S0IC8 [SA602A]	ST93C47C (16bit)
ST93C47C (16bit)@S0IC8 [SA602A]	ST93C47T (08bit)
ST93C47T (08bit)@S0IC8 [SA602A]	ST93C47T (16bit)
ST93C47T (16bit)@S0IC8 [SA602A]	ST93C56 (08bit)
ST93C56 (08bit)@S0IC8 [SA602A]	ST93C56 (16bit)
ST93C56 (16bit)@S0IC8 [SA602A]	ST93C56B (08bit)
ST93C56B (08bit)@S0IC8 [SA602A]	ST93C56B (16bit)
ST93C56B (16bit)@S0IC8 [SA602A]	ST93C56C (08bit)
ST93C56C (08bit)@S0IC8 [SA602A]	ST93C56C (16bit)
ST93C56C (16bit)@S0IC8 [SA602A]	ST93C57C (08bit)
ST93C57C (08bit)@S0IC8 [SA602A]	ST93C57C (16bit)
ST93C57C (16bit)@S0IC8 [SA602A]	ST93C66 (08bit)
ST93C66 (08bit)@S0IC8 [SA602A]	ST93C66 (16bit)
ST93C66 (16bit)@S0IC8 [SA602A]	ST93C67 (08bit)
ST93C67 (08bit)@S0IC8 [SA602A]	ST93C67 (16bit)
ST93C67 (16bit)@S0IC8 [SA602A]	ST93C76 (08bit)
ST93C76 (08bit)@S0IC8 [SA602A]	ST93C76 (16bit)
ST93C76 (16bit)@S0IC8 [SA602A]	ST93C86 (08bit)
ST93C86 (08bit)@S0IC8 [SA602A]	ST93C86 (16bit)
ST93C86 (16bit)@S0IC8 [SA602A]	ST93CS46
ST93CS46@S0IC8 [SA602A]	ST93CS47
ST93CS47@S0IC8 [SA602A]	ST93CS56
ST93CS56@S0IC8 [SA602A]	ST93CS566
ST93CS566@S0IC8 [SA602A]	ST93CS57
ST93CS57@S0IC8 [SA602A]	ST93CS66
ST93CS66@S0IC14 [SA602]	ST93CS67
ST93CS67@S0IC14 [SA602]	STTS2002@TDFN8 [SA724]
TS27C256	TS27C64
TS27C64@PLCC32 [SA015A1T]	TS27C64A
TS27C64A@PLCC32 [SA015A1T]	TS28C16A
TS28C17A	

## MICROCONTROLLER

ST7FDALIF2M6@S0IC20 (ISP)	ST7FLITE02B6 (ISP)
ST7FLITE02M6@S0IC16 (ISP)	ST7FLITE02Y0B6 (ISP)
ST7FLITE02Y0M6@S0IC16 (ISP)	ST7FLITE05B6 (ISP)
ST7FLITE05M6@S0IC16 (ISP)	ST7FLITE05Y0B6 (ISP)
ST7FLITE05Y0M6@S0IC16 (ISP)	ST7FLITE09B6 (ISP)
ST7FLITE09M6@S0IC16 (ISP)	ST7FLITE09Y0B6 (ISP)
ST7FLITE09Y0M6@S0IC16 (ISP)	ST7FLITE10F1B6 (ISP)
ST7FLITE10F1M6@S0IC20 (ISP)	ST7FLITE15F1B6 (ISP)
ST7FLITE15F1M6@S0IC20 (ISP)	ST7FLITE19F1B6 (ISP)
ST7FLITE19F1M6@S0IC20 (ISP)	ST7FLITE20F2B6 (ISP)
ST7FLITE20F2M6@S0IC20 (ISP)	ST7FLITE25F2B6 (ISP)
ST7FLITE25F2M6@S0IC20 (ISP)	ST7FLITE29F2B6 (ISP)
ST7FLITE29F2M6@S0IC20 (ISP)	ST7FLITE30F2B6 (ISP)
ST7FLITE30F2M6@S0IC20 (ISP)	ST7FLITE33F2B6 (ISP)
ST7FLITE33F2M6@S0IC20 (ISP)	ST7FLITE35F2B6 (ISP)

ST7FLITE35F2M6@SOIC20 (ISP)  
ST7FLITE39F2M6@SOIC20 (ISP)  
ST7FLITES2M6@SOIC16 (ISP)  
ST7FLITES2Y0M6@SOIC16 (ISP)  
ST7FLITES5M6@SOIC16 (ISP)  
ST7FLITES5Y0M6@SOIC16 (ISP)  
STM32F100C6@LQFP48 (ISP)  
STM32F100CB@LQFP48 (ISP)  
STM32F100R4@LQFP64 (ISP)  
STM32F100R6@LQFP64 (ISP)  
STM32F100R8@LQFP64 (ISP)  
STM32F100RB@LQFP64 (ISP)  
STM32F100RD@LQFP64 (ISP)  
STM32F100V8@LQFP100 (ISP)  
STM32F100VC@LQFP100 (ISP)  
STM32F100VE@LQFP100 (ISP)  
STM32F100ZD@LQFP144 (ISP)

ST7FLITE39F2B6 (ISP)  
ST7FLITES2B6 (ISP)  
ST7FLITES2Y0B6 (ISP)  
ST7FLITES5B6 (ISP)  
ST7FLITES5Y0B6 (ISP)  
STM32F100C4@LQFP48 (ISP)  
STM32F100C8@LQFP48 (ISP)  
STM32F100R4@BGA64 (ISP)  
STM32F100R6@BGA64 (ISP)  
STM32F100R8@BGA64 (ISP)  
STM32F100RB@BGA64 (ISP)  
STM32F100RC@LQFP64 (ISP)  
STM32F100RE@LQFP64 (ISP)  
STM32F100VB@LQFP100 (ISP)  
STM32F100VD@LQFP100 (ISP)  
STM32F100ZC@LQFP144 (ISP)  
STM32F100ZE@LQFP144 (ISP)

## STC

### MICROCONTROLLER

STC89C516RD	STC89C516RD@PLCC44 [SA244]
STC89C516RD@TQFP44 [SA245A-B4805]	
STC89C58RD	STC89C58RD@PLCC44 [SA244]
STC89C58RD@TQFP44 [SA245A-B4805]	STC89LE516AD
STC89LE516AD@PLCC44 [SA244]	
STC89LE516AD@TQFP44 [SA245A-B4805]	STC89LE516X2@PLCC44 [SA244]
STC89LE516X2	
STC89LE516X2@TQFP44 [SA245A-B4805]	STC89LE52AD@PLCC44 [SA244]
STC89LE52AD	
STC89LE52AD@TQFP44 [SA245A-B4805]	STC89LE54AD@PLCC44 [SA244]
STC89LE54AD	
STC89LE54AD@TQFP44 [SA245A-B4805]	STC89LE556AD@PLCC44 [SA244]
STC89LE556AD	
STC89LE556AD@TQFP44 [SA245A-B4805]	STC89LE556X2@PLCC44 [SA244]
STC89LE556X2	
STC89LE556X2@TQFP44 [SA245A-B4805]	STC89LE58AD@PLCC44 [SA244]
STC89LE58AD	
STC89LE58AD@TQFP44 [SA245A-B4805]	STC89LV516RD@PLCC44 [SA244]
STC89LV516RD	
STC89LV516RD@TQFP44 [SA245A-B4805]	STC89LV58RD@PLCC44 [SA244]
STC89LV58RD	
STC89LV58RD@TQFP44 [SA245A-B4805]	

## SUMMIT

### E (E) PROM/FRAM/NVRAM

S24022	S24022@SOIC8 [SA602A]
S24023	S24023@SOIC8 [SA602A]
S24042	S24042@SOIC8 [SA602A]

S24043	S24043@SOIC8 [SA602A]
S24162	S24162@SOIC8 [SA602A]
S24VP02	S24VP02@SOIC8 [SA602A]
S24VP04	S24VP04@SOIC8 [SA602A]
S24VP08	S24VP08@SOIC8 [SA602A]
S24VP16	S24VP16@SOIC8 [SA602A]
S93462 (08bit)	S93462 (08bit)@SOIC8 [SA602A]
S93462 (16bit)	S93462 (16bit)@SOIC8 [SA602A]
S93463 (08bit)	S93463 (08bit)@SOIC8 [SA602A]
S93463 (16bit)	S93463 (16bit)@SOIC8 [SA602A]
S93662 (08bit)	S93662 (08bit)@SOIC8 [SA602A]
S93662 (16bit)	S93662 (16bit)@SOIC8 [SA602A]
S93663 (08bit)	S93663 (08bit)@SOIC8 [SA602A]
S93663 (16bit)	S93663 (16bit)@SOIC8 [SA602A]
S93WD462 (08bit)	S93WD462 (08bit)@SOIC8 [SA602A]
S93WD462 (16bit)	S93WD462 (16bit)@SOIC8 [SA602A]
S93WD463 (08bit)	S93WD463 (08bit)@SOIC8 [SA602A]
S93WD463 (16bit)	S93WD463 (16bit)@SOIC8 [SA602A]
S93WD662 (08bit)	S93WD662 (08bit)@SOIC8 [SA602A]
S93WD662 (16bit)	S93WD662 (16bit)@SOIC8 [SA602A]
S93WD663 (08bit)	S93WD663 (08bit)@SOIC8 [SA602A]
S93WD663 (16bit)	S93WD663 (16bit)@SOIC8 [SA602A]

## SUNMOON

### E (E) PROM/FRAM/NVRAM

SM24C02	SM24C02@SOP8 [SA602A]
SM24C04	SM24C04@SOP8 [SA602A]
SM24C08	SM24C08@SOP8 [SA602A]
SM24C16	SM24C16@SOP8 [SA602A]

## SUNPLUS

### MICROCONTROLLER

SPMC65P2102A (dip18)	SPMC65P2102A (dip18) (ISP)
SPMC65P2102A@SOP18 [SA404]	SPMC65P2102A@SOP18 (ISP)
SPMC65P2104A (dip18)	SPMC65P2104A (dip18) (ISP)
SPMC65P2104A@SOP18 [SA404]	SPMC65P2104A@SOP18 (ISP)
SPMC65P2202A (dip16)	SPMC65P2202A (dip16) (ISP)
SPMC65P2202A (dip20)	SPMC65P2202A (dip20) (ISP)
SPMC65P2202A@SOP16 [SA404]	SPMC65P2202A@SOP16 (ISP)
SPMC65P2202A@SOP20 [SA404]	SPMC65P2202A@SOP20 (ISP)
SPMC65P2204A (dip16)	SPMC65P2204A (dip16) (ISP)
SPMC65P2204A (dip20)	SPMC65P2204A (dip20) (ISP)
SPMC65P2204A@SOP16 [SA404]	SPMC65P2204A@SOP16 (ISP)
SPMC65P2204A@SOP20 [SA404]	SPMC65P2204A@SOP20 (ISP)
SPMC65P2404A (dip20)	SPMC65P2404A (dip20) (ISP)
SPMC65P2404A (dip28)	SPMC65P2404A (dip28) (ISP)
SPMC65P2404A@SOP20 [SA404]	SPMC65P2404A@SOP20 (ISP)
SPMC65P2404A@SOP28 [SA404]	SPMC65P2404A@SOP28 (ISP)

SPMC65P2408A (dip28)  
SPMC65P2408A (dip32)  
SPMC65P2408A@SOP28 [SA404]  
SPMC65P2408A@SOP32 [SA603]

SPMC65P2408A (dip28) (ISP)  
SPMC65P2408A (dip32) (ISP)  
SPMC65P2408A@SOP28 (ISP)  
SPMC65P2408A@SOP32 (ISP)

## SYNCMOS

### E (E) PROM/FRAM/NVRAM

F29C31004B  
F29C31004B@TSOP32 [SA410T-B4001]  
F29C31004T@PLCC32 [SA015A1T]  
F29C51000B  
F29C51000B@TSOP32 [SA410T-B4001]  
F29C51000T@PLCC32 [SA015A1T]  
F29C51001B  
F29C51001B@TSOP32 [SA410T-B4001]  
F29C51001T@PLCC32 [SA015A1T]  
F29C51002B  
F29C51002B@TSOP32 [SA410T-B4001]  
F29C51002T@PLCC32 [SA015A1T]  
F29C51004B  
F29C51004B@TSOP32 [SA410T-B4001]  
F29C51004T@PLCC32 [SA015A1T]  
F29LC51000  
F29LC51000@TSOP32 [SA410T-B4001]  
F29LC51001@PLCC32 [SA015A1T]  
F29LC51002  
F29LC51002@TSOP32 [SA410T-B4001]  
S29C31001B@PLCC32 [SA015A1T]  
S29C31001T  
S29C31001T@TSOP32 [SA410T-B4001]  
S29C31002B@PLCC32 [SA015A1T]  
S29C31002T  
S29C31002T@TSOP32 [SA410T-B4001]  
S29C31004B@PLCC32 [SA015A1T]  
S29C31004T  
S29C31004T@TSOP32 [SA410T-B4001]  
S29C51001B@PLCC32 [SA015A1T]  
S29C51001T  
S29C51001T@TSOP32 [SA410T-B4001]  
S29C51002B@PLCC32 [SA015A1T]  
S29C51002T  
S29C51002T@TSOP32 [SA410T-B4001]  
S29C51004B@PLCC32 [SA015A1T]  
S29C51004T  
S29C51004T@TSOP32 [SA410T-B4001]

F29C31004B@PLCC32 [SA015A1T]  
F29C31004T  
F29C31004T@TSOP32 [SA410T-B4001]  
F29C51000B@PLCC32 [SA015A1T]  
F29C51000T  
F29C51000T@TSOP32 [SA410T-B4001]  
F29C51001B@PLCC32 [SA015A1T]  
F29C51001T  
F29C51001T@TSOP32 [SA410T-B4001]  
F29C51002B@PLCC32 [SA015A1T]  
F29C51002T  
F29C51002T@TSOP32 [SA410T-B4001]  
F29C51004B@PLCC32 [SA015A1T]  
F29C51004T  
F29C51004T@TSOP32 [SA410T-B4001]  
F29LC51000@PLCC32 [SA015A1T]  
F29LC51001  
F29LC51001@TSOP32 [SA410T-B4001]  
F29LC51002@PLCC32 [SA015A1T]  
S29C31001B  
S29C31001B@TSOP32 [SA410T-B4001]  
S29C31001T@PLCC32 [SA015A1T]  
S29C31002B  
S29C31002B@TSOP32 [SA410T-B4001]  
S29C31002T@PLCC32 [SA015A1T]  
S29C31004B  
S29C31004B@TSOP32 [SA410T-B4001]  
S29C31004T@PLCC32 [SA015A1T]  
S29C51001B  
S29C51001B@TSOP32 [SA410T-B4001]  
S29C51001T@PLCC32 [SA015A1T]  
S29C51002B  
S29C51002B@TSOP32 [SA410T-B4001]  
S29C51002T@PLCC32 [SA015A1T]  
S29C51004B  
S29C51004B@TSOP32 [SA410T-B4001]  
S29C51004T@PLCC32 [SA015A1T]

### MICROCONTROLLER

MSU1958  
MSU1958@TQFP44 [SA675-B4805]

MSU1958@PLCC44 [SA244]  
MSU2952

MSU2952@PLCC44 [SA244]  
MSU2964  
MSU2964@TQFP44 [SA675-B4805]  
OB37R04A1@SOP14 [SA602]  
OB37R259A@SOP14 [SA602]  
OB39A08T1@QFP32 [SA636]  
OB39A08T1@SOP20 [SA404]  
OB39A08T1@SOP28 [SA404]  
OB39A08T2@SOP28 [SA404]  
OB39A16D2@QFP48 [SA248-B4804]  
OB39A16T1@SOP16 [SA602]  
OB39A16T1@SOP24 [SA404]  
SM2958  
SM2958@TQFP44 [SA675-B4805]  
SM2965@PLCC44 [SA244]  
SM39A16M1@LQFP32 [SA636]  
SM39R02G1@DIP10  
SM39R02G1@MSOP10 [SA770]  
SM39R04G1@DIP10  
SM39R04G1@MSOP10 [SA770]  
SM39R05A3@DIP10  
SM39R05A3@DIP16  
SM39R05A3@SOP10 [SA770]  
SM39R05A3@SOP16 [SA602]  
SM39R05A3@SSOP20 [SA674]  
SM39R05A5@DIP8  
SM39R05A5@SOP8 [SA770]  
SM39R08A2 (dip20)  
SM39R08A2 (dip28)  
SM39R08A2@SOP16 [SA404]  
SM39R08A2@SOP24 [SA404]  
SM39R08A3@DIP10  
SM39R08A3@DIP16  
SM39R08A3@SOP10 [SA770]  
SM39R08A3@SOP16 [SA602]  
SM39R08A3@SSOP20 [SA674]  
SM39R08A5@DIP8  
SM39R08A5@SOP8 [SA770]  
SM39R12A2 (dip20)  
SM39R12A2 (dip28)  
SM39R12A2@SOP16 [SA404]  
SM39R12A2@SOP24 [SA404]  
SM39R16A2 (dip16)  
SM39R16A2 (dip24)  
SM39R16A2@PLCC28 [SA008A]  
SM39R16A2@SOP20 [SA404]  
SM39R16A2@SOP28 [SA404]  
SM39R16A3@DIP14  
SM39R16A3@DIP20  
SM39R16A3@LQFP32 [SA636]  
SM39R16A3@SOP14 [SA602]  
SM39R16A3@SOP20 [SA404]  
SM39R16A3@SSOP20 [SA674]

MSU2952@TQFP44 [SA675-B4805]  
MSU2964@PLCC44 [SA244]  
OB37R04A1@SOP10 [SA602]  
OB37R04A1@SOP16 [SA602]  
OB37R259A@SOP16 [SA602]  
OB39A08T1@SOP16 [SA602]  
OB39A08T1@SOP24 [SA404]  
OB39A08T2@SOP24 [SA404]  
OB39A16D1@QFP48 [SA248-B4804]  
OB39A16T1@QFP32 [SA636]  
OB39A16T1@SOP20 [SA404]  
OB39A16T1@SOP28 [SA404]  
SM2958@PLCC44 [SA244]  
SM2965  
SM2965@TQFP44 [SA675-B4805]  
SM39A16M1@SOP28 [SA404]  
SM39R02G1@DIP14  
SM39R02G1@SOP14 [SA602]  
SM39R04G1@DIP14  
SM39R04G1@SOP14 [SA602]  
SM39R05A3@DIP14  
SM39R05A3@DIP20  
SM39R05A3@SOP14 [SA602]  
SM39R05A3@SOP20 [SA404]  
SM39R05A5@DIP10  
SM39R05A5@SOP10 [SA770]  
SM39R08A2 (dip16)  
SM39R08A2 (dip24)  
SM39R08A2@PLCC28 [SA008A]  
SM39R08A2@SOP20 [SA404]  
SM39R08A2@SOP28 [SA404]  
SM39R08A3@DIP14  
SM39R08A3@DIP20  
SM39R08A3@SOP14 [SA602]  
SM39R08A3@SOP20 [SA404]  
SM39R08A5@DIP10  
SM39R08A5@SOP10 [SA770]  
SM39R12A2 (dip16)  
SM39R12A2 (dip24)  
SM39R12A2@PLCC28 [SA008A]  
SM39R12A2@SOP20 [SA404]  
SM39R12A2@SOP28 [SA404]  
SM39R16A2 (dip20)  
SM39R16A2 (dip28)  
SM39R16A2@SOP16 [SA404]  
SM39R16A2@SOP24 [SA404]  
SM39R16A3@DIP10  
SM39R16A3@DIP16  
SM39R16A3@DIP28  
SM39R16A3@SOP10 [SA770]  
SM39R16A3@SOP16 [SA602]  
SM39R16A3@SOP28 [SA404]  
SM39R16A6@LQFP32 [SA636]

SM39R16A6@SOP24 [SA404]  
SM39R2051  
SM39R4051  
SM59064  
SM59064@TQFP44 [SA675-B4805]  
SM59128C@PLCC44 [SA244]  
SM59128L  
SM59128L@TQFP44 [SA675-B4805]  
SM5912C (ISP)  
SM5912C@PLCC44 (ISP)  
SM5912C@TQFP44 (ISP)  
SM5912L (ISP)  
SM5912L@PLCC44 (ISP)  
SM5912L@TQFP44 (ISP)  
SM59164@PLCC44 [SA244]  
SM5916C  
SM5916C@PLCC44 [SA244]  
SM5916C@TQFP44 [SA675-B4805]  
SM5916L  
SM5916L@PLCC44 [SA244]  
SM5916L@TQFP44 [SA675-B4805]  
SM59264  
SM59264@TQFP44 [SA675-B4805]  
SM5952@PLCC44 [SA244]  
SM5952EW  
SM5952EW@TQFP44 [SA675-B4805]  
SM5953@PLCC44 [SA244]  
SM5954W  
SM5954W@TQFP44 [SA675-B4805]  
SM5958W@PLCC44 [SA244]  
SM5964  
SM5964@TQFP44 [SA675-B4805]  
SM5964A@PLCC44 [SA244]  
SM5964AC  
SM5964AC@TQFP44 [SA675-B4805]  
SM5964AL@PLCC44 [SA244]  
SM5964BW  
SM5964BW@QFP44 [SA675-B4805]  
SM5964C@PLCC44 [SA244]  
SM5964D0  
SM5964D0@TQFP44 [SA675-B4805]  
SM5964D0A@PLCC44 [SA244]  
SM5964D1A  
SM5964D1A@TQFP44 [SA675-B4805]  
SM59A16U1@LQFP44 [SA675-B4805]  
SM59D02G2C  
SM59D02G2C@PLCC44 [SA244]  
SM59D02G2C@TQFP44 [SA675-B4805]  
SM59D02G2L  
SM59D02G2L@PLCC44 [SA244]  
SM59D02G2L@TQFP44 [SA675-B4805]  
SM59D03G2C  
SM59D03G2C@PLCC44 [SA244]

SM39R16A6@SOP28 [SA404]  
SM39R2051@SOP20 [SA404]  
SM39R4051@SOP20 [SA404]  
SM59064@PLCC44 [SA244]  
SM59128C  
SM59128C@TQFP44 [SA675-B4805]  
SM59128L@PLCC44 [SA244]  
SM5912C  
SM5912C@PLCC44 [SA244]  
SM5912C@TQFP44 [SA675-B4805]  
SM5912L  
SM5912L@PLCC44 [SA244]  
SM5912L@TQFP44 [SA675-B4805]  
SM59164  
SM59164@TQFP44 [SA675-B4805]  
SM5916C (ISP)  
SM5916C@PLCC44 (ISP)  
SM5916C@TQFP44 (ISP)  
SM5916L (ISP)  
SM5916L@PLCC44 (ISP)  
SM5916L@TQFP44 (ISP)  
SM59264@PLCC44 [SA244]  
SM5952  
SM5952@QFP44 [SA675-B4805]  
SM5952EW@PLCC44 [SA244]  
SM5953  
SM5953@QFP44 [SA675-B4805]  
SM5954W@PLCC44 [SA244]  
SM5958W  
SM5958W@QFP44 [SA675-B4805]  
SM5964@PLCC44 [SA244]  
SM5964A  
SM5964A@TQFP44 [SA675-B4805]  
SM5964AC@PLCC44 [SA244]  
SM5964AL  
SM5964AL@TQFP44 [SA675-B4805]  
SM5964BW@PLCC44 [SA244]  
SM5964C  
SM5964C@TQFP44 [SA675-B4805]  
SM5964D0@PLCC44 [SA244]  
SM5964D0A  
SM5964D0A@TQFP44 [SA675-B4805]  
SM5964D1A@PLCC44 [SA244]  
SM59A16U1  
SM59A16U1@LQFP48 [SA248-B4804]  
SM59D02G2C (ISP)  
SM59D02G2C@PLCC44 (ISP)  
SM59D02G2C@TQFP44 (ISP)  
SM59D02G2L (ISP)  
SM59D02G2L@PLCC44 (ISP)  
SM59D02G2L@TQFP44 (ISP)  
SM59D03G2C (ISP)  
SM59D03G2C@PLCC44 (ISP)

SM59D03G2C@TQFP44 [SA675-B4805]  
SM59D03G2L  
SM59D03G2L@PLCC44 [SA244]  
SM59D03G2L@TQFP44 [SA675-B4805]  
SM59D04G2C  
SM59D04G2C@PLCC44 [SA244]  
SM59D04G2C@TQFP44 [SA675-B4805]  
SM59D04G2L  
SM59D04G2L@PLCC44 [SA244]  
SM59D04G2L@TQFP44 [SA675-B4805]  
SM59R01G1  
SM59R01G1@TQFP44 [SA675-B4805]  
SM59R02A1C@LQFP48 [SA248-B4804]  
SM59R02A1C@QFP44 [SA675-B4805]  
SM59R02A1L@LQFP48 [SA248-B4804]  
SM59R02A1L@QFP44 [SA675-B4805]  
SM59R02G1@PLCC44 [SA244]  
SM59R03A1C  
SM59R03A1C@PLCC44 [SA244]  
SM59R03A1L  
SM59R03A1L@PLCC44 [SA244]  
SM59R04A1C  
SM59R04A1C@PLCC44 [SA244]  
SM59R04A1L  
SM59R04A1L@PLCC44 [SA244]  
SM59R04A2C  
SM59R04A2C@PLCC44 [SA244]  
SM59R04A2L  
SM59R04A2L@PLCC44 [SA244]  
SM59R05A3C  
SM59R05A3C@PLCC44 [SA244]  
SM59R05A3L  
SM59R05A3L@PLCC44 [SA244]  
SM59R05A5C  
SM59R05A5C@PLCC44 [SA244]  
SM59R05A5L  
SM59R05A5L@PLCC44 [SA244]  
SM59R05G6W  
SM59R05G6W@PLCC44 [SA244]  
SM59R09A3C  
SM59R09A3C@PLCC44 [SA244]  
SM59R09A3L  
SM59R09A3L@PLCC44 [SA244]  
SM59R09A5C  
SM59R09A5C@PLCC44 [SA244]  
SM59R09A5L  
SM59R09A5L@PLCC44 [SA244]  
SM59R09G6W  
SM59R09G6W@PLCC44 [SA244]  
SM59R16A3C  
SM59R16A3C@PLCC44 [SA244]  
SM59R16A3L  
SM59R16A3L@PLCC44 [SA244]

SM59D03G2C@TQFP44 (ISP)  
SM59D03G2L (ISP)  
SM59D03G2L@PLCC44 (ISP)  
SM59D03G2L@TQFP44 (ISP)  
SM59D04G2C (ISP)  
SM59D04G2C@PLCC44 (ISP)  
SM59D04G2C@TQFP44 (ISP)  
SM59D04G2L (ISP)  
SM59D04G2L@PLCC44 (ISP)  
SM59D04G2L@TQFP44 (ISP)  
SM59R01G1@PLCC44 [SA244]  
SM59R02A1C  
SM59R02A1C@PLCC44 [SA244]  
SM59R02A1L  
SM59R02A1L@PLCC44 [SA244]  
SM59R02G1  
SM59R02G1@TQFP44 [SA675-B4805]  
SM59R03A1C@LQFP48 [SA248-B4804]  
SM59R03A1C@QFP44 [SA675-B4805]  
SM59R03A1L@LQFP48 [SA248-B4804]  
SM59R03A1L@QFP44 [SA675-B4805]  
SM59R04A1C@LQFP48 [SA248-B4804]  
SM59R04A1C@QFP44 [SA675-B4805]  
SM59R04A1L@LQFP48 [SA248-B4804]  
SM59R04A1L@QFP44 [SA675-B4805]  
SM59R04A2C@LQFP48 [SA248-B4804]  
SM59R04A2C@QFP44 [SA675-B4805]  
SM59R04A2L@LQFP48 [SA248-B4804]  
SM59R04A2L@QFP44 [SA675-B4805]  
SM59R05A3C@LQFP48 [SA248-B4804]  
SM59R05A3C@QFP44 [SA675-B4805]  
SM59R05A3L@LQFP48 [SA248-B4804]  
SM59R05A3L@QFP44 [SA675-B4805]  
SM59R05A5C@LQFP48 [SA248-B4804]  
SM59R05A5C@QFP44 [SA675-B4805]  
SM59R05A5L@LQFP48 [SA248-B4804]  
SM59R05A5L@QFP44 [SA675-B4805]  
SM59R05G6W@LQFP48 [SA248-B4804]  
SM59R05G6W@QFP44 [SA675-B4805]  
SM59R09A3C@LQFP48 [SA248-B4804]  
SM59R09A3C@QFP44 [SA675-B4805]  
SM59R09A3L@LQFP48 [SA248-B4804]  
SM59R09A3L@QFP44 [SA675-B4805]  
SM59R09A5C@LQFP48 [SA248-B4804]  
SM59R09A5C@QFP44 [SA675-B4805]  
SM59R09A5L@LQFP48 [SA248-B4804]  
SM59R09A5L@QFP44 [SA675-B4805]  
SM59R09G6W@LQFP48 [SA248-B4804]  
SM59R09G6W@QFP44 [SA675-B4805]  
SM59R16A3C@LQFP48 [SA248-B4804]  
SM59R16A3C@QFP44 [SA675-B4805]  
SM59R16A3L@LQFP48 [SA248-B4804]  
SM59R16A3L@QFP44 [SA675-B4805]

SM59R16A5C  
SM59R16A5C@PLCC44 [SA244]  
SM59R16A5L  
SM59R16A5L@PLCC44 [SA244]  
SM59R16G6W  
SM59R16G6W@PLCC44 [SA244]  
SM7908  
SM7908@TQFP44 [SA675-B4805]  
SM79108@PLCC44 [SA244]  
SM79164  
SM79164@TQFP44 [SA675-B4805]  
SM79164L@PLCC44 [SA244]  
SM79164V  
SM79164V@TQFP44 [SA675-B4805]  
SM7932@PLCC44 [SA244]  
SM7964  
SM7964@TQFP44 [SA675-B4805]  
SM894051@SOIC20 [SA023A]  
SM8951@PLCC44 [SA244]  
SM89516  
SM89516@TQFP44 [SA675-B4805]  
SM89516A@PLCC44 [SA244]  
SM89516AL  
SM89516AL@TQFP44 [SA675-B4805]  
SM89516B@PLCC44 [SA244]  
SM89516BL  
SM89516BL@TQFP44 [SA675-B4805]  
SM89516BW@PLCC44 [SA244]  
SM89516L  
SM89516L@TQFP44 [SA675-B4805]  
SM8951A@PLCC44 [SA244]  
SM8951AL  
SM8951AL@TQFP44 [SA675-B4805]  
SM8951B@PLCC44 [SA244]  
SM8951BL  
SM8951BL@TQFP44 [SA675-B4805]  
SM8951L@PLCC44 [SA244]  
SM8952  
SM8952@TQFP44 [SA675-B4805]  
SM8952A@PLCC44 [SA244]  
SM8952AL  
SM8952AL@TQFP44 [SA675-B4805]  
SM8952B@PLCC44 [SA244]  
SM8952BL  
SM8952BL@TQFP44 [SA675-B4805]  
SM8952BW@PLCC44 [SA244]  
SM8952L  
SM8952L@TQFP44 [SA675-B4805]  
SM8954@PLCC44 [SA244]  
SM8954A  
SM8954A@TQFP44 [SA675-B4805]  
SM8954AL@PLCC44 [SA244]  
SM8954B  
SM59R16A5C@LQFP48 [SA248-B4804]  
SM59R16A5C@QFP44 [SA675-B4805]  
SM59R16A5L@LQFP48 [SA248-B4804]  
SM59R16A5L@QFP44 [SA675-B4805]  
SM59R16G6W@LQFP48 [SA248-B4804]  
SM59R16G6W@QFP44 [SA675-B4805]  
SM7908@PLCC44 [SA244]  
SM79108  
SM79108@TQFP44 [SA675-B4805]  
SM79164@PLCC44 [SA244]  
SM79164L  
SM79164L@TQFP44 [SA675-B4805]  
SM79164V@PLCC44 [SA244]  
SM7932  
SM7932@TQFP44 [SA675-B4805]  
SM7964@PLCC44 [SA244]  
SM894051  
SM8951  
SM8951@TQFP44 [SA675-B4805]  
SM89516@PLCC44 [SA244]  
SM89516A  
SM89516A@TQFP44 [SA675-B4805]  
SM89516AL@PLCC44 [SA244]  
SM89516B  
SM89516B@TQFP44 [SA675-B4805]  
SM89516BL@PLCC44 [SA244]  
SM89516BW  
SM89516BW@QFP44 [SA675-B4805]  
SM89516L@PLCC44 [SA244]  
SM8951A  
SM8951A@TQFP44 [SA675-B4805]  
SM8951AL@PLCC44 [SA244]  
SM8951B  
SM8951B@TQFP44 [SA675-B4805]  
SM8951BL@PLCC44 [SA244]  
SM8951L  
SM8951L@TQFP44 [SA675-B4805]  
SM8952@PLCC44 [SA244]  
SM8952A  
SM8952A@TQFP44 [SA675-B4805]  
SM8952AL@PLCC44 [SA244]  
SM8952B  
SM8952B@TQFP44 [SA675-B4805]  
SM8952BL@PLCC44 [SA244]  
SM8952BW  
SM8952BW@QFP44 [SA675-B4805]  
SM8952L@PLCC44 [SA244]  
SM8954  
SM8954@TQFP44 [SA675-B4805]  
SM8954A@PLCC44 [SA244]  
SM8954AL  
SM8954AL@TQFP44 [SA675-B4805]  
SM8954B@PLCC44 [SA244]

SM8954B@TQFP44 [SA675-B4805]  
SM8954BL@PLCC44 [SA244]  
SM8954BW  
SM8954BW@QFP44 [SA675-B4805]  
SM8954L@PLCC44 [SA244]  
SM8958  
SM8958@TQFP44 [SA675-B4805]  
SM8958A@PLCC44 [SA244]  
SM8958AL  
SM8958AL@TQFP44 [SA675-B4805]  
SM8958B@PLCC44 [SA244]  
SM8958BL  
SM8958BL@TQFP44 [SA675-B4805]  
SM8958BW@PLCC44 [SA244]  
SM8958L  
SM8958L@TQFP44 [SA675-B4805]  
SM89S16R1C@PLCC44 [SA244]  
SM89T04R1C  
SM89T04R1C@TQFP44 [SA675-B4805]  
SM89T04R1L@PLCC44 [SA244]  
SM89T08R1C  
SM89T08R1C@TQFP44 [SA675-B4805]  
SM89T08R1L@PLCC44 [SA244]  
SM89T16R1C  
SM89T16R1C@TQFP44 [SA675-B4805]  
SM89T16R1L@PLCC44 [SA244]

SM8954BL  
SM8954BL@TQFP44 [SA675-B4805]  
SM8954BW@PLCC44 [SA244]  
SM8954L  
SM8954L@TQFP44 [SA675-B4805]  
SM8958@PLCC44 [SA244]  
SM8958A  
SM8958A@TQFP44 [SA675-B4805]  
SM8958AL@PLCC44 [SA244]  
SM8958B  
SM8958B@TQFP44 [SA675-B4805]  
SM8958BL@PLCC44 [SA244]  
SM8958BW  
SM8958BW@QFP44 [SA675-B4805]  
SM8958L@PLCC44 [SA244]  
SM89S16R1C  
SM89S16R1C@TQFP44 [SA675-B4805]  
SM89T04R1C@PLCC44 [SA244]  
SM89T04R1L  
SM89T04R1L@TQFP44 [SA675-B4805]  
SM89T08R1C@PLCC44 [SA244]  
SM89T08R1L  
SM89T08R1L@TQFP44 [SA675-B4805]  
SM89T16R1C@PLCC44 [SA244]  
SM89T16R1L  
SM89T16R1L@TQFP44 [SA675-B4805]

## SYNERTEK

### E (E) PROM/FRAM/NVRAM

SY2716

## SYNTEK

### MICROCONTROLLER

STK6031@LQFP48 [SA248-B4804]  
STK6031@QFP44 [SA675-B4805]  
STK6032@LQFP48 [SA248-B4804]  
STK6032@QFP44 [SA675-B4805]  
STK6033@LQFP48 [SA248-B4804]  
STK6033@QFP44 [SA675-B4805]

STK6031@PLCC44 [SA244]  
STK6032  
STK6032@PLCC44 [SA244]  
STK6033  
STK6033@PLCC44 [SA244]

## TECHCODE

### MICROCONTROLLER

T89C516  
T89C516@TQFP44 [SA675-B4805]  
T89C52@PLCC44 [SA244]

T89C516@PLCC44 [SA244]  
T89C52  
T89C52@TQFP44 [SA675-B4805]

T89C58  
T89C58@TQFP44 [SA675-B4805]

T89C58@PLCC44 [SA244]

## TEKMOS

### MICROCONTROLLER

TK87C751

TK87C751@PLCC28 [SA008A]

## TEMIC

### MICROCONTROLLER

T89C51RD2  
T89C51RD2@TQFP44 [SA245A-B4805]  
T89F64@PLCC44 [SA244]  
TS87C51RB2  
TS87C51RB2@TQFP44 [SA675-B4805]  
TS87C51RC2@PLCC44 [SA244]  
TS87C51RD2  
TS87C51RD2@TQFP44 [SA675-B4805]  
TS87C51U2@PLCC44 [SA244]  
TS87C52X2  
TS87C52X2@TQFP44 [SA675-B4805]  
TS87C54X2@PLCC44 [SA244]  
TS87C58X2  
TS87C58X2@TQFP44 [SA675-B4805]  
TSC71RBX2@PLCC44 [SA244]  
TSC71RCX2  
TSC71RCX2@TQFP44 [SA675-B4805]  
TSC71RDX2@PLCC44 [SA244]  
TSC71RDX2@TQFP44 [SA675-B4805]  
TSC87251A1@PLCC44 [SA244]  
TSC87251G1@PLCC44 [\$\$\$\$\$]  
TSC87251G1A@PLCC44 [SA244]  
TSC87251G2D@PLCC44 [SA244]  
TSC87251G2D@TQFP44 [SA245A-B4805]  
TSC87C51  
TSC87C51@TQFP44 [SA675-B4805]  
TSC87C52@PLCC44 [SA244]  
TSC87C54  
TSC87C54@TQFP44 [SA675-B4805]  
TSC87C58@PLCC44 [SA244]

T89C51RD2@PLCC44 [SA244]  
T89F64  
T89F64@TQFP44 [SA245A-B4805]  
TS87C51RB2@PLCC44 [SA244]  
TS87C51RC2  
TS87C51RC2@TQFP44 [SA675-B4805]  
TS87C51RD2@PLCC44 [SA244]  
TS87C51U2  
TS87C51U2@TQFP44 [SA675-B4805]  
TS87C52X2@PLCC44 [SA244]  
TS87C54X2  
TS87C54X2@TQFP44 [SA675-B4805]  
TS87C58X2@PLCC44 [SA244]  
TSC71RBX2  
TSC71RBX2@TQFP44 [SA675-B4805]  
TSC71RCX2@PLCC44 [SA244]  
TSC71RDX2  
TSC71RDX2@TQFP44 [SA675-B4805]  
TSC87251G1  
TSC87251G1A  
TSC87251G2D  
TSC87C51@PLCC44 [SA244]  
TSC87C52  
TSC87C52@TQFP44 [SA675-B4805]  
TSC87C54@PLCC44 [SA244]  
TSC87C58  
TSC87C58@TQFP44 [SA675-B4805]

## Terra Semiconductor

### E (E) PROM/FRAM/NVRAM

TS25L010AP [SA605B]  
TS25L020AP [SA605B]  
TS25L16AP [SA605B]  
TS25L16BP@SOP8 [SA605B]

TS25L010AP@SOP8 [SA605B]  
TS25L020AP@SOP8 [SA605B]  
TS25L16AP@SOP8 [SA605B]  
TS25L80AP [SA605B]

TS25L80AP@SOP8 [SA605B]

TI

E (E) PROM/FRAM/NVRAM

BQ3285	BQ3287
BQ3287A	BQ4010
BQ4010Y	BQ4011
BQ4011Y	BQ4013
BQ4013Y	BQ4014
BQ4014Y	BQ4015
BQ4015Y	SMJ2516
SMJ2532	SMJ2532A
SMJ2716	SMJ27C256
SMJ27C256@PLCC32 [SA015A1T]	SMJ27C512
SMJ27C512@PLCC32 [SA015A1T]	TMS2516
TMS2516JLW	TMS2532
TMS2532A	TMS25L32
TMS27128	TMS27128A
TMS2716	TMS2732
TMS2732A	TMS2764
TMS27C010	TMS27C010@PLCC32 [SA015A1T]
TMS27C010@TSOP32 [SA410T-B4001]	TMS27C010A
TMS27C010A@PLCC32 [SA015A1T]	TMS27C010A@TSOP32 [SA410T-B4001]
TMS27C020	TMS27C020@PLCC32 [SA015A1T]
TMS27C020@TSOP32 [SA410T-B4001]	TMS27C040
TMS27C040@PLCC32 [SA015A1T]	TMS27C040@TSOP32 [SA410T-B4001]
TMS27C128	TMS27C128@PLCC32
TMS27C2001	TMS27C2001@PLCC32 [SA015A1T]
TMS27C2001@TSOP32 [SA410T-B4001]	TMS27C210
TMS27C210@PLCC44 [SA244]	TMS27C210A
TMS27C210A@PLCC44 [SA244]	TMS27C240
TMS27C240@PLCC44 [SA244]	TMS27C256
TMS27C256@PLCC32 [SA015A1T]	TMS27C291
TMS27C291@PLCC28 [SA008A]	TMS27C292
TMS27C292@PLCC28 [SA008A]	TMS27C32
TMS27C512	TMS27C512@PLCC32 [SA015A1T]
TMS27C64	TMS27LV010A
TMS27LV010A@PLCC32 [SA015A1T]	
TMS27LV010A@TSOP32 [SA410T-B4001]	
TMS27P32A	TMS27P64
TMS27PC010	TMS27PC010@PLCC32 [SA015A1T]
TMS27PC010@TSOP32 [SA410T-B4001]	TMS27PC010A
TMS27PC010A@PLCC32 [SA015A1T]	
TMS27PC010A@TSOP32 [SA410T-B4001]	
TMS27PC020	TMS27PC020@PLCC32 [SA015A1T]
TMS27PC020@TSOP32 [SA410T-B4001]	TMS27PC040
TMS27PC040@PLCC32 [SA015A1T]	TMS27PC040@TSOP32 [SA410T-B4001]
TMS27PC128	TMS27PC128@PLCC32
TMS27PC210	TMS27PC210@PLCC44 [SA244]
TMS27PC210A	TMS27PC210A@PLCC44 [SA244]

TMS27PC240  
TMS27PC256  
TMS27PC291  
TMS27PC32  
TMS27PC512  
TMS27PC64  
TMS28F010 (REVERSE)@TSOP32 [SA410T-B4001]  
TMS28F010@PLCC32 [SA015A1T]  
TMS28F020  
TMS28F020 (REVERSE)@TSOP32 [SA410T-B4001]  
TMS28F020@PLCC32 [SA015A1T]  
TMS28F200AF-B@PSOP44 [SA638]  
TMS28F200AF-B@TSOP48 [SB247-B4806]  
TMS28F200AF-T@PSOP44 [SA638]  
TMS28F200AF-T@TSOP48 [SB247-B4806]  
TMS28F200BZ-B@PSOP44 [SA638]  
TMS28F210  
TMS28F210@TSOP40 [SA623-B4002]  
TMS28F400AE-B@TSOP48 [SB247-B4806]  
TMS28F400AE-T@PSOP44 [SA638]  
TMS28F400AE-T@TSOP48 [SB247-B4806]  
TMS28F400AF-B@PSOP44 [SA638]  
TMS28F400AF-B@TSOP48 [SB247-B4806]  
TMS28F400AF-T@PSOP44 [SA638]  
TMS28F400AF-T@TSOP48 [SB247-B4806]  
TMS28F400AM-B@PSOP44 [SA638]  
TMS28F400AM-B@TSOP48 [SB247-B4806]  
TMS28F400AM-T@PSOP44 [SA638]  
TMS28F400AM-T@TSOP48 [SB247-B4806]  
TMS28F400AS-B@PSOP44 [SA638]  
TMS28F400AS-B@TSOP48 [SB247-B4806]  
TMS28F400AS-T@PSOP44 [SA638]  
TMS28F400AS-T@TSOP48 [SB247-B4806]  
TMS28F400AZ-B@PSOP44 [SA638]  
TMS28F400AZ-B@TSOP48 [SB247-B4806]  
TMS28F400AZ-T@PSOP44 [SA638]  
TMS28F400AZ-T@TSOP48 [SB247-B4806]  
TMS28F400BZ-B@PSOP44 [SA638]  
TMS28F512  
TMS28F512 (REVERSE)@TSOP32 [SA410T-B4001]  
TMS28F512@PLCC32 [SA015A1T]  
TMS28F800AE-B@PSOP44 [SA638]  
TMS28F800AE-B@TSOP48 [SB247-B4806]  
TMS28F800AE-T@PSOP44 [SA638]  
TMS28F800AE-T@TSOP48 [SB247-B4806]  
TMS28F800AL-B@PSOP44 [SA638]  
TMS28F800AL-B@TSOP48 [SB247-B4806]  
TMS28F800AL-T@PSOP44 [SA638]  
TMS28F800AL-T@TSOP48 [SB247-B4806]  
TMS28F800AS-B@PSOP44 [SA638]  
TMS28F800AS-B@TSOP48 [SB247-B4806]  
TMS28F800AS-T@PSOP44 [SA638]  
TMS28F800AS-T@TSOP48 [SB247-B4806]

TMS28F800AV-B@PSOP44	[SA638]		
TMS28F800AV-B@TSOP48	[SB247-B4806]		
TMS28F800AV-T@PSOP44	[SA638]		
TMS28F800AV-T@TSOP48	[SB247-B4806]		
TMS28F800AZ-B@PSOP44	[SA638]		
TMS28F800AZ-B@TSOP48	[SB247-B4806]		
TMS28F800AZ-T@PSOP44	[SA638]		
TMS28F800AZ-T@TSOP48	[SB247-B4806]		
TMS28F800SE-B@PSOP44	[SA638]		
TMS28F800SE-B@TSOP48	[SB247-B4806]		
TMS28F800SE-T@PSOP44	[SA638]		
TMS28F800SE-T@TSOP48	[SB247-B4806]		
TMS28F800SZ-B@PSOP44	[SA638]		
TMS28F800SZ-B@TSOP48	[SB247-B4806]		
TMS28F800SZ-T@PSOP44	[SA638]		
TMS28F800SZ-T@TSOP48	[SB247-B4806]		
TMS29F040		TMS29F040@PLCC32	[SA015A1T]
TMS29F040@TSOP32	[SA410T-B4001]	TMS87C257	
TMS87C257@PLCC32	[SA015A1T]		

## PLD

EP910		EP910@PLCC44	[SA244]
-------	--	--------------	---------

## MICROCONTROLLER

BUF01900@DFN10	[SA695A]	BUF01900@TSSOP8	[SA643]
BUF01901@DFN10	[SA695A]	BUF01901@TSSOP8	[SA643]
BUF08821@SSOP20	[SA643]	BUF08832@SSOP20(*)	[SA643]
BUF20820@SSOP38	[SA693]	BUF22821@SSOP38	[SA693]
MSP430F110@SOIC20	[SA404]	MSP430F110@TSSOP20	[SA026]
MSP430F1101@SOIC20	[SA404]	MSP430F1101@TSSOP20	[SA026]
MSP430F1101A@QFN24	[SA710]	MSP430F1101A@QFN24 (ISP)	
MSP430F1101A@SOIC20	[SA404]	MSP430F1101A@SOIC20 (ISP)	
MSP430F1101A@TSSOP20	[SA026]	MSP430F1101A@TSSOP20 (ISP)	
MSP430F1111A@QFN24	[SA710]	MSP430F1111A@QFN24 (ISP)	
MSP430F1111A@SOIC20	[SA404]	MSP430F1111A@SOIC20 (ISP)	
MSP430F1111A@TSSOP20	[SA026]	MSP430F1111A@TSSOP20 (ISP)	
MSP430F112@SOIC20	[SA404]	MSP430F112@TSSOP20	[SA026]
MSP430F1121@SOIC20	[SA404]	MSP430F1121@TSSOP20	[SA026]
MSP430F1121A@QFN24	[SA710]	MSP430F1121A@QFN24 (ISP)	
MSP430F1121A@SOIC20	[SA404]	MSP430F1121A@SOIC20 (ISP)	
MSP430F1121A@TSSOP20	[SA026]	MSP430F1121A@TSSOP20 (ISP)	
MSP430F1122@QFN32	[SA686]	MSP430F1122@SOIC20	[SA404]
MSP430F1122@TSSOP20	[SA026]	MSP430F1132@QFN32	[SA686]
MSP430F1132@SOIC20	[SA404]	MSP430F1132@TSSOP20	[SA026]
MSP430F1222@QFN32	[SA686]	MSP430F1222@SOIC28	[SA404]
MSP430F1222@TSSOP28	[SA643]	MSP430F1232@QFN32	[SA686]
MSP430F1232@SOIC28	[SA404]	MSP430F1232@TSSOP28	[SA643]
MSP430F2001IN (ISP)		MSP430F2001IN (SPW ISP)	
MSP430F2001IPW@TSSOP14 (ISP)		MSP430F2001IPW@TSSOP14 (SPW ISP)	
MSP430F2001IRSA@QFN16 (ISP)		MSP430F2001IRSA@QFN16 (SPW ISP)	

MSP430F2001TN (ISP)  
MSP430F2001TPW@TSSOP14 (ISP)  
MSP430F2001TRSA@QFN16 (ISP)  
MSP430F2002IN (ISP)  
MSP430F2002IPW@TSSOP14 (ISP)  
MSP430F2002IRSA@QFN16 (ISP)  
MSP430F2002TN (ISP)  
MSP430F2002TPW@TSSOP14 (ISP)  
MSP430F2002TRSA@QFN16 (ISP)  
MSP430F2003IN (ISP)  
MSP430F2003IPW@TSSOP14 (ISP)  
MSP430F2003IRSA@QFN16 (ISP)  
MSP430F2003TN (ISP)  
MSP430F2003TPW@TSSOP14 (ISP)  
MSP430F2003TRSA@QFN16 (ISP)  
MSP430F2011IN (ISP)  
MSP430F2011IPW@TSSOP14 (ISP)  
MSP430F2011IRSA@QFN16 (ISP)  
MSP430F2011TN (ISP)  
MSP430F2011TPW@TSSOP14 (ISP)  
MSP430F2011TRSA@QFN16 (ISP)  
MSP430F2012IN (ISP)  
MSP430F2012IPW@TSSOP14 (ISP)  
MSP430F2012IRSA@QFN16 (ISP)  
MSP430F2012TN (ISP)  
MSP430F2012TPW@TSSOP14 (ISP)  
MSP430F2012TRSA@QFN16 (ISP)  
MSP430F2013IN (ISP)  
MSP430F2013IPW@TSSOP14 (ISP)  
MSP430F2013IRSA@QFN16 (ISP)  
MSP430F2013TN (ISP)  
MSP430F2013TPW@TSSOP14 (ISP)  
MSP430F2013TRSA@QFN16 (ISP)  
MSP430F2101@QFN24 [SA710]  
MSP430F2101@SOIC20 [SA404]  
MSP430F2101@TSSOP20 [SA643]  
MSP430F2101@TVSOP20 [\$\$\$\$\$]  
MSP430F2111@QFN24 [SA710]  
MSP430F2111@SOIC20 [SA404]  
MSP430F2111@TSSOP20 [SA643]  
MSP430F2111@TVSOP20 [\$\$\$\$\$]  
MSP430F2121@QFN24 [SA710]  
MSP430F2121@SOIC20 [SA404]  
MSP430F2121@TSSOP20 [SA643]  
MSP430F2121@TVSOP20 [\$\$\$\$\$]  
MSP430F2131@QFN24 [SA710]  
MSP430F2131@SOIC20 [SA404]  
MSP430F2131@TSSOP20 [SA643]  
MSP430F2131@TVSOP20 [\$\$\$\$\$]  
MSP430F2232IDA@SSOP38 (ISP)  
MSP430F2232IYFF (ISP) [\$\$\$\$\$]  
MSP430F2232TRHA@QFN40 (ISP)  
MSP430F2234IDA@SSOP38 (ISP)

MSP430F2001TN (SPW ISP)  
MSP430F2001TPW@TSSOP14 (SPW ISP)  
MSP430F2001TRSA@QFN16 (SPW ISP)  
MSP430F2002IN (SPW ISP)  
MSP430F2002IPW@TSSOP14 (SPW ISP)  
MSP430F2002IRSA@QFN16 (SPW ISP)  
MSP430F2002TN (SPW ISP)  
MSP430F2002TPW@TSSOP14 (SPW ISP)  
MSP430F2002TRSA@QFN16 (SPW ISP)  
MSP430F2003IN (SPW ISP)  
MSP430F2003IPW@TSSOP14 (SPW ISP)  
MSP430F2003IRSA@QFN16 (SPW ISP)  
MSP430F2003TN (SPW ISP)  
MSP430F2003TPW@TSSOP14 (SPW ISP)  
MSP430F2003TRSA@QFN16 (SPW ISP)  
MSP430F2011IN (SPW ISP)  
MSP430F2011IPW@TSSOP14 (SPW ISP)  
MSP430F2011IRSA@QFN16 (SPW ISP)  
MSP430F2011TN (SPW ISP)  
MSP430F2011TPW@TSSOP14 (SPW ISP)  
MSP430F2011TRSA@QFN16 (SPW ISP)  
MSP430F2012IN (SPW ISP)  
MSP430F2012IPW@TSSOP14 (SPW ISP)  
MSP430F2012IRSA@QFN16 (SPW ISP)  
MSP430F2012TN (SPW ISP)  
MSP430F2012TPW@TSSOP14 (SPW ISP)  
MSP430F2012TRSA@QFN16 (SPW ISP)  
MSP430F2013IN (SPW ISP)  
MSP430F2013IPW@TSSOP14 (SPW ISP)  
MSP430F2013IRSA@QFN16 (SPW ISP)  
MSP430F2013TN (SPW ISP)  
MSP430F2013TPW@TSSOP14 (SPW ISP)  
MSP430F2013TRSA@QFN16 (SPW ISP)  
MSP430F2101@QFN24 (ISP)  
MSP430F2101@SOIC20 (ISP)  
MSP430F2101@TSSOP20 (ISP)  
MSP430F2101@TVSOP20 (ISP)  
MSP430F2111@QFN24 (ISP)  
MSP430F2111@SOIC20 (ISP)  
MSP430F2111@TSSOP20 (ISP)  
MSP430F2111@TVSOP20 (ISP)  
MSP430F2121@QFN24 (ISP)  
MSP430F2121@SOIC20 (ISP)  
MSP430F2121@TSSOP20 (ISP)  
MSP430F2121@TVSOP20 (ISP)  
MSP430F2131@QFN24 (ISP)  
MSP430F2131@SOIC20 (ISP)  
MSP430F2131@TSSOP20 (ISP)  
MSP430F2131@TVSOP20 (ISP)  
MSP430F2232IRHA@QFN40 (ISP)  
MSP430F2232TDA@SSOP38 (ISP)  
MSP430F2232TYFF (ISP)  
MSP430F2234IRHA@QFN40 (ISP)

MSP430F2234IYFF (ISP)  
MSP430F2234TRHA@QFN40 (ISP)  
MSP430F2252IDA@SSOP38 (ISP)  
MSP430F2252IYFF (ISP)  
MSP430F2252TRHA@QFN40 (ISP)  
MSP430F2254IDA@SSOP38 (ISP)  
MSP430F2254IYFF (ISP)  
MSP430F2254TRHA@QFN40 (ISP)  
MSP430F2272IDA@SSOP38 (ISP)  
MSP430F2272IYFF (ISP)  
MSP430F2272TRHA@QFN40 (ISP)  
MSP430F2274IDA@SSOP38 (ISP)  
MSP430F2274IYFF (ISP)  
MSP430F2274TRHA@QFN40 (ISP)  
MSP430F2330IRHA@QFN40 (ISP)  
MSP430F2350IRHA@QFN40 (ISP)  
MSP430F2370IRHA@QFN40 (ISP)

MSP430F2234TDA@SSOP38 (ISP)  
MSP430F2234TYFF (ISP)  
MSP430F2252IRHA@QFN40 (ISP)  
MSP430F2252TDA@SSOP38 (ISP)  
MSP430F2252TYFF (ISP)  
MSP430F2254IRHA@QFN40 (ISP)  
MSP430F2254TDA@SSOP38 (ISP)  
MSP430F2254TYFF (ISP)  
MSP430F2272IRHA@QFN40 (ISP)  
MSP430F2272TDA@SSOP38 (ISP)  
MSP430F2272TYFF (ISP)  
MSP430F2274IRHA@QFN40 (ISP)  
MSP430F2274TDA@SSOP38 (ISP)  
MSP430F2274TYFF (ISP)  
MSP430F2330TRHA@QFN40 (ISP)  
MSP430F2350TRHA@QFN40 (ISP)  
MSP430F2370TRHA@QFN40 (ISP)

## TMC

### E (E) PROM/FRAM/NVRAM

24A01  
24A01@TSSOP8 [SA643]  
24A02@SOIC8 [SA602A]  
24A04  
24A04@TSSOP8 [SA643]  
24A08@SOIC8 [SA602A]  
24A16  
24A16@TSSOP8 [SA643]  
93LC46 (08bit)@SOIC8 [SA602A]  
93LC46 (16bit)  
93LC46 (16bit)@TSSOP8 [SA643]  
93LC56 (08bit)@SOIC8 [SA602A]  
93LC56 (16bit)  
93LC56 (16bit)@TSSOP8 [SA643]  
93LC57@SOIC8 [SA602A]  
93LC66 (08bit)  
93LC66 (08bit)@TSSOP8 [SA643]  
93LC66 (16bit)@SOIC8 [SA602A]  
93LC86 (08bit)  
93LC86 (08bit)@TSSOP8 [SA643]  
93LC86 (16bit)@SOIC8 [SA602A]

24A01@SOIC8 [SA602A]  
24A02  
24A02@TSSOP8 [SA643]  
24A04@SOIC8 [SA602A]  
24A08  
24A08@TSSOP8 [SA643]  
24A16@SOIC8 [SA602A]  
93LC46 (08bit)  
93LC46 (08bit)@TSSOP8 [SA643]  
93LC46 (16bit)@SOIC8 [SA602A]  
93LC56 (08bit)  
93LC56 (08bit)@TSSOP8 [SA643]  
93LC56 (16bit)@SOIC8 [SA602A]  
93LC57  
93LC57@TSSOP8 [SA643]  
93LC66 (08bit)@SOIC8 [SA602A]  
93LC66 (16bit)  
93LC66 (16bit)@TSSOP8 [SA643]  
93LC86 (08bit)@SOIC8 [SA602A]  
93LC86 (16bit)  
93LC86 (16bit)@TSSOP8 [SA643]

## TOSHIBA

### E (E) PROM/FRAM/NVRAM

TC541000AF@PLCC32  
TC541001AF@PLCC32  
TC54256AF  
TC54256AP

TC541000AP  
TC541001AP  
TC54256AF@SOIC28  
TC54256AP@SOIC28

TC544000P	TC54512AF
TC54512AP	TC571000
TC571000AD	TC571000D
TC571001AD	TC571001D
TC571024D	TC57256
TC57256A	TC57256AD
TC57256ADI	TC57256D
TC574000D	TC574096D
TC574200D	TC57512
TC57512AD	TC578200D
TC57H1000AD	TC57H1001AD
TC57H256D	TC58F400@PSOP44 [SA638]
TC58F400@TSOP48 [SB247-B4806]	TC58F401@PSOP44 [SA638]
TC58F401@TSOP48 [SB247-B4806]	
TC58FVB004FT@TSOP40 [SA409T-B4002]	
TC58FVB008FT@TSOP40 [SA409T-B4002]	
TC58FVB016FT@TSOP40 [SA409T-B4002]	
TC58FVB160AFT@TSOP48 [SB247-B4806]	
TC58FVB160FT@TSOP48 [SB247-B4806]	
TC58FVB321FT@TSOP48 [SB247-B4806]	
TC58FVB400F@PSOP44 [SA638]	
TC58FVB400FT@TSOP48 [SB247-B4806]	
TC58FVB641FT@TSOP48 [SB247-B4806]	
TC58FVB800F@PSOP44 [SA638]	
TC58FVB800FT@TSOP48 [SB247-B4806]	
TC58FVM5B2AFT@TSOP48 [SB247-B4806]	
TC58FVM5B2ATG@TSOP48 [SB247-B4806]	
TC58FVM5B3AFT@TSOP48 [SB247-B4806]	
TC58FVM5B3ATG@TSOP48 [SB247-B4806]	
TC58FVM5T2AFT@TSOP48 [SB247-B4806]	
TC58FVM5T2ATG@TSOP48 [SB247-B4806]	
TC58FVM5T3AFT@TSOP48 [SB247-B4806]	
TC58FVM5T3ATG@TSOP48 [SB247-B4806]	
TC58FVM6B2AFT@TSOP48 [SB247-B4806]	
TC58FVM6B5BTG@TSOP48 [SB247-B4806]	
TC58FVM6T2AFT@TSOP48 [SB247-B4806]	
TC58FVM6T5BTG@TSOP48 [SB247-B4806]	
TC58FVT004FT@TSOP40 [SA409T-B4002]	
TC58FVT008FT@TSOP40 [SA409T-B4002]	
TC58FVT016FT@TSOP40 [SA409T-B4002]	
TC58FVT160AFT@TSOP48 [SB247-B4806]	
TC58FVT160FT@TSOP48 [SB247-B4806]	
TC58FVT321FT@TSOP48 [SB247-B4806]	
TC58FVT400F@PSOP44 [SA638]	
TC58FVT400FT@TSOP48 [SB247-B4806]	
TC58FVT641FT@TSOP48 [SB247-B4806]	
TC58FVT800F@PSOP44 [SA638]	
TC58FVT800FT@TSOP48 [SB247-B4806]	
TC58FYB160FT@TSOP48 [SB247-B4806]	
TC58FYT160FT@TSOP48 [SB247-B4806]	
TC58NVG1S3ETA00@TSOP48 [SB247-B4806]	
TC58NVG2S3ETAI0@TSOP48 [SB247-B4806]	
TC89101 (08bit)	TC89101 (16bit)

TC89102 (08bit)  
TC89121  
TC89122  
TC97101  
TMM24128A  
TMM24256  
TMM24256AP  
TMM24512  
TMM24512P  
TMM27128  
TMM27128ADI  
TMM27256  
TMM27256AD  
TMM27256BD  
TMM27256D  
TMM2732  
TMM2732D  
TMM27512AD  
TMM27512D  
TMM2764  
TMM2764ADI  
TMM2764D

TC89102 (16bit)  
TC89121@SOIC8 [SA602A]  
TC89122@SOIC8 [SA602A]  
TMM24128  
TMM24128AP  
TMM24256A  
TMM24256B  
TMM24512A  
TMM2464AP  
TMM27128A  
TMM27128AP  
TMM27256A  
TMM27256ADI  
TMM27256BDI  
TMM27256DI  
TMM2732A  
TMM27512  
TMM27512ADI  
TMM27512DI  
TMM2764AD  
TMM2764AP  
TMM2764DI

## DRAM & SRAM

TC518128  
TC518129  
TC51832  
TC518512  
TC551001FL  
TC551001PL  
TC55257  
TC55257L  
TC55258  
TC55258L  
TC55328  
TC5563APL  
TC5564APL  
TC5565AFL  
TC5565APL  
TC5588  
TC55B88  
TMM2063

TC518128@SOIC32 [SA630]  
TC518129@SOIC32 [SA630]  
TC51832@SOIC28 [SA630]  
TC518512@SOIC32 [SA630]  
TC551001FL@SOIC32 [SA630]  
TC551001PL@SOIC32 [SA630]  
TC55257@SOIC28 [SA630]  
TC55257L@SOIC28 [SA630]  
TC55258@SOIC28 [SA630]  
TC55258L@SOIC28 [SA630]  
TC55328@SOIC28 [SA630]  
TC5563APL@SOIC28 [SA630]  
TC5564APL@SOIC28 [SA630]  
TC5565AFL@SOIC28 [SA630]  
TC5565APL@SOIC28 [SA630]  
TC5588@SOIC28 [SA630]  
TC55B88@SOIC28 [SA630]  
TMM2063@SOIC28 [SA630]

## MICROCONTROLLER

TMP47P443VM@SOIC28 [SA404]  
TMP47P443VN@SDIP28 [SA653]  
TMP86PH06N@SDIP42 [SA028]  
TMP86PH06U@QFP44 [SA245A-B4805]

TMP47P443VMG@SOIC28 [SA404]  
TMP47P443VNG@SDIP28 [SA653]  
TMP86PH06NG@SDIP42 [SA028]  
TMP86PH06UG@QFP44 [SA245A-B4805]

## TURBO IC

### E (E) PROM/FRAM/NVRAM

TU24C01	TU24C01@SOIC8 [SA602A]
TU24C02	TU24C02@SOIC8 [SA602A]
TU24C04	TU24C04@SOIC8 [SA602A]
TU24C08	TU24C08@SOIC8 [SA602A]
TU24C128	TU24C128@SOIC8 [SA602A]
TU24C16	TU24C16@SOIC8 [SA602A]
TU24C16@TSSOP8 [SA643]	TU24C256
TU24C256@SOIC8 [SA602A]	TU24C32
TU24C32@SOIC8 [SA602A]	TU24C64
TU24C64@SOIC8 [SA602A]	

## UMC

### E (E) PROM/FRAM/NVRAM

2732	2764
------	------

### DRAM & SRAM

UM61256	UM61256@SOIC28 [SA630]
UM61512	UM61512@SOIC32 [SA630]
UM6164	UM6164@SOIC28 [SA630]
UM621024	UM621024@SOIC32
UM62256	UM62256@SOIC28 [SA630]
UM62256A	UM62256A@SOIC28 [SA630]
UM6264	UM6264@SOIC28 [SA630]
UM6264A	UM6264A@SOIC28 [SA630]

## UNIGEN

### E (E) PROM/FRAM/NVRAM

UG24C01	UG24C01@SOP8 [SA602A]
UG24C01@TSSOP8 [SA643]	UG24C02
UG24C02@SOP8 [SA602A]	UG24C02@TSSOP8 [SA643]
UG24C04	UG24C04@SOP8 [SA602A]
UG24C04@TSSOP8 [SA643]	UG24C08
UG24C08@SOP8 [SA602A]	UG24C08@TSSOP8 [SA643]
UG24C16	UG24C16@SOP8 [SA602A]
UG24C16@TSSOP8 [SA643]	

## VERSACHIPS

### MICROCONTROLLER

V87C54	V87C54@PLCC44 [SA244]
--------	-----------------------

V87C54@TQFP44 [SA245A-B4805]  
V87C58@PLCC44 [SA244]

V87C58  
V87C58@TQFP44 [SA245A-B4805]

## VLSI

### E (E) PROM/FRAM/NVRAM

VT27C128  
VT27C512  
VT28H64

VT27C256  
VT27C64  
VT28HC64

### PLD

GAL16V8

## WELTRENDS

### MICROCONTROLLER

WT61P4K420@SDIP42 [SA028]  
WT61P4K422@SDIP42 [SA028]  
WT61P4N400  
WT61P6K420@SDIP42 [SA028]  
WT61P6L441@PLCC44 [SA244]  
WT61P7@LQFP44 [SA245A-B4805]  
WT61P7@TQFP48 [SA248-B4804]  
WT61P8S@TQFP44 [SA245A-B4805]  
WT62P1-N28 (dip28)  
WT62P1-N42 (dip42)  
WT62P2-K42@SDIP42 [SA028]  
WT62P2-N40 (dip40)  
WT62P2-S44@PSOP44 [SA638]  
WT6702F@SOP20 [SA404]  
WT6702F@SSOP20 [SA674]  
WT6703F@SOP24 [SA404]  
WT6703F@SSOP20 [SA674]  
WT6703FS161@SSOP16 [SA602]

WT61P4K421@SDIP42 [SA028]  
WT61P4L440@PLCC44 [SA244]  
WT61P4N401  
WT61P6L440@PLCC44 [SA244]  
WT61P6S@TQFP44 [SA245A-B4805]  
WT61P7@PLCC44 [SA244]  
WT61P8@TQFP44 [SA245A-B4805]  
WT62P1-K42@SDIP42 [SA028]  
WT62P1-N40 (dip40)  
WT62P1-S44@PSOP44 [SA638]  
WT62P2-L44@PLCC44 [SA244]  
WT62P2-N42 (dip42)  
WT6702F@SOP16 [SA602]  
WT6702F@SOP24 [SA404]  
WT6703F@SOP20 [SA404]  
WT6703F@SOP28 [SA404]  
WT6703F@SSOP24 [SA674]  
WT6703FS163@SSOP16 [SA602]

## WHITE ELECTRONIC DESIGNS

### E (E) PROM/FRAM/NVRAM

WE128K8  
WE512K8  
WF256K8@CLCC32 [SA015A1T]  
WF512K8  
WF512K8@CSOJ32 [SA646]  
WME128K8@CLCC32 [SA015A1T]  
WMF128K8  
WMF128K8@CSOJ32 [SA646]

WE256K8  
WF256K8  
WF256K8@CSOJ32 [SA646]  
WF512K8@CLCC32 [SA015A1T]  
WME128K8  
WME128K8@CSOJ32 [SA646]  
WMF128K8@CLCC32 [SA015A1T]  
WMF256K8

WMF256K8@CLCC32 [SA015A1T]  
WMF512K8  
WMF512K8@CSOJ32 [SA646]  
WMS128K8@CLCC32 [SA015A1T]  
WMS256K8  
WMS256K8@CSOJ32 [SA646]  
WMS512K8@CLCC32 [SA015A1T]

WMF256K8@CSOJ32 [SA646]  
WMF512K8@CLCC32 [SA015A1T]  
WMS128K8  
WMS128K8@CSOJ32 [SA646]  
WMS256K8@CLCC32 [SA015A1T]  
WMS512K8  
WMS512K8@CSOJ32 [SA646]

## WINBOND

### E (E) PROM/FRAM/NVRAM

W19B160BBT@TSOP48 [SB247-B4806]  
W19B320ABT@TSOP48 [SB247-B4806]  
W19B320BBT@TSOP48 [SB247-B4806]  
W19B320SBT@TSOP48 [SB247-B4806]  
W19B322MBT@TSOP48 [SB247-B4806]  
W19B323MBT@TSOP48 [SB247-B4806]  
W19B324MBT@TSOP48 [SB247-B4806]  
W19L320SBT@TSOP48 [SB247-B4806]

W19B160BTT@TSOP48 [SB247-B4806]  
W19B320ATT@TSOP48 [SB247-B4806]  
W19B320BTT@TSOP48 [SB247-B4806]  
W19B320STT@TSOP48 [SB247-B4806]  
W19B322MTT@TSOP48 [SB247-B4806]  
W19B323MTT@TSOP48 [SB247-B4806]  
W19B324MTT@TSOP48 [SB247-B4806]  
W19L320STT@TSOP48 [SB247-B4806]

W25B40 (Bottom Boot)@MLP8 [SA683]  
W25B40 (Bottom Boot)@SOIC8 [SA602A]  
W25B40 (Top Boot)@MLP8 [SA683]  
W25B40A (Bottom Boot)@MLP8 [SA683]  
W25B40A (Bottom Boot)@SOIC8 [SA602A]

W25B40 (Top Boot)@SOIC8 [SA602A]

W25B40A (Top Boot)@MLP8 [SA683]

W25B40A (Top Boot)@SOIC8 [SA602A]

W25D10

W25D10 (SN)@SOIC8 [SA602A]

W25D10 (SS)@SOIC8 [SA605B]

W25D10 (ZP)@WSON8 [SA683]

W25D16@SOIC16 [SA783]

W25D16@SOIC8 [SA605B]

W25D20

W25D20 (SN)@SOIC8 [SA602A]

W25D20 (SS)@SOIC8 [SA605B]

W25D20 (ZP)@WSON8 [SA683]

W25D40

W25D40 (SN)@SOIC8 [SA602A]

W25D40 (SS)@SOIC8 [SA605B]

W25D40 (ZP)@WSON8 [SA683]

W25D80

W25D80 (SN)@SOIC8 [SA602A]

W25D80 (SS)@SOIC8 [SA605B]

W25D80 (ZP)@WSON8 [SA683]

W25P10@MLP8 [SA683]

W25P10@SOIC8 [SA602A]

W25P16@MLP8 [SA683]

W25P16@MLP8 (ISP)

W25P16@SOIC16 [SA783]

W25P16@SOIC16 (ISP)

W25P16@SOIC8 [SA605B]

W25P16@SOIC8 (ISP)

W25P20@MLP8 [SA683]

W25P20@SOIC8 [SA602A]

W25P32@MLP8 [SA683]

W25P32@MLP8 (ISP)

W25P32@SOIC16 [SA783]

W25P32@SOIC16 (ISP)

W25P40@MLP8 [SA683]

W25P40@SOIC8 [SA602A]

W25P64@MLP8 [SA683]

W25P64@MLP8 (ISP)

W25P64@SOIC16 [SA783]

W25P64@SOIC16 (ISP)

W25P80@MLP8 [SA683]

W25P80@SOIC8 [SA602A]

W25Q05CV-SD8 [SA643]

W25Q05CV-SN8 [SA602A]

W25Q05CV-UX8 [SA724]

W25Q05CV-ZP8 [SA683]

W25Q10CV-SD8 [SA643]

W25Q10CV-SN8 [SA602A]

W25Q10CV-UX8 [SA724]

W25Q10CV-ZP8 [SA683]

W25Q128BV@SOIC16 [SA404]

W25Q128BV@WSON8 [SA684]

W25Q16@MLP8 [SA683]

W25Q16@MLP8 (ISP)

W25Q16@SOIC16 [SA783]  
W25Q16@SOIC8 [SA605B]  
W25Q16BV  
W25Q16BV (SN)@SOIC8 [SA602A]  
W25Q16BV (ZP)@WSON8 [SA683]  
W25Q16CL (SF)@SOIC16 [SA404]  
W25Q16CL (SS)@SOIC8 [SA605B]  
W25Q16CV (SF)@SOIC16 [SA404]  
W25Q16CV (SS)@SOIC8 [SA605B]  
W25Q16DV (SF)@SOIC16 [SA404]  
W25Q16DV (SS)@SOIC8 [SA605B]  
W25Q16DV@USON8 [SA744]  
W25Q16DW (SN)@SOIC8 [SA602A]  
W25Q16DW (ZP)@WSON8 [SA683]  
W25Q16V (SS)@SOIC8 [SA605B]  
W25Q20BW-SN8 [SA602A]  
W25Q20BW-UX8 [SA724]  
W25Q20CV-SN8 [SA602A]  
W25Q20CV-ZP8 [SA683]  
W25Q256FV@WSON8 [SA684]  
W25Q32@MLP8 (ISP)  
W25Q32@SOIC16 (ISP)  
W25Q32BV (SF)@SOIC16 [SA404]  
W25Q32BV (ZP)@WSON8 [SA683]  
W25Q32BW (SN)@SOIC8 [SA602A]  
W25Q32BW (ZP)@WSON8 [SA683]  
W25Q32DW (SN)@SOIC8 [SA602A]  
W25Q32DW (ZE)@WSON8 [SA684]  
W25Q32FV  
W25Q32FV (SS)@SOIC8 [SA605B]  
W25Q32FV (ZE)@WSON8 [SA684]  
W25Q32FW  
W25Q32FW (SS)@SOIC8 [SA605B]  
W25Q32FW (ZE)@WSON8 [SA684]  
W25Q32V (SF)@SOIC16 [SA783]  
W25Q32V (ZP)@WSON8 [SA683]  
W25Q40BL-SN8 [SA602A]  
W25Q40BL-SV8 [SA602A]  
W25Q40BL-ZP8 [SA683]  
W25Q40BV-SN8 [SA602A]  
W25Q40BV-SV8 [SA602A]  
W25Q40BV-ZP8 [SA683]  
W25Q40BW-SS8 [SA605B]  
W25Q40BW-UX8 [SA724]  
W25Q40CL  
W25Q40CL-SS8 [SA605B]  
W25Q40CL-UX8 [SA724]  
W25Q40CV  
W25Q40CV-SS8 [SA605B]  
W25Q40CV-UX8 [SA724]  
W25Q64BV  
W25Q64BV (SF)@SOIC16 (ISP)  
W25Q64BV (SS)@SOIC8 (ISP)

W25Q16@SOIC16 (ISP)  
W25Q16@SOIC8 (ISP)  
W25Q16BV (SF)@SOIC16 [SA783]  
W25Q16BV (SS)@SOIC8 [SA605B]  
W25Q16CL  
W25Q16CL (SN)@SOIC8 [SA602A]  
W25Q16CL (ZP)@WSON8 [SA683]  
W25Q16CV (SN)@SOIC8 [SA602A]  
W25Q16CV (ZP)@WSON8 [SA683]  
W25Q16DV (SN)@SOIC8 [SA602A]  
W25Q16DV (ZP)@WSON8 [SA683]  
W25Q16DW (SF)@SOIC16 [SA404]  
W25Q16DW (SS)@SOIC8 [SA605B]  
W25Q16V (SF)@SOIC16 [SA783]  
W25Q16V (ZP)@WSON8 [SA683]  
W25Q20BW-SV8 [SA602A]  
W25Q20BW-ZP8 [SA683]  
W25Q20CV-UX8 [SA724]  
W25Q256FV@SOIC16 [SA404]  
W25Q32@MLP8 [SA683]  
W25Q32@SOIC16 [SA783]  
W25Q32BV  
W25Q32BV (SS)@SOIC8 [SA605B]  
W25Q32BW (SF)@SOIC16 [SA404]  
W25Q32BW (SS)@SOIC8 [SA605B]  
W25Q32DW (SF)@SOIC16 [SA404]  
W25Q32DW (SS)@SOIC8 [SA605B]  
W25Q32DW (ZP)@WSON8 [SA683]  
W25Q32FV (SF)@SOIC16 [SA404]  
W25Q32FV (ST)@SOIC8 [SA605B]  
W25Q32FV (ZP)@WSON8 [SA683]  
W25Q32FW (SF)@SOIC16 [SA404]  
W25Q32FW (ST)@SOIC8 [SA605B]  
W25Q32FW (ZP)@WSON8 [SA683]  
W25Q32V (SS)@SOIC8 [SA605B]  
W25Q40BL  
W25Q40BL-SS8 [SA605B]  
W25Q40BL-UX8 [SA724]  
W25Q40BV  
W25Q40BV-SS8 [SA605B]  
W25Q40BV-UX8 [SA724]  
W25Q40BW-SN8 [SA602A]  
W25Q40BW-SV8 [SA602A]  
W25Q40BW-ZP8 [SA683]  
W25Q40CL-SN8 [SA602A]  
W25Q40CL-SV8 [SA602A]  
W25Q40CL-ZP8 [SA683]  
W25Q40CV-SN8 [SA602A]  
W25Q40CV-SV8 [SA602A]  
W25Q40CV-ZP8 [SA683]  
W25Q64BV (SF)@SOIC16 [SA783]  
W25Q64BV (SS)@SOIC8 [SA605B]  
W25Q64BV (ZE)@WSON8 [SA684]

W25Q64BV (ZE)@WSON8 (ISP)  
W25Q64CV (SS)@SOIC8 [SA605B]  
W25Q64DW (SF)@SOIC16 [SA404]  
W25Q64DW (ZE)@WSON8 [SA684]  
W25Q64FJ  
W25Q64FJ (SS)@SOIC8 [SA605B]  
W25Q64FJ (ZE)@WSON8 [SA684]  
W25Q64FV  
W25Q64FV (SS)@SOIC8 [SA605B]  
W25Q64FV (ZE)@WSON8 [SA684]  
W25Q64FW@SOIC8 [SA605B]  
W25Q64FW@WSON8 [SA683]  
W25Q80@SOIC8 [SA602A]  
W25Q80BL@SOIC16 [SA404]  
W25Q80BL@SOIC8 (200mil) [SA605B]  
W25Q80BL@VSOP8 (150mil) [SA602A]  
W25Q80BL@WSON8 [SA683]  
W25Q80BV@SOIC16 [SA404]  
W25Q80BV@SOIC8[5.4] [SA605B]  
W25Q80BW  
W25Q80BW@SOIC8[4.0] [SA602A]  
W25Q80BW@USON8 [SA724]  
W25Q80BW@VSOP8[5.4] [SA605B]  
W25Q80DW  
W25Q80DW@SOIC8[4.0] [SA602A]  
W25Q80DW@USON8 [SA602A]  
W25Q80DW@VSOP8[5.4] [SA605B]  
W25X05CL-SD8 [SA643]  
W25X05CL-UX8 [SA724]  
W25X10  
W25X10 (SS)@SOIC8 [SA605B]  
W25X10AL  
W25X10AL-SS8 [SA605B]  
W25X10AV  
W25X10AV (SS)@SOIC8 [SA605B]  
W25X10BL  
W25X10BL (SS)@SOIC8 [SA605B]  
W25X10BV  
W25X10BV (SS)@SOIC8 [SA605B]  
W25X10BV-SD8 [SA643]  
W25X10BV-UX8 [SA724]  
W25X10CL-SN8 [SA602A]  
W25X10CL-ZP8 [SA683]  
W25X10L (SN)@SOIC8 [SA602A]  
W25X10V  
W25X10V (SS)@SOIC8 [SA605B]  
W25X16@SOIC16 [SA783]  
W25X16@SOIC8 [SA605B]  
W25X16AL  
W25X16AL (SN)@SOIC8 [SA602A]  
W25X16AL (ZP)@WSON8 [SA683]  
W25X16AV (SF)@SOIC16 [SA783]  
W25X16AV (SS)@SOIC8 [SA605B]  
W25X16AV  
W25X16AV (SN)@SOIC8 [SA602A]  
W25X16AV (ZP)@WSON8 [SA683]  
W25Q64CV (SF)@SOIC16 [SA404]  
W25Q64CV (ZE)@WSON8 [SA684]  
W25Q64DW (SS)@SOIC8 [SA605B]  
W25Q64DW (ZP)@WSON8 [SA683]  
W25Q64FJ (SF)@SOIC16 [SA783]  
W25Q64FJ (ST)@SOIC8 [SA605B]  
W25Q64FJ (ZP)@WSON8 [SA683]  
W25Q64FV (SF)@SOIC16 [SA783]  
W25Q64FV (ST)@SOIC8 [SA605B]  
W25Q64FV (ZP)@WSON8 [SA683]  
W25Q64FW@VSOP8 [SA605B]  
W25Q80@MLP8 [SA683]  
W25Q80BL  
W25Q80BL@SOIC8 (150mil) [SA602A]  
W25Q80BL@USON8 [SA724]  
W25Q80BL@VSOP8 (200mil) [SA605B]  
W25Q80BV  
W25Q80BV@SOIC8[4.0] [SA602A]  
W25Q80BV@WSON8 [SA683]  
W25Q80BW@SOIC16 [SA404]  
W25Q80BW@SOIC8[5.4] [SA605B]  
W25Q80BW@VSOP8[4.0] [SA602A]  
W25Q80BW@WSON8 [SA683]  
W25Q80DW@SOIC16 [SA404]  
W25Q80DW@SOIC8[5.4] [SA605B]  
W25Q80DW@VSOP8[4.0] [SA602A]  
W25Q80DW@WSON8 [SA683]  
W25X05CL-SN8 [SA602A]  
W25X05CL-ZP8 [SA683]  
W25X10 (SN)@SOIC8 [SA602A]  
W25X10 (ZP)@WSON8 [SA683]  
W25X10AL-SN8 [SA602A]  
W25X10AL-ZP8 [SA683]  
W25X10AV (SN)@SOIC8 [SA602A]  
W25X10AV (ZP)@WSON8 [SA683]  
W25X10BL (SN)@SOIC8 [SA602A]  
W25X10BL (ZP)@WSON8 [SA683]  
W25X10BV (SN)@SOIC8 [SA602A]  
W25X10BV (ZP)@WSON8 [SA683]  
W25X10BV-SV8 [SA602A]  
W25X10CL-SD8 [SA643]  
W25X10CL-UX8 [SA724]  
W25X10L  
W25X10L (ZP)@WSON8 [SA683]  
W25X10V (SN)@SOIC8 [SA602A]  
W25X10V (ZP)@WSON8 [SA683]  
W25X16@SOIC16 (ISP)  
W25X16@SOIC8 (ISP)  
W25X16AL (SF)@SOIC16 [SA783]  
W25X16AL (SS)@SOIC8 [SA605B]

W25X16BV  
W25X16BV (SN)@SOIC8 [SA602A]  
W25X16BV (ZP)@WSON8 [SA683]  
W25X16V (SF)@SOIC16 [SA783]  
W25X16V (ZP)@WSON8 [SA683]  
W25X20 (SN)@SOIC8 [SA602A]  
W25X20 (ZP)@WSON8 [SA683]  
W25X20AL-SN8 [SA602A]  
W25X20AL-ZP8 [SA683]  
W25X20AV (SN)@SOIC8 [SA602A]  
W25X20AV (ZP)@WSON8 [SA683]  
W25X20BL (SN)@SOIC8 [SA602A]  
W25X20BL (ZP)@WSON8 [SA683]  
W25X20BL-UX8 [SA724]  
W25X20BV (SN)@SOIC8 [SA602A]  
W25X20BV (ZP)@WSON8 [SA683]  
W25X20CL-SN8 [SA602A]  
W25X20CL-UX8 [SA724]  
W25X20CV-SN8 [SA602A]  
W25X20CV-UX8 [SA724]  
W25X20L  
W25X20L (ZP)@WSON8 [SA683]  
W25X20V (SN)@SOIC8 [SA602A]  
W25X20V (ZP)@WSON8 [SA683]  
W25X32@SOIC16 [SA783]  
W25X32@SOIC8 [SA605B]  
W25X32AV (SF)@SOIC16 [SA783]  
W25X32AV (ZP)@WSON8 [SA683]  
W25X32V (SS)@SOIC8 [SA605B]  
W25X40  
W25X40 (SS)@SOIC8 [SA605B]  
W25X40AL  
W25X40AL (SS)@SOIC8 [SA605B]  
W25X40AV  
W25X40AV (SS)@SOIC8 [SA605B]  
W25X40BL  
W25X40BL (SS)@SOIC8 [SA605B]  
W25X40BL-SV8 [SA602A]  
W25X40BV  
W25X40BV (SS)@SOIC8 [SA605B]  
W25X40BV-SV8 [SA602A]  
W25X40CL  
W25X40CL-SS8 [SA605B]  
W25X40CL-UX8 [SA724]  
W25X40L  
W25X40L (SS)@SOIC8 [SA605B]  
W25X40V  
W25X40V (SS)@SOIC8 [SA605B]  
W25X41CL@SOIC8 [SA602A]  
W25X64@SOIC16 (ISP)  
W25X64@SOIC8 (ISP)  
W25X64BV (SS)@SOIC8 [SA605B]  
W25X64V (SF)@SOIC16 [SA783]

W25X16BV (SF)@SOIC16 [SA783]  
W25X16BV (SS)@SOIC8 [SA605B]  
W25X16V  
W25X16V (SS)@SOIC8 [SA605B]  
W25X20  
W25X20 (SS)@SOIC8 [SA605B]  
W25X20AL  
W25X20AL-SS8 [SA605B]  
W25X20AV  
W25X20AV (SS)@SOIC8 [SA605B]  
W25X20BL  
W25X20BL (SS)@SOIC8 [SA605B]  
W25X20BL-SV8 [SA602A]  
W25X20BV  
W25X20BV (SS)@SOIC8 [SA605B]  
W25X20BV-UX8 [SA724]  
W25X20CL-SV8 [SA602A]  
W25X20CL-ZP8 [SA683]  
W25X20CV-SV8 [SA602A]  
W25X20CV-ZP8 [SA683]  
W25X20L (SN)@SOIC8 [SA602A]  
W25X20V  
W25X20V (SS)@SOIC8 [SA605B]  
W25X21CL@SOIC8 [SA602A]  
W25X32@SOIC16 (ISP)  
W25X32@SOIC8 (ISP)  
W25X32AV (SS)@SOIC8 [SA605B]  
W25X32V (SF)@SOIC16 [SA783]  
W25X32V (ZP)@WSON8 [SA683]  
W25X40 (SN)@SOIC8 [SA602A]  
W25X40 (ZP)@WSON8 [SA683]  
W25X40AL (SN)@SOIC8 [SA602A]  
W25X40AL (ZP)@WSON8 [SA683]  
W25X40AV (SN)@SOIC8 [SA602A]  
W25X40AV (ZP)@WSON8 [SA683]  
W25X40BL (SN)@SOIC8 [SA602A]  
W25X40BL (ZP)@WSON8 [SA683]  
W25X40BL-UX8 [SA724]  
W25X40BV (SN)@SOIC8 [SA602A]  
W25X40BV (ZP)@WSON8 [SA683]  
W25X40BV-UX8 [SA724]  
W25X40CL-SN8 [SA602A]  
W25X40CL-SV8 [SA602A]  
W25X40CL-ZP8 [SA683]  
W25X40L (SN)@SOIC8 [SA602A]  
W25X40L (ZP)@WSON8 [SA683]  
W25X40V (SN)@SOIC8 [SA602A]  
W25X40V (ZP)@WSON8 [SA683]  
W25X64@SOIC16 [SA783]  
W25X64@SOIC8 [SA605B]  
W25X64BV (SF)@SOIC16 [SA783]  
W25X64BV (ZE)@WSON8 [SA684]  
W25X64V (SS)@SOIC8 [SA605B]

W25X64V (ZE)@WSON8 [SA684]  
W25X80 (SN)@SOIC8 [SA602A]  
W25X80 (ZP)@WSON8 [SA683]  
W25X80AL-SN8 [SA602A]  
W25X80AL-ZP8 [SA683]  
W25X80AV (SN)@SOIC8 [SA602A]  
W25X80AV (ZP)@WSON8 [SA683]  
W25X80BL-SN8 [SA602A]  
W25X80BL-ZP8 [SA683]  
W25X80L (SS)@SOIC8 [SA605B]  
W25X80V  
W25X80V (SS)@SOIC8 [SA605B]  
W27C01  
W27C01@VSOP32 [SA620-B4807]  
W27C010@PLCC32 [SA015A1T]  
W27C02  
W27C02@VSOP32 [SA620-B4807]  
W27C020@PLCC32 [SA015A1T]  
W27C020M@PLCC32 [SA015A1T]  
W27C257@PLCC32 [SA015A1T]  
W27C4096@PLCC44 [SA244]  
W27C512  
W27C512@TSOP28 [SA430T-B4003]  
W27C520@TSSOP20 [SA026]  
W27E01@PLCC32 [SA015A1T]  
W27E010  
W27E010@SOIC32 [SA603]  
W27E02@PLCC32 [SA015A1T]  
W27E020  
W27E040  
W27E040@SOIC32 [SA603]  
W27E257@PLCC32 [SA015A1T]  
W27E4096  
W27E4096@TSOP40 [SA409T-B4002]  
W27E512@PLCC32 [SA015A1T]  
W27E520@SOIC20 [SA404]  
W27L01  
W27L01@VSOP32 [SA620-B4807]  
W27L010@PLCC32 [SA015A1T]  
W27L02@PLCC32 [SA015A1T]  
W27L520@SOIC20 [SA404]  
W28F321BT@TSOP48 [SB247-B4806]  
W28F641BT@TSOP48 [SB247-B4806]  
W28J160BT@TSOP48 [SB247-B4806]  
W28J320BT@TSOP48 [SB247-B4806]  
W28J800BT@TSOP48 [SB247-B4806]  
W28V400BT@TSOP48 [SB247-B4806]  
W29C010  
W29C011A  
W29C020  
W29C020@SOIC32  
W29C020C  
W29C020C@TSOP32 [SA410T-B4001]  
W25X80  
W25X80 (SS)@SOIC8 [SA605B]  
W25X80AL  
W25X80AL-SS8 [SA605B]  
W25X80AV  
W25X80AV (SS)@SOIC8 [SA605B]  
W25X80BL  
W25X80BL-SS8 [SA605B]  
W25X80L  
W25X80L (ZP)@WSON8 [SA683]  
W25X80V (SN)@SOIC8 [SA602A]  
W25X80V (ZP)@WSON8 [SA683]  
W27C01@PLCC32 [SA015A1T]  
W27C010  
W27C010@SOIC32 [SA603]  
W27C02@PLCC32 [SA015A1T]  
W27C020  
W27C020M  
W27C257  
W27C4096  
W27C4096@TSOP40 [SA409T-B4002]  
W27C512@PLCC32 [SA015A1T]  
W27C520@SOIC20 [SA404]  
W27E01  
W27E01@VSOP32 [SA620-B4807]  
W27E010@PLCC32 [SA015A1T]  
W27E02  
W27E02@VSOP32 [SA620-B4807]  
W27E020@PLCC32 [SA015A1T]  
W27E040@PLCC32 [SA015A1T]  
W27E257  
W27E400  
W27E4096@PLCC44 [SA244]  
W27E512  
W27E512@TSOP28 [SA430T-B4003]  
W27E520@TSSOP20 [SA026]  
W27L01@PLCC32 [SA015A1T]  
W27L010  
W27L02  
W27L02@VSOP32 [SA620-B4807]  
W27L520@TSSOP20 [SA026]  
W28F321TT@TSOP48 [SB247-B4806]  
W28F641TT@TSOP48 [SB247-B4806]  
W28J160TT@TSOP48 [SB247-B4806]  
W28J320TT@TSOP48 [SB247-B4806]  
W28J800TT@TSOP48 [SB247-B4806]  
W28V400TT@TSOP48 [SB247-B4806]  
W29C010@PLCC32 [SA015A1T]  
W29C011A@PLCC32 [SA015A1T]  
W29C020@PLCC32 [SA015A1T]  
W29C020@TSOP32 [SA410T-B4001]  
W29C020C@PLCC32 [SA015A1T]  
W29C020C@VSOP32 [SA620-B4807]

W29C040  
W29C040@TSOP32 [SA410T-B4001]  
W29C101  
W29C101@TSOP40 [SA409T-B4002]  
W29C102@PLCC44 [SA244]  
W29C102@VSOP40 [SA623-B4002]  
W29EE010@PLCC32 [SA015A1T]  
W29EE011  
W29EE011@TSOP32 [SA410T-B4001]  
W29EE012@PLCC32 [SA015A1T]  
W29EE512  
W29EE512@TSOP32 [SA410T-B4001]  
W29F040@PLCC32 [SA015A1T]  
W29F102P@PLCC44 [SA244]  
W29GL032CB@TSOP48 [SB247-B4806]  
W29GL064CB@TSOP48 [SB247-B4806]  
W29L102P@PLCC44 [SA244]  
W29N01GVSCAA@TSOP48 [SB247-B4806]  
W29N01GVSIAA@TSOP48 [SB247-B4806]  
W29N02GVSIAA@TSOP48 [SB247-B4806]  
W39F010  
W39F010@TSOP32[12.4mm] [SA620-B4807]  
W39F010@TSOP32[18.4mm] [SA410T-B4001]  
W39L010@PLCC32 [SA015A1T]  
W39L020@PLCC32 [SA015A1T]  
W39L020@TSOP32[12.4mm] [SA620-B4807]  
W39L020@TSOP32[18.4mm] [SA410T-B4001]  
W39L040@PLCC32 [SA015A1T]  
W39L040@TSOP32[12.4mm] [SA620-B4807]  
W39L040@TSOP32[18.4mm] [SA410T-B4001]  
W39L040A  
W39L040A@TSOP32 [SA410T-B4001]  
W39L512@PLCC32 [SA015A1T]  
W39V040AP@PLCC32 [SA015A1T]  
W39V040B(P)@PLCC32 [SA015A1T]  
W39V040CP@PLCC32 [SA015A1T]  
W39V040CQ@VSOP32 [SA620-B4807]  
W39V040FAP@PLCC32 [SA015A1T]  
W39V040FAT@TSOP40 [SA409T-B4002]  
W39V040FB(Q)@VSOP32 [SA620-B4807]  
W39V040FCP@PLCC32 [SA015A1T]  
W39V040FCQ@VSOP32 [SA620-B4807]  
W39V080A(P)@PLCC32 [SA015A1T]  
W39V080A(T)@TSOP40 [SA409T-B4002]  
W39V080FA(P)@PLCC32 [SA015A1T]  
W39V080FA(Q)@VSOP32 [SA620-B4807]  
W39V080FA(T)@TSOP40 [SA409T-B4002]  
W45B012@PLCC32 [SA015A1T]  
W45B512@PLCC32 [SA015A1T]  
W49F002  
W49F002@TSOP32 [SA410T-B4001]  
W49F002B@PLCC32 [SA015A1T]  
W49F002N  
W29C040@PLCC32 [SA015A1T]  
W29C040@VSOP32 [SA620-B4807]  
W29C101@PLCC44 [SA244]  
W29C102  
W29C102@TSOP40 [SA409T-B4002]  
W29EE010  
W29EE010@TSOP32 [SA410T-B4001]  
W29EE011@PLCC32 [SA015A1T]  
W29EE012  
W29EE012@SOIC32 [SA438T]  
W29EE512@PLCC32 [SA015A1T]  
W29F040  
W29F040@TSOP32 [SA410T-B4001]  
W29F102Q@TSOP40 [SA623-B4002]  
W29GL032CT@TSOP48 [SB247-B4806]  
W29GL064CT@TSOP48 [SB247-B4806]  
W29L102Q@TSOP40 [SA623-B4002]  
W39F010@PLCC32 [SA015A1T]  
W39L010@TSOP32 [SA620-B4807]  
W39L040A@PLCC32 [SA015A1T]  
W39L040A@VSOP32 [SA620-B4807]  
W39L512@TSOP32 [SA620-B4807]  
W39V040AQ@VSOP32 [SA620-B4807]  
W39V040B(Q)@VSOP32 [SA620-B4807]  
W39V040CPZ@PLCC32 [SA015A1T]  
W39V040CQZ@VSOP32 [SA620-B4807]  
W39V040FAQ@VSOP32 [SA620-B4807]  
W39V040FB(P)@PLCC32 [SA015A1T]  
W39V040FCPZ@PLCC32 [SA015A1T]  
W39V040FCQZ@VSOP32 [SA620-B4807]  
W39V080A(Q)@VSOP32 [SA620-B4807]  
W45B012@SON8 [SA683]  
W45B512@SON8 [SA683]  
W49F002@PLCC32 [SA015A1T]  
W49F002B  
W49F002B@TSOP32 [SA410T-B4001]  
W49F002N@PLCC32 [SA015A1T]

W49F002N@TSOP32 [SA410T-B4001]  
W49F002U@PLCC32 [SA015A1T]  
W49F020  
W49F020@TSOP32 [SA410T-B4001]  
W49F102Q@TSOP40 [SA623-B4002]  
W49F201T@TSOP48 [SB247-B4806]  
W49L102Q@TSOP40 [SA623-B4002]  
W49L201T@TSOP48 [SB247-B4806]  
W49L401T@TSOP48 [SB247-B4806]  
W49V002A@VSOP32 [SA620-B4807]  
W49V002FA@VSOP32 [SA620-B4807]  
W49V002FP@VSOP32 [SA620-B4807]  
W49V002P@VSOP32 [SA620-B4807]  
W55F10A

W49F002U  
W49F002U@TSOP32 [SA410T-B4001]  
W49F020@PLCC32 [SA015A1T]  
W49F102P@PLCC44 [SA244]  
W49F201S@PSOP44 [SA638]  
W49L102P@PLCC44 [SA244]  
W49L201S@PSOP44 [SA638]  
W49L401S@PSOP44 [SA638]  
W49V002A@PLCC32 [SA015A1T]  
W49V002FA@PLCC32 [SA015A1T]  
W49V002FP@PLCC32 [SA015A1T]  
W49V002P@PLCC32 [SA015A1T]  
W55F05  
W55F20

## MICROCONTROLLER

N79E342AKG  
N79E342RAKG  
N79E352AEG  
N79E352ALG@TQFP48 [SA248-B4804]  
N79E8213AKG  
N79E8213RAKG  
W77E058A  
W77E058A@TQFP44 [SA675-B4805]  
W77E516@PLCC44 [SA244]  
W77E532  
W77E532@TQFP44 [SA675-B4805]  
W77E532A@PLCC44 [SA244]  
W77E58  
W77E58@TQFP44 [SA675-B4805]  
W77IE58@PLCC44 [SA244]  
W77L058A  
W77L058A@TQFP44 [SA675-B4805]  
W77L516A@PLCC44 [SA244]  
W77L532A  
W77L532A@TQFP44 [SA675-B4805]  
W77LE516@PLCC44 [SA244]  
W77LE532  
W77LE532@TQFP44 [SA675-B4805]  
W77LE58@PLCC44 [SA244]  
W77LE58A  
W77LE58A@TQFP44 [SA675-B4805]  
W78E051B@PLCC44 [SA244]  
W78E051C  
W78E051C@TQFP44 [SA675-B4805]  
W78E051DFG@PQFP44 [SA675-B4805]  
W78E051DPG@PLCC44 [SA244]  
W78E052B@PLCC44 [SA244]  
W78E052C  
W78E052C@TQFP44 [SA675-B4805]  
W78E052DFG@PQFP44 [SA675-B4805]

N79E342ASG@SOP16 [SA404]  
N79E342RASG@SOP16 [SA404]  
N79E352AFG@TQFP44 [SA675-B4805]  
N79E352APG@PLCC44 [SA244]  
N79E8213ASG@SOP20 [SA404]  
N79E8213RASG@SOP20 [SA404]  
W77E058A@PLCC44 [SA244]  
W77E516  
W77E516@TQFP44 [SA675-B4805]  
W77E532@PLCC44 [SA244]  
W77E532A  
W77E532A@TQFP44 [SA675-B4805]  
W77E58@PLCC44 [SA244]  
W77IE58  
W77IE58@TQFP44 [SA675-B4805]  
W77L058A@PLCC44 [SA244]  
W77L516A  
W77L516A@TQFP44 [SA675-B4805]  
W77L532A@PLCC44 [SA244]  
W77LE516  
W77LE516@TQFP44 [SA675-B4805]  
W77LE532@PLCC44 [SA244]  
W77LE58  
W77LE58@TQFP44 [SA675-B4805]  
W77LE58A@PLCC44 [SA244]  
W78E051B  
W78E051B@TQFP44 [SA675-B4805]  
W78E051C@PLCC44 [SA244]  
W78E051DDG  
W78E051DLG@LQFP48 [SA248-B4804]  
W78E052B  
W78E052B@TQFP44 [SA675-B4805]  
W78E052C@PLCC44 [SA244]  
W78E052DDG  
W78E052DLG@LQFP48 [SA248-B4804]

W78E052DPG@PLCC44 [SA244]  
W78E054B@PLCC44 [SA244]  
W78E054C  
W78E054C@TQFP44 [SA675-B4805]  
W78E054DFG@PQFP44 [SA675-B4805]  
W78E054DPG@PLCC44 [SA244]  
W78E058B@PLCC44 [SA244]  
W78E058DDG  
W78E058DLG@TQFP48 [SA248-B4804]  
W78E065  
W78E065@TQFP44 [SA675-B4805]  
W78E365@PLCC44 [SA244]  
W78E365A  
W78E365A@TQFP44 [SA675-B4805]  
W78E378  
W78E378P@PLCC44 [SA244]  
W78E51@PLCC44 [SA244]  
W78E516  
W78E516@TQFP44 [SA675-B4805]  
W78E516B@PLCC44 [SA244]  
W78E516DDG  
W78E516DLG@TQFP48 [SA248-B4804]  
W78E51B  
W78E51B@PQFP44 [SA675-B4805]  
W78E51C  
W78E51C@TQFP44 [SA675-B4805]  
W78E52@PLCC44 [SA244]  
W78E52B  
W78E52B@TQFP44 [SA675-B4805]  
W78E52C@PLCC44 [SA244]  
W78E54  
W78E54@PQFP44 [SA675-B4805]  
W78E54B  
W78E54B@TQFP44 [SA675-B4805]  
W78E54C@PLCC44 [SA244]  
W78E58  
W78E58@PQFP44 [SA675-B4805]  
W78E58B  
W78E58B@TQFP44 [SA675-B4805]  
W78E62B@PLCC44 [SA244]  
W78E65  
W78E65@TQFP44 [SA675-B4805]  
W78E858@PLCC44 [SA244]  
W78ERD2  
W78ERD2@TQFP44 [SA675-B4805]  
W78I051DFG@PQFP44 [SA675-B4805]  
W78I051DPG@PLCC44 [SA244]  
W78I052@PLCC44 [SA244]  
W78I052DFG@PQFP44 [SA675-B4805]  
W78I052DPG@PLCC44 [SA244]  
W78I054@PLCC44 [SA244]  
W78I054DFG@PQFP44 [SA675-B4805]  
W78I054DPG@PLCC44 [SA244]

W78E054B  
W78E054B@TQFP44 [SA675-B4805]  
W78E054C@PLCC44 [SA244]  
W78E054DDG  
W78E054DLG@LQFP48 [SA248-B4804]  
W78E058B  
W78E058B@TQFP44 [SA675-B4805]  
W78E058DFG@TQFP44 [SA675-B4805]  
W78E058DPG@PLCC44 [SA244]  
W78E065@PLCC44 [SA244]  
W78E365  
W78E365@TQFP44 [SA675-B4805]  
W78E365A@PLCC44 [SA244]  
W78E374B  
W78E378E  
W78E51  
W78E51@TQFP44 [SA675-B4805]  
W78E516@PLCC44 [SA244]  
W78E516B  
W78E516B@TQFP44 [SA675-B4805]  
W78E516DFG@TQFP44 [SA675-B4805]  
W78E516DPG@PLCC44 [SA244]  
W78E51B@PLCC44 [SA244]  
W78E51B@TQFP44 [SA245A-B4805]  
W78E51C@PLCC44 [SA244]  
W78E52  
W78E52@TQFP44 [SA675-B4805]  
W78E52B@PLCC44 [SA244]  
W78E52C  
W78E52C@TQFP44 [SA675-B4805]  
W78E54@PLCC44 [SA244]  
W78E54@TQFP44 [SA245A-B4805]  
W78E54B@PLCC44 [SA244]  
W78E54C  
W78E54C@TQFP44 [SA675-B4805]  
W78E58@PLCC44 [SA244]  
W78E58@TQFP44 [SA245A-B4805]  
W78E58B@PLCC44 [SA244]  
W78E62B  
W78E62B@TQFP44 [SA675-B4805]  
W78E65@PLCC44 [SA244]  
W78E858  
W78E858@TQFP44 [SA675-B4805]  
W78ERD2@PLCC44 [SA244]  
W78I051DDG  
W78I051DLG@LQFP48 [SA248-B4804]  
W78I052  
W78I052DDG  
W78I052DLG@LQFP48 [SA248-B4804]  
W78I054  
W78I054DDG  
W78I054DLG@LQFP48 [SA248-B4804]  
W78IE52

W78IE52@PLCC44 [SA244]  
W78IE54@PLCC44 [SA244]  
W78IRD2@PLCC44 [SA244]  
W78L051A  
W78L051A@TQFP44 [SA675-B4805]  
W78L051C@PLCC44 [SA244]  
W78L052A  
W78L052A@TQFP44 [SA675-B4805]  
W78L052C@PLCC44 [SA244]  
W78L054A  
W78L054A@TQFP44 [SA675-B4805]  
W78L054C@PLCC44 [SA244]  
W78L058A  
W78L058A@TQFP44 [SA675-B4805]  
W78L365@PLCC44 [SA244]  
W78L365@TQFP48 [SA248-B4804]  
W78L365A@PLCC44 [SA244]  
W78L365A@TQFP48 [SA248-B4804]  
W78L516@PLCC44 [SA244]  
W78L516A  
W78L516A@TQFP44 [SA675-B4805]  
W78L812A@PLCC44 [SA244]  
W78LE365  
W78LE365@TQFP44 [SA675-B4805]  
W78LE51  
W78LE51@TQFP44 [SA675-B4805]  
W78LE516@PLCC44 [SA244]  
W78LE51C  
W78LE51C@TQFP44 [SA675-B4805]  
W78LE52@PLCC44 [SA244]  
W78LE52C  
W78LE52C@TQFP44 [SA675-B4805]  
W78LE54@PLCC44 [SA244]  
W78LE54C  
W78LE54C@TQFP44 [SA675-B4805]  
W78LE58@PLCC44 [SA244]  
W78LE812  
W78LE812@TQFP44 [SA675-B4805]  
W79E201@TQFP44 [SA675-B4805]  
W79E2051 (dip16)  
W79E2051@S0IC14 [SA404]  
W79E2051@S0IC20 [SA404]  
W79E2051R@S0IC20 [SA404]  
W79E225APG@PLCC44 [SA244]  
W79E226APG@PLCC44 [SA244]  
W79E227APG@PLCC44 [SA244]  
W79E4051 (dip16)  
W79E4051@S0IC14 [SA404]  
W79E4051@S0IC20 [SA404]  
W79E4051R@S0IC20 [SA404]  
W79E532@PLCC44 [SA244]  
W79E532A  
W79E532A@TQFP44 [SA675-B4805]

W78IE54  
W78IRD2  
W78IRD2@TQFP44 [SA675-B4805]  
W78L051A@PLCC44 [SA244]  
W78L051C  
W78L051C@TQFP44 [SA675-B4805]  
W78L052A@PLCC44 [SA244]  
W78L052C  
W78L052C@TQFP44 [SA675-B4805]  
W78L054A@PLCC44 [SA244]  
W78L054C  
W78L054C@TQFP44 [SA675-B4805]  
W78L058A@PLCC44 [SA244]  
W78L365  
W78L365@TQFP44 [SA675-B4805]  
W78L365A  
W78L365A@TQFP44 [SA675-B4805]  
W78L516  
W78L516@TQFP44 [SA675-B4805]  
W78L516A@PLCC44 [SA244]  
W78L812A  
W78L812A@TQFP44 [SA675-B4805]  
W78LE365@PLCC44 [SA244]  
W78LE365@TQFP48 [SA248-B4804]  
W78LE51@PLCC44 [SA244]  
W78LE516  
W78LE516@TQFP44 [SA675-B4805]  
W78LE51C@PLCC44 [SA244]  
W78LE52  
W78LE52@TQFP44 [SA675-B4805]  
W78LE52C@PLCC44 [SA244]  
W78LE54  
W78LE54@TQFP44 [SA675-B4805]  
W78LE54C@PLCC44 [SA244]  
W78LE58  
W78LE58@TQFP44 [SA675-B4805]  
W78LE812@PLCC44 [SA244]  
W79E201@PLCC44 [SA244]  
W79E2051 (dip14)  
W79E2051 (dip20)  
W79E2051@S0IC16 [SA404]  
W79E2051R (dip20)  
W79E225ALG@TQFP48 [SA248-B4804]  
W79E226ALG@TQFP48 [SA248-B4804]  
W79E227ALG@TQFP48 [SA248-B4804]  
W79E4051 (dip14)  
W79E4051 (dip20)  
W79E4051@S0IC16 [SA404]  
W79E4051R (dip20)  
W79E532  
W79E532@TQFP44 [SA675-B4805]  
W79E532A@PLCC44 [SA244]  
W79E533A@PLCC44 [SA244]

W79E632  
W79E632@TQFP44 [SA675-B4805]  
W79E632A@PLCC44 [SA244]  
W79E633A@PLCC44 [SA244]  
W79E801A@S0IC20 [SA404]  
W79E802A@S0IC20 [SA404]  
W79E803A@S0IC20 [SA404]  
W79E804A@S0IC20 [SA404]  
W79E821A@S0IC20 [SA404]  
W79E822A@S0IC20 [SA404]  
W79E822B@S0IC20 [SA404]  
W79E823A@S0IC20 [SA404]  
W79E823B@S0IC20 [SA404]  
W79E824A@S0IC20 [SA404]  
W79E825A@S0IC20 [SA404]  
W79E831A@S0IC28 [SA404]  
W79E832A@S0IC28 [SA404]  
W79E833A@S0IC28 [SA404]  
W79E834A@S0IC28 [SA404]  
W79L532@PLCC44 [SA244]  
W79L632  
W79L632@TQFP44 [SA675-B4805]  
W79L632A@PLCC44 [SA244]  
W79L633A@PLCC44 [SA244]

W79E632@PLCC44 [SA244]  
W79E632A  
W79E632A@TQFP44 [SA675-B4805]  
W79E801A  
W79E802A  
W79E803A  
W79E804A  
W79E821A  
W79E822A  
W79E822B  
W79E823A  
W79E823B  
W79E824A  
W79E825A  
W79E831A  
W79E832A  
W79E833A  
W79E834A  
W79L532  
W79L532@TQFP44 [SA675-B4805]  
W79L632@PLCC44 [SA244]  
W79L632A  
W79L632A@TQFP44 [SA675-B4805]  
W99100DG@TQFP48 [SA248-B4804]

## WING Shing

### E (E) PROM/FRAM/NVRAM

WS24C02  
WS24C04  
WS24C08  
WS24C16  
WS24W04  
WS24W08  
WS24W16  
WS24C02@SOP8 [SA602A]  
WS24C04@SOP8 [SA602A]  
WS24C08@SOP8 [SA602A]  
WS24C16@SOP8 [SA602A]  
WS24W04@SOP8 [SA602A]  
WS24W08@SOP8 [SA602A]  
WS24W16@SOP8 [SA602A]

## WSI

### E (E) PROM/FRAM/NVRAM

WS27C010L  
WS27C010L@TSOP32 [SA410T-B4001]  
WS27C010R@PLCC32 [SA015A1T]  
WS27C040L  
WS27C040L@TSOP32 [SA410T-B4001]  
WS27C128F@PLCC32 [SA015A1T]  
WS27C128L@PLCC32 [SA015A1T]  
WS27C210L@PLCC44 [SA244]  
WS27C256F@PLCC32 [SA015A1T]  
WS27C256L@PLCC32 [SA015A1T]  
WS27C512F@PLCC32 [SA015A1T]  
WS27C010L@PLCC32 [SA015A1T]  
WS27C010R  
WS27C010R@TSOP32 [SA410T-B4001]  
WS27C040L@PLCC32 [SA015A1T]  
WS27C128F  
WS27C128L  
WS27C210L  
WS27C256F  
WS27C256L  
WS27C512F  
WS27C512L

WS27C512L@PLCC32 [SA015A1T]	WS27C64
WS27C64@PLCC32 [SA015A1T]	WS27C64F
WS27C64F@PLCC32 [SA015A1T]	WS27C64L
WS27C64L@PLCC32 [SA015A1T]	WS57C128
WS57C128@PLCC32 [SA015A1T]	WS57C128F
WS57C128F@PLCC32 [SA015A1T]	WS57C128FB
WS57C128FB@PLCC32 [SA015A1T]	WS57C191
WS57C191@PLCC28 [SA008A]	WS57C191B
WS57C191B@PLCC28 [SA008A]	WS57C191C
WS57C191C@PLCC28 [SA008A]	WS57C256F
WS57C256F@PLCC32 [SA015A1T]	WS57C256FB
WS57C256FB@PLCC32 [SA015A1T]	WS57C257
WS57C257@PLCC44 [SA244]	WS57C291
WS57C291@PLCC28 [SA008A]	WS57C291B
WS57C291B@PLCC28 [SA008A]	WS57C291C
WS57C291C@PLCC28 [SA008A]	WS57C43
WS57C43@PLCC28 [SA008A]	WS57C43B
WS57C43B@PLCC28 [SA008A]	WS57C43C
WS57C43C@PLCC28 [SA008A]	WS57C45
WS57C45@PLCC28 [SA008A]	WS57C49
WS57C49@PLCC28 [SA008A]	WS57C49B
WS57C49B@PLCC28 [SA008A]	WS57C49C
WS57C49C@PLCC28 [SA008A]	WS57C51
WS57C51@PLCC32 [SA015A1T]	WS57C51B
WS57C51B@PLCC32 [SA015A1T]	WS57C51C
WS57C51C@PLCC32 [SA015A1T]	WS57C64F
WS57C64F@PLCC32 [SA015A1T]	WS57C71C
WS57C71C@PLCC32 [SA015A1T]	WS57LV191C
WS57LV191C@PLCC28 [SA008A]	WS57LV291C
WS57LV291C@PLCC28 [SA008A]	

## XELTEK

### MICROCONTROLLER

#####22222222222UP	#####33333333333MCU
#####66666666666TST	SP5KTEST-LOG
SYSTEM-CLK-TEST	

## XICOR

### E (E) PROM/FRAM/NVRAM

X2004	X2004@PLCC32 [SA015A1T]
X2004D	X2004D@PLCC32 [SA015A1T]
X2004I	X2004I@PLCC32 [SA015A1T]
X2210	X2210@SOIC16 [SA404]
X2210A	X2210A@SOIC16 [SA404]
X2210I	X2210I@SOIC16 [SA404]
X2212	X2212@SOIC20 [SA404]
X2212A	X2212A@SOIC20 [SA404]
X2212I	X2212I@SOIC20 [SA404]

X22C10	X22C10@SOIC16 [SA404]
X22C10I	X22C10I@SOIC16 [SA404]
X22C12	X22C12@SOIC20 [SA404]
X22C12I	X22C12I@SOIC20 [SA404]
X24012	X24012@SOIC8 [SA602A]
X24022	X24022@SOIC8 [SA602A]
X24026	X24026@SOIC8 [SA602A]
X24042	X24042@SOIC8 [SA602A]
X24164	X24164@SOIC8 [SA602A]
X24165	X24165@SOIC8 [SA602A]
X24325	X24325@SOIC8 [SA602A]
X2444	X2444I
X24645	X24645@SOIC8 [SA602A]
X24C00	X24C00@MSOP8 [SA643]
X24C00@SOIC8 [SA602A]	X24C01
X24C01@MSOP8 [SA666]	X24C01@SOIC8 [SA602A]
X24C01A	X24C01A@SOIC8 [SA602A]
X24C01I	X24C01I@SOIC8 [SA602A]
X24C02	X24C02@SOIC8 [SA602A]
X24C02I	X24C02I@SOIC8 [SA602A]
X24C04	X24C04@SOIC14 [SA602]
X24C04@SOIC8 [SA602A]	X24C04I
X24C04I@SOIC14 [SA602]	X24C04I@SOIC8 [SA602A]
X24C08	X24C08@SOIC14 [SA602]
X24C08@SOIC8 [SA602A]	X24C08I
X24C08I@SOIC14 [SA602]	X24C08I@SOIC8 [SA602A]
X24C16	X24C16@SOIC14 [SA602]
X24C16@SOIC8 [SA602A]	X24C16I
X24C16I@SOIC14 [SA602]	X24C16I@SOIC8 [SA602A]
X24C44	X24C44@SOIC8 [SA602A]
X24C44I	X24C44I@SOIC8 [SA602A]
X24C45	X24C45@SOIC8 [SA602A]
X24C45I	X24C45I@SOIC8 [SA602A]
X24F008 (3V)	X24F008 (3V)@SOIC8 [SA602A]
X24F008 (3V)@TSSOP14 [SA602]	X24F008 (5V)
X24F008 (5V)@SOIC8 [SA602A]	X24F008 (5V)@TSSOP14 [SA602]
X24F016 (3V)	X24F016 (3V)@SOIC8 [SA602A]
X24F016 (3V)@TSSOP14 [SA602]	X24F016 (5V)
X24F016 (5V)@SOIC8 [SA602A]	X24F016 (5V)@TSSOP14 [SA602]
X24F032 (3V)	X24F032 (3V)@SOIC8 [SA602A]
X24F032 (3V)@TSSOP14 [SA602]	X24F032 (5V)
X24F032 (5V)@SOIC8 [SA602A]	X24F032 (5V)@TSSOP14 [SA602]
X24F064 (3V)	X24F064 (3V)@SOIC8 [SA602A]
X24F064 (3V)@TSSOP20 [SA404]	X24F064 (5V)
X24F064 (5V)@SOIC8 [SA602A]	X24F064 (5V)@TSSOP20 [SA404]
X25020	X25020@SOIC8 [SA602A]
X25021	X25021@SOIC8 [SA602A]
X25040	X25040@SOIC8 [SA602A]
X25041	X25041@SOIC8 [SA602A]
X25043	X25043@MSOP8 [SA666]
X25043@SOIC8 [SA602A]	X25043@TSSOP14 [SA026]
X25045	X25045@MSOP8 [SA666]
X25045@SOIC8 [SA602A]	X25045@TSSOP14 [SA026]

X25057@MSOP8 [SA666]  
X25080  
X25080@TSSOP14 [SA026]  
X25097@SOIC8 [SA602A]  
X25128  
X25138  
X25138@SOIC16 [SA602]  
X25138@TSSOP8 [SA643]  
X25160@SOIC8 [SA602A]  
X25163  
X25163@TSSOP14 [SA026]  
X25164@SOIC8 [SA602A]  
X25165  
X25165@TSSOP14 [SA026]  
X25166@SOIC8 [SA602A]  
X25168  
X25168@TSSOP14 [SA026]  
X25169@SOIC8 [SA602A]  
X25170@SOIC8 [SA602A]  
X25256@SOIC8 [SA602A]  
X25320  
X25323@SOIC8 [SA602A]  
X25324@SOIC8 [SA602A]  
X25325@SOIC8 [SA602A]  
X25326@SOIC8 [SA602A]  
X25328@TSSOP14 [SA026]  
X25329@TSSOP14 [SA026]  
X25330@TSSOP14 [SA026]  
X25401@SOIC8 [SA602A]  
X25640@SOIC14 [SA602]  
X25642@SOIC14 [SA602]  
X25642@TSSOP20 [SA026]  
X25644@SOIC14 [SA602]  
X25648@SOIC14 [SA602]  
X25650  
X25650@SOIC8 [SA602A]  
X25C02  
X25C02@TSSOP8 [SA643]  
X25F008 (3V)@SOIC8 [SA602A]  
X25F008 (3V)@TSSOP20 [SA404]  
X25F008 (5V)@SOIC8 [SA602A]  
X25F008 (5V)@TSSOP20 [SA404]  
X25F016 (3V)@SOIC8 [SA602A]  
X25F016 (3V)@TSSOP20 [SA404]  
X25F016 (5V)@SOIC8 [SA602A]  
X25F016 (5V)@TSSOP20 [SA404]  
X25F032 (3V)@SOIC8 [SA602A]  
X25F032 (3V)@TSSOP20 [SA404]  
X25F032 (5V)@SOIC8 [SA602A]  
X25F032 (5V)@TSSOP20 [SA404]  
X25F047 (3V)@MSOP8 [SA666]  
X25F047 (3V)@TSSOP8 [SA026]  
X25F047 (5V)@MSOP8 [SA666]  
X25057@TSSOP8 [SA643]  
X25080@SOIC8 [SA602A]  
X25097@MSOP8 [SA666]  
X25097@TSSOP8 [SA643]  
X25128@SOIC16 [SA602]  
X25138@SOIC14 [SA602]  
X25138@SOIC8 [SA602A]  
X25160  
X25160@TSSOP14 [SA026]  
X25163@SOIC8 [SA602A]  
X25164  
X25164@TSSOP14 [SA026]  
X25165@SOIC8 [SA602A]  
X25166  
X25166@TSSOP14 [SA026]  
X25168@SOIC8 [SA602A]  
X25169  
X25169@TSSOP14 [SA026]  
X25256  
X25256@TSSOP20 [SA026]  
X25320@SOIC8 [SA602A]  
X25323@TSSOP14 [SA026]  
X25324@TSSOP14 [SA026]  
X25325@TSSOP14 [SA026]  
X25328@SOIC8 [SA602A]  
X25329@SOIC8 [SA602A]  
X25330@SOIC8 [SA602A]  
X25401  
X25640  
X25642  
X25642@SOIC8 [SA602A]  
X25643@SOIC14 [SA602]  
X25645@SOIC14 [SA602]  
X25649@SOIC14 [SA602]  
X25650@SOIC14 [SA602]  
X25650@TSSOP20 [SA026]  
X25C02@SOIC8 [SA602A]  
X25F008 (3V)  
X25F008 (3V)@TSSOP14 [SA602]  
X25F008 (5V)  
X25F008 (5V)@TSSOP14 [SA602]  
X25F016 (3V)  
X25F016 (3V)@TSSOP14 [SA602]  
X25F016 (5V)  
X25F016 (5V)@TSSOP14 [SA602]  
X25F032 (3V)  
X25F032 (3V)@TSSOP14 [SA602]  
X25F032 (5V)  
X25F032 (5V)@TSSOP14 [SA602]  
X25F047 (3V)  
X25F047 (3V)@SOIC8 [SA602A]  
X25F047 (5V)  
X25F047 (5V)@SOIC8 [SA602A]

X25F047 (5V)@TSSOP8 [SA026]  
X25F064 (3V)@SOIC8 [SA602A]  
X25F064 (3V)@TSSOP20 [SA404]  
X25F064 (5V)@SOIC8 [SA602A]  
X25F064 (5V)@TSSOP20 [SA404]  
X25F087 (3V)@MSOP8 [SA666]  
X25F087 (3V)@TSSOP8 [SA026]  
X25F087 (5V)@MSOP8 [SA666]  
X25F087 (5V)@TSSOP8 [SA026]  
X25F128 (3V)@SOIC16 [SA602]  
X25F128 (5V)@SOIC16 [SA602]  
X28010@PLCC32 [SA015A1T]  
X2804A  
X2804A (MB)  
X2816A@PLCC32 [SA015A1T]  
X2816B@PLCC32 [SA015A1T]  
X2816BI@PLCC32 [SA015A1T]  
X2816C  
X28256  
X28256I  
X2864A  
X2864A (I)@PLCC32 [SA015A1T]  
X2864A (M)@PLCC32 [SA015A1T]  
X2864A (MB)@PLCC32 [SA015A1T]  
X2864A (T)@PLCC32 [SA015A1T]  
X2864B  
X2864B (I)@PLCC32 [SA015A1T]  
X2864B (M)@PLCC32 [SA015A1T]  
X2864H  
X2864H (I)@PLCC32 [SA015A1T]  
X28C010  
X28C16A  
X28C16B  
X28C16C  
X28C256  
X28C256@TSOP28 [SA430T-B4003]  
X28C512@PLCC32 [SA015A1T]  
X28C513  
X28C64  
X28C64@SOIC28 [SA404]  
X28HC16  
X28HC16@SOIC24 [SA404]  
X28HC256@PLCC32 [SA015A1T]  
X28HC256@TSOP28 [SA430T-B4003]  
X28HC64@PLCC32 [SA015A1T]  
X28HC64@TSOP28 [SA430T-B4003]  
X28LC512@PLCC32 [SA015A1T]  
X28LC513@PLCC32 [SA015A1T]  
X28VC256@PLCC32 [SA015A1T]  
X40231@SOIC16 [SA404]  
X40235@SOIC16 [SA404]  
X40239@SOIC16 [SA404]  
X4043@MSOP8 [SA026]  
X25F064 (3V)  
X25F064 (3V)@TSSOP14 [SA602]  
X25F064 (5V)  
X25F064 (5V)@TSSOP14 [SA602]  
X25F087 (3V)  
X25F087 (3V)@SOIC8 [SA602A]  
X25F087 (5V)  
X25F087 (5V)@SOIC8 [SA602A]  
X25F128 (3V)  
X25F128 (5V)  
X28010  
X28010@TSOP32 [SA410T-B4001]  
X2804A (I)  
X2816A  
X2816B  
X2816BI  
X2816BMB  
X2816C@PLCC32 [SA015A1T]  
X28256@PLCC32 [SA015A1T]  
X28256I@PLCC32 [SA015A1T]  
X2864A (I)  
X2864A (M)  
X2864A (MB)  
X2864A (T)  
X2864A@PLCC32 [SA015A1T]  
X2864B (I)  
X2864B (M)  
X2864B@PLCC32 [SA015A1T]  
X2864H (I)  
X2864H@PLCC32 [SA015A1T]  
X28C010@PLCC32 [SA015A1T]  
X28C16A@PLCC32 [SA015A1T]  
X28C16B@PLCC32 [SA015A1T]  
X28C16C@PLCC32 [SA015A1T]  
X28C256@PLCC32 [SA015A1T]  
X28C512  
X28C512@TSOP40 [SA409T-B4002]  
X28C513@PLCC32 [SA015A1T]  
X28C64@PLCC32 [SA015A1T]  
X28C64@TSOP28 [SA430T-B4003]  
X28HC16@PLCC32 [SA015A1T]  
X28HC256  
X28HC256@SOIC28 [SA404]  
X28HC64  
X28HC64@SOIC28 [SA404]  
X28LC512  
X28LC513  
X28VC256  
X28VC256@TSOP28 [SA430T-B4003]  
X40233@SOIC16 [SA404]  
X40237@SOIC16 [SA404]  
X4043  
X4043@SOIC8 [SA602A]

X40430@SOIC14 [SA404]  
X40431@SOIC14 [SA404]  
X40434@SOIC14 [SA404]  
X40435@SOIC14 [SA404]  
X4045  
X4045@SOIC8 [SA602A]  
X5043@MSOP8 [SA666]  
X5043@TSSOP14 [SA026]  
X5045@MSOP8 [SA666]  
X5045@TSSOP14 [SA026]  
X5083@SOIC8 [SA602A]  
X5163  
X5163@TSSOP14 [SA026]  
X51638@SOIC8 [SA602A]  
X5165  
X5165@TSSOP14 [SA026]  
X5168@SOIC8 [SA602A]  
X5169  
X5169@TSSOP14 [SA026]  
X5323@SOIC8 [SA602A]  
X5325  
X5325@TSSOP14 [SA026]  
X5328@SOIC8 [SA602A]  
X5329  
X5329@TSSOP14 [SA026]  
X5643@SOIC14  
X5643@TSSOP20 [SA026]  
X5645@SOIC14 [SA602]  
X5645@TSSOP20 [SA026]  
X5648@SOIC14 [SA602]  
X5649@SOIC14 [SA602]  
X68C64@SOIC24 [SA404]  
X76F041 (3)  
X76F041@SOIC8 [SA605B]  
X76F101@SOIC8 [SA602A]  
X76F400@TSSOP8 [SA026]  
X86C64@SOIC24 [SA404]  
X88064@SOIC24 [SA404]  
X88C64@SOIC24 [SA404]  
XD2210  
XM28C010  
XM28C040

X40430@TSSOP14 [SA026]  
X40431@TSSOP14 [SA026]  
X40434@TSSOP14 [SA026]  
X40435@TSSOP14 [SA026]  
X4045@MSOP8 [SA026]  
X5043  
X5043@SOIC8 [SA602A]  
X5045  
X5045@SOIC8 [SA602A]  
X5083  
X5083@TSSOP8 [SA026]  
X5163@SOIC8 [SA602A]  
X51638  
X51638@TSSOP14 [SA026]  
X5165@SOIC8 [SA602A]  
X5168  
X5168@TSSOP14 [SA026]  
X5169@SOIC8 [SA602A]  
X5323  
X5323@TSSOP14 [SA026]  
X5325@SOIC8 [SA602A]  
X5328  
X5328@TSSOP14 [SA026]  
X5329@SOIC8 [SA602A]  
X5643  
X5643@SOIC8 [SA602A]  
X5645  
X5645@SOIC8 [SA602A]  
X5648  
X5649  
X68C64  
X76F041  
X76F041 (3)@SOIC8 [SA605B]  
X76F101  
X76F400@SOIC8 [SA026]  
X86C64  
X88064  
X88C64  
X88C75  
XD2210@SOIC16 [SA404]  
XM28C020

## XILINX

### E (E) PROM/FRAM/NVRAM

XC1701  
XC1701@PLCC44 [SA244]  
XC1701L  
XC1701L@PLCC44 [SA244]  
XC1702L@PLCC44 [SA244]

XC1701@PLCC20 [SA001A-B2001]  
XC1701@SOIC20 [SA404]  
XC1701L@PLCC20 [SA001A-B2001]  
XC1701L@SOIC20 [SA404]  
XC1702L@TQFP44 [SA245A-B4805]

XC1704L@PLCC44 [SA244]  
XC17128D  
XC17128D@SOIC8 [SA602A]  
XC17128E  
XC17128E@VOIC8 [SA602A]  
XC17128EL@PLCC20 [SA001A-B2001]  
XC17128L  
XC17128L@SOIC8 [SA602A]  
XC17128X  
XC17128X@SOIC8 [SA602A]  
XC1718D  
XC1718D@SOIC8 [SA602A]  
XC1718L  
XC1718L@SOIC8 [SA602A]  
XC17256D  
XC17256D@SOIC8 [SA602A]  
XC17256E  
XC17256E@VOIC8 [SA602A]  
XC17256EL@PLCC20 [SA001A-B2001]  
XC17256L  
XC17256L@SOIC8 [SA602A]  
XC17256X  
XC17256X@SOIC8 [SA602A]  
XC1736D  
XC1736D@SOIC8 [SA602A]  
XC1736E  
XC1736E@SOIC8 [SA602A]  
XC17512L  
XC17512L@PLCC44 [SA244]  
XC1765D  
XC1765D@SOIC8 [SA602A]  
XC1765E  
XC1765E@SOIC8 [SA602A]  
XC1765EL  
XC1765EL@SOIC8 [SA602A]  
XC1765L  
XC1765L@SOIC8 [SA602A]  
XC1765X  
XC1765X@SOIC8 [SA602A]  
XC17S05  
XC17S05XL (L)  
XC17S10  
XC17S100A  
XC17S100A@SOIC8 [SA602A]  
XC17S100XL (L)@SOIC20 [SA404]  
XC17S10XL (L)@SOIC8 [SA602A]  
XC17S150A@SOIC20 [SA404]  
XC17S150XL (L)  
XC17S15A  
XC17S15A@SOIC8 [SA602A]  
XC17S20@SOIC8 [SA602A]  
XC17S200A@SOIC8 [SA602A]  
XC17S20XL (L)  
XC1704L@TQFP44 [SA245A-B4805]  
XC17128D@PLCC20 [SA001A-B2001]  
XC17128D@VOIC8 [SA602A]  
XC17128E@PLCC20 [SA001A-B2001]  
XC17128EL  
XC17128EL@VOIC8 [SA602A]  
XC17128L@PLCC20 [SA001A-B2001]  
XC17128L@VOIC8 [SA602A]  
XC17128X@PLCC20 [SA001A-B2001]  
XC17128X@VOIC8 [SA602A]  
XC1718D@PLCC20 [SA001A-B2001]  
XC1718D@VOIC8 [SA602A]  
XC1718L@PLCC20 [SA001A-B2001]  
XC1718L@VOIC8 [SA602A]  
XC17256D@PLCC20 [SA001A-B2001]  
XC17256D@VOIC8 [SA602A]  
XC17256E@PLCC20 [SA001A-B2001]  
XC17256EL  
XC17256EL@VOIC8 [SA602A]  
XC17256L@PLCC20 [SA001A-B2001]  
XC17256L@VOIC8 [SA602A]  
XC17256X@PLCC20 [SA001A-B2001]  
XC17256X@VOIC8 [SA602A]  
XC1736D@PLCC20 [SA001A-B2001]  
XC1736D@VOIC8 [SA602A]  
XC1736E@PLCC20 [SA001A-B2001]  
XC1736E@VOIC8 [SA602A]  
XC17512L@PLCC20 [SA001A-B2001]  
XC17512L@SOIC20 [SA404]  
XC1765D@PLCC20 [SA001A-B2001]  
XC1765D@VOIC8 [SA602A]  
XC1765E@PLCC20 [SA001A-B2001]  
XC1765E@VOIC8 [SA602A]  
XC1765EL@PLCC20 [SA001A-B2001]  
XC1765EL@VOIC8 [SA602A]  
XC1765L@PLCC20 [SA001A-B2001]  
XC1765L@VOIC8 [SA602A]  
XC1765X@PLCC20 [SA001A-B2001]  
XC1765X@VOIC8 [SA602A]  
XC17S05@SOIC8 [SA602A]  
XC17S05XL (L)@SOIC8 [SA602A]  
XC17S10@SOIC8 [SA602A]  
XC17S100A@SOIC20 [SA404]  
XC17S100XL (L)  
XC17S10XL (L)  
XC17S150A  
XC17S150A@SOIC8 [SA602A]  
XC17S150XL (L)@SOIC20 [SA404]  
XC17S15A@SOIC20 [SA404]  
XC17S20  
XC17S200A  
XC17S200A@TQFP44 [SA245A-B4805]  
XC17S20XL (L)@SOIC8 [SA602A]

XC17S30  
XC17S300A@TQFP44 [SA245A-B4805]  
XC17S30A@SOIC20 [SA404]  
XC17S30XL (L)  
XC17S40  
XC17S40XL (L)  
XC17S50A  
XC17S50A@SOIC8 [SA602A]  
XC17S50XL (L)@SOIC20 [SA404]  
XC17V01@SOIC20 [SA404]  
XC17V02@PLCC20 [SA001A-B2001]  
XC17V02@TQFP44 [SA245A-B4805]  
XC17V04@PLCC44 [SA244]  
XC17V08@PLCC44 [SA244]  
XC17V16@PLCC44 [SA244]  
XC18V01@PLCC20 [SA001A-B2001]  
XC18V01@TQFP44 [SA245A-B4805]  
XC18V02@TQFP44 [SA245A-B4805]  
XC18V04@TQFP44 [SA245A-B4805]  
XC18V256@SOIC20 [SA404]  
XC18V512@PLCC20 [SA001A-B2001]  
XC18V512@TQFP44 [SA245A-B4805]  
XCF08P (FSG)@FBGA48 (ISP)  
XCF08P (VOG)@TSOP48 (ISP)  
XCF16P (FSG)@FBGA48 (ISP)  
XCF16P (VOG)@TSOP48 (ISP)  
XCF32P (FSG)@FBGA48 (ISP)  
XCF32P (VOG)@TSOP48 (ISP)

XC17S30@SOIC8 [SA602A]  
XC17S30A  
XC17S30A@SOIC8 [SA602A]  
XC17S30XL (L)@SOIC8 [SA602A]  
XC17S40@SOIC20 [SA404]  
XC17S40XL (L)@SOIC20 [SA404]  
XC17S50A@SOIC20 [SA404]  
XC17S50XL (L)  
XC17V01@PLCC20 [SA001A-B2001]  
XC17V01@SOIC8 [SA602A]  
XC17V02@PLCC44 [SA244]  
XC17V04@PLCC20 [SA001A-B2001]  
XC17V04@TQFP44 [SA245A-B4805]  
XC17V08@TQFP44 [SA245A-B4805]  
XC17V16@TQFP44 [SA245A-B4805]  
XC18V01@SOIC20 [SA404]  
XC18V02@PLCC44 [SA411A]  
XC18V04@PLCC44 [SA411A]  
XC18V256@PLCC20 [SA001A-B2001]  
XC18V256@TQFP44 [SA245A-B4805]  
XC18V512@SOIC20 [SA404]  
XCF08P (FS)@FBGA48 (ISP)  
XCF08P (VO)@TSOP48 (ISP)  
XCF16P (FS)@FBGA48 (ISP)  
XCF16P (VO)@TSOP48 (ISP)  
XCF32P (FS)@FBGA48 (ISP)  
XCF32P (VO)@TSOP48 (ISP)

## PLD

XA9536XL@PLCC44 [SA244]  
XC9536@PLCC44 [SA244]  
XC9536XL@PLCC44 [SA244]  
XC9536XV@PLCC44 [SA244]  
XC9572@PLCC44 [SA244]  
XC9572XL@PLCC44 [SA244]  
XC9572XV@PLCC44 [SA244]

XA9536XL@VQFP44 [SA245A-B4805]  
XC9536@TQFP44 [SA245A-B4805]  
XC9536XL@VQFP44 [SA245A-B4805]  
XC9536XV@TQFP44 [SA245A-B4805]  
XC9572@TQFP44 [SA245A-B4805]  
XC9572XL@TQFP44 [SA245A-B4805]  
XC9572XV@TQFP44 [SA245A-B4805]

## XINNOVA

### MICROCONTROLLER

XN89F515  
XN89F515@TQFP44 [SA675-B4805]  
XN89L515@PLCC44 [SA244]  
XN89W517  
XN89W517@PLCC44 [SA244]

XN89F515@PLCC44 [SA244]  
XN89L515  
XN89L515@TQFP44 [SA675-B4805]  
XN89W517@LQFP48 [SA248-B4804]  
XN89W517@PQFP44 [SA675-B4805]

## XUMARS

## MICROCONTROLLER

HS32423SP28@SOIC28 [SA404]  
HS32533SP28@SOIC28 [SA404]

HS32423SP28@SOIC28 (ISP)  
HS32533SP28@SOIC28 (ISP)

## YMC

### E (E) PROM/FRAM/NVRAM

Y24LC01  
Y24LC01@TSSOP8 [SA643]  
Y24LC02@SOIC8 [SA602A]  
Y24LC02A  
Y24LC02A@TSSOP8 [SA643]  
Y24LC04@SOIC8 [SA602A]  
Y24LC08  
Y24LC08@TSSOP8 [SA643]  
Y24LC16@SOIC8 [SA602A]  
Y24LC32  
Y24LC32@TSSOP8 [SA643]  
Y24LC64@SOIC8 [SA602A]  
Y54LC64  
Y54LC64@TSSOP8 [SA026]  
Y93LC46 (16bit)@SOIC8 [SA602A]  
Y93LC46-08  
Y93LC46-08-T8 [SA643]  
Y93LC66 (08bit)@SOIC8 [SA602A]  
Y93LC66 (16bit)  
Y93LC66 (16bit)@TSSOP8 [SA643]  
Y93LC86 (08bit)@SOIC8 [SA602A]  
Y93LC86 (16bit)  
Y93LC86 (16bit)@TSSOP8 [SA643]

Y24LC01@SOIC8 [SA602A]  
Y24LC02  
Y24LC02@TSSOP8 [SA643]  
Y24LC02A@SOIC8 [SA602A]  
Y24LC04  
Y24LC04@TSSOP8 [SA643]  
Y24LC08@SOIC8 [SA602A]  
Y24LC16  
Y24LC16@TSSOP8 [SA643]  
Y24LC32@SOIC8 [SA602A]  
Y24LC64  
Y24LC64@TSSOP8 [SA643]  
Y54LC64@SOIC8 [SA602A]  
Y93LC46 (16bit)  
Y93LC46 (16bit)@TSSOP8 [SA643]  
Y93LC46-08-S8 [SA602A]  
Y93LC66 (08bit)  
Y93LC66 (08bit)@TSSOP8 [SA643]  
Y93LC66 (16bit)@SOIC8 [SA602A]  
Y93LC86 (08bit)  
Y93LC86 (08bit)@TSSOP8 [SA643]  
Y93LC86 (16bit)@SOIC8 [SA602A]

## YSS

### E (E) PROM/FRAM/NVRAM

Y25F05@SOP8 [SA602A]  
Y25F10@SOP8 [SA602A]

Y25F05@VQFN8 [SA683]  
Y25F10@VQFN8 [SA683]

## YXLDZ

### E (E) PROM/FRAM/NVRAM

YXL9020F [SA602A]

## ZETTA

### E (E) PROM/FRAM/NVRAM

ZD25D16  
ZD25D16@SOIC8[200 mil] [SA605B]  
ZD25D16@WSON8 [SA683]  
ZD25D20@SOIC8[200 mil] [SA605B]  
ZD25D20@USON8 [SA724]  
ZD25D40@SOIC8[200 mil] [SA605B]  
ZD25D40@USON8 [SA724]  
ZD25D80@SOIC8[200 mil] [SA605B]  
ZD25D80@WSON8 [SA683]

ZD25D16@SOIC8[150 mil] [SA602A]  
ZD25D16@TSSOP8 [SA026]  
ZD25D20@SOIC8[150 mil] [SA602A]  
ZD25D20@TSSOP8 [SA026]  
ZD25D40@SOIC8[150 mil] [SA602A]  
ZD25D40@TSSOP8 [SA026]  
ZD25D80@SOIC8[150 mil] [SA602A]  
ZD25D80@USON8 [SA724]

## ZHENGXIN

### E (E) PROM/FRAM/NVRAM

LX24C01  
LX24C01@TSSOP8 [SA643]  
LX24C02@SOIC8 [SA602A]  
LX24C04  
LX24C04@TSSOP8 [SA643]  
LX24C08@SOIC8 [SA602A]  
LX24C16  
LX24C16@TSSOP8 [SA643]

LX24C01@SOIC8 [SA602A]  
LX24C02  
LX24C02@TSSOP8 [SA643]  
LX24C04@SOIC8 [SA602A]  
LX24C08  
LX24C08@TSSOP8 [SA643]  
LX24C16@SOIC8 [SA602A]

## ZILOG

### MICROCONTROLLER

Z86E21  
Z86E21@TQFP44 [SA245A-B4805]  
Z86E2112@PLCC44 [SA244]  
Z86E2116  
Z86E2116@TQFP44 [SA245A-B4805]  
Z86E23@PLCC44 [SA244]  
Z86E2312  
Z86E2312@TQFP44 [SA245A-B4805]  
Z86E2316@PLCC44 [SA244]

Z86E21@PLCC44 [SA244]  
Z86E2112  
Z86E2112@TQFP44 [SA245A-B4805]  
Z86E2116@PLCC44 [SA244]  
Z86E23  
Z86E23@TQFP44 [SA245A-B4805]  
Z86E2312@PLCC44 [SA244]  
Z86E2316  
Z86E2316@TQFP44 [SA245A-B4805]

## ZMD

### E (E) PROM/FRAM/NVRAM

U62256  
U6264@SOIC28  
U6264A@SOIC28 [SA630]  
U62H256S@SOIC28 [SA630]  
U630H16  
U630H64  
U631H16  
U631H16@SOIC28 [SA630]  
U631H256@SOIC28 [SA630]  
U631H64@SOIC28 [SA630]

U6264  
U6264A  
U62H256A@SOIC28 [SA630]  
U62H64SA@SOIC28 [SA404]  
U630H16@SOIC28 [SA630]  
U630H64@SOIC28 [SA630]  
U631H16@SOIC24 [SA404]  
U631H256  
U631H64  
U632H16

U632H16@SOIC28 [SA630]  
U632H64@SOIC28 [SA630]  
U634H256@SOIC32 [SA630]  
U635H16@SOIC24 [SA404]  
U635H256@SOIC28 [SA630]  
U635H64@SOIC28 [SA630]  
U637256  
U637H256  
UL631H256@SOIC28 [SA630]  
UL634H256@SOIC32 [SA630]  
UL635H256@SOIC28 [SA630]

U632H64  
U634H256  
U635H16  
U635H256  
U635H64  
U63716  
U63764  
UL62H256A@SOIC28 [SA630]  
UL631H256@TSOP32 [SA410T-B4001]  
UL634H256@TSOP32 [SA410T-B4001]  
UL635H256@SOIC32 [SA410T-B4001]