



ENGLISH

Datasheet

RS Pro Tachometer, Best Accuracy $\pm 0.02\%$ Non Contact LCD 99999rpm

RS Stock No: **845-9680**



Product Details

RS Pro tachometer offers the latest technologies in a robust and durable housing. It can be used as both an optical tachometer to measure rotations and also a contact reader to measure rotational speed, linear speed and distance. This tool is just as important in the implementation and day to day operations of machinery and systems as it is for maintenance and would also benefit research and development laboratories. It has a speed range of 0 to 99999 rpm and best accuracy of $\pm 0.02\%$.

Features and Benefits

- Measures maximum, minimum and average values in both metric and imperial units
- LCD display
- Supplied with hard plastic carry case, 2 x AA batteries and 10 x reflective strips



ENGLISH

Specifications:

Battery Type	AA
Best Accuracy	±0.02%
Category	Non Contact
Dimensions	170 x 70 x 40 mm
Display Type	LCD
Height	40 mm
Length	170 mm
Maximum Operating Temperature	+50°C
Maximum Speed	99999 rpm
Minimum Operating Temperature	0°C
Minimum Speed	0 rpm
Weight	250 g
Width	70 mm