

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [180810-0001](#)
Status: **Active**
Description: LED Array Holder for 23.85 by 23.85mm COB, Round Version 50.00mm Outer Diameter with integrated pre-hold tab and Three-latch bayonet-style reflector attachment, Gold (Au) Plating

Documents:

[3D Model](#) [Test Summary TS-180155-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Application Specification AS-180810-001 \(PDF\)](#)

General

Product Family	Solid State Lighting
Series	180810
Beam Angle	N/A
Height	4.10mm
Product Name	LED Array Holder
Type	Socket Assembly
UPC	887191417356

Physical

Base Type	Direct Wire
Color Rendering Index (CRI)	N/A
Correlated Color Temp (CCT)	N/A
Lamp Type	Socket
Mounting Style	Screws
Net Weight	10.175/g
Packaging Type	Tray

Electrical

Lamp Wattage - Maximum	N/A
Lumens	N/A
Voltage (Fixture) - Maximum	300V DC

Material Info

Reference - Drawing Numbers

Application Specification	AS-180810-001
Sales Drawing	SD-180810-001
Test Summary	TS-180155-001



EU RoHS

**ELV and RoHS
Compliant**
**REACH SVHC
Contains SVHC: No**
**Low-Halogen Status
Not Low-Halogen**

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
180810Series