


Datasheet

Art.No. 80.063.4031.0

Relay FLARE MOVE 38 12VDC6A

flareMOVE, relay 12VDC, width 6,2mm, 1 change-over contact, plugable, input voltage 12 V/DC, output: 250 V AC / 6 A, gold-plated con tacts



Art.No.	80.063.4031.0
EAN	4015573659308
Order unit	10 pieces

Approvals

Technical data

General

Connection type	Plug-in connection
Number of change-over contacts	1
Detachable clamps	No
Drive, polarization	Polarity free
Drive, function	Mono stable
Forced-guided contacts	No
Complete with socket	No
Degree of protection (IP)	IP20

Technical data

Type of excitation	
Nominal voltage DC	12 V
Lower nominal voltage DC	12 V
Upper nominal voltage DC	12 V

Dimensions

Depth	15 mm
Width	5 mm
Height	28 mm

Classification

ECLASS 8.1	27371601: Switching relay
ETIM 5.0	EC001437: Switching relay
ETIM 4.0	EC001437: Switching relay
ETIM 3.0	EC001437: Switching relay