



ENGLISH

## Datasheet

Stock No: 235-708

# RS Pro Cage Guard For Use With Xenon Bulb



## Dimensions

Height: 190 mm

Top Circumference: 140 mm

Bottom Circumference: 175 mm

## Product Details

### 14W Xenon Beacon

A high performance range suitable for 12/24V applications requiring maximum visibility e.g. construction, utility or agricultural vehicles

Vibration protected circuits

Reverse polarity protection

Supply voltage: 12/24Vdc

Current consumption: 2A / 1A @ 12/24V

Single or Double Flash operation possible

Flash Rate: 125 fpm

IP56 rated

Operating temperature range: -30°C to +50°C

Magnetic versions are rated to 70mph



ENGLISH

**Note**

Lens must be purchased separately.  
DIN-mount stem only suitable for DIN mounting types.  
Large cage guard only suitable for Three-point mounting type.

**Approvals**

ECE65 where Amber or Blue lens are used

**Supplied with**

Bulb

**Specifications:**

For Use With

Xenon Bulb