



Nightlight

Nightlight 11W E27 220-250V P45 FR NL 1CT

Incandescent lamp applied as night light

PHILIPS
sense and simplicity

Product data

• General Characteristics

Cap-Base	ES [ES]
Cap-Base Information	Aluminium [Aluminium Cap]
Bulb	P45 [P 45mm]
Bulb Finish	Frosted
Burning Position	any [Any/Universal]
Main Application	Nightlight
Nominal Lifetime	2000 hr
Rated Lifetime (hours)	2000 hr
Rated Lifetime (years)	2 an

• Light Technical Characteristics

Colour Rendering Index	100 Ra8
Colour Temperature	2700 K
Lamp Luminous Flux	59 Lm
Rated Luminous Flux	59 Lm

• Electrical Characteristics

Rated Wattage	11.0 W
Lamp Wattage	11 W
Power Factor	1 -
Voltage	220-250 V
Dimmable	yes
Starting Time	0.0 s
Warm-up Time to 60% Light Outp	instant full light

• Environmental Characteristics

Energy Efficiency Label (EEL)	E
-------------------------------	---

Energy consumption kWh/1000h	11 kWh
------------------------------	--------

• Measuring Conditions

Switching cycle	8000X
-----------------	-------


• Product Dimensions

Overall Length C	71 (max) mm
Diameter D	45 (max) mm

• Product Data

Order code	949193 00
Full product code	872790094919300
Full product name	Nightlight 11W E27 220-250V P45 FR NL 1CT
Order product name	NightL 11W E27 220-250V P45 FR NL 1CT
Pieces per pack	1
Packing configuration	10X10F
Packs per outerbox	100
Bar code on pack - EAN1	8727900949193
Bar code on intermediate packing - EAN2	8727900949209
Bar code on outerbox - EAN3	8727900949216
Logistic code(s) - 12NC	921492543901
Net weight per piece	0.016 kg

Dimensional drawing



Nightlight 11W E27 220-250V P45 FR NL 1CT

Product	C (Max)	D (Norm)	D (Max)
NIGHTLIG 11W E27 220-250V P45 FR	71	-	45

Dimensional drawing



E27



© 2013 Koninklijke Philips Electronics N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com/lighting

2013, May 17
data subject to change