

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

- , - .



COPYRIGHT

-

BY TYCO ELECTRONICS CORPORATION.



ALL INTERNATIONAL RIGHTS RESERVED.

LOC

DIST


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	F	REDRAWN W/CHANGE	ECR-09-016911	30JUL09	TS KB




1. -A- 面より2mmの範囲で測定。
2. 相手ハウジングと所定の機能を満たして嵌合できること。
3. 適用リセプタクルコンタクト型番：170177, 170286
4. 適用製品規格番号：108-5093, 108-5099
5. 相手ハウジングとの嵌合力は29.4N (3Kg) 以下、
但し、コンタクトは含まない。

1. TO BE MEASURED WITHIN 2mm FROM -A-
2. IN COUPLING WITH THE PLUG HOUSING
MATING SATISFIES FUNCTION.
3. APPLIDE CONTACTPART NUMBER：170177, 170286
4. PRODUCT SPECIFICATION NUMBER：108-5093, 108-5099
5. IN COUPLING WITH THE PLUG HOUSING MATING FORCE
29.4N (3Kg) MAX. WITHOUT REC CONTACTS.



OBSOLETE	黄 / YELLOW	171354-7
OBSOLETE	灰 / GRAY	171354-6
	緑 / GREEN	171354-4
OBSOLETE	茶 / BROWN	171354-3
	黒 / BLACK	171354-2
	自然色 / NATURAL	171354-1
	色 / COLOR	型番 / PART NUMBER

GENERAL TOLERANCE	
10 ≥	: ±0.2
30 ≥ > 10	: ±0.25
100 ≥ > 30	: ±0.3
ANGLE	: ±3°

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T.SHINOHARA 30JUL09	 Tyco Electronics Corporation Kawasaki, Japan				
DIMENSIONS: mm		CHK K.BETSUI 30JUL09					
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -	APVD K.BETSUI 30JUL09	NAME MULTI-INTERLOCK CONNECTOR 17POSITION PLUG HOUSING				
		PRODUCT SPEC SEE NOTE 4					
		APPLICATION SPEC —					
		WEIGHT —					
MATERIAL 66 NYLON	FINISH —	CUSTOMER DRAWING		SIZE A3	CAGE CODE 00779	DRAWING NO C-171354	RESTRICTED TO —
				SCALE 2:1	SHEET 1 OF 1	REV F	