

EK EKHA 130 G



Sample photo

Order symbol: EKHA 130 G
Product nbr: 2538001
Description: Enclosure, PC
Remarks: Grey cover

EAN: 6418074013446
EI. number:
 Finland: 3425400
 Electric No. Italy: 7501010
 Electric No. Sweden: 2538001

Including: Flanged Base with screws for mounting plate, cover with PUR gasket and polyamide cover screws.

| Dimensions: | | | | Accessories: | |
|-------------------------------------|----------------------|-------|--------|---|-------------------------|
| | Length | Width | Height | | |
| mm: | 190 | 190 | 130 | EKHS | Base, PC |
| inch: | 7.5 | 7.5 | 5.1 | EKH 80-G | Cover |
| Materials: | | | | EKH 30-T | Cover |
| Material: | Polycarbonate | | | EKH 80-T | Cover |
| Base colour: | RAL 7035 -light grey | | | EKHVT | Mounting plate |
| Cover screws material: | Polyamide | | | EKHXT | Mounting plate isolated |
| Cover colour: | RAL 7035 -light grey | | | EKV 12 | DIN-35 Mounting rail |
| Cover screws colour: | Grey | | | Rating: | |
| Gasket material: | Polyurethane | | | Ingress Protection (EN 60529): IP66/IP67 | |
| Temperatures: | | | | Impact Resistance (EN 62262): IK08 | |
| Temperature °C (short term): | -40 ... 120 °C | | | Electrical insulation: Totally insulated | |
| Temperature °C (continuous): | -40 ... 80 °C | | | Halogen free (DIN/VDE 0472, Part 815): 1 | |
| Temperature °F (short term): | -40 ... 250 °F | | | UV resistance: UL 508 | |
| Temperature °F (continuous): | -40 ... 175 °F | | | Flammability Rating: UL 746C 5" | |
| Accessories: | | | | Glow Wire Test (IEC 695-2-1) °C: 960 | |
| EKHA | Base, PC | | | NEMA Class: NEMA 1, 3, 3S, 4, 4X, 6, 6P, 12 | |
| | | | | Certificates: | |
| | | | | SGS Fimko | |
| | | | | Gost R | |

