



PELITM
STORM CASETM



www.peliproducts.co.uk

Peli Storm Cases are rugged transit cases to hold and protect your valuables. Engineered for extreme conditions and wide ranging applications, Peli Storm cases are built from Pelican's patented HPX® high performance resin which makes them lightweight and virtually indestructible.

- 23 models to choose from
- Press & Pull latches open with the press of a button
- Impact resistant material
- O-ring sealed and watertight
- Vortex® valve automatically adjusts air pressure without letting in water
- Durable, wide, soft-grip handles
- Wheeled cases
- Withstands extreme temperatures
- iM2050 – iM2500 meets airline carry on regulations



Peli Storm Case Range

> SMALL CASES			> MEDIUM CASES				
iM2050	iM2075	iM2100	iM2200	iM2300	iM2306	iM2370	iM2400
> MEDIUM CASES				> LARGE CASES			
iM2450	iM2500	iM2600	iM2620	iM2700	iM2720		
> LARGE CASES							
iM2750	iM2875	iM2950	iM2975	iM3075			
> LARGE CASES							
iM3100	iM3200	iM3220	iM3300				

Wheeled Case



Press & Pull® Latches

These smooth-opening, dependable, patented latches hold tight under pressure and impact. Tested to over 180 Kg, they open with a simple release button.




Moulded-In Lockable Hasps

Twin mating hasp holes on the rim of the case allow attachment of padlocks to keep your gear in and thieves out. Peli's TSA (Travel Security Administration) cable padlock is a three digit combination lock. Works with a TSA pass key enabling access by inspectors (only in USA).



Rugged In-Line Wheels

Shielded from dust, dirt and other contaminants – ball bearing wheels provide low-friction, low-drag rolling with retractable handles for easy movement of heavy loads. Look for the  icon for availability on select models.



Vortex® Pressure Release Valve

The built-in technology of Peli Storm Cases automatic pressure equalisation valve is also a patented feature. This valve prevents vacuum lock allowing the case to be opened easily even after extreme altitude changes. At the same time, the microscopic filter blocks water molecules and dust particles so your gear stays clean and dry.



Double-Layer, Soft-Grip Handles

An overmoulded layer grips to the polymer handle for a durable, comfortable non-slip grip.

Specifications, Features and Options

Model	Interior Dimensions Total (mm)	Lid/Base Depth (mm)	Exterior Dimensions (mm)	Weight w/f (kg)	Colours	Padded Dividers	Base Bezel Kit	Lid Bezel Kit	Lid Organiser	Foam Sets	Telescopic Handle	Wheels
iM2050	241 x 190 x 108	38/70	300 x 249 x 119	1.36	■ ■ ■	0	0			P		
iM2075	241 x 190 x 184	38/146	300 x 249 x 196	1.68	■ ■ ■	0	0			P		
iM2100	330 x 234 x 152	51/101	361 x 289 x 165	2.22	■ ■ ■	0	0			P		
iM2200	381 x 267 x 152	51/101	411 x 322 x 168	2.77	■ ■ ■	0	0	0		P		
iM2300	432 x 297 x 157	51/106	462 x 340 x 170	3.22	■ ■ ■	0	0	0	0	P		
iM2306	432 x 160 x 157	51/106	462 x 213 x 170	2.13	■ ■ ■	0	0	0		P		
iM2370	462 x 307 x 132	43/89	508 x 373 x 147	3.27	■ ■ ■	0			0			
iM2370 CC1	includes laptop tray in base, lid organiser & shoulder strap		508 x 373 x 147	3.50	■ ■ ■				S			
iM2400	457 x 330 x 170	51/119	487 x 386 x 185	3.54	■ ■ ■	0	0	0	0	P		
iM2450	457 x 330 x 213	51/162	487 x 386 x 229	4.04	■ ■ ■	0	0	0	0	P		
iM2500	520 x 292 x 183	51/132	551 x 358 x 226	6.21	■ ■ ■	0	0	0	0	P	S	S
iM2600	508 x 355 x 196	51/145	538 x 406 x 211	5.26	■ ■ ■	0	0	0	0	P		
iM2620	508 x 355 x 254	51/203	538 x 406 x 269	6.58	■ ■ ■	0	0	0	0	P	S	S
iM2700	559 x 432 x 203	51/152	625 x 500 x 218	6.53	■ ■ ■	0	0	0	0	P		
iM2720	559 x 432 x 254	51/203	625 x 500 x 297	9.98	■ ■ ■	0	0	0	0	P	S	S
iM2750	559 x 432 x 322	51/271	625 x 500 x 366	10.61	■ ■ ■	0	0	0	0	P	S	S
iM2875	571 x 536 x 289	51/238	632 x 602 x 333	11.16	■ ■ ■	0	0	0	0	P	S	S
iM2950	736 x 457 x 267	51/216	795 x 518 x 310	13.02	■ ■ ■	0	0	0	0	P	S	S
iM2975	736 x 457 x 350	51/299	795 x 518 x 394	13.38	■ ■ ■	0	0	0	0	P	S	S
iM3075	757 x 528 x 452	102/350	845 x 620 x 490	20.41	■ ■ ■	0	0	0	0	P	S	S
iM3100	927 x 355 x 152	51/101	1011 x 419 x 170	8.98	■ ■ ■					SD		S
iM3200	1117 x 355 x 152	51/101	1198 x 419 x 170	9.57	■ ■ ■					SD		S
iM3220	1117 x 355 x 216	51/165	1198 x 419 x 234	11.25	■ ■ ■					SD		S
iM3300	1282 x 355 x 152	51/101	1366 x 419 x 170	10.43	■ ■ ■					SD		S

0 = Optional S = Standard SD = Solid P = Pick N Pluck