



(UK) Limited

Mastercheck 3.2 Voltage Tester



Technical Specifications

- Voltage Range: 6-400V AC/DC
- Voltage Indication: LED Display
- Input Resistance: 265 K Ohm
- Input Current: <2.5Ma At 400V
- Frequency Range: 0-100Hz (AC > 2Hz)
- Peak Current Resistance: 6Kv
- Continuity Testing: <500 K Ohm
- Enclosure: IP50
- Ambient Temperature: -10 - +55 Degrees Centigrade
- Battery Type: 2 x 1.5V AAA
- Battery Capacity: 1500 Operations
- Tested And Approved In Accordance To EN 61243-3 & VDE 0682 Part 401