



Jupiter A3

Ref: 5701801



- Suitable for frequent use in an office environment
- LED user interface makes using the laminator easy
- Entry width 330mm - laminates up to A3 size paper
- Ready to laminate in 4 minutes
- 5 temperature settings for a variety of lamination applications
- Audio and visual indicators clearly signal when ready to laminate
- Front flap serves as document guide and dust cover
- Laminates 1 sheet of A3 paper in 45 seconds (48cm per min)
- Manual reverse function ensures safe operation at all times
- HeatGuard™ reduces the surface temperature by up to 50%, ensuring laminator is always safe to touch.
- Unique "Easi-Access" system enables users to clean the rollers ensuring continuous lamination quality
- Side carry handles for easy transportation
- Active cooling system enables rapid shifts from hot to cooler settings
- Auto shut-off to ensure safe operation
- Starter kit for 10 documents included
- Suitable for Fellowes Enhance80, Impress100, Capture125 and Protect175 pouches

Product Features

Item Number	5701801
Usage	Heavy
Pouch Thickness (mic)	80-175 microns
Warm-up Time	4 minutes
Entry Width	330mm
Temperature Settings	5
Photo Capable	Yes
Adjustable Speed	No
Mounting Board Capable	No
Cold Lamination	Yes
Carrier Required	No
Number of Rollers	4
Item Weight (kgs)	6.76
Retail Pack Dimensions H x W x D (mm)	314.00 x 624.00 x 202.00
Units per Master Carton	1
Retail Pack Weight (kg)	8.18
SCS	50043859511124
UPC Code	043859511129
EAN Code	043859511129