

Magnetic label - PMM (EX25)R - 1014306

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Magnetic label, Roll, white, unlabeled, can be labeled with: THERMOMARK ROLL, THERMOMARK X, Mounting type: Magnetic adhesion, Lettering field: 15000 x 25 mm

Why buy this product

- Magnetic labels, unprinted
- The magnetic labels supplied in rolls represent an individual and flexible marking solution, e.g., for warehouse marking.
- High adhesive strength
- The flexible magnetic tape will also adhere to round objects with a radius from 12 mm
- Magnetic tape coated with polyester foil



Key commercial data

| | |
|--------------------------------------|---|
| Packing unit | 1 pc |
| GTIN |  4 046356 786102 |
| Weight per Piece (excluding packing) | 99.99 g |
| Custom tariff number | 39207380 |
| Country of origin | Germany |

Technical data

Dimensions

| | |
|------------|----------|
| Length (b) | 15000 mm |
| Width (a) | 25 mm |

Ambient conditions

| | |
|---------------------------------|------------------|
| Ambient temperature (operation) | -30 °C ... 55 °C |
|---------------------------------|------------------|

General

| | |
|-------------------------------------|-----------------------------|
| Color | white |
| Material | Magnetic tape |
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
| Number of individual labels | 1 |
| Number of individual labels per row | 1 |

Magnetic label - PMM (EX25)R - 1014306

Technical data

General

| | |
|-----------------------|-------------------|
| Marking mounting type | Magnetic adhesion |
|-----------------------|-------------------|

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.0 | 27141199 |
| eCl@ss 4.1 | 27141199 |
| eCl@ss 5.0 | 27371301 |
| eCl@ss 5.1 | 27371301 |
| eCl@ss 6.0 | 27371301 |
| eCl@ss 7.0 | 27371301 |
| eCl@ss 8.0 | 27141137 |

ETIM

| | |
|----------|----------|
| ETIM 3.0 | EC000712 |
| ETIM 4.0 | EC002498 |
| ETIM 5.0 | EC001777 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 43172501 |
| UNSPSC 7.0901 | 43212107 |
| UNSPSC 11 | 43172501 |
| UNSPSC 12.01 | 43212107 |
| UNSPSC 13.2 | 43212107 |

Accessories

Accessories

Ink ribbon

Ink ribbon - THERMOMARK-RIBBON 110 - 5145384



Ink ribbon, Length: 300000 mm, Width: 110 mm, Color: black