




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
J	—		F	REDRAWN W/CHANGE	ECR-09-016911	30JUL09	TS KB



1. -A- 面より2mmの範囲で測定。
2. 相手ハウジングと所定の機能を満たして嵌合できること。
3. 適用リセプタクルコンタクト型番：170177, 170286
4. 適用製品規格番号：108-5093, 108-5099
5. 相手ハウジングとの嵌合力は29.4N (3Kg) 以下、
但し、コンタクトは含まない。
1. TO BE MEASURED WITHIN 2mm FROM -A-
2. IN COUPLING WITH THE PLUG HOUSING
MATING SATISFIES FUNCTION.
3. APPLIDE CONTACTPART NUMBER：170177, 170286
4. PRODUCT SPECIFICATION NUMBER：108-5093, 108-5099
5. IN COUPLING WITH THE PLUG HOUSING MATING FORCE
29.4N (3Kg) MAX. WITHOUT REC CONTACTS.



OBSOLETE	青 / BLUE	172025-5
	緑 / GREEN	172025-4
OBSOLETE	茶 / BROWN	172025-3
	黒 / BLACK	172025-2
	自然色 / NATURAL	172025-1
	色 / COLOR	型番 / PART NUMBER

GENERAL TOLERANCE	
10 ≥	: ±0.2
30 ≥ > 10	: ±0.25
100 ≥ > 30	: ±0.3
ANGLE	: ±3°

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T.SHINOHARA 30JUL09	Tyco Electronics Corporation Kawasaki, Japan			
DIMENSIONS: mm		CHK K.BETSUI 30JUL09				
		APVD K.BETSUI 30JUL09	NAME MULTI-INTERLOCK CONNECTOR 7POSITION PLUG HOUSING			
		PRODUCT SPEC SEE NOTE 4				
MATERIAL 66 NYLON		APPLICATION SPEC —	SIZE A3		CAGE CODE 00779	DRAWING NO C-172025
		FINISH —	WEIGHT —		RESTRICTED TO —	
CUSTOMER DRAWING			SCALE 2:1	SHEET 1 OF 1	REV F	