

# Specifications for BMP41/BMP51/BMP53 Labelmaker Tape

<b>Adhesive</b>	Permanent Acrylic
<b>Application</b>	Indoor & Outdoor Grade Facility & Safety Identification; Voice & Data Communication
<b>Article No.</b>	131583
<b>Brady Material No.</b>	<a href="#">B-595</a>
<b>Material Type</b>	Vinyl
<b>Colour</b>	Black on Yellow
<b>Finish</b>	Gloss
<b>Laboratory Application</b>	Well Plates;General Identification
<b>Max. Service Temp. °C</b>	82
<b>Order Reference</b>	MC1-1000-595-YL-BK
<b>Printer Compatibility</b>	BMP41; BMP51; BMP53
<b>Shape</b>	Continuous
<b>Size - Length (m)</b>	7.62
<b>Size - Width (mm)</b>	25.40
<b>Additional Information</b>	Adhesive Stick on Strips, Cut to Size
<b>Total Qty per Pack</b>	1 Cartridge / Box
<b>Voice/Data Application</b>	Data Centre Equipment; Bay, Rack & Frame Labels
<b>Industry</b>	Data & Telecommunications; Facility & Safety Industry; Process
<b>Min. Application Temp. °C</b>	-18
<b>Min. Service Temp. °C</b>	-40
<b>QTY. per Row</b>	1
<b>Thickness (mm)</b>	0.1