

## Datasheet

# RS Pro Feed Through Terminal Block, CTS series, 16mm<sup>2</sup>, 1000 V, 76A, Screw Clamp Termination, Brown, Single Level

RS Stock No: **796-1025**



## Product Details

RS Pro feed through terminal block in brown colour, has 1000 V voltage rating and 76 A current rating. This single level, screw clamp termination system has marker holding recesses to accept marking tags for circuit identification and is suitable for 16 mm<sup>2</sup> wires. This block makes cross connection easy with the aid of shorting links/sleeves and screws. It is suitable for control, automation, instrumentation and power distribution applications.

## Features and Benefits

- Rated voltage 1000 V
- Marker holding recesses to accept marking tags for circuit identification
- Wire entry orientation side entry
- Suitable for control, automation, instrumentation and power distribution applications

**Specifications:**

Cable CSA	16 mm <sup>2</sup>
Colour	Brown
Current Rating	76 A
Maximum Operating Temperature	+85°C
Minimum Operating Temperature	-40°C
Number of Levels	Single
Termination Method	Screw Clamp
Voltage Rating	1000 V
Wire Size	20 to 4 AWG
Standards Met	RoHS Compliant