











TABLE 2


ALL HARDWARE IS 4-40, ALL SCREWS AND THUMB SCREWS ARE CAPTIVE. THE JACK NUT IS NOT CAPTIVE AND THIS ITEM CAN BE THREADED INTO THE HOUSING, OR THE HOLE CAN BE ENLARGED.



SECTION A-A



TOP AND BOTTOM
COVER PART NUMBER
SEE TABLE 1




PCB AND CONNECTORS
NOT SUPPLIED


SEE NOTE 3

NOTES:

1. ACTUAL PCB LENGTH IS A PRODUCT OF THE CONNECTORS SELECTED.
2. DIM "G" IS TOP AND BOTTOM COVER INSERT AREA X 1.450 [36,83] WIDE.
3. HARDWARE TO BE ORDERED SEPARATE FROM TABLE 2 PER CUSTOMER SPECIFIC REQUIREMENTS.



SECTION B-B



SECTION C-C




TABLE 1

CN SIZE	S	M	L
PART NUMBER	CNS-0103	CNM-0103	CNL-0103
DIM D PCB SIZE	1.706 [43,33]	2.206 [56,03]	2.706 [68,73]
DIM E OVERALL SIZE	2.724 [69,19]	3.234 [82,14]	3.724 [94,59]
DIM F MAX CRITICAL DIM	2.632 [66,85]	3.123 [79,32]	3.623 [84,40]
2X DIM G INSERT AREA	1.500 [38,10]	2.000 [50,80]	2.500 [63,50]

DB9 STRAIGHT CONNECTOR TO
DB25 STRAIGHT CONNECTOR

PACINTEC®
1-610-361-4200

CN-0103-SERIES
SEE TABLE 1

VISIT **PACINTEC®**
ON THE WORLD WIDE WEB
www.pactecenclosures.com

COLOR / MATERIAL CODE		
COLOR	94HB	94VO
BLACK	000	028
P.C.BONE	039	060

DRAWING NUMBER	REV
79578	A