






FEMALE END VIEW	PCB LAYOUT	SPECIFICATIONS	
 		CONTACT CARRIER MATERIAL	NYLON OR TPU
		CONTACT MATERIAL/PLATING	BRASS/GOLD
		HOUSING AND NUT MATERIAL/PLATING	BRASS/NICKEL
		RATED CURRENT [A]	4.0 A
		RATED VOLTAGE [V]	30 V
		TEMPERATURE RANGE	-25°C to +85°C (-13°F to +185°F)
		PROTECTION CLASS	MEETS NEMA IEC IP67



END VIEW
LOCK NUT NOT SHOWN
FOR CLARITY



SOURCE DRAWING - FOR REFERENCE ONLY

					RELATED DOCUMENTS		3RD ANGLE PROJECTION		THIS DRAWING IS PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED. TURCK INC High Technology Sensors and Automation Controls		3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax turck.com				
					1. 2. 3. 4.										
					MATERIAL				DRFT		RDS	DATE	04/29/03	DESCRIPTION MFKS 4F-PCBF	
					SEE SPECIFICATIONS				DSGN		SCALE		1=.5		
					FINISH		ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY		UNIT OF MEASUREMENT MILLIMETER [INCH]		IDENTIFICATION NO.		REV		
					SEE SPECIFICATIONS						CONTACT TURCK FOR MORE INFORMATION		U0884-04		F
F	DRAWING PROCESSED AS PART OF ECO 33971			CBM	04/07/11	33971	DO NOT SCALE THIS DRAWING		FILE: U0884-04		SHEET 1 OF 1				
REV	DESCRIPTION			BY	DATE	ECO NO.									