





METRIC

單位耗 DIMENSIONS IN MM. DO NOT SCALE PRINT

PRINT DIST



NOTE



1 MATERIAL:GLASS FIELD THERMO PLASTIC,POLYESTER
COLOR:BLACK

~~2 TO COAT ALL SURFACE OF HOUSING WITH TEFLON~~

注記

1 材料: ガラス入り熱可塑性ポリエステル樹脂
色: 黒色


△2 ハウジング全面にテフロン塗装のこと



CIRCUIT NO. 回路番号

B3	REVISED PER ECO-11-005030	RK	HMR
LTR	変更 (REVISION RECORD)	DR	CHK

		20	62.86	59.66	54.8	45.72	9	1-917659-8
OBSOLETE		↑	↑	↑	↑	↑	↑	7-917659-6
OBSOLETE								6-917659-6
OBSOLETE								5-917659-6
								3-917659-6
								2-917659-6
		12	42.54	39.34	34.48	25.4	5	1-917659-6
OBSOLETE		10	37.46	34.26	29.4	20.32	4	7-917659-5
		↑	↑	↑	↑	↑	↑	3-917659-5
								2-917659-5
		10	37.46	34.26	29.4	20.32	4	1-917659-5
	FINISH	POS.	A	B	C	D	N	PART NUMBER

		FINISH	POS.	A	B	C	D	N	PART NUMBER
						 TE Connectivity			
拾合電線断面(WIRE RANGE)  mm ² (AWG -)		被覆外径(INSULATION DIA.)  mmφ		名称(NAME) ダイナミック D3200 リセハウジング DYNAMIC D3200 REC HSG (DOUBLE ROW)					
材料(MATERIAL) 注記参照 SEE NOTE		仕上(FINISH) 		一般公差 (GENERAL TOLERANCE)		LOC 番号(No.)		917659	
DR. 14/APR/95 K.IKEDA		DE. 14/APR/95 K.IKEDA		10以下 : ±0.2 10を超え 30以下 : ±0.25 30を超え 100以下 : ±0.3 角 度 : ±3°		A3 J 尺 度(SCALE) 2-1		REV. B3 SHEET 1 OF 1	
CHK. 18/APR/96 S. MARABE		APP. 18/APR/96 S. MARABE							