




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
J	—		F1	REVISED PER ECO-11-005301	07MAR11	RK	HMR






1. MATING PART NO.; 176143
2. THIS PRODUCT CONSISTS OF A PLUG HOUSING, A SEAL RING AND A KEYING
3. PRODUCT SPECIFICATION; 108-5294
APPLICATION SPECIFICATION; 114-5126
CUSTOMER MANUAL; 412-5488
4. APPLIED CONTACTS

RECEPTACLE	CONTACT	P/N	WIRE RANGE (mm ²)	INSULATION DIA
		175090	0.5~1.25	ø2.0~ø2.6
		175091	2~3	ø2.9~ø3.8

1. 嵌合相手品番：176143
2. 本製品はプラグハウジングとキーイング、シールリングから構成されている。
3. 製品規格：108-5294
圧着規格：114-5126
取扱説明書：412-5488
4. 適用端子型番

リセプタクルコンタクト P/N	ワイヤーレンジ (mm ²)	被覆外径
175090	0.5~1.25	ø2.0~ø2.6
175091	2~3	ø2.9~ø3.8



黒 BLACK	淡灰 LIGHT GRAY	淡灰 LIGHT GRAY	6-176146-6
	濃灰 DARK GRAY	濃灰 DARK GRAY	176146-6
	黒 BLACK	黒 BLACK	176146-2
SEAL RING COLOR シールリング色	KEYING COLOR キーイング色	HOUSING COLOR ハウジング色	PARTS NO. 型番

WIRE RANGE SEE TABLE	THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Y.KINOSHITA 12NOV91	TE Connectivity			
INSULATION DIA SEE TABLE	DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED	CHK Y.KINOSHITA 12NOV91				
TOLERANCE UNLESS OTHERWISE SPECIFIED: 一般公差 0 < ≤ 10 : ±0.2 10 < ≤ 30 : ±0.25 30 < ≤ 100 : ±0.3 ANGLE : ±3° 角度		0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± FINISH	APVD S.ISOHATA 12NOV91	NAME			
			PRODUCT SPEC 108-5294	187 SERIES SEALED CONNECTOR 2POSITION PLUG HOUSING ASSY			
			APPLICATION SPEC 114-5126				
	MATERIAL PBT	SEE TABLE	WEIGHT 8.0 g	SIZE A2	CAGE CODE 00779	DRAWING NO C=176146	RESTRICTED TO —
CUSTOMER DRAWING				SCALE 2:1	SHEET 1 of 1	REV F1	