







DO NOT SCALE
DIMENSIONS IN mm

METRIC



NOTES:

- 1 MATERIAL DESCRIPTION : POCAN B4225. BLUE 5/378 COLOR.
- 2 AMP TRADEMARK.
- 3 MOLD CAVITY IDENTIFICATION NO. 0,1-0,5 RAISED CHAR.'S IN RECESSED AREA 0,2 DEEP.
- 4 TO DETERMINE DIMENSIONS TAKE $N = \text{NR. OF POSITIONS}$.
FOR EXAMPLE: 10 POS.: $N \times 2,54 = 25,40$.
FOR ORDERNR.: USE BASIC NR. + NR. OF POS.
FOR EXAMPLE 2x2 POS.: 0-281838-2 (SHORTEST VERSION).
2x18 POS.: 1-281838-8 (LONGEST VERSION).
- 5 TOLERANCES NOT ACCORDING TO IEC 603-8 SPEC..



-	-	-	-	-	CUSTOMER DRAWING		FOR REFERENCE ONLY WILL NOT BE UPDATED
-	-	-	-	-	© COPYRIGHT 19- BY AMP HOLLAND B.V.		
-	-	-	-	-	ALL INTERNATIONAL RIGHTS RESERVED. AMP PRODUCTS MAY BE		
-	-	-	-	-	COVERED BY U.S. AND FOREIGN AND/OR PATENTS PENDING.		
-	-	-	-	-	THIS DRAWING IS UNPUBLISHED		
-	-	-	-	-	RELEASED FOR PUBLICATION		
-	-	-	-	-	TO		
-	-	-	-	-	AMP HOLLAND B.V.		
-	-	-	-	-	's-Hertogenbosch,		
-	-	-	-	-	The Netherlands.		
NAME					DOUBLE ROW HOUSING FOR		
A EH-0394-97					HE 13-14 COSI CONTACT		
LTR.	REVISION RECORD		DR.	CHK.	DATE		
DR.	J. V. LIEMPT	CHK.	B. BROUW	APP.	E. L. J. TEN	DWG. No.	
DATE:	16 APR 97	DATE:	24 OCT 97	DATE:	24 OCT 97	C-281839	
					REV.	LTR.	SHEET
					A	1 OF 1	A3