





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
A1	—	E1		text for packaging corrected	ECR-08-001868	23.01.08	SR ST
		E2		REVISED PER ECO-11-002591		17FEB11	HMR MM




Contact arrangement view from termination side


Printing 1-24 Thermo




Printing 1-24 Screw



Printing 25-48 Screw




Printing 12+6+6 Screw/Thermo




Contact arrangement view from termination side


Printing 1-24




Printing 25-48



Panel cut-out for contact insert when used without housing



assembly directions



× distance for a safe
contact max: max: 21 mm

NOTES:

- SUITABLE CRIMP CONTACTS: SERIES HE/HA
OUTER DIMENSIONS OF INSULATION: MAX. Ø3,2 MM
- SUITABLE HOOD SIZE 8; 12: SERIES HB; HD; HIP; EMV
SUITABLE INSERTION AND EXTRACTION TOOL:
SCREWDRIVER 0,5x3 DIN 5264
- Strip lenght: Screw conection 10mm
Spring clamp conection 10mm Crimp conection 7.5mm
- STANDARDS:
DIN EN 61984; DIN EN 60664-1

5 PACKAGING:
5 SETS IN A CARTON, PRE-MOUNTED

6 SPECIAL PACKAGING: Krauss-Maffei
PACKAGING UNIT: 220 PIECES

1							1			Socket contact		light grey	5	earth wire contact with drillings Ø3,3 / without fixing screws
	1				1	1				Deckel Federklemmversion		light grey	4	
							1	1		Crimp Crimp version		light grey	3	
1		1	1	1				1	1	Cover screw version		light grey	2	
1	1	1	1	1	1	1	1	1	1	Buchseneinsatz		light grey	1	
0-10	-29	-31	-89	-49	-57	-97	-12	-92	-31	-91	-1			
ORDERING TEXT / BESTELLTEXT											DESCRIPTION / BENENNUNG	MATERIAL	COLOR / FARBE	ITEM NO. POS.
THIS DRAWING IS A CONTROLLED DOCUMENT.											DWN Schneider 08.02.2000	Tyco Electronics Corporation Harrisburg, Pa 17105-3608		
DIMENSIONS: mm											CHK Schweiger 08.02.2000			
TOLERANCES UNLESS OTHERWISE SPECIFIED: GENERAL TOLERANCES n ISO 8015 n ISO 2768 - mH - E n DIN 16901 - 140											APVD —	NAME Female insert HE.24.BU.S/C		
0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± — ANGLES ± —											PRODUCT SPEC —			
MATERIAL —											APPLICATION SPEC —	SIZE A2	CAGE CODE 00779	DRAWING NO C=1103641
FINISH —											WEIGHT —	SCALE 1:1	SHEET 1 OF 1	REV E2
CUSTOMER DRAWING														