

# Extra-Hard Use (EHU) Specification Grade Plug, Corrosion- Resistant, Yellow & White

CR5266X



Straight Blade Plug 2pole 3wire 15amp  
125volt Corrosion Resistant



## features & benefits

- Unit arrives completely ready-to-wire, cuts installation time significantly.
- Nylon housing provides impact and chemical resistance.
- Rugged two-piece cord grip provides more uniform cord retention.
- Internal dust shield keeps terminals free of contaminants.
- Tri-drive assembly screws are standard on all Specification Grade plugs and connectors.
- All 3-wire terminals located on the same plane, allows for quick wire termination from any angle.
- Heavy-duty brass alloy blades and contacts, resist heat rise, provide excellent conductivity.
- Cord-grip screws recessed to protect installer against screwdriver head slippage.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## specifications

### General Info

Color: yellow  
Type: Corrosion resistant

### Listing Agencies/Third Party Information

CSA Listing Info: No  
CUL Listing No: No

cULus: Yes  
cURus: No  
Federal Spec: No  
UL Listing No: No  
UN SPS C: 39121402  
UR: No

**Dimensions**

Depth U S: 0  
Weight: 0.14588

**Technical Information**

Volts A C: 125  
Grade Type: Specification

**Buy American Act Compliance**

Country of Origin: MEXICO  
Buy American Act Status: Trade Agreement Act Compliant