





LOC		DIST		REVISIONS				DATE		APPD	
CM		53		P	F	ZONE	LTR	DESCRIPTION			
								D		REV PER EC 061B-0103-98	
								6-11-98		JH	
										R5	



- 1 0.00076 [.000030] MIN GOLD IN LOCALIZED GOLD PLATE AREA OVER 0.00127 [.000050] MIN NICKEL.
- 2 WIRE RANGE: 0.5-2mm² (20-14 AWG).
- 3 INSULATION RANGE: 3.56 [.140] MAX. DIA.
- 4 DIMENSIONS IN BRACKETS ARE IN INCHES.




SECTION A-A
SCALE 10:1



SECTION B-B
SCALE 10:1



SECTION C-C
SCALE 10:1



SECTION D-D
SCALE 10:1

METRIC

		▲		0.25 [.010] BRASS		770145-5	
		PRE-TIN		0.25 [.010] BRASS		770145-1	
		FINISH		MATERIAL		PART NO	
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON : 2 PLC DEC ± 0.13[.005] 3 PLC DEC ± - ANGLES ± - MATERIAL SEE TABLE		DR 11-2-93 R. VESTAL		AMP AMP INCORPORATED Harrisburg, Pa. 17105			
		CHK 11-2-93 R. SWING					
		APPD 11-2-93 C. CASH					
		APPD 11-2-93 C. CASH		NAME PIN, .093, LOOSE PIECE, COMMERICAL PIN AND SOCKET			
FINISH SEE TABLE		PRODUCT SPEC -		SIZE D 00779			
		APPLICATION SPEC -		FSCM NO		DRAWING NO	
		WEIGHT		5:1		770145	
						SHEET 1 OF 1	