

Datasheet

RS 4 Core Screened Industrial Cable, PVC Sheath, 7.3mm OD, 0.5 mm² CSA 2.5 A, 300 V, 100m

Stock Number - 660-0489



Description:

Rated Temperature (oC): -20 ~ 80

Rated Voltage (V):300

Flammability Test: IEC60332-1



ENGLISH

Construction:

Conductor: Tinned Copper
Conductor Dia. (mm): 0.20±0.008 x 16
Insulation: PVC
Insulation Dia. (mm): 1.8±0.05 x 4C
Tape: Mylar Spiral
Coverage: ≥115%
Braid Shield : Tinned Copper
Conductor Dia. (mm): 0.20
Conductor Qty: 16x6
Pitch(mm):
Coverage : 91%
ID Thread : Green, White/Green
A rip cord : 210 D
Jacket: FR-PVC
Outer Dia. (mm): 7.3±0.2

Colour:

The colour of the insulation: Red , Blue
, Green , Yellow
The jacket colour: Black
Marking(3times/m):
RS 6600489 16 - 2 - 4C

Performance:**Electrical Characteristics:**

Max.Conductor DC Resistance at 20°C (Ω /Km) :
<37.7

Min.Insulation DC Resistance at 20°C ($M\Omega$ *KM) :
>200

Current Rating : 2.5 A

