

Datasheet

## RS Pro Straight 50Ω Coaxial Adapter TNC Socket to MMCX 0 to 5GHz

RS Stock No: **793-3639**



### Product Details

RS Pro straight TNC socket to MMCX coaxial adapter comes with waterproof IP68 inner sealing against gas and moisture ingress between insulators, inner and outer conductors and connector body and panel sealing between the connector body and panel mounting hole. This waterproof RF coaxial TNC jack to MMCX jack adapter has a nickel plated brass body, PTFE insulator, silicone 'O' rings and a gold plated centre contact.

### Features and Benefits

- TNC socket to MMCX coaxial adapter
- Nickel plated brass body, silicone 'O' rings and a gold plated centre contact
- 50Ω impedance

**Specifications:**

Adapter Type A	TNC
Adapter Type B	MMCX
Adapter Type	TNC Socket to MMCX Socket
Body Orientation	Straight
Body Plating	White Bronze
Contact Material	Beryllium Copper
Contact Plating	Gold
Gender A	Socket
Gender B	Socket
Impedance	50 $\Omega$
Length	24 mm
Operating Frequency	0 to 5 GHz
Body Material	Brass
Insulation Material	PTFE
Operating Temperature	-55 to +155°C
Voltage Rating	170 V