

# 805-0992 T120R0UVC2

Cable Tie, 120 lb., 15.24", Max. Bun. Dia. 4.13" , PA66UV Stabilized, Black, 100/pk

Article Number: 111-00400

Part Number: T120R0UVC2

Type: T120R



## Base Data

---

<b>Part No.</b>	T120R0UVC2
<b>Type</b>	T120R
<b>Color</b>	Black
<b>Features</b>	HellermannTyton offers cable ties made of PA66UV stabilized material. This provides additional protection against UV radiation for long term outdoor use and is available in various tensile strengths and bundle diameters.
<b>Application</b>	Used to bundle and secure wire and cable.
<b>Application Method</b>	Quick, simple fixing by hand or with HellermannTyton tensioning tools
<b>Identification Plate Position</b>	none
<b>Releasable Closure (Yes/No)</b>	No

**Tie Closure** plastic pawl

**Variant** Inside Serrated

### Product Dimensions

---

**Min. Tensile Strength** 120 lbs / 535 N

**Length (L)** 15.24 " / 387 mm

**Width (W)** 0.30 " / 7.6 mm

**Min. Ø Bundle** 0.12 " / 3.0 mm

**Max. Ø Bundle** 3.94 " / 100 mm

**Thickness** 1.8 mm

### Material and Specifications

---

**Material** Polyamide 6.6 UV-stabilized (PA66UV)

**Certification** MIL 53421

**CSA Certified** No

**Flammability** UL94 V2

**Material Specification** HF / RoHS

**Operating Temperature** -40 °C to +85 °C, intermittent +105 °C (for 500 h)

**ROHS Conformity**  RoHS

**UL Listed (US and Canada)** No

**UL Recognized (US  
and Canada)**

No