

**MODEL NO.: 04000**

**DESCRIPTION: Silverline Automotive Kit**

**PRODUCT AND PACKAGING SPECIFICATIONS:**

Pump Displacement:	1 in <sup>3</sup> (16cc) per stroke
Maximum Vacuum:	25 in Hg (85 kPa)
Maximum Pressure:	30+ psi (207+ kPa)
Packaged Weight:	3.3 lbs. (1.5 kg)
Unit Carton Qty:	1
Unit Carton Size:	12" (305 mm) x 8" (205 mm) x 3.4" (85 mm)
Unit Carton Type:	Blow molded case w/ graphics sleeve
Master Carton Qty:	10
Master Carton Size:	17.5" (445 mm) x 12.3" (310 mm) x 16.3" (10 mm)
Master Carton Weight:	36.5 lbs (16.6 kg)
Country of Origin:	USA
Languages:	English, Spanish, French, German
UPC Code:	6 46541 00039 2
SCC Code:	10646541000399
Harmonization Code:	8414100000
Service Parts Available:	Yes
CE Certified:	Yes
Patents:	5,362,214; 5,217,354



**APPLICATIONS:**

- Vacuum & pressure related engine performance diagnostics and tune-ups
- Brake bleeding
- Fluid transfer, evacuation, and sampling

**KEY FEATURES:**

- Includes everything for performing hundreds of automotive diagnostic and mechanical tests, and for one-person brake bleeding
- Patented one-finger trigger vacuum release
- Includes vacuum and pressure ports
- Diecast metal construction

**INCLUDES:**

- *Silverline* hand vacuum/pressure pump w/ 2" (50mm) diameter gauge w/ rubber boot
- 4.5 oz (135 ml) fluid reservoir w/ transfer lid, storage lid, and fluid pick-up tube
- (7) Tapered tube adapters
- (3) Bleed screw adapters
- (3) Connection tubes
- (2) Tapered manifold plugs
- (2) ¼" ID x 24" long (6.4 mm ID x 610 mm long) fluid transfer tubes
- Rubber cup adapter
- User Manual (English, French, Spanish, German)