

TradeMaster Decorator Duplex Receptacle, Ivory

885I



Sierraplex Receptacle, 15amp 125volt,
Screw Terminal & Speedwire, Ivory

features & benefits

- High impact-resistant thermoplastic construction.
- Extra-long strap.
- Quickloop wire looping aid.
- Long-term blade retention.
- Tri-drive screws.
- Extra-large circuit break-off tabs.
- Side-access push wire release.
- Ultrasonic welding of face to back body.
- Side wire accepts #12 - #14 AWG solid.
- Push wire accepts #14 AWG solid only.
- Self-grounding models provide automatic ground clip.

specifications

General Info

Color: Ivory
Number Of Poles: 2
Number Of Wires: 3

Listing Agencies/Third Party Information

CSA Listing Info: C22.2 No.42
CSA Standard: Yes
Federal Spec: No
UL Listing No: UL498
UL Standard: Yes

UN SPS C: 39121704

Dimensions

Depth U S: 1"
Height U S: 3.31"
Width U S: 1.29"

Technical Information

Amps: 15
Volts: 125
Volts A C: 125

Buy American Act Compliance

Country of Origin: CHINA
Buy American Act Status: No