





HOW TO ORDER:	9 POS.-----> PREFIX FOR ACCESSORIES BASIC PARTNR. SUFFIX FOR PLATING Z-338309-Y	1-XXXXXX-Y 2-XXXXXX-Y 3-XXXXXX-Y 4-XXXXXX-Y 5-XXXXXX-Y 6-XXXXXX-Y 7-XXXXXX-Y 8-XXXXXX-Y 9-XXXXXX-Y
----------------------	---	---

PLATING SUFFIX "Y"		
	GOLD OVER NICKEL AS PER PERFORMANCE LEVEL 2 (DIN 41652) SOLDERPART: 2,5µm Sn.	$\left. \begin{array}{c} \text{ } \\ \text{ } \end{array} \right\} -Y = -2$
	- - -	$\left. \begin{array}{c} \text{ } \\ \text{ } \end{array} \right\} -$

- 1 GROOVE INDICATES VERSION WITH 4-40 UNC INNER THREAD;
WITHOUT GROOVE INDICATES VERSION WITH M3 INNER THREAD.
- 2 CAVITY IDENTIFICATION AT FRONT SIDE ONLY.
- 3 PARTNUMBER AND DATE CODE.
- 4 WHEN BOARDLOCKS ARE USED, CONNECTOR CAN BE USED
FOR PCB THICKNESS OF 1,6 mm ONLY.
- 5 SHELL HAS 2x2 GROUNDING SPRINGS; PITCH IS 3,6 mm
- 6 AIR AND CREEPAGE DISTANCES ACCORDING TO DIN41652

ITEM NRS./MATERIAL :

- | | |
|--------------------|---|
| ① SHELL | : BRIGHT TINPLATED STEEL |
| ② HOUSING | : GLASSFILLED POLYESTER,
COLOR : BLACK |
| ③ CONTACTS | : PHOSPHORBRONZE
(PLATING : SEE TABLE ABOVE) |
| ④ FEMALE SCREWLOCK | : TINPLATED STEEL
(INNER THREAD 4-40 UNC OR M3) |
| ⑤ BUSHING | : TINPLATED STEEL (INNER THREAD 4-40
UNC OR M3 OR 3,1 DIA. THROUGH HOLE) |
| ⑥ BOARDLOCK | : TINPLATED PHOSPHORBRONZE |
| ⑦ STAND-OFF | : ULTRAMID V0
COLOR : BLACK |

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.V.LIEMPT 03JUL97 CHK C.SOUISA 09SEP97 APVD E.L.EWIFENS 09SEP97 PRODUCT SPEC — APPLICATION SPEC — WEIGHT —		 TE Connectivity HDP-20 SIZE 1 VERTICAL+ PLUG HEADER; WITH SOLDER CONTACTS	
DIMENSIONS: mm 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		NAME SIZE A2 CAGE CODE 00779 DRAWING NO C-338309 RESTRICTED TO —	
MATERIAL —		FINISH —		SCALE NTS SHEET 1 of 1 REV F2	
CUSTOMER DRAWING					