




2008/05/21 E Revise Molding Shape TOM

REVISIONS

DATE	LTR	DESCRIPTION	APVD
2008/01/03	A	New Drawing.	TOM
2008/01/17	B	Add specifications	
2008/04/08	C	Revise Item&Part NO. &Add 15M	TOM
2008/05/16	D	Revise Part NO.	TOM



Note:

- 1.HDMI-19P Mould NO:DM¹-H1011.
- 2.HDMI-19P After PRE-Mold Wrapped Copper Foil.
- 3.RO=RoHS.

specifications:

- 1.bandwidth up to 5 Gbps
- 2.10,000 Cycles
- 3.Gold-plated contacts
- 4.Lead-Free plating
- 5.Tray and embossed packaging
- 6.Current: 0.5A
- 7.Voltage:40V

Pin out		Pin out	
P1	P2	P1	P2
3 White	3	12 White	12
1 Brown	1	10 Blue	10
2 Drain wire	2	11 Drain wire	11
6 White	6	13 Red	13
4 Green	4	14 Pink	14
5 Drain wire	5	15 Gray	15
9 White	9	16 White	16
7 Red	7	17 Yellow	17
8 Drain wire	8	18 Orange	18
		19 Violet	19
		Shell Braid Shell	

Table:

PART NO	ITEM NO	LENGTH
489-399	P-A6C068-5-AL10M	10000±100
489-400	P-A6C068-5-AL15M	15000±150

RoHS

9	GC330030	Stick	Tin Stick-RO
8	NA360030	Paper Tape	Paper Tape.Single Side With Adhesive.W12*L60mm-RO
7	GC300160	Copper Foi	Copper Foil.W30*L60mm-RO
6	JA860380	H.S.T	Black Heat Shrink Tube-RO.ø2.5*L8mm
5	J1190010	PE	Transparent PE-RO
4	JB513960	PVC	PVC 45P-RO Black(T-000)
3	GC340080	Tin	OD:0.6mm-RO
2	1J280210	Conn.	HDMI-19PSGS4-K-A-RO W/PCB Shell Plated Nickel.Contact Gold Plated 15u"
1	LF090080	Cable	UL20276 (1P#24+AL+D+MYLAR)*4C+1P#24+5C#24-RO+AL+B OD9.5 Black(T-000)
No	Part No	Title	Description

UNLESS OTHERWISE SPECIFIED

TOLERANCE :
X. ±0.2 ANGLES : ±2°
X.X ±0.1
X.XX ±0.05 DO NOT SCALE DRAWING

DRAWN BY		TITLE		OEM CABLE ASSEMBLY		C3110	
CHECKED BY		SIZE A	UNIT MM	PART NO.	489-XXX	REV.	E
APPROVED BY		SCALE		THIRD ANGLE PROJECTION		PAGE	1 OF 1
DWG NO.	G489-XXX			ITEM NO.	P-A6C068-5-ALXXM	DATE	05/21/2008